

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331383-927

Luminaire Tested: **SA2XXDIP-C865D330U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331383-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D330U927-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3795.5 lumens
Efficiency: N/A
Efficacy: 87.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 43.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331383-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331383-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	87	87	87	78	78	78	73
1	103	99	94	91	98	94	90	87	85	82	79	76	74	72	69	67	66	62
2	94	86	80	74	89	82	76	71	74	70	66	67	63	60	60	58	55	52
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	54	50	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	41	38
5	72	60	52	45	68	57	50	44	52	46	41	48	42	38	43	39	35	33
6	67	54	46	39	63	52	44	38	47	41	36	43	38	34	39	35	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	45	36	31	54	43	35	30	39	33	28	36	31	27	33	28	25	23
9	54	41	33	28	51	39	32	27	36	30	26	33	28	24	30	26	23	21
10	50	38	30	25	48	36	29	24	33	27	23	31	26	22	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17651	17651	17651
5°	17718	17462	17566
10°	17613	17285	17372
15°	17396	17061	17043
20°	17086	16725	16706
25°	16778	16311	16311
30°	16384	15933	15795
35°	16015	15477	15248
40°	15553	15022	14733
45°	15098	14570	14209
50°	14601	14099	13599
55°	14083	13551	13050
60°	13511	12897	12426
65°	12894	12248	11687
70°	12109	11462	10914
75°	11017	10555	10293
80°	9772	9484	8991
85°	7984	7595	6817



TEST NUMBER: P331383-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.8	2.7
10°-20°	289.3	7.6
20°-30°	425.2	11.2
30°-40°	493.9	13.0
40°-50°	493.3	13.0
50°-60°	430.2	11.3
60°-70°	318.1	8.4
70°-80°	180.2	4.7
80°-90°	49.8	1.3
90°-100°	58.2	1.5
100°-110°	197.5	5.2
110°-120°	209.8	5.5
120°-130°	172.7	4.6
130°-140°	138.7	3.7
140°-150°	104.8	2.8
150°-160°	73.7	1.9
160°-170°	43.4	1.1
170°-180°	14.1	0.4
0°-30°	817.2	21.5
0°-40°	1311.1	34.5
0°-60°	2234.6	58.9
0°-90°	2782.6	73.3
90°-120°	465.5	12.3
90°-150°	881.7	23.2
90°-180°	1013.0	26.7
0°-180°	3795.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1093	1093	1093	1093	1093	
5°	1093	1089	1077	1085	1084	104
15°	1041	1034	1021	1024	1020	293
25°	942	933	916	917	916	433
35°	812	802	785	779	774	507
45°	661	653	638	627	622	510
55°	500	494	481	469	464	447
65°	338	331	321	311	306	334
75°	177	174	169	163	165	189
85°	43	42	41	38	37	49
90°	0	4	10	9	9	3
95°	10	24	110	41	32	10
105°	34	52	207	371	315	36
115°	60	76	174	358	415	60
125°	84	99	167	290	337	75
135°	98	118	165	244	279	76
145°	112	129	164	204	223	71
155°	128	138	159	180	187	59
165°	139	144	153	162	164	39
175°	145	145	147	148	148	14
180°	146	146	146	146	146	



TEST NUMBER: P331383-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2
2.5°	1098.3	1097.3	1096.4	1095.5	1094.6	1093.1	1091.0	1088.9	1086.9	1084.8	1086.7
5°	1093.2	1092.3	1091.4	1090.4	1089.5	1087.7	1085.2	1082.6	1080.1	1077.4	1079.3
7.5°	1083.5	1082.1	1080.7	1079.2	1077.8	1075.7	1073.1	1070.5	1067.9	1065.2	1067.1
10°	1074.3	1072.7	1071.0	1069.4	1067.8	1065.6	1062.7	1059.9	1057.2	1054.3	1056.2
12.5°	1061.7	1060.3	1058.8	1057.3	1055.9	1053.8	1051.0	1048.1	1045.4	1042.6	1043.9
15°	1040.7	1039.3	1037.8	1036.5	1035.1	1032.8	1029.8	1026.7	1023.7	1020.7	1021.6
17.5°	1013.8	1012.3	1011.0	1009.6	1008.1	1005.9	1002.8	999.7	996.6	993.6	994.7
20°	994.4	993.0	991.7	990.2	988.8	986.5	983.2	979.9	976.7	973.4	974.1
22.5°	975.1	973.1	971.1	969.2	967.3	964.7	961.6	958.5	955.5	952.4	952.5
25°	941.8	940.0	938.1	936.3	934.4	931.4	927.5	923.5	919.6	915.6	916.1
27.5°	904.0	902.4	900.6	899.0	897.3	894.8	891.8	888.6	885.5	882.3	881.7
30°	878.8	876.9	875.0	873.2	871.3	868.6	865.1	861.7	858.1	854.6	853.9
32.5°	851.9	850.4	848.9	847.4	845.9	843.3	839.6	835.9	832.3	828.5	827.3
35°	812.5	810.2	807.9	805.6	803.2	800.2	796.5	792.7	788.9	785.2	783.9
37.5°	768.2	766.1	764.1	762.0	760.0	757.1	753.4	749.6	745.8	742.1	740.4
40°	737.9	736.1	734.2	732.3	730.5	727.6	723.9	720.2	716.4	712.7	710.6
42.5°	708.5	706.6	704.7	702.9	701.0	698.2	694.5	690.8	687.0	683.3	681.0
45°	661.2	659.6	657.9	656.3	654.7	652.0	648.6	645.1	641.6	638.1	635.5
47.5°	614.1	612.6	611.0	609.5	607.9	605.3	601.7	598.0	594.4	590.7	588.0
50°	581.3	580.1	579.0	577.8	576.6	574.4	571.2	567.8	564.6	561.3	558.1
52.5°	549.4	547.8	546.3	544.7	543.2	540.9	537.8	534.7	531.6	528.5	525.9
55°	500.3	499.0	497.6	496.1	494.7	492.7	489.9	487.0	484.3	481.4	478.6
57.5°	451.1	450.0	448.9	447.8	446.7	444.6	441.5	438.4	435.3	432.2	429.5
60°	418.4	417.4	416.5	415.6	414.6	412.6	409.2	406.0	402.7	399.4	396.9
62.5°	386.4	384.9	383.4	381.9	380.4	378.4	375.9	373.4	370.8	368.4	366.0
65°	337.5	336.0	334.6	333.2	331.8	329.9	327.6	325.3	323.0	320.6	318.5
67.5°	287.6	286.5	285.3	284.2	283.1	281.5	279.4	277.3	275.2	273.1	271.5
70°	256.5	255.6	254.6	253.7	252.8	251.2	249.1	247.0	244.9	242.8	241.2
72.5°	224.5	223.6	222.7	221.7	220.8	219.7	218.3	217.0	215.6	214.2	212.6
75°	176.6	176.1	175.6	175.2	174.8	173.9	172.8	171.6	170.4	169.2	167.9
77.5°	133.7	132.9	132.1	131.3	130.6	129.9	129.4	129.0	128.5	128.0	127.3
80°	105.1	104.9	104.6	104.4	104.2	103.9	103.4	102.9	102.4	102.0	101.2
82.5°	78.2	78.2	78.1	78.0	78.0	77.9	77.6	77.3	77.0	76.8	75.8
85°	43.1	42.9	42.6	42.4	42.1	41.9	41.7	41.4	41.2	41.0	40.3
87.5°	15.2	15.0	14.8	14.6	14.3	14.1	14.0	14.0	14.0	13.7	13.1
90°	0.3	1.1	2.2	2.8	3.3	4.2	5.6	7.5	9.3	9.5	9.3
92.5°	3.4	4.9	7.0	8.2	10.1	12.7	19.0	28.0	35.9	36.4	30.7
95°	9.8	10.9	13.7	16.2	20.7	27.4	40.3	64.6	97.1	109.7	96.0
97.5°	15.9	17.4	20.4	24.2	29.4	37.0	53.2	87.1	141.1	187.3	196.5
100°	21.5	22.4	24.9	29.4	35.0	42.9	57.7	91.8	152.3	221.1	261.4
102.5°	26.7	27.3	29.9	34.3	40.2	48.0	61.7	92.1	148.0	222.2	285.6
105°	34.1	35.3	37.2	41.4	47.6	55.5	68.6	93.5	139.7	207.4	281.9
107.5°	42.2	43.1	45.0	48.9	55.0	62.9	75.7	97.4	135.5	191.5	257.3
110°	47.6	48.7	50.4	54.0	59.9	68.0	80.3	100.4	134.7	183.9	241.9



TEST NUMBER: P331383-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	52.5	53.6	55.5	58.9	64.6	73.0	84.8	103.9	134.8	179.0	231.1
115°	60.2	61.6	63.3	66.6	72.2	79.8	91.8	108.8	136.0	173.6	217.8
117.5°	68.1	69.2	70.9	73.9	79.3	87.1	98.2	114.2	138.1	170.9	209.4
120°	73.0	74.1	75.9	78.3	84.0	91.8	102.7	117.9	139.4	169.4	204.9
122.5°	77.8	78.7	80.3	83.1	88.6	96.7	106.9	121.0	140.9	168.4	201.1
125°	84.0	84.8	86.5	89.8	95.5	103.3	113.4	126.0	143.3	166.8	195.7
127.5°	88.9	90.0	92.4	96.1	101.4	109.5	119.3	130.6	145.7	165.9	190.6
130°	91.8	92.9	95.7	99.7	105.3	113.0	122.9	133.5	147.5	165.4	187.3
132.5°	94.5	95.9	98.9	103.0	108.8	116.7	126.0	136.4	149.3	165.2	184.6
135°	98.5	99.7	103.0	107.2	113.7	121.4	130.5	140.2	151.5	164.9	180.8
137.5°	102.3	103.7	107.0	111.5	117.9	125.2	134.0	143.1	153.4	164.8	178.2
140°	105.3	106.4	109.7	114.2	120.3	127.6	136.0	144.7	154.2	164.6	176.6
142.5°	108.1	109.1	112.2	116.7	122.6	129.4	137.6	146.1	154.9	164.6	175.1
145°	112.5	113.7	116.5	120.6	126.3	132.4	140.0	147.8	155.6	164.0	173.0
147.5°	117.2	118.0	120.7	124.6	129.3	134.8	141.9	148.8	155.8	163.0	170.9
150°	120.3	121.2	123.4	127.1	131.3	136.3	142.8	149.2	155.6	162.3	169.1
152.5°	123.5	123.9	126.1	129.3	133.3	137.8	143.6	149.4	155.2	161.2	167.5
155°	127.9	128.2	129.8	132.9	136.0	140.2	145.0	149.7	154.5	159.2	164.6
157.5°	131.6	131.9	133.2	135.9	138.4	141.9	145.9	149.7	153.2	157.2	161.8
160°	134.0	134.4	135.5	137.7	140.0	143.1	146.4	149.7	152.6	155.9	159.8
162.5°	136.6	136.3	137.5	139.3	141.3	143.7	146.6	149.5	151.9	154.8	158.0
165°	139.4	139.1	139.7	141.3	142.8	144.4	146.9	148.9	150.6	152.6	155.0
167.5°	141.7	141.4	141.9	143.0	144.0	145.0	146.9	148.5	149.3	150.6	152.2
170°	143.3	142.8	143.1	143.9	144.4	145.3	146.6	148.1	148.6	149.5	150.6
172.5°	144.2	143.9	143.7	144.6	144.9	145.5	146.5	147.4	147.7	148.1	149.0
175°	145.3	145.0	144.7	145.3	145.3	145.5	146.1	146.6	146.4	146.6	146.9
177.5°	145.8	145.3	145.1	145.5	145.5	145.5	145.8	146.2	145.8	145.5	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331383-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2	1093.2
2.5°	1088.5	1090.4	1092.3	1093.1	1092.7	1092.3	1091.9	1091.5
5°	1081.2	1083.1	1085.0	1085.6	1085.2	1084.7	1084.3	1083.8
7.5°	1069.0	1070.9	1072.8	1073.4	1072.9	1072.4	1071.9	1071.3
10°	1058.0	1059.9	1061.8	1062.4	1061.7	1061.0	1060.3	1059.6
12.5°	1045.2	1046.5	1047.8	1048.2	1047.7	1047.2	1046.6	1046.2
15°	1022.5	1023.5	1024.5	1024.3	1023.2	1022.0	1020.8	1019.6
17.5°	995.7	996.8	997.9	997.8	996.7	995.6	994.5	993.4
20°	974.8	975.5	976.2	976.0	975.2	974.2	973.3	972.3
22.5°	952.7	952.8	952.9	952.8	952.1	951.6	951.0	950.5
25°	916.6	917.0	917.4	917.4	917.0	916.6	916.1	915.6
27.5°	881.0	880.3	879.6	878.7	877.5	876.4	875.3	874.2
30°	853.2	852.5	851.8	851.0	850.1	849.1	848.2	847.2
32.5°	826.0	824.7	823.5	822.4	821.5	820.5	819.6	818.6
35°	782.4	781.0	779.7	778.3	777.2	776.0	774.8	773.6
37.5°	738.7	737.0	735.2	733.8	732.7	731.6	730.5	729.3
40°	708.5	706.4	704.3	702.7	701.9	700.9	700.0	699.0
42.5°	678.7	676.4	674.1	672.3	671.0	669.7	668.4	667.1
45°	633.0	630.3	627.8	626.1	625.1	624.2	623.2	622.3
47.5°	585.3	582.7	580.0	577.9	576.6	575.2	573.9	572.5
50°	554.8	551.5	548.3	546.1	544.9	543.7	542.6	541.4
52.5°	523.1	520.4	517.7	515.6	514.0	512.5	511.0	509.4
55°	475.9	473.0	470.2	468.3	467.1	465.9	464.8	463.6
57.5°	426.7	424.0	421.2	419.4	418.5	417.6	416.8	415.8
60°	394.3	391.7	389.2	387.5	386.8	386.1	385.4	384.8
62.5°	363.5	361.2	358.8	357.2	356.2	355.4	354.5	353.6
65°	316.4	314.3	312.2	310.5	309.4	308.2	307.0	305.9
67.5°	269.8	268.2	266.6	265.3	264.4	263.4	262.4	261.5
70°	239.6	237.9	236.3	235.0	234.1	233.1	232.2	231.2
72.5°	211.0	209.3	207.7	206.5	205.7	205.0	204.2	203.5
75°	166.4	165.0	163.7	163.2	163.7	164.1	164.5	165.0
77.5°	126.7	126.0	125.2	124.5	123.9	123.3	122.6	121.9
80°	100.5	99.9	99.2	98.5	98.1	97.7	97.2	96.7
82.5°	74.9	74.1	73.2	72.7	72.6	72.5	72.4	72.3
85°	39.6	38.9	38.2	37.7	37.5	37.2	37.0	36.8
87.5°	12.4	11.8	11.3	11.0	10.9	10.6	10.5	10.2
90°	9.0	8.4	9.0	9.3	9.3	9.3	9.3	9.3
92.5°	24.4	20.9	18.6	16.9	16.6	15.8	15.9	15.5
95°	73.4	56.2	44.5	38.3	34.7	32.5	31.6	31.9
97.5°	171.1	140.0	109.7	89.5	76.1	69.2	65.2	62.8
100°	255.6	220.9	182.5	148.6	125.4	113.4	105.3	100.2
102.5°	310.9	303.0	275.0	239.1	213.8	193.3	183.2	176.3
105°	340.1	371.7	375.3	366.1	348.7	331.4	319.3	315.4
107.5°	319.0	366.7	395.8	409.3	411.5	410.6	408.1	403.0
110°	300.9	351.0	386.8	409.8	421.8	427.1	429.7	429.4



TEST NUMBER: P331383-927

CATALOG NUMBER: SA2XXDIP-C865D330U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	284.3	332.4	370.7	397.0	413.8	422.6	427.4	428.9
115°	264.0	307.0	343.7	372.6	392.4	405.3	412.6	415.1
117.5°	248.6	286.5	319.7	346.7	367.0	380.6	388.2	390.4
120°	241.0	275.7	305.4	330.8	350.5	363.6	371.7	374.5
122.5°	235.0	266.7	294.9	317.8	335.4	348.4	355.6	357.9
125°	226.2	255.0	279.6	300.6	316.9	327.5	334.5	336.8
127.5°	217.5	243.6	266.8	286.1	300.3	310.3	316.3	318.1
130°	211.9	236.0	258.1	276.6	290.3	299.8	305.4	307.6
132.5°	206.5	228.8	249.1	266.5	280.0	289.5	294.6	296.7
135°	199.0	217.5	236.0	251.6	263.6	272.9	278.0	279.1
137.5°	193.1	208.5	223.2	236.8	247.8	255.7	260.2	261.8
140°	189.2	202.6	215.6	227.8	236.8	244.1	248.3	249.9
142.5°	186.1	197.5	208.6	218.9	227.4	234.0	237.7	238.1
145°	181.6	190.9	199.6	207.7	214.4	219.2	222.0	222.8
147.5°	178.2	185.5	192.3	198.2	203.7	207.6	209.5	210.0
150°	175.8	182.0	187.8	192.8	197.0	200.4	202.1	202.4
152.5°	173.3	179.0	184.0	188.4	191.7	194.6	195.8	195.9
155°	169.9	174.4	178.6	181.6	184.7	186.7	187.8	187.3
157.5°	166.0	169.7	173.2	175.6	177.8	179.4	179.9	179.9
160°	163.4	166.5	169.6	171.6	173.6	174.9	175.2	175.2
162.5°	161.0	163.7	166.3	167.8	169.8	170.7	171.0	170.7
165°	157.3	159.2	161.2	162.3	163.4	164.6	164.6	164.3
167.5°	153.8	155.3	156.6	157.6	158.1	158.8	158.7	158.4
170°	152.0	152.8	153.9	154.5	154.8	155.6	155.3	154.8
172.5°	150.0	150.6	151.5	151.8	152.1	152.5	152.2	151.9
175°	147.8	148.1	148.4	148.6	148.6	148.9	148.6	148.1
177.5°	146.2	146.2	146.5	146.5	146.5	146.5	146.2	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5

(END OF REPORT)