

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331323

Luminaire Tested: **SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331323  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6352.8 lumens  
Efficiency: N/A  
Efficacy: 128.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 49.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331323  
CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	94	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	35	29				
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	32	30	25				
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	29	28	26	21				
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	26	24	23	19				
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16				
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18	15				
7	57	45	37	32	51	41	34	30	33	29	25	27	23	20	20	18	16	13				
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	18	16	14	12				
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11				
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	15689	15689	15689	15689
5°	17590	15793	13994	15793
10°	20156	15662	12111	15662
15°	22298	15375	10700	15375
20°	21959	15067	9754	15067
25°	19800	14656	9155	14656
30°	16362	14001	8718	14001
35°	11925	13316	8406	13316
40°	9525	12507	8233	12507
45°	8323	11572	7999	11572
50°	7824	10665	7842	10665
55°	7212	9745	7631	9745
60°	6610	8767	7308	8767
65°	6021	7889	6991	7889
70°	5467	7034	6524	7034
75°	4847	6082	5777	6082
80°	4166	5040	4649	5040
85°	3742	3742	2760	3742



TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	92.5	1.5
10°-20°	269.0	4.2
20°-30°	390.5	6.1
30°-40°	412.0	6.5
40°-50°	364.8	5.7
50°-60°	291.1	4.6
60°-70°	197.9	3.1
70°-80°	101.5	1.6
80°-90°	29.9	0.5
90°-100°	241.5	3.8
100°-110°	819.6	12.9
110°-120°	870.7	13.7
120°-130°	716.8	11.3
130°-140°	575.6	9.1
140°-150°	435.0	6.8
150°-160°	305.7	4.8
160°-170°	180.0	2.8
170°-180°	58.6	0.9
0°-30°	752.0	11.8
0°-40°	1164.1	18.3
0°-60°	1820.1	28.6
0°-90°	2149.3	33.8
90°-120°	1931.9	30.4
90°-150°	3659.3	57.6
90°-180°	4204.0	66.2
0°-180°	6352.8	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	972	972	972	972	972	
5°	1085	974	863	974	1085	108
15°	1334	920	640	920	1334	368
25°	1111	823	514	823	1111	502
35°	605	676	426	676	605	393
45°	364	507	350	507	364	287
55°	256	346	271	346	256	230
65°	158	206	183	206	158	157
75°	78	98	93	98	78	83
85°	20	20	15	20	20	23
90°	38	1	38	1	38	21
95°	132	41	132	41	132	172
105°	1309	142	1309	142	1309	1267
115°	1723	250	1723	250	1723	1687
125°	1398	348	1398	348	1398	1263
135°	1158	409	1158	409	1158	900
145°	925	467	925	467	925	587
155°	777	531	777	531	777	363
165°	682	578	682	578	682	195
175°	614	603	614	603	614	60
180°	604	604	604	604	604	



TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1016.6	1016.9	1017.4	1012.7	1012.1	1012.1	1007.9	1004.3	1000.1	994.4	995.0
5°	1085.3	1089.4	1090.9	1086.4	1079.7	1078.9	1072.6	1062.1	1052.4	1044.6	1039.0
7.5°	1167.3	1168.9	1165.3	1159.4	1154.4	1145.4	1133.6	1122.0	1105.8	1090.9	1079.9
10°	1229.4	1231.7	1225.3	1216.7	1209.6	1199.2	1182.0	1164.4	1143.2	1122.6	1106.2
12.5°	1276.6	1282.2	1274.0	1272.9	1260.7	1246.4	1225.9	1217.0	1187.1	1158.5	1140.8
15°	1334.0	1333.6	1334.4	1327.3	1318.3	1316.1	1294.4	1270.9	1228.7	1211.9	1182.7
17.5°	1317.4	1323.1	1325.7	1325.6	1325.4	1324.0	1317.0	1302.2	1281.0	1253.8	1220.2
20°	1278.0	1285.4	1286.6	1295.2	1300.0	1306.4	1309.0	1304.9	1291.8	1269.0	1239.9
22.5°	1217.0	1219.1	1222.6	1236.0	1246.5	1262.4	1270.7	1284.5	1279.5	1268.4	1244.1
25°	1111.4	1107.7	1120.7	1127.5	1151.7	1177.1	1195.4	1215.6	1233.5	1244.4	1237.3
27.5°	984.6	979.0	998.6	1016.4	1036.1	1063.6	1092.1	1125.8	1153.8	1188.9	1200.9
30°	877.6	881.0	899.7	918.7	948.6	987.4	1019.5	1056.5	1096.5	1135.7	1162.9
32.5°	762.3	775.2	787.0	816.2	842.5	885.8	932.9	979.1	1029.0	1073.5	1115.7
35°	605.0	619.9	636.4	657.7	694.6	737.6	783.5	845.9	913.9	974.7	1024.8
37.5°	509.2	506.9	516.3	531.7	561.6	596.3	649.1	710.8	790.8	862.3	932.9
40°	451.9	450.4	457.1	471.3	494.1	519.5	565.8	619.9	694.3	781.6	865.7
42.5°	412.4	413.3	417.1	427.1	442.7	463.6	498.3	544.4	612.4	694.7	785.0
45°	364.5	367.1	371.2	376.1	385.0	402.2	421.6	454.5	508.3	577.0	665.9
47.5°	330.0	330.1	334.2	338.5	343.8	353.5	369.4	390.0	427.9	483.9	560.3
50°	311.5	308.8	311.8	315.2	320.8	327.5	338.0	357.4	382.8	428.0	491.8
52.5°	288.8	288.8	291.5	292.8	297.8	304.5	314.1	327.5	350.5	385.9	438.4
55°	256.2	258.1	259.6	261.8	266.3	271.1	278.6	287.6	305.5	332.0	370.8
57.5°	225.6	226.2	227.7	231.9	234.8	239.2	246.3	254.5	266.1	285.8	315.0
60°	204.7	204.7	207.6	209.5	213.2	217.7	223.3	231.2	241.6	257.7	281.2
62.5°	185.5	185.2	186.4	189.5	192.3	196.5	202.1	208.8	218.6	232.9	252.2
65°	157.6	156.9	159.1	159.8	162.8	166.9	171.4	178.5	186.4	196.8	214.0
67.5°	130.7	131.6	132.8	134.2	135.9	140.2	143.2	148.2	154.8	163.5	175.2
70°	115.8	115.8	115.8	116.9	119.1	121.4	124.4	128.5	134.8	142.3	152.7
72.5°	99.0	100.2	101.4	100.8	103.6	104.9	108.5	110.8	116.9	121.7	130.9
75°	77.7	77.7	77.7	79.5	80.7	81.8	84.0	86.3	89.3	95.2	100.1
77.5°	58.0	57.8	58.2	58.6	59.8	61.2	61.8	63.9	66.6	69.4	73.5
80°	44.8	45.6	45.9	46.7	46.7	47.4	47.8	50.4	52.3	54.2	56.8
82.5°	34.7	34.8	34.9	35.0	35.3	35.8	36.7	37.6	38.2	39.8	41.8
85°	20.2	19.8	19.8	20.5	20.2	20.2	20.9	21.7	21.7	22.0	23.2
87.5°	15.4	15.4	15.7	15.4	15.4	15.5	15.0	15.2	15.7	16.3	16.3
90°	38.3	38.3	38.3	38.3	38.3	37.2	34.9	37.2	38.3	39.5	38.3
92.5°	64.4	66.2	65.3	69.0	69.9	77.1	86.9	101.3	127.6	151.0	148.9
95°	132.4	131.3	134.8	144.0	159.1	184.7	233.5	304.4	398.5	455.4	403.1
97.5°	260.7	270.4	287.4	316.0	371.5	455.4	581.1	710.2	815.5	777.4	585.5
100°	415.9	436.8	470.5	520.4	616.8	757.4	916.6	1060.6	1085.0	917.7	631.9
102.5°	731.9	760.2	802.3	887.5	992.3	1141.2	1257.6	1290.2	1185.4	922.4	614.3
105°	1309.2	1325.5	1375.4	1447.4	1519.5	1557.8	1542.7	1411.4	1169.8	860.8	579.7
107.5°	1672.3	1693.9	1703.9	1707.9	1698.8	1642.6	1521.8	1324.1	1067.8	794.8	562.5
110°	1782.0	1783.2	1772.7	1750.6	1700.7	1605.4	1456.7	1248.8	1003.7	763.2	558.8



TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1780.1	1773.9	1754.1	1717.2	1647.7	1538.5	1379.6	1180.0	959.1	742.8	559.7
115°	1722.8	1712.3	1682.1	1628.7	1546.2	1426.5	1274.4	1095.5	903.8	720.2	564.6
117.5°	1620.3	1611.5	1579.6	1523.2	1439.1	1326.9	1188.9	1031.8	868.9	709.3	572.9
120°	1554.3	1542.7	1509.0	1454.4	1373.1	1267.4	1144.2	1000.2	850.3	702.8	578.5
122.5°	1485.5	1475.8	1445.8	1392.1	1319.2	1223.7	1107.1	975.1	834.5	699.1	585.0
125°	1397.5	1388.2	1359.2	1315.0	1247.6	1160.5	1058.3	938.6	812.0	692.4	594.8
127.5°	1320.4	1312.9	1287.8	1246.5	1187.7	1107.3	1010.9	902.6	791.1	688.4	604.8
130°	1276.7	1267.4	1244.2	1204.7	1147.7	1071.1	979.3	879.4	777.2	686.5	612.2
132.5°	1231.1	1222.8	1201.4	1161.9	1105.9	1033.9	949.6	857.1	766.0	685.6	619.6
135°	1158.2	1153.5	1132.6	1094.3	1044.3	979.3	902.6	825.9	750.4	684.2	628.5
137.5°	1086.6	1079.7	1061.3	1028.3	982.8	926.1	865.2	801.1	739.5	684.0	636.4
140°	1037.4	1030.4	1013.0	982.8	945.6	894.5	841.1	785.3	733.0	683.1	640.1
142.5°	988.1	986.7	971.2	943.7	908.4	865.7	819.7	772.3	726.5	683.1	642.9
145°	924.7	921.2	909.6	889.8	862.0	828.3	792.3	753.9	717.9	680.7	645.9
147.5°	871.5	869.4	861.5	845.7	822.7	798.1	770.0	739.8	709.1	676.6	646.8
150°	839.9	838.7	831.8	817.8	800.4	779.5	755.1	729.5	701.6	673.8	645.9
152.5°	812.9	812.7	807.6	795.5	781.8	763.7	743.0	719.3	695.1	669.1	644.0
155°	777.2	779.5	774.8	766.7	753.9	741.1	723.7	705.1	683.1	661.0	641.2
157.5°	746.7	746.7	744.6	737.9	728.8	718.8	704.2	688.6	671.7	652.6	635.9
160°	727.2	727.2	726.0	720.2	712.1	704.0	691.2	678.4	663.3	647.1	633.1
162.5°	708.6	709.5	708.4	704.4	696.3	690.0	679.1	668.2	655.9	642.4	630.3
165°	681.9	683.1	683.1	678.4	673.8	669.1	661.0	652.9	643.6	633.1	625.0
167.5°	657.3	658.7	658.9	656.3	654.3	650.1	644.5	638.2	631.5	625.0	619.6
170°	642.4	644.7	645.9	642.4	641.2	638.9	634.3	630.8	625.0	620.3	616.8
172.5°	630.3	631.7	632.9	631.3	630.1	628.7	625.0	622.4	618.5	614.8	613.1
175°	614.5	616.8	618.0	616.8	616.8	615.7	614.5	613.4	609.9	608.7	607.6
177.5°	605.0	606.9	607.8	607.8	607.8	607.8	606.9	606.9	605.0	604.1	605.0
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1



TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	997.1	994.7	993.2	987.9	983.1	978.3	976.8	977.4	970.8	964.6	961.9
5°	1036.0	1028.5	1021.4	1011.3	999.4	986.3	979.6	974.4	961.3	947.1	938.9
7.5°	1070.8	1060.1	1046.4	1027.5	1010.1	989.5	976.4	964.9	945.7	925.7	913.5
10°	1092.0	1077.4	1059.9	1036.7	1015.4	990.4	972.9	955.3	932.9	909.0	894.1
12.5°	1110.2	1090.6	1073.3	1043.6	1018.4	987.1	966.3	941.6	918.0	889.6	874.9
15°	1153.6	1117.4	1084.5	1050.9	1019.9	976.2	953.1	919.8	888.8	853.7	836.9
17.5°	1187.1	1146.4	1094.7	1052.0	1015.8	967.4	933.4	893.6	856.9	816.8	794.0
20°	1206.3	1159.6	1103.9	1053.2	1009.8	954.6	917.6	876.9	833.9	788.7	764.1
22.5°	1217.6	1168.6	1113.5	1048.7	997.9	944.1	897.6	853.0	809.4	760.7	734.8
25°	1221.2	1176.4	1118.1	1044.9	982.9	922.1	866.0	822.7	770.1	724.5	686.8
27.5°	1203.4	1171.3	1115.3	1037.9	965.7	894.5	832.1	783.0	727.4	678.0	640.0
30°	1181.6	1162.9	1108.4	1030.7	951.9	875.4	806.7	751.0	695.8	645.7	606.9
32.5°	1147.9	1143.8	1095.9	1020.6	937.3	851.2	780.1	723.8	662.6	613.4	576.4
35°	1081.5	1099.5	1069.2	997.9	909.7	816.8	739.8	675.6	612.1	565.0	530.3
37.5°	992.7	1037.2	1029.3	964.6	872.5	779.3	694.3	627.2	566.7	519.2	485.1
40°	931.4	988.2	996.4	939.2	846.3	750.3	660.3	593.4	534.4	491.1	456.7
42.5°	865.7	932.0	954.6	908.8	817.6	719.8	629.8	560.6	502.2	460.0	429.6
45°	755.5	843.3	884.0	857.8	769.7	669.6	577.0	506.8	453.8	414.2	390.6
47.5°	652.5	748.4	803.2	793.9	716.4	617.3	525.8	458.4	406.8	375.2	354.1
50°	579.6	678.2	744.3	747.3	678.2	580.0	488.1	424.6	377.2	347.7	330.5
52.5°	516.3	610.4	682.5	698.3	635.5	541.1	454.3	391.2	349.4	322.3	306.9
55°	433.6	513.1	593.1	622.2	571.8	482.1	401.8	346.2	307.0	288.3	274.9
57.5°	360.5	426.8	500.6	532.8	501.7	425.0	349.7	301.4	269.6	253.2	242.9
60°	321.9	374.2	439.9	478.4	451.5	383.2	317.4	271.5	245.4	230.8	221.1
62.5°	286.1	332.4	387.9	423.1	408.5	344.0	285.2	244.6	222.1	208.4	201.4
65°	236.0	272.6	315.6	348.1	338.4	289.4	241.3	206.5	188.6	177.8	172.2
67.5°	194.3	220.8	250.6	279.0	271.2	236.5	197.9	170.8	157.4	148.1	144.8
70°	168.1	188.2	214.7	237.5	231.2	202.8	172.2	149.0	137.4	129.6	126.2
72.5°	143.0	159.5	179.8	198.4	194.1	170.5	145.0	127.5	118.6	111.4	108.6
75°	107.9	120.6	133.0	145.3	144.2	125.9	110.9	97.5	90.4	84.8	83.7
77.5°	79.7	86.8	95.2	102.5	100.5	90.0	78.3	70.6	65.4	61.6	61.0
80°	60.9	65.0	71.0	76.2	73.6	69.1	59.8	54.2	50.4	46.7	45.2
82.5°	44.1	48.3	51.8	54.7	52.7	48.5	42.7	38.9	36.7	34.1	33.5
85°	23.2	25.4	26.9	27.6	26.9	24.3	21.7	20.2	18.3	17.2	16.8
87.5°	15.2	13.6	12.4	12.3	11.0	10.5	8.4	6.8	7.2	7.8	7.7
90°	31.4	23.2	17.4	13.9	11.6	9.3	4.6	1.2	4.6	9.3	11.6
92.5°	115.9	79.0	52.7	41.8	33.9	28.8	20.4	14.2	20.4	28.8	33.9
95°	268.3	167.3	113.8	86.0	67.4	56.9	45.3	40.7	45.3	56.9	67.4
97.5°	361.5	220.7	153.6	122.0	100.6	84.8	72.5	66.2	72.5	84.8	100.6
100°	381.0	239.3	177.7	145.2	122.0	103.4	92.9	89.4	92.9	103.4	122.0
102.5°	382.0	256.0	199.1	166.6	142.4	123.8	113.4	110.8	113.4	123.8	142.4
105°	388.0	284.6	230.0	197.5	171.9	154.5	146.4	141.7	146.4	154.5	171.9
107.5°	404.0	313.9	260.9	228.2	202.8	186.8	178.9	175.2	178.9	186.8	202.8
110°	417.0	333.4	282.3	248.6	224.2	209.1	202.1	197.5	202.1	209.1	224.2





TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	431.0	352.0	302.7	268.1	244.6	230.5	222.6	217.9	222.6	230.5	244.6
115°	451.9	381.0	331.1	299.7	276.5	262.5	255.6	249.8	255.6	262.5	276.5
117.5°	474.2	407.7	361.5	329.0	306.7	294.4	287.4	282.8	287.4	294.4	306.7
120°	489.1	426.3	381.0	348.5	325.3	314.8	307.8	303.2	307.8	314.8	325.3
122.5°	502.1	444.0	401.5	368.0	344.8	333.4	326.4	322.7	326.4	333.4	344.8
125°	522.8	470.5	428.7	396.1	372.9	359.0	352.0	348.5	352.0	359.0	372.9
127.5°	542.0	495.1	454.4	421.0	398.7	383.4	373.6	368.9	373.6	383.4	398.7
130°	554.1	510.0	469.3	436.8	413.6	397.3	385.7	381.0	385.7	397.3	413.6
132.5°	566.2	523.0	484.2	451.7	427.5	410.3	397.8	392.2	397.8	410.3	427.5
135°	582.0	541.3	504.2	471.6	444.9	427.5	413.6	408.9	413.6	427.5	444.9
137.5°	594.1	556.2	519.5	489.3	462.8	444.2	430.3	424.7	430.3	444.2	462.8
140°	600.6	564.6	529.7	499.5	474.0	455.4	441.4	436.8	441.4	455.4	474.0
142.5°	606.2	571.1	537.2	508.8	484.2	465.6	452.6	448.9	452.6	465.6	484.2
145°	613.4	580.8	549.5	523.9	500.7	483.3	471.6	467.0	471.6	483.3	500.7
147.5°	617.3	588.7	559.2	536.5	517.2	501.1	490.0	486.5	490.0	501.1	517.2
150°	619.2	592.5	565.7	544.8	527.4	512.3	503.0	499.5	503.0	512.3	527.4
152.5°	620.1	596.2	572.2	553.2	536.7	523.4	514.2	512.5	514.2	523.4	536.7
155°	621.5	601.7	582.0	564.6	551.8	539.0	532.0	530.9	532.0	539.0	551.8
157.5°	621.5	605.7	589.0	574.3	564.1	553.0	547.4	546.2	547.4	553.0	564.1
160°	621.5	607.6	593.6	580.8	571.5	562.2	557.6	556.4	557.6	562.2	571.5
162.5°	620.6	608.5	596.4	586.4	578.0	570.6	566.0	566.7	566.0	570.6	578.0
165°	618.0	609.9	599.4	592.5	586.6	579.7	577.4	578.5	577.4	579.7	586.6
167.5°	616.4	609.6	602.0	597.6	593.4	589.0	586.9	588.3	586.9	589.0	593.4
170°	614.5	608.7	602.9	599.4	597.1	593.6	592.5	594.8	592.5	593.6	597.1
172.5°	611.7	607.8	603.8	601.3	599.9	596.4	597.1	598.5	597.1	596.4	599.9
175°	608.7	606.4	604.1	602.9	602.9	600.6	601.7	602.9	601.7	600.6	602.9
177.5°	606.9	605.0	604.1	604.1	604.1	602.2	603.1	605.0	603.1	602.2	604.1
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1



TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	958.9	957.1	950.8	947.5	942.2	937.1	933.8	935.3	936.5	935.9	935.0
5°	931.4	924.3	913.5	904.1	897.4	885.1	879.9	877.3	875.0	872.4	869.8
7.5°	898.7	887.5	872.0	858.7	846.1	830.8	822.1	816.8	811.4	805.5	800.3
10°	875.4	859.7	843.3	824.6	809.7	795.8	783.5	775.3	767.8	760.7	755.5
12.5°	850.9	832.8	812.5	787.0	770.5	750.7	748.9	734.4	722.7	718.3	712.2
15°	811.9	786.5	760.7	730.5	717.4	699.5	688.3	677.1	667.0	659.9	658.0
17.5°	767.6	734.7	709.1	687.4	666.0	647.6	637.3	628.3	620.0	610.5	609.3
20°	733.8	705.5	677.5	658.4	636.4	617.7	605.0	596.0	588.9	583.3	578.5
22.5°	701.9	670.8	645.2	624.3	602.6	587.5	577.5	568.9	563.0	556.8	552.2
25°	650.6	626.3	598.3	574.8	556.8	547.1	538.9	531.4	527.7	523.6	518.4
27.5°	605.7	578.7	552.5	534.3	518.5	509.9	504.1	499.0	495.5	493.1	490.1
30°	574.0	546.7	526.2	508.3	495.2	486.6	482.9	479.9	475.8	474.3	472.8
32.5°	543.5	519.0	501.4	485.9	473.4	467.8	464.4	461.7	458.5	457.0	454.0
35°	500.4	479.9	462.7	454.1	444.0	439.2	436.6	432.8	429.9	428.4	428.0
37.5°	459.9	442.0	430.7	419.7	415.4	412.4	408.9	406.3	405.4	405.2	404.8
40°	433.6	419.0	408.9	400.0	398.1	393.6	390.6	388.4	388.4	388.8	388.4
42.5°	409.7	396.6	387.7	380.0	377.8	375.1	372.1	372.0	372.6	373.8	372.6
45°	373.5	364.1	357.8	354.0	349.9	347.3	346.9	348.1	348.4	348.8	349.9
47.5°	340.1	333.9	328.2	324.1	322.3	321.8	321.4	323.3	325.1	325.8	327.5
50°	320.4	313.3	308.5	305.9	304.4	303.6	304.4	306.6	308.1	310.0	311.1
52.5°	298.3	293.3	290.0	287.9	287.3	287.8	287.9	290.5	292.9	293.5	294.1
55°	267.8	264.0	263.3	259.9	261.4	261.0	262.9	264.4	266.6	268.9	269.3
57.5°	237.3	234.3	232.3	232.6	233.0	234.7	236.2	238.9	241.3	243.6	243.9
60°	217.0	215.5	214.4	214.4	215.1	217.4	219.2	221.8	223.3	224.8	225.9
62.5°	198.5	197.0	195.8	196.4	198.4	199.7	201.9	203.3	204.8	206.3	206.8
65°	169.2	168.4	169.6	170.3	170.7	172.5	175.2	176.3	177.8	178.5	181.1
67.5°	142.2	142.4	142.2	143.3	145.4	145.9	148.3	151.0	151.3	152.7	154.4
70°	124.0	124.7	125.5	126.2	128.1	128.8	130.7	131.8	133.3	134.4	135.6
72.5°	107.3	107.4	108.2	108.0	109.6	111.2	112.8	113.9	115.4	116.8	117.9
75°	82.5	82.5	83.3	83.7	85.5	87.4	87.0	87.8	89.3	90.8	91.5
77.5°	60.3	59.5	60.3	60.6	61.2	62.8	63.1	64.2	65.9	65.4	66.2
80°	45.9	44.8	45.9	46.3	46.3	48.2	48.2	48.9	50.0	48.9	50.0
82.5°	32.8	32.3	33.1	33.2	33.8	33.8	34.4	34.6	35.7	35.2	35.7
85°	16.4	16.1	16.4	16.1	16.4	16.8	16.8	16.4	16.4	17.2	16.1
87.5°	7.9	8.3	9.1	10.8	11.8	11.8	11.3	11.0	10.6	10.4	10.7
90°	13.9	17.4	23.2	31.4	38.3	39.5	38.3	37.2	34.9	37.2	38.3
92.5°	41.8	52.7	79.0	115.9	148.9	151.0	127.6	101.3	86.9	77.1	69.9
95°	86.0	113.8	167.3	268.3	403.1	455.4	398.5	304.4	233.5	184.7	159.1
97.5°	122.0	153.6	220.7	361.5	585.5	777.4	815.5	710.2	581.1	455.4	371.5
100°	145.2	177.7	239.3	381.0	631.9	917.7	1085.0	1060.6	916.6	757.4	616.8
102.5°	166.6	199.1	256.0	382.0	614.3	922.4	1185.4	1290.2	1257.6	1141.2	992.3
105°	197.5	230.0	284.6	388.0	579.7	860.8	1169.8	1411.4	1542.7	1557.8	1519.5
107.5°	228.2	260.9	313.9	404.0	562.5	794.8	1067.8	1324.1	1521.8	1642.6	1698.8
110°	248.6	282.3	333.4	417.0	558.8	763.2	1003.7	1248.8	1456.7	1605.4	1700.7



TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	268.1	302.7	352.0	431.0	559.7	742.8	959.1	1180.0	1379.6	1538.5	1647.7
115°	299.7	331.1	381.0	451.9	564.6	720.2	903.8	1095.5	1274.4	1426.5	1546.2
117.5°	329.0	361.5	407.7	474.2	572.9	709.3	868.9	1031.8	1188.9	1326.9	1439.1
120°	348.5	381.0	426.3	489.1	578.5	702.8	850.3	1000.2	1144.2	1267.4	1373.1
122.5°	368.0	401.5	444.0	502.1	585.0	699.1	834.5	975.1	1107.1	1223.7	1319.2
125°	396.1	428.7	470.5	522.8	594.8	692.4	812.0	938.6	1058.3	1160.5	1247.6
127.5°	421.0	454.4	495.1	542.0	604.8	688.4	791.1	902.6	1010.9	1107.3	1187.7
130°	436.8	469.3	510.0	554.1	612.2	686.5	777.2	879.4	979.3	1071.1	1147.7
132.5°	451.7	484.2	523.0	566.2	619.6	685.6	766.0	857.1	949.6	1033.9	1105.9
135°	471.6	504.2	541.3	582.0	628.5	684.2	750.4	825.9	902.6	979.3	1044.3
137.5°	489.3	519.5	556.2	594.1	636.4	684.0	739.5	801.1	865.2	926.1	982.8
140°	499.5	529.7	564.6	600.6	640.1	683.1	733.0	785.3	841.1	894.5	945.6
142.5°	508.8	537.2	571.1	606.2	642.9	683.1	726.5	772.3	819.7	865.7	908.4
145°	523.9	549.5	580.8	613.4	645.9	680.7	717.9	753.9	792.3	828.3	862.0
147.5°	536.5	559.2	588.7	617.3	646.8	676.6	709.1	739.8	770.0	798.1	822.7
150°	544.8	565.7	592.5	619.2	645.9	673.8	701.6	729.5	755.1	779.5	800.4
152.5°	553.2	572.2	596.2	620.1	644.0	669.1	695.1	719.3	743.0	763.7	781.8
155°	564.6	582.0	601.7	621.5	641.2	661.0	683.1	705.1	723.7	741.1	753.9
157.5°	574.3	589.0	605.7	621.5	635.9	652.6	671.7	688.6	704.2	718.8	728.8
160°	580.8	593.6	607.6	621.5	633.1	647.1	663.3	678.4	691.2	704.0	712.1
162.5°	586.4	596.4	608.5	620.6	630.3	642.4	655.9	668.2	679.1	690.0	696.3
165°	592.5	599.4	609.9	618.0	625.0	633.1	643.6	652.9	661.0	669.1	673.8
167.5°	597.6	602.0	609.6	616.4	619.6	625.0	631.5	638.2	644.5	650.1	654.3
170°	599.4	602.9	608.7	614.5	616.8	620.3	625.0	630.8	634.3	638.9	641.2
172.5°	601.3	603.8	607.8	611.7	613.1	614.8	618.5	622.4	625.0	628.7	630.1
175°	602.9	604.1	606.4	608.7	607.6	608.7	609.9	613.4	614.5	615.7	616.8
177.5°	604.1	604.1	605.0	606.9	605.0	604.1	605.0	606.9	606.9	607.8	607.8
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1



TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	932.0	931.4	931.4	928.7	931.4	931.4	932.0	935.0	935.9	936.5	935.3
5°	864.6	863.4	861.6	863.4	861.6	863.4	864.6	869.8	872.4	875.0	877.3
7.5°	797.9	793.4	792.7	788.3	792.7	793.4	797.9	800.3	805.5	811.4	816.8
10°	749.2	746.2	745.8	738.7	745.8	746.2	749.2	755.5	760.7	767.8	775.3
12.5°	712.1	704.9	706.4	702.3	706.4	704.9	712.1	712.2	718.3	722.7	734.4
15°	647.9	647.9	646.5	640.1	646.5	647.9	647.9	658.0	659.9	667.0	677.1
17.5°	601.9	601.1	597.5	599.3	597.5	601.1	601.9	609.3	610.5	620.0	628.3
20°	574.4	572.1	567.7	567.7	567.7	572.1	574.4	578.5	583.3	588.9	596.0
22.5°	548.4	548.2	543.5	545.0	543.5	548.2	548.4	552.2	556.8	563.0	568.9
25°	518.0	515.0	512.8	513.9	512.8	515.0	518.0	518.4	523.6	527.7	531.4
27.5°	489.2	487.5	487.4	484.3	487.4	487.5	489.2	490.1	493.1	495.5	499.0
30°	472.4	468.7	469.4	467.6	469.4	468.7	472.4	472.8	474.3	475.8	479.9
32.5°	453.3	452.0	451.2	449.6	451.2	452.0	453.3	454.0	457.0	458.5	461.7
35°	427.2	427.6	425.7	426.5	425.7	427.6	427.2	428.0	428.4	429.9	432.8
37.5°	404.5	405.7	404.8	405.0	404.8	405.7	404.5	404.8	405.2	405.4	406.3
40°	389.5	389.5	389.5	390.6	389.5	389.5	389.5	388.4	388.8	388.4	388.4
42.5°	375.2	374.6	374.0	373.9	374.0	374.6	375.2	372.6	373.8	372.6	372.0
45°	350.7	351.8	352.2	350.3	352.2	351.8	350.7	349.9	348.8	348.4	348.1
47.5°	328.5	328.6	328.5	330.1	328.5	328.6	328.5	327.5	325.8	325.1	323.3
50°	313.0	312.2	313.0	312.2	313.0	312.2	313.0	311.1	310.0	308.1	306.6
52.5°	296.5	296.7	296.2	296.1	296.2	296.7	296.5	294.1	293.5	292.9	290.5
55°	270.8	271.5	271.1	271.1	271.1	271.5	270.8	269.3	268.9	266.6	264.4
57.5°	244.1	244.8	245.3	243.6	245.3	244.8	244.1	243.9	243.6	241.3	238.9
60°	225.6	227.4	227.1	226.3	227.1	227.4	225.6	225.9	224.8	223.3	221.8
62.5°	208.5	209.2	209.1	209.0	209.1	209.2	208.5	206.8	206.3	204.8	203.3
65°	182.2	183.0	181.9	183.0	181.9	183.0	182.2	181.1	178.5	177.8	176.3
67.5°	153.9	154.2	155.0	155.5	155.0	154.2	153.9	154.4	152.7	151.3	151.0
70°	136.3	135.9	137.1	138.2	137.1	135.9	136.3	135.6	134.4	133.3	131.8
72.5°	117.8	118.6	118.2	119.1	118.2	118.6	117.8	117.9	116.8	115.4	113.9
75°	90.8	91.9	91.5	92.6	91.5	91.9	90.8	91.5	90.8	89.3	87.8
77.5°	65.6	65.7	65.6	66.2	65.6	65.7	65.6	66.2	65.4	65.9	64.2
80°	50.0	49.3	48.5	50.0	48.5	49.3	50.0	50.0	48.9	50.0	48.9
82.5°	34.8	35.3	34.5	34.5	34.5	35.3	34.8	35.7	35.2	35.7	34.6
85°	16.1	15.7	14.9	14.9	14.9	15.7	16.1	16.1	17.2	16.4	16.4
87.5°	10.7	10.4	10.4	10.1	10.4	10.4	10.7	10.7	10.4	10.6	11.0
90°	38.3	38.3	38.3	38.3	38.3	38.3	38.3	38.3	37.2	34.9	37.2
92.5°	69.0	65.3	66.2	64.4	66.2	65.3	69.0	69.9	77.1	86.9	101.3
95°	144.0	134.8	131.3	132.4	131.3	134.8	144.0	159.1	184.7	233.5	304.4
97.5°	316.0	287.4	270.4	260.7	270.4	287.4	316.0	371.5	455.4	581.1	710.2
100°	520.4	470.5	436.8	415.9	436.8	470.5	520.4	616.8	757.4	916.6	1060.6
102.5°	887.5	802.3	760.2	731.9	760.2	802.3	887.5	992.3	1141.2	1257.6	1290.2
105°	1447.4	1375.4	1325.5	1309.2	1325.5	1375.4	1447.4	1519.5	1557.8	1542.7	1411.4
107.5°	1707.9	1703.9	1693.9	1672.3	1693.9	1703.9	1707.9	1698.8	1642.6	1521.8	1324.1
110°	1750.6	1772.7	1783.2	1782.0	1783.2	1772.7	1750.6	1700.7	1605.4	1456.7	1248.8



TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1717.2	1754.1	1773.9	1780.1	1773.9	1754.1	1717.2	1647.7	1538.5	1379.6	1180.0
115°	1628.7	1682.1	1712.3	1722.8	1712.3	1682.1	1628.7	1546.2	1426.5	1274.4	1095.5
117.5°	1523.2	1579.6	1611.5	1620.3	1611.5	1579.6	1523.2	1439.1	1326.9	1188.9	1031.8
120°	1454.4	1509.0	1542.7	1554.3	1542.7	1509.0	1454.4	1373.1	1267.4	1144.2	1000.2
122.5°	1392.1	1445.8	1475.8	1485.5	1475.8	1445.8	1392.1	1319.2	1223.7	1107.1	975.1
125°	1315.0	1359.2	1388.2	1397.5	1388.2	1359.2	1315.0	1247.6	1160.5	1058.3	938.6
127.5°	1246.5	1287.8	1312.9	1320.4	1312.9	1287.8	1246.5	1187.7	1107.3	1010.9	902.6
130°	1204.7	1244.2	1267.4	1276.7	1267.4	1244.2	1204.7	1147.7	1071.1	979.3	879.4
132.5°	1161.9	1201.4	1222.8	1231.1	1222.8	1201.4	1161.9	1105.9	1033.9	949.6	857.1
135°	1094.3	1132.6	1153.5	1158.2	1153.5	1132.6	1094.3	1044.3	979.3	902.6	825.9
137.5°	1028.3	1061.3	1079.7	1086.6	1079.7	1061.3	1028.3	982.8	926.1	865.2	801.1
140°	982.8	1013.0	1030.4	1037.4	1030.4	1013.0	982.8	945.6	894.5	841.1	785.3
142.5°	943.7	971.2	986.7	988.1	986.7	971.2	943.7	908.4	865.7	819.7	772.3
145°	889.8	909.6	921.2	924.7	921.2	909.6	889.8	862.0	828.3	792.3	753.9
147.5°	845.7	861.5	869.4	871.5	869.4	861.5	845.7	822.7	798.1	770.0	739.8
150°	817.8	831.8	838.7	839.9	838.7	831.8	817.8	800.4	779.5	755.1	729.5
152.5°	795.5	807.6	812.7	812.9	812.7	807.6	795.5	781.8	763.7	743.0	719.3
155°	766.7	774.8	779.5	777.2	779.5	774.8	766.7	753.9	741.1	723.7	705.1
157.5°	737.9	744.6	746.7	746.7	746.7	744.6	737.9	728.8	718.8	704.2	688.6
160°	720.2	726.0	727.2	727.2	727.2	726.0	720.2	712.1	704.0	691.2	678.4
162.5°	704.4	708.4	709.5	708.6	709.5	708.4	704.4	696.3	690.0	679.1	668.2
165°	678.4	683.1	683.1	681.9	683.1	683.1	678.4	673.8	669.1	661.0	652.9
167.5°	656.3	658.9	658.7	657.3	658.7	658.9	656.3	654.3	650.1	644.5	638.2
170°	642.4	645.9	644.7	642.4	644.7	645.9	642.4	641.2	638.9	634.3	630.8
172.5°	631.3	632.9	631.7	630.3	631.7	632.9	631.3	630.1	628.7	625.0	622.4
175°	616.8	618.0	616.8	614.5	616.8	618.0	616.8	616.8	615.7	614.5	613.4
177.5°	607.8	607.8	606.9	605.0	606.9	607.8	607.8	607.8	607.8	606.9	606.9
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1



TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	933.8	937.1	942.2	947.5	950.8	957.1	958.9	961.9	964.6	970.8	977.4
5°	879.9	885.1	897.4	904.1	913.5	924.3	931.4	938.9	947.1	961.3	974.4
7.5°	822.1	830.8	846.1	858.7	872.0	887.5	898.7	913.5	925.7	945.7	964.9
10°	783.5	795.8	809.7	824.6	843.3	859.7	875.4	894.1	909.0	932.9	955.3
12.5°	748.9	750.7	770.5	787.0	812.5	832.8	850.9	874.9	889.6	918.0	941.6
15°	688.3	699.5	717.4	730.5	760.7	786.5	811.9	836.9	853.7	888.8	919.8
17.5°	637.3	647.6	666.0	687.4	709.1	734.7	767.6	794.0	816.8	856.9	893.6
20°	605.0	617.7	636.4	658.4	677.5	705.5	733.8	764.1	788.7	833.9	876.9
22.5°	577.5	587.5	602.6	624.3	645.2	670.8	701.9	734.8	760.7	809.4	853.0
25°	538.9	547.1	556.8	574.8	598.3	626.3	650.6	686.8	724.5	770.1	822.7
27.5°	504.1	509.9	518.5	534.3	552.5	578.7	605.7	640.0	678.0	727.4	783.0
30°	482.9	486.6	495.2	508.3	526.2	546.7	574.0	606.9	645.7	695.8	751.0
32.5°	464.4	467.8	473.4	485.9	501.4	519.0	543.5	576.4	613.4	662.6	723.8
35°	436.6	439.2	444.0	454.1	462.7	479.9	500.4	530.3	565.0	612.1	675.6
37.5°	408.9	412.4	415.4	419.7	430.7	442.0	459.9	485.1	519.2	566.7	627.2
40°	390.6	393.6	398.1	400.0	408.9	419.0	433.6	456.7	491.1	534.4	593.4
42.5°	372.1	375.1	377.8	380.0	387.7	396.6	409.7	429.6	460.0	502.2	560.6
45°	346.9	347.3	349.9	354.0	357.8	364.1	373.5	390.6	414.2	453.8	506.8
47.5°	321.4	321.8	322.3	324.1	328.2	333.9	340.1	354.1	375.2	406.8	458.4
50°	304.4	303.6	304.4	305.9	308.5	313.3	320.4	330.5	347.7	377.2	424.6
52.5°	287.9	287.8	287.3	287.9	290.0	293.3	298.3	306.9	322.3	349.4	391.2
55°	262.9	261.0	261.4	259.9	263.3	264.0	267.8	274.9	288.3	307.0	346.2
57.5°	236.2	234.7	233.0	232.6	232.3	234.3	237.3	242.9	253.2	269.6	301.4
60°	219.2	217.4	215.1	214.4	214.4	215.5	217.0	221.1	230.8	245.4	271.5
62.5°	201.9	199.7	198.4	196.4	195.8	197.0	198.5	201.4	208.4	222.1	244.6
65°	175.2	172.5	170.7	170.3	169.6	168.4	169.2	172.2	177.8	188.6	206.5
67.5°	148.3	145.9	145.4	143.3	142.2	142.4	142.2	144.8	148.1	157.4	170.8
70°	130.7	128.8	128.1	126.2	125.5	124.7	124.0	126.2	129.6	137.4	149.0
72.5°	112.8	111.2	109.6	108.0	108.2	107.4	107.3	108.6	111.4	118.6	127.5
75°	87.0	87.4	85.5	83.7	83.3	82.5	82.5	83.7	84.8	90.4	97.5
77.5°	63.1	62.8	61.2	60.6	60.3	59.5	60.3	61.0	61.6	65.4	70.6
80°	48.2	48.2	46.3	46.3	45.9	44.8	45.9	45.2	46.7	50.4	54.2
82.5°	34.4	33.8	33.8	33.2	33.1	32.3	32.8	33.5	34.1	36.7	38.9
85°	16.8	16.8	16.4	16.1	16.4	16.1	16.4	16.8	17.2	18.3	20.2
87.5°	11.3	11.8	11.8	10.8	9.1	8.3	7.9	7.7	7.8	7.2	6.8
90°	38.3	39.5	38.3	31.4	23.2	17.4	13.9	11.6	9.3	4.6	1.2
92.5°	127.6	151.0	148.9	115.9	79.0	52.7	41.8	33.9	28.8	20.4	14.2
95°	398.5	455.4	403.1	268.3	167.3	113.8	86.0	67.4	56.9	45.3	40.7
97.5°	815.5	777.4	585.5	361.5	220.7	153.6	122.0	100.6	84.8	72.5	66.2
100°	1085.0	917.7	631.9	381.0	239.3	177.7	145.2	122.0	103.4	92.9	89.4
102.5°	1185.4	922.4	614.3	382.0	256.0	199.1	166.6	142.4	123.8	113.4	110.8
105°	1169.8	860.8	579.7	388.0	284.6	230.0	197.5	171.9	154.5	146.4	141.7
107.5°	1067.8	794.8	562.5	404.0	313.9	260.9	228.2	202.8	186.8	178.9	175.2
110°	1003.7	763.2	558.8	417.0	333.4	282.3	248.6	224.2	209.1	202.1	197.5



TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	959.1	742.8	559.7	431.0	352.0	302.7	268.1	244.6	230.5	222.6	217.9
115°	903.8	720.2	564.6	451.9	381.0	331.1	299.7	276.5	262.5	255.6	249.8
117.5°	868.9	709.3	572.9	474.2	407.7	361.5	329.0	306.7	294.4	287.4	282.8
120°	850.3	702.8	578.5	489.1	426.3	381.0	348.5	325.3	314.8	307.8	303.2
122.5°	834.5	699.1	585.0	502.1	444.0	401.5	368.0	344.8	333.4	326.4	322.7
125°	812.0	692.4	594.8	522.8	470.5	428.7	396.1	372.9	359.0	352.0	348.5
127.5°	791.1	688.4	604.8	542.0	495.1	454.4	421.0	398.7	383.4	373.6	368.9
130°	777.2	686.5	612.2	554.1	510.0	469.3	436.8	413.6	397.3	385.7	381.0
132.5°	766.0	685.6	619.6	566.2	523.0	484.2	451.7	427.5	410.3	397.8	392.2
135°	750.4	684.2	628.5	582.0	541.3	504.2	471.6	444.9	427.5	413.6	408.9
137.5°	739.5	684.0	636.4	594.1	556.2	519.5	489.3	462.8	444.2	430.3	424.7
140°	733.0	683.1	640.1	600.6	564.6	529.7	499.5	474.0	455.4	441.4	436.8
142.5°	726.5	683.1	642.9	606.2	571.1	537.2	508.8	484.2	465.6	452.6	448.9
145°	717.9	680.7	645.9	613.4	580.8	549.5	523.9	500.7	483.3	471.6	467.0
147.5°	709.1	676.6	646.8	617.3	588.7	559.2	536.5	517.2	501.1	490.0	486.5
150°	701.6	673.8	645.9	619.2	592.5	565.7	544.8	527.4	512.3	503.0	499.5
152.5°	695.1	669.1	644.0	620.1	596.2	572.2	553.2	536.7	523.4	514.2	512.5
155°	683.1	661.0	641.2	621.5	601.7	582.0	564.6	551.8	539.0	532.0	530.9
157.5°	671.7	652.6	635.9	621.5	605.7	589.0	574.3	564.1	553.0	547.4	546.2
160°	663.3	647.1	633.1	621.5	607.6	593.6	580.8	571.5	562.2	557.6	556.4
162.5°	655.9	642.4	630.3	620.6	608.5	596.4	586.4	578.0	570.6	566.0	566.7
165°	643.6	633.1	625.0	618.0	609.9	599.4	592.5	586.6	579.7	577.4	578.5
167.5°	631.5	625.0	619.6	616.4	609.6	602.0	597.6	593.4	589.0	586.9	588.3
170°	625.0	620.3	616.8	614.5	608.7	602.9	599.4	597.1	593.6	592.5	594.8
172.5°	618.5	614.8	613.1	611.7	607.8	603.8	601.3	599.9	596.4	597.1	598.5
175°	609.9	608.7	607.6	608.7	606.4	604.1	602.9	602.9	600.6	601.7	602.9
177.5°	605.0	604.1	605.0	606.9	605.0	604.1	604.1	604.1	602.2	603.1	605.0
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1





TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	976.8	978.3	983.1	987.9	993.2	994.7	997.1	995.0	994.4	1000.1	1004.3
5°	979.6	986.3	999.4	1011.3	1021.4	1028.5	1036.0	1039.0	1044.6	1052.4	1062.1
7.5°	976.4	989.5	1010.1	1027.5	1046.4	1060.1	1070.8	1079.9	1090.9	1105.8	1122.0
10°	972.9	990.4	1015.4	1036.7	1059.9	1077.4	1092.0	1106.2	1122.6	1143.2	1164.4
12.5°	966.3	987.1	1018.4	1043.6	1073.3	1090.6	1110.2	1140.8	1158.5	1187.1	1217.0
15°	953.1	976.2	1019.9	1050.9	1084.5	1117.4	1153.6	1182.7	1211.9	1228.7	1270.9
17.5°	933.4	967.4	1015.8	1052.0	1094.7	1146.4	1187.1	1220.2	1253.8	1281.0	1302.2
20°	917.6	954.6	1009.8	1053.2	1103.9	1159.6	1206.3	1239.9	1269.0	1291.8	1304.9
22.5°	897.6	944.1	997.9	1048.7	1113.5	1168.6	1217.6	1244.1	1268.4	1279.5	1284.5
25°	866.0	922.1	982.9	1044.9	1118.1	1176.4	1221.2	1237.3	1244.4	1233.5	1215.6
27.5°	832.1	894.5	965.7	1037.9	1115.3	1171.3	1203.4	1200.9	1188.9	1153.8	1125.8
30°	806.7	875.4	951.9	1030.7	1108.4	1162.9	1181.6	1162.9	1135.7	1096.5	1056.5
32.5°	780.1	851.2	937.3	1020.6	1095.9	1143.8	1147.9	1115.7	1073.5	1029.0	979.1
35°	739.8	816.8	909.7	997.9	1069.2	1099.5	1081.5	1024.8	974.7	913.9	845.9
37.5°	694.3	779.3	872.5	964.6	1029.3	1037.2	992.7	932.9	862.3	790.8	710.8
40°	660.3	750.3	846.3	939.2	996.4	988.2	931.4	865.7	781.6	694.3	619.9
42.5°	629.8	719.8	817.6	908.8	954.6	932.0	865.7	785.0	694.7	612.4	544.4
45°	577.0	669.6	769.7	857.8	884.0	843.3	755.5	665.9	577.0	508.3	454.5
47.5°	525.8	617.3	716.4	793.9	803.2	748.4	652.5	560.3	483.9	427.9	390.0
50°	488.1	580.0	678.2	747.3	744.3	678.2	579.6	491.8	428.0	382.8	357.4
52.5°	454.3	541.1	635.5	698.3	682.5	610.4	516.3	438.4	385.9	350.5	327.5
55°	401.8	482.1	571.8	622.2	593.1	513.1	433.6	370.8	332.0	305.5	287.6
57.5°	349.7	425.0	501.7	532.8	500.6	426.8	360.5	315.0	285.8	266.1	254.5
60°	317.4	383.2	451.5	478.4	439.9	374.2	321.9	281.2	257.7	241.6	231.2
62.5°	285.2	344.0	408.5	423.1	387.9	332.4	286.1	252.2	232.9	218.6	208.8
65°	241.3	289.4	338.4	348.1	315.6	272.6	236.0	214.0	196.8	186.4	178.5
67.5°	197.9	236.5	271.2	279.0	250.6	220.8	194.3	175.2	163.5	154.8	148.2
70°	172.2	202.8	231.2	237.5	214.7	188.2	168.1	152.7	142.3	134.8	128.5
72.5°	145.0	170.5	194.1	198.4	179.8	159.5	143.0	130.9	121.7	116.9	110.8
75°	110.9	125.9	144.2	145.3	133.0	120.6	107.9	100.1	95.2	89.3	86.3
77.5°	78.3	90.0	100.5	102.5	95.2	86.8	79.7	73.5	69.4	66.6	63.9
80°	59.8	69.1	73.6	76.2	71.0	65.0	60.9	56.8	54.2	52.3	50.4
82.5°	42.7	48.5	52.7	54.7	51.8	48.3	44.1	41.8	39.8	38.2	37.6
85°	21.7	24.3	26.9	27.6	26.9	25.4	23.2	23.2	22.0	21.7	21.7
87.5°	8.4	10.5	11.0	12.3	12.4	13.6	15.2	16.3	16.3	15.7	15.2
90°	4.6	9.3	11.6	13.9	17.4	23.2	31.4	38.3	39.5	38.3	37.2
92.5°	20.4	28.8	33.9	41.8	52.7	79.0	115.9	148.9	151.0	127.6	101.3
95°	45.3	56.9	67.4	86.0	113.8	167.3	268.3	403.1	455.4	398.5	304.4
97.5°	72.5	84.8	100.6	122.0	153.6	220.7	361.5	585.5	777.4	815.5	710.2
100°	92.9	103.4	122.0	145.2	177.7	239.3	381.0	631.9	917.7	1085.0	1060.6
102.5°	113.4	123.8	142.4	166.6	199.1	256.0	382.0	614.3	922.4	1185.4	1290.2
105°	146.4	154.5	171.9	197.5	230.0	284.6	388.0	579.7	860.8	1169.8	1411.4
107.5°	178.9	186.8	202.8	228.2	260.9	313.9	404.0	562.5	794.8	1067.8	1324.1
110°	202.1	209.1	224.2	248.6	282.3	333.4	417.0	558.8	763.2	1003.7	1248.8





TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	222.6	230.5	244.6	268.1	302.7	352.0	431.0	559.7	742.8	959.1	1180.0
115°	255.6	262.5	276.5	299.7	331.1	381.0	451.9	564.6	720.2	903.8	1095.5
117.5°	287.4	294.4	306.7	329.0	361.5	407.7	474.2	572.9	709.3	868.9	1031.8
120°	307.8	314.8	325.3	348.5	381.0	426.3	489.1	578.5	702.8	850.3	1000.2
122.5°	326.4	333.4	344.8	368.0	401.5	444.0	502.1	585.0	699.1	834.5	975.1
125°	352.0	359.0	372.9	396.1	428.7	470.5	522.8	594.8	692.4	812.0	938.6
127.5°	373.6	383.4	398.7	421.0	454.4	495.1	542.0	604.8	688.4	791.1	902.6
130°	385.7	397.3	413.6	436.8	469.3	510.0	554.1	612.2	686.5	777.2	879.4
132.5°	397.8	410.3	427.5	451.7	484.2	523.0	566.2	619.6	685.6	766.0	857.1
135°	413.6	427.5	444.9	471.6	504.2	541.3	582.0	628.5	684.2	750.4	825.9
137.5°	430.3	444.2	462.8	489.3	519.5	556.2	594.1	636.4	684.0	739.5	801.1
140°	441.4	455.4	474.0	499.5	529.7	564.6	600.6	640.1	683.1	733.0	785.3
142.5°	452.6	465.6	484.2	508.8	537.2	571.1	606.2	642.9	683.1	726.5	772.3
145°	471.6	483.3	500.7	523.9	549.5	580.8	613.4	645.9	680.7	717.9	753.9
147.5°	490.0	501.1	517.2	536.5	559.2	588.7	617.3	646.8	676.6	709.1	739.8
150°	503.0	512.3	527.4	544.8	565.7	592.5	619.2	645.9	673.8	701.6	729.5
152.5°	514.2	523.4	536.7	553.2	572.2	596.2	620.1	644.0	669.1	695.1	719.3
155°	532.0	539.0	551.8	564.6	582.0	601.7	621.5	641.2	661.0	683.1	705.1
157.5°	547.4	553.0	564.1	574.3	589.0	605.7	621.5	635.9	652.6	671.7	688.6
160°	557.6	562.2	571.5	580.8	593.6	607.6	621.5	633.1	647.1	663.3	678.4
162.5°	566.0	570.6	578.0	586.4	596.4	608.5	620.6	630.3	642.4	655.9	668.2
165°	577.4	579.7	586.6	592.5	599.4	609.9	618.0	625.0	633.1	643.6	652.9
167.5°	586.9	589.0	593.4	597.6	602.0	609.6	616.4	619.6	625.0	631.5	638.2
170°	592.5	593.6	597.1	599.4	602.9	608.7	614.5	616.8	620.3	625.0	630.8
172.5°	597.1	596.4	599.9	601.3	603.8	607.8	611.7	613.1	614.8	618.5	622.4
175°	601.7	600.6	602.9	602.9	604.1	606.4	608.7	607.6	608.7	609.9	613.4
177.5°	603.1	602.2	604.1	604.1	604.1	605.0	606.9	605.0	604.1	605.0	606.9
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1



TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	971.7	971.7	971.7	971.7	971.7	971.7	971.7
2.5°	1007.9	1012.1	1012.1	1012.7	1017.4	1016.9	1016.6
5°	1072.6	1078.9	1079.7	1086.4	1090.9	1089.4	1085.3
7.5°	1133.6	1145.4	1154.4	1159.4	1165.3	1168.9	1167.3
10°	1182.0	1199.2	1209.6	1216.7	1225.3	1231.7	1229.4
12.5°	1225.9	1246.4	1260.7	1272.9	1274.0	1282.2	1276.6
15°	1294.4	1316.1	1318.3	1327.3	1334.4	1333.6	1334.0
17.5°	1317.0	1324.0	1325.4	1325.6	1325.7	1323.1	1317.4
20°	1309.0	1306.4	1300.0	1295.2	1286.6	1285.4	1278.0
22.5°	1270.7	1262.4	1246.5	1236.0	1222.6	1219.1	1217.0
25°	1195.4	1177.1	1151.7	1127.5	1120.7	1107.7	1111.4
27.5°	1092.1	1063.6	1036.1	1016.4	998.6	979.0	984.6
30°	1019.5	987.4	948.6	918.7	899.7	881.0	877.6
32.5°	932.9	885.8	842.5	816.2	787.0	775.2	762.3
35°	783.5	737.6	694.6	657.7	636.4	619.9	605.0
37.5°	649.1	596.3	561.6	531.7	516.3	506.9	509.2
40°	565.8	519.5	494.1	471.3	457.1	450.4	451.9
42.5°	498.3	463.6	442.7	427.1	417.1	413.3	412.4
45°	421.6	402.2	385.0	376.1	371.2	367.1	364.5
47.5°	369.4	353.5	343.8	338.5	334.2	330.1	330.0
50°	338.0	327.5	320.8	315.2	311.8	308.8	311.5
52.5°	314.1	304.5	297.8	292.8	291.5	288.8	288.8
55°	278.6	271.1	266.3	261.8	259.6	258.1	256.2
57.5°	246.3	239.2	234.8	231.9	227.7	226.2	225.6
60°	223.3	217.7	213.2	209.5	207.6	204.7	204.7
62.5°	202.1	196.5	192.3	189.5	186.4	185.2	185.5
65°	171.4	166.9	162.8	159.8	159.1	156.9	157.6
67.5°	143.2	140.2	135.9	134.2	132.8	131.6	130.7
70°	124.4	121.4	119.1	116.9	115.8	115.8	115.8
72.5°	108.5	104.9	103.6	100.8	101.4	100.2	99.0
75°	84.0	81.8	80.7	79.5	77.7	77.7	77.7
77.5°	61.8	61.2	59.8	58.6	58.2	57.8	58.0
80°	47.8	47.4	46.7	46.7	45.9	45.6	44.8
82.5°	36.7	35.8	35.3	35.0	34.9	34.8	34.7
85°	20.9	20.2	20.2	20.5	19.8	19.8	20.2
87.5°	15.0	15.5	15.4	15.4	15.7	15.4	15.4
90°	34.9	37.2	38.3	38.3	38.3	38.3	38.3
92.5°	86.9	77.1	69.9	69.0	65.3	66.2	64.4
95°	233.5	184.7	159.1	144.0	134.8	131.3	132.4
97.5°	581.1	455.4	371.5	316.0	287.4	270.4	260.7
100°	916.6	757.4	616.8	520.4	470.5	436.8	415.9
102.5°	1257.6	1141.2	992.3	887.5	802.3	760.2	731.9
105°	1542.7	1557.8	1519.5	1447.4	1375.4	1325.5	1309.2
107.5°	1521.8	1642.6	1698.8	1707.9	1703.9	1693.9	1672.3
110°	1456.7	1605.4	1700.7	1750.6	1772.7	1783.2	1782.0



TEST NUMBER: P331323

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	1379.6	1538.5	1647.7	1717.2	1754.1	1773.9	1780.1
115°	1274.4	1426.5	1546.2	1628.7	1682.1	1712.3	1722.8
117.5°	1188.9	1326.9	1439.1	1523.2	1579.6	1611.5	1620.3
120°	1144.2	1267.4	1373.1	1454.4	1509.0	1542.7	1554.3
122.5°	1107.1	1223.7	1319.2	1392.1	1445.8	1475.8	1485.5
125°	1058.3	1160.5	1247.6	1315.0	1359.2	1388.2	1397.5
127.5°	1010.9	1107.3	1187.7	1246.5	1287.8	1312.9	1320.4
130°	979.3	1071.1	1147.7	1204.7	1244.2	1267.4	1276.7
132.5°	949.6	1033.9	1105.9	1161.9	1201.4	1222.8	1231.1
135°	902.6	979.3	1044.3	1094.3	1132.6	1153.5	1158.2
137.5°	865.2	926.1	982.8	1028.3	1061.3	1079.7	1086.6
140°	841.1	894.5	945.6	982.8	1013.0	1030.4	1037.4
142.5°	819.7	865.7	908.4	943.7	971.2	986.7	988.1
145°	792.3	828.3	862.0	889.8	909.6	921.2	924.7
147.5°	770.0	798.1	822.7	845.7	861.5	869.4	871.5
150°	755.1	779.5	800.4	817.8	831.8	838.7	839.9
152.5°	743.0	763.7	781.8	795.5	807.6	812.7	812.9
155°	723.7	741.1	753.9	766.7	774.8	779.5	777.2
157.5°	704.2	718.8	728.8	737.9	744.6	746.7	746.7
160°	691.2	704.0	712.1	720.2	726.0	727.2	727.2
162.5°	679.1	690.0	696.3	704.4	708.4	709.5	708.6
165°	661.0	669.1	673.8	678.4	683.1	683.1	681.9
167.5°	644.5	650.1	654.3	656.3	658.9	658.7	657.3
170°	634.3	638.9	641.2	642.4	645.9	644.7	642.4
172.5°	625.0	628.7	630.1	631.3	632.9	631.7	630.3
175°	614.5	615.7	616.8	616.8	618.0	616.8	614.5
177.5°	606.9	607.8	607.8	607.8	607.8	606.9	605.0
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1

(END OF REPORT)