

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331393-927

Luminaire Tested: **SA2XXDIP-C865D725U927-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331393-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D725U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5314.5 lumens
Efficiency: N/A
Efficacy: 97.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331393-927
CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57				
1	100	96	92	89	93	89	86	83	77	75	73	66	64	63	56	55	54	49				
2	91	84	78	73	85	79	74	69	68	64	61	59	56	53	50	48	46	42				
3	84	75	67	62	78	70	63	58	61	56	52	52	49	46	45	42	40	36				
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31				
5	71	59	52	46	66	56	49	43	49	43	39	43	38	35	37	33	31	28				
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27	25				
7	61	49	41	35	56	46	39	34	40	35	31	35	31	28	31	27	25	22				
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20				
9	53	41	33	28	49	38	32	27	34	29	25	30	26	22	26	23	20	18				
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	24	21	18	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22083	22083	22083	22083
5°	24759	22227	19697	22227
10°	28370	22046	17046	22046
15°	31385	21641	15059	21641
20°	30907	21206	13728	21206
25°	27868	20630	12886	20630
30°	23029	19708	12269	19708
35°	16783	18743	11832	18743
40°	13405	17606	11590	17606
45°	11714	16287	11259	16287
50°	11012	15013	11037	15013
55°	10151	13717	10742	13717
60°	9300	12339	10285	12339
65°	8474	11106	9838	11106
70°	7695	9904	9182	9904
75°	6818	8559	8135	8559
80°	5867	7085	6546	7085
85°	5261	5261	3890	5261



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.3	2.5
10°-20°	378.7	7.1
20°-30°	549.6	10.3
30°-40°	579.9	10.9
40°-50°	513.5	9.7
50°-60°	409.8	7.7
60°-70°	278.5	5.2
70°-80°	142.8	2.7
80°-90°	36.4	0.7
90°-100°	26.1	0.5
100°-110°	95.8	1.8
110°-120°	256.1	4.8
120°-130°	422.7	8.0
130°-140°	449.6	8.5
140°-150°	417.8	7.9
150°-160°	335.9	6.3
160°-170°	216.5	4.1
170°-180°	74.5	1.4
0°-30°	1058.5	19.9
0°-40°	1638.5	30.8
0°-60°	2561.8	48.2
0°-90°	3019.4	56.8
90°-120°	378.0	7.1
90°-150°	1668.1	31.4
90°-180°	2295.0	43.2
0°-180°	5314.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1368	1368	1368	1368	1368	
5°	1528	1371	1215	1371	1528	153
15°	1878	1295	901	1295	1878	518
25°	1564	1158	723	1158	1564	707
35°	852	951	600	951	852	554
45°	513	713	493	713	513	403
55°	361	487	382	487	361	323
65°	222	291	258	291	222	221
75°	109	137	130	137	109	117
85°	28	28	21	28	28	31
90°	15	1	15	1	15	8
95°	24	37	24	37	24	23
105°	43	172	43	172	43	45
115°	46	326	46	326	46	116
125°	484	461	484	461	484	419
135°	589	570	589	570	589	454
145°	672	661	672	661	672	420
155°	729	728	729	728	729	336
165°	766	767	766	767	766	216
175°	780	785	780	785	780	74
180°	783	783	783	783	783	



TEST NUMBER: P331393-927
 CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1430.8	1431.2	1432.1	1425.4	1424.5	1424.5	1418.6	1413.6	1407.7	1399.7	1400.6
5°	1527.6	1533.3	1535.4	1529.1	1519.6	1518.6	1509.7	1494.9	1481.3	1470.2	1462.4
7.5°	1643.0	1645.3	1640.1	1631.8	1624.8	1612.2	1595.5	1579.3	1556.5	1535.6	1520.0
10°	1730.4	1733.6	1724.7	1712.5	1702.6	1687.8	1663.7	1638.9	1609.0	1580.1	1557.0
12.5°	1796.9	1804.7	1793.2	1791.6	1774.5	1754.3	1725.5	1713.0	1670.9	1630.5	1605.8
15°	1877.6	1877.1	1878.2	1868.1	1855.5	1852.4	1821.9	1788.8	1729.4	1705.7	1664.8
17.5°	1854.3	1862.3	1866.0	1865.8	1865.5	1863.5	1853.8	1832.9	1803.1	1764.7	1717.4
20°	1798.8	1809.3	1810.8	1823.0	1829.8	1838.7	1842.4	1836.6	1818.2	1786.1	1745.2
22.5°	1713.0	1715.9	1720.9	1739.7	1754.5	1776.9	1788.6	1808.0	1800.9	1785.3	1751.0
25°	1564.3	1559.1	1577.5	1586.9	1621.1	1656.8	1682.6	1711.0	1736.2	1751.4	1741.5
27.5°	1385.8	1377.9	1405.5	1430.6	1458.3	1497.1	1537.2	1584.6	1624.1	1673.3	1690.3
30°	1235.2	1240.0	1266.3	1293.1	1335.1	1389.8	1435.0	1487.1	1543.3	1598.5	1636.9
32.5°	1072.9	1091.2	1107.8	1148.8	1185.9	1246.8	1313.0	1378.2	1448.3	1511.0	1570.4
35°	851.5	872.6	895.7	925.7	977.7	1038.2	1102.8	1190.6	1286.3	1372.0	1442.4
37.5°	716.8	713.4	726.7	748.3	790.4	839.2	913.7	1000.4	1113.0	1213.7	1313.0
40°	636.0	633.9	643.4	663.4	695.5	731.2	796.4	872.6	977.2	1100.2	1218.5
42.5°	580.5	581.8	587.0	601.1	623.1	652.5	701.3	766.2	862.0	977.8	1104.9
45°	513.0	516.7	522.5	529.3	541.9	566.1	593.4	639.7	715.4	812.1	937.2
47.5°	464.5	464.5	470.5	476.4	483.9	497.6	519.8	548.9	602.3	681.0	788.6
50°	438.4	434.7	438.9	443.6	451.5	461.0	475.7	503.0	538.8	602.4	692.3
52.5°	406.5	406.5	410.4	412.1	419.1	428.6	442.0	461.0	493.4	543.1	617.0
55°	360.6	363.2	365.4	368.4	374.8	381.6	392.1	404.7	430.0	467.3	522.0
57.5°	317.5	318.3	320.4	326.5	330.4	336.8	346.7	358.1	374.5	402.2	443.3
60°	288.0	288.0	292.2	294.9	300.2	306.4	314.3	325.3	340.1	362.7	395.9
62.5°	261.2	260.7	262.4	266.7	270.7	276.6	284.5	293.8	307.7	327.8	355.1
65°	221.8	220.8	223.9	225.0	229.2	235.0	241.3	251.3	262.3	277.0	301.2
67.5°	183.9	185.2	187.0	188.9	191.2	197.3	201.5	208.6	217.9	230.1	246.5
70°	163.0	163.0	163.0	164.5	167.7	170.9	175.1	180.9	189.7	200.3	215.0
72.5°	139.4	141.1	142.8	141.8	145.8	147.7	152.7	156.0	164.5	171.3	184.3
75°	109.3	109.3	109.3	111.9	113.5	115.1	118.3	121.4	125.6	134.0	140.9
77.5°	81.6	81.4	81.9	82.5	84.2	86.1	87.1	89.9	93.8	97.7	103.5
80°	63.1	64.2	64.6	65.7	65.7	66.8	67.3	71.0	73.6	76.2	79.9
82.5°	48.8	49.0	49.1	49.3	49.7	50.4	51.7	52.9	53.8	56.0	58.9
85°	28.4	27.9	27.9	28.9	28.4	28.4	29.5	30.5	30.5	31.0	32.6
87.5°	14.0	13.9	14.3	13.9	13.8	14.1	14.0	13.5	13.8	14.0	14.3
90°	15.3	15.1	14.8	14.6	14.3	13.9	13.2	12.6	12.0	11.3	10.3
92.5°	15.3	15.1	15.0	14.8	14.7	14.4	14.1	13.8	13.5	13.2	12.7
95°	24.4	24.5	24.6	24.7	24.9	24.6	24.0	23.4	22.7	22.1	21.2
97.5°	32.6	32.4	32.2	32.1	31.9	31.6	31.1	30.6	30.1	29.5	27.6
100°	37.9	37.7	37.5	37.2	37.0	36.4	35.3	34.3	33.3	32.3	30.2
102.5°	40.7	40.3	40.0	39.6	39.3	38.4	37.2	35.8	34.5	33.2	31.1
105°	43.1	42.5	42.1	41.6	41.0	40.1	38.7	37.3	36.0	34.5	32.9
107.5°	44.3	43.8	43.3	42.8	42.3	42.8	44.1	45.6	47.0	48.4	49.6
110°	44.8	44.3	43.7	43.3	42.8	48.8	61.4	74.0	86.6	99.2	135.5



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	45.2	44.8	44.4	44.0	43.6	66.4	112.3	158.3	204.2	250.1	259.1
115°	46.5	55.5	64.6	73.7	82.7	116.5	174.8	233.1	291.4	349.7	346.5
117.5°	189.7	219.5	249.3	279.1	308.9	330.8	344.9	359.1	373.2	387.3	385.1
120°	345.7	362.7	379.7	396.6	413.7	421.4	419.9	418.4	416.8	415.3	413.1
122.5°	431.3	434.7	437.9	441.2	444.6	445.8	444.8	443.9	443.0	442.1	439.7
125°	484.5	484.1	483.8	483.4	483.0	482.4	481.5	480.6	479.7	478.9	476.4
127.5°	518.1	518.0	517.9	517.8	517.8	517.1	515.8	514.5	513.3	511.9	510.2
130°	538.9	539.0	539.2	539.3	539.4	538.8	537.4	536.0	534.6	533.2	531.9
132.5°	559.3	559.4	559.6	559.7	559.8	559.3	558.1	556.9	555.7	554.5	553.2
135°	588.7	589.0	589.3	589.5	589.8	589.3	588.0	586.8	585.5	584.2	583.1
137.5°	615.6	616.1	616.5	617.0	617.3	617.0	615.7	614.5	613.2	612.0	610.7
140°	632.4	633.0	633.7	634.3	634.9	634.7	633.5	632.4	631.3	630.2	628.8
142.5°	648.7	649.4	650.0	650.6	651.3	651.0	650.0	649.0	647.9	646.9	645.3
145°	671.5	672.2	672.8	673.4	674.0	673.9	673.0	672.2	671.3	670.3	668.2
147.5°	691.6	692.1	692.6	693.2	693.7	693.6	693.0	692.3	691.7	691.0	688.9
150°	703.8	704.4	705.0	705.7	706.3	706.2	705.5	704.7	704.0	703.2	701.2
152.5°	714.2	715.1	715.9	716.8	717.6	717.6	716.8	716.1	715.3	714.5	712.6
155°	728.7	729.8	730.8	731.7	732.8	732.9	732.1	731.4	730.6	729.8	728.3
157.5°	742.0	743.0	743.9	745.0	745.9	746.0	745.1	744.3	743.5	742.6	741.5
160°	749.7	750.6	751.5	752.3	753.2	753.3	752.6	751.8	751.1	750.3	749.5
162.5°	756.1	757.2	758.2	759.3	760.4	760.5	759.6	758.8	758.0	757.1	756.5
165°	765.6	766.4	767.3	768.3	769.1	769.1	768.3	767.3	766.4	765.6	765.2
167.5°	771.6	772.7	773.9	775.0	776.1	776.3	775.4	774.5	773.6	772.7	772.4
170°	775.2	776.3	777.4	778.6	779.7	779.9	779.0	778.1	777.2	776.3	776.1
172.5°	777.9	779.0	780.2	781.3	782.4	782.6	781.7	780.9	780.0	779.0	778.8
175°	780.3	781.6	782.8	784.1	785.4	785.5	784.7	783.8	782.9	782.0	781.7
177.5°	781.8	782.7	783.6	784.5	785.4	785.5	784.8	784.1	783.4	782.7	782.6
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1403.5	1400.1	1398.0	1390.4	1383.7	1377.0	1374.9	1375.7	1366.5	1357.6	1353.8
5°	1458.2	1447.6	1437.7	1423.5	1406.7	1388.2	1378.8	1371.4	1353.0	1333.1	1321.5
7.5°	1507.1	1492.1	1472.9	1446.2	1421.7	1392.7	1374.4	1358.0	1331.2	1303.0	1285.7
10°	1537.0	1516.5	1491.8	1459.2	1429.3	1394.0	1369.3	1344.7	1313.0	1279.5	1258.4
12.5°	1562.7	1535.0	1510.7	1468.9	1433.5	1389.4	1360.1	1325.2	1292.0	1252.1	1231.5
15°	1623.7	1572.7	1526.5	1479.2	1435.5	1374.0	1341.5	1294.7	1251.0	1201.7	1178.0
17.5°	1671.0	1613.7	1540.8	1480.7	1429.7	1361.7	1313.8	1257.7	1206.2	1149.7	1117.5
20°	1697.9	1632.1	1553.8	1482.3	1421.3	1343.5	1291.5	1234.2	1173.8	1110.2	1075.5
22.5°	1713.8	1644.7	1567.3	1476.0	1404.5	1328.8	1263.4	1200.6	1139.3	1070.6	1034.3
25°	1718.9	1655.8	1573.8	1470.8	1383.5	1297.8	1219.0	1158.0	1083.9	1019.8	966.7
27.5°	1693.8	1648.6	1569.8	1460.9	1359.2	1259.0	1171.2	1102.1	1023.9	954.3	900.9
30°	1663.2	1636.9	1560.1	1450.8	1339.9	1232.2	1135.4	1057.1	979.3	908.9	854.2
32.5°	1615.7	1610.0	1542.5	1436.5	1319.3	1198.1	1098.0	1018.8	932.6	863.4	811.3
35°	1522.3	1547.5	1504.9	1404.5	1280.5	1149.6	1041.3	950.9	861.6	795.3	746.4
37.5°	1397.2	1459.8	1448.7	1357.7	1228.1	1096.9	977.3	882.8	797.6	730.8	682.8
40°	1311.0	1390.8	1402.4	1322.0	1191.1	1056.1	929.4	835.3	752.2	691.3	642.9
42.5°	1218.5	1311.8	1343.5	1279.1	1150.7	1013.1	886.5	789.0	706.8	647.5	604.6
45°	1063.4	1186.9	1244.2	1207.4	1083.4	942.5	812.1	713.3	638.7	583.0	549.9
47.5°	918.4	1053.4	1130.4	1117.5	1008.4	868.9	740.0	645.2	572.5	528.1	498.4
50°	815.8	954.6	1047.6	1051.9	954.6	816.3	687.1	597.7	530.9	489.4	465.2
52.5°	726.7	859.1	960.6	982.9	894.5	761.7	639.5	550.6	491.8	453.6	432.0
55°	610.3	722.2	834.7	875.8	804.8	678.6	565.6	487.3	432.1	405.8	386.9
57.5°	507.4	600.7	704.6	749.9	706.2	598.2	492.2	424.2	379.4	356.4	341.9
60°	453.1	526.7	619.2	673.4	635.5	539.3	446.8	382.1	345.4	324.9	311.2
62.5°	402.7	467.9	546.1	595.6	575.0	484.3	401.4	344.3	312.5	293.3	283.4
65°	332.2	383.7	444.2	489.9	476.3	407.3	339.6	290.7	265.5	250.2	242.3
67.5°	273.5	310.8	352.7	392.8	381.8	333.0	278.5	240.4	221.7	208.5	203.7
70°	236.5	264.9	302.2	334.3	325.3	285.4	242.3	209.8	193.5	182.4	177.7
72.5°	201.2	224.6	253.0	279.2	273.2	240.0	204.1	179.4	166.9	156.8	152.9
75°	151.9	169.8	187.1	204.5	202.9	177.1	156.1	137.2	127.2	119.3	117.7
77.5°	112.2	122.2	134.0	144.3	141.4	126.7	110.2	99.3	92.0	86.7	85.9
80°	85.7	91.5	99.9	107.3	103.5	97.3	84.1	76.2	71.0	65.7	63.6
82.5°	62.1	67.9	73.0	76.9	74.1	68.2	60.1	54.7	51.7	48.0	47.2
85°	32.6	35.7	37.9	38.9	37.9	34.1	30.5	28.4	25.7	24.2	23.7
87.5°	14.5	14.3	14.1	14.7	13.2	12.8	10.9	9.3	9.2	9.1	8.5
90°	9.3	8.3	7.3	6.1	4.8	3.3	2.0	0.6	2.0	3.3	4.8
92.5°	12.1	11.6	11.2	10.9	11.1	11.2	11.3	11.4	11.3	11.2	11.1
95°	20.4	19.5	18.5	20.2	24.4	28.5	32.7	36.8	32.7	28.5	24.4
97.5°	25.5	23.4	21.4	26.2	37.9	49.7	61.4	73.1	61.4	49.7	37.9
100°	28.0	25.9	23.8	31.3	48.6	65.8	83.0	100.3	83.0	65.8	48.6
102.5°	69.0	86.9	104.8	115.6	119.3	122.9	126.6	130.2	126.6	122.9	119.3
105°	103.3	137.7	172.1	187.4	183.6	179.8	176.0	172.3	176.0	179.8	183.6
107.5°	130.9	172.1	213.3	232.4	229.3	226.3	223.2	220.2	223.2	226.3	229.3
110°	172.0	208.3	244.7	261.6	259.0	256.4	253.7	251.0	253.7	256.4	259.0



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	268.1	277.1	286.1	289.4	287.1	284.7	282.4	280.0	282.4	284.7	287.1
115°	343.3	340.2	337.1	334.4	332.2	330.1	328.0	325.8	328.0	330.1	332.2
117.5°	382.9	380.8	378.6	376.3	373.9	371.5	369.2	366.8	369.2	371.5	373.9
120°	410.8	408.6	406.3	404.3	402.3	400.4	398.5	396.6	398.5	400.4	402.3
122.5°	437.2	434.7	432.2	430.0	428.0	426.0	424.1	422.1	424.1	426.0	428.0
125°	474.0	471.7	469.3	467.2	465.6	464.0	462.3	460.7	462.3	464.0	465.6
127.5°	508.3	506.6	504.8	503.0	501.1	499.4	497.6	495.7	497.6	499.4	501.1
130°	530.4	529.1	527.7	526.0	523.9	522.0	520.0	517.9	520.0	522.0	523.9
132.5°	551.8	550.4	549.0	547.5	545.7	544.1	542.3	540.6	542.3	544.1	545.7
135°	581.9	580.8	579.7	578.1	576.2	574.1	572.1	570.1	572.1	574.1	576.2
137.5°	609.4	608.2	606.9	605.5	604.1	602.7	601.3	599.9	601.3	602.7	604.1
140°	627.4	626.0	624.6	623.4	622.4	621.4	620.4	619.4	620.4	621.4	622.4
142.5°	643.7	642.1	640.6	639.3	638.4	637.5	636.6	635.7	636.6	637.5	638.4
145°	666.1	663.9	661.8	660.8	660.9	661.1	661.2	661.3	661.2	661.1	660.9
147.5°	686.7	684.7	682.5	681.8	682.2	682.7	683.2	683.7	683.2	682.7	682.2
150°	699.2	697.2	695.2	694.6	695.5	696.4	697.3	698.2	697.3	696.4	695.5
152.5°	710.7	708.8	706.9	706.5	707.4	708.4	709.4	710.3	709.4	708.4	707.4
155°	726.8	725.3	723.8	723.7	724.8	725.9	727.1	728.2	727.1	725.9	724.8
157.5°	740.5	739.4	738.3	738.3	739.3	740.2	741.2	742.1	741.2	740.2	739.3
160°	748.8	748.0	747.3	747.3	748.0	748.8	749.5	750.3	749.5	748.8	748.0
162.5°	755.7	755.1	754.5	754.5	755.3	756.1	756.8	757.6	756.8	756.1	755.3
165°	764.9	764.5	764.1	764.2	765.0	765.8	766.5	767.3	766.5	765.8	765.0
167.5°	772.0	771.7	771.3	771.5	772.3	773.0	773.8	774.5	773.8	773.0	772.3
170°	775.9	775.6	775.3	775.6	776.3	777.1	777.8	778.6	777.8	777.1	776.3
172.5°	778.6	778.3	778.1	778.3	779.0	779.8	780.5	781.3	780.5	779.8	779.0
175°	781.5	781.3	781.0	781.3	782.2	783.1	783.9	784.8	783.9	783.1	782.2
177.5°	782.5	782.4	782.3	782.6	783.3	784.0	784.7	785.4	784.7	784.0	783.3
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1349.6	1347.1	1338.3	1333.7	1326.1	1319.0	1314.3	1316.4	1318.1	1317.2	1316.1
5°	1311.0	1301.0	1285.7	1272.6	1263.1	1245.8	1238.4	1234.8	1231.6	1227.9	1224.2
7.5°	1265.0	1249.2	1227.2	1208.6	1190.9	1169.3	1157.1	1149.7	1142.2	1133.9	1126.5
10°	1232.2	1210.1	1186.9	1160.6	1139.6	1120.1	1102.8	1091.2	1080.8	1070.7	1063.4
12.5°	1197.6	1172.2	1143.6	1107.6	1084.5	1056.7	1054.0	1033.6	1017.2	1011.1	1002.4
15°	1142.8	1107.0	1070.7	1028.2	1009.8	984.5	968.8	953.0	938.8	928.8	926.2
17.5°	1080.5	1034.2	998.1	967.5	937.3	911.5	897.0	884.4	872.7	859.4	857.5
20°	1032.9	992.9	953.5	926.7	895.7	869.4	851.5	838.9	828.9	821.1	814.2
22.5°	987.9	944.2	908.1	878.8	848.2	827.0	812.9	800.7	792.3	783.6	777.2
25°	915.7	881.5	842.1	809.0	783.7	770.1	758.5	748.0	742.8	737.0	729.6
27.5°	852.5	814.5	777.7	752.0	729.8	717.7	709.6	702.3	697.4	694.0	689.8
30°	807.9	769.5	740.6	715.4	697.0	684.9	679.7	675.5	669.7	667.6	665.5
32.5°	765.0	730.5	705.8	683.9	666.3	658.5	653.6	649.8	645.3	643.2	639.0
35°	704.4	675.5	651.3	639.2	625.0	618.1	614.5	609.3	605.0	602.9	602.4
37.5°	647.3	622.2	606.3	590.7	584.7	580.5	575.5	571.9	570.6	570.3	569.8
40°	610.3	589.8	575.6	563.0	560.3	554.1	549.9	546.7	546.7	547.2	546.7
42.5°	576.6	558.3	545.7	534.8	531.7	528.0	523.8	523.6	524.4	526.2	524.4
45°	525.6	512.5	503.6	498.3	492.5	488.9	488.3	489.9	490.4	491.0	492.5
47.5°	478.8	470.0	461.9	456.1	453.6	453.0	452.3	455.1	457.6	458.6	461.0
50°	451.0	441.0	434.2	430.5	428.4	427.4	428.4	431.6	433.6	436.3	437.8
52.5°	419.9	412.8	408.1	405.3	404.4	405.0	405.3	408.8	412.3	413.1	413.9
55°	376.9	371.6	370.6	365.8	368.0	367.4	370.0	372.2	375.3	378.5	379.0
57.5°	334.0	329.8	326.9	327.4	328.0	330.3	332.6	336.2	339.6	342.9	343.3
60°	305.4	303.3	301.7	301.7	302.8	305.9	308.6	312.2	314.3	316.5	318.0
62.5°	279.3	277.3	275.7	276.5	279.2	281.1	284.2	286.1	288.3	290.3	291.1
65°	238.1	237.1	238.7	239.7	240.2	242.9	246.5	248.1	250.2	251.3	254.9
67.5°	200.2	200.3	200.2	201.6	204.7	205.3	208.8	212.5	212.9	214.9	217.3
70°	174.5	175.5	176.7	177.7	180.3	181.3	183.9	185.5	187.7	189.3	190.8
72.5°	151.0	151.1	152.3	152.0	154.2	156.5	158.8	160.3	162.4	164.5	166.0
75°	116.1	116.1	117.2	117.7	120.4	123.0	122.5	123.5	125.6	127.7	128.8
77.5°	84.8	83.7	84.8	85.4	86.2	88.4	88.8	90.3	92.7	92.0	93.2
80°	64.6	63.1	64.6	65.2	65.2	67.8	67.8	68.8	70.4	68.8	70.4
82.5°	46.2	45.4	46.6	46.7	47.5	47.6	48.5	48.6	50.2	49.5	50.2
85°	23.1	22.6	23.1	22.6	23.1	23.7	23.7	23.1	23.1	24.2	22.6
87.5°	8.4	8.2	8.0	8.2	7.9	7.8	7.4	7.5	7.7	7.0	7.1
90°	6.1	7.3	8.3	9.3	10.3	11.3	12.0	12.6	13.2	13.9	14.3
92.5°	10.9	11.2	11.6	12.1	12.7	13.2	13.5	13.8	14.1	14.4	14.7
95°	20.2	18.5	19.5	20.4	21.2	22.1	22.7	23.4	24.0	24.6	24.9
97.5°	26.2	21.4	23.4	25.5	27.6	29.5	30.1	30.6	31.1	31.6	31.9
100°	31.3	23.8	25.9	28.0	30.2	32.3	33.3	34.3	35.3	36.4	37.0
102.5°	115.6	104.8	86.9	69.0	51.1	33.2	34.5	35.8	37.2	38.4	39.3
105°	187.4	172.1	137.7	103.3	68.9	34.5	36.0	37.3	38.7	40.1	41.0
107.5°	232.4	213.3	172.1	130.9	89.6	48.4	47.0	45.6	44.1	42.8	42.3
110°	261.6	244.7	208.3	172.0	135.5	99.2	86.6	74.0	61.4	48.8	42.8



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	289.4	286.1	277.1	268.1	259.1	250.1	204.2	158.3	112.3	66.4	43.6
115°	334.4	337.1	340.2	343.3	346.5	349.7	291.4	233.1	174.8	116.5	82.7
117.5°	376.3	378.6	380.8	382.9	385.1	387.3	373.2	359.1	344.9	330.8	308.9
120°	404.3	406.3	408.6	410.8	413.1	415.3	416.8	418.4	419.9	421.4	413.7
122.5°	430.0	432.2	434.7	437.2	439.7	442.1	443.0	443.9	444.8	445.8	444.6
125°	467.2	469.3	471.7	474.0	476.4	478.9	479.7	480.6	481.5	482.4	483.0
127.5°	503.0	504.8	506.6	508.3	510.2	511.9	513.3	514.5	515.8	517.1	517.8
130°	526.0	527.7	529.1	530.4	531.9	533.2	534.6	536.0	537.4	538.8	539.4
132.5°	547.5	549.0	550.4	551.8	553.2	554.5	555.7	556.9	558.1	559.3	559.8
135°	578.1	579.7	580.8	581.9	583.1	584.2	585.5	586.8	588.0	589.3	589.8
137.5°	605.5	606.9	608.2	609.4	610.7	612.0	613.2	614.5	615.7	617.0	617.3
140°	623.4	624.6	626.0	627.4	628.8	630.2	631.3	632.4	633.5	634.7	634.9
142.5°	639.3	640.6	642.1	643.7	645.3	646.9	647.9	649.0	650.0	651.0	651.3
145°	660.8	661.8	663.9	666.1	668.2	670.3	671.3	672.2	673.0	673.9	674.0
147.5°	681.8	682.5	684.7	686.7	688.9	691.0	691.7	692.3	693.0	693.6	693.7
150°	694.6	695.2	697.2	699.2	701.2	703.2	704.0	704.7	705.5	706.2	706.3
152.5°	706.5	706.9	708.8	710.7	712.6	714.5	715.3	716.1	716.8	717.6	717.6
155°	723.7	723.8	725.3	726.8	728.3	729.8	730.6	731.4	732.1	732.9	732.8
157.5°	738.3	738.3	739.4	740.5	741.5	742.6	743.5	744.3	745.1	746.0	745.9
160°	747.3	747.3	748.0	748.8	749.5	750.3	751.1	751.8	752.6	753.3	753.2
162.5°	754.5	754.5	755.1	755.7	756.5	757.1	758.0	758.8	759.6	760.5	760.4
165°	764.2	764.1	764.5	764.9	765.2	765.6	766.4	767.3	768.3	769.1	769.1
167.5°	771.5	771.3	771.7	772.0	772.4	772.7	773.6	774.5	775.4	776.3	776.1
170°	775.6	775.3	775.6	775.9	776.1	776.3	777.2	778.1	779.0	779.9	779.7
172.5°	778.3	778.1	778.3	778.6	778.8	779.0	780.0	780.9	781.7	782.6	782.4
175°	781.3	781.0	781.3	781.5	781.7	782.0	782.9	783.8	784.7	785.5	785.4
177.5°	782.6	782.3	782.4	782.5	782.6	782.7	783.4	784.1	784.8	785.5	785.4
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1311.8	1311.0	1311.0	1307.2	1311.0	1311.0	1311.8	1316.1	1317.2	1318.1	1316.4
5°	1216.9	1215.3	1212.7	1215.3	1212.7	1215.3	1216.9	1224.2	1227.9	1231.6	1234.8
7.5°	1123.0	1116.7	1115.7	1109.5	1115.7	1116.7	1123.0	1126.5	1133.9	1142.2	1149.7
10°	1054.5	1050.3	1049.7	1039.7	1049.7	1050.3	1054.5	1063.4	1070.7	1080.8	1091.2
12.5°	1002.3	992.2	994.2	988.4	994.2	992.2	1002.3	1002.4	1011.1	1017.2	1033.6
15°	912.0	912.0	909.9	900.9	909.9	912.0	912.0	926.2	928.8	938.8	953.0
17.5°	847.2	846.1	841.1	843.6	841.1	846.1	847.2	857.5	859.4	872.7	884.4
20°	808.4	805.3	799.0	799.0	799.0	805.3	808.4	814.2	821.1	828.9	838.9
22.5°	771.9	771.7	764.9	767.0	764.9	771.7	771.9	777.2	783.6	792.3	800.7
25°	729.0	724.8	721.8	723.3	721.8	724.8	729.0	729.6	737.0	742.8	748.0
27.5°	688.5	686.2	686.0	681.7	686.0	686.2	688.5	689.8	694.0	697.4	702.3
30°	665.0	659.7	660.8	658.1	660.8	659.7	665.0	665.5	667.6	669.7	675.5
32.5°	638.0	636.1	635.1	632.9	635.1	636.1	638.0	639.0	643.2	645.3	649.8
35°	601.3	601.9	599.2	600.3	599.2	601.9	601.3	602.4	602.9	605.0	609.3
37.5°	569.3	570.9	569.7	570.1	569.7	570.9	569.3	569.8	570.3	570.6	571.9
40°	548.3	548.3	548.3	549.9	548.3	548.3	548.3	546.7	547.2	546.7	546.7
42.5°	528.1	527.2	526.4	526.2	526.4	527.2	528.1	524.4	526.2	524.4	523.6
45°	493.6	495.2	495.7	493.1	495.7	495.2	493.6	492.5	491.0	490.4	489.9
47.5°	462.4	462.6	462.4	464.7	462.4	462.6	462.4	461.0	458.6	457.6	455.1
50°	440.5	439.4	440.5	439.4	440.5	439.4	440.5	437.8	436.3	433.6	431.6
52.5°	417.4	417.6	416.9	416.8	416.9	417.6	417.4	413.9	413.1	412.3	408.8
55°	381.1	382.1	381.6	381.6	381.6	382.1	381.1	379.0	378.5	375.3	372.2
57.5°	343.6	344.5	345.2	342.9	345.2	344.5	343.6	343.3	342.9	339.6	336.2
60°	317.5	320.1	319.6	318.5	319.6	320.1	317.5	318.0	316.5	314.3	312.2
62.5°	293.5	294.5	294.4	294.1	294.4	294.5	293.5	291.1	290.3	288.3	286.1
65°	256.5	257.5	256.0	257.5	256.0	257.5	256.5	254.9	251.3	250.2	248.1
67.5°	216.7	217.0	218.2	218.9	218.2	217.0	216.7	217.3	214.9	212.9	212.5
70°	191.9	191.3	192.9	194.5	192.9	191.3	191.9	190.8	189.3	187.7	185.5
72.5°	165.8	166.9	166.4	167.5	166.4	166.9	165.8	166.0	164.5	162.4	160.3
75°	127.7	129.3	128.8	130.4	128.8	129.3	127.7	128.8	127.7	125.6	123.5
77.5°	92.3	92.5	92.3	93.2	92.3	92.5	92.3	93.2	92.0	92.7	90.3
80°	70.4	69.4	68.4	70.4	68.4	69.4	70.4	70.4	68.8	70.4	68.8
82.5°	49.0	49.6	48.6	48.6	48.6	49.6	49.0	50.2	49.5	50.2	48.6
85°	22.6	22.1	21.0	21.0	21.0	22.1	22.6	22.6	24.2	23.1	23.1
87.5°	7.1	6.7	6.8	6.4	6.8	6.7	7.1	7.1	7.0	7.7	7.5
90°	14.6	14.8	15.1	15.3	15.1	14.8	14.6	14.3	13.9	13.2	12.6
92.5°	14.8	15.0	15.1	15.3	15.1	15.0	14.8	14.7	14.4	14.1	13.8
95°	24.7	24.6	24.5	24.4	24.5	24.6	24.7	24.9	24.6	24.0	23.4
97.5°	32.1	32.2	32.4	32.6	32.4	32.2	32.1	31.9	31.6	31.1	30.6
100°	37.2	37.5	37.7	37.9	37.7	37.5	37.2	37.0	36.4	35.3	34.3
102.5°	39.6	40.0	40.3	40.7	40.3	40.0	39.6	39.3	38.4	37.2	35.8
105°	41.6	42.1	42.5	43.1	42.5	42.1	41.6	41.0	40.1	38.7	37.3
107.5°	42.8	43.3	43.8	44.3	43.8	43.3	42.8	42.3	42.8	44.1	45.6
110°	43.3	43.7	44.3	44.8	44.3	43.7	43.3	42.8	48.8	61.4	74.0



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	44.0	44.4	44.8	45.2	44.8	44.4	44.0	43.6	66.4	112.3	158.3
115°	73.7	64.6	55.5	46.5	55.5	64.6	73.7	82.7	116.5	174.8	233.1
117.5°	279.1	249.3	219.5	189.7	219.5	249.3	279.1	308.9	330.8	344.9	359.1
120°	396.6	379.7	362.7	345.7	362.7	379.7	396.6	413.7	421.4	419.9	418.4
122.5°	441.2	437.9	434.7	431.3	434.7	437.9	441.2	444.6	445.8	444.8	443.9
125°	483.4	483.8	484.1	484.5	484.1	483.8	483.4	483.0	482.4	481.5	480.6
127.5°	517.8	517.9	518.0	518.1	518.0	517.9	517.8	517.8	517.1	515.8	514.5
130°	539.3	539.2	539.0	538.9	539.0	539.2	539.3	539.4	538.8	537.4	536.0
132.5°	559.7	559.6	559.4	559.3	559.4	559.6	559.7	559.8	559.3	558.1	556.9
135°	589.5	589.3	589.0	588.7	589.0	589.3	589.5	589.8	589.3	588.0	586.8
137.5°	617.0	616.5	616.1	615.6	616.1	616.5	617.0	617.3	617.0	615.7	614.5
140°	634.3	633.7	633.0	632.4	633.0	633.7	634.3	634.9	634.7	633.5	632.4
142.5°	650.6	650.0	649.4	648.7	649.4	650.0	650.6	651.3	651.0	650.0	649.0
145°	673.4	672.8	672.2	671.5	672.2	672.8	673.4	674.0	673.9	673.0	672.2
147.5°	693.2	692.6	692.1	691.6	692.1	692.6	693.2	693.7	693.6	693.0	692.3
150°	705.7	705.0	704.4	703.8	704.4	705.0	705.7	706.3	706.2	705.5	704.7
152.5°	716.8	715.9	715.1	714.2	715.1	715.9	716.8	717.6	717.6	716.8	716.1
155°	731.7	730.8	729.8	728.7	729.8	730.8	731.7	732.8	732.9	732.1	731.4
157.5°	745.0	743.9	743.0	742.0	743.0	743.9	745.0	745.9	746.0	745.1	744.3
160°	752.3	751.5	750.6	749.7	750.6	751.5	752.3	753.2	753.3	752.6	751.8
162.5°	759.3	758.2	757.2	756.1	757.2	758.2	759.3	760.4	760.5	759.6	758.8
165°	768.3	767.3	766.4	765.6	766.4	767.3	768.3	769.1	769.1	768.3	767.3
167.5°	775.0	773.9	772.7	771.6	772.7	773.9	775.0	776.1	776.3	775.4	774.5
170°	778.6	777.4	776.3	775.2	776.3	777.4	778.6	779.7	779.9	779.0	778.1
172.5°	781.3	780.2	779.0	777.9	779.0	780.2	781.3	782.4	782.6	781.7	780.9
175°	784.1	782.8	781.6	780.3	781.6	782.8	784.1	785.4	785.5	784.7	783.8
177.5°	784.5	783.6	782.7	781.8	782.7	783.6	784.5	785.4	785.5	784.8	784.1
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1314.3	1319.0	1326.1	1333.7	1338.3	1347.1	1349.6	1353.8	1357.6	1366.5	1375.7
5°	1238.4	1245.8	1263.1	1272.6	1285.7	1301.0	1311.0	1321.5	1333.1	1353.0	1371.4
7.5°	1157.1	1169.3	1190.9	1208.6	1227.2	1249.2	1265.0	1285.7	1303.0	1331.2	1358.0
10°	1102.8	1120.1	1139.6	1160.6	1186.9	1210.1	1232.2	1258.4	1279.5	1313.0	1344.7
12.5°	1054.0	1056.7	1084.5	1107.6	1143.6	1172.2	1197.6	1231.5	1252.1	1292.0	1325.2
15°	968.8	984.5	1009.8	1028.2	1070.7	1107.0	1142.8	1178.0	1201.7	1251.0	1294.7
17.5°	897.0	911.5	937.3	967.5	998.1	1034.2	1080.5	1117.5	1149.7	1206.2	1257.7
20°	851.5	869.4	895.7	926.7	953.5	992.9	1032.9	1075.5	1110.2	1173.8	1234.2
22.5°	812.9	827.0	848.2	878.8	908.1	944.2	987.9	1034.3	1070.6	1139.3	1200.6
25°	758.5	770.1	783.7	809.0	842.1	881.5	915.7	966.7	1019.8	1083.9	1158.0
27.5°	709.6	717.7	729.8	752.0	777.7	814.5	852.5	900.9	954.3	1023.9	1102.1
30°	679.7	684.9	697.0	715.4	740.6	769.5	807.9	854.2	908.9	979.3	1057.1
32.5°	653.6	658.5	666.3	683.9	705.8	730.5	765.0	811.3	863.4	932.6	1018.8
35°	614.5	618.1	625.0	639.2	651.3	675.5	704.4	746.4	795.3	861.6	950.9
37.5°	575.5	580.5	584.7	590.7	606.3	622.2	647.3	682.8	730.8	797.6	882.8
40°	549.9	554.1	560.3	563.0	575.6	589.8	610.3	642.9	691.3	752.2	835.3
42.5°	523.8	528.0	531.7	534.8	545.7	558.3	576.6	604.6	647.5	706.8	789.0
45°	488.3	488.9	492.5	498.3	503.6	512.5	525.6	549.9	583.0	638.7	713.3
47.5°	452.3	453.0	453.6	456.1	461.9	470.0	478.8	498.4	528.1	572.5	645.2
50°	428.4	427.4	428.4	430.5	434.2	441.0	451.0	465.2	489.4	530.9	597.7
52.5°	405.3	405.0	404.4	405.3	408.1	412.8	419.9	432.0	453.6	491.8	550.6
55°	370.0	367.4	368.0	365.8	370.6	371.6	376.9	386.9	405.8	432.1	487.3
57.5°	332.6	330.3	328.0	327.4	326.9	329.8	334.0	341.9	356.4	379.4	424.2
60°	308.6	305.9	302.8	301.7	301.7	303.3	305.4	311.2	324.9	345.4	382.1
62.5°	284.2	281.1	279.2	276.5	275.7	277.3	279.3	283.4	293.3	312.5	344.3
65°	246.5	242.9	240.2	239.7	238.7	237.1	238.1	242.3	250.2	265.5	290.7
67.5°	208.8	205.3	204.7	201.6	200.2	200.3	200.2	203.7	208.5	221.7	240.4
70°	183.9	181.3	180.3	177.7	176.7	175.5	174.5	177.7	182.4	193.5	209.8
72.5°	158.8	156.5	154.2	152.0	152.3	151.1	151.0	152.9	156.8	166.9	179.4
75°	122.5	123.0	120.4	117.7	117.2	116.1	116.1	117.7	119.3	127.2	137.2
77.5°	88.8	88.4	86.2	85.4	84.8	83.7	84.8	85.9	86.7	92.0	99.3
80°	67.8	67.8	65.2	65.2	64.6	63.1	64.6	63.6	65.7	71.0	76.2
82.5°	48.5	47.6	47.5	46.7	46.6	45.4	46.2	47.2	48.0	51.7	54.7
85°	23.7	23.7	23.1	22.6	23.1	22.6	23.1	23.7	24.2	25.7	28.4
87.5°	7.4	7.8	7.9	8.2	8.0	8.2	8.4	8.5	9.1	9.2	9.3
90°	12.0	11.3	10.3	9.3	8.3	7.3	6.1	4.8	3.3	2.0	0.6
92.5°	13.5	13.2	12.7	12.1	11.6	11.2	10.9	11.1	11.2	11.3	11.4
95°	22.7	22.1	21.2	20.4	19.5	18.5	20.2	24.4	28.5	32.7	36.8
97.5°	30.1	29.5	27.6	25.5	23.4	21.4	26.2	37.9	49.7	61.4	73.1
100°	33.3	32.3	30.2	28.0	25.9	23.8	31.3	48.6	65.8	83.0	100.3
102.5°	34.5	33.2	51.1	69.0	86.9	104.8	115.6	119.3	122.9	126.6	130.2
105°	36.0	34.5	68.9	103.3	137.7	172.1	187.4	183.6	179.8	176.0	172.3
107.5°	47.0	48.4	89.6	130.9	172.1	213.3	232.4	229.3	226.3	223.2	220.2
110°	86.6	99.2	135.5	172.0	208.3	244.7	261.6	259.0	256.4	253.7	251.0



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	204.2	250.1	259.1	268.1	277.1	286.1	289.4	287.1	284.7	282.4	280.0
115°	291.4	349.7	346.5	343.3	340.2	337.1	334.4	332.2	330.1	328.0	325.8
117.5°	373.2	387.3	385.1	382.9	380.8	378.6	376.3	373.9	371.5	369.2	366.8
120°	416.8	415.3	413.1	410.8	408.6	406.3	404.3	402.3	400.4	398.5	396.6
122.5°	443.0	442.1	439.7	437.2	434.7	432.2	430.0	428.0	426.0	424.1	422.1
125°	479.7	478.9	476.4	474.0	471.7	469.3	467.2	465.6	464.0	462.3	460.7
127.5°	513.3	511.9	510.2	508.3	506.6	504.8	503.0	501.1	499.4	497.6	495.7
130°	534.6	533.2	531.9	530.4	529.1	527.7	526.0	523.9	522.0	520.0	517.9
132.5°	555.7	554.5	553.2	551.8	550.4	549.0	547.5	545.7	544.1	542.3	540.6
135°	585.5	584.2	583.1	581.9	580.8	579.7	578.1	576.2	574.1	572.1	570.1
137.5°	613.2	612.0	610.7	609.4	608.2	606.9	605.5	604.1	602.7	601.3	599.9
140°	631.3	630.2	628.8	627.4	626.0	624.6	623.4	622.4	621.4	620.4	619.4
142.5°	647.9	646.9	645.3	643.7	642.1	640.6	639.3	638.4	637.5	636.6	635.7
145°	671.3	670.3	668.2	666.1	663.9	661.8	660.8	660.9	661.1	661.2	661.3
147.5°	691.7	691.0	688.9	686.7	684.7	682.5	681.8	682.2	682.7	683.2	683.7
150°	704.0	703.2	701.2	699.2	697.2	695.2	694.6	695.5	696.4	697.3	698.2
152.5°	715.3	714.5	712.6	710.7	708.8	706.9	706.5	707.4	708.4	709.4	710.3
155°	730.6	729.8	728.3	726.8	725.3	723.8	723.7	724.8	725.9	727.1	728.2
157.5°	743.5	742.6	741.5	740.5	739.4	738.3	738.3	739.3	740.2	741.2	742.1
160°	751.1	750.3	749.5	748.8	748.0	747.3	747.3	748.0	748.8	749.5	750.3
162.5°	758.0	757.1	756.5	755.7	755.1	754.5	754.5	755.3	756.1	756.8	757.6
165°	766.4	765.6	765.2	764.9	764.5	764.1	764.2	765.0	765.8	766.5	767.3
167.5°	773.6	772.7	772.4	772.0	771.7	771.3	771.5	772.3	773.0	773.8	774.5
170°	777.2	776.3	776.1	775.9	775.6	775.3	775.6	776.3	777.1	777.8	778.6
172.5°	780.0	779.0	778.8	778.6	778.3	778.1	778.3	779.0	779.8	780.5	781.3
175°	782.9	782.0	781.7	781.5	781.3	781.0	781.3	782.2	783.1	783.9	784.8
177.5°	783.4	782.7	782.6	782.5	782.4	782.3	782.6	783.3	784.0	784.7	785.4
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1374.9	1377.0	1383.7	1390.4	1398.0	1400.1	1403.5	1400.6	1399.7	1407.7	1413.6
5°	1378.8	1388.2	1406.7	1423.5	1437.7	1447.6	1458.2	1462.4	1470.2	1481.3	1494.9
7.5°	1374.4	1392.7	1421.7	1446.2	1472.9	1492.1	1507.1	1520.0	1535.6	1556.5	1579.3
10°	1369.3	1394.0	1429.3	1459.2	1491.8	1516.5	1537.0	1557.0	1580.1	1609.0	1638.9
12.5°	1360.1	1389.4	1433.5	1468.9	1510.7	1535.0	1562.7	1605.8	1630.5	1670.9	1713.0
15°	1341.5	1374.0	1435.5	1479.2	1526.5	1572.7	1623.7	1664.8	1705.7	1729.4	1788.8
17.5°	1313.8	1361.7	1429.7	1480.7	1540.8	1613.7	1671.0	1717.4	1764.7	1803.1	1832.9
20°	1291.5	1343.5	1421.3	1482.3	1553.8	1632.1	1697.9	1745.2	1786.1	1818.2	1836.6
22.5°	1263.4	1328.8	1404.5	1476.0	1567.3	1644.7	1713.8	1751.0	1785.3	1800.9	1808.0
25°	1219.0	1297.8	1383.5	1470.8	1573.8	1655.8	1718.9	1741.5	1751.4	1736.2	1711.0
27.5°	1171.2	1259.0	1359.2	1460.9	1569.8	1648.6	1693.8	1690.3	1673.3	1624.1	1584.6
30°	1135.4	1232.2	1339.9	1450.8	1560.1	1636.9	1663.2	1636.9	1598.5	1543.3	1487.1
32.5°	1098.0	1198.1	1319.3	1436.5	1542.5	1610.0	1615.7	1570.4	1511.0	1448.3	1378.2
35°	1041.3	1149.6	1280.5	1404.5	1504.9	1547.5	1522.3	1442.4	1372.0	1286.3	1190.6
37.5°	977.3	1096.9	1228.1	1357.7	1448.7	1459.8	1397.2	1313.0	1213.7	1113.0	1000.4
40°	929.4	1056.1	1191.1	1322.0	1402.4	1390.8	1311.0	1218.5	1100.2	977.2	872.6
42.5°	886.5	1013.1	1150.7	1279.1	1343.5	1311.8	1218.5	1104.9	977.8	862.0	766.2
45°	812.1	942.5	1083.4	1207.4	1244.2	1186.9	1063.4	937.2	812.1	715.4	639.7
47.5°	740.0	868.9	1008.4	1117.5	1130.4	1053.4	918.4	788.6	681.0	602.3	548.9
50°	687.1	816.3	954.6	1051.9	1047.6	954.6	815.8	692.3	602.4	538.8	503.0
52.5°	639.5	761.7	894.5	982.9	960.6	859.1	726.7	617.0	543.1	493.4	461.0
55°	565.6	678.6	804.8	875.8	834.7	722.2	610.3	522.0	467.3	430.0	404.7
57.5°	492.2	598.2	706.2	749.9	704.6	600.7	507.4	443.3	402.2	374.5	358.1
60°	446.8	539.3	635.5	673.4	619.2	526.7	453.1	395.9	362.7	340.1	325.3
62.5°	401.4	484.3	575.0	595.6	546.1	467.9	402.7	355.1	327.8	307.7	293.8
65°	339.6	407.3	476.3	489.9	444.2	383.7	332.2	301.2	277.0	262.3	251.3
67.5°	278.5	333.0	381.8	392.8	352.7	310.8	273.5	246.5	230.1	217.9	208.6
70°	242.3	285.4	325.3	334.3	302.2	264.9	236.5	215.0	200.3	189.7	180.9
72.5°	204.1	240.0	273.2	279.2	253.0	224.6	201.2	184.3	171.3	164.5	156.0
75°	156.1	177.1	202.9	204.5	187.1	169.8	151.9	140.9	134.0	125.6	121.4
77.5°	110.2	126.7	141.4	144.3	134.0	122.2	112.2	103.5	97.7	93.8	89.9
80°	84.1	97.3	103.5	107.3	99.9	91.5	85.7	79.9	76.2	73.6	71.0
82.5°	60.1	68.2	74.1	76.9	73.0	67.9	62.1	58.9	56.0	53.8	52.9
85°	30.5	34.1	37.9	38.9	37.9	35.7	32.6	32.6	31.0	30.5	30.5
87.5°	10.9	12.8	13.2	14.7	14.1	14.3	14.5	14.3	14.0	13.8	13.5
90°	2.0	3.3	4.8	6.1	7.3	8.3	9.3	10.3	11.3	12.0	12.6
92.5°	11.3	11.2	11.1	10.9	11.2	11.6	12.1	12.7	13.2	13.5	13.8
95°	32.7	28.5	24.4	20.2	18.5	19.5	20.4	21.2	22.1	22.7	23.4
97.5°	61.4	49.7	37.9	26.2	21.4	23.4	25.5	27.6	29.5	30.1	30.6
100°	83.0	65.8	48.6	31.3	23.8	25.9	28.0	30.2	32.3	33.3	34.3
102.5°	126.6	122.9	119.3	115.6	104.8	86.9	69.0	51.1	33.2	34.5	35.8
105°	176.0	179.8	183.6	187.4	172.1	137.7	103.3	68.9	34.5	36.0	37.3
107.5°	223.2	226.3	229.3	232.4	213.3	172.1	130.9	89.6	48.4	47.0	45.6
110°	253.7	256.4	259.0	261.6	244.7	208.3	172.0	135.5	99.2	86.6	74.0



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	282.4	284.7	287.1	289.4	286.1	277.1	268.1	259.1	250.1	204.2	158.3
115°	328.0	330.1	332.2	334.4	337.1	340.2	343.3	346.5	349.7	291.4	233.1
117.5°	369.2	371.5	373.9	376.3	378.6	380.8	382.9	385.1	387.3	373.2	359.1
120°	398.5	400.4	402.3	404.3	406.3	408.6	410.8	413.1	415.3	416.8	418.4
122.5°	424.1	426.0	428.0	430.0	432.2	434.7	437.2	439.7	442.1	443.0	443.9
125°	462.3	464.0	465.6	467.2	469.3	471.7	474.0	476.4	478.9	479.7	480.6
127.5°	497.6	499.4	501.1	503.0	504.8	506.6	508.3	510.2	511.9	513.3	514.5
130°	520.0	522.0	523.9	526.0	527.7	529.1	530.4	531.9	533.2	534.6	536.0
132.5°	542.3	544.1	545.7	547.5	549.0	550.4	551.8	553.2	554.5	555.7	556.9
135°	572.1	574.1	576.2	578.1	579.7	580.8	581.9	583.1	584.2	585.5	586.8
137.5°	601.3	602.7	604.1	605.5	606.9	608.2	609.4	610.7	612.0	613.2	614.5
140°	620.4	621.4	622.4	623.4	624.6	626.0	627.4	628.8	630.2	631.3	632.4
142.5°	636.6	637.5	638.4	639.3	640.6	642.1	643.7	645.3	646.9	647.9	649.0
145°	661.2	661.1	660.9	660.8	661.8	663.9	666.1	668.2	670.3	671.3	672.2
147.5°	683.2	682.7	682.2	681.8	682.5	684.7	686.7	688.9	691.0	691.7	692.3
150°	697.3	696.4	695.5	694.6	695.2	697.2	699.2	701.2	703.2	704.0	704.7
152.5°	709.4	708.4	707.4	706.5	706.9	708.8	710.7	712.6	714.5	715.3	716.1
155°	727.1	725.9	724.8	723.7	723.8	725.3	726.8	728.3	729.8	730.6	731.4
157.5°	741.2	740.2	739.3	738.3	738.3	739.4	740.5	741.5	742.6	743.5	744.3
160°	749.5	748.8	748.0	747.3	747.3	748.0	748.8	749.5	750.3	751.1	751.8
162.5°	756.8	756.1	755.3	754.5	754.5	755.1	755.7	756.5	757.1	758.0	758.8
165°	766.5	765.8	765.0	764.2	764.1	764.5	764.9	765.2	765.6	766.4	767.3
167.5°	773.8	773.0	772.3	771.5	771.3	771.7	772.0	772.4	772.7	773.6	774.5
170°	777.8	777.1	776.3	775.6	775.3	775.6	775.9	776.1	776.3	777.2	778.1
172.5°	780.5	779.8	779.0	778.3	778.1	778.3	778.6	778.8	779.0	780.0	780.9
175°	783.9	783.1	782.2	781.3	781.0	781.3	781.5	781.7	782.0	782.9	783.8
177.5°	784.7	784.0	783.3	782.6	782.3	782.4	782.5	782.6	782.7	783.4	784.1
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2	783.2



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1418.6	1424.5	1424.5	1425.4	1432.1	1431.2	1430.8
5°	1509.7	1518.6	1519.6	1529.1	1535.4	1533.3	1527.6
7.5°	1595.5	1612.2	1624.8	1631.8	1640.1	1645.3	1643.0
10°	1663.7	1687.8	1702.6	1712.5	1724.7	1733.6	1730.4
12.5°	1725.5	1754.3	1774.5	1791.6	1793.2	1804.7	1796.9
15°	1821.9	1852.4	1855.5	1868.1	1878.2	1877.1	1877.6
17.5°	1853.8	1863.5	1865.5	1865.8	1866.0	1862.3	1854.3
20°	1842.4	1838.7	1829.8	1823.0	1810.8	1809.3	1798.8
22.5°	1788.6	1776.9	1754.5	1739.7	1720.9	1715.9	1713.0
25°	1682.6	1656.8	1621.1	1586.9	1577.5	1559.1	1564.3
27.5°	1537.2	1497.1	1458.3	1430.6	1405.5	1377.9	1385.8
30°	1435.0	1389.8	1335.1	1293.1	1266.3	1240.0	1235.2
32.5°	1313.0	1246.8	1185.9	1148.8	1107.8	1091.2	1072.9
35°	1102.8	1038.2	977.7	925.7	895.7	872.6	851.5
37.5°	913.7	839.2	790.4	748.3	726.7	713.4	716.8
40°	796.4	731.2	695.5	663.4	643.4	633.9	636.0
42.5°	701.3	652.5	623.1	601.1	587.0	581.8	580.5
45°	593.4	566.1	541.9	529.3	522.5	516.7	513.0
47.5°	519.8	497.6	483.9	476.4	470.5	464.5	464.5
50°	475.7	461.0	451.5	443.6	438.9	434.7	438.4
52.5°	442.0	428.6	419.1	412.1	410.4	406.5	406.5
55°	392.1	381.6	374.8	368.4	365.4	363.2	360.6
57.5°	346.7	336.8	330.4	326.5	320.4	318.3	317.5
60°	314.3	306.4	300.2	294.9	292.2	288.0	288.0
62.5°	284.5	276.6	270.7	266.7	262.4	260.7	261.2
65°	241.3	235.0	229.2	225.0	223.9	220.8	221.8
67.5°	201.5	197.3	191.2	188.9	187.0	185.2	183.9
70°	175.1	170.9	167.7	164.5	163.0	163.0	163.0
72.5°	152.7	147.7	145.8	141.8	142.8	141.1	139.4
75°	118.3	115.1	113.5	111.9	109.3	109.3	109.3
77.5°	87.1	86.1	84.2	82.5	81.9	81.4	81.6
80°	67.3	66.8	65.7	65.7	64.6	64.2	63.1
82.5°	51.7	50.4	49.7	49.3	49.1	49.0	48.8
85°	29.5	28.4	28.4	28.9	27.9	27.9	28.4
87.5°	14.0	14.1	13.8	13.9	14.3	13.9	14.0
90°	13.2	13.9	14.3	14.6	14.8	15.1	15.3
92.5°	14.1	14.4	14.7	14.8	15.0	15.1	15.3
95°	24.0	24.6	24.9	24.7	24.6	24.5	24.4
97.5°	31.1	31.6	31.9	32.1	32.2	32.4	32.6
100°	35.3	36.4	37.0	37.2	37.5	37.7	37.9
102.5°	37.2	38.4	39.3	39.6	40.0	40.3	40.7
105°	38.7	40.1	41.0	41.6	42.1	42.5	43.1
107.5°	44.1	42.8	42.3	42.8	43.3	43.8	44.3
110°	61.4	48.8	42.8	43.3	43.7	44.3	44.8



TEST NUMBER: P331393-927

CATALOG NUMBER: SA2XXDIP-C865D725U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	112.3	66.4	43.6	44.0	44.4	44.8	45.2
115°	174.8	116.5	82.7	73.7	64.6	55.5	46.5
117.5°	344.9	330.8	308.9	279.1	249.3	219.5	189.7
120°	419.9	421.4	413.7	396.6	379.7	362.7	345.7
122.5°	444.8	445.8	444.6	441.2	437.9	434.7	431.3
125°	481.5	482.4	483.0	483.4	483.8	484.1	484.5
127.5°	515.8	517.1	517.8	517.8	517.9	518.0	518.1
130°	537.4	538.8	539.4	539.3	539.2	539.0	538.9
132.5°	558.1	559.3	559.8	559.7	559.6	559.4	559.3
135°	588.0	589.3	589.8	589.5	589.3	589.0	588.7
137.5°	615.7	617.0	617.3	617.0	616.5	616.1	615.6
140°	633.5	634.7	634.9	634.3	633.7	633.0	632.4
142.5°	650.0	651.0	651.3	650.6	650.0	649.4	648.7
145°	673.0	673.9	674.0	673.4	672.8	672.2	671.5
147.5°	693.0	693.6	693.7	693.2	692.6	692.1	691.6
150°	705.5	706.2	706.3	705.7	705.0	704.4	703.8
152.5°	716.8	717.6	717.6	716.8	715.9	715.1	714.2
155°	732.1	732.9	732.8	731.7	730.8	729.8	728.7
157.5°	745.1	746.0	745.9	745.0	743.9	743.0	742.0
160°	752.6	753.3	753.2	752.3	751.5	750.6	749.7
162.5°	759.6	760.5	760.4	759.3	758.2	757.2	756.1
165°	768.3	769.1	769.1	768.3	767.3	766.4	765.6
167.5°	775.4	776.3	776.1	775.0	773.9	772.7	771.6
170°	779.0	779.9	779.7	778.6	777.4	776.3	775.2
172.5°	781.7	782.6	782.4	781.3	780.2	779.0	777.9
175°	784.7	785.5	785.4	784.1	782.8	781.6	780.3
177.5°	784.8	785.5	785.4	784.5	783.6	782.7	781.8
180°	783.2	783.2	783.2	783.2	783.2	783.2	783.2

(END OF REPORT)