

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331329

Luminaire Tested: **SA2XXDIP-C485D1080U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331329
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D1080U835-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6185.0 lumens
Efficiency: N/A
Efficacy: 125.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331329
CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331329

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40	32
1	94	90	86	82	84	81	78	75	64	62	60	49	48	46	35	34	33	27
2	85	78	72	67	77	70	65	61	56	53	50	43	41	39	31	29	28	23
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24	19
4	71	61	53	47	64	55	48	43	44	39	35	34	31	28	24	22	21	16
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	20	18	14
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	18	16	13
7	55	43	36	30	50	39	33	28	32	27	23	25	21	19	18	16	14	11
8	51	39	32	27	46	36	29	25	29	24	20	23	19	16	17	14	12	10
9	48	36	29	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12540	12540	12540
5°	12588	12407	12480
10°	12514	12281	12342
15°	12359	12122	12109
20°	12139	11883	11869
25°	11922	11589	11589
30°	11641	11320	11222
35°	11379	10996	10835
40°	11051	10673	10467
45°	10727	10351	10095
50°	10374	10017	9661
55°	10007	9627	9272
60°	9597	9164	8825
65°	9158	8703	8302
70°	8601	8143	7756
75°	7829	7498	7317
80°	6946	6732	6388
85°	5669	5391	4835



TEST NUMBER: P331329

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	1.2
10°-20°	205.5	3.3
20°-30°	302.1	4.9
30°-40°	350.9	5.7
40°-50°	350.5	5.7
50°-60°	305.6	4.9
60°-70°	226.0	3.7
70°-80°	128.0	2.1
80°-90°	39.9	0.6
90°-100°	241.5	3.9
100°-110°	819.6	13.3
110°-120°	870.7	14.1
120°-130°	716.8	11.6
130°-140°	575.6	9.3
140°-150°	435.0	7.0
150°-160°	305.7	4.9
160°-170°	180.0	2.9
170°-180°	58.6	0.9
0°-30°	580.6	9.4
0°-40°	931.5	15.1
0°-60°	1587.6	25.7
0°-90°	1981.5	32.0
90°-120°	1931.9	31.2
90°-150°	3659.3	59.2
90°-180°	4204.0	68.0
0°-180°	6185.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	773	766	771	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	362
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	35
90°	1	16	40	38	38	4
95°	41	100	455	172	132	43
105°	142	214	861	1539	1309	151
115°	250	315	720	1486	1723	248
125°	348	412	692	1204	1398	309
135°	409	488	684	1012	1158	316
145°	467	537	681	845	925	293
155°	531	573	661	748	777	244
165°	578	596	633	671	682	163
175°	603	604	609	616	614	57
180°	604	604	604	604	604	



TEST NUMBER: P331329

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	780.3	779.6	779.0	778.3	777.6	776.6	775.1	773.7	772.2	770.7	772.1
5°	776.7	776.0	775.4	774.7	774.1	772.8	771.0	769.2	767.3	765.5	766.8
7.5°	769.8	768.8	767.8	766.7	765.7	764.3	762.4	760.6	758.7	756.8	758.2
10°	763.3	762.1	760.9	759.8	758.6	757.0	755.0	753.1	751.1	749.1	750.4
12.5°	754.3	753.3	752.2	751.2	750.2	748.7	746.7	744.7	742.7	740.7	741.6
15°	739.4	738.4	737.4	736.4	735.4	733.8	731.6	729.5	727.3	725.2	725.8
17.5°	720.2	719.3	718.3	717.3	716.3	714.7	712.5	710.3	708.1	705.9	706.7
20°	706.5	705.5	704.5	703.5	702.5	700.9	698.5	696.2	693.9	691.6	692.1
22.5°	692.8	691.4	690.0	688.6	687.2	685.4	683.2	681.0	678.8	676.6	676.7
25°	669.2	667.8	666.5	665.2	663.9	661.8	659.0	656.1	653.3	650.5	650.8
27.5°	642.3	641.1	639.9	638.7	637.5	635.8	633.6	631.3	629.1	626.9	626.4
30°	624.4	623.0	621.7	620.4	619.0	617.1	614.6	612.2	609.7	607.2	606.7
32.5°	605.2	604.2	603.1	602.0	601.0	599.1	596.5	593.9	591.3	588.7	587.8
35°	577.3	575.6	574.0	572.3	570.7	568.5	565.9	563.2	560.5	557.9	556.9
37.5°	545.8	544.3	542.9	541.4	539.9	537.9	535.2	532.6	529.9	527.3	526.0
40°	524.3	522.9	521.6	520.3	519.0	517.0	514.3	511.7	509.0	506.4	504.9
42.5°	503.4	502.0	500.7	499.4	498.1	496.1	493.4	490.8	488.1	485.4	483.8
45°	469.8	468.6	467.4	466.3	465.1	463.3	460.8	458.3	455.8	453.3	451.5
47.5°	436.3	435.2	434.1	433.0	431.9	430.1	427.5	424.9	422.3	419.7	417.8
50°	413.0	412.2	411.3	410.5	409.7	408.1	405.8	403.5	401.1	398.8	396.5
52.5°	390.3	389.2	388.1	387.0	385.9	384.3	382.1	379.9	377.7	375.5	373.6
55°	355.5	354.5	353.5	352.5	351.5	350.0	348.0	346.0	344.0	342.0	340.1
57.5°	320.5	319.7	318.9	318.2	317.4	315.9	313.7	311.5	309.3	307.1	305.1
60°	297.2	296.6	295.9	295.2	294.6	293.1	290.8	288.4	286.1	283.8	282.0
62.5°	274.5	273.5	272.4	271.3	270.3	268.9	267.1	265.3	263.5	261.7	260.0
65°	239.7	238.7	237.7	236.7	235.8	234.4	232.8	231.1	229.4	227.8	226.3
67.5°	204.3	203.5	202.7	201.9	201.1	200.0	198.5	197.0	195.5	194.0	192.9
70°	182.2	181.6	180.9	180.2	179.6	178.5	177.0	175.5	174.0	172.5	171.4
72.5°	159.5	158.9	158.2	157.5	156.9	156.1	155.1	154.1	153.2	152.2	151.0
75°	125.5	125.1	124.8	124.5	124.1	123.6	122.7	121.9	121.1	120.2	119.2
77.5°	95.0	94.4	93.9	93.3	92.7	92.3	92.0	91.6	91.3	91.0	90.5
80°	74.7	74.5	74.4	74.2	74.0	73.8	73.4	73.1	72.8	72.4	71.9
82.5°	55.6	55.5	55.5	55.5	55.4	55.3	55.1	54.9	54.7	54.5	53.9
85°	30.6	30.5	30.3	30.1	30.0	29.8	29.6	29.5	29.3	29.1	28.6
87.5°	11.0	11.4	12.1	12.3	12.5	12.9	13.8	15.2	16.3	16.3	15.6
90°	1.2	4.6	9.3	11.6	13.9	17.4	23.2	31.4	38.3	39.5	38.3
92.5°	14.2	20.4	28.8	33.9	41.8	52.7	79.0	115.9	148.9	151.0	127.6
95°	40.7	45.3	56.9	67.4	86.0	113.8	167.3	268.3	403.1	455.4	398.5
97.5°	66.2	72.5	84.8	100.6	122.0	153.6	220.7	361.5	585.5	777.4	815.5
100°	89.4	92.9	103.4	122.0	145.2	177.7	239.3	381.0	631.9	917.7	1085.0
102.5°	110.8	113.4	123.8	142.4	166.6	199.1	256.0	382.0	614.3	922.4	1185.4
105°	141.7	146.4	154.5	171.9	197.5	230.0	284.6	388.0	579.7	860.8	1169.8
107.5°	175.2	178.9	186.8	202.8	228.2	260.9	313.9	404.0	562.5	794.8	1067.8
110°	197.5	202.1	209.1	224.2	248.6	282.3	333.4	417.0	558.8	763.2	1003.7



TEST NUMBER: P331329

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.9	222.6	230.5	244.6	268.1	302.7	352.0	431.0	559.7	742.8	959.1
115°	249.8	255.6	262.5	276.5	299.7	331.1	381.0	451.9	564.6	720.2	903.8
117.5°	282.8	287.4	294.4	306.7	329.0	361.5	407.7	474.2	572.9	709.3	868.9
120°	303.2	307.8	314.8	325.3	348.5	381.0	426.3	489.1	578.5	702.8	850.3
122.5°	322.7	326.4	333.4	344.8	368.0	401.5	444.0	502.1	585.0	699.1	834.5
125°	348.5	352.0	359.0	372.9	396.1	428.7	470.5	522.8	594.8	692.4	812.0
127.5°	368.9	373.6	383.4	398.7	421.0	454.4	495.1	542.0	604.8	688.4	791.1
130°	381.0	385.7	397.3	413.6	436.8	469.3	510.0	554.1	612.2	686.5	777.2
132.5°	392.2	397.8	410.3	427.5	451.7	484.2	523.0	566.2	619.6	685.6	766.0
135°	408.9	413.6	427.5	444.9	471.6	504.2	541.3	582.0	628.5	684.2	750.4
137.5°	424.7	430.3	444.2	462.8	489.3	519.5	556.2	594.1	636.4	684.0	739.5
140°	436.8	441.4	455.4	474.0	499.5	529.7	564.6	600.6	640.1	683.1	733.0
142.5°	448.9	452.6	465.6	484.2	508.8	537.2	571.1	606.2	642.9	683.1	726.5
145°	467.0	471.6	483.3	500.7	523.9	549.5	580.8	613.4	645.9	680.7	717.9
147.5°	486.5	490.0	501.1	517.2	536.5	559.2	588.7	617.3	646.8	676.6	709.1
150°	499.5	503.0	512.3	527.4	544.8	565.7	592.5	619.2	645.9	673.8	701.6
152.5°	512.5	514.2	523.4	536.7	553.2	572.2	596.2	620.1	644.0	669.1	695.1
155°	530.9	532.0	539.0	551.8	564.6	582.0	601.7	621.5	641.2	661.0	683.1
157.5°	546.2	547.4	553.0	564.1	574.3	589.0	605.7	621.5	635.9	652.6	671.7
160°	556.4	557.6	562.2	571.5	580.8	593.6	607.6	621.5	633.1	647.1	663.3
162.5°	566.7	566.0	570.6	578.0	586.4	596.4	608.5	620.6	630.3	642.4	655.9
165°	578.5	577.4	579.7	586.6	592.5	599.4	609.9	618.0	625.0	633.1	643.6
167.5°	588.3	586.9	589.0	593.4	597.6	602.0	609.6	616.4	619.6	625.0	631.5
170°	594.8	592.5	593.6	597.1	599.4	602.9	608.7	614.5	616.8	620.3	625.0
172.5°	598.5	597.1	596.4	599.9	601.3	603.8	607.8	611.7	613.1	614.8	618.5
175°	602.9	601.7	600.6	602.9	602.9	604.1	606.4	608.7	607.6	608.7	609.9
177.5°	605.0	603.1	602.2	604.1	604.1	604.1	605.0	606.9	605.0	604.1	605.0
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1



TEST NUMBER: P331329

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	773.4	774.7	776.0	776.6	776.3	776.0	775.8	775.5
5°	768.2	769.5	770.8	771.3	771.0	770.6	770.3	770.0
7.5°	759.5	760.8	762.2	762.6	762.3	761.9	761.5	761.2
10°	751.7	753.1	754.4	754.8	754.3	753.8	753.3	752.8
12.5°	742.6	743.5	744.4	744.7	744.3	744.0	743.6	743.2
15°	726.5	727.2	727.8	727.7	726.9	726.1	725.3	724.4
17.5°	707.4	708.2	709.0	708.9	708.1	707.4	706.6	705.8
20°	692.6	693.1	693.6	693.5	692.8	692.1	691.5	690.8
22.5°	676.8	676.9	677.0	676.9	676.5	676.1	675.7	675.3
25°	651.2	651.5	651.8	651.8	651.5	651.2	650.8	650.5
27.5°	625.9	625.4	624.9	624.3	623.5	622.7	621.9	621.1
30°	606.2	605.7	605.2	604.6	603.9	603.3	602.6	601.9
32.5°	586.9	586.0	585.1	584.3	583.6	583.0	582.3	581.6
35°	555.9	554.9	553.9	553.0	552.2	551.3	550.5	549.7
37.5°	524.8	523.6	522.4	521.3	520.5	519.7	518.9	518.2
40°	503.4	501.9	500.4	499.3	498.6	498.0	497.3	496.6
42.5°	482.2	480.6	478.9	477.7	476.7	475.8	474.9	473.9
45°	449.7	447.9	446.0	444.8	444.1	443.5	442.8	442.1
47.5°	415.9	413.9	412.0	410.6	409.6	408.7	407.7	406.7
50°	394.2	391.8	389.5	387.9	387.1	386.3	385.4	384.6
52.5°	371.7	369.7	367.8	366.3	365.2	364.1	363.0	361.9
55°	338.1	336.1	334.1	332.7	331.8	331.0	330.2	329.4
57.5°	303.2	301.2	299.3	298.0	297.3	296.7	296.1	295.4
60°	280.1	278.3	276.5	275.3	274.8	274.3	273.8	273.3
62.5°	258.3	256.6	254.9	253.8	253.1	252.5	251.9	251.2
65°	224.8	223.3	221.8	220.6	219.8	219.0	218.2	217.3
67.5°	191.7	190.5	189.4	188.5	187.8	187.1	186.5	185.8
70°	170.2	169.0	167.9	167.0	166.3	165.6	165.0	164.3
72.5°	149.9	148.7	147.6	146.7	146.2	145.6	145.1	144.6
75°	118.2	117.3	116.3	115.9	116.3	116.6	116.9	117.3
77.5°	90.0	89.5	89.0	88.5	88.0	87.6	87.1	86.6
80°	71.4	70.9	70.5	70.0	69.7	69.4	69.0	68.7
82.5°	53.3	52.6	52.0	51.6	51.6	51.5	51.4	51.4
85°	28.1	27.6	27.1	26.8	26.6	26.5	26.3	26.1
87.5°	15.0	14.1	14.2	14.2	14.0	13.9	13.8	13.6
90°	37.2	34.9	37.2	38.3	38.3	38.3	38.3	38.3
92.5°	101.3	86.9	77.1	69.9	69.0	65.3	66.2	64.4
95°	304.4	233.5	184.7	159.1	144.0	134.8	131.3	132.4
97.5°	710.2	581.1	455.4	371.5	316.0	287.4	270.4	260.7
100°	1060.6	916.6	757.4	616.8	520.4	470.5	436.8	415.9
102.5°	1290.2	1257.6	1141.2	992.3	887.5	802.3	760.2	731.9
105°	1411.4	1542.7	1557.8	1519.5	1447.4	1375.4	1325.5	1309.2
107.5°	1324.1	1521.8	1642.6	1698.8	1707.9	1703.9	1693.9	1672.3
110°	1248.8	1456.7	1605.4	1700.7	1750.6	1772.7	1783.2	1782.0



TEST NUMBER: P331329

CATALOG NUMBER: SA2XXDIP-C485D1080U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1180.0	1379.6	1538.5	1647.7	1717.2	1754.1	1773.9	1780.1
115°	1095.5	1274.4	1426.5	1546.2	1628.7	1682.1	1712.3	1722.8
117.5°	1031.8	1188.9	1326.9	1439.1	1523.2	1579.6	1611.5	1620.3
120°	1000.2	1144.2	1267.4	1373.1	1454.4	1509.0	1542.7	1554.3
122.5°	975.1	1107.1	1223.7	1319.2	1392.1	1445.8	1475.8	1485.5
125°	938.6	1058.3	1160.5	1247.6	1315.0	1359.2	1388.2	1397.5
127.5°	902.6	1010.9	1107.3	1187.7	1246.5	1287.8	1312.9	1320.4
130°	879.4	979.3	1071.1	1147.7	1204.7	1244.2	1267.4	1276.7
132.5°	857.1	949.6	1033.9	1105.9	1161.9	1201.4	1222.8	1231.1
135°	825.9	902.6	979.3	1044.3	1094.3	1132.6	1153.5	1158.2
137.5°	801.1	865.2	926.1	982.8	1028.3	1061.3	1079.7	1086.6
140°	785.3	841.1	894.5	945.6	982.8	1013.0	1030.4	1037.4
142.5°	772.3	819.7	865.7	908.4	943.7	971.2	986.7	988.1
145°	753.9	792.3	828.3	862.0	889.8	909.6	921.2	924.7
147.5°	739.8	770.0	798.1	822.7	845.7	861.5	869.4	871.5
150°	729.5	755.1	779.5	800.4	817.8	831.8	838.7	839.9
152.5°	719.3	743.0	763.7	781.8	795.5	807.6	812.7	812.9
155°	705.1	723.7	741.1	753.9	766.7	774.8	779.5	777.2
157.5°	688.6	704.2	718.8	728.8	737.9	744.6	746.7	746.7
160°	678.4	691.2	704.0	712.1	720.2	726.0	727.2	727.2
162.5°	668.2	679.1	690.0	696.3	704.4	708.4	709.5	708.6
165°	652.9	661.0	669.1	673.8	678.4	683.1	683.1	681.9
167.5°	638.2	644.5	650.1	654.3	656.3	658.9	658.7	657.3
170°	630.8	634.3	638.9	641.2	642.4	645.9	644.7	642.4
172.5°	622.4	625.0	628.7	630.1	631.3	632.9	631.7	630.3
175°	613.4	614.5	615.7	616.8	616.8	618.0	616.8	614.5
177.5°	606.9	606.9	607.8	607.8	607.8	607.8	606.9	605.0
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1

(END OF REPORT)