

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331402-927

Luminaire Tested: **SA2XXDIP-C865D925U927-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331402-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D925U927-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5950.1 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331402-927
CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51
1	98	94	91	87	91	87	84	81	74	72	70	62	60	59	51	50	49	44
2	90	83	77	72	83	77	72	67	66	62	59	55	52	50	45	44	42	37
3	82	73	66	61	76	68	62	57	58	54	50	49	46	43	41	38	36	32
4	76	65	58	52	70	61	54	49	52	47	43	44	40	37	37	34	32	28
5	70	58	50	45	64	54	47	42	47	41	37	40	36	33	33	30	28	25
6	64	53	45	39	59	49	42	37	42	37	33	36	32	29	30	27	25	22
7	60	48	40	34	55	45	38	33	39	33	29	33	29	26	28	25	22	20
8	55	43	36	31	51	41	34	29	35	30	26	30	26	23	26	23	20	18
9	52	40	32	27	48	37	31	26	32	27	23	28	24	21	24	21	18	16
10	48	36	29	25	45	34	28	24	30	25	21	26	22	19	22	19	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	22083	22083	22083	22083
5°	24759	22227	19697	22227
10°	28370	22046	17046	22046
15°	31385	21641	15059	21641
20°	30907	21206	13728	21206
25°	27868	20630	12886	20630
30°	23029	19708	12269	19708
35°	16783	18743	11832	18743
40°	13405	17606	11590	17606
45°	11714	16287	11259	16287
50°	11012	15013	11037	15013
55°	10151	13717	10742	13717
60°	9300	12339	10285	12339
65°	8474	11106	9838	11106
70°	7695	9904	9182	9904
75°	6818	8559	8135	8559
80°	5867	7085	6546	7085
85°	5261	5261	3890	5261



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	130.3	2.2
10°-20°	378.7	6.4
20°-30°	549.6	9.2
30°-40°	579.9	9.7
40°-50°	513.5	8.6
50°-60°	409.8	6.9
60°-70°	278.5	4.7
70°-80°	142.8	2.4
80°-90°	36.9	0.6
90°-100°	33.4	0.6
100°-110°	122.3	2.1
110°-120°	326.9	5.5
120°-130°	539.7	9.1
130°-140°	574.0	9.6
140°-150°	533.5	9.0
150°-160°	428.9	7.2
160°-170°	276.4	4.6
170°-180°	95.1	1.6
0°-30°	1058.5	17.8
0°-40°	1638.5	27.5
0°-60°	2561.8	43.1
0°-90°	3020.0	50.8
90°-120°	482.6	8.1
90°-150°	2129.7	35.8
90°-180°	2930.0	49.2
0°-180°	5950.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1368	1368	1368	1368	1368	
5°	1528	1371	1215	1371	1528	153
15°	1878	1295	901	1295	1878	518
25°	1564	1158	723	1158	1564	707
35°	852	951	600	951	852	554
45°	513	713	493	713	513	403
55°	361	487	382	487	361	323
65°	222	291	258	291	222	221
75°	109	137	130	137	109	117
85°	28	28	21	28	28	32
90°	20	1	20	1	20	10
95°	31	47	31	47	31	29
105°	55	220	55	220	55	57
115°	59	416	59	416	59	149
125°	619	588	619	588	619	535
135°	752	728	752	728	752	579
145°	857	844	857	844	857	536
155°	930	930	930	930	930	429
165°	978	980	978	980	978	276
175°	996	1002	996	1002	996	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1430.8	1431.2	1432.1	1425.4	1424.5	1424.5	1418.6	1413.6	1407.7	1399.7	1400.6
5°	1527.6	1533.3	1535.4	1529.1	1519.6	1518.6	1509.7	1494.9	1481.3	1470.2	1462.4
7.5°	1643.0	1645.3	1640.1	1631.8	1624.8	1612.2	1595.5	1579.3	1556.5	1535.6	1520.0
10°	1730.4	1733.6	1724.7	1712.5	1702.6	1687.8	1663.7	1638.9	1609.0	1580.1	1557.0
12.5°	1796.9	1804.7	1793.2	1791.6	1774.5	1754.3	1725.5	1713.0	1670.9	1630.5	1605.8
15°	1877.6	1877.1	1878.2	1868.1	1855.5	1852.4	1821.9	1788.8	1729.4	1705.7	1664.8
17.5°	1854.3	1862.3	1866.0	1865.8	1865.5	1863.5	1853.8	1832.9	1803.1	1764.7	1717.4
20°	1798.8	1809.3	1810.8	1823.0	1829.8	1838.7	1842.4	1836.6	1818.2	1786.1	1745.2
22.5°	1713.0	1715.9	1720.9	1739.7	1754.5	1776.9	1788.6	1808.0	1800.9	1785.3	1751.0
25°	1564.3	1559.1	1577.5	1586.9	1621.1	1656.8	1682.6	1711.0	1736.2	1751.4	1741.5
27.5°	1385.8	1377.9	1405.5	1430.6	1458.3	1497.1	1537.2	1584.6	1624.1	1673.3	1690.3
30°	1235.2	1240.0	1266.3	1293.1	1335.1	1389.8	1435.0	1487.1	1543.3	1598.5	1636.9
32.5°	1072.9	1091.2	1107.8	1148.8	1185.9	1246.8	1313.0	1378.2	1448.3	1511.0	1570.4
35°	851.5	872.6	895.7	925.7	977.7	1038.2	1102.8	1190.6	1286.3	1372.0	1442.4
37.5°	716.8	713.4	726.7	748.3	790.4	839.2	913.7	1000.4	1113.0	1213.7	1313.0
40°	636.0	633.9	643.4	663.4	695.5	731.2	796.4	872.6	977.2	1100.2	1218.5
42.5°	580.5	581.8	587.0	601.1	623.1	652.5	701.3	766.2	862.0	977.8	1104.9
45°	513.0	516.7	522.5	529.3	541.9	566.1	593.4	639.7	715.4	812.1	937.2
47.5°	464.5	464.5	470.5	476.4	483.9	497.6	519.8	548.9	602.3	681.0	788.6
50°	438.4	434.7	438.9	443.6	451.5	461.0	475.7	503.0	538.8	602.4	692.3
52.5°	406.5	406.5	410.4	412.1	419.1	428.6	442.0	461.0	493.4	543.1	617.0
55°	360.6	363.2	365.4	368.4	374.8	381.6	392.1	404.7	430.0	467.3	522.0
57.5°	317.5	318.3	320.4	326.5	330.4	336.8	346.7	358.1	374.5	402.2	443.3
60°	288.0	288.0	292.2	294.9	300.2	306.4	314.3	325.3	340.1	362.7	395.9
62.5°	261.2	260.7	262.4	266.7	270.7	276.6	284.5	293.8	307.7	327.8	355.1
65°	221.8	220.8	223.9	225.0	229.2	235.0	241.3	251.3	262.3	277.0	301.2
67.5°	183.9	185.2	187.0	188.9	191.2	197.3	201.5	208.6	217.9	230.1	246.5
70°	163.0	163.0	163.0	164.5	167.7	170.9	175.1	180.9	189.7	200.3	215.0
72.5°	139.4	141.1	142.8	141.8	145.8	147.7	152.7	156.0	164.5	171.3	184.3
75°	109.3	109.3	109.3	111.9	113.5	115.1	118.3	121.4	125.6	134.0	140.9
77.5°	81.6	81.4	81.9	82.5	84.2	86.1	87.1	89.9	93.8	97.7	103.5
80°	63.1	64.2	64.6	65.7	65.7	66.8	67.3	71.0	73.6	76.2	79.9
82.5°	48.8	49.0	49.1	49.3	49.7	50.4	51.7	52.9	53.8	56.0	58.9
85°	28.4	27.9	27.9	28.9	28.4	28.4	29.5	30.5	30.5	31.0	32.6
87.5°	14.8	14.8	15.1	14.7	14.6	14.9	14.7	14.2	14.4	14.7	14.8
90°	19.6	19.3	18.9	18.5	18.2	17.7	16.9	16.1	15.3	14.5	13.2
92.5°	19.6	19.3	19.2	18.9	18.8	18.5	18.1	17.6	17.2	16.8	16.2
95°	31.1	31.3	31.4	31.6	31.8	31.4	30.7	29.8	29.0	28.2	27.1
97.5°	41.5	41.4	41.1	41.0	40.7	40.3	39.7	39.1	38.4	37.8	35.2
100°	48.5	48.2	47.8	47.5	47.2	46.4	45.1	43.8	42.5	41.3	38.5
102.5°	52.0	51.5	51.0	50.6	50.1	49.1	47.5	45.7	44.0	42.4	65.3
105°	55.0	54.3	53.7	53.1	52.4	51.2	49.4	47.7	45.9	44.1	88.0
107.5°	56.6	55.9	55.3	54.7	54.0	54.6	56.4	58.1	60.0	61.8	114.4
110°	57.2	56.5	55.8	55.2	54.6	62.3	78.3	94.4	110.5	126.6	173.1



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.8	57.2	56.7	56.2	55.7	84.8	143.4	202.1	260.7	319.3	330.8
115°	59.3	70.9	82.5	94.0	105.6	148.6	223.1	297.5	371.9	446.4	442.4
117.5°	242.2	280.3	318.3	356.3	394.3	422.4	440.5	458.4	476.4	494.4	491.7
120°	441.3	463.0	484.7	506.4	528.1	538.1	536.1	534.2	532.3	530.3	527.4
122.5°	550.7	554.9	559.1	563.4	567.6	569.1	567.9	566.8	565.6	564.5	561.3
125°	618.6	618.1	617.6	617.1	616.6	615.8	614.7	613.6	612.5	611.3	608.3
127.5°	661.4	661.3	661.2	661.2	661.0	660.2	658.5	656.9	655.2	653.6	651.3
130°	688.0	688.2	688.3	688.6	688.7	687.9	686.1	684.4	682.5	680.8	679.1
132.5°	714.1	714.2	714.4	714.5	714.7	714.1	712.6	711.1	709.6	708.0	706.2
135°	751.7	752.0	752.3	752.7	753.0	752.3	750.8	749.2	747.5	745.9	744.5
137.5°	786.0	786.6	787.1	787.7	788.2	787.7	786.1	784.5	782.9	781.4	779.7
140°	807.4	808.3	809.1	809.8	810.6	810.3	808.9	807.4	806.0	804.5	802.8
142.5°	828.2	829.1	829.9	830.7	831.5	831.2	829.9	828.5	827.3	825.9	823.9
145°	857.4	858.2	859.0	859.8	860.5	860.4	859.3	858.2	857.0	855.9	853.2
147.5°	883.0	883.6	884.3	884.9	885.7	885.6	884.7	883.9	883.0	882.3	879.6
150°	898.6	899.4	900.2	901.0	901.8	901.7	900.8	899.8	898.8	897.9	895.3
152.5°	911.9	913.0	914.0	915.0	916.2	916.2	915.2	914.3	913.3	912.4	909.9
155°	930.4	931.7	933.0	934.3	935.6	935.7	934.8	933.8	932.8	931.8	929.9
157.5°	947.4	948.6	949.8	951.1	952.4	952.4	951.3	950.2	949.2	948.1	946.7
160°	957.2	958.3	959.4	960.5	961.7	961.8	960.8	959.8	958.9	957.9	957.0
162.5°	965.3	966.7	968.0	969.5	970.8	971.0	969.9	968.8	967.7	966.6	965.7
165°	977.5	978.6	979.7	980.8	981.9	981.9	980.8	979.7	978.6	977.5	977.0
167.5°	985.1	986.6	988.0	989.4	990.9	991.1	989.9	988.8	987.7	986.6	986.1
170°	989.8	991.2	992.6	994.1	995.5	995.7	994.6	993.5	992.3	991.2	990.9
172.5°	993.2	994.7	996.1	997.5	999.0	999.2	998.1	996.9	995.8	994.7	994.3
175°	996.2	997.8	999.5	1001.1	1002.7	1002.9	1001.8	1000.7	999.6	998.4	998.1
177.5°	998.1	999.3	1000.4	1001.6	1002.7	1002.9	1002.0	1001.1	1000.2	999.3	999.2
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1403.5	1400.1	1398.0	1390.4	1383.7	1377.0	1374.9	1375.7	1366.5	1357.6	1353.8
5°	1458.2	1447.6	1437.7	1423.5	1406.7	1388.2	1378.8	1371.4	1353.0	1333.1	1321.5
7.5°	1507.1	1492.1	1472.9	1446.2	1421.7	1392.7	1374.4	1358.0	1331.2	1303.0	1285.7
10°	1537.0	1516.5	1491.8	1459.2	1429.3	1394.0	1369.3	1344.7	1313.0	1279.5	1258.4
12.5°	1562.7	1535.0	1510.7	1468.9	1433.5	1389.4	1360.1	1325.2	1292.0	1252.1	1231.5
15°	1623.7	1572.7	1526.5	1479.2	1435.5	1374.0	1341.5	1294.7	1251.0	1201.7	1178.0
17.5°	1671.0	1613.7	1540.8	1480.7	1429.7	1361.7	1313.8	1257.7	1206.2	1149.7	1117.5
20°	1697.9	1632.1	1553.8	1482.3	1421.3	1343.5	1291.5	1234.2	1173.8	1110.2	1075.5
22.5°	1713.8	1644.7	1567.3	1476.0	1404.5	1328.8	1263.4	1200.6	1139.3	1070.6	1034.3
25°	1718.9	1655.8	1573.8	1470.8	1383.5	1297.8	1219.0	1158.0	1083.9	1019.8	966.7
27.5°	1693.8	1648.6	1569.8	1460.9	1359.2	1259.0	1171.2	1102.1	1023.9	954.3	900.9
30°	1663.2	1636.9	1560.1	1450.8	1339.9	1232.2	1135.4	1057.1	979.3	908.9	854.2
32.5°	1615.7	1610.0	1542.5	1436.5	1319.3	1198.1	1098.0	1018.8	932.6	863.4	811.3
35°	1522.3	1547.5	1504.9	1404.5	1280.5	1149.6	1041.3	950.9	861.6	795.3	746.4
37.5°	1397.2	1459.8	1448.7	1357.7	1228.1	1096.9	977.3	882.8	797.6	730.8	682.8
40°	1311.0	1390.8	1402.4	1322.0	1191.1	1056.1	929.4	835.3	752.2	691.3	642.9
42.5°	1218.5	1311.8	1343.5	1279.1	1150.7	1013.1	886.5	789.0	706.8	647.5	604.6
45°	1063.4	1186.9	1244.2	1207.4	1083.4	942.5	812.1	713.3	638.7	583.0	549.9
47.5°	918.4	1053.4	1130.4	1117.5	1008.4	868.9	740.0	645.2	572.5	528.1	498.4
50°	815.8	954.6	1047.6	1051.9	954.6	816.3	687.1	597.7	530.9	489.4	465.2
52.5°	726.7	859.1	960.6	982.9	894.5	761.7	639.5	550.6	491.8	453.6	432.0
55°	610.3	722.2	834.7	875.8	804.8	678.6	565.6	487.3	432.1	405.8	386.9
57.5°	507.4	600.7	704.6	749.9	706.2	598.2	492.2	424.2	379.4	356.4	341.9
60°	453.1	526.7	619.2	673.4	635.5	539.3	446.8	382.1	345.4	324.9	311.2
62.5°	402.7	467.9	546.1	595.6	575.0	484.3	401.4	344.3	312.5	293.3	283.4
65°	332.2	383.7	444.2	489.9	476.3	407.3	339.6	290.7	265.5	250.2	242.3
67.5°	273.5	310.8	352.7	392.8	381.8	333.0	278.5	240.4	221.7	208.5	203.7
70°	236.5	264.9	302.2	334.3	325.3	285.4	242.3	209.8	193.5	182.4	177.7
72.5°	201.2	224.6	253.0	279.2	273.2	240.0	204.1	179.4	166.9	156.8	152.9
75°	151.9	169.8	187.1	204.5	202.9	177.1	156.1	137.2	127.2	119.3	117.7
77.5°	112.2	122.2	134.0	144.3	141.4	126.7	110.2	99.3	92.0	86.7	85.9
80°	85.7	91.5	99.9	107.3	103.5	97.3	84.1	76.2	71.0	65.7	63.6
82.5°	62.1	67.9	73.0	76.9	74.1	68.2	60.1	54.7	51.7	48.0	47.2
85°	32.6	35.7	37.9	38.9	37.9	34.1	30.5	28.4	25.7	24.2	23.7
87.5°	15.0	14.7	14.5	15.1	13.4	13.1	11.0	9.4	9.3	9.3	8.8
90°	11.9	10.6	9.3	7.8	6.0	4.3	2.5	0.7	2.5	4.3	6.0
92.5°	15.5	14.9	14.2	13.9	14.1	14.3	14.4	14.6	14.4	14.3	14.1
95°	26.0	24.9	23.7	25.8	31.1	36.4	41.7	47.1	41.7	36.4	31.1
97.5°	32.6	29.9	27.3	33.5	48.5	63.5	78.3	93.3	78.3	63.5	48.5
100°	35.8	33.0	30.3	39.9	61.9	84.0	106.0	128.1	106.0	84.0	61.9
102.5°	88.1	111.0	133.9	147.6	152.3	156.9	161.6	166.3	161.6	156.9	152.3
105°	131.9	175.8	219.7	239.2	234.4	229.6	224.7	219.9	224.7	229.6	234.4
107.5°	167.1	219.7	272.4	296.8	292.8	288.9	285.0	281.1	285.0	288.9	292.8
110°	219.5	266.0	312.4	334.0	330.7	327.3	323.9	320.5	323.9	327.3	330.7



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	342.3	353.8	365.3	369.5	366.5	363.5	360.5	357.5	360.5	363.5	366.5
115°	438.4	434.4	430.3	426.9	424.2	421.4	418.7	416.0	418.7	421.4	424.2
117.5°	488.9	486.2	483.4	480.5	477.4	474.4	471.3	468.3	471.3	474.4	477.4
120°	524.5	521.7	518.7	516.1	513.7	511.3	508.8	506.4	508.8	511.3	513.7
122.5°	558.2	555.0	551.8	549.0	546.4	543.9	541.4	538.8	541.4	543.9	546.4
125°	605.2	602.2	599.1	596.6	594.5	592.4	590.3	588.2	590.3	592.4	594.5
127.5°	649.0	646.7	644.4	642.1	639.8	637.5	635.3	632.9	635.3	637.5	639.8
130°	677.2	675.5	673.8	671.5	669.0	666.4	663.8	661.3	663.8	666.4	669.0
132.5°	704.5	702.7	700.9	698.9	696.8	694.6	692.4	690.2	692.4	694.6	696.8
135°	743.1	741.6	740.1	738.2	735.5	733.0	730.4	727.9	730.4	733.0	735.5
137.5°	778.1	776.4	774.8	773.1	771.3	769.5	767.7	765.9	767.7	769.5	771.3
140°	801.0	799.2	797.5	795.9	794.6	793.4	792.1	790.8	792.1	793.4	794.6
142.5°	821.9	819.8	817.8	816.3	815.1	814.0	812.8	811.6	812.8	814.0	815.1
145°	850.4	847.7	844.9	843.7	843.8	844.0	844.1	844.3	844.1	844.0	843.8
147.5°	876.9	874.1	871.4	870.4	871.0	871.6	872.2	872.8	872.2	871.6	871.0
150°	892.7	890.2	887.6	886.8	888.0	889.1	890.3	891.4	890.3	889.1	888.0
152.5°	907.4	905.0	902.5	902.0	903.2	904.4	905.7	907.0	905.7	904.4	903.2
155°	928.0	926.1	924.2	923.9	925.3	926.8	928.3	929.7	928.3	926.8	925.3
157.5°	945.4	944.0	942.7	942.6	943.8	945.1	946.3	947.5	946.3	945.1	943.8
160°	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9	957.0	956.0	955.0
162.5°	964.9	964.1	963.2	963.3	964.2	965.3	966.2	967.2	966.2	965.3	964.2
165°	976.4	976.0	975.5	975.7	976.7	977.7	978.7	979.6	978.7	977.7	976.7
167.5°	985.6	985.2	984.8	985.0	986.0	987.0	987.9	988.9	987.9	987.0	986.0
170°	990.5	990.2	989.9	990.2	991.2	992.1	993.1	994.1	993.1	992.1	991.2
172.5°	994.0	993.7	993.4	993.7	994.7	995.6	996.6	997.5	996.6	995.6	994.7
175°	997.8	997.4	997.1	997.5	998.6	999.8	1000.9	1002.0	1000.9	999.8	998.6
177.5°	999.0	998.9	998.8	999.2	1000.1	1001.0	1001.9	1002.7	1001.9	1001.0	1000.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1349.6	1347.1	1338.3	1333.7	1326.1	1319.0	1314.3	1316.4	1318.1	1317.2	1316.1
5°	1311.0	1301.0	1285.7	1272.6	1263.1	1245.8	1238.4	1234.8	1231.6	1227.9	1224.2
7.5°	1265.0	1249.2	1227.2	1208.6	1190.9	1169.3	1157.1	1149.7	1142.2	1133.9	1126.5
10°	1232.2	1210.1	1186.9	1160.6	1139.6	1120.1	1102.8	1091.2	1080.8	1070.7	1063.4
12.5°	1197.6	1172.2	1143.6	1107.6	1084.5	1056.7	1054.0	1033.6	1017.2	1011.1	1002.4
15°	1142.8	1107.0	1070.7	1028.2	1009.8	984.5	968.8	953.0	938.8	928.8	926.2
17.5°	1080.5	1034.2	998.1	967.5	937.3	911.5	897.0	884.4	872.7	859.4	857.5
20°	1032.9	992.9	953.5	926.7	895.7	869.4	851.5	838.9	828.9	821.1	814.2
22.5°	987.9	944.2	908.1	878.8	848.2	827.0	812.9	800.7	792.3	783.6	777.2
25°	915.7	881.5	842.1	809.0	783.7	770.1	758.5	748.0	742.8	737.0	729.6
27.5°	852.5	814.5	777.7	752.0	729.8	717.7	709.6	702.3	697.4	694.0	689.8
30°	807.9	769.5	740.6	715.4	697.0	684.9	679.7	675.5	669.7	667.6	665.5
32.5°	765.0	730.5	705.8	683.9	666.3	658.5	653.6	649.8	645.3	643.2	639.0
35°	704.4	675.5	651.3	639.2	625.0	618.1	614.5	609.3	605.0	602.9	602.4
37.5°	647.3	622.2	606.3	590.7	584.7	580.5	575.5	571.9	570.6	570.3	569.8
40°	610.3	589.8	575.6	563.0	560.3	554.1	549.9	546.7	546.7	547.2	546.7
42.5°	576.6	558.3	545.7	534.8	531.7	528.0	523.8	523.6	524.4	526.2	524.4
45°	525.6	512.5	503.6	498.3	492.5	488.9	488.3	489.9	490.4	491.0	492.5
47.5°	478.8	470.0	461.9	456.1	453.6	453.0	452.3	455.1	457.6	458.6	461.0
50°	451.0	441.0	434.2	430.5	428.4	427.4	428.4	431.6	433.6	436.3	437.8
52.5°	419.9	412.8	408.1	405.3	404.4	405.0	405.3	408.8	412.3	413.1	413.9
55°	376.9	371.6	370.6	365.8	368.0	367.4	370.0	372.2	375.3	378.5	379.0
57.5°	334.0	329.8	326.9	327.4	328.0	330.3	332.6	336.2	339.6	342.9	343.3
60°	305.4	303.3	301.7	301.7	302.8	305.9	308.6	312.2	314.3	316.5	318.0
62.5°	279.3	277.3	275.7	276.5	279.2	281.1	284.2	286.1	288.3	290.3	291.1
65°	238.1	237.1	238.7	239.7	240.2	242.9	246.5	248.1	250.2	251.3	254.9
67.5°	200.2	200.3	200.2	201.6	204.7	205.3	208.8	212.5	212.9	214.9	217.3
70°	174.5	175.5	176.7	177.7	180.3	181.3	183.9	185.5	187.7	189.3	190.8
72.5°	151.0	151.1	152.3	152.0	154.2	156.5	158.8	160.3	162.4	164.5	166.0
75°	116.1	116.1	117.2	117.7	120.4	123.0	122.5	123.5	125.6	127.7	128.8
77.5°	84.8	83.7	84.8	85.4	86.2	88.4	88.8	90.3	92.7	92.0	93.2
80°	64.6	63.1	64.6	65.2	65.2	67.8	67.8	68.8	70.4	68.8	70.4
82.5°	46.2	45.4	46.6	46.7	47.5	47.6	48.5	48.6	50.2	49.5	50.2
85°	23.1	22.6	23.1	22.6	23.1	23.7	23.7	23.1	23.1	24.2	22.6
87.5°	8.7	8.6	8.4	8.7	8.6	8.4	8.1	8.2	8.4	7.8	7.8
90°	7.8	9.3	10.6	11.9	13.2	14.5	15.3	16.1	16.9	17.7	18.2
92.5°	13.9	14.2	14.9	15.5	16.2	16.8	17.2	17.6	18.1	18.5	18.8
95°	25.8	23.7	24.9	26.0	27.1	28.2	29.0	29.8	30.7	31.4	31.8
97.5°	33.5	27.3	29.9	32.6	35.2	37.8	38.4	39.1	39.7	40.3	40.7
100°	39.9	30.3	33.0	35.8	38.5	41.3	42.5	43.8	45.1	46.4	47.2
102.5°	147.6	133.9	111.0	88.1	65.3	42.4	44.0	45.7	47.5	49.1	50.1
105°	239.2	219.7	175.8	131.9	88.0	44.1	45.9	47.7	49.4	51.2	52.4
107.5°	296.8	272.4	219.7	167.1	114.4	61.8	60.0	58.1	56.4	54.6	54.0
110°	334.0	312.4	266.0	219.5	173.1	126.6	110.5	94.4	78.3	62.3	54.6



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	369.5	365.3	353.8	342.3	330.8	319.3	260.7	202.1	143.4	84.8	55.7
115°	426.9	430.3	434.4	438.4	442.4	446.4	371.9	297.5	223.1	148.6	105.6
117.5°	480.5	483.4	486.2	488.9	491.7	494.4	476.4	458.4	440.5	422.4	394.3
120°	516.1	518.7	521.7	524.5	527.4	530.3	532.3	534.2	536.1	538.1	528.1
122.5°	549.0	551.8	555.0	558.2	561.3	564.5	565.6	566.8	567.9	569.1	567.6
125°	596.6	599.1	602.2	605.2	608.3	611.3	612.5	613.6	614.7	615.8	616.6
127.5°	642.1	644.4	646.7	649.0	651.3	653.6	655.2	656.9	658.5	660.2	661.0
130°	671.5	673.8	675.5	677.2	679.1	680.8	682.5	684.4	686.1	687.9	688.7
132.5°	698.9	700.9	702.7	704.5	706.2	708.0	709.6	711.1	712.6	714.1	714.7
135°	738.2	740.1	741.6	743.1	744.5	745.9	747.5	749.2	750.8	752.3	753.0
137.5°	773.1	774.8	776.4	778.1	779.7	781.4	782.9	784.5	786.1	787.7	788.2
140°	795.9	797.5	799.2	801.0	802.8	804.5	806.0	807.4	808.9	810.3	810.6
142.5°	816.3	817.8	819.8	821.9	823.9	825.9	827.3	828.5	829.9	831.2	831.5
145°	843.7	844.9	847.7	850.4	853.2	855.9	857.0	858.2	859.3	860.4	860.5
147.5°	870.4	871.4	874.1	876.9	879.6	882.3	883.0	883.9	884.7	885.6	885.7
150°	886.8	887.6	890.2	892.7	895.3	897.9	898.8	899.8	900.8	901.7	901.8
152.5°	902.0	902.5	905.0	907.4	909.9	912.4	913.3	914.3	915.2	916.2	916.2
155°	923.9	924.2	926.1	928.0	929.9	931.8	932.8	933.8	934.8	935.7	935.6
157.5°	942.6	942.7	944.0	945.4	946.7	948.1	949.2	950.2	951.3	952.4	952.4
160°	954.0	954.0	955.0	956.0	957.0	957.9	958.9	959.8	960.8	961.8	961.7
162.5°	963.3	963.2	964.1	964.9	965.7	966.6	967.7	968.8	969.9	971.0	970.8
165°	975.7	975.5	976.0	976.4	977.0	977.5	978.6	979.7	980.8	981.9	981.9
167.5°	985.0	984.8	985.2	985.6	986.1	986.6	987.7	988.8	989.9	991.1	990.9
170°	990.2	989.9	990.2	990.5	990.9	991.2	992.3	993.5	994.6	995.7	995.5
172.5°	993.7	993.4	993.7	994.0	994.3	994.7	995.8	996.9	998.1	999.2	999.0
175°	997.5	997.1	997.4	997.8	998.1	998.4	999.6	1000.7	1001.8	1002.9	1002.7
177.5°	999.2	998.8	998.9	999.0	999.2	999.3	1000.2	1001.1	1002.0	1002.9	1002.7
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1311.8	1311.0	1311.0	1307.2	1311.0	1311.0	1311.8	1316.1	1317.2	1318.1	1316.4
5°	1216.9	1215.3	1212.7	1215.3	1212.7	1215.3	1216.9	1224.2	1227.9	1231.6	1234.8
7.5°	1123.0	1116.7	1115.7	1109.5	1115.7	1116.7	1123.0	1126.5	1133.9	1142.2	1149.7
10°	1054.5	1050.3	1049.7	1039.7	1049.7	1050.3	1054.5	1063.4	1070.7	1080.8	1091.2
12.5°	1002.3	992.2	994.2	988.4	994.2	992.2	1002.3	1002.4	1011.1	1017.2	1033.6
15°	912.0	912.0	909.9	900.9	909.9	912.0	912.0	926.2	928.8	938.8	953.0
17.5°	847.2	846.1	841.1	843.6	841.1	846.1	847.2	857.5	859.4	872.7	884.4
20°	808.4	805.3	799.0	799.0	799.0	805.3	808.4	814.2	821.1	828.9	838.9
22.5°	771.9	771.7	764.9	767.0	764.9	771.7	771.9	777.2	783.6	792.3	800.7
25°	729.0	724.8	721.8	723.3	721.8	724.8	729.0	729.6	737.0	742.8	748.0
27.5°	688.5	686.2	686.0	681.7	686.0	686.2	688.5	689.8	694.0	697.4	702.3
30°	665.0	659.7	660.8	658.1	660.8	659.7	665.0	665.5	667.6	669.7	675.5
32.5°	638.0	636.1	635.1	632.9	635.1	636.1	638.0	639.0	643.2	645.3	649.8
35°	601.3	601.9	599.2	600.3	599.2	601.9	601.3	602.4	602.9	605.0	609.3
37.5°	569.3	570.9	569.7	570.1	569.7	570.9	569.3	569.8	570.3	570.6	571.9
40°	548.3	548.3	548.3	549.9	548.3	548.3	548.3	546.7	547.2	546.7	546.7
42.5°	528.1	527.2	526.4	526.2	526.4	527.2	528.1	524.4	526.2	524.4	523.6
45°	493.6	495.2	495.7	493.1	495.7	495.2	493.6	492.5	491.0	490.4	489.9
47.5°	462.4	462.6	462.4	464.7	462.4	462.6	462.4	461.0	458.6	457.6	455.1
50°	440.5	439.4	440.5	439.4	440.5	439.4	440.5	437.8	436.3	433.6	431.6
52.5°	417.4	417.6	416.9	416.8	416.9	417.6	417.4	413.9	413.1	412.3	408.8
55°	381.1	382.1	381.6	381.6	381.6	382.1	381.1	379.0	378.5	375.3	372.2
57.5°	343.6	344.5	345.2	342.9	345.2	344.5	343.6	343.3	342.9	339.6	336.2
60°	317.5	320.1	319.6	318.5	319.6	320.1	317.5	318.0	316.5	314.3	312.2
62.5°	293.5	294.5	294.4	294.1	294.4	294.5	293.5	291.1	290.3	288.3	286.1
65°	256.5	257.5	256.0	257.5	256.0	257.5	256.5	254.9	251.3	250.2	248.1
67.5°	216.7	217.0	218.2	218.9	218.2	217.0	216.7	217.3	214.9	212.9	212.5
70°	191.9	191.3	192.9	194.5	192.9	191.3	191.9	190.8	189.3	187.7	185.5
72.5°	165.8	166.9	166.4	167.5	166.4	166.9	165.8	166.0	164.5	162.4	160.3
75°	127.7	129.3	128.8	130.4	128.8	129.3	127.7	128.8	127.7	125.6	123.5
77.5°	92.3	92.5	92.3	93.2	92.3	92.5	92.3	93.2	92.0	92.7	90.3
80°	70.4	69.4	68.4	70.4	68.4	69.4	70.4	70.4	68.8	70.4	68.8
82.5°	49.0	49.6	48.6	48.6	48.6	49.6	49.0	50.2	49.5	50.2	48.6
85°	22.6	22.1	21.0	21.0	21.0	22.1	22.6	22.6	24.2	23.1	23.1
87.5°	7.9	7.5	7.6	7.3	7.6	7.5	7.9	7.8	7.8	8.4	8.2
90°	18.5	18.9	19.3	19.6	19.3	18.9	18.5	18.2	17.7	16.9	16.1
92.5°	18.9	19.2	19.3	19.6	19.3	19.2	18.9	18.8	18.5	18.1	17.6
95°	31.6	31.4	31.3	31.1	31.3	31.4	31.6	31.8	31.4	30.7	29.8
97.5°	41.0	41.1	41.4	41.5	41.4	41.1	41.0	40.7	40.3	39.7	39.1
100°	47.5	47.8	48.2	48.5	48.2	47.8	47.5	47.2	46.4	45.1	43.8
102.5°	50.6	51.0	51.5	52.0	51.5	51.0	50.6	50.1	49.1	47.5	45.7
105°	53.1	53.7	54.3	55.0	54.3	53.7	53.1	52.4	51.2	49.4	47.7
107.5°	54.7	55.3	55.9	56.6	55.9	55.3	54.7	54.0	54.6	56.4	58.1
110°	55.2	55.8	56.5	57.2	56.5	55.8	55.2	54.6	62.3	78.3	94.4



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	56.2	56.7	57.2	57.8	57.2	56.7	56.2	55.7	84.8	143.4	202.1
115°	94.0	82.5	70.9	59.3	70.9	82.5	94.0	105.6	148.6	223.1	297.5
117.5°	356.3	318.3	280.3	242.2	280.3	318.3	356.3	394.3	422.4	440.5	458.4
120°	506.4	484.7	463.0	441.3	463.0	484.7	506.4	528.1	538.1	536.1	534.2
122.5°	563.4	559.1	554.9	550.7	554.9	559.1	563.4	567.6	569.1	567.9	566.8
125°	617.1	617.6	618.1	618.6	618.1	617.6	617.1	616.6	615.8	614.7	613.6
127.5°	661.2	661.2	661.3	661.4	661.3	661.2	661.2	661.0	660.2	658.5	656.9
130°	688.6	688.3	688.2	688.0	688.2	688.3	688.6	688.7	687.9	686.1	684.4
132.5°	714.5	714.4	714.2	714.1	714.2	714.4	714.5	714.7	714.1	712.6	711.1
135°	752.7	752.3	752.0	751.7	752.0	752.3	752.7	753.0	752.3	750.8	749.2
137.5°	787.7	787.1	786.6	786.0	786.6	787.1	787.7	788.2	787.7	786.1	784.5
140°	809.8	809.1	808.3	807.4	808.3	809.1	809.8	810.6	810.3	808.9	807.4
142.5°	830.7	829.9	829.1	828.2	829.1	829.9	830.7	831.5	831.2	829.9	828.5
145°	859.8	859.0	858.2	857.4	858.2	859.0	859.8	860.5	860.4	859.3	858.2
147.5°	884.9	884.3	883.6	883.0	883.6	884.3	884.9	885.7	885.6	884.7	883.9
150°	901.0	900.2	899.4	898.6	899.4	900.2	901.0	901.8	901.7	900.8	899.8
152.5°	915.0	914.0	913.0	911.9	913.0	914.0	915.0	916.2	916.2	915.2	914.3
155°	934.3	933.0	931.7	930.4	931.7	933.0	934.3	935.6	935.7	934.8	933.8
157.5°	951.1	949.8	948.6	947.4	948.6	949.8	951.1	952.4	952.4	951.3	950.2
160°	960.5	959.4	958.3	957.2	958.3	959.4	960.5	961.7	961.8	960.8	959.8
162.5°	969.5	968.0	966.7	965.3	966.7	968.0	969.5	970.8	971.0	969.9	968.8
165°	980.8	979.7	978.6	977.5	978.6	979.7	980.8	981.9	981.9	980.8	979.7
167.5°	989.4	988.0	986.6	985.1	986.6	988.0	989.4	990.9	991.1	989.9	988.8
170°	994.1	992.6	991.2	989.8	991.2	992.6	994.1	995.5	995.7	994.6	993.5
172.5°	997.5	996.1	994.7	993.2	994.7	996.1	997.5	999.0	999.2	998.1	996.9
175°	1001.1	999.5	997.8	996.2	997.8	999.5	1001.1	1002.7	1002.9	1001.8	1000.7
177.5°	1001.6	1000.4	999.3	998.1	999.3	1000.4	1001.6	1002.7	1002.9	1002.0	1001.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331402-927
 CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1314.3	1319.0	1326.1	1333.7	1338.3	1347.1	1349.6	1353.8	1357.6	1366.5	1375.7
5°	1238.4	1245.8	1263.1	1272.6	1285.7	1301.0	1311.0	1321.5	1333.1	1353.0	1371.4
7.5°	1157.1	1169.3	1190.9	1208.6	1227.2	1249.2	1265.0	1285.7	1303.0	1331.2	1358.0
10°	1102.8	1120.1	1139.6	1160.6	1186.9	1210.1	1232.2	1258.4	1279.5	1313.0	1344.7
12.5°	1054.0	1056.7	1084.5	1107.6	1143.6	1172.2	1197.6	1231.5	1252.1	1292.0	1325.2
15°	968.8	984.5	1009.8	1028.2	1070.7	1107.0	1142.8	1178.0	1201.7	1251.0	1294.7
17.5°	897.0	911.5	937.3	967.5	998.1	1034.2	1080.5	1117.5	1149.7	1206.2	1257.7
20°	851.5	869.4	895.7	926.7	953.5	992.9	1032.9	1075.5	1110.2	1173.8	1234.2
22.5°	812.9	827.0	848.2	878.8	908.1	944.2	987.9	1034.3	1070.6	1139.3	1200.6
25°	758.5	770.1	783.7	809.0	842.1	881.5	915.7	966.7	1019.8	1083.9	1158.0
27.5°	709.6	717.7	729.8	752.0	777.7	814.5	852.5	900.9	954.3	1023.9	1102.1
30°	679.7	684.9	697.0	715.4	740.6	769.5	807.9	854.2	908.9	979.3	1057.1
32.5°	653.6	658.5	666.3	683.9	705.8	730.5	765.0	811.3	863.4	932.6	1018.8
35°	614.5	618.1	625.0	639.2	651.3	675.5	704.4	746.4	795.3	861.6	950.9
37.5°	575.5	580.5	584.7	590.7	606.3	622.2	647.3	682.8	730.8	797.6	882.8
40°	549.9	554.1	560.3	563.0	575.6	589.8	610.3	642.9	691.3	752.2	835.3
42.5°	523.8	528.0	531.7	534.8	545.7	558.3	576.6	604.6	647.5	706.8	789.0
45°	488.3	488.9	492.5	498.3	503.6	512.5	525.6	549.9	583.0	638.7	713.3
47.5°	452.3	453.0	453.6	456.1	461.9	470.0	478.8	498.4	528.1	572.5	645.2
50°	428.4	427.4	428.4	430.5	434.2	441.0	451.0	465.2	489.4	530.9	597.7
52.5°	405.3	405.0	404.4	405.3	408.1	412.8	419.9	432.0	453.6	491.8	550.6
55°	370.0	367.4	368.0	365.8	370.6	371.6	376.9	386.9	405.8	432.1	487.3
57.5°	332.6	330.3	328.0	327.4	326.9	329.8	334.0	341.9	356.4	379.4	424.2
60°	308.6	305.9	302.8	301.7	301.7	303.3	305.4	311.2	324.9	345.4	382.1
62.5°	284.2	281.1	279.2	276.5	275.7	277.3	279.3	283.4	293.3	312.5	344.3
65°	246.5	242.9	240.2	239.7	238.7	237.1	238.1	242.3	250.2	265.5	290.7
67.5°	208.8	205.3	204.7	201.6	200.2	200.3	200.2	203.7	208.5	221.7	240.4
70°	183.9	181.3	180.3	177.7	176.7	175.5	174.5	177.7	182.4	193.5	209.8
72.5°	158.8	156.5	154.2	152.0	152.3	151.1	151.0	152.9	156.8	166.9	179.4
75°	122.5	123.0	120.4	117.7	117.2	116.1	116.1	117.7	119.3	127.2	137.2
77.5°	88.8	88.4	86.2	85.4	84.8	83.7	84.8	85.9	86.7	92.0	99.3
80°	67.8	67.8	65.2	65.2	64.6	63.1	64.6	63.6	65.7	71.0	76.2
82.5°	48.5	47.6	47.5	46.7	46.6	45.4	46.2	47.2	48.0	51.7	54.7
85°	23.7	23.7	23.1	22.6	23.1	22.6	23.1	23.7	24.2	25.7	28.4
87.5°	8.1	8.4	8.6	8.7	8.4	8.6	8.7	8.8	9.3	9.3	9.4
90°	15.3	14.5	13.2	11.9	10.6	9.3	7.8	6.0	4.3	2.5	0.7
92.5°	17.2	16.8	16.2	15.5	14.9	14.2	13.9	14.1	14.3	14.4	14.6
95°	29.0	28.2	27.1	26.0	24.9	23.7	25.8	31.1	36.4	41.7	47.1
97.5°	38.4	37.8	35.2	32.6	29.9	27.3	33.5	48.5	63.5	78.3	93.3
100°	42.5	41.3	38.5	35.8	33.0	30.3	39.9	61.9	84.0	106.0	128.1
102.5°	44.0	42.4	65.3	88.1	111.0	133.9	147.6	152.3	156.9	161.6	166.3
105°	45.9	44.1	88.0	131.9	175.8	219.7	239.2	234.4	229.6	224.7	219.9
107.5°	60.0	61.8	114.4	167.1	219.7	272.4	296.8	292.8	288.9	285.0	281.1
110°	110.5	126.6	173.1	219.5	266.0	312.4	334.0	330.7	327.3	323.9	320.5



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.7	319.3	330.8	342.3	353.8	365.3	369.5	366.5	363.5	360.5	357.5
115°	371.9	446.4	442.4	438.4	434.4	430.3	426.9	424.2	421.4	418.7	416.0
117.5°	476.4	494.4	491.7	488.9	486.2	483.4	480.5	477.4	474.4	471.3	468.3
120°	532.3	530.3	527.4	524.5	521.7	518.7	516.1	513.7	511.3	508.8	506.4
122.5°	565.6	564.5	561.3	558.2	555.0	551.8	549.0	546.4	543.9	541.4	538.8
125°	612.5	611.3	608.3	605.2	602.2	599.1	596.6	594.5	592.4	590.3	588.2
127.5°	655.2	653.6	651.3	649.0	646.7	644.4	642.1	639.8	637.5	635.3	632.9
130°	682.5	680.8	679.1	677.2	675.5	673.8	671.5	669.0	666.4	663.8	661.3
132.5°	709.6	708.0	706.2	704.5	702.7	700.9	698.9	696.8	694.6	692.4	690.2
135°	747.5	745.9	744.5	743.1	741.6	740.1	738.2	735.5	733.0	730.4	727.9
137.5°	782.9	781.4	779.7	778.1	776.4	774.8	773.1	771.3	769.5	767.7	765.9
140°	806.0	804.5	802.8	801.0	799.2	797.5	795.9	794.6	793.4	792.1	790.8
142.5°	827.3	825.9	823.9	821.9	819.8	817.8	816.3	815.1	814.0	812.8	811.6
145°	857.0	855.9	853.2	850.4	847.7	844.9	843.7	843.8	844.0	844.1	844.3
147.5°	883.0	882.3	879.6	876.9	874.1	871.4	870.4	871.0	871.6	872.2	872.8
150°	898.8	897.9	895.3	892.7	890.2	887.6	886.8	888.0	889.1	890.3	891.4
152.5°	913.3	912.4	909.9	907.4	905.0	902.5	902.0	903.2	904.4	905.7	907.0
155°	932.8	931.8	929.9	928.0	926.1	924.2	923.9	925.3	926.8	928.3	929.7
157.5°	949.2	948.1	946.7	945.4	944.0	942.7	942.6	943.8	945.1	946.3	947.5
160°	958.9	957.9	957.0	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9
162.5°	967.7	966.6	965.7	964.9	964.1	963.2	963.3	964.2	965.3	966.2	967.2
165°	978.6	977.5	977.0	976.4	976.0	975.5	975.7	976.7	977.7	978.7	979.6
167.5°	987.7	986.6	986.1	985.6	985.2	984.8	985.0	986.0	987.0	987.9	988.9
170°	992.3	991.2	990.9	990.5	990.2	989.9	990.2	991.2	992.1	993.1	994.1
172.5°	995.8	994.7	994.3	994.0	993.7	993.4	993.7	994.7	995.6	996.6	997.5
175°	999.6	998.4	998.1	997.8	997.4	997.1	997.5	998.6	999.8	1000.9	1002.0
177.5°	1000.2	999.3	999.2	999.0	998.9	998.8	999.2	1000.1	1001.0	1001.9	1002.7
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1374.9	1377.0	1383.7	1390.4	1398.0	1400.1	1403.5	1400.6	1399.7	1407.7	1413.6
5°	1378.8	1388.2	1406.7	1423.5	1437.7	1447.6	1458.2	1462.4	1470.2	1481.3	1494.9
7.5°	1374.4	1392.7	1421.7	1446.2	1472.9	1492.1	1507.1	1520.0	1535.6	1556.5	1579.3
10°	1369.3	1394.0	1429.3	1459.2	1491.8	1516.5	1537.0	1557.0	1580.1	1609.0	1638.9
12.5°	1360.1	1389.4	1433.5	1468.9	1510.7	1535.0	1562.7	1605.8	1630.5	1670.9	1713.0
15°	1341.5	1374.0	1435.5	1479.2	1526.5	1572.7	1623.7	1664.8	1705.7	1729.4	1788.8
17.5°	1313.8	1361.7	1429.7	1480.7	1540.8	1613.7	1671.0	1717.4	1764.7	1803.1	1832.9
20°	1291.5	1343.5	1421.3	1482.3	1553.8	1632.1	1697.9	1745.2	1786.1	1818.2	1836.6
22.5°	1263.4	1328.8	1404.5	1476.0	1567.3	1644.7	1713.8	1751.0	1785.3	1800.9	1808.0
25°	1219.0	1297.8	1383.5	1470.8	1573.8	1655.8	1718.9	1741.5	1751.4	1736.2	1711.0
27.5°	1171.2	1259.0	1359.2	1460.9	1569.8	1648.6	1693.8	1690.3	1673.3	1624.1	1584.6
30°	1135.4	1232.2	1339.9	1450.8	1560.1	1636.9	1663.2	1636.9	1598.5	1543.3	1487.1
32.5°	1098.0	1198.1	1319.3	1436.5	1542.5	1610.0	1615.7	1570.4	1511.0	1448.3	1378.2
35°	1041.3	1149.6	1280.5	1404.5	1504.9	1547.5	1522.3	1442.4	1372.0	1286.3	1190.6
37.5°	977.3	1096.9	1228.1	1357.7	1448.7	1459.8	1397.2	1313.0	1213.7	1113.0	1000.4
40°	929.4	1056.1	1191.1	1322.0	1402.4	1390.8	1311.0	1218.5	1100.2	977.2	872.6
42.5°	886.5	1013.1	1150.7	1279.1	1343.5	1311.8	1218.5	1104.9	977.8	862.0	766.2
45°	812.1	942.5	1083.4	1207.4	1244.2	1186.9	1063.4	937.2	812.1	715.4	639.7
47.5°	740.0	868.9	1008.4	1117.5	1130.4	1053.4	918.4	788.6	681.0	602.3	548.9
50°	687.1	816.3	954.6	1051.9	1047.6	954.6	815.8	692.3	602.4	538.8	503.0
52.5°	639.5	761.7	894.5	982.9	960.6	859.1	726.7	617.0	543.1	493.4	461.0
55°	565.6	678.6	804.8	875.8	834.7	722.2	610.3	522.0	467.3	430.0	404.7
57.5°	492.2	598.2	706.2	749.9	704.6	600.7	507.4	443.3	402.2	374.5	358.1
60°	446.8	539.3	635.5	673.4	619.2	526.7	453.1	395.9	362.7	340.1	325.3
62.5°	401.4	484.3	575.0	595.6	546.1	467.9	402.7	355.1	327.8	307.7	293.8
65°	339.6	407.3	476.3	489.9	444.2	383.7	332.2	301.2	277.0	262.3	251.3
67.5°	278.5	333.0	381.8	392.8	352.7	310.8	273.5	246.5	230.1	217.9	208.6
70°	242.3	285.4	325.3	334.3	302.2	264.9	236.5	215.0	200.3	189.7	180.9
72.5°	204.1	240.0	273.2	279.2	253.0	224.6	201.2	184.3	171.3	164.5	156.0
75°	156.1	177.1	202.9	204.5	187.1	169.8	151.9	140.9	134.0	125.6	121.4
77.5°	110.2	126.7	141.4	144.3	134.0	122.2	112.2	103.5	97.7	93.8	89.9
80°	84.1	97.3	103.5	107.3	99.9	91.5	85.7	79.9	76.2	73.6	71.0
82.5°	60.1	68.2	74.1	76.9	73.0	67.9	62.1	58.9	56.0	53.8	52.9
85°	30.5	34.1	37.9	38.9	37.9	35.7	32.6	32.6	31.0	30.5	30.5
87.5°	11.0	13.1	13.4	15.1	14.5	14.7	15.0	14.8	14.7	14.4	14.2
90°	2.5	4.3	6.0	7.8	9.3	10.6	11.9	13.2	14.5	15.3	16.1
92.5°	14.4	14.3	14.1	13.9	14.2	14.9	15.5	16.2	16.8	17.2	17.6
95°	41.7	36.4	31.1	25.8	23.7	24.9	26.0	27.1	28.2	29.0	29.8
97.5°	78.3	63.5	48.5	33.5	27.3	29.9	32.6	35.2	37.8	38.4	39.1
100°	106.0	84.0	61.9	39.9	30.3	33.0	35.8	38.5	41.3	42.5	43.8
102.5°	161.6	156.9	152.3	147.6	133.9	111.0	88.1	65.3	42.4	44.0	45.7
105°	224.7	229.6	234.4	239.2	219.7	175.8	131.9	88.0	44.1	45.9	47.7
107.5°	285.0	288.9	292.8	296.8	272.4	219.7	167.1	114.4	61.8	60.0	58.1
110°	323.9	327.3	330.7	334.0	312.4	266.0	219.5	173.1	126.6	110.5	94.4



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	360.5	363.5	366.5	369.5	365.3	353.8	342.3	330.8	319.3	260.7	202.1
115°	418.7	421.4	424.2	426.9	430.3	434.4	438.4	442.4	446.4	371.9	297.5
117.5°	471.3	474.4	477.4	480.5	483.4	486.2	488.9	491.7	494.4	476.4	458.4
120°	508.8	511.3	513.7	516.1	518.7	521.7	524.5	527.4	530.3	532.3	534.2
122.5°	541.4	543.9	546.4	549.0	551.8	555.0	558.2	561.3	564.5	565.6	566.8
125°	590.3	592.4	594.5	596.6	599.1	602.2	605.2	608.3	611.3	612.5	613.6
127.5°	635.3	637.5	639.8	642.1	644.4	646.7	649.0	651.3	653.6	655.2	656.9
130°	663.8	666.4	669.0	671.5	673.8	675.5	677.2	679.1	680.8	682.5	684.4
132.5°	692.4	694.6	696.8	698.9	700.9	702.7	704.5	706.2	708.0	709.6	711.1
135°	730.4	733.0	735.5	738.2	740.1	741.6	743.1	744.5	745.9	747.5	749.2
137.5°	767.7	769.5	771.3	773.1	774.8	776.4	778.1	779.7	781.4	782.9	784.5
140°	792.1	793.4	794.6	795.9	797.5	799.2	801.0	802.8	804.5	806.0	807.4
142.5°	812.8	814.0	815.1	816.3	817.8	819.8	821.9	823.9	825.9	827.3	828.5
145°	844.1	844.0	843.8	843.7	844.9	847.7	850.4	853.2	855.9	857.0	858.2
147.5°	872.2	871.6	871.0	870.4	871.4	874.1	876.9	879.6	882.3	883.0	883.9
150°	890.3	889.1	888.0	886.8	887.6	890.2	892.7	895.3	897.9	898.8	899.8
152.5°	905.7	904.4	903.2	902.0	902.5	905.0	907.4	909.9	912.4	913.3	914.3
155°	928.3	926.8	925.3	923.9	924.2	926.1	928.0	929.9	931.8	932.8	933.8
157.5°	946.3	945.1	943.8	942.6	942.7	944.0	945.4	946.7	948.1	949.2	950.2
160°	957.0	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9	958.9	959.8
162.5°	966.2	965.3	964.2	963.3	963.2	964.1	964.9	965.7	966.6	967.7	968.8
165°	978.7	977.7	976.7	975.7	975.5	976.0	976.4	977.0	977.5	978.6	979.7
167.5°	987.9	987.0	986.0	985.0	984.8	985.2	985.6	986.1	986.6	987.7	988.8
170°	993.1	992.1	991.2	990.2	989.9	990.2	990.5	990.9	991.2	992.3	993.5
172.5°	996.6	995.6	994.7	993.7	993.4	993.7	994.0	994.3	994.7	995.8	996.9
175°	1000.9	999.8	998.6	997.5	997.1	997.4	997.8	998.1	998.4	999.6	1000.7
177.5°	1001.9	1001.0	1000.1	999.2	998.8	998.9	999.0	999.2	999.3	1000.2	1001.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331402-927
 CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7	1367.7
2.5°	1418.6	1424.5	1424.5	1425.4	1432.1	1431.2	1430.8
5°	1509.7	1518.6	1519.6	1529.1	1535.4	1533.3	1527.6
7.5°	1595.5	1612.2	1624.8	1631.8	1640.1	1645.3	1643.0
10°	1663.7	1687.8	1702.6	1712.5	1724.7	1733.6	1730.4
12.5°	1725.5	1754.3	1774.5	1791.6	1793.2	1804.7	1796.9
15°	1821.9	1852.4	1855.5	1868.1	1878.2	1877.1	1877.6
17.5°	1853.8	1863.5	1865.5	1865.8	1866.0	1862.3	1854.3
20°	1842.4	1838.7	1829.8	1823.0	1810.8	1809.3	1798.8
22.5°	1788.6	1776.9	1754.5	1739.7	1720.9	1715.9	1713.0
25°	1682.6	1656.8	1621.1	1586.9	1577.5	1559.1	1564.3
27.5°	1537.2	1497.1	1458.3	1430.6	1405.5	1377.9	1385.8
30°	1435.0	1389.8	1335.1	1293.1	1266.3	1240.0	1235.2
32.5°	1313.0	1246.8	1185.9	1148.8	1107.8	1091.2	1072.9
35°	1102.8	1038.2	977.7	925.7	895.7	872.6	851.5
37.5°	913.7	839.2	790.4	748.3	726.7	713.4	716.8
40°	796.4	731.2	695.5	663.4	643.4	633.9	636.0
42.5°	701.3	652.5	623.1	601.1	587.0	581.8	580.5
45°	593.4	566.1	541.9	529.3	522.5	516.7	513.0
47.5°	519.8	497.6	483.9	476.4	470.5	464.5	464.5
50°	475.7	461.0	451.5	443.6	438.9	434.7	438.4
52.5°	442.0	428.6	419.1	412.1	410.4	406.5	406.5
55°	392.1	381.6	374.8	368.4	365.4	363.2	360.6
57.5°	346.7	336.8	330.4	326.5	320.4	318.3	317.5
60°	314.3	306.4	300.2	294.9	292.2	288.0	288.0
62.5°	284.5	276.6	270.7	266.7	262.4	260.7	261.2
65°	241.3	235.0	229.2	225.0	223.9	220.8	221.8
67.5°	201.5	197.3	191.2	188.9	187.0	185.2	183.9
70°	175.1	170.9	167.7	164.5	163.0	163.0	163.0
72.5°	152.7	147.7	145.8	141.8	142.8	141.1	139.4
75°	118.3	115.1	113.5	111.9	109.3	109.3	109.3
77.5°	87.1	86.1	84.2	82.5	81.9	81.4	81.6
80°	67.3	66.8	65.7	65.7	64.6	64.2	63.1
82.5°	51.7	50.4	49.7	49.3	49.1	49.0	48.8
85°	29.5	28.4	28.4	28.9	27.9	27.9	28.4
87.5°	14.7	14.9	14.6	14.7	15.1	14.8	14.8
90°	16.9	17.7	18.2	18.5	18.9	19.3	19.6
92.5°	18.1	18.5	18.8	18.9	19.2	19.3	19.6
95°	30.7	31.4	31.8	31.6	31.4	31.3	31.1
97.5°	39.7	40.3	40.7	41.0	41.1	41.4	41.5
100°	45.1	46.4	47.2	47.5	47.8	48.2	48.5
102.5°	47.5	49.1	50.1	50.6	51.0	51.5	52.0
105°	49.4	51.2	52.4	53.1	53.7	54.3	55.0
107.5°	56.4	54.6	54.0	54.7	55.3	55.9	56.6
110°	78.3	62.3	54.6	55.2	55.8	56.5	57.2



TEST NUMBER: P331402-927

CATALOG NUMBER: SA2XXDIP-C865D925U927-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	143.4	84.8	55.7	56.2	56.7	57.2	57.8
115°	223.1	148.6	105.6	94.0	82.5	70.9	59.3
117.5°	440.5	422.4	394.3	356.3	318.3	280.3	242.2
120°	536.1	538.1	528.1	506.4	484.7	463.0	441.3
122.5°	567.9	569.1	567.6	563.4	559.1	554.9	550.7
125°	614.7	615.8	616.6	617.1	617.6	618.1	618.6
127.5°	658.5	660.2	661.0	661.2	661.2	661.3	661.4
130°	686.1	687.9	688.7	688.6	688.3	688.2	688.0
132.5°	712.6	714.1	714.7	714.5	714.4	714.2	714.1
135°	750.8	752.3	753.0	752.7	752.3	752.0	751.7
137.5°	786.1	787.7	788.2	787.7	787.1	786.6	786.0
140°	808.9	810.3	810.6	809.8	809.1	808.3	807.4
142.5°	829.9	831.2	831.5	830.7	829.9	829.1	828.2
145°	859.3	860.4	860.5	859.8	859.0	858.2	857.4
147.5°	884.7	885.6	885.7	884.9	884.3	883.6	883.0
150°	900.8	901.7	901.8	901.0	900.2	899.4	898.6
152.5°	915.2	916.2	916.2	915.0	914.0	913.0	911.9
155°	934.8	935.7	935.6	934.3	933.0	931.7	930.4
157.5°	951.3	952.4	952.4	951.1	949.8	948.6	947.4
160°	960.8	961.8	961.7	960.5	959.4	958.3	957.2
162.5°	969.9	971.0	970.8	969.5	968.0	966.7	965.3
165°	980.8	981.9	981.9	980.8	979.7	978.6	977.5
167.5°	989.9	991.1	990.9	989.4	988.0	986.6	985.1
170°	994.6	995.7	995.5	994.1	992.6	991.2	989.8
172.5°	998.1	999.2	999.0	997.5	996.1	994.7	993.2
175°	1001.8	1002.9	1002.7	1001.1	999.5	997.8	996.2
177.5°	1002.0	1002.9	1002.7	1001.6	1000.4	999.3	998.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9

(END OF REPORT)