

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331293

Luminaire Tested: **SA2XXDIP-C485D330U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331293
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D330U835-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3256.2 lumens
Efficiency: N/A
Efficacy: 118.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331293
CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331293

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	94	90	86	83	78	76	73	68	66	64	58	57	56	51
2	91	84	77	72	85	78	73	68	69	64	61	60	57	54	51	49	47	43
3	83	74	66	60	78	69	62	57	61	55	51	53	49	45	46	43	40	36
4	76	65	57	51	71	61	54	48	54	48	44	47	43	39	41	37	34	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	33	30	33	29	26	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	30	27	24	21
8	55	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	26	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12540	12540	12540
5°	12588	12407	12480
10°	12514	12281	12342
15°	12359	12122	12109
20°	12139	11883	11869
25°	11922	11589	11589
30°	11641	11320	11222
35°	11379	10996	10835
40°	11051	10673	10467
45°	10727	10351	10095
50°	10374	10017	9661
55°	10007	9627	9272
60°	9597	9164	8825
65°	9158	8703	8302
70°	8601	8143	7756
75°	7829	7498	7317
80°	6946	6732	6388
85°	5669	5391	4835



TEST NUMBER: P331293

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	2.2
10°-20°	205.5	6.3
20°-30°	302.1	9.3
30°-40°	350.9	10.8
40°-50°	350.5	10.8
50°-60°	305.6	9.4
60°-70°	226.0	6.9
70°-80°	128.0	3.9
80°-90°	36.1	1.1
90°-100°	73.5	2.3
100°-110°	249.3	7.7
110°-120°	264.8	8.1
120°-130°	218.0	6.7
130°-140°	175.1	5.4
140°-150°	132.3	4.1
150°-160°	93.0	2.9
160°-170°	54.7	1.7
170°-180°	17.8	0.5
0°-30°	580.6	17.8
0°-40°	931.5	28.6
0°-60°	1587.6	48.8
0°-90°	1977.7	60.7
90°-120°	587.6	18.0
90°-150°	1113.0	34.2
90°-180°	1279.0	39.3
0°-180°	3256.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	773	766	771	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	362
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	35
90°	0	5	12	12	12	2
95°	12	30	138	52	40	13
105°	43	65	262	468	398	46
115°	76	96	219	452	524	75
125°	106	125	211	366	425	94
135°	124	148	208	308	352	96
145°	142	163	207	257	281	89
155°	162	174	201	227	236	74
165°	176	181	193	204	207	50
175°	183	184	185	187	187	17
180°	184	184	184	184	184	



TEST NUMBER: P331293

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	780.3	779.6	779.0	778.3	777.6	776.6	775.1	773.7	772.2	770.7	772.1
5°	776.7	776.0	775.4	774.7	774.1	772.8	771.0	769.2	767.3	765.5	766.8
7.5°	769.8	768.8	767.8	766.7	765.7	764.3	762.4	760.6	758.7	756.8	758.2
10°	763.3	762.1	760.9	759.8	758.6	757.0	755.0	753.1	751.1	749.1	750.4
12.5°	754.3	753.3	752.2	751.2	750.2	748.7	746.7	744.7	742.7	740.7	741.6
15°	739.4	738.4	737.4	736.4	735.4	733.8	731.6	729.5	727.3	725.2	725.8
17.5°	720.2	719.3	718.3	717.3	716.3	714.7	712.5	710.3	708.1	705.9	706.7
20°	706.5	705.5	704.5	703.5	702.5	700.9	698.5	696.2	693.9	691.6	692.1
22.5°	692.8	691.4	690.0	688.6	687.2	685.4	683.2	681.0	678.8	676.6	676.7
25°	669.2	667.8	666.5	665.2	663.9	661.8	659.0	656.1	653.3	650.5	650.8
27.5°	642.3	641.1	639.9	638.7	637.5	635.8	633.6	631.3	629.1	626.9	626.4
30°	624.4	623.0	621.7	620.4	619.0	617.1	614.6	612.2	609.7	607.2	606.7
32.5°	605.2	604.2	603.1	602.0	601.0	599.1	596.5	593.9	591.3	588.7	587.8
35°	577.3	575.6	574.0	572.3	570.7	568.5	565.9	563.2	560.5	557.9	556.9
37.5°	545.8	544.3	542.9	541.4	539.9	537.9	535.2	532.6	529.9	527.3	526.0
40°	524.3	522.9	521.6	520.3	519.0	517.0	514.3	511.7	509.0	506.4	504.9
42.5°	503.4	502.0	500.7	499.4	498.1	496.1	493.4	490.8	488.1	485.4	483.8
45°	469.8	468.6	467.4	466.3	465.1	463.3	460.8	458.3	455.8	453.3	451.5
47.5°	436.3	435.2	434.1	433.0	431.9	430.1	427.5	424.9	422.3	419.7	417.8
50°	413.0	412.2	411.3	410.5	409.7	408.1	405.8	403.5	401.1	398.8	396.5
52.5°	390.3	389.2	388.1	387.0	385.9	384.3	382.1	379.9	377.7	375.5	373.6
55°	355.5	354.5	353.5	352.5	351.5	350.0	348.0	346.0	344.0	342.0	340.1
57.5°	320.5	319.7	318.9	318.2	317.4	315.9	313.7	311.5	309.3	307.1	305.1
60°	297.2	296.6	295.9	295.2	294.6	293.1	290.8	288.4	286.1	283.8	282.0
62.5°	274.5	273.5	272.4	271.3	270.3	268.9	267.1	265.3	263.5	261.7	260.0
65°	239.7	238.7	237.7	236.7	235.8	234.4	232.8	231.1	229.4	227.8	226.3
67.5°	204.3	203.5	202.7	201.9	201.1	200.0	198.5	197.0	195.5	194.0	192.9
70°	182.2	181.6	180.9	180.2	179.6	178.5	177.0	175.5	174.0	172.5	171.4
72.5°	159.5	158.9	158.2	157.5	156.9	156.1	155.1	154.1	153.2	152.2	151.0
75°	125.5	125.1	124.8	124.5	124.1	123.6	122.7	121.9	121.1	120.2	119.2
77.5°	95.0	94.4	93.9	93.3	92.7	92.3	92.0	91.6	91.3	91.0	90.5
80°	74.7	74.5	74.4	74.2	74.0	73.8	73.4	73.1	72.8	72.4	71.9
82.5°	55.6	55.5	55.5	55.5	55.4	55.3	55.1	54.9	54.7	54.5	53.9
85°	30.6	30.5	30.3	30.1	30.0	29.8	29.6	29.5	29.3	29.1	28.6
87.5°	10.8	10.8	10.8	10.7	10.5	10.5	10.6	10.8	11.0	10.8	10.3
90°	0.4	1.4	2.8	3.5	4.2	5.3	7.1	9.5	11.7	12.0	11.7
92.5°	4.3	6.2	8.8	10.3	12.7	16.0	24.0	35.3	45.3	45.9	38.8
95°	12.4	13.8	17.3	20.5	26.1	34.6	50.9	81.6	122.6	138.5	121.2
97.5°	20.1	22.0	25.8	30.6	37.1	46.7	67.1	110.0	178.1	236.4	248.0
100°	27.2	28.3	31.4	37.1	44.2	54.1	72.8	115.9	192.2	279.1	330.0
102.5°	33.7	34.5	37.7	43.3	50.7	60.6	77.9	116.2	186.8	280.5	360.5
105°	43.1	44.5	47.0	52.3	60.1	70.0	86.6	118.0	176.3	261.8	355.8
107.5°	53.3	54.4	56.8	61.7	69.4	79.4	95.5	122.9	171.1	241.7	324.8
110°	60.1	61.5	63.6	68.2	75.6	85.9	101.4	126.8	170.0	232.1	305.3



TEST NUMBER: P331293

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	66.3	67.7	70.1	74.4	81.5	92.1	107.1	131.1	170.2	225.9	291.7
115°	76.0	77.7	79.9	84.1	91.2	100.7	115.9	137.4	171.7	219.1	274.9
117.5°	86.0	87.4	89.5	93.3	100.1	110.0	124.0	144.2	174.3	215.7	264.3
120°	92.2	93.6	95.8	98.9	106.0	115.9	129.7	148.8	176.0	213.8	258.6
122.5°	98.2	99.3	101.4	104.9	111.9	122.1	135.0	152.7	177.9	212.6	253.8
125°	106.0	107.1	109.2	113.4	120.5	130.4	143.1	159.0	180.9	210.6	247.0
127.5°	112.2	113.6	116.6	121.3	128.0	138.2	150.6	164.9	183.9	209.4	240.6
130°	115.9	117.3	120.8	125.8	132.9	142.7	155.1	168.5	186.2	208.8	236.4
132.5°	119.3	121.0	124.8	130.0	137.4	147.3	159.1	172.2	188.5	208.5	233.0
135°	124.4	125.8	130.0	135.3	143.5	153.3	164.7	177.0	191.2	208.1	228.2
137.5°	129.2	130.9	135.1	140.8	148.8	158.0	169.2	180.7	193.6	208.0	224.9
140°	132.9	134.3	138.5	144.2	151.9	161.1	171.7	182.7	194.7	207.8	222.9
142.5°	136.5	137.7	141.6	147.3	154.8	163.4	173.7	184.4	195.5	207.8	221.0
145°	142.0	143.5	147.0	152.3	159.4	167.1	176.7	186.6	196.4	207.0	218.4
147.5°	148.0	149.0	152.4	157.3	163.2	170.1	179.1	187.8	196.7	205.8	215.7
150°	151.9	153.0	155.8	160.4	165.7	172.1	180.2	188.3	196.4	204.9	213.4
152.5°	155.9	156.4	159.2	163.2	168.3	174.0	181.3	188.6	195.9	203.5	211.4
155°	161.5	161.8	163.9	167.8	171.7	177.0	183.0	189.0	195.0	201.0	207.8
157.5°	166.1	166.5	168.2	171.6	174.7	179.1	184.2	189.0	193.4	198.5	204.3
160°	169.2	169.6	171.0	173.8	176.7	180.6	184.8	189.0	192.6	196.8	201.7
162.5°	172.4	172.1	173.6	175.8	178.4	181.4	185.1	188.7	191.7	195.4	199.5
165°	176.0	175.6	176.3	178.4	180.2	182.3	185.5	188.0	190.1	192.6	195.7
167.5°	178.9	178.5	179.1	180.5	181.8	183.1	185.4	187.5	188.5	190.1	192.1
170°	180.9	180.2	180.6	181.6	182.3	183.4	185.1	186.9	187.6	188.7	190.1
172.5°	182.0	181.6	181.4	182.5	182.9	183.7	184.9	186.1	186.5	187.0	188.1
175°	183.4	183.0	182.7	183.4	183.4	183.7	184.4	185.1	184.8	185.1	185.5
177.5°	184.0	183.4	183.2	183.7	183.7	183.7	184.0	184.6	184.0	183.7	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331293

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	773.4	774.7	776.0	776.6	776.3	776.0	775.8	775.5
5°	768.2	769.5	770.8	771.3	771.0	770.6	770.3	770.0
7.5°	759.5	760.8	762.2	762.6	762.3	761.9	761.5	761.2
10°	751.7	753.1	754.4	754.8	754.3	753.8	753.3	752.8
12.5°	742.6	743.5	744.4	744.7	744.3	744.0	743.6	743.2
15°	726.5	727.2	727.8	727.7	726.9	726.1	725.3	724.4
17.5°	707.4	708.2	709.0	708.9	708.1	707.4	706.6	705.8
20°	692.6	693.1	693.6	693.5	692.8	692.1	691.5	690.8
22.5°	676.8	676.9	677.0	676.9	676.5	676.1	675.7	675.3
25°	651.2	651.5	651.8	651.8	651.5	651.2	650.8	650.5
27.5°	625.9	625.4	624.9	624.3	623.5	622.7	621.9	621.1
30°	606.2	605.7	605.2	604.6	603.9	603.3	602.6	601.9
32.5°	586.9	586.0	585.1	584.3	583.6	583.0	582.3	581.6
35°	555.9	554.9	553.9	553.0	552.2	551.3	550.5	549.7
37.5°	524.8	523.6	522.4	521.3	520.5	519.7	518.9	518.2
40°	503.4	501.9	500.4	499.3	498.6	498.0	497.3	496.6
42.5°	482.2	480.6	478.9	477.7	476.7	475.8	474.9	473.9
45°	449.7	447.9	446.0	444.8	444.1	443.5	442.8	442.1
47.5°	415.9	413.9	412.0	410.6	409.6	408.7	407.7	406.7
50°	394.2	391.8	389.5	387.9	387.1	386.3	385.4	384.6
52.5°	371.7	369.7	367.8	366.3	365.2	364.1	363.0	361.9
55°	338.1	336.1	334.1	332.7	331.8	331.0	330.2	329.4
57.5°	303.2	301.2	299.3	298.0	297.3	296.7	296.1	295.4
60°	280.1	278.3	276.5	275.3	274.8	274.3	273.8	273.3
62.5°	258.3	256.6	254.9	253.8	253.1	252.5	251.9	251.2
65°	224.8	223.3	221.8	220.6	219.8	219.0	218.2	217.3
67.5°	191.7	190.5	189.4	188.5	187.8	187.1	186.5	185.8
70°	170.2	169.0	167.9	167.0	166.3	165.6	165.0	164.3
72.5°	149.9	148.7	147.6	146.7	146.2	145.6	145.1	144.6
75°	118.2	117.3	116.3	115.9	116.3	116.6	116.9	117.3
77.5°	90.0	89.5	89.0	88.5	88.0	87.6	87.1	86.6
80°	71.4	70.9	70.5	70.0	69.7	69.4	69.0	68.7
82.5°	53.3	52.6	52.0	51.6	51.6	51.5	51.4	51.4
85°	28.1	27.6	27.1	26.8	26.6	26.5	26.3	26.1
87.5°	9.8	9.3	9.0	8.8	8.7	8.6	8.4	8.3
90°	11.3	10.6	11.3	11.7	11.7	11.7	11.7	11.7
92.5°	30.8	26.4	23.5	21.3	21.0	19.9	20.1	19.6
95°	92.6	71.0	56.2	48.4	43.8	41.0	39.9	40.3
97.5°	216.0	176.7	138.5	113.0	96.1	87.4	82.3	79.3
100°	322.6	278.8	230.4	187.6	158.3	143.1	132.9	126.5
102.5°	392.4	382.5	347.1	301.8	269.9	244.0	231.2	222.6
105°	429.3	469.2	473.8	462.2	440.2	418.3	403.1	398.2
107.5°	402.7	462.9	499.6	516.7	519.5	518.3	515.2	508.7
110°	379.8	443.1	488.3	517.3	532.5	539.2	542.4	542.0



TEST NUMBER: P331293

CATALOG NUMBER: SA2XXDIP-C485D330U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	358.9	419.6	467.9	501.2	522.3	533.5	539.5	541.4
115°	333.2	387.6	433.9	470.3	495.4	511.6	520.8	524.0
117.5°	313.8	361.6	403.6	437.7	463.3	480.5	490.1	492.8
120°	304.2	348.0	385.5	417.6	442.4	459.0	469.2	472.8
122.5°	296.6	336.7	372.2	401.2	423.4	439.8	448.9	451.8
125°	285.5	321.9	353.0	379.5	400.0	413.4	422.2	425.1
127.5°	274.5	307.5	336.8	361.2	379.1	391.7	399.3	401.6
130°	267.5	297.9	325.8	349.1	366.4	378.4	385.5	388.3
132.5°	260.7	288.8	314.5	336.4	353.4	365.4	371.9	374.5
135°	251.2	274.5	297.9	317.6	332.8	344.5	350.9	352.3
137.5°	243.7	263.2	281.7	298.9	312.8	322.8	328.4	330.5
140°	238.8	255.8	272.1	287.6	298.9	308.1	313.4	315.5
142.5°	234.9	249.3	263.3	276.3	287.0	295.4	300.1	300.5
145°	229.3	241.0	251.9	262.2	270.6	276.7	280.2	281.2
147.5°	225.0	234.2	242.7	250.2	257.2	262.0	264.4	265.1
150°	221.9	229.7	237.1	243.4	248.7	253.0	255.1	255.5
152.5°	218.8	226.0	232.3	237.8	242.0	245.6	247.2	247.3
155°	214.5	220.1	225.4	229.3	233.2	235.7	237.1	236.4
157.5°	209.5	214.2	218.6	221.7	224.4	226.5	227.1	227.1
160°	206.3	210.2	214.1	216.6	219.1	220.8	221.2	221.2
162.5°	203.2	206.6	209.9	211.8	214.3	215.5	215.8	215.5
165°	198.6	201.0	203.5	204.9	206.3	207.8	207.8	207.4
167.5°	194.1	196.0	197.7	199.0	199.6	200.4	200.3	199.9
170°	191.9	192.9	194.3	195.0	195.4	196.4	196.1	195.4
172.5°	189.3	190.1	191.2	191.6	192.0	192.5	192.1	191.7
175°	186.6	186.9	187.3	187.6	187.6	188.0	187.6	186.9
177.5°	184.6	184.6	184.9	184.9	184.9	184.9	184.6	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7

(END OF REPORT)