

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331300

Luminaire Tested: **SA2XXDIP-C485D530U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331300  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D530U835-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4091.4 lumens  
Efficiency: N/A  
Efficacy: 124.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331300  
CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331300

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48	48	48	48	48	48	48	48	48	48	48	48																
	1	97	93	89	86	90	86	82	79	72	70	68	60	58	57	48	47	46	41	41	41	41	41	41	41	41	41	41	41	41																
	2	89	81	75	70	81	75	70	65	63	59	56	52	50	47	42	41	39	34	34	34	34	34	34	34	34	34	34	34	34																
	3	81	71	64	58	74	66	60	54	56	51	47	46	43	40	38	35	33	29	29	29	29	29	29	29	29	29	29	29	29																
	4	74	63	55	49	68	59	52	46	50	44	40	41	37	34	34	31	28	25	25	25	25	25	25	25	25	25	25	25	25																
	5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25	22	22	22	22	22	22	22	22	22	22	22	22																
	6	63	51	42	37	57	47	40	34	40	34	30	34	29	26	27	24	22	19	19	19	19	19	19	19	19	19	19	19	19																
	7	58	46	38	32	53	42	35	30	36	31	27	30	26	23	25	22	19	17	17	17	17	17	17	17	17	17	17	17	17																
	8	54	41	34	28	49	39	32	27	33	28	24	28	24	20	23	20	17	15	15	15	15	15	15	15	15	15	15	15	15																
	9	50	38	30	25	46	35	28	24	30	25	21	26	21	18	21	18	16	14	14	14	14	14	14	14	14	14	14	14	14																
	10	47	35	27	23	43	32	26	21	28	23	19	24	20	17	20	17	14	12	12	12	12	12	12	12	12	12	12	12	12																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	12540	12540	12540
5°	12588	12407	12480
10°	12514	12281	12342
15°	12359	12122	12109
20°	12139	11883	11869
25°	11922	11589	11589
30°	11641	11320	11222
35°	11379	10996	10835
40°	11051	10673	10467
45°	10727	10351	10095
50°	10374	10017	9661
55°	10007	9627	9272
60°	9597	9164	8825
65°	9158	8703	8302
70°	8601	8143	7756
75°	7829	7498	7317
80°	6946	6732	6388
85°	5669	5391	4835



TEST NUMBER: P331300

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	73.0	1.8
10°-20°	205.5	5.0
20°-30°	302.1	7.4
30°-40°	350.9	8.6
40°-50°	350.5	8.6
50°-60°	305.6	7.5
60°-70°	226.0	5.5
70°-80°	128.0	3.1
80°-90°	36.2	0.9
90°-100°	24.1	0.6
100°-110°	88.2	2.2
110°-120°	235.8	5.8
120°-130°	389.3	9.5
130°-140°	414.0	10.1
140°-150°	384.8	9.4
150°-160°	309.4	7.6
160°-170°	199.4	4.9
170°-180°	68.6	1.7
0°-30°	580.6	14.2
0°-40°	931.5	22.8
0°-60°	1587.6	38.8
0°-90°	1977.8	48.3
90°-120°	348.1	8.5
90°-150°	1536.2	37.5
90°-180°	2114.0	51.7
0°-180°	4091.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	777	777	777	777	777	
5°	777	773	766	771	770	74
15°	739	735	725	728	724	208
25°	669	663	650	652	650	308
35°	577	570	558	553	550	360
45°	470	464	453	445	442	362
55°	356	351	342	333	329	318
65°	240	235	228	221	217	237
75°	126	124	120	116	117	134
85°	31	30	29	27	26	35
90°	0	6	10	13	14	3
95°	34	18	20	23	22	41
105°	159	166	32	37	40	170
115°	300	309	322	92	43	295
125°	424	431	441	444	446	378
135°	525	533	538	543	542	405
145°	609	609	617	621	618	381
155°	671	666	672	675	671	309
165°	707	704	705	708	705	200
175°	723	719	720	723	719	69
180°	721	721	721	721	721	



TEST NUMBER: P331300

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	780.3	779.6	779.0	778.3	777.6	776.6	775.1	773.7	772.2	770.7	772.1
5°	776.7	776.0	775.4	774.7	774.1	772.8	771.0	769.2	767.3	765.5	766.8
7.5°	769.8	768.8	767.8	766.7	765.7	764.3	762.4	760.6	758.7	756.8	758.2
10°	763.3	762.1	760.9	759.8	758.6	757.0	755.0	753.1	751.1	749.1	750.4
12.5°	754.3	753.3	752.2	751.2	750.2	748.7	746.7	744.7	742.7	740.7	741.6
15°	739.4	738.4	737.4	736.4	735.4	733.8	731.6	729.5	727.3	725.2	725.8
17.5°	720.2	719.3	718.3	717.3	716.3	714.7	712.5	710.3	708.1	705.9	706.7
20°	706.5	705.5	704.5	703.5	702.5	700.9	698.5	696.2	693.9	691.6	692.1
22.5°	692.8	691.4	690.0	688.6	687.2	685.4	683.2	681.0	678.8	676.6	676.7
25°	669.2	667.8	666.5	665.2	663.9	661.8	659.0	656.1	653.3	650.5	650.8
27.5°	642.3	641.1	639.9	638.7	637.5	635.8	633.6	631.3	629.1	626.9	626.4
30°	624.4	623.0	621.7	620.4	619.0	617.1	614.6	612.2	609.7	607.2	606.7
32.5°	605.2	604.2	603.1	602.0	601.0	599.1	596.5	593.9	591.3	588.7	587.8
35°	577.3	575.6	574.0	572.3	570.7	568.5	565.9	563.2	560.5	557.9	556.9
37.5°	545.8	544.3	542.9	541.4	539.9	537.9	535.2	532.6	529.9	527.3	526.0
40°	524.3	522.9	521.6	520.3	519.0	517.0	514.3	511.7	509.0	506.4	504.9
42.5°	503.4	502.0	500.7	499.4	498.1	496.1	493.4	490.8	488.1	485.4	483.8
45°	469.8	468.6	467.4	466.3	465.1	463.3	460.8	458.3	455.8	453.3	451.5
47.5°	436.3	435.2	434.1	433.0	431.9	430.1	427.5	424.9	422.3	419.7	417.8
50°	413.0	412.2	411.3	410.5	409.7	408.1	405.8	403.5	401.1	398.8	396.5
52.5°	390.3	389.2	388.1	387.0	385.9	384.3	382.1	379.9	377.7	375.5	373.6
55°	355.5	354.5	353.5	352.5	351.5	350.0	348.0	346.0	344.0	342.0	340.1
57.5°	320.5	319.7	318.9	318.2	317.4	315.9	313.7	311.5	309.3	307.1	305.1
60°	297.2	296.6	295.9	295.2	294.6	293.1	290.8	288.4	286.1	283.8	282.0
62.5°	274.5	273.5	272.4	271.3	270.3	268.9	267.1	265.3	263.5	261.7	260.0
65°	239.7	238.7	237.7	236.7	235.8	234.4	232.8	231.1	229.4	227.8	226.3
67.5°	204.3	203.5	202.7	201.9	201.1	200.0	198.5	197.0	195.5	194.0	192.9
70°	182.2	181.6	180.9	180.2	179.6	178.5	177.0	175.5	174.0	172.5	171.4
72.5°	159.5	158.9	158.2	157.5	156.9	156.1	155.1	154.1	153.2	152.2	151.0
75°	125.5	125.1	124.8	124.5	124.1	123.6	122.7	121.9	121.1	120.2	119.2
77.5°	95.0	94.4	93.9	93.3	92.7	92.3	92.0	91.6	91.3	91.0	90.5
80°	74.7	74.5	74.4	74.2	74.0	73.8	73.4	73.1	72.8	72.4	71.9
82.5°	55.6	55.5	55.5	55.5	55.4	55.3	55.1	54.9	54.7	54.5	53.9
85°	30.6	30.5	30.3	30.1	30.0	29.8	29.6	29.5	29.3	29.1	28.6
87.5°	10.9	10.8	10.8	10.8	10.8	10.8	10.7	10.6	10.5	10.5	10.2
90°	0.5	1.8	3.1	4.3	5.6	6.7	7.7	8.6	9.5	10.4	11.0
92.5°	10.5	10.4	10.3	10.2	10.1	10.3	10.7	11.2	11.6	12.1	12.4
95°	33.9	30.1	26.3	22.4	18.6	17.1	17.9	18.7	19.5	20.4	20.9
97.5°	67.3	56.5	45.8	35.0	24.2	19.7	21.6	23.5	25.4	27.2	27.7
100°	92.4	76.5	60.6	44.7	28.8	21.9	23.8	25.8	27.8	29.7	30.7
102.5°	119.9	116.6	113.2	109.8	106.5	96.5	80.1	63.6	47.1	30.6	31.8
105°	158.6	162.1	165.6	169.1	172.6	158.5	126.8	95.2	63.5	31.8	33.1
107.5°	202.8	205.6	208.4	211.2	214.0	196.4	158.5	120.5	82.5	44.6	43.3
110°	231.2	233.6	236.1	238.5	240.9	225.4	191.9	158.4	124.8	91.3	79.7



TEST NUMBER: P331300

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	257.9	260.1	262.2	264.4	266.5	263.5	255.2	246.9	238.6	230.4	188.0
115°	300.1	302.0	304.0	306.0	308.0	310.4	313.3	316.2	319.1	322.0	268.3
117.5°	337.8	340.0	342.2	344.4	346.6	348.7	350.7	352.7	354.7	356.6	343.7
120°	365.3	367.0	368.8	370.5	372.3	374.2	376.3	378.4	380.4	382.5	383.9
122.5°	388.7	390.5	392.4	394.2	396.0	398.1	400.3	402.6	404.9	407.2	408.0
125°	424.3	425.8	427.3	428.8	430.3	432.2	434.4	436.6	438.8	441.0	441.8
127.5°	456.5	458.2	459.9	461.5	463.2	464.9	466.5	468.2	469.8	471.5	472.6
130°	477.0	478.8	480.7	482.6	484.4	486.0	487.3	488.5	489.8	491.1	492.4
132.5°	497.9	499.4	501.0	502.6	504.2	505.6	506.9	508.2	509.4	510.7	511.8
135°	525.0	526.9	528.7	530.6	532.4	533.9	534.9	536.0	537.0	538.0	539.2
137.5°	552.5	553.7	555.0	556.3	557.6	558.9	560.1	561.3	562.4	563.6	564.8
140°	570.4	571.3	572.3	573.2	574.1	575.2	576.5	577.8	579.0	580.3	581.4
142.5°	585.4	586.3	587.1	587.9	588.8	589.9	591.4	592.8	594.3	595.8	596.7
145°	609.0	608.9	608.8	608.7	608.6	609.5	611.5	613.4	615.4	617.4	618.2
147.5°	629.6	629.1	628.7	628.3	627.8	628.6	630.5	632.5	634.4	636.4	637.0
150°	642.9	642.1	641.3	640.5	639.7	640.2	642.1	643.9	645.8	647.6	648.3
152.5°	654.2	653.3	652.4	651.5	650.6	651.0	652.8	654.6	656.3	658.1	658.8
155°	670.6	669.6	668.5	667.5	666.4	666.6	668.0	669.4	670.8	672.2	672.9
157.5°	683.4	682.6	681.7	680.8	679.9	680.0	680.9	681.9	682.9	683.9	684.6
160°	691.0	690.3	689.6	688.9	688.2	688.2	688.9	689.6	690.3	691.0	691.7
162.5°	697.6	696.9	696.2	695.5	694.9	694.8	695.4	696.0	696.6	697.2	698.0
165°	706.6	705.9	705.2	704.5	703.8	703.7	704.0	704.3	704.7	705.0	705.9
167.5°	713.3	712.6	711.9	711.2	710.5	710.3	710.6	711.0	711.3	711.6	712.4
170°	717.0	716.4	715.7	715.0	714.3	714.0	714.3	714.5	714.7	715.0	715.8
172.5°	719.6	718.9	718.2	717.5	716.8	716.5	716.8	717.0	717.2	717.5	718.3
175°	722.8	722.0	721.2	720.4	719.5	719.3	719.5	719.7	719.9	720.2	721.0
177.5°	723.3	722.7	722.0	721.4	720.7	720.4	720.5	720.6	720.7	720.8	721.5
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2



TEST NUMBER: P331300

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	776.7	776.7	776.7	776.7	776.7	776.7	776.7	776.7
2.5°	773.4	774.7	776.0	776.6	776.3	776.0	775.8	775.5
5°	768.2	769.5	770.8	771.3	771.0	770.6	770.3	770.0
7.5°	759.5	760.8	762.2	762.6	762.3	761.9	761.5	761.2
10°	751.7	753.1	754.4	754.8	754.3	753.8	753.3	752.8
12.5°	742.6	743.5	744.4	744.7	744.3	744.0	743.6	743.2
15°	726.5	727.2	727.8	727.7	726.9	726.1	725.3	724.4
17.5°	707.4	708.2	709.0	708.9	708.1	707.4	706.6	705.8
20°	692.6	693.1	693.6	693.5	692.8	692.1	691.5	690.8
22.5°	676.8	676.9	677.0	676.9	676.5	676.1	675.7	675.3
25°	651.2	651.5	651.8	651.8	651.5	651.2	650.8	650.5
27.5°	625.9	625.4	624.9	624.3	623.5	622.7	621.9	621.1
30°	606.2	605.7	605.2	604.6	603.9	603.3	602.6	601.9
32.5°	586.9	586.0	585.1	584.3	583.6	583.0	582.3	581.6
35°	555.9	554.9	553.9	553.0	552.2	551.3	550.5	549.7
37.5°	524.8	523.6	522.4	521.3	520.5	519.7	518.9	518.2
40°	503.4	501.9	500.4	499.3	498.6	498.0	497.3	496.6
42.5°	482.2	480.6	478.9	477.7	476.7	475.8	474.9	473.9
45°	449.7	447.9	446.0	444.8	444.1	443.5	442.8	442.1
47.5°	415.9	413.9	412.0	410.6	409.6	408.7	407.7	406.7
50°	394.2	391.8	389.5	387.9	387.1	386.3	385.4	384.6
52.5°	371.7	369.7	367.8	366.3	365.2	364.1	363.0	361.9
55°	338.1	336.1	334.1	332.7	331.8	331.0	330.2	329.4
57.5°	303.2	301.2	299.3	298.0	297.3	296.7	296.1	295.4
60°	280.1	278.3	276.5	275.3	274.8	274.3	273.8	273.3
62.5°	258.3	256.6	254.9	253.8	253.1	252.5	251.9	251.2
65°	224.8	223.3	221.8	220.6	219.8	219.0	218.2	217.3
67.5°	191.7	190.5	189.4	188.5	187.8	187.1	186.5	185.8
70°	170.2	169.0	167.9	167.0	166.3	165.6	165.0	164.3
72.5°	149.9	148.7	147.6	146.7	146.2	145.6	145.1	144.6
75°	118.2	117.3	116.3	115.9	116.3	116.6	116.9	117.3
77.5°	90.0	89.5	89.0	88.5	88.0	87.6	87.1	86.6
80°	71.4	70.9	70.5	70.0	69.7	69.4	69.0	68.7
82.5°	53.3	52.6	52.0	51.6	51.6	51.5	51.4	51.4
85°	28.1	27.6	27.1	26.8	26.6	26.5	26.3	26.1
87.5°	9.9	9.6	9.3	9.1	9.1	9.0	8.9	8.8
90°	11.6	12.2	12.8	13.2	13.4	13.6	13.9	14.1
92.5°	12.7	13.0	13.3	13.5	13.7	13.8	14.0	14.1
95°	21.5	22.1	22.7	22.9	22.8	22.7	22.6	22.4
97.5°	28.2	28.6	29.1	29.4	29.5	29.7	29.8	30.0
100°	31.6	32.5	33.5	34.0	34.3	34.5	34.7	35.0
102.5°	33.0	34.2	35.4	36.2	36.5	36.8	37.1	37.5
105°	34.4	35.7	36.9	37.8	38.3	38.7	39.2	39.7
107.5°	42.0	40.7	39.4	39.0	39.4	39.9	40.3	40.8
110°	68.1	56.5	44.9	39.4	39.8	40.3	40.8	41.2





TEST NUMBER: P331300

CATALOG NUMBER: SA2XXDIP-C485D530U835-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	145.7	103.4	61.1	40.2	40.5	40.9	41.3	41.6
115°	214.6	160.9	107.2	76.2	67.8	59.5	51.1	42.8
117.5°	330.7	317.7	304.7	284.5	257.0	229.6	202.2	174.7
120°	385.3	386.7	388.1	381.0	365.3	349.7	334.0	318.3
122.5°	408.8	409.7	410.5	409.4	406.4	403.3	400.3	397.2
125°	442.6	443.4	444.2	444.8	445.2	445.5	445.9	446.2
127.5°	473.8	475.0	476.2	476.8	476.9	477.0	477.0	477.1
130°	493.6	494.9	496.2	496.8	496.6	496.5	496.4	496.3
132.5°	512.9	514.0	515.1	515.5	515.4	515.3	515.2	515.1
135°	540.4	541.5	542.7	543.2	542.9	542.7	542.5	542.2
137.5°	565.9	567.0	568.2	568.5	568.1	567.7	567.4	567.0
140°	582.4	583.4	584.5	584.7	584.1	583.6	583.0	582.4
142.5°	597.7	598.6	599.6	599.8	599.2	598.6	598.0	597.4
145°	619.0	619.8	620.6	620.7	620.2	619.6	619.0	618.4
147.5°	637.6	638.2	638.8	638.8	638.4	637.9	637.4	636.9
150°	649.0	649.7	650.4	650.5	649.9	649.3	648.7	648.2
152.5°	659.5	660.2	660.9	660.8	660.1	659.3	658.5	657.8
155°	673.6	674.3	675.0	674.8	673.9	673.0	672.1	671.1
157.5°	685.4	686.2	687.0	687.0	686.0	685.1	684.2	683.3
160°	692.3	693.0	693.7	693.7	692.9	692.1	691.2	690.4
162.5°	698.8	699.6	700.4	700.3	699.3	698.3	697.3	696.3
165°	706.7	707.5	708.3	708.3	707.5	706.7	705.9	705.0
167.5°	713.2	714.1	714.9	714.8	713.7	712.7	711.6	710.6
170°	716.6	717.4	718.2	718.1	717.0	716.0	715.0	713.9
172.5°	719.1	719.9	720.7	720.6	719.6	718.5	717.5	716.4
175°	721.8	722.6	723.4	723.3	722.1	720.9	719.8	718.6
177.5°	722.1	722.8	723.4	723.3	722.5	721.6	720.8	720.0
180°	721.2	721.2	721.2	721.2	721.2	721.2	721.2	721.2

(END OF REPORT)