

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331749-927

Luminaire Tested: **SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331749-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5263.1 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 60.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55	50
2	92	85	79	75	86	80	75	70	69	66	63	60	57	55	51	49	48	43
3	85	76	69	63	79	71	65	60	62	58	54	54	51	48	46	44	42	38
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	34
5	72	61	53	48	67	57	51	45	51	45	41	44	40	37	39	35	33	30
6	67	55	48	42	62	52	45	40	46	41	37	41	36	33	35	32	29	27
7	62	50	43	37	58	48	41	36	42	37	33	37	33	30	33	29	27	24
8	58	46	39	33	54	44	37	32	39	33	29	34	30	27	30	27	24	22
9	54	42	35	30	51	40	34	29	36	31	27	32	28	25	28	25	22	20
10	51	39	32	27	48	37	31	26	33	28	24	30	25	22	26	23	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	28208	28208	28208	28208
5°	31504	28386	25167	28386
10°	34954	28186	21815	28186
15°	36672	27773	17188	27773
20°	31792	27161	14874	27161
25°	20851	26323	13279	26323
30°	14033	25307	12020	25307
35°	11367	24025	10841	24025
40°	10108	22634	10030	22634
45°	9149	21000	8953	21000
50°	8324	19381	8297	19381
55°	7828	17582	7724	17582
60°	6546	15936	6468	15936
65°	5521	14472	6262	14472
70°	5103	12925	5906	12925
75°	4772	11248	5452	11248
80°	4407	9261	4854	9261
85°	4057	7317	4279	7317



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.6	3.1
10°-20°	461.5	8.8
20°-30°	594.7	11.3
30°-40°	565.1	10.7
40°-50°	484.1	9.2
50°-60°	368.7	7.0
60°-70°	233.1	4.4
70°-80°	116.4	2.2
80°-90°	33.2	0.6
90°-100°	128.7	2.4
100°-110°	436.9	8.3
110°-120°	464.2	8.8
120°-130°	382.1	7.3
130°-140°	306.8	5.8
140°-150°	231.9	4.4
150°-160°	163.0	3.1
160°-170°	95.9	1.8
170°-180°	31.2	0.6
0°-30°	1221.8	23.2
0°-40°	1786.9	34.0
0°-60°	2639.7	50.2
0°-90°	3022.3	57.4
90°-120°	1029.8	19.6
90°-150°	1950.7	37.1
90°-180°	2241.0	42.6
0°-180°	5263.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1747	1747	1747	1747	1747	
5°	1944	1751	1553	1751	1944	192
15°	2194	1662	1028	1662	2194	592
25°	1170	1478	745	1478	1170	555
35°	577	1219	550	1219	577	369
45°	401	920	392	920	401	310
55°	278	625	274	625	278	244
65°	144	379	164	379	144	147
75°	76	180	87	180	76	81
85°	22	40	23	40	22	24
90°	20	1	20	1	20	12
95°	71	22	71	22	71	92
105°	698	76	698	76	698	675
115°	918	133	918	133	918	899
125°	745	186	745	186	745	673
135°	617	218	617	218	617	480
145°	493	249	493	249	493	313
155°	414	283	414	283	414	193
165°	364	308	364	308	364	104
175°	328	321	328	321	328	32
180°	322	322	322	322	322	



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1818.0	1819.5	1820.9	1817.5	1817.5	1814.6	1808.3	1803.4	1789.9	1787.9	1787.9
5°	1943.8	1942.6	1945.0	1937.1	1926.2	1923.7	1912.2	1897.0	1881.3	1863.7	1860.0
7.5°	2068.9	2067.0	2062.1	2060.9	2052.5	2034.1	2015.5	1995.7	1969.5	1943.9	1931.0
10°	2132.0	2152.0	2139.8	2118.6	2122.9	2094.4	2079.2	2053.1	2031.2	1993.0	1984.5
12.5°	2194.1	2202.0	2198.1	2186.1	2180.6	2160.8	2140.3	2117.7	2077.3	2043.0	2013.1
15°	2193.9	2205.4	2208.4	2204.8	2207.9	2206.6	2195.7	2176.9	2141.7	2104.0	2071.2
17.5°	2031.9	2039.9	2059.8	2073.3	2090.3	2126.3	2144.0	2150.9	2145.7	2124.2	2101.1
20°	1850.3	1836.9	1892.8	1921.4	1945.6	2006.3	2058.5	2078.5	2110.7	2110.1	2104.0
22.5°	1592.9	1596.1	1649.0	1682.9	1753.8	1814.5	1874.0	1949.4	2011.7	2052.8	2076.9
25°	1170.4	1193.5	1246.3	1292.4	1371.3	1484.2	1586.8	1705.8	1818.1	1906.8	1991.2
27.5°	879.0	880.7	922.6	965.2	1012.1	1104.6	1233.7	1375.9	1536.0	1668.1	1820.0
30°	752.7	749.1	766.7	792.8	832.9	904.5	1001.6	1141.3	1300.9	1500.0	1677.3
32.5°	663.4	663.6	676.8	696.2	729.4	777.8	844.3	957.7	1108.6	1304.3	1512.2
35°	576.7	576.1	585.8	599.8	613.7	644.7	690.2	749.7	853.5	1036.3	1248.7
37.5°	514.5	517.2	522.0	530.7	546.1	563.3	590.7	630.6	704.6	812.6	991.2
40°	479.6	480.8	487.4	494.7	503.8	517.2	539.6	571.9	625.9	712.1	842.6
42.5°	447.5	448.8	453.4	460.3	467.5	480.8	499.4	527.2	571.0	638.3	745.9
45°	400.7	400.7	404.9	408.0	415.8	427.9	443.1	466.2	496.5	546.4	618.0
47.5°	356.7	356.8	359.7	364.9	369.8	379.3	394.2	413.0	435.1	473.6	534.8
50°	331.4	332.1	333.9	338.1	341.2	349.7	361.2	377.6	400.7	430.4	481.4
52.5°	311.1	310.7	313.0	314.8	316.9	323.0	331.6	346.0	366.6	392.5	434.7
55°	278.1	275.6	279.2	282.3	284.1	286.5	291.4	300.5	318.1	339.9	371.5
57.5°	236.8	235.8	238.4	241.1	246.8	253.4	257.5	263.3	272.4	288.1	319.4
60°	202.7	202.7	208.2	210.0	216.7	225.2	233.7	238.6	247.7	258.0	281.1
62.5°	172.6	173.2	175.7	177.5	181.3	191.7	203.6	214.3	222.9	232.7	248.0
65°	144.5	145.7	145.7	146.9	149.3	151.8	156.6	165.1	180.3	194.2	205.8
67.5°	122.6	123.0	123.3	124.5	125.2	127.9	129.8	133.6	137.0	150.3	164.6
70°	108.1	109.9	109.2	110.5	111.1	112.3	114.7	116.5	122.0	125.1	133.6
72.5°	94.4	95.8	95.7	96.4	98.0	98.2	100.1	102.0	105.5	108.1	112.6
75°	76.5	75.9	76.5	77.7	78.3	78.9	78.9	81.4	83.2	85.6	88.6
77.5°	59.0	59.7	59.5	59.7	59.7	60.8	60.7	61.8	63.6	64.8	66.3
80°	47.4	47.9	47.4	47.9	48.6	49.2	48.6	49.2	51.0	52.2	52.2
82.5°	36.7	36.8	37.2	37.3	37.4	37.5	38.3	38.5	39.8	39.6	40.1
85°	21.9	21.2	21.2	21.2	21.9	22.5	21.9	21.9	22.5	22.5	22.5
87.5°	11.9	12.4	12.4	12.4	12.4	12.2	12.0	12.7	12.4	13.0	12.4
90°	20.4	20.4	20.4	20.4	20.4	19.8	18.6	19.8	20.4	21.1	20.4
92.5°	34.3	35.3	34.8	36.8	37.3	41.1	46.3	54.0	68.0	80.5	79.4
95°	70.6	69.9	71.9	76.8	84.8	98.5	124.5	162.2	212.4	242.7	214.9
97.5°	138.9	144.2	153.2	168.4	198.0	242.7	309.7	378.6	434.7	414.4	312.1
100°	221.7	232.8	250.8	277.4	328.8	403.8	488.6	565.4	578.4	489.2	336.8
102.5°	390.1	405.2	427.6	473.1	528.9	608.3	670.4	687.8	631.8	491.7	327.5
105°	697.9	706.5	733.2	771.6	810.0	830.4	822.4	752.4	623.6	458.8	309.0
107.5°	891.4	903.0	908.3	910.5	905.6	875.6	811.2	705.8	569.2	423.7	299.8
110°	949.9	950.5	945.0	933.2	906.6	855.8	776.6	665.7	535.0	406.9	297.9



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	949.0	945.6	935.1	915.4	878.4	820.1	735.4	629.1	511.3	395.9	298.3
115°	918.4	912.8	896.7	868.2	824.2	760.4	679.3	583.9	481.8	384.0	301.0
117.5°	863.7	859.0	842.1	812.0	767.1	707.3	633.7	550.0	463.2	378.1	305.4
120°	828.5	822.4	804.4	775.3	732.0	675.6	610.0	533.1	453.3	374.6	308.4
122.5°	791.9	786.7	770.7	742.1	703.2	652.3	590.2	519.8	444.9	372.6	311.9
125°	745.0	740.0	724.5	701.0	665.0	618.6	564.1	500.3	432.8	369.1	317.0
127.5°	703.9	699.9	686.5	664.5	633.1	590.3	538.8	481.2	421.7	366.9	322.4
130°	680.6	675.6	663.2	642.1	611.8	570.9	522.0	468.7	414.3	366.0	326.4
132.5°	656.2	651.8	640.4	619.4	589.5	551.1	506.2	456.9	408.4	365.5	330.3
135°	617.4	614.9	603.8	583.4	556.7	522.0	481.2	440.3	400.1	364.7	335.0
137.5°	579.2	575.5	565.8	548.2	523.9	493.7	461.2	427.1	394.2	364.6	339.2
140°	553.0	549.3	540.0	523.9	504.1	476.8	448.4	418.6	390.8	364.1	341.2
142.5°	526.7	526.0	517.7	503.1	484.3	461.4	437.0	411.7	387.3	364.1	342.7
145°	492.9	491.1	484.9	474.4	459.5	441.6	422.3	401.9	382.7	362.9	344.3
147.5°	464.5	463.4	459.2	450.8	438.6	425.4	410.4	394.3	378.0	360.7	344.8
150°	447.7	447.1	443.4	435.9	426.7	415.5	402.5	388.9	374.0	359.2	344.3
152.5°	433.3	433.2	430.5	424.1	416.8	407.1	396.1	383.4	370.6	356.7	343.3
155°	414.3	415.5	413.0	408.7	401.9	395.1	385.8	375.9	364.1	352.4	341.8
157.5°	398.1	398.1	397.0	393.3	388.5	383.2	375.4	367.1	358.1	347.9	339.0
160°	387.6	387.6	387.1	384.0	379.6	375.3	368.4	361.6	353.6	344.9	337.5
162.5°	377.7	378.3	377.6	375.5	371.2	367.8	362.0	356.2	349.6	342.5	336.0
165°	363.5	364.1	364.1	361.6	359.2	356.7	352.4	348.0	343.1	337.5	333.2
167.5°	350.4	351.1	351.3	349.9	348.8	346.5	343.6	340.2	336.6	333.2	330.3
170°	342.5	343.6	344.3	342.5	341.8	340.6	338.1	336.3	333.2	330.7	328.8
172.5°	336.0	336.8	337.4	336.5	335.9	335.2	333.2	331.8	329.7	327.7	326.9
175°	327.6	328.8	329.5	328.8	328.8	328.2	327.6	326.9	325.1	324.5	323.8
177.5°	322.5	323.5	324.0	324.0	324.0	324.0	323.5	323.5	322.5	322.0	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1788.9	1784.9	1781.6	1772.8	1768.5	1758.7	1757.3	1756.8	1744.2	1732.0	1728.6
5°	1850.3	1840.6	1826.1	1809.0	1791.4	1773.2	1761.1	1751.4	1727.0	1704.0	1690.7
7.5°	1912.2	1891.3	1866.2	1834.1	1807.2	1777.1	1754.8	1734.7	1700.3	1667.2	1645.0
10°	1958.4	1924.4	1890.9	1846.7	1812.0	1778.1	1746.5	1719.2	1680.3	1636.6	1605.7
12.5°	1987.0	1949.6	1903.6	1860.3	1815.4	1772.3	1730.0	1694.9	1649.2	1604.1	1567.3
15°	2025.8	1985.7	1929.8	1867.9	1810.2	1753.8	1705.3	1661.5	1602.0	1548.0	1503.1
17.5°	2057.5	2002.3	1942.4	1870.7	1804.0	1732.2	1669.7	1613.8	1547.6	1482.4	1429.5
20°	2067.6	2013.0	1943.8	1872.2	1793.3	1708.9	1641.5	1580.8	1509.7	1438.7	1378.0
22.5°	2061.3	2018.8	1941.9	1856.2	1775.3	1687.0	1610.9	1540.5	1461.7	1389.2	1318.7
25°	2018.5	2003.9	1931.0	1837.5	1745.3	1642.7	1554.7	1477.6	1387.7	1310.0	1233.5
27.5°	1918.5	1950.0	1904.8	1805.2	1702.6	1592.7	1493.7	1406.0	1312.7	1225.3	1149.1
30°	1822.4	1894.6	1875.2	1782.9	1668.2	1560.1	1449.1	1357.4	1257.8	1168.0	1092.7
32.5°	1690.8	1810.1	1829.1	1751.8	1633.2	1514.5	1398.0	1306.9	1202.9	1108.3	1034.9
35°	1481.2	1659.7	1741.6	1692.5	1573.5	1445.4	1325.2	1218.9	1114.5	1021.0	948.2
37.5°	1231.2	1474.3	1610.9	1614.4	1505.1	1372.0	1241.0	1135.6	1028.7	936.9	858.2
40°	1069.1	1332.5	1510.4	1549.8	1457.5	1313.7	1181.3	1073.9	969.5	879.6	789.2
42.5°	923.4	1185.8	1404.5	1473.1	1399.8	1256.9	1124.0	1011.7	910.2	825.2	732.8
45°	746.7	976.1	1217.1	1339.7	1299.1	1166.7	1026.5	919.7	824.3	750.9	662.3
47.5°	629.9	791.6	1024.8	1190.6	1189.9	1069.1	931.2	828.9	740.5	671.6	599.9
50°	563.3	704.2	901.5	1089.6	1105.4	1004.1	872.9	771.6	689.0	616.8	559.1
52.5°	503.6	619.6	797.1	977.5	1022.4	934.6	807.4	713.8	633.7	567.2	517.8
55°	425.6	515.4	650.1	818.9	886.9	825.0	712.1	624.6	559.7	503.8	461.4
57.5°	360.0	427.4	535.5	671.4	750.6	711.6	618.5	547.5	491.9	441.3	407.8
60°	318.7	373.9	465.6	579.2	666.5	639.2	559.7	493.5	446.2	402.5	370.9
62.5°	279.9	327.3	405.9	498.0	578.1	566.9	501.9	446.4	404.9	365.1	338.3
65°	225.2	259.8	321.2	393.4	457.7	463.2	416.5	378.8	341.7	310.2	286.5
67.5°	179.4	201.9	245.1	305.9	354.2	371.4	342.9	314.1	284.7	260.3	239.8
70°	151.1	169.4	200.9	250.1	294.5	312.6	296.3	273.8	248.3	228.2	210.6
72.5°	122.5	140.2	163.5	199.6	237.6	257.3	251.6	235.4	214.8	198.1	181.5
75°	92.3	97.8	113.5	137.8	167.5	184.6	188.8	180.3	163.9	151.1	141.4
77.5°	68.2	71.5	79.1	91.8	111.2	126.4	132.6	131.6	120.3	112.9	103.8
80°	54.7	56.5	60.1	65.6	80.2	95.3	99.6	99.6	91.7	88.6	79.5
82.5°	41.5	42.9	45.1	48.1	54.9	68.1	72.9	73.8	68.8	64.8	57.7
85°	23.7	23.1	24.3	26.1	27.3	31.0	38.3	39.5	38.3	33.4	31.5
87.5°	11.6	11.2	10.6	9.7	10.0	10.2	12.1	14.2	12.7	11.6	10.9
90°	16.7	12.4	9.3	7.4	6.2	5.0	2.5	0.6	2.5	5.0	6.2
92.5°	61.8	42.1	28.1	22.3	18.1	15.4	10.9	7.5	10.9	15.4	18.1
95°	143.1	89.2	60.7	45.8	35.9	30.3	24.2	21.7	24.2	30.3	35.9
97.5°	192.7	117.6	81.8	65.0	53.6	45.2	38.7	35.3	38.7	45.2	53.6
100°	203.1	127.5	94.7	77.4	65.0	55.1	49.5	47.7	49.5	55.1	65.0
102.5°	203.6	136.5	106.2	88.8	75.9	66.0	60.4	59.1	60.4	66.0	75.9
105°	206.8	151.7	122.6	105.3	91.7	82.4	78.0	75.6	78.0	82.4	91.7
107.5°	215.4	167.3	139.1	121.6	108.1	99.6	95.4	93.4	95.4	99.6	108.1
110°	222.3	177.7	150.5	132.5	119.5	111.5	107.7	105.3	107.7	111.5	119.5



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	229.7	187.7	161.4	142.9	130.4	122.9	118.7	116.1	118.7	122.9	130.4
115°	240.9	203.1	176.5	159.8	147.3	140.0	136.3	133.2	136.3	140.0	147.3
117.5°	252.8	217.4	192.7	175.4	163.5	156.9	153.2	150.8	153.2	156.9	163.5
120°	260.7	227.3	203.1	185.8	173.4	167.8	164.1	161.6	164.1	167.8	173.4
122.5°	267.7	236.7	214.0	196.1	183.8	177.7	174.0	172.1	174.0	177.7	183.8
125°	278.7	250.8	228.5	211.2	198.8	191.3	187.7	185.8	187.7	191.3	198.8
127.5°	288.9	264.0	242.2	224.4	212.5	204.4	199.2	196.7	199.2	204.4	212.5
130°	295.4	271.9	250.2	232.8	220.5	211.8	205.6	203.1	205.6	211.8	220.5
132.5°	301.8	278.8	258.1	240.7	227.9	218.7	212.1	209.1	212.1	218.7	227.9
135°	310.2	288.6	268.8	251.4	237.2	227.9	220.5	218.0	220.5	227.9	237.2
137.5°	316.7	296.5	276.9	260.9	246.7	236.8	229.3	226.4	229.3	236.8	246.7
140°	320.1	301.0	282.4	266.3	252.6	242.7	235.3	232.8	235.3	242.7	252.6
142.5°	323.1	304.4	286.4	271.2	258.1	248.2	241.3	239.2	241.3	248.2	258.1
145°	326.9	309.7	292.9	279.2	266.9	257.6	251.4	248.9	251.4	257.6	266.9
147.5°	329.1	313.9	298.1	286.0	275.7	267.1	261.2	259.4	261.2	267.1	275.7
150°	330.0	315.8	301.6	290.4	281.1	273.1	268.2	266.3	268.2	273.1	281.1
152.5°	330.6	317.8	305.1	294.9	286.1	279.0	274.1	273.2	274.1	279.0	286.1
155°	331.3	320.8	310.2	301.0	294.1	287.3	283.6	283.0	283.6	287.3	294.1
157.5°	331.3	322.9	313.9	306.2	300.7	294.8	291.8	291.2	291.8	294.8	300.7
160°	331.3	323.8	316.4	309.7	304.7	299.7	297.2	296.6	297.2	299.7	304.7
162.5°	330.8	324.4	317.9	312.6	308.2	304.2	301.7	302.1	301.7	304.2	308.2
165°	329.5	325.1	319.6	315.8	312.8	309.0	307.8	308.4	307.8	309.0	312.8
167.5°	328.6	325.0	320.9	318.5	316.3	313.9	312.8	313.6	312.8	313.9	316.3
170°	327.6	324.5	321.4	319.6	318.3	316.4	315.8	317.0	315.8	316.4	318.3
172.5°	326.1	324.0	321.9	320.5	319.8	317.9	318.3	319.0	318.3	317.9	319.8
175°	324.5	323.2	322.0	321.4	321.4	320.1	320.8	321.4	320.8	320.1	321.4
177.5°	323.5	322.5	322.0	322.0	322.0	321.0	321.5	322.5	321.5	321.0	322.0
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1722.4	1719.0	1712.6	1702.9	1697.1	1686.9	1680.1	1683.9	1685.0	1683.9	1683.0
5°	1676.1	1663.3	1645.8	1628.7	1613.0	1595.9	1586.3	1582.0	1573.5	1568.6	1566.2
7.5°	1620.1	1598.1	1573.3	1543.6	1518.5	1492.2	1478.7	1472.0	1454.6	1445.2	1436.9
10°	1578.3	1543.7	1518.9	1480.0	1456.3	1421.7	1398.0	1398.7	1375.0	1361.6	1351.9
12.5°	1532.2	1494.2	1452.8	1417.8	1385.0	1357.2	1328.6	1317.1	1292.0	1279.1	1252.8
15°	1455.7	1411.4	1367.7	1320.3	1287.0	1243.9	1202.6	1152.2	1111.5	1076.3	1066.6
17.5°	1372.2	1317.3	1273.5	1217.9	1160.7	1088.2	1040.4	1011.1	986.6	968.0	954.2
20°	1314.9	1259.0	1212.3	1128.5	1051.4	1002.3	967.0	944.6	919.1	899.0	888.1
22.5°	1254.7	1196.4	1132.7	1039.2	979.1	939.6	908.2	882.4	865.1	849.5	839.6
25°	1169.2	1105.4	1000.4	936.0	887.5	846.2	824.3	808.6	790.4	769.1	759.5
27.5°	1078.9	977.5	902.1	854.2	807.9	781.0	761.4	737.8	721.5	711.9	701.9
30°	1011.4	910.0	851.1	798.9	766.1	736.3	713.3	700.0	684.1	667.7	661.1
32.5°	936.0	855.1	798.7	755.2	721.9	696.6	678.3	656.7	645.3	635.3	621.2
35°	842.6	781.3	729.7	694.5	662.9	642.3	621.0	608.2	587.6	579.2	573.7
37.5°	763.4	710.3	671.8	634.6	609.6	586.8	573.8	553.5	544.5	532.7	521.3
40°	718.7	666.5	629.5	599.1	571.2	554.2	537.8	521.5	508.1	502.6	488.7
42.5°	673.1	630.6	593.6	560.3	541.6	523.6	502.9	490.8	477.1	468.2	459.5
45°	610.1	572.4	540.9	513.6	492.9	474.1	460.7	440.7	432.8	415.3	408.0
47.5°	554.8	519.8	489.6	463.7	443.5	431.3	411.7	396.0	383.4	372.6	363.3
50°	515.4	486.2	457.1	434.0	415.8	398.2	378.2	370.3	350.9	345.4	339.9
52.5°	479.4	451.8	425.1	402.5	384.3	367.2	349.5	339.2	326.1	320.7	316.6
55°	429.2	402.5	377.0	357.0	338.7	321.2	310.2	297.5	291.4	287.2	282.3
57.5°	378.7	354.7	335.1	314.8	296.5	282.5	269.9	262.2	256.0	250.3	244.5
60°	346.7	323.5	305.9	287.2	268.3	256.7	247.1	238.0	230.7	222.2	219.8
62.5°	312.6	292.5	276.3	258.0	241.6	231.1	221.8	213.2	204.5	192.1	188.7
65°	265.9	250.1	233.1	217.9	203.4	193.1	179.7	170.0	166.4	165.1	164.5
67.5°	223.6	208.7	194.2	178.6	165.3	155.7	149.0	147.5	145.0	144.3	142.5
70°	195.5	181.5	166.9	152.3	139.7	137.8	135.4	132.9	129.9	128.7	127.5
72.5°	170.2	155.7	141.2	129.5	124.1	121.8	119.4	116.9	114.9	113.7	112.9
75°	130.6	117.2	107.4	103.2	100.1	98.3	94.7	92.8	91.7	89.8	89.2
77.5°	94.0	86.4	82.0	79.3	76.1	74.1	72.1	70.3	69.0	68.6	67.7
80°	71.6	68.0	65.0	61.3	60.1	57.7	57.0	55.2	55.8	54.0	54.0
82.5°	55.6	51.0	48.5	46.7	45.6	43.6	43.0	42.1	42.2	40.9	40.9
85°	28.5	27.3	26.1	24.9	24.9	23.1	23.7	23.1	23.1	21.9	21.2
87.5°	10.7	10.6	10.2	11.1	11.9	11.5	11.4	10.8	10.5	10.8	10.4
90°	7.4	9.3	12.4	16.7	20.4	21.1	20.4	19.8	18.6	19.8	20.4
92.5°	22.3	28.1	42.1	61.8	79.4	80.5	68.0	54.0	46.3	41.1	37.3
95°	45.8	60.7	89.2	143.1	214.9	242.7	212.4	162.2	124.5	98.5	84.8
97.5°	65.0	81.8	117.6	192.7	312.1	414.4	434.7	378.6	309.7	242.7	198.0
100°	77.4	94.7	127.5	203.1	336.8	489.2	578.4	565.4	488.6	403.8	328.8
102.5°	88.8	106.2	136.5	203.6	327.5	491.7	631.8	687.8	670.4	608.3	528.9
105°	105.3	122.6	151.7	206.8	309.0	458.8	623.6	752.4	822.4	830.4	810.0
107.5°	121.6	139.1	167.3	215.4	299.8	423.7	569.2	705.8	811.2	875.6	905.6
110°	132.5	150.5	177.7	222.3	297.9	406.9	535.0	665.7	776.6	855.8	906.6



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	142.9	161.4	187.7	229.7	298.3	395.9	511.3	629.1	735.4	820.1	878.4
115°	159.8	176.5	203.1	240.9	301.0	384.0	481.8	583.9	679.3	760.4	824.2
117.5°	175.4	192.7	217.4	252.8	305.4	378.1	463.2	550.0	633.7	707.3	767.1
120°	185.8	203.1	227.3	260.7	308.4	374.6	453.3	533.1	610.0	675.6	732.0
122.5°	196.1	214.0	236.7	267.7	311.9	372.6	444.9	519.8	590.2	652.3	703.2
125°	211.2	228.5	250.8	278.7	317.0	369.1	432.8	500.3	564.1	618.6	665.0
127.5°	224.4	242.2	264.0	288.9	322.4	366.9	421.7	481.2	538.8	590.3	633.1
130°	232.8	250.2	271.9	295.4	326.4	366.0	414.3	468.7	522.0	570.9	611.8
132.5°	240.7	258.1	278.8	301.8	330.3	365.5	408.4	456.9	506.2	551.1	589.5
135°	251.4	268.8	288.6	310.2	335.0	364.7	400.1	440.3	481.2	522.0	556.7
137.5°	260.9	276.9	296.5	316.7	339.2	364.6	394.2	427.1	461.2	493.7	523.9
140°	266.3	282.4	301.0	320.1	341.2	364.1	390.8	418.6	448.4	476.8	504.1
142.5°	271.2	286.4	304.4	323.1	342.7	364.1	387.3	411.7	437.0	461.4	484.3
145°	279.2	292.9	309.7	326.9	344.3	362.9	382.7	401.9	422.3	441.6	459.5
147.5°	286.0	298.1	313.9	329.1	344.8	360.7	378.0	394.3	410.4	425.4	438.6
150°	290.4	301.6	315.8	330.0	344.3	359.2	374.0	388.9	402.5	415.5	426.7
152.5°	294.9	305.1	317.8	330.6	343.3	356.7	370.6	383.4	396.1	407.1	416.8
155°	301.0	310.2	320.8	331.3	341.8	352.4	364.1	375.9	385.8	395.1	401.9
157.5°	306.2	313.9	322.9	331.3	339.0	347.9	358.1	367.1	375.4	383.2	388.5
160°	309.7	316.4	323.8	331.3	337.5	344.9	353.6	361.6	368.4	375.3	379.6
162.5°	312.6	317.9	324.4	330.8	336.0	342.5	349.6	356.2	362.0	367.8	371.2
165°	315.8	319.6	325.1	329.5	333.2	337.5	343.1	348.0	352.4	356.7	359.2
167.5°	318.5	320.9	325.0	328.6	330.3	333.2	336.6	340.2	343.6	346.5	348.8
170°	319.6	321.4	324.5	327.6	328.8	330.7	333.2	336.3	338.1	340.6	341.8
172.5°	320.5	321.9	324.0	326.1	326.9	327.7	329.7	331.8	333.2	335.2	335.9
175°	321.4	322.0	323.2	324.5	323.8	324.5	325.1	326.9	327.6	328.2	328.8
177.5°	322.0	322.0	322.5	323.5	322.5	322.0	322.5	323.5	323.5	324.0	324.0
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1677.7	1678.6	1677.2	1678.2	1677.2	1678.6	1677.7	1683.0	1683.9	1685.0	1683.9
5°	1563.1	1555.8	1554.7	1552.8	1554.7	1555.8	1563.1	1566.2	1568.6	1573.5	1582.0
7.5°	1426.5	1425.4	1422.4	1418.1	1422.4	1425.4	1426.5	1436.9	1445.2	1454.6	1472.0
10°	1338.6	1335.5	1334.9	1330.6	1334.9	1335.5	1338.6	1351.9	1361.6	1375.0	1398.7
12.5°	1235.6	1216.1	1214.0	1203.4	1214.0	1216.1	1235.6	1252.8	1279.1	1292.0	1317.1
15°	1052.0	1048.4	1036.3	1028.3	1036.3	1048.4	1052.0	1066.6	1076.3	1111.5	1152.2
17.5°	947.1	935.3	931.4	929.8	931.4	935.3	947.1	954.2	968.0	986.6	1011.1
20°	879.6	868.7	866.9	865.7	866.9	868.7	879.6	888.1	899.0	919.1	944.6
22.5°	833.0	821.6	816.8	813.2	816.8	821.6	833.0	839.6	849.5	865.1	882.4
25°	753.4	749.1	746.7	745.4	746.7	749.1	753.4	759.5	769.1	790.4	808.6
27.5°	691.1	681.8	679.9	676.8	679.9	681.8	691.1	701.9	711.9	721.5	737.8
30°	655.6	652.6	648.3	644.7	648.3	652.6	655.6	661.1	667.7	684.1	700.0
32.5°	613.9	611.3	607.5	605.9	607.5	611.3	613.9	621.2	635.3	645.3	656.7
35°	567.6	559.1	555.5	550.0	555.5	559.1	567.6	573.7	579.2	587.6	608.2
37.5°	518.6	514.2	509.1	510.9	509.1	514.2	518.6	521.3	532.7	544.5	553.5
40°	480.8	477.8	476.6	475.9	476.6	477.8	480.8	488.7	502.6	508.1	521.5
42.5°	450.7	442.3	439.1	439.0	439.1	442.3	450.7	459.5	468.2	477.1	490.8
45°	404.9	397.0	391.6	392.1	391.6	397.0	404.9	408.0	415.3	432.8	440.7
47.5°	358.1	357.8	354.4	355.5	354.4	357.8	358.1	363.3	372.6	383.4	396.0
50°	335.7	332.1	329.6	330.3	329.6	332.1	335.7	339.9	345.4	350.9	370.3
52.5°	314.3	311.2	309.3	311.8	309.3	311.2	314.3	316.6	320.7	326.1	339.2
55°	279.2	275.6	275.0	274.4	275.0	275.6	279.2	282.3	287.2	291.4	297.5
57.5°	240.0	237.6	233.9	232.3	233.9	237.6	240.0	244.5	250.3	256.0	262.2
60°	211.8	207.0	200.9	200.3	200.9	207.0	211.8	219.8	222.2	230.7	238.0
62.5°	186.1	185.1	183.9	183.8	183.9	185.1	186.1	188.7	192.1	204.5	213.2
65°	163.3	162.7	163.3	163.9	163.3	162.7	163.3	164.5	165.1	166.4	170.0
67.5°	142.3	141.2	140.1	140.6	140.1	141.2	142.3	142.5	144.3	145.0	147.5
70°	126.3	125.6	125.1	125.1	125.1	125.6	126.3	127.5	128.7	129.9	132.9
72.5°	110.7	110.6	110.0	109.5	110.0	110.6	110.7	112.9	113.7	114.9	116.9
75°	88.6	87.4	87.4	87.4	87.4	87.4	88.6	89.2	89.8	91.7	92.8
77.5°	67.5	66.9	66.3	65.8	66.3	66.9	67.5	67.7	68.6	69.0	70.3
80°	53.4	52.8	52.2	52.2	52.2	52.8	53.4	54.0	54.0	55.8	55.2
82.5°	40.8	40.2	40.1	39.6	40.1	40.2	40.8	40.9	40.9	42.2	42.1
85°	21.9	22.5	21.9	23.1	21.9	22.5	21.9	21.2	21.9	23.1	23.1
87.5°	10.4	9.9	10.4	9.9	10.4	9.9	10.4	10.4	10.8	10.5	10.8
90°	20.4	20.4	20.4	20.4	20.4	20.4	20.4	20.4	19.8	18.6	19.8
92.5°	36.8	34.8	35.3	34.3	35.3	34.8	36.8	37.3	41.1	46.3	54.0
95°	76.8	71.9	69.9	70.6	69.9	71.9	76.8	84.8	98.5	124.5	162.2
97.5°	168.4	153.2	144.2	138.9	144.2	153.2	168.4	198.0	242.7	309.7	378.6
100°	277.4	250.8	232.8	221.7	232.8	250.8	277.4	328.8	403.8	488.6	565.4
102.5°	473.1	427.6	405.2	390.1	405.2	427.6	473.1	528.9	608.3	670.4	687.8
105°	771.6	733.2	706.5	697.9	706.5	733.2	771.6	810.0	830.4	822.4	752.4
107.5°	910.5	908.3	903.0	891.4	903.0	908.3	910.5	905.6	875.6	811.2	705.8
110°	933.2	945.0	950.5	949.9	950.5	945.0	933.2	906.6	855.8	776.6	665.7



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	915.4	935.1	945.6	949.0	945.6	935.1	915.4	878.4	820.1	735.4	629.1
115°	868.2	896.7	912.8	918.4	912.8	896.7	868.2	824.2	760.4	679.3	583.9
117.5°	812.0	842.1	859.0	863.7	859.0	842.1	812.0	767.1	707.3	633.7	550.0
120°	775.3	804.4	822.4	828.5	822.4	804.4	775.3	732.0	675.6	610.0	533.1
122.5°	742.1	770.7	786.7	791.9	786.7	770.7	742.1	703.2	652.3	590.2	519.8
125°	701.0	724.5	740.0	745.0	740.0	724.5	701.0	665.0	618.6	564.1	500.3
127.5°	664.5	686.5	699.9	703.9	699.9	686.5	664.5	633.1	590.3	538.8	481.2
130°	642.1	663.2	675.6	680.6	675.6	663.2	642.1	611.8	570.9	522.0	468.7
132.5°	619.4	640.4	651.8	656.2	651.8	640.4	619.4	589.5	551.1	506.2	456.9
135°	583.4	603.8	614.9	617.4	614.9	603.8	583.4	556.7	522.0	481.2	440.3
137.5°	548.2	565.8	575.5	579.2	575.5	565.8	548.2	523.9	493.7	461.2	427.1
140°	523.9	540.0	549.3	553.0	549.3	540.0	523.9	504.1	476.8	448.4	418.6
142.5°	503.1	517.7	526.0	526.7	526.0	517.7	503.1	484.3	461.4	437.0	411.7
145°	474.4	484.9	491.1	492.9	491.1	484.9	474.4	459.5	441.6	422.3	401.9
147.5°	450.8	459.2	463.4	464.5	463.4	459.2	450.8	438.6	425.4	410.4	394.3
150°	435.9	443.4	447.1	447.7	447.1	443.4	435.9	426.7	415.5	402.5	388.9
152.5°	424.1	430.5	433.2	433.3	433.2	430.5	424.1	416.8	407.1	396.1	383.4
155°	408.7	413.0	415.5	414.3	415.5	413.0	408.7	401.9	395.1	385.8	375.9
157.5°	393.3	397.0	398.1	398.1	398.1	397.0	393.3	388.5	383.2	375.4	367.1
160°	384.0	387.1	387.6	387.6	387.6	387.1	384.0	379.6	375.3	368.4	361.6
162.5°	375.5	377.6	378.3	377.7	378.3	377.6	375.5	371.2	367.8	362.0	356.2
165°	361.6	364.1	364.1	363.5	364.1	364.1	361.6	359.2	356.7	352.4	348.0
167.5°	349.9	351.3	351.1	350.4	351.1	351.3	349.9	348.8	346.5	343.6	340.2
170°	342.5	344.3	343.6	342.5	343.6	344.3	342.5	341.8	340.6	338.1	336.3
172.5°	336.5	337.4	336.8	336.0	336.8	337.4	336.5	335.9	335.2	333.2	331.8
175°	328.8	329.5	328.8	327.6	328.8	329.5	328.8	328.8	328.2	327.6	326.9
177.5°	324.0	324.0	323.5	322.5	323.5	324.0	324.0	324.0	324.0	323.5	323.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1680.1	1686.9	1697.1	1702.9	1712.6	1719.0	1722.4	1728.6	1732.0	1744.2	1756.8
5°	1586.3	1595.9	1613.0	1628.7	1645.8	1663.3	1676.1	1690.7	1704.0	1727.0	1751.4
7.5°	1478.7	1492.2	1518.5	1543.6	1573.3	1598.1	1620.1	1645.0	1667.2	1700.3	1734.7
10°	1398.0	1421.7	1456.3	1480.0	1518.9	1543.7	1578.3	1605.7	1636.6	1680.3	1719.2
12.5°	1328.6	1357.2	1385.0	1417.8	1452.8	1494.2	1532.2	1567.3	1604.1	1649.2	1694.9
15°	1202.6	1243.9	1287.0	1320.3	1367.7	1411.4	1455.7	1503.1	1548.0	1602.0	1661.5
17.5°	1040.4	1088.2	1160.7	1217.9	1273.5	1317.3	1372.2	1429.5	1482.4	1547.6	1613.8
20°	967.0	1002.3	1051.4	1128.5	1212.3	1259.0	1314.9	1378.0	1438.7	1509.7	1580.8
22.5°	908.2	939.6	979.1	1039.2	1132.7	1196.4	1254.7	1318.7	1389.2	1461.7	1540.5
25°	824.3	846.2	887.5	936.0	1000.4	1105.4	1169.2	1233.5	1310.0	1387.7	1477.6
27.5°	761.4	781.0	807.9	854.2	902.1	977.5	1078.9	1149.1	1225.3	1312.7	1406.0
30°	713.3	736.3	766.1	798.9	851.1	910.0	1011.4	1092.7	1168.0	1257.8	1357.4
32.5°	678.3	696.6	721.9	755.2	798.7	855.1	936.0	1034.9	1108.3	1202.9	1306.9
35°	621.0	642.3	662.9	694.5	729.7	781.3	842.6	948.2	1021.0	1114.5	1218.9
37.5°	573.8	586.8	609.6	634.6	671.8	710.3	763.4	858.2	936.9	1028.7	1135.6
40°	537.8	554.2	571.2	599.1	629.5	666.5	718.7	789.2	879.6	969.5	1073.9
42.5°	502.9	523.6	541.6	560.3	593.6	630.6	673.1	732.8	825.2	910.2	1011.7
45°	460.7	474.1	492.9	513.6	540.9	572.4	610.1	662.3	750.9	824.3	919.7
47.5°	411.7	431.3	443.5	463.7	489.6	519.8	554.8	599.9	671.6	740.5	828.9
50°	378.2	398.2	415.8	434.0	457.1	486.2	515.4	559.1	616.8	689.0	771.6
52.5°	349.5	367.2	384.3	402.5	425.1	451.8	479.4	517.8	567.2	633.7	713.8
55°	310.2	321.2	338.7	357.0	377.0	402.5	429.2	461.4	503.8	559.7	624.6
57.5°	269.9	282.5	296.5	314.8	335.1	354.7	378.7	407.8	441.3	491.9	547.5
60°	247.1	256.7	268.3	287.2	305.9	323.5	346.7	370.9	402.5	446.2	493.5
62.5°	221.8	231.1	241.6	258.0	276.3	292.5	312.6	338.3	365.1	404.9	446.4
65°	179.7	193.1	203.4	217.9	233.1	250.1	265.9	286.5	310.2	341.7	378.8
67.5°	149.0	155.7	165.3	178.6	194.2	208.7	223.6	239.8	260.3	284.7	314.1
70°	135.4	137.8	139.7	152.3	166.9	181.5	195.5	210.6	228.2	248.3	273.8
72.5°	119.4	121.8	124.1	129.5	141.2	155.7	170.2	181.5	198.1	214.8	235.4
75°	94.7	98.3	100.1	103.2	107.4	117.2	130.6	141.4	151.1	163.9	180.3
77.5°	72.1	74.1	76.1	79.3	82.0	86.4	94.0	103.8	112.9	120.3	131.6
80°	57.0	57.7	60.1	61.3	65.0	68.0	71.6	79.5	88.6	91.7	99.6
82.5°	43.0	43.6	45.6	46.7	48.5	51.0	55.6	57.7	64.8	68.8	73.8
85°	23.7	23.1	24.9	24.9	26.1	27.3	28.5	31.5	33.4	38.3	39.5
87.5°	11.4	11.5	11.9	11.1	10.2	10.6	10.7	10.9	11.6	12.7	14.2
90°	20.4	21.1	20.4	16.7	12.4	9.3	7.4	6.2	5.0	2.5	0.6
92.5°	68.0	80.5	79.4	61.8	42.1	28.1	22.3	18.1	15.4	10.9	7.5
95°	212.4	242.7	214.9	143.1	89.2	60.7	45.8	35.9	30.3	24.2	21.7
97.5°	434.7	414.4	312.1	192.7	117.6	81.8	65.0	53.6	45.2	38.7	35.3
100°	578.4	489.2	336.8	203.1	127.5	94.7	77.4	65.0	55.1	49.5	47.7
102.5°	631.8	491.7	327.5	203.6	136.5	106.2	88.8	75.9	66.0	60.4	59.1
105°	623.6	458.8	309.0	206.8	151.7	122.6	105.3	91.7	82.4	78.0	75.6
107.5°	569.2	423.7	299.8	215.4	167.3	139.1	121.6	108.1	99.6	95.4	93.4
110°	535.0	406.9	297.9	222.3	177.7	150.5	132.5	119.5	111.5	107.7	105.3



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	511.3	395.9	298.3	229.7	187.7	161.4	142.9	130.4	122.9	118.7	116.1
115°	481.8	384.0	301.0	240.9	203.1	176.5	159.8	147.3	140.0	136.3	133.2
117.5°	463.2	378.1	305.4	252.8	217.4	192.7	175.4	163.5	156.9	153.2	150.8
120°	453.3	374.6	308.4	260.7	227.3	203.1	185.8	173.4	167.8	164.1	161.6
122.5°	444.9	372.6	311.9	267.7	236.7	214.0	196.1	183.8	177.7	174.0	172.1
125°	432.8	369.1	317.0	278.7	250.8	228.5	211.2	198.8	191.3	187.7	185.8
127.5°	421.7	366.9	322.4	288.9	264.0	242.2	224.4	212.5	204.4	199.2	196.7
130°	414.3	366.0	326.4	295.4	271.9	250.2	232.8	220.5	211.8	205.6	203.1
132.5°	408.4	365.5	330.3	301.8	278.8	258.1	240.7	227.9	218.7	212.1	209.1
135°	400.1	364.7	335.0	310.2	288.6	268.8	251.4	237.2	227.9	220.5	218.0
137.5°	394.2	364.6	339.2	316.7	296.5	276.9	260.9	246.7	236.8	229.3	226.4
140°	390.8	364.1	341.2	320.1	301.0	282.4	266.3	252.6	242.7	235.3	232.8
142.5°	387.3	364.1	342.7	323.1	304.4	286.4	271.2	258.1	248.2	241.3	239.2
145°	382.7	362.9	344.3	326.9	309.7	292.9	279.2	266.9	257.6	251.4	248.9
147.5°	378.0	360.7	344.8	329.1	313.9	298.1	286.0	275.7	267.1	261.2	259.4
150°	374.0	359.2	344.3	330.0	315.8	301.6	290.4	281.1	273.1	268.2	266.3
152.5°	370.6	356.7	343.3	330.6	317.8	305.1	294.9	286.1	279.0	274.1	273.2
155°	364.1	352.4	341.8	331.3	320.8	310.2	301.0	294.1	287.3	283.6	283.0
157.5°	358.1	347.9	339.0	331.3	322.9	313.9	306.2	300.7	294.8	291.8	291.2
160°	353.6	344.9	337.5	331.3	323.8	316.4	309.7	304.7	299.7	297.2	296.6
162.5°	349.6	342.5	336.0	330.8	324.4	317.9	312.6	308.2	304.2	301.7	302.1
165°	343.1	337.5	333.2	329.5	325.1	319.6	315.8	312.8	309.0	307.8	308.4
167.5°	336.6	333.2	330.3	328.6	325.0	320.9	318.5	316.3	313.9	312.8	313.6
170°	333.2	330.7	328.8	327.6	324.5	321.4	319.6	318.3	316.4	315.8	317.0
172.5°	329.7	327.7	326.9	326.1	324.0	321.9	320.5	319.8	317.9	318.3	319.0
175°	325.1	324.5	323.8	324.5	323.2	322.0	321.4	321.4	320.1	320.8	321.4
177.5°	322.5	322.0	322.5	323.5	322.5	322.0	322.0	322.0	321.0	321.5	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1757.3	1758.7	1768.5	1772.8	1781.6	1784.9	1788.9	1787.9	1787.9	1789.9	1803.4
5°	1761.1	1773.2	1791.4	1809.0	1826.1	1840.6	1850.3	1860.0	1863.7	1881.3	1897.0
7.5°	1754.8	1777.1	1807.2	1834.1	1866.2	1891.3	1912.2	1931.0	1943.9	1969.5	1995.7
10°	1746.5	1778.1	1812.0	1846.7	1890.9	1924.4	1958.4	1984.5	1993.0	2031.2	2053.1
12.5°	1730.0	1772.3	1815.4	1860.3	1903.6	1949.6	1987.0	2013.1	2043.0	2077.3	2117.7
15°	1705.3	1753.8	1810.2	1867.9	1929.8	1985.7	2025.8	2071.2	2104.0	2141.7	2176.9
17.5°	1669.7	1732.2	1804.0	1870.7	1942.4	2002.3	2057.5	2101.1	2124.2	2145.7	2150.9
20°	1641.5	1708.9	1793.3	1872.2	1943.8	2013.0	2067.6	2104.0	2110.1	2110.7	2078.5
22.5°	1610.9	1687.0	1775.3	1856.2	1941.9	2018.8	2061.3	2076.9	2052.8	2011.7	1949.4
25°	1554.7	1642.7	1745.3	1837.5	1931.0	2003.9	2018.5	1991.2	1906.8	1818.1	1705.8
27.5°	1493.7	1592.7	1702.6	1805.2	1904.8	1950.0	1918.5	1820.0	1668.1	1536.0	1375.9
30°	1449.1	1560.1	1668.2	1782.9	1875.2	1894.6	1822.4	1677.3	1500.0	1300.9	1141.3
32.5°	1398.0	1514.5	1633.2	1751.8	1829.1	1810.1	1690.8	1512.2	1304.3	1108.6	957.7
35°	1325.2	1445.4	1573.5	1692.5	1741.6	1659.7	1481.2	1248.7	1036.3	853.5	749.7
37.5°	1241.0	1372.0	1505.1	1614.4	1610.9	1474.3	1231.2	991.2	812.6	704.6	630.6
40°	1181.3	1313.7	1457.5	1549.8	1510.4	1332.5	1069.1	842.6	712.1	625.9	571.9
42.5°	1124.0	1256.9	1399.8	1473.1	1404.5	1185.8	923.4	745.9	638.3	571.0	527.2
45°	1026.5	1166.7	1299.1	1339.7	1217.1	976.1	746.7	618.0	546.4	496.5	466.2
47.5°	931.2	1069.1	1189.9	1190.6	1024.8	791.6	629.9	534.8	473.6	435.1	413.0
50°	872.9	1004.1	1105.4	1089.6	901.5	704.2	563.3	481.4	430.4	400.7	377.6
52.5°	807.4	934.6	1022.4	977.5	797.1	619.6	503.6	434.7	392.5	366.6	346.0
55°	712.1	825.0	886.9	818.9	650.1	515.4	425.6	371.5	339.9	318.1	300.5
57.5°	618.5	711.6	750.6	671.4	535.5	427.4	360.0	319.4	288.1	272.4	263.3
60°	559.7	639.2	666.5	579.2	465.6	373.9	318.7	281.1	258.0	247.7	238.6
62.5°	501.9	566.9	578.1	498.0	405.9	327.3	279.9	248.0	232.7	222.9	214.3
65°	416.5	463.2	457.7	393.4	321.2	259.8	225.2	205.8	194.2	180.3	165.1
67.5°	342.9	371.4	354.2	305.9	245.1	201.9	179.4	164.6	150.3	137.0	133.6
70°	296.3	312.6	294.5	250.1	200.9	169.4	151.1	133.6	125.1	122.0	116.5
72.5°	251.6	257.3	237.6	199.6	163.5	140.2	122.5	112.6	108.1	105.5	102.0
75°	188.8	184.6	167.5	137.8	113.5	97.8	92.3	88.6	85.6	83.2	81.4
77.5°	132.6	126.4	111.2	91.8	79.1	71.5	68.2	66.3	64.8	63.6	61.8
80°	99.6	95.3	80.2	65.6	60.1	56.5	54.7	52.2	52.2	51.0	49.2
82.5°	72.9	68.1	54.9	48.1	45.1	42.9	41.5	40.1	39.6	39.8	38.5
85°	38.3	31.0	27.3	26.1	24.3	23.1	23.7	22.5	22.5	22.5	21.9
87.5°	12.1	10.2	10.0	9.7	10.6	11.2	11.6	12.4	13.0	12.4	12.7
90°	2.5	5.0	6.2	7.4	9.3	12.4	16.7	20.4	21.1	20.4	19.8
92.5°	10.9	15.4	18.1	22.3	28.1	42.1	61.8	79.4	80.5	68.0	54.0
95°	24.2	30.3	35.9	45.8	60.7	89.2	143.1	214.9	242.7	212.4	162.2
97.5°	38.7	45.2	53.6	65.0	81.8	117.6	192.7	312.1	414.4	434.7	378.6
100°	49.5	55.1	65.0	77.4	94.7	127.5	203.1	336.8	489.2	578.4	565.4
102.5°	60.4	66.0	75.9	88.8	106.2	136.5	203.6	327.5	491.7	631.8	687.8
105°	78.0	82.4	91.7	105.3	122.6	151.7	206.8	309.0	458.8	623.6	752.4
107.5°	95.4	99.6	108.1	121.6	139.1	167.3	215.4	299.8	423.7	569.2	705.8
110°	107.7	111.5	119.5	132.5	150.5	177.7	222.3	297.9	406.9	535.0	665.7



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	118.7	122.9	130.4	142.9	161.4	187.7	229.7	298.3	395.9	511.3	629.1
115°	136.3	140.0	147.3	159.8	176.5	203.1	240.9	301.0	384.0	481.8	583.9
117.5°	153.2	156.9	163.5	175.4	192.7	217.4	252.8	305.4	378.1	463.2	550.0
120°	164.1	167.8	173.4	185.8	203.1	227.3	260.7	308.4	374.6	453.3	533.1
122.5°	174.0	177.7	183.8	196.1	214.0	236.7	267.7	311.9	372.6	444.9	519.8
125°	187.7	191.3	198.8	211.2	228.5	250.8	278.7	317.0	369.1	432.8	500.3
127.5°	199.2	204.4	212.5	224.4	242.2	264.0	288.9	322.4	366.9	421.7	481.2
130°	205.6	211.8	220.5	232.8	250.2	271.9	295.4	326.4	366.0	414.3	468.7
132.5°	212.1	218.7	227.9	240.7	258.1	278.8	301.8	330.3	365.5	408.4	456.9
135°	220.5	227.9	237.2	251.4	268.8	288.6	310.2	335.0	364.7	400.1	440.3
137.5°	229.3	236.8	246.7	260.9	276.9	296.5	316.7	339.2	364.6	394.2	427.1
140°	235.3	242.7	252.6	266.3	282.4	301.0	320.1	341.2	364.1	390.8	418.6
142.5°	241.3	248.2	258.1	271.2	286.4	304.4	323.1	342.7	364.1	387.3	411.7
145°	251.4	257.6	266.9	279.2	292.9	309.7	326.9	344.3	362.9	382.7	401.9
147.5°	261.2	267.1	275.7	286.0	298.1	313.9	329.1	344.8	360.7	378.0	394.3
150°	268.2	273.1	281.1	290.4	301.6	315.8	330.0	344.3	359.2	374.0	388.9
152.5°	274.1	279.0	286.1	294.9	305.1	317.8	330.6	343.3	356.7	370.6	383.4
155°	283.6	287.3	294.1	301.0	310.2	320.8	331.3	341.8	352.4	364.1	375.9
157.5°	291.8	294.8	300.7	306.2	313.9	322.9	331.3	339.0	347.9	358.1	367.1
160°	297.2	299.7	304.7	309.7	316.4	323.8	331.3	337.5	344.9	353.6	361.6
162.5°	301.7	304.2	308.2	312.6	317.9	324.4	330.8	336.0	342.5	349.6	356.2
165°	307.8	309.0	312.8	315.8	319.6	325.1	329.5	333.2	337.5	343.1	348.0
167.5°	312.8	313.9	316.3	318.5	320.9	325.0	328.6	330.3	333.2	336.6	340.2
170°	315.8	316.4	318.3	319.6	321.4	324.5	327.6	328.8	330.7	333.2	336.3
172.5°	318.3	317.9	319.8	320.5	321.9	324.0	326.1	326.9	327.7	329.7	331.8
175°	320.8	320.1	321.4	321.4	322.0	323.2	324.5	323.8	324.5	325.1	326.9
177.5°	321.5	321.0	322.0	322.0	322.0	322.5	323.5	322.5	322.0	322.5	323.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0	322.0



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1	1747.1
2.5°	1808.3	1814.6	1817.5	1817.5	1820.9	1819.5	1818.0
5°	1912.2	1923.7	1926.2	1937.1	1945.0	1942.6	1943.8
7.5°	2015.5	2034.1	2052.5	2060.9	2062.1	2067.0	2068.9
10°	2079.2	2094.4	2122.9	2118.6	2139.8	2152.0	2132.0
12.5°	2140.3	2160.8	2180.6	2186.1	2198.1	2202.0	2194.1
15°	2195.7	2206.6	2207.9	2204.8	2208.4	2205.4	2193.9
17.5°	2144.0	2126.3	2090.3	2073.3	2059.8	2039.9	2031.9
20°	2058.5	2006.3	1945.6	1921.4	1892.8	1836.9	1850.3
22.5°	1874.0	1814.5	1753.8	1682.9	1649.0	1596.1	1592.9
25°	1586.8	1484.2	1371.3	1292.4	1246.3	1193.5	1170.4
27.5°	1233.7	1104.6	1012.1	965.2	922.6	880.7	879.0
30°	1001.6	904.5	832.9	792.8	766.7	749.1	752.7
32.5°	844.3	777.8	729.4	696.2	676.8	663.6	663.4
35°	690.2	644.7	613.7	599.8	585.8	576.1	576.7
37.5°	590.7	563.3	546.1	530.7	522.0	517.2	514.5
40°	539.6	517.2	503.8	494.7	487.4	480.8	479.6
42.5°	499.4	480.8	467.5	460.3	453.4	448.8	447.5
45°	443.1	427.9	415.8	408.0	404.9	400.7	400.7
47.5°	394.2	379.3	369.8	364.9	359.7	356.8	356.7
50°	361.2	349.7	341.2	338.1	333.9	332.1	331.4
52.5°	331.6	323.0	316.9	314.8	313.0	310.7	311.1
55°	291.4	286.5	284.1	282.3	279.2	275.6	278.1
57.5°	257.5	253.4	246.8	241.1	238.4	235.8	236.8
60°	233.7	225.2	216.7	210.0	208.2	202.7	202.7
62.5°	203.6	191.7	181.3	177.5	175.7	173.2	172.6
65°	156.6	151.8	149.3	146.9	145.7	145.7	144.5
67.5°	129.8	127.9	125.2	124.5	123.3	123.0	122.6
70°	114.7	112.3	111.1	110.5	109.2	109.9	108.1
72.5°	100.1	98.2	98.0	96.4	95.7	95.8	94.4
75°	78.9	78.9	78.3	77.7	76.5	75.9	76.5
77.5°	60.7	60.8	59.7	59.7	59.5	59.7	59.0
80°	48.6	49.2	48.6	47.9	47.4	47.9	47.4
82.5°	38.3	37.5	37.4	37.3	37.2	36.8	36.7
85°	21.9	22.5	21.9	21.2	21.2	21.2	21.9
87.5°	12.0	12.2	12.4	12.4	12.4	12.4	11.9
90°	18.6	19.8	20.4	20.4	20.4	20.4	20.4
92.5°	46.3	41.1	37.3	36.8	34.8	35.3	34.3
95°	124.5	98.5	84.8	76.8	71.9	69.9	70.6
97.5°	309.7	242.7	198.0	168.4	153.2	144.2	138.9
100°	488.6	403.8	328.8	277.4	250.8	232.8	221.7
102.5°	670.4	608.3	528.9	473.1	427.6	405.2	390.1
105°	822.4	830.4	810.0	771.6	733.2	706.5	697.9
107.5°	811.2	875.6	905.6	910.5	908.3	903.0	891.4
110°	776.6	855.8	906.6	933.2	945.0	950.5	949.9



TEST NUMBER: P331749-927

CATALOG NUMBER: SA2XXRDIP-C1005D725U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	735.4	820.1	878.4	915.4	935.1	945.6	949.0
115°	679.3	760.4	824.2	868.2	896.7	912.8	918.4
117.5°	633.7	707.3	767.1	812.0	842.1	859.0	863.7
120°	610.0	675.6	732.0	775.3	804.4	822.4	828.5
122.5°	590.2	652.3	703.2	742.1	770.7	786.7	791.9
125°	564.1	618.6	665.0	701.0	724.5	740.0	745.0
127.5°	538.8	590.3	633.1	664.5	686.5	699.9	703.9
130°	522.0	570.9	611.8	642.1	663.2	675.6	680.6
132.5°	506.2	551.1	589.5	619.4	640.4	651.8	656.2
135°	481.2	522.0	556.7	583.4	603.8	614.9	617.4
137.5°	461.2	493.7	523.9	548.2	565.8	575.5	579.2
140°	448.4	476.8	504.1	523.9	540.0	549.3	553.0
142.5°	437.0	461.4	484.3	503.1	517.7	526.0	526.7
145°	422.3	441.6	459.5	474.4	484.9	491.1	492.9
147.5°	410.4	425.4	438.6	450.8	459.2	463.4	464.5
150°	402.5	415.5	426.7	435.9	443.4	447.1	447.7
152.5°	396.1	407.1	416.8	424.1	430.5	433.2	433.3
155°	385.8	395.1	401.9	408.7	413.0	415.5	414.3
157.5°	375.4	383.2	388.5	393.3	397.0	398.1	398.1
160°	368.4	375.3	379.6	384.0	387.1	387.6	387.6
162.5°	362.0	367.8	371.2	375.5	377.6	378.3	377.7
165°	352.4	356.7	359.2	361.6	364.1	364.1	363.5
167.5°	343.6	346.5	348.8	349.9	351.3	351.1	350.4
170°	338.1	340.6	341.8	342.5	344.3	343.6	342.5
172.5°	333.2	335.2	335.9	336.5	337.4	336.8	336.0
175°	327.6	328.2	328.8	328.8	329.5	328.8	327.6
177.5°	323.5	324.0	324.0	324.0	324.0	323.5	322.5
180°	322.0	322.0	322.0	322.0	322.0	322.0	322.0

(END OF REPORT)