

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331332

Luminaire Tested: **SA2XXDIP-C675D330U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331332  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4210.6 lumens  
Efficiency: N/A  
Efficacy: 120.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331332  
CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	70	
1	103	99	95	91	97	93	90	87	84	81	79	75	73	71	67	65	64	64	64	64	60	
2	94	87	81	76	89	83	77	73	74	70	66	67	63	61	59	57	55	55	55	55	51	
3	86	77	70	64	82	73	67	62	66	61	57	59	55	52	53	50	48	48	48	48	44	
4	79	69	61	55	75	65	58	53	59	54	49	53	49	45	48	45	42	42	42	42	39	
5	73	62	54	48	69	59	52	46	53	47	43	48	44	40	44	40	37	37	37	37	34	
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	33	33	33	30	
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	33	29	29	29	29	27	
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	27	27	27	24	
9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	24	24	24	22	
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	22	22	22	20	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	21447	21447	21447	21447
5°	24044	21585	19128	21585
10°	27552	21408	16554	21408
15°	30479	21016	14626	21016
20°	30015	20594	13332	20594
25°	27064	20035	12513	20035
30°	22365	19140	11915	19140
35°	16301	18203	11491	18203
40°	13019	17098	11255	17098
45°	11376	15817	10933	15817
50°	10693	14579	10721	14579
55°	9858	13320	10432	13320
60°	9032	11983	9991	11983
65°	8229	10785	9555	10785
70°	7468	9616	8917	9616
75°	6625	8309	7898	8309
80°	5700	6881	6360	6881
85°	5113	5113	3779	5113



TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	126.5	3.0
10°-20°	367.8	8.7
20°-30°	533.7	12.7
30°-40°	563.2	13.4
40°-50°	498.7	11.8
50°-60°	398.0	9.5
60°-70°	270.5	6.4
70°-80°	138.7	3.3
80°-90°	35.1	0.8
90°-100°	73.5	1.7
100°-110°	249.3	5.9
110°-120°	264.8	6.3
120°-130°	218.0	5.2
130°-140°	175.1	4.2
140°-150°	132.3	3.1
150°-160°	93.0	2.2
160°-170°	54.7	1.3
170°-180°	17.8	0.4
0°-30°	1028.0	24.4
0°-40°	1591.2	37.8
0°-60°	2487.8	59.1
0°-90°	2932.1	69.6
90°-120°	587.6	14.0
90°-150°	1113.0	26.4
90°-180°	1279.0	30.4
0°-180°	4210.6	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1484	1332	1180	1332	1484	148
15°	1823	1257	875	1257	1823	503
25°	1519	1125	702	1125	1519	687
35°	827	924	583	924	827	538
45°	498	693	479	693	498	392
55°	350	473	371	473	350	314
65°	215	282	250	282	215	214
75°	106	133	127	133	106	113
85°	28	28	20	28	28	30
90°	12	0	12	0	12	8
95°	40	12	40	12	40	52
105°	398	43	398	43	398	385
115°	524	76	524	76	524	513
125°	425	106	425	106	425	384
135°	352	124	352	124	352	274
145°	281	142	281	142	281	179
155°	236	162	236	162	236	110
165°	207	176	207	176	207	59
175°	187	183	187	183	187	18
180°	184	184	184	184	184	



TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1389.5	1389.9	1390.8	1384.2	1383.4	1383.4	1377.7	1372.8	1367.1	1359.3	1360.1
5°	1483.5	1489.1	1491.1	1485.0	1475.8	1474.8	1466.1	1451.8	1438.5	1427.8	1420.2
7.5°	1595.6	1597.8	1592.8	1584.7	1577.9	1565.7	1549.5	1533.7	1511.5	1491.2	1476.1
10°	1680.5	1683.6	1674.9	1663.2	1653.5	1639.2	1615.7	1591.7	1562.6	1534.5	1512.0
12.5°	1745.0	1752.6	1741.5	1739.9	1723.3	1703.7	1675.7	1663.6	1622.6	1583.5	1559.4
15°	1823.4	1822.9	1824.0	1814.3	1802.0	1798.9	1769.3	1737.2	1679.5	1656.5	1616.7
17.5°	1800.8	1808.5	1812.1	1812.0	1811.7	1809.8	1800.3	1780.0	1751.1	1713.8	1667.8
20°	1746.9	1757.1	1758.6	1770.4	1777.0	1785.7	1789.2	1783.6	1765.8	1734.6	1694.8
22.5°	1663.6	1666.4	1671.2	1689.5	1703.9	1725.6	1737.0	1755.9	1749.0	1733.8	1700.5
25°	1519.2	1514.1	1532.0	1541.1	1574.3	1609.0	1634.1	1661.6	1686.1	1700.9	1691.2
27.5°	1345.8	1338.2	1364.9	1389.3	1416.3	1453.9	1492.9	1538.9	1577.2	1625.1	1641.5
30°	1199.6	1204.2	1229.8	1255.8	1296.6	1349.7	1393.6	1444.2	1498.8	1552.4	1589.6
32.5°	1042.0	1059.7	1075.8	1115.7	1151.6	1210.9	1275.2	1338.4	1406.5	1467.4	1525.1
35°	827.0	847.4	869.9	899.0	949.5	1008.2	1071.0	1156.2	1249.2	1332.4	1400.8
37.5°	696.1	692.8	705.7	726.7	767.7	815.0	887.3	971.6	1080.9	1178.7	1275.2
40°	617.7	615.6	624.8	644.2	675.4	710.1	773.4	847.4	949.0	1068.4	1183.3
42.5°	563.8	565.0	570.1	583.8	605.1	633.7	681.1	744.1	837.1	949.6	1073.0
45°	498.2	501.8	507.4	514.1	526.3	549.8	576.3	621.3	694.8	788.7	910.2
47.5°	451.1	451.2	456.9	462.7	470.0	483.2	504.9	533.0	584.9	661.4	765.8
50°	425.7	422.2	426.3	430.8	438.5	447.7	462.0	488.5	523.2	585.0	672.3
52.5°	394.7	394.8	398.5	400.2	407.1	416.2	429.3	447.7	479.1	527.4	599.2
55°	350.2	352.7	354.8	357.8	364.0	370.6	380.8	393.1	417.6	453.8	506.9
57.5°	308.3	309.1	311.2	317.0	320.9	327.0	336.7	347.8	363.8	390.6	430.5
60°	279.7	279.7	283.8	286.4	291.5	297.6	305.3	316.0	330.3	352.2	384.4
62.5°	253.6	253.2	254.8	259.0	262.9	268.6	276.3	285.4	298.8	318.3	344.8
65°	215.4	214.4	217.5	218.5	222.6	228.2	234.3	244.0	254.7	269.0	292.5
67.5°	178.7	179.9	181.5	183.5	185.7	191.6	195.7	202.6	211.6	223.5	239.4
70°	158.2	158.2	158.2	159.8	162.8	165.9	170.0	175.6	184.3	194.5	208.8
72.5°	135.4	137.0	138.6	137.7	141.6	143.4	148.3	151.5	159.8	166.3	179.0
75°	106.2	106.2	106.2	108.7	110.3	111.8	114.9	117.9	122.0	130.2	136.8
77.5°	79.2	79.0	79.5	80.1	81.8	83.6	84.5	87.3	91.1	94.8	100.5
80°	61.3	62.3	62.8	63.8	63.8	64.8	65.3	68.9	71.5	74.0	77.6
82.5°	47.4	47.6	47.7	47.9	48.3	48.9	50.2	51.4	52.3	54.4	57.2
85°	27.6	27.1	27.1	28.1	27.6	27.6	28.6	29.6	29.6	30.1	31.6
87.5°	13.0	13.0	13.4	13.0	13.0	13.3	13.1	12.9	13.4	13.8	14.2
90°	11.7	11.7	11.7	11.7	11.7	11.3	10.6	11.3	11.7	12.0	11.7
92.5°	19.6	20.1	19.9	21.0	21.3	23.5	26.4	30.8	38.8	45.9	45.3
95°	40.3	39.9	41.0	43.8	48.4	56.2	71.0	92.6	121.2	138.5	122.6
97.5°	79.3	82.3	87.4	96.1	113.0	138.5	176.7	216.0	248.0	236.4	178.1
100°	126.5	132.9	143.1	158.3	187.6	230.4	278.8	322.6	330.0	279.1	192.2
102.5°	222.6	231.2	244.0	269.9	301.8	347.1	382.5	392.4	360.5	280.5	186.8
105°	398.2	403.1	418.3	440.2	462.2	473.8	469.2	429.3	355.8	261.8	176.3
107.5°	508.7	515.2	518.3	519.5	516.7	499.6	462.9	402.7	324.8	241.7	171.1
110°	542.0	542.4	539.2	532.5	517.3	488.3	443.1	379.8	305.3	232.1	170.0



TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	541.4	539.5	533.5	522.3	501.2	467.9	419.6	358.9	291.7	225.9	170.2
115°	524.0	520.8	511.6	495.4	470.3	433.9	387.6	333.2	274.9	219.1	171.7
117.5°	492.8	490.1	480.5	463.3	437.7	403.6	361.6	313.8	264.3	215.7	174.3
120°	472.8	469.2	459.0	442.4	417.6	385.5	348.0	304.2	258.6	213.8	176.0
122.5°	451.8	448.9	439.8	423.4	401.2	372.2	336.7	296.6	253.8	212.6	177.9
125°	425.1	422.2	413.4	400.0	379.5	353.0	321.9	285.5	247.0	210.6	180.9
127.5°	401.6	399.3	391.7	379.1	361.2	336.8	307.5	274.5	240.6	209.4	183.9
130°	388.3	385.5	378.4	366.4	349.1	325.8	297.9	267.5	236.4	208.8	186.2
132.5°	374.5	371.9	365.4	353.4	336.4	314.5	288.8	260.7	233.0	208.5	188.5
135°	352.3	350.9	344.5	332.8	317.6	297.9	274.5	251.2	228.2	208.1	191.2
137.5°	330.5	328.4	322.8	312.8	298.9	281.7	263.2	243.7	224.9	208.0	193.6
140°	315.5	313.4	308.1	298.9	287.6	272.1	255.8	238.8	222.9	207.8	194.7
142.5°	300.5	300.1	295.4	287.0	276.3	263.3	249.3	234.9	221.0	207.8	195.5
145°	281.2	280.2	276.7	270.6	262.2	251.9	241.0	229.3	218.4	207.0	196.4
147.5°	265.1	264.4	262.0	257.2	250.2	242.7	234.2	225.0	215.7	205.8	196.7
150°	255.5	255.1	253.0	248.7	243.4	237.1	229.7	221.9	213.4	204.9	196.4
152.5°	247.3	247.2	245.6	242.0	237.8	232.3	226.0	218.8	211.4	203.5	195.9
155°	236.4	237.1	235.7	233.2	229.3	225.4	220.1	214.5	207.8	201.0	195.0
157.5°	227.1	227.1	226.5	224.4	221.7	218.6	214.2	209.5	204.3	198.5	193.4
160°	221.2	221.2	220.8	219.1	216.6	214.1	210.2	206.3	201.7	196.8	192.6
162.5°	215.5	215.8	215.5	214.3	211.8	209.9	206.6	203.2	199.5	195.4	191.7
165°	207.4	207.8	207.8	206.3	204.9	203.5	201.0	198.6	195.7	192.6	190.1
167.5°	199.9	200.3	200.4	199.6	199.0	197.7	196.0	194.1	192.1	190.1	188.5
170°	195.4	196.1	196.4	195.4	195.0	194.3	192.9	191.9	190.1	188.7	187.6
172.5°	191.7	192.1	192.5	192.0	191.6	191.2	190.1	189.3	188.1	187.0	186.5
175°	186.9	187.6	188.0	187.6	187.6	187.3	186.9	186.6	185.5	185.1	184.8
177.5°	184.0	184.6	184.9	184.9	184.9	184.9	184.6	184.6	184.0	183.7	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1363.0	1359.7	1357.7	1350.3	1343.8	1337.3	1335.2	1336.0	1327.1	1318.5	1314.8
5°	1416.1	1405.9	1396.2	1382.4	1366.1	1348.2	1339.0	1331.8	1314.0	1294.6	1283.4
7.5°	1463.7	1449.1	1430.4	1404.4	1380.7	1352.6	1334.7	1318.9	1292.7	1265.4	1248.6
10°	1492.7	1472.7	1448.7	1417.1	1388.0	1353.8	1329.8	1305.8	1275.2	1242.5	1222.1
12.5°	1517.6	1490.7	1467.1	1426.5	1392.1	1349.3	1320.8	1287.0	1254.8	1216.0	1196.0
15°	1576.9	1527.4	1482.4	1436.5	1394.1	1334.4	1302.8	1257.3	1214.9	1167.0	1144.0
17.5°	1622.7	1567.1	1496.3	1437.9	1388.5	1322.4	1275.9	1221.5	1171.4	1116.5	1085.3
20°	1648.9	1585.0	1509.0	1439.6	1380.3	1304.8	1254.3	1198.6	1139.9	1078.1	1044.4
22.5°	1664.4	1597.3	1522.1	1433.4	1364.0	1290.5	1226.9	1165.9	1106.4	1039.8	1004.4
25°	1669.3	1608.0	1528.4	1428.3	1343.6	1260.4	1183.8	1124.6	1052.6	990.3	938.8
27.5°	1645.0	1601.1	1524.5	1418.7	1320.0	1222.7	1137.4	1070.3	994.3	926.7	874.9
30°	1615.2	1589.6	1515.1	1408.9	1301.2	1196.6	1102.6	1026.6	951.0	882.6	829.5
32.5°	1569.0	1563.5	1498.0	1395.0	1281.2	1163.5	1066.3	989.4	905.7	838.5	787.9
35°	1478.4	1502.9	1461.5	1364.0	1243.5	1116.4	1011.3	923.5	836.7	772.4	724.9
37.5°	1356.9	1417.7	1406.9	1318.6	1192.7	1065.2	949.1	857.3	774.6	709.7	663.1
40°	1273.1	1350.7	1362.0	1283.9	1156.8	1025.6	902.5	811.2	730.5	671.3	624.3
42.5°	1183.3	1274.0	1304.8	1242.2	1117.5	983.9	860.9	766.2	686.4	628.8	587.2
45°	1032.7	1152.7	1208.3	1172.6	1052.1	915.3	788.7	692.7	620.2	566.1	534.0
47.5°	891.9	1023.0	1097.8	1085.2	979.3	843.8	718.7	626.6	556.0	512.8	484.0
50°	792.3	927.0	1017.4	1021.5	927.0	792.8	667.2	580.4	515.6	475.3	451.8
52.5°	705.7	834.3	932.9	954.5	868.6	739.7	621.1	534.7	477.6	440.5	419.5
55°	592.7	701.4	810.6	850.5	781.5	659.0	549.3	473.2	419.6	394.1	375.7
57.5°	492.7	583.4	684.3	728.3	685.8	580.9	478.0	412.0	368.5	346.1	332.0
60°	440.0	511.5	601.3	653.9	617.2	523.8	433.9	371.1	335.4	315.5	302.2
62.5°	391.0	454.3	530.3	578.4	558.4	470.3	389.8	334.4	303.5	284.8	275.3
65°	322.6	372.7	431.4	475.8	462.5	395.6	329.8	282.3	257.8	243.0	235.3
67.5°	265.7	301.8	342.5	381.4	370.7	323.3	270.5	233.5	215.2	202.5	197.9
70°	229.7	257.3	293.5	324.7	316.0	277.2	235.3	203.7	187.9	177.1	172.5
72.5°	195.4	218.1	245.7	271.2	265.3	233.1	198.2	174.3	162.1	152.2	148.4
75°	147.5	164.9	181.7	198.6	197.0	172.0	151.6	133.2	123.5	115.9	114.3
77.5°	108.9	118.6	130.1	140.1	137.3	123.0	107.0	96.5	89.3	84.2	83.4
80°	83.2	88.8	97.0	104.1	100.6	94.4	81.7	74.0	68.9	63.8	61.8
82.5°	60.3	66.0	70.9	74.7	72.0	66.3	58.4	53.2	50.1	46.7	45.8
85°	31.6	34.7	36.8	37.8	36.8	33.2	29.6	27.6	25.0	23.5	23.0
87.5°	14.2	13.7	13.3	13.9	12.5	12.4	10.5	9.1	8.9	8.7	8.1
90°	9.5	7.1	5.3	4.2	3.5	2.8	1.4	0.4	1.4	2.8	3.5
92.5°	35.3	24.0	16.0	12.7	10.3	8.8	6.2	4.3	6.2	8.8	10.3
95°	81.6	50.9	34.6	26.1	20.5	17.3	13.8	12.4	13.8	17.3	20.5
97.5°	110.0	67.1	46.7	37.1	30.6	25.8	22.0	20.1	22.0	25.8	30.6
100°	115.9	72.8	54.1	44.2	37.1	31.4	28.3	27.2	28.3	31.4	37.1
102.5°	116.2	77.9	60.6	50.7	43.3	37.7	34.5	33.7	34.5	37.7	43.3
105°	118.0	86.6	70.0	60.1	52.3	47.0	44.5	43.1	44.5	47.0	52.3
107.5°	122.9	95.5	79.4	69.4	61.7	56.8	54.4	53.3	54.4	56.8	61.7
110°	126.8	101.4	85.9	75.6	68.2	63.6	61.5	60.1	61.5	63.6	68.2





TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	131.1	107.1	92.1	81.5	74.4	70.1	67.7	66.3	67.7	70.1	74.4
115°	137.4	115.9	100.7	91.2	84.1	79.9	77.7	76.0	77.7	79.9	84.1
117.5°	144.2	124.0	110.0	100.1	93.3	89.5	87.4	86.0	87.4	89.5	93.3
120°	148.8	129.7	115.9	106.0	98.9	95.8	93.6	92.2	93.6	95.8	98.9
122.5°	152.7	135.0	122.1	111.9	104.9	101.4	99.3	98.2	99.3	101.4	104.9
125°	159.0	143.1	130.4	120.5	113.4	109.2	107.1	106.0	107.1	109.2	113.4
127.5°	164.9	150.6	138.2	128.0	121.3	116.6	113.6	112.2	113.6	116.6	121.3
130°	168.5	155.1	142.7	132.9	125.8	120.8	117.3	115.9	117.3	120.8	125.8
132.5°	172.2	159.1	147.3	137.4	130.0	124.8	121.0	119.3	121.0	124.8	130.0
135°	177.0	164.7	153.3	143.5	135.3	130.0	125.8	124.4	125.8	130.0	135.3
137.5°	180.7	169.2	158.0	148.8	140.8	135.1	130.9	129.2	130.9	135.1	140.8
140°	182.7	171.7	161.1	151.9	144.2	138.5	134.3	132.9	134.3	138.5	144.2
142.5°	184.4	173.7	163.4	154.8	147.3	141.6	137.7	136.5	137.7	141.6	147.3
145°	186.6	176.7	167.1	159.4	152.3	147.0	143.5	142.0	143.5	147.0	152.3
147.5°	187.8	179.1	170.1	163.2	157.3	152.4	149.0	148.0	149.0	152.4	157.3
150°	188.3	180.2	172.1	165.7	160.4	155.8	153.0	151.9	153.0	155.8	160.4
152.5°	188.6	181.3	174.0	168.3	163.2	159.2	156.4	155.9	156.4	159.2	163.2
155°	189.0	183.0	177.0	171.7	167.8	163.9	161.8	161.5	161.8	163.9	167.8
157.5°	189.0	184.2	179.1	174.7	171.6	168.2	166.5	166.1	166.5	168.2	171.6
160°	189.0	184.8	180.6	176.7	173.8	171.0	169.6	169.2	169.6	171.0	173.8
162.5°	188.7	185.1	181.4	178.4	175.8	173.6	172.1	172.4	172.1	173.6	175.8
165°	188.0	185.5	182.3	180.2	178.4	176.3	175.6	176.0	175.6	176.3	178.4
167.5°	187.5	185.4	183.1	181.8	180.5	179.1	178.5	178.9	178.5	179.1	180.5
170°	186.9	185.1	183.4	182.3	181.6	180.6	180.2	180.9	180.2	180.6	181.6
172.5°	186.1	184.9	183.7	182.9	182.5	181.4	181.6	182.0	181.6	181.4	182.5
175°	185.1	184.4	183.7	183.4	183.4	182.7	183.0	183.4	183.0	182.7	183.4
177.5°	184.6	184.0	183.7	183.7	183.7	183.2	183.4	184.0	183.4	183.2	183.7
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1310.7	1308.3	1299.7	1295.2	1287.8	1280.9	1276.4	1278.5	1280.1	1279.3	1278.0
5°	1273.1	1263.4	1248.6	1235.9	1226.7	1209.8	1202.7	1199.1	1196.1	1192.5	1188.9
7.5°	1228.4	1213.1	1191.9	1173.7	1156.5	1135.6	1123.7	1116.5	1109.2	1101.1	1094.0
10°	1196.6	1175.1	1152.7	1127.1	1106.7	1087.8	1071.0	1059.8	1049.6	1039.9	1032.7
12.5°	1163.1	1138.4	1110.6	1075.7	1053.2	1026.2	1023.6	1003.8	987.9	981.9	973.5
15°	1109.8	1075.1	1039.9	998.5	980.6	956.1	940.8	925.5	911.7	902.0	899.5
17.5°	1049.2	1004.3	969.3	939.6	910.3	885.2	871.1	858.8	847.5	834.5	832.8
20°	1003.1	964.3	926.0	900.0	869.9	844.3	827.0	814.7	805.0	797.4	790.7
22.5°	959.4	916.9	881.9	853.4	823.7	803.1	789.4	777.6	769.5	761.0	754.8
25°	889.3	856.1	817.8	785.6	761.1	747.9	736.6	726.4	721.3	715.7	708.6
27.5°	827.9	791.0	755.2	730.3	708.8	697.0	689.0	682.1	677.3	674.0	670.0
30°	784.6	747.3	719.3	694.8	676.9	665.2	660.1	656.0	650.4	648.3	646.3
32.5°	743.0	709.4	685.4	664.1	647.1	639.4	634.7	631.1	626.7	624.6	620.5
35°	684.0	656.0	632.5	620.7	607.0	600.3	596.8	591.6	587.6	585.5	585.0
37.5°	628.6	604.2	588.8	573.7	567.9	563.8	558.9	555.4	554.2	553.9	553.4
40°	592.7	572.8	559.0	546.7	544.2	538.0	534.0	530.9	530.9	531.4	530.9
42.5°	560.0	542.1	530.0	519.4	516.4	512.7	508.6	508.4	509.3	511.0	509.3
45°	510.5	497.7	489.0	483.9	478.3	474.7	474.2	475.8	476.3	476.8	478.3
47.5°	464.9	456.5	448.6	443.0	440.5	439.9	439.3	442.0	444.4	445.3	447.7
50°	438.0	428.3	421.7	418.1	416.0	415.0	416.0	419.1	421.1	423.7	425.2
52.5°	407.8	400.9	396.3	393.6	392.8	393.4	393.6	397.1	400.3	401.2	402.0
55°	366.0	360.9	359.9	355.3	357.3	356.8	359.4	361.4	364.5	367.5	368.1
57.5°	324.4	320.3	317.5	317.9	318.5	320.8	322.9	326.5	329.8	333.0	333.3
60°	296.6	294.5	293.0	293.0	294.0	297.1	299.7	303.2	305.3	307.3	308.8
62.5°	271.3	269.2	267.7	268.5	271.2	273.0	276.0	277.9	279.9	282.0	282.7
65°	231.2	230.2	231.8	232.8	233.3	235.8	239.4	240.9	243.0	244.0	247.6
67.5°	194.4	194.6	194.4	195.8	198.8	199.4	202.8	206.3	206.7	208.7	211.0
70°	169.5	170.5	171.5	172.5	175.1	176.1	178.7	180.2	182.2	183.8	185.3
72.5°	146.6	146.8	147.8	147.6	149.8	152.0	154.2	155.7	157.7	159.7	161.2
75°	112.8	112.8	113.8	114.3	116.9	119.5	118.9	120.0	122.0	124.0	125.1
77.5°	82.4	81.3	82.4	82.9	83.7	85.9	86.3	87.7	90.0	89.3	90.5
80°	62.8	61.3	62.8	63.3	63.3	65.9	65.9	66.9	68.4	66.9	68.4
82.5°	44.8	44.1	45.2	45.3	46.1	46.2	47.1	47.3	48.8	48.1	48.8
85°	22.5	22.0	22.5	22.0	22.5	23.0	23.0	22.5	22.5	23.5	22.0
87.5°	7.8	7.6	7.5	8.0	8.0	7.7	7.2	7.2	7.0	6.3	6.4
90°	4.2	5.3	7.1	9.5	11.7	12.0	11.7	11.3	10.6	11.3	11.7
92.5°	12.7	16.0	24.0	35.3	45.3	45.9	38.8	30.8	26.4	23.5	21.3
95°	26.1	34.6	50.9	81.6	122.6	138.5	121.2	92.6	71.0	56.2	48.4
97.5°	37.1	46.7	67.1	110.0	178.1	236.4	248.0	216.0	176.7	138.5	113.0
100°	44.2	54.1	72.8	115.9	192.2	279.1	330.0	322.6	278.8	230.4	187.6
102.5°	50.7	60.6	77.9	116.2	186.8	280.5	360.5	392.4	382.5	347.1	301.8
105°	60.1	70.0	86.6	118.0	176.3	261.8	355.8	429.3	469.2	473.8	462.2
107.5°	69.4	79.4	95.5	122.9	171.1	241.7	324.8	402.7	462.9	499.6	516.7
110°	75.6	85.9	101.4	126.8	170.0	232.1	305.3	379.8	443.1	488.3	517.3



TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	81.5	92.1	107.1	131.1	170.2	225.9	291.7	358.9	419.6	467.9	501.2
115°	91.2	100.7	115.9	137.4	171.7	219.1	274.9	333.2	387.6	433.9	470.3
117.5°	100.1	110.0	124.0	144.2	174.3	215.7	264.3	313.8	361.6	403.6	437.7
120°	106.0	115.9	129.7	148.8	176.0	213.8	258.6	304.2	348.0	385.5	417.6
122.5°	111.9	122.1	135.0	152.7	177.9	212.6	253.8	296.6	336.7	372.2	401.2
125°	120.5	130.4	143.1	159.0	180.9	210.6	247.0	285.5	321.9	353.0	379.5
127.5°	128.0	138.2	150.6	164.9	183.9	209.4	240.6	274.5	307.5	336.8	361.2
130°	132.9	142.7	155.1	168.5	186.2	208.8	236.4	267.5	297.9	325.8	349.1
132.5°	137.4	147.3	159.1	172.2	188.5	208.5	233.0	260.7	288.8	314.5	336.4
135°	143.5	153.3	164.7	177.0	191.2	208.1	228.2	251.2	274.5	297.9	317.6
137.5°	148.8	158.0	169.2	180.7	193.6	208.0	224.9	243.7	263.2	281.7	298.9
140°	151.9	161.1	171.7	182.7	194.7	207.8	222.9	238.8	255.8	272.1	287.6
142.5°	154.8	163.4	173.7	184.4	195.5	207.8	221.0	234.9	249.3	263.3	276.3
145°	159.4	167.1	176.7	186.6	196.4	207.0	218.4	229.3	241.0	251.9	262.2
147.5°	163.2	170.1	179.1	187.8	196.7	205.8	215.7	225.0	234.2	242.7	250.2
150°	165.7	172.1	180.2	188.3	196.4	204.9	213.4	221.9	229.7	237.1	243.4
152.5°	168.3	174.0	181.3	188.6	195.9	203.5	211.4	218.8	226.0	232.3	237.8
155°	171.7	177.0	183.0	189.0	195.0	201.0	207.8	214.5	220.1	225.4	229.3
157.5°	174.7	179.1	184.2	189.0	193.4	198.5	204.3	209.5	214.2	218.6	221.7
160°	176.7	180.6	184.8	189.0	192.6	196.8	201.7	206.3	210.2	214.1	216.6
162.5°	178.4	181.4	185.1	188.7	191.7	195.4	199.5	203.2	206.6	209.9	211.8
165°	180.2	182.3	185.5	188.0	190.1	192.6	195.7	198.6	201.0	203.5	204.9
167.5°	181.8	183.1	185.4	187.5	188.5	190.1	192.1	194.1	196.0	197.7	199.0
170°	182.3	183.4	185.1	186.9	187.6	188.7	190.1	191.9	192.9	194.3	195.0
172.5°	182.9	183.7	184.9	186.1	186.5	187.0	188.1	189.3	190.1	191.2	191.6
175°	183.4	183.7	184.4	185.1	184.8	185.1	185.5	186.6	186.9	187.3	187.6
177.5°	183.7	183.7	184.0	184.6	184.0	183.7	184.0	184.6	184.6	184.9	184.9
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331332  
 CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1274.0	1273.1	1273.1	1269.5	1273.1	1273.1	1274.0	1278.0	1279.3	1280.1	1278.5
5°	1181.8	1180.2	1177.7	1180.2	1177.7	1180.2	1181.8	1188.9	1192.5	1196.1	1199.1
7.5°	1090.6	1084.5	1083.6	1077.5	1083.6	1084.5	1090.6	1094.0	1101.1	1109.2	1116.5
10°	1024.0	1019.9	1019.4	1009.7	1019.4	1019.9	1024.0	1032.7	1039.9	1049.6	1059.8
12.5°	973.4	963.6	965.5	959.9	965.5	963.6	973.4	973.5	981.9	987.9	1003.8
15°	885.7	885.7	883.6	875.0	883.6	885.7	885.7	899.5	902.0	911.7	925.5
17.5°	822.7	821.7	816.8	819.2	816.8	821.7	822.7	832.8	834.5	847.5	858.8
20°	785.1	782.1	775.9	775.9	775.9	782.1	785.1	790.7	797.4	805.0	814.7
22.5°	749.6	749.4	742.9	744.9	742.9	749.4	749.6	754.8	761.0	769.5	777.6
25°	708.0	704.0	700.9	702.4	700.9	704.0	708.0	708.6	715.7	721.3	726.4
27.5°	668.6	666.4	666.2	662.0	666.2	666.4	668.6	670.0	674.0	677.3	682.1
30°	645.8	640.7	641.7	639.1	641.7	640.7	645.8	646.3	648.3	650.4	656.0
32.5°	619.6	617.8	616.8	614.6	616.8	617.8	619.6	620.5	624.6	626.7	631.1
35°	584.0	584.5	582.0	583.0	582.0	584.5	584.0	585.0	585.5	587.6	591.6
37.5°	552.9	554.5	553.3	553.6	553.3	554.5	552.9	553.4	553.9	554.2	555.4
40°	532.4	532.4	532.4	534.0	532.4	532.4	532.4	530.9	531.4	530.9	530.9
42.5°	512.8	512.0	511.2	511.1	511.2	512.0	512.8	509.3	511.0	509.3	508.4
45°	479.3	480.9	481.4	478.8	481.4	480.9	479.3	478.3	476.8	476.3	475.8
47.5°	449.0	449.2	449.0	451.3	449.0	449.2	449.0	447.7	445.3	444.4	442.0
50°	427.8	426.8	427.8	426.8	427.8	426.8	427.8	425.2	423.7	421.1	419.1
52.5°	405.3	405.5	404.9	404.7	404.9	405.5	405.3	402.0	401.2	400.3	397.1
55°	370.1	371.1	370.6	370.6	370.6	371.1	370.1	368.1	367.5	364.5	361.4
57.5°	333.7	334.6	335.3	333.0	335.3	334.6	333.7	333.3	333.0	329.8	326.5
60°	308.3	310.9	310.4	309.4	310.4	310.9	308.3	308.8	307.3	305.3	303.2
62.5°	285.1	286.0	285.9	285.7	285.9	286.0	285.1	282.7	282.0	279.9	277.9
65°	249.1	250.1	248.6	250.1	248.6	250.1	249.1	247.6	244.0	243.0	240.9
67.5°	210.4	210.7	211.9	212.6	211.9	210.7	210.4	211.0	208.7	206.7	206.3
70°	186.3	185.8	187.3	188.9	187.3	185.8	186.3	185.3	183.8	182.2	180.2
72.5°	161.0	162.1	161.6	162.7	161.6	162.1	161.0	161.2	159.7	157.7	155.7
75°	124.0	125.6	125.1	126.6	125.1	125.6	124.0	125.1	124.0	122.0	120.0
77.5°	89.6	89.8	89.6	90.5	89.6	89.8	89.6	90.5	89.3	90.0	87.7
80°	68.4	67.4	66.4	68.4	66.4	67.4	68.4	68.4	66.9	68.4	66.9
82.5°	47.6	48.2	47.2	47.2	47.2	48.2	47.6	48.8	48.1	48.8	47.3
85°	22.0	21.4	20.4	20.4	20.4	21.4	22.0	22.0	23.5	22.5	22.5
87.5°	6.4	6.0	6.0	5.6	6.0	6.0	6.4	6.4	6.3	7.0	7.2
90°	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.7	11.3	10.6	11.3
92.5°	21.0	19.9	20.1	19.6	20.1	19.9	21.0	21.3	23.5	26.4	30.8
95°	43.8	41.0	39.9	40.3	39.9	41.0	43.8	48.4	56.2	71.0	92.6
97.5°	96.1	87.4	82.3	79.3	82.3	87.4	96.1	113.0	138.5	176.7	216.0
100°	158.3	143.1	132.9	126.5	132.9	143.1	158.3	187.6	230.4	278.8	322.6
102.5°	269.9	244.0	231.2	222.6	231.2	244.0	269.9	301.8	347.1	382.5	392.4
105°	440.2	418.3	403.1	398.2	403.1	418.3	440.2	462.2	473.8	469.2	429.3
107.5°	519.5	518.3	515.2	508.7	515.2	518.3	519.5	516.7	499.6	462.9	402.7
110°	532.5	539.2	542.4	542.0	542.4	539.2	532.5	517.3	488.3	443.1	379.8



TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	522.3	533.5	539.5	541.4	539.5	533.5	522.3	501.2	467.9	419.6	358.9
115°	495.4	511.6	520.8	524.0	520.8	511.6	495.4	470.3	433.9	387.6	333.2
117.5°	463.3	480.5	490.1	492.8	490.1	480.5	463.3	437.7	403.6	361.6	313.8
120°	442.4	459.0	469.2	472.8	469.2	459.0	442.4	417.6	385.5	348.0	304.2
122.5°	423.4	439.8	448.9	451.8	448.9	439.8	423.4	401.2	372.2	336.7	296.6
125°	400.0	413.4	422.2	425.1	422.2	413.4	400.0	379.5	353.0	321.9	285.5
127.5°	379.1	391.7	399.3	401.6	399.3	391.7	379.1	361.2	336.8	307.5	274.5
130°	366.4	378.4	385.5	388.3	385.5	378.4	366.4	349.1	325.8	297.9	267.5
132.5°	353.4	365.4	371.9	374.5	371.9	365.4	353.4	336.4	314.5	288.8	260.7
135°	332.8	344.5	350.9	352.3	350.9	344.5	332.8	317.6	297.9	274.5	251.2
137.5°	312.8	322.8	328.4	330.5	328.4	322.8	312.8	298.9	281.7	263.2	243.7
140°	298.9	308.1	313.4	315.5	313.4	308.1	298.9	287.6	272.1	255.8	238.8
142.5°	287.0	295.4	300.1	300.5	300.1	295.4	287.0	276.3	263.3	249.3	234.9
145°	270.6	276.7	280.2	281.2	280.2	276.7	270.6	262.2	251.9	241.0	229.3
147.5°	257.2	262.0	264.4	265.1	264.4	262.0	257.2	250.2	242.7	234.2	225.0
150°	248.7	253.0	255.1	255.5	255.1	253.0	248.7	243.4	237.1	229.7	221.9
152.5°	242.0	245.6	247.2	247.3	247.2	245.6	242.0	237.8	232.3	226.0	218.8
155°	233.2	235.7	237.1	236.4	237.1	235.7	233.2	229.3	225.4	220.1	214.5
157.5°	224.4	226.5	227.1	227.1	227.1	226.5	224.4	221.7	218.6	214.2	209.5
160°	219.1	220.8	221.2	221.2	221.2	220.8	219.1	216.6	214.1	210.2	206.3
162.5°	214.3	215.5	215.8	215.5	215.8	215.5	214.3	211.8	209.9	206.6	203.2
165°	206.3	207.8	207.8	207.4	207.8	207.8	206.3	204.9	203.5	201.0	198.6
167.5°	199.6	200.4	200.3	199.9	200.3	200.4	199.6	199.0	197.7	196.0	194.1
170°	195.4	196.4	196.1	195.4	196.1	196.4	195.4	195.0	194.3	192.9	191.9
172.5°	192.0	192.5	192.1	191.7	192.1	192.5	192.0	191.6	191.2	190.1	189.3
175°	187.6	188.0	187.6	186.9	187.6	188.0	187.6	187.6	187.3	186.9	186.6
177.5°	184.9	184.9	184.6	184.0	184.6	184.9	184.9	184.9	184.9	184.6	184.6
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1276.4	1280.9	1287.8	1295.2	1299.7	1308.3	1310.7	1314.8	1318.5	1327.1	1336.0
5°	1202.7	1209.8	1226.7	1235.9	1248.6	1263.4	1273.1	1283.4	1294.6	1314.0	1331.8
7.5°	1123.7	1135.6	1156.5	1173.7	1191.9	1213.1	1228.4	1248.6	1265.4	1292.7	1318.9
10°	1071.0	1087.8	1106.7	1127.1	1152.7	1175.1	1196.6	1222.1	1242.5	1275.2	1305.8
12.5°	1023.6	1026.2	1053.2	1075.7	1110.6	1138.4	1163.1	1196.0	1216.0	1254.8	1287.0
15°	940.8	956.1	980.6	998.5	1039.9	1075.1	1109.8	1144.0	1167.0	1214.9	1257.3
17.5°	871.1	885.2	910.3	939.6	969.3	1004.3	1049.2	1085.3	1116.5	1171.4	1221.5
20°	827.0	844.3	869.9	900.0	926.0	964.3	1003.1	1044.4	1078.1	1139.9	1198.6
22.5°	789.4	803.1	823.7	853.4	881.9	916.9	959.4	1004.4	1039.8	1106.4	1165.9
25°	736.6	747.9	761.1	785.6	817.8	856.1	889.3	938.8	990.3	1052.6	1124.6
27.5°	689.0	697.0	708.8	730.3	755.2	791.0	827.9	874.9	926.7	994.3	1070.3
30°	660.1	665.2	676.9	694.8	719.3	747.3	784.6	829.5	882.6	951.0	1026.6
32.5°	634.7	639.4	647.1	664.1	685.4	709.4	743.0	787.9	838.5	905.7	989.4
35°	596.8	600.3	607.0	620.7	632.5	656.0	684.0	724.9	772.4	836.7	923.5
37.5°	558.9	563.8	567.9	573.7	588.8	604.2	628.6	663.1	709.7	774.6	857.3
40°	534.0	538.0	544.2	546.7	559.0	572.8	592.7	624.3	671.3	730.5	811.2
42.5°	508.6	512.7	516.4	519.4	530.0	542.1	560.0	587.2	628.8	686.4	766.2
45°	474.2	474.7	478.3	483.9	489.0	497.7	510.5	534.0	566.1	620.2	692.7
47.5°	439.3	439.9	440.5	443.0	448.6	456.5	464.9	484.0	512.8	556.0	626.6
50°	416.0	415.0	416.0	418.1	421.7	428.3	438.0	451.8	475.3	515.6	580.4
52.5°	393.6	393.4	392.8	393.6	396.3	400.9	407.8	419.5	440.5	477.6	534.7
55°	359.4	356.8	357.3	355.3	359.9	360.9	366.0	375.7	394.1	419.6	473.2
57.5°	322.9	320.8	318.5	317.9	317.5	320.3	324.4	332.0	346.1	368.5	412.0
60°	299.7	297.1	294.0	293.0	293.0	294.5	296.6	302.2	315.5	335.4	371.1
62.5°	276.0	273.0	271.2	268.5	267.7	269.2	271.3	275.3	284.8	303.5	334.4
65°	239.4	235.8	233.3	232.8	231.8	230.2	231.2	235.3	243.0	257.8	282.3
67.5°	202.8	199.4	198.8	195.8	194.4	194.6	194.4	197.9	202.5	215.2	233.5
70°	178.7	176.1	175.1	172.5	171.5	170.5	169.5	172.5	177.1	187.9	203.7
72.5°	154.2	152.0	149.8	147.6	147.8	146.8	146.6	148.4	152.2	162.1	174.3
75°	118.9	119.5	116.9	114.3	113.8	112.8	112.8	114.3	115.9	123.5	133.2
77.5°	86.3	85.9	83.7	82.9	82.4	81.3	82.4	83.4	84.2	89.3	96.5
80°	65.9	65.9	63.3	63.3	62.8	61.3	62.8	61.8	63.8	68.9	74.0
82.5°	47.1	46.2	46.1	45.3	45.2	44.1	44.8	45.8	46.7	50.1	53.2
85°	23.0	23.0	22.5	22.0	22.5	22.0	22.5	23.0	23.5	25.0	27.6
87.5°	7.2	7.7	8.0	8.0	7.5	7.6	7.8	8.1	8.7	8.9	9.1
90°	11.7	12.0	11.7	9.5	7.1	5.3	4.2	3.5	2.8	1.4	0.4
92.5°	38.8	45.9	45.3	35.3	24.0	16.0	12.7	10.3	8.8	6.2	4.3
95°	121.2	138.5	122.6	81.6	50.9	34.6	26.1	20.5	17.3	13.8	12.4
97.5°	248.0	236.4	178.1	110.0	67.1	46.7	37.1	30.6	25.8	22.0	20.1
100°	330.0	279.1	192.2	115.9	72.8	54.1	44.2	37.1	31.4	28.3	27.2
102.5°	360.5	280.5	186.8	116.2	77.9	60.6	50.7	43.3	37.7	34.5	33.7
105°	355.8	261.8	176.3	118.0	86.6	70.0	60.1	52.3	47.0	44.5	43.1
107.5°	324.8	241.7	171.1	122.9	95.5	79.4	69.4	61.7	56.8	54.4	53.3
110°	305.3	232.1	170.0	126.8	101.4	85.9	75.6	68.2	63.6	61.5	60.1



TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	291.7	225.9	170.2	131.1	107.1	92.1	81.5	74.4	70.1	67.7	66.3
115°	274.9	219.1	171.7	137.4	115.9	100.7	91.2	84.1	79.9	77.7	76.0
117.5°	264.3	215.7	174.3	144.2	124.0	110.0	100.1	93.3	89.5	87.4	86.0
120°	258.6	213.8	176.0	148.8	129.7	115.9	106.0	98.9	95.8	93.6	92.2
122.5°	253.8	212.6	177.9	152.7	135.0	122.1	111.9	104.9	101.4	99.3	98.2
125°	247.0	210.6	180.9	159.0	143.1	130.4	120.5	113.4	109.2	107.1	106.0
127.5°	240.6	209.4	183.9	164.9	150.6	138.2	128.0	121.3	116.6	113.6	112.2
130°	236.4	208.8	186.2	168.5	155.1	142.7	132.9	125.8	120.8	117.3	115.9
132.5°	233.0	208.5	188.5	172.2	159.1	147.3	137.4	130.0	124.8	121.0	119.3
135°	228.2	208.1	191.2	177.0	164.7	153.3	143.5	135.3	130.0	125.8	124.4
137.5°	224.9	208.0	193.6	180.7	169.2	158.0	148.8	140.8	135.1	130.9	129.2
140°	222.9	207.8	194.7	182.7	171.7	161.1	151.9	144.2	138.5	134.3	132.9
142.5°	221.0	207.8	195.5	184.4	173.7	163.4	154.8	147.3	141.6	137.7	136.5
145°	218.4	207.0	196.4	186.6	176.7	167.1	159.4	152.3	147.0	143.5	142.0
147.5°	215.7	205.8	196.7	187.8	179.1	170.1	163.2	157.3	152.4	149.0	148.0
150°	213.4	204.9	196.4	188.3	180.2	172.1	165.7	160.4	155.8	153.0	151.9
152.5°	211.4	203.5	195.9	188.6	181.3	174.0	168.3	163.2	159.2	156.4	155.9
155°	207.8	201.0	195.0	189.0	183.0	177.0	171.7	167.8	163.9	161.8	161.5
157.5°	204.3	198.5	193.4	189.0	184.2	179.1	174.7	171.6	168.2	166.5	166.1
160°	201.7	196.8	192.6	189.0	184.8	180.6	176.7	173.8	171.0	169.6	169.2
162.5°	199.5	195.4	191.7	188.7	185.1	181.4	178.4	175.8	173.6	172.1	172.4
165°	195.7	192.6	190.1	188.0	185.5	182.3	180.2	178.4	176.3	175.6	176.0
167.5°	192.1	190.1	188.5	187.5	185.4	183.1	181.8	180.5	179.1	178.5	178.9
170°	190.1	188.7	187.6	186.9	185.1	183.4	182.3	181.6	180.6	180.2	180.9
172.5°	188.1	187.0	186.5	186.1	184.9	183.7	182.9	182.5	181.4	181.6	182.0
175°	185.5	185.1	184.8	185.1	184.4	183.7	183.4	183.4	182.7	183.0	183.4
177.5°	184.0	183.7	184.0	184.6	184.0	183.7	183.7	183.7	183.2	183.4	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1335.2	1337.3	1343.8	1350.3	1357.7	1359.7	1363.0	1360.1	1359.3	1367.1	1372.8
5°	1339.0	1348.2	1366.1	1382.4	1396.2	1405.9	1416.1	1420.2	1427.8	1438.5	1451.8
7.5°	1334.7	1352.6	1380.7	1404.4	1430.4	1449.1	1463.7	1476.1	1491.2	1511.5	1533.7
10°	1329.8	1353.8	1388.0	1417.1	1448.7	1472.7	1492.7	1512.0	1534.5	1562.6	1591.7
12.5°	1320.8	1349.3	1392.1	1426.5	1467.1	1490.7	1517.6	1559.4	1583.5	1622.6	1663.6
15°	1302.8	1334.4	1394.1	1436.5	1482.4	1527.4	1576.9	1616.7	1656.5	1679.5	1737.2
17.5°	1275.9	1322.4	1388.5	1437.9	1496.3	1567.1	1622.7	1667.8	1713.8	1751.1	1780.0
20°	1254.3	1304.8	1380.3	1439.6	1509.0	1585.0	1648.9	1694.8	1734.6	1765.8	1783.6
22.5°	1226.9	1290.5	1364.0	1433.4	1522.1	1597.3	1664.4	1700.5	1733.8	1749.0	1755.9
25°	1183.8	1260.4	1343.6	1428.3	1528.4	1608.0	1669.3	1691.2	1700.9	1686.1	1661.6
27.5°	1137.4	1222.7	1320.0	1418.7	1524.5	1601.1	1645.0	1641.5	1625.1	1577.2	1538.9
30°	1102.6	1196.6	1301.2	1408.9	1515.1	1589.6	1615.2	1589.6	1552.4	1498.8	1444.2
32.5°	1066.3	1163.5	1281.2	1395.0	1498.0	1563.5	1569.0	1525.1	1467.4	1406.5	1338.4
35°	1011.3	1116.4	1243.5	1364.0	1461.5	1502.9	1478.4	1400.8	1332.4	1249.2	1156.2
37.5°	949.1	1065.2	1192.7	1318.6	1406.9	1417.7	1356.9	1275.2	1178.7	1080.9	971.6
40°	902.5	1025.6	1156.8	1283.9	1362.0	1350.7	1273.1	1183.3	1068.4	949.0	847.4
42.5°	860.9	983.9	1117.5	1242.2	1304.8	1274.0	1183.3	1073.0	949.6	837.1	744.1
45°	788.7	915.3	1052.1	1172.6	1208.3	1152.7	1032.7	910.2	788.7	694.8	621.3
47.5°	718.7	843.8	979.3	1085.2	1097.8	1023.0	891.9	765.8	661.4	584.9	533.0
50°	667.2	792.8	927.0	1021.5	1017.4	927.0	792.3	672.3	585.0	523.2	488.5
52.5°	621.1	739.7	868.6	954.5	932.9	834.3	705.7	599.2	527.4	479.1	447.7
55°	549.3	659.0	781.5	850.5	810.6	701.4	592.7	506.9	453.8	417.6	393.1
57.5°	478.0	580.9	685.8	728.3	684.3	583.4	492.7	430.5	390.6	363.8	347.8
60°	433.9	523.8	617.2	653.9	601.3	511.5	440.0	384.4	352.2	330.3	316.0
62.5°	389.8	470.3	558.4	578.4	530.3	454.3	391.0	344.8	318.3	298.8	285.4
65°	329.8	395.6	462.5	475.8	431.4	372.7	322.6	292.5	269.0	254.7	244.0
67.5°	270.5	323.3	370.7	381.4	342.5	301.8	265.7	239.4	223.5	211.6	202.6
70°	235.3	277.2	316.0	324.7	293.5	257.3	229.7	208.8	194.5	184.3	175.6
72.5°	198.2	233.1	265.3	271.2	245.7	218.1	195.4	179.0	166.3	159.8	151.5
75°	151.6	172.0	197.0	198.6	181.7	164.9	147.5	136.8	130.2	122.0	117.9
77.5°	107.0	123.0	137.3	140.1	130.1	118.6	108.9	100.5	94.8	91.1	87.3
80°	81.7	94.4	100.6	104.1	97.0	88.8	83.2	77.6	74.0	71.5	68.9
82.5°	58.4	66.3	72.0	74.7	70.9	66.0	60.3	57.2	54.4	52.3	51.4
85°	29.6	33.2	36.8	37.8	36.8	34.7	31.6	31.6	30.1	29.6	29.6
87.5°	10.5	12.4	12.5	13.9	13.3	13.7	14.2	14.2	13.8	13.4	12.9
90°	1.4	2.8	3.5	4.2	5.3	7.1	9.5	11.7	12.0	11.7	11.3
92.5°	6.2	8.8	10.3	12.7	16.0	24.0	35.3	45.3	45.9	38.8	30.8
95°	13.8	17.3	20.5	26.1	34.6	50.9	81.6	122.6	138.5	121.2	92.6
97.5°	22.0	25.8	30.6	37.1	46.7	67.1	110.0	178.1	236.4	248.0	216.0
100°	28.3	31.4	37.1	44.2	54.1	72.8	115.9	192.2	279.1	330.0	322.6
102.5°	34.5	37.7	43.3	50.7	60.6	77.9	116.2	186.8	280.5	360.5	392.4
105°	44.5	47.0	52.3	60.1	70.0	86.6	118.0	176.3	261.8	355.8	429.3
107.5°	54.4	56.8	61.7	69.4	79.4	95.5	122.9	171.1	241.7	324.8	402.7
110°	61.5	63.6	68.2	75.6	85.9	101.4	126.8	170.0	232.1	305.3	379.8





TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	67.7	70.1	74.4	81.5	92.1	107.1	131.1	170.2	225.9	291.7	358.9
115°	77.7	79.9	84.1	91.2	100.7	115.9	137.4	171.7	219.1	274.9	333.2
117.5°	87.4	89.5	93.3	100.1	110.0	124.0	144.2	174.3	215.7	264.3	313.8
120°	93.6	95.8	98.9	106.0	115.9	129.7	148.8	176.0	213.8	258.6	304.2
122.5°	99.3	101.4	104.9	111.9	122.1	135.0	152.7	177.9	212.6	253.8	296.6
125°	107.1	109.2	113.4	120.5	130.4	143.1	159.0	180.9	210.6	247.0	285.5
127.5°	113.6	116.6	121.3	128.0	138.2	150.6	164.9	183.9	209.4	240.6	274.5
130°	117.3	120.8	125.8	132.9	142.7	155.1	168.5	186.2	208.8	236.4	267.5
132.5°	121.0	124.8	130.0	137.4	147.3	159.1	172.2	188.5	208.5	233.0	260.7
135°	125.8	130.0	135.3	143.5	153.3	164.7	177.0	191.2	208.1	228.2	251.2
137.5°	130.9	135.1	140.8	148.8	158.0	169.2	180.7	193.6	208.0	224.9	243.7
140°	134.3	138.5	144.2	151.9	161.1	171.7	182.7	194.7	207.8	222.9	238.8
142.5°	137.7	141.6	147.3	154.8	163.4	173.7	184.4	195.5	207.8	221.0	234.9
145°	143.5	147.0	152.3	159.4	167.1	176.7	186.6	196.4	207.0	218.4	229.3
147.5°	149.0	152.4	157.3	163.2	170.1	179.1	187.8	196.7	205.8	215.7	225.0
150°	153.0	155.8	160.4	165.7	172.1	180.2	188.3	196.4	204.9	213.4	221.9
152.5°	156.4	159.2	163.2	168.3	174.0	181.3	188.6	195.9	203.5	211.4	218.8
155°	161.8	163.9	167.8	171.7	177.0	183.0	189.0	195.0	201.0	207.8	214.5
157.5°	166.5	168.2	171.6	174.7	179.1	184.2	189.0	193.4	198.5	204.3	209.5
160°	169.6	171.0	173.8	176.7	180.6	184.8	189.0	192.6	196.8	201.7	206.3
162.5°	172.1	173.6	175.8	178.4	181.4	185.1	188.7	191.7	195.4	199.5	203.2
165°	175.6	176.3	178.4	180.2	182.3	185.5	188.0	190.1	192.6	195.7	198.6
167.5°	178.5	179.1	180.5	181.8	183.1	185.4	187.5	188.5	190.1	192.1	194.1
170°	180.2	180.6	181.6	182.3	183.4	185.1	186.9	187.6	188.7	190.1	191.9
172.5°	181.6	181.4	182.5	182.9	183.7	184.9	186.1	186.5	187.0	188.1	189.3
175°	183.0	182.7	183.4	183.4	183.7	184.4	185.1	184.8	185.1	185.5	186.6
177.5°	183.4	183.2	183.7	183.7	183.7	184.0	184.6	184.0	183.7	184.0	184.6
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1377.7	1383.4	1383.4	1384.2	1390.8	1389.9	1389.5
5°	1466.1	1474.8	1475.8	1485.0	1491.1	1489.1	1483.5
7.5°	1549.5	1565.7	1577.9	1584.7	1592.8	1597.8	1595.6
10°	1615.7	1639.2	1653.5	1663.2	1674.9	1683.6	1680.5
12.5°	1675.7	1703.7	1723.3	1739.9	1741.5	1752.6	1745.0
15°	1769.3	1798.9	1802.0	1814.3	1824.0	1822.9	1823.4
17.5°	1800.3	1809.8	1811.7	1812.0	1812.1	1808.5	1800.8
20°	1789.2	1785.7	1777.0	1770.4	1758.6	1757.1	1746.9
22.5°	1737.0	1725.6	1703.9	1689.5	1671.2	1666.4	1663.6
25°	1634.1	1609.0	1574.3	1541.1	1532.0	1514.1	1519.2
27.5°	1492.9	1453.9	1416.3	1389.3	1364.9	1338.2	1345.8
30°	1393.6	1349.7	1296.6	1255.8	1229.8	1204.2	1199.6
32.5°	1275.2	1210.9	1151.6	1115.7	1075.8	1059.7	1042.0
35°	1071.0	1008.2	949.5	899.0	869.9	847.4	827.0
37.5°	887.3	815.0	767.7	726.7	705.7	692.8	696.1
40°	773.4	710.1	675.4	644.2	624.8	615.6	617.7
42.5°	681.1	633.7	605.1	583.8	570.1	565.0	563.8
45°	576.3	549.8	526.3	514.1	507.4	501.8	498.2
47.5°	504.9	483.2	470.0	462.7	456.9	451.2	451.1
50°	462.0	447.7	438.5	430.8	426.3	422.2	425.7
52.5°	429.3	416.2	407.1	400.2	398.5	394.8	394.7
55°	380.8	370.6	364.0	357.8	354.8	352.7	350.2
57.5°	336.7	327.0	320.9	317.0	311.2	309.1	308.3
60°	305.3	297.6	291.5	286.4	283.8	279.7	279.7
62.5°	276.3	268.6	262.9	259.0	254.8	253.2	253.6
65°	234.3	228.2	222.6	218.5	217.5	214.4	215.4
67.5°	195.7	191.6	185.7	183.5	181.5	179.9	178.7
70°	170.0	165.9	162.8	159.8	158.2	158.2	158.2
72.5°	148.3	143.4	141.6	137.7	138.6	137.0	135.4
75°	114.9	111.8	110.3	108.7	106.2	106.2	106.2
77.5°	84.5	83.6	81.8	80.1	79.5	79.0	79.2
80°	65.3	64.8	63.8	63.8	62.8	62.3	61.3
82.5°	50.2	48.9	48.3	47.9	47.7	47.6	47.4
85°	28.6	27.6	27.6	28.1	27.1	27.1	27.6
87.5°	13.1	13.3	13.0	13.0	13.4	13.0	13.0
90°	10.6	11.3	11.7	11.7	11.7	11.7	11.7
92.5°	26.4	23.5	21.3	21.0	19.9	20.1	19.6
95°	71.0	56.2	48.4	43.8	41.0	39.9	40.3
97.5°	176.7	138.5	113.0	96.1	87.4	82.3	79.3
100°	278.8	230.4	187.6	158.3	143.1	132.9	126.5
102.5°	382.5	347.1	301.8	269.9	244.0	231.2	222.6
105°	469.2	473.8	462.2	440.2	418.3	403.1	398.2
107.5°	462.9	499.6	516.7	519.5	518.3	515.2	508.7
110°	443.1	488.3	517.3	532.5	539.2	542.4	542.0



TEST NUMBER: P331332

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	419.6	467.9	501.2	522.3	533.5	539.5	541.4
115°	387.6	433.9	470.3	495.4	511.6	520.8	524.0
117.5°	361.6	403.6	437.7	463.3	480.5	490.1	492.8
120°	348.0	385.5	417.6	442.4	459.0	469.2	472.8
122.5°	336.7	372.2	401.2	423.4	439.8	448.9	451.8
125°	321.9	353.0	379.5	400.0	413.4	422.2	425.1
127.5°	307.5	336.8	361.2	379.1	391.7	399.3	401.6
130°	297.9	325.8	349.1	366.4	378.4	385.5	388.3
132.5°	288.8	314.5	336.4	353.4	365.4	371.9	374.5
135°	274.5	297.9	317.6	332.8	344.5	350.9	352.3
137.5°	263.2	281.7	298.9	312.8	322.8	328.4	330.5
140°	255.8	272.1	287.6	298.9	308.1	313.4	315.5
142.5°	249.3	263.3	276.3	287.0	295.4	300.1	300.5
145°	241.0	251.9	262.2	270.6	276.7	280.2	281.2
147.5°	234.2	242.7	250.2	257.2	262.0	264.4	265.1
150°	229.7	237.1	243.4	248.7	253.0	255.1	255.5
152.5°	226.0	232.3	237.8	242.0	245.6	247.2	247.3
155°	220.1	225.4	229.3	233.2	235.7	237.1	236.4
157.5°	214.2	218.6	221.7	224.4	226.5	227.1	227.1
160°	210.2	214.1	216.6	219.1	220.8	221.2	221.2
162.5°	206.6	209.9	211.8	214.3	215.5	215.8	215.5
165°	201.0	203.5	204.9	206.3	207.8	207.8	207.4
167.5°	196.0	197.7	199.0	199.6	200.4	200.3	199.9
170°	192.9	194.3	195.0	195.4	196.4	196.1	195.4
172.5°	190.1	191.2	191.6	192.0	192.5	192.1	191.7
175°	186.9	187.3	187.6	187.6	188.0	187.6	186.9
177.5°	184.6	184.9	184.9	184.9	184.9	184.6	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7

(END OF REPORT)