

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331338

Luminaire Tested: **SA2XXDIP-C675D330U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331338
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D330U835-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3981.3 lumens
Efficiency: N/A
Efficacy: 113.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331338
CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331338

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	73	73	73	68
1	102	97	93	90	96	92	88	85	82	79	77	73	71	69	64	63	61	57
2	93	85	79	73	87	80	75	70	72	67	64	64	60	57	56	54	52	48
3	85	75	67	61	79	71	64	59	63	58	54	56	52	49	50	47	44	41
4	77	66	58	52	73	63	56	50	56	50	46	50	46	42	45	41	38	35
5	71	59	51	45	67	56	49	43	51	44	40	45	40	36	40	36	33	30
6	66	53	45	39	62	51	43	37	46	39	35	41	36	32	37	32	29	27
7	61	48	40	34	57	46	38	33	41	35	31	37	32	28	33	29	26	24
8	57	44	36	30	53	42	34	29	38	32	27	34	29	25	31	27	23	21
9	53	40	32	27	50	38	31	26	35	29	25	32	26	23	28	24	21	19
10	49	37	29	25	47	35	28	24	32	26	22	29	24	21	26	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17142	17142	17142
5°	17208	16960	17058
10°	17105	16787	16870
15°	16893	16568	16552
20°	16593	16242	16225
25°	16295	15841	15841
30°	15910	15474	15340
35°	15554	15031	14808
40°	15104	14587	14309
45°	14661	14150	13798
50°	14179	13692	13205
55°	13678	13163	12673
60°	13120	12526	12064
65°	12520	11897	11351
70°	11759	11131	10603
75°	10699	10256	10000
80°	9493	9205	8731
85°	7762	7373	6614



TEST NUMBER: P331338

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.8	2.5
10°-20°	280.9	7.1
20°-30°	412.9	10.4
30°-40°	479.6	12.0
40°-50°	479.1	12.0
50°-60°	417.8	10.5
60°-70°	308.9	7.8
70°-80°	175.0	4.4
80°-90°	48.7	1.2
90°-100°	73.5	1.8
100°-110°	249.3	6.3
110°-120°	264.8	6.7
120°-130°	218.0	5.5
130°-140°	175.1	4.4
140°-150°	132.3	3.3
150°-160°	93.0	2.3
160°-170°	54.7	1.4
170°-180°	17.8	0.4
0°-30°	793.6	19.9
0°-40°	1273.2	32.0
0°-60°	2170.1	54.5
0°-90°	2702.7	67.9
90°-120°	587.6	14.8
90°-150°	1113.0	28.0
90°-180°	1279.0	32.1
0°-180°	3981.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1062	1062	1062	1062	1062	
5°	1062	1057	1046	1054	1052	101
15°	1011	1004	991	995	990	284
25°	915	906	889	891	889	421
35°	789	779	763	756	751	492
45°	642	635	620	609	604	495
55°	486	479	468	456	450	434
65°	328	321	311	302	297	324
75°	172	169	164	159	160	183
85°	42	41	40	37	36	48
90°	0	5	12	12	12	3
95°	12	30	138	52	40	13
105°	43	65	262	468	398	46
115°	76	96	219	452	524	75
125°	106	125	211	366	425	94
135°	124	148	208	308	352	96
145°	142	163	207	257	281	89
155°	162	174	201	227	236	74
165°	176	181	193	204	207	50
175°	183	184	185	187	187	17
180°	184	184	184	184	184	



TEST NUMBER: P331338

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1066.6	1065.7	1064.8	1063.9	1063.0	1061.5	1059.5	1057.5	1055.5	1053.5	1055.3
5°	1061.7	1060.8	1059.9	1059.0	1058.1	1056.4	1053.9	1051.4	1048.9	1046.4	1048.2
7.5°	1052.3	1050.9	1049.5	1048.1	1046.7	1044.7	1042.2	1039.6	1037.1	1034.5	1036.3
10°	1043.3	1041.7	1040.1	1038.5	1037.0	1034.8	1032.1	1029.4	1026.6	1023.9	1025.7
12.5°	1031.1	1029.7	1028.2	1026.8	1025.4	1023.4	1020.6	1017.9	1015.2	1012.5	1013.8
15°	1010.6	1009.3	1007.9	1006.6	1005.2	1003.0	1000.1	997.1	994.2	991.2	992.2
17.5°	984.5	983.1	981.8	980.4	979.1	976.9	973.9	970.9	967.9	964.9	966.0
20°	965.7	964.4	963.0	961.6	960.3	958.0	954.8	951.7	948.5	945.3	946.0
22.5°	946.9	945.0	943.1	941.2	939.3	936.9	933.9	930.9	927.9	924.9	925.0
25°	914.7	912.9	911.1	909.2	907.4	904.6	900.7	896.9	893.0	889.2	889.6
27.5°	877.9	876.3	874.7	873.0	871.4	869.1	866.0	863.0	859.9	856.9	856.2
30°	853.4	851.6	849.8	848.0	846.2	843.6	840.2	836.8	833.4	830.0	829.3
32.5°	827.3	825.8	824.4	822.9	821.5	819.0	815.4	811.8	808.2	804.6	803.4
35°	789.1	786.9	784.6	782.3	780.0	777.1	773.5	769.8	766.2	762.6	761.2
37.5°	746.0	744.0	742.0	740.0	738.1	735.2	731.6	728.0	724.4	720.7	719.0
40°	716.6	714.8	713.0	711.2	709.4	706.7	703.0	699.4	695.8	692.1	690.1
42.5°	688.1	686.2	684.4	682.6	680.8	678.1	674.4	670.8	667.2	663.6	661.3
45°	642.1	640.5	638.9	637.4	635.8	633.3	629.9	626.5	623.1	619.7	617.2
47.5°	596.4	594.9	593.4	591.9	590.4	587.9	584.3	580.8	577.3	573.7	571.1
50°	564.5	563.4	562.3	561.1	560.0	557.8	554.7	551.5	548.3	545.1	542.0
52.5°	533.5	532.0	530.5	529.0	527.5	525.3	522.3	519.3	516.3	513.3	510.7
55°	485.9	484.6	483.2	481.8	480.5	478.4	475.7	473.0	470.3	467.6	464.8
57.5°	438.1	437.1	436.0	434.9	433.8	431.8	428.8	425.8	422.8	419.8	417.1
60°	406.3	405.4	404.5	403.6	402.7	400.6	397.5	394.3	391.1	387.9	385.4
62.5°	375.3	373.8	372.4	370.9	369.5	367.5	365.1	362.6	360.2	357.7	355.4
65°	327.7	326.3	325.0	323.6	322.2	320.4	318.2	315.9	313.6	311.4	309.3
67.5°	279.3	278.2	277.1	276.0	274.9	273.4	271.3	269.3	267.3	265.2	263.6
70°	249.1	248.2	247.3	246.4	245.5	244.0	241.9	239.9	237.9	235.8	234.2
72.5°	218.1	217.1	216.2	215.3	214.4	213.3	212.0	210.7	209.4	208.0	206.5
75°	171.5	171.0	170.6	170.1	169.7	168.9	167.8	166.6	165.5	164.4	163.0
77.5°	129.9	129.1	128.3	127.5	126.8	126.2	125.7	125.2	124.8	124.3	123.7
80°	102.1	101.9	101.6	101.4	101.2	100.8	100.4	99.9	99.5	99.0	98.3
82.5°	76.0	75.9	75.9	75.8	75.8	75.6	75.3	75.1	74.8	74.5	73.7
85°	41.9	41.6	41.4	41.2	40.9	40.7	40.5	40.3	40.0	39.8	39.1
87.5°	14.8	14.6	14.5	14.3	14.1	13.9	13.9	14.1	14.1	13.8	13.2
90°	0.4	1.4	2.8	3.5	4.2	5.3	7.1	9.5	11.7	12.0	11.7
92.5°	4.3	6.2	8.8	10.3	12.7	16.0	24.0	35.3	45.3	45.9	38.8
95°	12.4	13.8	17.3	20.5	26.1	34.6	50.9	81.6	122.6	138.5	121.2
97.5°	20.1	22.0	25.8	30.6	37.1	46.7	67.1	110.0	178.1	236.4	248.0
100°	27.2	28.3	31.4	37.1	44.2	54.1	72.8	115.9	192.2	279.1	330.0
102.5°	33.7	34.5	37.7	43.3	50.7	60.6	77.9	116.2	186.8	280.5	360.5
105°	43.1	44.5	47.0	52.3	60.1	70.0	86.6	118.0	176.3	261.8	355.8
107.5°	53.3	54.4	56.8	61.7	69.4	79.4	95.5	122.9	171.1	241.7	324.8
110°	60.1	61.5	63.6	68.2	75.6	85.9	101.4	126.8	170.0	232.1	305.3



TEST NUMBER: P331338

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	66.3	67.7	70.1	74.4	81.5	92.1	107.1	131.1	170.2	225.9	291.7
115°	76.0	77.7	79.9	84.1	91.2	100.7	115.9	137.4	171.7	219.1	274.9
117.5°	86.0	87.4	89.5	93.3	100.1	110.0	124.0	144.2	174.3	215.7	264.3
120°	92.2	93.6	95.8	98.9	106.0	115.9	129.7	148.8	176.0	213.8	258.6
122.5°	98.2	99.3	101.4	104.9	111.9	122.1	135.0	152.7	177.9	212.6	253.8
125°	106.0	107.1	109.2	113.4	120.5	130.4	143.1	159.0	180.9	210.6	247.0
127.5°	112.2	113.6	116.6	121.3	128.0	138.2	150.6	164.9	183.9	209.4	240.6
130°	115.9	117.3	120.8	125.8	132.9	142.7	155.1	168.5	186.2	208.8	236.4
132.5°	119.3	121.0	124.8	130.0	137.4	147.3	159.1	172.2	188.5	208.5	233.0
135°	124.4	125.8	130.0	135.3	143.5	153.3	164.7	177.0	191.2	208.1	228.2
137.5°	129.2	130.9	135.1	140.8	148.8	158.0	169.2	180.7	193.6	208.0	224.9
140°	132.9	134.3	138.5	144.2	151.9	161.1	171.7	182.7	194.7	207.8	222.9
142.5°	136.5	137.7	141.6	147.3	154.8	163.4	173.7	184.4	195.5	207.8	221.0
145°	142.0	143.5	147.0	152.3	159.4	167.1	176.7	186.6	196.4	207.0	218.4
147.5°	148.0	149.0	152.4	157.3	163.2	170.1	179.1	187.8	196.7	205.8	215.7
150°	151.9	153.0	155.8	160.4	165.7	172.1	180.2	188.3	196.4	204.9	213.4
152.5°	155.9	156.4	159.2	163.2	168.3	174.0	181.3	188.6	195.9	203.5	211.4
155°	161.5	161.8	163.9	167.8	171.7	177.0	183.0	189.0	195.0	201.0	207.8
157.5°	166.1	166.5	168.2	171.6	174.7	179.1	184.2	189.0	193.4	198.5	204.3
160°	169.2	169.6	171.0	173.8	176.7	180.6	184.8	189.0	192.6	196.8	201.7
162.5°	172.4	172.1	173.6	175.8	178.4	181.4	185.1	188.7	191.7	195.4	199.5
165°	176.0	175.6	176.3	178.4	180.2	182.3	185.5	188.0	190.1	192.6	195.7
167.5°	178.9	178.5	179.1	180.5	181.8	183.1	185.4	187.5	188.5	190.1	192.1
170°	180.9	180.2	180.6	181.6	182.3	183.4	185.1	186.9	187.6	188.7	190.1
172.5°	182.0	181.6	181.4	182.5	182.9	183.7	184.9	186.1	186.5	187.0	188.1
175°	183.4	183.0	182.7	183.4	183.4	183.7	184.4	185.1	184.8	185.1	185.5
177.5°	184.0	183.4	183.2	183.7	183.7	183.7	184.0	184.6	184.0	183.7	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331338

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1057.1	1059.0	1060.8	1061.5	1061.1	1060.8	1060.4	1060.1
5°	1050.0	1051.8	1053.6	1054.3	1053.9	1053.4	1053.0	1052.5
7.5°	1038.2	1040.0	1041.8	1042.4	1041.9	1041.5	1041.0	1040.5
10°	1027.5	1029.4	1031.2	1031.7	1031.1	1030.4	1029.7	1029.0
12.5°	1015.0	1016.3	1017.6	1017.9	1017.4	1017.0	1016.5	1016.0
15°	993.1	994.0	994.9	994.8	993.6	992.5	991.4	990.2
17.5°	967.0	968.0	969.1	969.1	968.0	966.9	965.8	964.7
20°	946.7	947.4	948.0	947.9	947.0	946.1	945.2	944.3
22.5°	925.2	925.3	925.4	925.2	924.7	924.1	923.6	923.1
25°	890.1	890.5	891.0	891.0	890.5	890.1	889.6	889.2
27.5°	855.5	854.9	854.2	853.3	852.2	851.1	850.0	848.9
30°	828.6	827.9	827.2	826.4	825.5	824.6	823.7	822.8
32.5°	802.2	801.0	799.7	798.7	797.8	796.9	795.9	795.0
35°	759.9	758.5	757.1	755.9	754.8	753.6	752.5	751.3
37.5°	717.4	715.7	714.0	712.6	711.5	710.4	709.4	708.3
40°	688.1	686.0	684.0	682.5	681.6	680.7	679.8	678.9
42.5°	659.1	656.9	654.7	652.9	651.6	650.4	649.1	647.8
45°	614.7	612.2	609.7	608.0	607.1	606.2	605.3	604.3
47.5°	568.5	565.8	563.2	561.2	559.9	558.6	557.3	556.0
50°	538.8	535.6	532.4	530.3	529.1	528.0	526.9	525.7
52.5°	508.0	505.4	502.8	500.7	499.2	497.7	496.2	494.7
55°	462.1	459.4	456.7	454.7	453.6	452.5	451.3	450.2
57.5°	414.4	411.7	409.1	407.3	406.4	405.6	404.7	403.8
60°	382.9	380.4	377.9	376.4	375.7	375.0	374.3	373.6
62.5°	353.1	350.8	348.5	346.9	346.0	345.1	344.3	343.4
65°	307.3	305.2	303.2	301.6	300.5	299.3	298.2	297.1
67.5°	262.0	260.5	258.9	257.6	256.7	255.8	254.9	254.0
70°	232.6	231.1	229.5	228.2	227.3	226.4	225.5	224.6
72.5°	204.9	203.3	201.7	200.5	199.8	199.1	198.4	197.6
75°	161.6	160.3	158.9	158.5	158.9	159.4	159.8	160.3
77.5°	123.0	122.3	121.6	121.0	120.3	119.7	119.1	118.4
80°	97.7	97.0	96.3	95.7	95.3	94.8	94.4	93.9
82.5°	72.8	71.9	71.1	70.6	70.5	70.4	70.3	70.2
85°	38.5	37.8	37.1	36.6	36.4	36.2	36.0	35.7
87.5°	12.6	11.9	11.5	11.2	11.0	10.9	10.7	10.5
90°	11.3	10.6	11.3	11.7	11.7	11.7	11.7	11.7
92.5°	30.8	26.4	23.5	21.3	21.0	19.9	20.1	19.6
95°	92.6	71.0	56.2	48.4	43.8	41.0	39.9	40.3
97.5°	216.0	176.7	138.5	113.0	96.1	87.4	82.3	79.3
100°	322.6	278.8	230.4	187.6	158.3	143.1	132.9	126.5
102.5°	392.4	382.5	347.1	301.8	269.9	244.0	231.2	222.6
105°	429.3	469.2	473.8	462.2	440.2	418.3	403.1	398.2
107.5°	402.7	462.9	499.6	516.7	519.5	518.3	515.2	508.7
110°	379.8	443.1	488.3	517.3	532.5	539.2	542.4	542.0



TEST NUMBER: P331338

CATALOG NUMBER: SA2XXDIP-C675D330U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	358.9	419.6	467.9	501.2	522.3	533.5	539.5	541.4
115°	333.2	387.6	433.9	470.3	495.4	511.6	520.8	524.0
117.5°	313.8	361.6	403.6	437.7	463.3	480.5	490.1	492.8
120°	304.2	348.0	385.5	417.6	442.4	459.0	469.2	472.8
122.5°	296.6	336.7	372.2	401.2	423.4	439.8	448.9	451.8
125°	285.5	321.9	353.0	379.5	400.0	413.4	422.2	425.1
127.5°	274.5	307.5	336.8	361.2	379.1	391.7	399.3	401.6
130°	267.5	297.9	325.8	349.1	366.4	378.4	385.5	388.3
132.5°	260.7	288.8	314.5	336.4	353.4	365.4	371.9	374.5
135°	251.2	274.5	297.9	317.6	332.8	344.5	350.9	352.3
137.5°	243.7	263.2	281.7	298.9	312.8	322.8	328.4	330.5
140°	238.8	255.8	272.1	287.6	298.9	308.1	313.4	315.5
142.5°	234.9	249.3	263.3	276.3	287.0	295.4	300.1	300.5
145°	229.3	241.0	251.9	262.2	270.6	276.7	280.2	281.2
147.5°	225.0	234.2	242.7	250.2	257.2	262.0	264.4	265.1
150°	221.9	229.7	237.1	243.4	248.7	253.0	255.1	255.5
152.5°	218.8	226.0	232.3	237.8	242.0	245.6	247.2	247.3
155°	214.5	220.1	225.4	229.3	233.2	235.7	237.1	236.4
157.5°	209.5	214.2	218.6	221.7	224.4	226.5	227.1	227.1
160°	206.3	210.2	214.1	216.6	219.1	220.8	221.2	221.2
162.5°	203.2	206.6	209.9	211.8	214.3	215.5	215.8	215.5
165°	198.6	201.0	203.5	204.9	206.3	207.8	207.8	207.4
167.5°	194.1	196.0	197.7	199.0	199.6	200.4	200.3	199.9
170°	191.9	192.9	194.3	195.0	195.4	196.4	196.1	195.4
172.5°	189.3	190.1	191.2	191.6	192.0	192.5	192.1	191.7
175°	186.6	186.9	187.3	187.6	187.6	188.0	187.6	186.9
177.5°	184.6	184.6	184.9	184.9	184.9	184.9	184.6	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7

(END OF REPORT)