

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331340

Luminaire Tested: **SA2XXDIP-C675D530U835-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331340
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4822.6 lumens
Efficiency: N/A
Efficacy: 119.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 40.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331340
CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	59	58	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45
3	85	75	68	62	79	71	65	59	62	58	53	55	51	48	47	45	42	39
4	78	67	59	53	73	63	56	51	56	50	46	49	45	41	43	40	37	34
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33	30
6	66	54	46	41	62	51	44	39	46	40	36	40	36	32	35	32	29	26
7	61	49	41	36	57	47	40	34	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	32	28	34	29	26	30	26	24	21
9	53	41	34	29	50	39	32	28	35	30	26	31	27	23	28	24	21	19
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	21447	21447	21447	21447
5°	24044	21585	19128	21585
10°	27552	21408	16554	21408
15°	30479	21016	14626	21016
20°	30015	20594	13332	20594
25°	27064	20035	12513	20035
30°	22365	19140	11915	19140
35°	16301	18203	11491	18203
40°	13019	17098	11255	17098
45°	11376	15817	10933	15817
50°	10693	14579	10721	14579
55°	9858	13320	10432	13320
60°	9032	11983	9991	11983
65°	8229	10785	9555	10785
70°	7468	9616	8917	9616
75°	6625	8309	7898	8309
80°	5700	6881	6360	6881
85°	5113	5113	3779	5113



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.5	2.6
10°-20°	367.8	7.6
20°-30°	533.7	11.1
30°-40°	563.2	11.7
40°-50°	498.7	10.3
50°-60°	398.0	8.3
60°-70°	270.5	5.6
70°-80°	138.7	2.9
80°-90°	36.1	0.7
90°-100°	42.8	0.9
100°-110°	133.0	2.8
110°-120°	227.3	4.7
120°-130°	298.9	6.2
130°-140°	335.5	7.0
140°-150°	329.0	6.8
150°-160°	275.9	5.7
160°-170°	183.0	3.8
170°-180°	64.0	1.3
0°-30°	1028.0	21.3
0°-40°	1591.2	33.0
0°-60°	2487.8	51.6
0°-90°	2933.1	60.8
90°-120°	403.1	8.4
90°-150°	1366.6	28.3
90°-180°	1889.0	39.2
0°-180°	4822.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1328	1328	1328	1328	1328	
5°	1484	1332	1180	1332	1484	148
15°	1823	1257	875	1257	1823	503
25°	1519	1125	702	1125	1519	687
35°	827	924	583	924	827	538
45°	498	693	479	693	498	392
55°	350	473	371	473	350	314
65°	215	282	250	282	215	214
75°	106	133	127	133	106	113
85°	28	28	20	28	28	31
90°	19	1	19	1	19	10
95°	35	30	35	30	35	39
105°	127	123	127	123	127	133
115°	228	228	228	228	228	225
125°	333	332	333	332	333	297
135°	434	429	434	429	434	334
145°	527	521	527	521	527	329
155°	600	596	600	596	600	276
165°	649	648	649	648	649	183
175°	672	675	672	675	672	64
180°	676	676	676	676	676	



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1389.5	1389.9	1390.8	1384.2	1383.4	1383.4	1377.7	1372.8	1367.1	1359.3	1360.1
5°	1483.5	1489.1	1491.1	1485.0	1475.8	1474.8	1466.1	1451.8	1438.5	1427.8	1420.2
7.5°	1595.6	1597.8	1592.8	1584.7	1577.9	1565.7	1549.5	1533.7	1511.5	1491.2	1476.1
10°	1680.5	1683.6	1674.9	1663.2	1653.5	1639.2	1615.7	1591.7	1562.6	1534.5	1512.0
12.5°	1745.0	1752.6	1741.5	1739.9	1723.3	1703.7	1675.7	1663.6	1622.6	1583.5	1559.4
15°	1823.4	1822.9	1824.0	1814.3	1802.0	1798.9	1769.3	1737.2	1679.5	1656.5	1616.7
17.5°	1800.8	1808.5	1812.1	1812.0	1811.7	1809.8	1800.3	1780.0	1751.1	1713.8	1667.8
20°	1746.9	1757.1	1758.6	1770.4	1777.0	1785.7	1789.2	1783.6	1765.8	1734.6	1694.8
22.5°	1663.6	1666.4	1671.2	1689.5	1703.9	1725.6	1737.0	1755.9	1749.0	1733.8	1700.5
25°	1519.2	1514.1	1532.0	1541.1	1574.3	1609.0	1634.1	1661.6	1686.1	1700.9	1691.2
27.5°	1345.8	1338.2	1364.9	1389.3	1416.3	1453.9	1492.9	1538.9	1577.2	1625.1	1641.5
30°	1199.6	1204.2	1229.8	1255.8	1296.6	1349.7	1393.6	1444.2	1498.8	1552.4	1589.6
32.5°	1042.0	1059.7	1075.8	1115.7	1151.6	1210.9	1275.2	1338.4	1406.5	1467.4	1525.1
35°	827.0	847.4	869.9	899.0	949.5	1008.2	1071.0	1156.2	1249.2	1332.4	1400.8
37.5°	696.1	692.8	705.7	726.7	767.7	815.0	887.3	971.6	1080.9	1178.7	1275.2
40°	617.7	615.6	624.8	644.2	675.4	710.1	773.4	847.4	949.0	1068.4	1183.3
42.5°	563.8	565.0	570.1	583.8	605.1	633.7	681.1	744.1	837.1	949.6	1073.0
45°	498.2	501.8	507.4	514.1	526.3	549.8	576.3	621.3	694.8	788.7	910.2
47.5°	451.1	451.2	456.9	462.7	470.0	483.2	504.9	533.0	584.9	661.4	765.8
50°	425.7	422.2	426.3	430.8	438.5	447.7	462.0	488.5	523.2	585.0	672.3
52.5°	394.7	394.8	398.5	400.2	407.1	416.2	429.3	447.7	479.1	527.4	599.2
55°	350.2	352.7	354.8	357.8	364.0	370.6	380.8	393.1	417.6	453.8	506.9
57.5°	308.3	309.1	311.2	317.0	320.9	327.0	336.7	347.8	363.8	390.6	430.5
60°	279.7	279.7	283.8	286.4	291.5	297.6	305.3	316.0	330.3	352.2	384.4
62.5°	253.6	253.2	254.8	259.0	262.9	268.6	276.3	285.4	298.8	318.3	344.8
65°	215.4	214.4	217.5	218.5	222.6	228.2	234.3	244.0	254.7	269.0	292.5
67.5°	178.7	179.9	181.5	183.5	185.7	191.6	195.7	202.6	211.6	223.5	239.4
70°	158.2	158.2	158.2	159.8	162.8	165.9	170.0	175.6	184.3	194.5	208.8
72.5°	135.4	137.0	138.6	137.7	141.6	143.4	148.3	151.5	159.8	166.3	179.0
75°	106.2	106.2	106.2	108.7	110.3	111.8	114.9	117.9	122.0	130.2	136.8
77.5°	79.2	79.0	79.5	80.1	81.8	83.6	84.5	87.3	91.1	94.8	100.5
80°	61.3	62.3	62.8	63.8	63.8	64.8	65.3	68.9	71.5	74.0	77.6
82.5°	47.4	47.6	47.7	47.9	48.3	48.9	50.2	51.4	52.3	54.4	57.2
85°	27.6	27.1	27.1	28.1	27.6	27.6	28.6	29.6	29.6	30.1	31.6
87.5°	14.5	14.5	14.9	14.4	14.4	14.8	14.9	14.5	15.0	15.4	15.3
90°	19.4	19.3	19.1	19.0	18.9	18.9	19.2	19.5	19.7	20.0	17.2
92.5°	18.5	18.5	18.4	18.4	18.4	18.3	18.3	18.2	18.2	18.1	17.5
95°	35.4	35.6	35.9	36.1	36.4	36.5	36.5	36.5	36.5	36.5	36.2
97.5°	61.2	61.3	61.3	61.3	61.3	61.4	61.4	61.4	61.4	61.4	60.9
100°	78.1	78.3	78.4	78.5	78.6	78.7	78.7	78.7	78.7	78.7	78.3
102.5°	97.3	97.4	97.5	97.7	97.8	97.8	97.7	97.6	97.5	97.4	96.9
105°	126.6	126.6	126.6	126.6	126.6	126.5	126.2	126.0	125.7	125.5	125.2
107.5°	154.2	154.8	155.4	155.9	156.5	156.8	156.7	156.6	156.5	156.4	156.4
110°	175.6	176.0	176.4	176.8	177.2	177.3	177.3	177.3	177.3	177.3	177.3



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	196.2	196.4	196.7	197.0	197.3	197.6	197.9	198.2	198.5	198.8	198.9
115°	228.1	228.5	228.9	229.2	229.6	229.9	230.0	230.1	230.3	230.4	230.6
117.5°	258.5	258.9	259.3	259.7	260.1	260.4	260.7	261.0	261.3	261.6	262.3
120°	280.0	280.4	280.8	281.1	281.5	281.7	281.7	281.7	281.7	281.7	282.7
122.5°	301.0	301.3	301.5	301.8	302.1	302.4	302.7	303.0	303.3	303.6	304.3
125°	333.0	333.1	333.3	333.4	333.5	333.8	334.2	334.5	334.9	335.3	335.7
127.5°	362.2	362.6	363.0	363.4	363.8	364.3	364.7	365.2	365.6	366.1	366.6
130°	383.2	383.7	384.2	384.7	385.2	385.6	385.9	386.1	386.4	386.6	386.9
132.5°	403.3	403.7	404.1	404.5	404.9	405.4	405.9	406.5	407.1	407.6	407.6
135°	434.5	434.9	435.3	435.7	436.0	436.3	436.4	436.6	436.7	436.8	436.6
137.5°	462.8	463.3	463.8	464.3	464.8	465.1	465.2	465.3	465.4	465.5	465.2
140°	482.4	482.9	483.4	483.9	484.5	484.7	484.7	484.7	484.7	484.7	484.1
142.5°	500.2	500.7	501.2	501.7	502.2	502.4	502.3	502.2	502.1	502.0	501.6
145°	526.9	527.4	527.9	528.4	528.9	529.1	529.0	528.9	528.7	528.6	527.9
147.5°	550.7	551.2	551.7	552.2	552.7	552.8	552.5	552.2	551.9	551.7	551.1
150°	566.3	566.6	567.0	567.4	567.8	567.8	567.4	567.0	566.6	566.3	565.7
152.5°	580.9	581.3	581.8	582.3	582.8	582.8	582.3	581.8	581.3	580.9	580.2
155°	600.5	600.8	601.2	601.6	602.0	601.9	601.2	600.6	600.0	599.3	598.9
157.5°	617.3	618.0	618.6	619.2	619.8	619.7	618.8	617.9	617.1	616.2	616.0
160°	627.8	628.3	628.9	629.4	629.9	629.7	629.0	628.2	627.5	626.7	626.6
162.5°	637.0	637.6	638.2	638.8	639.4	639.3	638.4	637.5	636.7	635.8	635.7
165°	648.9	649.6	650.2	650.8	651.5	651.3	650.5	649.6	648.7	647.8	647.8
167.5°	658.7	659.4	660.1	660.7	661.4	661.3	660.4	659.5	658.6	657.7	657.7
170°	663.8	664.5	665.3	666.0	666.8	666.7	665.9	665.0	664.1	663.2	663.3
172.5°	667.9	668.6	669.4	670.2	670.9	670.8	670.0	669.1	668.2	667.3	667.4
175°	672.3	673.1	673.8	674.6	675.4	675.3	674.4	673.5	672.6	671.7	672.0
177.5°	674.4	675.0	675.6	676.2	676.8	676.8	676.2	675.6	675.0	674.4	674.6
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1363.0	1359.7	1357.7	1350.3	1343.8	1337.3	1335.2	1336.0	1327.1	1318.5	1314.8
5°	1416.1	1405.9	1396.2	1382.4	1366.1	1348.2	1339.0	1331.8	1314.0	1294.6	1283.4
7.5°	1463.7	1449.1	1430.4	1404.4	1380.7	1352.6	1334.7	1318.9	1292.7	1265.4	1248.6
10°	1492.7	1472.7	1448.7	1417.1	1388.0	1353.8	1329.8	1305.8	1275.2	1242.5	1222.1
12.5°	1517.6	1490.7	1467.1	1426.5	1392.1	1349.3	1320.8	1287.0	1254.8	1216.0	1196.0
15°	1576.9	1527.4	1482.4	1436.5	1394.1	1334.4	1302.8	1257.3	1214.9	1167.0	1144.0
17.5°	1622.7	1567.1	1496.3	1437.9	1388.5	1322.4	1275.9	1221.5	1171.4	1116.5	1085.3
20°	1648.9	1585.0	1509.0	1439.6	1380.3	1304.8	1254.3	1198.6	1139.9	1078.1	1044.4
22.5°	1664.4	1597.3	1522.1	1433.4	1364.0	1290.5	1226.9	1165.9	1106.4	1039.8	1004.4
25°	1669.3	1608.0	1528.4	1428.3	1343.6	1260.4	1183.8	1124.6	1052.6	990.3	938.8
27.5°	1645.0	1601.1	1524.5	1418.7	1320.0	1222.7	1137.4	1070.3	994.3	926.7	874.9
30°	1615.2	1589.6	1515.1	1408.9	1301.2	1196.6	1102.6	1026.6	951.0	882.6	829.5
32.5°	1569.0	1563.5	1498.0	1395.0	1281.2	1163.5	1066.3	989.4	905.7	838.5	787.9
35°	1478.4	1502.9	1461.5	1364.0	1243.5	1116.4	1011.3	923.5	836.7	772.4	724.9
37.5°	1356.9	1417.7	1406.9	1318.6	1192.7	1065.2	949.1	857.3	774.6	709.7	663.1
40°	1273.1	1350.7	1362.0	1283.9	1156.8	1025.6	902.5	811.2	730.5	671.3	624.3
42.5°	1183.3	1274.0	1304.8	1242.2	1117.5	983.9	860.9	766.2	686.4	628.8	587.2
45°	1032.7	1152.7	1208.3	1172.6	1052.1	915.3	788.7	692.7	620.2	566.1	534.0
47.5°	891.9	1023.0	1097.8	1085.2	979.3	843.8	718.7	626.6	556.0	512.8	484.0
50°	792.3	927.0	1017.4	1021.5	927.0	792.8	667.2	580.4	515.6	475.3	451.8
52.5°	705.7	834.3	932.9	954.5	868.6	739.7	621.1	534.7	477.6	440.5	419.5
55°	592.7	701.4	810.6	850.5	781.5	659.0	549.3	473.2	419.6	394.1	375.7
57.5°	492.7	583.4	684.3	728.3	685.8	580.9	478.0	412.0	368.5	346.1	332.0
60°	440.0	511.5	601.3	653.9	617.2	523.8	433.9	371.1	335.4	315.5	302.2
62.5°	391.0	454.3	530.3	578.4	558.4	470.3	389.8	334.4	303.5	284.8	275.3
65°	322.6	372.7	431.4	475.8	462.5	395.6	329.8	282.3	257.8	243.0	235.3
67.5°	265.7	301.8	342.5	381.4	370.7	323.3	270.5	233.5	215.2	202.5	197.9
70°	229.7	257.3	293.5	324.7	316.0	277.2	235.3	203.7	187.9	177.1	172.5
72.5°	195.4	218.1	245.7	271.2	265.3	233.1	198.2	174.3	162.1	152.2	148.4
75°	147.5	164.9	181.7	198.6	197.0	172.0	151.6	133.2	123.5	115.9	114.3
77.5°	108.9	118.6	130.1	140.1	137.3	123.0	107.0	96.5	89.3	84.2	83.4
80°	83.2	88.8	97.0	104.1	100.6	94.4	81.7	74.0	68.9	63.8	61.8
82.5°	60.3	66.0	70.9	74.7	72.0	66.3	58.4	53.2	50.1	46.7	45.8
85°	31.6	34.7	36.8	37.8	36.8	33.2	29.6	27.6	25.0	23.5	23.0
87.5°	15.1	14.6	14.0	14.4	12.9	12.6	10.6	9.1	9.0	8.9	8.4
90°	14.4	11.6	8.8	6.7	5.1	3.6	2.1	0.6	2.1	3.6	5.1
92.5°	16.8	16.2	15.5	14.6	13.5	12.4	11.3	10.2	11.3	12.4	13.5
95°	36.0	35.7	35.5	34.7	33.5	32.2	30.9	29.7	30.9	32.2	33.5
97.5°	60.4	59.9	59.4	58.6	57.5	56.4	55.3	54.2	55.3	56.4	57.5
100°	77.9	77.6	77.2	76.5	75.5	74.4	73.4	72.4	73.4	74.4	75.5
102.5°	96.4	96.0	95.5	94.8	94.0	93.2	92.4	91.6	92.4	93.2	94.0
105°	124.9	124.7	124.4	124.1	123.7	123.4	123.0	122.6	123.0	123.4	123.7
107.5°	156.4	156.4	156.4	156.1	155.5	155.0	154.4	153.9	154.4	155.0	155.5
110°	177.3	177.3	177.3	177.0	176.2	175.4	174.7	173.9	174.7	175.4	176.2



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	199.0	199.1	199.2	198.9	198.1	197.3	196.6	195.8	196.6	197.3	198.1
115°	230.9	231.1	231.4	231.1	230.4	229.6	228.9	228.1	228.9	229.6	230.4
117.5°	263.0	263.8	264.5	264.3	263.3	262.3	261.3	260.3	261.3	262.3	263.3
120°	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7	282.7	283.7	284.7
122.5°	305.0	305.7	306.4	306.2	305.0	303.8	302.5	301.3	302.5	303.8	305.0
125°	336.1	336.4	336.8	336.4	335.3	334.2	333.0	331.9	333.0	334.2	335.3
127.5°	367.0	367.5	367.9	367.4	366.0	364.5	363.1	361.6	363.1	364.5	366.0
130°	387.1	387.4	387.6	386.9	385.3	383.6	382.0	380.4	382.0	383.6	385.3
132.5°	407.5	407.5	407.4	406.7	405.4	404.0	402.7	401.3	402.7	404.0	405.4
135°	436.3	436.0	435.8	435.0	433.6	432.2	430.8	429.4	430.8	432.2	433.6
137.5°	464.9	464.6	464.2	463.5	462.4	461.2	460.1	458.9	460.1	461.2	462.4
140°	483.4	482.8	482.2	481.3	480.1	479.0	477.9	476.7	477.9	479.0	480.1
142.5°	501.2	500.8	500.3	499.5	498.4	497.3	496.1	495.0	496.1	497.3	498.4
145°	527.1	526.3	525.6	524.8	523.9	523.0	522.1	521.2	522.1	523.0	523.9
147.5°	550.6	550.1	549.6	548.8	547.8	546.7	545.6	544.6	545.6	546.7	547.8
150°	565.2	564.7	564.2	563.6	562.8	562.1	561.3	560.6	561.3	562.1	562.8
152.5°	579.6	579.0	578.4	577.7	577.0	576.2	575.5	574.7	575.5	576.2	577.0
155°	598.6	598.2	597.8	597.4	597.0	596.7	596.3	595.9	596.3	596.7	597.0
157.5°	615.8	615.5	615.3	615.1	614.8	614.5	614.3	614.0	614.3	614.5	614.8
160°	626.4	626.3	626.2	626.0	625.7	625.5	625.2	625.0	625.2	625.5	625.7
162.5°	635.6	635.4	635.3	635.2	635.2	635.1	635.1	635.0	635.1	635.1	635.2
165°	647.8	647.8	647.8	647.9	648.0	648.1	648.2	648.4	648.2	648.1	648.0
167.5°	657.8	657.8	657.8	658.0	658.4	658.8	659.2	659.5	659.2	658.8	658.4
170°	663.4	663.6	663.7	664.0	664.3	664.7	665.1	665.5	665.1	664.7	664.3
172.5°	667.6	667.7	667.8	668.1	668.4	668.8	669.2	669.6	669.2	668.8	668.4
175°	672.3	672.5	672.8	673.1	673.5	673.8	674.2	674.6	674.2	673.8	673.5
177.5°	674.8	675.0	675.2	675.4	675.7	676.0	676.3	676.7	676.3	676.0	675.7
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331340
 CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1310.7	1308.3	1299.7	1295.2	1287.8	1280.9	1276.4	1278.5	1280.1	1279.3	1278.0
5°	1273.1	1263.4	1248.6	1235.9	1226.7	1209.8	1202.7	1199.1	1196.1	1192.5	1188.9
7.5°	1228.4	1213.1	1191.9	1173.7	1156.5	1135.6	1123.7	1116.5	1109.2	1101.1	1094.0
10°	1196.6	1175.1	1152.7	1127.1	1106.7	1087.8	1071.0	1059.8	1049.6	1039.9	1032.7
12.5°	1163.1	1138.4	1110.6	1075.7	1053.2	1026.2	1023.6	1003.8	987.9	981.9	973.5
15°	1109.8	1075.1	1039.9	998.5	980.6	956.1	940.8	925.5	911.7	902.0	899.5
17.5°	1049.2	1004.3	969.3	939.6	910.3	885.2	871.1	858.8	847.5	834.5	832.8
20°	1003.1	964.3	926.0	900.0	869.9	844.3	827.0	814.7	805.0	797.4	790.7
22.5°	959.4	916.9	881.9	853.4	823.7	803.1	789.4	777.6	769.5	761.0	754.8
25°	889.3	856.1	817.8	785.6	761.1	747.9	736.6	726.4	721.3	715.7	708.6
27.5°	827.9	791.0	755.2	730.3	708.8	697.0	689.0	682.1	677.3	674.0	670.0
30°	784.6	747.3	719.3	694.8	676.9	665.2	660.1	656.0	650.4	648.3	646.3
32.5°	743.0	709.4	685.4	664.1	647.1	639.4	634.7	631.1	626.7	624.6	620.5
35°	684.0	656.0	632.5	620.7	607.0	600.3	596.8	591.6	587.6	585.5	585.0
37.5°	628.6	604.2	588.8	573.7	567.9	563.8	558.9	555.4	554.2	553.9	553.4
40°	592.7	572.8	559.0	546.7	544.2	538.0	534.0	530.9	530.9	531.4	530.9
42.5°	560.0	542.1	530.0	519.4	516.4	512.7	508.6	508.4	509.3	511.0	509.3
45°	510.5	497.7	489.0	483.9	478.3	474.7	474.2	475.8	476.3	476.8	478.3
47.5°	464.9	456.5	448.6	443.0	440.5	439.9	439.3	442.0	444.4	445.3	447.7
50°	438.0	428.3	421.7	418.1	416.0	415.0	416.0	419.1	421.1	423.7	425.2
52.5°	407.8	400.9	396.3	393.6	392.8	393.4	393.6	397.1	400.3	401.2	402.0
55°	366.0	360.9	359.9	355.3	357.3	356.8	359.4	361.4	364.5	367.5	368.1
57.5°	324.4	320.3	317.5	317.9	318.5	320.8	322.9	326.5	329.8	333.0	333.3
60°	296.6	294.5	293.0	293.0	294.0	297.1	299.7	303.2	305.3	307.3	308.8
62.5°	271.3	269.2	267.7	268.5	271.2	273.0	276.0	277.9	279.9	282.0	282.7
65°	231.2	230.2	231.8	232.8	233.3	235.8	239.4	240.9	243.0	244.0	247.6
67.5°	194.4	194.6	194.4	195.8	198.8	199.4	202.8	206.3	206.7	208.7	211.0
70°	169.5	170.5	171.5	172.5	175.1	176.1	178.7	180.2	182.2	183.8	185.3
72.5°	146.6	146.8	147.8	147.6	149.8	152.0	154.2	155.7	157.7	159.7	161.2
75°	112.8	112.8	113.8	114.3	116.9	119.5	118.9	120.0	122.0	124.0	125.1
77.5°	82.4	81.3	82.4	82.9	83.7	85.9	86.3	87.7	90.0	89.3	90.5
80°	62.8	61.3	62.8	63.3	63.3	65.9	65.9	66.9	68.4	66.9	68.4
82.5°	44.8	44.1	45.2	45.3	46.1	46.2	47.1	47.3	48.8	48.1	48.8
85°	22.5	22.0	22.5	22.0	22.5	23.0	23.0	22.5	22.5	23.5	22.0
87.5°	8.3	8.3	8.4	9.0	9.2	9.3	8.8	8.8	8.7	7.9	7.9
90°	6.7	8.8	11.6	14.4	17.2	20.0	19.7	19.5	19.2	18.9	18.9
92.5°	14.6	15.5	16.2	16.8	17.5	18.1	18.2	18.2	18.3	18.3	18.4
95°	34.7	35.5	35.7	36.0	36.2	36.5	36.5	36.5	36.5	36.5	36.4
97.5°	58.6	59.4	59.9	60.4	60.9	61.4	61.4	61.4	61.4	61.4	61.3
100°	76.5	77.2	77.6	77.9	78.3	78.7	78.7	78.7	78.7	78.7	78.6
102.5°	94.8	95.5	96.0	96.4	96.9	97.4	97.5	97.6	97.7	97.8	97.8
105°	124.1	124.4	124.7	124.9	125.2	125.5	125.7	126.0	126.2	126.5	126.6
107.5°	156.1	156.4	156.4	156.4	156.4	156.4	156.5	156.6	156.7	156.8	156.5
110°	177.0	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.3	177.2



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	198.9	199.2	199.1	199.0	198.9	198.8	198.5	198.2	197.9	197.6	197.3
115°	231.1	231.4	231.1	230.9	230.6	230.4	230.3	230.1	230.0	229.9	229.6
117.5°	264.3	264.5	263.8	263.0	262.3	261.6	261.3	261.0	260.7	260.4	260.1
120°	285.8	285.8	284.7	283.7	282.7	281.7	281.7	281.7	281.7	281.7	281.5
122.5°	306.2	306.4	305.7	305.0	304.3	303.6	303.3	303.0	302.7	302.4	302.1
125°	336.4	336.8	336.4	336.1	335.7	335.3	334.9	334.5	334.2	333.8	333.5
127.5°	367.4	367.9	367.5	367.0	366.6	366.1	365.6	365.2	364.7	364.3	363.8
130°	386.9	387.6	387.4	387.1	386.9	386.6	386.4	386.1	385.9	385.6	385.2
132.5°	406.7	407.4	407.5	407.5	407.6	407.6	407.1	406.5	405.9	405.4	404.9
135°	435.0	435.8	436.0	436.3	436.6	436.8	436.7	436.6	436.4	436.3	436.0
137.5°	463.5	464.2	464.6	464.9	465.2	465.5	465.4	465.3	465.2	465.1	464.8
140°	481.3	482.2	482.8	483.4	484.1	484.7	484.7	484.7	484.7	484.7	484.5
142.5°	499.5	500.3	500.8	501.2	501.6	502.0	502.1	502.2	502.3	502.4	502.2
145°	524.8	525.6	526.3	527.1	527.9	528.6	528.7	528.9	529.0	529.1	528.9
147.5°	548.8	549.6	550.1	550.6	551.1	551.7	551.9	552.2	552.5	552.8	552.7
150°	563.6	564.2	564.7	565.2	565.7	566.3	566.6	567.0	567.4	567.8	567.8
152.5°	577.7	578.4	579.0	579.6	580.2	580.9	581.3	581.8	582.3	582.8	582.8
155°	597.4	597.8	598.2	598.6	598.9	599.3	600.0	600.6	601.2	601.9	602.0
157.5°	615.1	615.3	615.5	615.8	616.0	616.2	617.1	617.9	618.8	619.7	619.8
160°	626.0	626.2	626.3	626.4	626.6	626.7	627.5	628.2	629.0	629.7	629.9
162.5°	635.2	635.3	635.4	635.6	635.7	635.8	636.7	637.5	638.4	639.3	639.4
165°	647.9	647.8	647.8	647.8	647.8	647.8	648.7	649.6	650.5	651.3	651.5
167.5°	658.0	657.8	657.8	657.8	657.7	657.7	658.6	659.5	660.4	661.3	661.4
170°	664.0	663.7	663.6	663.4	663.3	663.2	664.1	665.0	665.9	666.7	666.8
172.5°	668.1	667.8	667.7	667.6	667.4	667.3	668.2	669.1	670.0	670.8	670.9
175°	673.1	672.8	672.5	672.3	672.0	671.7	672.6	673.5	674.4	675.3	675.4
177.5°	675.4	675.2	675.0	674.8	674.6	674.4	675.0	675.6	676.2	676.8	676.8
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1274.0	1273.1	1273.1	1269.5	1273.1	1273.1	1274.0	1278.0	1279.3	1280.1	1278.5
5°	1181.8	1180.2	1177.7	1180.2	1177.7	1180.2	1181.8	1188.9	1192.5	1196.1	1199.1
7.5°	1090.6	1084.5	1083.6	1077.5	1083.6	1084.5	1090.6	1094.0	1101.1	1109.2	1116.5
10°	1024.0	1019.9	1019.4	1009.7	1019.4	1019.9	1024.0	1032.7	1039.9	1049.6	1059.8
12.5°	973.4	963.6	965.5	959.9	965.5	963.6	973.4	973.5	981.9	987.9	1003.8
15°	885.7	885.7	883.6	875.0	883.6	885.7	885.7	899.5	902.0	911.7	925.5
17.5°	822.7	821.7	816.8	819.2	816.8	821.7	822.7	832.8	834.5	847.5	858.8
20°	785.1	782.1	775.9	775.9	775.9	782.1	785.1	790.7	797.4	805.0	814.7
22.5°	749.6	749.4	742.9	744.9	742.9	749.4	749.6	754.8	761.0	769.5	777.6
25°	708.0	704.0	700.9	702.4	700.9	704.0	708.0	708.6	715.7	721.3	726.4
27.5°	668.6	666.4	666.2	662.0	666.2	666.4	668.6	670.0	674.0	677.3	682.1
30°	645.8	640.7	641.7	639.1	641.7	640.7	645.8	646.3	648.3	650.4	656.0
32.5°	619.6	617.8	616.8	614.6	616.8	617.8	619.6	620.5	624.6	626.7	631.1
35°	584.0	584.5	582.0	583.0	582.0	584.5	584.0	585.0	585.5	587.6	591.6
37.5°	552.9	554.5	553.3	553.6	553.3	554.5	552.9	553.4	553.9	554.2	555.4
40°	532.4	532.4	532.4	534.0	532.4	532.4	532.4	530.9	531.4	530.9	530.9
42.5°	512.8	512.0	511.2	511.1	511.2	512.0	512.8	509.3	511.0	509.3	508.4
45°	479.3	480.9	481.4	478.8	481.4	480.9	479.3	478.3	476.8	476.3	475.8
47.5°	449.0	449.2	449.0	451.3	449.0	449.2	449.0	447.7	445.3	444.4	442.0
50°	427.8	426.8	427.8	426.8	427.8	426.8	427.8	425.2	423.7	421.1	419.1
52.5°	405.3	405.5	404.9	404.7	404.9	405.5	405.3	402.0	401.2	400.3	397.1
55°	370.1	371.1	370.6	370.6	370.6	371.1	370.1	368.1	367.5	364.5	361.4
57.5°	333.7	334.6	335.3	333.0	335.3	334.6	333.7	333.3	333.0	329.8	326.5
60°	308.3	310.9	310.4	309.4	310.4	310.9	308.3	308.8	307.3	305.3	303.2
62.5°	285.1	286.0	285.9	285.7	285.9	286.0	285.1	282.7	282.0	279.9	277.9
65°	249.1	250.1	248.6	250.1	248.6	250.1	249.1	247.6	244.0	243.0	240.9
67.5°	210.4	210.7	211.9	212.6	211.9	210.7	210.4	211.0	208.7	206.7	206.3
70°	186.3	185.8	187.3	188.9	187.3	185.8	186.3	185.3	183.8	182.2	180.2
72.5°	161.0	162.1	161.6	162.7	161.6	162.1	161.0	161.2	159.7	157.7	155.7
75°	124.0	125.6	125.1	126.6	125.1	125.6	124.0	125.1	124.0	122.0	120.0
77.5°	89.6	89.8	89.6	90.5	89.6	89.8	89.6	90.5	89.3	90.0	87.7
80°	68.4	67.4	66.4	68.4	66.4	67.4	68.4	68.4	66.9	68.4	66.9
82.5°	47.6	48.2	47.2	47.2	47.2	48.2	47.6	48.8	48.1	48.8	47.3
85°	22.0	21.4	20.4	20.4	20.4	21.4	22.0	22.0	23.5	22.5	22.5
87.5°	7.9	7.5	7.5	7.1	7.5	7.5	7.9	7.9	7.9	8.7	8.8
90°	19.0	19.1	19.3	19.4	19.3	19.1	19.0	18.9	18.9	19.2	19.5
92.5°	18.4	18.4	18.5	18.5	18.5	18.4	18.4	18.4	18.3	18.3	18.2
95°	36.1	35.9	35.6	35.4	35.6	35.9	36.1	36.4	36.5	36.5	36.5
97.5°	61.3	61.3	61.3	61.2	61.3	61.3	61.3	61.3	61.4	61.4	61.4
100°	78.5	78.4	78.3	78.1	78.3	78.4	78.5	78.6	78.7	78.7	78.7
102.5°	97.7	97.5	97.4	97.3	97.4	97.5	97.7	97.8	97.8	97.7	97.6
105°	126.6	126.6	126.6	126.6	126.6	126.6	126.6	126.6	126.5	126.2	126.0
107.5°	155.9	155.4	154.8	154.2	154.8	155.4	155.9	156.5	156.8	156.7	156.6
110°	176.8	176.4	176.0	175.6	176.0	176.4	176.8	177.2	177.3	177.3	177.3



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	197.0	196.7	196.4	196.2	196.4	196.7	197.0	197.3	197.6	197.9	198.2
115°	229.2	228.9	228.5	228.1	228.5	228.9	229.2	229.6	229.9	230.0	230.1
117.5°	259.7	259.3	258.9	258.5	258.9	259.3	259.7	260.1	260.4	260.7	261.0
120°	281.1	280.8	280.4	280.0	280.4	280.8	281.1	281.5	281.7	281.7	281.7
122.5°	301.8	301.5	301.3	301.0	301.3	301.5	301.8	302.1	302.4	302.7	303.0
125°	333.4	333.3	333.1	333.0	333.1	333.3	333.4	333.5	333.8	334.2	334.5
127.5°	363.4	363.0	362.6	362.2	362.6	363.0	363.4	363.8	364.3	364.7	365.2
130°	384.7	384.2	383.7	383.2	383.7	384.2	384.7	385.2	385.6	385.9	386.1
132.5°	404.5	404.1	403.7	403.3	403.7	404.1	404.5	404.9	405.4	405.9	406.5
135°	435.7	435.3	434.9	434.5	434.9	435.3	435.7	436.0	436.3	436.4	436.6
137.5°	464.3	463.8	463.3	462.8	463.3	463.8	464.3	464.8	465.1	465.2	465.3
140°	483.9	483.4	482.9	482.4	482.9	483.4	483.9	484.5	484.7	484.7	484.7
142.5°	501.7	501.2	500.7	500.2	500.7	501.2	501.7	502.2	502.4	502.3	502.2
145°	528.4	527.9	527.4	526.9	527.4	527.9	528.4	528.9	529.1	529.0	528.9
147.5°	552.2	551.7	551.2	550.7	551.2	551.7	552.2	552.7	552.8	552.5	552.2
150°	567.4	567.0	566.6	566.3	566.6	567.0	567.4	567.8	567.8	567.4	567.0
152.5°	582.3	581.8	581.3	580.9	581.3	581.8	582.3	582.8	582.8	582.3	581.8
155°	601.6	601.2	600.8	600.5	600.8	601.2	601.6	602.0	601.9	601.2	600.6
157.5°	619.2	618.6	618.0	617.3	618.0	618.6	619.2	619.8	619.7	618.8	617.9
160°	629.4	628.9	628.3	627.8	628.3	628.9	629.4	629.9	629.7	629.0	628.2
162.5°	638.8	638.2	637.6	637.0	637.6	638.2	638.8	639.4	639.3	638.4	637.5
165°	650.8	650.2	649.6	648.9	649.6	650.2	650.8	651.5	651.3	650.5	649.6
167.5°	660.7	660.1	659.4	658.7	659.4	660.1	660.7	661.4	661.3	660.4	659.5
170°	666.0	665.3	664.5	663.8	664.5	665.3	666.0	666.8	666.7	665.9	665.0
172.5°	670.2	669.4	668.6	667.9	668.6	669.4	670.2	670.9	670.8	670.0	669.1
175°	674.6	673.8	673.1	672.3	673.1	673.8	674.6	675.4	675.3	674.4	673.5
177.5°	676.2	675.6	675.0	674.4	675.0	675.6	676.2	676.8	676.8	676.2	675.6
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1276.4	1280.9	1287.8	1295.2	1299.7	1308.3	1310.7	1314.8	1318.5	1327.1	1336.0
5°	1202.7	1209.8	1226.7	1235.9	1248.6	1263.4	1273.1	1283.4	1294.6	1314.0	1331.8
7.5°	1123.7	1135.6	1156.5	1173.7	1191.9	1213.1	1228.4	1248.6	1265.4	1292.7	1318.9
10°	1071.0	1087.8	1106.7	1127.1	1152.7	1175.1	1196.6	1222.1	1242.5	1275.2	1305.8
12.5°	1023.6	1026.2	1053.2	1075.7	1110.6	1138.4	1163.1	1196.0	1216.0	1254.8	1287.0
15°	940.8	956.1	980.6	998.5	1039.9	1075.1	1109.8	1144.0	1167.0	1214.9	1257.3
17.5°	871.1	885.2	910.3	939.6	969.3	1004.3	1049.2	1085.3	1116.5	1171.4	1221.5
20°	827.0	844.3	869.9	900.0	926.0	964.3	1003.1	1044.4	1078.1	1139.9	1198.6
22.5°	789.4	803.1	823.7	853.4	881.9	916.9	959.4	1004.4	1039.8	1106.4	1165.9
25°	736.6	747.9	761.1	785.6	817.8	856.1	889.3	938.8	990.3	1052.6	1124.6
27.5°	689.0	697.0	708.8	730.3	755.2	791.0	827.9	874.9	926.7	994.3	1070.3
30°	660.1	665.2	676.9	694.8	719.3	747.3	784.6	829.5	882.6	951.0	1026.6
32.5°	634.7	639.4	647.1	664.1	685.4	709.4	743.0	787.9	838.5	905.7	989.4
35°	596.8	600.3	607.0	620.7	632.5	656.0	684.0	724.9	772.4	836.7	923.5
37.5°	558.9	563.8	567.9	573.7	588.8	604.2	628.6	663.1	709.7	774.6	857.3
40°	534.0	538.0	544.2	546.7	559.0	572.8	592.7	624.3	671.3	730.5	811.2
42.5°	508.6	512.7	516.4	519.4	530.0	542.1	560.0	587.2	628.8	686.4	766.2
45°	474.2	474.7	478.3	483.9	489.0	497.7	510.5	534.0	566.1	620.2	692.7
47.5°	439.3	439.9	440.5	443.0	448.6	456.5	464.9	484.0	512.8	556.0	626.6
50°	416.0	415.0	416.0	418.1	421.7	428.3	438.0	451.8	475.3	515.6	580.4
52.5°	393.6	393.4	392.8	393.6	396.3	400.9	407.8	419.5	440.5	477.6	534.7
55°	359.4	356.8	357.3	355.3	359.9	360.9	366.0	375.7	394.1	419.6	473.2
57.5°	322.9	320.8	318.5	317.9	317.5	320.3	324.4	332.0	346.1	368.5	412.0
60°	299.7	297.1	294.0	293.0	293.0	294.5	296.6	302.2	315.5	335.4	371.1
62.5°	276.0	273.0	271.2	268.5	267.7	269.2	271.3	275.3	284.8	303.5	334.4
65°	239.4	235.8	233.3	232.8	231.8	230.2	231.2	235.3	243.0	257.8	282.3
67.5°	202.8	199.4	198.8	195.8	194.4	194.6	194.4	197.9	202.5	215.2	233.5
70°	178.7	176.1	175.1	172.5	171.5	170.5	169.5	172.5	177.1	187.9	203.7
72.5°	154.2	152.0	149.8	147.6	147.8	146.8	146.6	148.4	152.2	162.1	174.3
75°	118.9	119.5	116.9	114.3	113.8	112.8	112.8	114.3	115.9	123.5	133.2
77.5°	86.3	85.9	83.7	82.9	82.4	81.3	82.4	83.4	84.2	89.3	96.5
80°	65.9	65.9	63.3	63.3	62.8	61.3	62.8	61.8	63.8	68.9	74.0
82.5°	47.1	46.2	46.1	45.3	45.2	44.1	44.8	45.8	46.7	50.1	53.2
85°	23.0	23.0	22.5	22.0	22.5	22.0	22.5	23.0	23.5	25.0	27.6
87.5°	8.8	9.3	9.2	9.0	8.4	8.3	8.3	8.4	8.9	9.0	9.1
90°	19.7	20.0	17.2	14.4	11.6	8.8	6.7	5.1	3.6	2.1	0.6
92.5°	18.2	18.1	17.5	16.8	16.2	15.5	14.6	13.5	12.4	11.3	10.2
95°	36.5	36.5	36.2	36.0	35.7	35.5	34.7	33.5	32.2	30.9	29.7
97.5°	61.4	61.4	60.9	60.4	59.9	59.4	58.6	57.5	56.4	55.3	54.2
100°	78.7	78.7	78.3	77.9	77.6	77.2	76.5	75.5	74.4	73.4	72.4
102.5°	97.5	97.4	96.9	96.4	96.0	95.5	94.8	94.0	93.2	92.4	91.6
105°	125.7	125.5	125.2	124.9	124.7	124.4	124.1	123.7	123.4	123.0	122.6
107.5°	156.5	156.4	156.4	156.4	156.4	156.4	156.1	155.5	155.0	154.4	153.9
110°	177.3	177.3	177.3	177.3	177.3	177.3	177.0	176.2	175.4	174.7	173.9



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	198.5	198.8	198.9	199.0	199.1	199.2	198.9	198.1	197.3	196.6	195.8
115°	230.3	230.4	230.6	230.9	231.1	231.4	231.1	230.4	229.6	228.9	228.1
117.5°	261.3	261.6	262.3	263.0	263.8	264.5	264.3	263.3	262.3	261.3	260.3
120°	281.7	281.7	282.7	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7
122.5°	303.3	303.6	304.3	305.0	305.7	306.4	306.2	305.0	303.8	302.5	301.3
125°	334.9	335.3	335.7	336.1	336.4	336.8	336.4	335.3	334.2	333.0	331.9
127.5°	365.6	366.1	366.6	367.0	367.5	367.9	367.4	366.0	364.5	363.1	361.6
130°	386.4	386.6	386.9	387.1	387.4	387.6	386.9	385.3	383.6	382.0	380.4
132.5°	407.1	407.6	407.6	407.5	407.5	407.4	406.7	405.4	404.0	402.7	401.3
135°	436.7	436.8	436.6	436.3	436.0	435.8	435.0	433.6	432.2	430.8	429.4
137.5°	465.4	465.5	465.2	464.9	464.6	464.2	463.5	462.4	461.2	460.1	458.9
140°	484.7	484.7	484.1	483.4	482.8	482.2	481.3	480.1	479.0	477.9	476.7
142.5°	502.1	502.0	501.6	501.2	500.8	500.3	499.5	498.4	497.3	496.1	495.0
145°	528.7	528.6	527.9	527.1	526.3	525.6	524.8	523.9	523.0	522.1	521.2
147.5°	551.9	551.7	551.1	550.6	550.1	549.6	548.8	547.8	546.7	545.6	544.6
150°	566.6	566.3	565.7	565.2	564.7	564.2	563.6	562.8	562.1	561.3	560.6
152.5°	581.3	580.9	580.2	579.6	579.0	578.4	577.7	577.0	576.2	575.5	574.7
155°	600.0	599.3	598.9	598.6	598.2	597.8	597.4	597.0	596.7	596.3	595.9
157.5°	617.1	616.2	616.0	615.8	615.5	615.3	615.1	614.8	614.5	614.3	614.0
160°	627.5	626.7	626.6	626.4	626.3	626.2	626.0	625.7	625.5	625.2	625.0
162.5°	636.7	635.8	635.7	635.6	635.4	635.3	635.2	635.2	635.1	635.1	635.0
165°	648.7	647.8	647.8	647.8	647.8	647.8	647.9	648.0	648.1	648.2	648.4
167.5°	658.6	657.7	657.7	657.8	657.8	657.8	658.0	658.4	658.8	659.2	659.5
170°	664.1	663.2	663.3	663.4	663.6	663.7	664.0	664.3	664.7	665.1	665.5
172.5°	668.2	667.3	667.4	667.6	667.7	667.8	668.1	668.4	668.8	669.2	669.6
175°	672.6	671.7	672.0	672.3	672.5	672.8	673.1	673.5	673.8	674.2	674.6
177.5°	675.0	674.4	674.6	674.8	675.0	675.2	675.4	675.7	676.0	676.3	676.7
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1335.2	1337.3	1343.8	1350.3	1357.7	1359.7	1363.0	1360.1	1359.3	1367.1	1372.8
5°	1339.0	1348.2	1366.1	1382.4	1396.2	1405.9	1416.1	1420.2	1427.8	1438.5	1451.8
7.5°	1334.7	1352.6	1380.7	1404.4	1430.4	1449.1	1463.7	1476.1	1491.2	1511.5	1533.7
10°	1329.8	1353.8	1388.0	1417.1	1448.7	1472.7	1492.7	1512.0	1534.5	1562.6	1591.7
12.5°	1320.8	1349.3	1392.1	1426.5	1467.1	1490.7	1517.6	1559.4	1583.5	1622.6	1663.6
15°	1302.8	1334.4	1394.1	1436.5	1482.4	1527.4	1576.9	1616.7	1656.5	1679.5	1737.2
17.5°	1275.9	1322.4	1388.5	1437.9	1496.3	1567.1	1622.7	1667.8	1713.8	1751.1	1780.0
20°	1254.3	1304.8	1380.3	1439.6	1509.0	1585.0	1648.9	1694.8	1734.6	1765.8	1783.6
22.5°	1226.9	1290.5	1364.0	1433.4	1522.1	1597.3	1664.4	1700.5	1733.8	1749.0	1755.9
25°	1183.8	1260.4	1343.6	1428.3	1528.4	1608.0	1669.3	1691.2	1700.9	1686.1	1661.6
27.5°	1137.4	1222.7	1320.0	1418.7	1524.5	1601.1	1645.0	1641.5	1625.1	1577.2	1538.9
30°	1102.6	1196.6	1301.2	1408.9	1515.1	1589.6	1615.2	1589.6	1552.4	1498.8	1444.2
32.5°	1066.3	1163.5	1281.2	1395.0	1498.0	1563.5	1569.0	1525.1	1467.4	1406.5	1338.4
35°	1011.3	1116.4	1243.5	1364.0	1461.5	1502.9	1478.4	1400.8	1332.4	1249.2	1156.2
37.5°	949.1	1065.2	1192.7	1318.6	1406.9	1417.7	1356.9	1275.2	1178.7	1080.9	971.6
40°	902.5	1025.6	1156.8	1283.9	1362.0	1350.7	1273.1	1183.3	1068.4	949.0	847.4
42.5°	860.9	983.9	1117.5	1242.2	1304.8	1274.0	1183.3	1073.0	949.6	837.1	744.1
45°	788.7	915.3	1052.1	1172.6	1208.3	1152.7	1032.7	910.2	788.7	694.8	621.3
47.5°	718.7	843.8	979.3	1085.2	1097.8	1023.0	891.9	765.8	661.4	584.9	533.0
50°	667.2	792.8	927.0	1021.5	1017.4	927.0	792.3	672.3	585.0	523.2	488.5
52.5°	621.1	739.7	868.6	954.5	932.9	834.3	705.7	599.2	527.4	479.1	447.7
55°	549.3	659.0	781.5	850.5	810.6	701.4	592.7	506.9	453.8	417.6	393.1
57.5°	478.0	580.9	685.8	728.3	684.3	583.4	492.7	430.5	390.6	363.8	347.8
60°	433.9	523.8	617.2	653.9	601.3	511.5	440.0	384.4	352.2	330.3	316.0
62.5°	389.8	470.3	558.4	578.4	530.3	454.3	391.0	344.8	318.3	298.8	285.4
65°	329.8	395.6	462.5	475.8	431.4	372.7	322.6	292.5	269.0	254.7	244.0
67.5°	270.5	323.3	370.7	381.4	342.5	301.8	265.7	239.4	223.5	211.6	202.6
70°	235.3	277.2	316.0	324.7	293.5	257.3	229.7	208.8	194.5	184.3	175.6
72.5°	198.2	233.1	265.3	271.2	245.7	218.1	195.4	179.0	166.3	159.8	151.5
75°	151.6	172.0	197.0	198.6	181.7	164.9	147.5	136.8	130.2	122.0	117.9
77.5°	107.0	123.0	137.3	140.1	130.1	118.6	108.9	100.5	94.8	91.1	87.3
80°	81.7	94.4	100.6	104.1	97.0	88.8	83.2	77.6	74.0	71.5	68.9
82.5°	58.4	66.3	72.0	74.7	70.9	66.0	60.3	57.2	54.4	52.3	51.4
85°	29.6	33.2	36.8	37.8	36.8	34.7	31.6	31.6	30.1	29.6	29.6
87.5°	10.6	12.6	12.9	14.4	14.0	14.6	15.1	15.3	15.4	15.0	14.5
90°	2.1	3.6	5.1	6.7	8.8	11.6	14.4	17.2	20.0	19.7	19.5
92.5°	11.3	12.4	13.5	14.6	15.5	16.2	16.8	17.5	18.1	18.2	18.2
95°	30.9	32.2	33.5	34.7	35.5	35.7	36.0	36.2	36.5	36.5	36.5
97.5°	55.3	56.4	57.5	58.6	59.4	59.9	60.4	60.9	61.4	61.4	61.4
100°	73.4	74.4	75.5	76.5	77.2	77.6	77.9	78.3	78.7	78.7	78.7
102.5°	92.4	93.2	94.0	94.8	95.5	96.0	96.4	96.9	97.4	97.5	97.6
105°	123.0	123.4	123.7	124.1	124.4	124.7	124.9	125.2	125.5	125.7	126.0
107.5°	154.4	155.0	155.5	156.1	156.4	156.4	156.4	156.4	156.4	156.5	156.6
110°	174.7	175.4	176.2	177.0	177.3	177.3	177.3	177.3	177.3	177.3	177.3



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	196.6	197.3	198.1	198.9	199.2	199.1	199.0	198.9	198.8	198.5	198.2
115°	228.9	229.6	230.4	231.1	231.4	231.1	230.9	230.6	230.4	230.3	230.1
117.5°	261.3	262.3	263.3	264.3	264.5	263.8	263.0	262.3	261.6	261.3	261.0
120°	282.7	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7	281.7	281.7
122.5°	302.5	303.8	305.0	306.2	306.4	305.7	305.0	304.3	303.6	303.3	303.0
125°	333.0	334.2	335.3	336.4	336.8	336.4	336.1	335.7	335.3	334.9	334.5
127.5°	363.1	364.5	366.0	367.4	367.9	367.5	367.0	366.6	366.1	365.6	365.2
130°	382.0	383.6	385.3	386.9	387.6	387.4	387.1	386.9	386.6	386.4	386.1
132.5°	402.7	404.0	405.4	406.7	407.4	407.5	407.5	407.6	407.6	407.1	406.5
135°	430.8	432.2	433.6	435.0	435.8	436.0	436.3	436.6	436.8	436.7	436.6
137.5°	460.1	461.2	462.4	463.5	464.2	464.6	464.9	465.2	465.5	465.4	465.3
140°	477.9	479.0	480.1	481.3	482.2	482.8	483.4	484.1	484.7	484.7	484.7
142.5°	496.1	497.3	498.4	499.5	500.3	500.8	501.2	501.6	502.0	502.1	502.2
145°	522.1	523.0	523.9	524.8	525.6	526.3	527.1	527.9	528.6	528.7	528.9
147.5°	545.6	546.7	547.8	548.8	549.6	550.1	550.6	551.1	551.7	551.9	552.2
150°	561.3	562.1	562.8	563.6	564.2	564.7	565.2	565.7	566.3	566.6	567.0
152.5°	575.5	576.2	577.0	577.7	578.4	579.0	579.6	580.2	580.9	581.3	581.8
155°	596.3	596.7	597.0	597.4	597.8	598.2	598.6	598.9	599.3	600.0	600.6
157.5°	614.3	614.5	614.8	615.1	615.3	615.5	615.8	616.0	616.2	617.1	617.9
160°	625.2	625.5	625.7	626.0	626.2	626.3	626.4	626.6	626.7	627.5	628.2
162.5°	635.1	635.1	635.2	635.2	635.3	635.4	635.6	635.7	635.8	636.7	637.5
165°	648.2	648.1	648.0	647.9	647.8	647.8	647.8	647.8	647.8	648.7	649.6
167.5°	659.2	658.8	658.4	658.0	657.8	657.8	657.8	657.7	657.7	658.6	659.5
170°	665.1	664.7	664.3	664.0	663.7	663.6	663.4	663.3	663.2	664.1	665.0
172.5°	669.2	668.8	668.4	668.1	667.8	667.7	667.6	667.4	667.3	668.2	669.1
175°	674.2	673.8	673.5	673.1	672.8	672.5	672.3	672.0	671.7	672.6	673.5
177.5°	676.3	676.0	675.7	675.4	675.2	675.0	674.8	674.6	674.4	675.0	675.6
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3	1328.3
2.5°	1377.7	1383.4	1383.4	1384.2	1390.8	1389.9	1389.5
5°	1466.1	1474.8	1475.8	1485.0	1491.1	1489.1	1483.5
7.5°	1549.5	1565.7	1577.9	1584.7	1592.8	1597.8	1595.6
10°	1615.7	1639.2	1653.5	1663.2	1674.9	1683.6	1680.5
12.5°	1675.7	1703.7	1723.3	1739.9	1741.5	1752.6	1745.0
15°	1769.3	1798.9	1802.0	1814.3	1824.0	1822.9	1823.4
17.5°	1800.3	1809.8	1811.7	1812.0	1812.1	1808.5	1800.8
20°	1789.2	1785.7	1777.0	1770.4	1758.6	1757.1	1746.9
22.5°	1737.0	1725.6	1703.9	1689.5	1671.2	1666.4	1663.6
25°	1634.1	1609.0	1574.3	1541.1	1532.0	1514.1	1519.2
27.5°	1492.9	1453.9	1416.3	1389.3	1364.9	1338.2	1345.8
30°	1393.6	1349.7	1296.6	1255.8	1229.8	1204.2	1199.6
32.5°	1275.2	1210.9	1151.6	1115.7	1075.8	1059.7	1042.0
35°	1071.0	1008.2	949.5	899.0	869.9	847.4	827.0
37.5°	887.3	815.0	767.7	726.7	705.7	692.8	696.1
40°	773.4	710.1	675.4	644.2	624.8	615.6	617.7
42.5°	681.1	633.7	605.1	583.8	570.1	565.0	563.8
45°	576.3	549.8	526.3	514.1	507.4	501.8	498.2
47.5°	504.9	483.2	470.0	462.7	456.9	451.2	451.1
50°	462.0	447.7	438.5	430.8	426.3	422.2	425.7
52.5°	429.3	416.2	407.1	400.2	398.5	394.8	394.7
55°	380.8	370.6	364.0	357.8	354.8	352.7	350.2
57.5°	336.7	327.0	320.9	317.0	311.2	309.1	308.3
60°	305.3	297.6	291.5	286.4	283.8	279.7	279.7
62.5°	276.3	268.6	262.9	259.0	254.8	253.2	253.6
65°	234.3	228.2	222.6	218.5	217.5	214.4	215.4
67.5°	195.7	191.6	185.7	183.5	181.5	179.9	178.7
70°	170.0	165.9	162.8	159.8	158.2	158.2	158.2
72.5°	148.3	143.4	141.6	137.7	138.6	137.0	135.4
75°	114.9	111.8	110.3	108.7	106.2	106.2	106.2
77.5°	84.5	83.6	81.8	80.1	79.5	79.0	79.2
80°	65.3	64.8	63.8	63.8	62.8	62.3	61.3
82.5°	50.2	48.9	48.3	47.9	47.7	47.6	47.4
85°	28.6	27.6	27.6	28.1	27.1	27.1	27.6
87.5°	14.9	14.8	14.4	14.4	14.9	14.5	14.5
90°	19.2	18.9	18.9	19.0	19.1	19.3	19.4
92.5°	18.3	18.3	18.4	18.4	18.4	18.5	18.5
95°	36.5	36.5	36.4	36.1	35.9	35.6	35.4
97.5°	61.4	61.4	61.3	61.3	61.3	61.3	61.2
100°	78.7	78.7	78.6	78.5	78.4	78.3	78.1
102.5°	97.7	97.8	97.8	97.7	97.5	97.4	97.3
105°	126.2	126.5	126.6	126.6	126.6	126.6	126.6
107.5°	156.7	156.8	156.5	155.9	155.4	154.8	154.2
110°	177.3	177.3	177.2	176.8	176.4	176.0	175.6



TEST NUMBER: P331340

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	197.9	197.6	197.3	197.0	196.7	196.4	196.2
115°	230.0	229.9	229.6	229.2	228.9	228.5	228.1
117.5°	260.7	260.4	260.1	259.7	259.3	258.9	258.5
120°	281.7	281.7	281.5	281.1	280.8	280.4	280.0
122.5°	302.7	302.4	302.1	301.8	301.5	301.3	301.0
125°	334.2	333.8	333.5	333.4	333.3	333.1	333.0
127.5°	364.7	364.3	363.8	363.4	363.0	362.6	362.2
130°	385.9	385.6	385.2	384.7	384.2	383.7	383.2
132.5°	405.9	405.4	404.9	404.5	404.1	403.7	403.3
135°	436.4	436.3	436.0	435.7	435.3	434.9	434.5
137.5°	465.2	465.1	464.8	464.3	463.8	463.3	462.8
140°	484.7	484.7	484.5	483.9	483.4	482.9	482.4
142.5°	502.3	502.4	502.2	501.7	501.2	500.7	500.2
145°	529.0	529.1	528.9	528.4	527.9	527.4	526.9
147.5°	552.5	552.8	552.7	552.2	551.7	551.2	550.7
150°	567.4	567.8	567.8	567.4	567.0	566.6	566.3
152.5°	582.3	582.8	582.8	582.3	581.8	581.3	580.9
155°	601.2	601.9	602.0	601.6	601.2	600.8	600.5
157.5°	618.8	619.7	619.8	619.2	618.6	618.0	617.3
160°	629.0	629.7	629.9	629.4	628.9	628.3	627.8
162.5°	638.4	639.3	639.4	638.8	638.2	637.6	637.0
165°	650.5	651.3	651.5	650.8	650.2	649.6	648.9
167.5°	660.4	661.3	661.4	660.7	660.1	659.4	658.7
170°	665.9	666.7	666.8	666.0	665.3	664.5	663.8
172.5°	670.0	670.8	670.9	670.2	669.4	668.6	667.9
175°	674.4	675.3	675.4	674.6	673.8	673.1	672.3
177.5°	676.2	676.8	676.8	676.2	675.6	675.0	674.4
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7

(END OF REPORT)