

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331655-927

Luminaire Tested: **SA2XXRDIP-C485D530U927-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331655-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2843.5 lumens  
Efficiency: N/A  
Efficacy: 86.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 32.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331655-927  
CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331655-927

CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41	
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	40				35	
3	82	73	66	60	75	67	61	56	57	52	49	47	44	41	38	36	34				30	
4	75	65	57	51	69	60	53	48	51	46	42	42	39	36	35	32	30				26	
5	69	58	50	44	63	54	47	41	46	40	36	38	34	31	31	29	26				23	
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	23				20	
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	26	23	21				18	
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19				17	
9	51	39	32	27	47	37	30	25	32	26	23	27	23	20	22	19	17				15	
10	48	36	29	24	44	34	27	23	29	24	21	25	21	18	21	18	16				14	

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10555	10555	10555
5°	10595	10423	10481
10°	10516	10252	10165
15°	10394	9949	9663
20°	10227	9514	9036
25°	10055	9021	8432
30°	9818	8516	7655
35°	9585	7965	6974
40°	9352	7396	6184
45°	9079	6754	5471
50°	8796	6106	4770
55°	8510	5413	4096
60°	8176	4682	3400
65°	7798	3931	3095
70°	7345	3238	2851
75°	6787	2951	2658
80°	5997	2641	2427
85°	4705	2075	2075



TEST NUMBER: P331655-927

CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	61.2	2.2
10°-20°	168.0	5.9
20°-30°	235.9	8.3
30°-40°	257.3	9.0
40°-50°	236.6	8.3
50°-60°	185.8	6.5
60°-70°	121.1	4.3
70°-80°	62.5	2.2
80°-90°	18.3	0.6
90°-100°	33.9	1.2
100°-110°	105.4	3.7
110°-120°	180.1	6.3
120°-130°	236.8	8.3
130°-140°	265.8	9.3
140°-150°	260.6	9.2
150°-160°	218.6	7.7
160°-170°	145.0	5.1
170°-180°	50.7	1.8
0°-30°	465.2	16.4
0°-40°	722.4	25.4
0°-60°	1144.8	40.3
0°-90°	1346.7	47.4
90°-120°	319.4	11.2
90°-150°	1082.6	38.1
90°-180°	1497.0	52.6
0°-180°	2843.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	654	654	654	654	654	
5°	654	650	643	648	647	62
15°	622	615	595	584	578	175
25°	564	544	506	483	473	259
35°	486	455	404	368	354	304
45°	398	357	296	255	240	307
55°	302	255	192	158	146	270
65°	204	156	103	84	81	202
75°	109	69	47	43	43	115
85°	25	14	11	11	11	30
90°	0	6	16	15	15	2
95°	24	28	29	29	28	27
105°	97	98	99	100	100	103
115°	181	183	182	182	181	179
125°	263	267	266	264	264	235
135°	340	345	346	346	344	263
145°	413	416	419	419	417	258
155°	472	473	475	477	476	217
165°	514	513	513	516	514	145
175°	534	533	532	535	533	51
180°	535	535	535	535	535	



TEST NUMBER: P331655-927

CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	656.1	655.6	655.1	654.5	654.0	653.2	652.0	650.9	649.7	648.6	649.6
5°	653.7	653.1	652.4	651.8	651.1	649.9	648.2	646.5	644.8	643.1	644.3
7.5°	647.0	646.2	645.4	644.5	643.7	642.3	640.3	638.3	636.4	634.4	634.7
10°	641.4	640.4	639.4	638.6	637.6	635.9	633.3	630.6	628.0	625.3	625.0
12.5°	634.2	633.1	631.9	630.8	629.7	627.5	624.1	620.8	617.3	614.0	613.3
15°	621.8	620.4	618.9	617.4	616.0	613.1	608.6	604.1	599.7	595.2	592.7
17.5°	606.6	604.4	602.1	599.9	597.7	593.7	588.0	582.3	576.6	570.8	567.8
20°	595.2	592.6	589.9	587.3	584.6	580.0	573.5	566.9	560.3	553.7	550.5
22.5°	582.9	580.0	576.9	574.0	571.1	565.9	558.5	551.0	543.7	536.2	532.0
25°	564.4	560.2	556.0	551.8	547.6	541.1	532.4	523.8	515.1	506.4	501.1
27.5°	542.2	537.6	533.0	528.5	523.9	516.7	506.9	497.1	487.4	477.5	471.3
30°	526.6	521.6	516.6	511.6	506.6	498.8	488.3	477.8	467.2	456.8	450.0
32.5°	511.4	505.6	499.7	493.9	488.1	479.7	469.1	458.3	447.6	436.9	429.2
35°	486.3	479.6	472.9	466.2	459.5	450.4	438.8	427.2	415.7	404.1	395.8
37.5°	461.2	453.8	446.5	439.1	431.8	421.9	409.6	397.3	384.9	372.6	363.5
40°	443.7	435.9	427.9	420.1	412.2	401.9	389.1	376.4	363.6	350.9	341.5
42.5°	425.7	417.4	409.1	400.8	392.5	381.8	368.6	355.4	342.2	329.1	319.4
45°	397.6	388.8	379.9	371.1	362.3	351.0	337.2	323.4	309.6	295.8	286.5
47.5°	370.1	360.8	351.5	342.1	332.8	321.0	306.7	292.5	278.2	264.0	254.7
50°	350.2	340.9	331.6	322.3	312.9	301.0	286.5	272.1	257.6	243.1	234.1
52.5°	330.8	321.1	311.3	301.6	291.8	279.9	265.7	251.6	237.4	223.3	214.5
55°	302.3	292.1	281.8	271.6	261.3	249.1	234.9	220.7	206.4	192.3	184.4
57.5°	273.1	262.6	252.1	241.5	231.0	219.0	205.3	191.6	178.0	164.4	157.1
60°	253.2	242.7	232.2	221.7	211.1	199.2	185.6	172.1	158.5	145.0	138.2
62.5°	233.8	223.3	212.8	202.2	191.7	180.1	167.2	154.2	141.3	128.4	122.0
65°	204.1	193.5	182.8	172.1	161.5	150.3	138.5	126.6	114.8	102.9	98.5
67.5°	175.5	164.9	154.3	143.8	133.2	122.6	111.9	101.3	90.6	80.0	78.0
70°	155.6	145.4	135.1	124.8	114.5	104.9	95.9	86.7	77.7	68.6	67.3
72.5°	136.7	126.8	117.0	107.2	97.4	88.8	81.5	74.2	66.9	59.7	58.5
75°	108.8	99.7	90.5	81.3	72.0	65.2	60.8	56.2	51.8	47.3	46.4
77.5°	81.5	73.4	65.4	57.3	49.3	44.1	42.0	39.8	37.6	35.5	34.9
80°	64.5	57.8	51.1	44.4	37.6	33.7	32.3	31.1	29.7	28.4	27.9
82.5°	48.9	43.6	38.4	33.2	28.0	24.9	24.0	23.1	22.2	21.3	21.0
85°	25.4	22.7	19.9	17.2	14.4	12.8	12.4	12.0	11.6	11.2	11.2
87.5°	7.7	7.1	6.5	5.9	5.2	5.1	5.6	6.1	6.5	7.0	6.8
90°	0.5	1.7	2.9	4.0	5.3	7.0	9.2	11.4	13.6	15.8	15.6
92.5°	8.1	9.0	9.8	10.7	11.6	12.3	12.8	13.3	13.9	14.3	14.4
95°	23.5	24.5	25.5	26.5	27.5	28.1	28.3	28.5	28.7	28.9	28.9
97.5°	42.9	43.8	44.7	45.6	46.4	47.1	47.5	47.8	48.2	48.6	48.6
100°	57.4	58.1	58.9	59.8	60.6	61.2	61.5	61.7	62.0	62.3	62.3
102.5°	72.6	73.2	73.8	74.5	75.1	75.7	76.0	76.4	76.8	77.2	77.2
105°	97.1	97.4	97.8	98.0	98.3	98.5	98.8	98.9	99.2	99.4	99.6
107.5°	121.9	122.3	122.8	123.2	123.7	123.9	123.9	123.9	123.9	123.9	124.0
110°	137.8	138.4	138.9	139.6	140.2	140.5	140.5	140.5	140.5	140.5	140.5



TEST NUMBER: P331655-927

CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	155.1	155.7	156.3	156.9	157.6	157.8	157.7	157.6	157.6	157.5	157.2
115°	180.7	181.3	181.9	182.5	183.1	183.3	183.1	182.9	182.7	182.5	182.4
117.5°	206.2	207.0	207.8	208.6	209.4	209.5	209.0	208.3	207.8	207.2	207.0
120°	223.2	223.9	224.7	225.5	226.4	226.4	225.5	224.7	223.9	223.2	223.2
122.5°	238.7	239.6	240.7	241.6	242.6	242.7	242.2	241.6	241.1	240.5	240.3
125°	262.9	263.8	264.7	265.6	266.5	266.8	266.5	266.3	265.9	265.6	265.3
127.5°	286.5	287.6	288.8	289.9	291.0	291.4	291.1	290.7	290.4	290.0	289.6
130°	301.3	302.6	303.9	305.2	306.5	307.0	306.9	306.7	306.5	306.3	306.1
132.5°	317.9	319.0	320.0	321.2	322.2	322.7	322.8	322.8	322.9	322.9	322.5
135°	340.2	341.3	342.4	343.5	344.6	345.2	345.4	345.6	345.9	346.0	345.9
137.5°	363.5	364.5	365.4	366.3	367.2	367.7	368.0	368.3	368.5	368.8	368.7
140°	377.6	378.6	379.5	380.3	381.3	382.0	382.5	382.9	383.5	384.0	384.0
142.5°	392.1	393.0	394.0	394.8	395.7	396.3	396.7	397.0	397.4	397.7	397.8
145°	412.9	413.6	414.3	415.0	415.7	416.4	416.9	417.6	418.2	418.7	418.8
147.5°	431.4	432.2	433.1	434.0	434.7	435.4	435.8	436.2	436.6	437.0	437.2
150°	444.1	444.7	445.3	445.8	446.5	446.9	447.3	447.7	448.1	448.6	448.9
152.5°	455.3	455.9	456.5	457.1	457.6	458.2	458.7	459.1	459.6	460.2	460.5
155°	472.1	472.4	472.7	472.9	473.2	473.6	473.9	474.2	474.4	474.8	475.3
157.5°	486.4	486.6	486.8	487.0	487.3	487.4	487.6	487.8	488.0	488.1	488.9
160°	495.1	495.3	495.5	495.7	495.9	496.1	496.1	496.2	496.4	496.5	497.1
162.5°	503.0	503.1	503.1	503.2	503.2	503.3	503.4	503.5	503.6	503.7	504.4
165°	513.7	513.5	513.4	513.3	513.3	513.2	513.2	513.2	513.2	513.2	513.9
167.5°	522.4	522.2	521.9	521.6	521.3	521.1	521.1	521.1	521.0	521.0	521.7
170°	527.2	526.9	526.6	526.2	526.0	525.8	525.7	525.5	525.5	525.4	526.1
172.5°	530.4	530.1	529.8	529.5	529.3	529.0	528.9	528.9	528.7	528.6	529.3
175°	534.4	534.1	533.8	533.5	533.2	533.0	532.7	532.6	532.3	532.1	532.8
177.5°	536.1	535.8	535.5	535.3	535.0	534.9	534.7	534.6	534.4	534.2	534.7
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3



TEST NUMBER: P331655-927

CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	650.6	651.7	652.8	653.2	653.0	652.8	652.5	652.4
5°	645.5	646.7	647.8	648.2	647.8	647.5	647.1	646.7
7.5°	635.0	635.3	635.7	635.6	634.9	634.1	633.5	632.8
10°	624.6	624.2	623.8	623.2	622.4	621.6	620.8	620.0
12.5°	612.6	611.9	611.2	610.1	608.8	607.5	606.2	604.9
15°	590.2	587.7	585.2	583.3	581.9	580.7	579.3	578.1
17.5°	564.8	561.9	558.9	556.3	554.1	551.8	549.5	547.2
20°	547.2	543.9	540.6	537.5	534.6	531.7	528.9	525.9
22.5°	527.8	523.6	519.4	516.1	514.0	511.8	509.7	507.5
25°	495.7	490.3	484.9	481.2	479.2	477.2	475.3	473.3
27.5°	465.0	458.7	452.4	447.7	444.6	441.5	438.3	435.2
30°	443.3	436.7	429.9	424.8	421.2	417.7	414.2	410.6
32.5°	421.5	413.9	406.2	400.8	397.4	394.1	390.7	387.4
35°	387.5	379.2	371.0	365.4	362.5	359.6	356.7	353.8
37.5°	354.3	345.2	336.1	329.9	326.6	323.3	320.0	316.6
40°	332.2	322.8	313.5	307.1	303.7	300.3	296.8	293.4
42.5°	309.7	300.1	290.5	284.0	280.7	277.3	274.0	270.7
45°	277.1	267.8	258.5	252.2	249.1	245.9	242.7	239.6
47.5°	245.4	236.1	226.9	220.8	217.9	215.1	212.1	209.3
50°	225.0	215.9	206.8	201.0	198.2	195.4	192.7	189.9
52.5°	205.7	197.0	188.2	182.6	180.1	177.5	174.9	172.4
55°	176.5	168.6	160.7	155.5	153.0	150.5	148.1	145.5
57.5°	149.9	142.7	135.5	130.8	128.7	126.6	124.5	122.3
60°	131.5	124.8	118.1	113.8	111.6	109.5	107.4	105.3
62.5°	115.6	109.2	102.8	99.0	97.8	96.5	95.2	94.0
65°	94.0	89.5	85.1	82.6	82.2	81.8	81.4	81.0
67.5°	75.9	73.8	71.8	70.6	70.1	69.7	69.3	68.8
70°	66.0	64.7	63.4	62.4	61.9	61.4	60.8	60.4
72.5°	57.4	56.3	55.2	54.5	54.2	53.9	53.6	53.2
75°	45.5	44.6	43.6	43.1	43.0	42.9	42.7	42.6
77.5°	34.5	33.9	33.4	33.0	32.8	32.6	32.4	32.2
80°	27.3	26.9	26.3	26.1	26.1	26.1	26.1	26.1
82.5°	20.7	20.4	20.0	19.9	19.9	19.9	19.9	19.9
85°	11.2	11.2	11.2	11.2	11.2	11.2	11.2	11.2
87.5°	6.7	6.5	6.3	6.3	6.3	6.3	6.3	6.4
90°	15.4	15.2	15.0	15.0	15.1	15.1	15.3	15.4
92.5°	14.4	14.5	14.5	14.6	14.6	14.6	14.7	14.7
95°	28.9	28.9	28.9	28.8	28.6	28.4	28.2	28.0
97.5°	48.6	48.6	48.6	48.6	48.6	48.6	48.6	48.5
100°	62.3	62.3	62.3	62.3	62.2	62.1	62.0	61.9
102.5°	77.3	77.4	77.5	77.5	77.4	77.2	77.2	77.1
105°	99.8	100.0	100.2	100.3	100.3	100.3	100.3	100.3
107.5°	124.1	124.1	124.2	124.0	123.5	123.1	122.6	122.2
110°	140.5	140.5	140.5	140.4	140.1	139.7	139.4	139.1





TEST NUMBER: P331655-927

CATALOG NUMBER: SA2XXRDIP-C485D530U927-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	157.0	156.8	156.5	156.3	156.1	155.8	155.6	155.4
115°	182.3	182.2	182.1	181.9	181.6	181.3	181.0	180.7
117.5°	206.8	206.5	206.3	206.0	205.7	205.4	205.1	204.8
120°	223.2	223.2	223.2	223.0	222.7	222.4	222.1	221.8
122.5°	240.0	239.8	239.6	239.3	239.1	238.8	238.7	238.4
125°	265.0	264.7	264.4	264.2	264.1	264.0	263.9	263.8
127.5°	289.3	288.9	288.6	288.2	287.9	287.6	287.2	286.9
130°	305.9	305.7	305.5	305.1	304.8	304.4	304.0	303.6
132.5°	322.0	321.5	321.2	320.8	320.4	320.1	319.8	319.5
135°	345.9	345.7	345.6	345.4	345.2	344.8	344.5	344.2
137.5°	368.6	368.5	368.4	368.2	367.8	367.4	367.0	366.6
140°	384.0	384.0	384.0	383.8	383.3	382.9	382.5	382.1
142.5°	397.8	397.9	398.0	397.8	397.4	397.0	396.6	396.2
145°	419.0	419.1	419.1	419.0	418.6	418.2	417.8	417.4
147.5°	437.4	437.7	437.9	437.8	437.4	437.0	436.7	436.3
150°	449.2	449.5	449.8	449.8	449.5	449.2	448.9	448.6
152.5°	460.9	461.3	461.7	461.7	461.3	460.9	460.5	460.2
155°	475.8	476.3	476.8	476.9	476.6	476.3	475.9	475.7
157.5°	489.5	490.2	490.9	491.0	490.5	490.0	489.6	489.0
160°	497.6	498.3	498.8	499.0	498.6	498.2	497.7	497.3
162.5°	505.0	505.7	506.4	506.5	506.0	505.6	505.1	504.6
165°	514.6	515.3	515.9	516.1	515.6	515.1	514.6	514.0
167.5°	522.4	523.2	523.9	523.9	523.4	522.9	522.4	521.8
170°	526.8	527.5	528.1	528.2	527.6	527.0	526.4	525.9
172.5°	530.0	530.8	531.4	531.5	530.9	530.3	529.7	529.1
175°	533.5	534.2	535.0	535.0	534.4	533.8	533.2	532.6
177.5°	535.2	535.7	536.1	536.1	535.7	535.2	534.7	534.2
180°	535.3	535.3	535.3	535.3	535.3	535.3	535.3	535.3

(END OF REPORT)