

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331347

Luminaire Tested: **SA2XXDIP-C675D530U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331347  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D530U835-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4767.4 lumens  
Efficiency: N/A  
Efficacy: 118.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 40.3  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331347

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331347

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	99	95	91	87	92	88	85	82	76	74	72	65	63	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	48	46	44	40
3	82	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34
4	75	65	57	50	70	60	53	48	53	47	43	45	41	37	38	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	32	35	31	28	25
6	64	52	43	38	59	48	41	36	42	36	32	37	32	28	31	28	25	22
7	59	47	39	33	55	44	37	31	38	33	28	33	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	17142	17142	17142
5°	17208	16960	17058
10°	17105	16787	16870
15°	16893	16568	16552
20°	16593	16242	16225
25°	16295	15841	15841
30°	15910	15474	15340
35°	15554	15031	14808
40°	15104	14587	14309
45°	14661	14150	13798
50°	14179	13692	13205
55°	13678	13163	12673
60°	13120	12526	12064
65°	12520	11897	11351
70°	11759	11131	10603
75°	10699	10256	10000
80°	9493	9205	8731
85°	7762	7373	6614



TEST NUMBER: P331347

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	99.8	2.1
10°-20°	280.9	5.9
20°-30°	412.9	8.7
30°-40°	479.6	10.1
40°-50°	479.1	10.0
50°-60°	417.8	8.8
60°-70°	308.9	6.5
70°-80°	175.0	3.7
80°-90°	49.7	1.0
90°-100°	118.6	2.5
100°-110°	402.4	8.4
110°-120°	427.5	9.0
120°-130°	351.9	7.4
130°-140°	282.6	5.9
140°-150°	213.5	4.5
150°-160°	150.1	3.1
160°-170°	88.3	1.9
170°-180°	28.8	0.6
0°-30°	793.6	16.6
0°-40°	1273.2	26.7
0°-60°	2170.1	45.5
0°-90°	2703.8	56.7
90°-120°	948.4	19.9
90°-150°	1796.4	37.7
90°-180°	2064.0	43.3
0°-180°	4767.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1062	1062	1062	1062	1062	
5°	1062	1057	1046	1054	1052	101
15°	1011	1004	991	995	990	284
25°	915	906	889	891	889	421
35°	789	779	763	756	751	492
45°	642	635	620	609	604	495
55°	486	479	468	456	450	434
65°	328	321	311	302	297	324
75°	172	169	164	159	160	183
85°	42	41	40	37	36	48
90°	1	8	19	18	19	3
95°	20	49	224	84	65	21
105°	70	105	423	755	643	74
115°	123	155	354	730	846	122
125°	171	202	340	591	686	152
135°	201	240	336	497	569	155
145°	229	263	334	415	454	144
155°	261	281	324	367	382	120
165°	284	293	311	330	335	80
175°	296	296	299	303	302	28
180°	296	296	296	296	296	



TEST NUMBER: P331347

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1066.6	1065.7	1064.8	1063.9	1063.0	1061.5	1059.5	1057.5	1055.5	1053.5	1055.3
5°	1061.7	1060.8	1059.9	1059.0	1058.1	1056.4	1053.9	1051.4	1048.9	1046.4	1048.2
7.5°	1052.3	1050.9	1049.5	1048.1	1046.7	1044.7	1042.2	1039.6	1037.1	1034.5	1036.3
10°	1043.3	1041.7	1040.1	1038.5	1037.0	1034.8	1032.1	1029.4	1026.6	1023.9	1025.7
12.5°	1031.1	1029.7	1028.2	1026.8	1025.4	1023.4	1020.6	1017.9	1015.2	1012.5	1013.8
15°	1010.6	1009.3	1007.9	1006.6	1005.2	1003.0	1000.1	997.1	994.2	991.2	992.2
17.5°	984.5	983.1	981.8	980.4	979.1	976.9	973.9	970.9	967.9	964.9	966.0
20°	965.7	964.4	963.0	961.6	960.3	958.0	954.8	951.7	948.5	945.3	946.0
22.5°	946.9	945.0	943.1	941.2	939.3	936.9	933.9	930.9	927.9	924.9	925.0
25°	914.7	912.9	911.1	909.2	907.4	904.6	900.7	896.9	893.0	889.2	889.6
27.5°	877.9	876.3	874.7	873.0	871.4	869.1	866.0	863.0	859.9	856.9	856.2
30°	853.4	851.6	849.8	848.0	846.2	843.6	840.2	836.8	833.4	830.0	829.3
32.5°	827.3	825.8	824.4	822.9	821.5	819.0	815.4	811.8	808.2	804.6	803.4
35°	789.1	786.9	784.6	782.3	780.0	777.1	773.5	769.8	766.2	762.6	761.2
37.5°	746.0	744.0	742.0	740.0	738.1	735.2	731.6	728.0	724.4	720.7	719.0
40°	716.6	714.8	713.0	711.2	709.4	706.7	703.0	699.4	695.8	692.1	690.1
42.5°	688.1	686.2	684.4	682.6	680.8	678.1	674.4	670.8	667.2	663.6	661.3
45°	642.1	640.5	638.9	637.4	635.8	633.3	629.9	626.5	623.1	619.7	617.2
47.5°	596.4	594.9	593.4	591.9	590.4	587.9	584.3	580.8	577.3	573.7	571.1
50°	564.5	563.4	562.3	561.1	560.0	557.8	554.7	551.5	548.3	545.1	542.0
52.5°	533.5	532.0	530.5	529.0	527.5	525.3	522.3	519.3	516.3	513.3	510.7
55°	485.9	484.6	483.2	481.8	480.5	478.4	475.7	473.0	470.3	467.6	464.8
57.5°	438.1	437.1	436.0	434.9	433.8	431.8	428.8	425.8	422.8	419.8	417.1
60°	406.3	405.4	404.5	403.6	402.7	400.6	397.5	394.3	391.1	387.9	385.4
62.5°	375.3	373.8	372.4	370.9	369.5	367.5	365.1	362.6	360.2	357.7	355.4
65°	327.7	326.3	325.0	323.6	322.2	320.4	318.2	315.9	313.6	311.4	309.3
67.5°	279.3	278.2	277.1	276.0	274.9	273.4	271.3	269.3	267.3	265.2	263.6
70°	249.1	248.2	247.3	246.4	245.5	244.0	241.9	239.9	237.9	235.8	234.2
72.5°	218.1	217.1	216.2	215.3	214.4	213.3	212.0	210.7	209.4	208.0	206.5
75°	171.5	171.0	170.6	170.1	169.7	168.9	167.8	166.6	165.5	164.4	163.0
77.5°	129.9	129.1	128.3	127.5	126.8	126.2	125.7	125.2	124.8	124.3	123.7
80°	102.1	101.9	101.6	101.4	101.2	100.8	100.4	99.9	99.5	99.0	98.3
82.5°	76.0	75.9	75.9	75.8	75.8	75.6	75.3	75.1	74.8	74.5	73.7
85°	41.9	41.6	41.4	41.2	40.9	40.7	40.5	40.3	40.0	39.8	39.1
87.5°	14.8	14.8	14.9	14.8	14.6	14.6	14.8	15.2	15.6	15.3	14.7
90°	0.6	2.3	4.6	5.7	6.8	8.6	11.4	15.4	18.8	19.4	18.8
92.5°	7.0	10.0	14.1	16.7	20.5	25.9	38.8	56.9	73.1	74.1	62.6
95°	20.0	22.2	27.9	33.1	42.2	55.9	82.1	131.7	197.9	223.6	195.6
97.5°	32.5	35.6	41.6	49.4	59.9	75.4	108.4	177.5	287.4	381.6	400.3
100°	43.9	45.6	50.8	59.9	71.3	87.3	117.5	187.1	310.2	450.5	532.6
102.5°	54.4	55.7	60.8	69.9	81.8	97.7	125.7	187.5	301.6	452.8	581.9
105°	69.6	71.9	75.8	84.4	96.9	112.9	139.7	190.5	284.6	422.6	574.3
107.5°	86.0	87.8	91.7	99.6	112.0	128.1	154.1	198.3	276.1	390.2	524.2
110°	96.9	99.2	102.7	110.1	122.0	138.6	163.7	204.7	274.3	374.7	492.7



TEST NUMBER: P331347

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	107.0	109.3	113.1	120.1	131.6	148.6	172.8	211.6	274.8	364.6	470.8
115°	122.6	125.5	128.9	135.7	147.1	162.5	187.1	221.8	277.2	353.6	443.7
117.5°	138.8	141.1	144.5	150.6	161.5	177.5	200.2	232.8	281.3	348.2	426.6
120°	148.8	151.1	154.5	159.7	171.1	187.1	209.3	240.1	284.0	345.0	417.5
122.5°	158.4	160.3	163.7	169.3	180.7	197.1	218.0	246.5	287.2	343.2	409.7
125°	171.1	172.8	176.2	183.1	194.5	210.4	231.0	256.6	292.0	339.9	398.6
127.5°	181.1	183.4	188.2	195.7	206.7	223.1	243.1	266.1	296.9	338.0	388.4
130°	187.1	189.3	195.0	203.0	214.4	230.4	250.4	272.0	300.5	337.0	381.5
132.5°	192.5	195.3	201.4	209.9	221.7	237.7	256.7	278.0	304.2	336.6	376.0
135°	200.7	203.0	209.9	218.4	231.5	247.5	265.8	285.7	308.5	335.9	368.4
137.5°	208.5	211.2	218.1	227.2	240.2	255.0	273.1	291.6	312.4	335.8	363.0
140°	214.4	216.7	223.6	232.7	245.2	260.1	277.2	294.8	314.2	335.3	359.9
142.5°	220.4	222.2	228.6	237.7	249.8	263.7	280.4	297.6	315.6	335.3	356.7
145°	229.3	231.5	237.2	245.8	257.2	269.7	285.1	301.1	317.1	334.2	352.4
147.5°	238.8	240.5	246.0	253.9	263.4	274.5	289.0	303.1	317.5	332.1	348.1
150°	245.2	246.9	251.5	258.9	267.5	277.7	290.8	304.0	317.1	330.8	344.5
152.5°	251.6	252.4	257.0	263.5	271.6	280.9	292.7	304.4	316.2	328.5	341.3
155°	260.6	261.2	264.6	270.9	277.2	285.7	295.4	305.1	314.8	324.5	335.3
157.5°	268.1	268.7	271.5	276.9	282.0	289.1	297.3	305.1	312.2	320.4	329.7
160°	273.2	273.7	276.0	280.6	285.1	291.4	298.3	305.1	310.8	317.7	325.6
162.5°	278.2	277.8	280.1	283.8	287.9	292.8	298.7	304.6	309.4	315.4	322.0
165°	284.0	283.4	284.6	288.0	290.8	294.3	299.4	303.4	306.8	310.8	315.9
167.5°	288.8	288.1	289.1	291.3	293.4	295.5	299.3	302.6	304.2	306.8	310.0
170°	292.0	290.8	291.4	293.1	294.3	296.0	298.8	301.7	302.8	304.5	306.8
172.5°	293.8	293.1	292.8	294.5	295.2	296.4	298.4	300.3	301.0	301.8	303.6
175°	296.0	295.4	294.8	296.0	296.0	296.5	297.7	298.8	298.3	298.8	299.4
177.5°	297.0	296.1	295.6	296.5	296.5	296.5	297.0	297.9	297.0	296.5	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5



TEST NUMBER: P331347

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1057.1	1059.0	1060.8	1061.5	1061.1	1060.8	1060.4	1060.1
5°	1050.0	1051.8	1053.6	1054.3	1053.9	1053.4	1053.0	1052.5
7.5°	1038.2	1040.0	1041.8	1042.4	1041.9	1041.5	1041.0	1040.5
10°	1027.5	1029.4	1031.2	1031.7	1031.1	1030.4	1029.7	1029.0
12.5°	1015.0	1016.3	1017.6	1017.9	1017.4	1017.0	1016.5	1016.0
15°	993.1	994.0	994.9	994.8	993.6	992.5	991.4	990.2
17.5°	967.0	968.0	969.1	969.1	968.0	966.9	965.8	964.7
20°	946.7	947.4	948.0	947.9	947.0	946.1	945.2	944.3
22.5°	925.2	925.3	925.4	925.2	924.7	924.1	923.6	923.1
25°	890.1	890.5	891.0	891.0	890.5	890.1	889.6	889.2
27.5°	855.5	854.9	854.2	853.3	852.2	851.1	850.0	848.9
30°	828.6	827.9	827.2	826.4	825.5	824.6	823.7	822.8
32.5°	802.2	801.0	799.7	798.7	797.8	796.9	795.9	795.0
35°	759.9	758.5	757.1	755.9	754.8	753.6	752.5	751.3
37.5°	717.4	715.7	714.0	712.6	711.5	710.4	709.4	708.3
40°	688.1	686.0	684.0	682.5	681.6	680.7	679.8	678.9
42.5°	659.1	656.9	654.7	652.9	651.6	650.4	649.1	647.8
45°	614.7	612.2	609.7	608.0	607.1	606.2	605.3	604.3
47.5°	568.5	565.8	563.2	561.2	559.9	558.6	557.3	556.0
50°	538.8	535.6	532.4	530.3	529.1	528.0	526.9	525.7
52.5°	508.0	505.4	502.8	500.7	499.2	497.7	496.2	494.7
55°	462.1	459.4	456.7	454.7	453.6	452.5	451.3	450.2
57.5°	414.4	411.7	409.1	407.3	406.4	405.6	404.7	403.8
60°	382.9	380.4	377.9	376.4	375.7	375.0	374.3	373.6
62.5°	353.1	350.8	348.5	346.9	346.0	345.1	344.3	343.4
65°	307.3	305.2	303.2	301.6	300.5	299.3	298.2	297.1
67.5°	262.0	260.5	258.9	257.6	256.7	255.8	254.9	254.0
70°	232.6	231.1	229.5	228.2	227.3	226.4	225.5	224.6
72.5°	204.9	203.3	201.7	200.5	199.8	199.1	198.4	197.6
75°	161.6	160.3	158.9	158.5	158.9	159.4	159.8	160.3
77.5°	123.0	122.3	121.6	121.0	120.3	119.7	119.1	118.4
80°	97.7	97.0	96.3	95.7	95.3	94.8	94.4	93.9
82.5°	72.8	71.9	71.1	70.6	70.5	70.4	70.3	70.2
85°	38.5	37.8	37.1	36.6	36.4	36.2	36.0	35.7
87.5°	14.0	13.2	12.9	12.7	12.5	12.3	12.1	11.9
90°	18.2	17.1	18.2	18.8	18.8	18.8	18.8	18.8
92.5°	49.7	42.7	37.9	34.3	33.9	32.1	32.5	31.6
95°	149.4	114.6	90.7	78.1	70.7	66.2	64.4	65.0
97.5°	348.7	285.3	223.6	182.4	155.1	141.1	132.8	128.0
100°	520.7	450.0	371.8	302.8	255.5	231.0	214.4	204.2
102.5°	633.4	617.4	560.3	487.1	435.7	393.8	373.2	359.3
105°	692.9	757.3	764.8	745.9	710.6	675.2	650.7	642.7
107.5°	650.0	747.1	806.4	834.0	838.4	836.5	831.6	821.0
110°	613.1	715.1	788.1	834.9	859.4	870.3	875.4	874.8





TEST NUMBER: P331347

CATALOG NUMBER: SA2XXDIP-C675D530U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	579.3	677.3	755.3	808.9	843.0	861.1	870.8	873.9
115°	537.8	625.6	700.3	759.1	799.5	825.8	840.6	845.7
117.5°	506.5	583.6	651.4	706.5	747.8	775.5	791.1	795.4
120°	491.0	561.7	622.2	674.1	714.0	740.8	757.3	763.0
122.5°	478.7	543.5	600.7	647.6	683.4	709.8	724.5	729.3
125°	460.8	519.5	569.7	612.5	645.6	667.2	681.5	686.1
127.5°	443.1	496.3	543.6	583.1	611.9	632.2	644.5	648.2
130°	431.7	480.8	525.8	563.4	591.4	610.8	622.2	626.7
132.5°	420.8	466.2	507.6	542.9	570.4	589.8	600.3	604.4
135°	405.5	443.1	480.8	512.7	537.2	556.0	566.3	568.6
137.5°	393.3	424.8	454.6	482.5	504.8	521.0	530.0	533.4
140°	385.5	412.9	439.1	464.2	482.5	497.3	505.8	509.3
142.5°	379.1	402.4	425.0	446.0	463.3	476.8	484.4	485.1
145°	370.1	388.9	406.6	423.2	436.8	446.5	452.2	453.9
147.5°	363.2	378.0	391.8	403.9	415.2	422.9	426.8	427.8
150°	358.1	370.7	382.7	392.9	401.5	408.3	411.7	412.3
152.5°	353.1	364.8	374.9	383.8	390.5	396.5	399.0	399.1
155°	346.2	355.3	363.8	370.1	376.4	380.4	382.7	381.5
157.5°	338.1	345.7	352.9	357.8	362.2	365.6	366.6	366.6
160°	333.0	339.3	345.6	349.6	353.6	356.4	357.0	357.0
162.5°	328.0	333.4	338.8	341.8	345.8	347.8	348.3	347.9
165°	320.5	324.5	328.5	330.8	333.0	335.3	335.3	334.8
167.5°	313.3	316.4	319.1	321.2	322.2	323.5	323.4	322.7
170°	309.7	311.4	313.7	314.8	315.4	317.1	316.5	315.4
172.5°	305.6	306.8	308.6	309.3	309.9	310.7	310.1	309.4
175°	301.1	301.7	302.3	302.8	302.8	303.4	302.8	301.7
177.5°	297.9	297.9	298.4	298.4	298.4	298.4	297.9	297.0
180°	296.5	296.5	296.5	296.5	296.5	296.5	296.5	296.5

(END OF REPORT)