

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331363

Luminaire Tested: **SA2XXDIP-C675D925U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331363
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D925U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6403.0 lumens
Efficiency: N/A
Efficacy: 123.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331363
CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331363

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42
1	96	92	88	84	88	84	81	78	69	67	65	56	54	53	43	42	41	36
2	87	80	74	69	80	73	68	64	61	57	54	49	46	44	38	36	35	30
3	80	70	63	57	73	65	58	53	53	49	45	43	40	37	34	32	30	25
4	73	62	54	48	66	57	50	45	47	42	38	39	35	32	30	28	26	22
5	67	55	47	41	61	51	44	39	42	37	33	35	31	28	27	24	22	19
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17
7	57	45	37	31	52	41	34	29	35	29	25	28	24	21	22	20	17	15
8	53	41	33	28	48	37	31	26	32	26	22	26	22	19	21	18	16	13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17142	17142	17142
5°	17208	16960	17058
10°	17105	16787	16870
15°	16893	16568	16552
20°	16593	16242	16225
25°	16295	15841	15841
30°	15910	15474	15340
35°	15554	15031	14808
40°	15104	14587	14309
45°	14661	14150	13798
50°	14179	13692	13205
55°	13678	13163	12673
60°	13120	12526	12064
65°	12520	11897	11351
70°	11759	11131	10603
75°	10699	10256	10000
80°	9493	9205	8731
85°	7762	7373	6614



TEST NUMBER: P331363

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.8	1.6
10°-20°	280.9	4.4
20°-30°	412.9	6.4
30°-40°	479.6	7.5
40°-50°	479.1	7.5
50°-60°	417.8	6.5
60°-70°	308.9	4.8
70°-80°	175.0	2.7
80°-90°	50.2	0.8
90°-100°	42.1	0.7
100°-110°	154.4	2.4
110°-120°	412.7	6.4
120°-130°	681.3	10.6
130°-140°	724.5	11.3
140°-150°	673.4	10.5
150°-160°	541.4	8.5
160°-170°	348.9	5.4
170°-180°	120.1	1.9
0°-30°	793.6	12.4
0°-40°	1273.2	19.9
0°-60°	2170.1	33.9
0°-90°	2704.2	42.2
90°-120°	609.2	9.5
90°-150°	2688.4	42.0
90°-180°	3699.0	57.8
0°-180°	6403.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1062	1062	1062	1062	1062	
5°	1062	1057	1046	1054	1052	101
15°	1011	1004	991	995	990	284
25°	915	906	889	891	889	421
35°	789	779	763	756	751	492
45°	642	635	620	609	604	495
55°	486	479	468	456	450	434
65°	328	321	311	302	297	324
75°	172	169	164	159	160	183
85°	42	41	40	37	36	48
90°	1	11	18	23	25	5
95°	59	31	36	40	39	73
105°	278	290	56	65	69	297
115°	525	541	564	160	75	517
125°	742	755	772	778	781	662
135°	919	933	942	950	949	709
145°	1066	1066	1080	1086	1082	666
155°	1174	1166	1176	1181	1174	541
165°	1237	1232	1234	1240	1234	349
175°	1265	1259	1260	1266	1258	120
180°	1262	1262	1262	1262	1262	



TEST NUMBER: P331363

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1066.6	1065.7	1064.8	1063.9	1063.0	1061.5	1059.5	1057.5	1055.5	1053.5	1055.3
5°	1061.7	1060.8	1059.9	1059.0	1058.1	1056.4	1053.9	1051.4	1048.9	1046.4	1048.2
7.5°	1052.3	1050.9	1049.5	1048.1	1046.7	1044.7	1042.2	1039.6	1037.1	1034.5	1036.3
10°	1043.3	1041.7	1040.1	1038.5	1037.0	1034.8	1032.1	1029.4	1026.6	1023.9	1025.7
12.5°	1031.1	1029.7	1028.2	1026.8	1025.4	1023.4	1020.6	1017.9	1015.2	1012.5	1013.8
15°	1010.6	1009.3	1007.9	1006.6	1005.2	1003.0	1000.1	997.1	994.2	991.2	992.2
17.5°	984.5	983.1	981.8	980.4	979.1	976.9	973.9	970.9	967.9	964.9	966.0
20°	965.7	964.4	963.0	961.6	960.3	958.0	954.8	951.7	948.5	945.3	946.0
22.5°	946.9	945.0	943.1	941.2	939.3	936.9	933.9	930.9	927.9	924.9	925.0
25°	914.7	912.9	911.1	909.2	907.4	904.6	900.7	896.9	893.0	889.2	889.6
27.5°	877.9	876.3	874.7	873.0	871.4	869.1	866.0	863.0	859.9	856.9	856.2
30°	853.4	851.6	849.8	848.0	846.2	843.6	840.2	836.8	833.4	830.0	829.3
32.5°	827.3	825.8	824.4	822.9	821.5	819.0	815.4	811.8	808.2	804.6	803.4
35°	789.1	786.9	784.6	782.3	780.0	777.1	773.5	769.8	766.2	762.6	761.2
37.5°	746.0	744.0	742.0	740.0	738.1	735.2	731.6	728.0	724.4	720.7	719.0
40°	716.6	714.8	713.0	711.2	709.4	706.7	703.0	699.4	695.8	692.1	690.1
42.5°	688.1	686.2	684.4	682.6	680.8	678.1	674.4	670.8	667.2	663.6	661.3
45°	642.1	640.5	638.9	637.4	635.8	633.3	629.9	626.5	623.1	619.7	617.2
47.5°	596.4	594.9	593.4	591.9	590.4	587.9	584.3	580.8	577.3	573.7	571.1
50°	564.5	563.4	562.3	561.1	560.0	557.8	554.7	551.5	548.3	545.1	542.0
52.5°	533.5	532.0	530.5	529.0	527.5	525.3	522.3	519.3	516.3	513.3	510.7
55°	485.9	484.6	483.2	481.8	480.5	478.4	475.7	473.0	470.3	467.6	464.8
57.5°	438.1	437.1	436.0	434.9	433.8	431.8	428.8	425.8	422.8	419.8	417.1
60°	406.3	405.4	404.5	403.6	402.7	400.6	397.5	394.3	391.1	387.9	385.4
62.5°	375.3	373.8	372.4	370.9	369.5	367.5	365.1	362.6	360.2	357.7	355.4
65°	327.7	326.3	325.0	323.6	322.2	320.4	318.2	315.9	313.6	311.4	309.3
67.5°	279.3	278.2	277.1	276.0	274.9	273.4	271.3	269.3	267.3	265.2	263.6
70°	249.1	248.2	247.3	246.4	245.5	244.0	241.9	239.9	237.9	235.8	234.2
72.5°	218.1	217.1	216.2	215.3	214.4	213.3	212.0	210.7	209.4	208.0	206.5
75°	171.5	171.0	170.6	170.1	169.7	168.9	167.8	166.6	165.5	164.4	163.0
77.5°	129.9	129.1	128.3	127.5	126.8	126.2	125.7	125.2	124.8	124.3	123.7
80°	102.1	101.9	101.6	101.4	101.2	100.8	100.4	99.9	99.5	99.0	98.3
82.5°	76.0	75.9	75.9	75.8	75.8	75.6	75.3	75.1	74.8	74.5	73.7
85°	41.9	41.6	41.4	41.2	40.9	40.7	40.5	40.3	40.0	39.8	39.1
87.5°	14.9	15.0	15.0	15.1	15.2	15.2	15.2	15.2	15.1	15.1	14.7
90°	0.9	3.1	5.4	7.6	9.8	11.8	13.4	15.0	16.6	18.3	19.3
92.5°	18.4	18.2	18.0	17.8	17.6	17.9	18.8	19.6	20.4	21.2	21.7
95°	59.4	52.7	46.0	39.3	32.6	29.9	31.4	32.8	34.2	35.6	36.6
97.5°	117.8	98.9	80.1	61.2	42.3	34.5	37.8	41.1	44.4	47.7	48.5
100°	161.7	133.8	106.0	78.2	50.4	38.3	41.7	45.2	48.6	52.1	53.7
102.5°	209.9	204.0	198.1	192.2	186.3	169.0	140.1	111.2	82.4	53.5	55.6
105°	277.6	283.7	289.8	295.9	302.0	277.3	221.9	166.5	111.1	55.7	57.9
107.5°	354.9	359.8	364.7	369.6	374.6	343.8	277.3	210.9	144.4	78.0	75.7
110°	404.6	408.9	413.1	417.4	421.6	394.4	335.8	277.1	218.5	159.8	139.5



TEST NUMBER: P331363

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	451.3	455.1	458.9	462.7	466.4	461.1	446.6	432.1	417.6	403.1	329.1
115°	525.1	528.6	532.0	535.5	538.9	543.2	548.3	553.4	558.4	563.5	469.5
117.5°	591.1	594.9	598.8	602.7	606.5	610.2	613.7	617.2	620.7	624.1	601.4
120°	639.3	642.3	645.4	648.4	651.5	654.8	658.5	662.1	665.8	669.4	671.9
122.5°	680.2	683.4	686.6	689.8	693.0	696.6	700.6	704.6	708.6	712.6	714.0
125°	742.5	745.1	747.8	750.4	753.1	756.3	760.2	764.0	767.9	771.7	773.2
127.5°	798.9	801.9	804.8	807.7	810.6	813.5	816.4	819.3	822.2	825.1	827.1
130°	834.8	838.0	841.2	844.5	847.7	850.5	852.7	854.9	857.2	859.4	861.6
132.5°	871.3	874.0	876.8	879.6	882.3	884.8	887.1	889.3	891.5	893.7	895.7
135°	918.8	922.0	925.3	928.5	931.8	934.3	936.1	938.0	939.8	941.6	943.6
137.5°	966.8	969.1	971.4	973.6	975.9	978.1	980.1	982.2	984.3	986.4	988.3
140°	998.2	999.9	1001.5	1003.1	1004.7	1006.7	1008.9	1011.1	1013.4	1015.6	1017.4
142.5°	1024.5	1026.0	1027.5	1028.9	1030.4	1032.4	1034.9	1037.5	1040.1	1042.6	1044.3
145°	1065.8	1065.6	1065.4	1065.2	1065.0	1066.6	1070.1	1073.5	1077.0	1080.4	1081.8
147.5°	1101.8	1101.0	1100.3	1099.5	1098.7	1100.0	1103.4	1106.9	1110.3	1113.7	1114.7
150°	1125.2	1123.8	1122.3	1120.9	1119.5	1120.4	1123.7	1126.9	1130.2	1133.4	1134.6
152.5°	1144.9	1143.3	1141.7	1140.2	1138.6	1139.3	1142.4	1145.5	1148.6	1151.7	1152.9
155°	1173.6	1171.8	1169.9	1168.1	1166.3	1166.6	1169.0	1171.5	1173.9	1176.3	1177.5
157.5°	1196.0	1194.5	1193.0	1191.4	1189.9	1190.0	1191.7	1193.4	1195.1	1196.8	1198.2
160°	1209.2	1208.0	1206.8	1205.5	1204.3	1204.3	1205.5	1206.8	1208.0	1209.2	1210.4
162.5°	1220.9	1219.7	1218.5	1217.2	1216.0	1215.9	1217.0	1218.0	1219.1	1220.2	1221.5
165°	1236.6	1235.4	1234.2	1232.9	1231.7	1231.4	1232.0	1232.6	1233.3	1233.9	1235.3
167.5°	1248.3	1247.1	1245.9	1244.6	1243.4	1243.1	1243.7	1244.2	1244.8	1245.4	1246.8
170°	1254.9	1253.6	1252.4	1251.2	1250.0	1249.6	1250.0	1250.4	1250.8	1251.2	1252.6
172.5°	1259.2	1258.0	1256.8	1255.6	1254.4	1254.0	1254.4	1254.8	1255.2	1255.6	1257.0
175°	1264.9	1263.5	1262.1	1260.6	1259.2	1258.7	1259.1	1259.5	1259.9	1260.3	1261.8
177.5°	1265.8	1264.7	1263.6	1262.4	1261.3	1260.8	1261.0	1261.1	1261.3	1261.4	1262.6
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2



TEST NUMBER: P331363

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7	1061.7
2.5°	1057.1	1059.0	1060.8	1061.5	1061.1	1060.8	1060.4	1060.1
5°	1050.0	1051.8	1053.6	1054.3	1053.9	1053.4	1053.0	1052.5
7.5°	1038.2	1040.0	1041.8	1042.4	1041.9	1041.5	1041.0	1040.5
10°	1027.5	1029.4	1031.2	1031.7	1031.1	1030.4	1029.7	1029.0
12.5°	1015.0	1016.3	1017.6	1017.9	1017.4	1017.0	1016.5	1016.0
15°	993.1	994.0	994.9	994.8	993.6	992.5	991.4	990.2
17.5°	967.0	968.0	969.1	969.1	968.0	966.9	965.8	964.7
20°	946.7	947.4	948.0	947.9	947.0	946.1	945.2	944.3
22.5°	925.2	925.3	925.4	925.2	924.7	924.1	923.6	923.1
25°	890.1	890.5	891.0	891.0	890.5	890.1	889.6	889.2
27.5°	855.5	854.9	854.2	853.3	852.2	851.1	850.0	848.9
30°	828.6	827.9	827.2	826.4	825.5	824.6	823.7	822.8
32.5°	802.2	801.0	799.7	798.7	797.8	796.9	795.9	795.0
35°	759.9	758.5	757.1	755.9	754.8	753.6	752.5	751.3
37.5°	717.4	715.7	714.0	712.6	711.5	710.4	709.4	708.3
40°	688.1	686.0	684.0	682.5	681.6	680.7	679.8	678.9
42.5°	659.1	656.9	654.7	652.9	651.6	650.4	649.1	647.8
45°	614.7	612.2	609.7	608.0	607.1	606.2	605.3	604.3
47.5°	568.5	565.8	563.2	561.2	559.9	558.6	557.3	556.0
50°	538.8	535.6	532.4	530.3	529.1	528.0	526.9	525.7
52.5°	508.0	505.4	502.8	500.7	499.2	497.7	496.2	494.7
55°	462.1	459.4	456.7	454.7	453.6	452.5	451.3	450.2
57.5°	414.4	411.7	409.1	407.3	406.4	405.6	404.7	403.8
60°	382.9	380.4	377.9	376.4	375.7	375.0	374.3	373.6
62.5°	353.1	350.8	348.5	346.9	346.0	345.1	344.3	343.4
65°	307.3	305.2	303.2	301.6	300.5	299.3	298.2	297.1
67.5°	262.0	260.5	258.9	257.6	256.7	255.8	254.9	254.0
70°	232.6	231.1	229.5	228.2	227.3	226.4	225.5	224.6
72.5°	204.9	203.3	201.7	200.5	199.8	199.1	198.4	197.6
75°	161.6	160.3	158.9	158.5	158.9	159.4	159.8	160.3
77.5°	123.0	122.3	121.6	121.0	120.3	119.7	119.1	118.4
80°	97.7	97.0	96.3	95.7	95.3	94.8	94.4	93.9
82.5°	72.8	71.9	71.1	70.6	70.5	70.4	70.3	70.2
85°	38.5	37.8	37.1	36.6	36.4	36.2	36.0	35.7
87.5°	14.4	14.1	13.7	13.5	13.4	13.3	13.2	13.1
90°	20.3	21.3	22.3	23.0	23.4	23.8	24.3	24.7
92.5°	22.2	22.8	23.3	23.7	23.9	24.2	24.4	24.7
95°	37.6	38.7	39.7	40.1	39.9	39.7	39.5	39.3
97.5°	49.3	50.1	50.9	51.4	51.7	51.9	52.2	52.4
100°	55.3	56.9	58.6	59.6	60.0	60.4	60.8	61.2
102.5°	57.7	59.9	62.0	63.3	63.9	64.4	65.0	65.6
105°	60.2	62.4	64.6	66.2	67.0	67.8	68.6	69.4
107.5°	73.4	71.2	68.9	68.2	69.0	69.8	70.6	71.4
110°	119.2	98.9	78.6	68.9	69.7	70.5	71.3	72.2



TEST NUMBER: P331363

CATALOG NUMBER: SA2XXDIP-C675D925U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	255.1	181.0	107.0	70.3	70.9	71.6	72.2	72.9
115°	375.6	281.6	187.6	133.3	118.7	104.1	89.5	74.9
117.5°	578.7	556.0	533.2	497.8	449.8	401.8	353.8	305.8
120°	674.3	676.8	679.2	666.7	639.3	611.9	584.5	557.1
122.5°	715.5	716.9	718.4	716.5	711.2	705.8	700.5	695.2
125°	774.6	776.0	777.4	778.4	779.0	779.6	780.3	780.9
127.5°	829.2	831.3	833.4	834.4	834.6	834.7	834.8	834.9
130°	863.9	866.1	868.3	869.4	869.2	868.9	868.7	868.5
132.5°	897.6	899.5	901.4	902.2	902.0	901.8	901.6	901.4
135°	945.7	947.7	949.7	950.5	950.1	949.7	949.3	948.9
137.5°	990.3	992.3	994.3	995.0	994.3	993.6	992.9	992.2
140°	1019.2	1021.1	1022.9	1023.3	1022.3	1021.3	1020.3	1019.2
142.5°	1045.9	1047.6	1049.3	1049.6	1048.6	1047.6	1046.6	1045.5
145°	1083.3	1084.7	1086.1	1086.3	1085.3	1084.3	1083.3	1082.3
147.5°	1115.8	1116.8	1117.9	1118.0	1117.1	1116.3	1115.4	1114.6
150°	1135.8	1137.1	1138.3	1138.4	1137.4	1136.3	1135.3	1134.3
152.5°	1154.1	1155.3	1156.5	1156.5	1155.1	1153.8	1152.5	1151.1
155°	1178.8	1180.0	1181.2	1181.0	1179.4	1177.7	1176.1	1174.5
157.5°	1199.5	1200.9	1202.3	1202.2	1200.6	1199.0	1197.4	1195.9
160°	1211.6	1212.9	1214.1	1214.0	1212.5	1211.1	1209.7	1208.3
162.5°	1222.9	1224.3	1225.7	1225.5	1223.8	1222.0	1220.3	1218.5
165°	1236.7	1238.1	1239.5	1239.5	1238.1	1236.7	1235.3	1233.9
167.5°	1248.2	1249.6	1251.1	1250.8	1249.0	1247.2	1245.4	1243.5
170°	1254.1	1255.5	1256.9	1256.7	1254.9	1253.0	1251.2	1249.4
172.5°	1258.4	1259.9	1261.3	1261.1	1259.2	1257.4	1255.6	1253.8
175°	1263.2	1264.6	1266.0	1265.7	1263.7	1261.7	1259.6	1257.6
177.5°	1263.7	1264.9	1266.0	1265.8	1264.4	1262.9	1261.4	1260.0
180°	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2	1262.2

(END OF REPORT)