

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331411

Luminaire Tested: **SA2XXDIP-C865D1080U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331411
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8118.1 lumens
Efficiency: N/A
Efficacy: 124.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 65.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331411
CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47				47
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	40				40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	43	41	39	35				35
3	82	73	66	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30				30
4	75	64	57	51	69	60	53	48	51	46	42	42	39	36	34	32	30	26				26
5	69	58	50	44	63	53	47	41	46	40	36	38	34	31	31	28	26	23				23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	27	28	26	23	20				20
7	59	47	39	34	54	44	37	32	37	32	28	32	28	24	26	23	21	18				18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16				16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15				15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14				14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27876	27876	27876	27876
5°	31253	28058	24864	28058
10°	35813	27829	21518	27829
15°	39619	27318	19010	27318
20°	39015	26770	17330	26770
25°	35179	26042	16265	26042
30°	29071	24878	15489	24878
35°	21187	23660	14937	23660
40°	16923	22223	14629	22223
45°	14787	20559	14212	20559
50°	13901	18952	13933	18952
55°	12814	17315	13560	17315
60°	11741	15578	12984	15578
65°	10697	14017	12420	14017
70°	9711	12500	11589	12500
75°	8609	10805	10268	10805
80°	7401	8945	8266	8945
85°	6632	6632	4909	6632



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.4	2.0
10°-20°	478.0	5.9
20°-30°	693.8	8.5
30°-40°	732.1	9.0
40°-50°	648.2	8.0
50°-60°	517.3	6.4
60°-70°	351.6	4.3
70°-80°	180.3	2.2
80°-90°	47.1	0.6
90°-100°	49.0	0.6
100°-110°	179.7	2.2
110°-120°	480.4	5.9
120°-130°	793.0	9.8
130°-140°	843.3	10.4
140°-150°	783.8	9.7
150°-160°	630.2	7.8
160°-170°	406.1	5.0
170°-180°	139.8	1.7
0°-30°	1336.2	16.5
0°-40°	2068.3	25.5
0°-60°	3233.8	39.8
0°-90°	3812.7	47.0
90°-120°	709.1	8.7
90°-150°	3129.2	38.5
90°-180°	4305.0	53.0
0°-180°	8118.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1726	1726	1726	1726	1726	
5°	1928	1731	1534	1731	1928	193
15°	2370	1634	1137	1634	2370	654
25°	1975	1462	913	1462	1975	893
35°	1075	1200	758	1200	1075	699
45°	648	900	622	900	648	509
55°	455	615	482	615	455	408
65°	280	367	325	367	280	278
75°	138	173	165	173	138	147
85°	36	36	26	36	36	40
90°	29	1	29	1	29	14
95°	46	69	46	69	46	43
105°	81	323	81	323	81	84
115°	87	611	87	611	87	218
125°	909	864	909	864	909	786
135°	1104	1069	1104	1069	1104	851
145°	1260	1241	1260	1241	1260	788
155°	1367	1366	1367	1366	1367	631
165°	1436	1439	1436	1439	1436	405
175°	1464	1472	1464	1472	1464	139
180°	1469	1469	1469	1469	1469	



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1806.2	1806.7	1807.8	1799.3	1798.2	1798.2	1790.8	1784.4	1777.0	1766.9	1768.0
5°	1928.3	1935.6	1938.2	1930.3	1918.3	1917.0	1905.7	1887.1	1869.9	1855.9	1846.0
7.5°	2074.0	2076.9	2070.4	2059.9	2051.0	2035.1	2014.1	1993.6	1964.8	1938.4	1918.7
10°	2184.4	2188.4	2177.1	2161.8	2149.2	2130.6	2100.1	2068.9	2031.1	1994.6	1965.4
12.5°	2268.3	2278.1	2263.6	2261.6	2240.0	2214.5	2178.2	2162.4	2109.2	2058.3	2027.0
15°	2370.2	2369.5	2370.9	2358.2	2342.3	2338.3	2299.9	2258.1	2183.1	2153.2	2101.5
17.5°	2340.7	2350.8	2355.5	2355.3	2354.9	2352.4	2340.1	2313.7	2276.1	2227.7	2167.9
20°	2270.7	2283.9	2285.9	2301.2	2309.8	2321.1	2325.7	2318.4	2295.2	2254.7	2203.0
22.5°	2162.4	2166.1	2172.3	2196.1	2214.8	2243.1	2257.8	2282.3	2273.4	2253.7	2210.4
25°	1974.7	1968.1	1991.3	2003.2	2046.4	2091.5	2124.0	2159.8	2191.7	2210.9	2198.3
27.5°	1749.4	1739.4	1774.2	1805.9	1840.9	1889.8	1940.5	2000.3	2050.1	2112.3	2133.7
30°	1559.3	1565.3	1598.5	1632.3	1685.4	1754.4	1811.5	1877.2	1948.2	2017.8	2066.3
32.5°	1354.4	1377.4	1398.4	1450.2	1497.0	1573.9	1657.5	1739.7	1828.2	1907.4	1982.4
35°	1074.9	1101.5	1130.7	1168.5	1234.2	1310.5	1392.1	1502.9	1623.7	1731.9	1820.8
37.5°	904.8	900.6	917.3	944.6	997.8	1059.4	1153.4	1262.9	1405.0	1532.1	1657.5
40°	802.9	800.2	812.2	837.4	877.9	923.0	1005.3	1101.5	1233.5	1388.8	1538.1
42.5°	732.8	734.4	741.0	758.8	786.6	823.7	885.3	967.2	1088.1	1234.3	1394.8
45°	647.6	652.3	659.6	668.2	684.1	714.6	749.1	807.5	903.1	1025.2	1183.1
47.5°	586.3	586.4	593.9	601.4	610.9	628.1	656.2	692.9	760.3	859.7	995.5
50°	553.4	548.8	554.1	560.0	570.0	581.9	600.5	635.0	680.1	760.4	873.9
52.5°	513.1	513.2	518.0	520.2	529.1	541.1	558.0	581.9	622.8	685.6	778.9
55°	455.2	458.5	461.2	465.1	473.1	481.7	495.0	510.9	542.8	589.9	658.9
57.5°	400.8	401.8	404.5	412.1	417.1	425.1	437.7	452.1	472.8	507.7	559.6
60°	363.6	363.6	368.9	372.2	378.9	386.8	396.8	410.7	429.3	457.8	499.7
62.5°	329.7	329.1	331.2	336.7	341.7	349.2	359.1	370.9	388.4	413.8	448.2
65°	280.0	278.7	282.7	284.0	289.3	296.6	304.6	317.2	331.1	349.7	380.2
67.5°	232.2	233.8	236.0	238.5	241.4	249.1	254.4	263.3	275.1	290.5	311.2
70°	205.7	205.7	205.7	207.7	211.7	215.7	221.0	228.3	239.5	252.8	271.4
72.5°	176.0	178.1	180.2	179.0	184.1	186.5	192.8	196.9	207.7	216.2	232.6
75°	138.0	138.0	138.0	141.3	143.3	145.3	149.3	153.3	158.6	169.2	177.8
77.5°	103.0	102.7	103.4	104.2	106.3	108.7	109.9	113.5	118.4	123.3	130.6
80°	79.6	81.0	81.6	82.9	82.9	84.3	84.9	89.6	92.9	96.2	100.9
82.5°	61.6	61.8	62.0	62.2	62.8	63.6	65.3	66.8	67.9	70.7	74.3
85°	35.8	35.2	35.2	36.5	35.8	35.8	37.2	38.5	38.5	39.1	41.1
87.5°	19.5	19.4	19.9	19.3	19.2	19.5	19.3	18.5	18.8	19.1	19.3
90°	28.7	28.2	27.8	27.3	26.8	26.0	24.8	23.6	22.4	21.3	19.4
92.5°	28.7	28.4	28.1	27.9	27.6	27.1	26.5	25.9	25.3	24.7	23.7
95°	45.7	45.9	46.2	46.4	46.7	46.2	45.0	43.8	42.6	41.5	39.8
97.5°	61.0	60.7	60.5	60.2	59.9	59.3	58.3	57.4	56.4	55.5	51.7
100°	71.2	70.8	70.3	69.8	69.3	68.2	66.3	64.4	62.5	60.6	56.6
102.5°	76.3	75.7	75.0	74.3	73.7	72.1	69.7	67.2	64.8	62.3	59.9
105°	80.8	79.8	78.9	78.0	77.0	75.2	72.6	70.0	67.4	64.8	62.3
107.5°	83.1	82.2	81.2	80.3	79.4	80.2	82.8	85.5	88.1	90.8	168.1
110°	84.0	83.0	82.1	81.1	80.2	91.5	115.2	138.8	162.4	186.0	254.3



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.8	84.1	83.3	82.6	81.8	124.5	210.7	296.9	383.1	469.2	486.1
115°	87.2	104.2	121.2	138.2	155.2	218.4	327.8	437.1	546.5	655.9	650.0
117.5°	355.9	411.8	467.7	523.6	579.5	620.7	647.1	673.6	700.0	726.5	722.4
120°	648.5	680.3	712.2	744.1	776.0	790.6	787.7	784.9	782.0	779.2	775.0
122.5°	809.2	815.4	821.6	827.8	833.9	836.2	834.5	832.8	831.1	829.4	824.8
125°	908.9	908.2	907.5	906.8	906.1	904.9	903.2	901.6	899.9	898.3	893.8
127.5°	971.8	971.7	971.6	971.4	971.3	970.0	967.6	965.2	962.8	960.4	957.0
130°	1011.0	1011.2	1011.4	1011.7	1011.9	1010.7	1008.1	1005.5	1002.9	1000.3	997.7
132.5°	1049.2	1049.5	1049.7	1049.9	1050.2	1049.2	1047.0	1044.7	1042.5	1040.3	1037.7
135°	1104.5	1105.0	1105.4	1105.9	1106.4	1105.4	1103.1	1100.7	1098.4	1096.0	1093.9
137.5°	1154.9	1155.7	1156.5	1157.3	1158.1	1157.3	1155.0	1152.7	1150.4	1148.1	1145.7
140°	1186.4	1187.5	1188.7	1189.9	1191.1	1190.6	1188.5	1186.4	1184.2	1182.1	1179.5
142.5°	1217.0	1218.2	1219.3	1220.5	1221.7	1221.3	1219.4	1217.4	1215.5	1213.6	1210.6
145°	1259.7	1260.9	1262.1	1263.3	1264.4	1264.2	1262.5	1260.9	1259.2	1257.6	1253.6
147.5°	1297.3	1298.3	1299.3	1300.3	1301.3	1301.2	1300.0	1298.7	1297.5	1296.3	1292.3
150°	1320.3	1321.5	1322.7	1323.8	1325.0	1324.9	1323.5	1322.1	1320.7	1319.2	1315.5
152.5°	1339.9	1341.4	1343.0	1344.5	1346.1	1346.2	1344.8	1343.3	1341.9	1340.5	1336.9
155°	1367.1	1369.0	1370.9	1372.7	1374.6	1374.9	1373.5	1372.0	1370.6	1369.2	1366.4
157.5°	1391.9	1393.8	1395.6	1397.5	1399.3	1399.4	1397.8	1396.2	1394.6	1393.0	1391.0
160°	1406.4	1408.1	1409.7	1411.4	1413.0	1413.1	1411.7	1410.3	1408.9	1407.5	1406.1
162.5°	1418.3	1420.3	1422.4	1424.4	1426.4	1426.7	1425.0	1423.4	1421.8	1420.2	1419.0
165°	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8	1441.1	1439.5	1437.8	1436.2	1435.5
167.5°	1447.4	1449.6	1451.7	1453.8	1455.9	1456.2	1454.5	1452.9	1451.2	1449.6	1448.9
170°	1454.2	1456.4	1458.5	1460.6	1462.7	1463.0	1461.3	1459.7	1458.0	1456.4	1455.9
172.5°	1459.3	1461.5	1463.6	1465.7	1467.9	1468.1	1466.4	1464.8	1463.1	1461.5	1461.0
175°	1463.8	1466.2	1468.5	1470.9	1473.3	1473.6	1472.0	1470.3	1468.7	1467.0	1466.5
177.5°	1466.6	1468.3	1470.0	1471.7	1473.4	1473.6	1472.2	1470.9	1469.6	1468.3	1468.1
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1771.7	1767.4	1764.8	1755.2	1746.7	1738.2	1735.6	1736.6	1725.0	1713.8	1709.0
5°	1840.7	1827.4	1814.8	1796.9	1775.7	1752.4	1740.5	1731.2	1708.0	1682.8	1668.2
7.5°	1902.5	1883.5	1859.3	1825.6	1794.6	1758.1	1734.9	1714.3	1680.4	1644.8	1623.0
10°	1940.2	1914.3	1883.1	1842.0	1804.2	1759.7	1728.5	1697.4	1657.5	1615.1	1588.5
12.5°	1972.6	1937.7	1907.0	1854.2	1809.5	1753.9	1716.9	1672.9	1631.0	1580.6	1554.6
15°	2049.7	1985.3	1926.9	1867.2	1812.1	1734.5	1693.4	1634.3	1579.2	1516.9	1487.0
17.5°	2109.3	2037.0	1945.0	1869.1	1804.8	1718.9	1658.5	1587.7	1522.6	1451.3	1410.7
20°	2143.3	2060.3	1961.4	1871.2	1794.2	1696.0	1630.3	1558.0	1481.7	1401.4	1357.6
22.5°	2163.4	2076.2	1978.4	1863.2	1773.0	1677.4	1594.8	1515.5	1438.2	1351.5	1305.6
25°	2169.8	2090.2	1986.7	1856.6	1746.5	1638.3	1538.8	1461.8	1368.2	1287.3	1220.3
27.5°	2138.2	2081.1	1981.6	1844.1	1715.8	1589.3	1478.4	1391.2	1292.5	1204.6	1137.2
30°	2099.5	2066.3	1969.4	1831.4	1691.4	1555.4	1433.3	1334.4	1236.2	1147.3	1078.3
32.5°	2039.5	2032.3	1947.1	1813.3	1665.4	1512.4	1386.0	1286.1	1177.3	1089.9	1024.1
35°	1921.6	1953.5	1899.7	1773.0	1616.4	1451.2	1314.5	1200.4	1087.6	1003.9	942.2
37.5°	1763.7	1842.8	1828.7	1713.9	1550.3	1384.6	1233.7	1114.4	1006.9	922.5	861.9
40°	1654.9	1755.7	1770.3	1668.8	1503.6	1333.1	1173.2	1054.4	949.5	872.6	811.5
42.5°	1538.1	1655.9	1696.0	1614.7	1452.6	1278.9	1119.0	996.0	892.2	817.4	763.2
45°	1342.4	1498.3	1570.6	1524.2	1367.6	1189.7	1025.2	900.4	806.2	735.9	694.1
47.5°	1159.3	1329.7	1427.0	1410.6	1272.9	1096.8	934.1	814.4	722.7	666.6	629.2
50°	1029.8	1205.0	1322.4	1327.8	1205.0	1030.5	867.3	754.5	670.2	617.8	587.2
52.5°	917.3	1084.5	1212.6	1240.7	1129.1	961.5	807.3	695.0	620.8	572.6	545.3
55°	770.4	911.7	1053.7	1105.5	1015.9	856.6	714.0	615.1	545.4	512.3	488.4
57.5°	640.5	758.3	889.4	946.6	891.4	755.1	621.3	535.5	478.9	449.9	431.6
60°	572.0	664.9	781.7	850.0	802.2	680.8	564.0	482.4	436.0	410.1	392.8
62.5°	508.3	590.6	689.3	751.8	725.8	611.3	506.7	434.6	394.5	370.3	357.8
65°	419.4	484.4	560.7	618.4	601.2	514.2	428.7	366.9	335.1	315.8	305.9
67.5°	345.3	392.3	445.2	495.8	481.9	420.3	351.5	303.5	279.8	263.2	257.2
70°	298.6	334.4	381.5	422.0	410.7	360.3	305.9	264.8	244.2	230.3	224.3
72.5°	254.0	283.5	319.4	352.5	344.9	303.0	257.6	226.5	210.7	197.9	193.0
75°	191.8	214.3	236.2	258.1	256.1	223.6	197.1	173.2	160.6	150.6	148.6
77.5°	141.6	154.2	169.1	182.1	178.5	159.9	139.1	125.4	116.1	109.5	108.4
80°	108.2	115.5	126.1	135.4	130.7	122.8	106.2	96.2	89.6	82.9	80.3
82.5°	78.4	85.7	92.1	97.1	93.6	86.1	75.9	69.1	65.2	60.6	59.6
85°	41.1	45.1	47.8	49.1	47.8	43.1	38.5	35.8	32.5	30.5	29.9
87.5°	19.4	19.0	18.7	19.3	17.2	16.6	14.0	11.9	11.9	11.9	11.3
90°	17.5	15.6	13.7	11.5	8.9	6.3	3.7	1.1	3.7	6.3	8.9
92.5°	22.8	21.8	20.9	20.5	20.8	21.0	21.2	21.5	21.2	21.0	20.8
95°	38.2	36.5	34.8	37.9	45.7	53.5	61.3	69.1	61.3	53.5	45.7
97.5°	47.8	44.0	40.2	49.3	71.2	93.2	115.2	137.1	115.2	93.2	71.2
100°	52.6	48.5	44.5	58.7	91.1	123.4	155.8	188.2	155.8	123.4	91.1
102.5°	129.5	163.1	196.7	216.9	223.7	230.6	237.4	244.3	237.4	230.6	223.7
105°	193.8	258.3	322.8	351.5	344.4	337.3	330.3	323.2	330.3	337.3	344.4
107.5°	245.5	322.8	400.2	436.0	430.2	424.5	418.8	413.1	418.8	424.5	430.2
110°	322.6	390.8	459.1	490.8	485.8	480.9	475.9	470.9	475.9	480.9	485.8



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	503.0	519.8	536.7	542.9	538.5	534.1	529.8	525.4	529.8	534.1	538.5
115°	644.1	638.2	632.3	627.3	623.3	619.3	615.3	611.3	615.3	619.3	623.3
117.5°	718.4	714.3	710.2	706.0	701.5	697.0	692.5	688.0	692.5	697.0	701.5
120°	770.7	766.5	762.2	758.3	754.8	751.2	747.7	744.1	747.7	751.2	754.8
122.5°	820.1	815.5	810.9	806.7	803.0	799.2	795.5	791.8	795.5	799.2	803.0
125°	889.3	884.8	880.3	876.5	873.5	870.4	867.3	864.3	867.3	870.4	873.5
127.5°	953.6	950.3	946.9	943.6	940.2	936.8	933.4	930.0	933.4	936.8	940.2
130°	995.1	992.5	989.9	986.7	983.0	979.2	975.4	971.6	975.4	979.2	983.0
132.5°	1035.1	1032.5	1029.9	1027.0	1023.8	1020.6	1017.4	1014.1	1017.4	1020.6	1023.8
135°	1091.7	1089.6	1087.5	1084.5	1080.8	1077.0	1073.2	1069.4	1073.2	1077.0	1080.8
137.5°	1143.3	1140.9	1138.4	1135.9	1133.3	1130.6	1128.0	1125.3	1128.0	1130.6	1133.3
140°	1176.9	1174.3	1171.7	1169.5	1167.6	1165.7	1163.8	1161.9	1163.8	1165.7	1167.6
142.5°	1207.6	1204.6	1201.7	1199.3	1197.6	1195.9	1194.2	1192.5	1194.2	1195.9	1197.6
145°	1249.5	1245.5	1241.5	1239.6	1239.9	1240.1	1240.3	1240.6	1240.3	1240.1	1239.9
147.5°	1288.3	1284.4	1280.4	1278.9	1279.8	1280.7	1281.6	1282.5	1281.6	1280.7	1279.8
150°	1311.7	1307.9	1304.1	1303.1	1304.7	1306.4	1308.0	1309.7	1308.0	1306.4	1304.7
152.5°	1333.3	1329.7	1326.1	1325.3	1327.1	1328.9	1330.8	1332.6	1330.8	1328.9	1327.1
155°	1363.5	1360.7	1357.9	1357.5	1359.6	1361.8	1363.9	1366.0	1363.9	1361.8	1359.6
157.5°	1389.0	1387.1	1385.1	1385.0	1386.8	1388.6	1390.4	1392.2	1390.4	1388.6	1386.8
160°	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1406.1	1404.6	1403.2
162.5°	1417.8	1416.5	1415.3	1415.4	1416.8	1418.2	1419.7	1421.1	1419.7	1418.2	1416.8
165°	1434.8	1434.0	1433.3	1433.7	1435.1	1436.5	1437.9	1439.4	1437.9	1436.5	1435.1
167.5°	1448.2	1447.6	1446.9	1447.3	1448.7	1450.1	1451.6	1453.0	1451.6	1450.1	1448.7
170°	1455.4	1455.0	1454.5	1455.0	1456.4	1457.8	1459.2	1460.6	1459.2	1457.8	1456.4
172.5°	1460.5	1460.1	1459.6	1460.1	1461.5	1462.9	1464.3	1465.7	1464.3	1462.9	1461.5
175°	1466.1	1465.6	1465.1	1465.7	1467.4	1469.0	1470.7	1472.3	1470.7	1469.0	1467.4
177.5°	1467.9	1467.7	1467.5	1468.1	1469.4	1470.7	1472.1	1473.4	1472.1	1470.7	1469.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1703.7	1700.5	1689.4	1683.6	1674.0	1665.0	1659.1	1661.8	1663.9	1662.8	1661.3
5°	1654.9	1642.3	1623.0	1606.4	1594.5	1572.6	1563.3	1558.7	1554.7	1550.0	1545.4
7.5°	1596.8	1576.9	1549.2	1525.6	1503.3	1476.1	1460.6	1451.3	1441.8	1431.3	1422.0
10°	1555.4	1527.5	1498.3	1465.1	1438.6	1414.0	1392.1	1377.5	1364.3	1351.6	1342.4
12.5°	1511.8	1479.7	1443.6	1398.2	1369.0	1333.9	1330.5	1304.8	1284.1	1276.3	1265.4
15°	1442.6	1397.4	1351.6	1297.9	1274.7	1242.8	1222.9	1203.0	1185.1	1172.5	1169.2
17.5°	1363.9	1305.5	1259.9	1221.3	1183.2	1150.6	1132.3	1116.4	1101.6	1084.8	1082.5
20°	1303.9	1253.4	1203.7	1169.8	1130.7	1097.5	1074.9	1059.0	1046.4	1036.5	1027.8
22.5°	1247.1	1191.9	1146.3	1109.3	1070.7	1043.9	1026.1	1010.7	1000.2	989.2	981.1
25°	1155.9	1112.8	1063.0	1021.2	989.3	972.1	957.5	944.2	937.6	930.3	921.0
27.5°	1076.1	1028.2	981.7	949.3	921.3	906.0	895.7	886.6	880.4	876.1	870.8
30°	1019.9	971.4	934.9	903.1	879.9	864.6	858.0	852.7	845.4	842.7	840.1
32.5°	965.7	922.1	890.9	863.3	841.1	831.2	825.1	820.3	814.6	811.9	806.6
35°	889.2	852.7	822.1	806.9	789.0	780.3	775.7	769.1	763.7	761.1	760.4
37.5°	817.1	785.4	765.3	745.7	738.1	732.8	726.5	721.9	720.3	719.9	719.3
40°	770.4	744.5	726.6	710.7	707.3	699.4	694.1	690.1	690.1	690.8	690.1
42.5°	727.9	704.7	688.9	675.1	671.2	666.5	661.2	660.9	662.0	664.2	662.0
45°	663.5	647.0	635.7	629.0	621.7	617.1	616.4	618.4	619.1	619.8	621.7
47.5°	604.4	593.3	583.1	575.8	572.6	571.8	571.0	574.5	577.7	578.9	581.9
50°	569.3	556.7	548.1	543.4	540.8	539.5	540.8	544.8	547.4	550.7	552.7
52.5°	530.0	521.1	515.2	511.6	510.5	511.3	511.6	516.1	520.4	521.5	522.5
55°	475.8	469.1	467.8	461.8	464.5	463.8	467.1	469.8	473.8	477.8	478.4
57.5°	421.6	416.3	412.7	413.3	414.1	417.0	419.8	424.4	428.7	432.9	433.3
60°	385.5	382.9	380.9	380.9	382.2	386.2	389.5	394.1	396.8	399.5	401.4
62.5°	352.6	350.0	348.0	349.0	352.5	354.9	358.7	361.2	363.9	366.5	367.5
65°	300.6	299.3	301.3	302.6	303.2	306.6	311.2	313.2	315.8	317.2	321.8
67.5°	252.7	252.9	252.7	254.5	258.4	259.2	263.6	268.2	268.7	271.3	274.3
70°	220.3	221.6	223.0	224.3	227.6	228.9	232.2	234.2	236.9	238.9	240.9
72.5°	190.6	190.8	192.2	191.9	194.7	197.6	200.4	202.4	205.0	207.6	209.5
75°	146.6	146.6	148.0	148.6	152.0	155.3	154.6	155.9	158.6	161.2	162.6
77.5°	107.1	105.6	107.1	107.8	108.8	111.6	112.1	114.0	117.0	116.1	117.6
80°	81.6	79.6	81.6	82.3	82.3	85.6	85.6	86.9	88.9	86.9	88.9
82.5°	58.3	57.3	58.8	58.9	60.0	60.1	61.2	61.4	63.4	62.5	63.4
85°	29.2	28.5	29.2	28.5	29.2	29.9	29.9	29.2	29.2	30.5	28.5
87.5°	11.3	11.2	11.1	11.5	11.3	11.2	10.9	11.1	11.3	10.5	10.7
90°	11.5	13.7	15.6	17.5	19.4	21.3	22.4	23.6	24.8	26.0	26.8
92.5°	20.5	20.9	21.8	22.8	23.7	24.7	25.3	25.9	26.5	27.1	27.6
95°	37.9	34.8	36.5	38.2	39.8	41.5	42.6	43.8	45.0	46.2	46.7
97.5°	49.3	40.2	44.0	47.8	51.7	55.5	56.4	57.4	58.3	59.3	59.9
100°	58.7	44.5	48.5	52.6	56.6	60.6	62.5	64.4	66.3	68.2	69.3
102.5°	216.9	196.7	163.1	129.5	95.9	62.3	64.8	67.2	69.7	72.1	73.7
105°	351.5	322.8	258.3	193.8	129.3	64.8	67.4	70.0	72.6	75.2	77.0
107.5°	436.0	400.2	322.8	245.5	168.1	90.8	88.1	85.5	82.8	80.2	79.4
110°	490.8	459.1	390.8	322.6	254.3	186.0	162.4	138.8	115.2	91.5	80.2



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	542.9	536.7	519.8	503.0	486.1	469.2	383.1	296.9	210.7	124.5	81.8
115°	627.3	632.3	638.2	644.1	650.0	655.9	546.5	437.1	327.8	218.4	155.2
117.5°	706.0	710.2	714.3	718.4	722.4	726.5	700.0	673.6	647.1	620.7	579.5
120°	758.3	762.2	766.5	770.7	775.0	779.2	782.0	784.9	787.7	790.6	776.0
122.5°	806.7	810.9	815.5	820.1	824.8	829.4	831.1	832.8	834.5	836.2	833.9
125°	876.5	880.3	884.8	889.3	893.8	898.3	899.9	901.6	903.2	904.9	906.1
127.5°	943.6	946.9	950.3	953.6	957.0	960.4	962.8	965.2	967.6	970.0	971.3
130°	986.7	989.9	992.5	995.1	997.7	1000.3	1002.9	1005.5	1008.1	1010.7	1011.9
132.5°	1027.0	1029.9	1032.5	1035.1	1037.7	1040.3	1042.5	1044.7	1047.0	1049.2	1050.2
135°	1084.5	1087.5	1089.6	1091.7	1093.9	1096.0	1098.4	1100.7	1103.1	1105.4	1106.4
137.5°	1135.9	1138.4	1140.9	1143.3	1145.7	1148.1	1150.4	1152.7	1155.0	1157.3	1158.1
140°	1169.5	1171.7	1174.3	1176.9	1179.5	1182.1	1184.2	1186.4	1188.5	1190.6	1191.1
142.5°	1199.3	1201.7	1204.6	1207.6	1210.6	1213.6	1215.5	1217.4	1219.4	1221.3	1221.7
145°	1239.6	1241.5	1245.5	1249.5	1253.6	1257.6	1259.2	1260.9	1262.5	1264.2	1264.4
147.5°	1278.9	1280.4	1284.4	1288.3	1292.3	1296.3	1297.5	1298.7	1300.0	1301.2	1301.3
150°	1303.1	1304.1	1307.9	1311.7	1315.5	1319.2	1320.7	1322.1	1323.5	1324.9	1325.0
152.5°	1325.3	1326.1	1329.7	1333.3	1336.9	1340.5	1341.9	1343.3	1344.8	1346.2	1346.1
155°	1357.5	1357.9	1360.7	1363.5	1366.4	1369.2	1370.6	1372.0	1373.5	1374.9	1374.6
157.5°	1385.0	1385.1	1387.1	1389.0	1391.0	1393.0	1394.6	1396.2	1397.8	1399.4	1399.3
160°	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1408.9	1410.3	1411.7	1413.1	1413.0
162.5°	1415.4	1415.3	1416.5	1417.8	1419.0	1420.2	1421.8	1423.4	1425.0	1426.7	1426.4
165°	1433.7	1433.3	1434.0	1434.8	1435.5	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8
167.5°	1447.3	1446.9	1447.6	1448.2	1448.9	1449.6	1451.2	1452.9	1454.5	1456.2	1455.9
170°	1455.0	1454.5	1455.0	1455.4	1455.9	1456.4	1458.0	1459.7	1461.3	1463.0	1462.7
172.5°	1460.1	1459.6	1460.1	1460.5	1461.0	1461.5	1463.1	1464.8	1466.4	1468.1	1467.9
175°	1465.7	1465.1	1465.6	1466.1	1466.5	1467.0	1468.7	1470.3	1472.0	1473.6	1473.3
177.5°	1468.1	1467.5	1467.7	1467.9	1468.1	1468.3	1469.6	1470.9	1472.2	1473.6	1473.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1655.9	1654.9	1654.9	1650.1	1654.9	1654.9	1655.9	1661.3	1662.8	1663.9	1661.8
5°	1536.1	1534.1	1530.8	1534.1	1530.8	1534.1	1536.1	1545.4	1550.0	1554.7	1558.7
7.5°	1417.6	1409.6	1408.4	1400.6	1408.4	1409.6	1417.6	1422.0	1431.3	1441.8	1451.3
10°	1331.1	1325.8	1325.1	1312.5	1325.1	1325.8	1331.1	1342.4	1351.6	1364.3	1377.5
12.5°	1265.3	1252.5	1255.0	1247.7	1255.0	1252.5	1265.3	1265.4	1276.3	1284.1	1304.8
15°	1151.3	1151.3	1148.6	1137.3	1148.6	1151.3	1151.3	1169.2	1172.5	1185.1	1203.0
17.5°	1069.4	1068.0	1061.7	1064.9	1061.7	1068.0	1069.4	1082.5	1084.8	1101.6	1116.4
20°	1020.5	1016.6	1008.6	1008.6	1008.6	1016.6	1020.5	1027.8	1036.5	1046.4	1059.0
22.5°	974.4	974.1	965.6	968.2	965.6	974.1	974.4	981.1	989.2	1000.2	1010.7
25°	920.3	915.0	911.1	913.0	911.1	915.0	920.3	921.0	930.3	937.6	944.2
27.5°	869.1	866.2	865.9	860.5	865.9	866.2	869.1	870.8	876.1	880.4	886.6
30°	839.4	832.8	834.1	830.8	834.1	832.8	839.4	840.1	842.7	845.4	852.7
32.5°	805.4	803.0	801.7	798.9	801.7	803.0	805.4	806.6	811.9	814.6	820.3
35°	759.1	759.8	756.4	757.8	756.4	759.8	759.1	760.4	761.1	763.7	769.1
37.5°	718.6	720.7	719.2	719.6	719.2	720.7	718.6	719.3	719.9	720.3	721.9
40°	692.1	692.1	692.1	694.1	692.1	692.1	692.1	690.1	690.8	690.1	690.1
42.5°	666.6	665.5	664.5	664.3	664.5	665.5	666.6	662.0	664.2	662.0	660.9
45°	623.1	625.1	625.7	622.4	625.7	625.1	623.1	621.7	619.8	619.1	618.4
47.5°	583.7	583.9	583.7	586.6	583.7	583.9	583.7	581.9	578.9	577.7	574.5
50°	556.1	554.7	556.1	554.7	556.1	554.7	556.1	552.7	550.7	547.4	544.8
52.5°	526.9	527.1	526.3	526.1	526.3	527.1	526.9	522.5	521.5	520.4	516.1
55°	481.1	482.4	481.7	481.7	481.7	482.4	481.1	478.4	477.8	473.8	469.8
57.5°	433.7	434.9	435.8	432.9	435.8	434.9	433.7	433.3	432.9	428.7	424.4
60°	400.8	404.1	403.4	402.1	403.4	404.1	400.8	401.4	399.5	396.8	394.1
62.5°	370.5	371.7	371.6	371.3	371.6	371.7	370.5	367.5	366.5	363.9	361.2
65°	323.8	325.1	323.1	325.1	323.1	325.1	323.8	321.8	317.2	315.8	313.2
67.5°	273.5	273.9	275.4	276.3	275.4	273.9	273.5	274.3	271.3	268.7	268.2
70°	242.2	241.5	243.5	245.5	243.5	241.5	242.2	240.9	238.9	236.9	234.2
72.5°	209.3	210.7	210.1	211.5	210.1	210.7	209.3	209.5	207.6	205.0	202.4
75°	161.2	163.2	162.6	164.6	162.6	163.2	161.2	162.6	161.2	158.6	155.9
77.5°	116.5	116.8	116.5	117.6	116.5	116.8	116.5	117.6	116.1	117.0	114.0
80°	88.9	87.6	86.3	88.9	86.3	87.6	88.9	88.9	86.9	88.9	86.9
82.5°	61.8	62.6	61.3	61.3	61.3	62.6	61.8	63.4	62.5	63.4	61.4
85°	28.5	27.9	26.5	26.5	26.5	27.9	28.5	28.5	30.5	29.2	29.2
87.5°	10.8	10.3	10.4	10.0	10.4	10.3	10.8	10.7	10.5	11.3	11.1
90°	27.3	27.8	28.2	28.7	28.2	27.8	27.3	26.8	26.0	24.8	23.6
92.5°	27.9	28.1	28.4	28.7	28.4	28.1	27.9	27.6	27.1	26.5	25.9
95°	46.4	46.2	45.9	45.7	45.9	46.2	46.4	46.7	46.2	45.0	43.8
97.5°	60.2	60.5	60.7	61.0	60.7	60.5	60.2	59.9	59.3	58.3	57.4
100°	69.8	70.3	70.8	71.2	70.8	70.3	69.8	69.3	68.2	66.3	64.4
102.5°	74.3	75.0	75.7	76.3	75.7	75.0	74.3	73.7	72.1	69.7	67.2
105°	78.0	78.9	79.8	80.8	79.8	78.9	78.0	77.0	75.2	72.6	70.0
107.5°	80.3	81.2	82.2	83.1	82.2	81.2	80.3	79.4	80.2	82.8	85.5
110°	81.1	82.1	83.0	84.0	83.0	82.1	81.1	80.2	91.5	115.2	138.8



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	82.6	83.3	84.1	84.8	84.1	83.3	82.6	81.8	124.5	210.7	296.9
115°	138.2	121.2	104.2	87.2	104.2	121.2	138.2	155.2	218.4	327.8	437.1
117.5°	523.6	467.7	411.8	355.9	411.8	467.7	523.6	579.5	620.7	647.1	673.6
120°	744.1	712.2	680.3	648.5	680.3	712.2	744.1	776.0	790.6	787.7	784.9
122.5°	827.8	821.6	815.4	809.2	815.4	821.6	827.8	833.9	836.2	834.5	832.8
125°	906.8	907.5	908.2	908.9	908.2	907.5	906.8	906.1	904.9	903.2	901.6
127.5°	971.4	971.6	971.7	971.8	971.7	971.6	971.4	971.3	970.0	967.6	965.2
130°	1011.7	1011.4	1011.2	1011.0	1011.2	1011.4	1011.7	1011.9	1010.7	1008.1	1005.5
132.5°	1049.9	1049.7	1049.5	1049.2	1049.5	1049.7	1049.9	1050.2	1049.2	1047.0	1044.7
135°	1105.9	1105.4	1105.0	1104.5	1105.0	1105.4	1105.9	1106.4	1105.4	1103.1	1100.7
137.5°	1157.3	1156.5	1155.7	1154.9	1155.7	1156.5	1157.3	1158.1	1157.3	1155.0	1152.7
140°	1189.9	1188.7	1187.5	1186.4	1187.5	1188.7	1189.9	1191.1	1190.6	1188.5	1186.4
142.5°	1220.5	1219.3	1218.2	1217.0	1218.2	1219.3	1220.5	1221.7	1221.3	1219.4	1217.4
145°	1263.3	1262.1	1260.9	1259.7	1260.9	1262.1	1263.3	1264.4	1264.2	1262.5	1260.9
147.5°	1300.3	1299.3	1298.3	1297.3	1298.3	1299.3	1300.3	1301.3	1301.2	1300.0	1298.7
150°	1323.8	1322.7	1321.5	1320.3	1321.5	1322.7	1323.8	1325.0	1324.9	1323.5	1322.1
152.5°	1344.5	1343.0	1341.4	1339.9	1341.4	1343.0	1344.5	1346.1	1346.2	1344.8	1343.3
155°	1372.7	1370.9	1369.0	1367.1	1369.0	1370.9	1372.7	1374.6	1374.9	1373.5	1372.0
157.5°	1397.5	1395.6	1393.8	1391.9	1393.8	1395.6	1397.5	1399.3	1399.4	1397.8	1396.2
160°	1411.4	1409.7	1408.1	1406.4	1408.1	1409.7	1411.4	1413.0	1413.1	1411.7	1410.3
162.5°	1424.4	1422.4	1420.3	1418.3	1420.3	1422.4	1424.4	1426.4	1426.7	1425.0	1423.4
165°	1441.1	1439.5	1437.8	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8	1441.1	1439.5
167.5°	1453.8	1451.7	1449.6	1447.4	1449.6	1451.7	1453.8	1455.9	1456.2	1454.5	1452.9
170°	1460.6	1458.5	1456.4	1454.2	1456.4	1458.5	1460.6	1462.7	1463.0	1461.3	1459.7
172.5°	1465.7	1463.6	1461.5	1459.3	1461.5	1463.6	1465.7	1467.9	1468.1	1466.4	1464.8
175°	1470.9	1468.5	1466.2	1463.8	1466.2	1468.5	1470.9	1473.3	1473.6	1472.0	1470.3
177.5°	1471.7	1470.0	1468.3	1466.6	1468.3	1470.0	1471.7	1473.4	1473.6	1472.2	1470.9
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1659.1	1665.0	1674.0	1683.6	1689.4	1700.5	1703.7	1709.0	1713.8	1725.0	1736.6
5°	1563.3	1572.6	1594.5	1606.4	1623.0	1642.3	1654.9	1668.2	1682.8	1708.0	1731.2
7.5°	1460.6	1476.1	1503.3	1525.6	1549.2	1576.9	1596.8	1623.0	1644.8	1680.4	1714.3
10°	1392.1	1414.0	1438.6	1465.1	1498.3	1527.5	1555.4	1588.5	1615.1	1657.5	1697.4
12.5°	1330.5	1333.9	1369.0	1398.2	1443.6	1479.7	1511.8	1554.6	1580.6	1631.0	1672.9
15°	1222.9	1242.8	1274.7	1297.9	1351.6	1397.4	1442.6	1487.0	1516.9	1579.2	1634.3
17.5°	1132.3	1150.6	1183.2	1221.3	1259.9	1305.5	1363.9	1410.7	1451.3	1522.6	1587.7
20°	1074.9	1097.5	1130.7	1169.8	1203.7	1253.4	1303.9	1357.6	1401.4	1481.7	1558.0
22.5°	1026.1	1043.9	1070.7	1109.3	1146.3	1191.9	1247.1	1305.6	1351.5	1438.2	1515.5
25°	957.5	972.1	989.3	1021.2	1063.0	1112.8	1155.9	1220.3	1287.3	1368.2	1461.8
27.5°	895.7	906.0	921.3	949.3	981.7	1028.2	1076.1	1137.2	1204.6	1292.5	1391.2
30°	858.0	864.6	879.9	903.1	934.9	971.4	1019.9	1078.3	1147.3	1236.2	1334.4
32.5°	825.1	831.2	841.1	863.3	890.9	922.1	965.7	1024.1	1089.9	1177.3	1286.1
35°	775.7	780.3	789.0	806.9	822.1	852.7	889.2	942.2	1003.9	1087.6	1200.4
37.5°	726.5	732.8	738.1	745.7	765.3	785.4	817.1	861.9	922.5	1006.9	1114.4
40°	694.1	699.4	707.3	710.7	726.6	744.5	770.4	811.5	872.6	949.5	1054.4
42.5°	661.2	666.5	671.2	675.1	688.9	704.7	727.9	763.2	817.4	892.2	996.0
45°	616.4	617.1	621.7	629.0	635.7	647.0	663.5	694.1	735.9	806.2	900.4
47.5°	571.0	571.8	572.6	575.8	583.1	593.3	604.4	629.2	666.6	722.7	814.4
50°	540.8	539.5	540.8	543.4	548.1	556.7	569.3	587.2	617.8	670.2	754.5
52.5°	511.6	511.3	510.5	511.6	515.2	521.1	530.0	545.3	572.6	620.8	695.0
55°	467.1	463.8	464.5	461.8	467.8	469.1	475.8	488.4	512.3	545.4	615.1
57.5°	419.8	417.0	414.1	413.3	412.7	416.3	421.6	431.6	449.9	478.9	535.5
60°	389.5	386.2	382.2	380.9	380.9	382.9	385.5	392.8	410.1	436.0	482.4
62.5°	358.7	354.9	352.5	349.0	348.0	350.0	352.6	357.8	370.3	394.5	434.6
65°	311.2	306.6	303.2	302.6	301.3	299.3	300.6	305.9	315.8	335.1	366.9
67.5°	263.6	259.2	258.4	254.5	252.7	252.9	252.7	257.2	263.2	279.8	303.5
70°	232.2	228.9	227.6	224.3	223.0	221.6	220.3	224.3	230.3	244.2	264.8
72.5°	200.4	197.6	194.7	191.9	192.2	190.8	190.6	193.0	197.9	210.7	226.5
75°	154.6	155.3	152.0	148.6	148.0	146.6	146.6	148.6	150.6	160.6	173.2
77.5°	112.1	111.6	108.8	107.8	107.1	105.6	107.1	108.4	109.5	116.1	125.4
80°	85.6	85.6	82.3	82.3	81.6	79.6	81.6	80.3	82.9	89.6	96.2
82.5°	61.2	60.1	60.0	58.9	58.8	57.3	58.3	59.6	60.6	65.2	69.1
85°	29.9	29.9	29.2	28.5	29.2	28.5	29.2	29.9	30.5	32.5	35.8
87.5°	10.9	11.2	11.3	11.5	11.1	11.2	11.3	11.3	11.9	11.9	11.9
90°	22.4	21.3	19.4	17.5	15.6	13.7	11.5	8.9	6.3	3.7	1.1
92.5°	25.3	24.7	23.7	22.8	21.8	20.9	20.5	20.8	21.0	21.2	21.5
95°	42.6	41.5	39.8	38.2	36.5	34.8	37.9	45.7	53.5	61.3	69.1
97.5°	56.4	55.5	51.7	47.8	44.0	40.2	49.3	71.2	93.2	115.2	137.1
100°	62.5	60.6	56.6	52.6	48.5	44.5	58.7	91.1	123.4	155.8	188.2
102.5°	64.8	62.3	95.9	129.5	163.1	196.7	216.9	223.7	230.6	237.4	244.3
105°	67.4	64.8	129.3	193.8	258.3	322.8	351.5	344.4	337.3	330.3	323.2
107.5°	88.1	90.8	168.1	245.5	322.8	400.2	436.0	430.2	424.5	418.8	413.1
110°	162.4	186.0	254.3	322.6	390.8	459.1	490.8	485.8	480.9	475.9	470.9



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	383.1	469.2	486.1	503.0	519.8	536.7	542.9	538.5	534.1	529.8	525.4
115°	546.5	655.9	650.0	644.1	638.2	632.3	627.3	623.3	619.3	615.3	611.3
117.5°	700.0	726.5	722.4	718.4	714.3	710.2	706.0	701.5	697.0	692.5	688.0
120°	782.0	779.2	775.0	770.7	766.5	762.2	758.3	754.8	751.2	747.7	744.1
122.5°	831.1	829.4	824.8	820.1	815.5	810.9	806.7	803.0	799.2	795.5	791.8
125°	899.9	898.3	893.8	889.3	884.8	880.3	876.5	873.5	870.4	867.3	864.3
127.5°	962.8	960.4	957.0	953.6	950.3	946.9	943.6	940.2	936.8	933.4	930.0
130°	1002.9	1000.3	997.7	995.1	992.5	989.9	986.7	983.0	979.2	975.4	971.6
132.5°	1042.5	1040.3	1037.7	1035.1	1032.5	1029.9	1027.0	1023.8	1020.6	1017.4	1014.1
135°	1098.4	1096.0	1093.9	1091.7	1089.6	1087.5	1084.5	1080.8	1077.0	1073.2	1069.4
137.5°	1150.4	1148.1	1145.7	1143.3	1140.9	1138.4	1135.9	1133.3	1130.6	1128.0	1125.3
140°	1184.2	1182.1	1179.5	1176.9	1174.3	1171.7	1169.5	1167.6	1165.7	1163.8	1161.9
142.5°	1215.5	1213.6	1210.6	1207.6	1204.6	1201.7	1199.3	1197.6	1195.9	1194.2	1192.5
145°	1259.2	1257.6	1253.6	1249.5	1245.5	1241.5	1239.6	1239.9	1240.1	1240.3	1240.6
147.5°	1297.5	1296.3	1292.3	1288.3	1284.4	1280.4	1278.9	1279.8	1280.7	1281.6	1282.5
150°	1320.7	1319.2	1315.5	1311.7	1307.9	1304.1	1303.1	1304.7	1306.4	1308.0	1309.7
152.5°	1341.9	1340.5	1336.9	1333.3	1329.7	1326.1	1325.3	1327.1	1328.9	1330.8	1332.6
155°	1370.6	1369.2	1366.4	1363.5	1360.7	1357.9	1357.5	1359.6	1361.8	1363.9	1366.0
157.5°	1394.6	1393.0	1391.0	1389.0	1387.1	1385.1	1385.0	1386.8	1388.6	1390.4	1392.2
160°	1408.9	1407.5	1406.1	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5
162.5°	1421.8	1420.2	1419.0	1417.8	1416.5	1415.3	1415.4	1416.8	1418.2	1419.7	1421.1
165°	1437.8	1436.2	1435.5	1434.8	1434.0	1433.3	1433.7	1435.1	1436.5	1437.9	1439.4
167.5°	1451.2	1449.6	1448.9	1448.2	1447.6	1446.9	1447.3	1448.7	1450.1	1451.6	1453.0
170°	1458.0	1456.4	1455.9	1455.4	1455.0	1454.5	1455.0	1456.4	1457.8	1459.2	1460.6
172.5°	1463.1	1461.5	1461.0	1460.5	1460.1	1459.6	1460.1	1461.5	1462.9	1464.3	1465.7
175°	1468.7	1467.0	1466.5	1466.1	1465.6	1465.1	1465.7	1467.4	1469.0	1470.7	1472.3
177.5°	1469.6	1468.3	1468.1	1467.9	1467.7	1467.5	1468.1	1469.4	1470.7	1472.1	1473.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1735.6	1738.2	1746.7	1755.2	1764.8	1767.4	1771.7	1768.0	1766.9	1777.0	1784.4
5°	1740.5	1752.4	1775.7	1796.9	1814.8	1827.4	1840.7	1846.0	1855.9	1869.9	1887.1
7.5°	1734.9	1758.1	1794.6	1825.6	1859.3	1883.5	1902.5	1918.7	1938.4	1964.8	1993.6
10°	1728.5	1759.7	1804.2	1842.0	1883.1	1914.3	1940.2	1965.4	1994.6	2031.1	2068.9
12.5°	1716.9	1753.9	1809.5	1854.2	1907.0	1937.7	1972.6	2027.0	2058.3	2109.2	2162.4
15°	1693.4	1734.5	1812.1	1867.2	1926.9	1985.3	2049.7	2101.5	2153.2	2183.1	2258.1
17.5°	1658.5	1718.9	1804.8	1869.1	1945.0	2037.0	2109.3	2167.9	2227.7	2276.1	2313.7
20°	1630.3	1696.0	1794.2	1871.2	1961.4	2060.3	2143.3	2203.0	2254.7	2295.2	2318.4
22.5°	1594.8	1677.4	1773.0	1863.2	1978.4	2076.2	2163.4	2210.4	2253.7	2273.4	2282.3
25°	1538.8	1638.3	1746.5	1856.6	1986.7	2090.2	2169.8	2198.3	2210.9	2191.7	2159.8
27.5°	1478.4	1589.3	1715.8	1844.1	1981.6	2081.1	2138.2	2133.7	2112.3	2050.1	2000.3
30°	1433.3	1555.4	1691.4	1831.4	1969.4	2066.3	2099.5	2066.3	2017.8	1948.2	1877.2
32.5°	1386.0	1512.4	1665.4	1813.3	1947.1	2032.3	2039.5	1982.4	1907.4	1828.2	1739.7
35°	1314.5	1451.2	1616.4	1773.0	1899.7	1953.5	1921.6	1820.8	1731.9	1623.7	1502.9
37.5°	1233.7	1384.6	1550.3	1713.9	1828.7	1842.8	1763.7	1657.5	1532.1	1405.0	1262.9
40°	1173.2	1333.1	1503.6	1668.8	1770.3	1755.7	1654.9	1538.1	1388.8	1233.5	1101.5
42.5°	1119.0	1278.9	1452.6	1614.7	1696.0	1655.9	1538.1	1394.8	1234.3	1088.1	967.2
45°	1025.2	1189.7	1367.6	1524.2	1570.6	1498.3	1342.4	1183.1	1025.2	903.1	807.5
47.5°	934.1	1096.8	1272.9	1410.6	1427.0	1329.7	1159.3	995.5	859.7	760.3	692.9
50°	867.3	1030.5	1205.0	1327.8	1322.4	1205.0	1029.8	873.9	760.4	680.1	635.0
52.5°	807.3	961.5	1129.1	1240.7	1212.6	1084.5	917.3	778.9	685.6	622.8	581.9
55°	714.0	856.6	1015.9	1105.5	1053.7	911.7	770.4	658.9	589.9	542.8	510.9
57.5°	621.3	755.1	891.4	946.6	889.4	758.3	640.5	559.6	507.7	472.8	452.1
60°	564.0	680.8	802.2	850.0	781.7	664.9	572.0	499.7	457.8	429.3	410.7
62.5°	506.7	611.3	725.8	751.8	689.3	590.6	508.3	448.2	413.8	388.4	370.9
65°	428.7	514.2	601.2	618.4	560.7	484.4	419.4	380.2	349.7	331.1	317.2
67.5°	351.5	420.3	481.9	495.8	445.2	392.3	345.3	311.2	290.5	275.1	263.3
70°	305.9	360.3	410.7	422.0	381.5	334.4	298.6	271.4	252.8	239.5	228.3
72.5°	257.6	303.0	344.9	352.5	319.4	283.5	254.0	232.6	216.2	207.7	196.9
75°	197.1	223.6	256.1	258.1	236.2	214.3	191.8	177.8	169.2	158.6	153.3
77.5°	139.1	159.9	178.5	182.1	169.1	154.2	141.6	130.6	123.3	118.4	113.5
80°	106.2	122.8	130.7	135.4	126.1	115.5	108.2	100.9	96.2	92.9	89.6
82.5°	75.9	86.1	93.6	97.1	92.1	85.7	78.4	74.3	70.7	67.9	66.8
85°	38.5	43.1	47.8	49.1	47.8	45.1	41.1	41.1	39.1	38.5	38.5
87.5°	14.0	16.6	17.2	19.3	18.7	19.0	19.4	19.3	19.1	18.8	18.5
90°	3.7	6.3	8.9	11.5	13.7	15.6	17.5	19.4	21.3	22.4	23.6
92.5°	21.2	21.0	20.8	20.5	20.9	21.8	22.8	23.7	24.7	25.3	25.9
95°	61.3	53.5	45.7	37.9	34.8	36.5	38.2	39.8	41.5	42.6	43.8
97.5°	115.2	93.2	71.2	49.3	40.2	44.0	47.8	51.7	55.5	56.4	57.4
100°	155.8	123.4	91.1	58.7	44.5	48.5	52.6	56.6	60.6	62.5	64.4
102.5°	237.4	230.6	223.7	216.9	196.7	163.1	129.5	95.9	62.3	64.8	67.2
105°	330.3	337.3	344.4	351.5	322.8	258.3	193.8	129.3	64.8	67.4	70.0
107.5°	418.8	424.5	430.2	436.0	400.2	322.8	245.5	168.1	90.8	88.1	85.5
110°	475.9	480.9	485.8	490.8	459.1	390.8	322.6	254.3	186.0	162.4	138.8



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	529.8	534.1	538.5	542.9	536.7	519.8	503.0	486.1	469.2	383.1	296.9
115°	615.3	619.3	623.3	627.3	632.3	638.2	644.1	650.0	655.9	546.5	437.1
117.5°	692.5	697.0	701.5	706.0	710.2	714.3	718.4	722.4	726.5	700.0	673.6
120°	747.7	751.2	754.8	758.3	762.2	766.5	770.7	775.0	779.2	782.0	784.9
122.5°	795.5	799.2	803.0	806.7	810.9	815.5	820.1	824.8	829.4	831.1	832.8
125°	867.3	870.4	873.5	876.5	880.3	884.8	889.3	893.8	898.3	899.9	901.6
127.5°	933.4	936.8	940.2	943.6	946.9	950.3	953.6	957.0	960.4	962.8	965.2
130°	975.4	979.2	983.0	986.7	989.9	992.5	995.1	997.7	1000.3	1002.9	1005.5
132.5°	1017.4	1020.6	1023.8	1027.0	1029.9	1032.5	1035.1	1037.7	1040.3	1042.5	1044.7
135°	1073.2	1077.0	1080.8	1084.5	1087.5	1089.6	1091.7	1093.9	1096.0	1098.4	1100.7
137.5°	1128.0	1130.6	1133.3	1135.9	1138.4	1140.9	1143.3	1145.7	1148.1	1150.4	1152.7
140°	1163.8	1165.7	1167.6	1169.5	1171.7	1174.3	1176.9	1179.5	1182.1	1184.2	1186.4
142.5°	1194.2	1195.9	1197.6	1199.3	1201.7	1204.6	1207.6	1210.6	1213.6	1215.5	1217.4
145°	1240.3	1240.1	1239.9	1239.6	1241.5	1245.5	1249.5	1253.6	1257.6	1259.2	1260.9
147.5°	1281.6	1280.7	1279.8	1278.9	1280.4	1284.4	1288.3	1292.3	1296.3	1297.5	1298.7
150°	1308.0	1306.4	1304.7	1303.1	1304.1	1307.9	1311.7	1315.5	1319.2	1320.7	1322.1
152.5°	1330.8	1328.9	1327.1	1325.3	1326.1	1329.7	1333.3	1336.9	1340.5	1341.9	1343.3
155°	1363.9	1361.8	1359.6	1357.5	1357.9	1360.7	1363.5	1366.4	1369.2	1370.6	1372.0
157.5°	1390.4	1388.6	1386.8	1385.0	1385.1	1387.1	1389.0	1391.0	1393.0	1394.6	1396.2
160°	1406.1	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1408.9	1410.3
162.5°	1419.7	1418.2	1416.8	1415.4	1415.3	1416.5	1417.8	1419.0	1420.2	1421.8	1423.4
165°	1437.9	1436.5	1435.1	1433.7	1433.3	1434.0	1434.8	1435.5	1436.2	1437.8	1439.5
167.5°	1451.6	1450.1	1448.7	1447.3	1446.9	1447.6	1448.2	1448.9	1449.6	1451.2	1452.9
170°	1459.2	1457.8	1456.4	1455.0	1454.5	1455.0	1455.4	1455.9	1456.4	1458.0	1459.7
172.5°	1464.3	1462.9	1461.5	1460.1	1459.6	1460.1	1460.5	1461.0	1461.5	1463.1	1464.8
175°	1470.7	1469.0	1467.4	1465.7	1465.1	1465.6	1466.1	1466.5	1467.0	1468.7	1470.3
177.5°	1472.1	1470.7	1469.4	1468.1	1467.5	1467.7	1467.9	1468.1	1468.3	1469.6	1470.9
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1790.8	1798.2	1798.2	1799.3	1807.8	1806.7	1806.2
5°	1905.7	1917.0	1918.3	1930.3	1938.2	1935.6	1928.3
7.5°	2014.1	2035.1	2051.0	2059.9	2070.4	2076.9	2074.0
10°	2100.1	2130.6	2149.2	2161.8	2177.1	2188.4	2184.4
12.5°	2178.2	2214.5	2240.0	2261.6	2263.6	2278.1	2268.3
15°	2299.9	2338.3	2342.3	2358.2	2370.9	2369.5	2370.2
17.5°	2340.1	2352.4	2354.9	2355.3	2355.5	2350.8	2340.7
20°	2325.7	2321.1	2309.8	2301.2	2285.9	2283.9	2270.7
22.5°	2257.8	2243.1	2214.8	2196.1	2172.3	2166.1	2162.4
25°	2124.0	2091.5	2046.4	2003.2	1991.3	1968.1	1974.7
27.5°	1940.5	1889.8	1840.9	1805.9	1774.2	1739.4	1749.4
30°	1811.5	1754.4	1685.4	1632.3	1598.5	1565.3	1559.3
32.5°	1657.5	1573.9	1497.0	1450.2	1398.4	1377.4	1354.4
35°	1392.1	1310.5	1234.2	1168.5	1130.7	1101.5	1074.9
37.5°	1153.4	1059.4	997.8	944.6	917.3	900.6	904.8
40°	1005.3	923.0	877.9	837.4	812.2	800.2	802.9
42.5°	885.3	823.7	786.6	758.8	741.0	734.4	732.8
45°	749.1	714.6	684.1	668.2	659.6	652.3	647.6
47.5°	656.2	628.1	610.9	601.4	593.9	586.4	586.3
50°	600.5	581.9	570.0	560.0	554.1	548.8	553.4
52.5°	558.0	541.1	529.1	520.2	518.0	513.2	513.1
55°	495.0	481.7	473.1	465.1	461.2	458.5	455.2
57.5°	437.7	425.1	417.1	412.1	404.5	401.8	400.8
60°	396.8	386.8	378.9	372.2	368.9	363.6	363.6
62.5°	359.1	349.2	341.7	336.7	331.2	329.1	329.7
65°	304.6	296.6	289.3	284.0	282.7	278.7	280.0
67.5°	254.4	249.1	241.4	238.5	236.0	233.8	232.2
70°	221.0	215.7	211.7	207.7	205.7	205.7	205.7
72.5°	192.8	186.5	184.1	179.0	180.2	178.1	176.0
75°	149.3	145.3	143.3	141.3	138.0	138.0	138.0
77.5°	109.9	108.7	106.3	104.2	103.4	102.7	103.0
80°	84.9	84.3	82.9	82.9	81.6	81.0	79.6
82.5°	65.3	63.6	62.8	62.2	62.0	61.8	61.6
85°	37.2	35.8	35.8	36.5	35.2	35.2	35.8
87.5°	19.3	19.5	19.2	19.3	19.9	19.4	19.5
90°	24.8	26.0	26.8	27.3	27.8	28.2	28.7
92.5°	26.5	27.1	27.6	27.9	28.1	28.4	28.7
95°	45.0	46.2	46.7	46.4	46.2	45.9	45.7
97.5°	58.3	59.3	59.9	60.2	60.5	60.7	61.0
100°	66.3	68.2	69.3	69.8	70.3	70.8	71.2
102.5°	69.7	72.1	73.7	74.3	75.0	75.7	76.3
105°	72.6	75.2	77.0	78.0	78.9	79.8	80.8
107.5°	82.8	80.2	79.4	80.3	81.2	82.2	83.1
110°	115.2	91.5	80.2	81.1	82.1	83.0	84.0



TEST NUMBER: P331411

CATALOG NUMBER: SA2XXDIP-C865D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	210.7	124.5	81.8	82.6	83.3	84.1	84.8
115°	327.8	218.4	155.2	138.2	121.2	104.2	87.2
117.5°	647.1	620.7	579.5	523.6	467.7	411.8	355.9
120°	787.7	790.6	776.0	744.1	712.2	680.3	648.5
122.5°	834.5	836.2	833.9	827.8	821.6	815.4	809.2
125°	903.2	904.9	906.1	906.8	907.5	908.2	908.9
127.5°	967.6	970.0	971.3	971.4	971.6	971.7	971.8
130°	1008.1	1010.7	1011.9	1011.7	1011.4	1011.2	1011.0
132.5°	1047.0	1049.2	1050.2	1049.9	1049.7	1049.5	1049.2
135°	1103.1	1105.4	1106.4	1105.9	1105.4	1105.0	1104.5
137.5°	1155.0	1157.3	1158.1	1157.3	1156.5	1155.7	1154.9
140°	1188.5	1190.6	1191.1	1189.9	1188.7	1187.5	1186.4
142.5°	1219.4	1221.3	1221.7	1220.5	1219.3	1218.2	1217.0
145°	1262.5	1264.2	1264.4	1263.3	1262.1	1260.9	1259.7
147.5°	1300.0	1301.2	1301.3	1300.3	1299.3	1298.3	1297.3
150°	1323.5	1324.9	1325.0	1323.8	1322.7	1321.5	1320.3
152.5°	1344.8	1346.2	1346.1	1344.5	1343.0	1341.4	1339.9
155°	1373.5	1374.9	1374.6	1372.7	1370.9	1369.0	1367.1
157.5°	1397.8	1399.4	1399.3	1397.5	1395.6	1393.8	1391.9
160°	1411.7	1413.1	1413.0	1411.4	1409.7	1408.1	1406.4
162.5°	1425.0	1426.7	1426.4	1424.4	1422.4	1420.3	1418.3
165°	1441.1	1442.8	1442.8	1441.1	1439.5	1437.8	1436.2
167.5°	1454.5	1456.2	1455.9	1453.8	1451.7	1449.6	1447.4
170°	1461.3	1463.0	1462.7	1460.6	1458.5	1456.4	1454.2
172.5°	1466.4	1468.1	1467.9	1465.7	1463.6	1461.5	1459.3
175°	1472.0	1473.6	1473.3	1470.9	1468.5	1466.2	1463.8
177.5°	1472.2	1473.6	1473.4	1471.7	1470.0	1468.3	1466.6
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1

(END OF REPORT)