

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331676-927

Luminaire Tested: **SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331676-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2940.0 lumens  
Efficiency: N/A  
Efficacy: 84.0 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 35  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	68				
1	103	99	95	92	97	94	90	88	84	81	79	75	73	71	66	65	64	60				
2	95	88	82	77	89	83	78	74	75	71	67	67	64	61	60	57	55	52				
3	87	78	71	66	82	74	68	63	67	62	58	60	56	53	54	51	49	45				
4	80	70	63	57	76	67	60	55	60	55	51	55	50	47	49	46	43	40				
5	74	63	56	50	70	60	53	48	55	49	45	50	45	41	45	41	38	36				
6	69	57	50	44	65	55	48	43	50	44	40	46	41	37	41	37	34	32				
7	64	52	45	39	61	50	43	38	46	40	36	42	37	33	38	34	31	29				
8	60	48	41	35	57	46	39	34	42	37	32	39	34	30	35	31	28	26				
9	56	44	37	32	53	43	36	31	39	33	30	36	31	28	33	29	26	24				
10	53	41	34	29	50	39	33	29	36	31	27	34	29	26	31	27	24	22				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	18791	18791	18791	18791
5°	20985	18908	16765	18908
10°	23282	18775	14532	18775
15°	24428	18501	11450	18501
20°	21179	18093	9907	18093
25°	13890	17533	8845	17533
30°	9350	16858	8006	16858
35°	7571	16005	7222	16005
40°	6734	15076	6681	15076
45°	6094	13988	5966	13988
50°	5546	12911	5526	12911
55°	5213	11713	5146	11713
60°	4363	10618	4308	10618
65°	3679	9639	4172	9639
70°	3399	8611	3932	8611
75°	3175	7492	3631	7492
80°	2929	6165	3236	6165
85°	2705	4872	2853	4872



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	110.3	3.8
10°-20°	307.4	10.5
20°-30°	396.1	13.5
30°-40°	376.4	12.8
40°-50°	322.5	11.0
50°-60°	245.6	8.4
60°-70°	155.2	5.3
70°-80°	77.5	2.6
80°-90°	21.5	0.7
90°-100°	21.0	0.7
100°-110°	65.3	2.2
110°-120°	111.6	3.8
120°-130°	146.7	5.0
130°-140°	164.7	5.6
140°-150°	161.5	5.5
150°-160°	135.4	4.6
160°-170°	89.8	3.1
170°-180°	31.4	1.1
0°-30°	813.8	27.7
0°-40°	1190.3	40.5
0°-60°	1758.3	59.8
0°-90°	2012.6	68.5
90°-120°	197.9	6.7
90°-150°	670.7	22.8
90°-180°	927.0	31.5
0°-180°	2940.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1164	1164	1164	1164	1164	
5°	1295	1167	1034	1167	1295	128
15°	1461	1107	685	1107	1461	394
25°	780	984	496	984	780	370
35°	384	812	366	812	384	246
45°	267	613	261	613	267	207
55°	185	416	183	416	185	163
65°	96	252	109	252	96	98
75°	51	120	58	120	51	54
85°	15	26	15	26	15	16
90°	10	0	10	0	10	5
95°	17	15	17	15	17	19
105°	62	60	62	60	62	65
115°	112	112	112	112	112	111
125°	163	163	163	163	163	146
135°	213	211	213	211	213	164
145°	259	256	259	256	259	161
155°	295	292	295	292	295	136
165°	318	318	318	318	318	90
175°	330	331	330	331	330	31
180°	332	332	332	332	332	



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1211.0	1212.0	1213.0	1210.7	1210.7	1208.7	1204.5	1201.3	1192.2	1191.0	1191.0
5°	1294.8	1294.0	1295.6	1290.4	1283.1	1281.4	1273.7	1263.7	1253.2	1241.4	1239.0
7.5°	1378.1	1376.9	1373.6	1372.8	1367.1	1354.9	1342.6	1329.4	1311.9	1294.9	1286.3
10°	1420.1	1433.5	1425.4	1411.3	1414.1	1395.1	1385.0	1367.6	1353.0	1327.5	1321.9
12.5°	1461.6	1466.8	1464.3	1456.2	1452.5	1439.4	1425.8	1410.6	1383.8	1360.9	1341.0
15°	1461.4	1469.1	1471.1	1468.7	1470.7	1469.9	1462.6	1450.1	1426.6	1401.5	1379.7
17.5°	1353.5	1358.8	1372.1	1381.1	1392.4	1416.3	1428.1	1432.7	1429.3	1415.0	1399.6
20°	1232.6	1223.6	1260.8	1279.8	1296.0	1336.4	1371.2	1384.6	1406.0	1405.6	1401.5
22.5°	1061.0	1063.2	1098.4	1121.0	1168.2	1208.6	1248.3	1298.5	1340.0	1367.4	1383.5
25°	779.7	795.0	830.2	860.9	913.5	988.7	1057.0	1136.3	1211.1	1270.1	1326.4
27.5°	585.5	586.7	614.6	642.9	674.1	735.8	821.8	916.5	1023.1	1111.1	1212.4
30°	501.5	499.0	510.7	528.1	554.8	602.5	667.2	760.3	866.6	999.2	1117.3
32.5°	441.9	442.0	450.9	463.7	485.9	518.1	562.4	637.9	738.5	868.9	1007.3
35°	384.1	383.7	390.2	399.5	408.8	429.4	459.8	499.4	568.5	690.2	831.8
37.5°	342.8	344.5	347.7	353.5	363.8	375.3	393.5	420.1	469.3	541.3	660.3
40°	319.5	320.3	324.7	329.5	335.6	344.5	359.5	380.9	416.9	474.4	561.3
42.5°	298.1	298.9	302.1	306.6	311.3	320.3	332.6	351.2	380.3	425.2	496.9
45°	266.9	266.9	269.7	271.7	277.0	285.1	295.2	310.5	330.8	363.9	411.6
47.5°	237.6	237.7	239.6	243.0	246.4	252.6	262.6	275.1	289.9	315.5	356.2
50°	220.8	221.2	222.4	225.2	227.3	232.9	240.6	251.5	266.9	286.7	320.7
52.5°	207.2	206.9	208.5	209.7	211.1	215.2	220.9	230.5	244.2	261.5	289.6
55°	185.2	183.5	186.0	188.1	189.3	190.8	194.1	200.2	211.9	226.5	247.5
57.5°	157.7	157.1	158.8	160.7	164.5	168.8	171.5	175.4	181.5	191.9	212.8
60°	135.1	135.1	138.7	139.9	144.3	150.0	155.7	158.9	165.0	171.8	187.2
62.5°	115.0	115.3	117.0	118.3	120.7	127.7	135.6	142.8	148.5	155.0	165.2
65°	96.3	97.0	97.0	97.8	99.5	101.1	104.3	110.0	120.1	129.4	137.0
67.5°	81.7	81.9	82.1	82.9	83.4	85.2	86.4	89.0	91.3	100.1	109.6
70°	72.0	73.2	72.8	73.6	74.0	74.8	76.4	77.6	81.3	83.3	89.0
72.5°	62.9	63.8	63.7	64.2	65.3	65.4	66.7	68.0	70.3	72.0	75.0
75°	50.9	50.5	50.9	51.7	52.1	52.6	52.6	54.2	55.4	57.0	59.0
77.5°	39.3	39.7	39.6	39.7	39.8	40.5	40.4	41.2	42.4	43.2	44.1
80°	31.5	31.9	31.5	31.9	32.3	32.7	32.3	32.7	34.0	34.8	34.8
82.5°	24.4	24.5	24.7	24.8	24.9	25.0	25.6	25.7	26.5	26.4	26.7
85°	14.6	14.2	14.2	14.2	14.6	15.0	14.6	14.6	15.0	15.0	15.0
87.5°	7.1	7.4	7.4	7.4	7.4	7.4	7.4	7.8	7.4	7.8	7.2
90°	9.5	9.4	9.4	9.3	9.3	9.3	9.4	9.6	9.7	9.8	8.4
92.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	8.9	8.6
95°	17.3	17.5	17.6	17.7	17.8	17.9	17.9	17.9	17.9	17.9	17.8
97.5°	30.0	30.1	30.1	30.1	30.1	30.1	30.1	30.1	30.1	30.1	29.9
100°	38.3	38.4	38.5	38.5	38.6	38.7	38.7	38.7	38.7	38.7	38.4
102.5°	47.8	47.8	47.8	47.9	48.0	48.0	47.9	47.9	47.8	47.8	47.5
105°	62.1	62.1	62.1	62.1	62.1	62.1	61.9	61.8	61.7	61.6	61.5
107.5°	75.7	76.0	76.3	76.5	76.8	76.9	76.9	76.8	76.8	76.8	76.8
110°	86.2	86.4	86.6	86.7	87.0	87.1	87.1	87.1	87.1	87.1	87.1



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	96.3	96.4	96.6	96.7	96.8	97.0	97.1	97.3	97.4	97.6	97.6
115°	111.9	112.2	112.3	112.5	112.7	112.8	112.9	113.0	113.0	113.0	113.2
117.5°	126.9	127.1	127.3	127.5	127.6	127.8	127.9	128.1	128.3	128.4	128.7
120°	137.4	137.6	137.8	138.0	138.2	138.2	138.2	138.2	138.2	138.2	138.8
122.5°	147.7	147.8	148.0	148.1	148.3	148.4	148.5	148.7	148.9	149.0	149.3
125°	163.4	163.5	163.6	163.7	163.7	163.8	164.0	164.2	164.4	164.5	164.8
127.5°	177.8	178.0	178.2	178.4	178.6	178.8	179.0	179.3	179.4	179.7	179.9
130°	188.1	188.3	188.5	188.9	189.1	189.3	189.4	189.5	189.6	189.7	189.9
132.5°	198.0	198.1	198.4	198.5	198.8	199.0	199.2	199.5	199.8	200.0	200.0
135°	213.3	213.5	213.7	213.8	214.0	214.1	214.2	214.3	214.3	214.4	214.3
137.5°	227.1	227.4	227.7	227.9	228.1	228.3	228.3	228.4	228.5	228.5	228.3
140°	236.8	237.0	237.3	237.5	237.7	237.9	237.9	237.9	237.9	237.9	237.6
142.5°	245.5	245.7	246.0	246.3	246.5	246.6	246.5	246.5	246.4	246.4	246.2
145°	258.6	258.9	259.1	259.4	259.6	259.7	259.6	259.6	259.5	259.4	259.0
147.5°	270.3	270.5	270.8	271.0	271.2	271.3	271.2	271.0	270.9	270.8	270.5
150°	277.9	278.1	278.3	278.5	278.7	278.7	278.5	278.3	278.1	277.9	277.7
152.5°	285.1	285.3	285.6	285.8	286.1	286.1	285.8	285.6	285.3	285.1	284.8
155°	294.7	294.9	295.1	295.2	295.5	295.4	295.1	294.8	294.5	294.1	294.0
157.5°	303.0	303.3	303.6	303.9	304.2	304.1	303.7	303.2	302.9	302.5	302.3
160°	308.2	308.4	308.6	308.9	309.1	309.1	308.7	308.3	307.9	307.6	307.5
162.5°	312.6	312.9	313.2	313.5	313.8	313.8	313.3	312.9	312.5	312.0	312.0
165°	318.5	318.8	319.1	319.4	319.7	319.6	319.2	318.8	318.4	317.9	317.9
167.5°	323.3	323.6	323.9	324.3	324.6	324.6	324.1	323.7	323.2	322.8	322.8
170°	325.7	326.1	326.5	326.9	327.3	327.3	326.8	326.4	325.9	325.5	325.6
172.5°	327.8	328.2	328.5	328.9	329.3	329.2	328.8	328.4	328.0	327.5	327.6
175°	329.9	330.3	330.7	331.1	331.4	331.4	331.0	330.6	330.1	329.7	329.8
177.5°	331.0	331.3	331.6	331.8	332.2	332.2	331.8	331.6	331.3	331.0	331.1
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1191.6	1189.0	1186.8	1180.9	1178.1	1171.6	1170.6	1170.3	1161.8	1153.7	1151.5
5°	1232.6	1226.1	1216.3	1205.0	1193.3	1181.1	1173.1	1166.6	1150.4	1135.0	1126.2
7.5°	1273.7	1259.9	1243.1	1221.7	1203.8	1183.8	1168.9	1155.6	1132.6	1110.6	1095.7
10°	1304.5	1281.8	1259.6	1230.1	1207.0	1184.4	1163.4	1145.2	1119.3	1090.2	1069.5
12.5°	1323.6	1298.7	1268.0	1239.1	1209.3	1180.5	1152.4	1129.0	1098.6	1068.5	1044.0
15°	1349.4	1322.7	1285.5	1244.3	1205.9	1168.2	1135.9	1106.8	1067.1	1031.2	1001.2
17.5°	1370.5	1333.8	1293.8	1246.1	1201.7	1153.8	1112.1	1075.0	1030.9	987.5	952.2
20°	1377.3	1340.9	1294.8	1247.1	1194.5	1138.3	1093.4	1053.0	1005.7	958.4	917.9
22.5°	1373.1	1344.8	1293.5	1236.4	1182.6	1123.7	1073.0	1026.1	973.7	925.3	878.5
25°	1344.6	1334.8	1286.3	1224.0	1162.6	1094.2	1035.6	984.2	924.4	872.7	821.7
27.5°	1277.9	1298.9	1268.8	1202.5	1134.2	1060.9	995.0	936.5	874.4	816.2	765.4
30°	1213.9	1262.0	1249.1	1187.6	1111.2	1039.3	965.3	904.2	837.9	778.0	727.9
32.5°	1126.2	1205.8	1218.4	1167.0	1087.9	1008.8	931.3	870.5	801.3	738.2	689.4
35°	986.7	1105.6	1160.2	1127.4	1048.1	962.8	882.7	812.0	742.4	680.2	631.6
37.5°	820.1	982.1	1073.0	1075.4	1002.6	913.9	826.7	756.5	685.2	624.1	571.6
40°	712.1	887.6	1006.1	1032.4	970.9	875.0	786.9	715.3	645.8	585.9	525.7
42.5°	615.1	789.9	935.6	981.3	932.4	837.2	748.8	673.9	606.3	549.7	488.1
45°	497.4	650.2	810.8	892.5	865.4	777.2	683.8	612.6	549.1	500.2	441.2
47.5°	419.5	527.3	682.6	793.1	792.7	712.2	620.3	552.2	493.3	447.4	399.6
50°	375.3	469.1	600.5	725.9	736.3	668.8	581.5	514.0	459.0	410.8	372.4
52.5°	335.5	412.8	530.9	651.1	681.0	622.6	537.8	475.5	422.1	377.9	344.9
55°	283.4	343.3	433.1	545.5	590.8	549.5	474.4	416.1	372.8	335.6	307.3
57.5°	239.8	284.7	356.7	447.3	499.9	474.0	411.9	364.6	327.6	294.0	271.6
60°	212.3	249.1	310.1	385.8	444.0	425.8	372.8	328.8	297.2	268.1	247.1
62.5°	186.4	218.0	270.4	331.8	385.2	377.6	334.3	297.4	269.7	243.2	225.4
65°	150.0	173.1	213.9	262.1	304.9	308.6	277.4	252.3	227.7	206.6	190.8
67.5°	119.5	134.5	163.3	203.8	235.9	247.4	228.4	209.2	189.6	173.4	159.7
70°	100.7	112.8	133.9	166.6	196.1	208.3	197.3	182.4	165.4	152.0	140.3
72.5°	81.6	93.4	108.9	132.9	158.3	171.3	167.5	156.9	143.1	132.0	120.9
75°	61.5	65.1	75.7	91.8	111.6	122.9	125.8	120.1	109.2	100.7	94.2
77.5°	45.5	47.6	52.7	61.2	74.1	84.2	88.3	87.7	80.2	75.2	69.2
80°	36.4	37.6	40.0	43.6	53.4	63.5	66.3	66.3	61.1	59.0	53.0
82.5°	27.6	28.5	30.0	32.0	36.5	45.4	48.6	49.2	45.9	43.2	38.4
85°	15.8	15.4	16.2	17.3	18.2	20.6	25.5	26.3	25.5	22.3	21.0
87.5°	6.9	7.0	6.7	6.2	6.3	6.5	8.0	9.4	8.3	7.4	7.0
90°	7.1	5.7	4.4	3.2	2.5	1.7	1.0	0.3	1.0	1.7	2.5
92.5°	8.2	7.9	7.6	7.2	6.7	6.1	5.5	5.0	5.5	6.1	6.7
95°	17.7	17.5	17.4	17.0	16.4	15.8	15.2	14.6	15.2	15.8	16.4
97.5°	29.6	29.4	29.2	28.8	28.2	27.6	27.2	26.6	27.2	27.6	28.2
100°	38.3	38.0	37.9	37.5	37.1	36.5	36.0	35.6	36.0	36.5	37.1
102.5°	47.3	47.1	46.9	46.5	46.1	45.7	45.3	44.9	45.3	45.7	46.1
105°	61.3	61.2	61.1	60.9	60.8	60.5	60.4	60.2	60.4	60.5	60.8
107.5°	76.8	76.8	76.8	76.6	76.4	76.0	75.8	75.5	75.8	76.0	76.4
110°	87.1	87.1	87.1	86.8	86.5	86.1	85.7	85.4	85.7	86.1	86.5





TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	97.7	97.7	97.8	97.6	97.2	96.9	96.5	96.1	96.5	96.9	97.2
115°	113.3	113.4	113.6	113.4	113.0	112.7	112.3	111.9	112.3	112.7	113.0
117.5°	129.1	129.4	129.8	129.8	129.2	128.7	128.3	127.7	128.3	128.7	129.2
120°	139.3	139.7	140.2	140.2	139.7	139.3	138.8	138.2	138.8	139.3	139.7
122.5°	149.7	150.0	150.4	150.3	149.6	149.1	148.5	147.9	148.5	149.1	149.6
125°	164.9	165.1	165.3	165.1	164.5	164.0	163.4	162.9	163.4	164.0	164.5
127.5°	180.1	180.4	180.5	180.3	179.6	179.0	178.2	177.5	178.2	179.0	179.6
130°	190.0	190.1	190.3	189.9	189.1	188.3	187.5	186.7	187.5	188.3	189.1
132.5°	200.0	199.9	199.9	199.6	198.9	198.3	197.6	197.0	197.6	198.3	198.9
135°	214.1	214.0	213.9	213.5	212.8	212.1	211.4	210.7	211.4	212.1	212.8
137.5°	228.1	228.0	227.8	227.5	227.0	226.3	225.8	225.2	225.8	226.3	227.0
140°	237.3	236.9	236.6	236.2	235.7	235.1	234.6	234.0	234.6	235.1	235.7
142.5°	246.0	245.7	245.6	245.2	244.6	244.1	243.5	243.0	243.5	244.1	244.6
145°	258.7	258.3	257.9	257.5	257.1	256.7	256.3	255.8	256.3	256.7	257.1
147.5°	270.3	270.0	269.7	269.3	268.9	268.3	267.8	267.3	267.8	268.3	268.9
150°	277.4	277.2	276.9	276.6	276.2	275.8	275.5	275.1	275.5	275.8	276.2
152.5°	284.5	284.2	283.9	283.5	283.2	282.8	282.4	282.1	282.4	282.8	283.2
155°	293.7	293.6	293.4	293.2	293.0	292.9	292.6	292.5	292.6	292.9	293.0
157.5°	302.2	302.1	302.0	301.9	301.7	301.6	301.5	301.3	301.5	301.6	301.7
160°	307.4	307.4	307.4	307.2	307.1	307.0	306.9	306.7	306.9	307.0	307.1
162.5°	312.0	311.9	311.8	311.8	311.7	311.7	311.7	311.6	311.7	311.7	311.7
165°	317.9	317.9	317.9	318.0	318.1	318.1	318.1	318.2	318.1	318.1	318.1
167.5°	322.8	322.8	322.9	323.0	323.1	323.4	323.5	323.7	323.5	323.4	323.1
170°	325.6	325.7	325.7	325.9	326.1	326.2	326.5	326.6	326.5	326.2	326.1
172.5°	327.6	327.7	327.7	327.9	328.0	328.3	328.4	328.6	328.4	328.3	328.0
175°	329.9	330.1	330.2	330.3	330.5	330.7	330.9	331.1	330.9	330.7	330.5
177.5°	331.2	331.3	331.4	331.5	331.7	331.8	331.9	332.1	331.9	331.8	331.7
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1147.3	1145.0	1140.8	1134.3	1130.4	1123.6	1119.1	1121.7	1122.4	1121.7	1121.1
5°	1116.5	1107.9	1096.2	1084.9	1074.4	1063.1	1056.6	1053.8	1048.1	1044.9	1043.3
7.5°	1079.2	1064.5	1048.0	1028.3	1011.5	994.0	985.0	980.5	968.9	962.7	957.1
10°	1051.4	1028.3	1011.8	985.9	970.1	947.1	931.3	931.7	915.9	907.0	900.6
12.5°	1020.6	995.3	967.7	944.4	922.5	904.0	885.0	877.3	860.5	852.0	834.6
15°	969.7	940.2	911.1	879.5	857.3	828.5	801.1	767.5	740.4	716.9	710.5
17.5°	914.0	877.5	848.3	811.3	773.2	724.8	693.0	673.5	657.2	644.8	635.6
20°	875.8	838.7	807.6	751.7	700.4	667.7	644.2	629.2	612.2	598.9	591.6
22.5°	835.8	796.9	754.5	692.2	652.2	625.9	605.0	587.8	576.3	565.9	559.3
25°	778.8	736.3	666.4	623.5	591.2	563.7	549.1	538.6	526.5	512.3	505.9
27.5°	718.7	651.1	600.9	569.0	538.1	520.2	507.2	491.5	480.6	474.3	467.5
30°	673.7	606.2	567.0	532.2	510.3	490.5	475.2	466.3	455.7	444.8	440.4
32.5°	623.5	569.6	532.0	503.0	480.9	464.0	451.9	437.4	429.8	423.1	413.8
35°	561.3	520.5	486.1	462.6	441.6	427.9	413.7	405.2	391.4	385.8	382.1
37.5°	508.5	473.1	447.5	422.7	406.1	390.9	382.2	368.7	362.7	354.9	347.2
40°	478.8	444.0	419.3	399.1	380.5	369.2	358.3	347.4	338.4	334.9	325.5
42.5°	448.4	420.1	395.4	373.2	360.8	348.8	335.0	327.0	317.7	311.9	306.1
45°	406.4	381.4	360.3	342.1	328.4	315.8	306.9	293.6	288.4	276.6	271.7
47.5°	369.6	346.2	326.1	308.9	295.4	287.2	274.3	263.8	255.4	248.2	242.0
50°	343.3	323.9	304.5	289.1	277.0	265.3	251.9	246.7	233.7	230.0	226.5
52.5°	319.4	301.0	283.1	268.1	256.0	244.5	232.8	225.9	217.2	213.6	211.0
55°	285.9	268.1	251.1	237.7	225.6	213.9	206.6	198.1	194.1	191.2	188.1
57.5°	252.2	236.2	223.2	209.7	197.5	188.2	179.7	174.7	170.5	166.8	162.9
60°	230.9	215.6	203.8	191.2	178.7	171.0	164.6	158.5	153.7	148.0	146.4
62.5°	208.3	194.8	184.1	171.8	161.0	153.9	147.7	142.0	136.2	127.9	125.6
65°	177.1	166.6	155.3	145.2	135.5	128.6	119.7	113.2	110.8	110.0	109.6
67.5°	149.0	139.0	129.3	119.0	110.1	103.8	99.3	98.2	96.6	96.1	95.0
70°	130.2	120.9	111.2	101.5	93.0	91.8	90.2	88.6	86.5	85.7	84.9
72.5°	113.4	103.8	94.0	86.3	82.6	81.1	79.5	77.9	76.5	75.7	75.2
75°	86.9	78.0	71.6	68.8	66.7	65.5	63.1	61.9	61.1	59.8	59.4
77.5°	62.6	57.6	54.6	52.8	50.7	49.4	48.0	46.8	45.9	45.7	45.1
80°	47.7	45.3	43.3	40.9	40.0	38.4	38.0	36.8	37.2	36.0	36.0
82.5°	37.1	34.0	32.2	31.1	30.3	29.1	28.6	28.0	28.1	27.3	27.3
85°	19.0	18.2	17.3	16.6	16.6	15.4	15.8	15.4	15.4	14.6	14.2
87.5°	6.8	6.7	6.3	6.6	6.9	6.8	6.8	6.4	6.4	6.4	6.0
90°	3.2	4.4	5.7	7.1	8.4	9.8	9.7	9.6	9.4	9.3	9.3
92.5°	7.2	7.6	7.9	8.2	8.6	8.9	9.0	9.0	9.0	9.0	9.0
95°	17.0	17.4	17.5	17.7	17.8	17.9	17.9	17.9	17.9	17.9	17.8
97.5°	28.8	29.2	29.4	29.6	29.9	30.1	30.1	30.1	30.1	30.1	30.1
100°	37.5	37.9	38.0	38.3	38.4	38.7	38.7	38.7	38.7	38.7	38.6
102.5°	46.5	46.9	47.1	47.3	47.5	47.8	47.8	47.9	47.9	48.0	48.0
105°	60.9	61.1	61.2	61.3	61.5	61.6	61.7	61.8	61.9	62.1	62.1
107.5°	76.6	76.8	76.8	76.8	76.8	76.8	76.8	76.8	76.9	76.9	76.8
110°	86.8	87.1	87.1	87.1	87.1	87.1	87.1	87.1	87.1	87.1	87.0



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	97.6	97.8	97.7	97.7	97.6	97.6	97.4	97.3	97.1	97.0	96.8
115°	113.4	113.6	113.4	113.3	113.2	113.0	113.0	113.0	112.9	112.8	112.7
117.5°	129.8	129.8	129.4	129.1	128.7	128.4	128.3	128.1	127.9	127.8	127.6
120°	140.2	140.2	139.7	139.3	138.8	138.2	138.2	138.2	138.2	138.2	138.2
122.5°	150.3	150.4	150.0	149.7	149.3	149.0	148.9	148.7	148.5	148.4	148.3
125°	165.1	165.3	165.1	164.9	164.8	164.5	164.4	164.2	164.0	163.8	163.7
127.5°	180.3	180.5	180.4	180.1	179.9	179.7	179.4	179.3	179.0	178.8	178.6
130°	189.9	190.3	190.1	190.0	189.9	189.7	189.6	189.5	189.4	189.3	189.1
132.5°	199.6	199.9	199.9	200.0	200.0	200.0	199.8	199.5	199.2	199.0	198.8
135°	213.5	213.9	214.0	214.1	214.3	214.4	214.3	214.3	214.2	214.1	214.0
137.5°	227.5	227.8	228.0	228.1	228.3	228.5	228.5	228.4	228.3	228.3	228.1
140°	236.2	236.6	236.9	237.3	237.6	237.9	237.9	237.9	237.9	237.9	237.7
142.5°	245.2	245.6	245.7	246.0	246.2	246.4	246.4	246.5	246.5	246.6	246.5
145°	257.5	257.9	258.3	258.7	259.0	259.4	259.5	259.6	259.6	259.7	259.6
147.5°	269.3	269.7	270.0	270.3	270.5	270.8	270.9	271.0	271.2	271.3	271.2
150°	276.6	276.9	277.2	277.4	277.7	277.9	278.1	278.3	278.5	278.7	278.7
152.5°	283.5	283.9	284.2	284.5	284.8	285.1	285.3	285.6	285.8	286.1	286.1
155°	293.2	293.4	293.6	293.7	294.0	294.1	294.5	294.8	295.1	295.4	295.5
157.5°	301.9	302.0	302.1	302.2	302.3	302.5	302.9	303.2	303.7	304.1	304.2
160°	307.2	307.4	307.4	307.4	307.5	307.6	307.9	308.3	308.7	309.1	309.1
162.5°	311.8	311.8	311.9	312.0	312.0	312.0	312.5	312.9	313.3	313.8	313.8
165°	318.0	317.9	317.9	317.9	317.9	317.9	318.4	318.8	319.2	319.6	319.7
167.5°	323.0	322.9	322.8	322.8	322.8	322.8	323.2	323.7	324.1	324.6	324.6
170°	325.9	325.7	325.7	325.6	325.6	325.5	325.9	326.4	326.8	327.3	327.3
172.5°	327.9	327.7	327.7	327.6	327.6	327.5	328.0	328.4	328.8	329.2	329.3
175°	330.3	330.2	330.1	329.9	329.8	329.7	330.1	330.6	331.0	331.4	331.4
177.5°	331.5	331.4	331.3	331.2	331.1	331.0	331.3	331.6	331.8	332.2	332.2
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1117.5	1118.2	1117.2	1117.8	1117.2	1118.2	1117.5	1121.1	1121.7	1122.4	1121.7
5°	1041.2	1036.4	1035.6	1034.4	1035.6	1036.4	1041.2	1043.3	1044.9	1048.1	1053.8
7.5°	950.2	949.4	947.5	944.6	947.5	949.4	950.2	957.1	962.7	968.9	980.5
10°	891.6	889.6	889.2	886.4	889.2	889.6	891.6	900.6	907.0	915.9	931.7
12.5°	823.1	810.0	808.7	801.6	808.7	810.0	823.1	834.6	852.0	860.5	877.3
15°	700.8	698.4	690.2	685.0	690.2	698.4	700.8	710.5	716.9	740.4	767.5
17.5°	630.9	623.0	620.4	619.3	620.4	623.0	630.9	635.6	644.8	657.2	673.5
20°	585.9	578.7	577.4	576.6	577.4	578.7	585.9	591.6	598.9	612.2	629.2
22.5°	554.8	547.2	544.2	541.7	544.2	547.2	554.8	559.3	565.9	576.3	587.8
25°	501.8	499.0	497.4	496.5	497.4	499.0	501.8	505.9	512.3	526.5	538.6
27.5°	460.3	454.1	452.9	450.8	452.9	454.1	460.3	467.5	474.3	480.6	491.5
30°	436.7	434.7	431.9	429.4	431.9	434.7	436.7	440.4	444.8	455.7	466.3
32.5°	408.9	407.2	404.7	403.5	404.7	407.2	408.9	413.8	423.1	429.8	437.4
35°	378.1	372.4	370.0	366.4	370.0	372.4	378.1	382.1	385.8	391.4	405.2
37.5°	345.5	342.5	339.1	340.3	339.1	342.5	345.5	347.2	354.9	362.7	368.7
40°	320.3	318.2	317.4	317.0	317.4	318.2	320.3	325.5	334.9	338.4	347.4
42.5°	300.2	294.6	292.6	292.5	292.6	294.6	300.2	306.1	311.9	317.7	327.0
45°	269.7	264.4	260.8	261.3	260.8	264.4	269.7	271.7	276.6	288.4	293.6
47.5°	238.5	238.4	236.1	236.8	236.1	238.4	238.5	242.0	248.2	255.4	263.8
50°	223.6	221.2	219.6	220.0	219.6	221.2	223.6	226.5	230.0	233.7	246.7
52.5°	209.4	207.3	206.0	207.7	206.0	207.3	209.4	211.0	213.6	217.2	225.9
55°	186.0	183.5	183.2	182.8	183.2	183.5	186.0	188.1	191.2	194.1	198.1
57.5°	159.9	158.3	155.8	154.8	155.8	158.3	159.9	162.9	166.8	170.5	174.7
60°	141.1	137.9	133.9	133.4	133.9	137.9	141.1	146.4	148.0	153.7	158.5
62.5°	124.0	123.3	122.6	122.5	122.6	123.3	124.0	125.6	127.9	136.2	142.0
65°	108.8	108.4	108.8	109.2	108.8	108.4	108.8	109.6	110.0	110.8	113.2
67.5°	94.8	94.0	93.3	93.6	93.3	94.0	94.8	95.0	96.1	96.6	98.2
70°	84.1	83.7	83.3	83.3	83.3	83.7	84.1	84.9	85.7	86.5	88.6
72.5°	73.8	73.7	73.3	73.0	73.3	73.7	73.8	75.2	75.7	76.5	77.9
75°	59.0	58.2	58.2	58.2	58.2	58.2	59.0	59.4	59.8	61.1	61.9
77.5°	45.0	44.6	44.1	43.8	44.1	44.6	45.0	45.1	45.7	45.9	46.8
80°	35.6	35.2	34.8	34.8	34.8	35.2	35.6	36.0	36.0	37.2	36.8
82.5°	27.2	26.8	26.7	26.4	26.7	26.8	27.2	27.3	27.3	28.1	28.0
85°	14.6	15.0	14.6	15.4	14.6	15.0	14.6	14.2	14.6	15.4	15.4
87.5°	6.1	5.8	6.1	5.8	6.1	5.8	6.1	6.0	6.4	6.4	6.4
90°	9.3	9.4	9.4	9.5	9.4	9.4	9.3	9.3	9.3	9.4	9.6
92.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0	9.0
95°	17.7	17.6	17.5	17.3	17.5	17.6	17.7	17.8	17.9	17.9	17.9
97.5°	30.1	30.1	30.1	30.0	30.1	30.1	30.1	30.1	30.1	30.1	30.1
100°	38.5	38.5	38.4	38.3	38.4	38.5	38.5	38.6	38.7	38.7	38.7
102.5°	47.9	47.8	47.8	47.8	47.8	47.8	47.9	48.0	48.0	47.9	47.9
105°	62.1	62.1	62.1	62.1	62.1	62.1	62.1	62.1	62.1	61.9	61.8
107.5°	76.5	76.3	76.0	75.7	76.0	76.3	76.5	76.8	76.9	76.9	76.8
110°	86.7	86.6	86.4	86.2	86.4	86.6	86.7	87.0	87.1	87.1	87.1



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	96.7	96.6	96.4	96.3	96.4	96.6	96.7	96.8	97.0	97.1	97.3
115°	112.5	112.3	112.2	111.9	112.2	112.3	112.5	112.7	112.8	112.9	113.0
117.5°	127.5	127.3	127.1	126.9	127.1	127.3	127.5	127.6	127.8	127.9	128.1
120°	138.0	137.8	137.6	137.4	137.6	137.8	138.0	138.2	138.2	138.2	138.2
122.5°	148.1	148.0	147.8	147.7	147.8	148.0	148.1	148.3	148.4	148.5	148.7
125°	163.7	163.6	163.5	163.4	163.5	163.6	163.7	163.7	163.8	164.0	164.2
127.5°	178.4	178.2	178.0	177.8	178.0	178.2	178.4	178.6	178.8	179.0	179.3
130°	188.9	188.5	188.3	188.1	188.3	188.5	188.9	189.1	189.3	189.4	189.5
132.5°	198.5	198.4	198.1	198.0	198.1	198.4	198.5	198.8	199.0	199.2	199.5
135°	213.8	213.7	213.5	213.3	213.5	213.7	213.8	214.0	214.1	214.2	214.3
137.5°	227.9	227.7	227.4	227.1	227.4	227.7	227.9	228.1	228.3	228.3	228.4
140°	237.5	237.3	237.0	236.8	237.0	237.3	237.5	237.7	237.9	237.9	237.9
142.5°	246.3	246.0	245.7	245.5	245.7	246.0	246.3	246.5	246.6	246.5	246.5
145°	259.4	259.1	258.9	258.6	258.9	259.1	259.4	259.6	259.7	259.6	259.6
147.5°	271.0	270.8	270.5	270.3	270.5	270.8	271.0	271.2	271.3	271.2	271.0
150°	278.5	278.3	278.1	277.9	278.1	278.3	278.5	278.7	278.7	278.5	278.3
152.5°	285.8	285.6	285.3	285.1	285.3	285.6	285.8	286.1	286.1	285.8	285.6
155°	295.2	295.1	294.9	294.7	294.9	295.1	295.2	295.5	295.4	295.1	294.8
157.5°	303.9	303.6	303.3	303.0	303.3	303.6	303.9	304.2	304.1	303.7	303.2
160°	308.9	308.6	308.4	308.2	308.4	308.6	308.9	309.1	309.1	308.7	308.3
162.5°	313.5	313.2	312.9	312.6	312.9	313.2	313.5	313.8	313.8	313.3	312.9
165°	319.4	319.1	318.8	318.5	318.8	319.1	319.4	319.7	319.6	319.2	318.8
167.5°	324.3	323.9	323.6	323.3	323.6	323.9	324.3	324.6	324.6	324.1	323.7
170°	326.9	326.5	326.1	325.7	326.1	326.5	326.9	327.3	327.3	326.8	326.4
172.5°	328.9	328.5	328.2	327.8	328.2	328.5	328.9	329.3	329.2	328.8	328.4
175°	331.1	330.7	330.3	329.9	330.3	330.7	331.1	331.4	331.4	331.0	330.6
177.5°	331.8	331.6	331.3	331.0	331.3	331.6	331.8	332.2	332.2	331.8	331.6
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1119.1	1123.6	1130.4	1134.3	1140.8	1145.0	1147.3	1151.5	1153.7	1161.8	1170.3
5°	1056.6	1063.1	1074.4	1084.9	1096.2	1107.9	1116.5	1126.2	1135.0	1150.4	1166.6
7.5°	985.0	994.0	1011.5	1028.3	1048.0	1064.5	1079.2	1095.7	1110.6	1132.6	1155.6
10°	931.3	947.1	970.1	985.9	1011.8	1028.3	1051.4	1069.5	1090.2	1119.3	1145.2
12.5°	885.0	904.0	922.5	944.4	967.7	995.3	1020.6	1044.0	1068.5	1098.6	1129.0
15°	801.1	828.5	857.3	879.5	911.1	940.2	969.7	1001.2	1031.2	1067.1	1106.8
17.5°	693.0	724.8	773.2	811.3	848.3	877.5	914.0	952.2	987.5	1030.9	1075.0
20°	644.2	667.7	700.4	751.7	807.6	838.7	875.8	917.9	958.4	1005.7	1053.0
22.5°	605.0	625.9	652.2	692.2	754.5	796.9	835.8	878.5	925.3	973.7	1026.1
25°	549.1	563.7	591.2	623.5	666.4	736.3	778.8	821.7	872.7	924.4	984.2
27.5°	507.2	520.2	538.1	569.0	600.9	651.1	718.7	765.4	816.2	874.4	936.5
30°	475.2	490.5	510.3	532.2	567.0	606.2	673.7	727.9	778.0	837.9	904.2
32.5°	451.9	464.0	480.9	503.0	532.0	569.6	623.5	689.4	738.2	801.3	870.5
35°	413.7	427.9	441.6	462.6	486.1	520.5	561.3	631.6	680.2	742.4	812.0
37.5°	382.2	390.9	406.1	422.7	447.5	473.1	508.5	571.6	624.1	685.2	756.5
40°	358.3	369.2	380.5	399.1	419.3	444.0	478.8	525.7	585.9	645.8	715.3
42.5°	335.0	348.8	360.8	373.2	395.4	420.1	448.4	488.1	549.7	606.3	673.9
45°	306.9	315.8	328.4	342.1	360.3	381.4	406.4	441.2	500.2	549.1	612.6
47.5°	274.3	287.2	295.4	308.9	326.1	346.2	369.6	399.6	447.4	493.3	552.2
50°	251.9	265.3	277.0	289.1	304.5	323.9	343.3	372.4	410.8	459.0	514.0
52.5°	232.8	244.5	256.0	268.1	283.1	301.0	319.4	344.9	377.9	422.1	475.5
55°	206.6	213.9	225.6	237.7	251.1	268.1	285.9	307.3	335.6	372.8	416.1
57.5°	179.7	188.2	197.5	209.7	223.2	236.2	252.2	271.6	294.0	327.6	364.6
60°	164.6	171.0	178.7	191.2	203.8	215.6	230.9	247.1	268.1	297.2	328.8
62.5°	147.7	153.9	161.0	171.8	184.1	194.8	208.3	225.4	243.2	269.7	297.4
65°	119.7	128.6	135.5	145.2	155.3	166.6	177.1	190.8	206.6	227.7	252.3
67.5°	99.3	103.8	110.1	119.0	129.3	139.0	149.0	159.7	173.4	189.6	209.2
70°	90.2	91.8	93.0	101.5	111.2	120.9	130.2	140.3	152.0	165.4	182.4
72.5°	79.5	81.1	82.6	86.3	94.0	103.8	113.4	120.9	132.0	143.1	156.9
75°	63.1	65.5	66.7	68.8	71.6	78.0	86.9	94.2	100.7	109.2	120.1
77.5°	48.0	49.4	50.7	52.8	54.6	57.6	62.6	69.2	75.2	80.2	87.7
80°	38.0	38.4	40.0	40.9	43.3	45.3	47.7	53.0	59.0	61.1	66.3
82.5°	28.6	29.1	30.3	31.1	32.2	34.0	37.1	38.4	43.2	45.9	49.2
85°	15.8	15.4	16.6	16.6	17.3	18.2	19.0	21.0	22.3	25.5	26.3
87.5°	6.8	6.8	6.9	6.6	6.3	6.7	6.8	7.0	7.4	8.3	9.4
90°	9.7	9.8	8.4	7.1	5.7	4.4	3.2	2.5	1.7	1.0	0.3
92.5°	9.0	8.9	8.6	8.2	7.9	7.6	7.2	6.7	6.1	5.5	5.0
95°	17.9	17.9	17.8	17.7	17.5	17.4	17.0	16.4	15.8	15.2	14.6
97.5°	30.1	30.1	29.9	29.6	29.4	29.2	28.8	28.2	27.6	27.2	26.6
100°	38.7	38.7	38.4	38.3	38.0	37.9	37.5	37.1	36.5	36.0	35.6
102.5°	47.8	47.8	47.5	47.3	47.1	46.9	46.5	46.1	45.7	45.3	44.9
105°	61.7	61.6	61.5	61.3	61.2	61.1	60.9	60.8	60.5	60.4	60.2
107.5°	76.8	76.8	76.8	76.8	76.8	76.8	76.6	76.4	76.0	75.8	75.5
110°	87.1	87.1	87.1	87.1	87.1	87.1	86.8	86.5	86.1	85.7	85.4



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	97.4	97.6	97.6	97.7	97.7	97.8	97.6	97.2	96.9	96.5	96.1
115°	113.0	113.0	113.2	113.3	113.4	113.6	113.4	113.0	112.7	112.3	111.9
117.5°	128.3	128.4	128.7	129.1	129.4	129.8	129.8	129.2	128.7	128.3	127.7
120°	138.2	138.2	138.8	139.3	139.7	140.2	140.2	139.7	139.3	138.8	138.2
122.5°	148.9	149.0	149.3	149.7	150.0	150.4	150.3	149.6	149.1	148.5	147.9
125°	164.4	164.5	164.8	164.9	165.1	165.3	165.1	164.5	164.0	163.4	162.9
127.5°	179.4	179.7	179.9	180.1	180.4	180.5	180.3	179.6	179.0	178.2	177.5
130°	189.6	189.7	189.9	190.0	190.1	190.3	189.9	189.1	188.3	187.5	186.7
132.5°	199.8	200.0	200.0	200.0	199.9	199.9	199.6	198.9	198.3	197.6	197.0
135°	214.3	214.4	214.3	214.1	214.0	213.9	213.5	212.8	212.1	211.4	210.7
137.5°	228.5	228.5	228.3	228.1	228.0	227.8	227.5	227.0	226.3	225.8	225.2
140°	237.9	237.9	237.6	237.3	236.9	236.6	236.2	235.7	235.1	234.6	234.0
142.5°	246.4	246.4	246.2	246.0	245.7	245.6	245.2	244.6	244.1	243.5	243.0
145°	259.5	259.4	259.0	258.7	258.3	257.9	257.5	257.1	256.7	256.3	255.8
147.5°	270.9	270.8	270.5	270.3	270.0	269.7	269.3	268.9	268.3	267.8	267.3
150°	278.1	277.9	277.7	277.4	277.2	276.9	276.6	276.2	275.8	275.5	275.1
152.5°	285.3	285.1	284.8	284.5	284.2	283.9	283.5	283.2	282.8	282.4	282.1
155°	294.5	294.1	294.0	293.7	293.6	293.4	293.2	293.0	292.9	292.6	292.5
157.5°	302.9	302.5	302.3	302.2	302.1	302.0	301.9	301.7	301.6	301.5	301.3
160°	307.9	307.6	307.5	307.4	307.4	307.4	307.2	307.1	307.0	306.9	306.7
162.5°	312.5	312.0	312.0	312.0	311.9	311.8	311.8	311.7	311.7	311.7	311.6
165°	318.4	317.9	317.9	317.9	317.9	317.9	318.0	318.1	318.1	318.1	318.2
167.5°	323.2	322.8	322.8	322.8	322.8	322.9	323.0	323.1	323.4	323.5	323.7
170°	325.9	325.5	325.6	325.6	325.7	325.7	325.9	326.1	326.2	326.5	326.6
172.5°	328.0	327.5	327.6	327.6	327.7	327.7	327.9	328.0	328.3	328.4	328.6
175°	330.1	329.7	329.8	329.9	330.1	330.2	330.3	330.5	330.7	330.9	331.1
177.5°	331.3	331.0	331.1	331.2	331.3	331.4	331.5	331.7	331.8	331.9	332.1
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331676-927  
 CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1170.6	1171.6	1178.1	1180.9	1186.8	1189.0	1191.6	1191.0	1191.0	1192.2	1201.3
5°	1173.1	1181.1	1193.3	1205.0	1216.3	1226.1	1232.6	1239.0	1241.4	1253.2	1263.7
7.5°	1168.9	1183.8	1203.8	1221.7	1243.1	1259.9	1273.7	1286.3	1294.9	1311.9	1329.4
10°	1163.4	1184.4	1207.0	1230.1	1259.6	1281.8	1304.5	1321.9	1327.5	1353.0	1367.6
12.5°	1152.4	1180.5	1209.3	1239.1	1268.0	1298.7	1323.6	1341.0	1360.9	1383.8	1410.6
15°	1135.9	1168.2	1205.9	1244.3	1285.5	1322.7	1349.4	1379.7	1401.5	1426.6	1450.1
17.5°	1112.1	1153.8	1201.7	1246.1	1293.8	1333.8	1370.5	1399.6	1415.0	1429.3	1432.7
20°	1093.4	1138.3	1194.5	1247.1	1294.8	1340.9	1377.3	1401.5	1405.6	1406.0	1384.6
22.5°	1073.0	1123.7	1182.6	1236.4	1293.5	1344.8	1373.1	1383.5	1367.4	1340.0	1298.5
25°	1035.6	1094.2	1162.6	1224.0	1286.3	1334.8	1344.6	1326.4	1270.1	1211.1	1136.3
27.5°	995.0	1060.9	1134.2	1202.5	1268.8	1298.9	1277.9	1212.4	1111.1	1023.1	916.5
30°	965.3	1039.3	1111.2	1187.6	1249.1	1262.0	1213.9	1117.3	999.2	866.6	760.3
32.5°	931.3	1008.8	1087.9	1167.0	1218.4	1205.8	1126.2	1007.3	868.9	738.5	637.9
35°	882.7	962.8	1048.1	1127.4	1160.2	1105.6	986.7	831.8	690.2	568.5	499.4
37.5°	826.7	913.9	1002.6	1075.4	1073.0	982.1	820.1	660.3	541.3	469.3	420.1
40°	786.9	875.0	970.9	1032.4	1006.1	887.6	712.1	561.3	474.4	416.9	380.9
42.5°	748.8	837.2	932.4	981.3	935.6	789.9	615.1	496.9	425.2	380.3	351.2
45°	683.8	777.2	865.4	892.5	810.8	650.2	497.4	411.6	363.9	330.8	310.5
47.5°	620.3	712.2	792.7	793.1	682.6	527.3	419.5	356.2	315.5	289.9	275.1
50°	581.5	668.8	736.3	725.9	600.5	469.1	375.3	320.7	286.7	266.9	251.5
52.5°	537.8	622.6	681.0	651.1	530.9	412.8	335.5	289.6	261.5	244.2	230.5
55°	474.4	549.5	590.8	545.5	433.1	343.3	283.4	247.5	226.5	211.9	200.2
57.5°	411.9	474.0	499.9	447.3	356.7	284.7	239.8	212.8	191.9	181.5	175.4
60°	372.8	425.8	444.0	385.8	310.1	249.1	212.3	187.2	171.8	165.0	158.9
62.5°	334.3	377.6	385.2	331.8	270.4	218.0	186.4	165.2	155.0	148.5	142.8
65°	277.4	308.6	304.9	262.1	213.9	173.1	150.0	137.0	129.4	120.1	110.0
67.5°	228.4	247.4	235.9	203.8	163.3	134.5	119.5	109.6	100.1	91.3	89.0
70°	197.3	208.3	196.1	166.6	133.9	112.8	100.7	89.0	83.3	81.3	77.6
72.5°	167.5	171.3	158.3	132.9	108.9	93.4	81.6	75.0	72.0	70.3	68.0
75°	125.8	122.9	111.6	91.8	75.7	65.1	61.5	59.0	57.0	55.4	54.2
77.5°	88.3	84.2	74.1	61.2	52.7	47.6	45.5	44.1	43.2	42.4	41.2
80°	66.3	63.5	53.4	43.6	40.0	37.6	36.4	34.8	34.8	34.0	32.7
82.5°	48.6	45.4	36.5	32.0	30.0	28.5	27.6	26.7	26.4	26.5	25.7
85°	25.5	20.6	18.2	17.3	16.2	15.4	15.8	15.0	15.0	15.0	14.6
87.5°	8.0	6.5	6.3	6.2	6.7	7.0	6.9	7.2	7.8	7.4	7.8
90°	1.0	1.7	2.5	3.2	4.4	5.7	7.1	8.4	9.8	9.7	9.6
92.5°	5.5	6.1	6.7	7.2	7.6	7.9	8.2	8.6	8.9	9.0	9.0
95°	15.2	15.8	16.4	17.0	17.4	17.5	17.7	17.8	17.9	17.9	17.9
97.5°	27.2	27.6	28.2	28.8	29.2	29.4	29.6	29.9	30.1	30.1	30.1
100°	36.0	36.5	37.1	37.5	37.9	38.0	38.3	38.4	38.7	38.7	38.7
102.5°	45.3	45.7	46.1	46.5	46.9	47.1	47.3	47.5	47.8	47.8	47.9
105°	60.4	60.5	60.8	60.9	61.1	61.2	61.3	61.5	61.6	61.7	61.8
107.5°	75.8	76.0	76.4	76.6	76.8	76.8	76.8	76.8	76.8	76.8	76.8
110°	85.7	86.1	86.5	86.8	87.1	87.1	87.1	87.1	87.1	87.1	87.1





TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	96.5	96.9	97.2	97.6	97.8	97.7	97.7	97.6	97.6	97.4	97.3
115°	112.3	112.7	113.0	113.4	113.6	113.4	113.3	113.2	113.0	113.0	113.0
117.5°	128.3	128.7	129.2	129.8	129.8	129.4	129.1	128.7	128.4	128.3	128.1
120°	138.8	139.3	139.7	140.2	140.2	139.7	139.3	138.8	138.2	138.2	138.2
122.5°	148.5	149.1	149.6	150.3	150.4	150.0	149.7	149.3	149.0	148.9	148.7
125°	163.4	164.0	164.5	165.1	165.3	165.1	164.9	164.8	164.5	164.4	164.2
127.5°	178.2	179.0	179.6	180.3	180.5	180.4	180.1	179.9	179.7	179.4	179.3
130°	187.5	188.3	189.1	189.9	190.3	190.1	190.0	189.9	189.7	189.6	189.5
132.5°	197.6	198.3	198.9	199.6	199.9	199.9	200.0	200.0	200.0	199.8	199.5
135°	211.4	212.1	212.8	213.5	213.9	214.0	214.1	214.3	214.4	214.3	214.3
137.5°	225.8	226.3	227.0	227.5	227.8	228.0	228.1	228.3	228.5	228.5	228.4
140°	234.6	235.1	235.7	236.2	236.6	236.9	237.3	237.6	237.9	237.9	237.9
142.5°	243.5	244.1	244.6	245.2	245.6	245.7	246.0	246.2	246.4	246.4	246.5
145°	256.3	256.7	257.1	257.5	257.9	258.3	258.7	259.0	259.4	259.5	259.6
147.5°	267.8	268.3	268.9	269.3	269.7	270.0	270.3	270.5	270.8	270.9	271.0
150°	275.5	275.8	276.2	276.6	276.9	277.2	277.4	277.7	277.9	278.1	278.3
152.5°	282.4	282.8	283.2	283.5	283.9	284.2	284.5	284.8	285.1	285.3	285.6
155°	292.6	292.9	293.0	293.2	293.4	293.6	293.7	294.0	294.1	294.5	294.8
157.5°	301.5	301.6	301.7	301.9	302.0	302.1	302.2	302.3	302.5	302.9	303.2
160°	306.9	307.0	307.1	307.2	307.4	307.4	307.4	307.5	307.6	307.9	308.3
162.5°	311.7	311.7	311.7	311.8	311.8	311.9	312.0	312.0	312.0	312.5	312.9
165°	318.1	318.1	318.1	318.0	317.9	317.9	317.9	317.9	317.9	318.4	318.8
167.5°	323.5	323.4	323.1	323.0	322.9	322.8	322.8	322.8	322.8	323.2	323.7
170°	326.5	326.2	326.1	325.9	325.7	325.7	325.6	325.6	325.5	325.9	326.4
172.5°	328.4	328.3	328.0	327.9	327.7	327.7	327.6	327.6	327.5	328.0	328.4
175°	330.9	330.7	330.5	330.3	330.2	330.1	329.9	329.8	329.7	330.1	330.6
177.5°	331.9	331.8	331.7	331.5	331.4	331.3	331.2	331.1	331.0	331.3	331.6
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7	331.7



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1204.5	1208.7	1210.7	1210.7	1213.0	1212.0	1211.0
5°	1273.7	1281.4	1283.1	1290.4	1295.6	1294.0	1294.8
7.5°	1342.6	1354.9	1367.1	1372.8	1373.6	1376.9	1378.1
10°	1385.0	1395.1	1414.1	1411.3	1425.4	1433.5	1420.1
12.5°	1425.8	1439.4	1452.5	1456.2	1464.3	1466.8	1461.6
15°	1462.6	1469.9	1470.7	1468.7	1471.1	1469.1	1461.4
17.5°	1428.1	1416.3	1392.4	1381.1	1372.1	1358.8	1353.5
20°	1371.2	1336.4	1296.0	1279.8	1260.8	1223.6	1232.6
22.5°	1248.3	1208.6	1168.2	1121.0	1098.4	1063.2	1061.0
25°	1057.0	988.7	913.5	860.9	830.2	795.0	779.7
27.5°	821.8	735.8	674.1	642.9	614.6	586.7	585.5
30°	667.2	602.5	554.8	528.1	510.7	499.0	501.5
32.5°	562.4	518.1	485.9	463.7	450.9	442.0	441.9
35°	459.8	429.4	408.8	399.5	390.2	383.7	384.1
37.5°	393.5	375.3	363.8	353.5	347.7	344.5	342.8
40°	359.5	344.5	335.6	329.5	324.7	320.3	319.5
42.5°	332.6	320.3	311.3	306.6	302.1	298.9	298.1
45°	295.2	285.1	277.0	271.7	269.7	266.9	266.9
47.5°	262.6	252.6	246.4	243.0	239.6	237.7	237.6
50°	240.6	232.9	227.3	225.2	222.4	221.2	220.8
52.5°	220.9	215.2	211.1	209.7	208.5	206.9	207.2
55°	194.1	190.8	189.3	188.1	186.0	183.5	185.2
57.5°	171.5	168.8	164.5	160.7	158.8	157.1	157.7
60°	155.7	150.0	144.3	139.9	138.7	135.1	135.1
62.5°	135.6	127.7	120.7	118.3	117.0	115.3	115.0
65°	104.3	101.1	99.5	97.8	97.0	97.0	96.3
67.5°	86.4	85.2	83.4	82.9	82.1	81.9	81.7
70°	76.4	74.8	74.0	73.6	72.8	73.2	72.0
72.5°	66.7	65.4	65.3	64.2	63.7	63.8	62.9
75°	52.6	52.6	52.1	51.7	50.9	50.5	50.9
77.5°	40.4	40.5	39.8	39.7	39.6	39.7	39.3
80°	32.3	32.7	32.3	31.9	31.5	31.9	31.5
82.5°	25.6	25.0	24.9	24.8	24.7	24.5	24.4
85°	14.6	15.0	14.6	14.2	14.2	14.2	14.6
87.5°	7.4	7.4	7.4	7.4	7.4	7.4	7.1
90°	9.4	9.3	9.3	9.3	9.4	9.4	9.5
92.5°	9.0	9.0	9.0	9.0	9.0	9.0	9.0
95°	17.9	17.9	17.8	17.7	17.6	17.5	17.3
97.5°	30.1	30.1	30.1	30.1	30.1	30.1	30.0
100°	38.7	38.7	38.6	38.5	38.5	38.4	38.3
102.5°	47.9	48.0	48.0	47.9	47.8	47.8	47.8
105°	61.9	62.1	62.1	62.1	62.1	62.1	62.1
107.5°	76.9	76.9	76.8	76.5	76.3	76.0	75.7
110°	87.1	87.1	87.0	86.7	86.6	86.4	86.2



TEST NUMBER: P331676-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	97.1	97.0	96.8	96.7	96.6	96.4	96.3
115°	112.9	112.8	112.7	112.5	112.3	112.2	111.9
117.5°	127.9	127.8	127.6	127.5	127.3	127.1	126.9
120°	138.2	138.2	138.2	138.0	137.8	137.6	137.4
122.5°	148.5	148.4	148.3	148.1	148.0	147.8	147.7
125°	164.0	163.8	163.7	163.7	163.6	163.5	163.4
127.5°	179.0	178.8	178.6	178.4	178.2	178.0	177.8
130°	189.4	189.3	189.1	188.9	188.5	188.3	188.1
132.5°	199.2	199.0	198.8	198.5	198.4	198.1	198.0
135°	214.2	214.1	214.0	213.8	213.7	213.5	213.3
137.5°	228.3	228.3	228.1	227.9	227.7	227.4	227.1
140°	237.9	237.9	237.7	237.5	237.3	237.0	236.8
142.5°	246.5	246.6	246.5	246.3	246.0	245.7	245.5
145°	259.6	259.7	259.6	259.4	259.1	258.9	258.6
147.5°	271.2	271.3	271.2	271.0	270.8	270.5	270.3
150°	278.5	278.7	278.7	278.5	278.3	278.1	277.9
152.5°	285.8	286.1	286.1	285.8	285.6	285.3	285.1
155°	295.1	295.4	295.5	295.2	295.1	294.9	294.7
157.5°	303.7	304.1	304.2	303.9	303.6	303.3	303.0
160°	308.7	309.1	309.1	308.9	308.6	308.4	308.2
162.5°	313.3	313.8	313.8	313.5	313.2	312.9	312.6
165°	319.2	319.6	319.7	319.4	319.1	318.8	318.5
167.5°	324.1	324.6	324.6	324.3	323.9	323.6	323.3
170°	326.8	327.3	327.3	326.9	326.5	326.1	325.7
172.5°	328.8	329.2	329.3	328.9	328.5	328.2	327.8
175°	331.0	331.4	331.4	331.1	330.7	330.3	329.9
177.5°	331.8	332.2	332.2	331.8	331.6	331.3	331.0
180°	331.7	331.7	331.7	331.7	331.7	331.7	331.7

(END OF REPORT)