

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331680-927

Luminaire Tested: **SA2XXRDIP-C675D330U927-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331680-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2852.1 lumens
Efficiency: N/A
Efficacy: 81.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331680-927
CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331680-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	91	91	91	80	80	80	69	69	69	64				
1	102	97	94	90	95	92	88	86	81	79	76	71	70	68	62	61	60	56				
2	93	86	80	75	87	81	76	71	72	68	64	63	60	58	56	53	51	48				
3	85	76	69	63	80	72	65	60	64	59	55	57	53	50	50	47	44	41				
4	78	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39	36				
5	72	61	53	47	68	58	50	45	52	46	41	46	41	38	41	37	34	31				
6	67	55	47	41	63	52	45	40	47	41	36	42	37	33	37	33	31	28				
7	62	50	42	36	58	47	40	35	43	37	32	38	34	30	34	30	27	25				
8	58	46	38	33	54	43	36	31	39	33	29	35	30	27	32	28	25	23				
9	54	42	34	29	51	40	33	28	36	30	26	33	28	24	29	25	23	21				
10	51	39	31	26	48	37	30	26	33	28	24	30	26	22	27	23	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14428	14428	14428
5°	14483	14248	14326
10°	14372	14014	13895
15°	14206	13600	13207
20°	13979	13005	12352
25°	13744	12332	11526
30°	13420	11639	10465
35°	13102	10886	9532
40°	12783	10108	8454
45°	12408	9232	7478
50°	12024	8349	6521
55°	11634	7398	5599
60°	11176	6397	4647
65°	10659	5375	4233
70°	10041	4428	3895
75°	9283	4036	3631
80°	8201	3608	3310
85°	6447	2853	2853



TEST NUMBER: P331680-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.6	2.9
10°-20°	229.7	8.1
20°-30°	322.5	11.3
30°-40°	351.7	12.3
40°-50°	323.4	11.3
50°-60°	254.0	8.9
60°-70°	165.6	5.8
70°-80°	85.4	3.0
80°-90°	23.5	0.8
90°-100°	58.2	2.0
100°-110°	197.5	6.9
110°-120°	209.8	7.4
120°-130°	172.7	6.1
130°-140°	138.7	4.9
140°-150°	104.8	3.7
150°-160°	73.7	2.6
160°-170°	43.4	1.5
170°-180°	14.1	0.5
0°-30°	635.8	22.3
0°-40°	987.5	34.6
0°-60°	1564.8	54.9
0°-90°	1839.3	64.5
90°-120°	465.5	16.3
90°-150°	881.7	30.9
90°-180°	1013.0	35.5
0°-180°	2852.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	894	894	894	894	894	
5°	894	889	879	886	884	85
15°	850	840	814	799	790	239
25°	772	744	692	660	647	355
35°	665	622	552	503	484	416
45°	543	488	404	349	328	419
55°	413	349	263	216	199	369
65°	279	213	141	115	111	277
75°	149	94	65	59	58	158
85°	35	19	15	15	15	41
90°	0	4	10	9	9	2
95°	10	24	110	41	32	10
105°	34	52	207	371	315	36
115°	60	76	174	358	415	60
125°	84	99	167	290	337	75
135°	98	118	165	244	279	76
145°	112	129	164	204	223	71
155°	128	138	159	180	187	59
165°	139	144	153	162	164	39
175°	145	145	147	148	148	14
180°	146	146	146	146	146	



TEST NUMBER: P331680-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	896.8	896.1	895.4	894.7	894.0	892.8	891.2	889.6	888.1	886.5	888.0
5°	893.6	892.7	891.8	890.9	890.0	888.4	886.1	883.8	881.4	879.1	880.7
7.5°	884.4	883.3	882.2	881.1	880.0	878.0	875.3	872.6	869.8	867.1	867.5
10°	876.6	875.4	874.1	872.8	871.6	869.2	865.5	862.0	858.4	854.8	854.3
12.5°	866.9	865.4	863.8	862.3	860.7	857.7	853.1	848.5	843.8	839.2	838.3
15°	849.9	848.0	846.0	844.0	842.0	838.0	831.9	825.8	819.7	813.6	810.2
17.5°	829.1	826.1	823.1	820.0	817.0	811.6	803.7	795.9	788.1	780.2	776.2
20°	813.6	809.9	806.4	802.8	799.2	792.9	783.9	774.9	766.0	756.9	752.4
22.5°	796.7	792.7	788.7	784.7	780.6	773.6	763.4	753.3	743.1	733.0	727.2
25°	771.5	765.7	760.0	754.2	748.5	739.7	727.9	716.0	704.1	692.2	684.8
27.5°	741.1	734.8	728.6	722.3	716.1	706.2	692.9	679.5	666.1	652.8	644.2
30°	719.8	712.9	706.1	699.3	692.4	681.8	667.4	653.1	638.7	624.3	615.1
32.5°	699.0	691.0	683.1	675.1	667.1	655.8	641.1	626.5	611.8	597.1	586.7
35°	664.7	655.6	646.4	637.2	628.1	615.6	599.8	584.0	568.2	552.3	541.0
37.5°	630.5	620.4	610.3	600.2	590.2	576.7	559.9	543.0	526.2	509.3	496.9
40°	606.5	595.7	584.9	574.2	563.4	549.3	531.9	514.4	497.0	479.6	466.8
42.5°	581.9	570.6	559.2	547.9	536.5	521.8	503.8	485.8	467.8	449.8	436.6
45°	543.4	531.4	519.4	507.3	495.3	479.8	461.0	442.1	423.2	404.3	391.6
47.5°	505.9	493.1	480.4	467.6	454.9	438.8	419.3	399.8	380.3	360.8	348.2
50°	478.7	466.0	453.2	440.5	427.7	411.5	391.7	371.9	352.1	332.4	320.0
52.5°	452.3	438.9	425.6	412.3	398.9	382.5	363.2	343.9	324.6	305.2	293.3
55°	413.3	399.3	385.2	371.2	357.2	340.5	321.1	301.7	282.3	262.8	252.1
57.5°	373.3	358.9	344.5	330.2	315.8	299.3	280.6	262.0	243.3	224.7	214.8
60°	346.1	331.8	317.3	303.0	288.6	272.2	253.7	235.1	216.7	198.1	188.9
62.5°	319.6	305.2	290.8	276.5	262.1	246.1	228.5	210.8	193.1	175.5	166.8
65°	279.0	264.4	249.9	235.4	220.8	205.4	189.3	173.1	156.9	140.7	134.6
67.5°	239.9	225.4	211.0	196.5	182.0	167.5	153.0	138.5	123.9	109.3	106.5
70°	212.7	198.7	184.7	170.6	156.6	143.4	131.0	118.6	106.2	93.8	92.0
72.5°	186.8	173.3	159.9	146.5	133.0	121.4	111.4	101.4	91.5	81.5	80.0
75°	148.8	136.3	123.7	111.1	98.5	89.1	83.0	76.9	70.8	64.7	63.5
77.5°	111.5	100.4	89.4	78.3	67.3	60.3	57.4	54.4	51.5	48.6	47.8
80°	88.2	79.0	69.8	60.7	51.5	46.0	44.2	42.4	40.6	38.8	38.1
82.5°	66.8	59.7	52.5	45.3	38.2	34.0	32.8	31.5	30.3	29.2	28.7
85°	34.8	31.0	27.3	23.4	19.6	17.5	17.0	16.5	15.9	15.4	15.4
87.5°	10.4	9.4	8.5	7.4	6.4	6.0	6.3	6.7	7.1	7.1	6.9
90°	0.3	1.1	2.2	2.8	3.3	4.2	5.6	7.5	9.3	9.5	9.3
92.5°	3.4	4.9	7.0	8.2	10.1	12.7	19.0	28.0	35.9	36.4	30.7
95°	9.8	10.9	13.7	16.2	20.7	27.4	40.3	64.6	97.1	109.7	96.0
97.5°	15.9	17.4	20.4	24.2	29.4	37.0	53.2	87.1	141.1	187.3	196.5
100°	21.5	22.4	24.9	29.4	35.0	42.9	57.7	91.8	152.3	221.1	261.4
102.5°	26.7	27.3	29.9	34.3	40.2	48.0	61.7	92.1	148.0	222.2	285.6
105°	34.1	35.3	37.2	41.4	47.6	55.5	68.6	93.5	139.7	207.4	281.9
107.5°	42.2	43.1	45.0	48.9	55.0	62.9	75.7	97.4	135.5	191.5	257.3
110°	47.6	48.7	50.4	54.0	59.9	68.0	80.3	100.4	134.7	183.9	241.9



TEST NUMBER: P331680-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	52.5	53.6	55.5	58.9	64.6	73.0	84.8	103.9	134.8	179.0	231.1
115°	60.2	61.6	63.3	66.6	72.2	79.8	91.8	108.8	136.0	173.6	217.8
117.5°	68.1	69.2	70.9	73.9	79.3	87.1	98.2	114.2	138.1	170.9	209.4
120°	73.0	74.1	75.9	78.3	84.0	91.8	102.7	117.9	139.4	169.4	204.9
122.5°	77.8	78.7	80.3	83.1	88.6	96.7	106.9	121.0	140.9	168.4	201.1
125°	84.0	84.8	86.5	89.8	95.5	103.3	113.4	126.0	143.3	166.8	195.7
127.5°	88.9	90.0	92.4	96.1	101.4	109.5	119.3	130.6	145.7	165.9	190.6
130°	91.8	92.9	95.7	99.7	105.3	113.0	122.9	133.5	147.5	165.4	187.3
132.5°	94.5	95.9	98.9	103.0	108.8	116.7	126.0	136.4	149.3	165.2	184.6
135°	98.5	99.7	103.0	107.2	113.7	121.4	130.5	140.2	151.5	164.9	180.8
137.5°	102.3	103.7	107.0	111.5	117.9	125.2	134.0	143.1	153.4	164.8	178.2
140°	105.3	106.4	109.7	114.2	120.3	127.6	136.0	144.7	154.2	164.6	176.6
142.5°	108.1	109.1	112.2	116.7	122.6	129.4	137.6	146.1	154.9	164.6	175.1
145°	112.5	113.7	116.5	120.6	126.3	132.4	140.0	147.8	155.6	164.0	173.0
147.5°	117.2	118.0	120.7	124.6	129.3	134.8	141.9	148.8	155.8	163.0	170.9
150°	120.3	121.2	123.4	127.1	131.3	136.3	142.8	149.2	155.6	162.3	169.1
152.5°	123.5	123.9	126.1	129.3	133.3	137.8	143.6	149.4	155.2	161.2	167.5
155°	127.9	128.2	129.8	132.9	136.0	140.2	145.0	149.7	154.5	159.2	164.6
157.5°	131.6	131.9	133.2	135.9	138.4	141.9	145.9	149.7	153.2	157.2	161.8
160°	134.0	134.4	135.5	137.7	140.0	143.1	146.4	149.7	152.6	155.9	159.8
162.5°	136.6	136.3	137.5	139.3	141.3	143.7	146.6	149.5	151.9	154.8	158.0
165°	139.4	139.1	139.7	141.3	142.8	144.4	146.9	148.9	150.6	152.6	155.0
167.5°	141.7	141.4	141.9	143.0	144.0	145.0	146.9	148.5	149.3	150.6	152.2
170°	143.3	142.8	143.1	143.9	144.4	145.3	146.6	148.1	148.6	149.5	150.6
172.5°	144.2	143.9	143.7	144.6	144.9	145.5	146.5	147.4	147.7	148.1	149.0
175°	145.3	145.0	144.7	145.3	145.3	145.5	146.1	146.6	146.4	146.6	146.9
177.5°	145.8	145.3	145.1	145.5	145.5	145.5	145.8	146.2	145.8	145.5	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5



TEST NUMBER: P331680-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	893.6	893.6	893.6	893.6	893.6	893.6	893.6	893.6
2.5°	889.4	890.8	892.2	892.8	892.6	892.2	892.0	891.7
5°	882.3	883.9	885.5	886.1	885.5	884.9	884.5	883.9
7.5°	868.0	868.5	868.9	868.7	867.8	866.9	865.9	865.0
10°	853.7	853.2	852.6	851.8	850.7	849.7	848.6	847.5
12.5°	837.3	836.4	835.4	834.0	832.2	830.4	828.6	826.8
15°	806.8	803.3	799.9	797.3	795.5	793.7	791.9	790.1
17.5°	772.1	768.0	764.0	760.4	757.3	754.2	751.1	748.1
20°	748.0	743.5	738.9	734.7	730.8	726.8	722.9	718.9
22.5°	721.4	715.7	709.9	705.5	702.5	699.6	696.6	693.7
25°	677.5	670.1	662.7	657.7	655.1	652.4	649.7	647.0
27.5°	635.6	627.0	618.5	612.0	607.7	603.4	599.1	594.8
30°	606.0	596.8	587.6	580.7	575.8	570.9	566.1	561.3
32.5°	576.2	565.8	555.3	547.8	543.2	538.7	534.1	529.6
35°	529.7	518.4	507.1	499.4	495.4	491.5	487.6	483.6
37.5°	484.3	471.9	459.5	450.9	446.4	441.9	437.4	432.8
40°	454.0	441.2	428.5	419.8	415.1	410.4	405.8	401.1
42.5°	423.4	410.2	397.0	388.2	383.7	379.1	374.6	370.0
45°	378.8	366.1	353.3	344.8	340.5	336.1	331.8	327.5
47.5°	335.5	322.8	310.1	301.8	297.9	294.0	290.0	286.1
50°	307.6	295.2	282.8	274.6	270.9	267.1	263.4	259.6
52.5°	281.3	269.3	257.3	249.6	246.1	242.6	239.2	235.7
55°	241.3	230.4	219.7	212.6	209.2	205.7	202.3	198.9
57.5°	204.9	195.0	185.1	178.7	175.9	173.0	170.1	167.2
60°	179.8	170.6	161.4	155.4	152.6	149.7	146.8	143.9
62.5°	158.0	149.2	140.5	135.3	133.6	131.9	130.2	128.4
65°	128.5	122.4	116.3	113.0	112.4	111.9	111.3	110.8
67.5°	103.7	100.9	98.2	96.4	95.9	95.3	94.7	94.1
70°	90.2	88.4	86.6	85.4	84.6	83.9	83.2	82.5
72.5°	78.5	77.0	75.5	74.5	74.1	73.7	73.2	72.8
75°	62.2	60.9	59.7	58.9	58.8	58.6	58.4	58.2
77.5°	47.1	46.3	45.6	45.2	44.8	44.6	44.3	44.0
80°	37.4	36.7	36.0	35.6	35.6	35.6	35.6	35.6
82.5°	28.3	27.8	27.4	27.2	27.2	27.2	27.2	27.2
85°	15.4	15.4	15.4	15.4	15.4	15.4	15.4	15.4
87.5°	6.7	6.4	6.4	6.3	6.3	6.3	6.3	6.3
90°	9.0	8.4	9.0	9.3	9.3	9.3	9.3	9.3
92.5°	24.4	20.9	18.6	16.9	16.6	15.8	15.9	15.5
95°	73.4	56.2	44.5	38.3	34.7	32.5	31.6	31.9
97.5°	171.1	140.0	109.7	89.5	76.1	69.2	65.2	62.8
100°	255.6	220.9	182.5	148.6	125.4	113.4	105.3	100.2
102.5°	310.9	303.0	275.0	239.1	213.8	193.3	183.2	176.3
105°	340.1	371.7	375.3	366.1	348.7	331.4	319.3	315.4
107.5°	319.0	366.7	395.8	409.3	411.5	410.6	408.1	403.0
110°	300.9	351.0	386.8	409.8	421.8	427.1	429.7	429.4



TEST NUMBER: P331680-927

CATALOG NUMBER: SA2XXRDIP-C675D330U927-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	284.3	332.4	370.7	397.0	413.8	422.6	427.4	428.9
115°	264.0	307.0	343.7	372.6	392.4	405.3	412.6	415.1
117.5°	248.6	286.5	319.7	346.7	367.0	380.6	388.2	390.4
120°	241.0	275.7	305.4	330.8	350.5	363.6	371.7	374.5
122.5°	235.0	266.7	294.9	317.8	335.4	348.4	355.6	357.9
125°	226.2	255.0	279.6	300.6	316.9	327.5	334.5	336.8
127.5°	217.5	243.6	266.8	286.1	300.3	310.3	316.3	318.1
130°	211.9	236.0	258.1	276.6	290.3	299.8	305.4	307.6
132.5°	206.5	228.8	249.1	266.5	280.0	289.5	294.6	296.7
135°	199.0	217.5	236.0	251.6	263.6	272.9	278.0	279.1
137.5°	193.1	208.5	223.2	236.8	247.8	255.7	260.2	261.8
140°	189.2	202.6	215.6	227.8	236.8	244.1	248.3	249.9
142.5°	186.1	197.5	208.6	218.9	227.4	234.0	237.7	238.1
145°	181.6	190.9	199.6	207.7	214.4	219.2	222.0	222.8
147.5°	178.2	185.5	192.3	198.2	203.7	207.6	209.5	210.0
150°	175.8	182.0	187.8	192.8	197.0	200.4	202.1	202.4
152.5°	173.3	179.0	184.0	188.4	191.7	194.6	195.8	195.9
155°	169.9	174.4	178.6	181.6	184.7	186.7	187.8	187.3
157.5°	166.0	169.7	173.2	175.6	177.8	179.4	179.9	179.9
160°	163.4	166.5	169.6	171.6	173.6	174.9	175.2	175.2
162.5°	161.0	163.7	166.3	167.8	169.8	170.7	171.0	170.7
165°	157.3	159.2	161.2	162.3	163.4	164.6	164.6	164.3
167.5°	153.8	155.3	156.6	157.6	158.1	158.8	158.7	158.4
170°	152.0	152.8	153.9	154.5	154.8	155.6	155.3	154.8
172.5°	150.0	150.6	151.5	151.8	152.1	152.5	152.2	151.9
175°	147.8	148.1	148.4	148.6	148.6	148.9	148.6	148.1
177.5°	146.2	146.2	146.5	146.5	146.5	146.5	146.2	145.8
180°	145.5	145.5	145.5	145.5	145.5	145.5	145.5	145.5

(END OF REPORT)