

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331695-927

Luminaire Tested: **SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331695-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4875.9 lumens
Efficiency: N/A
Efficacy: 93.8 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 52
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331695-927
CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41
1	96	92	89	86	88	85	81	79	70	68	66	56	55	53	43	43	42	36
2	88	81	76	71	80	75	70	66	62	58	55	50	48	46	39	38	36	31
3	81	72	65	60	74	66	60	56	55	51	47	45	42	39	35	33	32	27
4	74	64	57	51	68	59	53	48	49	45	41	40	37	34	32	30	28	24
5	69	58	50	44	63	53	47	42	45	40	36	37	33	30	29	27	25	21
6	63	52	44	39	58	48	41	36	40	35	32	33	30	27	27	24	22	19
7	59	47	40	34	54	44	37	32	37	32	28	31	27	24	25	22	20	17
8	55	43	36	31	50	40	33	29	34	29	25	28	24	22	23	20	18	16
9	51	39	32	27	47	37	30	26	31	26	23	26	22	20	21	19	17	15
10	48	36	29	25	44	34	28	23	29	24	21	24	21	18	20	17	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	18791	18791	18791	18791
5°	20985	18908	16765	18908
10°	23282	18775	14532	18775
15°	24428	18501	11450	18501
20°	21179	18093	9907	18093
25°	13890	17533	8845	17533
30°	9350	16858	8006	16858
35°	7571	16005	7222	16005
40°	6734	15076	6681	15076
45°	6094	13988	5966	13988
50°	5546	12911	5526	12911
55°	5213	11713	5146	11713
60°	4363	10618	4308	10618
65°	3679	9639	4172	9639
70°	3399	8611	3932	8611
75°	3175	7492	3631	7492
80°	2929	6165	3236	6165
85°	2705	4872	2853	4872



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.3	2.3
10°-20°	307.4	6.3
20°-30°	396.1	8.1
30°-40°	376.4	7.7
40°-50°	322.5	6.6
50°-60°	245.6	5.0
60°-70°	155.2	3.2
70°-80°	77.5	1.6
80°-90°	23.9	0.5
90°-100°	164.4	3.4
100°-110°	557.8	11.4
110°-120°	592.6	12.2
120°-130°	487.8	10.0
130°-140°	391.8	8.0
140°-150°	296.0	6.1
150°-160°	208.1	4.3
160°-170°	122.5	2.5
170°-180°	39.9	0.8
0°-30°	813.8	16.7
0°-40°	1190.3	24.4
0°-60°	1758.3	36.1
0°-90°	2015.0	41.3
90°-120°	1314.8	27.0
90°-150°	2490.5	51.1
90°-180°	2861.0	58.7
0°-180°	4875.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1164	1164	1164	1164	1164	
5°	1295	1167	1034	1167	1295	128
15°	1461	1107	685	1107	1461	394
25°	780	984	496	984	780	370
35°	384	812	366	812	384	246
45°	267	613	261	613	267	207
55°	185	416	183	416	185	163
65°	96	252	109	252	96	98
75°	51	120	58	120	51	54
85°	15	26	15	26	15	16
90°	26	1	26	1	26	15
95°	90	28	90	28	90	117
105°	891	96	891	96	891	862
115°	1172	170	1172	170	1172	1148
125°	951	237	951	237	951	859
135°	788	278	788	278	788	612
145°	629	318	629	318	629	400
155°	529	361	529	361	529	247
165°	464	394	464	394	464	133
175°	418	410	418	410	418	41
180°	411	411	411	411	411	



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1211.0	1212.0	1213.0	1210.7	1210.7	1208.7	1204.5	1201.3	1192.2	1191.0	1191.0
5°	1294.8	1294.0	1295.6	1290.4	1283.1	1281.4	1273.7	1263.7	1253.2	1241.4	1239.0
7.5°	1378.1	1376.9	1373.6	1372.8	1367.1	1354.9	1342.6	1329.4	1311.9	1294.9	1286.3
10°	1420.1	1433.5	1425.4	1411.3	1414.1	1395.1	1385.0	1367.6	1353.0	1327.5	1321.9
12.5°	1461.6	1466.8	1464.3	1456.2	1452.5	1439.4	1425.8	1410.6	1383.8	1360.9	1341.0
15°	1461.4	1469.1	1471.1	1468.7	1470.7	1469.9	1462.6	1450.1	1426.6	1401.5	1379.7
17.5°	1353.5	1358.8	1372.1	1381.1	1392.4	1416.3	1428.1	1432.7	1429.3	1415.0	1399.6
20°	1232.6	1223.6	1260.8	1279.8	1296.0	1336.4	1371.2	1384.6	1406.0	1405.6	1401.5
22.5°	1061.0	1063.2	1098.4	1121.0	1168.2	1208.6	1248.3	1298.5	1340.0	1367.4	1383.5
25°	779.7	795.0	830.2	860.9	913.5	988.7	1057.0	1136.3	1211.1	1270.1	1326.4
27.5°	585.5	586.7	614.6	642.9	674.1	735.8	821.8	916.5	1023.1	1111.1	1212.4
30°	501.5	499.0	510.7	528.1	554.8	602.5	667.2	760.3	866.6	999.2	1117.3
32.5°	441.9	442.0	450.9	463.7	485.9	518.1	562.4	637.9	738.5	868.9	1007.3
35°	384.1	383.7	390.2	399.5	408.8	429.4	459.8	499.4	568.5	690.2	831.8
37.5°	342.8	344.5	347.7	353.5	363.8	375.3	393.5	420.1	469.3	541.3	660.3
40°	319.5	320.3	324.7	329.5	335.6	344.5	359.5	380.9	416.9	474.4	561.3
42.5°	298.1	298.9	302.1	306.6	311.3	320.3	332.6	351.2	380.3	425.2	496.9
45°	266.9	266.9	269.7	271.7	277.0	285.1	295.2	310.5	330.8	363.9	411.6
47.5°	237.6	237.7	239.6	243.0	246.4	252.6	262.6	275.1	289.9	315.5	356.2
50°	220.8	221.2	222.4	225.2	227.3	232.9	240.6	251.5	266.9	286.7	320.7
52.5°	207.2	206.9	208.5	209.7	211.1	215.2	220.9	230.5	244.2	261.5	289.6
55°	185.2	183.5	186.0	188.1	189.3	190.8	194.1	200.2	211.9	226.5	247.5
57.5°	157.7	157.1	158.8	160.7	164.5	168.8	171.5	175.4	181.5	191.9	212.8
60°	135.1	135.1	138.7	139.9	144.3	150.0	155.7	158.9	165.0	171.8	187.2
62.5°	115.0	115.3	117.0	118.3	120.7	127.7	135.6	142.8	148.5	155.0	165.2
65°	96.3	97.0	97.0	97.8	99.5	101.1	104.3	110.0	120.1	129.4	137.0
67.5°	81.7	81.9	82.1	82.9	83.4	85.2	86.4	89.0	91.3	100.1	109.6
70°	72.0	73.2	72.8	73.6	74.0	74.8	76.4	77.6	81.3	83.3	89.0
72.5°	62.9	63.8	63.7	64.2	65.3	65.4	66.7	68.0	70.3	72.0	75.0
75°	50.9	50.5	50.9	51.7	52.1	52.6	52.6	54.2	55.4	57.0	59.0
77.5°	39.3	39.7	39.6	39.7	39.8	40.5	40.4	41.2	42.4	43.2	44.1
80°	31.5	31.9	31.5	31.9	32.3	32.7	32.3	32.7	34.0	34.8	34.8
82.5°	24.4	24.5	24.7	24.8	24.9	25.0	25.6	25.7	26.5	26.4	26.7
85°	14.6	14.2	14.2	14.2	14.6	15.0	14.6	14.6	15.0	15.0	15.0
87.5°	10.4	10.7	10.7	10.7	10.7	10.5	10.2	10.9	10.7	11.2	10.7
90°	26.1	26.1	26.1	26.1	26.1	25.3	23.7	25.3	26.1	26.9	26.1
92.5°	43.8	45.1	44.4	47.0	47.6	52.5	59.2	68.9	86.8	102.7	101.3
95°	90.2	89.4	91.7	98.1	108.3	125.7	158.9	207.2	271.2	309.9	274.3
97.5°	177.4	184.0	195.6	215.1	252.9	309.9	395.5	483.4	555.0	529.1	398.5
100°	283.0	297.3	320.2	354.2	419.9	515.5	623.8	721.8	738.5	624.6	430.1
102.5°	498.1	517.4	546.0	604.0	675.3	776.7	856.0	878.1	806.8	627.7	418.1
105°	891.0	902.1	936.1	985.1	1034.1	1060.3	1050.0	960.6	796.1	585.8	394.5
107.5°	1138.2	1152.9	1159.7	1162.4	1156.2	1117.9	1035.7	901.2	726.7	541.0	382.8
110°	1212.8	1213.6	1206.5	1191.4	1157.5	1092.7	991.4	849.9	683.1	519.4	380.3



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1211.6	1207.3	1193.8	1168.7	1121.4	1047.1	939.0	803.1	652.8	505.5	380.9
115°	1172.5	1165.4	1144.8	1108.4	1052.3	970.9	867.3	745.5	615.1	490.2	384.2
117.5°	1102.7	1096.8	1075.1	1036.6	979.5	903.0	809.1	702.2	591.4	482.8	389.9
120°	1057.9	1050.0	1027.0	989.8	934.5	862.5	778.8	680.7	578.8	478.3	393.7
122.5°	1011.1	1004.4	984.0	947.5	897.9	832.8	753.4	663.6	568.0	475.8	398.2
125°	951.1	944.8	925.0	895.0	849.1	789.8	720.3	638.8	552.6	471.2	404.8
127.5°	898.7	893.6	876.5	848.3	808.3	753.6	688.0	614.3	538.4	468.5	411.6
130°	868.9	862.5	846.8	819.9	781.2	729.0	666.5	598.5	528.9	467.2	416.7
132.5°	837.9	832.2	817.7	790.8	752.7	703.6	646.3	583.3	521.3	466.6	421.7
135°	788.2	785.1	770.9	744.7	710.7	666.5	614.3	562.1	510.7	465.6	427.7
137.5°	739.6	734.8	722.3	699.9	668.8	630.3	588.8	545.2	503.3	465.5	433.1
140°	706.0	701.3	689.4	668.8	643.6	608.8	572.4	534.5	498.9	464.9	435.6
142.5°	672.5	671.5	661.0	642.3	618.3	589.1	557.9	525.6	494.5	464.9	437.5
145°	629.3	626.9	619.1	605.6	586.6	563.7	539.2	513.1	488.6	463.3	439.6
147.5°	593.1	591.7	586.3	575.6	559.9	543.1	524.0	503.4	482.6	460.5	440.2
150°	571.6	570.8	566.1	556.6	544.7	530.5	513.9	496.5	477.5	458.6	439.6
152.5°	553.3	553.1	549.6	541.4	532.1	519.8	505.6	489.6	473.1	455.4	438.3
155°	528.9	530.5	527.4	521.8	513.1	504.4	492.6	479.9	464.9	449.9	436.4
157.5°	508.2	508.2	506.8	502.2	496.1	489.3	479.3	468.7	457.2	444.2	432.8
160°	495.0	495.0	494.2	490.2	484.7	479.1	470.4	461.7	451.5	440.4	430.9
162.5°	482.3	482.9	482.1	479.4	473.9	469.6	462.2	454.8	446.4	437.2	429.0
165°	464.1	464.9	464.9	461.7	458.6	455.4	449.9	444.3	438.0	430.9	425.3
167.5°	447.3	448.3	448.5	446.7	445.3	442.4	438.6	434.4	429.8	425.3	421.7
170°	437.2	438.8	439.6	437.2	436.4	434.8	431.7	429.3	425.3	422.2	419.9
172.5°	429.0	429.9	430.7	429.6	428.8	427.9	425.3	423.6	421.0	418.4	417.3
175°	418.3	419.9	420.6	419.9	419.9	419.1	418.3	417.5	415.1	414.3	413.5
177.5°	411.8	413.0	413.7	413.7	413.7	413.7	413.0	413.0	411.8	411.1	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1191.6	1189.0	1186.8	1180.9	1178.1	1171.6	1170.6	1170.3	1161.8	1153.7	1151.5
5°	1232.6	1226.1	1216.3	1205.0	1193.3	1181.1	1173.1	1166.6	1150.4	1135.0	1126.2
7.5°	1273.7	1259.9	1243.1	1221.7	1203.8	1183.8	1168.9	1155.6	1132.6	1110.6	1095.7
10°	1304.5	1281.8	1259.6	1230.1	1207.0	1184.4	1163.4	1145.2	1119.3	1090.2	1069.5
12.5°	1323.6	1298.7	1268.0	1239.1	1209.3	1180.5	1152.4	1129.0	1098.6	1068.5	1044.0
15°	1349.4	1322.7	1285.5	1244.3	1205.9	1168.2	1135.9	1106.8	1067.1	1031.2	1001.2
17.5°	1370.5	1333.8	1293.8	1246.1	1201.7	1153.8	1112.1	1075.0	1030.9	987.5	952.2
20°	1377.3	1340.9	1294.8	1247.1	1194.5	1138.3	1093.4	1053.0	1005.7	958.4	917.9
22.5°	1373.1	1344.8	1293.5	1236.4	1182.6	1123.7	1073.0	1026.1	973.7	925.3	878.5
25°	1344.6	1334.8	1286.3	1224.0	1162.6	1094.2	1035.6	984.2	924.4	872.7	821.7
27.5°	1277.9	1298.9	1268.8	1202.5	1134.2	1060.9	995.0	936.5	874.4	816.2	765.4
30°	1213.9	1262.0	1249.1	1187.6	1111.2	1039.3	965.3	904.2	837.9	778.0	727.9
32.5°	1126.2	1205.8	1218.4	1167.0	1087.9	1008.8	931.3	870.5	801.3	738.2	689.4
35°	986.7	1105.6	1160.2	1127.4	1048.1	962.8	882.7	812.0	742.4	680.2	631.6
37.5°	820.1	982.1	1073.0	1075.4	1002.6	913.9	826.7	756.5	685.2	624.1	571.6
40°	712.1	887.6	1006.1	1032.4	970.9	875.0	786.9	715.3	645.8	585.9	525.7
42.5°	615.1	789.9	935.6	981.3	932.4	837.2	748.8	673.9	606.3	549.7	488.1
45°	497.4	650.2	810.8	892.5	865.4	777.2	683.8	612.6	549.1	500.2	441.2
47.5°	419.5	527.3	682.6	793.1	792.7	712.2	620.3	552.2	493.3	447.4	399.6
50°	375.3	469.1	600.5	725.9	736.3	668.8	581.5	514.0	459.0	410.8	372.4
52.5°	335.5	412.8	530.9	651.1	681.0	622.6	537.8	475.5	422.1	377.9	344.9
55°	283.4	343.3	433.1	545.5	590.8	549.5	474.4	416.1	372.8	335.6	307.3
57.5°	239.8	284.7	356.7	447.3	499.9	474.0	411.9	364.6	327.6	294.0	271.6
60°	212.3	249.1	310.1	385.8	444.0	425.8	372.8	328.8	297.2	268.1	247.1
62.5°	186.4	218.0	270.4	331.8	385.2	377.6	334.3	297.4	269.7	243.2	225.4
65°	150.0	173.1	213.9	262.1	304.9	308.6	277.4	252.3	227.7	206.6	190.8
67.5°	119.5	134.5	163.3	203.8	235.9	247.4	228.4	209.2	189.6	173.4	159.7
70°	100.7	112.8	133.9	166.6	196.1	208.3	197.3	182.4	165.4	152.0	140.3
72.5°	81.6	93.4	108.9	132.9	158.3	171.3	167.5	156.9	143.1	132.0	120.9
75°	61.5	65.1	75.7	91.8	111.6	122.9	125.8	120.1	109.2	100.7	94.2
77.5°	45.5	47.6	52.7	61.2	74.1	84.2	88.3	87.7	80.2	75.2	69.2
80°	36.4	37.6	40.0	43.6	53.4	63.5	66.3	66.3	61.1	59.0	53.0
82.5°	27.6	28.5	30.0	32.0	36.5	45.4	48.6	49.2	45.9	43.2	38.4
85°	15.8	15.4	16.2	17.3	18.2	20.6	25.5	26.3	25.5	22.3	21.0
87.5°	9.7	9.0	8.2	7.4	7.4	7.4	8.4	9.5	8.7	8.4	8.1
90°	21.3	15.8	11.9	9.5	7.9	6.3	3.2	0.8	3.2	6.3	7.9
92.5°	78.9	53.8	35.9	28.4	23.1	19.6	13.9	9.7	13.9	19.6	23.1
95°	182.6	113.8	77.5	58.5	45.9	38.7	30.8	27.6	30.8	38.7	45.9
97.5°	246.1	150.2	104.5	83.0	68.4	57.8	49.4	45.1	49.4	57.8	68.4
100°	259.4	162.9	121.0	98.9	83.0	70.3	63.2	60.8	63.2	70.3	83.0
102.5°	260.0	174.3	135.5	113.4	97.0	84.3	77.2	75.4	77.2	84.3	97.0
105°	264.0	193.7	156.5	134.4	117.0	105.1	99.7	96.5	99.7	105.1	117.0
107.5°	275.0	213.7	177.6	155.3	138.1	127.1	121.8	119.2	121.8	127.1	138.1
110°	283.8	226.9	192.1	169.2	152.6	142.3	137.6	134.4	137.6	142.3	152.6



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	293.3	239.6	206.0	182.4	166.5	156.9	151.5	148.3	151.5	156.9	166.5
115°	307.5	259.4	225.3	204.0	188.1	178.7	174.0	170.0	174.0	178.7	188.1
117.5°	322.7	277.5	246.1	223.9	208.7	200.3	195.6	192.4	195.6	200.3	208.7
120°	332.9	290.2	259.4	237.2	221.3	214.3	209.5	206.4	209.5	214.3	221.3
122.5°	341.7	302.1	273.2	250.5	234.6	226.9	222.1	219.7	222.1	226.9	234.6
125°	355.8	320.2	291.8	269.6	253.8	244.3	239.6	237.2	239.6	244.3	253.8
127.5°	368.9	337.0	309.3	286.5	271.3	260.9	254.3	251.1	254.3	260.9	271.3
130°	377.2	347.1	319.4	297.3	281.5	270.4	262.4	259.4	262.4	270.4	281.5
132.5°	385.3	355.9	329.5	307.4	291.0	279.2	270.7	266.9	270.7	279.2	291.0
135°	396.1	368.4	343.1	321.0	302.8	291.0	281.5	278.3	281.5	291.0	302.8
137.5°	404.3	378.6	353.6	333.0	315.0	302.3	292.9	289.1	292.9	302.3	315.0
140°	408.8	384.2	360.5	340.0	322.6	309.9	300.5	297.3	300.5	309.9	322.6
142.5°	412.6	388.6	365.6	346.3	329.5	316.9	308.0	305.5	308.0	316.9	329.5
145°	417.5	395.3	374.0	356.6	340.8	328.9	321.0	317.8	321.0	328.9	340.8
147.5°	420.2	400.7	380.6	365.1	352.0	341.0	333.5	331.1	333.5	341.0	352.0
150°	421.4	403.2	385.0	370.8	358.9	348.6	342.3	340.0	342.3	348.6	358.9
152.5°	422.0	405.8	389.4	376.5	365.3	356.2	349.9	348.8	349.9	356.2	365.3
155°	422.9	409.6	396.1	384.2	375.6	366.9	362.1	361.3	362.1	366.9	375.6
157.5°	422.9	412.3	400.8	390.9	383.9	376.4	372.6	371.8	372.6	376.4	383.9
160°	422.9	413.5	404.0	395.3	389.0	382.6	379.5	378.7	379.5	382.6	389.0
162.5°	422.3	414.2	405.9	399.1	393.4	388.3	385.2	385.6	385.2	388.3	393.4
165°	420.6	415.1	408.0	403.2	399.3	394.5	392.9	393.7	392.9	394.5	399.3
167.5°	419.5	414.9	409.7	406.7	403.9	400.8	399.4	400.4	399.4	400.8	403.9
170°	418.3	414.3	410.4	408.0	406.4	404.0	403.2	404.8	403.2	404.0	406.4
172.5°	416.4	413.7	411.0	409.2	408.3	405.9	406.4	407.3	406.4	405.9	408.3
175°	414.3	412.7	411.1	410.4	410.4	408.8	409.6	410.4	409.6	408.8	410.4
177.5°	413.0	411.8	411.1	411.1	411.1	409.9	410.5	411.8	410.5	409.9	411.1
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1147.3	1145.0	1140.8	1134.3	1130.4	1123.6	1119.1	1121.7	1122.4	1121.7	1121.1
5°	1116.5	1107.9	1096.2	1084.9	1074.4	1063.1	1056.6	1053.8	1048.1	1044.9	1043.3
7.5°	1079.2	1064.5	1048.0	1028.3	1011.5	994.0	985.0	980.5	968.9	962.7	957.1
10°	1051.4	1028.3	1011.8	985.9	970.1	947.1	931.3	931.7	915.9	907.0	900.6
12.5°	1020.6	995.3	967.7	944.4	922.5	904.0	885.0	877.3	860.5	852.0	834.6
15°	969.7	940.2	911.1	879.5	857.3	828.5	801.1	767.5	740.4	716.9	710.5
17.5°	914.0	877.5	848.3	811.3	773.2	724.8	693.0	673.5	657.2	644.8	635.6
20°	875.8	838.7	807.6	751.7	700.4	667.7	644.2	629.2	612.2	598.9	591.6
22.5°	835.8	796.9	754.5	692.2	652.2	625.9	605.0	587.8	576.3	565.9	559.3
25°	778.8	736.3	666.4	623.5	591.2	563.7	549.1	538.6	526.5	512.3	505.9
27.5°	718.7	651.1	600.9	569.0	538.1	520.2	507.2	491.5	480.6	474.3	467.5
30°	673.7	606.2	567.0	532.2	510.3	490.5	475.2	466.3	455.7	444.8	440.4
32.5°	623.5	569.6	532.0	503.0	480.9	464.0	451.9	437.4	429.8	423.1	413.8
35°	561.3	520.5	486.1	462.6	441.6	427.9	413.7	405.2	391.4	385.8	382.1
37.5°	508.5	473.1	447.5	422.7	406.1	390.9	382.2	368.7	362.7	354.9	347.2
40°	478.8	444.0	419.3	399.1	380.5	369.2	358.3	347.4	338.4	334.9	325.5
42.5°	448.4	420.1	395.4	373.2	360.8	348.8	335.0	327.0	317.7	311.9	306.1
45°	406.4	381.4	360.3	342.1	328.4	315.8	306.9	293.6	288.4	276.6	271.7
47.5°	369.6	346.2	326.1	308.9	295.4	287.2	274.3	263.8	255.4	248.2	242.0
50°	343.3	323.9	304.5	289.1	277.0	265.3	251.9	246.7	233.7	230.0	226.5
52.5°	319.4	301.0	283.1	268.1	256.0	244.5	232.8	225.9	217.2	213.6	211.0
55°	285.9	268.1	251.1	237.7	225.6	213.9	206.6	198.1	194.1	191.2	188.1
57.5°	252.2	236.2	223.2	209.7	197.5	188.2	179.7	174.7	170.5	166.8	162.9
60°	230.9	215.6	203.8	191.2	178.7	171.0	164.6	158.5	153.7	148.0	146.4
62.5°	208.3	194.8	184.1	171.8	161.0	153.9	147.7	142.0	136.2	127.9	125.6
65°	177.1	166.6	155.3	145.2	135.5	128.6	119.7	113.2	110.8	110.0	109.6
67.5°	149.0	139.0	129.3	119.0	110.1	103.8	99.3	98.2	96.6	96.1	95.0
70°	130.2	120.9	111.2	101.5	93.0	91.8	90.2	88.6	86.5	85.7	84.9
72.5°	113.4	103.8	94.0	86.3	82.6	81.1	79.5	77.9	76.5	75.7	75.2
75°	86.9	78.0	71.6	68.8	66.7	65.5	63.1	61.9	61.1	59.8	59.4
77.5°	62.6	57.6	54.6	52.8	50.7	49.4	48.0	46.8	45.9	45.7	45.1
80°	47.7	45.3	43.3	40.9	40.0	38.4	38.0	36.8	37.2	36.0	36.0
82.5°	37.1	34.0	32.2	31.1	30.3	29.1	28.6	28.0	28.1	27.3	27.3
85°	19.0	18.2	17.3	16.6	16.6	15.4	15.8	15.4	15.4	14.6	14.2
87.5°	8.1	8.2	8.3	9.4	10.4	10.2	10.1	9.6	9.3	9.6	9.4
90°	9.5	11.9	15.8	21.3	26.1	26.9	26.1	25.3	23.7	25.3	26.1
92.5°	28.4	35.9	53.8	78.9	101.3	102.7	86.8	68.9	59.2	52.5	47.6
95°	58.5	77.5	113.8	182.6	274.3	309.9	271.2	207.2	158.9	125.7	108.3
97.5°	83.0	104.5	150.2	246.1	398.5	529.1	555.0	483.4	395.5	309.9	252.9
100°	98.9	121.0	162.9	259.4	430.1	624.6	738.5	721.8	623.8	515.5	419.9
102.5°	113.4	135.5	174.3	260.0	418.1	627.7	806.8	878.1	856.0	776.7	675.3
105°	134.4	156.5	193.7	264.0	394.5	585.8	796.1	960.6	1050.0	1060.3	1034.1
107.5°	155.3	177.6	213.7	275.0	382.8	541.0	726.7	901.2	1035.7	1117.9	1156.2
110°	169.2	192.1	226.9	283.8	380.3	519.4	683.1	849.9	991.4	1092.7	1157.5



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	182.4	206.0	239.6	293.3	380.9	505.5	652.8	803.1	939.0	1047.1	1121.4
115°	204.0	225.3	259.4	307.5	384.2	490.2	615.1	745.5	867.3	970.9	1052.3
117.5°	223.9	246.1	277.5	322.7	389.9	482.8	591.4	702.2	809.1	903.0	979.5
120°	237.2	259.4	290.2	332.9	393.7	478.3	578.8	680.7	778.8	862.5	934.5
122.5°	250.5	273.2	302.1	341.7	398.2	475.8	568.0	663.6	753.4	832.8	897.9
125°	269.6	291.8	320.2	355.8	404.8	471.2	552.6	638.8	720.3	789.8	849.1
127.5°	286.5	309.3	337.0	368.9	411.6	468.5	538.4	614.3	688.0	753.6	808.3
130°	297.3	319.4	347.1	377.2	416.7	467.2	528.9	598.5	666.5	729.0	781.2
132.5°	307.4	329.5	355.9	385.3	421.7	466.6	521.3	583.3	646.3	703.6	752.7
135°	321.0	343.1	368.4	396.1	427.7	465.6	510.7	562.1	614.3	666.5	710.7
137.5°	333.0	353.6	378.6	404.3	433.1	465.5	503.3	545.2	588.8	630.3	668.8
140°	340.0	360.5	384.2	408.8	435.6	464.9	498.9	534.5	572.4	608.8	643.6
142.5°	346.3	365.6	388.6	412.6	437.5	464.9	494.5	525.6	557.9	589.1	618.3
145°	356.6	374.0	395.3	417.5	439.6	463.3	488.6	513.1	539.2	563.7	586.6
147.5°	365.1	380.6	400.7	420.2	440.2	460.5	482.6	503.4	524.0	543.1	559.9
150°	370.8	385.0	403.2	421.4	439.6	458.6	477.5	496.5	513.9	530.5	544.7
152.5°	376.5	389.4	405.8	422.0	438.3	455.4	473.1	489.6	505.6	519.8	532.1
155°	384.2	396.1	409.6	422.9	436.4	449.9	464.9	479.9	492.6	504.4	513.1
157.5°	390.9	400.8	412.3	422.9	432.8	444.2	457.2	468.7	479.3	489.3	496.1
160°	395.3	404.0	413.5	422.9	430.9	440.4	451.5	461.7	470.4	479.1	484.7
162.5°	399.1	405.9	414.2	422.3	429.0	437.2	446.4	454.8	462.2	469.6	473.9
165°	403.2	408.0	415.1	420.6	425.3	430.9	438.0	444.3	449.9	455.4	458.6
167.5°	406.7	409.7	414.9	419.5	421.7	425.3	429.8	434.4	438.6	442.4	445.3
170°	408.0	410.4	414.3	418.3	419.9	422.2	425.3	429.3	431.7	434.8	436.4
172.5°	409.2	411.0	413.7	416.4	417.3	418.4	421.0	423.6	425.3	427.9	428.8
175°	410.4	411.1	412.7	414.3	413.5	414.3	415.1	417.5	418.3	419.1	419.9
177.5°	411.1	411.1	411.8	413.0	411.8	411.1	411.8	413.0	413.0	413.7	413.7
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1117.5	1118.2	1117.2	1117.8	1117.2	1118.2	1117.5	1121.1	1121.7	1122.4	1121.7
5°	1041.2	1036.4	1035.6	1034.4	1035.6	1036.4	1041.2	1043.3	1044.9	1048.1	1053.8
7.5°	950.2	949.4	947.5	944.6	947.5	949.4	950.2	957.1	962.7	968.9	980.5
10°	891.6	889.6	889.2	886.4	889.2	889.6	891.6	900.6	907.0	915.9	931.7
12.5°	823.1	810.0	808.7	801.6	808.7	810.0	823.1	834.6	852.0	860.5	877.3
15°	700.8	698.4	690.2	685.0	690.2	698.4	700.8	710.5	716.9	740.4	767.5
17.5°	630.9	623.0	620.4	619.3	620.4	623.0	630.9	635.6	644.8	657.2	673.5
20°	585.9	578.7	577.4	576.6	577.4	578.7	585.9	591.6	598.9	612.2	629.2
22.5°	554.8	547.2	544.2	541.7	544.2	547.2	554.8	559.3	565.9	576.3	587.8
25°	501.8	499.0	497.4	496.5	497.4	499.0	501.8	505.9	512.3	526.5	538.6
27.5°	460.3	454.1	452.9	450.8	452.9	454.1	460.3	467.5	474.3	480.6	491.5
30°	436.7	434.7	431.9	429.4	431.9	434.7	436.7	440.4	444.8	455.7	466.3
32.5°	408.9	407.2	404.7	403.5	404.7	407.2	408.9	413.8	423.1	429.8	437.4
35°	378.1	372.4	370.0	366.4	370.0	372.4	378.1	382.1	385.8	391.4	405.2
37.5°	345.5	342.5	339.1	340.3	339.1	342.5	345.5	347.2	354.9	362.7	368.7
40°	320.3	318.2	317.4	317.0	317.4	318.2	320.3	325.5	334.9	338.4	347.4
42.5°	300.2	294.6	292.6	292.5	292.6	294.6	300.2	306.1	311.9	317.7	327.0
45°	269.7	264.4	260.8	261.3	260.8	264.4	269.7	271.7	276.6	288.4	293.6
47.5°	238.5	238.4	236.1	236.8	236.1	238.4	238.5	242.0	248.2	255.4	263.8
50°	223.6	221.2	219.6	220.0	219.6	221.2	223.6	226.5	230.0	233.7	246.7
52.5°	209.4	207.3	206.0	207.7	206.0	207.3	209.4	211.0	213.6	217.2	225.9
55°	186.0	183.5	183.2	182.8	183.2	183.5	186.0	188.1	191.2	194.1	198.1
57.5°	159.9	158.3	155.8	154.8	155.8	158.3	159.9	162.9	166.8	170.5	174.7
60°	141.1	137.9	133.9	133.4	133.9	137.9	141.1	146.4	148.0	153.7	158.5
62.5°	124.0	123.3	122.6	122.5	122.6	123.3	124.0	125.6	127.9	136.2	142.0
65°	108.8	108.4	108.8	109.2	108.8	108.4	108.8	109.6	110.0	110.8	113.2
67.5°	94.8	94.0	93.3	93.6	93.3	94.0	94.8	95.0	96.1	96.6	98.2
70°	84.1	83.7	83.3	83.3	83.3	83.7	84.1	84.9	85.7	86.5	88.6
72.5°	73.8	73.7	73.3	73.0	73.3	73.7	73.8	75.2	75.7	76.5	77.9
75°	59.0	58.2	58.2	58.2	58.2	58.2	59.0	59.4	59.8	61.1	61.9
77.5°	45.0	44.6	44.1	43.8	44.1	44.6	45.0	45.1	45.7	45.9	46.8
80°	35.6	35.2	34.8	34.8	34.8	35.2	35.6	36.0	36.0	37.2	36.8
82.5°	27.2	26.8	26.7	26.4	26.7	26.8	27.2	27.3	27.3	28.1	28.0
85°	14.6	15.0	14.6	15.4	14.6	15.0	14.6	14.2	14.6	15.4	15.4
87.5°	9.4	9.1	9.4	9.1	9.4	9.1	9.4	9.4	9.6	9.3	9.6
90°	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	25.3	23.7	25.3
92.5°	47.0	44.4	45.1	43.8	45.1	44.4	47.0	47.6	52.5	59.2	68.9
95°	98.1	91.7	89.4	90.2	89.4	91.7	98.1	108.3	125.7	158.9	207.2
97.5°	215.1	195.6	184.0	177.4	184.0	195.6	215.1	252.9	309.9	395.5	483.4
100°	354.2	320.2	297.3	283.0	297.3	320.2	354.2	419.9	515.5	623.8	721.8
102.5°	604.0	546.0	517.4	498.1	517.4	546.0	604.0	675.3	776.7	856.0	878.1
105°	985.1	936.1	902.1	891.0	902.1	936.1	985.1	1034.1	1060.3	1050.0	960.6
107.5°	1162.4	1159.7	1152.9	1138.2	1152.9	1159.7	1162.4	1156.2	1117.9	1035.7	901.2
110°	1191.4	1206.5	1213.6	1212.8	1213.6	1206.5	1191.4	1157.5	1092.7	991.4	849.9



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1168.7	1193.8	1207.3	1211.6	1207.3	1193.8	1168.7	1121.4	1047.1	939.0	803.1
115°	1108.4	1144.8	1165.4	1172.5	1165.4	1144.8	1108.4	1052.3	970.9	867.3	745.5
117.5°	1036.6	1075.1	1096.8	1102.7	1096.8	1075.1	1036.6	979.5	903.0	809.1	702.2
120°	989.8	1027.0	1050.0	1057.9	1050.0	1027.0	989.8	934.5	862.5	778.8	680.7
122.5°	947.5	984.0	1004.4	1011.1	1004.4	984.0	947.5	897.9	832.8	753.4	663.6
125°	895.0	925.0	944.8	951.1	944.8	925.0	895.0	849.1	789.8	720.3	638.8
127.5°	848.3	876.5	893.6	898.7	893.6	876.5	848.3	808.3	753.6	688.0	614.3
130°	819.9	846.8	862.5	868.9	862.5	846.8	819.9	781.2	729.0	666.5	598.5
132.5°	790.8	817.7	832.2	837.9	832.2	817.7	790.8	752.7	703.6	646.3	583.3
135°	744.7	770.9	785.1	788.2	785.1	770.9	744.7	710.7	666.5	614.3	562.1
137.5°	699.9	722.3	734.8	739.6	734.8	722.3	699.9	668.8	630.3	588.8	545.2
140°	668.8	689.4	701.3	706.0	701.3	689.4	668.8	643.6	608.8	572.4	534.5
142.5°	642.3	661.0	671.5	672.5	671.5	661.0	642.3	618.3	589.1	557.9	525.6
145°	605.6	619.1	626.9	629.3	626.9	619.1	605.6	586.6	563.7	539.2	513.1
147.5°	575.6	586.3	591.7	593.1	591.7	586.3	575.6	559.9	543.1	524.0	503.4
150°	556.6	566.1	570.8	571.6	570.8	566.1	556.6	544.7	530.5	513.9	496.5
152.5°	541.4	549.6	553.1	553.3	553.1	549.6	541.4	532.1	519.8	505.6	489.6
155°	521.8	527.4	530.5	528.9	530.5	527.4	521.8	513.1	504.4	492.6	479.9
157.5°	502.2	506.8	508.2	508.2	508.2	506.8	502.2	496.1	489.3	479.3	468.7
160°	490.2	494.2	495.0	495.0	495.0	494.2	490.2	484.7	479.1	470.4	461.7
162.5°	479.4	482.1	482.9	482.3	482.9	482.1	479.4	473.9	469.6	462.2	454.8
165°	461.7	464.9	464.9	464.1	464.9	464.9	461.7	458.6	455.4	449.9	444.3
167.5°	446.7	448.5	448.3	447.3	448.3	448.5	446.7	445.3	442.4	438.6	434.4
170°	437.2	439.6	438.8	437.2	438.8	439.6	437.2	436.4	434.8	431.7	429.3
172.5°	429.6	430.7	429.9	429.0	429.9	430.7	429.6	428.8	427.9	425.3	423.6
175°	419.9	420.6	419.9	418.3	419.9	420.6	419.9	419.9	419.1	418.3	417.5
177.5°	413.7	413.7	413.0	411.8	413.0	413.7	413.7	413.7	413.7	413.0	413.0
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1119.1	1123.6	1130.4	1134.3	1140.8	1145.0	1147.3	1151.5	1153.7	1161.8	1170.3
5°	1056.6	1063.1	1074.4	1084.9	1096.2	1107.9	1116.5	1126.2	1135.0	1150.4	1166.6
7.5°	985.0	994.0	1011.5	1028.3	1048.0	1064.5	1079.2	1095.7	1110.6	1132.6	1155.6
10°	931.3	947.1	970.1	985.9	1011.8	1028.3	1051.4	1069.5	1090.2	1119.3	1145.2
12.5°	885.0	904.0	922.5	944.4	967.7	995.3	1020.6	1044.0	1068.5	1098.6	1129.0
15°	801.1	828.5	857.3	879.5	911.1	940.2	969.7	1001.2	1031.2	1067.1	1106.8
17.5°	693.0	724.8	773.2	811.3	848.3	877.5	914.0	952.2	987.5	1030.9	1075.0
20°	644.2	667.7	700.4	751.7	807.6	838.7	875.8	917.9	958.4	1005.7	1053.0
22.5°	605.0	625.9	652.2	692.2	754.5	796.9	835.8	878.5	925.3	973.7	1026.1
25°	549.1	563.7	591.2	623.5	666.4	736.3	778.8	821.7	872.7	924.4	984.2
27.5°	507.2	520.2	538.1	569.0	600.9	651.1	718.7	765.4	816.2	874.4	936.5
30°	475.2	490.5	510.3	532.2	567.0	606.2	673.7	727.9	778.0	837.9	904.2
32.5°	451.9	464.0	480.9	503.0	532.0	569.6	623.5	689.4	738.2	801.3	870.5
35°	413.7	427.9	441.6	462.6	486.1	520.5	561.3	631.6	680.2	742.4	812.0
37.5°	382.2	390.9	406.1	422.7	447.5	473.1	508.5	571.6	624.1	685.2	756.5
40°	358.3	369.2	380.5	399.1	419.3	444.0	478.8	525.7	585.9	645.8	715.3
42.5°	335.0	348.8	360.8	373.2	395.4	420.1	448.4	488.1	549.7	606.3	673.9
45°	306.9	315.8	328.4	342.1	360.3	381.4	406.4	441.2	500.2	549.1	612.6
47.5°	274.3	287.2	295.4	308.9	326.1	346.2	369.6	399.6	447.4	493.3	552.2
50°	251.9	265.3	277.0	289.1	304.5	323.9	343.3	372.4	410.8	459.0	514.0
52.5°	232.8	244.5	256.0	268.1	283.1	301.0	319.4	344.9	377.9	422.1	475.5
55°	206.6	213.9	225.6	237.7	251.1	268.1	285.9	307.3	335.6	372.8	416.1
57.5°	179.7	188.2	197.5	209.7	223.2	236.2	252.2	271.6	294.0	327.6	364.6
60°	164.6	171.0	178.7	191.2	203.8	215.6	230.9	247.1	268.1	297.2	328.8
62.5°	147.7	153.9	161.0	171.8	184.1	194.8	208.3	225.4	243.2	269.7	297.4
65°	119.7	128.6	135.5	145.2	155.3	166.6	177.1	190.8	206.6	227.7	252.3
67.5°	99.3	103.8	110.1	119.0	129.3	139.0	149.0	159.7	173.4	189.6	209.2
70°	90.2	91.8	93.0	101.5	111.2	120.9	130.2	140.3	152.0	165.4	182.4
72.5°	79.5	81.1	82.6	86.3	94.0	103.8	113.4	120.9	132.0	143.1	156.9
75°	63.1	65.5	66.7	68.8	71.6	78.0	86.9	94.2	100.7	109.2	120.1
77.5°	48.0	49.4	50.7	52.8	54.6	57.6	62.6	69.2	75.2	80.2	87.7
80°	38.0	38.4	40.0	40.9	43.3	45.3	47.7	53.0	59.0	61.1	66.3
82.5°	28.6	29.1	30.3	31.1	32.2	34.0	37.1	38.4	43.2	45.9	49.2
85°	15.8	15.4	16.6	16.6	17.3	18.2	19.0	21.0	22.3	25.5	26.3
87.5°	10.1	10.2	10.4	9.4	8.3	8.2	8.1	8.1	8.4	8.7	9.5
90°	26.1	26.9	26.1	21.3	15.8	11.9	9.5	7.9	6.3	3.2	0.8
92.5°	86.8	102.7	101.3	78.9	53.8	35.9	28.4	23.1	19.6	13.9	9.7
95°	271.2	309.9	274.3	182.6	113.8	77.5	58.5	45.9	38.7	30.8	27.6
97.5°	555.0	529.1	398.5	246.1	150.2	104.5	83.0	68.4	57.8	49.4	45.1
100°	738.5	624.6	430.1	259.4	162.9	121.0	98.9	83.0	70.3	63.2	60.8
102.5°	806.8	627.7	418.1	260.0	174.3	135.5	113.4	97.0	84.3	77.2	75.4
105°	796.1	585.8	394.5	264.0	193.7	156.5	134.4	117.0	105.1	99.7	96.5
107.5°	726.7	541.0	382.8	275.0	213.7	177.6	155.3	138.1	127.1	121.8	119.2
110°	683.1	519.4	380.3	283.8	226.9	192.1	169.2	152.6	142.3	137.6	134.4



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	652.8	505.5	380.9	293.3	239.6	206.0	182.4	166.5	156.9	151.5	148.3
115°	615.1	490.2	384.2	307.5	259.4	225.3	204.0	188.1	178.7	174.0	170.0
117.5°	591.4	482.8	389.9	322.7	277.5	246.1	223.9	208.7	200.3	195.6	192.4
120°	578.8	478.3	393.7	332.9	290.2	259.4	237.2	221.3	214.3	209.5	206.4
122.5°	568.0	475.8	398.2	341.7	302.1	273.2	250.5	234.6	226.9	222.1	219.7
125°	552.6	471.2	404.8	355.8	320.2	291.8	269.6	253.8	244.3	239.6	237.2
127.5°	538.4	468.5	411.6	368.9	337.0	309.3	286.5	271.3	260.9	254.3	251.1
130°	528.9	467.2	416.7	377.2	347.1	319.4	297.3	281.5	270.4	262.4	259.4
132.5°	521.3	466.6	421.7	385.3	355.9	329.5	307.4	291.0	279.2	270.7	266.9
135°	510.7	465.6	427.7	396.1	368.4	343.1	321.0	302.8	291.0	281.5	278.3
137.5°	503.3	465.5	433.1	404.3	378.6	353.6	333.0	315.0	302.3	292.9	289.1
140°	498.9	464.9	435.6	408.8	384.2	360.5	340.0	322.6	309.9	300.5	297.3
142.5°	494.5	464.9	437.5	412.6	388.6	365.6	346.3	329.5	316.9	308.0	305.5
145°	488.6	463.3	439.6	417.5	395.3	374.0	356.6	340.8	328.9	321.0	317.8
147.5°	482.6	460.5	440.2	420.2	400.7	380.6	365.1	352.0	341.0	333.5	331.1
150°	477.5	458.6	439.6	421.4	403.2	385.0	370.8	358.9	348.6	342.3	340.0
152.5°	473.1	455.4	438.3	422.0	405.8	389.4	376.5	365.3	356.2	349.9	348.8
155°	464.9	449.9	436.4	422.9	409.6	396.1	384.2	375.6	366.9	362.1	361.3
157.5°	457.2	444.2	432.8	422.9	412.3	400.8	390.9	383.9	376.4	372.6	371.8
160°	451.5	440.4	430.9	422.9	413.5	404.0	395.3	389.0	382.6	379.5	378.7
162.5°	446.4	437.2	429.0	422.3	414.2	405.9	399.1	393.4	388.3	385.2	385.6
165°	438.0	430.9	425.3	420.6	415.1	408.0	403.2	399.3	394.5	392.9	393.7
167.5°	429.8	425.3	421.7	419.5	414.9	409.7	406.7	403.9	400.8	399.4	400.4
170°	425.3	422.2	419.9	418.3	414.3	410.4	408.0	406.4	404.0	403.2	404.8
172.5°	421.0	418.4	417.3	416.4	413.7	411.0	409.2	408.3	405.9	406.4	407.3
175°	415.1	414.3	413.5	414.3	412.7	411.1	410.4	410.4	408.8	409.6	410.4
177.5°	411.8	411.1	411.8	413.0	411.8	411.1	411.1	411.1	409.9	410.5	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1170.6	1171.6	1178.1	1180.9	1186.8	1189.0	1191.6	1191.0	1191.0	1192.2	1201.3
5°	1173.1	1181.1	1193.3	1205.0	1216.3	1226.1	1232.6	1239.0	1241.4	1253.2	1263.7
7.5°	1168.9	1183.8	1203.8	1221.7	1243.1	1259.9	1273.7	1286.3	1294.9	1311.9	1329.4
10°	1163.4	1184.4	1207.0	1230.1	1259.6	1281.8	1304.5	1321.9	1327.5	1353.0	1367.6
12.5°	1152.4	1180.5	1209.3	1239.1	1268.0	1298.7	1323.6	1341.0	1360.9	1383.8	1410.6
15°	1135.9	1168.2	1205.9	1244.3	1285.5	1322.7	1349.4	1379.7	1401.5	1426.6	1450.1
17.5°	1112.1	1153.8	1201.7	1246.1	1293.8	1333.8	1370.5	1399.6	1415.0	1429.3	1432.7
20°	1093.4	1138.3	1194.5	1247.1	1294.8	1340.9	1377.3	1401.5	1405.6	1406.0	1384.6
22.5°	1073.0	1123.7	1182.6	1236.4	1293.5	1344.8	1373.1	1383.5	1367.4	1340.0	1298.5
25°	1035.6	1094.2	1162.6	1224.0	1286.3	1334.8	1344.6	1326.4	1270.1	1211.1	1136.3
27.5°	995.0	1060.9	1134.2	1202.5	1268.8	1298.9	1277.9	1212.4	1111.1	1023.1	916.5
30°	965.3	1039.3	1111.2	1187.6	1249.1	1262.0	1213.9	1117.3	999.2	866.6	760.3
32.5°	931.3	1008.8	1087.9	1167.0	1218.4	1205.8	1126.2	1007.3	868.9	738.5	637.9
35°	882.7	962.8	1048.1	1127.4	1160.2	1105.6	986.7	831.8	690.2	568.5	499.4
37.5°	826.7	913.9	1002.6	1075.4	1073.0	982.1	820.1	660.3	541.3	469.3	420.1
40°	786.9	875.0	970.9	1032.4	1006.1	887.6	712.1	561.3	474.4	416.9	380.9
42.5°	748.8	837.2	932.4	981.3	935.6	789.9	615.1	496.9	425.2	380.3	351.2
45°	683.8	777.2	865.4	892.5	810.8	650.2	497.4	411.6	363.9	330.8	310.5
47.5°	620.3	712.2	792.7	793.1	682.6	527.3	419.5	356.2	315.5	289.9	275.1
50°	581.5	668.8	736.3	725.9	600.5	469.1	375.3	320.7	286.7	266.9	251.5
52.5°	537.8	622.6	681.0	651.1	530.9	412.8	335.5	289.6	261.5	244.2	230.5
55°	474.4	549.5	590.8	545.5	433.1	343.3	283.4	247.5	226.5	211.9	200.2
57.5°	411.9	474.0	499.9	447.3	356.7	284.7	239.8	212.8	191.9	181.5	175.4
60°	372.8	425.8	444.0	385.8	310.1	249.1	212.3	187.2	171.8	165.0	158.9
62.5°	334.3	377.6	385.2	331.8	270.4	218.0	186.4	165.2	155.0	148.5	142.8
65°	277.4	308.6	304.9	262.1	213.9	173.1	150.0	137.0	129.4	120.1	110.0
67.5°	228.4	247.4	235.9	203.8	163.3	134.5	119.5	109.6	100.1	91.3	89.0
70°	197.3	208.3	196.1	166.6	133.9	112.8	100.7	89.0	83.3	81.3	77.6
72.5°	167.5	171.3	158.3	132.9	108.9	93.4	81.6	75.0	72.0	70.3	68.0
75°	125.8	122.9	111.6	91.8	75.7	65.1	61.5	59.0	57.0	55.4	54.2
77.5°	88.3	84.2	74.1	61.2	52.7	47.6	45.5	44.1	43.2	42.4	41.2
80°	66.3	63.5	53.4	43.6	40.0	37.6	36.4	34.8	34.8	34.0	32.7
82.5°	48.6	45.4	36.5	32.0	30.0	28.5	27.6	26.7	26.4	26.5	25.7
85°	25.5	20.6	18.2	17.3	16.2	15.4	15.8	15.0	15.0	15.0	14.6
87.5°	8.4	7.4	7.4	7.4	8.2	9.0	9.7	10.7	11.2	10.7	10.9
90°	3.2	6.3	7.9	9.5	11.9	15.8	21.3	26.1	26.9	26.1	25.3
92.5°	13.9	19.6	23.1	28.4	35.9	53.8	78.9	101.3	102.7	86.8	68.9
95°	30.8	38.7	45.9	58.5	77.5	113.8	182.6	274.3	309.9	271.2	207.2
97.5°	49.4	57.8	68.4	83.0	104.5	150.2	246.1	398.5	529.1	555.0	483.4
100°	63.2	70.3	83.0	98.9	121.0	162.9	259.4	430.1	624.6	738.5	721.8
102.5°	77.2	84.3	97.0	113.4	135.5	174.3	260.0	418.1	627.7	806.8	878.1
105°	99.7	105.1	117.0	134.4	156.5	193.7	264.0	394.5	585.8	796.1	960.6
107.5°	121.8	127.1	138.1	155.3	177.6	213.7	275.0	382.8	541.0	726.7	901.2
110°	137.6	142.3	152.6	169.2	192.1	226.9	283.8	380.3	519.4	683.1	849.9



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	151.5	156.9	166.5	182.4	206.0	239.6	293.3	380.9	505.5	652.8	803.1
115°	174.0	178.7	188.1	204.0	225.3	259.4	307.5	384.2	490.2	615.1	745.5
117.5°	195.6	200.3	208.7	223.9	246.1	277.5	322.7	389.9	482.8	591.4	702.2
120°	209.5	214.3	221.3	237.2	259.4	290.2	332.9	393.7	478.3	578.8	680.7
122.5°	222.1	226.9	234.6	250.5	273.2	302.1	341.7	398.2	475.8	568.0	663.6
125°	239.6	244.3	253.8	269.6	291.8	320.2	355.8	404.8	471.2	552.6	638.8
127.5°	254.3	260.9	271.3	286.5	309.3	337.0	368.9	411.6	468.5	538.4	614.3
130°	262.4	270.4	281.5	297.3	319.4	347.1	377.2	416.7	467.2	528.9	598.5
132.5°	270.7	279.2	291.0	307.4	329.5	355.9	385.3	421.7	466.6	521.3	583.3
135°	281.5	291.0	302.8	321.0	343.1	368.4	396.1	427.7	465.6	510.7	562.1
137.5°	292.9	302.3	315.0	333.0	353.6	378.6	404.3	433.1	465.5	503.3	545.2
140°	300.5	309.9	322.6	340.0	360.5	384.2	408.8	435.6	464.9	498.9	534.5
142.5°	308.0	316.9	329.5	346.3	365.6	388.6	412.6	437.5	464.9	494.5	525.6
145°	321.0	328.9	340.8	356.6	374.0	395.3	417.5	439.6	463.3	488.6	513.1
147.5°	333.5	341.0	352.0	365.1	380.6	400.7	420.2	440.2	460.5	482.6	503.4
150°	342.3	348.6	358.9	370.8	385.0	403.2	421.4	439.6	458.6	477.5	496.5
152.5°	349.9	356.2	365.3	376.5	389.4	405.8	422.0	438.3	455.4	473.1	489.6
155°	362.1	366.9	375.6	384.2	396.1	409.6	422.9	436.4	449.9	464.9	479.9
157.5°	372.6	376.4	383.9	390.9	400.8	412.3	422.9	432.8	444.2	457.2	468.7
160°	379.5	382.6	389.0	395.3	404.0	413.5	422.9	430.9	440.4	451.5	461.7
162.5°	385.2	388.3	393.4	399.1	405.9	414.2	422.3	429.0	437.2	446.4	454.8
165°	392.9	394.5	399.3	403.2	408.0	415.1	420.6	425.3	430.9	438.0	444.3
167.5°	399.4	400.8	403.9	406.7	409.7	414.9	419.5	421.7	425.3	429.8	434.4
170°	403.2	404.0	406.4	408.0	410.4	414.3	418.3	419.9	422.2	425.3	429.3
172.5°	406.4	405.9	408.3	409.2	411.0	413.7	416.4	417.3	418.4	421.0	423.6
175°	409.6	408.8	410.4	410.4	411.1	412.7	414.3	413.5	414.3	415.1	417.5
177.5°	410.5	409.9	411.1	411.1	411.1	411.8	413.0	411.8	411.1	411.8	413.0
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8	1163.8
2.5°	1204.5	1208.7	1210.7	1210.7	1213.0	1212.0	1211.0
5°	1273.7	1281.4	1283.1	1290.4	1295.6	1294.0	1294.8
7.5°	1342.6	1354.9	1367.1	1372.8	1373.6	1376.9	1378.1
10°	1385.0	1395.1	1414.1	1411.3	1425.4	1433.5	1420.1
12.5°	1425.8	1439.4	1452.5	1456.2	1464.3	1466.8	1461.6
15°	1462.6	1469.9	1470.7	1468.7	1471.1	1469.1	1461.4
17.5°	1428.1	1416.3	1392.4	1381.1	1372.1	1358.8	1353.5
20°	1371.2	1336.4	1296.0	1279.8	1260.8	1223.6	1232.6
22.5°	1248.3	1208.6	1168.2	1121.0	1098.4	1063.2	1061.0
25°	1057.0	988.7	913.5	860.9	830.2	795.0	779.7
27.5°	821.8	735.8	674.1	642.9	614.6	586.7	585.5
30°	667.2	602.5	554.8	528.1	510.7	499.0	501.5
32.5°	562.4	518.1	485.9	463.7	450.9	442.0	441.9
35°	459.8	429.4	408.8	399.5	390.2	383.7	384.1
37.5°	393.5	375.3	363.8	353.5	347.7	344.5	342.8
40°	359.5	344.5	335.6	329.5	324.7	320.3	319.5
42.5°	332.6	320.3	311.3	306.6	302.1	298.9	298.1
45°	295.2	285.1	277.0	271.7	269.7	266.9	266.9
47.5°	262.6	252.6	246.4	243.0	239.6	237.7	237.6
50°	240.6	232.9	227.3	225.2	222.4	221.2	220.8
52.5°	220.9	215.2	211.1	209.7	208.5	206.9	207.2
55°	194.1	190.8	189.3	188.1	186.0	183.5	185.2
57.5°	171.5	168.8	164.5	160.7	158.8	157.1	157.7
60°	155.7	150.0	144.3	139.9	138.7	135.1	135.1
62.5°	135.6	127.7	120.7	118.3	117.0	115.3	115.0
65°	104.3	101.1	99.5	97.8	97.0	97.0	96.3
67.5°	86.4	85.2	83.4	82.9	82.1	81.9	81.7
70°	76.4	74.8	74.0	73.6	72.8	73.2	72.0
72.5°	66.7	65.4	65.3	64.2	63.7	63.8	62.9
75°	52.6	52.6	52.1	51.7	50.9	50.5	50.9
77.5°	40.4	40.5	39.8	39.7	39.6	39.7	39.3
80°	32.3	32.7	32.3	31.9	31.5	31.9	31.5
82.5°	25.6	25.0	24.9	24.8	24.7	24.5	24.4
85°	14.6	15.0	14.6	14.2	14.2	14.2	14.6
87.5°	10.2	10.5	10.7	10.7	10.7	10.7	10.4
90°	23.7	25.3	26.1	26.1	26.1	26.1	26.1
92.5°	59.2	52.5	47.6	47.0	44.4	45.1	43.8
95°	158.9	125.7	108.3	98.1	91.7	89.4	90.2
97.5°	395.5	309.9	252.9	215.1	195.6	184.0	177.4
100°	623.8	515.5	419.9	354.2	320.2	297.3	283.0
102.5°	856.0	776.7	675.3	604.0	546.0	517.4	498.1
105°	1050.0	1060.3	1034.1	985.1	936.1	902.1	891.0
107.5°	1035.7	1117.9	1156.2	1162.4	1159.7	1152.9	1138.2
110°	991.4	1092.7	1157.5	1191.4	1206.5	1213.6	1212.8



TEST NUMBER: P331695-927

CATALOG NUMBER: SA2XXRDIP-C675D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	939.0	1047.1	1121.4	1168.7	1193.8	1207.3	1211.6
115°	867.3	970.9	1052.3	1108.4	1144.8	1165.4	1172.5
117.5°	809.1	903.0	979.5	1036.6	1075.1	1096.8	1102.7
120°	778.8	862.5	934.5	989.8	1027.0	1050.0	1057.9
122.5°	753.4	832.8	897.9	947.5	984.0	1004.4	1011.1
125°	720.3	789.8	849.1	895.0	925.0	944.8	951.1
127.5°	688.0	753.6	808.3	848.3	876.5	893.6	898.7
130°	666.5	729.0	781.2	819.9	846.8	862.5	868.9
132.5°	646.3	703.6	752.7	790.8	817.7	832.2	837.9
135°	614.3	666.5	710.7	744.7	770.9	785.1	788.2
137.5°	588.8	630.3	668.8	699.9	722.3	734.8	739.6
140°	572.4	608.8	643.6	668.8	689.4	701.3	706.0
142.5°	557.9	589.1	618.3	642.3	661.0	671.5	672.5
145°	539.2	563.7	586.6	605.6	619.1	626.9	629.3
147.5°	524.0	543.1	559.9	575.6	586.3	591.7	593.1
150°	513.9	530.5	544.7	556.6	566.1	570.8	571.6
152.5°	505.6	519.8	532.1	541.4	549.6	553.1	553.3
155°	492.6	504.4	513.1	521.8	527.4	530.5	528.9
157.5°	479.3	489.3	496.1	502.2	506.8	508.2	508.2
160°	470.4	479.1	484.7	490.2	494.2	495.0	495.0
162.5°	462.2	469.6	473.9	479.4	482.1	482.9	482.3
165°	449.9	455.4	458.6	461.7	464.9	464.9	464.1
167.5°	438.6	442.4	445.3	446.7	448.5	448.3	447.3
170°	431.7	434.8	436.4	437.2	439.6	438.8	437.2
172.5°	425.3	427.9	428.8	429.6	430.7	429.9	429.0
175°	418.3	419.1	419.9	419.9	420.6	419.9	418.3
177.5°	413.0	413.7	413.7	413.7	413.7	413.0	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1

(END OF REPORT)