

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331393

Luminaire Tested: **SA2XXDIP-C865D725U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331393
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D725U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6708.6 lumens
Efficiency: N/A
Efficacy: 123.3 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331393
CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	100	96	92	89	93	89	86	83	77	75	73	66	64	63	56	55	54	49
2	91	84	78	73	85	79	74	69	68	64	61	59	56	53	50	48	46	42
3	84	75	67	62	78	70	63	58	61	56	52	52	49	46	45	42	40	36
4	77	66	59	53	71	62	55	50	54	49	45	47	43	40	40	37	35	31
5	71	59	52	46	66	56	49	43	49	43	39	43	38	35	37	33	31	28
6	65	54	46	40	61	50	43	38	44	39	34	39	34	31	33	30	27	25
7	61	49	41	35	56	46	39	34	40	35	31	35	31	28	31	27	25	22
8	56	44	37	31	53	42	35	30	37	31	27	33	28	25	28	25	22	20
9	53	41	33	28	49	38	32	27	34	29	25	30	26	22	26	23	20	18
10	49	37	30	25	46	35	29	24	32	26	22	28	24	20	24	21	18	17

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27876	27876	27876	27876
5°	31253	28058	24864	28058
10°	35813	27829	21518	27829
15°	39619	27318	19010	27318
20°	39015	26770	17330	26770
25°	35179	26042	16265	26042
30°	29071	24878	15489	24878
35°	21187	23660	14937	23660
40°	16923	22223	14629	22223
45°	14787	20559	14212	20559
50°	13901	18952	13933	18952
55°	12814	17315	13560	17315
60°	11741	15578	12984	15578
65°	10697	14017	12420	14017
70°	9711	12500	11589	12500
75°	8609	10805	10268	10805
80°	7401	8945	8266	8945
85°	6632	6632	4909	6632



TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	164.4	2.5
10°-20°	478.0	7.1
20°-30°	693.8	10.3
30°-40°	732.1	10.9
40°-50°	648.2	9.7
50°-60°	517.3	7.7
60°-70°	351.6	5.2
70°-80°	180.3	2.7
80°-90°	45.9	0.7
90°-100°	33.0	0.5
100°-110°	120.9	1.8
110°-120°	323.3	4.8
120°-130°	533.6	8.0
130°-140°	567.5	8.5
140°-150°	527.5	7.9
150°-160°	424.1	6.3
160°-170°	273.3	4.1
170°-180°	94.1	1.4
0°-30°	1336.2	19.9
0°-40°	2068.3	30.8
0°-60°	3233.8	48.2
0°-90°	3811.5	56.8
90°-120°	477.2	7.1
90°-150°	2105.7	31.4
90°-180°	2897.0	43.2
0°-180°	6708.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1726	1726	1726	1726	1726	
5°	1928	1731	1534	1731	1928	193
15°	2370	1634	1137	1634	2370	654
25°	1975	1462	913	1462	1975	893
35°	1075	1200	758	1200	1075	699
45°	648	900	622	900	648	509
55°	455	615	482	615	455	408
65°	280	367	325	367	280	278
75°	138	173	165	173	138	147
85°	36	36	26	36	36	40
90°	19	1	19	1	19	10
95°	31	46	31	46	31	29
105°	54	218	54	218	54	57
115°	59	411	59	411	59	147
125°	612	582	612	582	612	529
135°	743	720	743	720	743	573
145°	848	835	848	835	848	530
155°	920	919	920	919	920	424
165°	966	969	966	969	966	273
175°	985	991	985	991	985	94
180°	989	989	989	989	989	



TEST NUMBER: P331393
 CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1806.2	1806.7	1807.8	1799.3	1798.2	1798.2	1790.8	1784.4	1777.0	1766.9	1768.0
5°	1928.3	1935.6	1938.2	1930.3	1918.3	1917.0	1905.7	1887.1	1869.9	1855.9	1846.0
7.5°	2074.0	2076.9	2070.4	2059.9	2051.0	2035.1	2014.1	1993.6	1964.8	1938.4	1918.7
10°	2184.4	2188.4	2177.1	2161.8	2149.2	2130.6	2100.1	2068.9	2031.1	1994.6	1965.4
12.5°	2268.3	2278.1	2263.6	2261.6	2240.0	2214.5	2178.2	2162.4	2109.2	2058.3	2027.0
15°	2370.2	2369.5	2370.9	2358.2	2342.3	2338.3	2299.9	2258.1	2183.1	2153.2	2101.5
17.5°	2340.7	2350.8	2355.5	2355.3	2354.9	2352.4	2340.1	2313.7	2276.1	2227.7	2167.9
20°	2270.7	2283.9	2285.9	2301.2	2309.8	2321.1	2325.7	2318.4	2295.2	2254.7	2203.0
22.5°	2162.4	2166.1	2172.3	2196.1	2214.8	2243.1	2257.8	2282.3	2273.4	2253.7	2210.4
25°	1974.7	1968.1	1991.3	2003.2	2046.4	2091.5	2124.0	2159.8	2191.7	2210.9	2198.3
27.5°	1749.4	1739.4	1774.2	1805.9	1840.9	1889.8	1940.5	2000.3	2050.1	2112.3	2133.7
30°	1559.3	1565.3	1598.5	1632.3	1685.4	1754.4	1811.5	1877.2	1948.2	2017.8	2066.3
32.5°	1354.4	1377.4	1398.4	1450.2	1497.0	1573.9	1657.5	1739.7	1828.2	1907.4	1982.4
35°	1074.9	1101.5	1130.7	1168.5	1234.2	1310.5	1392.1	1502.9	1623.7	1731.9	1820.8
37.5°	904.8	900.6	917.3	944.6	997.8	1059.4	1153.4	1262.9	1405.0	1532.1	1657.5
40°	802.9	800.2	812.2	837.4	877.9	923.0	1005.3	1101.5	1233.5	1388.8	1538.1
42.5°	732.8	734.4	741.0	758.8	786.6	823.7	885.3	967.2	1088.1	1234.3	1394.8
45°	647.6	652.3	659.6	668.2	684.1	714.6	749.1	807.5	903.1	1025.2	1183.1
47.5°	586.3	586.4	593.9	601.4	610.9	628.1	656.2	692.9	760.3	859.7	995.5
50°	553.4	548.8	554.1	560.0	570.0	581.9	600.5	635.0	680.1	760.4	873.9
52.5°	513.1	513.2	518.0	520.2	529.1	541.1	558.0	581.9	622.8	685.6	778.9
55°	455.2	458.5	461.2	465.1	473.1	481.7	495.0	510.9	542.8	589.9	658.9
57.5°	400.8	401.8	404.5	412.1	417.1	425.1	437.7	452.1	472.8	507.7	559.6
60°	363.6	363.6	368.9	372.2	378.9	386.8	396.8	410.7	429.3	457.8	499.7
62.5°	329.7	329.1	331.2	336.7	341.7	349.2	359.1	370.9	388.4	413.8	448.2
65°	280.0	278.7	282.7	284.0	289.3	296.6	304.6	317.2	331.1	349.7	380.2
67.5°	232.2	233.8	236.0	238.5	241.4	249.1	254.4	263.3	275.1	290.5	311.2
70°	205.7	205.7	205.7	207.7	211.7	215.7	221.0	228.3	239.5	252.8	271.4
72.5°	176.0	178.1	180.2	179.0	184.1	186.5	192.8	196.9	207.7	216.2	232.6
75°	138.0	138.0	138.0	141.3	143.3	145.3	149.3	153.3	158.6	169.2	177.8
77.5°	103.0	102.7	103.4	104.2	106.3	108.7	109.9	113.5	118.4	123.3	130.6
80°	79.6	81.0	81.6	82.9	82.9	84.3	84.9	89.6	92.9	96.2	100.9
82.5°	61.6	61.8	62.0	62.2	62.8	63.6	65.3	66.8	67.9	70.7	74.3
85°	35.8	35.2	35.2	36.5	35.8	35.8	37.2	38.5	38.5	39.1	41.1
87.5°	17.7	17.6	18.1	17.5	17.4	17.8	17.7	17.0	17.4	17.7	18.0
90°	19.3	19.0	18.7	18.4	18.0	17.5	16.7	15.9	15.1	14.3	13.0
92.5°	19.3	19.1	18.9	18.7	18.6	18.2	17.8	17.4	17.0	16.6	16.0
95°	30.8	30.9	31.1	31.2	31.4	31.1	30.3	29.5	28.7	27.9	26.8
97.5°	41.1	40.9	40.7	40.5	40.3	39.9	39.2	38.6	38.0	37.3	34.8
100°	47.9	47.6	47.3	47.0	46.7	45.9	44.6	43.3	42.0	40.8	38.1
102.5°	51.4	50.9	50.5	50.0	49.6	48.5	46.9	45.2	43.6	41.9	64.5
105°	54.4	53.7	53.1	52.5	51.8	50.6	48.9	47.1	45.4	43.6	87.0
107.5°	55.9	55.3	54.7	54.0	53.4	54.0	55.7	57.5	59.3	61.1	113.1
110°	56.5	55.9	55.2	54.6	54.0	61.6	77.5	93.4	109.3	125.2	171.1



TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.1	56.6	56.1	55.6	55.0	83.8	141.8	199.8	257.8	315.7	327.1
115°	58.7	70.1	81.5	93.0	104.4	147.0	220.6	294.2	367.8	441.4	437.4
117.5°	239.5	277.1	314.7	352.3	389.9	417.6	435.4	453.3	471.1	488.9	486.1
120°	436.4	457.8	479.3	500.7	522.2	532.0	530.1	528.2	526.2	524.3	521.5
122.5°	544.5	548.7	552.8	557.0	561.2	562.7	561.5	560.4	559.2	558.1	555.0
125°	611.6	611.1	610.7	610.2	609.7	608.9	607.8	606.7	605.6	604.5	601.4
127.5°	654.0	653.9	653.8	653.7	653.6	652.7	651.1	649.5	647.9	646.2	644.0
130°	680.3	680.4	680.6	680.8	680.9	680.1	678.4	676.6	674.9	673.1	671.4
132.5°	706.0	706.2	706.4	706.5	706.7	706.0	704.5	703.0	701.5	700.0	698.3
135°	743.2	743.5	743.9	744.2	744.5	743.9	742.3	740.7	739.1	737.5	736.1
137.5°	777.1	777.7	778.2	778.8	779.3	778.8	777.2	775.7	774.1	772.6	770.9
140°	798.3	799.1	799.9	800.7	801.5	801.2	799.7	798.3	796.9	795.5	793.7
142.5°	818.9	819.7	820.5	821.3	822.1	821.8	820.5	819.2	817.9	816.6	814.6
145°	847.7	848.5	849.3	850.1	850.8	850.7	849.6	848.5	847.4	846.2	843.5
147.5°	873.0	873.7	874.3	875.0	875.7	875.6	874.8	873.9	873.1	872.3	869.6
150°	888.4	889.2	890.0	890.8	891.6	891.5	890.6	889.6	888.7	887.7	885.2
152.5°	901.6	902.7	903.7	904.8	905.8	905.9	904.9	903.9	903.0	902.0	899.6
155°	919.9	921.2	922.5	923.7	925.0	925.2	924.2	923.3	922.3	921.3	919.4
157.5°	936.7	937.9	939.1	940.4	941.6	941.7	940.6	939.5	938.5	937.4	936.0
160°	946.4	947.5	948.6	949.7	950.8	950.9	950.0	949.0	948.1	947.1	946.1
162.5°	954.4	955.8	957.1	958.5	959.9	960.0	958.9	957.8	956.8	955.7	954.9
165°	966.4	967.5	968.6	969.8	970.9	970.9	969.8	968.6	967.5	966.4	965.9
167.5°	974.0	975.4	976.9	978.3	979.7	979.9	978.8	977.7	976.5	975.4	975.0
170°	978.6	980.0	981.4	982.9	984.3	984.5	983.3	982.2	981.1	980.0	979.7
172.5°	982.0	983.4	984.9	986.3	987.7	987.9	986.8	985.7	984.6	983.4	983.1
175°	985.0	986.6	988.2	989.8	991.4	991.6	990.5	989.4	988.3	987.2	986.8
177.5°	986.9	988.0	989.2	990.3	991.5	991.6	990.7	989.8	988.9	988.0	987.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331393
 CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1771.7	1767.4	1764.8	1755.2	1746.7	1738.2	1735.6	1736.6	1725.0	1713.8	1709.0
5°	1840.7	1827.4	1814.8	1796.9	1775.7	1752.4	1740.5	1731.2	1708.0	1682.8	1668.2
7.5°	1902.5	1883.5	1859.3	1825.6	1794.6	1758.1	1734.9	1714.3	1680.4	1644.8	1623.0
10°	1940.2	1914.3	1883.1	1842.0	1804.2	1759.7	1728.5	1697.4	1657.5	1615.1	1588.5
12.5°	1972.6	1937.7	1907.0	1854.2	1809.5	1753.9	1716.9	1672.9	1631.0	1580.6	1554.6
15°	2049.7	1985.3	1926.9	1867.2	1812.1	1734.5	1693.4	1634.3	1579.2	1516.9	1487.0
17.5°	2109.3	2037.0	1945.0	1869.1	1804.8	1718.9	1658.5	1587.7	1522.6	1451.3	1410.7
20°	2143.3	2060.3	1961.4	1871.2	1794.2	1696.0	1630.3	1558.0	1481.7	1401.4	1357.6
22.5°	2163.4	2076.2	1978.4	1863.2	1773.0	1677.4	1594.8	1515.5	1438.2	1351.5	1305.6
25°	2169.8	2090.2	1986.7	1856.6	1746.5	1638.3	1538.8	1461.8	1368.2	1287.3	1220.3
27.5°	2138.2	2081.1	1981.6	1844.1	1715.8	1589.3	1478.4	1391.2	1292.5	1204.6	1137.2
30°	2099.5	2066.3	1969.4	1831.4	1691.4	1555.4	1433.3	1334.4	1236.2	1147.3	1078.3
32.5°	2039.5	2032.3	1947.1	1813.3	1665.4	1512.4	1386.0	1286.1	1177.3	1089.9	1024.1
35°	1921.6	1953.5	1899.7	1773.0	1616.4	1451.2	1314.5	1200.4	1087.6	1003.9	942.2
37.5°	1763.7	1842.8	1828.7	1713.9	1550.3	1384.6	1233.7	1114.4	1006.9	922.5	861.9
40°	1654.9	1755.7	1770.3	1668.8	1503.6	1333.1	1173.2	1054.4	949.5	872.6	811.5
42.5°	1538.1	1655.9	1696.0	1614.7	1452.6	1278.9	1119.0	996.0	892.2	817.4	763.2
45°	1342.4	1498.3	1570.6	1524.2	1367.6	1189.7	1025.2	900.4	806.2	735.9	694.1
47.5°	1159.3	1329.7	1427.0	1410.6	1272.9	1096.8	934.1	814.4	722.7	666.6	629.2
50°	1029.8	1205.0	1322.4	1327.8	1205.0	1030.5	867.3	754.5	670.2	617.8	587.2
52.5°	917.3	1084.5	1212.6	1240.7	1129.1	961.5	807.3	695.0	620.8	572.6	545.3
55°	770.4	911.7	1053.7	1105.5	1015.9	856.6	714.0	615.1	545.4	512.3	488.4
57.5°	640.5	758.3	889.4	946.6	891.4	755.1	621.3	535.5	478.9	449.9	431.6
60°	572.0	664.9	781.7	850.0	802.2	680.8	564.0	482.4	436.0	410.1	392.8
62.5°	508.3	590.6	689.3	751.8	725.8	611.3	506.7	434.6	394.5	370.3	357.8
65°	419.4	484.4	560.7	618.4	601.2	514.2	428.7	366.9	335.1	315.8	305.9
67.5°	345.3	392.3	445.2	495.8	481.9	420.3	351.5	303.5	279.8	263.2	257.2
70°	298.6	334.4	381.5	422.0	410.7	360.3	305.9	264.8	244.2	230.3	224.3
72.5°	254.0	283.5	319.4	352.5	344.9	303.0	257.6	226.5	210.7	197.9	193.0
75°	191.8	214.3	236.2	258.1	256.1	223.6	197.1	173.2	160.6	150.6	148.6
77.5°	141.6	154.2	169.1	182.1	178.5	159.9	139.1	125.4	116.1	109.5	108.4
80°	108.2	115.5	126.1	135.4	130.7	122.8	106.2	96.2	89.6	82.9	80.3
82.5°	78.4	85.7	92.1	97.1	93.6	86.1	75.9	69.1	65.2	60.6	59.6
85°	41.1	45.1	47.8	49.1	47.8	43.1	38.5	35.8	32.5	30.5	29.9
87.5°	18.3	18.0	17.8	18.5	16.6	16.2	13.8	11.8	11.6	11.5	10.7
90°	11.8	10.5	9.2	7.7	6.0	4.2	2.5	0.7	2.5	4.2	6.0
92.5°	15.3	14.7	14.1	13.8	14.0	14.1	14.3	14.4	14.3	14.1	14.0
95°	25.7	24.6	23.4	25.5	30.8	36.0	41.3	46.5	41.3	36.0	30.8
97.5°	32.2	29.6	27.0	33.1	47.9	62.7	77.5	92.3	77.5	62.7	47.9
100°	35.4	32.7	30.0	39.5	61.3	83.1	104.8	126.6	104.8	83.1	61.3
102.5°	87.1	109.7	132.3	145.9	150.6	155.2	159.8	164.4	159.8	155.2	150.6
105°	130.4	173.8	217.2	236.5	231.8	227.0	222.2	217.5	222.2	227.0	231.8
107.5°	165.2	217.2	269.3	293.4	289.5	285.7	281.8	278.0	281.8	285.7	289.5
110°	217.1	263.0	308.9	330.2	326.9	323.6	320.2	316.9	320.2	323.6	326.9



TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	338.4	349.8	361.1	365.3	362.4	359.4	356.5	353.5	356.5	359.4	362.4
115°	433.4	429.4	425.5	422.1	419.4	416.7	414.0	411.3	414.0	416.7	419.4
117.5°	483.4	480.7	477.9	475.0	472.0	469.0	466.0	463.0	466.0	469.0	472.0
120°	518.6	515.8	512.9	510.3	507.9	505.5	503.1	500.7	503.1	505.5	507.9
122.5°	551.9	548.8	545.6	542.8	540.3	537.8	535.3	532.8	535.3	537.8	540.3
125°	598.4	595.4	592.4	589.8	587.8	585.7	583.6	581.6	583.6	585.7	587.8
127.5°	641.7	639.5	637.2	634.9	632.6	630.4	628.1	625.8	628.1	630.4	632.6
130°	669.6	667.9	666.1	664.0	661.4	658.9	656.4	653.8	656.4	658.9	661.4
132.5°	696.5	694.8	693.0	691.1	688.9	686.8	684.6	682.4	684.6	686.8	688.9
135°	734.6	733.2	731.8	729.8	727.3	724.7	722.2	719.6	722.2	724.7	727.3
137.5°	769.3	767.7	766.1	764.4	762.6	760.8	759.0	757.3	759.0	760.8	762.6
140°	792.0	790.2	788.5	786.9	785.7	784.4	783.1	781.9	783.1	784.4	785.7
142.5°	812.6	810.6	808.6	807.0	805.9	804.8	803.6	802.5	803.6	804.8	805.9
145°	840.8	838.1	835.4	834.2	834.3	834.5	834.6	834.8	834.6	834.5	834.3
147.5°	866.9	864.3	861.6	860.6	861.2	861.8	862.4	863.0	862.4	861.8	861.2
150°	882.6	880.1	877.6	876.8	878.0	879.1	880.2	881.3	880.2	879.1	878.0
152.5°	897.2	894.8	892.4	891.8	893.0	894.3	895.5	896.7	895.5	894.3	893.0
155°	917.5	915.6	913.7	913.5	914.9	916.3	917.8	919.2	917.8	916.3	914.9
157.5°	934.7	933.4	932.0	932.0	933.2	934.4	935.6	936.8	935.6	934.4	933.2
160°	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1	946.1	945.2	944.2
162.5°	954.0	953.2	952.4	952.4	953.4	954.4	955.3	956.3	955.3	954.4	953.4
165°	965.5	965.0	964.5	964.7	965.7	966.7	967.6	968.6	967.6	966.7	965.7
167.5°	974.5	974.1	973.6	973.9	974.9	975.8	976.8	977.7	976.8	975.8	974.9
170°	979.4	979.1	978.7	979.1	980.0	981.0	981.9	982.9	981.9	981.0	980.0
172.5°	982.8	982.5	982.2	982.5	983.4	984.4	985.3	986.3	985.3	984.4	983.4
175°	986.5	986.2	985.9	986.3	987.4	988.5	989.6	990.7	989.6	988.5	987.4
177.5°	987.8	987.6	987.5	987.9	988.8	989.7	990.6	991.5	990.6	989.7	988.8
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1703.7	1700.5	1689.4	1683.6	1674.0	1665.0	1659.1	1661.8	1663.9	1662.8	1661.3
5°	1654.9	1642.3	1623.0	1606.4	1594.5	1572.6	1563.3	1558.7	1554.7	1550.0	1545.4
7.5°	1596.8	1576.9	1549.2	1525.6	1503.3	1476.1	1460.6	1451.3	1441.8	1431.3	1422.0
10°	1555.4	1527.5	1498.3	1465.1	1438.6	1414.0	1392.1	1377.5	1364.3	1351.6	1342.4
12.5°	1511.8	1479.7	1443.6	1398.2	1369.0	1333.9	1330.5	1304.8	1284.1	1276.3	1265.4
15°	1442.6	1397.4	1351.6	1297.9	1274.7	1242.8	1222.9	1203.0	1185.1	1172.5	1169.2
17.5°	1363.9	1305.5	1259.9	1221.3	1183.2	1150.6	1132.3	1116.4	1101.6	1084.8	1082.5
20°	1303.9	1253.4	1203.7	1169.8	1130.7	1097.5	1074.9	1059.0	1046.4	1036.5	1027.8
22.5°	1247.1	1191.9	1146.3	1109.3	1070.7	1043.9	1026.1	1010.7	1000.2	989.2	981.1
25°	1155.9	1112.8	1063.0	1021.2	989.3	972.1	957.5	944.2	937.6	930.3	921.0
27.5°	1076.1	1028.2	981.7	949.3	921.3	906.0	895.7	886.6	880.4	876.1	870.8
30°	1019.9	971.4	934.9	903.1	879.9	864.6	858.0	852.7	845.4	842.7	840.1
32.5°	965.7	922.1	890.9	863.3	841.1	831.2	825.1	820.3	814.6	811.9	806.6
35°	889.2	852.7	822.1	806.9	789.0	780.3	775.7	769.1	763.7	761.1	760.4
37.5°	817.1	785.4	765.3	745.7	738.1	732.8	726.5	721.9	720.3	719.9	719.3
40°	770.4	744.5	726.6	710.7	707.3	699.4	694.1	690.1	690.1	690.8	690.1
42.5°	727.9	704.7	688.9	675.1	671.2	666.5	661.2	660.9	662.0	664.2	662.0
45°	663.5	647.0	635.7	629.0	621.7	617.1	616.4	618.4	619.1	619.8	621.7
47.5°	604.4	593.3	583.1	575.8	572.6	571.8	571.0	574.5	577.7	578.9	581.9
50°	569.3	556.7	548.1	543.4	540.8	539.5	540.8	544.8	547.4	550.7	552.7
52.5°	530.0	521.1	515.2	511.6	510.5	511.3	511.6	516.1	520.4	521.5	522.5
55°	475.8	469.1	467.8	461.8	464.5	463.8	467.1	469.8	473.8	477.8	478.4
57.5°	421.6	416.3	412.7	413.3	414.1	417.0	419.8	424.4	428.7	432.9	433.3
60°	385.5	382.9	380.9	380.9	382.2	386.2	389.5	394.1	396.8	399.5	401.4
62.5°	352.6	350.0	348.0	349.0	352.5	354.9	358.7	361.2	363.9	366.5	367.5
65°	300.6	299.3	301.3	302.6	303.2	306.6	311.2	313.2	315.8	317.2	321.8
67.5°	252.7	252.9	252.7	254.5	258.4	259.2	263.6	268.2	268.7	271.3	274.3
70°	220.3	221.6	223.0	224.3	227.6	228.9	232.2	234.2	236.9	238.9	240.9
72.5°	190.6	190.8	192.2	191.9	194.7	197.6	200.4	202.4	205.0	207.6	209.5
75°	146.6	146.6	148.0	148.6	152.0	155.3	154.6	155.9	158.6	161.2	162.6
77.5°	107.1	105.6	107.1	107.8	108.8	111.6	112.1	114.0	117.0	116.1	117.6
80°	81.6	79.6	81.6	82.3	82.3	85.6	85.6	86.9	88.9	86.9	88.9
82.5°	58.3	57.3	58.8	58.9	60.0	60.1	61.2	61.4	63.4	62.5	63.4
85°	29.2	28.5	29.2	28.5	29.2	29.9	29.9	29.2	29.2	30.5	28.5
87.5°	10.6	10.3	10.1	10.3	10.0	9.8	9.4	9.5	9.7	8.8	8.9
90°	7.7	9.2	10.5	11.8	13.0	14.3	15.1	15.9	16.7	17.5	18.0
92.5°	13.8	14.1	14.7	15.3	16.0	16.6	17.0	17.4	17.8	18.2	18.6
95°	25.5	23.4	24.6	25.7	26.8	27.9	28.7	29.5	30.3	31.1	31.4
97.5°	33.1	27.0	29.6	32.2	34.8	37.3	38.0	38.6	39.2	39.9	40.3
100°	39.5	30.0	32.7	35.4	38.1	40.8	42.0	43.3	44.6	45.9	46.7
102.5°	145.9	132.3	109.7	87.1	64.5	41.9	43.6	45.2	46.9	48.5	49.6
105°	236.5	217.2	173.8	130.4	87.0	43.6	45.4	47.1	48.9	50.6	51.8
107.5°	293.4	269.3	217.2	165.2	113.1	61.1	59.3	57.5	55.7	54.0	53.4
110°	330.2	308.9	263.0	217.1	171.1	125.2	109.3	93.4	77.5	61.6	54.0



TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	365.3	361.1	349.8	338.4	327.1	315.7	257.8	199.8	141.8	83.8	55.0
115°	422.1	425.5	429.4	433.4	437.4	441.4	367.8	294.2	220.6	147.0	104.4
117.5°	475.0	477.9	480.7	483.4	486.1	488.9	471.1	453.3	435.4	417.6	389.9
120°	510.3	512.9	515.8	518.6	521.5	524.3	526.2	528.2	530.1	532.0	522.2
122.5°	542.8	545.6	548.8	551.9	555.0	558.1	559.2	560.4	561.5	562.7	561.2
125°	589.8	592.4	595.4	598.4	601.4	604.5	605.6	606.7	607.8	608.9	609.7
127.5°	634.9	637.2	639.5	641.7	644.0	646.2	647.9	649.5	651.1	652.7	653.6
130°	664.0	666.1	667.9	669.6	671.4	673.1	674.9	676.6	678.4	680.1	680.9
132.5°	691.1	693.0	694.8	696.5	698.3	700.0	701.5	703.0	704.5	706.0	706.7
135°	729.8	731.8	733.2	734.6	736.1	737.5	739.1	740.7	742.3	743.9	744.5
137.5°	764.4	766.1	767.7	769.3	770.9	772.6	774.1	775.7	777.2	778.8	779.3
140°	786.9	788.5	790.2	792.0	793.7	795.5	796.9	798.3	799.7	801.2	801.5
142.5°	807.0	808.6	810.6	812.6	814.6	816.6	817.9	819.2	820.5	821.8	822.1
145°	834.2	835.4	838.1	840.8	843.5	846.2	847.4	848.5	849.6	850.7	850.8
147.5°	860.6	861.6	864.3	866.9	869.6	872.3	873.1	873.9	874.8	875.6	875.7
150°	876.8	877.6	880.1	882.6	885.2	887.7	888.7	889.6	890.6	891.5	891.6
152.5°	891.8	892.4	894.8	897.2	899.6	902.0	903.0	903.9	904.9	905.9	905.8
155°	913.5	913.7	915.6	917.5	919.4	921.3	922.3	923.3	924.2	925.2	925.0
157.5°	932.0	932.0	933.4	934.7	936.0	937.4	938.5	939.5	940.6	941.7	941.6
160°	943.3	943.3	944.2	945.2	946.1	947.1	948.1	949.0	950.0	950.9	950.8
162.5°	952.4	952.4	953.2	954.0	954.9	955.7	956.8	957.8	958.9	960.0	959.9
165°	964.7	964.5	965.0	965.5	965.9	966.4	967.5	968.6	969.8	970.9	970.9
167.5°	973.9	973.6	974.1	974.5	975.0	975.4	976.5	977.7	978.8	979.9	979.7
170°	979.1	978.7	979.1	979.4	979.7	980.0	981.1	982.2	983.3	984.5	984.3
172.5°	982.5	982.2	982.5	982.8	983.1	983.4	984.6	985.7	986.8	987.9	987.7
175°	986.3	985.9	986.2	986.5	986.8	987.2	988.3	989.4	990.5	991.6	991.4
177.5°	987.9	987.5	987.6	987.8	987.9	988.0	988.9	989.8	990.7	991.6	991.5
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1655.9	1654.9	1654.9	1650.1	1654.9	1654.9	1655.9	1661.3	1662.8	1663.9	1661.8
5°	1536.1	1534.1	1530.8	1534.1	1530.8	1534.1	1536.1	1545.4	1550.0	1554.7	1558.7
7.5°	1417.6	1409.6	1408.4	1400.6	1408.4	1409.6	1417.6	1422.0	1431.3	1441.8	1451.3
10°	1331.1	1325.8	1325.1	1312.5	1325.1	1325.8	1331.1	1342.4	1351.6	1364.3	1377.5
12.5°	1265.3	1252.5	1255.0	1247.7	1255.0	1252.5	1265.3	1265.4	1276.3	1284.1	1304.8
15°	1151.3	1151.3	1148.6	1137.3	1148.6	1151.3	1151.3	1169.2	1172.5	1185.1	1203.0
17.5°	1069.4	1068.0	1061.7	1064.9	1061.7	1068.0	1069.4	1082.5	1084.8	1101.6	1116.4
20°	1020.5	1016.6	1008.6	1008.6	1008.6	1016.6	1020.5	1027.8	1036.5	1046.4	1059.0
22.5°	974.4	974.1	965.6	968.2	965.6	974.1	974.4	981.1	989.2	1000.2	1010.7
25°	920.3	915.0	911.1	913.0	911.1	915.0	920.3	921.0	930.3	937.6	944.2
27.5°	869.1	866.2	865.9	860.5	865.9	866.2	869.1	870.8	876.1	880.4	886.6
30°	839.4	832.8	834.1	830.8	834.1	832.8	839.4	840.1	842.7	845.4	852.7
32.5°	805.4	803.0	801.7	798.9	801.7	803.0	805.4	806.6	811.9	814.6	820.3
35°	759.1	759.8	756.4	757.8	756.4	759.8	759.1	760.4	761.1	763.7	769.1
37.5°	718.6	720.7	719.2	719.6	719.2	720.7	718.6	719.3	719.9	720.3	721.9
40°	692.1	692.1	692.1	694.1	692.1	692.1	692.1	690.1	690.8	690.1	690.1
42.5°	666.6	665.5	664.5	664.3	664.5	665.5	666.6	662.0	664.2	662.0	660.9
45°	623.1	625.1	625.7	622.4	625.7	625.1	623.1	621.7	619.8	619.1	618.4
47.5°	583.7	583.9	583.7	586.6	583.7	583.9	583.7	581.9	578.9	577.7	574.5
50°	556.1	554.7	556.1	554.7	556.1	554.7	556.1	552.7	550.7	547.4	544.8
52.5°	526.9	527.1	526.3	526.1	526.3	527.1	526.9	522.5	521.5	520.4	516.1
55°	481.1	482.4	481.7	481.7	481.7	482.4	481.1	478.4	477.8	473.8	469.8
57.5°	433.7	434.9	435.8	432.9	435.8	434.9	433.7	433.3	432.9	428.7	424.4
60°	400.8	404.1	403.4	402.1	403.4	404.1	400.8	401.4	399.5	396.8	394.1
62.5°	370.5	371.7	371.6	371.3	371.6	371.7	370.5	367.5	366.5	363.9	361.2
65°	323.8	325.1	323.1	325.1	323.1	325.1	323.8	321.8	317.2	315.8	313.2
67.5°	273.5	273.9	275.4	276.3	275.4	273.9	273.5	274.3	271.3	268.7	268.2
70°	242.2	241.5	243.5	245.5	243.5	241.5	242.2	240.9	238.9	236.9	234.2
72.5°	209.3	210.7	210.1	211.5	210.1	210.7	209.3	209.5	207.6	205.0	202.4
75°	161.2	163.2	162.6	164.6	162.6	163.2	161.2	162.6	161.2	158.6	155.9
77.5°	116.5	116.8	116.5	117.6	116.5	116.8	116.5	117.6	116.1	117.0	114.0
80°	88.9	87.6	86.3	88.9	86.3	87.6	88.9	88.9	86.9	88.9	86.9
82.5°	61.8	62.6	61.3	61.3	61.3	62.6	61.8	63.4	62.5	63.4	61.4
85°	28.5	27.9	26.5	26.5	26.5	27.9	28.5	28.5	30.5	29.2	29.2
87.5°	9.0	8.5	8.6	8.1	8.6	8.5	9.0	8.9	8.8	9.7	9.5
90°	18.4	18.7	19.0	19.3	19.0	18.7	18.4	18.0	17.5	16.7	15.9
92.5°	18.7	18.9	19.1	19.3	19.1	18.9	18.7	18.6	18.2	17.8	17.4
95°	31.2	31.1	30.9	30.8	30.9	31.1	31.2	31.4	31.1	30.3	29.5
97.5°	40.5	40.7	40.9	41.1	40.9	40.7	40.5	40.3	39.9	39.2	38.6
100°	47.0	47.3	47.6	47.9	47.6	47.3	47.0	46.7	45.9	44.6	43.3
102.5°	50.0	50.5	50.9	51.4	50.9	50.5	50.0	49.6	48.5	46.9	45.2
105°	52.5	53.1	53.7	54.4	53.7	53.1	52.5	51.8	50.6	48.9	47.1
107.5°	54.0	54.7	55.3	55.9	55.3	54.7	54.0	53.4	54.0	55.7	57.5
110°	54.6	55.2	55.9	56.5	55.9	55.2	54.6	54.0	61.6	77.5	93.4



TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	55.6	56.1	56.6	57.1	56.6	56.1	55.6	55.0	83.8	141.8	199.8
115°	93.0	81.5	70.1	58.7	70.1	81.5	93.0	104.4	147.0	220.6	294.2
117.5°	352.3	314.7	277.1	239.5	277.1	314.7	352.3	389.9	417.6	435.4	453.3
120°	500.7	479.3	457.8	436.4	457.8	479.3	500.7	522.2	532.0	530.1	528.2
122.5°	557.0	552.8	548.7	544.5	548.7	552.8	557.0	561.2	562.7	561.5	560.4
125°	610.2	610.7	611.1	611.6	611.1	610.7	610.2	609.7	608.9	607.8	606.7
127.5°	653.7	653.8	653.9	654.0	653.9	653.8	653.7	653.6	652.7	651.1	649.5
130°	680.8	680.6	680.4	680.3	680.4	680.6	680.8	680.9	680.1	678.4	676.6
132.5°	706.5	706.4	706.2	706.0	706.2	706.4	706.5	706.7	706.0	704.5	703.0
135°	744.2	743.9	743.5	743.2	743.5	743.9	744.2	744.5	743.9	742.3	740.7
137.5°	778.8	778.2	777.7	777.1	777.7	778.2	778.8	779.3	778.8	777.2	775.7
140°	800.7	799.9	799.1	798.3	799.1	799.9	800.7	801.5	801.2	799.7	798.3
142.5°	821.3	820.5	819.7	818.9	819.7	820.5	821.3	822.1	821.8	820.5	819.2
145°	850.1	849.3	848.5	847.7	848.5	849.3	850.1	850.8	850.7	849.6	848.5
147.5°	875.0	874.3	873.7	873.0	873.7	874.3	875.0	875.7	875.6	874.8	873.9
150°	890.8	890.0	889.2	888.4	889.2	890.0	890.8	891.6	891.5	890.6	889.6
152.5°	904.8	903.7	902.7	901.6	902.7	903.7	904.8	905.8	905.9	904.9	903.9
155°	923.7	922.5	921.2	919.9	921.2	922.5	923.7	925.0	925.2	924.2	923.3
157.5°	940.4	939.1	937.9	936.7	937.9	939.1	940.4	941.6	941.7	940.6	939.5
160°	949.7	948.6	947.5	946.4	947.5	948.6	949.7	950.8	950.9	950.0	949.0
162.5°	958.5	957.1	955.8	954.4	955.8	957.1	958.5	959.9	960.0	958.9	957.8
165°	969.8	968.6	967.5	966.4	967.5	968.6	969.8	970.9	970.9	969.8	968.6
167.5°	978.3	976.9	975.4	974.0	975.4	976.9	978.3	979.7	979.9	978.8	977.7
170°	982.9	981.4	980.0	978.6	980.0	981.4	982.9	984.3	984.5	983.3	982.2
172.5°	986.3	984.9	983.4	982.0	983.4	984.9	986.3	987.7	987.9	986.8	985.7
175°	989.8	988.2	986.6	985.0	986.6	988.2	989.8	991.4	991.6	990.5	989.4
177.5°	990.3	989.2	988.0	986.9	988.0	989.2	990.3	991.5	991.6	990.7	989.8
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1659.1	1665.0	1674.0	1683.6	1689.4	1700.5	1703.7	1709.0	1713.8	1725.0	1736.6
5°	1563.3	1572.6	1594.5	1606.4	1623.0	1642.3	1654.9	1668.2	1682.8	1708.0	1731.2
7.5°	1460.6	1476.1	1503.3	1525.6	1549.2	1576.9	1596.8	1623.0	1644.8	1680.4	1714.3
10°	1392.1	1414.0	1438.6	1465.1	1498.3	1527.5	1555.4	1588.5	1615.1	1657.5	1697.4
12.5°	1330.5	1333.9	1369.0	1398.2	1443.6	1479.7	1511.8	1554.6	1580.6	1631.0	1672.9
15°	1222.9	1242.8	1274.7	1297.9	1351.6	1397.4	1442.6	1487.0	1516.9	1579.2	1634.3
17.5°	1132.3	1150.6	1183.2	1221.3	1259.9	1305.5	1363.9	1410.7	1451.3	1522.6	1587.7
20°	1074.9	1097.5	1130.7	1169.8	1203.7	1253.4	1303.9	1357.6	1401.4	1481.7	1558.0
22.5°	1026.1	1043.9	1070.7	1109.3	1146.3	1191.9	1247.1	1305.6	1351.5	1438.2	1515.5
25°	957.5	972.1	989.3	1021.2	1063.0	1112.8	1155.9	1220.3	1287.3	1368.2	1461.8
27.5°	895.7	906.0	921.3	949.3	981.7	1028.2	1076.1	1137.2	1204.6	1292.5	1391.2
30°	858.0	864.6	879.9	903.1	934.9	971.4	1019.9	1078.3	1147.3	1236.2	1334.4
32.5°	825.1	831.2	841.1	863.3	890.9	922.1	965.7	1024.1	1089.9	1177.3	1286.1
35°	775.7	780.3	789.0	806.9	822.1	852.7	889.2	942.2	1003.9	1087.6	1200.4
37.5°	726.5	732.8	738.1	745.7	765.3	785.4	817.1	861.9	922.5	1006.9	1114.4
40°	694.1	699.4	707.3	710.7	726.6	744.5	770.4	811.5	872.6	949.5	1054.4
42.5°	661.2	666.5	671.2	675.1	688.9	704.7	727.9	763.2	817.4	892.2	996.0
45°	616.4	617.1	621.7	629.0	635.7	647.0	663.5	694.1	735.9	806.2	900.4
47.5°	571.0	571.8	572.6	575.8	583.1	593.3	604.4	629.2	666.6	722.7	814.4
50°	540.8	539.5	540.8	543.4	548.1	556.7	569.3	587.2	617.8	670.2	754.5
52.5°	511.6	511.3	510.5	511.6	515.2	521.1	530.0	545.3	572.6	620.8	695.0
55°	467.1	463.8	464.5	461.8	467.8	469.1	475.8	488.4	512.3	545.4	615.1
57.5°	419.8	417.0	414.1	413.3	412.7	416.3	421.6	431.6	449.9	478.9	535.5
60°	389.5	386.2	382.2	380.9	380.9	382.9	385.5	392.8	410.1	436.0	482.4
62.5°	358.7	354.9	352.5	349.0	348.0	350.0	352.6	357.8	370.3	394.5	434.6
65°	311.2	306.6	303.2	302.6	301.3	299.3	300.6	305.9	315.8	335.1	366.9
67.5°	263.6	259.2	258.4	254.5	252.7	252.9	252.7	257.2	263.2	279.8	303.5
70°	232.2	228.9	227.6	224.3	223.0	221.6	220.3	224.3	230.3	244.2	264.8
72.5°	200.4	197.6	194.7	191.9	192.2	190.8	190.6	193.0	197.9	210.7	226.5
75°	154.6	155.3	152.0	148.6	148.0	146.6	146.6	148.6	150.6	160.6	173.2
77.5°	112.1	111.6	108.8	107.8	107.1	105.6	107.1	108.4	109.5	116.1	125.4
80°	85.6	85.6	82.3	82.3	81.6	79.6	81.6	80.3	82.9	89.6	96.2
82.5°	61.2	60.1	60.0	58.9	58.8	57.3	58.3	59.6	60.6	65.2	69.1
85°	29.9	29.9	29.2	28.5	29.2	28.5	29.2	29.9	30.5	32.5	35.8
87.5°	9.4	9.8	10.0	10.3	10.1	10.3	10.6	10.7	11.5	11.6	11.8
90°	15.1	14.3	13.0	11.8	10.5	9.2	7.7	6.0	4.2	2.5	0.7
92.5°	17.0	16.6	16.0	15.3	14.7	14.1	13.8	14.0	14.1	14.3	14.4
95°	28.7	27.9	26.8	25.7	24.6	23.4	25.5	30.8	36.0	41.3	46.5
97.5°	38.0	37.3	34.8	32.2	29.6	27.0	33.1	47.9	62.7	77.5	92.3
100°	42.0	40.8	38.1	35.4	32.7	30.0	39.5	61.3	83.1	104.8	126.6
102.5°	43.6	41.9	64.5	87.1	109.7	132.3	145.9	150.6	155.2	159.8	164.4
105°	45.4	43.6	87.0	130.4	173.8	217.2	236.5	231.8	227.0	222.2	217.5
107.5°	59.3	61.1	113.1	165.2	217.2	269.3	293.4	289.5	285.7	281.8	278.0
110°	109.3	125.2	171.1	217.1	263.0	308.9	330.2	326.9	323.6	320.2	316.9



TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	257.8	315.7	327.1	338.4	349.8	361.1	365.3	362.4	359.4	356.5	353.5
115°	367.8	441.4	437.4	433.4	429.4	425.5	422.1	419.4	416.7	414.0	411.3
117.5°	471.1	488.9	486.1	483.4	480.7	477.9	475.0	472.0	469.0	466.0	463.0
120°	526.2	524.3	521.5	518.6	515.8	512.9	510.3	507.9	505.5	503.1	500.7
122.5°	559.2	558.1	555.0	551.9	548.8	545.6	542.8	540.3	537.8	535.3	532.8
125°	605.6	604.5	601.4	598.4	595.4	592.4	589.8	587.8	585.7	583.6	581.6
127.5°	647.9	646.2	644.0	641.7	639.5	637.2	634.9	632.6	630.4	628.1	625.8
130°	674.9	673.1	671.4	669.6	667.9	666.1	664.0	661.4	658.9	656.4	653.8
132.5°	701.5	700.0	698.3	696.5	694.8	693.0	691.1	688.9	686.8	684.6	682.4
135°	739.1	737.5	736.1	734.6	733.2	731.8	729.8	727.3	724.7	722.2	719.6
137.5°	774.1	772.6	770.9	769.3	767.7	766.1	764.4	762.6	760.8	759.0	757.3
140°	796.9	795.5	793.7	792.0	790.2	788.5	786.9	785.7	784.4	783.1	781.9
142.5°	817.9	816.6	814.6	812.6	810.6	808.6	807.0	805.9	804.8	803.6	802.5
145°	847.4	846.2	843.5	840.8	838.1	835.4	834.2	834.3	834.5	834.6	834.8
147.5°	873.1	872.3	869.6	866.9	864.3	861.6	860.6	861.2	861.8	862.4	863.0
150°	888.7	887.7	885.2	882.6	880.1	877.6	876.8	878.0	879.1	880.2	881.3
152.5°	903.0	902.0	899.6	897.2	894.8	892.4	891.8	893.0	894.3	895.5	896.7
155°	922.3	921.3	919.4	917.5	915.6	913.7	913.5	914.9	916.3	917.8	919.2
157.5°	938.5	937.4	936.0	934.7	933.4	932.0	932.0	933.2	934.4	935.6	936.8
160°	948.1	947.1	946.1	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1
162.5°	956.8	955.7	954.9	954.0	953.2	952.4	952.4	953.4	954.4	955.3	956.3
165°	967.5	966.4	965.9	965.5	965.0	964.5	964.7	965.7	966.7	967.6	968.6
167.5°	976.5	975.4	975.0	974.5	974.1	973.6	973.9	974.9	975.8	976.8	977.7
170°	981.1	980.0	979.7	979.4	979.1	978.7	979.1	980.0	981.0	981.9	982.9
172.5°	984.6	983.4	983.1	982.8	982.5	982.2	982.5	983.4	984.4	985.3	986.3
175°	988.3	987.2	986.8	986.5	986.2	985.9	986.3	987.4	988.5	989.6	990.7
177.5°	988.9	988.0	987.9	987.8	987.6	987.5	987.9	988.8	989.7	990.6	991.5
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331393
 CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1735.6	1738.2	1746.7	1755.2	1764.8	1767.4	1771.7	1768.0	1766.9	1777.0	1784.4
5°	1740.5	1752.4	1775.7	1796.9	1814.8	1827.4	1840.7	1846.0	1855.9	1869.9	1887.1
7.5°	1734.9	1758.1	1794.6	1825.6	1859.3	1883.5	1902.5	1918.7	1938.4	1964.8	1993.6
10°	1728.5	1759.7	1804.2	1842.0	1883.1	1914.3	1940.2	1965.4	1994.6	2031.1	2068.9
12.5°	1716.9	1753.9	1809.5	1854.2	1907.0	1937.7	1972.6	2027.0	2058.3	2109.2	2162.4
15°	1693.4	1734.5	1812.1	1867.2	1926.9	1985.3	2049.7	2101.5	2153.2	2183.1	2258.1
17.5°	1658.5	1718.9	1804.8	1869.1	1945.0	2037.0	2109.3	2167.9	2227.7	2276.1	2313.7
20°	1630.3	1696.0	1794.2	1871.2	1961.4	2060.3	2143.3	2203.0	2254.7	2295.2	2318.4
22.5°	1594.8	1677.4	1773.0	1863.2	1978.4	2076.2	2163.4	2210.4	2253.7	2273.4	2282.3
25°	1538.8	1638.3	1746.5	1856.6	1986.7	2090.2	2169.8	2198.3	2210.9	2191.7	2159.8
27.5°	1478.4	1589.3	1715.8	1844.1	1981.6	2081.1	2138.2	2133.7	2112.3	2050.1	2000.3
30°	1433.3	1555.4	1691.4	1831.4	1969.4	2066.3	2099.5	2066.3	2017.8	1948.2	1877.2
32.5°	1386.0	1512.4	1665.4	1813.3	1947.1	2032.3	2039.5	1982.4	1907.4	1828.2	1739.7
35°	1314.5	1451.2	1616.4	1773.0	1899.7	1953.5	1921.6	1820.8	1731.9	1623.7	1502.9
37.5°	1233.7	1384.6	1550.3	1713.9	1828.7	1842.8	1763.7	1657.5	1532.1	1405.0	1262.9
40°	1173.2	1333.1	1503.6	1668.8	1770.3	1755.7	1654.9	1538.1	1388.8	1233.5	1101.5
42.5°	1119.0	1278.9	1452.6	1614.7	1696.0	1655.9	1538.1	1394.8	1234.3	1088.1	967.2
45°	1025.2	1189.7	1367.6	1524.2	1570.6	1498.3	1342.4	1183.1	1025.2	903.1	807.5
47.5°	934.1	1096.8	1272.9	1410.6	1427.0	1329.7	1159.3	995.5	859.7	760.3	692.9
50°	867.3	1030.5	1205.0	1327.8	1322.4	1205.0	1029.8	873.9	760.4	680.1	635.0
52.5°	807.3	961.5	1129.1	1240.7	1212.6	1084.5	917.3	778.9	685.6	622.8	581.9
55°	714.0	856.6	1015.9	1105.5	1053.7	911.7	770.4	658.9	589.9	542.8	510.9
57.5°	621.3	755.1	891.4	946.6	889.4	758.3	640.5	559.6	507.7	472.8	452.1
60°	564.0	680.8	802.2	850.0	781.7	664.9	572.0	499.7	457.8	429.3	410.7
62.5°	506.7	611.3	725.8	751.8	689.3	590.6	508.3	448.2	413.8	388.4	370.9
65°	428.7	514.2	601.2	618.4	560.7	484.4	419.4	380.2	349.7	331.1	317.2
67.5°	351.5	420.3	481.9	495.8	445.2	392.3	345.3	311.2	290.5	275.1	263.3
70°	305.9	360.3	410.7	422.0	381.5	334.4	298.6	271.4	252.8	239.5	228.3
72.5°	257.6	303.0	344.9	352.5	319.4	283.5	254.0	232.6	216.2	207.7	196.9
75°	197.1	223.6	256.1	258.1	236.2	214.3	191.8	177.8	169.2	158.6	153.3
77.5°	139.1	159.9	178.5	182.1	169.1	154.2	141.6	130.6	123.3	118.4	113.5
80°	106.2	122.8	130.7	135.4	126.1	115.5	108.2	100.9	96.2	92.9	89.6
82.5°	75.9	86.1	93.6	97.1	92.1	85.7	78.4	74.3	70.7	67.9	66.8
85°	38.5	43.1	47.8	49.1	47.8	45.1	41.1	41.1	39.1	38.5	38.5
87.5°	13.8	16.2	16.6	18.5	17.8	18.0	18.3	18.0	17.7	17.4	17.0
90°	2.5	4.2	6.0	7.7	9.2	10.5	11.8	13.0	14.3	15.1	15.9
92.5°	14.3	14.1	14.0	13.8	14.1	14.7	15.3	16.0	16.6	17.0	17.4
95°	41.3	36.0	30.8	25.5	23.4	24.6	25.7	26.8	27.9	28.7	29.5
97.5°	77.5	62.7	47.9	33.1	27.0	29.6	32.2	34.8	37.3	38.0	38.6
100°	104.8	83.1	61.3	39.5	30.0	32.7	35.4	38.1	40.8	42.0	43.3
102.5°	159.8	155.2	150.6	145.9	132.3	109.7	87.1	64.5	41.9	43.6	45.2
105°	222.2	227.0	231.8	236.5	217.2	173.8	130.4	87.0	43.6	45.4	47.1
107.5°	281.8	285.7	289.5	293.4	269.3	217.2	165.2	113.1	61.1	59.3	57.5
110°	320.2	323.6	326.9	330.2	308.9	263.0	217.1	171.1	125.2	109.3	93.4



TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	356.5	359.4	362.4	365.3	361.1	349.8	338.4	327.1	315.7	257.8	199.8
115°	414.0	416.7	419.4	422.1	425.5	429.4	433.4	437.4	441.4	367.8	294.2
117.5°	466.0	469.0	472.0	475.0	477.9	480.7	483.4	486.1	488.9	471.1	453.3
120°	503.1	505.5	507.9	510.3	512.9	515.8	518.6	521.5	524.3	526.2	528.2
122.5°	535.3	537.8	540.3	542.8	545.6	548.8	551.9	555.0	558.1	559.2	560.4
125°	583.6	585.7	587.8	589.8	592.4	595.4	598.4	601.4	604.5	605.6	606.7
127.5°	628.1	630.4	632.6	634.9	637.2	639.5	641.7	644.0	646.2	647.9	649.5
130°	656.4	658.9	661.4	664.0	666.1	667.9	669.6	671.4	673.1	674.9	676.6
132.5°	684.6	686.8	688.9	691.1	693.0	694.8	696.5	698.3	700.0	701.5	703.0
135°	722.2	724.7	727.3	729.8	731.8	733.2	734.6	736.1	737.5	739.1	740.7
137.5°	759.0	760.8	762.6	764.4	766.1	767.7	769.3	770.9	772.6	774.1	775.7
140°	783.1	784.4	785.7	786.9	788.5	790.2	792.0	793.7	795.5	796.9	798.3
142.5°	803.6	804.8	805.9	807.0	808.6	810.6	812.6	814.6	816.6	817.9	819.2
145°	834.6	834.5	834.3	834.2	835.4	838.1	840.8	843.5	846.2	847.4	848.5
147.5°	862.4	861.8	861.2	860.6	861.6	864.3	866.9	869.6	872.3	873.1	873.9
150°	880.2	879.1	878.0	876.8	877.6	880.1	882.6	885.2	887.7	888.7	889.6
152.5°	895.5	894.3	893.0	891.8	892.4	894.8	897.2	899.6	902.0	903.0	903.9
155°	917.8	916.3	914.9	913.5	913.7	915.6	917.5	919.4	921.3	922.3	923.3
157.5°	935.6	934.4	933.2	932.0	932.0	933.4	934.7	936.0	937.4	938.5	939.5
160°	946.1	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1	948.1	949.0
162.5°	955.3	954.4	953.4	952.4	952.4	953.2	954.0	954.9	955.7	956.8	957.8
165°	967.6	966.7	965.7	964.7	964.5	965.0	965.5	965.9	966.4	967.5	968.6
167.5°	976.8	975.8	974.9	973.9	973.6	974.1	974.5	975.0	975.4	976.5	977.7
170°	981.9	981.0	980.0	979.1	978.7	979.1	979.4	979.7	980.0	981.1	982.2
172.5°	985.3	984.4	983.4	982.5	982.2	982.5	982.8	983.1	983.4	984.6	985.7
175°	989.6	988.5	987.4	986.3	985.9	986.2	986.5	986.8	987.2	988.3	989.4
177.5°	990.6	989.7	988.8	987.9	987.5	987.6	987.8	987.9	988.0	988.9	989.8
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5	1726.5
2.5°	1790.8	1798.2	1798.2	1799.3	1807.8	1806.7	1806.2
5°	1905.7	1917.0	1918.3	1930.3	1938.2	1935.6	1928.3
7.5°	2014.1	2035.1	2051.0	2059.9	2070.4	2076.9	2074.0
10°	2100.1	2130.6	2149.2	2161.8	2177.1	2188.4	2184.4
12.5°	2178.2	2214.5	2240.0	2261.6	2263.6	2278.1	2268.3
15°	2299.9	2338.3	2342.3	2358.2	2370.9	2369.5	2370.2
17.5°	2340.1	2352.4	2354.9	2355.3	2355.5	2350.8	2340.7
20°	2325.7	2321.1	2309.8	2301.2	2285.9	2283.9	2270.7
22.5°	2257.8	2243.1	2214.8	2196.1	2172.3	2166.1	2162.4
25°	2124.0	2091.5	2046.4	2003.2	1991.3	1968.1	1974.7
27.5°	1940.5	1889.8	1840.9	1805.9	1774.2	1739.4	1749.4
30°	1811.5	1754.4	1685.4	1632.3	1598.5	1565.3	1559.3
32.5°	1657.5	1573.9	1497.0	1450.2	1398.4	1377.4	1354.4
35°	1392.1	1310.5	1234.2	1168.5	1130.7	1101.5	1074.9
37.5°	1153.4	1059.4	997.8	944.6	917.3	900.6	904.8
40°	1005.3	923.0	877.9	837.4	812.2	800.2	802.9
42.5°	885.3	823.7	786.6	758.8	741.0	734.4	732.8
45°	749.1	714.6	684.1	668.2	659.6	652.3	647.6
47.5°	656.2	628.1	610.9	601.4	593.9	586.4	586.3
50°	600.5	581.9	570.0	560.0	554.1	548.8	553.4
52.5°	558.0	541.1	529.1	520.2	518.0	513.2	513.1
55°	495.0	481.7	473.1	465.1	461.2	458.5	455.2
57.5°	437.7	425.1	417.1	412.1	404.5	401.8	400.8
60°	396.8	386.8	378.9	372.2	368.9	363.6	363.6
62.5°	359.1	349.2	341.7	336.7	331.2	329.1	329.7
65°	304.6	296.6	289.3	284.0	282.7	278.7	280.0
67.5°	254.4	249.1	241.4	238.5	236.0	233.8	232.2
70°	221.0	215.7	211.7	207.7	205.7	205.7	205.7
72.5°	192.8	186.5	184.1	179.0	180.2	178.1	176.0
75°	149.3	145.3	143.3	141.3	138.0	138.0	138.0
77.5°	109.9	108.7	106.3	104.2	103.4	102.7	103.0
80°	84.9	84.3	82.9	82.9	81.6	81.0	79.6
82.5°	65.3	63.6	62.8	62.2	62.0	61.8	61.6
85°	37.2	35.8	35.8	36.5	35.2	35.2	35.8
87.5°	17.7	17.8	17.4	17.5	18.1	17.6	17.7
90°	16.7	17.5	18.0	18.4	18.7	19.0	19.3
92.5°	17.8	18.2	18.6	18.7	18.9	19.1	19.3
95°	30.3	31.1	31.4	31.2	31.1	30.9	30.8
97.5°	39.2	39.9	40.3	40.5	40.7	40.9	41.1
100°	44.6	45.9	46.7	47.0	47.3	47.6	47.9
102.5°	46.9	48.5	49.6	50.0	50.5	50.9	51.4
105°	48.9	50.6	51.8	52.5	53.1	53.7	54.4
107.5°	55.7	54.0	53.4	54.0	54.7	55.3	55.9
110°	77.5	61.6	54.0	54.6	55.2	55.9	56.5



TEST NUMBER: P331393

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	141.8	83.8	55.0	55.6	56.1	56.6	57.1
115°	220.6	147.0	104.4	93.0	81.5	70.1	58.7
117.5°	435.4	417.6	389.9	352.3	314.7	277.1	239.5
120°	530.1	532.0	522.2	500.7	479.3	457.8	436.4
122.5°	561.5	562.7	561.2	557.0	552.8	548.7	544.5
125°	607.8	608.9	609.7	610.2	610.7	611.1	611.6
127.5°	651.1	652.7	653.6	653.7	653.8	653.9	654.0
130°	678.4	680.1	680.9	680.8	680.6	680.4	680.3
132.5°	704.5	706.0	706.7	706.5	706.4	706.2	706.0
135°	742.3	743.9	744.5	744.2	743.9	743.5	743.2
137.5°	777.2	778.8	779.3	778.8	778.2	777.7	777.1
140°	799.7	801.2	801.5	800.7	799.9	799.1	798.3
142.5°	820.5	821.8	822.1	821.3	820.5	819.7	818.9
145°	849.6	850.7	850.8	850.1	849.3	848.5	847.7
147.5°	874.8	875.6	875.7	875.0	874.3	873.7	873.0
150°	890.6	891.5	891.6	890.8	890.0	889.2	888.4
152.5°	904.9	905.9	905.8	904.8	903.7	902.7	901.6
155°	924.2	925.2	925.0	923.7	922.5	921.2	919.9
157.5°	940.6	941.7	941.6	940.4	939.1	937.9	936.7
160°	950.0	950.9	950.8	949.7	948.6	947.5	946.4
162.5°	958.9	960.0	959.9	958.5	957.1	955.8	954.4
165°	969.8	970.9	970.9	969.8	968.6	967.5	966.4
167.5°	978.8	979.9	979.7	978.3	976.9	975.4	974.0
170°	983.3	984.5	984.3	982.9	981.4	980.0	978.6
172.5°	986.8	987.9	987.7	986.3	984.9	983.4	982.0
175°	990.5	991.6	991.4	989.8	988.2	986.6	985.0
177.5°	990.7	991.6	991.5	990.3	989.2	988.0	986.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6

(END OF REPORT)