

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331714-927

Luminaire Tested: **SA2XXRDIP-C865D530U927-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331714-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4064.8 lumens
Efficiency: N/A
Efficacy: 83.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 48.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331714-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331714-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59				
1	100	96	92	89	93	90	87	84	78	76	74	68	66	64	58	56	55	51				
2	92	85	79	74	85	79	74	70	69	65	62	60	57	55	51	49	47	43				
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	43	41	37				
4	77	67	59	53	72	63	56	51	55	50	45	48	44	41	42	38	36	33				
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	38	34	32	29				
6	66	54	46	40	61	51	44	38	45	39	35	40	35	32	34	31	28	25				
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23				
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21				
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	23	21	19				
10	50	38	31	26	46	36	29	25	32	27	23	28	24	21	25	22	19	17				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18755	18755	18755
5°	18827	18519	18621
10°	18682	18216	18061
15°	18467	17677	17167
20°	18170	16905	16057
25°	17865	16030	14982
30°	17443	15129	13601
35°	17030	14152	12390
40°	16617	13139	10989
45°	16130	12001	9720
50°	15631	10854	8475
55°	15122	9619	7279
60°	14528	8315	6042
65°	13857	6988	5501
70°	13053	5755	5061
75°	12071	5246	4722
80°	10646	4695	4305
85°	8373	3705	3705



TEST NUMBER: P331714-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.7	2.7
10°-20°	298.5	7.3
20°-30°	419.2	10.3
30°-40°	457.1	11.2
40°-50°	420.3	10.3
50°-60°	330.1	8.1
60°-70°	215.2	5.3
70°-80°	111.0	2.7
80°-90°	30.2	0.7
90°-100°	19.1	0.5
100°-110°	69.9	1.7
110°-120°	186.8	4.6
120°-130°	308.4	7.6
130°-140°	328.0	8.1
140°-150°	304.8	7.5
150°-160°	245.1	6.0
160°-170°	157.9	3.9
170°-180°	54.4	1.3
0°-30°	826.5	20.3
0°-40°	1283.6	31.6
0°-60°	2034.0	50.0
0°-90°	2390.4	58.8
90°-120°	275.8	6.8
90°-150°	1217.0	29.9
90°-180°	1674.0	41.2
0°-180°	4064.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1162	1162	1162	1162	1162	
5°	1162	1156	1143	1151	1149	110
15°	1105	1092	1058	1038	1027	311
25°	1003	967	900	858	841	461
35°	864	808	718	654	629	541
45°	706	634	526	454	426	545
55°	537	453	342	281	259	480
65°	363	277	183	149	144	359
75°	194	122	84	77	76	205
85°	45	24	20	20	20	53
90°	0	5	8	10	11	3
95°	27	14	16	18	18	33
105°	126	131	25	30	31	134
115°	238	245	255	73	34	234
125°	336	342	349	352	354	300
135°	416	422	426	430	430	321
145°	482	482	489	492	490	302
155°	531	528	532	535	532	245
165°	560	558	558	561	558	158
175°	573	570	570	573	569	54
180°	571	571	571	571	571	



TEST NUMBER: P331714-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1165.8	1164.8	1163.9	1162.9	1162.1	1160.5	1158.5	1156.4	1154.4	1152.3	1154.2
5°	1161.6	1160.4	1159.2	1158.0	1156.9	1154.8	1151.8	1148.7	1145.7	1142.6	1144.7
7.5°	1149.5	1148.1	1146.7	1145.3	1143.8	1141.3	1137.7	1134.2	1130.6	1127.0	1127.7
10°	1139.5	1137.8	1136.2	1134.6	1132.9	1129.8	1125.1	1120.5	1115.8	1111.1	1110.4
12.5°	1126.9	1124.8	1122.8	1120.9	1118.8	1114.8	1108.8	1102.9	1096.9	1090.9	1089.6
15°	1104.8	1102.2	1099.6	1097.1	1094.5	1089.3	1081.3	1073.4	1065.4	1057.5	1053.0
17.5°	1077.7	1073.7	1069.8	1065.9	1062.0	1054.9	1044.7	1034.5	1024.4	1014.2	1008.9
20°	1057.5	1052.8	1048.1	1043.5	1038.8	1030.6	1018.9	1007.3	995.6	983.9	978.0
22.5°	1035.6	1030.4	1025.2	1019.9	1014.7	1005.5	992.3	979.1	966.0	952.8	945.2
25°	1002.8	995.4	987.9	980.4	973.0	961.5	946.0	930.7	915.2	899.8	890.3
27.5°	963.3	955.1	947.1	938.9	930.8	918.1	900.6	883.3	865.9	848.5	837.3
30°	935.6	926.7	917.8	908.9	900.1	886.3	867.6	848.9	830.2	811.5	799.6
32.5°	908.6	898.3	887.9	877.5	867.1	852.5	833.4	814.3	795.3	776.2	762.6
35°	864.0	852.2	840.3	828.3	816.4	800.2	779.6	759.1	738.6	718.0	703.2
37.5°	819.5	806.4	793.4	780.2	767.1	749.6	727.8	705.8	684.0	662.0	645.8
40°	788.4	774.4	760.3	746.3	732.3	714.0	691.3	668.7	646.0	623.4	606.7
42.5°	756.5	741.6	726.9	712.2	697.4	678.3	654.9	631.4	608.1	584.6	567.5
45°	706.4	690.7	675.1	659.4	643.8	623.7	599.2	574.6	550.1	525.6	509.0
47.5°	657.6	641.0	624.5	607.8	591.3	570.3	545.0	519.7	494.3	469.1	452.6
50°	622.3	605.7	589.1	572.5	556.0	534.8	509.1	483.4	457.7	432.1	415.9
52.5°	587.8	570.5	553.2	535.8	518.5	497.3	472.1	446.9	421.8	396.7	381.1
55°	537.2	519.0	500.7	482.5	464.3	442.5	417.3	392.1	366.9	341.7	327.6
57.5°	485.2	466.5	447.8	429.1	410.5	389.0	364.7	340.5	316.2	292.0	279.2
60°	449.9	431.2	412.6	393.9	375.2	353.8	329.7	305.6	281.6	257.5	245.7
62.5°	415.4	396.7	378.0	359.3	340.6	319.9	296.9	274.0	251.0	228.1	216.7
65°	362.7	343.7	324.8	305.9	287.0	267.0	246.0	225.0	203.9	182.9	175.0
67.5°	311.8	293.0	274.3	255.4	236.6	217.8	198.9	180.0	161.1	142.1	138.5
70°	276.5	258.3	240.0	221.8	203.6	186.4	170.3	154.2	138.1	121.9	119.6
72.5°	242.8	225.4	207.9	190.4	172.9	157.7	144.8	131.8	118.9	106.0	104.0
75°	193.5	177.1	160.7	144.3	128.0	115.9	107.9	100.0	92.1	84.1	82.5
77.5°	144.9	130.5	116.1	101.8	87.5	78.4	74.5	70.7	66.9	63.1	62.1
80°	114.5	102.7	90.8	78.8	66.9	59.8	57.4	55.1	52.8	50.5	49.5
82.5°	86.8	77.6	68.2	58.9	49.7	44.2	42.6	41.0	39.5	37.9	37.3
85°	45.2	40.3	35.4	30.5	25.6	22.8	22.1	21.4	20.7	20.0	20.0
87.5°	13.5	12.3	10.9	9.7	8.4	7.8	7.9	8.1	8.2	8.4	8.3
90°	0.4	1.4	2.5	3.4	4.4	5.3	6.1	6.8	7.5	8.2	8.7
92.5°	8.3	8.2	8.2	8.1	8.0	8.2	8.5	8.9	9.2	9.6	9.8
95°	26.9	23.8	20.8	17.7	14.7	13.5	14.2	14.8	15.4	16.2	16.6
97.5°	53.3	44.8	36.3	27.7	19.2	15.6	17.1	18.6	20.1	21.5	21.9
100°	73.2	60.6	48.0	35.4	22.8	17.3	18.9	20.4	22.0	23.5	24.3
102.5°	95.0	92.4	89.7	87.0	84.4	76.4	63.5	50.4	37.3	24.2	25.2
105°	125.6	128.4	131.2	134.0	136.7	125.6	100.4	75.4	50.3	25.2	26.2
107.5°	160.7	162.9	165.1	167.3	169.5	155.6	125.6	95.5	65.4	35.3	34.3
110°	183.2	185.1	187.0	188.9	190.8	178.6	152.0	125.5	98.9	72.3	63.1



TEST NUMBER: P331714-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	204.3	206.0	207.7	209.5	211.1	208.7	202.2	195.6	189.0	182.5	148.9
115°	237.7	239.2	240.8	242.4	244.0	245.9	248.2	250.5	252.8	255.1	212.5
117.5°	267.6	269.3	271.1	272.8	274.6	276.2	277.8	279.4	281.0	282.5	272.3
120°	289.4	290.7	292.2	293.5	294.9	296.4	298.1	299.8	301.3	303.0	304.1
122.5°	307.9	309.3	310.9	312.3	313.7	315.4	317.1	318.9	320.8	322.6	323.2
125°	336.1	337.3	338.5	339.7	340.9	342.4	344.1	345.9	347.6	349.4	350.0
127.5°	361.6	363.0	364.3	365.6	366.9	368.3	369.6	370.9	372.2	373.5	374.4
130°	377.9	379.3	380.8	382.3	383.7	385.0	386.0	387.0	388.0	389.0	390.1
132.5°	394.4	395.6	396.9	398.2	399.4	400.5	401.6	402.6	403.5	404.6	405.4
135°	415.9	417.4	418.8	420.3	421.8	422.9	423.7	424.6	425.4	426.2	427.1
137.5°	437.7	438.6	439.7	440.7	441.7	442.8	443.7	444.7	445.5	446.5	447.4
140°	451.9	452.6	453.4	454.1	454.8	455.7	456.7	457.7	458.7	459.7	460.6
142.5°	463.7	464.5	465.1	465.7	466.4	467.3	468.5	469.6	470.8	472.0	472.7
145°	482.4	482.4	482.3	482.2	482.1	482.8	484.4	485.9	487.5	489.1	489.7
147.5°	498.8	498.4	498.0	497.7	497.3	498.0	499.5	501.1	502.6	504.1	504.6
150°	509.3	508.7	508.0	507.4	506.8	507.2	508.7	510.1	511.6	513.0	513.6
152.5°	518.2	517.5	516.8	516.1	515.4	515.7	517.1	518.6	519.9	521.3	521.9
155°	531.2	530.4	529.6	528.8	527.9	528.1	529.2	530.3	531.4	532.5	533.1
157.5°	541.4	540.7	540.0	539.3	538.6	538.7	539.4	540.2	541.0	541.8	542.3
160°	547.4	546.8	546.3	545.7	545.2	545.2	545.7	546.3	546.8	547.4	548.0
162.5°	552.6	552.1	551.5	551.0	550.5	550.4	550.9	551.4	551.8	552.3	552.9
165°	559.8	559.2	558.6	558.1	557.5	557.5	557.7	557.9	558.3	558.5	559.2
167.5°	565.1	564.5	564.0	563.4	562.8	562.7	562.9	563.2	563.5	563.7	564.4
170°	568.0	567.5	567.0	566.4	565.9	565.6	565.9	566.0	566.2	566.4	567.0
172.5°	570.1	569.5	568.9	568.4	567.8	567.6	567.8	568.0	568.2	568.4	569.0
175°	572.6	572.0	571.3	570.7	570.0	569.8	570.0	570.1	570.3	570.5	571.2
177.5°	573.0	572.5	572.0	571.5	570.9	570.7	570.8	570.8	570.9	571.0	571.6
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3



TEST NUMBER: P331714-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6	1161.6
2.5°	1156.0	1157.9	1159.8	1160.5	1160.2	1159.8	1159.4	1159.0
5°	1146.8	1148.9	1151.0	1151.8	1151.0	1150.3	1149.6	1148.9
7.5°	1128.3	1128.9	1129.5	1129.2	1128.0	1126.8	1125.5	1124.3
10°	1109.7	1109.0	1108.3	1107.2	1105.8	1104.5	1103.0	1101.6
12.5°	1088.4	1087.1	1085.8	1084.1	1081.7	1079.4	1077.1	1074.8
15°	1048.6	1044.2	1039.7	1036.3	1034.0	1031.7	1029.4	1027.0
17.5°	1003.6	998.3	993.1	988.4	984.4	980.4	976.4	972.3
20°	972.2	966.4	960.5	955.1	949.9	944.8	939.6	934.5
22.5°	937.8	930.3	922.7	917.0	913.2	909.3	905.5	901.7
25°	880.7	871.1	861.5	854.9	851.4	848.0	844.5	841.0
27.5°	826.2	815.0	803.8	795.5	790.0	784.3	778.8	773.2
30°	787.7	775.8	763.8	754.7	748.5	742.1	735.9	729.5
32.5°	749.0	735.4	721.8	712.0	706.2	700.2	694.3	688.3
35°	688.5	673.8	659.1	649.2	644.0	638.9	633.7	628.6
37.5°	629.6	613.4	597.2	586.1	580.3	574.3	568.5	562.6
40°	590.2	573.6	557.0	545.7	539.6	533.5	527.4	521.4
42.5°	550.4	533.2	516.1	504.5	498.7	492.8	486.9	481.0
45°	492.4	475.9	459.2	448.1	442.5	437.0	431.3	425.7
47.5°	436.0	419.5	403.1	392.3	387.2	382.1	377.0	371.9
50°	399.8	383.7	367.6	357.0	352.1	347.2	342.3	337.4
52.5°	365.6	350.1	334.5	324.5	319.9	315.4	310.9	306.3
55°	313.6	299.6	285.6	276.3	271.9	267.4	263.0	258.6
57.5°	266.3	253.5	240.7	232.3	228.6	224.8	221.1	217.4
60°	233.7	221.8	209.8	202.1	198.3	194.6	190.8	187.1
62.5°	205.4	194.1	182.7	175.9	173.6	171.4	169.1	166.9
65°	167.0	159.1	151.1	146.8	146.1	145.4	144.7	144.0
67.5°	134.8	131.2	127.5	125.3	124.6	123.8	123.1	122.4
70°	117.2	114.9	112.6	111.0	110.0	109.1	108.1	107.2
72.5°	102.0	100.1	98.1	96.9	96.3	95.7	95.1	94.6
75°	80.8	79.2	77.6	76.6	76.4	76.1	75.9	75.7
77.5°	61.2	60.3	59.3	58.7	58.3	57.9	57.6	57.2
80°	48.6	47.7	46.7	46.3	46.3	46.3	46.3	46.3
82.5°	36.8	36.1	35.6	35.3	35.3	35.3	35.3	35.3
85°	20.0	20.0	20.0	20.0	20.0	20.0	20.0	20.0
87.5°	8.2	8.1	8.0	8.0	8.0	8.1	8.1	8.1
90°	9.2	9.7	10.1	10.5	10.6	10.8	11.0	11.2
92.5°	10.1	10.3	10.5	10.7	10.9	10.9	11.1	11.2
95°	17.0	17.5	18.0	18.1	18.1	18.0	17.9	17.7
97.5°	22.3	22.7	23.1	23.3	23.4	23.5	23.6	23.8
100°	25.0	25.7	26.5	26.9	27.2	27.3	27.5	27.7
102.5°	26.1	27.1	28.0	28.7	28.9	29.2	29.4	29.7
105°	27.3	28.3	29.2	29.9	30.3	30.7	31.1	31.4
107.5°	33.3	32.2	31.2	30.9	31.2	31.6	31.9	32.3
110°	53.9	44.8	35.6	31.2	31.5	31.9	32.3	32.6



TEST NUMBER: P331714-927

CATALOG NUMBER: SA2XXRDIP-C865D530U927-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	115.4	81.9	48.4	31.8	32.1	32.4	32.7	33.0
115°	170.0	127.5	84.9	60.4	53.7	47.1	40.5	33.9
117.5°	262.0	251.7	241.4	225.4	203.6	181.9	160.2	138.4
120°	305.2	306.3	307.4	301.8	289.4	277.0	264.6	252.2
122.5°	323.8	324.6	325.2	324.3	321.9	319.5	317.1	314.7
125°	350.6	351.3	351.9	352.4	352.7	352.9	353.2	353.5
127.5°	375.3	376.3	377.2	377.7	377.8	377.9	377.9	378.0
130°	391.0	392.1	393.1	393.6	393.4	393.3	393.2	393.2
132.5°	406.3	407.2	408.1	408.4	408.3	408.2	408.1	408.1
135°	428.1	429.0	429.9	430.3	430.1	429.9	429.8	429.5
137.5°	448.3	449.2	450.1	450.4	450.0	449.7	449.5	449.2
140°	461.4	462.2	463.0	463.2	462.7	462.3	461.8	461.4
142.5°	473.5	474.2	475.0	475.2	474.7	474.2	473.7	473.2
145°	490.4	491.0	491.6	491.7	491.3	490.8	490.4	489.9
147.5°	505.1	505.6	506.0	506.0	505.7	505.3	504.9	504.5
150°	514.1	514.7	515.2	515.3	514.8	514.4	513.9	513.5
152.5°	522.4	523.0	523.6	523.5	522.9	522.3	521.7	521.1
155°	533.6	534.2	534.7	534.6	533.9	533.1	532.4	531.6
157.5°	543.0	543.6	544.2	544.2	543.4	542.7	542.0	541.3
160°	548.4	549.0	549.5	549.5	548.9	548.3	547.6	546.9
162.5°	553.6	554.2	554.8	554.8	554.0	553.2	552.4	551.6
165°	559.8	560.5	561.1	561.1	560.5	559.8	559.2	558.5
167.5°	565.0	565.7	566.3	566.3	565.4	564.6	563.7	562.9
170°	567.7	568.3	568.9	568.9	568.0	567.2	566.4	565.5
172.5°	569.7	570.3	570.9	570.8	570.1	569.2	568.4	567.5
175°	571.8	572.4	573.1	573.0	572.0	571.1	570.2	569.3
177.5°	572.0	572.6	573.1	573.0	572.4	571.6	571.0	570.4
180°	571.3	571.3	571.3	571.3	571.3	571.3	571.3	571.3

(END OF REPORT)