

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331401

Luminaire Tested: **SA2XXDIP-C865D725U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331401
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D725U835-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6343.2 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 54.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331401
CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331401

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55				
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52	47				
2	90	83	76	71	83	77	72	67	66	62	59	57	54	51	48	45	43	39				
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	39	37	33				
4	75	64	56	50	70	60	53	47	52	47	42	45	40	37	38	34	32	28				
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25				
6	64	51	43	37	59	48	41	36	42	36	32	36	32	28	31	27	24	22				
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19				
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17				
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16				
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22281	22281	22281
5°	22366	22044	22174
10°	22233	21820	21930
15°	21959	21538	21514
20°	21569	21113	21089
25°	21180	20591	20591
30°	20681	20113	19939
35°	20217	19537	19249
40°	19633	18963	18598
45°	19057	18393	17938
50°	18432	17799	17166
55°	17779	17106	16473
60°	17053	16281	15684
65°	16275	15461	14751
70°	15286	14469	13780
75°	13905	13325	12994
80°	12338	11967	11353
85°	10078	9596	8596



TEST NUMBER: P331401

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.8	2.0
10°-20°	365.1	5.8
20°-30°	536.7	8.5
30°-40°	623.4	9.8
40°-50°	622.7	9.8
50°-60°	543.1	8.6
60°-70°	401.6	6.3
70°-80°	227.4	3.6
80°-90°	64.8	1.0
90°-100°	162.5	2.6
100°-110°	551.5	8.7
110°-120°	585.9	9.2
120°-130°	482.3	7.6
130°-140°	387.3	6.1
140°-150°	292.7	4.6
150°-160°	205.7	3.2
160°-170°	121.1	1.9
170°-180°	39.4	0.6
0°-30°	1031.6	16.3
0°-40°	1655.0	26.1
0°-60°	2820.8	44.5
0°-90°	3514.6	55.4
90°-120°	1300.0	20.5
90°-150°	2462.4	38.8
90°-180°	2829.0	44.6
0°-180°	6343.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1380	1380	1380	1380	1380	
5°	1380	1374	1360	1370	1368	131
15°	1314	1305	1288	1293	1287	370
25°	1189	1178	1156	1158	1156	547
35°	1026	1012	991	983	977	640
45°	835	825	806	791	786	644
55°	632	623	608	592	585	565
65°	426	418	405	393	386	421
75°	223	220	214	206	208	238
85°	54	53	52	48	46	62
90°	1	11	27	25	26	4
95°	27	67	306	116	89	29
105°	95	144	579	1035	881	101
115°	168	212	485	1000	1159	167
125°	234	278	466	810	940	208
135°	275	328	460	681	779	213
145°	314	361	458	569	622	197
155°	357	386	445	503	523	164
165°	389	401	426	452	459	110
175°	406	406	410	415	414	39
180°	406	406	406	406	406	



TEST NUMBER: P331401

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0
2.5°	1386.4	1385.2	1384.0	1382.9	1381.7	1379.8	1377.2	1374.6	1372.0	1369.4	1371.8
5°	1380.0	1378.8	1377.7	1376.5	1375.3	1373.1	1369.9	1366.6	1363.4	1360.1	1362.5
7.5°	1367.8	1366.0	1364.2	1362.3	1360.5	1357.9	1354.6	1351.3	1348.0	1344.7	1347.1
10°	1356.1	1354.1	1352.0	1349.9	1347.9	1345.1	1341.5	1338.0	1334.5	1330.9	1333.3
12.5°	1340.2	1338.4	1336.6	1334.7	1332.9	1330.2	1326.7	1323.1	1319.6	1316.1	1317.7
15°	1313.7	1311.9	1310.1	1308.4	1306.6	1303.8	1300.0	1296.1	1292.3	1288.5	1289.6
17.5°	1279.7	1277.9	1276.2	1274.4	1272.6	1269.8	1265.9	1262.0	1258.1	1254.2	1255.6
20°	1255.3	1253.5	1251.8	1250.0	1248.2	1245.3	1241.1	1237.0	1232.9	1228.8	1229.6
22.5°	1230.9	1228.4	1225.9	1223.4	1221.0	1217.8	1213.9	1210.0	1206.1	1202.2	1202.4
25°	1188.9	1186.6	1184.2	1181.9	1179.5	1175.8	1170.8	1165.8	1160.8	1155.8	1156.4
27.5°	1141.2	1139.1	1136.9	1134.8	1132.7	1129.6	1125.7	1121.7	1117.8	1113.8	1113.0
30°	1109.3	1107.0	1104.6	1102.3	1099.9	1096.5	1092.1	1087.7	1083.2	1078.8	1077.9
32.5°	1075.4	1073.5	1071.6	1069.7	1067.8	1064.5	1059.9	1055.2	1050.6	1045.9	1044.3
35°	1025.7	1022.8	1019.8	1016.9	1013.9	1010.1	1005.4	1000.7	995.9	991.2	989.5
37.5°	969.7	967.1	964.5	961.9	959.4	955.7	951.0	946.3	941.5	936.8	934.6
40°	931.5	929.2	926.8	924.4	922.1	918.5	913.8	909.1	904.4	899.7	897.0
42.5°	894.4	892.0	889.6	887.3	884.9	881.4	876.7	872.0	867.2	862.5	859.6
45°	834.6	832.6	830.5	828.5	826.4	823.1	818.7	814.3	809.9	805.5	802.2
47.5°	775.2	773.3	771.3	769.4	767.4	764.1	759.5	754.9	750.3	745.7	742.3
50°	733.8	732.3	730.9	729.4	727.9	725.1	721.0	716.8	712.7	708.6	704.5
52.5°	693.5	691.5	689.6	687.6	685.7	682.8	678.9	675.0	671.1	667.2	663.8
55°	631.6	629.9	628.1	626.3	624.5	621.9	618.4	614.8	611.3	607.7	604.2
57.5°	569.5	568.1	566.7	565.3	563.9	561.2	557.3	553.4	549.5	545.6	542.2
60°	528.1	526.9	525.8	524.6	523.4	520.8	516.6	512.5	508.4	504.2	501.0
62.5°	487.8	485.9	484.0	482.1	480.2	477.7	474.5	471.3	468.1	465.0	462.0
65°	426.0	424.2	422.4	420.6	418.9	416.5	413.6	410.6	407.7	404.7	402.1
67.5°	363.1	361.6	360.2	358.8	357.4	355.4	352.7	350.0	347.4	344.7	342.7
70°	323.8	322.6	321.4	320.2	319.1	317.1	314.5	311.8	309.2	306.5	304.5
72.5°	283.4	282.3	281.1	279.9	278.7	277.3	275.6	273.9	272.1	270.4	268.4
75°	222.9	222.3	221.7	221.2	220.6	219.5	218.1	216.6	215.1	213.6	211.9
77.5°	168.8	167.8	166.8	165.8	164.8	164.0	163.4	162.8	162.2	161.6	160.7
80°	132.7	132.4	132.1	131.8	131.5	131.1	130.5	129.9	129.3	128.7	127.8
82.5°	98.7	98.7	98.6	98.5	98.5	98.3	97.9	97.6	97.2	96.9	95.7
85°	54.4	54.1	53.8	53.5	53.2	52.9	52.6	52.3	52.0	51.8	50.9
87.5°	19.3	19.3	19.4	19.3	19.1	19.1	19.4	20.0	20.5	20.2	19.3
90°	0.8	3.1	6.3	7.8	9.4	11.7	15.6	21.1	25.8	26.6	25.8
92.5°	9.5	13.8	19.4	22.8	28.1	35.5	53.2	78.0	100.2	101.6	85.8
95°	27.4	30.5	38.3	45.3	57.8	76.6	112.6	180.6	271.3	306.4	268.1
97.5°	44.6	48.8	57.1	67.7	82.1	103.3	148.5	243.3	394.0	523.1	548.8
100°	60.2	62.5	69.6	82.1	97.7	119.6	161.0	256.4	425.2	617.5	730.1
102.5°	74.6	76.3	83.3	95.8	112.1	134.0	172.3	257.0	413.4	620.7	797.6
105°	95.4	98.5	104.0	115.7	132.9	154.8	191.5	261.1	390.1	579.2	787.2
107.5°	117.9	120.4	125.7	136.5	153.5	175.6	211.2	271.9	378.5	534.8	718.5
110°	132.9	136.0	140.7	150.9	167.3	190.0	224.3	280.6	376.0	513.6	675.4



TEST NUMBER: P331401

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.6	149.8	155.1	164.6	180.4	203.7	236.9	290.0	376.6	499.8	645.4
115°	168.1	172.0	176.7	186.0	201.7	222.8	256.4	304.1	379.9	484.7	608.2
117.5°	190.3	193.4	198.1	206.4	221.4	243.3	274.4	319.1	385.5	477.3	584.7
120°	204.0	207.2	211.8	218.9	234.5	256.4	286.9	329.1	389.3	472.9	572.2
122.5°	217.2	219.7	224.3	232.0	247.6	270.2	298.8	337.9	393.7	470.4	561.6
125°	234.5	236.9	241.5	250.9	266.6	288.4	316.6	351.8	400.2	465.9	546.4
127.5°	248.3	251.4	258.0	268.3	283.3	305.8	333.2	364.7	407.0	463.2	532.3
130°	256.4	259.5	267.3	278.3	293.9	315.8	343.2	372.9	412.0	462.0	523.0
132.5°	263.9	267.7	276.1	287.7	303.9	325.8	351.9	381.0	417.0	461.4	515.5
135°	275.2	278.3	287.7	299.4	317.4	339.3	364.3	391.6	422.9	460.4	505.0
137.5°	285.8	289.5	298.9	311.4	329.3	349.6	374.3	399.8	428.2	460.3	497.6
140°	293.9	297.0	306.4	318.9	336.1	356.5	379.9	404.1	430.7	459.6	493.3
142.5°	302.0	304.6	313.3	325.8	342.4	361.5	384.3	407.9	432.6	459.6	488.9
145°	314.2	317.4	325.2	336.9	352.5	369.7	390.9	412.7	434.6	458.1	483.1
147.5°	327.4	329.7	337.2	348.0	361.0	376.3	396.2	415.4	435.3	455.3	477.2
150°	336.1	338.5	344.7	354.9	366.6	380.7	398.7	416.6	434.6	453.4	472.1
152.5°	344.9	346.0	352.2	361.1	372.2	385.1	401.2	417.3	433.4	450.3	467.8
155°	357.2	358.0	362.7	371.3	379.9	391.6	404.9	418.2	431.5	444.8	459.6
157.5°	367.6	368.3	372.1	379.6	386.5	396.3	407.6	418.2	427.9	439.2	452.0
160°	374.4	375.2	378.3	384.6	390.9	399.4	408.8	418.2	426.0	435.4	446.4
162.5°	381.3	380.8	384.0	389.0	394.6	401.3	409.5	417.6	424.2	432.3	441.3
165°	389.3	388.5	390.1	394.8	398.7	403.4	410.4	415.9	420.6	426.0	433.1
167.5°	395.9	394.9	396.3	399.3	402.1	405.1	410.2	414.8	417.0	420.6	424.9
170°	400.2	398.7	399.4	401.8	403.4	405.7	409.6	413.5	415.1	417.4	420.6
172.5°	402.7	401.8	401.3	403.7	404.6	406.3	409.0	411.6	412.6	413.7	416.2
175°	405.7	404.9	404.1	405.7	405.7	406.5	408.0	409.6	408.8	409.6	410.4
177.5°	407.1	405.9	405.2	406.5	406.5	406.5	407.1	408.4	407.1	406.5	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331401

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0	1380.0
2.5°	1374.1	1376.5	1378.8	1379.8	1379.3	1378.8	1378.4	1377.9
5°	1364.8	1367.2	1369.6	1370.4	1369.9	1369.3	1368.7	1368.1
7.5°	1349.4	1351.8	1354.2	1355.0	1354.4	1353.7	1353.1	1352.4
10°	1335.6	1338.0	1340.4	1341.1	1340.2	1339.3	1338.4	1337.6
12.5°	1319.4	1321.0	1322.7	1323.2	1322.5	1321.9	1321.2	1320.6
15°	1290.8	1292.0	1293.2	1293.0	1291.6	1290.1	1288.6	1287.1
17.5°	1256.9	1258.3	1259.7	1259.6	1258.2	1256.8	1255.4	1254.0
20°	1230.5	1231.4	1232.3	1232.1	1231.0	1229.8	1228.6	1227.4
22.5°	1202.6	1202.7	1202.9	1202.7	1201.9	1201.2	1200.5	1199.8
25°	1157.0	1157.5	1158.1	1158.1	1157.5	1157.0	1156.4	1155.8
27.5°	1112.1	1111.2	1110.3	1109.2	1107.7	1106.3	1104.9	1103.5
30°	1077.0	1076.2	1075.3	1074.2	1073.1	1071.9	1070.7	1069.5
32.5°	1042.7	1041.1	1039.5	1038.1	1037.0	1035.8	1034.6	1033.4
35°	987.7	985.9	984.2	982.5	981.1	979.6	978.1	976.6
37.5°	932.5	930.3	928.1	926.3	924.9	923.5	922.1	920.6
40°	894.4	891.7	889.1	887.1	886.0	884.8	883.6	882.4
42.5°	856.7	853.8	851.0	848.7	847.0	845.4	843.7	842.1
45°	799.0	795.7	792.5	790.3	789.1	787.9	786.7	785.6
47.5°	738.9	735.5	732.1	729.5	727.8	726.1	724.4	722.7
50°	700.3	696.2	692.1	689.3	687.8	686.3	684.9	683.4
52.5°	660.3	656.9	653.5	650.8	648.9	646.9	645.0	643.0
55°	600.7	597.1	593.6	591.1	589.6	588.1	586.7	585.2
57.5°	538.7	535.2	531.7	529.4	528.3	527.2	526.1	524.9
60°	497.8	494.5	491.3	489.2	488.3	487.4	486.5	485.7
62.5°	458.9	455.9	452.9	450.9	449.7	448.6	447.5	446.4
65°	399.4	396.8	394.1	392.0	390.6	389.1	387.6	386.1
67.5°	340.6	338.5	336.5	334.9	333.7	332.5	331.3	330.1
70°	302.4	300.3	298.3	296.6	295.5	294.3	293.1	291.9
72.5°	266.3	264.2	262.2	260.7	259.7	258.8	257.8	256.9
75°	210.1	208.3	206.6	206.0	206.6	207.2	207.7	208.3
77.5°	159.9	159.0	158.1	157.2	156.4	155.6	154.8	153.9
80°	126.9	126.1	125.2	124.4	123.8	123.3	122.7	122.1
82.5°	94.6	93.5	92.4	91.8	91.6	91.5	91.4	91.3
85°	50.0	49.1	48.2	47.6	47.3	47.0	46.7	46.4
87.5°	18.4	17.4	17.0	16.7	16.5	16.2	16.0	15.8
90°	25.0	23.5	25.0	25.8	25.8	25.8	25.8	25.8
92.5°	68.2	58.5	51.9	47.1	46.4	43.9	44.6	43.3
95°	204.8	157.1	124.3	107.1	96.9	90.7	88.3	89.1
97.5°	477.9	391.0	306.4	250.0	212.6	193.4	182.0	175.4
100°	713.7	616.8	509.7	415.1	350.2	316.6	293.9	279.8
102.5°	868.2	846.3	767.9	667.7	597.2	539.8	511.5	492.5
105°	949.8	1038.1	1048.3	1022.5	974.0	925.5	891.9	881.0
107.5°	891.0	1024.0	1105.3	1143.2	1149.3	1146.6	1139.9	1125.3
110°	840.3	980.3	1080.3	1144.4	1178.0	1192.9	1199.9	1199.1



TEST NUMBER: P331401

CATALOG NUMBER: SA2XXDIP-C865D725U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	794.1	928.3	1035.3	1108.8	1155.5	1180.4	1193.7	1197.9
115°	737.1	857.5	959.9	1040.4	1095.9	1131.9	1152.2	1159.3
117.5°	694.3	800.0	892.9	968.4	1025.0	1063.0	1084.4	1090.3
120°	673.0	770.0	852.8	924.0	978.7	1015.4	1038.1	1045.9
122.5°	656.2	745.0	823.4	887.7	936.8	972.9	993.1	999.6
125°	631.6	712.1	780.9	839.5	884.9	914.6	934.1	940.4
127.5°	607.4	680.2	745.1	799.2	838.8	866.6	883.5	888.5
130°	591.7	659.0	720.7	772.3	810.6	837.2	852.8	859.1
132.5°	576.7	639.0	695.7	744.2	781.9	808.4	822.8	828.4
135°	555.8	607.4	659.0	702.7	736.4	762.2	776.2	779.4
137.5°	539.1	582.2	623.2	661.3	692.0	714.2	726.5	731.2
140°	528.4	566.0	601.9	636.3	661.3	681.6	693.4	698.1
142.5°	519.7	551.6	582.5	611.3	635.1	653.5	664.0	664.9
145°	507.3	533.1	557.4	580.0	598.8	612.1	619.9	622.2
147.5°	497.8	518.1	537.0	553.6	569.1	579.7	585.0	586.4
150°	490.9	508.1	524.5	538.6	550.3	559.7	564.4	565.2
152.5°	484.0	500.0	513.9	526.1	535.3	543.4	546.9	547.0
155°	474.5	487.0	498.7	507.3	515.9	521.4	524.5	523.0
157.5°	463.4	473.9	483.7	490.4	496.5	501.1	502.5	502.5
160°	456.5	465.1	473.7	479.2	484.7	488.6	489.3	489.3
162.5°	449.6	457.0	464.3	468.6	474.0	476.7	477.5	476.8
165°	439.3	444.8	450.3	453.4	456.5	459.6	459.6	458.9
167.5°	429.5	433.7	437.4	440.3	441.7	443.4	443.2	442.3
170°	424.5	426.8	429.9	431.5	432.3	434.6	433.8	432.3
172.5°	418.8	420.6	423.1	424.0	424.8	425.9	425.1	424.2
175°	412.7	413.5	414.3	415.1	415.1	415.9	415.1	413.5
177.5°	408.4	408.4	409.0	409.0	409.0	409.0	408.4	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5

(END OF REPORT)