

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331406

Luminaire Tested: **SA2XXDIP-C865D925U835-4F0-1E-UDD-D1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331406
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C865D925U835-4F0-1E-UDD-D1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6804.5 lumens
Efficiency: N/A
Efficacy: 112.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331406

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P331406

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46
1	95	91	86	82	87	83	79	76	69	66	64	56	54	52	44	43	41	36
2	86	78	72	66	79	72	66	61	60	55	51	48	45	42	38	36	34	29
3	78	68	61	54	71	63	56	50	52	47	43	42	38	35	33	30	28	24
4	71	60	52	45	65	55	48	42	46	40	36	37	33	30	29	26	24	20
5	65	53	45	39	60	49	42	36	41	35	31	33	29	26	26	23	21	17
6	60	48	39	33	55	44	36	31	37	31	27	30	26	22	24	20	18	15
7	56	43	35	29	51	40	32	27	33	27	23	27	23	19	22	18	16	13
8	51	39	31	25	47	36	29	24	30	25	21	25	20	17	20	16	14	12
9	48	35	28	23	44	33	26	21	28	22	18	23	18	15	18	15	13	10
10	45	32	25	20	41	30	23	19	25	20	16	21	17	14	17	14	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14783	14783	14783
5°	14855	14230	14176
10°	14762	13809	13655
15°	14558	13364	13106
20°	14300	12888	12577
25°	14048	12428	12096
30°	13689	11955	11614
35°	13327	11498	11275
40°	12947	11110	10935
45°	12584	10762	10645
50°	12196	10448	10360
55°	11790	10109	10067
60°	11292	9759	9760
65°	10774	9347	9393
70°	10189	8905	8999
75°	9446	8470	8637
80°	8274	8029	8266
85°	7152	7646	7981



TEST NUMBER: P331406

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.8	1.3
10°-20°	248.8	3.7
20°-30°	377.0	5.5
30°-40°	459.2	6.7
40°-50°	494.0	7.3
50°-60°	479.7	7.1
60°-70°	418.9	6.2
70°-80°	322.5	4.7
80°-90°	221.1	3.3
90°-100°	224.0	3.3
100°-110°	341.6	5.0
110°-120°	469.7	6.9
120°-130°	563.3	8.3
130°-140°	604.0	8.9
140°-150°	578.7	8.5
150°-160°	482.9	7.1
160°-170°	320.3	4.7
170°-180°	111.9	1.6
0°-30°	712.5	10.5
0°-40°	1171.7	17.2
0°-60°	2145.5	31.5
0°-90°	3108.0	45.7
90°-120°	1035.4	15.2
90°-150°	2781.3	40.9
90°-180°	3696.0	54.3
0°-180°	6804.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	916	916	916	916	916	
5°	918	914	906	914	913	87
15°	876	878	878	890	889	247
25°	796	806	817	833	837	366
35°	686	709	734	762	772	429
45°	563	599	645	684	699	434
55°	431	480	548	594	613	385
65°	295	360	438	490	510	293
75°	163	238	322	377	397	173
85°	48	130	215	269	289	51
90°	14	104	210	259	278	12
95°	62	135	216	265	281	68
105°	221	264	334	380	397	234
115°	404	427	483	520	533	400
125°	584	594	632	664	676	522
135°	753	764	779	805	814	582
145°	912	919	925	934	937	570
155°	1043	1046	1049	1053	1051	480
165°	1135	1134	1134	1140	1136	320
175°	1181	1178	1176	1182	1177	112
180°	1183	1183	1183	1183	1183	



TEST NUMBER: P331406

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.6	915.6	915.6	915.6	915.6	915.6	915.6	915.6	915.6	915.6	915.6
2.5°	920.9	920.2	919.5	918.8	918.1	916.9	915.2	913.6	911.9	910.3	911.5
5°	918.2	917.4	916.5	915.6	914.7	913.4	911.6	909.8	908.1	906.3	908.1
7.5°	910.0	909.4	908.8	908.3	907.7	906.7	905.3	904.0	902.6	901.3	903.4
10°	903.7	903.1	902.5	901.9	901.3	900.6	899.7	898.8	897.9	897.0	899.4
12.5°	893.0	893.2	893.3	893.4	893.5	893.2	892.6	891.9	891.3	890.6	893.0
15°	875.8	876.4	877.0	877.6	878.1	878.4	878.4	878.4	878.4	878.4	881.1
17.5°	853.5	854.7	856.0	857.2	858.4	859.5	860.5	861.4	862.4	863.3	866.1
20°	838.6	840.1	841.6	843.1	844.5	845.9	847.0	848.2	849.4	850.6	853.8
22.5°	822.7	824.4	826.1	827.8	829.5	831.2	832.9	834.5	836.2	837.8	841.1
25°	796.2	798.2	800.3	802.4	804.4	806.8	809.4	812.1	814.7	817.4	820.9
27.5°	764.3	767.7	771.0	774.4	777.8	781.0	784.1	787.3	790.4	793.5	798.0
30°	743.1	746.9	750.8	754.6	758.4	762.3	766.1	769.9	773.8	777.6	782.3
32.5°	719.7	724.0	728.3	732.7	737.0	741.4	745.9	750.5	755.0	759.5	765.0
35°	686.0	691.0	696.1	701.1	706.1	711.4	717.0	722.6	728.2	733.8	740.3
37.5°	649.4	655.2	661.0	666.7	672.5	679.0	686.3	693.6	700.8	708.1	715.3
40°	625.0	631.5	638.0	644.5	650.9	658.2	666.1	674.1	682.1	690.0	697.7
42.5°	601.6	608.1	614.6	621.1	627.6	635.4	644.5	653.7	662.8	672.0	680.3
45°	562.6	570.6	578.5	586.5	594.5	603.6	613.9	624.3	634.6	644.9	654.0
47.5°	524.1	532.8	541.5	550.2	558.8	569.2	581.3	593.4	605.5	617.6	627.1
50°	497.6	506.7	515.9	525.0	534.2	545.4	558.6	571.9	585.2	598.5	608.5
52.5°	472.1	481.7	491.4	501.0	510.6	522.4	536.4	550.3	564.3	578.3	588.5
55°	431.3	441.9	452.5	463.1	473.7	486.7	502.0	517.4	532.7	548.0	558.6
57.5°	390.9	402.9	414.9	426.8	438.8	452.6	468.2	483.9	499.5	515.1	526.6
60°	362.3	374.9	387.6	400.3	413.0	427.7	444.5	461.3	478.1	495.0	506.2
62.5°	336.8	349.9	363.1	376.2	389.4	404.4	421.2	438.0	454.8	471.6	483.5
65°	294.6	309.0	323.5	337.9	352.4	368.3	385.7	403.1	420.5	437.9	450.0
67.5°	255.8	270.9	286.0	301.1	316.2	332.7	350.5	368.3	386.1	403.9	416.1
70°	228.2	243.6	258.9	274.2	289.6	306.4	324.7	342.9	361.2	379.5	392.2
72.5°	202.8	218.6	234.4	250.2	266.0	283.1	301.7	320.2	338.7	357.2	369.7
75°	163.2	179.7	196.2	212.8	229.3	247.0	265.8	284.7	303.6	322.4	335.1
77.5°	125.0	142.3	159.6	176.8	194.1	212.3	231.5	250.7	269.8	289.0	301.6
80°	99.5	117.5	135.5	153.5	171.5	190.0	209.2	228.4	247.5	266.7	279.1
82.5°	78.3	96.0	113.8	131.5	149.3	167.9	187.3	206.7	226.1	245.5	257.9
85°	47.8	66.1	84.3	102.6	120.9	139.5	158.3	177.2	196.1	215.0	227.4
87.5°	26.2	44.3	62.4	80.5	98.6	117.6	137.5	157.3	177.2	197.0	208.9
90°	14.3	34.0	53.8	73.6	93.3	115.1	138.8	162.6	186.3	210.1	221.4
92.5°	30.0	47.8	65.7	83.6	101.5	120.1	139.4	158.7	178.0	197.3	209.0
95°	62.5	78.6	94.7	110.7	126.8	143.9	162.1	180.2	198.3	216.5	227.7
97.5°	104.1	118.4	132.6	146.9	161.2	177.3	195.1	212.9	230.7	248.6	259.5
100°	136.0	148.7	161.4	174.1	186.8	201.7	218.9	236.1	253.2	270.4	281.3
102.5°	168.5	179.9	191.3	202.7	214.0	228.2	245.1	261.9	278.8	295.7	306.6
105°	221.2	230.4	239.6	248.8	258.1	270.6	286.3	302.1	317.9	333.7	344.4
107.5°	275.6	283.4	291.3	299.1	306.9	318.1	332.8	347.5	362.2	376.9	387.0
110°	309.7	316.9	324.1	331.4	338.6	349.4	363.9	378.3	392.8	407.2	416.7



TEST NUMBER: P331406

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	348.0	354.3	360.6	366.9	373.1	383.1	396.6	410.2	423.8	437.3	446.2
115°	404.5	409.1	413.6	418.2	422.8	431.5	444.3	457.1	470.0	482.8	491.4
117.5°	459.4	463.3	467.2	471.1	475.0	482.5	493.5	504.5	515.6	526.6	534.8
120°	497.0	499.9	502.9	505.8	508.8	515.3	525.3	535.3	545.3	555.4	563.6
122.5°	531.3	533.9	536.5	539.1	541.7	547.9	557.8	567.6	577.5	587.3	594.8
125°	583.5	585.5	587.5	589.4	591.4	596.8	605.6	614.4	623.1	631.9	639.2
127.5°	635.6	637.8	640.0	642.3	644.5	649.0	655.8	662.6	669.4	676.2	682.8
130°	668.3	670.9	673.5	676.1	678.6	682.8	688.6	694.3	700.1	705.8	712.4
132.5°	705.0	707.1	709.1	711.2	713.2	716.7	721.6	726.4	731.3	736.2	742.0
135°	752.8	755.2	757.7	760.1	762.5	765.5	768.9	772.2	775.6	779.0	785.0
137.5°	804.5	806.4	808.4	810.3	812.2	814.1	816.0	817.9	819.8	821.6	826.9
140°	835.6	837.3	839.0	840.7	842.4	844.1	845.8	847.5	849.2	850.9	855.6
142.5°	867.5	869.3	871.0	872.7	874.4	875.6	876.5	877.4	878.3	879.1	883.1
145°	912.1	913.7	915.2	916.8	918.3	919.8	921.1	922.4	923.8	925.1	927.1
147.5°	953.0	954.9	956.8	958.6	960.5	961.9	962.8	963.6	964.5	965.4	966.1
150°	981.0	982.3	983.6	985.0	986.3	987.4	988.3	989.2	990.1	991.0	991.6
152.5°	1005.7	1007.1	1008.4	1009.7	1011.1	1012.3	1013.3	1014.4	1015.4	1016.5	1017.4
155°	1042.9	1043.5	1044.2	1044.9	1045.5	1046.2	1046.9	1047.5	1048.2	1048.8	1050.0
157.5°	1074.6	1075.0	1075.5	1075.9	1076.4	1076.8	1077.2	1077.6	1078.0	1078.4	1079.9
160°	1093.8	1094.2	1094.6	1095.1	1095.5	1095.9	1096.1	1096.3	1096.5	1096.7	1098.1
162.5°	1111.3	1111.4	1111.5	1111.6	1111.7	1111.8	1112.1	1112.3	1112.5	1112.7	1114.2
165°	1134.7	1134.5	1134.2	1134.0	1133.8	1133.7	1133.7	1133.7	1133.7	1133.7	1135.2
167.5°	1154.2	1153.6	1152.9	1152.2	1151.6	1151.2	1151.2	1151.1	1151.1	1151.0	1152.6
170°	1164.6	1163.9	1163.3	1162.6	1161.9	1161.5	1161.3	1161.1	1160.8	1160.6	1162.2
172.5°	1171.8	1171.1	1170.5	1169.8	1169.1	1168.7	1168.5	1168.2	1168.0	1167.8	1169.4
175°	1180.6	1179.9	1179.2	1178.6	1177.9	1177.4	1176.9	1176.5	1176.0	1175.6	1177.1
177.5°	1184.2	1183.6	1183.1	1182.6	1182.0	1181.6	1181.2	1180.9	1180.5	1180.2	1181.2
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331406

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	915.6	915.6	915.6	915.6	915.6	915.6	915.6	915.6
2.5°	912.6	913.8	915.0	915.4	914.9	914.4	913.9	913.5
5°	909.8	911.6	913.4	914.1	913.8	913.5	913.2	912.9
7.5°	905.5	907.6	909.8	910.7	910.4	910.1	909.8	909.5
10°	901.7	904.1	906.5	907.5	907.2	906.9	906.6	906.3
12.5°	895.4	897.7	900.1	901.1	900.8	900.5	900.2	899.9
15°	883.7	886.4	889.1	890.2	889.9	889.6	889.3	889.1
17.5°	868.9	871.6	874.4	875.8	875.8	875.8	875.8	875.8
20°	857.1	860.3	863.5	865.2	865.2	865.2	865.2	865.2
22.5°	844.3	847.6	850.8	852.7	853.1	853.6	854.1	854.6
25°	824.5	828.0	831.6	833.8	834.6	835.5	836.4	837.3
27.5°	802.5	807.0	811.4	814.0	814.7	815.3	816.0	816.6
30°	787.0	791.7	796.5	799.3	800.1	801.0	801.9	802.8
32.5°	770.4	775.8	781.2	784.8	786.3	787.9	789.5	791.1
35°	746.8	753.3	759.8	764.0	766.1	768.2	770.2	772.3
37.5°	722.4	729.6	736.8	741.5	743.7	745.9	748.1	750.3
40°	705.3	713.0	720.7	725.8	728.5	731.1	733.8	736.5
42.5°	688.7	697.1	705.5	711.0	713.6	716.3	718.9	721.6
45°	663.2	672.3	681.5	687.5	690.5	693.4	696.4	699.3
47.5°	636.7	646.2	655.8	662.2	665.4	668.7	671.9	675.2
50°	618.5	628.5	638.6	645.2	648.4	651.7	654.9	658.2
52.5°	598.8	609.1	619.3	626.2	629.7	633.2	636.6	640.1
55°	569.3	579.9	590.5	597.7	601.5	605.4	609.2	613.0
57.5°	538.0	549.4	560.9	568.6	572.4	576.3	580.2	584.1
60°	517.4	528.6	539.8	547.4	551.6	555.7	559.8	564.0
62.5°	495.4	507.3	519.2	527.2	531.0	534.9	538.8	542.7
65°	462.1	474.2	486.3	494.2	498.0	501.9	505.7	509.5
67.5°	428.3	440.5	452.8	460.9	464.9	468.9	472.9	476.9
70°	404.9	417.5	430.2	438.3	441.9	445.4	449.0	452.5
72.5°	382.1	394.5	407.0	415.3	419.6	423.8	428.1	432.3
75°	347.8	360.5	373.2	381.4	385.3	389.1	392.9	396.8
77.5°	314.3	326.9	339.5	347.9	352.0	356.1	360.3	364.4
80°	291.5	303.9	316.3	324.5	328.6	332.8	336.9	341.0
82.5°	270.3	282.6	295.0	303.2	307.1	310.9	314.8	318.7
85°	239.7	252.1	264.5	272.8	276.9	281.0	285.1	289.3
87.5°	220.9	232.8	244.8	252.7	256.5	260.3	264.1	267.9
90°	232.8	244.1	255.5	263.0	266.8	270.6	274.3	278.1
92.5°	220.6	232.3	243.9	251.5	255.1	258.7	262.3	265.9
95°	238.9	250.1	261.3	268.4	271.5	274.6	277.7	280.8
97.5°	270.4	281.3	292.2	299.4	302.8	306.3	309.7	313.1
100°	292.2	303.1	314.1	321.0	324.0	327.1	330.1	333.1
102.5°	317.4	328.3	339.1	346.1	349.1	352.1	355.1	358.1
105°	355.2	366.0	376.7	383.7	387.0	390.2	393.5	396.7
107.5°	397.0	407.1	417.2	423.4	425.6	427.8	430.0	432.3
110°	426.1	435.5	445.0	451.0	453.6	456.1	458.7	461.3



TEST NUMBER: P331406

CATALOG NUMBER: SA2XXDIP-C865D925U835-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	455.1	464.0	472.9	478.8	481.5	484.3	487.0	489.8
115°	500.0	508.7	517.3	522.9	525.5	528.0	530.6	533.2
117.5°	543.0	551.2	559.4	564.7	567.0	569.3	571.7	574.0
120°	571.9	580.1	588.4	593.8	596.4	599.0	601.5	604.1
122.5°	602.3	609.8	617.3	622.1	624.4	626.7	629.0	631.3
125°	646.5	653.8	661.1	666.0	668.4	670.8	673.3	675.7
127.5°	689.3	695.8	702.3	706.5	708.4	710.3	712.2	714.0
130°	719.1	725.7	732.3	736.4	737.9	739.3	740.8	742.3
132.5°	747.9	753.8	759.6	763.4	765.0	766.7	768.3	770.0
135°	791.0	796.9	802.9	806.7	808.4	810.1	811.8	813.5
137.5°	832.1	837.4	842.6	845.8	846.9	848.0	849.2	850.3
140°	860.3	865.1	869.8	872.6	873.5	874.4	875.2	876.1
142.5°	887.0	891.0	894.9	897.2	897.9	898.5	899.2	899.8
145°	929.1	931.1	933.1	934.4	934.9	935.5	936.1	936.7
147.5°	966.9	967.6	968.3	968.6	968.5	968.3	968.2	968.1
150°	992.3	993.0	993.6	993.6	993.0	992.3	991.6	991.0
152.5°	1018.2	1019.0	1019.9	1019.9	1019.0	1018.2	1017.4	1016.5
155°	1051.1	1052.2	1053.3	1053.5	1052.8	1052.2	1051.5	1050.8
157.5°	1081.4	1082.9	1084.4	1084.6	1083.6	1082.5	1081.4	1080.4
160°	1099.4	1100.7	1102.1	1102.3	1101.4	1100.5	1099.6	1098.7
162.5°	1115.7	1117.2	1118.7	1119.0	1117.9	1116.8	1115.8	1114.7
165°	1136.8	1138.3	1139.9	1140.1	1139.0	1137.9	1136.8	1135.7
167.5°	1154.1	1155.7	1157.2	1157.4	1156.3	1155.1	1154.0	1152.8
170°	1163.7	1165.3	1166.8	1166.9	1165.6	1164.3	1162.9	1161.6
172.5°	1170.9	1172.5	1174.0	1174.1	1172.8	1171.5	1170.1	1168.8
175°	1178.7	1180.2	1181.8	1181.9	1180.6	1179.2	1177.9	1176.6
177.5°	1182.3	1183.4	1184.4	1184.4	1183.4	1182.3	1181.2	1180.2
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6

(END OF REPORT)