

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331723-927

Luminaire Tested: **SA2XXRDIP-C865D925U927-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331723-927  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5546.9 lumens  
Efficiency: N/A  
Efficacy: 91.7 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 60.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331723-927  
CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	54	54	54	47				47
1	98	94	90	87	90	86	83	81	73	71	69	60	59	57	48	47	47	41				41
2	90	83	77	72	82	76	72	67	65	61	58	54	51	49	44	42	40	36				36
3	82	74	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35	31				31
4	76	66	58	53	70	61	54	49	52	47	43	43	40	37	36	33	31	28				28
5	70	59	51	46	64	55	48	43	47	42	38	39	36	33	33	30	28	25				25
6	65	53	46	40	59	50	43	38	43	37	33	36	32	29	30	27	25	22				22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	23	20				20
8	56	44	37	32	52	41	35	30	36	31	27	30	27	24	26	23	20	18				18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	24	21	19	17				17
10	49	37	30	26	45	35	29	25	30	26	22	26	22	20	22	19	17	15				15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	24425	24425	24425	24425
5°	27279	24577	21793	24577
10°	30263	24405	18889	24405
15°	31753	24047	14883	24047
20°	27527	23517	12880	23517
25°	18054	22792	11500	22792
30°	12152	21912	10407	21912
35°	9841	20802	9386	20802
40°	8753	19597	8686	19597
45°	7921	18182	7752	18182
50°	7209	16779	7181	16779
55°	6776	15226	6688	15226
60°	5667	13798	5603	13798
65°	4779	12531	5421	12531
70°	4419	11188	5113	11188
75°	4130	9738	4722	9738
80°	3812	8015	4203	8015
85°	3501	6317	3705	6317



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.4	2.6
10°-20°	399.6	7.2
20°-30°	514.9	9.3
30°-40°	489.3	8.8
40°-50°	419.2	7.6
50°-60°	319.2	5.8
60°-70°	201.8	3.6
70°-80°	100.8	1.8
80°-90°	28.7	0.5
90°-100°	33.4	0.6
100°-110°	122.3	2.2
110°-120°	326.9	5.9
120°-130°	539.7	9.7
130°-140°	574.0	10.3
140°-150°	533.5	9.6
150°-160°	428.9	7.7
160°-170°	276.4	5.0
170°-180°	95.1	1.7
0°-30°	1057.9	19.1
0°-40°	1547.2	27.9
0°-60°	2285.6	41.2
0°-90°	2616.8	47.2
90°-120°	482.6	8.7
90°-150°	2129.7	38.4
90°-180°	2930.0	52.8
0°-180°	5546.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1513	1513	1513	1513	1513	
5°	1683	1516	1345	1516	1683	166
15°	1900	1439	890	1439	1900	512
25°	1013	1279	646	1279	1013	481
35°	499	1055	476	1055	499	319
45°	347	796	340	796	347	269
55°	241	541	238	541	241	211
65°	125	328	142	328	125	127
75°	66	156	76	156	66	70
85°	19	34	20	34	19	21
90°	20	1	20	1	20	10
95°	31	47	31	47	31	29
105°	55	220	55	220	55	57
115°	59	416	59	416	59	149
125°	619	588	619	588	619	535
135°	752	728	752	728	752	579
145°	857	844	857	844	857	536
155°	930	930	930	930	930	429
165°	978	980	978	980	978	276
175°	996	1002	996	1002	996	95
180°	1000	1000	1000	1000	1000	



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1574.1	1575.4	1576.7	1573.7	1573.7	1571.2	1565.7	1561.5	1549.7	1548.1	1548.1
5°	1683.1	1682.0	1684.1	1677.3	1667.8	1665.7	1655.7	1642.6	1628.9	1613.7	1610.5
7.5°	1791.3	1789.7	1785.5	1784.4	1777.1	1761.3	1745.2	1728.1	1705.3	1683.1	1672.0
10°	1845.9	1863.3	1852.8	1834.4	1838.1	1813.4	1800.2	1777.7	1758.7	1725.6	1718.2
12.5°	1899.8	1906.6	1903.3	1892.8	1888.2	1871.0	1853.2	1833.6	1798.6	1768.9	1743.0
15°	1899.6	1909.6	1912.2	1909.1	1911.7	1910.7	1901.2	1884.8	1854.4	1821.8	1793.4
17.5°	1759.4	1766.3	1783.5	1795.2	1809.9	1841.0	1856.4	1862.3	1857.8	1839.2	1819.2
20°	1602.1	1590.5	1638.9	1663.6	1684.6	1737.2	1782.4	1799.8	1827.6	1827.1	1821.8
22.5°	1379.2	1382.0	1427.8	1457.1	1518.5	1571.1	1622.6	1687.9	1741.8	1777.4	1798.3
25°	1013.4	1033.4	1079.1	1119.0	1187.4	1285.2	1374.0	1477.0	1574.2	1651.0	1724.0
27.5°	761.1	762.6	798.8	835.8	876.3	956.4	1068.3	1191.3	1329.9	1444.3	1575.9
30°	651.8	648.6	663.8	686.4	721.1	783.2	867.3	988.2	1126.4	1298.8	1452.3
32.5°	574.4	574.6	586.1	602.8	631.6	673.4	731.0	829.3	959.9	1129.3	1309.3
35°	499.3	498.8	507.2	519.3	531.4	558.2	597.6	649.1	739.0	897.2	1081.2
37.5°	445.5	447.8	451.9	459.5	472.9	487.7	511.4	546.1	610.1	703.6	858.3
40°	415.3	416.3	422.1	428.4	436.3	447.8	467.3	495.1	541.9	616.6	729.5
42.5°	387.5	388.6	392.6	398.5	404.7	416.3	432.4	456.5	494.4	552.6	645.9
45°	346.9	346.9	350.6	353.2	360.0	370.6	383.7	403.7	429.9	473.1	535.1
47.5°	308.9	309.0	311.4	315.9	320.2	328.4	341.4	357.7	376.8	410.1	463.1
50°	287.0	287.5	289.1	292.8	295.4	302.8	312.8	326.9	346.9	372.6	416.8
52.5°	269.3	269.0	271.0	272.6	274.4	279.6	287.1	299.6	317.5	339.8	376.4
55°	240.7	238.6	241.8	244.4	246.0	248.1	252.3	260.2	275.4	294.4	321.7
57.5°	205.0	204.1	206.4	208.7	213.7	219.4	223.0	228.0	235.9	249.5	276.6
60°	175.5	175.5	180.3	181.9	187.7	195.0	202.4	206.6	214.4	223.4	243.4
62.5°	149.5	149.9	152.1	153.7	156.9	166.0	176.3	185.5	193.0	201.5	214.8
65°	125.1	126.1	126.1	127.2	129.3	131.4	135.6	143.0	156.1	168.2	178.2
67.5°	106.2	106.5	106.8	107.9	108.4	110.7	112.4	115.7	118.7	130.2	142.5
70°	93.6	95.1	94.6	95.7	96.2	97.2	99.3	100.9	105.7	108.3	115.7
72.5°	81.8	82.9	82.9	83.5	84.8	85.1	86.7	88.3	91.3	93.6	97.5
75°	66.2	65.7	66.2	67.3	67.8	68.4	68.4	70.4	72.0	74.1	76.8
77.5°	51.1	51.7	51.5	51.7	51.7	52.7	52.6	53.5	55.1	56.2	57.4
80°	41.0	41.5	41.0	41.5	42.1	42.5	42.1	42.5	44.1	45.2	45.2
82.5°	31.8	31.8	32.2	32.2	32.4	32.5	33.2	33.4	34.5	34.3	34.7
85°	18.9	18.4	18.4	18.4	18.9	19.4	18.9	18.9	19.4	19.4	19.4
87.5°	10.6	11.0	10.9	10.9	10.8	10.7	10.5	10.8	10.2	10.5	9.8
90°	19.6	19.3	18.9	18.5	18.2	17.7	16.9	16.1	15.3	14.5	13.2
92.5°	19.6	19.3	19.2	18.9	18.8	18.5	18.1	17.6	17.2	16.8	16.2
95°	31.1	31.3	31.4	31.6	31.8	31.4	30.7	29.8	29.0	28.2	27.1
97.5°	41.5	41.4	41.1	41.0	40.7	40.3	39.7	39.1	38.4	37.8	35.2
100°	48.5	48.2	47.8	47.5	47.2	46.4	45.1	43.8	42.5	41.3	38.5
102.5°	52.0	51.5	51.0	50.6	50.1	49.1	47.5	45.7	44.0	42.4	65.3
105°	55.0	54.3	53.7	53.1	52.4	51.2	49.4	47.7	45.9	44.1	88.0
107.5°	56.6	55.9	55.3	54.7	54.0	54.6	56.4	58.1	60.0	61.8	114.4
110°	57.2	56.5	55.8	55.2	54.6	62.3	78.3	94.4	110.5	126.6	173.1



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.8	57.2	56.7	56.2	55.7	84.8	143.4	202.1	260.7	319.3	330.8
115°	59.3	70.9	82.5	94.0	105.6	148.6	223.1	297.5	371.9	446.4	442.4
117.5°	242.2	280.3	318.3	356.3	394.3	422.4	440.5	458.4	476.4	494.4	491.7
120°	441.3	463.0	484.7	506.4	528.1	538.1	536.1	534.2	532.3	530.3	527.4
122.5°	550.7	554.9	559.1	563.4	567.6	569.1	567.9	566.8	565.6	564.5	561.3
125°	618.6	618.1	617.6	617.1	616.6	615.8	614.7	613.6	612.5	611.3	608.3
127.5°	661.4	661.3	661.2	661.2	661.0	660.2	658.5	656.9	655.2	653.6	651.3
130°	688.0	688.2	688.3	688.6	688.7	687.9	686.1	684.4	682.5	680.8	679.1
132.5°	714.1	714.2	714.4	714.5	714.7	714.1	712.6	711.1	709.6	708.0	706.2
135°	751.7	752.0	752.3	752.7	753.0	752.3	750.8	749.2	747.5	745.9	744.5
137.5°	786.0	786.6	787.1	787.7	788.2	787.7	786.1	784.5	782.9	781.4	779.7
140°	807.4	808.3	809.1	809.8	810.6	810.3	808.9	807.4	806.0	804.5	802.8
142.5°	828.2	829.1	829.9	830.7	831.5	831.2	829.9	828.5	827.3	825.9	823.9
145°	857.4	858.2	859.0	859.8	860.5	860.4	859.3	858.2	857.0	855.9	853.2
147.5°	883.0	883.6	884.3	884.9	885.7	885.6	884.7	883.9	883.0	882.3	879.6
150°	898.6	899.4	900.2	901.0	901.8	901.7	900.8	899.8	898.8	897.9	895.3
152.5°	911.9	913.0	914.0	915.0	916.2	916.2	915.2	914.3	913.3	912.4	909.9
155°	930.4	931.7	933.0	934.3	935.6	935.7	934.8	933.8	932.8	931.8	929.9
157.5°	947.4	948.6	949.8	951.1	952.4	952.4	951.3	950.2	949.2	948.1	946.7
160°	957.2	958.3	959.4	960.5	961.7	961.8	960.8	959.8	958.9	957.9	957.0
162.5°	965.3	966.7	968.0	969.5	970.8	971.0	969.9	968.8	967.7	966.6	965.7
165°	977.5	978.6	979.7	980.8	981.9	981.9	980.8	979.7	978.6	977.5	977.0
167.5°	985.1	986.6	988.0	989.4	990.9	991.1	989.9	988.8	987.7	986.6	986.1
170°	989.8	991.2	992.6	994.1	995.5	995.7	994.6	993.5	992.3	991.2	990.9
172.5°	993.2	994.7	996.1	997.5	999.0	999.2	998.1	996.9	995.8	994.7	994.3
175°	996.2	997.8	999.5	1001.1	1002.7	1002.9	1001.8	1000.7	999.6	998.4	998.1
177.5°	998.1	999.3	1000.4	1001.6	1002.7	1002.9	1002.0	1001.1	1000.2	999.3	999.2
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1548.9	1545.5	1542.6	1535.0	1531.2	1522.8	1521.5	1521.1	1510.2	1499.7	1496.7
5°	1602.1	1593.7	1581.0	1566.4	1551.1	1535.3	1524.8	1516.4	1495.4	1475.4	1463.9
7.5°	1655.7	1637.6	1615.9	1588.0	1564.8	1538.7	1519.3	1502.0	1472.2	1443.6	1424.3
10°	1695.7	1666.2	1637.3	1598.9	1569.0	1539.5	1512.2	1488.6	1454.9	1417.1	1390.3
12.5°	1720.5	1688.1	1648.2	1610.7	1571.9	1534.5	1497.9	1467.5	1428.0	1388.9	1357.0
15°	1754.0	1719.3	1671.0	1617.3	1567.4	1518.5	1476.5	1438.6	1387.1	1340.3	1301.4
17.5°	1781.5	1733.7	1681.8	1619.8	1561.9	1499.8	1445.7	1397.3	1340.0	1283.6	1237.7
20°	1790.3	1743.0	1683.1	1621.0	1552.7	1479.6	1421.3	1368.7	1307.2	1245.7	1193.2
22.5°	1784.8	1748.0	1681.3	1607.1	1537.2	1460.7	1394.8	1333.8	1265.6	1202.8	1141.9
25°	1747.7	1735.0	1672.0	1591.0	1511.2	1422.4	1346.1	1279.4	1201.6	1134.3	1068.0
27.5°	1661.2	1688.4	1649.3	1563.1	1474.3	1379.0	1293.3	1217.3	1136.6	1060.9	994.9
30°	1577.9	1640.5	1623.7	1543.7	1444.4	1350.8	1254.7	1175.3	1089.1	1011.3	946.1
32.5°	1464.0	1567.3	1583.7	1516.9	1414.1	1311.3	1210.5	1131.6	1041.6	959.6	896.0
35°	1282.5	1437.0	1508.0	1465.5	1362.4	1251.5	1147.4	1055.4	965.0	884.1	821.0
37.5°	1066.0	1276.5	1394.8	1397.8	1303.2	1187.9	1074.6	983.3	890.7	811.3	743.0
40°	925.6	1153.7	1307.7	1341.9	1262.0	1137.4	1022.9	929.8	839.4	761.6	683.3
42.5°	799.5	1026.7	1216.1	1275.5	1212.0	1088.2	973.3	876.0	788.1	714.5	634.5
45°	646.5	845.2	1053.8	1160.1	1124.8	1010.3	888.8	796.3	713.8	650.2	573.5
47.5°	545.4	685.4	887.3	1030.9	1030.3	925.7	806.3	717.7	641.1	581.5	519.4
50°	487.7	609.7	780.5	943.5	957.1	869.3	755.8	668.0	596.6	534.0	484.1
52.5°	436.0	536.5	690.1	846.4	885.3	809.2	699.1	618.1	548.7	491.2	448.4
55°	368.4	446.2	562.9	709.1	767.9	714.3	616.6	540.9	484.7	436.3	399.5
57.5°	311.7	370.0	463.7	581.3	649.9	616.2	535.5	474.0	425.9	382.1	353.1
60°	275.9	323.8	403.1	501.5	577.1	553.5	484.7	427.3	386.3	348.5	321.2
62.5°	242.3	283.4	351.4	431.2	500.6	490.8	434.6	386.5	350.6	316.1	292.9
65°	195.0	225.0	278.1	340.6	396.3	401.1	360.6	328.0	296.0	268.6	248.1
67.5°	155.3	174.8	212.2	264.9	306.7	321.5	296.8	272.0	246.5	225.4	207.6
70°	130.9	146.6	174.0	216.6	254.9	270.7	256.5	237.0	215.0	197.6	182.4
72.5°	106.1	121.4	141.6	172.9	205.7	222.8	217.9	203.8	185.9	171.6	157.2
75°	79.9	84.6	98.3	119.3	145.0	159.8	163.5	156.1	141.9	130.9	122.5
77.5°	59.1	61.9	68.4	79.5	96.3	109.4	114.8	113.9	104.2	97.8	89.9
80°	47.3	48.9	52.0	56.8	69.4	82.5	86.2	86.2	79.4	76.8	68.8
82.5°	36.0	37.1	39.0	41.6	47.5	58.9	63.1	63.9	59.6	56.2	49.9
85°	20.5	20.0	21.0	22.6	23.7	26.8	33.1	34.1	33.1	28.9	27.3
87.5°	9.5	9.7	9.4	8.7	8.8	8.9	10.6	12.4	11.0	10.1	9.6
90°	11.9	10.6	9.3	7.8	6.0	4.3	2.5	0.7	2.5	4.3	6.0
92.5°	15.5	14.9	14.2	13.9	14.1	14.3	14.4	14.6	14.4	14.3	14.1
95°	26.0	24.9	23.7	25.8	31.1	36.4	41.7	47.1	41.7	36.4	31.1
97.5°	32.6	29.9	27.3	33.5	48.5	63.5	78.3	93.3	78.3	63.5	48.5
100°	35.8	33.0	30.3	39.9	61.9	84.0	106.0	128.1	106.0	84.0	61.9
102.5°	88.1	111.0	133.9	147.6	152.3	156.9	161.6	166.3	161.6	156.9	152.3
105°	131.9	175.8	219.7	239.2	234.4	229.6	224.7	219.9	224.7	229.6	234.4
107.5°	167.1	219.7	272.4	296.8	292.8	288.9	285.0	281.1	285.0	288.9	292.8
110°	219.5	266.0	312.4	334.0	330.7	327.3	323.9	320.5	323.9	327.3	330.7





TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	342.3	353.8	365.3	369.5	366.5	363.5	360.5	357.5	360.5	363.5	366.5
115°	438.4	434.4	430.3	426.9	424.2	421.4	418.7	416.0	418.7	421.4	424.2
117.5°	488.9	486.2	483.4	480.5	477.4	474.4	471.3	468.3	471.3	474.4	477.4
120°	524.5	521.7	518.7	516.1	513.7	511.3	508.8	506.4	508.8	511.3	513.7
122.5°	558.2	555.0	551.8	549.0	546.4	543.9	541.4	538.8	541.4	543.9	546.4
125°	605.2	602.2	599.1	596.6	594.5	592.4	590.3	588.2	590.3	592.4	594.5
127.5°	649.0	646.7	644.4	642.1	639.8	637.5	635.3	632.9	635.3	637.5	639.8
130°	677.2	675.5	673.8	671.5	669.0	666.4	663.8	661.3	663.8	666.4	669.0
132.5°	704.5	702.7	700.9	698.9	696.8	694.6	692.4	690.2	692.4	694.6	696.8
135°	743.1	741.6	740.1	738.2	735.5	733.0	730.4	727.9	730.4	733.0	735.5
137.5°	778.1	776.4	774.8	773.1	771.3	769.5	767.7	765.9	767.7	769.5	771.3
140°	801.0	799.2	797.5	795.9	794.6	793.4	792.1	790.8	792.1	793.4	794.6
142.5°	821.9	819.8	817.8	816.3	815.1	814.0	812.8	811.6	812.8	814.0	815.1
145°	850.4	847.7	844.9	843.7	843.8	844.0	844.1	844.3	844.1	844.0	843.8
147.5°	876.9	874.1	871.4	870.4	871.0	871.6	872.2	872.8	872.2	871.6	871.0
150°	892.7	890.2	887.6	886.8	888.0	889.1	890.3	891.4	890.3	889.1	888.0
152.5°	907.4	905.0	902.5	902.0	903.2	904.4	905.7	907.0	905.7	904.4	903.2
155°	928.0	926.1	924.2	923.9	925.3	926.8	928.3	929.7	928.3	926.8	925.3
157.5°	945.4	944.0	942.7	942.6	943.8	945.1	946.3	947.5	946.3	945.1	943.8
160°	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9	957.0	956.0	955.0
162.5°	964.9	964.1	963.2	963.3	964.2	965.3	966.2	967.2	966.2	965.3	964.2
165°	976.4	976.0	975.5	975.7	976.7	977.7	978.7	979.6	978.7	977.7	976.7
167.5°	985.6	985.2	984.8	985.0	986.0	987.0	987.9	988.9	987.9	987.0	986.0
170°	990.5	990.2	989.9	990.2	991.2	992.1	993.1	994.1	993.1	992.1	991.2
172.5°	994.0	993.7	993.4	993.7	994.7	995.6	996.6	997.5	996.6	995.6	994.7
175°	997.8	997.4	997.1	997.5	998.6	999.8	1000.9	1002.0	1000.9	999.8	998.6
177.5°	999.0	998.9	998.8	999.2	1000.1	1001.0	1001.9	1002.7	1001.9	1001.0	1000.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1491.3	1488.4	1482.9	1474.5	1469.4	1460.6	1454.7	1458.1	1458.9	1458.1	1457.2
5°	1451.2	1440.2	1425.0	1410.2	1396.5	1381.9	1373.4	1369.8	1362.4	1358.2	1356.1
7.5°	1402.8	1383.8	1362.2	1336.6	1314.8	1292.0	1280.3	1274.5	1259.5	1251.3	1244.1
10°	1366.6	1336.6	1315.1	1281.4	1261.0	1231.0	1210.5	1211.0	1190.5	1178.9	1170.5
12.5°	1326.7	1293.8	1257.9	1227.6	1199.1	1175.0	1150.4	1140.3	1118.6	1107.5	1084.7
15°	1260.4	1222.1	1184.2	1143.2	1114.3	1077.0	1041.2	997.6	962.4	931.9	923.5
17.5°	1188.1	1140.6	1102.6	1054.5	1005.0	942.2	900.8	875.4	854.2	838.1	826.2
20°	1138.5	1090.1	1049.6	977.2	910.4	867.8	837.3	817.8	795.8	778.5	769.0
22.5°	1086.3	1035.9	980.7	899.8	847.7	813.6	786.4	764.1	749.1	735.5	726.9
25°	1012.3	957.1	866.3	810.5	768.4	732.7	713.8	700.1	684.4	666.0	657.5
27.5°	934.1	846.4	781.1	739.7	699.5	676.3	659.3	638.8	624.7	616.5	607.7
30°	875.7	787.9	736.9	691.7	663.3	637.5	617.6	606.0	592.4	578.2	572.4
32.5°	810.5	740.4	691.5	653.9	625.0	603.1	587.3	568.6	558.7	550.0	537.9
35°	729.5	676.4	631.8	601.3	574.0	556.1	537.7	526.6	508.8	501.5	496.7
37.5°	661.0	615.0	581.6	549.5	527.8	508.0	496.8	479.3	471.5	461.3	451.3
40°	622.3	577.1	545.1	518.8	494.6	479.9	465.7	451.5	440.0	435.2	423.1
42.5°	582.8	546.1	514.0	485.1	469.0	453.4	435.5	425.0	413.0	405.4	397.9
45°	528.2	495.7	468.3	444.7	426.8	410.5	398.9	381.6	374.8	359.5	353.2
47.5°	480.3	450.0	424.0	401.5	384.0	373.4	356.5	342.9	332.0	322.7	314.5
50°	446.2	421.0	395.8	375.8	360.0	344.8	327.5	320.6	303.8	299.0	294.4
52.5°	415.1	391.2	368.0	348.5	332.7	317.9	302.6	293.7	282.3	277.7	274.2
55°	371.6	348.5	326.4	309.0	293.3	278.1	268.6	257.5	252.3	248.6	244.4
57.5°	327.9	307.0	290.2	272.6	256.7	244.6	233.7	227.0	221.6	216.7	211.8
60°	300.2	280.1	264.9	248.6	232.3	222.4	213.9	206.0	199.7	192.3	190.3
62.5°	270.7	253.3	239.2	223.4	209.2	200.0	192.0	184.6	177.1	166.3	163.3
65°	230.2	216.6	201.8	188.7	176.1	167.2	155.6	147.2	144.0	143.0	142.4
67.5°	193.6	180.7	168.1	154.6	143.1	134.9	129.0	127.7	125.5	124.8	123.4
70°	169.2	157.2	144.6	131.9	120.9	119.3	117.2	115.1	112.5	111.5	110.4
72.5°	147.3	134.9	122.2	112.2	107.4	105.4	103.3	101.2	99.4	98.4	97.8
75°	113.0	101.5	93.0	89.4	86.7	85.2	82.0	80.4	79.4	77.8	77.2
77.5°	81.4	74.9	71.0	68.7	65.9	64.2	62.4	60.8	59.7	59.4	58.5
80°	62.0	58.9	56.2	53.1	52.0	49.9	49.4	47.8	48.3	46.8	46.8
82.5°	48.2	44.1	41.9	40.5	39.5	37.7	37.2	36.4	36.6	35.4	35.4
85°	24.7	23.7	22.6	21.5	21.5	20.0	20.5	20.0	20.0	18.9	18.4
87.5°	9.6	9.4	8.9	9.1	9.3	9.2	9.3	9.1	9.3	9.4	9.1
90°	7.8	9.3	10.6	11.9	13.2	14.5	15.3	16.1	16.9	17.7	18.2
92.5°	13.9	14.2	14.9	15.5	16.2	16.8	17.2	17.6	18.1	18.5	18.8
95°	25.8	23.7	24.9	26.0	27.1	28.2	29.0	29.8	30.7	31.4	31.8
97.5°	33.5	27.3	29.9	32.6	35.2	37.8	38.4	39.1	39.7	40.3	40.7
100°	39.9	30.3	33.0	35.8	38.5	41.3	42.5	43.8	45.1	46.4	47.2
102.5°	147.6	133.9	111.0	88.1	65.3	42.4	44.0	45.7	47.5	49.1	50.1
105°	239.2	219.7	175.8	131.9	88.0	44.1	45.9	47.7	49.4	51.2	52.4
107.5°	296.8	272.4	219.7	167.1	114.4	61.8	60.0	58.1	56.4	54.6	54.0
110°	334.0	312.4	266.0	219.5	173.1	126.6	110.5	94.4	78.3	62.3	54.6



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	369.5	365.3	353.8	342.3	330.8	319.3	260.7	202.1	143.4	84.8	55.7
115°	426.9	430.3	434.4	438.4	442.4	446.4	371.9	297.5	223.1	148.6	105.6
117.5°	480.5	483.4	486.2	488.9	491.7	494.4	476.4	458.4	440.5	422.4	394.3
120°	516.1	518.7	521.7	524.5	527.4	530.3	532.3	534.2	536.1	538.1	528.1
122.5°	549.0	551.8	555.0	558.2	561.3	564.5	565.6	566.8	567.9	569.1	567.6
125°	596.6	599.1	602.2	605.2	608.3	611.3	612.5	613.6	614.7	615.8	616.6
127.5°	642.1	644.4	646.7	649.0	651.3	653.6	655.2	656.9	658.5	660.2	661.0
130°	671.5	673.8	675.5	677.2	679.1	680.8	682.5	684.4	686.1	687.9	688.7
132.5°	698.9	700.9	702.7	704.5	706.2	708.0	709.6	711.1	712.6	714.1	714.7
135°	738.2	740.1	741.6	743.1	744.5	745.9	747.5	749.2	750.8	752.3	753.0
137.5°	773.1	774.8	776.4	778.1	779.7	781.4	782.9	784.5	786.1	787.7	788.2
140°	795.9	797.5	799.2	801.0	802.8	804.5	806.0	807.4	808.9	810.3	810.6
142.5°	816.3	817.8	819.8	821.9	823.9	825.9	827.3	828.5	829.9	831.2	831.5
145°	843.7	844.9	847.7	850.4	853.2	855.9	857.0	858.2	859.3	860.4	860.5
147.5°	870.4	871.4	874.1	876.9	879.6	882.3	883.0	883.9	884.7	885.6	885.7
150°	886.8	887.6	890.2	892.7	895.3	897.9	898.8	899.8	900.8	901.7	901.8
152.5°	902.0	902.5	905.0	907.4	909.9	912.4	913.3	914.3	915.2	916.2	916.2
155°	923.9	924.2	926.1	928.0	929.9	931.8	932.8	933.8	934.8	935.7	935.6
157.5°	942.6	942.7	944.0	945.4	946.7	948.1	949.2	950.2	951.3	952.4	952.4
160°	954.0	954.0	955.0	956.0	957.0	957.9	958.9	959.8	960.8	961.8	961.7
162.5°	963.3	963.2	964.1	964.9	965.7	966.6	967.7	968.8	969.9	971.0	970.8
165°	975.7	975.5	976.0	976.4	977.0	977.5	978.6	979.7	980.8	981.9	981.9
167.5°	985.0	984.8	985.2	985.6	986.1	986.6	987.7	988.8	989.9	991.1	990.9
170°	990.2	989.9	990.2	990.5	990.9	991.2	992.3	993.5	994.6	995.7	995.5
172.5°	993.7	993.4	993.7	994.0	994.3	994.7	995.8	996.9	998.1	999.2	999.0
175°	997.5	997.1	997.4	997.8	998.1	998.4	999.6	1000.7	1001.8	1002.9	1002.7
177.5°	999.2	998.8	998.9	999.0	999.2	999.3	1000.2	1001.1	1002.0	1002.9	1002.7
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1452.6	1453.4	1452.1	1453.0	1452.1	1453.4	1452.6	1457.2	1458.1	1458.9	1458.1
5°	1353.4	1347.2	1346.1	1344.6	1346.1	1347.2	1353.4	1356.1	1358.2	1362.4	1369.8
7.5°	1235.1	1234.1	1231.5	1227.9	1231.5	1234.1	1235.1	1244.1	1251.3	1259.5	1274.5
10°	1159.0	1156.3	1155.9	1152.1	1155.9	1156.3	1159.0	1170.5	1178.9	1190.5	1211.0
12.5°	1069.8	1052.9	1051.1	1042.0	1051.1	1052.9	1069.8	1084.7	1107.5	1118.6	1140.3
15°	910.9	907.8	897.2	890.4	897.2	907.8	910.9	923.5	931.9	962.4	997.6
17.5°	820.1	809.8	806.5	805.0	806.5	809.8	820.1	826.2	838.1	854.2	875.4
20°	761.6	752.2	750.6	749.6	750.6	752.2	761.6	769.0	778.5	795.8	817.8
22.5°	721.3	711.4	707.3	704.1	707.3	711.4	721.3	726.9	735.5	749.1	764.1
25°	652.3	648.6	646.5	645.5	646.5	648.6	652.3	657.5	666.0	684.4	700.1
27.5°	598.3	590.3	588.7	586.0	588.7	590.3	598.3	607.7	616.5	624.7	638.8
30°	567.7	565.1	561.3	558.2	561.3	565.1	567.7	572.4	578.2	592.4	606.0
32.5°	531.5	529.3	526.0	524.6	526.0	529.3	531.5	537.9	550.0	558.7	568.6
35°	491.5	484.1	480.9	476.2	480.9	484.1	491.5	496.7	501.5	508.8	526.6
37.5°	449.1	445.2	440.8	442.4	440.8	445.2	449.1	451.3	461.3	471.5	479.3
40°	416.3	413.7	412.6	412.1	412.6	413.7	416.3	423.1	435.2	440.0	451.5
42.5°	390.2	382.9	380.2	380.1	380.2	382.9	390.2	397.9	405.4	413.0	425.0
45°	350.6	343.7	339.1	339.5	339.1	343.7	350.6	353.2	359.5	374.8	381.6
47.5°	310.0	309.8	306.9	307.8	306.9	309.8	310.0	314.5	322.7	332.0	342.9
50°	290.7	287.5	285.4	285.9	285.4	287.5	290.7	294.4	299.0	303.8	320.6
52.5°	272.2	269.4	267.8	270.0	267.8	269.4	272.2	274.2	277.7	282.3	293.7
55°	241.8	238.6	238.1	237.6	238.1	238.6	241.8	244.4	248.6	252.3	257.5
57.5°	207.9	205.7	202.6	201.2	202.6	205.7	207.9	211.8	216.7	221.6	227.0
60°	183.5	179.3	174.0	173.5	174.0	179.3	183.5	190.3	192.3	199.7	206.0
62.5°	161.1	160.3	159.2	159.1	159.2	160.3	161.1	163.3	166.3	177.1	184.6
65°	141.4	140.9	141.4	141.9	141.4	140.9	141.4	142.4	143.0	144.0	147.2
67.5°	123.2	122.2	121.3	121.8	121.3	122.2	123.2	123.4	124.8	125.5	127.7
70°	109.3	108.8	108.3	108.3	108.3	108.8	109.3	110.4	111.5	112.5	115.1
72.5°	95.9	95.8	95.2	94.8	95.2	95.8	95.9	97.8	98.4	99.4	101.2
75°	76.8	75.7	75.7	75.7	75.7	75.7	76.8	77.2	77.8	79.4	80.4
77.5°	58.5	57.9	57.4	57.0	57.4	57.9	58.5	58.5	59.4	59.7	60.8
80°	46.3	45.7	45.2	45.2	45.2	45.7	46.3	46.8	46.8	48.3	47.8
82.5°	35.3	34.8	34.7	34.3	34.7	34.8	35.3	35.4	35.4	36.6	36.4
85°	18.9	19.4	18.9	20.0	18.9	19.4	18.9	18.4	18.9	20.0	20.0
87.5°	9.2	8.8	9.3	9.0	9.3	8.8	9.2	9.1	9.4	9.3	9.1
90°	18.5	18.9	19.3	19.6	19.3	18.9	18.5	18.2	17.7	16.9	16.1
92.5°	18.9	19.2	19.3	19.6	19.3	19.2	18.9	18.8	18.5	18.1	17.6
95°	31.6	31.4	31.3	31.1	31.3	31.4	31.6	31.8	31.4	30.7	29.8
97.5°	41.0	41.1	41.4	41.5	41.4	41.1	41.0	40.7	40.3	39.7	39.1
100°	47.5	47.8	48.2	48.5	48.2	47.8	47.5	47.2	46.4	45.1	43.8
102.5°	50.6	51.0	51.5	52.0	51.5	51.0	50.6	50.1	49.1	47.5	45.7
105°	53.1	53.7	54.3	55.0	54.3	53.7	53.1	52.4	51.2	49.4	47.7
107.5°	54.7	55.3	55.9	56.6	55.9	55.3	54.7	54.0	54.6	56.4	58.1
110°	55.2	55.8	56.5	57.2	56.5	55.8	55.2	54.6	62.3	78.3	94.4



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	56.2	56.7	57.2	57.8	57.2	56.7	56.2	55.7	84.8	143.4	202.1
115°	94.0	82.5	70.9	59.3	70.9	82.5	94.0	105.6	148.6	223.1	297.5
117.5°	356.3	318.3	280.3	242.2	280.3	318.3	356.3	394.3	422.4	440.5	458.4
120°	506.4	484.7	463.0	441.3	463.0	484.7	506.4	528.1	538.1	536.1	534.2
122.5°	563.4	559.1	554.9	550.7	554.9	559.1	563.4	567.6	569.1	567.9	566.8
125°	617.1	617.6	618.1	618.6	618.1	617.6	617.1	616.6	615.8	614.7	613.6
127.5°	661.2	661.2	661.3	661.4	661.3	661.2	661.2	661.0	660.2	658.5	656.9
130°	688.6	688.3	688.2	688.0	688.2	688.3	688.6	688.7	687.9	686.1	684.4
132.5°	714.5	714.4	714.2	714.1	714.2	714.4	714.5	714.7	714.1	712.6	711.1
135°	752.7	752.3	752.0	751.7	752.0	752.3	752.7	753.0	752.3	750.8	749.2
137.5°	787.7	787.1	786.6	786.0	786.6	787.1	787.7	788.2	787.7	786.1	784.5
140°	809.8	809.1	808.3	807.4	808.3	809.1	809.8	810.6	810.3	808.9	807.4
142.5°	830.7	829.9	829.1	828.2	829.1	829.9	830.7	831.5	831.2	829.9	828.5
145°	859.8	859.0	858.2	857.4	858.2	859.0	859.8	860.5	860.4	859.3	858.2
147.5°	884.9	884.3	883.6	883.0	883.6	884.3	884.9	885.7	885.6	884.7	883.9
150°	901.0	900.2	899.4	898.6	899.4	900.2	901.0	901.8	901.7	900.8	899.8
152.5°	915.0	914.0	913.0	911.9	913.0	914.0	915.0	916.2	916.2	915.2	914.3
155°	934.3	933.0	931.7	930.4	931.7	933.0	934.3	935.6	935.7	934.8	933.8
157.5°	951.1	949.8	948.6	947.4	948.6	949.8	951.1	952.4	952.4	951.3	950.2
160°	960.5	959.4	958.3	957.2	958.3	959.4	960.5	961.7	961.8	960.8	959.8
162.5°	969.5	968.0	966.7	965.3	966.7	968.0	969.5	970.8	971.0	969.9	968.8
165°	980.8	979.7	978.6	977.5	978.6	979.7	980.8	981.9	981.9	980.8	979.7
167.5°	989.4	988.0	986.6	985.1	986.6	988.0	989.4	990.9	991.1	989.9	988.8
170°	994.1	992.6	991.2	989.8	991.2	992.6	994.1	995.5	995.7	994.6	993.5
172.5°	997.5	996.1	994.7	993.2	994.7	996.1	997.5	999.0	999.2	998.1	996.9
175°	1001.1	999.5	997.8	996.2	997.8	999.5	1001.1	1002.7	1002.9	1001.8	1000.7
177.5°	1001.6	1000.4	999.3	998.1	999.3	1000.4	1001.6	1002.7	1002.9	1002.0	1001.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1454.7	1460.6	1469.4	1474.5	1482.9	1488.4	1491.3	1496.7	1499.7	1510.2	1521.1
5°	1373.4	1381.9	1396.5	1410.2	1425.0	1440.2	1451.2	1463.9	1475.4	1495.4	1516.4
7.5°	1280.3	1292.0	1314.8	1336.6	1362.2	1383.8	1402.8	1424.3	1443.6	1472.2	1502.0
10°	1210.5	1231.0	1261.0	1281.4	1315.1	1336.6	1366.6	1390.3	1417.1	1454.9	1488.6
12.5°	1150.4	1175.0	1199.1	1227.6	1257.9	1293.8	1326.7	1357.0	1388.9	1428.0	1467.5
15°	1041.2	1077.0	1114.3	1143.2	1184.2	1222.1	1260.4	1301.4	1340.3	1387.1	1438.6
17.5°	900.8	942.2	1005.0	1054.5	1102.6	1140.6	1188.1	1237.7	1283.6	1340.0	1397.3
20°	837.3	867.8	910.4	977.2	1049.6	1090.1	1138.5	1193.2	1245.7	1307.2	1368.7
22.5°	786.4	813.6	847.7	899.8	980.7	1035.9	1086.3	1141.9	1202.8	1265.6	1333.8
25°	713.8	732.7	768.4	810.5	866.3	957.1	1012.3	1068.0	1134.3	1201.6	1279.4
27.5°	659.3	676.3	699.5	739.7	781.1	846.4	934.1	994.9	1060.9	1136.6	1217.3
30°	617.6	637.5	663.3	691.7	736.9	787.9	875.7	946.1	1011.3	1089.1	1175.3
32.5°	587.3	603.1	625.0	653.9	691.5	740.4	810.5	896.0	959.6	1041.6	1131.6
35°	537.7	556.1	574.0	601.3	631.8	676.4	729.5	821.0	884.1	965.0	1055.4
37.5°	496.8	508.0	527.8	549.5	581.6	615.0	661.0	743.0	811.3	890.7	983.3
40°	465.7	479.9	494.6	518.8	545.1	577.1	622.3	683.3	761.6	839.4	929.8
42.5°	435.5	453.4	469.0	485.1	514.0	546.1	582.8	634.5	714.5	788.1	876.0
45°	398.9	410.5	426.8	444.7	468.3	495.7	528.2	573.5	650.2	713.8	796.3
47.5°	356.5	373.4	384.0	401.5	424.0	450.0	480.3	519.4	581.5	641.1	717.7
50°	327.5	344.8	360.0	375.8	395.8	421.0	446.2	484.1	534.0	596.6	668.0
52.5°	302.6	317.9	332.7	348.5	368.0	391.2	415.1	448.4	491.2	548.7	618.1
55°	268.6	278.1	293.3	309.0	326.4	348.5	371.6	399.5	436.3	484.7	540.9
57.5°	233.7	244.6	256.7	272.6	290.2	307.0	327.9	353.1	382.1	425.9	474.0
60°	213.9	222.4	232.3	248.6	264.9	280.1	300.2	321.2	348.5	386.3	427.3
62.5°	192.0	200.0	209.2	223.4	239.2	253.3	270.7	292.9	316.1	350.6	386.5
65°	155.6	167.2	176.1	188.7	201.8	216.6	230.2	248.1	268.6	296.0	328.0
67.5°	129.0	134.9	143.1	154.6	168.1	180.7	193.6	207.6	225.4	246.5	272.0
70°	117.2	119.3	120.9	131.9	144.6	157.2	169.2	182.4	197.6	215.0	237.0
72.5°	103.3	105.4	107.4	112.2	122.2	134.9	147.3	157.2	171.6	185.9	203.8
75°	82.0	85.2	86.7	89.4	93.0	101.5	113.0	122.5	130.9	141.9	156.1
77.5°	62.4	64.2	65.9	68.7	71.0	74.9	81.4	89.9	97.8	104.2	113.9
80°	49.4	49.9	52.0	53.1	56.2	58.9	62.0	68.8	76.8	79.4	86.2
82.5°	37.2	37.7	39.5	40.5	41.9	44.1	48.2	49.9	56.2	59.6	63.9
85°	20.5	20.0	21.5	21.5	22.6	23.7	24.7	27.3	28.9	33.1	34.1
87.5°	9.3	9.2	9.3	9.1	8.9	9.4	9.6	9.6	10.1	11.0	12.4
90°	15.3	14.5	13.2	11.9	10.6	9.3	7.8	6.0	4.3	2.5	0.7
92.5°	17.2	16.8	16.2	15.5	14.9	14.2	13.9	14.1	14.3	14.4	14.6
95°	29.0	28.2	27.1	26.0	24.9	23.7	25.8	31.1	36.4	41.7	47.1
97.5°	38.4	37.8	35.2	32.6	29.9	27.3	33.5	48.5	63.5	78.3	93.3
100°	42.5	41.3	38.5	35.8	33.0	30.3	39.9	61.9	84.0	106.0	128.1
102.5°	44.0	42.4	65.3	88.1	111.0	133.9	147.6	152.3	156.9	161.6	166.3
105°	45.9	44.1	88.0	131.9	175.8	219.7	239.2	234.4	229.6	224.7	219.9
107.5°	60.0	61.8	114.4	167.1	219.7	272.4	296.8	292.8	288.9	285.0	281.1
110°	110.5	126.6	173.1	219.5	266.0	312.4	334.0	330.7	327.3	323.9	320.5



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	260.7	319.3	330.8	342.3	353.8	365.3	369.5	366.5	363.5	360.5	357.5
115°	371.9	446.4	442.4	438.4	434.4	430.3	426.9	424.2	421.4	418.7	416.0
117.5°	476.4	494.4	491.7	488.9	486.2	483.4	480.5	477.4	474.4	471.3	468.3
120°	532.3	530.3	527.4	524.5	521.7	518.7	516.1	513.7	511.3	508.8	506.4
122.5°	565.6	564.5	561.3	558.2	555.0	551.8	549.0	546.4	543.9	541.4	538.8
125°	612.5	611.3	608.3	605.2	602.2	599.1	596.6	594.5	592.4	590.3	588.2
127.5°	655.2	653.6	651.3	649.0	646.7	644.4	642.1	639.8	637.5	635.3	632.9
130°	682.5	680.8	679.1	677.2	675.5	673.8	671.5	669.0	666.4	663.8	661.3
132.5°	709.6	708.0	706.2	704.5	702.7	700.9	698.9	696.8	694.6	692.4	690.2
135°	747.5	745.9	744.5	743.1	741.6	740.1	738.2	735.5	733.0	730.4	727.9
137.5°	782.9	781.4	779.7	778.1	776.4	774.8	773.1	771.3	769.5	767.7	765.9
140°	806.0	804.5	802.8	801.0	799.2	797.5	795.9	794.6	793.4	792.1	790.8
142.5°	827.3	825.9	823.9	821.9	819.8	817.8	816.3	815.1	814.0	812.8	811.6
145°	857.0	855.9	853.2	850.4	847.7	844.9	843.7	843.8	844.0	844.1	844.3
147.5°	883.0	882.3	879.6	876.9	874.1	871.4	870.4	871.0	871.6	872.2	872.8
150°	898.8	897.9	895.3	892.7	890.2	887.6	886.8	888.0	889.1	890.3	891.4
152.5°	913.3	912.4	909.9	907.4	905.0	902.5	902.0	903.2	904.4	905.7	907.0
155°	932.8	931.8	929.9	928.0	926.1	924.2	923.9	925.3	926.8	928.3	929.7
157.5°	949.2	948.1	946.7	945.4	944.0	942.7	942.6	943.8	945.1	946.3	947.5
160°	958.9	957.9	957.0	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9
162.5°	967.7	966.6	965.7	964.9	964.1	963.2	963.3	964.2	965.3	966.2	967.2
165°	978.6	977.5	977.0	976.4	976.0	975.5	975.7	976.7	977.7	978.7	979.6
167.5°	987.7	986.6	986.1	985.6	985.2	984.8	985.0	986.0	987.0	987.9	988.9
170°	992.3	991.2	990.9	990.5	990.2	989.9	990.2	991.2	992.1	993.1	994.1
172.5°	995.8	994.7	994.3	994.0	993.7	993.4	993.7	994.7	995.6	996.6	997.5
175°	999.6	998.4	998.1	997.8	997.4	997.1	997.5	998.6	999.8	1000.9	1002.0
177.5°	1000.2	999.3	999.2	999.0	998.9	998.8	999.2	1000.1	1001.0	1001.9	1002.7
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1521.5	1522.8	1531.2	1535.0	1542.6	1545.5	1548.9	1548.1	1548.1	1549.7	1561.5
5°	1524.8	1535.3	1551.1	1566.4	1581.0	1593.7	1602.1	1610.5	1613.7	1628.9	1642.6
7.5°	1519.3	1538.7	1564.8	1588.0	1615.9	1637.6	1655.7	1672.0	1683.1	1705.3	1728.1
10°	1512.2	1539.5	1569.0	1598.9	1637.3	1666.2	1695.7	1718.2	1725.6	1758.7	1777.7
12.5°	1497.9	1534.5	1571.9	1610.7	1648.2	1688.1	1720.5	1743.0	1768.9	1798.6	1833.6
15°	1476.5	1518.5	1567.4	1617.3	1671.0	1719.3	1754.0	1793.4	1821.8	1854.4	1884.8
17.5°	1445.7	1499.8	1561.9	1619.8	1681.8	1733.7	1781.5	1819.2	1839.2	1857.8	1862.3
20°	1421.3	1479.6	1552.7	1621.0	1683.1	1743.0	1790.3	1821.8	1827.1	1827.6	1799.8
22.5°	1394.8	1460.7	1537.2	1607.1	1681.3	1748.0	1784.8	1798.3	1777.4	1741.8	1687.9
25°	1346.1	1422.4	1511.2	1591.0	1672.0	1735.0	1747.7	1724.0	1651.0	1574.2	1477.0
27.5°	1293.3	1379.0	1474.3	1563.1	1649.3	1688.4	1661.2	1575.9	1444.3	1329.9	1191.3
30°	1254.7	1350.8	1444.4	1543.7	1623.7	1640.5	1577.9	1452.3	1298.8	1126.4	988.2
32.5°	1210.5	1311.3	1414.1	1516.9	1583.7	1567.3	1464.0	1309.3	1129.3	959.9	829.3
35°	1147.4	1251.5	1362.4	1465.5	1508.0	1437.0	1282.5	1081.2	897.2	739.0	649.1
37.5°	1074.6	1187.9	1303.2	1397.8	1394.8	1276.5	1066.0	858.3	703.6	610.1	546.1
40°	1022.9	1137.4	1262.0	1341.9	1307.7	1153.7	925.6	729.5	616.6	541.9	495.1
42.5°	973.3	1088.2	1212.0	1275.5	1216.1	1026.7	799.5	645.9	552.6	494.4	456.5
45°	888.8	1010.3	1124.8	1160.1	1053.8	845.2	646.5	535.1	473.1	429.9	403.7
47.5°	806.3	925.7	1030.3	1030.9	887.3	685.4	545.4	463.1	410.1	376.8	357.7
50°	755.8	869.3	957.1	943.5	780.5	609.7	487.7	416.8	372.6	346.9	326.9
52.5°	699.1	809.2	885.3	846.4	690.1	536.5	436.0	376.4	339.8	317.5	299.6
55°	616.6	714.3	767.9	709.1	562.9	446.2	368.4	321.7	294.4	275.4	260.2
57.5°	535.5	616.2	649.9	581.3	463.7	370.0	311.7	276.6	249.5	235.9	228.0
60°	484.7	553.5	577.1	501.5	403.1	323.8	275.9	243.4	223.4	214.4	206.6
62.5°	434.6	490.8	500.6	431.2	351.4	283.4	242.3	214.8	201.5	193.0	185.5
65°	360.6	401.1	396.3	340.6	278.1	225.0	195.0	178.2	168.2	156.1	143.0
67.5°	296.8	321.5	306.7	264.9	212.2	174.8	155.3	142.5	130.2	118.7	115.7
70°	256.5	270.7	254.9	216.6	174.0	146.6	130.9	115.7	108.3	105.7	100.9
72.5°	217.9	222.8	205.7	172.9	141.6	121.4	106.1	97.5	93.6	91.3	88.3
75°	163.5	159.8	145.0	119.3	98.3	84.6	79.9	76.8	74.1	72.0	70.4
77.5°	114.8	109.4	96.3	79.5	68.4	61.9	59.1	57.4	56.2	55.1	53.5
80°	86.2	82.5	69.4	56.8	52.0	48.9	47.3	45.2	45.2	44.1	42.5
82.5°	63.1	58.9	47.5	41.6	39.0	37.1	36.0	34.7	34.3	34.5	33.4
85°	33.1	26.8	23.7	22.6	21.0	20.0	20.5	19.4	19.4	19.4	18.9
87.5°	10.6	8.9	8.8	8.7	9.4	9.7	9.5	9.8	10.5	10.2	10.8
90°	2.5	4.3	6.0	7.8	9.3	10.6	11.9	13.2	14.5	15.3	16.1
92.5°	14.4	14.3	14.1	13.9	14.2	14.9	15.5	16.2	16.8	17.2	17.6
95°	41.7	36.4	31.1	25.8	23.7	24.9	26.0	27.1	28.2	29.0	29.8
97.5°	78.3	63.5	48.5	33.5	27.3	29.9	32.6	35.2	37.8	38.4	39.1
100°	106.0	84.0	61.9	39.9	30.3	33.0	35.8	38.5	41.3	42.5	43.8
102.5°	161.6	156.9	152.3	147.6	133.9	111.0	88.1	65.3	42.4	44.0	45.7
105°	224.7	229.6	234.4	239.2	219.7	175.8	131.9	88.0	44.1	45.9	47.7
107.5°	285.0	288.9	292.8	296.8	272.4	219.7	167.1	114.4	61.8	60.0	58.1
110°	323.9	327.3	330.7	334.0	312.4	266.0	219.5	173.1	126.6	110.5	94.4





TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	360.5	363.5	366.5	369.5	365.3	353.8	342.3	330.8	319.3	260.7	202.1
115°	418.7	421.4	424.2	426.9	430.3	434.4	438.4	442.4	446.4	371.9	297.5
117.5°	471.3	474.4	477.4	480.5	483.4	486.2	488.9	491.7	494.4	476.4	458.4
120°	508.8	511.3	513.7	516.1	518.7	521.7	524.5	527.4	530.3	532.3	534.2
122.5°	541.4	543.9	546.4	549.0	551.8	555.0	558.2	561.3	564.5	565.6	566.8
125°	590.3	592.4	594.5	596.6	599.1	602.2	605.2	608.3	611.3	612.5	613.6
127.5°	635.3	637.5	639.8	642.1	644.4	646.7	649.0	651.3	653.6	655.2	656.9
130°	663.8	666.4	669.0	671.5	673.8	675.5	677.2	679.1	680.8	682.5	684.4
132.5°	692.4	694.6	696.8	698.9	700.9	702.7	704.5	706.2	708.0	709.6	711.1
135°	730.4	733.0	735.5	738.2	740.1	741.6	743.1	744.5	745.9	747.5	749.2
137.5°	767.7	769.5	771.3	773.1	774.8	776.4	778.1	779.7	781.4	782.9	784.5
140°	792.1	793.4	794.6	795.9	797.5	799.2	801.0	802.8	804.5	806.0	807.4
142.5°	812.8	814.0	815.1	816.3	817.8	819.8	821.9	823.9	825.9	827.3	828.5
145°	844.1	844.0	843.8	843.7	844.9	847.7	850.4	853.2	855.9	857.0	858.2
147.5°	872.2	871.6	871.0	870.4	871.4	874.1	876.9	879.6	882.3	883.0	883.9
150°	890.3	889.1	888.0	886.8	887.6	890.2	892.7	895.3	897.9	898.8	899.8
152.5°	905.7	904.4	903.2	902.0	902.5	905.0	907.4	909.9	912.4	913.3	914.3
155°	928.3	926.8	925.3	923.9	924.2	926.1	928.0	929.9	931.8	932.8	933.8
157.5°	946.3	945.1	943.8	942.6	942.7	944.0	945.4	946.7	948.1	949.2	950.2
160°	957.0	956.0	955.0	954.0	954.0	955.0	956.0	957.0	957.9	958.9	959.8
162.5°	966.2	965.3	964.2	963.3	963.2	964.1	964.9	965.7	966.6	967.7	968.8
165°	978.7	977.7	976.7	975.7	975.5	976.0	976.4	977.0	977.5	978.6	979.7
167.5°	987.9	987.0	986.0	985.0	984.8	985.2	985.6	986.1	986.6	987.7	988.8
170°	993.1	992.1	991.2	990.2	989.9	990.2	990.5	990.9	991.2	992.3	993.5
172.5°	996.6	995.6	994.7	993.7	993.4	993.7	994.0	994.3	994.7	995.8	996.9
175°	1000.9	999.8	998.6	997.5	997.1	997.4	997.8	998.1	998.4	999.6	1000.7
177.5°	1001.9	1001.0	1000.1	999.2	998.8	998.9	999.0	999.2	999.3	1000.2	1001.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9	999.9



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1565.7	1571.2	1573.7	1573.7	1576.7	1575.4	1574.1
5°	1655.7	1665.7	1667.8	1677.3	1684.1	1682.0	1683.1
7.5°	1745.2	1761.3	1777.1	1784.4	1785.5	1789.7	1791.3
10°	1800.2	1813.4	1838.1	1834.4	1852.8	1863.3	1845.9
12.5°	1853.2	1871.0	1888.2	1892.8	1903.3	1906.6	1899.8
15°	1901.2	1910.7	1911.7	1909.1	1912.2	1909.6	1899.6
17.5°	1856.4	1841.0	1809.9	1795.2	1783.5	1766.3	1759.4
20°	1782.4	1737.2	1684.6	1663.6	1638.9	1590.5	1602.1
22.5°	1622.6	1571.1	1518.5	1457.1	1427.8	1382.0	1379.2
25°	1374.0	1285.2	1187.4	1119.0	1079.1	1033.4	1013.4
27.5°	1068.3	956.4	876.3	835.8	798.8	762.6	761.1
30°	867.3	783.2	721.1	686.4	663.8	648.6	651.8
32.5°	731.0	673.4	631.6	602.8	586.1	574.6	574.4
35°	597.6	558.2	531.4	519.3	507.2	498.8	499.3
37.5°	511.4	487.7	472.9	459.5	451.9	447.8	445.5
40°	467.3	447.8	436.3	428.4	422.1	416.3	415.3
42.5°	432.4	416.3	404.7	398.5	392.6	388.6	387.5
45°	383.7	370.6	360.0	353.2	350.6	346.9	346.9
47.5°	341.4	328.4	320.2	315.9	311.4	309.0	308.9
50°	312.8	302.8	295.4	292.8	289.1	287.5	287.0
52.5°	287.1	279.6	274.4	272.6	271.0	269.0	269.3
55°	252.3	248.1	246.0	244.4	241.8	238.6	240.7
57.5°	223.0	219.4	213.7	208.7	206.4	204.1	205.0
60°	202.4	195.0	187.7	181.9	180.3	175.5	175.5
62.5°	176.3	166.0	156.9	153.7	152.1	149.9	149.5
65°	135.6	131.4	129.3	127.2	126.1	126.1	125.1
67.5°	112.4	110.7	108.4	107.9	106.8	106.5	106.2
70°	99.3	97.2	96.2	95.7	94.6	95.1	93.6
72.5°	86.7	85.1	84.8	83.5	82.9	82.9	81.8
75°	68.4	68.4	67.8	67.3	66.2	65.7	66.2
77.5°	52.6	52.7	51.7	51.7	51.5	51.7	51.1
80°	42.1	42.5	42.1	41.5	41.0	41.5	41.0
82.5°	33.2	32.5	32.4	32.2	32.2	31.8	31.8
85°	18.9	19.4	18.9	18.4	18.4	18.4	18.9
87.5°	10.5	10.7	10.8	10.9	10.9	11.0	10.6
90°	16.9	17.7	18.2	18.5	18.9	19.3	19.6
92.5°	18.1	18.5	18.8	18.9	19.2	19.3	19.6
95°	30.7	31.4	31.8	31.6	31.4	31.3	31.1
97.5°	39.7	40.3	40.7	41.0	41.1	41.4	41.5
100°	45.1	46.4	47.2	47.5	47.8	48.2	48.5
102.5°	47.5	49.1	50.1	50.6	51.0	51.5	52.0
105°	49.4	51.2	52.4	53.1	53.7	54.3	55.0
107.5°	56.4	54.6	54.0	54.7	55.3	55.9	56.6
110°	78.3	62.3	54.6	55.2	55.8	56.5	57.2



TEST NUMBER: P331723-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	143.4	84.8	55.7	56.2	56.7	57.2	57.8
115°	223.1	148.6	105.6	94.0	82.5	70.9	59.3
117.5°	440.5	422.4	394.3	356.3	318.3	280.3	242.2
120°	536.1	538.1	528.1	506.4	484.7	463.0	441.3
122.5°	567.9	569.1	567.6	563.4	559.1	554.9	550.7
125°	614.7	615.8	616.6	617.1	617.6	618.1	618.6
127.5°	658.5	660.2	661.0	661.2	661.2	661.3	661.4
130°	686.1	687.9	688.7	688.6	688.3	688.2	688.0
132.5°	712.6	714.1	714.7	714.5	714.4	714.2	714.1
135°	750.8	752.3	753.0	752.7	752.3	752.0	751.7
137.5°	786.1	787.7	788.2	787.7	787.1	786.6	786.0
140°	808.9	810.3	810.6	809.8	809.1	808.3	807.4
142.5°	829.9	831.2	831.5	830.7	829.9	829.1	828.2
145°	859.3	860.4	860.5	859.8	859.0	858.2	857.4
147.5°	884.7	885.6	885.7	884.9	884.3	883.6	883.0
150°	900.8	901.7	901.8	901.0	900.2	899.4	898.6
152.5°	915.2	916.2	916.2	915.0	914.0	913.0	911.9
155°	934.8	935.7	935.6	934.3	933.0	931.7	930.4
157.5°	951.3	952.4	952.4	951.1	949.8	948.6	947.4
160°	960.8	961.8	961.7	960.5	959.4	958.3	957.2
162.5°	969.9	971.0	970.8	969.5	968.0	966.7	965.3
165°	980.8	981.9	981.9	980.8	979.7	978.6	977.5
167.5°	989.9	991.1	990.9	989.4	988.0	986.6	985.1
170°	994.6	995.7	995.5	994.1	992.6	991.2	989.8
172.5°	998.1	999.2	999.0	997.5	996.1	994.7	993.2
175°	1001.8	1002.9	1002.7	1001.1	999.5	997.8	996.2
177.5°	1002.0	1002.9	1002.7	1001.6	1000.4	999.3	998.1
180°	999.9	999.9	999.9	999.9	999.9	999.9	999.9

(END OF REPORT)