

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331725-927

Luminaire Tested: **SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331725-927
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 925 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5478.9 lumens
Efficiency: N/A
Efficacy: 90.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 60.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331725-927
CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	48				
1	98	94	90	87	90	87	84	81	73	71	69	60	59	58	49	48	47	42				
2	90	83	77	72	83	77	72	68	65	61	58	54	52	49	44	42	41	36				
3	83	74	67	61	76	68	62	57	58	54	50	49	45	43	40	38	36	32				
4	76	66	58	53	70	61	55	49	52	47	43	44	40	37	36	34	32	28				
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28	25				
6	65	53	46	40	60	50	43	38	43	38	34	36	32	29	30	27	25	22				
7	60	48	41	36	55	45	38	34	39	34	30	33	29	26	28	25	23	20				
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21	18				
9	52	41	33	29	48	38	32	27	33	28	24	28	24	22	24	21	19	17				
10	49	37	30	26	45	35	29	25	31	26	22	26	23	20	22	20	17	16				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	24425	24425	24425	24425
5°	27279	24577	21793	24577
10°	30263	24405	18889	24405
15°	31753	24047	14883	24047
20°	27527	23517	12880	23517
25°	18054	22792	11500	22792
30°	12152	21912	10407	21912
35°	9841	20802	9386	20802
40°	8753	19597	8686	19597
45°	7921	18182	7752	18182
50°	7209	16779	7181	16779
55°	6776	15226	6688	15226
60°	5667	13798	5603	13798
65°	4779	12531	5421	12531
70°	4419	11188	5113	11188
75°	4130	9738	4722	9738
80°	3812	8015	4203	8015
85°	3501	6317	3705	6317



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.4	2.6
10°-20°	399.6	7.3
20°-30°	514.9	9.4
30°-40°	489.3	8.9
40°-50°	419.2	7.7
50°-60°	319.2	5.8
60°-70°	201.8	3.7
70°-80°	100.8	1.8
80°-90°	29.9	0.5
90°-100°	164.4	3.0
100°-110°	557.8	10.2
110°-120°	592.6	10.8
120°-130°	487.8	8.9
130°-140°	391.8	7.2
140°-150°	296.0	5.4
150°-160°	208.1	3.8
160°-170°	122.5	2.2
170°-180°	39.9	0.7
0°-30°	1057.9	19.3
0°-40°	1547.2	28.2
0°-60°	2285.6	41.7
0°-90°	2618.0	47.8
90°-120°	1314.8	24.0
90°-150°	2490.5	45.5
90°-180°	2861.0	52.2
0°-180°	5478.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1513	1513	1513	1513	1513	
5°	1683	1516	1345	1516	1683	166
15°	1900	1439	890	1439	1900	512
25°	1013	1279	646	1279	1013	481
35°	499	1055	476	1055	499	319
45°	347	796	340	796	347	269
55°	241	541	238	541	241	211
65°	125	328	142	328	125	127
75°	66	156	76	156	66	70
85°	19	34	20	34	19	21
90°	26	1	26	1	26	15
95°	90	28	90	28	90	117
105°	891	96	891	96	891	862
115°	1172	170	1172	170	1172	1148
125°	951	237	951	237	951	859
135°	788	278	788	278	788	612
145°	629	318	629	318	629	400
155°	529	361	529	361	529	247
165°	464	394	464	394	464	133
175°	418	410	418	410	418	41
180°	411	411	411	411	411	



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1574.1	1575.4	1576.7	1573.7	1573.7	1571.2	1565.7	1561.5	1549.7	1548.1	1548.1
5°	1683.1	1682.0	1684.1	1677.3	1667.8	1665.7	1655.7	1642.6	1628.9	1613.7	1610.5
7.5°	1791.3	1789.7	1785.5	1784.4	1777.1	1761.3	1745.2	1728.1	1705.3	1683.1	1672.0
10°	1845.9	1863.3	1852.8	1834.4	1838.1	1813.4	1800.2	1777.7	1758.7	1725.6	1718.2
12.5°	1899.8	1906.6	1903.3	1892.8	1888.2	1871.0	1853.2	1833.6	1798.6	1768.9	1743.0
15°	1899.6	1909.6	1912.2	1909.1	1911.7	1910.7	1901.2	1884.8	1854.4	1821.8	1793.4
17.5°	1759.4	1766.3	1783.5	1795.2	1809.9	1841.0	1856.4	1862.3	1857.8	1839.2	1819.2
20°	1602.1	1590.5	1638.9	1663.6	1684.6	1737.2	1782.4	1799.8	1827.6	1827.1	1821.8
22.5°	1379.2	1382.0	1427.8	1457.1	1518.5	1571.1	1622.6	1687.9	1741.8	1777.4	1798.3
25°	1013.4	1033.4	1079.1	1119.0	1187.4	1285.2	1374.0	1477.0	1574.2	1651.0	1724.0
27.5°	761.1	762.6	798.8	835.8	876.3	956.4	1068.3	1191.3	1329.9	1444.3	1575.9
30°	651.8	648.6	663.8	686.4	721.1	783.2	867.3	988.2	1126.4	1298.8	1452.3
32.5°	574.4	574.6	586.1	602.8	631.6	673.4	731.0	829.3	959.9	1129.3	1309.3
35°	499.3	498.8	507.2	519.3	531.4	558.2	597.6	649.1	739.0	897.2	1081.2
37.5°	445.5	447.8	451.9	459.5	472.9	487.7	511.4	546.1	610.1	703.6	858.3
40°	415.3	416.3	422.1	428.4	436.3	447.8	467.3	495.1	541.9	616.6	729.5
42.5°	387.5	388.6	392.6	398.5	404.7	416.3	432.4	456.5	494.4	552.6	645.9
45°	346.9	346.9	350.6	353.2	360.0	370.6	383.7	403.7	429.9	473.1	535.1
47.5°	308.9	309.0	311.4	315.9	320.2	328.4	341.4	357.7	376.8	410.1	463.1
50°	287.0	287.5	289.1	292.8	295.4	302.8	312.8	326.9	346.9	372.6	416.8
52.5°	269.3	269.0	271.0	272.6	274.4	279.6	287.1	299.6	317.5	339.8	376.4
55°	240.7	238.6	241.8	244.4	246.0	248.1	252.3	260.2	275.4	294.4	321.7
57.5°	205.0	204.1	206.4	208.7	213.7	219.4	223.0	228.0	235.9	249.5	276.6
60°	175.5	175.5	180.3	181.9	187.7	195.0	202.4	206.6	214.4	223.4	243.4
62.5°	149.5	149.9	152.1	153.7	156.9	166.0	176.3	185.5	193.0	201.5	214.8
65°	125.1	126.1	126.1	127.2	129.3	131.4	135.6	143.0	156.1	168.2	178.2
67.5°	106.2	106.5	106.8	107.9	108.4	110.7	112.4	115.7	118.7	130.2	142.5
70°	93.6	95.1	94.6	95.7	96.2	97.2	99.3	100.9	105.7	108.3	115.7
72.5°	81.8	82.9	82.9	83.5	84.8	85.1	86.7	88.3	91.3	93.6	97.5
75°	66.2	65.7	66.2	67.3	67.8	68.4	68.4	70.4	72.0	74.1	76.8
77.5°	51.1	51.7	51.5	51.7	51.7	52.7	52.6	53.5	55.1	56.2	57.4
80°	41.0	41.5	41.0	41.5	42.1	42.5	42.1	42.5	44.1	45.2	45.2
82.5°	31.8	31.8	32.2	32.2	32.4	32.5	33.2	33.4	34.5	34.3	34.7
85°	18.9	18.4	18.4	18.4	18.9	19.4	18.9	18.9	19.4	19.4	19.4
87.5°	12.0	12.4	12.4	12.4	12.4	12.2	11.9	12.6	12.4	12.9	12.4
90°	26.1	26.1	26.1	26.1	26.1	25.3	23.7	25.3	26.1	26.9	26.1
92.5°	43.8	45.1	44.4	47.0	47.6	52.5	59.2	68.9	86.8	102.7	101.3
95°	90.2	89.4	91.7	98.1	108.3	125.7	158.9	207.2	271.2	309.9	274.3
97.5°	177.4	184.0	195.6	215.1	252.9	309.9	395.5	483.4	555.0	529.1	398.5
100°	283.0	297.3	320.2	354.2	419.9	515.5	623.8	721.8	738.5	624.6	430.1
102.5°	498.1	517.4	546.0	604.0	675.3	776.7	856.0	878.1	806.8	627.7	418.1
105°	891.0	902.1	936.1	985.1	1034.1	1060.3	1050.0	960.6	796.1	585.8	394.5
107.5°	1138.2	1152.9	1159.7	1162.4	1156.2	1117.9	1035.7	901.2	726.7	541.0	382.8
110°	1212.8	1213.6	1206.5	1191.4	1157.5	1092.7	991.4	849.9	683.1	519.4	380.3



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1211.6	1207.3	1193.8	1168.7	1121.4	1047.1	939.0	803.1	652.8	505.5	380.9
115°	1172.5	1165.4	1144.8	1108.4	1052.3	970.9	867.3	745.5	615.1	490.2	384.2
117.5°	1102.7	1096.8	1075.1	1036.6	979.5	903.0	809.1	702.2	591.4	482.8	389.9
120°	1057.9	1050.0	1027.0	989.8	934.5	862.5	778.8	680.7	578.8	478.3	393.7
122.5°	1011.1	1004.4	984.0	947.5	897.9	832.8	753.4	663.6	568.0	475.8	398.2
125°	951.1	944.8	925.0	895.0	849.1	789.8	720.3	638.8	552.6	471.2	404.8
127.5°	898.7	893.6	876.5	848.3	808.3	753.6	688.0	614.3	538.4	468.5	411.6
130°	868.9	862.5	846.8	819.9	781.2	729.0	666.5	598.5	528.9	467.2	416.7
132.5°	837.9	832.2	817.7	790.8	752.7	703.6	646.3	583.3	521.3	466.6	421.7
135°	788.2	785.1	770.9	744.7	710.7	666.5	614.3	562.1	510.7	465.6	427.7
137.5°	739.6	734.8	722.3	699.9	668.8	630.3	588.8	545.2	503.3	465.5	433.1
140°	706.0	701.3	689.4	668.8	643.6	608.8	572.4	534.5	498.9	464.9	435.6
142.5°	672.5	671.5	661.0	642.3	618.3	589.1	557.9	525.6	494.5	464.9	437.5
145°	629.3	626.9	619.1	605.6	586.6	563.7	539.2	513.1	488.6	463.3	439.6
147.5°	593.1	591.7	586.3	575.6	559.9	543.1	524.0	503.4	482.6	460.5	440.2
150°	571.6	570.8	566.1	556.6	544.7	530.5	513.9	496.5	477.5	458.6	439.6
152.5°	553.3	553.1	549.6	541.4	532.1	519.8	505.6	489.6	473.1	455.4	438.3
155°	528.9	530.5	527.4	521.8	513.1	504.4	492.6	479.9	464.9	449.9	436.4
157.5°	508.2	508.2	506.8	502.2	496.1	489.3	479.3	468.7	457.2	444.2	432.8
160°	495.0	495.0	494.2	490.2	484.7	479.1	470.4	461.7	451.5	440.4	430.9
162.5°	482.3	482.9	482.1	479.4	473.9	469.6	462.2	454.8	446.4	437.2	429.0
165°	464.1	464.9	464.9	461.7	458.6	455.4	449.9	444.3	438.0	430.9	425.3
167.5°	447.3	448.3	448.5	446.7	445.3	442.4	438.6	434.4	429.8	425.3	421.7
170°	437.2	438.8	439.6	437.2	436.4	434.8	431.7	429.3	425.3	422.2	419.9
172.5°	429.0	429.9	430.7	429.6	428.8	427.9	425.3	423.6	421.0	418.4	417.3
175°	418.3	419.9	420.6	419.9	419.9	419.1	418.3	417.5	415.1	414.3	413.5
177.5°	411.8	413.0	413.7	413.7	413.7	413.7	413.0	413.0	411.8	411.1	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1548.9	1545.5	1542.6	1535.0	1531.2	1522.8	1521.5	1521.1	1510.2	1499.7	1496.7
5°	1602.1	1593.7	1581.0	1566.4	1551.1	1535.3	1524.8	1516.4	1495.4	1475.4	1463.9
7.5°	1655.7	1637.6	1615.9	1588.0	1564.8	1538.7	1519.3	1502.0	1472.2	1443.6	1424.3
10°	1695.7	1666.2	1637.3	1598.9	1569.0	1539.5	1512.2	1488.6	1454.9	1417.1	1390.3
12.5°	1720.5	1688.1	1648.2	1610.7	1571.9	1534.5	1497.9	1467.5	1428.0	1388.9	1357.0
15°	1754.0	1719.3	1671.0	1617.3	1567.4	1518.5	1476.5	1438.6	1387.1	1340.3	1301.4
17.5°	1781.5	1733.7	1681.8	1619.8	1561.9	1499.8	1445.7	1397.3	1340.0	1283.6	1237.7
20°	1790.3	1743.0	1683.1	1621.0	1552.7	1479.6	1421.3	1368.7	1307.2	1245.7	1193.2
22.5°	1784.8	1748.0	1681.3	1607.1	1537.2	1460.7	1394.8	1333.8	1265.6	1202.8	1141.9
25°	1747.7	1735.0	1672.0	1591.0	1511.2	1422.4	1346.1	1279.4	1201.6	1134.3	1068.0
27.5°	1661.2	1688.4	1649.3	1563.1	1474.3	1379.0	1293.3	1217.3	1136.6	1060.9	994.9
30°	1577.9	1640.5	1623.7	1543.7	1444.4	1350.8	1254.7	1175.3	1089.1	1011.3	946.1
32.5°	1464.0	1567.3	1583.7	1516.9	1414.1	1311.3	1210.5	1131.6	1041.6	959.6	896.0
35°	1282.5	1437.0	1508.0	1465.5	1362.4	1251.5	1147.4	1055.4	965.0	884.1	821.0
37.5°	1066.0	1276.5	1394.8	1397.8	1303.2	1187.9	1074.6	983.3	890.7	811.3	743.0
40°	925.6	1153.7	1307.7	1341.9	1262.0	1137.4	1022.9	929.8	839.4	761.6	683.3
42.5°	799.5	1026.7	1216.1	1275.5	1212.0	1088.2	973.3	876.0	788.1	714.5	634.5
45°	646.5	845.2	1053.8	1160.1	1124.8	1010.3	888.8	796.3	713.8	650.2	573.5
47.5°	545.4	685.4	887.3	1030.9	1030.3	925.7	806.3	717.7	641.1	581.5	519.4
50°	487.7	609.7	780.5	943.5	957.1	869.3	755.8	668.0	596.6	534.0	484.1
52.5°	436.0	536.5	690.1	846.4	885.3	809.2	699.1	618.1	548.7	491.2	448.4
55°	368.4	446.2	562.9	709.1	767.9	714.3	616.6	540.9	484.7	436.3	399.5
57.5°	311.7	370.0	463.7	581.3	649.9	616.2	535.5	474.0	425.9	382.1	353.1
60°	275.9	323.8	403.1	501.5	577.1	553.5	484.7	427.3	386.3	348.5	321.2
62.5°	242.3	283.4	351.4	431.2	500.6	490.8	434.6	386.5	350.6	316.1	292.9
65°	195.0	225.0	278.1	340.6	396.3	401.1	360.6	328.0	296.0	268.6	248.1
67.5°	155.3	174.8	212.2	264.9	306.7	321.5	296.8	272.0	246.5	225.4	207.6
70°	130.9	146.6	174.0	216.6	254.9	270.7	256.5	237.0	215.0	197.6	182.4
72.5°	106.1	121.4	141.6	172.9	205.7	222.8	217.9	203.8	185.9	171.6	157.2
75°	79.9	84.6	98.3	119.3	145.0	159.8	163.5	156.1	141.9	130.9	122.5
77.5°	59.1	61.9	68.4	79.5	96.3	109.4	114.8	113.9	104.2	97.8	89.9
80°	47.3	48.9	52.0	56.8	69.4	82.5	86.2	86.2	79.4	76.8	68.8
82.5°	36.0	37.1	39.0	41.6	47.5	58.9	63.1	63.9	59.6	56.2	49.9
85°	20.5	20.0	21.0	22.6	23.7	26.8	33.1	34.1	33.1	28.9	27.3
87.5°	11.4	10.7	9.9	9.0	9.2	9.3	10.7	12.4	11.2	10.5	10.0
90°	21.3	15.8	11.9	9.5	7.9	6.3	3.2	0.8	3.2	6.3	7.9
92.5°	78.9	53.8	35.9	28.4	23.1	19.6	13.9	9.7	13.9	19.6	23.1
95°	182.6	113.8	77.5	58.5	45.9	38.7	30.8	27.6	30.8	38.7	45.9
97.5°	246.1	150.2	104.5	83.0	68.4	57.8	49.4	45.1	49.4	57.8	68.4
100°	259.4	162.9	121.0	98.9	83.0	70.3	63.2	60.8	63.2	70.3	83.0
102.5°	260.0	174.3	135.5	113.4	97.0	84.3	77.2	75.4	77.2	84.3	97.0
105°	264.0	193.7	156.5	134.4	117.0	105.1	99.7	96.5	99.7	105.1	117.0
107.5°	275.0	213.7	177.6	155.3	138.1	127.1	121.8	119.2	121.8	127.1	138.1
110°	283.8	226.9	192.1	169.2	152.6	142.3	137.6	134.4	137.6	142.3	152.6



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	293.3	239.6	206.0	182.4	166.5	156.9	151.5	148.3	151.5	156.9	166.5
115°	307.5	259.4	225.3	204.0	188.1	178.7	174.0	170.0	174.0	178.7	188.1
117.5°	322.7	277.5	246.1	223.9	208.7	200.3	195.6	192.4	195.6	200.3	208.7
120°	332.9	290.2	259.4	237.2	221.3	214.3	209.5	206.4	209.5	214.3	221.3
122.5°	341.7	302.1	273.2	250.5	234.6	226.9	222.1	219.7	222.1	226.9	234.6
125°	355.8	320.2	291.8	269.6	253.8	244.3	239.6	237.2	239.6	244.3	253.8
127.5°	368.9	337.0	309.3	286.5	271.3	260.9	254.3	251.1	254.3	260.9	271.3
130°	377.2	347.1	319.4	297.3	281.5	270.4	262.4	259.4	262.4	270.4	281.5
132.5°	385.3	355.9	329.5	307.4	291.0	279.2	270.7	266.9	270.7	279.2	291.0
135°	396.1	368.4	343.1	321.0	302.8	291.0	281.5	278.3	281.5	291.0	302.8
137.5°	404.3	378.6	353.6	333.0	315.0	302.3	292.9	289.1	292.9	302.3	315.0
140°	408.8	384.2	360.5	340.0	322.6	309.9	300.5	297.3	300.5	309.9	322.6
142.5°	412.6	388.6	365.6	346.3	329.5	316.9	308.0	305.5	308.0	316.9	329.5
145°	417.5	395.3	374.0	356.6	340.8	328.9	321.0	317.8	321.0	328.9	340.8
147.5°	420.2	400.7	380.6	365.1	352.0	341.0	333.5	331.1	333.5	341.0	352.0
150°	421.4	403.2	385.0	370.8	358.9	348.6	342.3	340.0	342.3	348.6	358.9
152.5°	422.0	405.8	389.4	376.5	365.3	356.2	349.9	348.8	349.9	356.2	365.3
155°	422.9	409.6	396.1	384.2	375.6	366.9	362.1	361.3	362.1	366.9	375.6
157.5°	422.9	412.3	400.8	390.9	383.9	376.4	372.6	371.8	372.6	376.4	383.9
160°	422.9	413.5	404.0	395.3	389.0	382.6	379.5	378.7	379.5	382.6	389.0
162.5°	422.3	414.2	405.9	399.1	393.4	388.3	385.2	385.6	385.2	388.3	393.4
165°	420.6	415.1	408.0	403.2	399.3	394.5	392.9	393.7	392.9	394.5	399.3
167.5°	419.5	414.9	409.7	406.7	403.9	400.8	399.4	400.4	399.4	400.8	403.9
170°	418.3	414.3	410.4	408.0	406.4	404.0	403.2	404.8	403.2	404.0	406.4
172.5°	416.4	413.7	411.0	409.2	408.3	405.9	406.4	407.3	406.4	405.9	408.3
175°	414.3	412.7	411.1	410.4	410.4	408.8	409.6	410.4	409.6	408.8	410.4
177.5°	413.0	411.8	411.1	411.1	411.1	409.9	410.5	411.8	410.5	409.9	411.1
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1491.3	1488.4	1482.9	1474.5	1469.4	1460.6	1454.7	1458.1	1458.9	1458.1	1457.2
5°	1451.2	1440.2	1425.0	1410.2	1396.5	1381.9	1373.4	1369.8	1362.4	1358.2	1356.1
7.5°	1402.8	1383.8	1362.2	1336.6	1314.8	1292.0	1280.3	1274.5	1259.5	1251.3	1244.1
10°	1366.6	1336.6	1315.1	1281.4	1261.0	1231.0	1210.5	1211.0	1190.5	1178.9	1170.5
12.5°	1326.7	1293.8	1257.9	1227.6	1199.1	1175.0	1150.4	1140.3	1118.6	1107.5	1084.7
15°	1260.4	1222.1	1184.2	1143.2	1114.3	1077.0	1041.2	997.6	962.4	931.9	923.5
17.5°	1188.1	1140.6	1102.6	1054.5	1005.0	942.2	900.8	875.4	854.2	838.1	826.2
20°	1138.5	1090.1	1049.6	977.2	910.4	867.8	837.3	817.8	795.8	778.5	769.0
22.5°	1086.3	1035.9	980.7	899.8	847.7	813.6	786.4	764.1	749.1	735.5	726.9
25°	1012.3	957.1	866.3	810.5	768.4	732.7	713.8	700.1	684.4	666.0	657.5
27.5°	934.1	846.4	781.1	739.7	699.5	676.3	659.3	638.8	624.7	616.5	607.7
30°	875.7	787.9	736.9	691.7	663.3	637.5	617.6	606.0	592.4	578.2	572.4
32.5°	810.5	740.4	691.5	653.9	625.0	603.1	587.3	568.6	558.7	550.0	537.9
35°	729.5	676.4	631.8	601.3	574.0	556.1	537.7	526.6	508.8	501.5	496.7
37.5°	661.0	615.0	581.6	549.5	527.8	508.0	496.8	479.3	471.5	461.3	451.3
40°	622.3	577.1	545.1	518.8	494.6	479.9	465.7	451.5	440.0	435.2	423.1
42.5°	582.8	546.1	514.0	485.1	469.0	453.4	435.5	425.0	413.0	405.4	397.9
45°	528.2	495.7	468.3	444.7	426.8	410.5	398.9	381.6	374.8	359.5	353.2
47.5°	480.3	450.0	424.0	401.5	384.0	373.4	356.5	342.9	332.0	322.7	314.5
50°	446.2	421.0	395.8	375.8	360.0	344.8	327.5	320.6	303.8	299.0	294.4
52.5°	415.1	391.2	368.0	348.5	332.7	317.9	302.6	293.7	282.3	277.7	274.2
55°	371.6	348.5	326.4	309.0	293.3	278.1	268.6	257.5	252.3	248.6	244.4
57.5°	327.9	307.0	290.2	272.6	256.7	244.6	233.7	227.0	221.6	216.7	211.8
60°	300.2	280.1	264.9	248.6	232.3	222.4	213.9	206.0	199.7	192.3	190.3
62.5°	270.7	253.3	239.2	223.4	209.2	200.0	192.0	184.6	177.1	166.3	163.3
65°	230.2	216.6	201.8	188.7	176.1	167.2	155.6	147.2	144.0	143.0	142.4
67.5°	193.6	180.7	168.1	154.6	143.1	134.9	129.0	127.7	125.5	124.8	123.4
70°	169.2	157.2	144.6	131.9	120.9	119.3	117.2	115.1	112.5	111.5	110.4
72.5°	147.3	134.9	122.2	112.2	107.4	105.4	103.3	101.2	99.4	98.4	97.8
75°	113.0	101.5	93.0	89.4	86.7	85.2	82.0	80.4	79.4	77.8	77.2
77.5°	81.4	74.9	71.0	68.7	65.9	64.2	62.4	60.8	59.7	59.4	58.5
80°	62.0	58.9	56.2	53.1	52.0	49.9	49.4	47.8	48.3	46.8	46.8
82.5°	48.2	44.1	41.9	40.5	39.5	37.7	37.2	36.4	36.6	35.4	35.4
85°	24.7	23.7	22.6	21.5	21.5	20.0	20.5	20.0	20.0	18.9	18.4
87.5°	9.9	9.9	9.9	11.0	12.0	11.6	11.5	10.9	10.6	10.9	10.7
90°	9.5	11.9	15.8	21.3	26.1	26.9	26.1	25.3	23.7	25.3	26.1
92.5°	28.4	35.9	53.8	78.9	101.3	102.7	86.8	68.9	59.2	52.5	47.6
95°	58.5	77.5	113.8	182.6	274.3	309.9	271.2	207.2	158.9	125.7	108.3
97.5°	83.0	104.5	150.2	246.1	398.5	529.1	555.0	483.4	395.5	309.9	252.9
100°	98.9	121.0	162.9	259.4	430.1	624.6	738.5	721.8	623.8	515.5	419.9
102.5°	113.4	135.5	174.3	260.0	418.1	627.7	806.8	878.1	856.0	776.7	675.3
105°	134.4	156.5	193.7	264.0	394.5	585.8	796.1	960.6	1050.0	1060.3	1034.1
107.5°	155.3	177.6	213.7	275.0	382.8	541.0	726.7	901.2	1035.7	1117.9	1156.2
110°	169.2	192.1	226.9	283.8	380.3	519.4	683.1	849.9	991.4	1092.7	1157.5



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	182.4	206.0	239.6	293.3	380.9	505.5	652.8	803.1	939.0	1047.1	1121.4
115°	204.0	225.3	259.4	307.5	384.2	490.2	615.1	745.5	867.3	970.9	1052.3
117.5°	223.9	246.1	277.5	322.7	389.9	482.8	591.4	702.2	809.1	903.0	979.5
120°	237.2	259.4	290.2	332.9	393.7	478.3	578.8	680.7	778.8	862.5	934.5
122.5°	250.5	273.2	302.1	341.7	398.2	475.8	568.0	663.6	753.4	832.8	897.9
125°	269.6	291.8	320.2	355.8	404.8	471.2	552.6	638.8	720.3	789.8	849.1
127.5°	286.5	309.3	337.0	368.9	411.6	468.5	538.4	614.3	688.0	753.6	808.3
130°	297.3	319.4	347.1	377.2	416.7	467.2	528.9	598.5	666.5	729.0	781.2
132.5°	307.4	329.5	355.9	385.3	421.7	466.6	521.3	583.3	646.3	703.6	752.7
135°	321.0	343.1	368.4	396.1	427.7	465.6	510.7	562.1	614.3	666.5	710.7
137.5°	333.0	353.6	378.6	404.3	433.1	465.5	503.3	545.2	588.8	630.3	668.8
140°	340.0	360.5	384.2	408.8	435.6	464.9	498.9	534.5	572.4	608.8	643.6
142.5°	346.3	365.6	388.6	412.6	437.5	464.9	494.5	525.6	557.9	589.1	618.3
145°	356.6	374.0	395.3	417.5	439.6	463.3	488.6	513.1	539.2	563.7	586.6
147.5°	365.1	380.6	400.7	420.2	440.2	460.5	482.6	503.4	524.0	543.1	559.9
150°	370.8	385.0	403.2	421.4	439.6	458.6	477.5	496.5	513.9	530.5	544.7
152.5°	376.5	389.4	405.8	422.0	438.3	455.4	473.1	489.6	505.6	519.8	532.1
155°	384.2	396.1	409.6	422.9	436.4	449.9	464.9	479.9	492.6	504.4	513.1
157.5°	390.9	400.8	412.3	422.9	432.8	444.2	457.2	468.7	479.3	489.3	496.1
160°	395.3	404.0	413.5	422.9	430.9	440.4	451.5	461.7	470.4	479.1	484.7
162.5°	399.1	405.9	414.2	422.3	429.0	437.2	446.4	454.8	462.2	469.6	473.9
165°	403.2	408.0	415.1	420.6	425.3	430.9	438.0	444.3	449.9	455.4	458.6
167.5°	406.7	409.7	414.9	419.5	421.7	425.3	429.8	434.4	438.6	442.4	445.3
170°	408.0	410.4	414.3	418.3	419.9	422.2	425.3	429.3	431.7	434.8	436.4
172.5°	409.2	411.0	413.7	416.4	417.3	418.4	421.0	423.6	425.3	427.9	428.8
175°	410.4	411.1	412.7	414.3	413.5	414.3	415.1	417.5	418.3	419.1	419.9
177.5°	411.1	411.1	411.8	413.0	411.8	411.1	411.8	413.0	413.0	413.7	413.7
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1452.6	1453.4	1452.1	1453.0	1452.1	1453.4	1452.6	1457.2	1458.1	1458.9	1458.1
5°	1353.4	1347.2	1346.1	1344.6	1346.1	1347.2	1353.4	1356.1	1358.2	1362.4	1369.8
7.5°	1235.1	1234.1	1231.5	1227.9	1231.5	1234.1	1235.1	1244.1	1251.3	1259.5	1274.5
10°	1159.0	1156.3	1155.9	1152.1	1155.9	1156.3	1159.0	1170.5	1178.9	1190.5	1211.0
12.5°	1069.8	1052.9	1051.1	1042.0	1051.1	1052.9	1069.8	1084.7	1107.5	1118.6	1140.3
15°	910.9	907.8	897.2	890.4	897.2	907.8	910.9	923.5	931.9	962.4	997.6
17.5°	820.1	809.8	806.5	805.0	806.5	809.8	820.1	826.2	838.1	854.2	875.4
20°	761.6	752.2	750.6	749.6	750.6	752.2	761.6	769.0	778.5	795.8	817.8
22.5°	721.3	711.4	707.3	704.1	707.3	711.4	721.3	726.9	735.5	749.1	764.1
25°	652.3	648.6	646.5	645.5	646.5	648.6	652.3	657.5	666.0	684.4	700.1
27.5°	598.3	590.3	588.7	586.0	588.7	590.3	598.3	607.7	616.5	624.7	638.8
30°	567.7	565.1	561.3	558.2	561.3	565.1	567.7	572.4	578.2	592.4	606.0
32.5°	531.5	529.3	526.0	524.6	526.0	529.3	531.5	537.9	550.0	558.7	568.6
35°	491.5	484.1	480.9	476.2	480.9	484.1	491.5	496.7	501.5	508.8	526.6
37.5°	449.1	445.2	440.8	442.4	440.8	445.2	449.1	451.3	461.3	471.5	479.3
40°	416.3	413.7	412.6	412.1	412.6	413.7	416.3	423.1	435.2	440.0	451.5
42.5°	390.2	382.9	380.2	380.1	380.2	382.9	390.2	397.9	405.4	413.0	425.0
45°	350.6	343.7	339.1	339.5	339.1	343.7	350.6	353.2	359.5	374.8	381.6
47.5°	310.0	309.8	306.9	307.8	306.9	309.8	310.0	314.5	322.7	332.0	342.9
50°	290.7	287.5	285.4	285.9	285.4	287.5	290.7	294.4	299.0	303.8	320.6
52.5°	272.2	269.4	267.8	270.0	267.8	269.4	272.2	274.2	277.7	282.3	293.7
55°	241.8	238.6	238.1	237.6	238.1	238.6	241.8	244.4	248.6	252.3	257.5
57.5°	207.9	205.7	202.6	201.2	202.6	205.7	207.9	211.8	216.7	221.6	227.0
60°	183.5	179.3	174.0	173.5	174.0	179.3	183.5	190.3	192.3	199.7	206.0
62.5°	161.1	160.3	159.2	159.1	159.2	160.3	161.1	163.3	166.3	177.1	184.6
65°	141.4	140.9	141.4	141.9	141.4	140.9	141.4	142.4	143.0	144.0	147.2
67.5°	123.2	122.2	121.3	121.8	121.3	122.2	123.2	123.4	124.8	125.5	127.7
70°	109.3	108.8	108.3	108.3	108.3	108.8	109.3	110.4	111.5	112.5	115.1
72.5°	95.9	95.8	95.2	94.8	95.2	95.8	95.9	97.8	98.4	99.4	101.2
75°	76.8	75.7	75.7	75.7	75.7	75.7	76.8	77.2	77.8	79.4	80.4
77.5°	58.5	57.9	57.4	57.0	57.4	57.9	58.5	58.5	59.4	59.7	60.8
80°	46.3	45.7	45.2	45.2	45.2	45.7	46.3	46.8	46.8	48.3	47.8
82.5°	35.3	34.8	34.7	34.3	34.7	34.8	35.3	35.4	35.4	36.6	36.4
85°	18.9	19.4	18.9	20.0	18.9	19.4	18.9	18.4	18.9	20.0	20.0
87.5°	10.7	10.3	10.7	10.3	10.7	10.3	10.7	10.7	10.9	10.6	10.9
90°	26.1	26.1	26.1	26.1	26.1	26.1	26.1	26.1	25.3	23.7	25.3
92.5°	47.0	44.4	45.1	43.8	45.1	44.4	47.0	47.6	52.5	59.2	68.9
95°	98.1	91.7	89.4	90.2	89.4	91.7	98.1	108.3	125.7	158.9	207.2
97.5°	215.1	195.6	184.0	177.4	184.0	195.6	215.1	252.9	309.9	395.5	483.4
100°	354.2	320.2	297.3	283.0	297.3	320.2	354.2	419.9	515.5	623.8	721.8
102.5°	604.0	546.0	517.4	498.1	517.4	546.0	604.0	675.3	776.7	856.0	878.1
105°	985.1	936.1	902.1	891.0	902.1	936.1	985.1	1034.1	1060.3	1050.0	960.6
107.5°	1162.4	1159.7	1152.9	1138.2	1152.9	1159.7	1162.4	1156.2	1117.9	1035.7	901.2
110°	1191.4	1206.5	1213.6	1212.8	1213.6	1206.5	1191.4	1157.5	1092.7	991.4	849.9



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1168.7	1193.8	1207.3	1211.6	1207.3	1193.8	1168.7	1121.4	1047.1	939.0	803.1
115°	1108.4	1144.8	1165.4	1172.5	1165.4	1144.8	1108.4	1052.3	970.9	867.3	745.5
117.5°	1036.6	1075.1	1096.8	1102.7	1096.8	1075.1	1036.6	979.5	903.0	809.1	702.2
120°	989.8	1027.0	1050.0	1057.9	1050.0	1027.0	989.8	934.5	862.5	778.8	680.7
122.5°	947.5	984.0	1004.4	1011.1	1004.4	984.0	947.5	897.9	832.8	753.4	663.6
125°	895.0	925.0	944.8	951.1	944.8	925.0	895.0	849.1	789.8	720.3	638.8
127.5°	848.3	876.5	893.6	898.7	893.6	876.5	848.3	808.3	753.6	688.0	614.3
130°	819.9	846.8	862.5	868.9	862.5	846.8	819.9	781.2	729.0	666.5	598.5
132.5°	790.8	817.7	832.2	837.9	832.2	817.7	790.8	752.7	703.6	646.3	583.3
135°	744.7	770.9	785.1	788.2	785.1	770.9	744.7	710.7	666.5	614.3	562.1
137.5°	699.9	722.3	734.8	739.6	734.8	722.3	699.9	668.8	630.3	588.8	545.2
140°	668.8	689.4	701.3	706.0	701.3	689.4	668.8	643.6	608.8	572.4	534.5
142.5°	642.3	661.0	671.5	672.5	671.5	661.0	642.3	618.3	589.1	557.9	525.6
145°	605.6	619.1	626.9	629.3	626.9	619.1	605.6	586.6	563.7	539.2	513.1
147.5°	575.6	586.3	591.7	593.1	591.7	586.3	575.6	559.9	543.1	524.0	503.4
150°	556.6	566.1	570.8	571.6	570.8	566.1	556.6	544.7	530.5	513.9	496.5
152.5°	541.4	549.6	553.1	553.3	553.1	549.6	541.4	532.1	519.8	505.6	489.6
155°	521.8	527.4	530.5	528.9	530.5	527.4	521.8	513.1	504.4	492.6	479.9
157.5°	502.2	506.8	508.2	508.2	508.2	506.8	502.2	496.1	489.3	479.3	468.7
160°	490.2	494.2	495.0	495.0	495.0	494.2	490.2	484.7	479.1	470.4	461.7
162.5°	479.4	482.1	482.9	482.3	482.9	482.1	479.4	473.9	469.6	462.2	454.8
165°	461.7	464.9	464.9	464.1	464.9	464.9	461.7	458.6	455.4	449.9	444.3
167.5°	446.7	448.5	448.3	447.3	448.3	448.5	446.7	445.3	442.4	438.6	434.4
170°	437.2	439.6	438.8	437.2	438.8	439.6	437.2	436.4	434.8	431.7	429.3
172.5°	429.6	430.7	429.9	429.0	429.9	430.7	429.6	428.8	427.9	425.3	423.6
175°	419.9	420.6	419.9	418.3	419.9	420.6	419.9	419.9	419.1	418.3	417.5
177.5°	413.7	413.7	413.0	411.8	413.0	413.7	413.7	413.7	413.7	413.0	413.0
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1454.7	1460.6	1469.4	1474.5	1482.9	1488.4	1491.3	1496.7	1499.7	1510.2	1521.1
5°	1373.4	1381.9	1396.5	1410.2	1425.0	1440.2	1451.2	1463.9	1475.4	1495.4	1516.4
7.5°	1280.3	1292.0	1314.8	1336.6	1362.2	1383.8	1402.8	1424.3	1443.6	1472.2	1502.0
10°	1210.5	1231.0	1261.0	1281.4	1315.1	1336.6	1366.6	1390.3	1417.1	1454.9	1488.6
12.5°	1150.4	1175.0	1199.1	1227.6	1257.9	1293.8	1326.7	1357.0	1388.9	1428.0	1467.5
15°	1041.2	1077.0	1114.3	1143.2	1184.2	1222.1	1260.4	1301.4	1340.3	1387.1	1438.6
17.5°	900.8	942.2	1005.0	1054.5	1102.6	1140.6	1188.1	1237.7	1283.6	1340.0	1397.3
20°	837.3	867.8	910.4	977.2	1049.6	1090.1	1138.5	1193.2	1245.7	1307.2	1368.7
22.5°	786.4	813.6	847.7	899.8	980.7	1035.9	1086.3	1141.9	1202.8	1265.6	1333.8
25°	713.8	732.7	768.4	810.5	866.3	957.1	1012.3	1068.0	1134.3	1201.6	1279.4
27.5°	659.3	676.3	699.5	739.7	781.1	846.4	934.1	994.9	1060.9	1136.6	1217.3
30°	617.6	637.5	663.3	691.7	736.9	787.9	875.7	946.1	1011.3	1089.1	1175.3
32.5°	587.3	603.1	625.0	653.9	691.5	740.4	810.5	896.0	959.6	1041.6	1131.6
35°	537.7	556.1	574.0	601.3	631.8	676.4	729.5	821.0	884.1	965.0	1055.4
37.5°	496.8	508.0	527.8	549.5	581.6	615.0	661.0	743.0	811.3	890.7	983.3
40°	465.7	479.9	494.6	518.8	545.1	577.1	622.3	683.3	761.6	839.4	929.8
42.5°	435.5	453.4	469.0	485.1	514.0	546.1	582.8	634.5	714.5	788.1	876.0
45°	398.9	410.5	426.8	444.7	468.3	495.7	528.2	573.5	650.2	713.8	796.3
47.5°	356.5	373.4	384.0	401.5	424.0	450.0	480.3	519.4	581.5	641.1	717.7
50°	327.5	344.8	360.0	375.8	395.8	421.0	446.2	484.1	534.0	596.6	668.0
52.5°	302.6	317.9	332.7	348.5	368.0	391.2	415.1	448.4	491.2	548.7	618.1
55°	268.6	278.1	293.3	309.0	326.4	348.5	371.6	399.5	436.3	484.7	540.9
57.5°	233.7	244.6	256.7	272.6	290.2	307.0	327.9	353.1	382.1	425.9	474.0
60°	213.9	222.4	232.3	248.6	264.9	280.1	300.2	321.2	348.5	386.3	427.3
62.5°	192.0	200.0	209.2	223.4	239.2	253.3	270.7	292.9	316.1	350.6	386.5
65°	155.6	167.2	176.1	188.7	201.8	216.6	230.2	248.1	268.6	296.0	328.0
67.5°	129.0	134.9	143.1	154.6	168.1	180.7	193.6	207.6	225.4	246.5	272.0
70°	117.2	119.3	120.9	131.9	144.6	157.2	169.2	182.4	197.6	215.0	237.0
72.5°	103.3	105.4	107.4	112.2	122.2	134.9	147.3	157.2	171.6	185.9	203.8
75°	82.0	85.2	86.7	89.4	93.0	101.5	113.0	122.5	130.9	141.9	156.1
77.5°	62.4	64.2	65.9	68.7	71.0	74.9	81.4	89.9	97.8	104.2	113.9
80°	49.4	49.9	52.0	53.1	56.2	58.9	62.0	68.8	76.8	79.4	86.2
82.5°	37.2	37.7	39.5	40.5	41.9	44.1	48.2	49.9	56.2	59.6	63.9
85°	20.5	20.0	21.5	21.5	22.6	23.7	24.7	27.3	28.9	33.1	34.1
87.5°	11.5	11.6	12.0	11.0	9.9	9.9	9.9	10.0	10.5	11.2	12.4
90°	26.1	26.9	26.1	21.3	15.8	11.9	9.5	7.9	6.3	3.2	0.8
92.5°	86.8	102.7	101.3	78.9	53.8	35.9	28.4	23.1	19.6	13.9	9.7
95°	271.2	309.9	274.3	182.6	113.8	77.5	58.5	45.9	38.7	30.8	27.6
97.5°	555.0	529.1	398.5	246.1	150.2	104.5	83.0	68.4	57.8	49.4	45.1
100°	738.5	624.6	430.1	259.4	162.9	121.0	98.9	83.0	70.3	63.2	60.8
102.5°	806.8	627.7	418.1	260.0	174.3	135.5	113.4	97.0	84.3	77.2	75.4
105°	796.1	585.8	394.5	264.0	193.7	156.5	134.4	117.0	105.1	99.7	96.5
107.5°	726.7	541.0	382.8	275.0	213.7	177.6	155.3	138.1	127.1	121.8	119.2
110°	683.1	519.4	380.3	283.8	226.9	192.1	169.2	152.6	142.3	137.6	134.4



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	652.8	505.5	380.9	293.3	239.6	206.0	182.4	166.5	156.9	151.5	148.3
115°	615.1	490.2	384.2	307.5	259.4	225.3	204.0	188.1	178.7	174.0	170.0
117.5°	591.4	482.8	389.9	322.7	277.5	246.1	223.9	208.7	200.3	195.6	192.4
120°	578.8	478.3	393.7	332.9	290.2	259.4	237.2	221.3	214.3	209.5	206.4
122.5°	568.0	475.8	398.2	341.7	302.1	273.2	250.5	234.6	226.9	222.1	219.7
125°	552.6	471.2	404.8	355.8	320.2	291.8	269.6	253.8	244.3	239.6	237.2
127.5°	538.4	468.5	411.6	368.9	337.0	309.3	286.5	271.3	260.9	254.3	251.1
130°	528.9	467.2	416.7	377.2	347.1	319.4	297.3	281.5	270.4	262.4	259.4
132.5°	521.3	466.6	421.7	385.3	355.9	329.5	307.4	291.0	279.2	270.7	266.9
135°	510.7	465.6	427.7	396.1	368.4	343.1	321.0	302.8	291.0	281.5	278.3
137.5°	503.3	465.5	433.1	404.3	378.6	353.6	333.0	315.0	302.3	292.9	289.1
140°	498.9	464.9	435.6	408.8	384.2	360.5	340.0	322.6	309.9	300.5	297.3
142.5°	494.5	464.9	437.5	412.6	388.6	365.6	346.3	329.5	316.9	308.0	305.5
145°	488.6	463.3	439.6	417.5	395.3	374.0	356.6	340.8	328.9	321.0	317.8
147.5°	482.6	460.5	440.2	420.2	400.7	380.6	365.1	352.0	341.0	333.5	331.1
150°	477.5	458.6	439.6	421.4	403.2	385.0	370.8	358.9	348.6	342.3	340.0
152.5°	473.1	455.4	438.3	422.0	405.8	389.4	376.5	365.3	356.2	349.9	348.8
155°	464.9	449.9	436.4	422.9	409.6	396.1	384.2	375.6	366.9	362.1	361.3
157.5°	457.2	444.2	432.8	422.9	412.3	400.8	390.9	383.9	376.4	372.6	371.8
160°	451.5	440.4	430.9	422.9	413.5	404.0	395.3	389.0	382.6	379.5	378.7
162.5°	446.4	437.2	429.0	422.3	414.2	405.9	399.1	393.4	388.3	385.2	385.6
165°	438.0	430.9	425.3	420.6	415.1	408.0	403.2	399.3	394.5	392.9	393.7
167.5°	429.8	425.3	421.7	419.5	414.9	409.7	406.7	403.9	400.8	399.4	400.4
170°	425.3	422.2	419.9	418.3	414.3	410.4	408.0	406.4	404.0	403.2	404.8
172.5°	421.0	418.4	417.3	416.4	413.7	411.0	409.2	408.3	405.9	406.4	407.3
175°	415.1	414.3	413.5	414.3	412.7	411.1	410.4	410.4	408.8	409.6	410.4
177.5°	411.8	411.1	411.8	413.0	411.8	411.1	411.1	411.1	409.9	410.5	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1521.5	1522.8	1531.2	1535.0	1542.6	1545.5	1548.9	1548.1	1548.1	1549.7	1561.5
5°	1524.8	1535.3	1551.1	1566.4	1581.0	1593.7	1602.1	1610.5	1613.7	1628.9	1642.6
7.5°	1519.3	1538.7	1564.8	1588.0	1615.9	1637.6	1655.7	1672.0	1683.1	1705.3	1728.1
10°	1512.2	1539.5	1569.0	1598.9	1637.3	1666.2	1695.7	1718.2	1725.6	1758.7	1777.7
12.5°	1497.9	1534.5	1571.9	1610.7	1648.2	1688.1	1720.5	1743.0	1768.9	1798.6	1833.6
15°	1476.5	1518.5	1567.4	1617.3	1671.0	1719.3	1754.0	1793.4	1821.8	1854.4	1884.8
17.5°	1445.7	1499.8	1561.9	1619.8	1681.8	1733.7	1781.5	1819.2	1839.2	1857.8	1862.3
20°	1421.3	1479.6	1552.7	1621.0	1683.1	1743.0	1790.3	1821.8	1827.1	1827.6	1799.8
22.5°	1394.8	1460.7	1537.2	1607.1	1681.3	1748.0	1784.8	1798.3	1777.4	1741.8	1687.9
25°	1346.1	1422.4	1511.2	1591.0	1672.0	1735.0	1747.7	1724.0	1651.0	1574.2	1477.0
27.5°	1293.3	1379.0	1474.3	1563.1	1649.3	1688.4	1661.2	1575.9	1444.3	1329.9	1191.3
30°	1254.7	1350.8	1444.4	1543.7	1623.7	1640.5	1577.9	1452.3	1298.8	1126.4	988.2
32.5°	1210.5	1311.3	1414.1	1516.9	1583.7	1567.3	1464.0	1309.3	1129.3	959.9	829.3
35°	1147.4	1251.5	1362.4	1465.5	1508.0	1437.0	1282.5	1081.2	897.2	739.0	649.1
37.5°	1074.6	1187.9	1303.2	1397.8	1394.8	1276.5	1066.0	858.3	703.6	610.1	546.1
40°	1022.9	1137.4	1262.0	1341.9	1307.7	1153.7	925.6	729.5	616.6	541.9	495.1
42.5°	973.3	1088.2	1212.0	1275.5	1216.1	1026.7	799.5	645.9	552.6	494.4	456.5
45°	888.8	1010.3	1124.8	1160.1	1053.8	845.2	646.5	535.1	473.1	429.9	403.7
47.5°	806.3	925.7	1030.3	1030.9	887.3	685.4	545.4	463.1	410.1	376.8	357.7
50°	755.8	869.3	957.1	943.5	780.5	609.7	487.7	416.8	372.6	346.9	326.9
52.5°	699.1	809.2	885.3	846.4	690.1	536.5	436.0	376.4	339.8	317.5	299.6
55°	616.6	714.3	767.9	709.1	562.9	446.2	368.4	321.7	294.4	275.4	260.2
57.5°	535.5	616.2	649.9	581.3	463.7	370.0	311.7	276.6	249.5	235.9	228.0
60°	484.7	553.5	577.1	501.5	403.1	323.8	275.9	243.4	223.4	214.4	206.6
62.5°	434.6	490.8	500.6	431.2	351.4	283.4	242.3	214.8	201.5	193.0	185.5
65°	360.6	401.1	396.3	340.6	278.1	225.0	195.0	178.2	168.2	156.1	143.0
67.5°	296.8	321.5	306.7	264.9	212.2	174.8	155.3	142.5	130.2	118.7	115.7
70°	256.5	270.7	254.9	216.6	174.0	146.6	130.9	115.7	108.3	105.7	100.9
72.5°	217.9	222.8	205.7	172.9	141.6	121.4	106.1	97.5	93.6	91.3	88.3
75°	163.5	159.8	145.0	119.3	98.3	84.6	79.9	76.8	74.1	72.0	70.4
77.5°	114.8	109.4	96.3	79.5	68.4	61.9	59.1	57.4	56.2	55.1	53.5
80°	86.2	82.5	69.4	56.8	52.0	48.9	47.3	45.2	45.2	44.1	42.5
82.5°	63.1	58.9	47.5	41.6	39.0	37.1	36.0	34.7	34.3	34.5	33.4
85°	33.1	26.8	23.7	22.6	21.0	20.0	20.5	19.4	19.4	19.4	18.9
87.5°	10.7	9.3	9.2	9.0	9.9	10.7	11.4	12.4	12.9	12.4	12.6
90°	3.2	6.3	7.9	9.5	11.9	15.8	21.3	26.1	26.9	26.1	25.3
92.5°	13.9	19.6	23.1	28.4	35.9	53.8	78.9	101.3	102.7	86.8	68.9
95°	30.8	38.7	45.9	58.5	77.5	113.8	182.6	274.3	309.9	271.2	207.2
97.5°	49.4	57.8	68.4	83.0	104.5	150.2	246.1	398.5	529.1	555.0	483.4
100°	63.2	70.3	83.0	98.9	121.0	162.9	259.4	430.1	624.6	738.5	721.8
102.5°	77.2	84.3	97.0	113.4	135.5	174.3	260.0	418.1	627.7	806.8	878.1
105°	99.7	105.1	117.0	134.4	156.5	193.7	264.0	394.5	585.8	796.1	960.6
107.5°	121.8	127.1	138.1	155.3	177.6	213.7	275.0	382.8	541.0	726.7	901.2
110°	137.6	142.3	152.6	169.2	192.1	226.9	283.8	380.3	519.4	683.1	849.9



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	151.5	156.9	166.5	182.4	206.0	239.6	293.3	380.9	505.5	652.8	803.1
115°	174.0	178.7	188.1	204.0	225.3	259.4	307.5	384.2	490.2	615.1	745.5
117.5°	195.6	200.3	208.7	223.9	246.1	277.5	322.7	389.9	482.8	591.4	702.2
120°	209.5	214.3	221.3	237.2	259.4	290.2	332.9	393.7	478.3	578.8	680.7
122.5°	222.1	226.9	234.6	250.5	273.2	302.1	341.7	398.2	475.8	568.0	663.6
125°	239.6	244.3	253.8	269.6	291.8	320.2	355.8	404.8	471.2	552.6	638.8
127.5°	254.3	260.9	271.3	286.5	309.3	337.0	368.9	411.6	468.5	538.4	614.3
130°	262.4	270.4	281.5	297.3	319.4	347.1	377.2	416.7	467.2	528.9	598.5
132.5°	270.7	279.2	291.0	307.4	329.5	355.9	385.3	421.7	466.6	521.3	583.3
135°	281.5	291.0	302.8	321.0	343.1	368.4	396.1	427.7	465.6	510.7	562.1
137.5°	292.9	302.3	315.0	333.0	353.6	378.6	404.3	433.1	465.5	503.3	545.2
140°	300.5	309.9	322.6	340.0	360.5	384.2	408.8	435.6	464.9	498.9	534.5
142.5°	308.0	316.9	329.5	346.3	365.6	388.6	412.6	437.5	464.9	494.5	525.6
145°	321.0	328.9	340.8	356.6	374.0	395.3	417.5	439.6	463.3	488.6	513.1
147.5°	333.5	341.0	352.0	365.1	380.6	400.7	420.2	440.2	460.5	482.6	503.4
150°	342.3	348.6	358.9	370.8	385.0	403.2	421.4	439.6	458.6	477.5	496.5
152.5°	349.9	356.2	365.3	376.5	389.4	405.8	422.0	438.3	455.4	473.1	489.6
155°	362.1	366.9	375.6	384.2	396.1	409.6	422.9	436.4	449.9	464.9	479.9
157.5°	372.6	376.4	383.9	390.9	400.8	412.3	422.9	432.8	444.2	457.2	468.7
160°	379.5	382.6	389.0	395.3	404.0	413.5	422.9	430.9	440.4	451.5	461.7
162.5°	385.2	388.3	393.4	399.1	405.9	414.2	422.3	429.0	437.2	446.4	454.8
165°	392.9	394.5	399.3	403.2	408.0	415.1	420.6	425.3	430.9	438.0	444.3
167.5°	399.4	400.8	403.9	406.7	409.7	414.9	419.5	421.7	425.3	429.8	434.4
170°	403.2	404.0	406.4	408.0	410.4	414.3	418.3	419.9	422.2	425.3	429.3
172.5°	406.4	405.9	408.3	409.2	411.0	413.7	416.4	417.3	418.4	421.0	423.6
175°	409.6	408.8	410.4	410.4	411.1	412.7	414.3	413.5	414.3	415.1	417.5
177.5°	410.5	409.9	411.1	411.1	411.1	411.8	413.0	411.8	411.1	411.8	413.0
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1	411.1



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8	1512.8
2.5°	1565.7	1571.2	1573.7	1573.7	1576.7	1575.4	1574.1
5°	1655.7	1665.7	1667.8	1677.3	1684.1	1682.0	1683.1
7.5°	1745.2	1761.3	1777.1	1784.4	1785.5	1789.7	1791.3
10°	1800.2	1813.4	1838.1	1834.4	1852.8	1863.3	1845.9
12.5°	1853.2	1871.0	1888.2	1892.8	1903.3	1906.6	1899.8
15°	1901.2	1910.7	1911.7	1909.1	1912.2	1909.6	1899.6
17.5°	1856.4	1841.0	1809.9	1795.2	1783.5	1766.3	1759.4
20°	1782.4	1737.2	1684.6	1663.6	1638.9	1590.5	1602.1
22.5°	1622.6	1571.1	1518.5	1457.1	1427.8	1382.0	1379.2
25°	1374.0	1285.2	1187.4	1119.0	1079.1	1033.4	1013.4
27.5°	1068.3	956.4	876.3	835.8	798.8	762.6	761.1
30°	867.3	783.2	721.1	686.4	663.8	648.6	651.8
32.5°	731.0	673.4	631.6	602.8	586.1	574.6	574.4
35°	597.6	558.2	531.4	519.3	507.2	498.8	499.3
37.5°	511.4	487.7	472.9	459.5	451.9	447.8	445.5
40°	467.3	447.8	436.3	428.4	422.1	416.3	415.3
42.5°	432.4	416.3	404.7	398.5	392.6	388.6	387.5
45°	383.7	370.6	360.0	353.2	350.6	346.9	346.9
47.5°	341.4	328.4	320.2	315.9	311.4	309.0	308.9
50°	312.8	302.8	295.4	292.8	289.1	287.5	287.0
52.5°	287.1	279.6	274.4	272.6	271.0	269.0	269.3
55°	252.3	248.1	246.0	244.4	241.8	238.6	240.7
57.5°	223.0	219.4	213.7	208.7	206.4	204.1	205.0
60°	202.4	195.0	187.7	181.9	180.3	175.5	175.5
62.5°	176.3	166.0	156.9	153.7	152.1	149.9	149.5
65°	135.6	131.4	129.3	127.2	126.1	126.1	125.1
67.5°	112.4	110.7	108.4	107.9	106.8	106.5	106.2
70°	99.3	97.2	96.2	95.7	94.6	95.1	93.6
72.5°	86.7	85.1	84.8	83.5	82.9	82.9	81.8
75°	68.4	68.4	67.8	67.3	66.2	65.7	66.2
77.5°	52.6	52.7	51.7	51.7	51.5	51.7	51.1
80°	42.1	42.5	42.1	41.5	41.0	41.5	41.0
82.5°	33.2	32.5	32.4	32.2	32.2	31.8	31.8
85°	18.9	19.4	18.9	18.4	18.4	18.4	18.9
87.5°	11.9	12.2	12.4	12.4	12.4	12.4	12.0
90°	23.7	25.3	26.1	26.1	26.1	26.1	26.1
92.5°	59.2	52.5	47.6	47.0	44.4	45.1	43.8
95°	158.9	125.7	108.3	98.1	91.7	89.4	90.2
97.5°	395.5	309.9	252.9	215.1	195.6	184.0	177.4
100°	623.8	515.5	419.9	354.2	320.2	297.3	283.0
102.5°	856.0	776.7	675.3	604.0	546.0	517.4	498.1
105°	1050.0	1060.3	1034.1	985.1	936.1	902.1	891.0
107.5°	1035.7	1117.9	1156.2	1162.4	1159.7	1152.9	1138.2
110°	991.4	1092.7	1157.5	1191.4	1206.5	1213.6	1212.8



TEST NUMBER: P331725-927

CATALOG NUMBER: SA2XXRDIP-C865D925U927-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	939.0	1047.1	1121.4	1168.7	1193.8	1207.3	1211.6
115°	867.3	970.9	1052.3	1108.4	1144.8	1165.4	1172.5
117.5°	809.1	903.0	979.5	1036.6	1075.1	1096.8	1102.7
120°	778.8	862.5	934.5	989.8	1027.0	1050.0	1057.9
122.5°	753.4	832.8	897.9	947.5	984.0	1004.4	1011.1
125°	720.3	789.8	849.1	895.0	925.0	944.8	951.1
127.5°	688.0	753.6	808.3	848.3	876.5	893.6	898.7
130°	666.5	729.0	781.2	819.9	846.8	862.5	868.9
132.5°	646.3	703.6	752.7	790.8	817.7	832.2	837.9
135°	614.3	666.5	710.7	744.7	770.9	785.1	788.2
137.5°	588.8	630.3	668.8	699.9	722.3	734.8	739.6
140°	572.4	608.8	643.6	668.8	689.4	701.3	706.0
142.5°	557.9	589.1	618.3	642.3	661.0	671.5	672.5
145°	539.2	563.7	586.6	605.6	619.1	626.9	629.3
147.5°	524.0	543.1	559.9	575.6	586.3	591.7	593.1
150°	513.9	530.5	544.7	556.6	566.1	570.8	571.6
152.5°	505.6	519.8	532.1	541.4	549.6	553.1	553.3
155°	492.6	504.4	513.1	521.8	527.4	530.5	528.9
157.5°	479.3	489.3	496.1	502.2	506.8	508.2	508.2
160°	470.4	479.1	484.7	490.2	494.2	495.0	495.0
162.5°	462.2	469.6	473.9	479.4	482.1	482.9	482.3
165°	449.9	455.4	458.6	461.7	464.9	464.9	464.1
167.5°	438.6	442.4	445.3	446.7	448.5	448.3	447.3
170°	431.7	434.8	436.4	437.2	439.6	438.8	437.2
172.5°	425.3	427.9	428.8	429.6	430.7	429.9	429.0
175°	418.3	419.1	419.9	419.9	420.6	419.9	418.3
177.5°	413.0	413.7	413.7	413.7	413.7	413.0	411.8
180°	411.1	411.1	411.1	411.1	411.1	411.1	411.1

(END OF REPORT)