

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331764

Luminaire Tested: **SA2XXRDIP-C1005D1080U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331764  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C1005D1080U835-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7691.9 lumens  
Efficiency: N/A  
Efficacy: 107.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331764  
CATALOG NUMBER: SA2XXRDIP-C1005D1080U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331764

CATALOG NUMBER: SA2XXRDIP-C1005D1080U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	45	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33				
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29				
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25				
5	69	57	50	44	63	53	46	41	45	40	36	37	34	30	30	28	25	22				
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20				
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	18				
8	54	42	35	30	50	39	33	28	34	29	25	28	24	21	23	20	18	16				
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	17	14				
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	27341	27341	27341
5°	27446	27000	27149
10°	27237	26558	26332
15°	26924	25770	25028
20°	26490	24646	23409
25°	26045	23370	21841
30°	25430	22057	19829
35°	24829	20631	18065
40°	24226	19155	16021
45°	23516	17497	14173
50°	22790	15822	12356
55°	22044	14021	10612
60°	21180	12126	8809
65°	20199	10189	8023
70°	19029	8393	7378
75°	17592	7648	6881
80°	15528	6843	6267
85°	12208	5391	5391



TEST NUMBER: P331764

CATALOG NUMBER: SA2XXRDIP-C1005D1080U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.5	2.1
10°-20°	435.2	5.7
20°-30°	611.2	7.9
30°-40°	666.5	8.7
40°-50°	612.8	8.0
50°-60°	481.3	6.3
60°-70°	313.8	4.1
70°-80°	161.8	2.1
80°-90°	47.4	0.6
90°-100°	241.5	3.1
100°-110°	819.6	10.7
110°-120°	870.7	11.3
120°-130°	716.8	9.3
130°-140°	575.6	7.5
140°-150°	435.0	5.7
150°-160°	305.7	4.0
160°-170°	180.0	2.3
170°-180°	58.6	0.8
0°-30°	1204.9	15.7
0°-40°	1871.4	24.3
0°-60°	2965.4	38.6
0°-90°	3488.4	45.4
90°-120°	1931.9	25.1
90°-150°	3659.3	47.6
90°-180°	4204.0	54.7
0°-180°	7691.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1693	1693	1693	1693	1693	
5°	1693	1685	1666	1679	1675	160
15°	1611	1592	1542	1513	1497	454
25°	1462	1410	1312	1251	1226	672
35°	1260	1178	1047	954	916	788
45°	1030	924	766	661	621	795
55°	783	661	498	410	377	700
65°	529	404	267	217	210	524
75°	282	178	123	112	110	298
85°	66	35	29	29	29	78
90°	1	16	40	38	38	5
95°	41	100	455	172	132	43
105°	142	214	861	1539	1309	151
115°	250	315	720	1486	1723	248
125°	348	412	692	1204	1398	309
135°	409	488	684	1012	1158	316
145°	467	537	681	845	925	293
155°	531	573	661	748	777	244
165°	578	596	633	671	682	163
175°	603	604	609	616	614	57
180°	604	604	604	604	604	



TEST NUMBER: P331764

CATALOG NUMBER: SA2XXRDIP-C1005D1080U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1699.6	1698.2	1696.8	1695.5	1694.1	1691.9	1688.9	1686.0	1683.0	1680.0	1682.7
5°	1693.4	1691.7	1690.0	1688.3	1686.6	1683.6	1679.1	1674.7	1670.3	1665.9	1668.9
7.5°	1676.0	1673.9	1671.8	1669.6	1667.5	1663.9	1658.7	1653.5	1648.4	1643.2	1644.1
10°	1661.3	1658.9	1656.5	1654.1	1651.7	1647.1	1640.3	1633.5	1626.7	1619.9	1618.9
12.5°	1642.9	1639.9	1637.0	1634.1	1631.2	1625.3	1616.6	1607.9	1599.2	1590.5	1588.6
15°	1610.7	1606.9	1603.2	1599.4	1595.7	1588.0	1576.5	1564.9	1553.3	1541.7	1535.3
17.5°	1571.1	1565.4	1559.7	1554.0	1548.3	1538.0	1523.1	1508.3	1493.4	1478.6	1470.9
20°	1541.7	1534.9	1528.1	1521.3	1514.5	1502.6	1485.5	1468.5	1451.5	1434.4	1425.9
22.5°	1509.8	1502.2	1494.6	1487.0	1479.3	1465.9	1446.7	1427.5	1408.3	1389.1	1378.1
25°	1462.0	1451.1	1440.2	1429.3	1418.4	1401.8	1379.3	1356.8	1334.3	1311.8	1297.9
27.5°	1404.4	1392.6	1380.7	1368.9	1357.0	1338.4	1313.1	1287.7	1262.4	1237.1	1220.8
30°	1364.0	1351.0	1338.1	1325.1	1312.2	1292.1	1264.8	1237.6	1210.4	1183.1	1165.7
32.5°	1324.7	1309.6	1294.5	1279.4	1264.2	1242.8	1215.0	1187.2	1159.4	1131.6	1111.8
35°	1259.7	1242.4	1225.0	1207.6	1190.3	1166.6	1136.6	1106.7	1076.7	1046.7	1025.3
37.5°	1194.8	1175.7	1156.6	1137.5	1118.5	1093.0	1061.0	1029.1	997.1	965.2	941.6
40°	1149.4	1129.0	1108.5	1088.1	1067.7	1040.9	1007.9	974.9	941.8	908.8	884.6
42.5°	1102.8	1081.3	1059.8	1038.2	1016.7	988.9	954.8	920.6	886.5	852.4	827.4
45°	1029.9	1007.0	984.2	961.4	938.6	909.3	873.5	837.8	802.0	766.3	742.1
47.5°	958.7	934.6	910.4	886.2	862.0	831.5	794.6	757.6	720.7	683.8	659.8
50°	907.3	883.1	858.9	834.7	810.5	779.7	742.3	704.8	667.3	629.9	606.4
52.5°	857.0	831.7	806.5	781.2	755.9	725.0	688.3	651.7	615.0	578.4	555.7
55°	783.1	756.6	730.0	703.4	676.9	645.2	608.4	571.6	534.9	498.1	477.6
57.5°	707.4	680.2	652.9	625.7	598.4	567.1	531.8	496.4	461.1	425.7	407.0
60°	655.9	628.7	601.4	574.2	546.9	515.8	480.7	445.6	410.5	375.5	358.1
62.5°	605.7	578.4	551.2	523.9	496.7	466.3	432.9	399.4	366.0	332.6	316.0
65°	528.7	501.1	473.6	446.0	418.4	389.3	358.6	328.0	297.3	266.7	255.1
67.5°	454.5	427.2	399.8	372.4	345.0	317.5	290.0	262.4	234.8	207.2	201.9
70°	403.1	376.5	349.9	323.4	296.8	271.8	248.3	224.8	201.3	177.8	174.4
72.5°	354.0	328.5	303.1	277.6	252.1	229.9	211.1	192.2	173.3	154.5	151.6
75°	282.0	258.1	234.3	210.5	186.6	168.9	157.3	145.8	134.2	122.6	120.2
77.5°	211.2	190.3	169.4	148.5	127.5	114.3	108.7	103.1	97.5	92.0	90.6
80°	167.0	149.7	132.3	114.9	97.6	87.2	83.8	80.4	77.0	73.6	72.2
82.5°	126.6	113.0	99.5	85.9	72.4	64.4	62.1	59.8	57.5	55.2	54.4
85°	65.9	58.7	51.6	44.4	37.3	33.2	32.2	31.2	30.1	29.1	29.1
87.5°	19.8	18.4	17.1	15.4	13.7	13.3	14.5	16.1	17.5	17.7	17.2
90°	1.2	4.6	9.3	11.6	13.9	17.4	23.2	31.4	38.3	39.5	38.3
92.5°	14.2	20.4	28.8	33.9	41.8	52.7	79.0	115.9	148.9	151.0	127.6
95°	40.7	45.3	56.9	67.4	86.0	113.8	167.3	268.3	403.1	455.4	398.5
97.5°	66.2	72.5	84.8	100.6	122.0	153.6	220.7	361.5	585.5	777.4	815.5
100°	89.4	92.9	103.4	122.0	145.2	177.7	239.3	381.0	631.9	917.7	1085.0
102.5°	110.8	113.4	123.8	142.4	166.6	199.1	256.0	382.0	614.3	922.4	1185.4
105°	141.7	146.4	154.5	171.9	197.5	230.0	284.6	388.0	579.7	860.8	1169.8
107.5°	175.2	178.9	186.8	202.8	228.2	260.9	313.9	404.0	562.5	794.8	1067.8
110°	197.5	202.1	209.1	224.2	248.6	282.3	333.4	417.0	558.8	763.2	1003.7



TEST NUMBER: P331764

CATALOG NUMBER: SA2XXRDIP-C1005D1080U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	217.9	222.6	230.5	244.6	268.1	302.7	352.0	431.0	559.7	742.8	959.1
115°	249.8	255.6	262.5	276.5	299.7	331.1	381.0	451.9	564.6	720.2	903.8
117.5°	282.8	287.4	294.4	306.7	329.0	361.5	407.7	474.2	572.9	709.3	868.9
120°	303.2	307.8	314.8	325.3	348.5	381.0	426.3	489.1	578.5	702.8	850.3
122.5°	322.7	326.4	333.4	344.8	368.0	401.5	444.0	502.1	585.0	699.1	834.5
125°	348.5	352.0	359.0	372.9	396.1	428.7	470.5	522.8	594.8	692.4	812.0
127.5°	368.9	373.6	383.4	398.7	421.0	454.4	495.1	542.0	604.8	688.4	791.1
130°	381.0	385.7	397.3	413.6	436.8	469.3	510.0	554.1	612.2	686.5	777.2
132.5°	392.2	397.8	410.3	427.5	451.7	484.2	523.0	566.2	619.6	685.6	766.0
135°	408.9	413.6	427.5	444.9	471.6	504.2	541.3	582.0	628.5	684.2	750.4
137.5°	424.7	430.3	444.2	462.8	489.3	519.5	556.2	594.1	636.4	684.0	739.5
140°	436.8	441.4	455.4	474.0	499.5	529.7	564.6	600.6	640.1	683.1	733.0
142.5°	448.9	452.6	465.6	484.2	508.8	537.2	571.1	606.2	642.9	683.1	726.5
145°	467.0	471.6	483.3	500.7	523.9	549.5	580.8	613.4	645.9	680.7	717.9
147.5°	486.5	490.0	501.1	517.2	536.5	559.2	588.7	617.3	646.8	676.6	709.1
150°	499.5	503.0	512.3	527.4	544.8	565.7	592.5	619.2	645.9	673.8	701.6
152.5°	512.5	514.2	523.4	536.7	553.2	572.2	596.2	620.1	644.0	669.1	695.1
155°	530.9	532.0	539.0	551.8	564.6	582.0	601.7	621.5	641.2	661.0	683.1
157.5°	546.2	547.4	553.0	564.1	574.3	589.0	605.7	621.5	635.9	652.6	671.7
160°	556.4	557.6	562.2	571.5	580.8	593.6	607.6	621.5	633.1	647.1	663.3
162.5°	566.7	566.0	570.6	578.0	586.4	596.4	608.5	620.6	630.3	642.4	655.9
165°	578.5	577.4	579.7	586.6	592.5	599.4	609.9	618.0	625.0	633.1	643.6
167.5°	588.3	586.9	589.0	593.4	597.6	602.0	609.6	616.4	619.6	625.0	631.5
170°	594.8	592.5	593.6	597.1	599.4	602.9	608.7	614.5	616.8	620.3	625.0
172.5°	598.5	597.1	596.4	599.9	601.3	603.8	607.8	611.7	613.1	614.8	618.5
175°	602.9	601.7	600.6	602.9	602.9	604.1	606.4	608.7	607.6	608.7	609.9
177.5°	605.0	603.1	602.2	604.1	604.1	604.1	605.0	606.9	605.0	604.1	605.0
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1



TEST NUMBER: P331764

CATALOG NUMBER: SA2XXRDIP-C1005D1080U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1685.4	1688.1	1690.9	1691.9	1691.4	1690.9	1690.3	1689.8
5°	1672.0	1675.1	1678.1	1679.1	1678.1	1677.1	1676.1	1675.1
7.5°	1644.9	1645.8	1646.7	1646.3	1644.5	1642.7	1641.0	1639.2
10°	1617.8	1616.8	1615.8	1614.3	1612.2	1610.2	1608.1	1606.1
12.5°	1586.8	1584.9	1583.1	1580.5	1577.1	1573.7	1570.3	1566.9
15°	1528.8	1522.3	1515.8	1510.9	1507.5	1504.1	1500.7	1497.3
17.5°	1463.2	1455.5	1447.8	1441.0	1435.2	1429.3	1423.4	1417.6
20°	1417.4	1408.9	1400.4	1392.4	1384.9	1377.4	1369.9	1362.4
22.5°	1367.2	1356.2	1345.2	1336.9	1331.4	1325.8	1320.2	1314.6
25°	1283.9	1270.0	1256.0	1246.5	1241.3	1236.2	1231.1	1226.0
27.5°	1204.5	1188.2	1171.9	1159.7	1151.6	1143.5	1135.4	1127.3
30°	1148.4	1131.0	1113.6	1100.4	1091.2	1082.0	1072.8	1063.6
32.5°	1092.0	1072.2	1052.3	1038.1	1029.5	1020.8	1012.1	1003.5
35°	1003.8	982.4	960.9	946.4	938.9	931.4	923.9	916.5
37.5°	917.9	894.3	870.6	854.5	846.0	837.4	828.8	820.2
40°	860.4	836.2	812.1	795.6	786.7	777.8	769.0	760.1
42.5°	802.4	777.4	752.4	735.6	727.0	718.4	709.9	701.3
45°	717.9	693.7	669.5	653.4	645.2	637.0	628.8	620.7
47.5°	635.7	611.7	587.6	571.9	564.5	557.1	549.6	542.2
50°	582.9	559.4	535.9	520.5	513.4	506.2	499.1	491.9
52.5°	533.0	510.3	487.7	473.0	466.4	459.8	453.2	446.6
55°	457.2	436.8	416.3	402.9	396.4	389.9	383.5	377.0
57.5°	388.3	369.5	350.8	338.7	333.3	327.8	322.4	316.9
60°	340.7	323.4	306.0	294.6	289.1	283.7	278.2	272.8
62.5°	299.5	282.9	266.4	256.4	253.2	249.9	246.6	243.4
65°	243.5	231.9	220.3	214.0	213.0	212.0	211.0	210.0
67.5°	196.6	191.3	185.9	182.7	181.7	180.6	179.5	178.4
70°	171.0	167.6	164.2	161.8	160.4	159.0	157.7	156.3
72.5°	148.8	145.9	143.0	141.2	140.4	139.6	138.7	137.9
75°	117.8	115.5	113.1	111.7	111.4	111.0	110.7	110.3
77.5°	89.2	87.9	86.5	85.5	85.0	84.5	83.9	83.4
80°	70.8	69.5	68.1	67.4	67.4	67.4	67.4	67.4
82.5°	53.5	52.7	51.9	51.5	51.5	51.5	51.5	51.5
85°	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
87.5°	16.7	16.0	16.2	16.2	16.2	16.2	16.2	16.2
90°	37.2	34.9	37.2	38.3	38.3	38.3	38.3	38.3
92.5°	101.3	86.9	77.1	69.9	69.0	65.3	66.2	64.4
95°	304.4	233.5	184.7	159.1	144.0	134.8	131.3	132.4
97.5°	710.2	581.1	455.4	371.5	316.0	287.4	270.4	260.7
100°	1060.6	916.6	757.4	616.8	520.4	470.5	436.8	415.9
102.5°	1290.2	1257.6	1141.2	992.3	887.5	802.3	760.2	731.9
105°	1411.4	1542.7	1557.8	1519.5	1447.4	1375.4	1325.5	1309.2
107.5°	1324.1	1521.8	1642.6	1698.8	1707.9	1703.9	1693.9	1672.3
110°	1248.8	1456.7	1605.4	1700.7	1750.6	1772.7	1783.2	1782.0





TEST NUMBER: P331764

CATALOG NUMBER: SA2XXRDIP-C1005D1080U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1180.0	1379.6	1538.5	1647.7	1717.2	1754.1	1773.9	1780.1
115°	1095.5	1274.4	1426.5	1546.2	1628.7	1682.1	1712.3	1722.8
117.5°	1031.8	1188.9	1326.9	1439.1	1523.2	1579.6	1611.5	1620.3
120°	1000.2	1144.2	1267.4	1373.1	1454.4	1509.0	1542.7	1554.3
122.5°	975.1	1107.1	1223.7	1319.2	1392.1	1445.8	1475.8	1485.5
125°	938.6	1058.3	1160.5	1247.6	1315.0	1359.2	1388.2	1397.5
127.5°	902.6	1010.9	1107.3	1187.7	1246.5	1287.8	1312.9	1320.4
130°	879.4	979.3	1071.1	1147.7	1204.7	1244.2	1267.4	1276.7
132.5°	857.1	949.6	1033.9	1105.9	1161.9	1201.4	1222.8	1231.1
135°	825.9	902.6	979.3	1044.3	1094.3	1132.6	1153.5	1158.2
137.5°	801.1	865.2	926.1	982.8	1028.3	1061.3	1079.7	1086.6
140°	785.3	841.1	894.5	945.6	982.8	1013.0	1030.4	1037.4
142.5°	772.3	819.7	865.7	908.4	943.7	971.2	986.7	988.1
145°	753.9	792.3	828.3	862.0	889.8	909.6	921.2	924.7
147.5°	739.8	770.0	798.1	822.7	845.7	861.5	869.4	871.5
150°	729.5	755.1	779.5	800.4	817.8	831.8	838.7	839.9
152.5°	719.3	743.0	763.7	781.8	795.5	807.6	812.7	812.9
155°	705.1	723.7	741.1	753.9	766.7	774.8	779.5	777.2
157.5°	688.6	704.2	718.8	728.8	737.9	744.6	746.7	746.7
160°	678.4	691.2	704.0	712.1	720.2	726.0	727.2	727.2
162.5°	668.2	679.1	690.0	696.3	704.4	708.4	709.5	708.6
165°	652.9	661.0	669.1	673.8	678.4	683.1	683.1	681.9
167.5°	638.2	644.5	650.1	654.3	656.3	658.9	658.7	657.3
170°	630.8	634.3	638.9	641.2	642.4	645.9	644.7	642.4
172.5°	622.4	625.0	628.7	630.1	631.3	632.9	631.7	630.3
175°	613.4	614.5	615.7	616.8	616.8	618.0	616.8	614.5
177.5°	606.9	606.9	607.8	607.8	607.8	607.8	606.9	605.0
180°	604.1	604.1	604.1	604.1	604.1	604.1	604.1	604.1

(END OF REPORT)