

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331735

Luminaire Tested: **SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331735  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5122.1 lumens  
Efficiency: N/A  
Efficacy: 102.9 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331735  
CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	79	79	79	74
1	104	100	97	93	99	96	92	90	87	84	82	79	77	75	71	70	69	65
2	96	89	83	78	91	85	80	76	78	74	70	71	67	65	64	62	60	56
3	89	80	73	67	84	76	70	65	70	65	60	64	60	56	58	55	52	49
4	82	71	64	58	78	68	62	56	63	57	53	58	53	50	53	49	46	44
5	76	65	57	51	72	62	55	50	57	51	47	53	48	44	48	44	41	39
6	70	59	51	45	67	56	49	44	52	46	42	48	43	39	44	40	37	35
7	66	54	46	40	62	52	45	39	48	42	37	44	39	36	41	37	34	31
8	61	49	42	36	58	48	41	36	44	38	34	41	36	32	38	34	31	29
9	57	45	38	33	55	44	37	32	41	35	31	38	33	30	36	31	28	26
10	54	42	35	30	52	41	34	30	38	32	28	36	31	27	33	29	26	24

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	35608	35608	35608	35608
5°	39768	35832	31770	35832
10°	44124	35580	27539	35580
15°	46292	35059	21698	35059
20°	40132	34287	18777	34287
25°	26320	33228	16764	33228
30°	17715	31946	15172	31946
35°	14349	30328	13685	30328
40°	12760	28572	12663	28572
45°	11549	26510	11303	26510
50°	10510	24465	10472	24465
55°	9880	22196	9751	22196
60°	8263	20118	8167	20118
65°	6968	18269	7904	18269
70°	6439	16315	7454	16315
75°	6026	14198	6881	14198
80°	5560	11688	6127	11688
85°	5113	9226	5391	9226



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	209.1	4.1
10°-20°	582.5	11.4
20°-30°	750.7	14.7
30°-40°	713.4	13.9
40°-50°	611.1	11.9
50°-60°	465.4	9.1
60°-70°	294.2	5.7
70°-80°	146.9	2.9
80°-90°	39.3	0.8
90°-100°	14.9	0.3
100°-110°	54.7	1.1
110°-120°	146.1	2.9
120°-130°	241.2	4.7
130°-140°	256.5	5.0
140°-150°	238.4	4.7
150°-160°	191.7	3.7
160°-170°	123.5	2.4
170°-180°	42.5	0.8
0°-30°	1542.3	30.1
0°-40°	2255.7	44.0
0°-60°	3332.1	65.1
0°-90°	3812.6	74.4
90°-120°	215.7	4.2
90°-150°	951.8	18.6
90°-180°	1309.0	25.6
0°-180°	5122.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	2205	2205	2205	2205	2205	
5°	2454	2211	1960	2211	2454	242
15°	2769	2097	1298	2097	2769	747
25°	1477	1865	941	1865	1477	701
35°	728	1539	694	1539	728	466
45°	506	1161	495	1161	506	391
55°	351	788	346	788	351	308
65°	182	478	207	478	182	186
75°	97	228	110	228	97	102
85°	28	50	29	50	28	30
90°	9	0	9	0	9	5
95°	14	21	14	21	14	13
105°	25	98	25	98	25	26
115°	26	186	26	186	26	66
125°	276	263	276	263	276	239
135°	336	325	336	325	336	259
145°	383	377	383	377	383	240
155°	416	416	416	416	416	192
165°	437	438	437	438	437	123
175°	445	448	445	448	445	42
180°	447	447	447	447	447	



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2294.9	2296.8	2298.6	2294.3	2294.3	2290.6	2282.7	2276.5	2259.4	2256.9	2256.9
5°	2453.7	2452.2	2455.2	2445.3	2431.5	2428.4	2413.9	2394.7	2374.8	2352.6	2348.0
7.5°	2611.6	2609.3	2603.1	2601.5	2590.9	2567.7	2544.3	2519.3	2486.2	2453.9	2437.6
10°	2691.3	2716.6	2701.2	2674.4	2679.8	2643.8	2624.6	2591.7	2564.1	2515.8	2505.1
12.5°	2769.7	2779.7	2774.8	2759.6	2752.7	2727.7	2701.8	2673.2	2622.3	2578.9	2541.2
15°	2769.4	2784.0	2787.8	2783.2	2787.1	2785.5	2771.7	2748.0	2703.5	2656.0	2614.6
17.5°	2565.0	2575.1	2600.2	2617.2	2638.7	2684.1	2706.4	2715.2	2708.6	2681.5	2652.3
20°	2335.7	2318.8	2389.3	2425.4	2456.0	2532.6	2598.5	2623.8	2664.4	2663.7	2656.0
22.5°	2010.8	2014.8	2081.6	2124.4	2213.9	2290.5	2365.6	2460.8	2539.4	2591.3	2621.7
25°	1477.4	1506.6	1573.2	1631.5	1731.1	1873.6	2003.1	2153.3	2295.1	2407.0	2513.5
27.5°	1109.6	1111.8	1164.6	1218.4	1277.6	1394.4	1557.4	1736.8	1938.9	2105.7	2297.5
30°	950.2	945.6	967.8	1000.8	1051.4	1141.8	1264.4	1440.7	1642.2	1893.5	2117.3
32.5°	837.4	837.7	854.4	878.8	920.8	981.8	1065.8	1208.9	1399.4	1646.5	1908.9
35°	728.0	727.2	739.5	757.1	774.7	813.8	871.3	946.4	1077.4	1308.1	1576.3
37.5°	649.5	652.9	658.9	669.9	689.4	711.1	745.6	796.0	889.4	1025.8	1251.2
40°	605.4	606.9	615.3	624.5	636.0	652.9	681.2	721.9	790.1	898.9	1063.6
42.5°	564.9	566.5	572.4	581.0	590.1	606.9	630.4	665.5	720.8	805.7	941.6
45°	505.8	505.8	511.1	515.0	524.9	540.2	559.4	588.5	626.8	689.7	780.1
47.5°	450.3	450.4	454.0	460.6	466.8	478.8	497.6	521.4	549.3	597.9	675.1
50°	418.4	419.2	421.5	426.8	430.7	441.4	456.0	476.6	505.8	543.3	607.7
52.5°	392.7	392.2	395.1	397.4	400.0	407.7	418.6	436.8	462.8	495.5	548.8
55°	351.0	347.9	352.5	356.3	358.6	361.7	367.8	379.3	401.5	429.1	469.0
57.5°	298.9	297.6	300.9	304.4	311.6	319.9	325.1	332.4	343.9	363.7	403.2
60°	255.9	255.9	262.8	265.1	273.6	284.3	295.0	301.2	312.7	325.7	354.8
62.5°	217.9	218.6	221.8	224.1	228.8	242.0	257.0	270.5	281.4	293.8	313.1
65°	182.4	183.9	183.9	185.4	188.5	191.6	197.7	208.4	227.6	245.2	259.8
67.5°	154.8	155.3	155.7	157.2	158.0	161.4	163.8	168.6	173.0	189.7	207.8
70°	136.4	138.7	137.9	139.5	140.2	141.8	144.8	147.1	154.0	157.9	168.6
72.5°	119.2	120.9	120.8	121.7	123.7	124.0	126.4	128.7	133.2	136.4	142.2
75°	96.6	95.8	96.6	98.1	98.9	99.6	99.6	102.7	105.0	108.0	111.9
77.5°	74.5	75.3	75.1	75.3	75.4	76.8	76.6	78.0	80.3	81.8	83.7
80°	59.8	60.5	59.8	60.5	61.3	62.1	61.3	62.1	64.4	65.9	65.9
82.5°	46.3	46.4	46.9	47.1	47.2	47.4	48.4	48.6	50.3	50.0	50.6
85°	27.6	26.8	26.8	26.8	27.6	28.4	27.6	27.6	28.4	28.4	28.4
87.5°	11.6	12.1	12.1	12.1	12.1	12.0	11.9	12.5	11.8	12.3	11.6
90°	8.7	8.6	8.4	8.3	8.2	7.9	7.5	7.2	6.8	6.5	5.9
92.5°	8.7	8.6	8.6	8.5	8.4	8.2	8.1	7.9	7.7	7.5	7.2
95°	13.9	14.0	14.0	14.1	14.2	14.0	13.7	13.3	13.0	12.6	12.1
97.5°	18.6	18.5	18.4	18.3	18.2	18.0	17.7	17.5	17.2	16.9	15.7
100°	21.7	21.5	21.4	21.2	21.1	20.7	20.2	19.6	19.0	18.4	17.2
102.5°	23.2	23.0	22.8	22.6	22.4	21.9	21.2	20.4	19.7	18.9	29.2
105°	24.6	24.3	24.0	23.7	23.4	22.9	22.1	21.3	20.5	19.7	39.3
107.5°	25.3	25.0	24.7	24.4	24.1	24.4	25.2	26.0	26.8	27.6	51.1
110°	25.5	25.3	25.0	24.7	24.4	27.8	35.0	42.2	49.4	56.6	77.3



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	25.8	25.6	25.3	25.1	24.9	37.9	64.1	90.3	116.5	142.7	147.8
115°	26.5	31.7	36.9	42.0	47.2	66.4	99.7	133.0	166.2	199.5	197.7
117.5°	108.3	125.3	142.3	159.3	176.3	188.8	196.8	204.9	212.9	221.0	219.7
120°	197.2	206.9	216.6	226.3	236.0	240.4	239.6	238.7	237.9	237.0	235.7
122.5°	246.1	248.0	249.9	251.8	253.6	254.3	253.8	253.3	252.8	252.3	250.9
125°	276.4	276.2	276.0	275.8	275.6	275.2	274.7	274.2	273.7	273.2	271.8
127.5°	295.6	295.5	295.5	295.5	295.4	295.0	294.3	293.6	292.8	292.1	291.1
130°	307.5	307.6	307.6	307.7	307.8	307.4	306.6	305.8	305.0	304.3	303.5
132.5°	319.1	319.2	319.3	319.3	319.4	319.1	318.4	317.8	317.1	316.4	315.6
135°	335.9	336.1	336.2	336.4	336.5	336.2	335.5	334.8	334.1	333.4	332.7
137.5°	351.3	351.5	351.8	352.0	352.2	352.0	351.3	350.6	349.9	349.2	348.5
140°	360.8	361.2	361.6	361.9	362.3	362.1	361.5	360.8	360.2	359.5	358.8
142.5°	370.1	370.5	370.9	371.2	371.6	371.5	370.9	370.3	369.7	369.1	368.2
145°	383.1	383.5	383.9	384.2	384.6	384.5	384.0	383.5	383.0	382.5	381.3
147.5°	394.6	394.9	395.2	395.5	395.8	395.8	395.4	395.0	394.6	394.3	393.1
150°	401.6	401.9	402.3	402.7	403.0	403.0	402.5	402.1	401.7	401.3	400.1
152.5°	407.5	408.0	408.5	408.9	409.4	409.4	409.0	408.6	408.1	407.7	406.6
155°	415.8	416.4	417.0	417.5	418.1	418.2	417.7	417.3	416.9	416.4	415.6
157.5°	423.4	423.9	424.5	425.0	425.6	425.6	425.2	424.7	424.2	423.7	423.1
160°	427.8	428.3	428.8	429.3	429.8	429.8	429.4	429.0	428.5	428.1	427.7
162.5°	431.4	432.0	432.6	433.2	433.9	433.9	433.4	432.9	432.5	432.0	431.6
165°	436.8	437.3	437.8	438.3	438.8	438.8	438.3	437.8	437.3	436.8	436.6
167.5°	440.2	440.9	441.5	442.2	442.8	442.9	442.4	441.9	441.4	440.9	440.7
170°	442.3	443.0	443.6	444.3	444.9	445.0	444.5	444.0	443.5	443.0	442.8
172.5°	443.9	444.5	445.2	445.8	446.5	446.5	446.0	445.5	445.0	444.5	444.4
175°	445.2	445.9	446.7	447.4	448.1	448.2	447.7	447.2	446.7	446.2	446.1
177.5°	446.1	446.6	447.1	447.6	448.1	448.2	447.8	447.4	447.0	446.6	446.5
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2258.2	2253.2	2249.0	2237.9	2232.4	2220.1	2218.3	2217.7	2201.8	2186.4	2182.1
5°	2335.7	2323.4	2305.1	2283.6	2261.4	2238.4	2223.1	2210.8	2180.1	2151.0	2134.2
7.5°	2413.9	2387.5	2355.8	2315.2	2281.3	2243.3	2215.1	2189.8	2146.3	2104.6	2076.5
10°	2472.1	2429.2	2387.0	2331.1	2287.4	2244.5	2204.7	2170.2	2121.1	2066.0	2026.9
12.5°	2508.3	2461.1	2403.0	2348.3	2291.7	2237.2	2183.8	2139.5	2081.9	2024.9	1978.5
15°	2557.2	2506.6	2436.1	2357.9	2285.1	2213.9	2152.6	2097.4	2022.3	1954.1	1897.4
17.5°	2597.2	2527.6	2451.9	2361.5	2277.2	2186.6	2107.7	2037.2	1953.6	1871.3	1804.5
20°	2610.0	2541.1	2453.7	2363.3	2263.7	2157.2	2072.1	1995.5	1905.8	1816.1	1739.5
22.5°	2602.1	2548.4	2451.3	2343.1	2241.0	2129.6	2033.5	1944.6	1845.1	1753.6	1664.7
25°	2548.0	2529.6	2437.6	2319.6	2203.1	2073.6	1962.5	1865.2	1751.8	1653.7	1557.1
27.5°	2421.8	2461.5	2404.5	2278.8	2149.3	2010.5	1885.6	1774.8	1657.1	1546.7	1450.5
30°	2300.5	2391.6	2367.1	2250.6	2105.8	1969.4	1829.2	1713.5	1587.8	1474.4	1379.4
32.5°	2134.3	2285.0	2308.9	2211.4	2061.7	1911.8	1764.8	1649.7	1518.5	1399.0	1306.4
35°	1869.8	2095.1	2198.5	2136.5	1986.3	1824.6	1672.8	1538.7	1406.9	1288.9	1197.0
37.5°	1554.2	1861.1	2033.5	2037.9	1900.0	1731.9	1566.6	1433.5	1298.6	1182.7	1083.3
40°	1349.5	1682.0	1906.6	1956.4	1839.9	1658.3	1491.2	1355.6	1223.8	1110.4	996.2
42.5°	1165.6	1496.9	1772.9	1859.5	1767.0	1586.6	1418.9	1277.1	1149.0	1041.7	925.1
45°	942.6	1232.2	1536.4	1691.2	1639.9	1472.8	1295.8	1161.0	1040.6	947.9	836.0
47.5°	795.1	999.3	1293.7	1503.0	1502.1	1349.6	1175.5	1046.3	934.7	847.8	757.3
50°	711.1	888.9	1138.0	1375.5	1395.4	1267.5	1101.9	974.0	869.8	778.6	705.8
52.5°	635.7	782.2	1006.2	1233.9	1290.6	1179.8	1019.2	901.0	799.9	716.0	653.7
55°	537.2	650.6	820.7	1033.7	1119.6	1041.4	898.9	788.5	706.5	636.0	582.4
57.5°	454.4	539.5	676.0	847.5	947.5	898.3	780.7	691.1	620.9	557.1	514.8
60°	402.3	472.0	587.8	731.1	841.4	806.9	706.5	623.0	563.2	508.1	468.2
62.5°	353.3	413.2	512.4	628.7	729.8	715.6	633.6	563.5	511.1	460.9	427.1
65°	284.3	328.0	405.4	496.6	577.8	584.7	525.7	478.2	431.4	391.6	361.7
67.5°	226.4	254.9	309.4	386.2	447.1	468.8	432.8	396.5	359.4	328.6	302.7
70°	190.8	213.8	253.6	315.7	371.7	394.6	374.0	345.6	313.4	288.1	265.9
72.5°	154.6	177.0	206.4	252.0	299.9	324.8	317.6	297.2	271.1	250.1	229.1
75°	116.5	123.4	143.3	174.0	211.5	233.0	238.3	227.6	206.9	190.8	178.5
77.5°	86.1	90.3	99.8	115.9	140.4	159.5	167.4	166.1	151.9	142.5	131.0
80°	69.0	71.3	75.9	82.8	101.2	120.3	125.7	125.7	115.7	111.9	100.4
82.5°	52.4	54.1	56.9	60.7	69.3	86.0	92.0	93.2	86.9	81.8	72.8
85°	29.9	29.1	30.7	33.0	34.5	39.1	48.3	49.8	48.3	42.1	39.8
87.5°	11.5	12.0	11.9	11.1	11.6	12.0	14.9	17.8	15.5	13.9	12.8
90°	5.3	4.7	4.2	3.5	2.7	1.9	1.1	0.3	1.1	1.9	2.7
92.5°	6.9	6.6	6.4	6.2	6.3	6.4	6.5	6.5	6.5	6.4	6.3
95°	11.6	11.1	10.6	11.5	13.9	16.3	18.6	21.0	18.6	16.3	13.9
97.5°	14.5	13.4	12.2	15.0	21.7	28.3	35.0	41.7	35.0	28.3	21.7
100°	16.0	14.8	13.5	17.9	27.7	37.5	47.4	57.2	47.4	37.5	27.7
102.5°	39.4	49.6	59.8	66.0	68.1	70.1	72.2	74.3	72.2	70.1	68.1
105°	59.0	78.6	98.2	106.9	104.8	102.6	100.4	98.3	100.4	102.6	104.8
107.5°	74.7	98.2	121.7	132.6	130.9	129.1	127.4	125.6	127.4	129.1	130.9
110°	98.1	118.9	139.6	149.3	147.8	146.3	144.7	143.2	144.7	146.3	147.8





TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	153.0	158.1	163.2	165.1	163.8	162.5	161.1	159.8	161.1	162.5	163.8
115°	195.9	194.1	192.3	190.8	189.6	188.4	187.1	185.9	187.1	188.4	189.6
117.5°	218.5	217.3	216.0	214.7	213.4	212.0	210.6	209.3	210.6	212.0	213.4
120°	234.4	233.1	231.8	230.6	229.6	228.5	227.4	226.3	227.4	228.5	229.6
122.5°	249.4	248.0	246.6	245.4	244.2	243.1	242.0	240.8	242.0	243.1	244.2
125°	270.5	269.1	267.8	266.6	265.7	264.7	263.8	262.9	263.8	264.7	265.7
127.5°	290.1	289.0	288.0	287.0	286.0	284.9	283.9	282.8	283.9	284.9	286.0
130°	302.7	301.9	301.1	300.1	299.0	297.8	296.7	295.5	296.7	297.8	299.0
132.5°	314.8	314.0	313.2	312.4	311.4	310.4	309.4	308.5	309.4	310.4	311.4
135°	332.1	331.4	330.8	329.9	328.7	327.6	326.4	325.3	326.4	327.6	328.7
137.5°	347.7	347.0	346.3	345.5	344.7	343.9	343.1	342.3	343.1	343.9	344.7
140°	358.0	357.2	356.4	355.7	355.1	354.5	354.0	353.4	354.0	354.5	355.1
142.5°	367.3	366.4	365.5	364.8	364.3	363.7	363.2	362.7	363.2	363.7	364.3
145°	380.1	378.8	377.6	377.0	377.1	377.2	377.3	377.3	377.3	377.2	377.1
147.5°	391.9	390.6	389.4	389.0	389.2	389.5	389.8	390.1	389.8	389.5	389.2
150°	399.0	397.8	396.7	396.3	396.8	397.3	397.8	398.3	397.8	397.3	396.8
152.5°	405.5	404.4	403.3	403.1	403.6	404.2	404.8	405.3	404.8	404.2	403.6
155°	414.7	413.9	413.0	412.9	413.5	414.2	414.8	415.5	414.8	414.2	413.5
157.5°	422.5	421.9	421.3	421.2	421.8	422.3	422.9	423.4	422.9	422.3	421.8
160°	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	427.7	427.2	426.8
162.5°	431.2	430.8	430.5	430.5	430.9	431.4	431.8	432.2	431.8	431.4	430.9
165°	436.4	436.2	436.0	436.1	436.5	436.9	437.4	437.8	437.4	436.9	436.5
167.5°	440.5	440.3	440.1	440.2	440.6	441.1	441.5	441.9	441.5	441.1	440.6
170°	442.7	442.5	442.4	442.5	443.0	443.4	443.8	444.3	443.8	443.4	443.0
172.5°	444.2	444.1	443.9	444.1	444.5	444.9	445.4	445.8	445.4	444.9	444.5
175°	445.9	445.8	445.6	445.8	446.3	446.8	447.3	447.8	447.3	446.8	446.3
177.5°	446.5	446.4	446.4	446.5	446.9	447.3	447.7	448.1	447.7	447.3	446.9
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2174.2	2169.9	2161.9	2149.6	2142.3	2129.4	2120.8	2125.7	2127.0	2125.7	2124.5
5°	2115.8	2099.7	2077.5	2056.0	2036.1	2014.6	2002.4	1997.0	1986.3	1980.1	1977.1
7.5°	2045.1	2017.4	1986.0	1948.6	1916.8	1883.6	1866.6	1858.1	1836.2	1824.3	1813.8
10°	1992.4	1948.7	1917.3	1868.3	1838.4	1794.7	1764.8	1765.6	1735.7	1718.8	1706.6
12.5°	1934.2	1886.2	1833.9	1789.8	1748.3	1713.2	1677.1	1662.6	1630.9	1614.6	1581.5
15°	1837.6	1781.7	1726.5	1666.7	1624.6	1570.2	1518.1	1454.5	1403.1	1358.7	1346.4
17.5°	1732.2	1662.9	1607.6	1537.4	1465.2	1373.7	1313.3	1276.4	1245.4	1222.0	1204.5
20°	1659.8	1589.3	1530.3	1424.6	1327.2	1265.2	1220.7	1192.4	1160.2	1134.9	1121.1
22.5°	1583.8	1510.2	1429.8	1311.8	1235.9	1186.1	1146.5	1113.9	1092.1	1072.4	1059.8
25°	1475.9	1395.4	1262.9	1181.6	1120.3	1068.2	1040.6	1020.7	997.7	970.9	958.7
27.5°	1361.9	1233.9	1138.7	1078.3	1019.8	985.9	961.1	931.4	910.8	898.7	886.0
30°	1276.7	1148.7	1074.4	1008.5	967.1	929.5	900.4	883.6	863.6	842.9	834.5
32.5°	1181.6	1079.4	1008.2	953.3	911.3	879.3	856.3	829.0	814.6	801.9	784.2
35°	1063.6	986.2	921.1	876.7	836.8	810.8	783.9	767.8	741.8	731.1	724.2
37.5°	963.7	896.6	848.0	801.1	769.5	740.7	724.3	698.7	687.4	672.5	658.0
40°	907.3	841.4	794.7	756.3	721.1	699.6	678.9	658.3	641.4	634.5	616.9
42.5°	849.7	796.0	749.3	707.3	683.7	661.0	634.8	619.6	602.2	591.0	580.1
45°	770.1	722.6	682.8	648.3	622.2	598.5	581.6	556.3	546.4	524.2	515.0
47.5°	700.3	656.1	618.1	585.3	559.9	544.4	519.7	499.9	484.0	470.4	458.6
50°	650.6	613.8	577.0	547.9	524.9	502.7	477.4	467.4	442.9	436.0	429.1
52.5°	605.2	570.3	536.6	508.1	485.1	463.5	441.2	428.2	411.7	404.8	399.7
55°	541.8	508.1	475.9	450.6	427.6	405.4	391.6	375.5	367.8	362.5	356.3
57.5°	478.0	447.7	423.0	397.4	374.3	356.6	340.7	331.0	323.1	316.0	308.7
60°	437.6	408.4	386.2	362.5	338.7	324.1	311.9	300.4	291.2	280.5	277.4
62.5°	394.6	369.2	348.8	325.7	305.0	291.7	280.0	269.1	258.1	242.5	238.2
65°	335.6	315.7	294.3	275.1	256.7	243.7	226.8	214.6	210.0	208.4	207.7
67.5°	282.3	263.5	245.1	225.4	208.7	196.6	188.1	186.2	183.0	182.1	179.9
70°	246.8	229.1	210.7	192.3	176.3	174.0	170.9	167.8	164.0	162.5	160.9
72.5°	214.9	196.6	178.2	163.5	156.6	153.7	150.7	147.6	145.0	143.5	142.5
75°	164.8	147.9	135.6	130.3	126.4	124.1	119.5	117.2	115.7	113.4	112.6
77.5°	118.6	109.1	103.5	100.1	96.1	93.6	91.0	88.7	87.1	86.6	85.4
80°	90.4	85.8	82.0	77.4	75.9	72.8	72.0	69.7	70.5	68.2	68.2
82.5°	70.2	64.4	61.2	59.0	57.5	55.0	54.3	53.2	53.3	51.6	51.6
85°	36.0	34.5	33.0	31.4	31.4	29.1	29.9	29.1	29.1	27.6	26.8
87.5°	12.3	11.9	10.8	10.9	11.0	10.5	10.6	10.0	10.1	10.2	9.6
90°	3.5	4.2	4.7	5.3	5.9	6.5	6.8	7.2	7.5	7.9	8.2
92.5°	6.2	6.4	6.6	6.9	7.2	7.5	7.7	7.9	8.1	8.2	8.4
95°	11.5	10.6	11.1	11.6	12.1	12.6	13.0	13.3	13.7	14.0	14.2
97.5°	15.0	12.2	13.4	14.5	15.7	16.9	17.2	17.5	17.7	18.0	18.2
100°	17.9	13.5	14.8	16.0	17.2	18.4	19.0	19.6	20.2	20.7	21.1
102.5°	66.0	59.8	49.6	39.4	29.2	18.9	19.7	20.4	21.2	21.9	22.4
105°	106.9	98.2	78.6	59.0	39.3	19.7	20.5	21.3	22.1	22.9	23.4
107.5°	132.6	121.7	98.2	74.7	51.1	27.6	26.8	26.0	25.2	24.4	24.1
110°	149.3	139.6	118.9	98.1	77.3	56.6	49.4	42.2	35.0	27.8	24.4



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	165.1	163.2	158.1	153.0	147.8	142.7	116.5	90.3	64.1	37.9	24.9
115°	190.8	192.3	194.1	195.9	197.7	199.5	166.2	133.0	99.7	66.4	47.2
117.5°	214.7	216.0	217.3	218.5	219.7	221.0	212.9	204.9	196.8	188.8	176.3
120°	230.6	231.8	233.1	234.4	235.7	237.0	237.9	238.7	239.6	240.4	236.0
122.5°	245.4	246.6	248.0	249.4	250.9	252.3	252.8	253.3	253.8	254.3	253.6
125°	266.6	267.8	269.1	270.5	271.8	273.2	273.7	274.2	274.7	275.2	275.6
127.5°	287.0	288.0	289.0	290.1	291.1	292.1	292.8	293.6	294.3	295.0	295.4
130°	300.1	301.1	301.9	302.7	303.5	304.3	305.0	305.8	306.6	307.4	307.8
132.5°	312.4	313.2	314.0	314.8	315.6	316.4	317.1	317.8	318.4	319.1	319.4
135°	329.9	330.8	331.4	332.1	332.7	333.4	334.1	334.8	335.5	336.2	336.5
137.5°	345.5	346.3	347.0	347.7	348.5	349.2	349.9	350.6	351.3	352.0	352.2
140°	355.7	356.4	357.2	358.0	358.8	359.5	360.2	360.8	361.5	362.1	362.3
142.5°	364.8	365.5	366.4	367.3	368.2	369.1	369.7	370.3	370.9	371.5	371.6
145°	377.0	377.6	378.8	380.1	381.3	382.5	383.0	383.5	384.0	384.5	384.6
147.5°	389.0	389.4	390.6	391.9	393.1	394.3	394.6	395.0	395.4	395.8	395.8
150°	396.3	396.7	397.8	399.0	400.1	401.3	401.7	402.1	402.5	403.0	403.0
152.5°	403.1	403.3	404.4	405.5	406.6	407.7	408.1	408.6	409.0	409.4	409.4
155°	412.9	413.0	413.9	414.7	415.6	416.4	416.9	417.3	417.7	418.2	418.1
157.5°	421.2	421.3	421.9	422.5	423.1	423.7	424.2	424.7	425.2	425.6	425.6
160°	426.4	426.4	426.8	427.2	427.7	428.1	428.5	429.0	429.4	429.8	429.8
162.5°	430.5	430.5	430.8	431.2	431.6	432.0	432.5	432.9	433.4	433.9	433.9
165°	436.1	436.0	436.2	436.4	436.6	436.8	437.3	437.8	438.3	438.8	438.8
167.5°	440.2	440.1	440.3	440.5	440.7	440.9	441.4	441.9	442.4	442.9	442.8
170°	442.5	442.4	442.5	442.7	442.8	443.0	443.5	444.0	444.5	445.0	444.9
172.5°	444.1	443.9	444.1	444.2	444.4	444.5	445.0	445.5	446.0	446.5	446.5
175°	445.8	445.6	445.8	445.9	446.1	446.2	446.7	447.2	447.7	448.2	448.1
177.5°	446.5	446.4	446.4	446.5	446.5	446.6	447.0	447.4	447.8	448.2	448.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2117.8	2119.0	2117.2	2118.4	2117.2	2119.0	2117.8	2124.5	2125.7	2127.0	2125.7
5°	1973.2	1964.0	1962.5	1960.2	1962.5	1964.0	1973.2	1977.1	1980.1	1986.3	1997.0
7.5°	1800.7	1799.3	1795.5	1790.1	1795.5	1799.3	1800.7	1813.8	1824.3	1836.2	1858.1
10°	1689.7	1685.9	1685.1	1679.7	1685.1	1685.9	1689.7	1706.6	1718.8	1735.7	1765.6
12.5°	1559.7	1535.1	1532.5	1519.1	1532.5	1535.1	1559.7	1581.5	1614.6	1630.9	1662.6
15°	1328.0	1323.4	1308.1	1298.1	1308.1	1323.4	1328.0	1346.4	1358.7	1403.1	1454.5
17.5°	1195.6	1180.6	1175.8	1173.7	1175.8	1180.6	1195.6	1204.5	1222.0	1245.4	1276.4
20°	1110.4	1096.6	1094.3	1092.8	1094.3	1096.6	1110.4	1121.1	1134.9	1160.2	1192.4
22.5°	1051.5	1037.1	1031.1	1026.5	1031.1	1037.1	1051.5	1059.8	1072.4	1092.1	1113.9
25°	951.0	945.6	942.6	941.0	942.6	945.6	951.0	958.7	970.9	997.7	1020.7
27.5°	872.4	860.6	858.3	854.3	858.3	860.6	872.4	886.0	898.7	910.8	931.4
30°	827.6	823.8	818.4	813.8	818.4	823.8	827.6	834.5	842.9	863.6	883.6
32.5°	774.9	771.7	766.9	764.8	766.9	771.7	774.9	784.2	801.9	814.6	829.0
35°	716.5	705.8	701.2	694.3	701.2	705.8	716.5	724.2	731.1	741.8	767.8
37.5°	654.7	649.1	642.6	644.9	642.6	649.1	654.7	658.0	672.5	687.4	698.7
40°	606.9	603.1	601.6	600.8	601.6	603.1	606.9	616.9	634.5	641.4	658.3
42.5°	568.9	558.3	554.3	554.2	554.3	558.3	568.9	580.1	591.0	602.2	619.6
45°	511.1	501.2	494.3	495.0	494.3	501.2	511.1	515.0	524.2	546.4	556.3
47.5°	452.0	451.7	447.4	448.7	447.4	451.7	452.0	458.6	470.4	484.0	499.9
50°	423.8	419.2	416.1	416.9	416.1	419.2	423.8	429.1	436.0	442.9	467.4
52.5°	396.8	392.8	390.4	393.6	390.4	392.8	396.8	399.7	404.8	411.7	428.2
55°	352.5	347.9	347.1	346.4	347.1	347.9	352.5	356.3	362.5	367.8	375.5
57.5°	303.0	299.9	295.3	293.3	295.3	299.9	303.0	308.7	316.0	323.1	331.0
60°	267.4	261.3	253.6	252.9	253.6	261.3	267.4	277.4	280.5	291.2	300.4
62.5°	234.9	233.7	232.2	232.0	232.2	233.7	234.9	238.2	242.5	258.1	269.1
65°	206.1	205.4	206.1	206.9	206.1	205.4	206.1	207.7	208.4	210.0	214.6
67.5°	179.6	178.2	176.9	177.5	176.9	178.2	179.6	179.9	182.1	183.0	186.2
70°	159.4	158.6	157.9	157.9	157.9	158.6	159.4	160.9	162.5	164.0	167.8
72.5°	139.8	139.6	138.9	138.2	138.9	139.6	139.8	142.5	143.5	145.0	147.6
75°	111.9	110.3	110.3	110.3	110.3	110.3	111.9	112.6	113.4	115.7	117.2
77.5°	85.2	84.4	83.7	83.1	83.7	84.4	85.2	85.4	86.6	87.1	88.7
80°	67.4	66.7	65.9	65.9	65.9	66.7	67.4	68.2	68.2	70.5	69.7
82.5°	51.5	50.7	50.6	50.0	50.6	50.7	51.5	51.6	51.6	53.3	53.2
85°	27.6	28.4	27.6	29.1	27.6	28.4	27.6	26.8	27.6	29.1	29.1
87.5°	9.6	9.0	9.7	9.1	9.7	9.0	9.6	9.6	10.2	10.1	10.0
90°	8.3	8.4	8.6	8.7	8.6	8.4	8.3	8.2	7.9	7.5	7.2
92.5°	8.5	8.6	8.6	8.7	8.6	8.6	8.5	8.4	8.2	8.1	7.9
95°	14.1	14.0	14.0	13.9	14.0	14.0	14.1	14.2	14.0	13.7	13.3
97.5°	18.3	18.4	18.5	18.6	18.5	18.4	18.3	18.2	18.0	17.7	17.5
100°	21.2	21.4	21.5	21.7	21.5	21.4	21.2	21.1	20.7	20.2	19.6
102.5°	22.6	22.8	23.0	23.2	23.0	22.8	22.6	22.4	21.9	21.2	20.4
105°	23.7	24.0	24.3	24.6	24.3	24.0	23.7	23.4	22.9	22.1	21.3
107.5°	24.4	24.7	25.0	25.3	25.0	24.7	24.4	24.1	24.4	25.2	26.0
110°	24.7	25.0	25.3	25.5	25.3	25.0	24.7	24.4	27.8	35.0	42.2



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	25.1	25.3	25.6	25.8	25.6	25.3	25.1	24.9	37.9	64.1	90.3
115°	42.0	36.9	31.7	26.5	31.7	36.9	42.0	47.2	66.4	99.7	133.0
117.5°	159.3	142.3	125.3	108.3	125.3	142.3	159.3	176.3	188.8	196.8	204.9
120°	226.3	216.6	206.9	197.2	206.9	216.6	226.3	236.0	240.4	239.6	238.7
122.5°	251.8	249.9	248.0	246.1	248.0	249.9	251.8	253.6	254.3	253.8	253.3
125°	275.8	276.0	276.2	276.4	276.2	276.0	275.8	275.6	275.2	274.7	274.2
127.5°	295.5	295.5	295.5	295.6	295.5	295.5	295.5	295.4	295.0	294.3	293.6
130°	307.7	307.6	307.6	307.5	307.6	307.6	307.7	307.8	307.4	306.6	305.8
132.5°	319.3	319.3	319.2	319.1	319.2	319.3	319.3	319.4	319.1	318.4	317.8
135°	336.4	336.2	336.1	335.9	336.1	336.2	336.4	336.5	336.2	335.5	334.8
137.5°	352.0	351.8	351.5	351.3	351.5	351.8	352.0	352.2	352.0	351.3	350.6
140°	361.9	361.6	361.2	360.8	361.2	361.6	361.9	362.3	362.1	361.5	360.8
142.5°	371.2	370.9	370.5	370.1	370.5	370.9	371.2	371.6	371.5	370.9	370.3
145°	384.2	383.9	383.5	383.1	383.5	383.9	384.2	384.6	384.5	384.0	383.5
147.5°	395.5	395.2	394.9	394.6	394.9	395.2	395.5	395.8	395.8	395.4	395.0
150°	402.7	402.3	401.9	401.6	401.9	402.3	402.7	403.0	403.0	402.5	402.1
152.5°	408.9	408.5	408.0	407.5	408.0	408.5	408.9	409.4	409.4	409.0	408.6
155°	417.5	417.0	416.4	415.8	416.4	417.0	417.5	418.1	418.2	417.7	417.3
157.5°	425.0	424.5	423.9	423.4	423.9	424.5	425.0	425.6	425.6	425.2	424.7
160°	429.3	428.8	428.3	427.8	428.3	428.8	429.3	429.8	429.8	429.4	429.0
162.5°	433.2	432.6	432.0	431.4	432.0	432.6	433.2	433.9	433.9	433.4	432.9
165°	438.3	437.8	437.3	436.8	437.3	437.8	438.3	438.8	438.8	438.3	437.8
167.5°	442.2	441.5	440.9	440.2	440.9	441.5	442.2	442.8	442.9	442.4	441.9
170°	444.3	443.6	443.0	442.3	443.0	443.6	444.3	444.9	445.0	444.5	444.0
172.5°	445.8	445.2	444.5	443.9	444.5	445.2	445.8	446.5	446.5	446.0	445.5
175°	447.4	446.7	445.9	445.2	445.9	446.7	447.4	448.1	448.2	447.7	447.2
177.5°	447.6	447.1	446.6	446.1	446.6	447.1	447.6	448.1	448.2	447.8	447.4
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2120.8	2129.4	2142.3	2149.6	2161.9	2169.9	2174.2	2182.1	2186.4	2201.8	2217.7
5°	2002.4	2014.6	2036.1	2056.0	2077.5	2099.7	2115.8	2134.2	2151.0	2180.1	2210.8
7.5°	1866.6	1883.6	1916.8	1948.6	1986.0	2017.4	2045.1	2076.5	2104.6	2146.3	2189.8
10°	1764.8	1794.7	1838.4	1868.3	1917.3	1948.7	1992.4	2026.9	2066.0	2121.1	2170.2
12.5°	1677.1	1713.2	1748.3	1789.8	1833.9	1886.2	1934.2	1978.5	2024.9	2081.9	2139.5
15°	1518.1	1570.2	1624.6	1666.7	1726.5	1781.7	1837.6	1897.4	1954.1	2022.3	2097.4
17.5°	1313.3	1373.7	1465.2	1537.4	1607.6	1662.9	1732.2	1804.5	1871.3	1953.6	2037.2
20°	1220.7	1265.2	1327.2	1424.6	1530.3	1589.3	1659.8	1739.5	1816.1	1905.8	1995.5
22.5°	1146.5	1186.1	1235.9	1311.8	1429.8	1510.2	1583.8	1664.7	1753.6	1845.1	1944.6
25°	1040.6	1068.2	1120.3	1181.6	1262.9	1395.4	1475.9	1557.1	1653.7	1751.8	1865.2
27.5°	961.1	985.9	1019.8	1078.3	1138.7	1233.9	1361.9	1450.5	1546.7	1657.1	1774.8
30°	900.4	929.5	967.1	1008.5	1074.4	1148.7	1276.7	1379.4	1474.4	1587.8	1713.5
32.5°	856.3	879.3	911.3	953.3	1008.2	1079.4	1181.6	1306.4	1399.0	1518.5	1649.7
35°	783.9	810.8	836.8	876.7	921.1	986.2	1063.6	1197.0	1288.9	1406.9	1538.7
37.5°	724.3	740.7	769.5	801.1	848.0	896.6	963.7	1083.3	1182.7	1298.6	1433.5
40°	678.9	699.6	721.1	756.3	794.7	841.4	907.3	996.2	1110.4	1223.8	1355.6
42.5°	634.8	661.0	683.7	707.3	749.3	796.0	849.7	925.1	1041.7	1149.0	1277.1
45°	581.6	598.5	622.2	648.3	682.8	722.6	770.1	836.0	947.9	1040.6	1161.0
47.5°	519.7	544.4	559.9	585.3	618.1	656.1	700.3	757.3	847.8	934.7	1046.3
50°	477.4	502.7	524.9	547.9	577.0	613.8	650.6	705.8	778.6	869.8	974.0
52.5°	441.2	463.5	485.1	508.1	536.6	570.3	605.2	653.7	716.0	799.9	901.0
55°	391.6	405.4	427.6	450.6	475.9	508.1	541.8	582.4	636.0	706.5	788.5
57.5°	340.7	356.6	374.3	397.4	423.0	447.7	478.0	514.8	557.1	620.9	691.1
60°	311.9	324.1	338.7	362.5	386.2	408.4	437.6	468.2	508.1	563.2	623.0
62.5°	280.0	291.7	305.0	325.7	348.8	369.2	394.6	427.1	460.9	511.1	563.5
65°	226.8	243.7	256.7	275.1	294.3	315.7	335.6	361.7	391.6	431.4	478.2
67.5°	188.1	196.6	208.7	225.4	245.1	263.5	282.3	302.7	328.6	359.4	396.5
70°	170.9	174.0	176.3	192.3	210.7	229.1	246.8	265.9	288.1	313.4	345.6
72.5°	150.7	153.7	156.6	163.5	178.2	196.6	214.9	229.1	250.1	271.1	297.2
75°	119.5	124.1	126.4	130.3	135.6	147.9	164.8	178.5	190.8	206.9	227.6
77.5°	91.0	93.6	96.1	100.1	103.5	109.1	118.6	131.0	142.5	151.9	166.1
80°	72.0	72.8	75.9	77.4	82.0	85.8	90.4	100.4	111.9	115.7	125.7
82.5°	54.3	55.0	57.5	59.0	61.2	64.4	70.2	72.8	81.8	86.9	93.2
85°	29.9	29.1	31.4	31.4	33.0	34.5	36.0	39.8	42.1	48.3	49.8
87.5°	10.6	10.5	11.0	10.9	10.8	11.9	12.3	12.8	13.9	15.5	17.8
90°	6.8	6.5	5.9	5.3	4.7	4.2	3.5	2.7	1.9	1.1	0.3
92.5°	7.7	7.5	7.2	6.9	6.6	6.4	6.2	6.3	6.4	6.5	6.5
95°	13.0	12.6	12.1	11.6	11.1	10.6	11.5	13.9	16.3	18.6	21.0
97.5°	17.2	16.9	15.7	14.5	13.4	12.2	15.0	21.7	28.3	35.0	41.7
100°	19.0	18.4	17.2	16.0	14.8	13.5	17.9	27.7	37.5	47.4	57.2
102.5°	19.7	18.9	29.2	39.4	49.6	59.8	66.0	68.1	70.1	72.2	74.3
105°	20.5	19.7	39.3	59.0	78.6	98.2	106.9	104.8	102.6	100.4	98.3
107.5°	26.8	27.6	51.1	74.7	98.2	121.7	132.6	130.9	129.1	127.4	125.6
110°	49.4	56.6	77.3	98.1	118.9	139.6	149.3	147.8	146.3	144.7	143.2



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	116.5	142.7	147.8	153.0	158.1	163.2	165.1	163.8	162.5	161.1	159.8
115°	166.2	199.5	197.7	195.9	194.1	192.3	190.8	189.6	188.4	187.1	185.9
117.5°	212.9	221.0	219.7	218.5	217.3	216.0	214.7	213.4	212.0	210.6	209.3
120°	237.9	237.0	235.7	234.4	233.1	231.8	230.6	229.6	228.5	227.4	226.3
122.5°	252.8	252.3	250.9	249.4	248.0	246.6	245.4	244.2	243.1	242.0	240.8
125°	273.7	273.2	271.8	270.5	269.1	267.8	266.6	265.7	264.7	263.8	262.9
127.5°	292.8	292.1	291.1	290.1	289.0	288.0	287.0	286.0	284.9	283.9	282.8
130°	305.0	304.3	303.5	302.7	301.9	301.1	300.1	299.0	297.8	296.7	295.5
132.5°	317.1	316.4	315.6	314.8	314.0	313.2	312.4	311.4	310.4	309.4	308.5
135°	334.1	333.4	332.7	332.1	331.4	330.8	329.9	328.7	327.6	326.4	325.3
137.5°	349.9	349.2	348.5	347.7	347.0	346.3	345.5	344.7	343.9	343.1	342.3
140°	360.2	359.5	358.8	358.0	357.2	356.4	355.7	355.1	354.5	354.0	353.4
142.5°	369.7	369.1	368.2	367.3	366.4	365.5	364.8	364.3	363.7	363.2	362.7
145°	383.0	382.5	381.3	380.1	378.8	377.6	377.0	377.1	377.2	377.3	377.3
147.5°	394.6	394.3	393.1	391.9	390.6	389.4	389.0	389.2	389.5	389.8	390.1
150°	401.7	401.3	400.1	399.0	397.8	396.7	396.3	396.8	397.3	397.8	398.3
152.5°	408.1	407.7	406.6	405.5	404.4	403.3	403.1	403.6	404.2	404.8	405.3
155°	416.9	416.4	415.6	414.7	413.9	413.0	412.9	413.5	414.2	414.8	415.5
157.5°	424.2	423.7	423.1	422.5	421.9	421.3	421.2	421.8	422.3	422.9	423.4
160°	428.5	428.1	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1
162.5°	432.5	432.0	431.6	431.2	430.8	430.5	430.5	430.9	431.4	431.8	432.2
165°	437.3	436.8	436.6	436.4	436.2	436.0	436.1	436.5	436.9	437.4	437.8
167.5°	441.4	440.9	440.7	440.5	440.3	440.1	440.2	440.6	441.1	441.5	441.9
170°	443.5	443.0	442.8	442.7	442.5	442.4	442.5	443.0	443.4	443.8	444.3
172.5°	445.0	444.5	444.4	444.2	444.1	443.9	444.1	444.5	444.9	445.4	445.8
175°	446.7	446.2	446.1	445.9	445.8	445.6	445.8	446.3	446.8	447.3	447.8
177.5°	447.0	446.6	446.5	446.5	446.4	446.4	446.5	446.9	447.3	447.7	448.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2218.3	2220.1	2232.4	2237.9	2249.0	2253.2	2258.2	2256.9	2256.9	2259.4	2276.5
5°	2223.1	2238.4	2261.4	2283.6	2305.1	2323.4	2335.7	2348.0	2352.6	2374.8	2394.7
7.5°	2215.1	2243.3	2281.3	2315.2	2355.8	2387.5	2413.9	2437.6	2453.9	2486.2	2519.3
10°	2204.7	2244.5	2287.4	2331.1	2387.0	2429.2	2472.1	2505.1	2515.8	2564.1	2591.7
12.5°	2183.8	2237.2	2291.7	2348.3	2403.0	2461.1	2508.3	2541.2	2578.9	2622.3	2673.2
15°	2152.6	2213.9	2285.1	2357.9	2436.1	2506.6	2557.2	2614.6	2656.0	2703.5	2748.0
17.5°	2107.7	2186.6	2277.2	2361.5	2451.9	2527.6	2597.2	2652.3	2681.5	2708.6	2715.2
20°	2072.1	2157.2	2263.7	2363.3	2453.7	2541.1	2610.0	2656.0	2663.7	2664.4	2623.8
22.5°	2033.5	2129.6	2241.0	2343.1	2451.3	2548.4	2602.1	2621.7	2591.3	2539.4	2460.8
25°	1962.5	2073.6	2203.1	2319.6	2437.6	2529.6	2548.0	2513.5	2407.0	2295.1	2153.3
27.5°	1885.6	2010.5	2149.3	2278.8	2404.5	2461.5	2421.8	2297.5	2105.7	1938.9	1736.8
30°	1829.2	1969.4	2105.8	2250.6	2367.1	2391.6	2300.5	2117.3	1893.5	1642.2	1440.7
32.5°	1764.8	1911.8	2061.7	2211.4	2308.9	2285.0	2134.3	1908.9	1646.5	1399.4	1208.9
35°	1672.8	1824.6	1986.3	2136.5	2198.5	2095.1	1869.8	1576.3	1308.1	1077.4	946.4
37.5°	1566.6	1731.9	1900.0	2037.9	2033.5	1861.1	1554.2	1251.2	1025.8	889.4	796.0
40°	1491.2	1658.3	1839.9	1956.4	1906.6	1682.0	1349.5	1063.6	898.9	790.1	721.9
42.5°	1418.9	1586.6	1767.0	1859.5	1772.9	1496.9	1165.6	941.6	805.7	720.8	665.5
45°	1295.8	1472.8	1639.9	1691.2	1536.4	1232.2	942.6	780.1	689.7	626.8	588.5
47.5°	1175.5	1349.6	1502.1	1503.0	1293.7	999.3	795.1	675.1	597.9	549.3	521.4
50°	1101.9	1267.5	1395.4	1375.5	1138.0	888.9	711.1	607.7	543.3	505.8	476.6
52.5°	1019.2	1179.8	1290.6	1233.9	1006.2	782.2	635.7	548.8	495.5	462.8	436.8
55°	898.9	1041.4	1119.6	1033.7	820.7	650.6	537.2	469.0	429.1	401.5	379.3
57.5°	780.7	898.3	947.5	847.5	676.0	539.5	454.4	403.2	363.7	343.9	332.4
60°	706.5	806.9	841.4	731.1	587.8	472.0	402.3	354.8	325.7	312.7	301.2
62.5°	633.6	715.6	729.8	628.7	512.4	413.2	353.3	313.1	293.8	281.4	270.5
65°	525.7	584.7	577.8	496.6	405.4	328.0	284.3	259.8	245.2	227.6	208.4
67.5°	432.8	468.8	447.1	386.2	309.4	254.9	226.4	207.8	189.7	173.0	168.6
70°	374.0	394.6	371.7	315.7	253.6	213.8	190.8	168.6	157.9	154.0	147.1
72.5°	317.6	324.8	299.9	252.0	206.4	177.0	154.6	142.2	136.4	133.2	128.7
75°	238.3	233.0	211.5	174.0	143.3	123.4	116.5	111.9	108.0	105.0	102.7
77.5°	167.4	159.5	140.4	115.9	99.8	90.3	86.1	83.7	81.8	80.3	78.0
80°	125.7	120.3	101.2	82.8	75.9	71.3	69.0	65.9	65.9	64.4	62.1
82.5°	92.0	86.0	69.3	60.7	56.9	54.1	52.4	50.6	50.0	50.3	48.6
85°	48.3	39.1	34.5	33.0	30.7	29.1	29.9	28.4	28.4	28.4	27.6
87.5°	14.9	12.0	11.6	11.1	11.9	12.0	11.5	11.6	12.3	11.8	12.5
90°	1.1	1.9	2.7	3.5	4.2	4.7	5.3	5.9	6.5	6.8	7.2
92.5°	6.5	6.4	6.3	6.2	6.4	6.6	6.9	7.2	7.5	7.7	7.9
95°	18.6	16.3	13.9	11.5	10.6	11.1	11.6	12.1	12.6	13.0	13.3
97.5°	35.0	28.3	21.7	15.0	12.2	13.4	14.5	15.7	16.9	17.2	17.5
100°	47.4	37.5	27.7	17.9	13.5	14.8	16.0	17.2	18.4	19.0	19.6
102.5°	72.2	70.1	68.1	66.0	59.8	49.6	39.4	29.2	18.9	19.7	20.4
105°	100.4	102.6	104.8	106.9	98.2	78.6	59.0	39.3	19.7	20.5	21.3
107.5°	127.4	129.1	130.9	132.6	121.7	98.2	74.7	51.1	27.6	26.8	26.0
110°	144.7	146.3	147.8	149.3	139.6	118.9	98.1	77.3	56.6	49.4	42.2





TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	161.1	162.5	163.8	165.1	163.2	158.1	153.0	147.8	142.7	116.5	90.3
115°	187.1	188.4	189.6	190.8	192.3	194.1	195.9	197.7	199.5	166.2	133.0
117.5°	210.6	212.0	213.4	214.7	216.0	217.3	218.5	219.7	221.0	212.9	204.9
120°	227.4	228.5	229.6	230.6	231.8	233.1	234.4	235.7	237.0	237.9	238.7
122.5°	242.0	243.1	244.2	245.4	246.6	248.0	249.4	250.9	252.3	252.8	253.3
125°	263.8	264.7	265.7	266.6	267.8	269.1	270.5	271.8	273.2	273.7	274.2
127.5°	283.9	284.9	286.0	287.0	288.0	289.0	290.1	291.1	292.1	292.8	293.6
130°	296.7	297.8	299.0	300.1	301.1	301.9	302.7	303.5	304.3	305.0	305.8
132.5°	309.4	310.4	311.4	312.4	313.2	314.0	314.8	315.6	316.4	317.1	317.8
135°	326.4	327.6	328.7	329.9	330.8	331.4	332.1	332.7	333.4	334.1	334.8
137.5°	343.1	343.9	344.7	345.5	346.3	347.0	347.7	348.5	349.2	349.9	350.6
140°	354.0	354.5	355.1	355.7	356.4	357.2	358.0	358.8	359.5	360.2	360.8
142.5°	363.2	363.7	364.3	364.8	365.5	366.4	367.3	368.2	369.1	369.7	370.3
145°	377.3	377.2	377.1	377.0	377.6	378.8	380.1	381.3	382.5	383.0	383.5
147.5°	389.8	389.5	389.2	389.0	389.4	390.6	391.9	393.1	394.3	394.6	395.0
150°	397.8	397.3	396.8	396.3	396.7	397.8	399.0	400.1	401.3	401.7	402.1
152.5°	404.8	404.2	403.6	403.1	403.3	404.4	405.5	406.6	407.7	408.1	408.6
155°	414.8	414.2	413.5	412.9	413.0	413.9	414.7	415.6	416.4	416.9	417.3
157.5°	422.9	422.3	421.8	421.2	421.3	421.9	422.5	423.1	423.7	424.2	424.7
160°	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	428.5	429.0
162.5°	431.8	431.4	430.9	430.5	430.5	430.8	431.2	431.6	432.0	432.5	432.9
165°	437.4	436.9	436.5	436.1	436.0	436.2	436.4	436.6	436.8	437.3	437.8
167.5°	441.5	441.1	440.6	440.2	440.1	440.3	440.5	440.7	440.9	441.4	441.9
170°	443.8	443.4	443.0	442.5	442.4	442.5	442.7	442.8	443.0	443.5	444.0
172.5°	445.4	444.9	444.5	444.1	443.9	444.1	444.2	444.4	444.5	445.0	445.5
175°	447.3	446.8	446.3	445.8	445.6	445.8	445.9	446.1	446.2	446.7	447.2
177.5°	447.7	447.3	446.9	446.5	446.4	446.4	446.5	446.5	446.6	447.0	447.4
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4	2205.4
2.5°	2282.7	2290.6	2294.3	2294.3	2298.6	2296.8	2294.9
5°	2413.9	2428.4	2431.5	2445.3	2455.2	2452.2	2453.7
7.5°	2544.3	2567.7	2590.9	2601.5	2603.1	2609.3	2611.6
10°	2624.6	2643.8	2679.8	2674.4	2701.2	2716.6	2691.3
12.5°	2701.8	2727.7	2752.7	2759.6	2774.8	2779.7	2769.7
15°	2771.7	2785.5	2787.1	2783.2	2787.8	2784.0	2769.4
17.5°	2706.4	2684.1	2638.7	2617.2	2600.2	2575.1	2565.0
20°	2598.5	2532.6	2456.0	2425.4	2389.3	2318.8	2335.7
22.5°	2365.6	2290.5	2213.9	2124.4	2081.6	2014.8	2010.8
25°	2003.1	1873.6	1731.1	1631.5	1573.2	1506.6	1477.4
27.5°	1557.4	1394.4	1277.6	1218.4	1164.6	1111.8	1109.6
30°	1264.4	1141.8	1051.4	1000.8	967.8	945.6	950.2
32.5°	1065.8	981.8	920.8	878.8	854.4	837.7	837.4
35°	871.3	813.8	774.7	757.1	739.5	727.2	728.0
37.5°	745.6	711.1	689.4	669.9	658.9	652.9	649.5
40°	681.2	652.9	636.0	624.5	615.3	606.9	605.4
42.5°	630.4	606.9	590.1	581.0	572.4	566.5	564.9
45°	559.4	540.2	524.9	515.0	511.1	505.8	505.8
47.5°	497.6	478.8	466.8	460.6	454.0	450.4	450.3
50°	456.0	441.4	430.7	426.8	421.5	419.2	418.4
52.5°	418.6	407.7	400.0	397.4	395.1	392.2	392.7
55°	367.8	361.7	358.6	356.3	352.5	347.9	351.0
57.5°	325.1	319.9	311.6	304.4	300.9	297.6	298.9
60°	295.0	284.3	273.6	265.1	262.8	255.9	255.9
62.5°	257.0	242.0	228.8	224.1	221.8	218.6	217.9
65°	197.7	191.6	188.5	185.4	183.9	183.9	182.4
67.5°	163.8	161.4	158.0	157.2	155.7	155.3	154.8
70°	144.8	141.8	140.2	139.5	137.9	138.7	136.4
72.5°	126.4	124.0	123.7	121.7	120.8	120.9	119.2
75°	99.6	99.6	98.9	98.1	96.6	95.8	96.6
77.5°	76.6	76.8	75.4	75.3	75.1	75.3	74.5
80°	61.3	62.1	61.3	60.5	59.8	60.5	59.8
82.5°	48.4	47.4	47.2	47.1	46.9	46.4	46.3
85°	27.6	28.4	27.6	26.8	26.8	26.8	27.6
87.5°	11.9	12.0	12.1	12.1	12.1	12.1	11.6
90°	7.5	7.9	8.2	8.3	8.4	8.6	8.7
92.5°	8.1	8.2	8.4	8.5	8.6	8.6	8.7
95°	13.7	14.0	14.2	14.1	14.0	14.0	13.9
97.5°	17.7	18.0	18.2	18.3	18.4	18.5	18.6
100°	20.2	20.7	21.1	21.2	21.4	21.5	21.7
102.5°	21.2	21.9	22.4	22.6	22.8	23.0	23.2
105°	22.1	22.9	23.4	23.7	24.0	24.3	24.6
107.5°	25.2	24.4	24.1	24.4	24.7	25.0	25.3
110°	35.0	27.8	24.4	24.7	25.0	25.3	25.5



TEST NUMBER: P331735

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	64.1	37.9	24.9	25.1	25.3	25.6	25.8
115°	99.7	66.4	47.2	42.0	36.9	31.7	26.5
117.5°	196.8	188.8	176.3	159.3	142.3	125.3	108.3
120°	239.6	240.4	236.0	226.3	216.6	206.9	197.2
122.5°	253.8	254.3	253.6	251.8	249.9	248.0	246.1
125°	274.7	275.2	275.6	275.8	276.0	276.2	276.4
127.5°	294.3	295.0	295.4	295.5	295.5	295.5	295.6
130°	306.6	307.4	307.8	307.7	307.6	307.6	307.5
132.5°	318.4	319.1	319.4	319.3	319.3	319.2	319.1
135°	335.5	336.2	336.5	336.4	336.2	336.1	335.9
137.5°	351.3	352.0	352.2	352.0	351.8	351.5	351.3
140°	361.5	362.1	362.3	361.9	361.6	361.2	360.8
142.5°	370.9	371.5	371.6	371.2	370.9	370.5	370.1
145°	384.0	384.5	384.6	384.2	383.9	383.5	383.1
147.5°	395.4	395.8	395.8	395.5	395.2	394.9	394.6
150°	402.5	403.0	403.0	402.7	402.3	401.9	401.6
152.5°	409.0	409.4	409.4	408.9	408.5	408.0	407.5
155°	417.7	418.2	418.1	417.5	417.0	416.4	415.8
157.5°	425.2	425.6	425.6	425.0	424.5	423.9	423.4
160°	429.4	429.8	429.8	429.3	428.8	428.3	427.8
162.5°	433.4	433.9	433.9	433.2	432.6	432.0	431.4
165°	438.3	438.8	438.8	438.3	437.8	437.3	436.8
167.5°	442.4	442.9	442.8	442.2	441.5	440.9	440.2
170°	444.5	445.0	444.9	444.3	443.6	443.0	442.3
172.5°	446.0	446.5	446.5	445.8	445.2	444.5	443.9
175°	447.7	448.2	448.1	447.4	446.7	445.9	445.2
177.5°	447.8	448.2	448.1	447.6	447.1	446.6	446.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8

(END OF REPORT)