

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331461-830

Luminaire Tested: **SA2XXDIP-C1005D1080U830-4F0-1E-UDD-D4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331461-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-D4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7769.6 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: General Diffuse


Input Watts (W): 71.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331461-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-D4

Luminous Intensity Polar Plot





TEST NUMBER: P331461-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-D4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	95	90	86	82	87	82	79	75	68	65	63	55	53	51	42	41	40	34
2	86	78	71	66	78	71	66	61	59	54	51	47	44	41	36	34	32	27
3	78	68	60	54	71	62	56	50	51	46	42	41	38	34	32	29	27	23
4	71	60	52	45	65	55	48	42	45	40	35	36	32	29	28	25	23	19
5	65	53	45	39	59	49	41	36	40	35	30	33	28	25	25	22	20	16
6	60	48	39	33	54	44	36	31	36	30	26	29	25	22	23	20	17	14
7	55	43	35	29	50	39	32	27	33	27	23	27	22	19	21	18	15	12
8	51	39	31	25	47	36	29	24	30	24	20	24	20	17	19	16	14	11
9	48	35	28	22	43	32	26	21	27	22	18	22	18	15	18	14	12	10
10	44	32	25	20	41	30	23	19	25	20	16	20	16	14	16	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16091	16091	16091
5°	16172	15491	15432
10°	16069	15033	14865
15°	15848	14548	14266
20°	15567	14030	13691
25°	15292	13528	13167
30°	14902	13015	12643
35°	14508	12517	12274
40°	14092	12094	11903
45°	13700	11715	11587
50°	13277	11373	11276
55°	12834	11004	10959
60°	12292	10623	10624
65°	11728	10173	10227
70°	11096	9693	9797
75°	10286	9222	9401
80°	9006	8739	9001
85°	7780	8321	8687



TEST NUMBER: P331461-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-D4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.4	1.2
10°-20°	270.8	3.5
20°-30°	410.4	5.3
30°-40°	499.9	6.4
40°-50°	537.8	6.9
50°-60°	522.2	6.7
60°-70°	456.0	5.9
70°-80°	351.0	4.5
80°-90°	240.7	3.1
90°-100°	390.0	5.0
100°-110°	891.1	11.5
110°-120°	899.0	11.6
120°-130°	719.3	9.3
130°-140°	560.9	7.2
140°-150°	413.2	5.3
150°-160°	288.1	3.7
160°-170°	169.6	2.2
170°-180°	55.2	0.7
0°-30°	775.7	10.0
0°-40°	1275.5	16.4
0°-60°	2335.5	30.1
0°-90°	3383.3	43.5
90°-120°	2180.0	28.1
90°-150°	3873.4	49.9
90°-180°	4386.0	56.5
0°-180°	7769.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	997	997	997	997	997	
5°	1000	995	987	995	994	95
15°	953	956	956	968	968	268
25°	867	877	890	906	911	398
35°	747	772	799	829	841	467
45°	612	652	702	745	761	473
55°	470	523	596	647	667	420
65°	321	392	477	534	555	318
75°	178	259	351	411	432	188
85°	52	142	234	292	315	56
90°	16	114	228	282	302	12
95°	50	175	595	381	363	50
105°	141	252	936	1623	1425	150
115°	241	322	766	1529	1770	239
125°	331	394	702	1222	1418	295
135°	387	462	661	999	1149	299
145°	440	506	642	805	887	276
155°	500	540	623	705	732	230
165°	545	562	597	633	643	154
175°	568	569	574	581	579	54
180°	569	569	569	569	569	



TEST NUMBER: P331461-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	996.6	996.6	996.6	996.6	996.6	996.6	996.6	996.6	996.6	996.6	996.6
2.5°	1002.5	1001.7	1000.9	1000.1	999.4	998.1	996.3	994.5	992.7	990.9	992.2
5°	999.6	998.6	997.7	996.6	995.7	994.3	992.4	990.4	988.5	986.6	988.5
7.5°	990.6	990.0	989.3	988.7	988.1	987.0	985.5	984.0	982.6	981.1	983.4
10°	983.7	983.1	982.4	981.8	981.1	980.3	979.4	978.4	977.4	976.5	979.0
12.5°	972.1	972.2	972.4	972.5	972.6	972.3	971.7	970.9	970.3	969.5	972.1
15°	953.4	954.0	954.6	955.3	955.9	956.2	956.2	956.2	956.2	956.2	959.1
17.5°	929.1	930.5	931.8	933.1	934.4	935.7	936.7	937.7	938.8	939.8	942.8
20°	912.9	914.5	916.2	917.8	919.4	920.8	922.1	923.3	924.6	926.0	929.4
22.5°	895.6	897.4	899.3	901.2	903.1	904.8	906.6	908.4	910.2	912.0	915.6
25°	866.7	868.9	871.2	873.5	875.7	878.3	881.1	884.0	886.9	889.8	893.6
27.5°	832.0	835.7	839.3	843.0	846.7	850.2	853.6	857.0	860.4	863.8	868.6
30°	808.9	813.0	817.3	821.4	825.6	829.8	834.0	838.1	842.3	846.5	851.6
32.5°	783.4	788.2	792.9	797.6	802.2	807.0	812.0	816.9	821.9	826.8	832.7
35°	746.8	752.2	757.7	763.2	768.6	774.4	780.5	786.6	792.7	798.8	805.9
37.5°	706.9	713.2	719.5	725.8	732.1	739.1	747.1	755.0	762.9	770.8	778.6
40°	680.3	687.4	694.5	701.5	708.6	716.4	725.1	733.8	742.4	751.1	759.5
42.5°	655.0	661.9	669.0	676.1	683.2	691.6	701.6	711.6	721.5	731.5	740.6
45°	612.5	621.1	629.8	638.5	647.1	657.0	668.4	679.6	690.8	702.0	712.0
47.5°	570.6	580.0	589.5	598.9	608.3	619.6	632.8	645.9	659.1	672.2	682.7
50°	541.7	551.7	561.6	571.6	581.5	593.7	608.1	622.5	637.0	651.5	662.4
52.5°	514.0	524.4	534.9	545.4	555.8	568.6	583.8	599.1	614.3	629.5	640.6
55°	469.5	481.0	492.6	504.2	515.7	529.8	546.5	563.2	579.9	596.5	608.1
57.5°	425.6	438.6	451.6	464.7	477.7	492.7	509.7	526.7	543.8	560.7	573.2
60°	394.4	408.1	422.0	435.7	449.6	465.6	483.9	502.2	520.5	538.8	551.0
62.5°	366.6	380.9	395.2	409.5	423.9	440.2	458.5	476.7	495.1	513.4	526.3
65°	320.7	336.4	352.1	367.9	383.6	401.0	419.9	438.8	457.7	476.6	489.8
67.5°	278.5	294.9	311.3	327.8	344.2	362.1	381.5	401.0	420.3	439.7	453.0
70°	248.5	265.1	281.8	298.5	315.2	333.5	353.5	373.3	393.2	413.1	426.9
72.5°	220.7	237.9	255.1	272.3	289.5	308.2	328.4	348.6	368.7	388.9	402.4
75°	177.7	195.7	213.6	231.6	249.6	268.8	289.4	309.9	330.5	351.0	364.8
77.5°	136.1	154.9	173.7	192.5	211.3	231.1	252.0	272.9	293.7	314.6	328.4
80°	108.3	127.9	147.5	167.1	186.6	206.9	227.7	248.6	269.5	290.3	303.8
82.5°	85.2	104.5	123.9	143.2	162.5	182.8	203.9	225.0	246.1	267.2	280.7
85°	52.0	71.9	91.8	111.7	131.6	151.8	172.4	192.9	213.5	234.0	247.5
87.5°	28.6	48.4	68.3	87.9	107.4	128.0	149.6	171.6	193.5	214.3	227.2
90°	15.6	37.4	60.4	81.2	102.1	124.9	150.9	179.2	206.2	227.9	239.7
92.5°	26.7	49.9	75.1	97.3	122.1	150.9	195.4	250.0	300.9	322.6	313.1
95°	49.9	69.4	95.4	120.4	152.9	196.4	266.0	380.5	526.8	595.3	553.8
97.5°	72.5	91.9	116.9	145.2	178.7	224.5	306.2	457.4	687.0	886.5	934.2
100°	94.4	109.6	131.3	160.7	194.4	240.1	316.0	467.6	722.1	1009.5	1179.0
102.5°	113.4	126.7	147.4	175.8	209.3	254.2	325.3	461.5	697.9	1005.7	1265.3
105°	140.8	154.5	171.4	197.2	230.6	274.3	342.4	456.6	653.9	935.6	1238.0
107.5°	172.0	183.0	197.9	220.5	251.8	294.4	360.2	461.2	626.6	861.5	1129.6
110°	191.9	202.7	215.7	236.4	265.8	308.6	372.5	467.0	616.4	824.8	1061.8



TEST NUMBER: P331461-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	211.2	220.9	233.8	252.5	280.0	322.8	384.3	473.6	609.9	797.5	1011.6
115°	241.2	250.2	260.3	276.9	302.4	340.9	402.5	483.7	604.4	765.5	948.1
117.5°	270.8	277.5	286.4	300.3	323.7	362.1	419.1	495.0	601.5	743.4	903.3
120°	290.1	295.8	303.6	314.8	337.9	375.7	431.2	503.1	600.3	730.3	878.4
122.5°	308.5	312.5	319.6	330.8	353.3	391.1	443.2	510.0	600.3	719.9	856.3
125°	331.4	334.7	341.2	354.4	376.3	412.1	461.8	521.3	599.5	701.7	823.1
127.5°	350.6	354.7	363.5	377.7	398.4	433.9	480.5	533.0	600.5	687.6	792.3
130°	362.0	366.1	376.7	391.7	413.3	447.1	492.2	540.5	602.1	678.9	771.9
132.5°	372.5	377.5	389.0	404.8	427.3	460.4	502.2	548.1	603.7	671.1	754.3
135°	386.8	391.2	404.4	420.8	446.0	478.2	516.5	558.0	605.0	660.8	729.9
137.5°	401.7	406.9	420.0	437.4	462.4	491.5	527.5	564.7	605.9	652.2	710.5
140°	413.1	417.2	430.0	447.2	471.0	499.6	533.1	567.7	605.6	646.7	698.9
142.5°	424.5	427.7	439.6	456.9	479.8	506.3	538.5	571.7	606.3	644.4	689.5
145°	440.2	444.5	455.5	471.9	493.8	517.9	547.4	578.2	608.8	641.6	678.6
147.5°	458.5	461.8	472.3	487.5	505.7	527.1	554.9	581.8	609.6	637.7	668.6
150°	470.8	474.1	482.9	497.1	513.5	533.2	558.5	583.6	608.8	635.1	661.3
152.5°	483.1	484.7	493.3	505.9	521.4	539.3	561.9	584.5	607.0	630.7	655.2
155°	500.4	501.4	508.0	520.1	532.2	548.6	567.1	585.8	604.4	623.0	643.9
157.5°	514.8	515.9	521.2	531.7	541.3	555.2	570.9	585.8	599.4	615.1	633.1
160°	524.4	525.6	529.9	538.7	547.4	559.5	572.7	585.8	596.7	609.9	625.2
162.5°	534.1	533.5	537.8	544.8	552.7	562.1	573.5	584.9	594.1	605.5	618.2
165°	545.3	544.2	546.4	552.9	558.5	565.0	574.9	582.5	589.1	596.7	606.6
167.5°	554.5	553.2	555.2	559.3	563.3	567.4	574.6	581.0	584.0	589.1	595.2
170°	560.6	558.5	559.5	562.8	565.0	568.3	573.7	579.2	581.4	584.7	589.1
172.5°	564.1	562.8	562.1	565.4	566.8	569.1	572.9	576.6	577.9	579.5	583.0
175°	568.3	567.1	566.1	568.3	568.3	569.4	571.6	573.7	572.7	573.7	574.9
177.5°	570.2	568.4	567.6	569.4	569.4	569.4	570.2	572.0	570.2	569.4	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331461-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	996.6	996.6	996.6	996.6	996.6	996.6	996.6	996.6
2.5°	993.4	994.8	996.1	996.5	995.9	995.4	994.9	994.4
5°	990.4	992.4	994.3	995.0	994.8	994.5	994.1	993.8
7.5°	985.7	988.1	990.3	991.4	991.0	990.7	990.3	990.0
10°	981.6	984.2	986.7	987.9	987.5	987.2	986.9	986.6
12.5°	974.7	977.2	979.8	980.9	980.6	980.2	980.0	979.7
15°	962.1	964.9	967.8	969.1	968.7	968.5	968.1	967.8
17.5°	945.8	948.9	951.9	953.4	953.4	953.4	953.4	953.4
20°	932.9	936.5	940.0	941.8	941.8	941.8	941.8	941.8
22.5°	919.1	922.7	926.1	928.2	928.7	929.3	929.7	930.3
25°	897.5	901.4	905.2	907.6	908.6	909.6	910.5	911.4
27.5°	873.5	878.4	883.4	886.1	886.8	887.5	888.3	888.9
30°	856.8	861.9	867.0	870.1	871.0	871.9	873.0	873.9
32.5°	838.7	844.5	850.5	854.2	856.0	857.7	859.5	861.2
35°	812.9	820.0	827.1	831.7	834.0	836.2	838.5	840.7
37.5°	786.5	794.3	802.1	807.2	809.5	812.0	814.4	816.7
40°	767.8	776.2	784.5	790.1	793.1	795.9	798.8	801.7
42.5°	749.7	758.8	768.0	773.9	776.8	779.8	782.6	785.5
45°	721.9	731.9	741.8	748.4	751.6	754.8	758.0	761.2
47.5°	693.1	703.4	713.9	720.9	724.3	727.9	731.4	735.0
50°	673.3	684.2	695.1	702.4	705.9	709.4	712.9	716.4
52.5°	651.9	663.0	674.2	681.6	685.4	689.3	693.1	696.8
55°	619.7	631.2	642.8	650.6	654.8	659.0	663.2	667.3
57.5°	585.7	598.1	610.6	618.9	623.1	627.4	631.6	635.8
60°	563.2	575.4	587.6	596.0	600.4	604.9	609.4	613.9
62.5°	539.3	552.2	565.2	573.8	578.1	582.3	586.5	590.8
65°	503.0	516.1	529.3	538.0	542.2	546.3	550.5	554.7
67.5°	466.3	479.6	492.9	501.7	506.1	510.4	514.8	519.2
70°	440.7	454.5	468.3	477.1	481.0	484.8	488.7	492.6
72.5°	415.9	429.5	443.0	452.1	456.8	461.4	466.0	470.6
75°	378.6	392.4	406.2	415.2	419.3	423.6	427.7	431.9
77.5°	342.0	355.8	369.6	378.7	383.1	387.7	392.2	396.6
80°	317.3	330.8	344.3	353.3	357.8	362.2	366.7	371.3
82.5°	294.2	307.6	321.1	330.0	334.2	338.5	342.7	346.9
85°	261.0	274.5	287.9	296.9	301.4	305.9	310.4	314.9
87.5°	240.1	252.7	266.3	275.0	279.2	283.3	287.4	291.5
90°	251.4	262.0	277.1	286.5	290.4	294.2	298.0	301.9
92.5°	301.0	299.9	303.3	304.7	307.7	308.0	312.8	314.9
95°	477.4	422.8	389.0	373.0	362.6	357.6	358.3	363.2
97.5°	846.9	737.0	630.4	559.2	510.7	487.5	475.3	469.9
100°	1167.9	1044.0	905.9	781.1	693.7	650.2	622.0	605.8
102.5°	1375.6	1356.6	1258.5	1125.7	1030.5	953.7	917.6	894.4
105°	1477.1	1612.0	1637.5	1608.7	1544.4	1480.0	1436.4	1424.7
107.5°	1382.0	1579.0	1703.7	1763.9	1775.9	1775.8	1769.9	1753.0
110°	1303.1	1509.3	1659.7	1756.4	1807.0	1831.4	1844.7	1847.2



TEST NUMBER: P331461-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-D4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	1230.1	1428.5	1588.6	1698.4	1767.4	1805.7	1827.9	1837.3
115°	1138.4	1316.7	1469.8	1589.1	1670.4	1724.3	1756.2	1769.6
117.5°	1066.3	1223.9	1363.5	1475.6	1558.1	1614.7	1647.9	1659.5
120°	1028.6	1173.4	1298.4	1404.3	1484.5	1539.5	1574.8	1589.2
122.5°	997.5	1130.6	1249.2	1345.2	1416.9	1470.6	1501.8	1514.0
125°	951.1	1072.6	1177.6	1265.6	1331.9	1376.4	1406.7	1418.3
127.5°	905.4	1015.4	1114.3	1195.4	1253.6	1295.4	1321.9	1331.7
130°	876.0	977.9	1072.1	1149.5	1205.7	1245.6	1270.0	1281.3
132.5°	847.5	942.2	1029.2	1102.0	1157.3	1197.1	1219.8	1230.3
135°	807.9	886.8	965.9	1031.8	1081.5	1120.2	1142.5	1149.4
137.5°	774.4	840.7	904.0	961.5	1006.6	1039.9	1059.3	1068.1
140°	753.4	811.1	866.5	918.2	955.2	985.6	1003.9	1012.5
142.5°	736.7	785.5	832.9	876.1	911.1	938.6	955.0	957.9
145°	714.4	752.5	788.3	821.9	849.8	870.0	882.6	887.4
147.5°	697.8	726.5	753.3	776.9	799.4	815.1	823.3	826.0
150°	687.6	711.7	734.7	754.4	770.8	784.0	790.5	791.6
152.5°	678.0	700.3	719.8	736.9	749.8	761.2	766.0	766.2
155°	664.6	682.1	698.5	710.6	722.6	730.3	734.7	732.5
157.5°	649.0	663.7	677.5	686.9	695.5	701.8	703.8	703.8
160°	639.4	651.5	663.5	671.2	678.8	684.3	685.4	685.4
162.5°	629.8	640.1	650.4	656.3	663.9	667.7	668.7	667.9
165°	615.4	623.0	630.7	635.1	639.4	643.9	643.9	642.7
167.5°	601.5	607.5	612.7	616.7	618.6	621.0	620.9	619.5
170°	594.6	597.9	602.2	604.4	605.5	608.8	607.7	605.5
172.5°	586.6	589.1	592.6	593.9	595.0	596.5	595.4	594.1
175°	578.2	579.2	580.3	581.4	581.4	582.5	581.4	579.2
177.5°	572.0	572.0	572.9	572.9	572.9	572.9	572.0	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4

(END OF REPORT)