

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331740

Luminaire Tested: **SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331740  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 330 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4763.2 lumens  
Efficiency: N/A  
Efficacy: 95.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331740

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331740

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	104	99	96	92	98	95	91	88	86	83	81	77	75	74	70	68	67	63
2	95	88	82	77	90	84	78	74	76	72	68	69	65	63	62	60	57	54
3	87	78	71	65	83	74	68	62	68	62	58	61	57	54	56	52	50	47
4	80	69	62	56	76	66	59	54	61	55	50	55	51	47	50	46	43	41
5	74	62	54	48	70	60	52	47	55	49	44	50	45	41	46	42	38	36
6	68	56	48	42	65	54	47	41	50	43	39	46	40	36	42	37	34	32
7	64	51	43	38	60	49	42	37	45	39	35	42	36	33	38	34	31	28
8	59	47	39	34	56	45	38	33	42	35	31	38	33	29	35	31	28	26
9	55	43	36	30	53	41	34	30	38	32	28	36	30	27	33	28	25	23
10	52	40	32	28	49	38	32	27	36	30	26	33	28	24	31	26	23	21

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	27341	27341	27341
5°	27446	27000	27149
10°	27237	26558	26332
15°	26924	25770	25028
20°	26490	24646	23409
25°	26045	23370	21841
30°	25430	22057	19829
35°	24829	20631	18065
40°	24226	19155	16021
45°	23516	17497	14173
50°	22790	15822	12356
55°	22044	14021	10612
60°	21180	12126	8809
65°	20199	10189	8023
70°	19029	8393	7378
75°	17592	7648	6881
80°	15528	6843	6267
85°	12208	5391	5391



TEST NUMBER: P331740

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	158.5	3.3
10°-20°	435.2	9.1
20°-30°	611.2	12.8
30°-40°	666.5	14.0
40°-50°	612.8	12.9
50°-60°	481.3	10.1
60°-70°	313.8	6.6
70°-80°	161.8	3.4
80°-90°	43.6	0.9
90°-100°	73.5	1.5
100°-110°	249.3	5.2
110°-120°	264.8	5.6
120°-130°	218.0	4.6
130°-140°	175.1	3.7
140°-150°	132.3	2.8
150°-160°	93.0	2.0
160°-170°	54.7	1.1
170°-180°	17.8	0.4
0°-30°	1204.9	25.3
0°-40°	1871.4	39.3
0°-60°	2965.4	62.3
0°-90°	3484.6	73.2
90°-120°	587.6	12.3
90°-150°	1113.0	23.4
90°-180°	1279.0	26.9
0°-180°	4763.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1693	1693	1693	1693	1693	
5°	1693	1685	1666	1679	1675	160
15°	1611	1592	1542	1513	1497	454
25°	1462	1410	1312	1251	1226	672
35°	1260	1178	1047	954	916	788
45°	1030	924	766	661	621	795
55°	783	661	498	410	377	700
65°	529	404	267	217	210	524
75°	282	178	123	112	110	298
85°	66	35	29	29	29	78
90°	0	5	12	12	12	3
95°	12	30	138	52	40	13
105°	43	65	262	468	398	46
115°	76	96	219	452	524	75
125°	106	125	211	366	425	94
135°	124	148	208	308	352	96
145°	142	163	207	257	281	89
155°	162	174	201	227	236	74
165°	176	181	193	204	207	50
175°	183	184	185	187	187	17
180°	184	184	184	184	184	



TEST NUMBER: P331740

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1699.6	1698.2	1696.8	1695.5	1694.1	1691.9	1688.9	1686.0	1683.0	1680.0	1682.7
5°	1693.4	1691.7	1690.0	1688.3	1686.6	1683.6	1679.1	1674.7	1670.3	1665.9	1668.9
7.5°	1676.0	1673.9	1671.8	1669.6	1667.5	1663.9	1658.7	1653.5	1648.4	1643.2	1644.1
10°	1661.3	1658.9	1656.5	1654.1	1651.7	1647.1	1640.3	1633.5	1626.7	1619.9	1618.9
12.5°	1642.9	1639.9	1637.0	1634.1	1631.2	1625.3	1616.6	1607.9	1599.2	1590.5	1588.6
15°	1610.7	1606.9	1603.2	1599.4	1595.7	1588.0	1576.5	1564.9	1553.3	1541.7	1535.3
17.5°	1571.1	1565.4	1559.7	1554.0	1548.3	1538.0	1523.1	1508.3	1493.4	1478.6	1470.9
20°	1541.7	1534.9	1528.1	1521.3	1514.5	1502.6	1485.5	1468.5	1451.5	1434.4	1425.9
22.5°	1509.8	1502.2	1494.6	1487.0	1479.3	1465.9	1446.7	1427.5	1408.3	1389.1	1378.1
25°	1462.0	1451.1	1440.2	1429.3	1418.4	1401.8	1379.3	1356.8	1334.3	1311.8	1297.9
27.5°	1404.4	1392.6	1380.7	1368.9	1357.0	1338.4	1313.1	1287.7	1262.4	1237.1	1220.8
30°	1364.0	1351.0	1338.1	1325.1	1312.2	1292.1	1264.8	1237.6	1210.4	1183.1	1165.7
32.5°	1324.7	1309.6	1294.5	1279.4	1264.2	1242.8	1215.0	1187.2	1159.4	1131.6	1111.8
35°	1259.7	1242.4	1225.0	1207.6	1190.3	1166.6	1136.6	1106.7	1076.7	1046.7	1025.3
37.5°	1194.8	1175.7	1156.6	1137.5	1118.5	1093.0	1061.0	1029.1	997.1	965.2	941.6
40°	1149.4	1129.0	1108.5	1088.1	1067.7	1040.9	1007.9	974.9	941.8	908.8	884.6
42.5°	1102.8	1081.3	1059.8	1038.2	1016.7	988.9	954.8	920.6	886.5	852.4	827.4
45°	1029.9	1007.0	984.2	961.4	938.6	909.3	873.5	837.8	802.0	766.3	742.1
47.5°	958.7	934.6	910.4	886.2	862.0	831.5	794.6	757.6	720.7	683.8	659.8
50°	907.3	883.1	858.9	834.7	810.5	779.7	742.3	704.8	667.3	629.9	606.4
52.5°	857.0	831.7	806.5	781.2	755.9	725.0	688.3	651.7	615.0	578.4	555.7
55°	783.1	756.6	730.0	703.4	676.9	645.2	608.4	571.6	534.9	498.1	477.6
57.5°	707.4	680.2	652.9	625.7	598.4	567.1	531.8	496.4	461.1	425.7	407.0
60°	655.9	628.7	601.4	574.2	546.9	515.8	480.7	445.6	410.5	375.5	358.1
62.5°	605.7	578.4	551.2	523.9	496.7	466.3	432.9	399.4	366.0	332.6	316.0
65°	528.7	501.1	473.6	446.0	418.4	389.3	358.6	328.0	297.3	266.7	255.1
67.5°	454.5	427.2	399.8	372.4	345.0	317.5	290.0	262.4	234.8	207.2	201.9
70°	403.1	376.5	349.9	323.4	296.8	271.8	248.3	224.8	201.3	177.8	174.4
72.5°	354.0	328.5	303.1	277.6	252.1	229.9	211.1	192.2	173.3	154.5	151.6
75°	282.0	258.1	234.3	210.5	186.6	168.9	157.3	145.8	134.2	122.6	120.2
77.5°	211.2	190.3	169.4	148.5	127.5	114.3	108.7	103.1	97.5	92.0	90.6
80°	167.0	149.7	132.3	114.9	97.6	87.2	83.8	80.4	77.0	73.6	72.2
82.5°	126.6	113.0	99.5	85.9	72.4	64.4	62.1	59.8	57.5	55.2	54.4
85°	65.9	58.7	51.6	44.4	37.3	33.2	32.2	31.2	30.1	29.1	29.1
87.5°	19.7	17.7	15.8	13.8	11.7	10.9	11.2	11.7	12.1	12.2	11.9
90°	0.4	1.4	2.8	3.5	4.2	5.3	7.1	9.5	11.7	12.0	11.7
92.5°	4.3	6.2	8.8	10.3	12.7	16.0	24.0	35.3	45.3	45.9	38.8
95°	12.4	13.8	17.3	20.5	26.1	34.6	50.9	81.6	122.6	138.5	121.2
97.5°	20.1	22.0	25.8	30.6	37.1	46.7	67.1	110.0	178.1	236.4	248.0
100°	27.2	28.3	31.4	37.1	44.2	54.1	72.8	115.9	192.2	279.1	330.0
102.5°	33.7	34.5	37.7	43.3	50.7	60.6	77.9	116.2	186.8	280.5	360.5
105°	43.1	44.5	47.0	52.3	60.1	70.0	86.6	118.0	176.3	261.8	355.8
107.5°	53.3	54.4	56.8	61.7	69.4	79.4	95.5	122.9	171.1	241.7	324.8
110°	60.1	61.5	63.6	68.2	75.6	85.9	101.4	126.8	170.0	232.1	305.3



TEST NUMBER: P331740

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	66.3	67.7	70.1	74.4	81.5	92.1	107.1	131.1	170.2	225.9	291.7
115°	76.0	77.7	79.9	84.1	91.2	100.7	115.9	137.4	171.7	219.1	274.9
117.5°	86.0	87.4	89.5	93.3	100.1	110.0	124.0	144.2	174.3	215.7	264.3
120°	92.2	93.6	95.8	98.9	106.0	115.9	129.7	148.8	176.0	213.8	258.6
122.5°	98.2	99.3	101.4	104.9	111.9	122.1	135.0	152.7	177.9	212.6	253.8
125°	106.0	107.1	109.2	113.4	120.5	130.4	143.1	159.0	180.9	210.6	247.0
127.5°	112.2	113.6	116.6	121.3	128.0	138.2	150.6	164.9	183.9	209.4	240.6
130°	115.9	117.3	120.8	125.8	132.9	142.7	155.1	168.5	186.2	208.8	236.4
132.5°	119.3	121.0	124.8	130.0	137.4	147.3	159.1	172.2	188.5	208.5	233.0
135°	124.4	125.8	130.0	135.3	143.5	153.3	164.7	177.0	191.2	208.1	228.2
137.5°	129.2	130.9	135.1	140.8	148.8	158.0	169.2	180.7	193.6	208.0	224.9
140°	132.9	134.3	138.5	144.2	151.9	161.1	171.7	182.7	194.7	207.8	222.9
142.5°	136.5	137.7	141.6	147.3	154.8	163.4	173.7	184.4	195.5	207.8	221.0
145°	142.0	143.5	147.0	152.3	159.4	167.1	176.7	186.6	196.4	207.0	218.4
147.5°	148.0	149.0	152.4	157.3	163.2	170.1	179.1	187.8	196.7	205.8	215.7
150°	151.9	153.0	155.8	160.4	165.7	172.1	180.2	188.3	196.4	204.9	213.4
152.5°	155.9	156.4	159.2	163.2	168.3	174.0	181.3	188.6	195.9	203.5	211.4
155°	161.5	161.8	163.9	167.8	171.7	177.0	183.0	189.0	195.0	201.0	207.8
157.5°	166.1	166.5	168.2	171.6	174.7	179.1	184.2	189.0	193.4	198.5	204.3
160°	169.2	169.6	171.0	173.8	176.7	180.6	184.8	189.0	192.6	196.8	201.7
162.5°	172.4	172.1	173.6	175.8	178.4	181.4	185.1	188.7	191.7	195.4	199.5
165°	176.0	175.6	176.3	178.4	180.2	182.3	185.5	188.0	190.1	192.6	195.7
167.5°	178.9	178.5	179.1	180.5	181.8	183.1	185.4	187.5	188.5	190.1	192.1
170°	180.9	180.2	180.6	181.6	182.3	183.4	185.1	186.9	187.6	188.7	190.1
172.5°	182.0	181.6	181.4	182.5	182.9	183.7	184.9	186.1	186.5	187.0	188.1
175°	183.4	183.0	182.7	183.4	183.4	183.7	184.4	185.1	184.8	185.1	185.5
177.5°	184.0	183.4	183.2	183.7	183.7	183.7	184.0	184.6	184.0	183.7	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7



TEST NUMBER: P331740

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1685.4	1688.1	1690.9	1691.9	1691.4	1690.9	1690.3	1689.8
5°	1672.0	1675.1	1678.1	1679.1	1678.1	1677.1	1676.1	1675.1
7.5°	1644.9	1645.8	1646.7	1646.3	1644.5	1642.7	1641.0	1639.2
10°	1617.8	1616.8	1615.8	1614.3	1612.2	1610.2	1608.1	1606.1
12.5°	1586.8	1584.9	1583.1	1580.5	1577.1	1573.7	1570.3	1566.9
15°	1528.8	1522.3	1515.8	1510.9	1507.5	1504.1	1500.7	1497.3
17.5°	1463.2	1455.5	1447.8	1441.0	1435.2	1429.3	1423.4	1417.6
20°	1417.4	1408.9	1400.4	1392.4	1384.9	1377.4	1369.9	1362.4
22.5°	1367.2	1356.2	1345.2	1336.9	1331.4	1325.8	1320.2	1314.6
25°	1283.9	1270.0	1256.0	1246.5	1241.3	1236.2	1231.1	1226.0
27.5°	1204.5	1188.2	1171.9	1159.7	1151.6	1143.5	1135.4	1127.3
30°	1148.4	1131.0	1113.6	1100.4	1091.2	1082.0	1072.8	1063.6
32.5°	1092.0	1072.2	1052.3	1038.1	1029.5	1020.8	1012.1	1003.5
35°	1003.8	982.4	960.9	946.4	938.9	931.4	923.9	916.5
37.5°	917.9	894.3	870.6	854.5	846.0	837.4	828.8	820.2
40°	860.4	836.2	812.1	795.6	786.7	777.8	769.0	760.1
42.5°	802.4	777.4	752.4	735.6	727.0	718.4	709.9	701.3
45°	717.9	693.7	669.5	653.4	645.2	637.0	628.8	620.7
47.5°	635.7	611.7	587.6	571.9	564.5	557.1	549.6	542.2
50°	582.9	559.4	535.9	520.5	513.4	506.2	499.1	491.9
52.5°	533.0	510.3	487.7	473.0	466.4	459.8	453.2	446.6
55°	457.2	436.8	416.3	402.9	396.4	389.9	383.5	377.0
57.5°	388.3	369.5	350.8	338.7	333.3	327.8	322.4	316.9
60°	340.7	323.4	306.0	294.6	289.1	283.7	278.2	272.8
62.5°	299.5	282.9	266.4	256.4	253.2	249.9	246.6	243.4
65°	243.5	231.9	220.3	214.0	213.0	212.0	211.0	210.0
67.5°	196.6	191.3	185.9	182.7	181.7	180.6	179.5	178.4
70°	171.0	167.6	164.2	161.8	160.4	159.0	157.7	156.3
72.5°	148.8	145.9	143.0	141.2	140.4	139.6	138.7	137.9
75°	117.8	115.5	113.1	111.7	111.4	111.0	110.7	110.3
77.5°	89.2	87.9	86.5	85.5	85.0	84.5	83.9	83.4
80°	70.8	69.5	68.1	67.4	67.4	67.4	67.4	67.4
82.5°	53.5	52.7	51.9	51.5	51.5	51.5	51.5	51.5
85°	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
87.5°	11.5	11.1	11.0	10.9	10.9	10.9	10.9	10.9
90°	11.3	10.6	11.3	11.7	11.7	11.7	11.7	11.7
92.5°	30.8	26.4	23.5	21.3	21.0	19.9	20.1	19.6
95°	92.6	71.0	56.2	48.4	43.8	41.0	39.9	40.3
97.5°	216.0	176.7	138.5	113.0	96.1	87.4	82.3	79.3
100°	322.6	278.8	230.4	187.6	158.3	143.1	132.9	126.5
102.5°	392.4	382.5	347.1	301.8	269.9	244.0	231.2	222.6
105°	429.3	469.2	473.8	462.2	440.2	418.3	403.1	398.2
107.5°	402.7	462.9	499.6	516.7	519.5	518.3	515.2	508.7
110°	379.8	443.1	488.3	517.3	532.5	539.2	542.4	542.0





TEST NUMBER: P331740

CATALOG NUMBER: SA2XXRDIP-C1005D330U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	358.9	419.6	467.9	501.2	522.3	533.5	539.5	541.4
115°	333.2	387.6	433.9	470.3	495.4	511.6	520.8	524.0
117.5°	313.8	361.6	403.6	437.7	463.3	480.5	490.1	492.8
120°	304.2	348.0	385.5	417.6	442.4	459.0	469.2	472.8
122.5°	296.6	336.7	372.2	401.2	423.4	439.8	448.9	451.8
125°	285.5	321.9	353.0	379.5	400.0	413.4	422.2	425.1
127.5°	274.5	307.5	336.8	361.2	379.1	391.7	399.3	401.6
130°	267.5	297.9	325.8	349.1	366.4	378.4	385.5	388.3
132.5°	260.7	288.8	314.5	336.4	353.4	365.4	371.9	374.5
135°	251.2	274.5	297.9	317.6	332.8	344.5	350.9	352.3
137.5°	243.7	263.2	281.7	298.9	312.8	322.8	328.4	330.5
140°	238.8	255.8	272.1	287.6	298.9	308.1	313.4	315.5
142.5°	234.9	249.3	263.3	276.3	287.0	295.4	300.1	300.5
145°	229.3	241.0	251.9	262.2	270.6	276.7	280.2	281.2
147.5°	225.0	234.2	242.7	250.2	257.2	262.0	264.4	265.1
150°	221.9	229.7	237.1	243.4	248.7	253.0	255.1	255.5
152.5°	218.8	226.0	232.3	237.8	242.0	245.6	247.2	247.3
155°	214.5	220.1	225.4	229.3	233.2	235.7	237.1	236.4
157.5°	209.5	214.2	218.6	221.7	224.4	226.5	227.1	227.1
160°	206.3	210.2	214.1	216.6	219.1	220.8	221.2	221.2
162.5°	203.2	206.6	209.9	211.8	214.3	215.5	215.8	215.5
165°	198.6	201.0	203.5	204.9	206.3	207.8	207.8	207.4
167.5°	194.1	196.0	197.7	199.0	199.6	200.4	200.3	199.9
170°	191.9	192.9	194.3	195.0	195.4	196.4	196.1	195.4
172.5°	189.3	190.1	191.2	191.6	192.0	192.5	192.1	191.7
175°	186.6	186.9	187.3	187.6	187.6	188.0	187.6	186.9
177.5°	184.6	184.6	184.9	184.9	184.9	184.9	184.6	184.0
180°	183.7	183.7	183.7	183.7	183.7	183.7	183.7	183.7

(END OF REPORT)