

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331463-830

Luminaire Tested: **SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331463-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7454.9 lumens  
Efficiency: N/A  
Efficacy: 104.0 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 71.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331463-830  
CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331463-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51	51	51
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	51	49	48	43	43	43
2	89	82	76	70	82	76	70	66	65	61	57	54	51	49	45	43	41	36	36	36
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35	31	31	31
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26	26	26
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23	23	23
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23	20	20	20
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20	18	18	18
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16	16	16
9	50	38	31	26	47	36	29	24	31	25	22	27	22	19	22	19	17	14	14	14
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	17	15	13	13	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24254	24254	24254
5°	24347	23995	24136
10°	24202	23753	23871
15°	23903	23445	23422
20°	23479	22983	22957
25°	23058	22413	22413
30°	22514	21893	21705
35°	22007	21268	20954
40°	21372	20643	20244
45°	20747	20021	19527
50°	20065	19376	18686
55°	19356	18624	17931
60°	18564	17725	17073
65°	17712	16829	16061
70°	16636	15753	15002
75°	15140	14504	14148
80°	13436	13036	12357
85°	10967	10448	9355



TEST NUMBER: P331463-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.3	1.9
10°-20°	397.5	5.3
20°-30°	584.2	7.8
30°-40°	678.6	9.1
40°-50°	677.9	9.1
50°-60°	591.2	7.9
60°-70°	437.1	5.9
70°-80°	247.6	3.3
80°-90°	71.8	1.0
90°-100°	82.2	1.1
100°-110°	255.3	3.4
110°-120°	436.4	5.9
120°-130°	573.9	7.7
130°-140°	644.2	8.6
140°-150°	631.6	8.5
150°-160°	529.8	7.1
160°-170°	351.4	4.7
170°-180°	122.8	1.6
0°-30°	1123.0	15.1
0°-40°	1801.6	24.2
0°-60°	3070.7	41.2
0°-90°	3827.1	51.3
90°-120°	774.0	10.4
90°-150°	2623.7	35.2
90°-180°	3628.0	48.7
0°-180°	7454.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1502	1496	1480	1491	1489	142
15°	1430	1421	1403	1408	1401	402
25°	1294	1282	1258	1261	1258	595
35°	1116	1102	1079	1070	1063	697
45°	909	898	877	862	855	701
55°	688	678	662	645	637	615
65°	464	455	440	428	420	458
75°	243	240	232	225	227	259
85°	59	58	56	52	50	68
90°	1	15	38	36	37	6
95°	57	67	70	70	68	65
105°	235	239	241	243	243	249
115°	438	444	442	441	438	433
125°	637	646	644	641	639	569
135°	824	836	839	837	834	637
145°	1001	1008	1015	1016	1012	625
155°	1144	1147	1151	1156	1153	526
165°	1245	1244	1244	1251	1246	351
175°	1295	1292	1290	1297	1291	123
180°	1297	1297	1297	1297	1297	



TEST NUMBER: P331463-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1509.2	1507.9	1506.7	1505.3	1504.0	1502.0	1499.2	1496.4	1493.6	1490.7	1493.3
5°	1502.2	1501.0	1499.7	1498.4	1497.1	1494.7	1491.2	1487.6	1484.1	1480.5	1483.2
7.5°	1488.9	1487.0	1485.0	1483.0	1481.0	1478.2	1474.6	1471.0	1467.4	1463.9	1466.4
10°	1476.2	1474.0	1471.8	1469.5	1467.3	1464.2	1460.4	1456.5	1452.6	1448.8	1451.4
12.5°	1459.0	1456.9	1454.9	1452.9	1451.0	1448.0	1444.2	1440.3	1436.5	1432.7	1434.5
15°	1430.0	1428.1	1426.2	1424.3	1422.3	1419.3	1415.1	1410.9	1406.7	1402.6	1403.9
17.5°	1393.1	1391.1	1389.2	1387.2	1385.3	1382.2	1378.0	1373.8	1369.5	1365.4	1366.8
20°	1366.5	1364.5	1362.6	1360.7	1358.8	1355.6	1351.0	1346.6	1342.1	1337.6	1338.5
22.5°	1339.9	1337.2	1334.5	1331.8	1329.1	1325.7	1321.4	1317.2	1313.0	1308.7	1308.9
25°	1294.3	1291.7	1289.1	1286.6	1284.0	1280.0	1274.5	1269.0	1263.6	1258.1	1258.8
27.5°	1242.3	1239.9	1237.7	1235.3	1233.0	1229.7	1225.4	1221.1	1216.8	1212.5	1211.5
30°	1207.6	1205.0	1202.4	1199.9	1197.3	1193.6	1188.8	1184.0	1179.2	1174.3	1173.4
32.5°	1170.6	1168.6	1166.5	1164.4	1162.3	1158.9	1153.8	1148.7	1143.6	1138.5	1136.8
35°	1116.5	1113.3	1110.1	1106.9	1103.7	1099.6	1094.4	1089.3	1084.2	1079.0	1077.1
37.5°	1055.6	1052.8	1050.0	1047.2	1044.3	1040.4	1035.2	1030.1	1024.9	1019.8	1017.4
40°	1014.0	1011.4	1008.9	1006.4	1003.7	999.9	994.8	989.7	984.5	979.4	976.5
42.5°	973.6	971.0	968.5	965.9	963.3	959.4	954.3	949.1	944.1	938.9	935.8
45°	908.6	906.3	904.1	901.8	899.6	896.1	891.3	886.5	881.7	876.8	873.3
47.5°	843.9	841.8	839.6	837.5	835.4	831.8	826.8	821.8	816.8	811.8	808.0
50°	798.8	797.2	795.6	794.0	792.4	789.3	784.9	780.3	775.8	771.4	766.9
52.5°	754.9	752.8	750.6	748.6	746.4	743.2	739.0	734.7	730.6	726.3	722.6
55°	687.6	685.6	683.7	681.8	679.9	676.9	673.2	669.3	665.4	661.6	657.7
57.5°	620.0	618.4	616.9	615.4	613.8	611.0	606.7	602.5	598.2	594.0	590.2
60°	574.9	573.6	572.3	571.1	569.8	566.8	562.4	557.9	553.4	548.9	545.4
62.5°	531.0	529.0	526.9	524.8	522.7	520.0	516.5	513.1	509.6	506.1	502.8
65°	463.6	461.8	459.9	457.9	456.0	453.4	450.2	447.0	443.7	440.5	437.7
67.5°	395.2	393.7	392.1	390.6	389.1	386.8	383.9	381.1	378.1	375.3	373.1
70°	352.4	351.2	349.9	348.6	347.3	345.3	342.3	339.4	336.6	333.7	331.4
72.5°	308.5	307.3	305.9	304.7	303.4	301.8	300.0	298.1	296.2	294.4	292.1
75°	242.7	242.0	241.4	240.7	240.1	238.9	237.3	235.7	234.1	232.5	230.6
77.5°	183.7	182.7	181.5	180.5	179.4	178.5	177.9	177.2	176.5	176.0	174.9
80°	144.5	144.1	143.8	143.5	143.2	142.7	142.0	141.4	140.7	140.2	139.1
82.5°	107.4	107.4	107.4	107.3	107.2	107.0	106.6	106.2	105.8	105.5	104.2
85°	59.2	58.9	58.6	58.2	58.0	57.6	57.3	56.9	56.6	56.4	55.3
87.5°	21.0	21.1	21.2	21.2	21.3	21.6	22.1	22.7	23.3	23.8	23.0
90°	1.1	4.1	7.0	9.9	12.8	16.9	22.2	27.6	33.0	38.4	37.8
92.5°	19.5	21.6	23.8	25.9	28.1	29.8	31.0	32.3	33.6	34.8	34.9
95°	56.9	59.4	61.8	64.2	66.6	68.1	68.6	69.1	69.6	70.0	70.0
97.5°	104.1	106.1	108.3	110.5	112.5	114.1	115.0	115.9	116.9	117.8	117.8
100°	139.0	141.0	143.0	144.9	146.8	148.2	148.9	149.6	150.3	151.1	151.1
102.5°	175.9	177.4	179.0	180.5	182.1	183.3	184.3	185.1	186.1	187.0	187.2
105°	235.4	236.1	236.9	237.6	238.3	238.9	239.4	239.9	240.3	240.8	241.4
107.5°	295.4	296.4	297.6	298.6	299.6	300.2	300.2	300.2	300.2	300.2	300.4
110°	333.9	335.4	336.9	338.3	339.8	340.5	340.5	340.5	340.5	340.5	340.5



TEST NUMBER: P331463-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	376.0	377.4	378.9	380.3	381.8	382.5	382.2	382.0	381.8	381.6	381.1
115°	437.9	439.4	440.8	442.3	443.7	444.2	443.7	443.3	442.8	442.3	442.1
117.5°	499.6	501.6	503.6	505.5	507.5	507.7	506.4	505.0	503.7	502.3	501.7
120°	540.8	542.8	544.8	546.7	548.7	548.7	546.7	544.8	542.8	540.8	540.8
122.5°	578.5	580.9	583.2	585.5	587.9	588.3	587.0	585.6	584.3	582.9	582.3
125°	637.2	639.4	641.6	643.8	645.9	646.7	645.9	645.3	644.5	643.8	643.0
127.5°	694.4	697.1	699.9	702.7	705.4	706.4	705.5	704.6	703.8	702.9	702.0
130°	730.3	733.4	736.6	739.7	742.9	744.2	743.8	743.3	742.8	742.3	741.8
132.5°	770.5	773.2	775.7	778.3	780.9	782.2	782.3	782.4	782.5	782.6	781.6
135°	824.4	827.1	829.8	832.5	835.1	836.7	837.2	837.6	838.2	838.7	838.4
137.5°	881.1	883.4	885.5	887.7	889.9	891.3	891.9	892.6	893.2	893.8	893.6
140°	915.3	917.5	919.6	921.9	924.1	925.8	927.0	928.2	929.4	930.6	930.6
142.5°	950.4	952.5	954.7	956.9	959.0	960.5	961.4	962.2	963.1	963.9	964.1
145°	1000.7	1002.4	1004.1	1005.8	1007.5	1009.1	1010.5	1012.0	1013.4	1014.9	1015.1
147.5°	1045.6	1047.6	1049.6	1051.7	1053.8	1055.3	1056.2	1057.2	1058.2	1059.1	1059.7
150°	1076.2	1077.7	1079.1	1080.6	1082.0	1083.3	1084.3	1085.2	1086.2	1087.2	1087.9
152.5°	1103.3	1104.8	1106.3	1107.8	1109.2	1110.5	1111.7	1112.9	1114.1	1115.2	1116.2
155°	1144.2	1144.8	1145.6	1146.3	1147.1	1147.7	1148.5	1149.2	1150.0	1150.7	1151.9
157.5°	1178.9	1179.4	1179.9	1180.3	1180.9	1181.3	1181.8	1182.2	1182.6	1183.1	1184.8
160°	1200.0	1200.4	1200.9	1201.4	1201.9	1202.2	1202.5	1202.8	1203.0	1203.2	1204.7
162.5°	1219.2	1219.3	1219.4	1219.5	1219.7	1219.7	1220.0	1220.2	1220.5	1220.8	1222.4
165°	1244.8	1244.6	1244.3	1244.1	1243.9	1243.8	1243.8	1243.8	1243.8	1243.8	1245.5
167.5°	1266.3	1265.6	1264.8	1264.1	1263.4	1263.0	1262.9	1262.9	1262.8	1262.8	1264.5
170°	1277.7	1277.0	1276.2	1275.4	1274.8	1274.3	1274.0	1273.8	1273.6	1273.3	1275.0
172.5°	1285.5	1284.9	1284.1	1283.4	1282.6	1282.1	1282.0	1281.7	1281.4	1281.2	1282.9
175°	1295.2	1294.5	1293.7	1293.0	1292.3	1291.7	1291.2	1290.7	1290.2	1289.7	1291.5
177.5°	1299.1	1298.5	1298.0	1297.4	1296.8	1296.3	1295.9	1295.5	1295.1	1294.8	1295.9
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331463-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1495.8	1498.4	1501.0	1502.0	1501.5	1501.0	1500.4	1500.0
5°	1485.7	1488.3	1490.8	1491.9	1491.2	1490.5	1489.9	1489.2
7.5°	1469.0	1471.5	1474.1	1475.1	1474.3	1473.7	1472.9	1472.3
10°	1454.0	1456.5	1459.1	1459.9	1459.0	1457.9	1457.0	1456.0
12.5°	1436.2	1438.0	1439.8	1440.4	1439.6	1439.0	1438.2	1437.6
15°	1405.1	1406.5	1407.7	1407.6	1406.0	1404.4	1402.8	1401.2
17.5°	1368.3	1369.8	1371.2	1371.2	1369.6	1368.1	1366.6	1365.0
20°	1339.5	1340.5	1341.4	1341.2	1340.0	1338.7	1337.5	1336.1
22.5°	1309.1	1309.3	1309.5	1309.2	1308.4	1307.7	1306.8	1306.1
25°	1259.4	1260.1	1260.7	1260.7	1260.1	1259.4	1258.8	1258.1
27.5°	1210.6	1209.6	1208.6	1207.4	1205.9	1204.3	1202.8	1201.3
30°	1172.4	1171.5	1170.5	1169.4	1168.1	1166.8	1165.5	1164.2
32.5°	1135.1	1133.3	1131.6	1130.1	1128.8	1127.6	1126.2	1124.9
35°	1075.2	1073.3	1071.3	1069.6	1068.0	1066.4	1064.7	1063.1
37.5°	1015.0	1012.7	1010.3	1008.3	1006.8	1005.2	1003.7	1002.2
40°	973.6	970.7	967.8	965.7	964.4	963.2	961.9	960.5
42.5°	932.6	929.4	926.3	923.9	922.1	920.3	918.5	916.6
45°	869.8	866.2	862.7	860.3	858.9	857.7	856.4	855.2
47.5°	804.4	800.6	796.9	794.1	792.2	790.4	788.5	786.6
50°	762.3	757.9	753.4	750.4	748.8	747.2	745.6	743.9
52.5°	718.9	715.1	711.4	708.5	706.3	704.3	702.1	700.0
55°	653.8	650.0	646.2	643.5	641.9	640.3	638.7	637.0
57.5°	586.4	582.6	578.8	576.3	575.1	573.9	572.7	571.5
60°	541.9	538.3	534.8	532.5	531.6	530.7	529.6	528.7
62.5°	499.6	496.3	493.0	490.8	489.6	488.3	487.1	485.9
65°	434.8	431.9	429.0	426.8	425.2	423.6	422.0	420.4
67.5°	370.8	368.5	366.3	364.5	363.3	361.9	360.7	359.4
70°	329.1	327.0	324.7	322.9	321.6	320.4	319.1	317.8
72.5°	289.9	287.7	285.4	283.8	282.8	281.7	280.7	279.7
75°	228.8	226.8	224.9	224.2	224.9	225.5	226.1	226.8
77.5°	174.0	173.1	172.1	171.2	170.2	169.4	168.4	167.6
80°	138.2	137.2	136.3	135.4	134.8	134.2	133.6	132.9
82.5°	103.0	101.8	100.6	99.9	99.7	99.6	99.5	99.3
85°	54.4	53.4	52.5	51.8	51.6	51.2	50.9	50.5
87.5°	22.1	21.2	20.4	19.8	19.6	19.4	19.2	19.0
90°	37.3	36.9	36.4	36.3	36.5	36.8	36.9	37.2
92.5°	35.0	35.1	35.3	35.3	35.3	35.3	35.4	35.4
95°	70.0	70.0	70.0	69.8	69.4	68.9	68.3	67.9
97.5°	117.8	117.8	117.8	117.8	117.7	117.7	117.6	117.6
100°	151.1	151.1	151.1	151.0	150.7	150.5	150.2	150.0
102.5°	187.4	187.6	187.8	187.8	187.5	187.3	187.0	186.8
105°	241.9	242.3	242.8	243.1	243.1	243.1	243.1	243.1
107.5°	300.6	300.8	301.0	300.5	299.4	298.3	297.2	296.1
110°	340.5	340.5	340.5	340.2	339.4	338.7	337.9	337.2





TEST NUMBER: P331463-830

CATALOG NUMBER: SA2XXDIP-C1005D1080U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	380.5	379.9	379.4	378.8	378.2	377.7	377.2	376.6
115°	441.9	441.6	441.3	440.8	440.2	439.4	438.7	437.9
117.5°	501.1	500.6	500.0	499.4	498.6	497.9	497.1	496.4
120°	540.8	540.8	540.8	540.5	539.8	539.0	538.3	537.5
122.5°	581.7	581.2	580.5	580.0	579.5	578.9	578.4	577.9
125°	642.3	641.6	640.8	640.4	640.1	639.9	639.6	639.4
127.5°	701.2	700.2	699.4	698.5	697.8	697.0	696.3	695.4
130°	741.3	740.8	740.4	739.6	738.7	737.6	736.7	735.7
132.5°	780.4	779.4	778.4	777.4	776.7	775.8	775.1	774.3
135°	838.2	837.9	837.6	837.2	836.4	835.8	835.0	834.2
137.5°	893.4	893.2	893.1	892.5	891.5	890.5	889.6	888.5
140°	930.6	930.6	930.6	930.1	929.2	928.2	927.2	926.2
142.5°	964.3	964.5	964.7	964.3	963.3	962.3	961.4	960.4
145°	1015.4	1015.7	1015.9	1015.5	1014.6	1013.6	1012.6	1011.6
147.5°	1060.3	1060.7	1061.3	1061.1	1060.2	1059.2	1058.3	1057.4
150°	1088.6	1089.4	1090.1	1090.1	1089.4	1088.6	1087.9	1087.2
152.5°	1117.1	1117.9	1118.9	1118.9	1117.9	1117.1	1116.2	1115.2
155°	1153.1	1154.3	1155.6	1155.7	1155.1	1154.3	1153.6	1152.8
157.5°	1186.4	1188.1	1189.7	1190.0	1188.7	1187.6	1186.5	1185.2
160°	1206.2	1207.6	1209.1	1209.3	1208.3	1207.4	1206.4	1205.4
162.5°	1224.1	1225.7	1227.4	1227.6	1226.4	1225.3	1224.1	1222.9
165°	1247.2	1248.9	1250.6	1250.8	1249.6	1248.4	1247.2	1245.9
167.5°	1266.2	1267.9	1269.6	1269.8	1268.6	1267.2	1266.0	1264.8
170°	1276.7	1278.4	1280.1	1280.3	1278.7	1277.3	1275.8	1274.4
172.5°	1284.6	1286.3	1288.0	1288.1	1286.7	1285.2	1283.7	1282.2
175°	1293.2	1294.9	1296.6	1296.7	1295.2	1293.7	1292.3	1290.8
177.5°	1297.1	1298.3	1299.4	1299.4	1298.3	1297.1	1295.9	1294.8
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4

(END OF REPORT)