

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331745

Luminaire Tested: **SA2XXRDIP-C1005D530U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331745
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C1005D530U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5375.2 lumens
Efficiency: N/A
Efficacy: 97.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 55.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331745
CATALOG NUMBER: SA2XXRDIP-C1005D530U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331745

CATALOG NUMBER: SA2XXRDIP-C1005D530U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65				
1	102	98	94	90	96	92	89	86	81	79	77	72	70	68	63	61	60	56				
2	93	86	80	75	87	81	76	71	72	68	64	64	61	58	56	54	52	48				
3	85	76	69	63	80	72	66	60	64	59	55	57	53	50	50	47	45	41				
4	78	68	60	54	74	64	57	52	57	52	47	51	47	43	45	42	39	36				
5	72	61	53	47	68	58	50	45	52	46	41	46	42	38	41	37	34	32				
6	67	55	47	41	63	52	45	40	47	41	37	42	37	34	37	34	31	28				
7	62	50	42	36	58	47	40	35	43	37	33	38	34	30	34	30	28	25				
8	58	46	38	33	54	43	36	31	39	33	29	35	31	27	32	28	25	23				
9	54	42	34	29	51	40	33	28	36	30	26	33	28	25	29	26	23	21				
10	51	39	31	27	48	37	30	26	34	28	24	30	26	22	27	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27341	27341	27341
5°	27446	27000	27149
10°	27237	26558	26332
15°	26924	25770	25028
20°	26490	24646	23409
25°	26045	23370	21841
30°	25430	22057	19829
35°	24829	20631	18065
40°	24226	19155	16021
45°	23516	17497	14173
50°	22790	15822	12356
55°	22044	14021	10612
60°	21180	12126	8809
65°	20199	10189	8023
70°	19029	8393	7378
75°	17592	7648	6881
80°	15528	6843	6267
85°	12208	5391	5391



TEST NUMBER: P331745

CATALOG NUMBER: SA2XXRDIP-C1005D530U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.5	2.9
10°-20°	435.2	8.1
20°-30°	611.2	11.4
30°-40°	666.5	12.4
40°-50°	612.8	11.4
50°-60°	481.3	9.0
60°-70°	313.8	5.8
70°-80°	161.8	3.0
80°-90°	44.7	0.8
90°-100°	42.8	0.8
100°-110°	133.0	2.5
110°-120°	227.3	4.2
120°-130°	298.9	5.6
130°-140°	335.5	6.2
140°-150°	329.0	6.1
150°-160°	275.9	5.1
160°-170°	183.0	3.4
170°-180°	64.0	1.2
0°-30°	1204.9	22.4
0°-40°	1871.4	34.8
0°-60°	2965.4	55.2
0°-90°	3485.7	64.8
90°-120°	403.1	7.5
90°-150°	1366.6	25.4
90°-180°	1889.0	35.1
0°-180°	5375.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1693	1693	1693	1693	1693	
5°	1693	1685	1666	1679	1675	160
15°	1611	1592	1542	1513	1497	454
25°	1462	1410	1312	1251	1226	672
35°	1260	1178	1047	954	916	788
45°	1030	924	766	661	621	795
55°	783	661	498	410	377	700
65°	529	404	267	217	210	524
75°	282	178	123	112	110	298
85°	66	35	29	29	29	78
90°	1	8	20	19	19	4
95°	30	35	36	36	35	34
105°	123	124	126	127	127	129
115°	228	231	230	230	228	226
125°	332	337	335	334	333	296
135°	429	435	437	436	434	332
145°	521	525	529	529	527	325
155°	596	598	599	602	600	274
165°	648	648	648	651	649	183
175°	675	673	672	675	672	64
180°	676	676	676	676	676	



TEST NUMBER: P331745

CATALOG NUMBER: SA2XXRDIP-C1005D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1699.6	1698.2	1696.8	1695.5	1694.1	1691.9	1688.9	1686.0	1683.0	1680.0	1682.7
5°	1693.4	1691.7	1690.0	1688.3	1686.6	1683.6	1679.1	1674.7	1670.3	1665.9	1668.9
7.5°	1676.0	1673.9	1671.8	1669.6	1667.5	1663.9	1658.7	1653.5	1648.4	1643.2	1644.1
10°	1661.3	1658.9	1656.5	1654.1	1651.7	1647.1	1640.3	1633.5	1626.7	1619.9	1618.9
12.5°	1642.9	1639.9	1637.0	1634.1	1631.2	1625.3	1616.6	1607.9	1599.2	1590.5	1588.6
15°	1610.7	1606.9	1603.2	1599.4	1595.7	1588.0	1576.5	1564.9	1553.3	1541.7	1535.3
17.5°	1571.1	1565.4	1559.7	1554.0	1548.3	1538.0	1523.1	1508.3	1493.4	1478.6	1470.9
20°	1541.7	1534.9	1528.1	1521.3	1514.5	1502.6	1485.5	1468.5	1451.5	1434.4	1425.9
22.5°	1509.8	1502.2	1494.6	1487.0	1479.3	1465.9	1446.7	1427.5	1408.3	1389.1	1378.1
25°	1462.0	1451.1	1440.2	1429.3	1418.4	1401.8	1379.3	1356.8	1334.3	1311.8	1297.9
27.5°	1404.4	1392.6	1380.7	1368.9	1357.0	1338.4	1313.1	1287.7	1262.4	1237.1	1220.8
30°	1364.0	1351.0	1338.1	1325.1	1312.2	1292.1	1264.8	1237.6	1210.4	1183.1	1165.7
32.5°	1324.7	1309.6	1294.5	1279.4	1264.2	1242.8	1215.0	1187.2	1159.4	1131.6	1111.8
35°	1259.7	1242.4	1225.0	1207.6	1190.3	1166.6	1136.6	1106.7	1076.7	1046.7	1025.3
37.5°	1194.8	1175.7	1156.6	1137.5	1118.5	1093.0	1061.0	1029.1	997.1	965.2	941.6
40°	1149.4	1129.0	1108.5	1088.1	1067.7	1040.9	1007.9	974.9	941.8	908.8	884.6
42.5°	1102.8	1081.3	1059.8	1038.2	1016.7	988.9	954.8	920.6	886.5	852.4	827.4
45°	1029.9	1007.0	984.2	961.4	938.6	909.3	873.5	837.8	802.0	766.3	742.1
47.5°	958.7	934.6	910.4	886.2	862.0	831.5	794.6	757.6	720.7	683.8	659.8
50°	907.3	883.1	858.9	834.7	810.5	779.7	742.3	704.8	667.3	629.9	606.4
52.5°	857.0	831.7	806.5	781.2	755.9	725.0	688.3	651.7	615.0	578.4	555.7
55°	783.1	756.6	730.0	703.4	676.9	645.2	608.4	571.6	534.9	498.1	477.6
57.5°	707.4	680.2	652.9	625.7	598.4	567.1	531.8	496.4	461.1	425.7	407.0
60°	655.9	628.7	601.4	574.2	546.9	515.8	480.7	445.6	410.5	375.5	358.1
62.5°	605.7	578.4	551.2	523.9	496.7	466.3	432.9	399.4	366.0	332.6	316.0
65°	528.7	501.1	473.6	446.0	418.4	389.3	358.6	328.0	297.3	266.7	255.1
67.5°	454.5	427.2	399.8	372.4	345.0	317.5	290.0	262.4	234.8	207.2	201.9
70°	403.1	376.5	349.9	323.4	296.8	271.8	248.3	224.8	201.3	177.8	174.4
72.5°	354.0	328.5	303.1	277.6	252.1	229.9	211.1	192.2	173.3	154.5	151.6
75°	282.0	258.1	234.3	210.5	186.6	168.9	157.3	145.8	134.2	122.6	120.2
77.5°	211.2	190.3	169.4	148.5	127.5	114.3	108.7	103.1	97.5	92.0	90.6
80°	167.0	149.7	132.3	114.9	97.6	87.2	83.8	80.4	77.0	73.6	72.2
82.5°	126.6	113.0	99.5	85.9	72.4	64.4	62.1	59.8	57.5	55.2	54.4
85°	65.9	58.7	51.6	44.4	37.3	33.2	32.2	31.2	30.1	29.1	29.1
87.5°	19.7	17.9	16.0	14.1	12.2	11.6	12.1	12.7	13.2	13.8	13.5
90°	0.6	2.1	3.6	5.1	6.7	8.8	11.6	14.4	17.2	20.0	19.7
92.5°	10.2	11.3	12.4	13.5	14.6	15.5	16.2	16.8	17.5	18.1	18.2
95°	29.7	30.9	32.2	33.5	34.7	35.5	35.7	36.0	36.2	36.5	36.5
97.5°	54.2	55.3	56.4	57.5	58.6	59.4	59.9	60.4	60.9	61.4	61.4
100°	72.4	73.4	74.4	75.5	76.5	77.2	77.6	77.9	78.3	78.7	78.7
102.5°	91.6	92.4	93.2	94.0	94.8	95.5	96.0	96.4	96.9	97.4	97.5
105°	122.6	123.0	123.4	123.7	124.1	124.4	124.7	124.9	125.2	125.5	125.7
107.5°	153.9	154.4	155.0	155.5	156.1	156.4	156.4	156.4	156.4	156.4	156.5
110°	173.9	174.7	175.4	176.2	177.0	177.3	177.3	177.3	177.3	177.3	177.3



TEST NUMBER: P331745

CATALOG NUMBER: SA2XXRDIP-C1005D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	195.8	196.6	197.3	198.1	198.9	199.2	199.1	199.0	198.9	198.8	198.5
115°	228.1	228.9	229.6	230.4	231.1	231.4	231.1	230.9	230.6	230.4	230.3
117.5°	260.3	261.3	262.3	263.3	264.3	264.5	263.8	263.0	262.3	261.6	261.3
120°	281.7	282.7	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7	281.7
122.5°	301.3	302.5	303.8	305.0	306.2	306.4	305.7	305.0	304.3	303.6	303.3
125°	331.9	333.0	334.2	335.3	336.4	336.8	336.4	336.1	335.7	335.3	334.9
127.5°	361.6	363.1	364.5	366.0	367.4	367.9	367.5	367.0	366.6	366.1	365.6
130°	380.4	382.0	383.6	385.3	386.9	387.6	387.4	387.1	386.9	386.6	386.4
132.5°	401.3	402.7	404.0	405.4	406.7	407.4	407.5	407.5	407.6	407.6	407.1
135°	429.4	430.8	432.2	433.6	435.0	435.8	436.0	436.3	436.6	436.8	436.7
137.5°	458.9	460.1	461.2	462.4	463.5	464.2	464.6	464.9	465.2	465.5	465.4
140°	476.7	477.9	479.0	480.1	481.3	482.2	482.8	483.4	484.1	484.7	484.7
142.5°	495.0	496.1	497.3	498.4	499.5	500.3	500.8	501.2	501.6	502.0	502.1
145°	521.2	522.1	523.0	523.9	524.8	525.6	526.3	527.1	527.9	528.6	528.7
147.5°	544.6	545.6	546.7	547.8	548.8	549.6	550.1	550.6	551.1	551.7	551.9
150°	560.6	561.3	562.1	562.8	563.6	564.2	564.7	565.2	565.7	566.3	566.6
152.5°	574.7	575.5	576.2	577.0	577.7	578.4	579.0	579.6	580.2	580.9	581.3
155°	595.9	596.3	596.7	597.0	597.4	597.8	598.2	598.6	598.9	599.3	600.0
157.5°	614.0	614.3	614.5	614.8	615.1	615.3	615.5	615.8	616.0	616.2	617.1
160°	625.0	625.2	625.5	625.7	626.0	626.2	626.3	626.4	626.6	626.7	627.5
162.5°	635.0	635.1	635.1	635.2	635.2	635.3	635.4	635.6	635.7	635.8	636.7
165°	648.4	648.2	648.1	648.0	647.9	647.8	647.8	647.8	647.8	647.8	648.7
167.5°	659.5	659.2	658.8	658.4	658.0	657.8	657.8	657.8	657.7	657.7	658.6
170°	665.5	665.1	664.7	664.3	664.0	663.7	663.6	663.4	663.3	663.2	664.1
172.5°	669.6	669.2	668.8	668.4	668.1	667.8	667.7	667.6	667.4	667.3	668.2
175°	674.6	674.2	673.8	673.5	673.1	672.8	672.5	672.3	672.0	671.7	672.6
177.5°	676.7	676.3	676.0	675.7	675.4	675.2	675.0	674.8	674.6	674.4	675.0
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331745

CATALOG NUMBER: SA2XXRDIP-C1005D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4	1693.4
2.5°	1685.4	1688.1	1690.9	1691.9	1691.4	1690.9	1690.3	1689.8
5°	1672.0	1675.1	1678.1	1679.1	1678.1	1677.1	1676.1	1675.1
7.5°	1644.9	1645.8	1646.7	1646.3	1644.5	1642.7	1641.0	1639.2
10°	1617.8	1616.8	1615.8	1614.3	1612.2	1610.2	1608.1	1606.1
12.5°	1586.8	1584.9	1583.1	1580.5	1577.1	1573.7	1570.3	1566.9
15°	1528.8	1522.3	1515.8	1510.9	1507.5	1504.1	1500.7	1497.3
17.5°	1463.2	1455.5	1447.8	1441.0	1435.2	1429.3	1423.4	1417.6
20°	1417.4	1408.9	1400.4	1392.4	1384.9	1377.4	1369.9	1362.4
22.5°	1367.2	1356.2	1345.2	1336.9	1331.4	1325.8	1320.2	1314.6
25°	1283.9	1270.0	1256.0	1246.5	1241.3	1236.2	1231.1	1226.0
27.5°	1204.5	1188.2	1171.9	1159.7	1151.6	1143.5	1135.4	1127.3
30°	1148.4	1131.0	1113.6	1100.4	1091.2	1082.0	1072.8	1063.6
32.5°	1092.0	1072.2	1052.3	1038.1	1029.5	1020.8	1012.1	1003.5
35°	1003.8	982.4	960.9	946.4	938.9	931.4	923.9	916.5
37.5°	917.9	894.3	870.6	854.5	846.0	837.4	828.8	820.2
40°	860.4	836.2	812.1	795.6	786.7	777.8	769.0	760.1
42.5°	802.4	777.4	752.4	735.6	727.0	718.4	709.9	701.3
45°	717.9	693.7	669.5	653.4	645.2	637.0	628.8	620.7
47.5°	635.7	611.7	587.6	571.9	564.5	557.1	549.6	542.2
50°	582.9	559.4	535.9	520.5	513.4	506.2	499.1	491.9
52.5°	533.0	510.3	487.7	473.0	466.4	459.8	453.2	446.6
55°	457.2	436.8	416.3	402.9	396.4	389.9	383.5	377.0
57.5°	388.3	369.5	350.8	338.7	333.3	327.8	322.4	316.9
60°	340.7	323.4	306.0	294.6	289.1	283.7	278.2	272.8
62.5°	299.5	282.9	266.4	256.4	253.2	249.9	246.6	243.4
65°	243.5	231.9	220.3	214.0	213.0	212.0	211.0	210.0
67.5°	196.6	191.3	185.9	182.7	181.7	180.6	179.5	178.4
70°	171.0	167.6	164.2	161.8	160.4	159.0	157.7	156.3
72.5°	148.8	145.9	143.0	141.2	140.4	139.6	138.7	137.9
75°	117.8	115.5	113.1	111.7	111.4	111.0	110.7	110.3
77.5°	89.2	87.9	86.5	85.5	85.0	84.5	83.9	83.4
80°	70.8	69.5	68.1	67.4	67.4	67.4	67.4	67.4
82.5°	53.5	52.7	51.9	51.5	51.5	51.5	51.5	51.5
85°	29.1	29.1	29.1	29.1	29.1	29.1	29.1	29.1
87.5°	13.2	12.8	12.5	12.4	12.4	12.4	12.4	12.5
90°	19.5	19.2	18.9	18.9	19.0	19.1	19.3	19.4
92.5°	18.2	18.3	18.3	18.4	18.4	18.4	18.5	18.5
95°	36.5	36.5	36.5	36.4	36.1	35.9	35.6	35.4
97.5°	61.4	61.4	61.4	61.3	61.3	61.3	61.3	61.2
100°	78.7	78.7	78.7	78.6	78.5	78.4	78.3	78.1
102.5°	97.6	97.7	97.8	97.8	97.7	97.5	97.4	97.3
105°	126.0	126.2	126.5	126.6	126.6	126.6	126.6	126.6
107.5°	156.6	156.7	156.8	156.5	155.9	155.4	154.8	154.2
110°	177.3	177.3	177.3	177.2	176.8	176.4	176.0	175.6



TEST NUMBER: P331745

CATALOG NUMBER: SA2XXRDIP-C1005D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.2	197.9	197.6	197.3	197.0	196.7	196.4	196.2
115°	230.1	230.0	229.9	229.6	229.2	228.9	228.5	228.1
117.5°	261.0	260.7	260.4	260.1	259.7	259.3	258.9	258.5
120°	281.7	281.7	281.7	281.5	281.1	280.8	280.4	280.0
122.5°	303.0	302.7	302.4	302.1	301.8	301.5	301.3	301.0
125°	334.5	334.2	333.8	333.5	333.4	333.3	333.1	333.0
127.5°	365.2	364.7	364.3	363.8	363.4	363.0	362.6	362.2
130°	386.1	385.9	385.6	385.2	384.7	384.2	383.7	383.2
132.5°	406.5	405.9	405.4	404.9	404.5	404.1	403.7	403.3
135°	436.6	436.4	436.3	436.0	435.7	435.3	434.9	434.5
137.5°	465.3	465.2	465.1	464.8	464.3	463.8	463.3	462.8
140°	484.7	484.7	484.7	484.5	483.9	483.4	482.9	482.4
142.5°	502.2	502.3	502.4	502.2	501.7	501.2	500.7	500.2
145°	528.9	529.0	529.1	528.9	528.4	527.9	527.4	526.9
147.5°	552.2	552.5	552.8	552.7	552.2	551.7	551.2	550.7
150°	567.0	567.4	567.8	567.8	567.4	567.0	566.6	566.3
152.5°	581.8	582.3	582.8	582.8	582.3	581.8	581.3	580.9
155°	600.6	601.2	601.9	602.0	601.6	601.2	600.8	600.5
157.5°	617.9	618.8	619.7	619.8	619.2	618.6	618.0	617.3
160°	628.2	629.0	629.7	629.9	629.4	628.9	628.3	627.8
162.5°	637.5	638.4	639.3	639.4	638.8	638.2	637.6	637.0
165°	649.6	650.5	651.3	651.5	650.8	650.2	649.6	648.9
167.5°	659.5	660.4	661.3	661.4	660.7	660.1	659.4	658.7
170°	665.0	665.9	666.7	666.8	666.0	665.3	664.5	663.8
172.5°	669.1	670.0	670.8	670.9	670.2	669.4	668.6	667.9
175°	673.5	674.4	675.3	675.4	674.6	673.8	673.1	672.3
177.5°	675.6	676.2	676.8	676.8	676.2	675.6	675.0	674.4
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7

(END OF REPORT)