

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331427-830

Luminaire Tested: **SA2XXDIP-C1005D330U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331427-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D330U830-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4926.9 lumens  
Efficiency: N/A  
Efficacy: 98.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 49.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331427-830  
CATALOG NUMBER: SA2XXDIP-C1005D330U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331427-830

CATALOG NUMBER: SA2XXDIP-C1005D330U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	114	114	114	114	108	108	108	108	99	99	99	90	90	90	81	81	81	78
1	104	99	95	92	99	95	91	88	87	84	81	79	77	75	72	70	69	65
2	95	87	80	75	90	83	77	72	76	71	67	69	66	63	63	61	58	55
3	86	76	69	63	82	73	66	61	67	61	57	61	57	53	56	53	49	46
4	79	68	60	53	75	65	57	52	60	53	49	55	50	46	50	46	43	40
5	73	61	52	46	69	58	50	45	54	47	42	49	44	40	45	41	37	35
6	67	55	46	40	64	52	45	39	48	42	37	45	39	35	41	37	33	30
7	62	49	41	35	59	48	40	34	44	37	33	41	35	31	38	33	29	27
8	58	45	37	31	55	43	36	31	40	34	29	37	32	28	35	30	26	24
9	54	41	33	28	52	40	33	28	37	31	26	34	29	25	32	27	24	22
10	51	38	31	25	48	37	30	25	34	28	24	32	27	23	30	25	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24254	24254	24254
5°	24347	23995	24136
10°	24202	23753	23871
15°	23903	23445	23422
20°	23479	22983	22957
25°	23058	22413	22413
30°	22514	21893	21705
35°	22007	21268	20954
40°	21372	20643	20244
45°	20747	20021	19527
50°	20065	19376	18686
55°	19356	18624	17931
60°	18564	17725	17073
65°	17712	16829	16061
70°	16636	15753	15002
75°	15140	14504	14148
80°	13436	13036	12357
85°	10967	10448	9355



TEST NUMBER: P331427-830

CATALOG NUMBER: SA2XXDIP-C1005D330U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	141.3	2.9
10°-20°	397.5	8.1
20°-30°	584.2	11.9
30°-40°	678.6	13.8
40°-50°	677.9	13.8
50°-60°	591.2	12.0
60°-70°	437.1	8.9
70°-80°	247.6	5.0
80°-90°	68.1	1.4
90°-100°	25.0	0.5
100°-110°	77.7	1.6
110°-120°	132.8	2.7
120°-130°	174.6	3.5
130°-140°	195.9	4.0
140°-150°	192.1	3.9
150°-160°	161.1	3.3
160°-170°	106.9	2.2
170°-180°	37.4	0.8
0°-30°	1123.0	22.8
0°-40°	1801.6	36.6
0°-60°	3070.7	62.3
0°-90°	3823.5	77.6
90°-120°	235.4	4.8
90°-150°	798.0	16.2
90°-180°	1103.0	22.4
0°-180°	4926.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1502	1502	1502	1502	1502	
5°	1502	1496	1480	1491	1489	142
15°	1430	1421	1403	1408	1401	402
25°	1294	1282	1258	1261	1258	595
35°	1116	1102	1079	1070	1063	697
45°	909	898	877	862	855	701
55°	688	678	662	645	637	615
65°	464	455	440	428	420	458
75°	243	240	232	225	227	259
85°	59	58	56	52	50	68
90°	0	5	12	11	11	4
95°	17	20	21	21	21	20
105°	72	73	73	74	74	76
115°	133	135	134	134	133	132
125°	194	197	196	195	194	173
135°	251	254	255	255	254	194
145°	304	307	309	309	308	190
155°	348	349	350	352	351	160
165°	379	378	378	380	379	107
175°	394	393	392	394	393	37
180°	395	395	395	395	395	



TEST NUMBER: P331427-830

CATALOG NUMBER: SA2XXDIP-C1005D330U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1509.2	1507.9	1506.7	1505.3	1504.0	1502.0	1499.2	1496.4	1493.6	1490.7	1493.3
5°	1502.2	1501.0	1499.7	1498.4	1497.1	1494.7	1491.2	1487.6	1484.1	1480.5	1483.2
7.5°	1488.9	1487.0	1485.0	1483.0	1481.0	1478.2	1474.6	1471.0	1467.4	1463.9	1466.4
10°	1476.2	1474.0	1471.8	1469.5	1467.3	1464.2	1460.4	1456.5	1452.6	1448.8	1451.4
12.5°	1459.0	1456.9	1454.9	1452.9	1451.0	1448.0	1444.2	1440.3	1436.5	1432.7	1434.5
15°	1430.0	1428.1	1426.2	1424.3	1422.3	1419.3	1415.1	1410.9	1406.7	1402.6	1403.9
17.5°	1393.1	1391.1	1389.2	1387.2	1385.3	1382.2	1378.0	1373.8	1369.5	1365.4	1366.8
20°	1366.5	1364.5	1362.6	1360.7	1358.8	1355.6	1351.0	1346.6	1342.1	1337.6	1338.5
22.5°	1339.9	1337.2	1334.5	1331.8	1329.1	1325.7	1321.4	1317.2	1313.0	1308.7	1308.9
25°	1294.3	1291.7	1289.1	1286.6	1284.0	1280.0	1274.5	1269.0	1263.6	1258.1	1258.8
27.5°	1242.3	1239.9	1237.7	1235.3	1233.0	1229.7	1225.4	1221.1	1216.8	1212.5	1211.5
30°	1207.6	1205.0	1202.4	1199.9	1197.3	1193.6	1188.8	1184.0	1179.2	1174.3	1173.4
32.5°	1170.6	1168.6	1166.5	1164.4	1162.3	1158.9	1153.8	1148.7	1143.6	1138.5	1136.8
35°	1116.5	1113.3	1110.1	1106.9	1103.7	1099.6	1094.4	1089.3	1084.2	1079.0	1077.1
37.5°	1055.6	1052.8	1050.0	1047.2	1044.3	1040.4	1035.2	1030.1	1024.9	1019.8	1017.4
40°	1014.0	1011.4	1008.9	1006.4	1003.7	999.9	994.8	989.7	984.5	979.4	976.5
42.5°	973.6	971.0	968.5	965.9	963.3	959.4	954.3	949.1	944.1	938.9	935.8
45°	908.6	906.3	904.1	901.8	899.6	896.1	891.3	886.5	881.7	876.8	873.3
47.5°	843.9	841.8	839.6	837.5	835.4	831.8	826.8	821.8	816.8	811.8	808.0
50°	798.8	797.2	795.6	794.0	792.4	789.3	784.9	780.3	775.8	771.4	766.9
52.5°	754.9	752.8	750.6	748.6	746.4	743.2	739.0	734.7	730.6	726.3	722.6
55°	687.6	685.6	683.7	681.8	679.9	676.9	673.2	669.3	665.4	661.6	657.7
57.5°	620.0	618.4	616.9	615.4	613.8	611.0	606.7	602.5	598.2	594.0	590.2
60°	574.9	573.6	572.3	571.1	569.8	566.8	562.4	557.9	553.4	548.9	545.4
62.5°	531.0	529.0	526.9	524.8	522.7	520.0	516.5	513.1	509.6	506.1	502.8
65°	463.6	461.8	459.9	457.9	456.0	453.4	450.2	447.0	443.7	440.5	437.7
67.5°	395.2	393.7	392.1	390.6	389.1	386.8	383.9	381.1	378.1	375.3	373.1
70°	352.4	351.2	349.9	348.6	347.3	345.3	342.3	339.4	336.6	333.7	331.4
72.5°	308.5	307.3	305.9	304.7	303.4	301.8	300.0	298.1	296.2	294.4	292.1
75°	242.7	242.0	241.4	240.7	240.1	238.9	237.3	235.7	234.1	232.5	230.6
77.5°	183.7	182.7	181.5	180.5	179.4	178.5	177.9	177.2	176.5	176.0	174.9
80°	144.5	144.1	143.8	143.5	143.2	142.7	142.0	141.4	140.7	140.2	139.1
82.5°	107.4	107.4	107.4	107.3	107.2	107.0	106.6	106.2	105.8	105.5	104.2
85°	59.2	58.9	58.6	58.2	58.0	57.6	57.3	56.9	56.6	56.4	55.3
87.5°	20.8	20.5	20.2	19.9	19.5	19.2	19.0	18.9	18.7	18.5	17.7
90°	0.4	1.2	2.1	3.0	3.9	5.2	6.8	8.4	10.0	11.7	11.5
92.5°	5.9	6.6	7.3	7.9	8.6	9.0	9.4	9.8	10.2	10.6	10.7
95°	17.3	18.1	18.8	19.5	20.3	20.7	20.8	21.0	21.2	21.3	21.3
97.5°	31.7	32.3	32.9	33.6	34.2	34.7	35.0	35.3	35.5	35.8	35.8
100°	42.3	42.9	43.5	44.1	44.7	45.1	45.2	45.5	45.7	46.0	46.0
102.5°	53.4	53.9	54.4	54.9	55.3	55.8	56.0	56.3	56.6	56.8	56.9
105°	71.6	71.8	72.0	72.3	72.5	72.7	72.9	73.0	73.1	73.2	73.4
107.5°	89.8	90.2	90.5	90.9	91.1	91.3	91.3	91.3	91.3	91.3	91.3
110°	101.6	102.0	102.5	102.9	103.3	103.6	103.6	103.6	103.6	103.6	103.6



TEST NUMBER: P331427-830

CATALOG NUMBER: SA2XXDIP-C1005D330U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	114.3	114.8	115.3	115.6	116.1	116.3	116.2	116.2	116.1	116.1	115.9
115°	133.2	133.7	134.1	134.5	135.0	135.2	135.0	134.8	134.7	134.5	134.5
117.5°	151.9	152.6	153.2	153.7	154.4	154.5	154.0	153.6	153.2	152.8	152.6
120°	164.5	165.1	165.7	166.3	166.8	166.8	166.3	165.7	165.1	164.5	164.5
122.5°	176.0	176.6	177.4	178.0	178.8	179.0	178.5	178.1	177.7	177.3	177.1
125°	193.8	194.4	195.1	195.8	196.4	196.7	196.4	196.2	196.0	195.8	195.6
127.5°	211.2	212.1	212.9	213.7	214.5	214.8	214.6	214.3	214.1	213.8	213.5
130°	222.2	223.1	224.0	225.0	225.9	226.4	226.2	226.1	225.9	225.7	225.6
132.5°	234.4	235.2	235.9	236.7	237.5	237.9	237.9	238.0	238.0	238.0	237.7
135°	250.7	251.6	252.4	253.2	254.0	254.5	254.7	254.8	255.0	255.1	255.0
137.5°	268.0	268.6	269.3	270.0	270.7	271.1	271.3	271.5	271.6	271.8	271.8
140°	278.4	279.1	279.7	280.4	281.1	281.5	281.9	282.3	282.7	283.0	283.0
142.5°	289.1	289.7	290.4	291.1	291.7	292.2	292.4	292.7	292.9	293.1	293.2
145°	304.3	304.9	305.4	305.9	306.4	306.9	307.4	307.8	308.2	308.7	308.8
147.5°	318.0	318.7	319.2	319.9	320.5	320.9	321.2	321.6	321.9	322.2	322.3
150°	327.3	327.8	328.2	328.7	329.1	329.5	329.8	330.1	330.4	330.6	330.9
152.5°	335.6	336.0	336.5	337.0	337.3	337.8	338.1	338.5	338.8	339.2	339.5
155°	348.0	348.2	348.5	348.6	348.8	349.1	349.3	349.5	349.8	350.0	350.3
157.5°	358.5	358.7	358.8	359.0	359.2	359.3	359.5	359.6	359.7	359.9	360.3
160°	365.0	365.1	365.2	365.4	365.5	365.7	365.7	365.8	365.9	366.0	366.4
162.5°	370.8	370.9	370.9	370.9	371.0	371.0	371.1	371.2	371.3	371.3	371.8
165°	378.6	378.5	378.4	378.4	378.3	378.2	378.2	378.2	378.2	378.2	378.8
167.5°	385.1	384.9	384.7	384.5	384.3	384.2	384.1	384.1	384.1	384.1	384.6
170°	388.6	388.4	388.1	388.0	387.8	387.6	387.5	387.4	387.4	387.3	387.8
172.5°	391.0	390.8	390.6	390.3	390.1	389.9	389.9	389.8	389.7	389.6	390.2
175°	394.0	393.7	393.5	393.2	393.0	392.9	392.8	392.6	392.4	392.3	392.8
177.5°	395.1	394.9	394.7	394.6	394.5	394.3	394.2	394.1	393.9	393.8	394.2
180°	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6



TEST NUMBER: P331427-830

CATALOG NUMBER: SA2XXDIP-C1005D330U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2	1502.2
2.5°	1495.8	1498.4	1501.0	1502.0	1501.5	1501.0	1500.4	1500.0
5°	1485.7	1488.3	1490.8	1491.9	1491.2	1490.5	1489.9	1489.2
7.5°	1469.0	1471.5	1474.1	1475.1	1474.3	1473.7	1472.9	1472.3
10°	1454.0	1456.5	1459.1	1459.9	1459.0	1457.9	1457.0	1456.0
12.5°	1436.2	1438.0	1439.8	1440.4	1439.6	1439.0	1438.2	1437.6
15°	1405.1	1406.5	1407.7	1407.6	1406.0	1404.4	1402.8	1401.2
17.5°	1368.3	1369.8	1371.2	1371.2	1369.6	1368.1	1366.6	1365.0
20°	1339.5	1340.5	1341.4	1341.2	1340.0	1338.7	1337.5	1336.1
22.5°	1309.1	1309.3	1309.5	1309.2	1308.4	1307.7	1306.8	1306.1
25°	1259.4	1260.1	1260.7	1260.7	1260.1	1259.4	1258.8	1258.1
27.5°	1210.6	1209.6	1208.6	1207.4	1205.9	1204.3	1202.8	1201.3
30°	1172.4	1171.5	1170.5	1169.4	1168.1	1166.8	1165.5	1164.2
32.5°	1135.1	1133.3	1131.6	1130.1	1128.8	1127.6	1126.2	1124.9
35°	1075.2	1073.3	1071.3	1069.6	1068.0	1066.4	1064.7	1063.1
37.5°	1015.0	1012.7	1010.3	1008.3	1006.8	1005.2	1003.7	1002.2
40°	973.6	970.7	967.8	965.7	964.4	963.2	961.9	960.5
42.5°	932.6	929.4	926.3	923.9	922.1	920.3	918.5	916.6
45°	869.8	866.2	862.7	860.3	858.9	857.7	856.4	855.2
47.5°	804.4	800.6	796.9	794.1	792.2	790.4	788.5	786.6
50°	762.3	757.9	753.4	750.4	748.8	747.2	745.6	743.9
52.5°	718.9	715.1	711.4	708.5	706.3	704.3	702.1	700.0
55°	653.8	650.0	646.2	643.5	641.9	640.3	638.7	637.0
57.5°	586.4	582.6	578.8	576.3	575.1	573.9	572.7	571.5
60°	541.9	538.3	534.8	532.5	531.6	530.7	529.6	528.7
62.5°	499.6	496.3	493.0	490.8	489.6	488.3	487.1	485.9
65°	434.8	431.9	429.0	426.8	425.2	423.6	422.0	420.4
67.5°	370.8	368.5	366.3	364.5	363.3	361.9	360.7	359.4
70°	329.1	327.0	324.7	322.9	321.6	320.4	319.1	317.8
72.5°	289.9	287.7	285.4	283.8	282.8	281.7	280.7	279.7
75°	228.8	226.8	224.9	224.2	224.9	225.5	226.1	226.8
77.5°	174.0	173.1	172.1	171.2	170.2	169.4	168.4	167.6
80°	138.2	137.2	136.3	135.4	134.8	134.2	133.6	132.9
82.5°	103.0	101.8	100.6	99.9	99.7	99.6	99.5	99.3
85°	54.4	53.4	52.5	51.8	51.6	51.2	50.9	50.5
87.5°	16.9	16.1	15.3	14.8	14.5	14.3	14.0	13.9
90°	11.4	11.2	11.0	11.0	11.1	11.2	11.2	11.3
92.5°	10.7	10.7	10.7	10.7	10.7	10.7	10.7	10.7
95°	21.3	21.3	21.3	21.2	21.1	20.9	20.8	20.6
97.5°	35.8	35.8	35.8	35.8	35.8	35.8	35.8	35.7
100°	46.0	46.0	46.0	45.9	45.8	45.8	45.7	45.6
102.5°	57.0	57.0	57.1	57.1	57.0	56.9	56.9	56.8
105°	73.5	73.7	73.9	73.9	73.9	73.9	73.9	73.9
107.5°	91.4	91.5	91.5	91.4	91.0	90.8	90.4	90.0
110°	103.6	103.6	103.6	103.5	103.2	103.0	102.8	102.5





TEST NUMBER: P331427-830

CATALOG NUMBER: SA2XXDIP-C1005D330U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	115.7	115.6	115.4	115.2	115.1	114.9	114.7	114.5
115°	134.4	134.3	134.2	134.1	133.8	133.7	133.5	133.2
117.5°	152.4	152.2	152.0	151.8	151.7	151.5	151.2	151.0
120°	164.5	164.5	164.5	164.4	164.2	163.9	163.7	163.5
122.5°	176.9	176.7	176.5	176.4	176.3	176.1	175.9	175.8
125°	195.4	195.1	194.9	194.7	194.7	194.6	194.5	194.4
127.5°	213.3	213.0	212.7	212.4	212.3	212.0	211.8	211.5
130°	225.5	225.4	225.2	225.0	224.7	224.3	224.0	223.8
132.5°	237.3	237.0	236.8	236.5	236.2	236.0	235.7	235.5
135°	255.0	254.9	254.8	254.7	254.4	254.2	254.0	253.7
137.5°	271.7	271.6	271.6	271.5	271.2	270.9	270.6	270.2
140°	283.0	283.0	283.0	282.9	282.6	282.3	282.0	281.7
142.5°	293.3	293.3	293.4	293.3	293.0	292.7	292.4	292.1
145°	308.9	308.9	309.0	308.9	308.6	308.3	308.0	307.6
147.5°	322.4	322.6	322.8	322.7	322.4	322.2	321.9	321.6
150°	331.1	331.3	331.6	331.6	331.3	331.1	330.9	330.6
152.5°	339.8	340.1	340.4	340.4	340.1	339.8	339.5	339.2
155°	350.7	351.1	351.5	351.6	351.3	351.1	350.9	350.6
157.5°	360.8	361.4	361.8	361.9	361.6	361.2	360.9	360.5
160°	366.8	367.3	367.8	367.8	367.5	367.2	366.9	366.6
162.5°	372.3	372.8	373.3	373.3	373.1	372.7	372.3	371.9
165°	379.3	379.8	380.3	380.4	380.0	379.7	379.3	379.0
167.5°	385.1	385.6	386.2	386.3	385.9	385.4	385.0	384.7
170°	388.3	388.8	389.4	389.4	389.0	388.5	388.0	387.6
172.5°	390.7	391.2	391.7	391.8	391.3	390.9	390.5	390.0
175°	393.3	393.8	394.4	394.4	394.0	393.5	393.0	392.6
177.5°	394.5	394.8	395.2	395.2	394.8	394.5	394.2	393.8
180°	394.6	394.6	394.6	394.6	394.6	394.6	394.6	394.6

(END OF REPORT)