

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331429-830

Luminaire Tested: **SA2XXDIP-C1005D530U830-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331429-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 530 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6140.3 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 55.1  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	68
1	102	98	94	91	96	93	90	87	83	80	78	73	72	70	65	64	62	58
2	94	87	81	75	88	82	77	72	73	69	66	65	62	59	58	56	53	50
3	86	77	69	64	81	73	66	61	65	60	56	58	54	51	52	49	46	43
4	79	68	61	55	74	65	58	53	58	53	48	52	48	44	47	43	40	37
5	73	61	53	47	69	58	51	46	53	47	42	47	43	39	43	39	36	33
6	67	55	47	42	64	53	46	40	48	42	37	43	38	35	39	35	32	29
7	63	50	42	37	59	48	41	36	44	38	33	40	35	31	36	32	29	26
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	24
9	55	42	35	30	52	40	34	29	37	31	27	34	29	25	31	26	24	22
10	51	39	32	27	48	37	31	26	34	29	25	31	26	23	28	24	22	20

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	30344	30344	30344	30344
5°	34020	30543	27067	30543
10°	38984	30293	23423	30293
15°	43127	29737	20694	29737
20°	42471	29141	18866	29141
25°	38297	28349	17706	28349
30°	31646	27082	16861	27082
35°	23065	25754	16259	25754
40°	18421	24190	15924	24190
45°	16098	22379	15470	22379
50°	15131	20627	15169	20627
55°	13948	18849	14762	18849
60°	12784	16956	14134	16956
65°	11645	15259	13521	15259
70°	10570	13605	12619	13605
75°	9370	11759	11179	11759
80°	8061	9735	9000	9735
85°	7225	7225	5354	7225



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	179.0	2.9
10°-20°	520.4	8.5
20°-30°	755.2	12.3
30°-40°	796.9	13.0
40°-50°	705.6	11.5
50°-60°	563.1	9.2
60°-70°	382.7	6.2
70°-80°	196.2	3.2
80°-90°	49.0	0.8
90°-100°	22.7	0.4
100°-110°	83.2	1.4
110°-120°	222.3	3.6
120°-130°	366.9	6.0
130°-140°	390.2	6.4
140°-150°	362.7	5.9
150°-160°	291.6	4.7
160°-170°	187.9	3.1
170°-180°	64.7	1.1
0°-30°	1454.6	23.7
0°-40°	2251.5	36.7
0°-60°	3520.2	57.3
0°-90°	4148.2	67.6
90°-120°	328.1	5.3
90°-150°	1447.9	23.6
90°-180°	1992.0	32.4
0°-180°	6140.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1879	1879	1879	1879	1879	
5°	2099	1884	1670	1884	2099	210
15°	2580	1779	1238	1779	2580	712
25°	2150	1591	994	1591	2150	972
35°	1170	1307	825	1307	1170	761
45°	705	980	678	980	705	554
55°	496	670	524	670	496	444
65°	305	399	354	399	305	303
75°	150	188	179	188	150	161
85°	39	39	29	39	39	43
90°	13	0	13	0	13	8
95°	21	32	21	32	21	20
105°	37	150	37	150	37	39
115°	40	283	40	283	40	101
125°	421	400	421	400	421	364
135°	511	495	511	495	511	394
145°	583	574	583	574	583	365
155°	632	632	632	632	632	292
165°	664	666	664	666	664	188
175°	677	681	677	681	677	65
180°	680	680	680	680	680	



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1966.1	1966.7	1967.8	1958.6	1957.5	1957.5	1949.4	1942.5	1934.4	1923.4	1924.6
5°	2099.0	2107.0	2109.9	2101.2	2088.2	2086.8	2074.5	2054.3	2035.5	2020.3	2009.5
7.5°	2257.7	2260.9	2253.8	2242.4	2232.7	2215.4	2192.5	2170.1	2138.8	2110.1	2088.7
10°	2377.8	2382.2	2369.9	2353.3	2339.6	2319.4	2286.1	2252.2	2211.0	2171.3	2139.5
12.5°	2469.2	2479.8	2464.1	2461.9	2438.5	2410.6	2371.1	2353.9	2295.9	2240.6	2206.6
15°	2580.1	2579.4	2580.9	2567.1	2549.8	2545.4	2503.6	2458.1	2376.4	2343.9	2287.6
17.5°	2548.1	2559.0	2564.1	2563.9	2563.5	2560.8	2547.3	2518.6	2477.7	2425.0	2359.9
20°	2471.8	2486.2	2488.4	2505.0	2514.4	2526.7	2531.8	2523.8	2498.5	2454.5	2398.1
22.5°	2353.9	2358.0	2364.7	2390.6	2410.9	2441.8	2457.8	2484.4	2474.8	2453.2	2406.2
25°	2149.7	2142.4	2167.7	2180.7	2227.6	2276.7	2312.2	2351.2	2385.9	2406.8	2393.0
27.5°	1904.3	1893.5	1931.4	1965.9	2004.0	2057.2	2112.3	2177.5	2231.7	2299.4	2322.7
30°	1697.4	1703.9	1740.0	1776.9	1834.7	1909.8	1971.9	2043.4	2120.7	2196.6	2249.3
32.5°	1474.4	1499.4	1522.2	1578.7	1629.6	1713.4	1804.3	1893.8	1990.2	2076.4	2158.0
35°	1170.2	1199.0	1230.9	1272.0	1343.5	1426.5	1515.4	1636.1	1767.6	1885.3	1982.1
37.5°	985.0	980.3	998.5	1028.3	1086.2	1153.3	1255.6	1374.7	1529.5	1667.8	1804.3
40°	874.0	871.1	884.1	911.5	955.6	1004.8	1094.3	1199.0	1342.7	1511.8	1674.3
42.5°	797.8	799.5	806.7	826.0	856.2	896.6	963.7	1052.8	1184.5	1343.7	1518.3
45°	705.0	710.0	718.0	727.4	744.7	778.0	815.5	879.1	983.1	1116.0	1287.9
47.5°	638.2	638.4	646.5	654.7	665.0	683.7	714.4	754.2	827.6	935.9	1083.6
50°	602.4	597.4	603.1	609.6	620.5	633.5	653.7	691.3	740.4	827.7	951.3
52.5°	558.5	558.6	563.8	566.3	576.0	589.0	607.5	633.5	678.0	746.3	847.8
55°	495.5	499.1	502.0	506.3	515.0	524.4	538.9	556.2	590.9	642.2	717.3
57.5°	436.3	437.4	440.4	448.6	454.0	462.7	476.5	492.2	514.7	552.7	609.2
60°	395.9	395.9	401.6	405.2	412.5	421.1	432.0	447.1	467.3	498.4	543.9
62.5°	358.8	358.3	360.6	366.5	372.0	380.1	390.9	403.8	422.8	450.4	487.9
65°	304.8	303.4	307.7	309.2	314.9	322.9	331.6	345.3	360.4	380.7	413.9
67.5°	252.8	254.6	256.8	259.6	262.8	271.2	276.9	286.6	299.4	316.2	338.7
70°	223.9	223.9	223.9	226.1	230.5	234.8	240.5	248.5	260.8	275.2	295.4
72.5°	191.5	193.9	196.1	194.9	200.4	202.9	209.9	214.4	226.1	235.4	253.3
75°	150.2	150.2	150.2	153.8	156.0	158.2	162.5	166.8	172.7	184.2	193.6
77.5°	112.1	111.8	112.5	113.4	115.7	118.3	119.6	123.5	128.8	134.2	142.1
80°	86.7	88.1	88.9	90.3	90.3	91.7	92.5	97.6	101.1	104.7	109.8
82.5°	67.0	67.3	67.5	67.8	68.3	69.2	71.1	72.7	74.0	77.0	80.9
85°	39.0	38.3	38.3	39.7	39.0	39.0	40.4	41.8	41.8	42.6	44.8
87.5°	17.7	17.6	18.2	17.5	17.5	18.0	17.9	17.2	17.7	18.2	18.6
90°	13.3	13.1	12.8	12.6	12.4	12.1	11.5	10.9	10.4	9.8	9.0
92.5°	13.3	13.2	13.0	12.9	12.7	12.5	12.3	12.0	11.7	11.4	10.9
95°	21.1	21.3	21.4	21.5	21.6	21.4	20.8	20.3	19.7	19.2	18.4
97.5°	28.3	28.1	28.0	27.8	27.7	27.4	27.0	26.6	26.1	25.6	23.9
100°	33.0	32.7	32.5	32.3	32.0	31.6	30.6	29.8	28.9	28.0	26.2
102.5°	35.3	35.0	34.7	34.4	34.1	33.4	32.2	31.1	30.0	28.8	44.4
105°	37.4	36.9	36.5	36.1	35.6	34.8	33.6	32.4	31.2	30.0	59.9
107.5°	38.5	38.0	37.6	37.1	36.8	37.1	38.4	39.6	40.8	42.0	77.8
110°	38.8	38.5	38.0	37.5	37.1	42.3	53.3	64.2	75.1	86.1	117.6



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	39.2	38.9	38.5	38.2	37.9	57.6	97.5	137.3	177.2	217.2	224.9
115°	40.3	48.2	56.1	63.9	71.8	101.0	151.7	202.3	252.9	303.5	300.8
117.5°	164.7	190.6	216.4	242.2	268.2	287.2	299.4	311.7	324.0	336.1	334.3
120°	300.0	314.8	329.6	344.3	359.1	365.8	364.5	363.2	361.8	360.5	358.5
122.5°	374.4	377.3	380.1	383.0	385.9	386.9	386.2	385.3	384.6	383.8	381.6
125°	420.6	420.3	419.9	419.6	419.2	418.7	417.9	417.2	416.4	415.7	413.6
127.5°	449.7	449.6	449.6	449.5	449.4	448.8	447.7	446.6	445.4	444.4	442.8
130°	467.8	467.9	468.0	468.1	468.3	467.7	466.5	465.2	464.1	462.9	461.7
132.5°	485.5	485.6	485.7	485.8	485.9	485.5	484.5	483.4	482.4	481.4	480.1
135°	511.0	511.3	511.5	511.7	512.0	511.5	510.4	509.3	508.2	507.1	506.1
137.5°	534.4	534.8	535.1	535.5	535.8	535.6	534.4	533.4	532.3	531.2	530.1
140°	548.9	549.5	550.1	550.5	551.1	550.9	549.9	548.9	548.0	547.0	545.7
142.5°	563.1	563.6	564.2	564.8	565.3	565.1	564.2	563.4	562.4	561.6	560.2
145°	582.9	583.4	584.0	584.6	585.0	584.9	584.2	583.4	582.7	581.9	580.0
147.5°	600.3	600.8	601.2	601.7	602.1	602.1	601.5	601.0	600.4	599.8	597.9
150°	611.0	611.4	612.0	612.6	613.1	613.0	612.4	611.7	611.1	610.4	608.7
152.5°	620.0	620.7	621.4	622.2	622.8	622.9	622.3	621.6	620.9	620.3	618.6
155°	632.5	633.5	634.3	635.2	636.0	636.2	635.6	634.9	634.2	633.6	632.3
157.5°	644.0	644.9	645.7	646.6	647.5	647.5	646.8	646.0	645.3	644.6	643.7
160°	650.7	651.5	652.3	653.1	653.8	653.8	653.2	652.5	652.0	651.3	650.6
162.5°	656.3	657.2	658.2	659.1	660.1	660.2	659.4	658.6	657.9	657.1	656.6
165°	664.5	665.3	666.1	666.8	667.6	667.6	666.8	666.1	665.3	664.5	664.2
167.5°	669.8	670.7	671.8	672.7	673.7	673.8	673.1	672.2	671.5	670.7	670.4
170°	672.9	673.9	674.9	675.8	676.8	676.9	676.2	675.4	674.7	673.9	673.6
172.5°	675.2	676.3	677.2	678.3	679.2	679.3	678.5	677.8	677.0	676.3	676.0
175°	677.3	678.4	679.5	680.6	681.7	681.8	681.1	680.3	679.6	678.8	678.5
177.5°	678.6	679.4	680.1	681.0	681.7	681.8	681.3	680.6	680.0	679.4	679.3
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1928.6	1924.0	1921.1	1910.7	1901.4	1892.2	1889.3	1890.5	1877.7	1865.6	1860.4
5°	2003.8	1989.2	1975.6	1956.1	1933.0	1907.6	1894.6	1884.5	1859.3	1831.8	1815.9
7.5°	2071.0	2050.4	2023.9	1987.3	1953.6	1913.8	1888.6	1866.1	1829.2	1790.5	1766.8
10°	2112.0	2083.9	2049.9	2005.2	1964.0	1915.6	1881.6	1847.7	1804.3	1758.1	1729.2
12.5°	2147.3	2109.3	2075.9	2018.5	1969.7	1909.2	1869.0	1821.1	1775.5	1720.5	1692.2
15°	2231.3	2161.2	2097.6	2032.6	1972.6	1888.1	1843.3	1779.0	1719.1	1651.2	1618.7
17.5°	2296.1	2217.3	2117.2	2034.7	1964.7	1871.1	1805.3	1728.3	1657.5	1579.9	1535.7
20°	2333.1	2242.8	2135.1	2036.9	1953.1	1846.3	1774.7	1696.0	1613.0	1525.5	1477.9
22.5°	2355.0	2260.1	2153.7	2028.3	1930.0	1826.0	1736.0	1649.7	1565.6	1471.2	1421.3
25°	2362.0	2275.3	2162.7	2021.1	1901.1	1783.4	1675.1	1591.3	1489.4	1401.3	1328.3
27.5°	2327.6	2265.5	2157.1	2007.4	1867.7	1730.1	1609.3	1514.4	1406.9	1311.3	1237.9
30°	2285.4	2249.3	2143.8	1993.6	1841.2	1693.1	1560.2	1452.6	1345.7	1248.9	1173.7
32.5°	2220.2	2212.3	2119.6	1974.0	1812.9	1646.3	1508.8	1400.0	1281.6	1186.5	1114.8
35°	2091.9	2126.5	2068.0	1930.0	1759.5	1579.7	1430.9	1306.6	1183.9	1092.9	1025.7
37.5°	1920.0	2006.0	1990.7	1865.8	1687.6	1507.2	1342.9	1213.1	1096.1	1004.2	938.3
40°	1801.5	1911.3	1927.1	1816.7	1636.8	1451.1	1277.1	1147.7	1033.6	949.9	883.4
42.5°	1674.3	1802.6	1846.3	1757.7	1581.3	1392.2	1218.1	1084.2	971.2	889.8	830.9
45°	1461.2	1631.0	1709.8	1659.2	1488.7	1295.1	1116.0	980.1	877.6	801.1	755.5
47.5°	1262.1	1447.6	1553.4	1535.5	1385.7	1194.0	1016.9	886.6	786.7	725.7	684.9
50°	1121.1	1311.7	1439.5	1445.4	1311.7	1121.7	944.1	821.2	729.5	672.5	639.2
52.5°	998.5	1180.5	1319.9	1350.6	1229.1	1046.6	878.7	756.6	675.8	623.4	593.6
55°	838.6	992.5	1147.1	1203.3	1105.9	932.6	777.2	669.6	593.7	557.6	531.6
57.5°	697.2	825.5	968.2	1030.5	970.3	822.0	676.4	582.9	521.4	489.7	469.8
60°	622.6	723.8	850.9	925.3	873.3	741.1	614.0	525.1	474.6	446.4	427.6
62.5°	553.3	642.9	750.4	818.4	790.0	665.4	551.6	473.2	429.5	403.0	389.5
65°	456.5	527.3	610.4	673.2	654.4	559.8	466.7	399.4	364.8	343.8	333.0
67.5°	375.9	427.1	484.7	539.7	524.5	457.5	382.7	330.4	304.5	286.4	279.9
70°	325.1	364.0	415.4	459.4	447.1	392.2	333.0	288.2	265.8	250.6	244.1
72.5°	276.5	308.6	347.7	383.7	375.4	329.8	280.4	246.6	229.4	215.4	210.1
75°	208.8	233.3	257.1	281.0	278.8	243.5	214.5	188.5	174.8	164.0	161.8
77.5°	154.1	167.9	184.1	198.2	194.3	174.1	151.4	136.5	126.4	119.1	118.0
80°	117.7	125.6	137.2	147.3	142.3	133.7	115.6	104.7	97.6	90.3	87.4
82.5°	85.4	93.3	100.3	105.8	101.9	93.8	82.7	75.3	71.0	66.0	64.8
85°	44.8	49.1	52.0	53.4	52.0	46.9	41.8	39.0	35.4	33.3	32.5
87.5°	18.9	18.8	18.6	19.5	17.5	17.3	14.8	12.8	12.4	12.2	11.2
90°	8.1	7.3	6.3	5.3	4.1	2.9	1.7	0.5	1.7	2.9	4.1
92.5°	10.6	10.1	9.7	9.5	9.6	9.7	9.8	9.9	9.8	9.7	9.6
95°	17.6	16.9	16.1	17.5	21.1	24.8	28.4	32.0	28.4	24.8	21.1
97.5°	22.1	20.4	18.6	22.8	33.0	43.2	53.3	63.4	53.3	43.2	33.0
100°	24.3	22.4	20.6	27.1	42.1	57.1	72.1	87.1	72.1	57.1	42.1
102.5°	59.9	75.5	91.0	100.4	103.5	106.7	109.9	113.0	109.9	106.7	103.5
105°	89.7	119.5	149.4	162.7	159.4	156.1	152.8	149.5	152.8	156.1	159.4
107.5°	113.6	149.4	185.1	201.7	199.1	196.4	193.8	191.1	193.8	196.4	199.1
110°	149.3	180.9	212.4	227.1	224.8	222.5	220.2	217.9	220.2	222.5	224.8





TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	232.7	240.5	248.4	251.2	249.2	247.1	245.2	243.1	245.2	247.1	249.2
115°	298.0	295.3	292.6	290.3	288.4	286.5	284.6	282.9	284.6	286.5	288.4
117.5°	332.4	330.5	328.7	326.7	324.6	322.5	320.5	318.4	320.5	322.5	324.6
120°	356.7	354.7	352.7	350.9	349.2	347.6	345.9	344.3	345.9	347.6	349.2
122.5°	379.5	377.3	375.2	373.2	371.6	369.9	368.1	366.4	368.1	369.9	371.6
125°	411.5	409.4	407.4	405.6	404.2	402.7	401.3	399.9	401.3	402.7	404.2
127.5°	441.3	439.7	438.2	436.6	435.0	433.5	431.9	430.3	431.9	433.5	435.0
130°	460.4	459.3	458.1	456.6	454.9	453.1	451.3	449.6	451.3	453.1	454.9
132.5°	479.0	477.8	476.5	475.2	473.7	472.2	470.7	469.3	470.7	472.2	473.7
135°	505.2	504.2	503.2	501.8	500.1	498.3	496.6	494.8	496.6	498.3	500.1
137.5°	529.0	527.9	526.8	525.6	524.3	523.1	521.9	520.8	521.9	523.1	524.3
140°	544.6	543.4	542.2	541.1	540.3	539.4	538.5	537.6	538.5	539.4	540.3
142.5°	558.7	557.4	556.0	555.0	554.1	553.4	552.6	551.8	552.6	553.4	554.1
145°	578.2	576.4	574.5	573.6	573.7	573.8	573.9	574.0	573.9	573.8	573.7
147.5°	596.2	594.3	592.5	591.7	592.2	592.6	593.0	593.4	593.0	592.6	592.2
150°	606.9	605.2	603.4	602.9	603.7	604.5	605.2	606.0	605.2	604.5	603.7
152.5°	617.0	615.3	613.6	613.2	614.1	614.9	615.8	616.6	615.8	614.9	614.1
155°	630.9	629.6	628.3	628.1	629.1	630.1	631.1	632.1	631.1	630.1	629.1
157.5°	642.7	641.8	640.9	640.8	641.7	642.5	643.4	644.1	643.4	642.5	641.7
160°	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3	650.6	650.0	649.3
162.5°	656.0	655.4	654.9	655.0	655.5	656.2	656.9	657.5	656.9	656.2	655.5
165°	663.8	663.5	663.3	663.4	664.0	664.7	665.3	666.0	665.3	664.7	664.0
167.5°	670.1	669.8	669.5	669.7	670.3	671.0	671.7	672.3	671.7	671.0	670.3
170°	673.4	673.3	673.0	673.3	673.9	674.6	675.2	675.8	675.2	674.6	673.9
172.5°	675.8	675.6	675.3	675.6	676.3	676.9	677.6	678.3	677.6	676.9	676.3
175°	678.3	678.2	678.0	678.2	679.0	679.8	680.5	681.3	680.5	679.8	679.0
177.5°	679.2	679.1	679.0	679.3	680.0	680.5	681.2	681.7	681.2	680.5	680.0
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1854.6	1851.2	1839.0	1832.7	1822.3	1812.4	1806.1	1809.0	1811.3	1810.2	1808.4
5°	1801.5	1787.7	1766.8	1748.7	1735.7	1711.9	1701.8	1696.8	1692.4	1687.3	1682.2
7.5°	1738.1	1716.6	1686.5	1660.8	1636.4	1606.8	1590.0	1579.9	1569.4	1558.0	1547.9
10°	1693.1	1662.7	1631.0	1594.9	1566.0	1539.3	1515.4	1499.5	1485.1	1471.4	1461.2
12.5°	1645.8	1610.8	1571.5	1522.1	1490.3	1452.0	1448.4	1420.4	1397.8	1389.3	1377.4
15°	1570.3	1521.2	1471.4	1412.9	1387.6	1352.9	1331.2	1309.6	1290.1	1276.3	1272.7
17.5°	1484.7	1421.1	1371.5	1329.5	1288.1	1252.5	1232.6	1215.2	1199.2	1180.8	1178.4
20°	1419.4	1364.4	1310.3	1273.5	1230.9	1194.7	1170.2	1152.8	1139.1	1128.2	1118.9
22.5°	1357.5	1297.4	1247.8	1207.6	1165.5	1136.3	1117.0	1100.2	1088.8	1076.9	1068.0
25°	1258.3	1211.4	1157.2	1111.6	1076.9	1058.2	1042.3	1027.8	1020.7	1012.7	1002.6
27.5°	1171.5	1119.3	1068.6	1033.3	1002.9	986.3	975.0	965.2	958.4	953.8	948.0
30°	1110.2	1057.4	1017.8	983.1	957.8	941.2	934.0	928.2	920.2	917.4	914.5
32.5°	1051.2	1003.7	969.8	939.7	915.6	904.7	898.1	893.0	886.7	883.8	878.1
35°	967.9	928.2	894.9	878.4	858.8	849.4	844.4	837.2	831.4	828.5	827.7
37.5°	889.5	855.0	833.1	811.7	803.5	797.8	790.8	785.9	784.2	783.7	783.0
40°	838.6	810.4	791.0	773.6	770.0	761.3	755.5	751.2	751.2	752.0	751.2
42.5°	792.4	767.1	749.9	734.9	730.7	725.5	719.7	719.4	720.6	723.0	720.6
45°	722.4	704.3	692.0	684.8	676.8	671.8	671.0	673.2	673.9	674.7	676.8
47.5°	657.9	645.9	634.8	626.8	623.4	622.5	621.6	625.4	628.9	630.2	633.5
50°	619.7	606.1	596.6	591.5	588.7	587.2	588.7	593.0	595.9	599.6	601.7
52.5°	577.0	567.3	560.8	556.9	555.7	556.7	556.9	561.8	566.5	567.8	568.7
55°	517.9	510.7	509.3	502.8	505.6	504.9	508.5	511.4	515.8	520.1	520.8
57.5°	458.9	453.2	449.3	449.9	450.7	453.9	456.9	462.0	466.7	471.3	471.6
60°	419.7	416.8	414.6	414.6	416.0	420.4	424.0	429.0	432.0	434.8	437.0
62.5°	383.8	381.0	378.8	379.9	383.7	386.3	390.5	393.2	396.2	399.0	400.0
65°	327.3	325.7	327.9	329.4	330.1	333.8	338.7	340.9	343.8	345.3	350.3
67.5°	275.0	275.3	275.0	277.1	281.3	282.1	286.9	292.0	292.6	295.3	298.6
70°	239.8	241.3	242.7	244.1	247.8	249.2	252.8	255.0	257.9	260.0	262.2
72.5°	207.5	207.7	209.2	208.9	211.9	215.1	218.1	220.3	223.2	225.9	228.1
75°	159.7	159.7	161.1	161.8	165.4	169.0	168.3	169.8	172.7	175.5	177.0
77.5°	116.6	115.0	116.6	117.3	118.5	121.5	122.1	124.1	127.4	126.4	128.0
80°	88.9	86.7	88.9	89.5	89.5	93.2	93.2	94.6	96.8	94.6	96.8
82.5°	63.4	62.4	64.0	64.2	65.3	65.4	66.6	66.9	69.1	68.1	69.1
85°	31.8	31.1	31.8	31.1	31.8	32.5	32.5	31.8	31.8	33.3	31.1
87.5°	10.8	10.6	10.1	10.3	9.9	9.5	9.0	9.1	9.2	8.2	8.3
90°	5.3	6.3	7.3	8.1	9.0	9.8	10.4	10.9	11.5	12.1	12.4
92.5°	9.5	9.7	10.1	10.6	10.9	11.4	11.7	12.0	12.3	12.5	12.7
95°	17.5	16.1	16.9	17.6	18.4	19.2	19.7	20.3	20.8	21.4	21.6
97.5°	22.8	18.6	20.4	22.1	23.9	25.6	26.1	26.6	27.0	27.4	27.7
100°	27.1	20.6	22.4	24.3	26.2	28.0	28.9	29.8	30.6	31.6	32.0
102.5°	100.4	91.0	75.5	59.9	44.4	28.8	30.0	31.1	32.2	33.4	34.1
105°	162.7	149.4	119.5	89.7	59.9	30.0	31.2	32.4	33.6	34.8	35.6
107.5°	201.7	185.1	149.4	113.6	77.8	42.0	40.8	39.6	38.4	37.1	36.8
110°	227.1	212.4	180.9	149.3	117.6	86.1	75.1	64.2	53.3	42.3	37.1



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	251.2	248.4	240.5	232.7	224.9	217.2	177.2	137.3	97.5	57.6	37.9
115°	290.3	292.6	295.3	298.0	300.8	303.5	252.9	202.3	151.7	101.0	71.8
117.5°	326.7	328.7	330.5	332.4	334.3	336.1	324.0	311.7	299.4	287.2	268.2
120°	350.9	352.7	354.7	356.7	358.5	360.5	361.8	363.2	364.5	365.8	359.1
122.5°	373.2	375.2	377.3	379.5	381.6	383.8	384.6	385.3	386.2	386.9	385.9
125°	405.6	407.4	409.4	411.5	413.6	415.7	416.4	417.2	417.9	418.7	419.2
127.5°	436.6	438.2	439.7	441.3	442.8	444.4	445.4	446.6	447.7	448.8	449.4
130°	456.6	458.1	459.3	460.4	461.7	462.9	464.1	465.2	466.5	467.7	468.3
132.5°	475.2	476.5	477.8	479.0	480.1	481.4	482.4	483.4	484.5	485.5	485.9
135°	501.8	503.2	504.2	505.2	506.1	507.1	508.2	509.3	510.4	511.5	512.0
137.5°	525.6	526.8	527.9	529.0	530.1	531.2	532.3	533.4	534.4	535.6	535.8
140°	541.1	542.2	543.4	544.6	545.7	547.0	548.0	548.9	549.9	550.9	551.1
142.5°	555.0	556.0	557.4	558.7	560.2	561.6	562.4	563.4	564.2	565.1	565.3
145°	573.6	574.5	576.4	578.2	580.0	581.9	582.7	583.4	584.2	584.9	585.0
147.5°	591.7	592.5	594.3	596.2	597.9	599.8	600.4	601.0	601.5	602.1	602.1
150°	602.9	603.4	605.2	606.9	608.7	610.4	611.1	611.7	612.4	613.0	613.1
152.5°	613.2	613.6	615.3	617.0	618.6	620.3	620.9	621.6	622.3	622.9	622.8
155°	628.1	628.3	629.6	630.9	632.3	633.6	634.2	634.9	635.6	636.2	636.0
157.5°	640.8	640.9	641.8	642.7	643.7	644.6	645.3	646.0	646.8	647.5	647.5
160°	648.7	648.7	649.3	650.0	650.6	651.3	652.0	652.5	653.2	653.8	653.8
162.5°	655.0	654.9	655.4	656.0	656.6	657.1	657.9	658.6	659.4	660.2	660.1
165°	663.4	663.3	663.5	663.8	664.2	664.5	665.3	666.1	666.8	667.6	667.6
167.5°	669.7	669.5	669.8	670.1	670.4	670.7	671.5	672.2	673.1	673.8	673.7
170°	673.3	673.0	673.3	673.4	673.6	673.9	674.7	675.4	676.2	676.9	676.8
172.5°	675.6	675.3	675.6	675.8	676.0	676.3	677.0	677.8	678.5	679.3	679.2
175°	678.2	678.0	678.2	678.3	678.5	678.8	679.6	680.3	681.1	681.8	681.7
177.5°	679.3	679.0	679.1	679.2	679.3	679.4	680.0	680.6	681.3	681.8	681.7
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1802.6	1801.5	1801.5	1796.3	1801.5	1801.5	1802.6	1808.4	1810.2	1811.3	1809.0
5°	1672.2	1670.0	1666.4	1670.0	1666.4	1670.0	1672.2	1682.2	1687.3	1692.4	1696.8
7.5°	1543.1	1534.5	1533.2	1524.7	1533.2	1534.5	1543.1	1547.9	1558.0	1569.4	1579.9
10°	1449.0	1443.2	1442.5	1428.7	1442.5	1443.2	1449.0	1461.2	1471.4	1485.1	1499.5
12.5°	1377.3	1363.5	1366.2	1358.2	1366.2	1363.5	1377.3	1377.4	1389.3	1397.8	1420.4
15°	1253.2	1253.2	1250.4	1238.0	1250.4	1253.2	1253.2	1272.7	1276.3	1290.1	1309.6
17.5°	1164.1	1162.6	1155.7	1159.1	1155.7	1162.6	1164.1	1178.4	1180.8	1199.2	1215.2
20°	1110.9	1106.6	1098.0	1098.0	1098.0	1106.6	1110.9	1118.9	1128.2	1139.1	1152.8
22.5°	1060.6	1060.4	1051.1	1054.0	1051.1	1060.4	1060.6	1068.0	1076.9	1088.8	1100.2
25°	1001.8	996.1	991.7	993.9	991.7	996.1	1001.8	1002.6	1012.7	1020.7	1027.8
27.5°	946.1	942.9	942.6	936.7	942.6	942.9	946.1	948.0	953.8	958.4	965.2
30°	913.7	906.5	908.0	904.4	908.0	906.5	913.7	914.5	917.4	920.2	928.2
32.5°	876.8	874.1	872.7	869.7	872.7	874.1	876.8	878.1	883.8	886.7	893.0
35°	826.3	827.1	823.4	824.9	823.4	827.1	826.3	827.7	828.5	831.4	837.2
37.5°	782.3	784.6	782.9	783.3	782.9	784.6	782.3	783.0	783.7	784.2	785.9
40°	753.4	753.4	753.4	755.5	753.4	753.4	753.4	751.2	752.0	751.2	751.2
42.5°	725.7	724.5	723.3	723.2	723.3	724.5	725.7	720.6	723.0	720.6	719.4
45°	678.3	680.4	681.2	677.5	681.2	680.4	678.3	676.8	674.7	673.9	673.2
47.5°	635.4	635.7	635.4	638.6	635.4	635.7	635.4	633.5	630.2	628.9	625.4
50°	605.3	603.9	605.3	603.9	605.3	603.9	605.3	601.7	599.6	595.9	593.0
52.5°	573.5	573.8	573.0	572.7	573.0	573.8	573.5	568.7	567.8	566.5	561.8
55°	523.7	525.1	524.4	524.4	524.4	525.1	523.7	520.8	520.1	515.8	511.4
57.5°	472.1	473.4	474.4	471.3	474.4	473.4	472.1	471.6	471.3	466.7	462.0
60°	436.3	439.9	439.1	437.7	439.1	439.9	436.3	437.0	434.8	432.0	429.0
62.5°	403.3	404.6	404.5	404.3	404.5	404.6	403.3	400.0	399.0	396.2	393.2
65°	352.5	353.9	351.8	353.9	351.8	353.9	352.5	350.3	345.3	343.8	340.9
67.5°	297.7	298.2	299.7	300.8	299.7	298.2	297.7	298.6	295.3	292.6	292.0
70°	263.6	263.0	265.1	267.3	265.1	263.0	263.6	262.2	260.0	257.9	255.0
72.5°	227.8	229.4	228.7	230.3	228.7	229.4	227.8	228.1	225.9	223.2	220.3
75°	175.5	177.7	177.0	179.2	177.0	177.7	175.5	177.0	175.5	172.7	169.8
77.5°	126.9	127.1	126.9	128.0	126.9	127.1	126.9	128.0	126.4	127.4	124.1
80°	96.8	95.4	93.9	96.8	93.9	95.4	96.8	96.8	94.6	96.8	94.6
82.5°	67.3	68.1	66.7	66.7	66.7	68.1	67.3	69.1	68.1	69.1	66.9
85°	31.1	30.3	28.9	28.9	28.9	30.3	31.1	31.1	33.3	31.8	31.8
87.5°	8.3	7.7	7.8	7.3	7.8	7.7	8.3	8.3	8.2	9.2	9.1
90°	12.6	12.8	13.1	13.3	13.1	12.8	12.6	12.4	12.1	11.5	10.9
92.5°	12.9	13.0	13.2	13.3	13.2	13.0	12.9	12.7	12.5	12.3	12.0
95°	21.5	21.4	21.3	21.1	21.3	21.4	21.5	21.6	21.4	20.8	20.3
97.5°	27.8	28.0	28.1	28.3	28.1	28.0	27.8	27.7	27.4	27.0	26.6
100°	32.3	32.5	32.7	33.0	32.7	32.5	32.3	32.0	31.6	30.6	29.8
102.5°	34.4	34.7	35.0	35.3	35.0	34.7	34.4	34.1	33.4	32.2	31.1
105°	36.1	36.5	36.9	37.4	36.9	36.5	36.1	35.6	34.8	33.6	32.4
107.5°	37.1	37.6	38.0	38.5	38.0	37.6	37.1	36.8	37.1	38.4	39.6
110°	37.5	38.0	38.5	38.8	38.5	38.0	37.5	37.1	42.3	53.3	64.2



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	38.2	38.5	38.9	39.2	38.9	38.5	38.2	37.9	57.6	97.5	137.3
115°	63.9	56.1	48.2	40.3	48.2	56.1	63.9	71.8	101.0	151.7	202.3
117.5°	242.2	216.4	190.6	164.7	190.6	216.4	242.2	268.2	287.2	299.4	311.7
120°	344.3	329.6	314.8	300.0	314.8	329.6	344.3	359.1	365.8	364.5	363.2
122.5°	383.0	380.1	377.3	374.4	377.3	380.1	383.0	385.9	386.9	386.2	385.3
125°	419.6	419.9	420.3	420.6	420.3	419.9	419.6	419.2	418.7	417.9	417.2
127.5°	449.5	449.6	449.6	449.7	449.6	449.6	449.5	449.4	448.8	447.7	446.6
130°	468.1	468.0	467.9	467.8	467.9	468.0	468.1	468.3	467.7	466.5	465.2
132.5°	485.8	485.7	485.6	485.5	485.6	485.7	485.8	485.9	485.5	484.5	483.4
135°	511.7	511.5	511.3	511.0	511.3	511.5	511.7	512.0	511.5	510.4	509.3
137.5°	535.5	535.1	534.8	534.4	534.8	535.1	535.5	535.8	535.6	534.4	533.4
140°	550.5	550.1	549.5	548.9	549.5	550.1	550.5	551.1	550.9	549.9	548.9
142.5°	564.8	564.2	563.6	563.1	563.6	564.2	564.8	565.3	565.1	564.2	563.4
145°	584.6	584.0	583.4	582.9	583.4	584.0	584.6	585.0	584.9	584.2	583.4
147.5°	601.7	601.2	600.8	600.3	600.8	601.2	601.7	602.1	602.1	601.5	601.0
150°	612.6	612.0	611.4	611.0	611.4	612.0	612.6	613.1	613.0	612.4	611.7
152.5°	622.2	621.4	620.7	620.0	620.7	621.4	622.2	622.8	622.9	622.3	621.6
155°	635.2	634.3	633.5	632.5	633.5	634.3	635.2	636.0	636.2	635.6	634.9
157.5°	646.6	645.7	644.9	644.0	644.9	645.7	646.6	647.5	647.5	646.8	646.0
160°	653.1	652.3	651.5	650.7	651.5	652.3	653.1	653.8	653.8	653.2	652.5
162.5°	659.1	658.2	657.2	656.3	657.2	658.2	659.1	660.1	660.2	659.4	658.6
165°	666.8	666.1	665.3	664.5	665.3	666.1	666.8	667.6	667.6	666.8	666.1
167.5°	672.7	671.8	670.7	669.8	670.7	671.8	672.7	673.7	673.8	673.1	672.2
170°	675.8	674.9	673.9	672.9	673.9	674.9	675.8	676.8	676.9	676.2	675.4
172.5°	678.3	677.2	676.3	675.2	676.3	677.2	678.3	679.2	679.3	678.5	677.8
175°	680.6	679.5	678.4	677.3	678.4	679.5	680.6	681.7	681.8	681.1	680.3
177.5°	681.0	680.1	679.4	678.6	679.4	680.1	681.0	681.7	681.8	681.3	680.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1806.1	1812.4	1822.3	1832.7	1839.0	1851.2	1854.6	1860.4	1865.6	1877.7	1890.5
5°	1701.8	1711.9	1735.7	1748.7	1766.8	1787.7	1801.5	1815.9	1831.8	1859.3	1884.5
7.5°	1590.0	1606.8	1636.4	1660.8	1686.5	1716.6	1738.1	1766.8	1790.5	1829.2	1866.1
10°	1515.4	1539.3	1566.0	1594.9	1631.0	1662.7	1693.1	1729.2	1758.1	1804.3	1847.7
12.5°	1448.4	1452.0	1490.3	1522.1	1571.5	1610.8	1645.8	1692.2	1720.5	1775.5	1821.1
15°	1331.2	1352.9	1387.6	1412.9	1471.4	1521.2	1570.3	1618.7	1651.2	1719.1	1779.0
17.5°	1232.6	1252.5	1288.1	1329.5	1371.5	1421.1	1484.7	1535.7	1579.9	1657.5	1728.3
20°	1170.2	1194.7	1230.9	1273.5	1310.3	1364.4	1419.4	1477.9	1525.5	1613.0	1696.0
22.5°	1117.0	1136.3	1165.5	1207.6	1247.8	1297.4	1357.5	1421.3	1471.2	1565.6	1649.7
25°	1042.3	1058.2	1076.9	1111.6	1157.2	1211.4	1258.3	1328.3	1401.3	1489.4	1591.3
27.5°	975.0	986.3	1002.9	1033.3	1068.6	1119.3	1171.5	1237.9	1311.3	1406.9	1514.4
30°	934.0	941.2	957.8	983.1	1017.8	1057.4	1110.2	1173.7	1248.9	1345.7	1452.6
32.5°	898.1	904.7	915.6	939.7	969.8	1003.7	1051.2	1114.8	1186.5	1281.6	1400.0
35°	844.4	849.4	858.8	878.4	894.9	928.2	967.9	1025.7	1092.9	1183.9	1306.6
37.5°	790.8	797.8	803.5	811.7	833.1	855.0	889.5	938.3	1004.2	1096.1	1213.1
40°	755.5	761.3	770.0	773.6	791.0	810.4	838.6	883.4	949.9	1033.6	1147.7
42.5°	719.7	725.5	730.7	734.9	749.9	767.1	792.4	830.9	889.8	971.2	1084.2
45°	671.0	671.8	676.8	684.8	692.0	704.3	722.4	755.5	801.1	877.6	980.1
47.5°	621.6	622.5	623.4	626.8	634.8	645.9	657.9	684.9	725.7	786.7	886.6
50°	588.7	587.2	588.7	591.5	596.6	606.1	619.7	639.2	672.5	729.5	821.2
52.5°	556.9	556.7	555.7	556.9	560.8	567.3	577.0	593.6	623.4	675.8	756.6
55°	508.5	504.9	505.6	502.8	509.3	510.7	517.9	531.6	557.6	593.7	669.6
57.5°	456.9	453.9	450.7	449.9	449.3	453.2	458.9	469.8	489.7	521.4	582.9
60°	424.0	420.4	416.0	414.6	414.6	416.8	419.7	427.6	446.4	474.6	525.1
62.5°	390.5	386.3	383.7	379.9	378.8	381.0	383.8	389.5	403.0	429.5	473.2
65°	338.7	333.8	330.1	329.4	327.9	325.7	327.3	333.0	343.8	364.8	399.4
67.5°	286.9	282.1	281.3	277.1	275.0	275.3	275.0	279.9	286.4	304.5	330.4
70°	252.8	249.2	247.8	244.1	242.7	241.3	239.8	244.1	250.6	265.8	288.2
72.5°	218.1	215.1	211.9	208.9	209.2	207.7	207.5	210.1	215.4	229.4	246.6
75°	168.3	169.0	165.4	161.8	161.1	159.7	159.7	161.8	164.0	174.8	188.5
77.5°	122.1	121.5	118.5	117.3	116.6	115.0	116.6	118.0	119.1	126.4	136.5
80°	93.2	93.2	89.5	89.5	88.9	86.7	88.9	87.4	90.3	97.6	104.7
82.5°	66.6	65.4	65.3	64.2	64.0	62.4	63.4	64.8	66.0	71.0	75.3
85°	32.5	32.5	31.8	31.1	31.8	31.1	31.8	32.5	33.3	35.4	39.0
87.5°	9.0	9.5	9.9	10.3	10.1	10.6	10.8	11.2	12.2	12.4	12.8
90°	10.4	9.8	9.0	8.1	7.3	6.3	5.3	4.1	2.9	1.7	0.5
92.5°	11.7	11.4	10.9	10.6	10.1	9.7	9.5	9.6	9.7	9.8	9.9
95°	19.7	19.2	18.4	17.6	16.9	16.1	17.5	21.1	24.8	28.4	32.0
97.5°	26.1	25.6	23.9	22.1	20.4	18.6	22.8	33.0	43.2	53.3	63.4
100°	28.9	28.0	26.2	24.3	22.4	20.6	27.1	42.1	57.1	72.1	87.1
102.5°	30.0	28.8	44.4	59.9	75.5	91.0	100.4	103.5	106.7	109.9	113.0
105°	31.2	30.0	59.9	89.7	119.5	149.4	162.7	159.4	156.1	152.8	149.5
107.5°	40.8	42.0	77.8	113.6	149.4	185.1	201.7	199.1	196.4	193.8	191.1
110°	75.1	86.1	117.6	149.3	180.9	212.4	227.1	224.8	222.5	220.2	217.9



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	177.2	217.2	224.9	232.7	240.5	248.4	251.2	249.2	247.1	245.2	243.1
115°	252.9	303.5	300.8	298.0	295.3	292.6	290.3	288.4	286.5	284.6	282.9
117.5°	324.0	336.1	334.3	332.4	330.5	328.7	326.7	324.6	322.5	320.5	318.4
120°	361.8	360.5	358.5	356.7	354.7	352.7	350.9	349.2	347.6	345.9	344.3
122.5°	384.6	383.8	381.6	379.5	377.3	375.2	373.2	371.6	369.9	368.1	366.4
125°	416.4	415.7	413.6	411.5	409.4	407.4	405.6	404.2	402.7	401.3	399.9
127.5°	445.4	444.4	442.8	441.3	439.7	438.2	436.6	435.0	433.5	431.9	430.3
130°	464.1	462.9	461.7	460.4	459.3	458.1	456.6	454.9	453.1	451.3	449.6
132.5°	482.4	481.4	480.1	479.0	477.8	476.5	475.2	473.7	472.2	470.7	469.3
135°	508.2	507.1	506.1	505.2	504.2	503.2	501.8	500.1	498.3	496.6	494.8
137.5°	532.3	531.2	530.1	529.0	527.9	526.8	525.6	524.3	523.1	521.9	520.8
140°	548.0	547.0	545.7	544.6	543.4	542.2	541.1	540.3	539.4	538.5	537.6
142.5°	562.4	561.6	560.2	558.7	557.4	556.0	555.0	554.1	553.4	552.6	551.8
145°	582.7	581.9	580.0	578.2	576.4	574.5	573.6	573.7	573.8	573.9	574.0
147.5°	600.4	599.8	597.9	596.2	594.3	592.5	591.7	592.2	592.6	593.0	593.4
150°	611.1	610.4	608.7	606.9	605.2	603.4	602.9	603.7	604.5	605.2	606.0
152.5°	620.9	620.3	618.6	617.0	615.3	613.6	613.2	614.1	614.9	615.8	616.6
155°	634.2	633.6	632.3	630.9	629.6	628.3	628.1	629.1	630.1	631.1	632.1
157.5°	645.3	644.6	643.7	642.7	641.8	640.9	640.8	641.7	642.5	643.4	644.1
160°	652.0	651.3	650.6	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3
162.5°	657.9	657.1	656.6	656.0	655.4	654.9	655.0	655.5	656.2	656.9	657.5
165°	665.3	664.5	664.2	663.8	663.5	663.3	663.4	664.0	664.7	665.3	666.0
167.5°	671.5	670.7	670.4	670.1	669.8	669.5	669.7	670.3	671.0	671.7	672.3
170°	674.7	673.9	673.6	673.4	673.3	673.0	673.3	673.9	674.6	675.2	675.8
172.5°	677.0	676.3	676.0	675.8	675.6	675.3	675.6	676.3	676.9	677.6	678.3
175°	679.6	678.8	678.5	678.3	678.2	678.0	678.2	679.0	679.8	680.5	681.3
177.5°	680.0	679.4	679.3	679.2	679.1	679.0	679.3	680.0	680.5	681.2	681.7
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1889.3	1892.2	1901.4	1910.7	1921.1	1924.0	1928.6	1924.6	1923.4	1934.4	1942.5
5°	1894.6	1907.6	1933.0	1956.1	1975.6	1989.2	2003.8	2009.5	2020.3	2035.5	2054.3
7.5°	1888.6	1913.8	1953.6	1987.3	2023.9	2050.4	2071.0	2088.7	2110.1	2138.8	2170.1
10°	1881.6	1915.6	1964.0	2005.2	2049.9	2083.9	2112.0	2139.5	2171.3	2211.0	2252.2
12.5°	1869.0	1909.2	1969.7	2018.5	2075.9	2109.3	2147.3	2206.6	2240.6	2295.9	2353.9
15°	1843.3	1888.1	1972.6	2032.6	2097.6	2161.2	2231.3	2287.6	2343.9	2376.4	2458.1
17.5°	1805.3	1871.1	1964.7	2034.7	2117.2	2217.3	2296.1	2359.9	2425.0	2477.7	2518.6
20°	1774.7	1846.3	1953.1	2036.9	2135.1	2242.8	2333.1	2398.1	2454.5	2498.5	2523.8
22.5°	1736.0	1826.0	1930.0	2028.3	2153.7	2260.1	2355.0	2406.2	2453.2	2474.8	2484.4
25°	1675.1	1783.4	1901.1	2021.1	2162.7	2275.3	2362.0	2393.0	2406.8	2385.9	2351.2
27.5°	1609.3	1730.1	1867.7	2007.4	2157.1	2265.5	2327.6	2322.7	2299.4	2231.7	2177.5
30°	1560.2	1693.1	1841.2	1993.6	2143.8	2249.3	2285.4	2249.3	2196.6	2120.7	2043.4
32.5°	1508.8	1646.3	1812.9	1974.0	2119.6	2212.3	2220.2	2158.0	2076.4	1990.2	1893.8
35°	1430.9	1579.7	1759.5	1930.0	2068.0	2126.5	2091.9	1982.1	1885.3	1767.6	1636.1
37.5°	1342.9	1507.2	1687.6	1865.8	1990.7	2006.0	1920.0	1804.3	1667.8	1529.5	1374.7
40°	1277.1	1451.1	1636.8	1816.7	1927.1	1911.3	1801.5	1674.3	1511.8	1342.7	1199.0
42.5°	1218.1	1392.2	1581.3	1757.7	1846.3	1802.6	1674.3	1518.3	1343.7	1184.5	1052.8
45°	1116.0	1295.1	1488.7	1659.2	1709.8	1631.0	1461.2	1287.9	1116.0	983.1	879.1
47.5°	1016.9	1194.0	1385.7	1535.5	1553.4	1447.6	1262.1	1083.6	935.9	827.6	754.2
50°	944.1	1121.7	1311.7	1445.4	1439.5	1311.7	1121.1	951.3	827.7	740.4	691.3
52.5°	878.7	1046.6	1229.1	1350.6	1319.9	1180.5	998.5	847.8	746.3	678.0	633.5
55°	777.2	932.6	1105.9	1203.3	1147.1	992.5	838.6	717.3	642.2	590.9	556.2
57.5°	676.4	822.0	970.3	1030.5	968.2	825.5	697.2	609.2	552.7	514.7	492.2
60°	614.0	741.1	873.3	925.3	850.9	723.8	622.6	543.9	498.4	467.3	447.1
62.5°	551.6	665.4	790.0	818.4	750.4	642.9	553.3	487.9	450.4	422.8	403.8
65°	466.7	559.8	654.4	673.2	610.4	527.3	456.5	413.9	380.7	360.4	345.3
67.5°	382.7	457.5	524.5	539.7	484.7	427.1	375.9	338.7	316.2	299.4	286.6
70°	333.0	392.2	447.1	459.4	415.4	364.0	325.1	295.4	275.2	260.8	248.5
72.5°	280.4	329.8	375.4	383.7	347.7	308.6	276.5	253.3	235.4	226.1	214.4
75°	214.5	243.5	278.8	281.0	257.1	233.3	208.8	193.6	184.2	172.7	166.8
77.5°	151.4	174.1	194.3	198.2	184.1	167.9	154.1	142.1	134.2	128.8	123.5
80°	115.6	133.7	142.3	147.3	137.2	125.6	117.7	109.8	104.7	101.1	97.6
82.5°	82.7	93.8	101.9	105.8	100.3	93.3	85.4	80.9	77.0	74.0	72.7
85°	41.8	46.9	52.0	53.4	52.0	49.1	44.8	44.8	42.6	41.8	41.8
87.5°	14.8	17.3	17.5	19.5	18.6	18.8	18.9	18.6	18.2	17.7	17.2
90°	1.7	2.9	4.1	5.3	6.3	7.3	8.1	9.0	9.8	10.4	10.9
92.5°	9.8	9.7	9.6	9.5	9.7	10.1	10.6	10.9	11.4	11.7	12.0
95°	28.4	24.8	21.1	17.5	16.1	16.9	17.6	18.4	19.2	19.7	20.3
97.5°	53.3	43.2	33.0	22.8	18.6	20.4	22.1	23.9	25.6	26.1	26.6
100°	72.1	57.1	42.1	27.1	20.6	22.4	24.3	26.2	28.0	28.9	29.8
102.5°	109.9	106.7	103.5	100.4	91.0	75.5	59.9	44.4	28.8	30.0	31.1
105°	152.8	156.1	159.4	162.7	149.4	119.5	89.7	59.9	30.0	31.2	32.4
107.5°	193.8	196.4	199.1	201.7	185.1	149.4	113.6	77.8	42.0	40.8	39.6
110°	220.2	222.5	224.8	227.1	212.4	180.9	149.3	117.6	86.1	75.1	64.2





TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	245.2	247.1	249.2	251.2	248.4	240.5	232.7	224.9	217.2	177.2	137.3
115°	284.6	286.5	288.4	290.3	292.6	295.3	298.0	300.8	303.5	252.9	202.3
117.5°	320.5	322.5	324.6	326.7	328.7	330.5	332.4	334.3	336.1	324.0	311.7
120°	345.9	347.6	349.2	350.9	352.7	354.7	356.7	358.5	360.5	361.8	363.2
122.5°	368.1	369.9	371.6	373.2	375.2	377.3	379.5	381.6	383.8	384.6	385.3
125°	401.3	402.7	404.2	405.6	407.4	409.4	411.5	413.6	415.7	416.4	417.2
127.5°	431.9	433.5	435.0	436.6	438.2	439.7	441.3	442.8	444.4	445.4	446.6
130°	451.3	453.1	454.9	456.6	458.1	459.3	460.4	461.7	462.9	464.1	465.2
132.5°	470.7	472.2	473.7	475.2	476.5	477.8	479.0	480.1	481.4	482.4	483.4
135°	496.6	498.3	500.1	501.8	503.2	504.2	505.2	506.1	507.1	508.2	509.3
137.5°	521.9	523.1	524.3	525.6	526.8	527.9	529.0	530.1	531.2	532.3	533.4
140°	538.5	539.4	540.3	541.1	542.2	543.4	544.6	545.7	547.0	548.0	548.9
142.5°	552.6	553.4	554.1	555.0	556.0	557.4	558.7	560.2	561.6	562.4	563.4
145°	573.9	573.8	573.7	573.6	574.5	576.4	578.2	580.0	581.9	582.7	583.4
147.5°	593.0	592.6	592.2	591.7	592.5	594.3	596.2	597.9	599.8	600.4	601.0
150°	605.2	604.5	603.7	602.9	603.4	605.2	606.9	608.7	610.4	611.1	611.7
152.5°	615.8	614.9	614.1	613.2	613.6	615.3	617.0	618.6	620.3	620.9	621.6
155°	631.1	630.1	629.1	628.1	628.3	629.6	630.9	632.3	633.6	634.2	634.9
157.5°	643.4	642.5	641.7	640.8	640.9	641.8	642.7	643.7	644.6	645.3	646.0
160°	650.6	650.0	649.3	648.7	648.7	649.3	650.0	650.6	651.3	652.0	652.5
162.5°	656.9	656.2	655.5	655.0	654.9	655.4	656.0	656.6	657.1	657.9	658.6
165°	665.3	664.7	664.0	663.4	663.3	663.5	663.8	664.2	664.5	665.3	666.1
167.5°	671.7	671.0	670.3	669.7	669.5	669.8	670.1	670.4	670.7	671.5	672.2
170°	675.2	674.6	673.9	673.3	673.0	673.3	673.4	673.6	673.9	674.7	675.4
172.5°	677.6	676.9	676.3	675.6	675.3	675.6	675.8	676.0	676.3	677.0	677.8
175°	680.5	679.8	679.0	678.2	678.0	678.2	678.3	678.5	678.8	679.6	680.3
177.5°	681.2	680.5	680.0	679.3	679.0	679.1	679.2	679.3	679.4	680.0	680.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8	679.8



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4	1879.4
2.5°	1949.4	1957.5	1957.5	1958.6	1967.8	1966.7	1966.1
5°	2074.5	2086.8	2088.2	2101.2	2109.9	2107.0	2099.0
7.5°	2192.5	2215.4	2232.7	2242.4	2253.8	2260.9	2257.7
10°	2286.1	2319.4	2339.6	2353.3	2369.9	2382.2	2377.8
12.5°	2371.1	2410.6	2438.5	2461.9	2464.1	2479.8	2469.2
15°	2503.6	2545.4	2549.8	2567.1	2580.9	2579.4	2580.1
17.5°	2547.3	2560.8	2563.5	2563.9	2564.1	2559.0	2548.1
20°	2531.8	2526.7	2514.4	2505.0	2488.4	2486.2	2471.8
22.5°	2457.8	2441.8	2410.9	2390.6	2364.7	2358.0	2353.9
25°	2312.2	2276.7	2227.6	2180.7	2167.7	2142.4	2149.7
27.5°	2112.3	2057.2	2004.0	1965.9	1931.4	1893.5	1904.3
30°	1971.9	1909.8	1834.7	1776.9	1740.0	1703.9	1697.4
32.5°	1804.3	1713.4	1629.6	1578.7	1522.2	1499.4	1474.4
35°	1515.4	1426.5	1343.5	1272.0	1230.9	1199.0	1170.2
37.5°	1255.6	1153.3	1086.2	1028.3	998.5	980.3	985.0
40°	1094.3	1004.8	955.6	911.5	884.1	871.1	874.0
42.5°	963.7	896.6	856.2	826.0	806.7	799.5	797.8
45°	815.5	778.0	744.7	727.4	718.0	710.0	705.0
47.5°	714.4	683.7	665.0	654.7	646.5	638.4	638.2
50°	653.7	633.5	620.5	609.6	603.1	597.4	602.4
52.5°	607.5	589.0	576.0	566.3	563.8	558.6	558.5
55°	538.9	524.4	515.0	506.3	502.0	499.1	495.5
57.5°	476.5	462.7	454.0	448.6	440.4	437.4	436.3
60°	432.0	421.1	412.5	405.2	401.6	395.9	395.9
62.5°	390.9	380.1	372.0	366.5	360.6	358.3	358.8
65°	331.6	322.9	314.9	309.2	307.7	303.4	304.8
67.5°	276.9	271.2	262.8	259.6	256.8	254.6	252.8
70°	240.5	234.8	230.5	226.1	223.9	223.9	223.9
72.5°	209.9	202.9	200.4	194.9	196.1	193.9	191.5
75°	162.5	158.2	156.0	153.8	150.2	150.2	150.2
77.5°	119.6	118.3	115.7	113.4	112.5	111.8	112.1
80°	92.5	91.7	90.3	90.3	88.9	88.1	86.7
82.5°	71.1	69.2	68.3	67.8	67.5	67.3	67.0
85°	40.4	39.0	39.0	39.7	38.3	38.3	39.0
87.5°	17.9	18.0	17.5	17.5	18.2	17.6	17.7
90°	11.5	12.1	12.4	12.6	12.8	13.1	13.3
92.5°	12.3	12.5	12.7	12.9	13.0	13.2	13.3
95°	20.8	21.4	21.6	21.5	21.4	21.3	21.1
97.5°	27.0	27.4	27.7	27.8	28.0	28.1	28.3
100°	30.6	31.6	32.0	32.3	32.5	32.7	33.0
102.5°	32.2	33.4	34.1	34.4	34.7	35.0	35.3
105°	33.6	34.8	35.6	36.1	36.5	36.9	37.4
107.5°	38.4	37.1	36.8	37.1	37.6	38.0	38.5
110°	53.3	42.3	37.1	37.5	38.0	38.5	38.8



TEST NUMBER: P331429-830

CATALOG NUMBER: SA2XXDIP-C1005D530U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	97.5	57.6	37.9	38.2	38.5	38.9	39.2
115°	151.7	101.0	71.8	63.9	56.1	48.2	40.3
117.5°	299.4	287.2	268.2	242.2	216.4	190.6	164.7
120°	364.5	365.8	359.1	344.3	329.6	314.8	300.0
122.5°	386.2	386.9	385.9	383.0	380.1	377.3	374.4
125°	417.9	418.7	419.2	419.6	419.9	420.3	420.6
127.5°	447.7	448.8	449.4	449.5	449.6	449.6	449.7
130°	466.5	467.7	468.3	468.1	468.0	467.9	467.8
132.5°	484.5	485.5	485.9	485.8	485.7	485.6	485.5
135°	510.4	511.5	512.0	511.7	511.5	511.3	511.0
137.5°	534.4	535.6	535.8	535.5	535.1	534.8	534.4
140°	549.9	550.9	551.1	550.5	550.1	549.5	548.9
142.5°	564.2	565.1	565.3	564.8	564.2	563.6	563.1
145°	584.2	584.9	585.0	584.6	584.0	583.4	582.9
147.5°	601.5	602.1	602.1	601.7	601.2	600.8	600.3
150°	612.4	613.0	613.1	612.6	612.0	611.4	611.0
152.5°	622.3	622.9	622.8	622.2	621.4	620.7	620.0
155°	635.6	636.2	636.0	635.2	634.3	633.5	632.5
157.5°	646.8	647.5	647.5	646.6	645.7	644.9	644.0
160°	653.2	653.8	653.8	653.1	652.3	651.5	650.7
162.5°	659.4	660.2	660.1	659.1	658.2	657.2	656.3
165°	666.8	667.6	667.6	666.8	666.1	665.3	664.5
167.5°	673.1	673.8	673.7	672.7	671.8	670.7	669.8
170°	676.2	676.9	676.8	675.8	674.9	673.9	672.9
172.5°	678.5	679.3	679.2	678.3	677.2	676.3	675.2
175°	681.1	681.8	681.7	680.6	679.5	678.4	677.3
177.5°	681.3	681.8	681.7	681.0	680.1	679.4	678.6
180°	679.8	679.8	679.8	679.8	679.8	679.8	679.8

(END OF REPORT)