

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331618

Luminaire Tested: **SA2XXRDIP-C290D330U835-4F0-1E-UDD-F**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331618
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D330U835-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2343.0 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 20.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331618
CATALOG NUMBER: SA2XXRDIP-C290D330U835-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331618

CATALOG NUMBER: SA2XXRDIP-C290D330U835-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44				44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44				38	
2	89	81	76	71	81	75	70	66	62	59	56	51	49	46	41	39	37				32	
3	81	72	65	59	74	66	60	55	55	51	47	46	42	40	36	34	32				28	
4	74	64	56	51	68	59	52	47	50	45	41	41	37	34	33	30	28				24	
5	68	57	49	44	62	53	46	41	45	39	35	37	33	30	30	27	25				21	
6	63	51	44	38	58	48	41	36	40	35	31	33	29	26	27	24	22				19	
7	58	46	39	33	53	43	36	31	37	31	27	31	27	24	25	22	20				17	
8	54	42	35	30	50	39	33	28	33	28	24	28	24	21	23	20	18				15	
9	51	39	31	26	46	36	29	25	31	26	22	26	22	19	21	18	16				14	
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15				13	

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8105	8105	8105
5°	8136	8003	8047
10°	8073	7873	7806
15°	7980	7639	7418
20°	7852	7306	6940
25°	7721	6928	6474
30°	7538	6538	5878
35°	7360	6116	5355
40°	7181	5678	4749
45°	6971	5186	4201
50°	6754	4690	3662
55°	6533	4155	3147
60°	6278	3594	2612
65°	5987	3018	2376
70°	5641	2488	2186
75°	5215	2264	2040
80°	4603	2027	1860
85°	3612	1593	1593



TEST NUMBER: P331618

CATALOG NUMBER: SA2XXRDIP-C290D330U835-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	2.0
10°-20°	129.0	5.5
20°-30°	181.2	7.7
30°-40°	197.6	8.4
40°-50°	181.6	7.8
50°-60°	142.7	6.1
60°-70°	93.0	4.0
70°-80°	48.0	2.0
80°-90°	13.5	0.6
90°-100°	14.9	0.6
100°-110°	54.7	2.3
110°-120°	146.1	6.2
120°-130°	241.2	10.3
130°-140°	256.5	10.9
140°-150°	238.4	10.2
150°-160°	191.7	8.2
160°-170°	123.5	5.3
170°-180°	42.5	1.8
0°-30°	357.2	15.2
0°-40°	554.7	23.7
0°-60°	879.0	37.5
0°-90°	1033.5	44.1
90°-120°	215.7	9.2
90°-150°	951.8	40.6
90°-180°	1309.0	55.9
0°-180°	2343.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	502	500	494	498	496	48
15°	477	472	457	449	444	134
25°	433	418	389	371	363	199
35°	373	349	310	283	272	234
45°	305	274	227	196	184	236
55°	232	196	148	121	112	207
65°	157	120	79	64	62	155
75°	84	53	36	33	33	88
85°	20	10	9	9	9	23
90°	0	4	6	8	9	2
95°	21	11	13	14	14	26
105°	98	103	20	23	25	105
115°	186	192	200	57	26	183
125°	263	267	273	275	276	234
135°	325	330	333	336	336	251
145°	377	377	382	385	383	236
155°	416	413	416	418	416	191
165°	438	436	437	439	437	124
175°	448	446	446	448	445	43
180°	447	447	447	447	447	



TEST NUMBER: P331618

CATALOG NUMBER: SA2XXRDIP-C290D330U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	503.8	503.4	503.0	502.6	502.2	501.5	500.6	499.8	498.9	498.0	498.8
5°	502.0	501.5	501.0	500.5	500.0	499.0	497.7	496.4	495.1	493.8	494.7
7.5°	496.8	496.2	495.5	494.9	494.3	493.2	491.7	490.1	488.6	487.1	487.3
10°	492.4	491.7	491.0	490.3	489.6	488.2	486.2	484.2	482.2	480.2	479.9
12.5°	487.0	486.1	485.2	484.4	483.5	481.8	479.2	476.6	474.0	471.4	470.9
15°	477.4	476.3	475.2	474.1	473.0	470.7	467.3	463.9	460.4	457.0	455.1
17.5°	465.7	464.0	462.3	460.6	458.9	455.9	451.5	447.1	442.7	438.3	436.0
20°	457.0	455.0	453.0	450.9	448.9	445.4	440.3	435.3	430.3	425.2	422.7
22.5°	447.6	445.3	443.0	440.8	438.5	434.5	428.8	423.1	417.5	411.8	408.5
25°	433.4	430.1	426.9	423.7	420.5	415.5	408.8	402.2	395.5	388.9	384.7
27.5°	416.3	412.8	409.3	405.8	402.2	396.7	389.2	381.7	374.2	366.7	361.9
30°	404.3	400.5	396.6	392.8	389.0	383.0	374.9	366.9	358.8	350.7	345.6
32.5°	392.7	388.2	383.7	379.2	374.7	368.4	360.2	351.9	343.7	335.4	329.6
35°	373.4	368.3	363.1	358.0	352.8	345.8	336.9	328.0	319.2	310.3	303.9
37.5°	354.2	348.5	342.8	337.2	331.5	324.0	314.5	305.0	295.6	286.1	279.1
40°	340.7	334.7	328.6	322.5	316.5	308.6	298.8	289.0	279.2	269.4	262.2
42.5°	326.9	320.5	314.1	307.8	301.4	293.1	283.0	272.9	262.8	252.7	245.3
45°	305.3	298.5	291.7	285.0	278.2	269.5	258.9	248.3	237.7	227.1	220.0
47.5°	284.2	277.0	269.9	262.7	255.5	246.5	235.5	224.6	213.6	202.7	195.6
50°	268.9	261.8	254.6	247.4	240.3	231.1	220.0	208.9	197.8	186.7	179.7
52.5°	254.0	246.5	239.1	231.6	224.1	214.9	204.0	193.2	182.3	171.4	164.7
55°	232.1	224.3	216.4	208.5	200.6	191.3	180.3	169.4	158.5	147.6	141.6
57.5°	209.7	201.6	193.5	185.5	177.4	168.1	157.6	147.2	136.7	126.2	120.6
60°	194.4	186.4	178.3	170.2	162.1	152.9	142.5	132.1	121.7	111.3	106.1
62.5°	179.5	171.5	163.4	155.3	147.2	138.2	128.3	118.4	108.5	98.6	93.7
65°	156.7	148.5	140.4	132.2	124.0	115.4	106.3	97.2	88.1	79.0	75.6
67.5°	134.7	126.6	118.5	110.4	102.3	94.1	85.9	77.8	69.6	61.4	59.8
70°	119.5	111.6	103.7	95.9	88.0	80.6	73.6	66.6	59.7	52.7	51.7
72.5°	104.9	97.4	89.8	82.3	74.7	68.2	62.6	57.0	51.4	45.8	44.9
75°	83.6	76.5	69.5	62.4	55.3	50.1	46.6	43.2	39.8	36.3	35.6
77.5°	62.6	56.4	50.2	44.0	37.8	33.9	32.2	30.6	28.9	27.3	26.9
80°	49.5	44.4	39.2	34.1	28.9	25.8	24.8	23.8	22.8	21.8	21.4
82.5°	37.5	33.5	29.5	25.5	21.5	19.1	18.4	17.7	17.0	16.4	16.1
85°	19.5	17.4	15.3	13.2	11.1	9.8	9.5	9.2	8.9	8.6	8.6
87.5°	5.9	5.4	4.9	4.4	3.9	3.7	3.9	4.0	4.1	4.2	4.2
90°	0.3	1.1	1.9	2.7	3.5	4.2	4.7	5.3	5.9	6.5	6.8
92.5°	6.5	6.5	6.4	6.3	6.2	6.4	6.6	6.9	7.2	7.5	7.7
95°	21.0	18.6	16.3	13.9	11.5	10.6	11.1	11.6	12.1	12.6	13.0
97.5°	41.7	35.0	28.3	21.7	15.0	12.2	13.4	14.5	15.7	16.9	17.2
100°	57.2	47.4	37.5	27.7	17.9	13.5	14.8	16.0	17.2	18.4	19.0
102.5°	74.3	72.2	70.1	68.1	66.0	59.8	49.6	39.4	29.2	18.9	19.7
105°	98.3	100.4	102.6	104.8	106.9	98.2	78.6	59.0	39.3	19.7	20.5
107.5°	125.6	127.4	129.1	130.9	132.6	121.7	98.2	74.7	51.1	27.6	26.8
110°	143.2	144.7	146.3	147.8	149.3	139.6	118.9	98.1	77.3	56.6	49.4



TEST NUMBER: P331618

CATALOG NUMBER: SA2XXRDIP-C290D330U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	159.8	161.1	162.5	163.8	165.1	163.2	158.1	153.0	147.8	142.7	116.5
115°	185.9	187.1	188.4	189.6	190.8	192.3	194.1	195.9	197.7	199.5	166.2
117.5°	209.3	210.6	212.0	213.4	214.7	216.0	217.3	218.5	219.7	221.0	212.9
120°	226.3	227.4	228.5	229.6	230.6	231.8	233.1	234.4	235.7	237.0	237.9
122.5°	240.8	242.0	243.1	244.2	245.4	246.6	248.0	249.4	250.9	252.3	252.8
125°	262.9	263.8	264.7	265.7	266.6	267.8	269.1	270.5	271.8	273.2	273.7
127.5°	282.8	283.9	284.9	286.0	287.0	288.0	289.0	290.1	291.1	292.1	292.8
130°	295.5	296.7	297.8	299.0	300.1	301.1	301.9	302.7	303.5	304.3	305.0
132.5°	308.5	309.4	310.4	311.4	312.4	313.2	314.0	314.8	315.6	316.4	317.1
135°	325.3	326.4	327.6	328.7	329.9	330.8	331.4	332.1	332.7	333.4	334.1
137.5°	342.3	343.1	343.9	344.7	345.5	346.3	347.0	347.7	348.5	349.2	349.9
140°	353.4	354.0	354.5	355.1	355.7	356.4	357.2	358.0	358.8	359.5	360.2
142.5°	362.7	363.2	363.7	364.3	364.8	365.5	366.4	367.3	368.2	369.1	369.7
145°	377.3	377.3	377.2	377.1	377.0	377.6	378.8	380.1	381.3	382.5	383.0
147.5°	390.1	389.8	389.5	389.2	389.0	389.4	390.6	391.9	393.1	394.3	394.6
150°	398.3	397.8	397.3	396.8	396.3	396.7	397.8	399.0	400.1	401.3	401.7
152.5°	405.3	404.8	404.2	403.6	403.1	403.3	404.4	405.5	406.6	407.7	408.1
155°	415.5	414.8	414.2	413.5	412.9	413.0	413.9	414.7	415.6	416.4	416.9
157.5°	423.4	422.9	422.3	421.8	421.2	421.3	421.9	422.5	423.1	423.7	424.2
160°	428.1	427.7	427.2	426.8	426.4	426.4	426.8	427.2	427.7	428.1	428.5
162.5°	432.2	431.8	431.4	430.9	430.5	430.5	430.8	431.2	431.6	432.0	432.5
165°	437.8	437.4	436.9	436.5	436.1	436.0	436.2	436.4	436.6	436.8	437.3
167.5°	441.9	441.5	441.1	440.6	440.2	440.1	440.3	440.5	440.7	440.9	441.4
170°	444.3	443.8	443.4	443.0	442.5	442.4	442.5	442.7	442.8	443.0	443.5
172.5°	445.8	445.4	444.9	444.5	444.1	443.9	444.1	444.2	444.4	444.5	445.0
175°	447.8	447.3	446.8	446.3	445.8	445.6	445.8	445.9	446.1	446.2	446.7
177.5°	448.1	447.7	447.3	446.9	446.5	446.4	446.4	446.5	446.5	446.6	447.0
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8



TEST NUMBER: P331618

CATALOG NUMBER: SA2XXRDIP-C290D330U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	499.6	500.4	501.2	501.5	501.4	501.2	501.0	500.9
5°	495.6	496.5	497.4	497.7	497.4	497.1	496.8	496.5
7.5°	487.6	487.9	488.1	488.0	487.5	486.9	486.4	485.9
10°	479.6	479.3	479.0	478.5	477.9	477.3	476.7	476.1
12.5°	470.4	469.8	469.3	468.5	467.5	466.5	465.5	464.5
15°	453.2	451.2	449.3	447.9	446.9	445.8	444.8	443.8
17.5°	433.7	431.4	429.2	427.2	425.4	423.7	421.9	420.2
20°	420.2	417.6	415.1	412.7	410.5	408.3	406.1	403.9
22.5°	405.3	402.0	398.8	396.3	394.6	393.0	391.3	389.7
25°	380.6	376.4	372.3	369.5	368.0	366.4	364.9	363.4
27.5°	357.0	352.2	347.4	343.8	341.4	339.0	336.6	334.2
30°	340.4	335.3	330.1	326.2	323.4	320.7	318.0	315.3
32.5°	323.7	317.8	311.9	307.7	305.2	302.6	300.0	297.5
35°	297.6	291.2	284.8	280.5	278.3	276.1	273.9	271.7
37.5°	272.1	265.1	258.1	253.3	250.8	248.2	245.7	243.1
40°	255.1	247.9	240.7	235.8	233.2	230.6	227.9	225.3
42.5°	237.8	230.4	223.0	218.1	215.5	213.0	210.4	207.9
45°	212.8	205.6	198.5	193.7	191.3	188.8	186.4	184.0
47.5°	188.4	181.3	174.2	169.5	167.3	165.1	162.9	160.7
50°	172.8	165.8	158.8	154.3	152.2	150.1	147.9	145.8
52.5°	158.0	151.3	144.6	140.2	138.3	136.3	134.3	132.4
55°	135.5	129.5	123.4	119.4	117.5	115.6	113.7	111.8
57.5°	115.1	109.5	104.0	100.4	98.8	97.2	95.6	93.9
60°	101.0	95.9	90.7	87.3	85.7	84.1	82.5	80.9
62.5°	88.8	83.9	79.0	76.0	75.0	74.1	73.1	72.1
65°	72.2	68.7	65.3	63.4	63.1	62.8	62.5	62.2
67.5°	58.3	56.7	55.1	54.2	53.8	53.5	53.2	52.9
70°	50.7	49.7	48.7	48.0	47.5	47.1	46.7	46.3
72.5°	44.1	43.2	42.4	41.9	41.6	41.4	41.1	40.9
75°	34.9	34.2	33.5	33.1	33.0	32.9	32.8	32.7
77.5°	26.4	26.0	25.6	25.4	25.2	25.0	24.9	24.7
80°	21.0	20.6	20.2	20.0	20.0	20.0	20.0	20.0
82.5°	15.9	15.6	15.4	15.3	15.3	15.3	15.3	15.3
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
87.5°	4.2	4.2	4.2	4.2	4.2	4.2	4.3	4.3
90°	7.2	7.5	7.9	8.2	8.3	8.4	8.6	8.7
92.5°	7.9	8.1	8.2	8.4	8.5	8.6	8.6	8.7
95°	13.3	13.7	14.0	14.2	14.1	14.0	14.0	13.9
97.5°	17.5	17.7	18.0	18.2	18.3	18.4	18.5	18.6
100°	19.6	20.2	20.7	21.1	21.2	21.4	21.5	21.7
102.5°	20.4	21.2	21.9	22.4	22.6	22.8	23.0	23.2
105°	21.3	22.1	22.9	23.4	23.7	24.0	24.3	24.6
107.5°	26.0	25.2	24.4	24.1	24.4	24.7	25.0	25.3
110°	42.2	35.0	27.8	24.4	24.7	25.0	25.3	25.5



TEST NUMBER: P331618

CATALOG NUMBER: SA2XXRDIP-C290D330U835-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	90.3	64.1	37.9	24.9	25.1	25.3	25.6	25.8
115°	133.0	99.7	66.4	47.2	42.0	36.9	31.7	26.5
117.5°	204.9	196.8	188.8	176.3	159.3	142.3	125.3	108.3
120°	238.7	239.6	240.4	236.0	226.3	216.6	206.9	197.2
122.5°	253.3	253.8	254.3	253.6	251.8	249.9	248.0	246.1
125°	274.2	274.7	275.2	275.6	275.8	276.0	276.2	276.4
127.5°	293.6	294.3	295.0	295.4	295.5	295.5	295.5	295.6
130°	305.8	306.6	307.4	307.8	307.7	307.6	307.6	307.5
132.5°	317.8	318.4	319.1	319.4	319.3	319.3	319.2	319.1
135°	334.8	335.5	336.2	336.5	336.4	336.2	336.1	335.9
137.5°	350.6	351.3	352.0	352.2	352.0	351.8	351.5	351.3
140°	360.8	361.5	362.1	362.3	361.9	361.6	361.2	360.8
142.5°	370.3	370.9	371.5	371.6	371.2	370.9	370.5	370.1
145°	383.5	384.0	384.5	384.6	384.2	383.9	383.5	383.1
147.5°	395.0	395.4	395.8	395.8	395.5	395.2	394.9	394.6
150°	402.1	402.5	403.0	403.0	402.7	402.3	401.9	401.6
152.5°	408.6	409.0	409.4	409.4	408.9	408.5	408.0	407.5
155°	417.3	417.7	418.2	418.1	417.5	417.0	416.4	415.8
157.5°	424.7	425.2	425.6	425.6	425.0	424.5	423.9	423.4
160°	429.0	429.4	429.8	429.8	429.3	428.8	428.3	427.8
162.5°	432.9	433.4	433.9	433.9	433.2	432.6	432.0	431.4
165°	437.8	438.3	438.8	438.8	438.3	437.8	437.3	436.8
167.5°	441.9	442.4	442.9	442.8	442.2	441.5	440.9	440.2
170°	444.0	444.5	445.0	444.9	444.3	443.6	443.0	442.3
172.5°	445.5	446.0	446.5	446.5	445.8	445.2	444.5	443.9
175°	447.2	447.7	448.2	448.1	447.4	446.7	445.9	445.2
177.5°	447.4	447.8	448.2	448.1	447.6	447.1	446.6	446.1
180°	446.8	446.8	446.8	446.8	446.8	446.8	446.8	446.8

(END OF REPORT)