

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331625

Luminaire Tested: **SA2XXRDIP-C290D530U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331625
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D530U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 530 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2924.6 lumens
Efficiency: N/A
Efficacy: 114.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 25.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331625
CATALOG NUMBER: SA2XXRDIP-C290D530U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331625

CATALOG NUMBER: SA2XXRDIP-C290D530U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	43	43	43	35
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	37	37	30
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	33	31	26
3	79	70	63	58	71	64	58	53	52	48	44	41	38	35	30	29	27	22
4	73	62	55	49	65	57	50	45	46	42	38	36	33	31	27	25	24	20
5	67	56	48	42	60	51	44	39	41	37	33	33	29	27	25	23	21	17
6	61	50	42	37	55	46	39	34	37	32	29	30	26	23	23	20	18	15
7	57	45	37	32	51	41	35	30	34	29	25	27	24	21	21	18	16	14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12
9	49	37	30	25	44	34	28	24	28	24	20	23	19	17	18	15	13	11
10	46	34	27	23	42	31	25	21	26	21	18	21	18	15	16	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8105	8105	8105
5°	8136	8003	8047
10°	8073	7873	7806
15°	7980	7639	7418
20°	7852	7306	6940
25°	7721	6928	6474
30°	7538	6538	5878
35°	7360	6116	5355
40°	7181	5678	4749
45°	6971	5186	4201
50°	6754	4690	3662
55°	6533	4155	3147
60°	6278	3594	2612
65°	5987	3018	2376
70°	5641	2488	2186
75°	5215	2264	2040
80°	4603	2027	1860
85°	3612	1593	1593



TEST NUMBER: P331625

CATALOG NUMBER: SA2XXRDIP-C290D530U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	1.6
10°-20°	129.0	4.4
20°-30°	181.2	6.2
30°-40°	197.6	6.8
40°-50°	181.6	6.2
50°-60°	142.7	4.9
60°-70°	93.0	3.2
70°-80°	48.0	1.6
80°-90°	15.1	0.5
90°-100°	42.8	1.5
100°-110°	133.0	4.5
110°-120°	227.3	7.8
120°-130°	298.9	10.2
130°-140°	335.5	11.5
140°-150°	329.0	11.2
150°-160°	275.9	9.4
160°-170°	183.0	6.3
170°-180°	64.0	2.2
0°-30°	357.2	12.2
0°-40°	554.7	19.0
0°-60°	879.0	30.1
0°-90°	1035.1	35.4
90°-120°	403.1	13.8
90°-150°	1366.6	46.7
90°-180°	1889.0	64.6
0°-180°	2924.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	502	500	494	498	496	48
15°	477	472	457	449	444	134
25°	433	418	389	371	363	199
35°	373	349	310	283	272	234
45°	305	274	227	196	184	236
55°	232	196	148	121	112	207
65°	157	120	79	64	62	155
75°	84	53	36	33	33	88
85°	20	10	9	9	9	23
90°	1	8	20	19	19	2
95°	30	35	36	36	35	34
105°	123	124	126	127	127	129
115°	228	231	230	230	228	226
125°	332	337	335	334	333	296
135°	429	435	437	436	434	332
145°	521	525	529	529	527	325
155°	596	598	599	602	600	274
165°	648	648	648	651	649	183
175°	675	673	672	675	672	64
180°	676	676	676	676	676	



TEST NUMBER: P331625

CATALOG NUMBER: SA2XXRDIP-C290D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	503.8	503.4	503.0	502.6	502.2	501.5	500.6	499.8	498.9	498.0	498.8
5°	502.0	501.5	501.0	500.5	500.0	499.0	497.7	496.4	495.1	493.8	494.7
7.5°	496.8	496.2	495.5	494.9	494.3	493.2	491.7	490.1	488.6	487.1	487.3
10°	492.4	491.7	491.0	490.3	489.6	488.2	486.2	484.2	482.2	480.2	479.9
12.5°	487.0	486.1	485.2	484.4	483.5	481.8	479.2	476.6	474.0	471.4	470.9
15°	477.4	476.3	475.2	474.1	473.0	470.7	467.3	463.9	460.4	457.0	455.1
17.5°	465.7	464.0	462.3	460.6	458.9	455.9	451.5	447.1	442.7	438.3	436.0
20°	457.0	455.0	453.0	450.9	448.9	445.4	440.3	435.3	430.3	425.2	422.7
22.5°	447.6	445.3	443.0	440.8	438.5	434.5	428.8	423.1	417.5	411.8	408.5
25°	433.4	430.1	426.9	423.7	420.5	415.5	408.8	402.2	395.5	388.9	384.7
27.5°	416.3	412.8	409.3	405.8	402.2	396.7	389.2	381.7	374.2	366.7	361.9
30°	404.3	400.5	396.6	392.8	389.0	383.0	374.9	366.9	358.8	350.7	345.6
32.5°	392.7	388.2	383.7	379.2	374.7	368.4	360.2	351.9	343.7	335.4	329.6
35°	373.4	368.3	363.1	358.0	352.8	345.8	336.9	328.0	319.2	310.3	303.9
37.5°	354.2	348.5	342.8	337.2	331.5	324.0	314.5	305.0	295.6	286.1	279.1
40°	340.7	334.7	328.6	322.5	316.5	308.6	298.8	289.0	279.2	269.4	262.2
42.5°	326.9	320.5	314.1	307.8	301.4	293.1	283.0	272.9	262.8	252.7	245.3
45°	305.3	298.5	291.7	285.0	278.2	269.5	258.9	248.3	237.7	227.1	220.0
47.5°	284.2	277.0	269.9	262.7	255.5	246.5	235.5	224.6	213.6	202.7	195.6
50°	268.9	261.8	254.6	247.4	240.3	231.1	220.0	208.9	197.8	186.7	179.7
52.5°	254.0	246.5	239.1	231.6	224.1	214.9	204.0	193.2	182.3	171.4	164.7
55°	232.1	224.3	216.4	208.5	200.6	191.3	180.3	169.4	158.5	147.6	141.6
57.5°	209.7	201.6	193.5	185.5	177.4	168.1	157.6	147.2	136.7	126.2	120.6
60°	194.4	186.4	178.3	170.2	162.1	152.9	142.5	132.1	121.7	111.3	106.1
62.5°	179.5	171.5	163.4	155.3	147.2	138.2	128.3	118.4	108.5	98.6	93.7
65°	156.7	148.5	140.4	132.2	124.0	115.4	106.3	97.2	88.1	79.0	75.6
67.5°	134.7	126.6	118.5	110.4	102.3	94.1	85.9	77.8	69.6	61.4	59.8
70°	119.5	111.6	103.7	95.9	88.0	80.6	73.6	66.6	59.7	52.7	51.7
72.5°	104.9	97.4	89.8	82.3	74.7	68.2	62.6	57.0	51.4	45.8	44.9
75°	83.6	76.5	69.5	62.4	55.3	50.1	46.6	43.2	39.8	36.3	35.6
77.5°	62.6	56.4	50.2	44.0	37.8	33.9	32.2	30.6	28.9	27.3	26.9
80°	49.5	44.4	39.2	34.1	28.9	25.8	24.8	23.8	22.8	21.8	21.4
82.5°	37.5	33.5	29.5	25.5	21.5	19.1	18.4	17.7	17.0	16.4	16.1
85°	19.5	17.4	15.3	13.2	11.1	9.8	9.5	9.2	8.9	8.6	8.6
87.5°	5.9	5.6	5.2	4.9	4.6	4.7	5.2	5.8	6.3	6.9	6.8
90°	0.6	2.1	3.6	5.1	6.7	8.8	11.6	14.4	17.2	20.0	19.7
92.5°	10.2	11.3	12.4	13.5	14.6	15.5	16.2	16.8	17.5	18.1	18.2
95°	29.7	30.9	32.2	33.5	34.7	35.5	35.7	36.0	36.2	36.5	36.5
97.5°	54.2	55.3	56.4	57.5	58.6	59.4	59.9	60.4	60.9	61.4	61.4
100°	72.4	73.4	74.4	75.5	76.5	77.2	77.6	77.9	78.3	78.7	78.7
102.5°	91.6	92.4	93.2	94.0	94.8	95.5	96.0	96.4	96.9	97.4	97.5
105°	122.6	123.0	123.4	123.7	124.1	124.4	124.7	124.9	125.2	125.5	125.7
107.5°	153.9	154.4	155.0	155.5	156.1	156.4	156.4	156.4	156.4	156.4	156.5
110°	173.9	174.7	175.4	176.2	177.0	177.3	177.3	177.3	177.3	177.3	177.3



TEST NUMBER: P331625

CATALOG NUMBER: SA2XXRDIP-C290D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	195.8	196.6	197.3	198.1	198.9	199.2	199.1	199.0	198.9	198.8	198.5
115°	228.1	228.9	229.6	230.4	231.1	231.4	231.1	230.9	230.6	230.4	230.3
117.5°	260.3	261.3	262.3	263.3	264.3	264.5	263.8	263.0	262.3	261.6	261.3
120°	281.7	282.7	283.7	284.7	285.8	285.8	284.7	283.7	282.7	281.7	281.7
122.5°	301.3	302.5	303.8	305.0	306.2	306.4	305.7	305.0	304.3	303.6	303.3
125°	331.9	333.0	334.2	335.3	336.4	336.8	336.4	336.1	335.7	335.3	334.9
127.5°	361.6	363.1	364.5	366.0	367.4	367.9	367.5	367.0	366.6	366.1	365.6
130°	380.4	382.0	383.6	385.3	386.9	387.6	387.4	387.1	386.9	386.6	386.4
132.5°	401.3	402.7	404.0	405.4	406.7	407.4	407.5	407.5	407.6	407.6	407.1
135°	429.4	430.8	432.2	433.6	435.0	435.8	436.0	436.3	436.6	436.8	436.7
137.5°	458.9	460.1	461.2	462.4	463.5	464.2	464.6	464.9	465.2	465.5	465.4
140°	476.7	477.9	479.0	480.1	481.3	482.2	482.8	483.4	484.1	484.7	484.7
142.5°	495.0	496.1	497.3	498.4	499.5	500.3	500.8	501.2	501.6	502.0	502.1
145°	521.2	522.1	523.0	523.9	524.8	525.6	526.3	527.1	527.9	528.6	528.7
147.5°	544.6	545.6	546.7	547.8	548.8	549.6	550.1	550.6	551.1	551.7	551.9
150°	560.6	561.3	562.1	562.8	563.6	564.2	564.7	565.2	565.7	566.3	566.6
152.5°	574.7	575.5	576.2	577.0	577.7	578.4	579.0	579.6	580.2	580.9	581.3
155°	595.9	596.3	596.7	597.0	597.4	597.8	598.2	598.6	598.9	599.3	600.0
157.5°	614.0	614.3	614.5	614.8	615.1	615.3	615.5	615.8	616.0	616.2	617.1
160°	625.0	625.2	625.5	625.7	626.0	626.2	626.3	626.4	626.6	626.7	627.5
162.5°	635.0	635.1	635.1	635.2	635.2	635.3	635.4	635.6	635.7	635.8	636.7
165°	648.4	648.2	648.1	648.0	647.9	647.8	647.8	647.8	647.8	647.8	648.7
167.5°	659.5	659.2	658.8	658.4	658.0	657.8	657.8	657.8	657.7	657.7	658.6
170°	665.5	665.1	664.7	664.3	664.0	663.7	663.6	663.4	663.3	663.2	664.1
172.5°	669.6	669.2	668.8	668.4	668.1	667.8	667.7	667.6	667.4	667.3	668.2
175°	674.6	674.2	673.8	673.5	673.1	672.8	672.5	672.3	672.0	671.7	672.6
177.5°	676.7	676.3	676.0	675.7	675.4	675.2	675.0	674.8	674.6	674.4	675.0
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7



TEST NUMBER: P331625

CATALOG NUMBER: SA2XXRDIP-C290D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	499.6	500.4	501.2	501.5	501.4	501.2	501.0	500.9
5°	495.6	496.5	497.4	497.7	497.4	497.1	496.8	496.5
7.5°	487.6	487.9	488.1	488.0	487.5	486.9	486.4	485.9
10°	479.6	479.3	479.0	478.5	477.9	477.3	476.7	476.1
12.5°	470.4	469.8	469.3	468.5	467.5	466.5	465.5	464.5
15°	453.2	451.2	449.3	447.9	446.9	445.8	444.8	443.8
17.5°	433.7	431.4	429.2	427.2	425.4	423.7	421.9	420.2
20°	420.2	417.6	415.1	412.7	410.5	408.3	406.1	403.9
22.5°	405.3	402.0	398.8	396.3	394.6	393.0	391.3	389.7
25°	380.6	376.4	372.3	369.5	368.0	366.4	364.9	363.4
27.5°	357.0	352.2	347.4	343.8	341.4	339.0	336.6	334.2
30°	340.4	335.3	330.1	326.2	323.4	320.7	318.0	315.3
32.5°	323.7	317.8	311.9	307.7	305.2	302.6	300.0	297.5
35°	297.6	291.2	284.8	280.5	278.3	276.1	273.9	271.7
37.5°	272.1	265.1	258.1	253.3	250.8	248.2	245.7	243.1
40°	255.1	247.9	240.7	235.8	233.2	230.6	227.9	225.3
42.5°	237.8	230.4	223.0	218.1	215.5	213.0	210.4	207.9
45°	212.8	205.6	198.5	193.7	191.3	188.8	186.4	184.0
47.5°	188.4	181.3	174.2	169.5	167.3	165.1	162.9	160.7
50°	172.8	165.8	158.8	154.3	152.2	150.1	147.9	145.8
52.5°	158.0	151.3	144.6	140.2	138.3	136.3	134.3	132.4
55°	135.5	129.5	123.4	119.4	117.5	115.6	113.7	111.8
57.5°	115.1	109.5	104.0	100.4	98.8	97.2	95.6	93.9
60°	101.0	95.9	90.7	87.3	85.7	84.1	82.5	80.9
62.5°	88.8	83.9	79.0	76.0	75.0	74.1	73.1	72.1
65°	72.2	68.7	65.3	63.4	63.1	62.8	62.5	62.2
67.5°	58.3	56.7	55.1	54.2	53.8	53.5	53.2	52.9
70°	50.7	49.7	48.7	48.0	47.5	47.1	46.7	46.3
72.5°	44.1	43.2	42.4	41.9	41.6	41.4	41.1	40.9
75°	34.9	34.2	33.5	33.1	33.0	32.9	32.8	32.7
77.5°	26.4	26.0	25.6	25.4	25.2	25.0	24.9	24.7
80°	21.0	20.6	20.2	20.0	20.0	20.0	20.0	20.0
82.5°	15.9	15.6	15.4	15.3	15.3	15.3	15.3	15.3
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
87.5°	6.6	6.5	6.4	6.3	6.3	6.4	6.4	6.4
90°	19.5	19.2	18.9	18.9	19.0	19.1	19.3	19.4
92.5°	18.2	18.3	18.3	18.4	18.4	18.4	18.5	18.5
95°	36.5	36.5	36.5	36.4	36.1	35.9	35.6	35.4
97.5°	61.4	61.4	61.4	61.3	61.3	61.3	61.3	61.2
100°	78.7	78.7	78.7	78.6	78.5	78.4	78.3	78.1
102.5°	97.6	97.7	97.8	97.8	97.7	97.5	97.4	97.3
105°	126.0	126.2	126.5	126.6	126.6	126.6	126.6	126.6
107.5°	156.6	156.7	156.8	156.5	155.9	155.4	154.8	154.2
110°	177.3	177.3	177.3	177.2	176.8	176.4	176.0	175.6



TEST NUMBER: P331625

CATALOG NUMBER: SA2XXRDIP-C290D530U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	198.2	197.9	197.6	197.3	197.0	196.7	196.4	196.2
115°	230.1	230.0	229.9	229.6	229.2	228.9	228.5	228.1
117.5°	261.0	260.7	260.4	260.1	259.7	259.3	258.9	258.5
120°	281.7	281.7	281.7	281.5	281.1	280.8	280.4	280.0
122.5°	303.0	302.7	302.4	302.1	301.8	301.5	301.3	301.0
125°	334.5	334.2	333.8	333.5	333.4	333.3	333.1	333.0
127.5°	365.2	364.7	364.3	363.8	363.4	363.0	362.6	362.2
130°	386.1	385.9	385.6	385.2	384.7	384.2	383.7	383.2
132.5°	406.5	405.9	405.4	404.9	404.5	404.1	403.7	403.3
135°	436.6	436.4	436.3	436.0	435.7	435.3	434.9	434.5
137.5°	465.3	465.2	465.1	464.8	464.3	463.8	463.3	462.8
140°	484.7	484.7	484.7	484.5	483.9	483.4	482.9	482.4
142.5°	502.2	502.3	502.4	502.2	501.7	501.2	500.7	500.2
145°	528.9	529.0	529.1	528.9	528.4	527.9	527.4	526.9
147.5°	552.2	552.5	552.8	552.7	552.2	551.7	551.2	550.7
150°	567.0	567.4	567.8	567.8	567.4	567.0	566.6	566.3
152.5°	581.8	582.3	582.8	582.8	582.3	581.8	581.3	580.9
155°	600.6	601.2	601.9	602.0	601.6	601.2	600.8	600.5
157.5°	617.9	618.8	619.7	619.8	619.2	618.6	618.0	617.3
160°	628.2	629.0	629.7	629.9	629.4	628.9	628.3	627.8
162.5°	637.5	638.4	639.3	639.4	638.8	638.2	637.6	637.0
165°	649.6	650.5	651.3	651.5	650.8	650.2	649.6	648.9
167.5°	659.5	660.4	661.3	661.4	660.7	660.1	659.4	658.7
170°	665.0	665.9	666.7	666.8	666.0	665.3	664.5	663.8
172.5°	669.1	670.0	670.8	670.9	670.2	669.4	668.6	667.9
175°	673.5	674.4	675.3	675.4	674.6	673.8	673.1	672.3
177.5°	675.6	676.2	676.8	676.8	676.2	675.6	675.0	674.4
180°	675.7	675.7	675.7	675.7	675.7	675.7	675.7	675.7

(END OF REPORT)