

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331627

Luminaire Tested: **SA2XXRDIP-C290D725U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331627  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 725 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4029.3 lumens  
Efficiency: N/A  
Efficacy: 129.1 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 31.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331627  
CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36	28				
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	32	32	31	24				
2	85	78	73	68	76	70	66	62	56	52	50	42	40	38	29	28	27	21				
3	78	69	63	57	70	62	57	52	49	45	42	37	35	33	26	25	23	19				
4	72	62	54	49	64	56	49	44	44	40	36	34	31	28	24	22	21	16				
5	66	55	47	42	59	50	43	38	40	35	32	30	27	25	22	20	18	15				
6	61	49	42	36	54	45	38	33	36	31	28	28	24	22	20	18	16	13				
7	56	45	37	32	50	40	34	29	33	28	24	25	22	20	18	16	15	12				
8	52	41	33	28	47	37	31	26	30	25	22	23	20	18	17	15	13	11				
9	48	37	30	25	44	34	28	23	27	23	20	21	18	16	16	14	12	10				
10	45	34	27	23	41	31	25	21	25	21	18	20	17	14	15	13	11	9				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	10555	10555	10555	10555
5°	11788	10621	9418	10621
10°	13080	10547	8163	10547
15°	13722	10392	6432	10392
20°	11897	10163	5565	10163
25°	7801	9850	4969	9850
30°	5252	9469	4497	9469
35°	4254	8990	4056	8990
40°	3781	8469	3754	8469
45°	3423	7857	3350	7857
50°	3115	7252	3105	7252
55°	2928	6579	2891	6579
60°	2451	5964	2422	5964
65°	2067	5414	2342	5414
70°	1907	4834	2209	4834
75°	1784	4211	2040	4211
80°	1646	3468	1813	3468
85°	1519	2742	1593	2742



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	62.0	1.5
10°-20°	172.7	4.3
20°-30°	222.5	5.5
30°-40°	211.5	5.2
40°-50°	181.1	4.5
50°-60°	137.9	3.4
60°-70°	87.2	2.2
70°-80°	43.5	1.1
80°-90°	13.8	0.3
90°-100°	33.0	0.8
100°-110°	120.9	3.0
110°-120°	323.3	8.0
120°-130°	533.6	13.2
130°-140°	567.5	14.1
140°-150°	527.5	13.1
150°-160°	424.1	10.5
160°-170°	273.3	6.8
170°-180°	94.1	2.3
0°-30°	457.2	11.3
0°-40°	668.6	16.6
0°-60°	987.7	24.5
0°-90°	1132.2	28.1
90°-120°	477.2	11.8
90°-150°	2105.7	52.3
90°-180°	2897.0	71.9
0°-180°	4029.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	654	654	654	654	654	
5°	727	655	581	655	727	72
15°	821	622	385	622	821	221
25°	438	553	279	553	438	208
35°	216	456	206	456	216	138
45°	150	344	147	344	150	116
55°	104	234	103	234	104	91
65°	54	142	61	142	54	55
75°	29	68	33	68	29	30
85°	8	15	9	15	8	9
90°	19	1	19	1	19	9
95°	31	46	31	46	31	29
105°	54	218	54	218	54	57
115°	59	411	59	411	59	147
125°	612	582	612	582	612	529
135°	743	720	743	720	743	573
145°	848	835	848	835	848	530
155°	920	919	920	919	920	424
165°	966	969	966	969	966	273
175°	985	991	985	991	985	94
180°	989	989	989	989	989	



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	680.3	680.8	681.4	680.1	680.1	679.0	676.6	674.8	669.7	669.0	669.0
5°	727.3	726.9	727.8	724.8	720.8	719.8	715.5	709.8	703.9	697.4	696.0
7.5°	774.1	773.4	771.6	771.1	768.0	761.1	754.2	746.8	737.0	727.4	722.6
10°	797.8	805.3	800.7	792.8	794.3	783.7	778.0	768.2	760.0	745.7	742.6
12.5°	821.0	824.0	822.5	818.0	816.0	808.6	800.9	792.4	777.3	764.5	753.3
15°	820.9	825.2	826.4	825.0	826.1	825.7	821.6	814.6	801.4	787.3	775.0
17.5°	760.3	763.3	770.8	775.8	782.2	795.6	802.3	804.8	802.9	794.8	786.2
20°	692.4	687.4	708.3	718.9	728.0	750.7	770.3	777.8	789.8	789.6	787.3
22.5°	596.0	597.2	617.0	629.7	656.2	679.0	701.2	729.4	752.7	768.1	777.1
25°	437.9	446.6	466.3	483.6	513.1	555.4	593.8	638.3	680.3	713.5	745.1
27.5°	328.9	329.6	345.2	361.2	378.7	413.3	461.7	514.8	574.7	624.2	681.0
30°	281.7	280.3	286.9	296.7	311.7	338.5	374.8	427.0	486.8	561.3	627.6
32.5°	248.2	248.3	253.3	260.5	272.9	291.0	315.9	358.4	414.8	488.1	565.8
35°	215.8	215.6	219.2	224.4	229.6	241.2	258.3	280.5	319.4	387.7	467.2
37.5°	192.5	193.5	195.3	198.6	204.3	210.8	221.0	236.0	263.6	304.1	370.9
40°	179.4	179.9	182.4	185.1	188.5	193.5	201.9	214.0	234.2	266.4	315.3
42.5°	167.5	167.9	169.7	172.2	174.9	179.9	186.9	197.3	213.7	238.8	279.1
45°	149.9	149.9	151.5	152.6	155.6	160.1	165.8	174.5	185.8	204.4	231.2
47.5°	133.5	133.5	134.6	136.5	138.4	141.9	147.5	154.6	162.8	177.2	200.1
50°	124.0	124.3	124.9	126.5	127.7	130.8	135.2	141.3	149.9	161.1	180.1
52.5°	116.4	116.3	117.1	117.8	118.6	120.8	124.1	129.5	137.2	146.9	162.7
55°	104.0	103.1	104.5	105.6	106.3	107.2	109.0	112.4	119.0	127.2	139.0
57.5°	88.6	88.2	89.2	90.2	92.4	94.8	96.4	98.5	101.9	107.8	119.5
60°	75.9	75.9	77.9	78.6	81.1	84.3	87.5	89.3	92.7	96.5	105.2
62.5°	64.6	64.8	65.7	66.4	67.8	71.7	76.2	80.2	83.4	87.1	92.8
65°	54.1	54.5	54.5	55.0	55.9	56.8	58.6	61.8	67.5	72.7	77.0
67.5°	45.9	46.0	46.2	46.6	46.8	47.8	48.6	50.0	51.3	56.2	61.6
70°	40.4	41.1	40.9	41.3	41.6	42.0	42.9	43.6	45.7	46.8	50.0
72.5°	35.3	35.8	35.8	36.1	36.7	36.8	37.5	38.2	39.5	40.4	42.2
75°	28.6	28.4	28.6	29.1	29.3	29.5	29.5	30.4	31.1	32.0	33.2
77.5°	22.1	22.3	22.3	22.3	22.4	22.8	22.7	23.1	23.8	24.3	24.8
80°	17.7	17.9	17.7	17.9	18.2	18.4	18.2	18.4	19.1	19.5	19.5
82.5°	13.7	13.8	13.9	13.9	14.0	14.0	14.4	14.4	14.9	14.8	15.0
85°	8.2	8.0	8.0	8.0	8.2	8.4	8.2	8.2	8.4	8.4	8.4
87.5°	6.8	6.9	6.8	6.8	6.7	6.6	6.4	6.5	6.1	6.1	5.7
90°	19.3	19.0	18.7	18.4	18.0	17.5	16.7	15.9	15.1	14.3	13.0
92.5°	19.3	19.1	18.9	18.7	18.6	18.2	17.8	17.4	17.0	16.6	16.0
95°	30.8	30.9	31.1	31.2	31.4	31.1	30.3	29.5	28.7	27.9	26.8
97.5°	41.1	40.9	40.7	40.5	40.3	39.9	39.2	38.6	38.0	37.3	34.8
100°	47.9	47.6	47.3	47.0	46.7	45.9	44.6	43.3	42.0	40.8	38.1
102.5°	51.4	50.9	50.5	50.0	49.6	48.5	46.9	45.2	43.6	41.9	64.5
105°	54.4	53.7	53.1	52.5	51.8	50.6	48.9	47.1	45.4	43.6	87.0
107.5°	55.9	55.3	54.7	54.0	53.4	54.0	55.7	57.5	59.3	61.1	113.1
110°	56.5	55.9	55.2	54.6	54.0	61.6	77.5	93.4	109.3	125.2	171.1



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	57.1	56.6	56.1	55.6	55.0	83.8	141.8	199.8	257.8	315.7	327.1
115°	58.7	70.1	81.5	93.0	104.4	147.0	220.6	294.2	367.8	441.4	437.4
117.5°	239.5	277.1	314.7	352.3	389.9	417.6	435.4	453.3	471.1	488.9	486.1
120°	436.4	457.8	479.3	500.7	522.2	532.0	530.1	528.2	526.2	524.3	521.5
122.5°	544.5	548.7	552.8	557.0	561.2	562.7	561.5	560.4	559.2	558.1	555.0
125°	611.6	611.1	610.7	610.2	609.7	608.9	607.8	606.7	605.6	604.5	601.4
127.5°	654.0	653.9	653.8	653.7	653.6	652.7	651.1	649.5	647.9	646.2	644.0
130°	680.3	680.4	680.6	680.8	680.9	680.1	678.4	676.6	674.9	673.1	671.4
132.5°	706.0	706.2	706.4	706.5	706.7	706.0	704.5	703.0	701.5	700.0	698.3
135°	743.2	743.5	743.9	744.2	744.5	743.9	742.3	740.7	739.1	737.5	736.1
137.5°	777.1	777.7	778.2	778.8	779.3	778.8	777.2	775.7	774.1	772.6	770.9
140°	798.3	799.1	799.9	800.7	801.5	801.2	799.7	798.3	796.9	795.5	793.7
142.5°	818.9	819.7	820.5	821.3	822.1	821.8	820.5	819.2	817.9	816.6	814.6
145°	847.7	848.5	849.3	850.1	850.8	850.7	849.6	848.5	847.4	846.2	843.5
147.5°	873.0	873.7	874.3	875.0	875.7	875.6	874.8	873.9	873.1	872.3	869.6
150°	888.4	889.2	890.0	890.8	891.6	891.5	890.6	889.6	888.7	887.7	885.2
152.5°	901.6	902.7	903.7	904.8	905.8	905.9	904.9	903.9	903.0	902.0	899.6
155°	919.9	921.2	922.5	923.7	925.0	925.2	924.2	923.3	922.3	921.3	919.4
157.5°	936.7	937.9	939.1	940.4	941.6	941.7	940.6	939.5	938.5	937.4	936.0
160°	946.4	947.5	948.6	949.7	950.8	950.9	950.0	949.0	948.1	947.1	946.1
162.5°	954.4	955.8	957.1	958.5	959.9	960.0	958.9	957.8	956.8	955.7	954.9
165°	966.4	967.5	968.6	969.8	970.9	970.9	969.8	968.6	967.5	966.4	965.9
167.5°	974.0	975.4	976.9	978.3	979.7	979.9	978.8	977.7	976.5	975.4	975.0
170°	978.6	980.0	981.4	982.9	984.3	984.5	983.3	982.2	981.1	980.0	979.7
172.5°	982.0	983.4	984.9	986.3	987.7	987.9	986.8	985.7	984.6	983.4	983.1
175°	985.0	986.6	988.2	989.8	991.4	991.6	990.5	989.4	988.3	987.2	986.8
177.5°	986.9	988.0	989.2	990.3	991.5	991.6	990.7	989.8	988.9	988.0	987.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	669.4	667.9	666.6	663.4	661.7	658.1	657.6	657.4	652.7	648.1	646.8
5°	692.4	688.7	683.3	676.9	670.3	663.5	659.0	655.3	646.2	637.6	632.6
7.5°	715.5	707.7	698.3	686.3	676.2	665.0	656.6	649.1	636.2	623.8	615.5
10°	732.8	720.1	707.6	691.0	678.0	665.3	653.5	643.3	628.8	612.4	600.8
12.5°	743.5	729.5	712.3	696.1	679.3	663.1	647.3	634.2	617.1	600.2	586.5
15°	758.0	743.0	722.1	698.9	677.4	656.2	638.1	621.7	599.5	579.2	562.4
17.5°	769.9	749.2	726.8	700.0	675.0	648.2	624.8	603.9	579.1	554.7	534.9
20°	773.7	753.2	727.3	700.5	671.0	639.4	614.2	591.5	564.9	538.3	515.6
22.5°	771.3	755.4	726.6	694.5	664.3	631.3	602.8	576.4	546.9	519.8	493.5
25°	755.3	749.8	722.6	687.6	653.1	614.7	581.7	552.9	519.3	490.2	461.6
27.5°	717.9	729.7	712.8	675.5	637.1	596.0	558.9	526.1	491.2	458.5	430.0
30°	681.9	708.9	701.7	667.1	624.2	583.8	542.2	507.9	470.7	437.0	408.9
32.5°	632.7	677.3	684.4	655.5	611.1	566.7	523.1	489.0	450.1	414.7	387.2
35°	554.2	621.0	651.7	633.3	588.8	540.8	495.9	456.1	417.0	382.1	354.8
37.5°	460.7	551.7	602.8	604.1	563.2	513.4	464.4	424.9	384.9	350.6	321.1
40°	400.0	498.6	565.2	579.9	545.4	491.6	442.0	401.8	362.8	329.1	295.3
42.5°	345.5	443.7	525.5	551.2	523.8	470.3	420.6	378.6	340.6	308.8	274.2
45°	279.4	365.3	455.4	501.3	486.1	436.6	384.1	344.1	308.5	281.0	247.8
47.5°	235.7	296.2	383.5	445.5	445.3	400.1	348.4	310.2	277.1	251.3	224.5
50°	210.8	263.5	337.3	407.7	413.6	375.7	326.6	288.7	257.8	230.8	209.2
52.5°	188.4	231.9	298.2	365.8	382.6	349.7	302.1	267.1	237.1	212.2	193.8
55°	159.2	192.9	243.3	306.4	331.9	308.7	266.4	233.7	209.4	188.5	172.6
57.5°	134.7	159.9	200.4	251.2	280.8	266.3	231.4	204.8	184.0	165.1	152.6
60°	119.3	139.9	174.2	216.7	249.4	239.2	209.4	184.7	167.0	150.6	138.8
62.5°	104.7	122.5	151.9	186.4	216.3	212.1	187.8	167.0	151.5	136.6	126.6
65°	84.3	97.2	120.2	147.2	171.3	173.3	155.8	141.7	127.9	116.1	107.2
67.5°	67.1	75.6	91.7	114.5	132.5	139.0	128.3	117.5	106.5	97.4	89.7
70°	56.6	63.4	75.2	93.6	110.2	117.0	110.8	102.4	92.9	85.4	78.8
72.5°	45.8	52.5	61.2	74.7	88.9	96.3	94.1	88.1	80.4	74.1	67.9
75°	34.5	36.6	42.5	51.6	62.7	69.1	70.6	67.5	61.3	56.6	52.9
77.5°	25.5	26.8	29.6	34.3	41.6	47.3	49.6	49.2	45.0	42.3	38.8
80°	20.4	21.1	22.5	24.5	30.0	35.7	37.3	37.3	34.3	33.2	29.8
82.5°	15.5	16.0	16.9	18.0	20.5	25.5	27.3	27.6	25.8	24.3	21.6
85°	8.9	8.6	9.1	9.8	10.2	11.6	14.3	14.8	14.3	12.5	11.8
87.5°	5.4	5.4	5.1	4.6	4.5	4.3	4.9	5.4	5.0	4.8	4.8
90°	11.8	10.5	9.2	7.7	6.0	4.2	2.5	0.7	2.5	4.2	6.0
92.5°	15.3	14.7	14.1	13.8	14.0	14.1	14.3	14.4	14.3	14.1	14.0
95°	25.7	24.6	23.4	25.5	30.8	36.0	41.3	46.5	41.3	36.0	30.8
97.5°	32.2	29.6	27.0	33.1	47.9	62.7	77.5	92.3	77.5	62.7	47.9
100°	35.4	32.7	30.0	39.5	61.3	83.1	104.8	126.6	104.8	83.1	61.3
102.5°	87.1	109.7	132.3	145.9	150.6	155.2	159.8	164.4	159.8	155.2	150.6
105°	130.4	173.8	217.2	236.5	231.8	227.0	222.2	217.5	222.2	227.0	231.8
107.5°	165.2	217.2	269.3	293.4	289.5	285.7	281.8	278.0	281.8	285.7	289.5
110°	217.1	263.0	308.9	330.2	326.9	323.6	320.2	316.9	320.2	323.6	326.9





TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	338.4	349.8	361.1	365.3	362.4	359.4	356.5	353.5	356.5	359.4	362.4
115°	433.4	429.4	425.5	422.1	419.4	416.7	414.0	411.3	414.0	416.7	419.4
117.5°	483.4	480.7	477.9	475.0	472.0	469.0	466.0	463.0	466.0	469.0	472.0
120°	518.6	515.8	512.9	510.3	507.9	505.5	503.1	500.7	503.1	505.5	507.9
122.5°	551.9	548.8	545.6	542.8	540.3	537.8	535.3	532.8	535.3	537.8	540.3
125°	598.4	595.4	592.4	589.8	587.8	585.7	583.6	581.6	583.6	585.7	587.8
127.5°	641.7	639.5	637.2	634.9	632.6	630.4	628.1	625.8	628.1	630.4	632.6
130°	669.6	667.9	666.1	664.0	661.4	658.9	656.4	653.8	656.4	658.9	661.4
132.5°	696.5	694.8	693.0	691.1	688.9	686.8	684.6	682.4	684.6	686.8	688.9
135°	734.6	733.2	731.8	729.8	727.3	724.7	722.2	719.6	722.2	724.7	727.3
137.5°	769.3	767.7	766.1	764.4	762.6	760.8	759.0	757.3	759.0	760.8	762.6
140°	792.0	790.2	788.5	786.9	785.7	784.4	783.1	781.9	783.1	784.4	785.7
142.5°	812.6	810.6	808.6	807.0	805.9	804.8	803.6	802.5	803.6	804.8	805.9
145°	840.8	838.1	835.4	834.2	834.3	834.5	834.6	834.8	834.6	834.5	834.3
147.5°	866.9	864.3	861.6	860.6	861.2	861.8	862.4	863.0	862.4	861.8	861.2
150°	882.6	880.1	877.6	876.8	878.0	879.1	880.2	881.3	880.2	879.1	878.0
152.5°	897.2	894.8	892.4	891.8	893.0	894.3	895.5	896.7	895.5	894.3	893.0
155°	917.5	915.6	913.7	913.5	914.9	916.3	917.8	919.2	917.8	916.3	914.9
157.5°	934.7	933.4	932.0	932.0	933.2	934.4	935.6	936.8	935.6	934.4	933.2
160°	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1	946.1	945.2	944.2
162.5°	954.0	953.2	952.4	952.4	953.4	954.4	955.3	956.3	955.3	954.4	953.4
165°	965.5	965.0	964.5	964.7	965.7	966.7	967.6	968.6	967.6	966.7	965.7
167.5°	974.5	974.1	973.6	973.9	974.9	975.8	976.8	977.7	976.8	975.8	974.9
170°	979.4	979.1	978.7	979.1	980.0	981.0	981.9	982.9	981.9	981.0	980.0
172.5°	982.8	982.5	982.2	982.5	983.4	984.4	985.3	986.3	985.3	984.4	983.4
175°	986.5	986.2	985.9	986.3	987.4	988.5	989.6	990.7	989.6	988.5	987.4
177.5°	987.8	987.6	987.5	987.9	988.8	989.7	990.6	991.5	990.6	989.7	988.8
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	644.5	643.2	640.8	637.2	635.0	631.2	628.7	630.1	630.5	630.1	629.8
5°	627.2	622.4	615.8	609.4	603.5	597.2	593.5	592.0	588.8	587.0	586.0
7.5°	606.2	598.0	588.7	577.6	568.2	558.3	553.3	550.8	544.3	540.8	537.7
10°	590.6	577.6	568.3	553.8	544.9	532.0	523.1	523.4	514.5	509.5	505.9
12.5°	573.3	559.1	543.6	530.5	518.2	507.8	497.1	492.8	483.4	478.6	468.8
15°	544.7	528.1	511.8	494.1	481.6	465.4	450.0	431.1	415.9	402.7	399.1
17.5°	513.5	492.9	476.5	455.7	434.3	407.2	389.3	378.3	369.2	362.2	357.0
20°	492.0	471.1	453.6	422.3	393.4	375.0	361.9	353.4	343.9	336.4	332.3
22.5°	469.5	447.7	423.8	388.8	366.3	351.6	339.9	330.2	323.7	317.9	314.1
25°	437.5	413.6	374.3	350.3	332.1	316.6	308.5	302.6	295.8	287.8	284.2
27.5°	403.7	365.8	337.5	319.6	302.3	292.3	284.9	276.1	270.0	266.4	262.6
30°	378.4	340.5	318.5	298.9	286.7	275.5	266.9	261.9	256.0	249.9	247.4
32.5°	350.3	320.0	298.8	282.6	270.1	260.6	253.8	245.7	241.5	237.7	232.5
35°	315.3	292.3	273.0	259.9	248.0	240.3	232.4	227.6	219.9	216.7	214.7
37.5°	285.7	265.8	251.4	237.5	228.1	219.6	214.7	207.1	203.8	199.3	195.0
40°	268.9	249.4	235.6	224.2	213.7	207.4	201.3	195.1	190.1	188.1	182.9
42.5°	251.9	236.0	222.1	209.7	202.7	195.9	188.2	183.7	178.5	175.2	172.0
45°	228.3	214.2	202.4	192.2	184.4	177.4	172.4	164.9	162.0	155.4	152.6
47.5°	207.6	194.5	183.2	173.5	166.0	161.4	154.1	148.2	143.5	139.4	135.9
50°	192.9	181.9	171.0	162.4	155.6	149.0	141.5	138.6	131.3	129.2	127.2
52.5°	179.4	169.0	159.1	150.6	143.8	137.4	130.8	126.9	122.0	120.0	118.5
55°	160.6	150.6	141.1	133.6	126.8	120.2	116.1	111.3	109.0	107.4	105.6
57.5°	141.7	132.7	125.4	117.8	110.9	105.7	101.0	98.1	95.8	93.7	91.5
60°	129.7	121.1	114.5	107.4	100.4	96.1	92.5	89.0	86.3	83.1	82.2
62.5°	117.0	109.4	103.4	96.5	90.4	86.5	83.0	79.8	76.5	71.9	70.6
65°	99.5	93.6	87.2	81.5	76.1	72.2	67.2	63.6	62.2	61.8	61.6
67.5°	83.7	78.1	72.6	66.8	61.9	58.3	55.7	55.2	54.2	54.0	53.3
70°	73.1	67.9	62.5	57.0	52.2	51.6	50.7	49.7	48.6	48.2	47.7
72.5°	63.7	58.3	52.8	48.5	46.4	45.6	44.7	43.7	43.0	42.5	42.3
75°	48.8	43.8	40.2	38.6	37.5	36.8	35.4	34.8	34.3	33.6	33.4
77.5°	35.2	32.3	30.7	29.7	28.5	27.8	27.0	26.3	25.8	25.7	25.3
80°	26.8	25.4	24.3	22.9	22.5	21.6	21.4	20.7	20.9	20.2	20.2
82.5°	20.8	19.1	18.1	17.5	17.0	16.3	16.1	15.8	15.8	15.3	15.3
85°	10.7	10.2	9.8	9.3	9.3	8.6	8.9	8.6	8.6	8.2	8.0
87.5°	5.0	5.1	5.0	5.3	5.5	5.6	5.7	5.7	5.9	6.0	6.0
90°	7.7	9.2	10.5	11.8	13.0	14.3	15.1	15.9	16.7	17.5	18.0
92.5°	13.8	14.1	14.7	15.3	16.0	16.6	17.0	17.4	17.8	18.2	18.6
95°	25.5	23.4	24.6	25.7	26.8	27.9	28.7	29.5	30.3	31.1	31.4
97.5°	33.1	27.0	29.6	32.2	34.8	37.3	38.0	38.6	39.2	39.9	40.3
100°	39.5	30.0	32.7	35.4	38.1	40.8	42.0	43.3	44.6	45.9	46.7
102.5°	145.9	132.3	109.7	87.1	64.5	41.9	43.6	45.2	46.9	48.5	49.6
105°	236.5	217.2	173.8	130.4	87.0	43.6	45.4	47.1	48.9	50.6	51.8
107.5°	293.4	269.3	217.2	165.2	113.1	61.1	59.3	57.5	55.7	54.0	53.4
110°	330.2	308.9	263.0	217.1	171.1	125.2	109.3	93.4	77.5	61.6	54.0



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	365.3	361.1	349.8	338.4	327.1	315.7	257.8	199.8	141.8	83.8	55.0
115°	422.1	425.5	429.4	433.4	437.4	441.4	367.8	294.2	220.6	147.0	104.4
117.5°	475.0	477.9	480.7	483.4	486.1	488.9	471.1	453.3	435.4	417.6	389.9
120°	510.3	512.9	515.8	518.6	521.5	524.3	526.2	528.2	530.1	532.0	522.2
122.5°	542.8	545.6	548.8	551.9	555.0	558.1	559.2	560.4	561.5	562.7	561.2
125°	589.8	592.4	595.4	598.4	601.4	604.5	605.6	606.7	607.8	608.9	609.7
127.5°	634.9	637.2	639.5	641.7	644.0	646.2	647.9	649.5	651.1	652.7	653.6
130°	664.0	666.1	667.9	669.6	671.4	673.1	674.9	676.6	678.4	680.1	680.9
132.5°	691.1	693.0	694.8	696.5	698.3	700.0	701.5	703.0	704.5	706.0	706.7
135°	729.8	731.8	733.2	734.6	736.1	737.5	739.1	740.7	742.3	743.9	744.5
137.5°	764.4	766.1	767.7	769.3	770.9	772.6	774.1	775.7	777.2	778.8	779.3
140°	786.9	788.5	790.2	792.0	793.7	795.5	796.9	798.3	799.7	801.2	801.5
142.5°	807.0	808.6	810.6	812.6	814.6	816.6	817.9	819.2	820.5	821.8	822.1
145°	834.2	835.4	838.1	840.8	843.5	846.2	847.4	848.5	849.6	850.7	850.8
147.5°	860.6	861.6	864.3	866.9	869.6	872.3	873.1	873.9	874.8	875.6	875.7
150°	876.8	877.6	880.1	882.6	885.2	887.7	888.7	889.6	890.6	891.5	891.6
152.5°	891.8	892.4	894.8	897.2	899.6	902.0	903.0	903.9	904.9	905.9	905.8
155°	913.5	913.7	915.6	917.5	919.4	921.3	922.3	923.3	924.2	925.2	925.0
157.5°	932.0	932.0	933.4	934.7	936.0	937.4	938.5	939.5	940.6	941.7	941.6
160°	943.3	943.3	944.2	945.2	946.1	947.1	948.1	949.0	950.0	950.9	950.8
162.5°	952.4	952.4	953.2	954.0	954.9	955.7	956.8	957.8	958.9	960.0	959.9
165°	964.7	964.5	965.0	965.5	965.9	966.4	967.5	968.6	969.8	970.9	970.9
167.5°	973.9	973.6	974.1	974.5	975.0	975.4	976.5	977.7	978.8	979.9	979.7
170°	979.1	978.7	979.1	979.4	979.7	980.0	981.1	982.2	983.3	984.5	984.3
172.5°	982.5	982.2	982.5	982.8	983.1	983.4	984.6	985.7	986.8	987.9	987.7
175°	986.3	985.9	986.2	986.5	986.8	987.2	988.3	989.4	990.5	991.6	991.4
177.5°	987.9	987.5	987.6	987.8	987.9	988.0	988.9	989.8	990.7	991.6	991.5
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	627.8	628.1	627.6	627.9	627.6	628.1	627.8	629.8	630.1	630.5	630.1
5°	584.9	582.2	581.7	581.1	581.7	582.2	584.9	586.0	587.0	588.8	592.0
7.5°	533.8	533.4	532.2	530.6	532.2	533.4	533.8	537.7	540.8	544.3	550.8
10°	500.9	499.7	499.5	497.9	499.5	499.7	500.9	505.9	509.5	514.5	523.4
12.5°	462.3	455.0	454.3	450.3	454.3	455.0	462.3	468.8	478.6	483.4	492.8
15°	393.7	392.3	387.7	384.8	387.7	392.3	393.7	399.1	402.7	415.9	431.1
17.5°	354.4	349.9	348.5	347.9	348.5	349.9	354.4	357.0	362.2	369.2	378.3
20°	329.1	325.1	324.4	323.9	324.4	325.1	329.1	332.3	336.4	343.9	353.4
22.5°	311.7	307.4	305.7	304.3	305.7	307.4	311.7	314.1	317.9	323.7	330.2
25°	281.9	280.3	279.4	278.9	279.4	280.3	281.9	284.2	287.8	295.8	302.6
27.5°	258.6	255.1	254.4	253.2	254.4	255.1	258.6	262.6	266.4	270.0	276.1
30°	245.3	244.2	242.6	241.2	242.6	244.2	245.3	247.4	249.9	256.0	261.9
32.5°	229.7	228.7	227.3	226.7	227.3	228.7	229.7	232.5	237.7	241.5	245.7
35°	212.4	209.2	207.8	205.8	207.8	209.2	212.4	214.7	216.7	219.9	227.6
37.5°	194.1	192.4	190.5	191.2	190.5	192.4	194.1	195.0	199.3	203.8	207.1
40°	179.9	178.8	178.3	178.1	178.3	178.8	179.9	182.9	188.1	190.1	195.1
42.5°	168.6	165.5	164.3	164.3	164.3	165.5	168.6	172.0	175.2	178.5	183.7
45°	151.5	148.6	146.5	146.7	146.5	148.6	151.5	152.6	155.4	162.0	164.9
47.5°	134.0	133.9	132.6	133.0	132.6	133.9	134.0	135.9	139.4	143.5	148.2
50°	125.6	124.3	123.3	123.6	123.3	124.3	125.6	127.2	129.2	131.3	138.6
52.5°	117.6	116.4	115.7	116.7	115.7	116.4	117.6	118.5	120.0	122.0	126.9
55°	104.5	103.1	102.9	102.7	102.9	103.1	104.5	105.6	107.4	109.0	111.3
57.5°	89.8	88.9	87.5	87.0	87.5	88.9	89.8	91.5	93.7	95.8	98.1
60°	79.3	77.5	75.2	75.0	75.2	77.5	79.3	82.2	83.1	86.3	89.0
62.5°	69.6	69.3	68.8	68.8	68.8	69.3	69.6	70.6	71.9	76.5	79.8
65°	61.1	60.9	61.1	61.3	61.1	60.9	61.1	61.6	61.8	62.2	63.6
67.5°	53.2	52.8	52.4	52.6	52.4	52.8	53.2	53.3	54.0	54.2	55.2
70°	47.2	47.0	46.8	46.8	46.8	47.0	47.2	47.7	48.2	48.6	49.7
72.5°	41.4	41.4	41.2	41.0	41.2	41.4	41.4	42.3	42.5	43.0	43.7
75°	33.2	32.7	32.7	32.7	32.7	32.7	33.2	33.4	33.6	34.3	34.8
77.5°	25.3	25.0	24.8	24.6	24.8	25.0	25.3	25.3	25.7	25.8	26.3
80°	20.0	19.8	19.5	19.5	19.5	19.8	20.0	20.2	20.2	20.9	20.7
82.5°	15.3	15.0	15.0	14.8	15.0	15.0	15.3	15.3	15.3	15.8	15.8
85°	8.2	8.4	8.2	8.6	8.2	8.4	8.2	8.0	8.2	8.6	8.6
87.5°	6.0	5.9	6.2	6.0	6.2	5.9	6.0	6.0	6.0	5.9	5.7
90°	18.4	18.7	19.0	19.3	19.0	18.7	18.4	18.0	17.5	16.7	15.9
92.5°	18.7	18.9	19.1	19.3	19.1	18.9	18.7	18.6	18.2	17.8	17.4
95°	31.2	31.1	30.9	30.8	30.9	31.1	31.2	31.4	31.1	30.3	29.5
97.5°	40.5	40.7	40.9	41.1	40.9	40.7	40.5	40.3	39.9	39.2	38.6
100°	47.0	47.3	47.6	47.9	47.6	47.3	47.0	46.7	45.9	44.6	43.3
102.5°	50.0	50.5	50.9	51.4	50.9	50.5	50.0	49.6	48.5	46.9	45.2
105°	52.5	53.1	53.7	54.4	53.7	53.1	52.5	51.8	50.6	48.9	47.1
107.5°	54.0	54.7	55.3	55.9	55.3	54.7	54.0	53.4	54.0	55.7	57.5
110°	54.6	55.2	55.9	56.5	55.9	55.2	54.6	54.0	61.6	77.5	93.4



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	55.6	56.1	56.6	57.1	56.6	56.1	55.6	55.0	83.8	141.8	199.8
115°	93.0	81.5	70.1	58.7	70.1	81.5	93.0	104.4	147.0	220.6	294.2
117.5°	352.3	314.7	277.1	239.5	277.1	314.7	352.3	389.9	417.6	435.4	453.3
120°	500.7	479.3	457.8	436.4	457.8	479.3	500.7	522.2	532.0	530.1	528.2
122.5°	557.0	552.8	548.7	544.5	548.7	552.8	557.0	561.2	562.7	561.5	560.4
125°	610.2	610.7	611.1	611.6	611.1	610.7	610.2	609.7	608.9	607.8	606.7
127.5°	653.7	653.8	653.9	654.0	653.9	653.8	653.7	653.6	652.7	651.1	649.5
130°	680.8	680.6	680.4	680.3	680.4	680.6	680.8	680.9	680.1	678.4	676.6
132.5°	706.5	706.4	706.2	706.0	706.2	706.4	706.5	706.7	706.0	704.5	703.0
135°	744.2	743.9	743.5	743.2	743.5	743.9	744.2	744.5	743.9	742.3	740.7
137.5°	778.8	778.2	777.7	777.1	777.7	778.2	778.8	779.3	778.8	777.2	775.7
140°	800.7	799.9	799.1	798.3	799.1	799.9	800.7	801.5	801.2	799.7	798.3
142.5°	821.3	820.5	819.7	818.9	819.7	820.5	821.3	822.1	821.8	820.5	819.2
145°	850.1	849.3	848.5	847.7	848.5	849.3	850.1	850.8	850.7	849.6	848.5
147.5°	875.0	874.3	873.7	873.0	873.7	874.3	875.0	875.7	875.6	874.8	873.9
150°	890.8	890.0	889.2	888.4	889.2	890.0	890.8	891.6	891.5	890.6	889.6
152.5°	904.8	903.7	902.7	901.6	902.7	903.7	904.8	905.8	905.9	904.9	903.9
155°	923.7	922.5	921.2	919.9	921.2	922.5	923.7	925.0	925.2	924.2	923.3
157.5°	940.4	939.1	937.9	936.7	937.9	939.1	940.4	941.6	941.7	940.6	939.5
160°	949.7	948.6	947.5	946.4	947.5	948.6	949.7	950.8	950.9	950.0	949.0
162.5°	958.5	957.1	955.8	954.4	955.8	957.1	958.5	959.9	960.0	958.9	957.8
165°	969.8	968.6	967.5	966.4	967.5	968.6	969.8	970.9	970.9	969.8	968.6
167.5°	978.3	976.9	975.4	974.0	975.4	976.9	978.3	979.7	979.9	978.8	977.7
170°	982.9	981.4	980.0	978.6	980.0	981.4	982.9	984.3	984.5	983.3	982.2
172.5°	986.3	984.9	983.4	982.0	983.4	984.9	986.3	987.7	987.9	986.8	985.7
175°	989.8	988.2	986.6	985.0	986.6	988.2	989.8	991.4	991.6	990.5	989.4
177.5°	990.3	989.2	988.0	986.9	988.0	989.2	990.3	991.5	991.6	990.7	989.8
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	628.7	631.2	635.0	637.2	640.8	643.2	644.5	646.8	648.1	652.7	657.4
5°	593.5	597.2	603.5	609.4	615.8	622.4	627.2	632.6	637.6	646.2	655.3
7.5°	553.3	558.3	568.2	577.6	588.7	598.0	606.2	615.5	623.8	636.2	649.1
10°	523.1	532.0	544.9	553.8	568.3	577.6	590.6	600.8	612.4	628.8	643.3
12.5°	497.1	507.8	518.2	530.5	543.6	559.1	573.3	586.5	600.2	617.1	634.2
15°	450.0	465.4	481.6	494.1	511.8	528.1	544.7	562.4	579.2	599.5	621.7
17.5°	389.3	407.2	434.3	455.7	476.5	492.9	513.5	534.9	554.7	579.1	603.9
20°	361.9	375.0	393.4	422.3	453.6	471.1	492.0	515.6	538.3	564.9	591.5
22.5°	339.9	351.6	366.3	388.8	423.8	447.7	469.5	493.5	519.8	546.9	576.4
25°	308.5	316.6	332.1	350.3	374.3	413.6	437.5	461.6	490.2	519.3	552.9
27.5°	284.9	292.3	302.3	319.6	337.5	365.8	403.7	430.0	458.5	491.2	526.1
30°	266.9	275.5	286.7	298.9	318.5	340.5	378.4	408.9	437.0	470.7	507.9
32.5°	253.8	260.6	270.1	282.6	298.8	320.0	350.3	387.2	414.7	450.1	489.0
35°	232.4	240.3	248.0	259.9	273.0	292.3	315.3	354.8	382.1	417.0	456.1
37.5°	214.7	219.6	228.1	237.5	251.4	265.8	285.7	321.1	350.6	384.9	424.9
40°	201.3	207.4	213.7	224.2	235.6	249.4	268.9	295.3	329.1	362.8	401.8
42.5°	188.2	195.9	202.7	209.7	222.1	236.0	251.9	274.2	308.8	340.6	378.6
45°	172.4	177.4	184.4	192.2	202.4	214.2	228.3	247.8	281.0	308.5	344.1
47.5°	154.1	161.4	166.0	173.5	183.2	194.5	207.6	224.5	251.3	277.1	310.2
50°	141.5	149.0	155.6	162.4	171.0	181.9	192.9	209.2	230.8	257.8	288.7
52.5°	130.8	137.4	143.8	150.6	159.1	169.0	179.4	193.8	212.2	237.1	267.1
55°	116.1	120.2	126.8	133.6	141.1	150.6	160.6	172.6	188.5	209.4	233.7
57.5°	101.0	105.7	110.9	117.8	125.4	132.7	141.7	152.6	165.1	184.0	204.8
60°	92.5	96.1	100.4	107.4	114.5	121.1	129.7	138.8	150.6	167.0	184.7
62.5°	83.0	86.5	90.4	96.5	103.4	109.4	117.0	126.6	136.6	151.5	167.0
65°	67.2	72.2	76.1	81.5	87.2	93.6	99.5	107.2	116.1	127.9	141.7
67.5°	55.7	58.3	61.9	66.8	72.6	78.1	83.7	89.7	97.4	106.5	117.5
70°	50.7	51.6	52.2	57.0	62.5	67.9	73.1	78.8	85.4	92.9	102.4
72.5°	44.7	45.6	46.4	48.5	52.8	58.3	63.7	67.9	74.1	80.4	88.1
75°	35.4	36.8	37.5	38.6	40.2	43.8	48.8	52.9	56.6	61.3	67.5
77.5°	27.0	27.8	28.5	29.7	30.7	32.3	35.2	38.8	42.3	45.0	49.2
80°	21.4	21.6	22.5	22.9	24.3	25.4	26.8	29.8	33.2	34.3	37.3
82.5°	16.1	16.3	17.0	17.5	18.1	19.1	20.8	21.6	24.3	25.8	27.6
85°	8.9	8.6	9.3	9.3	9.8	10.2	10.7	11.8	12.5	14.3	14.8
87.5°	5.7	5.6	5.5	5.3	5.0	5.1	5.0	4.8	4.8	5.0	5.4
90°	15.1	14.3	13.0	11.8	10.5	9.2	7.7	6.0	4.2	2.5	0.7
92.5°	17.0	16.6	16.0	15.3	14.7	14.1	13.8	14.0	14.1	14.3	14.4
95°	28.7	27.9	26.8	25.7	24.6	23.4	25.5	30.8	36.0	41.3	46.5
97.5°	38.0	37.3	34.8	32.2	29.6	27.0	33.1	47.9	62.7	77.5	92.3
100°	42.0	40.8	38.1	35.4	32.7	30.0	39.5	61.3	83.1	104.8	126.6
102.5°	43.6	41.9	64.5	87.1	109.7	132.3	145.9	150.6	155.2	159.8	164.4
105°	45.4	43.6	87.0	130.4	173.8	217.2	236.5	231.8	227.0	222.2	217.5
107.5°	59.3	61.1	113.1	165.2	217.2	269.3	293.4	289.5	285.7	281.8	278.0
110°	109.3	125.2	171.1	217.1	263.0	308.9	330.2	326.9	323.6	320.2	316.9



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	257.8	315.7	327.1	338.4	349.8	361.1	365.3	362.4	359.4	356.5	353.5
115°	367.8	441.4	437.4	433.4	429.4	425.5	422.1	419.4	416.7	414.0	411.3
117.5°	471.1	488.9	486.1	483.4	480.7	477.9	475.0	472.0	469.0	466.0	463.0
120°	526.2	524.3	521.5	518.6	515.8	512.9	510.3	507.9	505.5	503.1	500.7
122.5°	559.2	558.1	555.0	551.9	548.8	545.6	542.8	540.3	537.8	535.3	532.8
125°	605.6	604.5	601.4	598.4	595.4	592.4	589.8	587.8	585.7	583.6	581.6
127.5°	647.9	646.2	644.0	641.7	639.5	637.2	634.9	632.6	630.4	628.1	625.8
130°	674.9	673.1	671.4	669.6	667.9	666.1	664.0	661.4	658.9	656.4	653.8
132.5°	701.5	700.0	698.3	696.5	694.8	693.0	691.1	688.9	686.8	684.6	682.4
135°	739.1	737.5	736.1	734.6	733.2	731.8	729.8	727.3	724.7	722.2	719.6
137.5°	774.1	772.6	770.9	769.3	767.7	766.1	764.4	762.6	760.8	759.0	757.3
140°	796.9	795.5	793.7	792.0	790.2	788.5	786.9	785.7	784.4	783.1	781.9
142.5°	817.9	816.6	814.6	812.6	810.6	808.6	807.0	805.9	804.8	803.6	802.5
145°	847.4	846.2	843.5	840.8	838.1	835.4	834.2	834.3	834.5	834.6	834.8
147.5°	873.1	872.3	869.6	866.9	864.3	861.6	860.6	861.2	861.8	862.4	863.0
150°	888.7	887.7	885.2	882.6	880.1	877.6	876.8	878.0	879.1	880.2	881.3
152.5°	903.0	902.0	899.6	897.2	894.8	892.4	891.8	893.0	894.3	895.5	896.7
155°	922.3	921.3	919.4	917.5	915.6	913.7	913.5	914.9	916.3	917.8	919.2
157.5°	938.5	937.4	936.0	934.7	933.4	932.0	932.0	933.2	934.4	935.6	936.8
160°	948.1	947.1	946.1	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1
162.5°	956.8	955.7	954.9	954.0	953.2	952.4	952.4	953.4	954.4	955.3	956.3
165°	967.5	966.4	965.9	965.5	965.0	964.5	964.7	965.7	966.7	967.6	968.6
167.5°	976.5	975.4	975.0	974.5	974.1	973.6	973.9	974.9	975.8	976.8	977.7
170°	981.1	980.0	979.7	979.4	979.1	978.7	979.1	980.0	981.0	981.9	982.9
172.5°	984.6	983.4	983.1	982.8	982.5	982.2	982.5	983.4	984.4	985.3	986.3
175°	988.3	987.2	986.8	986.5	986.2	985.9	986.3	987.4	988.5	989.6	990.7
177.5°	988.9	988.0	987.9	987.8	987.6	987.5	987.9	988.8	989.7	990.6	991.5
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	657.6	658.1	661.7	663.4	666.6	667.9	669.4	669.0	669.0	669.7	674.8
5°	659.0	663.5	670.3	676.9	683.3	688.7	692.4	696.0	697.4	703.9	709.8
7.5°	656.6	665.0	676.2	686.3	698.3	707.7	715.5	722.6	727.4	737.0	746.8
10°	653.5	665.3	678.0	691.0	707.6	720.1	732.8	742.6	745.7	760.0	768.2
12.5°	647.3	663.1	679.3	696.1	712.3	729.5	743.5	753.3	764.5	777.3	792.4
15°	638.1	656.2	677.4	698.9	722.1	743.0	758.0	775.0	787.3	801.4	814.6
17.5°	624.8	648.2	675.0	700.0	726.8	749.2	769.9	786.2	794.8	802.9	804.8
20°	614.2	639.4	671.0	700.5	727.3	753.2	773.7	787.3	789.6	789.8	777.8
22.5°	602.8	631.3	664.3	694.5	726.6	755.4	771.3	777.1	768.1	752.7	729.4
25°	581.7	614.7	653.1	687.6	722.6	749.8	755.3	745.1	713.5	680.3	638.3
27.5°	558.9	596.0	637.1	675.5	712.8	729.7	717.9	681.0	624.2	574.7	514.8
30°	542.2	583.8	624.2	667.1	701.7	708.9	681.9	627.6	561.3	486.8	427.0
32.5°	523.1	566.7	611.1	655.5	684.4	677.3	632.7	565.8	488.1	414.8	358.4
35°	495.9	540.8	588.8	633.3	651.7	621.0	554.2	467.2	387.7	319.4	280.5
37.5°	464.4	513.4	563.2	604.1	602.8	551.7	460.7	370.9	304.1	263.6	236.0
40°	442.0	491.6	545.4	579.9	565.2	498.6	400.0	315.3	266.4	234.2	214.0
42.5°	420.6	470.3	523.8	551.2	525.5	443.7	345.5	279.1	238.8	213.7	197.3
45°	384.1	436.6	486.1	501.3	455.4	365.3	279.4	231.2	204.4	185.8	174.5
47.5°	348.4	400.1	445.3	445.5	383.5	296.2	235.7	200.1	177.2	162.8	154.6
50°	326.6	375.7	413.6	407.7	337.3	263.5	210.8	180.1	161.1	149.9	141.3
52.5°	302.1	349.7	382.6	365.8	298.2	231.9	188.4	162.7	146.9	137.2	129.5
55°	266.4	308.7	331.9	306.4	243.3	192.9	159.2	139.0	127.2	119.0	112.4
57.5°	231.4	266.3	280.8	251.2	200.4	159.9	134.7	119.5	107.8	101.9	98.5
60°	209.4	239.2	249.4	216.7	174.2	139.9	119.3	105.2	96.5	92.7	89.3
62.5°	187.8	212.1	216.3	186.4	151.9	122.5	104.7	92.8	87.1	83.4	80.2
65°	155.8	173.3	171.3	147.2	120.2	97.2	84.3	77.0	72.7	67.5	61.8
67.5°	128.3	139.0	132.5	114.5	91.7	75.6	67.1	61.6	56.2	51.3	50.0
70°	110.8	117.0	110.2	93.6	75.2	63.4	56.6	50.0	46.8	45.7	43.6
72.5°	94.1	96.3	88.9	74.7	61.2	52.5	45.8	42.2	40.4	39.5	38.2
75°	70.6	69.1	62.7	51.6	42.5	36.6	34.5	33.2	32.0	31.1	30.4
77.5°	49.6	47.3	41.6	34.3	29.6	26.8	25.5	24.8	24.3	23.8	23.1
80°	37.3	35.7	30.0	24.5	22.5	21.1	20.4	19.5	19.5	19.1	18.4
82.5°	27.3	25.5	20.5	18.0	16.9	16.0	15.5	15.0	14.8	14.9	14.4
85°	14.3	11.6	10.2	9.8	9.1	8.6	8.9	8.4	8.4	8.4	8.2
87.5°	4.9	4.3	4.5	4.6	5.1	5.4	5.4	5.7	6.1	6.1	6.5
90°	2.5	4.2	6.0	7.7	9.2	10.5	11.8	13.0	14.3	15.1	15.9
92.5°	14.3	14.1	14.0	13.8	14.1	14.7	15.3	16.0	16.6	17.0	17.4
95°	41.3	36.0	30.8	25.5	23.4	24.6	25.7	26.8	27.9	28.7	29.5
97.5°	77.5	62.7	47.9	33.1	27.0	29.6	32.2	34.8	37.3	38.0	38.6
100°	104.8	83.1	61.3	39.5	30.0	32.7	35.4	38.1	40.8	42.0	43.3
102.5°	159.8	155.2	150.6	145.9	132.3	109.7	87.1	64.5	41.9	43.6	45.2
105°	222.2	227.0	231.8	236.5	217.2	173.8	130.4	87.0	43.6	45.4	47.1
107.5°	281.8	285.7	289.5	293.4	269.3	217.2	165.2	113.1	61.1	59.3	57.5
110°	320.2	323.6	326.9	330.2	308.9	263.0	217.1	171.1	125.2	109.3	93.4





TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	356.5	359.4	362.4	365.3	361.1	349.8	338.4	327.1	315.7	257.8	199.8
115°	414.0	416.7	419.4	422.1	425.5	429.4	433.4	437.4	441.4	367.8	294.2
117.5°	466.0	469.0	472.0	475.0	477.9	480.7	483.4	486.1	488.9	471.1	453.3
120°	503.1	505.5	507.9	510.3	512.9	515.8	518.6	521.5	524.3	526.2	528.2
122.5°	535.3	537.8	540.3	542.8	545.6	548.8	551.9	555.0	558.1	559.2	560.4
125°	583.6	585.7	587.8	589.8	592.4	595.4	598.4	601.4	604.5	605.6	606.7
127.5°	628.1	630.4	632.6	634.9	637.2	639.5	641.7	644.0	646.2	647.9	649.5
130°	656.4	658.9	661.4	664.0	666.1	667.9	669.6	671.4	673.1	674.9	676.6
132.5°	684.6	686.8	688.9	691.1	693.0	694.8	696.5	698.3	700.0	701.5	703.0
135°	722.2	724.7	727.3	729.8	731.8	733.2	734.6	736.1	737.5	739.1	740.7
137.5°	759.0	760.8	762.6	764.4	766.1	767.7	769.3	770.9	772.6	774.1	775.7
140°	783.1	784.4	785.7	786.9	788.5	790.2	792.0	793.7	795.5	796.9	798.3
142.5°	803.6	804.8	805.9	807.0	808.6	810.6	812.6	814.6	816.6	817.9	819.2
145°	834.6	834.5	834.3	834.2	835.4	838.1	840.8	843.5	846.2	847.4	848.5
147.5°	862.4	861.8	861.2	860.6	861.6	864.3	866.9	869.6	872.3	873.1	873.9
150°	880.2	879.1	878.0	876.8	877.6	880.1	882.6	885.2	887.7	888.7	889.6
152.5°	895.5	894.3	893.0	891.8	892.4	894.8	897.2	899.6	902.0	903.0	903.9
155°	917.8	916.3	914.9	913.5	913.7	915.6	917.5	919.4	921.3	922.3	923.3
157.5°	935.6	934.4	933.2	932.0	932.0	933.4	934.7	936.0	937.4	938.5	939.5
160°	946.1	945.2	944.2	943.3	943.3	944.2	945.2	946.1	947.1	948.1	949.0
162.5°	955.3	954.4	953.4	952.4	952.4	953.2	954.0	954.9	955.7	956.8	957.8
165°	967.6	966.7	965.7	964.7	964.5	965.0	965.5	965.9	966.4	967.5	968.6
167.5°	976.8	975.8	974.9	973.9	973.6	974.1	974.5	975.0	975.4	976.5	977.7
170°	981.9	981.0	980.0	979.1	978.7	979.1	979.4	979.7	980.0	981.1	982.2
172.5°	985.3	984.4	983.4	982.5	982.2	982.5	982.8	983.1	983.4	984.6	985.7
175°	989.6	988.5	987.4	986.3	985.9	986.2	986.5	986.8	987.2	988.3	989.4
177.5°	990.6	989.7	988.8	987.9	987.5	987.6	987.8	987.9	988.0	988.9	989.8
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6	988.6



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	653.7	653.7	653.7	653.7	653.7	653.7	653.7
2.5°	676.6	679.0	680.1	680.1	681.4	680.8	680.3
5°	715.5	719.8	720.8	724.8	727.8	726.9	727.3
7.5°	754.2	761.1	768.0	771.1	771.6	773.4	774.1
10°	778.0	783.7	794.3	792.8	800.7	805.3	797.8
12.5°	800.9	808.6	816.0	818.0	822.5	824.0	821.0
15°	821.6	825.7	826.1	825.0	826.4	825.2	820.9
17.5°	802.3	795.6	782.2	775.8	770.8	763.3	760.3
20°	770.3	750.7	728.0	718.9	708.3	687.4	692.4
22.5°	701.2	679.0	656.2	629.7	617.0	597.2	596.0
25°	593.8	555.4	513.1	483.6	466.3	446.6	437.9
27.5°	461.7	413.3	378.7	361.2	345.2	329.6	328.9
30°	374.8	338.5	311.7	296.7	286.9	280.3	281.7
32.5°	315.9	291.0	272.9	260.5	253.3	248.3	248.2
35°	258.3	241.2	229.6	224.4	219.2	215.6	215.8
37.5°	221.0	210.8	204.3	198.6	195.3	193.5	192.5
40°	201.9	193.5	188.5	185.1	182.4	179.9	179.4
42.5°	186.9	179.9	174.9	172.2	169.7	167.9	167.5
45°	165.8	160.1	155.6	152.6	151.5	149.9	149.9
47.5°	147.5	141.9	138.4	136.5	134.6	133.5	133.5
50°	135.2	130.8	127.7	126.5	124.9	124.3	124.0
52.5°	124.1	120.8	118.6	117.8	117.1	116.3	116.4
55°	109.0	107.2	106.3	105.6	104.5	103.1	104.0
57.5°	96.4	94.8	92.4	90.2	89.2	88.2	88.6
60°	87.5	84.3	81.1	78.6	77.9	75.9	75.9
62.5°	76.2	71.7	67.8	66.4	65.7	64.8	64.6
65°	58.6	56.8	55.9	55.0	54.5	54.5	54.1
67.5°	48.6	47.8	46.8	46.6	46.2	46.0	45.9
70°	42.9	42.0	41.6	41.3	40.9	41.1	40.4
72.5°	37.5	36.8	36.7	36.1	35.8	35.8	35.3
75°	29.5	29.5	29.3	29.1	28.6	28.4	28.6
77.5°	22.7	22.8	22.4	22.3	22.3	22.3	22.1
80°	18.2	18.4	18.2	17.9	17.7	17.9	17.7
82.5°	14.4	14.0	14.0	13.9	13.9	13.8	13.7
85°	8.2	8.4	8.2	8.0	8.0	8.0	8.2
87.5°	6.4	6.6	6.7	6.8	6.8	6.9	6.8
90°	16.7	17.5	18.0	18.4	18.7	19.0	19.3
92.5°	17.8	18.2	18.6	18.7	18.9	19.1	19.3
95°	30.3	31.1	31.4	31.2	31.1	30.9	30.8
97.5°	39.2	39.9	40.3	40.5	40.7	40.9	41.1
100°	44.6	45.9	46.7	47.0	47.3	47.6	47.9
102.5°	46.9	48.5	49.6	50.0	50.5	50.9	51.4
105°	48.9	50.6	51.8	52.5	53.1	53.7	54.4
107.5°	55.7	54.0	53.4	54.0	54.7	55.3	55.9
110°	77.5	61.6	54.0	54.6	55.2	55.9	56.5



TEST NUMBER: P331627

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	141.8	83.8	55.0	55.6	56.1	56.6	57.1
115°	220.6	147.0	104.4	93.0	81.5	70.1	58.7
117.5°	435.4	417.6	389.9	352.3	314.7	277.1	239.5
120°	530.1	532.0	522.2	500.7	479.3	457.8	436.4
122.5°	561.5	562.7	561.2	557.0	552.8	548.7	544.5
125°	607.8	608.9	609.7	610.2	610.7	611.1	611.6
127.5°	651.1	652.7	653.6	653.7	653.8	653.9	654.0
130°	678.4	680.1	680.9	680.8	680.6	680.4	680.3
132.5°	704.5	706.0	706.7	706.5	706.4	706.2	706.0
135°	742.3	743.9	744.5	744.2	743.9	743.5	743.2
137.5°	777.2	778.8	779.3	778.8	778.2	777.7	777.1
140°	799.7	801.2	801.5	800.7	799.9	799.1	798.3
142.5°	820.5	821.8	822.1	821.3	820.5	819.7	818.9
145°	849.6	850.7	850.8	850.1	849.3	848.5	847.7
147.5°	874.8	875.6	875.7	875.0	874.3	873.7	873.0
150°	890.6	891.5	891.6	890.8	890.0	889.2	888.4
152.5°	904.9	905.9	905.8	904.8	903.7	902.7	901.6
155°	924.2	925.2	925.0	923.7	922.5	921.2	919.9
157.5°	940.6	941.7	941.6	940.4	939.1	937.9	936.7
160°	950.0	950.9	950.8	949.7	948.6	947.5	946.4
162.5°	958.9	960.0	959.9	958.5	957.1	955.8	954.4
165°	969.8	970.9	970.9	969.8	968.6	967.5	966.4
167.5°	978.8	979.9	979.7	978.3	976.9	975.4	974.0
170°	983.3	984.5	984.3	982.9	981.4	980.0	978.6
172.5°	986.8	987.9	987.7	986.3	984.9	983.4	982.0
175°	990.5	991.6	991.4	989.8	988.2	986.6	985.0
177.5°	990.7	991.6	991.5	990.3	989.2	988.0	986.9
180°	988.6	988.6	988.6	988.6	988.6	988.6	988.6

(END OF REPORT)