

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331632

Luminaire Tested: **SA2XXRDIP-C290D725U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331632
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3864.7 lumens
Efficiency: N/A
Efficacy: 123.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 31.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331632
CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331632

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23
2	85	78	72	67	75	70	65	61	55	51	48	41	38	37	28	26	25	20
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22	17
4	71	61	53	48	63	55	48	43	43	39	35	32	29	27	22	21	19	15
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15	12
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	15	13	12	9
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11	8
10	44	33	26	21	40	30	24	20	24	20	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	8105	8105	8105
5°	8136	8003	8047
10°	8073	7873	7806
15°	7980	7639	7418
20°	7852	7306	6940
25°	7721	6928	6474
30°	7538	6538	5878
35°	7360	6116	5355
40°	7181	5678	4749
45°	6971	5186	4201
50°	6754	4690	3662
55°	6533	4155	3147
60°	6278	3594	2612
65°	5987	3018	2376
70°	5641	2488	2186
75°	5215	2264	2040
80°	4603	2027	1860
85°	3612	1593	1593



TEST NUMBER: P331632

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	1.2
10°-20°	129.0	3.3
20°-30°	181.2	4.7
30°-40°	197.6	5.1
40°-50°	181.6	4.7
50°-60°	142.7	3.7
60°-70°	93.0	2.4
70°-80°	48.0	1.2
80°-90°	16.1	0.4
90°-100°	162.5	4.2
100°-110°	551.5	14.3
110°-120°	585.9	15.2
120°-130°	482.3	12.5
130°-140°	387.3	10.0
140°-150°	292.7	7.6
150°-160°	205.7	5.3
160°-170°	121.1	3.1
170°-180°	39.4	1.0
0°-30°	357.2	9.2
0°-40°	554.7	14.4
0°-60°	879.0	22.7
0°-90°	1036.1	26.8
90°-120°	1300.0	33.6
90°-150°	2462.4	63.7
90°-180°	2829.0	73.2
0°-180°	3864.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	502	502	502	502	502	
5°	502	500	494	498	496	48
15°	477	472	457	449	444	134
25°	433	418	389	371	363	199
35°	373	349	310	283	272	234
45°	305	274	227	196	184	236
55°	232	196	148	121	112	207
65°	157	120	79	64	62	155
75°	84	53	36	33	33	88
85°	20	10	9	9	9	23
90°	1	11	27	25	26	2
95°	27	67	306	116	89	29
105°	95	144	579	1035	881	101
115°	168	212	485	1000	1159	167
125°	234	278	466	810	940	208
135°	275	328	460	681	779	213
145°	314	361	458	569	622	197
155°	357	386	445	503	523	164
165°	389	401	426	452	459	110
175°	406	406	410	415	414	39
180°	406	406	406	406	406	



TEST NUMBER: P331632

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	503.8	503.4	503.0	502.6	502.2	501.5	500.6	499.8	498.9	498.0	498.8
5°	502.0	501.5	501.0	500.5	500.0	499.0	497.7	496.4	495.1	493.8	494.7
7.5°	496.8	496.2	495.5	494.9	494.3	493.2	491.7	490.1	488.6	487.1	487.3
10°	492.4	491.7	491.0	490.3	489.6	488.2	486.2	484.2	482.2	480.2	479.9
12.5°	487.0	486.1	485.2	484.4	483.5	481.8	479.2	476.6	474.0	471.4	470.9
15°	477.4	476.3	475.2	474.1	473.0	470.7	467.3	463.9	460.4	457.0	455.1
17.5°	465.7	464.0	462.3	460.6	458.9	455.9	451.5	447.1	442.7	438.3	436.0
20°	457.0	455.0	453.0	450.9	448.9	445.4	440.3	435.3	430.3	425.2	422.7
22.5°	447.6	445.3	443.0	440.8	438.5	434.5	428.8	423.1	417.5	411.8	408.5
25°	433.4	430.1	426.9	423.7	420.5	415.5	408.8	402.2	395.5	388.9	384.7
27.5°	416.3	412.8	409.3	405.8	402.2	396.7	389.2	381.7	374.2	366.7	361.9
30°	404.3	400.5	396.6	392.8	389.0	383.0	374.9	366.9	358.8	350.7	345.6
32.5°	392.7	388.2	383.7	379.2	374.7	368.4	360.2	351.9	343.7	335.4	329.6
35°	373.4	368.3	363.1	358.0	352.8	345.8	336.9	328.0	319.2	310.3	303.9
37.5°	354.2	348.5	342.8	337.2	331.5	324.0	314.5	305.0	295.6	286.1	279.1
40°	340.7	334.7	328.6	322.5	316.5	308.6	298.8	289.0	279.2	269.4	262.2
42.5°	326.9	320.5	314.1	307.8	301.4	293.1	283.0	272.9	262.8	252.7	245.3
45°	305.3	298.5	291.7	285.0	278.2	269.5	258.9	248.3	237.7	227.1	220.0
47.5°	284.2	277.0	269.9	262.7	255.5	246.5	235.5	224.6	213.6	202.7	195.6
50°	268.9	261.8	254.6	247.4	240.3	231.1	220.0	208.9	197.8	186.7	179.7
52.5°	254.0	246.5	239.1	231.6	224.1	214.9	204.0	193.2	182.3	171.4	164.7
55°	232.1	224.3	216.4	208.5	200.6	191.3	180.3	169.4	158.5	147.6	141.6
57.5°	209.7	201.6	193.5	185.5	177.4	168.1	157.6	147.2	136.7	126.2	120.6
60°	194.4	186.4	178.3	170.2	162.1	152.9	142.5	132.1	121.7	111.3	106.1
62.5°	179.5	171.5	163.4	155.3	147.2	138.2	128.3	118.4	108.5	98.6	93.7
65°	156.7	148.5	140.4	132.2	124.0	115.4	106.3	97.2	88.1	79.0	75.6
67.5°	134.7	126.6	118.5	110.4	102.3	94.1	85.9	77.8	69.6	61.4	59.8
70°	119.5	111.6	103.7	95.9	88.0	80.6	73.6	66.6	59.7	52.7	51.7
72.5°	104.9	97.4	89.8	82.3	74.7	68.2	62.6	57.0	51.4	45.8	44.9
75°	83.6	76.5	69.5	62.4	55.3	50.1	46.6	43.2	39.8	36.3	35.6
77.5°	62.6	56.4	50.2	44.0	37.8	33.9	32.2	30.6	28.9	27.3	26.9
80°	49.5	44.4	39.2	34.1	28.9	25.8	24.8	23.8	22.8	21.8	21.4
82.5°	37.5	33.5	29.5	25.5	21.5	19.1	18.4	17.7	17.0	16.4	16.1
85°	19.5	17.4	15.3	13.2	11.1	9.8	9.5	9.2	8.9	8.6	8.6
87.5°	6.0	5.8	5.8	5.4	5.1	5.3	6.0	7.1	8.1	8.2	8.0
90°	0.8	3.1	6.3	7.8	9.4	11.7	15.6	21.1	25.8	26.6	25.8
92.5°	9.5	13.8	19.4	22.8	28.1	35.5	53.2	78.0	100.2	101.6	85.8
95°	27.4	30.5	38.3	45.3	57.8	76.6	112.6	180.6	271.3	306.4	268.1
97.5°	44.6	48.8	57.1	67.7	82.1	103.3	148.5	243.3	394.0	523.1	548.8
100°	60.2	62.5	69.6	82.1	97.7	119.6	161.0	256.4	425.2	617.5	730.1
102.5°	74.6	76.3	83.3	95.8	112.1	134.0	172.3	257.0	413.4	620.7	797.6
105°	95.4	98.5	104.0	115.7	132.9	154.8	191.5	261.1	390.1	579.2	787.2
107.5°	117.9	120.4	125.7	136.5	153.5	175.6	211.2	271.9	378.5	534.8	718.5
110°	132.9	136.0	140.7	150.9	167.3	190.0	224.3	280.6	376.0	513.6	675.4



TEST NUMBER: P331632

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.6	149.8	155.1	164.6	180.4	203.7	236.9	290.0	376.6	499.8	645.4
115°	168.1	172.0	176.7	186.0	201.7	222.8	256.4	304.1	379.9	484.7	608.2
117.5°	190.3	193.4	198.1	206.4	221.4	243.3	274.4	319.1	385.5	477.3	584.7
120°	204.0	207.2	211.8	218.9	234.5	256.4	286.9	329.1	389.3	472.9	572.2
122.5°	217.2	219.7	224.3	232.0	247.6	270.2	298.8	337.9	393.7	470.4	561.6
125°	234.5	236.9	241.5	250.9	266.6	288.4	316.6	351.8	400.2	465.9	546.4
127.5°	248.3	251.4	258.0	268.3	283.3	305.8	333.2	364.7	407.0	463.2	532.3
130°	256.4	259.5	267.3	278.3	293.9	315.8	343.2	372.9	412.0	462.0	523.0
132.5°	263.9	267.7	276.1	287.7	303.9	325.8	351.9	381.0	417.0	461.4	515.5
135°	275.2	278.3	287.7	299.4	317.4	339.3	364.3	391.6	422.9	460.4	505.0
137.5°	285.8	289.5	298.9	311.4	329.3	349.6	374.3	399.8	428.2	460.3	497.6
140°	293.9	297.0	306.4	318.9	336.1	356.5	379.9	404.1	430.7	459.6	493.3
142.5°	302.0	304.6	313.3	325.8	342.4	361.5	384.3	407.9	432.6	459.6	488.9
145°	314.2	317.4	325.2	336.9	352.5	369.7	390.9	412.7	434.6	458.1	483.1
147.5°	327.4	329.7	337.2	348.0	361.0	376.3	396.2	415.4	435.3	455.3	477.2
150°	336.1	338.5	344.7	354.9	366.6	380.7	398.7	416.6	434.6	453.4	472.1
152.5°	344.9	346.0	352.2	361.1	372.2	385.1	401.2	417.3	433.4	450.3	467.8
155°	357.2	358.0	362.7	371.3	379.9	391.6	404.9	418.2	431.5	444.8	459.6
157.5°	367.6	368.3	372.1	379.6	386.5	396.3	407.6	418.2	427.9	439.2	452.0
160°	374.4	375.2	378.3	384.6	390.9	399.4	408.8	418.2	426.0	435.4	446.4
162.5°	381.3	380.8	384.0	389.0	394.6	401.3	409.5	417.6	424.2	432.3	441.3
165°	389.3	388.5	390.1	394.8	398.7	403.4	410.4	415.9	420.6	426.0	433.1
167.5°	395.9	394.9	396.3	399.3	402.1	405.1	410.2	414.8	417.0	420.6	424.9
170°	400.2	398.7	399.4	401.8	403.4	405.7	409.6	413.5	415.1	417.4	420.6
172.5°	402.7	401.8	401.3	403.7	404.6	406.3	409.0	411.6	412.6	413.7	416.2
175°	405.7	404.9	404.1	405.7	405.7	406.5	408.0	409.6	408.8	409.6	410.4
177.5°	407.1	405.9	405.2	406.5	406.5	406.5	407.1	408.4	407.1	406.5	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331632

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	502.0	502.0	502.0	502.0	502.0	502.0	502.0	502.0
2.5°	499.6	500.4	501.2	501.5	501.4	501.2	501.0	500.9
5°	495.6	496.5	497.4	497.7	497.4	497.1	496.8	496.5
7.5°	487.6	487.9	488.1	488.0	487.5	486.9	486.4	485.9
10°	479.6	479.3	479.0	478.5	477.9	477.3	476.7	476.1
12.5°	470.4	469.8	469.3	468.5	467.5	466.5	465.5	464.5
15°	453.2	451.2	449.3	447.9	446.9	445.8	444.8	443.8
17.5°	433.7	431.4	429.2	427.2	425.4	423.7	421.9	420.2
20°	420.2	417.6	415.1	412.7	410.5	408.3	406.1	403.9
22.5°	405.3	402.0	398.8	396.3	394.6	393.0	391.3	389.7
25°	380.6	376.4	372.3	369.5	368.0	366.4	364.9	363.4
27.5°	357.0	352.2	347.4	343.8	341.4	339.0	336.6	334.2
30°	340.4	335.3	330.1	326.2	323.4	320.7	318.0	315.3
32.5°	323.7	317.8	311.9	307.7	305.2	302.6	300.0	297.5
35°	297.6	291.2	284.8	280.5	278.3	276.1	273.9	271.7
37.5°	272.1	265.1	258.1	253.3	250.8	248.2	245.7	243.1
40°	255.1	247.9	240.7	235.8	233.2	230.6	227.9	225.3
42.5°	237.8	230.4	223.0	218.1	215.5	213.0	210.4	207.9
45°	212.8	205.6	198.5	193.7	191.3	188.8	186.4	184.0
47.5°	188.4	181.3	174.2	169.5	167.3	165.1	162.9	160.7
50°	172.8	165.8	158.8	154.3	152.2	150.1	147.9	145.8
52.5°	158.0	151.3	144.6	140.2	138.3	136.3	134.3	132.4
55°	135.5	129.5	123.4	119.4	117.5	115.6	113.7	111.8
57.5°	115.1	109.5	104.0	100.4	98.8	97.2	95.6	93.9
60°	101.0	95.9	90.7	87.3	85.7	84.1	82.5	80.9
62.5°	88.8	83.9	79.0	76.0	75.0	74.1	73.1	72.1
65°	72.2	68.7	65.3	63.4	63.1	62.8	62.5	62.2
67.5°	58.3	56.7	55.1	54.2	53.8	53.5	53.2	52.9
70°	50.7	49.7	48.7	48.0	47.5	47.1	46.7	46.3
72.5°	44.1	43.2	42.4	41.9	41.6	41.4	41.1	40.9
75°	34.9	34.2	33.5	33.1	33.0	32.9	32.8	32.7
77.5°	26.4	26.0	25.6	25.4	25.2	25.0	24.9	24.7
80°	21.0	20.6	20.2	20.0	20.0	20.0	20.0	20.0
82.5°	15.9	15.6	15.4	15.3	15.3	15.3	15.3	15.3
85°	8.6	8.6	8.6	8.6	8.6	8.6	8.6	8.6
87.5°	7.7	7.4	7.6	7.7	7.7	7.7	7.7	7.7
90°	25.0	23.5	25.0	25.8	25.8	25.8	25.8	25.8
92.5°	68.2	58.5	51.9	47.1	46.4	43.9	44.6	43.3
95°	204.8	157.1	124.3	107.1	96.9	90.7	88.3	89.1
97.5°	477.9	391.0	306.4	250.0	212.6	193.4	182.0	175.4
100°	713.7	616.8	509.7	415.1	350.2	316.6	293.9	279.8
102.5°	868.2	846.3	767.9	667.7	597.2	539.8	511.5	492.5
105°	949.8	1038.1	1048.3	1022.5	974.0	925.5	891.9	881.0
107.5°	891.0	1024.0	1105.3	1143.2	1149.3	1146.6	1139.9	1125.3
110°	840.3	980.3	1080.3	1144.4	1178.0	1192.9	1199.9	1199.1



TEST NUMBER: P331632

CATALOG NUMBER: SA2XXRDIP-C290D725U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	794.1	928.3	1035.3	1108.8	1155.5	1180.4	1193.7	1197.9
115°	737.1	857.5	959.9	1040.4	1095.9	1131.9	1152.2	1159.3
117.5°	694.3	800.0	892.9	968.4	1025.0	1063.0	1084.4	1090.3
120°	673.0	770.0	852.8	924.0	978.7	1015.4	1038.1	1045.9
122.5°	656.2	745.0	823.4	887.7	936.8	972.9	993.1	999.6
125°	631.6	712.1	780.9	839.5	884.9	914.6	934.1	940.4
127.5°	607.4	680.2	745.1	799.2	838.8	866.6	883.5	888.5
130°	591.7	659.0	720.7	772.3	810.6	837.2	852.8	859.1
132.5°	576.7	639.0	695.7	744.2	781.9	808.4	822.8	828.4
135°	555.8	607.4	659.0	702.7	736.4	762.2	776.2	779.4
137.5°	539.1	582.2	623.2	661.3	692.0	714.2	726.5	731.2
140°	528.4	566.0	601.9	636.3	661.3	681.6	693.4	698.1
142.5°	519.7	551.6	582.5	611.3	635.1	653.5	664.0	664.9
145°	507.3	533.1	557.4	580.0	598.8	612.1	619.9	622.2
147.5°	497.8	518.1	537.0	553.6	569.1	579.7	585.0	586.4
150°	490.9	508.1	524.5	538.6	550.3	559.7	564.4	565.2
152.5°	484.0	500.0	513.9	526.1	535.3	543.4	546.9	547.0
155°	474.5	487.0	498.7	507.3	515.9	521.4	524.5	523.0
157.5°	463.4	473.9	483.7	490.4	496.5	501.1	502.5	502.5
160°	456.5	465.1	473.7	479.2	484.7	488.6	489.3	489.3
162.5°	449.6	457.0	464.3	468.6	474.0	476.7	477.5	476.8
165°	439.3	444.8	450.3	453.4	456.5	459.6	459.6	458.9
167.5°	429.5	433.7	437.4	440.3	441.7	443.4	443.2	442.3
170°	424.5	426.8	429.9	431.5	432.3	434.6	433.8	432.3
172.5°	418.8	420.6	423.1	424.0	424.8	425.9	425.1	424.2
175°	412.7	413.5	414.3	415.1	415.1	415.9	415.1	413.5
177.5°	408.4	408.4	409.0	409.0	409.0	409.0	408.4	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5

(END OF REPORT)