

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331323-830

Luminaire Tested: **SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331323-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5987.8 lumens
Efficiency: N/A
Efficacy: 121.2 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 49.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331323-830
CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

Luminous Intensity Polar Plot





TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	93	93	93	93	74	74	74	57	57	57	41	41	41	34				
1	94	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	35	29				
2	86	79	73	69	78	72	67	63	58	54	51	45	43	41	33	32	30	25				
3	79	70	63	57	71	63	57	53	51	47	44	40	37	35	29	28	26	21				
4	72	62	54	49	65	56	50	45	46	41	37	36	33	30	26	24	23	19				
5	66	55	48	42	60	50	44	39	41	36	32	32	29	26	24	22	20	16				
6	61	50	42	36	55	45	39	34	37	32	28	29	26	23	22	20	18	15				
7	57	45	37	32	51	41	34	30	33	29	25	27	23	20	20	18	16	13				
8	52	41	33	28	47	37	31	26	31	26	22	24	21	18	18	16	14	12				
9	49	37	30	25	44	34	28	23	28	23	20	22	19	16	17	15	13	11				
10	46	34	27	22	41	31	25	21	26	21	18	21	17	15	16	14	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14788	14788	14788	14788
5°	16579	14885	13190	14885
10°	18998	14762	11416	14762
15°	21018	14492	10084	14492
20°	20697	14201	9194	14201
25°	18661	13814	8630	13814
30°	15422	13196	8216	13196
35°	11239	12552	7924	12552
40°	8977	11788	7761	11788
45°	7846	10908	7540	10908
50°	7375	10052	7392	10052
55°	6798	9185	7192	9185
60°	6229	8263	6888	8263
65°	5673	7435	6590	7435
70°	5150	6628	6151	6628
75°	4566	5733	5446	5733
80°	3924	4751	4379	4751
85°	3520	3520	2594	3520



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.2	1.5
10°-20°	253.6	4.2
20°-30°	368.0	6.1
30°-40°	388.4	6.5
40°-50°	343.9	5.7
50°-60°	274.4	4.6
60°-70°	186.5	3.1
70°-80°	95.6	1.6
80°-90°	28.2	0.5
90°-100°	227.7	3.8
100°-110°	772.5	12.9
110°-120°	820.7	13.7
120°-130°	675.6	11.3
130°-140°	542.5	9.1
140°-150°	410.0	6.8
150°-160°	288.1	4.8
160°-170°	169.6	2.8
170°-180°	55.2	0.9
0°-30°	708.8	11.8
0°-40°	1097.2	18.3
0°-60°	1715.5	28.6
0°-90°	2025.8	33.8
90°-120°	1820.9	30.4
90°-150°	3449.0	57.6
90°-180°	3962.0	66.2
0°-180°	5987.8	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	916	916	916	916	916	
5°	1023	918	814	918	1023	102
15°	1257	867	603	867	1257	347
25°	1048	775	484	775	1048	473
35°	570	637	402	637	570	371
45°	344	478	330	478	344	270
55°	242	326	256	326	242	217
65°	148	195	172	195	148	148
75°	73	92	87	92	73	78
85°	19	19	14	19	19	22
90°	36	1	36	1	36	20
95°	125	38	125	38	125	162
105°	1234	134	1234	134	1234	1194
115°	1624	235	1624	235	1624	1590
125°	1317	328	1317	328	1317	1190
135°	1092	385	1092	385	1092	848
145°	872	440	872	440	872	554
155°	732	500	732	500	732	342
165°	643	545	643	545	643	184
175°	579	568	579	568	579	56
180°	569	569	569	569	569	



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	958.2	958.5	958.9	954.5	953.9	953.9	950.0	946.6	942.6	937.3	937.8
5°	1022.9	1026.8	1028.2	1024.0	1017.7	1016.9	1011.0	1001.1	991.9	984.6	979.3
7.5°	1100.2	1101.7	1098.3	1092.8	1088.1	1079.6	1068.5	1057.5	1042.3	1028.2	1017.9
10°	1158.8	1160.9	1154.9	1146.8	1140.1	1130.3	1114.1	1097.5	1077.5	1058.1	1042.6
12.5°	1203.2	1208.5	1200.8	1199.8	1188.3	1174.8	1155.5	1147.1	1118.9	1091.9	1075.3
15°	1257.4	1257.0	1257.7	1251.0	1242.6	1240.5	1220.0	1197.9	1158.1	1142.3	1114.7
17.5°	1241.7	1247.1	1249.5	1249.4	1249.2	1247.9	1241.3	1227.4	1207.4	1181.8	1150.1
20°	1204.6	1211.5	1212.7	1220.8	1225.3	1231.3	1233.8	1229.9	1217.6	1196.1	1168.7
22.5°	1147.1	1149.1	1152.4	1165.0	1174.9	1189.9	1197.7	1210.7	1206.0	1195.5	1172.6
25°	1047.5	1044.1	1056.3	1062.7	1085.5	1109.5	1126.7	1145.8	1162.6	1172.9	1166.2
27.5°	928.0	922.7	941.2	958.0	976.6	1002.5	1029.4	1061.1	1087.5	1120.6	1131.9
30°	827.2	830.4	848.0	865.9	894.1	930.7	960.9	995.8	1033.5	1070.4	1096.1
32.5°	718.5	730.7	741.8	769.3	794.1	834.9	879.3	922.8	969.9	1011.8	1051.6
35°	570.2	584.3	599.8	619.9	654.7	695.2	738.5	797.3	861.4	918.7	965.9
37.5°	479.9	477.8	486.6	501.1	529.3	562.0	611.8	670.0	745.4	812.8	879.3
40°	425.9	424.5	430.8	444.2	465.7	489.7	533.3	584.3	654.4	736.7	816.0
42.5°	388.7	389.6	393.1	402.6	417.3	437.0	469.7	513.1	577.2	654.8	739.9
45°	343.6	346.0	349.9	354.5	362.9	379.1	397.4	428.4	479.1	543.8	627.6
47.5°	311.0	311.1	315.0	319.1	324.0	333.2	348.2	367.6	403.3	456.1	528.1
50°	293.6	291.1	293.9	297.1	302.4	308.7	318.6	336.9	360.8	403.4	463.5
52.5°	272.2	272.2	274.8	276.0	280.7	287.0	296.1	308.7	330.4	363.7	413.2
55°	241.5	243.3	244.7	246.8	251.0	255.5	262.6	271.1	287.9	312.9	349.5
57.5°	212.6	213.2	214.6	218.6	221.3	225.5	232.1	239.9	250.8	269.4	296.9
60°	192.9	192.9	195.7	197.5	201.0	205.2	210.5	217.9	227.7	242.9	265.0
62.5°	174.8	174.6	175.7	178.6	181.3	185.2	190.5	196.8	206.0	219.5	237.7
65°	148.5	147.9	150.0	150.6	153.4	157.3	161.6	168.2	175.7	185.5	201.7
67.5°	123.2	124.0	125.2	126.5	128.1	132.1	135.0	139.7	145.9	154.1	165.1
70°	109.1	109.1	109.1	110.2	112.3	114.4	117.3	121.1	127.1	134.1	143.9
72.5°	93.3	94.4	95.6	95.0	97.6	98.9	102.3	104.4	110.2	114.7	123.4
75°	73.2	73.2	73.2	74.9	76.1	77.1	79.2	81.3	84.2	89.7	94.3
77.5°	54.7	54.5	54.9	55.2	56.4	57.7	58.2	60.2	62.8	65.4	69.3
80°	42.2	43.0	43.3	44.0	44.0	44.7	45.1	47.5	49.3	51.1	53.5
82.5°	32.7	32.8	32.9	33.0	33.3	33.7	34.6	35.4	36.0	37.5	39.4
85°	19.0	18.7	18.7	19.3	19.0	19.0	19.7	20.5	20.5	20.7	21.9
87.5°	14.5	14.5	14.8	14.5	14.5	14.6	14.1	14.3	14.8	15.4	15.4
90°	36.1	36.1	36.1	36.1	36.1	35.1	32.9	35.1	36.1	37.2	36.1
92.5°	60.7	62.4	61.5	65.0	65.9	72.7	81.9	95.5	120.3	142.3	140.3
95°	124.8	123.8	127.1	135.7	150.0	174.1	220.1	286.9	375.6	429.2	379.9
97.5°	245.7	254.9	270.9	297.8	350.2	429.2	547.7	669.4	768.6	732.7	551.9
100°	392.0	411.7	443.5	490.5	581.4	713.9	863.9	999.7	1022.7	865.0	595.6
102.5°	689.8	716.5	756.2	836.5	935.3	1075.6	1185.3	1216.1	1117.3	869.4	579.0
105°	1234.0	1249.3	1296.4	1364.2	1432.2	1468.3	1454.1	1330.3	1102.6	811.3	546.4
107.5°	1576.2	1596.6	1606.0	1609.8	1601.2	1548.2	1434.4	1248.0	1006.4	749.1	530.2
110°	1679.6	1680.7	1670.8	1650.0	1603.0	1513.2	1373.0	1177.0	946.0	719.3	526.7



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1677.8	1672.0	1653.3	1618.5	1553.0	1450.1	1300.3	1112.2	904.0	700.1	527.5
115°	1623.8	1613.9	1585.5	1535.1	1457.4	1344.5	1201.2	1032.6	851.9	678.8	532.2
117.5°	1527.2	1518.9	1488.8	1435.7	1356.4	1250.7	1120.6	972.5	819.0	668.5	540.0
120°	1465.0	1454.1	1422.3	1370.8	1294.2	1194.6	1078.5	942.7	801.4	662.4	545.3
122.5°	1400.1	1391.0	1362.7	1312.1	1243.4	1153.4	1043.5	919.1	786.6	658.9	551.4
125°	1317.2	1308.4	1281.1	1239.4	1175.9	1093.8	997.5	884.7	765.3	652.6	560.6
127.5°	1244.5	1237.5	1213.8	1174.9	1119.5	1043.7	952.8	850.7	745.6	648.8	570.0
130°	1203.3	1194.6	1172.7	1135.5	1081.8	1009.6	923.0	828.9	732.5	647.1	577.0
132.5°	1160.4	1152.5	1132.4	1095.1	1042.4	974.5	895.0	807.9	722.0	646.2	584.0
135°	1091.7	1087.2	1067.5	1031.4	984.3	923.0	850.7	778.4	707.3	644.9	592.4
137.5°	1024.2	1017.7	1000.3	969.2	926.3	872.9	815.5	755.1	697.0	644.7	599.8
140°	977.8	971.2	954.8	926.3	891.3	843.1	792.8	740.2	690.9	643.9	603.3
142.5°	931.3	930.0	915.4	889.5	856.2	816.0	772.6	727.9	684.8	643.9	606.0
145°	871.6	868.3	857.3	838.7	812.5	780.7	746.8	710.6	676.7	641.6	608.8
147.5°	821.4	819.4	812.0	797.1	775.4	752.2	725.8	697.3	668.4	637.7	609.6
150°	791.6	790.5	784.0	770.8	754.4	734.7	711.7	687.6	661.3	635.1	608.8
152.5°	766.2	766.0	761.2	749.8	736.9	719.8	700.3	678.0	655.2	630.7	607.0
155°	732.5	734.7	730.3	722.6	710.6	698.5	682.1	664.6	643.9	623.0	604.4
157.5°	703.8	703.8	701.8	695.5	686.9	677.5	663.7	649.0	633.1	615.1	599.4
160°	685.4	685.4	684.3	678.8	671.2	663.5	651.5	639.4	625.2	609.9	596.7
162.5°	667.9	668.7	667.7	663.9	656.3	650.4	640.1	629.8	618.2	605.5	594.1
165°	642.7	643.9	643.9	639.4	635.1	630.7	623.0	615.4	606.6	596.7	589.1
167.5°	619.5	620.9	621.0	618.6	616.7	612.7	607.5	601.5	595.2	589.1	584.0
170°	605.5	607.7	608.8	605.5	604.4	602.2	597.9	594.6	589.1	584.7	581.4
172.5°	594.1	595.4	596.5	595.0	593.9	592.6	589.1	586.6	583.0	579.5	577.9
175°	579.2	581.4	582.5	581.4	581.4	580.3	579.2	578.2	574.9	573.7	572.7
177.5°	570.2	572.0	572.9	572.9	572.9	572.9	572.0	572.0	570.2	569.4	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	939.8	937.5	936.1	931.1	926.6	922.1	920.7	921.2	915.0	909.2	906.6
5°	976.5	969.4	962.7	953.2	942.0	929.6	923.3	918.4	906.1	892.7	885.0
7.5°	1009.3	999.2	986.3	968.5	952.1	932.6	920.3	909.5	891.4	872.5	861.0
10°	1029.3	1015.5	999.0	977.1	957.1	933.5	917.0	900.4	879.3	856.8	842.7
12.5°	1046.4	1027.9	1011.6	983.6	959.9	930.4	910.8	887.5	865.3	838.5	824.6
15°	1087.3	1053.2	1022.2	990.5	961.3	920.1	898.3	867.0	837.7	804.6	788.8
17.5°	1118.9	1080.5	1031.8	991.6	957.4	911.8	879.8	842.3	807.7	769.9	748.4
20°	1137.0	1093.0	1040.5	992.7	951.8	899.8	864.9	826.5	786.0	743.4	720.2
22.5°	1147.6	1101.5	1049.5	988.4	940.6	889.9	846.0	804.0	762.9	717.0	692.6
25°	1151.0	1108.8	1053.9	984.9	926.4	869.1	816.2	775.4	725.9	682.9	647.3
27.5°	1134.3	1104.0	1051.2	978.3	910.2	843.1	784.3	738.0	685.6	639.0	603.2
30°	1113.7	1096.1	1044.7	971.5	897.2	825.1	760.3	707.8	655.8	608.6	572.0
32.5°	1081.9	1078.1	1032.9	962.0	883.4	802.3	735.3	682.2	624.5	578.2	543.3
35°	1019.4	1036.3	1007.8	940.6	857.4	769.9	697.3	636.8	576.9	532.5	499.8
37.5°	935.7	977.6	970.2	909.2	822.4	734.5	654.4	591.2	534.1	489.4	457.2
40°	877.9	931.4	939.1	885.2	797.7	707.2	622.4	559.3	503.7	462.9	430.5
42.5°	816.0	878.4	899.8	856.6	770.6	678.4	593.6	528.4	473.3	433.6	404.9
45°	712.1	794.8	833.2	808.5	725.5	631.1	543.8	477.7	427.7	390.4	368.2
47.5°	615.0	705.4	757.1	748.3	675.2	581.8	495.6	432.1	383.4	353.6	333.8
50°	546.3	639.2	701.5	704.4	639.2	546.7	460.1	400.2	355.5	327.7	311.5
52.5°	486.6	575.3	643.3	658.2	599.0	510.0	428.2	368.7	329.3	303.8	289.3
55°	408.7	483.6	559.0	586.4	538.9	454.4	378.7	326.3	289.4	271.7	259.1
57.5°	339.8	402.3	471.8	502.2	472.9	400.6	329.6	284.1	254.1	238.7	228.9
60°	303.4	352.7	414.6	450.9	425.6	361.2	299.2	255.9	231.3	217.5	208.4
62.5°	269.7	313.3	365.6	398.8	385.0	324.2	268.8	230.5	209.3	196.4	189.8
65°	222.4	256.9	297.5	328.1	319.0	272.8	227.4	194.6	177.8	167.6	162.3
67.5°	183.1	208.1	236.2	263.0	255.6	222.9	186.5	161.0	148.4	139.6	136.5
70°	158.4	177.4	202.4	223.9	217.9	191.1	162.3	140.4	129.5	122.2	118.9
72.5°	134.8	150.3	169.5	187.0	182.9	160.7	136.7	120.2	111.8	105.0	102.4
75°	101.7	113.7	125.4	137.0	135.9	118.7	104.5	91.9	85.2	79.9	78.9
77.5°	75.1	81.8	89.7	96.6	94.7	84.8	73.8	66.5	61.6	58.1	57.5
80°	57.4	61.3	66.9	71.8	69.4	65.1	56.4	51.1	47.5	44.0	42.6
82.5°	41.6	45.5	48.8	51.6	49.7	45.7	40.2	36.7	34.6	32.1	31.6
85°	21.9	23.9	25.4	26.0	25.4	22.9	20.5	19.0	17.2	16.2	15.8
87.5°	14.3	12.8	11.7	11.6	10.4	9.9	7.9	6.4	6.8	7.4	7.3
90°	29.6	21.9	16.4	13.1	10.9	8.8	4.3	1.1	4.3	8.8	10.9
92.5°	109.2	74.5	49.7	39.4	32.0	27.1	19.2	13.4	19.2	27.1	32.0
95°	252.9	157.7	107.3	81.1	63.5	53.6	42.7	38.4	42.7	53.6	63.5
97.5°	340.7	208.0	144.8	115.0	94.8	79.9	68.3	62.4	68.3	79.9	94.8
100°	359.1	225.6	167.5	136.9	115.0	97.5	87.6	84.3	87.6	97.5	115.0
102.5°	360.1	241.3	187.7	157.0	134.2	116.7	106.9	104.4	106.9	116.7	134.2
105°	365.7	268.2	216.8	186.2	162.0	145.6	138.0	133.6	138.0	145.6	162.0
107.5°	380.8	295.9	245.9	215.1	191.1	176.1	168.6	165.1	168.6	176.1	191.1
110°	393.0	314.2	266.1	234.3	211.3	197.1	190.5	186.2	190.5	197.1	211.3



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	406.2	331.8	285.3	252.7	230.5	217.3	209.8	205.4	209.8	217.3	230.5
115°	425.9	359.1	312.1	282.5	260.6	247.4	240.9	235.4	240.9	247.4	260.6
117.5°	447.0	384.3	340.7	310.1	289.1	277.5	270.9	266.6	270.9	277.5	289.1
120°	461.0	401.8	359.1	328.5	306.6	296.7	290.1	285.8	290.1	296.7	306.6
122.5°	473.3	418.5	378.4	346.9	325.0	314.2	307.6	304.2	307.6	314.2	325.0
125°	492.8	443.5	404.1	373.3	351.5	338.4	331.8	328.5	331.8	338.4	351.5
127.5°	510.9	466.7	428.3	396.8	375.8	361.4	352.1	347.7	352.1	361.4	375.8
130°	522.3	480.7	442.3	411.7	389.8	374.5	363.5	359.1	363.5	374.5	389.8
132.5°	533.7	492.9	456.4	425.7	402.9	386.7	374.9	369.7	374.9	386.7	402.9
135°	548.6	510.2	475.2	444.5	419.3	402.9	389.8	385.4	389.8	402.9	419.3
137.5°	560.0	524.2	489.7	461.2	436.2	418.7	405.6	400.3	405.6	418.7	436.2
140°	566.1	532.2	499.3	470.8	446.8	429.2	416.0	411.7	416.0	429.2	446.8
142.5°	571.4	538.3	506.3	479.6	456.4	438.8	426.6	423.1	426.6	438.8	456.4
145°	578.2	547.4	517.9	493.8	471.9	455.5	444.5	440.2	444.5	455.5	471.9
147.5°	581.8	554.9	527.1	505.7	487.5	472.3	461.8	458.5	461.8	472.3	487.5
150°	583.6	558.5	533.2	513.5	497.1	482.9	474.1	470.8	474.1	482.9	497.1
152.5°	584.5	561.9	539.3	521.4	505.9	493.3	484.7	483.1	484.7	493.3	505.9
155°	585.8	567.1	548.6	532.2	520.1	508.0	501.4	500.4	501.4	508.0	520.1
157.5°	585.8	570.9	555.2	541.3	531.7	521.2	515.9	514.8	515.9	521.2	531.7
160°	585.8	572.7	559.5	547.4	538.7	529.9	525.6	524.4	525.6	529.9	538.7
162.5°	584.9	573.5	562.1	552.7	544.8	537.8	533.5	534.1	533.5	537.8	544.8
165°	582.5	574.9	565.0	558.5	552.9	546.4	544.2	545.3	544.2	546.4	552.9
167.5°	581.0	574.6	567.4	563.3	559.3	555.2	553.2	554.5	553.2	555.2	559.3
170°	579.2	573.7	568.3	565.0	562.8	559.5	558.5	560.6	558.5	559.5	562.8
172.5°	576.6	572.9	569.1	566.8	565.4	562.1	562.8	564.1	562.8	562.1	565.4
175°	573.7	571.6	569.4	568.3	568.3	566.1	567.1	568.3	567.1	566.1	568.3
177.5°	572.0	570.2	569.4	569.4	569.4	567.6	568.4	570.2	568.4	567.6	569.4
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	903.8	902.1	896.2	893.1	888.1	883.3	880.1	881.6	882.7	882.1	881.3
5°	877.9	871.2	861.0	852.2	845.8	834.2	829.3	826.9	824.7	822.3	819.8
7.5°	847.1	836.5	821.9	809.4	797.5	783.1	774.9	769.9	764.8	759.2	754.3
10°	825.1	810.3	794.8	777.2	763.2	750.1	738.5	730.8	723.7	717.0	712.1
12.5°	802.0	784.9	765.8	741.8	726.2	707.6	705.9	692.2	681.2	677.0	671.3
15°	765.3	741.3	717.0	688.5	676.2	659.3	648.8	638.2	628.7	622.0	620.2
17.5°	723.5	692.5	668.4	647.9	627.7	610.4	600.7	592.2	584.4	575.4	574.3
20°	691.6	665.0	638.6	620.6	599.8	582.2	570.2	561.8	555.1	549.8	545.3
22.5°	661.6	632.3	608.1	588.4	568.0	553.7	544.3	536.2	530.7	524.8	520.5
25°	613.2	590.3	563.9	541.8	524.8	515.7	507.9	500.9	497.4	493.5	488.6
27.5°	570.9	545.4	520.8	503.6	488.7	480.6	475.1	470.3	467.0	464.8	461.9
30°	541.0	515.3	496.0	479.1	466.7	458.6	455.2	452.3	448.5	447.0	445.6
32.5°	512.3	489.2	472.6	458.0	446.2	440.9	437.7	435.2	432.2	430.7	427.9
35°	471.6	452.3	436.1	428.0	418.5	414.0	411.5	407.9	405.2	403.8	403.4
37.5°	433.5	416.6	406.0	395.6	391.5	388.7	385.4	383.0	382.1	381.9	381.5
40°	408.7	394.9	385.4	377.0	375.2	371.0	368.2	366.1	366.1	366.5	366.1
42.5°	386.2	373.8	365.4	358.2	356.1	353.5	350.7	350.6	351.2	352.3	351.2
45°	352.0	343.2	337.2	333.7	329.8	327.3	327.0	328.1	328.4	328.8	329.8
47.5°	320.6	314.7	309.3	305.5	303.8	303.3	302.9	304.7	306.4	307.1	308.7
50°	302.0	295.3	290.8	288.3	286.9	286.2	286.9	289.0	290.4	292.2	293.2
52.5°	281.2	276.4	273.3	271.4	270.8	271.3	271.4	273.8	276.1	276.6	277.2
55°	252.4	248.8	248.2	245.0	246.4	246.0	247.8	249.2	251.3	253.4	253.8
57.5°	223.7	220.8	219.0	219.2	219.6	221.2	222.6	225.2	227.4	229.6	229.9
60°	204.5	203.1	202.1	202.1	202.7	204.9	206.6	209.1	210.5	211.9	212.9
62.5°	187.1	185.7	184.5	185.1	187.0	188.2	190.3	191.6	193.0	194.4	194.9
65°	159.5	158.7	159.9	160.5	160.9	162.6	165.1	166.2	167.6	168.2	170.7
67.5°	134.0	134.2	134.0	135.1	137.0	137.5	139.8	142.3	142.6	143.9	145.5
70°	116.9	117.5	118.3	118.9	120.7	121.4	123.2	124.2	125.6	126.7	127.8
72.5°	101.1	101.2	102.0	101.8	103.3	104.8	106.3	107.4	108.8	110.1	111.1
75°	77.8	77.8	78.5	78.9	80.6	82.4	82.0	82.8	84.2	85.6	86.2
77.5°	56.8	56.1	56.8	57.1	57.7	59.2	59.5	60.5	62.1	61.6	62.4
80°	43.3	42.2	43.3	43.6	43.6	45.4	45.4	46.1	47.1	46.1	47.1
82.5°	30.9	30.4	31.2	31.3	31.9	31.9	32.4	32.6	33.6	33.2	33.6
85°	15.5	15.2	15.5	15.2	15.5	15.8	15.8	15.5	15.5	16.2	15.2
87.5°	7.4	7.8	8.6	10.2	11.1	11.1	10.7	10.4	10.0	9.8	10.1
90°	13.1	16.4	21.9	29.6	36.1	37.2	36.1	35.1	32.9	35.1	36.1
92.5°	39.4	49.7	74.5	109.2	140.3	142.3	120.3	95.5	81.9	72.7	65.9
95°	81.1	107.3	157.7	252.9	379.9	429.2	375.6	286.9	220.1	174.1	150.0
97.5°	115.0	144.8	208.0	340.7	551.9	732.7	768.6	669.4	547.7	429.2	350.2
100°	136.9	167.5	225.6	359.1	595.6	865.0	1022.7	999.7	863.9	713.9	581.4
102.5°	157.0	187.7	241.3	360.1	579.0	869.4	1117.3	1216.1	1185.3	1075.6	935.3
105°	186.2	216.8	268.2	365.7	546.4	811.3	1102.6	1330.3	1454.1	1468.3	1432.2
107.5°	215.1	245.9	295.9	380.8	530.2	749.1	1006.4	1248.0	1434.4	1548.2	1601.2
110°	234.3	266.1	314.2	393.0	526.7	719.3	946.0	1177.0	1373.0	1513.2	1603.0



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	252.7	285.3	331.8	406.2	527.5	700.1	904.0	1112.2	1300.3	1450.1	1553.0
115°	282.5	312.1	359.1	425.9	532.2	678.8	851.9	1032.6	1201.2	1344.5	1457.4
117.5°	310.1	340.7	384.3	447.0	540.0	668.5	819.0	972.5	1120.6	1250.7	1356.4
120°	328.5	359.1	401.8	461.0	545.3	662.4	801.4	942.7	1078.5	1194.6	1294.2
122.5°	346.9	378.4	418.5	473.3	551.4	658.9	786.6	919.1	1043.5	1153.4	1243.4
125°	373.3	404.1	443.5	492.8	560.6	652.6	765.3	884.7	997.5	1093.8	1175.9
127.5°	396.8	428.3	466.7	510.9	570.0	648.8	745.6	850.7	952.8	1043.7	1119.5
130°	411.7	442.3	480.7	522.3	577.0	647.1	732.5	828.9	923.0	1009.6	1081.8
132.5°	425.7	456.4	492.9	533.7	584.0	646.2	722.0	807.9	895.0	974.5	1042.4
135°	444.5	475.2	510.2	548.6	592.4	644.9	707.3	778.4	850.7	923.0	984.3
137.5°	461.2	489.7	524.2	560.0	599.8	644.7	697.0	755.1	815.5	872.9	926.3
140°	470.8	499.3	532.2	566.1	603.3	643.9	690.9	740.2	792.8	843.1	891.3
142.5°	479.6	506.3	538.3	571.4	606.0	643.9	684.8	727.9	772.6	816.0	856.2
145°	493.8	517.9	547.4	578.2	608.8	641.6	676.7	710.6	746.8	780.7	812.5
147.5°	505.7	527.1	554.9	581.8	609.6	637.7	668.4	697.3	725.8	752.2	775.4
150°	513.5	533.2	558.5	583.6	608.8	635.1	661.3	687.6	711.7	734.7	754.4
152.5°	521.4	539.3	561.9	584.5	607.0	630.7	655.2	678.0	700.3	719.8	736.9
155°	532.2	548.6	567.1	585.8	604.4	623.0	643.9	664.6	682.1	698.5	710.6
157.5°	541.3	555.2	570.9	585.8	599.4	615.1	633.1	649.0	663.7	677.5	686.9
160°	547.4	559.5	572.7	585.8	596.7	609.9	625.2	639.4	651.5	663.5	671.2
162.5°	552.7	562.1	573.5	584.9	594.1	605.5	618.2	629.8	640.1	650.4	656.3
165°	558.5	565.0	574.9	582.5	589.1	596.7	606.6	615.4	623.0	630.7	635.1
167.5°	563.3	567.4	574.6	581.0	584.0	589.1	595.2	601.5	607.5	612.7	616.7
170°	565.0	568.3	573.7	579.2	581.4	584.7	589.1	594.6	597.9	602.2	604.4
172.5°	566.8	569.1	572.9	576.6	577.9	579.5	583.0	586.6	589.1	592.6	593.9
175°	568.3	569.4	571.6	573.7	572.7	573.7	574.9	578.2	579.2	580.3	581.4
177.5°	569.4	569.4	570.2	572.0	570.2	569.4	570.2	572.0	572.0	572.9	572.9
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331323-830
 CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	878.4	877.9	877.9	875.3	877.9	877.9	878.4	881.3	882.1	882.7	881.6
5°	814.9	813.8	812.1	813.8	812.1	813.8	814.9	819.8	822.3	824.7	826.9
7.5°	752.1	747.8	747.2	743.0	747.2	747.8	752.1	754.3	759.2	764.8	769.9
10°	706.2	703.3	702.9	696.3	702.9	703.3	706.2	712.1	717.0	723.7	730.8
12.5°	671.2	664.4	665.8	661.9	665.8	664.4	671.2	671.3	677.0	681.2	692.2
15°	610.7	610.7	609.4	603.3	609.4	610.7	610.7	620.2	622.0	628.7	638.2
17.5°	567.3	566.6	563.2	564.9	563.2	566.6	567.3	574.3	575.4	584.4	592.2
20°	541.4	539.2	535.1	535.1	535.1	539.2	541.4	545.3	549.8	555.1	561.8
22.5°	516.9	516.7	512.3	513.7	512.3	516.7	516.9	520.5	524.8	530.7	536.2
25°	488.2	485.4	483.3	484.4	483.3	485.4	488.2	488.6	493.5	497.4	500.9
27.5°	461.1	459.5	459.4	456.5	459.4	459.5	461.1	461.9	464.8	467.0	470.3
30°	445.3	441.8	442.4	440.7	442.4	441.8	445.3	445.6	447.0	448.5	452.3
32.5°	427.3	426.0	425.3	423.8	425.3	426.0	427.3	427.9	430.7	432.2	435.2
35°	402.7	403.0	401.2	402.0	401.2	403.0	402.7	403.4	403.8	405.2	407.9
37.5°	381.3	382.4	381.5	381.7	381.5	382.4	381.3	381.5	381.9	382.1	383.0
40°	367.1	367.1	367.1	368.2	367.1	367.1	367.1	366.1	366.5	366.1	366.1
42.5°	353.6	353.1	352.5	352.4	352.5	353.1	353.6	351.2	352.3	351.2	350.6
45°	330.5	331.6	332.0	330.2	332.0	331.6	330.5	329.8	328.8	328.4	328.1
47.5°	309.6	309.7	309.6	311.1	309.6	309.7	309.6	308.7	307.1	306.4	304.7
50°	295.0	294.3	295.0	294.3	295.0	294.3	295.0	293.2	292.2	290.4	289.0
52.5°	279.5	279.7	279.2	279.1	279.2	279.7	279.5	277.2	276.6	276.1	273.8
55°	255.2	255.9	255.5	255.5	255.5	255.9	255.2	253.8	253.4	251.3	249.2
57.5°	230.1	230.7	231.2	229.6	231.2	230.7	230.1	229.9	229.6	227.4	225.2
60°	212.6	214.3	214.1	213.3	214.1	214.3	212.6	212.9	211.9	210.5	209.1
62.5°	196.5	197.2	197.1	197.0	197.1	197.2	196.5	194.9	194.4	193.0	191.6
65°	171.7	172.5	171.4	172.5	171.4	172.5	171.7	170.7	168.2	167.6	166.2
67.5°	145.1	145.3	146.1	146.6	146.1	145.3	145.1	145.5	143.9	142.6	142.3
70°	128.5	128.1	129.2	130.3	129.2	128.1	128.5	127.8	126.7	125.6	124.2
72.5°	111.0	111.8	111.4	112.3	111.4	111.8	111.0	111.1	110.1	108.8	107.4
75°	85.6	86.6	86.2	87.3	86.2	86.6	85.6	86.2	85.6	84.2	82.8
77.5°	61.8	61.9	61.8	62.4	61.8	61.9	61.8	62.4	61.6	62.1	60.5
80°	47.1	46.5	45.7	47.1	45.7	46.5	47.1	47.1	46.1	47.1	46.1
82.5°	32.8	33.3	32.5	32.5	32.5	33.3	32.8	33.6	33.2	33.6	32.6
85°	15.2	14.8	14.0	14.0	14.0	14.8	15.2	15.2	16.2	15.5	15.5
87.5°	10.1	9.8	9.8	9.5	9.8	9.8	10.1	10.1	9.8	10.0	10.4
90°	36.1	36.1	36.1	36.1	36.1	36.1	36.1	36.1	35.1	32.9	35.1
92.5°	65.0	61.5	62.4	60.7	62.4	61.5	65.0	65.9	72.7	81.9	95.5
95°	135.7	127.1	123.8	124.8	123.8	127.1	135.7	150.0	174.1	220.1	286.9
97.5°	297.8	270.9	254.9	245.7	254.9	270.9	297.8	350.2	429.2	547.7	669.4
100°	490.5	443.5	411.7	392.0	411.7	443.5	490.5	581.4	713.9	863.9	999.7
102.5°	836.5	756.2	716.5	689.8	716.5	756.2	836.5	935.3	1075.6	1185.3	1216.1
105°	1364.2	1296.4	1249.3	1234.0	1249.3	1296.4	1364.2	1432.2	1468.3	1454.1	1330.3
107.5°	1609.8	1606.0	1596.6	1576.2	1596.6	1606.0	1609.8	1601.2	1548.2	1434.4	1248.0
110°	1650.0	1670.8	1680.7	1679.6	1680.7	1670.8	1650.0	1603.0	1513.2	1373.0	1177.0



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1618.5	1653.3	1672.0	1677.8	1672.0	1653.3	1618.5	1553.0	1450.1	1300.3	1112.2
115°	1535.1	1585.5	1613.9	1623.8	1613.9	1585.5	1535.1	1457.4	1344.5	1201.2	1032.6
117.5°	1435.7	1488.8	1518.9	1527.2	1518.9	1488.8	1435.7	1356.4	1250.7	1120.6	972.5
120°	1370.8	1422.3	1454.1	1465.0	1454.1	1422.3	1370.8	1294.2	1194.6	1078.5	942.7
122.5°	1312.1	1362.7	1391.0	1400.1	1391.0	1362.7	1312.1	1243.4	1153.4	1043.5	919.1
125°	1239.4	1281.1	1308.4	1317.2	1308.4	1281.1	1239.4	1175.9	1093.8	997.5	884.7
127.5°	1174.9	1213.8	1237.5	1244.5	1237.5	1213.8	1174.9	1119.5	1043.7	952.8	850.7
130°	1135.5	1172.7	1194.6	1203.3	1194.6	1172.7	1135.5	1081.8	1009.6	923.0	828.9
132.5°	1095.1	1132.4	1152.5	1160.4	1152.5	1132.4	1095.1	1042.4	974.5	895.0	807.9
135°	1031.4	1067.5	1087.2	1091.7	1087.2	1067.5	1031.4	984.3	923.0	850.7	778.4
137.5°	969.2	1000.3	1017.7	1024.2	1017.7	1000.3	969.2	926.3	872.9	815.5	755.1
140°	926.3	954.8	971.2	977.8	971.2	954.8	926.3	891.3	843.1	792.8	740.2
142.5°	889.5	915.4	930.0	931.3	930.0	915.4	889.5	856.2	816.0	772.6	727.9
145°	838.7	857.3	868.3	871.6	868.3	857.3	838.7	812.5	780.7	746.8	710.6
147.5°	797.1	812.0	819.4	821.4	819.4	812.0	797.1	775.4	752.2	725.8	697.3
150°	770.8	784.0	790.5	791.6	790.5	784.0	770.8	754.4	734.7	711.7	687.6
152.5°	749.8	761.2	766.0	766.2	766.0	761.2	749.8	736.9	719.8	700.3	678.0
155°	722.6	730.3	734.7	732.5	734.7	730.3	722.6	710.6	698.5	682.1	664.6
157.5°	695.5	701.8	703.8	703.8	703.8	701.8	695.5	686.9	677.5	663.7	649.0
160°	678.8	684.3	685.4	685.4	685.4	684.3	678.8	671.2	663.5	651.5	639.4
162.5°	663.9	667.7	668.7	667.9	668.7	667.7	663.9	656.3	650.4	640.1	629.8
165°	639.4	643.9	643.9	642.7	643.9	643.9	639.4	635.1	630.7	623.0	615.4
167.5°	618.6	621.0	620.9	619.5	620.9	621.0	618.6	616.7	612.7	607.5	601.5
170°	605.5	608.8	607.7	605.5	607.7	608.8	605.5	604.4	602.2	597.9	594.6
172.5°	595.0	596.5	595.4	594.1	595.4	596.5	595.0	593.9	592.6	589.1	586.6
175°	581.4	582.5	581.4	579.2	581.4	582.5	581.4	581.4	580.3	579.2	578.2
177.5°	572.9	572.9	572.0	570.2	572.0	572.9	572.9	572.9	572.9	572.0	572.0
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	880.1	883.3	888.1	893.1	896.2	902.1	903.8	906.6	909.2	915.0	921.2
5°	829.3	834.2	845.8	852.2	861.0	871.2	877.9	885.0	892.7	906.1	918.4
7.5°	774.9	783.1	797.5	809.4	821.9	836.5	847.1	861.0	872.5	891.4	909.5
10°	738.5	750.1	763.2	777.2	794.8	810.3	825.1	842.7	856.8	879.3	900.4
12.5°	705.9	707.6	726.2	741.8	765.8	784.9	802.0	824.6	838.5	865.3	887.5
15°	648.8	659.3	676.2	688.5	717.0	741.3	765.3	788.8	804.6	837.7	867.0
17.5°	600.7	610.4	627.7	647.9	668.4	692.5	723.5	748.4	769.9	807.7	842.3
20°	570.2	582.2	599.8	620.6	638.6	665.0	691.6	720.2	743.4	786.0	826.5
22.5°	544.3	553.7	568.0	588.4	608.1	632.3	661.6	692.6	717.0	762.9	804.0
25°	507.9	515.7	524.8	541.8	563.9	590.3	613.2	647.3	682.9	725.9	775.4
27.5°	475.1	480.6	488.7	503.6	520.8	545.4	570.9	603.2	639.0	685.6	738.0
30°	455.2	458.6	466.7	479.1	496.0	515.3	541.0	572.0	608.6	655.8	707.8
32.5°	437.7	440.9	446.2	458.0	472.6	489.2	512.3	543.3	578.2	624.5	682.2
35°	411.5	414.0	418.5	428.0	436.1	452.3	471.6	499.8	532.5	576.9	636.8
37.5°	385.4	388.7	391.5	395.6	406.0	416.6	433.5	457.2	489.4	534.1	591.2
40°	368.2	371.0	375.2	377.0	385.4	394.9	408.7	430.5	462.9	503.7	559.3
42.5°	350.7	353.5	356.1	358.2	365.4	373.8	386.2	404.9	433.6	473.3	528.4
45°	327.0	327.3	329.8	333.7	337.2	343.2	352.0	368.2	390.4	427.7	477.7
47.5°	302.9	303.3	303.8	305.5	309.3	314.7	320.6	333.8	353.6	383.4	432.1
50°	286.9	286.2	286.9	288.3	290.8	295.3	302.0	311.5	327.7	355.5	400.2
52.5°	271.4	271.3	270.8	271.4	273.3	276.4	281.2	289.3	303.8	329.3	368.7
55°	247.8	246.0	246.4	245.0	248.2	248.8	252.4	259.1	271.7	289.4	326.3
57.5°	222.6	221.2	219.6	219.2	219.0	220.8	223.7	228.9	238.7	254.1	284.1
60°	206.6	204.9	202.7	202.1	202.1	203.1	204.5	208.4	217.5	231.3	255.9
62.5°	190.3	188.2	187.0	185.1	184.5	185.7	187.1	189.8	196.4	209.3	230.5
65°	165.1	162.6	160.9	160.5	159.9	158.7	159.5	162.3	167.6	177.8	194.6
67.5°	139.8	137.5	137.0	135.1	134.0	134.2	134.0	136.5	139.6	148.4	161.0
70°	123.2	121.4	120.7	118.9	118.3	117.5	116.9	118.9	122.2	129.5	140.4
72.5°	106.3	104.8	103.3	101.8	102.0	101.2	101.1	102.4	105.0	111.8	120.2
75°	82.0	82.4	80.6	78.9	78.5	77.8	77.8	78.9	79.9	85.2	91.9
77.5°	59.5	59.2	57.7	57.1	56.8	56.1	56.8	57.5	58.1	61.6	66.5
80°	45.4	45.4	43.6	43.6	43.3	42.2	43.3	42.6	44.0	47.5	51.1
82.5°	32.4	31.9	31.9	31.3	31.2	30.4	30.9	31.6	32.1	34.6	36.7
85°	15.8	15.8	15.5	15.2	15.5	15.2	15.5	15.8	16.2	17.2	19.0
87.5°	10.7	11.1	11.1	10.2	8.6	7.8	7.4	7.3	7.4	6.8	6.4
90°	36.1	37.2	36.1	29.6	21.9	16.4	13.1	10.9	8.8	4.3	1.1
92.5°	120.3	142.3	140.3	109.2	74.5	49.7	39.4	32.0	27.1	19.2	13.4
95°	375.6	429.2	379.9	252.9	157.7	107.3	81.1	63.5	53.6	42.7	38.4
97.5°	768.6	732.7	551.9	340.7	208.0	144.8	115.0	94.8	79.9	68.3	62.4
100°	1022.7	865.0	595.6	359.1	225.6	167.5	136.9	115.0	97.5	87.6	84.3
102.5°	1117.3	869.4	579.0	360.1	241.3	187.7	157.0	134.2	116.7	106.9	104.4
105°	1102.6	811.3	546.4	365.7	268.2	216.8	186.2	162.0	145.6	138.0	133.6
107.5°	1006.4	749.1	530.2	380.8	295.9	245.9	215.1	191.1	176.1	168.6	165.1
110°	946.0	719.3	526.7	393.0	314.2	266.1	234.3	211.3	197.1	190.5	186.2



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	904.0	700.1	527.5	406.2	331.8	285.3	252.7	230.5	217.3	209.8	205.4
115°	851.9	678.8	532.2	425.9	359.1	312.1	282.5	260.6	247.4	240.9	235.4
117.5°	819.0	668.5	540.0	447.0	384.3	340.7	310.1	289.1	277.5	270.9	266.6
120°	801.4	662.4	545.3	461.0	401.8	359.1	328.5	306.6	296.7	290.1	285.8
122.5°	786.6	658.9	551.4	473.3	418.5	378.4	346.9	325.0	314.2	307.6	304.2
125°	765.3	652.6	560.6	492.8	443.5	404.1	373.3	351.5	338.4	331.8	328.5
127.5°	745.6	648.8	570.0	510.9	466.7	428.3	396.8	375.8	361.4	352.1	347.7
130°	732.5	647.1	577.0	522.3	480.7	442.3	411.7	389.8	374.5	363.5	359.1
132.5°	722.0	646.2	584.0	533.7	492.9	456.4	425.7	402.9	386.7	374.9	369.7
135°	707.3	644.9	592.4	548.6	510.2	475.2	444.5	419.3	402.9	389.8	385.4
137.5°	697.0	644.7	599.8	560.0	524.2	489.7	461.2	436.2	418.7	405.6	400.3
140°	690.9	643.9	603.3	566.1	532.2	499.3	470.8	446.8	429.2	416.0	411.7
142.5°	684.8	643.9	606.0	571.4	538.3	506.3	479.6	456.4	438.8	426.6	423.1
145°	676.7	641.6	608.8	578.2	547.4	517.9	493.8	471.9	455.5	444.5	440.2
147.5°	668.4	637.7	609.6	581.8	554.9	527.1	505.7	487.5	472.3	461.8	458.5
150°	661.3	635.1	608.8	583.6	558.5	533.2	513.5	497.1	482.9	474.1	470.8
152.5°	655.2	630.7	607.0	584.5	561.9	539.3	521.4	505.9	493.3	484.7	483.1
155°	643.9	623.0	604.4	585.8	567.1	548.6	532.2	520.1	508.0	501.4	500.4
157.5°	633.1	615.1	599.4	585.8	570.9	555.2	541.3	531.7	521.2	515.9	514.8
160°	625.2	609.9	596.7	585.8	572.7	559.5	547.4	538.7	529.9	525.6	524.4
162.5°	618.2	605.5	594.1	584.9	573.5	562.1	552.7	544.8	537.8	533.5	534.1
165°	606.6	596.7	589.1	582.5	574.9	565.0	558.5	552.9	546.4	544.2	545.3
167.5°	595.2	589.1	584.0	581.0	574.6	567.4	563.3	559.3	555.2	553.2	554.5
170°	589.1	584.7	581.4	579.2	573.7	568.3	565.0	562.8	559.5	558.5	560.6
172.5°	583.0	579.5	577.9	576.6	572.9	569.1	566.8	565.4	562.1	562.8	564.1
175°	574.9	573.7	572.7	573.7	571.6	569.4	568.3	568.3	566.1	567.1	568.3
177.5°	570.2	569.4	570.2	572.0	570.2	569.4	569.4	569.4	567.6	568.4	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331323-830
 CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	920.7	922.1	926.6	931.1	936.1	937.5	939.8	937.8	937.3	942.6	946.6
5°	923.3	929.6	942.0	953.2	962.7	969.4	976.5	979.3	984.6	991.9	1001.1
7.5°	920.3	932.6	952.1	968.5	986.3	999.2	1009.3	1017.9	1028.2	1042.3	1057.5
10°	917.0	933.5	957.1	977.1	999.0	1015.5	1029.3	1042.6	1058.1	1077.5	1097.5
12.5°	910.8	930.4	959.9	983.6	1011.6	1027.9	1046.4	1075.3	1091.9	1118.9	1147.1
15°	898.3	920.1	961.3	990.5	1022.2	1053.2	1087.3	1114.7	1142.3	1158.1	1197.9
17.5°	879.8	911.8	957.4	991.6	1031.8	1080.5	1118.9	1150.1	1181.8	1207.4	1227.4
20°	864.9	899.8	951.8	992.7	1040.5	1093.0	1137.0	1168.7	1196.1	1217.6	1229.9
22.5°	846.0	889.9	940.6	988.4	1049.5	1101.5	1147.6	1172.6	1195.5	1206.0	1210.7
25°	816.2	869.1	926.4	984.9	1053.9	1108.8	1151.0	1166.2	1172.9	1162.6	1145.8
27.5°	784.3	843.1	910.2	978.3	1051.2	1104.0	1134.3	1131.9	1120.6	1087.5	1061.1
30°	760.3	825.1	897.2	971.5	1044.7	1096.1	1113.7	1096.1	1070.4	1033.5	995.8
32.5°	735.3	802.3	883.4	962.0	1032.9	1078.1	1081.9	1051.6	1011.8	969.9	922.8
35°	697.3	769.9	857.4	940.6	1007.8	1036.3	1019.4	965.9	918.7	861.4	797.3
37.5°	654.4	734.5	822.4	909.2	970.2	977.6	935.7	879.3	812.8	745.4	670.0
40°	622.4	707.2	797.7	885.2	939.1	931.4	877.9	816.0	736.7	654.4	584.3
42.5°	593.6	678.4	770.6	856.6	899.8	878.4	816.0	739.9	654.8	577.2	513.1
45°	543.8	631.1	725.5	808.5	833.2	794.8	712.1	627.6	543.8	479.1	428.4
47.5°	495.6	581.8	675.2	748.3	757.1	705.4	615.0	528.1	456.1	403.3	367.6
50°	460.1	546.7	639.2	704.4	701.5	639.2	546.3	463.5	403.4	360.8	336.9
52.5°	428.2	510.0	599.0	658.2	643.3	575.3	486.6	413.2	363.7	330.4	308.7
55°	378.7	454.4	538.9	586.4	559.0	483.6	408.7	349.5	312.9	287.9	271.1
57.5°	329.6	400.6	472.9	502.2	471.8	402.3	339.8	296.9	269.4	250.8	239.9
60°	299.2	361.2	425.6	450.9	414.6	352.7	303.4	265.0	242.9	227.7	217.9
62.5°	268.8	324.2	385.0	398.8	365.6	313.3	269.7	237.7	219.5	206.0	196.8
65°	227.4	272.8	319.0	328.1	297.5	256.9	222.4	201.7	185.5	175.7	168.2
67.5°	186.5	222.9	255.6	263.0	236.2	208.1	183.1	165.1	154.1	145.9	139.7
70°	162.3	191.1	217.9	223.9	202.4	177.4	158.4	143.9	134.1	127.1	121.1
72.5°	136.7	160.7	182.9	187.0	169.5	150.3	134.8	123.4	114.7	110.2	104.4
75°	104.5	118.7	135.9	137.0	125.4	113.7	101.7	94.3	89.7	84.2	81.3
77.5°	73.8	84.8	94.7	96.6	89.7	81.8	75.1	69.3	65.4	62.8	60.2
80°	56.4	65.1	69.4	71.8	66.9	61.3	57.4	53.5	51.1	49.3	47.5
82.5°	40.2	45.7	49.7	51.6	48.8	45.5	41.6	39.4	37.5	36.0	35.4
85°	20.5	22.9	25.4	26.0	25.4	23.9	21.9	21.9	20.7	20.5	20.5
87.5°	7.9	9.9	10.4	11.6	11.7	12.8	14.3	15.4	15.4	14.8	14.3
90°	4.3	8.8	10.9	13.1	16.4	21.9	29.6	36.1	37.2	36.1	35.1
92.5°	19.2	27.1	32.0	39.4	49.7	74.5	109.2	140.3	142.3	120.3	95.5
95°	42.7	53.6	63.5	81.1	107.3	157.7	252.9	379.9	429.2	375.6	286.9
97.5°	68.3	79.9	94.8	115.0	144.8	208.0	340.7	551.9	732.7	768.6	669.4
100°	87.6	97.5	115.0	136.9	167.5	225.6	359.1	595.6	865.0	1022.7	999.7
102.5°	106.9	116.7	134.2	157.0	187.7	241.3	360.1	579.0	869.4	1117.3	1216.1
105°	138.0	145.6	162.0	186.2	216.8	268.2	365.7	546.4	811.3	1102.6	1330.3
107.5°	168.6	176.1	191.1	215.1	245.9	295.9	380.8	530.2	749.1	1006.4	1248.0
110°	190.5	197.1	211.3	234.3	266.1	314.2	393.0	526.7	719.3	946.0	1177.0



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	209.8	217.3	230.5	252.7	285.3	331.8	406.2	527.5	700.1	904.0	1112.2
115°	240.9	247.4	260.6	282.5	312.1	359.1	425.9	532.2	678.8	851.9	1032.6
117.5°	270.9	277.5	289.1	310.1	340.7	384.3	447.0	540.0	668.5	819.0	972.5
120°	290.1	296.7	306.6	328.5	359.1	401.8	461.0	545.3	662.4	801.4	942.7
122.5°	307.6	314.2	325.0	346.9	378.4	418.5	473.3	551.4	658.9	786.6	919.1
125°	331.8	338.4	351.5	373.3	404.1	443.5	492.8	560.6	652.6	765.3	884.7
127.5°	352.1	361.4	375.8	396.8	428.3	466.7	510.9	570.0	648.8	745.6	850.7
130°	363.5	374.5	389.8	411.7	442.3	480.7	522.3	577.0	647.1	732.5	828.9
132.5°	374.9	386.7	402.9	425.7	456.4	492.9	533.7	584.0	646.2	722.0	807.9
135°	389.8	402.9	419.3	444.5	475.2	510.2	548.6	592.4	644.9	707.3	778.4
137.5°	405.6	418.7	436.2	461.2	489.7	524.2	560.0	599.8	644.7	697.0	755.1
140°	416.0	429.2	446.8	470.8	499.3	532.2	566.1	603.3	643.9	690.9	740.2
142.5°	426.6	438.8	456.4	479.6	506.3	538.3	571.4	606.0	643.9	684.8	727.9
145°	444.5	455.5	471.9	493.8	517.9	547.4	578.2	608.8	641.6	676.7	710.6
147.5°	461.8	472.3	487.5	505.7	527.1	554.9	581.8	609.6	637.7	668.4	697.3
150°	474.1	482.9	497.1	513.5	533.2	558.5	583.6	608.8	635.1	661.3	687.6
152.5°	484.7	493.3	505.9	521.4	539.3	561.9	584.5	607.0	630.7	655.2	678.0
155°	501.4	508.0	520.1	532.2	548.6	567.1	585.8	604.4	623.0	643.9	664.6
157.5°	515.9	521.2	531.7	541.3	555.2	570.9	585.8	599.4	615.1	633.1	649.0
160°	525.6	529.9	538.7	547.4	559.5	572.7	585.8	596.7	609.9	625.2	639.4
162.5°	533.5	537.8	544.8	552.7	562.1	573.5	584.9	594.1	605.5	618.2	629.8
165°	544.2	546.4	552.9	558.5	565.0	574.9	582.5	589.1	596.7	606.6	615.4
167.5°	553.2	555.2	559.3	563.3	567.4	574.6	581.0	584.0	589.1	595.2	601.5
170°	558.5	559.5	562.8	565.0	568.3	573.7	579.2	581.4	584.7	589.1	594.6
172.5°	562.8	562.1	565.4	566.8	569.1	572.9	576.6	577.9	579.5	583.0	586.6
175°	567.1	566.1	568.3	568.3	569.4	571.6	573.7	572.7	573.7	574.9	578.2
177.5°	568.4	567.6	569.4	569.4	569.4	570.2	572.0	570.2	569.4	570.2	572.0
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4	569.4



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	950.0	953.9	953.9	954.5	958.9	958.5	958.2
5°	1011.0	1016.9	1017.7	1024.0	1028.2	1026.8	1022.9
7.5°	1068.5	1079.6	1088.1	1092.8	1098.3	1101.7	1100.2
10°	1114.1	1130.3	1140.1	1146.8	1154.9	1160.9	1158.8
12.5°	1155.5	1174.8	1188.3	1199.8	1200.8	1208.5	1203.2
15°	1220.0	1240.5	1242.6	1251.0	1257.7	1257.0	1257.4
17.5°	1241.3	1247.9	1249.2	1249.4	1249.5	1247.1	1241.7
20°	1233.8	1231.3	1225.3	1220.8	1212.7	1211.5	1204.6
22.5°	1197.7	1189.9	1174.9	1165.0	1152.4	1149.1	1147.1
25°	1126.7	1109.5	1085.5	1062.7	1056.3	1044.1	1047.5
27.5°	1029.4	1002.5	976.6	958.0	941.2	922.7	928.0
30°	960.9	930.7	894.1	865.9	848.0	830.4	827.2
32.5°	879.3	834.9	794.1	769.3	741.8	730.7	718.5
35°	738.5	695.2	654.7	619.9	599.8	584.3	570.2
37.5°	611.8	562.0	529.3	501.1	486.6	477.8	479.9
40°	533.3	489.7	465.7	444.2	430.8	424.5	425.9
42.5°	469.7	437.0	417.3	402.6	393.1	389.6	388.7
45°	397.4	379.1	362.9	354.5	349.9	346.0	343.6
47.5°	348.2	333.2	324.0	319.1	315.0	311.1	311.0
50°	318.6	308.7	302.4	297.1	293.9	291.1	293.6
52.5°	296.1	287.0	280.7	276.0	274.8	272.2	272.2
55°	262.6	255.5	251.0	246.8	244.7	243.3	241.5
57.5°	232.1	225.5	221.3	218.6	214.6	213.2	212.6
60°	210.5	205.2	201.0	197.5	195.7	192.9	192.9
62.5°	190.5	185.2	181.3	178.6	175.7	174.6	174.8
65°	161.6	157.3	153.4	150.6	150.0	147.9	148.5
67.5°	135.0	132.1	128.1	126.5	125.2	124.0	123.2
70°	117.3	114.4	112.3	110.2	109.1	109.1	109.1
72.5°	102.3	98.9	97.6	95.0	95.6	94.4	93.3
75°	79.2	77.1	76.1	74.9	73.2	73.2	73.2
77.5°	58.2	57.7	56.4	55.2	54.9	54.5	54.7
80°	45.1	44.7	44.0	44.0	43.3	43.0	42.2
82.5°	34.6	33.7	33.3	33.0	32.9	32.8	32.7
85°	19.7	19.0	19.0	19.3	18.7	18.7	19.0
87.5°	14.1	14.6	14.5	14.5	14.8	14.5	14.5
90°	32.9	35.1	36.1	36.1	36.1	36.1	36.1
92.5°	81.9	72.7	65.9	65.0	61.5	62.4	60.7
95°	220.1	174.1	150.0	135.7	127.1	123.8	124.8
97.5°	547.7	429.2	350.2	297.8	270.9	254.9	245.7
100°	863.9	713.9	581.4	490.5	443.5	411.7	392.0
102.5°	1185.3	1075.6	935.3	836.5	756.2	716.5	689.8
105°	1454.1	1468.3	1432.2	1364.2	1296.4	1249.3	1234.0
107.5°	1434.4	1548.2	1601.2	1609.8	1606.0	1596.6	1576.2
110°	1373.0	1513.2	1603.0	1650.0	1670.8	1680.7	1679.6



TEST NUMBER: P331323-830

CATALOG NUMBER: SA2XXDIP-C485D1080U830-4F0-1E-UDD-A4

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	1300.3	1450.1	1553.0	1618.5	1653.3	1672.0	1677.8
115°	1201.2	1344.5	1457.4	1535.1	1585.5	1613.9	1623.8
117.5°	1120.6	1250.7	1356.4	1435.7	1488.8	1518.9	1527.2
120°	1078.5	1194.6	1294.2	1370.8	1422.3	1454.1	1465.0
122.5°	1043.5	1153.4	1243.4	1312.1	1362.7	1391.0	1400.1
125°	997.5	1093.8	1175.9	1239.4	1281.1	1308.4	1317.2
127.5°	952.8	1043.7	1119.5	1174.9	1213.8	1237.5	1244.5
130°	923.0	1009.6	1081.8	1135.5	1172.7	1194.6	1203.3
132.5°	895.0	974.5	1042.4	1095.1	1132.4	1152.5	1160.4
135°	850.7	923.0	984.3	1031.4	1067.5	1087.2	1091.7
137.5°	815.5	872.9	926.3	969.2	1000.3	1017.7	1024.2
140°	792.8	843.1	891.3	926.3	954.8	971.2	977.8
142.5°	772.6	816.0	856.2	889.5	915.4	930.0	931.3
145°	746.8	780.7	812.5	838.7	857.3	868.3	871.6
147.5°	725.8	752.2	775.4	797.1	812.0	819.4	821.4
150°	711.7	734.7	754.4	770.8	784.0	790.5	791.6
152.5°	700.3	719.8	736.9	749.8	761.2	766.0	766.2
155°	682.1	698.5	710.6	722.6	730.3	734.7	732.5
157.5°	663.7	677.5	686.9	695.5	701.8	703.8	703.8
160°	651.5	663.5	671.2	678.8	684.3	685.4	685.4
162.5°	640.1	650.4	656.3	663.9	667.7	668.7	667.9
165°	623.0	630.7	635.1	639.4	643.9	643.9	642.7
167.5°	607.5	612.7	616.7	618.6	621.0	620.9	619.5
170°	597.9	602.2	604.4	605.5	608.8	607.7	605.5
172.5°	589.1	592.6	593.9	595.0	596.5	595.4	594.1
175°	579.2	580.3	581.4	581.4	582.5	581.4	579.2
177.5°	572.0	572.9	572.9	572.9	572.9	572.0	570.2
180°	569.4	569.4	569.4	569.4	569.4	569.4	569.4

(END OF REPORT)