

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331285-830

Luminaire Tested: **SA2XXDIP-C485D330U830-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331285-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D330U830-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 330 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3255.9 lumens  
Efficiency: N/A  
Efficacy: 118.4 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 27.5  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331285-830  
CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331285-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62				
1	101	97	93	90	95	91	88	85	80	77	75	70	68	66	60	59	58	53				
2	93	85	79	74	87	80	75	71	71	67	63	62	59	56	54	52	50	46				
3	85	76	68	63	79	71	65	60	63	58	54	55	52	48	48	45	43	39				
4	78	67	60	54	73	64	57	51	56	51	47	50	45	42	44	40	38	34				
5	72	60	52	46	67	57	50	45	51	45	41	45	40	37	40	36	33	30				
6	66	55	47	41	62	52	44	39	46	40	36	41	36	33	36	32	30	27				
7	62	49	42	36	58	47	40	35	42	36	32	37	33	29	33	29	27	24				
8	57	45	37	32	54	43	36	31	39	33	29	34	30	26	31	27	24	22				
9	54	41	34	29	50	39	33	28	35	30	26	32	27	24	28	25	22	20				
10	50	38	31	26	47	36	30	25	33	27	23	30	25	22	26	23	20	18				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	14788	14788	14788	14788
5°	16579	14885	13190	14885
10°	18998	14762	11416	14762
15°	21018	14492	10084	14492
20°	20697	14201	9194	14201
25°	18661	13814	8630	13814
30°	15422	13196	8216	13196
35°	11239	12552	7924	12552
40°	8977	11788	7761	11788
45°	7846	10908	7540	10908
50°	7375	10052	7392	10052
55°	6798	9185	7192	9185
60°	6229	8263	6888	8263
65°	5673	7435	6590	7435
70°	5150	6628	6151	6628
75°	4566	5733	5446	5733
80°	3924	4751	4379	4751
85°	3520	3520	2594	3520



TEST NUMBER: P331285-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.2	2.7
10°-20°	253.6	7.8
20°-30°	368.0	11.3
30°-40°	388.4	11.9
40°-50°	343.9	10.6
50°-60°	274.4	8.4
60°-70°	186.5	5.7
70°-80°	95.6	2.9
80°-90°	24.1	0.7
90°-100°	14.0	0.4
100°-110°	51.5	1.6
110°-120°	137.7	4.2
120°-130°	227.3	7.0
130°-140°	241.8	7.4
140°-150°	224.7	6.9
150°-160°	180.7	5.5
160°-170°	116.4	3.6
170°-180°	40.1	1.2
0°-30°	708.8	21.8
0°-40°	1097.2	33.7
0°-60°	1715.5	52.7
0°-90°	2021.7	62.1
90°-120°	203.3	6.2
90°-150°	897.1	27.6
90°-180°	1234.0	37.9
0°-180°	3255.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	916	916	916	916	916	
5°	1023	918	814	918	1023	102
15°	1257	867	603	867	1257	347
25°	1048	775	484	775	1048	473
35°	570	637	402	637	570	371
45°	344	478	330	478	344	270
55°	242	326	256	326	242	217
65°	148	195	172	195	148	148
75°	73	92	87	92	73	78
85°	19	19	14	19	19	21
90°	8	0	8	0	8	5
95°	13	20	13	20	13	12
105°	23	93	23	93	23	24
115°	25	175	25	175	25	63
125°	260	248	260	248	260	225
135°	317	307	317	307	317	244
145°	361	356	361	356	361	226
155°	392	392	392	392	392	181
165°	412	413	412	413	412	116
175°	420	422	420	422	420	40
180°	421	421	421	421	421	



TEST NUMBER: P331285-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	958.2	958.5	958.9	954.5	953.9	953.9	950.0	946.6	942.6	937.3	937.8
5°	1022.9	1026.8	1028.2	1024.0	1017.7	1016.9	1011.0	1001.1	991.9	984.6	979.3
7.5°	1100.2	1101.7	1098.3	1092.8	1088.1	1079.6	1068.5	1057.5	1042.3	1028.2	1017.9
10°	1158.8	1160.9	1154.9	1146.8	1140.1	1130.3	1114.1	1097.5	1077.5	1058.1	1042.6
12.5°	1203.2	1208.5	1200.8	1199.8	1188.3	1174.8	1155.5	1147.1	1118.9	1091.9	1075.3
15°	1257.4	1257.0	1257.7	1251.0	1242.6	1240.5	1220.0	1197.9	1158.1	1142.3	1114.7
17.5°	1241.7	1247.1	1249.5	1249.4	1249.2	1247.9	1241.3	1227.4	1207.4	1181.8	1150.1
20°	1204.6	1211.5	1212.7	1220.8	1225.3	1231.3	1233.8	1229.9	1217.6	1196.1	1168.7
22.5°	1147.1	1149.1	1152.4	1165.0	1174.9	1189.9	1197.7	1210.7	1206.0	1195.5	1172.6
25°	1047.5	1044.1	1056.3	1062.7	1085.5	1109.5	1126.7	1145.8	1162.6	1172.9	1166.2
27.5°	928.0	922.7	941.2	958.0	976.6	1002.5	1029.4	1061.1	1087.5	1120.6	1131.9
30°	827.2	830.4	848.0	865.9	894.1	930.7	960.9	995.8	1033.5	1070.4	1096.1
32.5°	718.5	730.7	741.8	769.3	794.1	834.9	879.3	922.8	969.9	1011.8	1051.6
35°	570.2	584.3	599.8	619.9	654.7	695.2	738.5	797.3	861.4	918.7	965.9
37.5°	479.9	477.8	486.6	501.1	529.3	562.0	611.8	670.0	745.4	812.8	879.3
40°	425.9	424.5	430.8	444.2	465.7	489.7	533.3	584.3	654.4	736.7	816.0
42.5°	388.7	389.6	393.1	402.6	417.3	437.0	469.7	513.1	577.2	654.8	739.9
45°	343.6	346.0	349.9	354.5	362.9	379.1	397.4	428.4	479.1	543.8	627.6
47.5°	311.0	311.1	315.0	319.1	324.0	333.2	348.2	367.6	403.3	456.1	528.1
50°	293.6	291.1	293.9	297.1	302.4	308.7	318.6	336.9	360.8	403.4	463.5
52.5°	272.2	272.2	274.8	276.0	280.7	287.0	296.1	308.7	330.4	363.7	413.2
55°	241.5	243.3	244.7	246.8	251.0	255.5	262.6	271.1	287.9	312.9	349.5
57.5°	212.6	213.2	214.6	218.6	221.3	225.5	232.1	239.9	250.8	269.4	296.9
60°	192.9	192.9	195.7	197.5	201.0	205.2	210.5	217.9	227.7	242.9	265.0
62.5°	174.8	174.6	175.7	178.6	181.3	185.2	190.5	196.8	206.0	219.5	237.7
65°	148.5	147.9	150.0	150.6	153.4	157.3	161.6	168.2	175.7	185.5	201.7
67.5°	123.2	124.0	125.2	126.5	128.1	132.1	135.0	139.7	145.9	154.1	165.1
70°	109.1	109.1	109.1	110.2	112.3	114.4	117.3	121.1	127.1	134.1	143.9
72.5°	93.3	94.4	95.6	95.0	97.6	98.9	102.3	104.4	110.2	114.7	123.4
75°	73.2	73.2	73.2	74.9	76.1	77.1	79.2	81.3	84.2	89.7	94.3
77.5°	54.7	54.5	54.9	55.2	56.4	57.7	58.2	60.2	62.8	65.4	69.3
80°	42.2	43.0	43.3	44.0	44.0	44.7	45.1	47.5	49.3	51.1	53.5
82.5°	32.7	32.8	32.9	33.0	33.3	33.7	34.6	35.4	36.0	37.5	39.4
85°	19.0	18.7	18.7	19.3	19.0	19.0	19.7	20.5	20.5	20.7	21.9
87.5°	9.0	9.0	9.2	8.9	8.9	9.0	9.0	8.7	8.9	9.1	9.2
90°	8.2	8.1	7.9	7.8	7.7	7.4	7.1	6.8	6.4	6.1	5.6
92.5°	8.2	8.1	8.1	8.0	7.9	7.7	7.6	7.4	7.3	7.1	6.8
95°	13.1	13.2	13.2	13.3	13.4	13.2	12.9	12.5	12.3	11.9	11.4
97.5°	17.5	17.4	17.3	17.2	17.2	17.0	16.7	16.5	16.2	15.9	14.8
100°	20.5	20.3	20.2	20.0	19.9	19.5	19.0	18.5	17.9	17.3	16.2
102.5°	21.9	21.7	21.5	21.3	21.1	20.6	20.0	19.2	18.6	17.8	27.5
105°	23.2	22.9	22.6	22.3	22.1	21.6	20.8	20.1	19.3	18.6	37.0
107.5°	23.8	23.6	23.3	23.0	22.7	23.0	23.8	24.5	25.3	26.0	48.2
110°	24.0	23.8	23.6	23.3	23.0	26.2	33.0	39.8	46.6	53.3	72.9



TEST NUMBER: P331285-830  
 CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	24.3	24.1	23.8	23.7	23.5	35.7	60.4	85.1	109.8	134.5	139.3
115°	25.0	29.9	34.8	39.6	44.5	62.6	94.0	125.4	156.7	188.0	186.3
117.5°	102.1	118.1	134.1	150.1	166.2	178.0	185.5	193.1	200.7	208.3	207.1
120°	185.9	195.0	204.2	213.3	222.4	226.6	225.8	225.0	224.2	223.4	222.2
122.5°	232.0	233.8	235.5	237.3	239.0	239.7	239.2	238.7	238.3	237.8	236.5
125°	260.5	260.3	260.1	260.0	259.8	259.4	258.9	258.4	258.0	257.5	256.2
127.5°	278.6	278.5	278.5	278.5	278.4	278.1	277.4	276.7	276.0	275.3	274.4
130°	289.8	289.9	289.9	290.0	290.1	289.7	289.0	288.2	287.5	286.8	286.1
132.5°	300.8	300.9	301.0	301.0	301.0	300.8	300.1	299.5	298.9	298.2	297.5
135°	316.6	316.8	316.9	317.1	317.2	316.9	316.2	315.6	314.9	314.2	313.6
137.5°	331.1	331.3	331.6	331.8	332.0	331.8	331.1	330.5	329.8	329.1	328.5
140°	340.1	340.4	340.8	341.1	341.5	341.3	340.7	340.1	339.5	338.8	338.2
142.5°	348.8	349.2	349.6	349.9	350.2	350.2	349.6	349.0	348.5	347.9	347.0
145°	361.1	361.5	361.8	362.1	362.5	362.4	361.9	361.5	361.0	360.5	359.4
147.5°	371.9	372.2	372.5	372.8	373.1	373.1	372.7	372.3	371.9	371.6	370.5
150°	378.5	378.8	379.2	379.6	379.8	379.8	379.4	379.0	378.6	378.2	377.1
152.5°	384.1	384.6	385.0	385.4	385.9	385.9	385.5	385.1	384.7	384.3	383.2
155°	391.9	392.5	393.0	393.5	394.1	394.2	393.7	393.3	392.9	392.5	391.7
157.5°	399.1	399.5	400.1	400.6	401.1	401.1	400.8	400.3	399.8	399.4	398.8
160°	403.2	403.7	404.2	404.6	405.1	405.1	404.7	404.4	403.9	403.5	403.1
162.5°	406.6	407.2	407.7	408.3	409.0	409.0	408.5	408.0	407.6	407.2	406.8
165°	411.7	412.2	412.6	413.1	413.6	413.6	413.1	412.6	412.2	411.7	411.5
167.5°	414.9	415.6	416.1	416.8	417.4	417.5	417.0	416.5	416.0	415.6	415.4
170°	416.9	417.5	418.1	418.8	419.3	419.4	419.0	418.5	418.0	417.5	417.4
172.5°	418.4	419.0	419.6	420.2	420.8	420.8	420.4	419.9	419.4	419.0	418.9
175°	419.6	420.3	421.0	421.7	422.4	422.4	422.0	421.5	421.0	420.6	420.5
177.5°	420.5	420.9	421.4	421.9	422.4	422.4	422.1	421.7	421.3	420.9	420.8
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331285-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	939.8	937.5	936.1	931.1	926.6	922.1	920.7	921.2	915.0	909.2	906.6
5°	976.5	969.4	962.7	953.2	942.0	929.6	923.3	918.4	906.1	892.7	885.0
7.5°	1009.3	999.2	986.3	968.5	952.1	932.6	920.3	909.5	891.4	872.5	861.0
10°	1029.3	1015.5	999.0	977.1	957.1	933.5	917.0	900.4	879.3	856.8	842.7
12.5°	1046.4	1027.9	1011.6	983.6	959.9	930.4	910.8	887.5	865.3	838.5	824.6
15°	1087.3	1053.2	1022.2	990.5	961.3	920.1	898.3	867.0	837.7	804.6	788.8
17.5°	1118.9	1080.5	1031.8	991.6	957.4	911.8	879.8	842.3	807.7	769.9	748.4
20°	1137.0	1093.0	1040.5	992.7	951.8	899.8	864.9	826.5	786.0	743.4	720.2
22.5°	1147.6	1101.5	1049.5	988.4	940.6	889.9	846.0	804.0	762.9	717.0	692.6
25°	1151.0	1108.8	1053.9	984.9	926.4	869.1	816.2	775.4	725.9	682.9	647.3
27.5°	1134.3	1104.0	1051.2	978.3	910.2	843.1	784.3	738.0	685.6	639.0	603.2
30°	1113.7	1096.1	1044.7	971.5	897.2	825.1	760.3	707.8	655.8	608.6	572.0
32.5°	1081.9	1078.1	1032.9	962.0	883.4	802.3	735.3	682.2	624.5	578.2	543.3
35°	1019.4	1036.3	1007.8	940.6	857.4	769.9	697.3	636.8	576.9	532.5	499.8
37.5°	935.7	977.6	970.2	909.2	822.4	734.5	654.4	591.2	534.1	489.4	457.2
40°	877.9	931.4	939.1	885.2	797.7	707.2	622.4	559.3	503.7	462.9	430.5
42.5°	816.0	878.4	899.8	856.6	770.6	678.4	593.6	528.4	473.3	433.6	404.9
45°	712.1	794.8	833.2	808.5	725.5	631.1	543.8	477.7	427.7	390.4	368.2
47.5°	615.0	705.4	757.1	748.3	675.2	581.8	495.6	432.1	383.4	353.6	333.8
50°	546.3	639.2	701.5	704.4	639.2	546.7	460.1	400.2	355.5	327.7	311.5
52.5°	486.6	575.3	643.3	658.2	599.0	510.0	428.2	368.7	329.3	303.8	289.3
55°	408.7	483.6	559.0	586.4	538.9	454.4	378.7	326.3	289.4	271.7	259.1
57.5°	339.8	402.3	471.8	502.2	472.9	400.6	329.6	284.1	254.1	238.7	228.9
60°	303.4	352.7	414.6	450.9	425.6	361.2	299.2	255.9	231.3	217.5	208.4
62.5°	269.7	313.3	365.6	398.8	385.0	324.2	268.8	230.5	209.3	196.4	189.8
65°	222.4	256.9	297.5	328.1	319.0	272.8	227.4	194.6	177.8	167.6	162.3
67.5°	183.1	208.1	236.2	263.0	255.6	222.9	186.5	161.0	148.4	139.6	136.5
70°	158.4	177.4	202.4	223.9	217.9	191.1	162.3	140.4	129.5	122.2	118.9
72.5°	134.8	150.3	169.5	187.0	182.9	160.7	136.7	120.2	111.8	105.0	102.4
75°	101.7	113.7	125.4	137.0	135.9	118.7	104.5	91.9	85.2	79.9	78.9
77.5°	75.1	81.8	89.7	96.6	94.7	84.8	73.8	66.5	61.6	58.1	57.5
80°	57.4	61.3	66.9	71.8	69.4	65.1	56.4	51.1	47.5	44.0	42.6
82.5°	41.6	45.5	48.8	51.6	49.7	45.7	40.2	36.7	34.6	32.1	31.6
85°	21.9	23.9	25.4	26.0	25.4	22.9	20.5	19.0	17.2	16.2	15.8
87.5°	9.4	9.3	9.2	9.7	8.7	8.5	7.3	6.2	6.1	6.0	5.6
90°	5.0	4.4	4.0	3.3	2.5	1.8	1.0	0.3	1.0	1.8	2.5
92.5°	6.5	6.2	6.0	5.8	5.9	6.0	6.1	6.1	6.1	6.0	5.9
95°	10.9	10.5	10.0	10.8	13.1	15.4	17.5	19.8	17.5	15.4	13.1
97.5°	13.7	12.6	11.5	14.1	20.5	26.7	33.0	39.3	33.0	26.7	20.5
100°	15.1	13.9	12.7	16.9	26.1	35.3	44.7	53.9	44.7	35.3	26.1
102.5°	37.1	46.8	56.4	62.2	64.2	66.1	68.1	70.0	68.1	66.1	64.2
105°	55.6	74.1	92.6	100.8	98.8	96.7	94.6	92.7	94.6	96.7	98.8
107.5°	70.4	92.6	114.7	125.0	123.4	121.7	120.1	118.4	120.1	121.7	123.4
110°	92.5	112.1	131.6	140.7	139.3	137.9	136.4	135.0	136.4	137.9	139.3





TEST NUMBER: P331285-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	144.2	149.0	153.8	155.6	154.4	153.2	151.8	150.6	151.8	153.2	154.4
115°	184.6	182.9	181.3	179.8	178.7	177.6	176.3	175.2	176.3	177.6	178.7
117.5°	205.9	204.8	203.6	202.4	201.1	199.8	198.5	197.3	198.5	199.8	201.1
120°	220.9	219.7	218.5	217.4	216.4	215.4	214.3	213.3	214.3	215.4	216.4
122.5°	235.1	233.8	232.4	231.3	230.2	229.1	228.1	227.0	228.1	229.1	230.2
125°	255.0	253.6	252.4	251.3	250.4	249.5	248.6	247.8	248.6	249.5	250.4
127.5°	273.4	272.4	271.5	270.5	269.6	268.5	267.6	266.6	267.6	268.5	269.6
130°	285.3	284.6	283.8	282.9	281.8	280.7	279.7	278.5	279.7	280.7	281.8
132.5°	296.7	296.0	295.2	294.5	293.5	292.6	291.6	290.8	291.6	292.6	293.5
135°	313.0	312.4	311.8	310.9	309.8	308.8	307.6	306.6	307.6	308.8	309.8
137.5°	327.7	327.1	326.4	325.6	324.9	324.1	323.4	322.6	323.4	324.1	324.9
140°	337.4	336.7	335.9	335.3	334.7	334.1	333.7	333.1	333.7	334.1	334.7
142.5°	346.2	345.3	344.5	343.8	343.4	342.8	342.3	341.9	342.3	342.8	343.4
145°	358.3	357.0	355.9	355.3	355.4	355.5	355.6	355.6	355.6	355.5	355.4
147.5°	369.4	368.2	367.0	366.6	366.8	367.1	367.4	367.7	367.4	367.1	366.8
150°	376.1	374.9	373.9	373.5	374.0	374.5	374.9	375.4	374.9	374.5	374.0
152.5°	382.2	381.2	380.1	379.9	380.4	381.0	381.5	382.0	381.5	381.0	380.4
155°	390.9	390.1	389.3	389.2	389.7	390.4	391.0	391.6	391.0	390.4	389.7
157.5°	398.2	397.7	397.1	397.0	397.6	398.0	398.6	399.1	398.6	398.0	397.6
160°	402.7	402.3	401.9	401.9	402.3	402.7	403.1	403.5	403.1	402.7	402.3
162.5°	406.4	406.0	405.8	405.8	406.1	406.6	407.0	407.4	407.0	406.6	406.1
165°	411.3	411.1	410.9	411.0	411.4	411.8	412.3	412.6	412.3	411.8	411.4
167.5°	415.2	415.0	414.8	414.9	415.3	415.8	416.1	416.5	416.1	415.8	415.3
170°	417.3	417.1	417.0	417.1	417.5	417.9	418.3	418.8	418.3	417.9	417.5
172.5°	418.7	418.6	418.4	418.6	419.0	419.3	419.8	420.2	419.8	419.3	419.0
175°	420.3	420.2	420.0	420.2	420.7	421.1	421.6	422.1	421.6	421.1	420.7
177.5°	420.8	420.8	420.8	420.8	421.2	421.6	422.0	422.4	422.0	421.6	421.2
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331285-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	903.8	902.1	896.2	893.1	888.1	883.3	880.1	881.6	882.7	882.1	881.3
5°	877.9	871.2	861.0	852.2	845.8	834.2	829.3	826.9	824.7	822.3	819.8
7.5°	847.1	836.5	821.9	809.4	797.5	783.1	774.9	769.9	764.8	759.2	754.3
10°	825.1	810.3	794.8	777.2	763.2	750.1	738.5	730.8	723.7	717.0	712.1
12.5°	802.0	784.9	765.8	741.8	726.2	707.6	705.9	692.2	681.2	677.0	671.3
15°	765.3	741.3	717.0	688.5	676.2	659.3	648.8	638.2	628.7	622.0	620.2
17.5°	723.5	692.5	668.4	647.9	627.7	610.4	600.7	592.2	584.4	575.4	574.3
20°	691.6	665.0	638.6	620.6	599.8	582.2	570.2	561.8	555.1	549.8	545.3
22.5°	661.6	632.3	608.1	588.4	568.0	553.7	544.3	536.2	530.7	524.8	520.5
25°	613.2	590.3	563.9	541.8	524.8	515.7	507.9	500.9	497.4	493.5	488.6
27.5°	570.9	545.4	520.8	503.6	488.7	480.6	475.1	470.3	467.0	464.8	461.9
30°	541.0	515.3	496.0	479.1	466.7	458.6	455.2	452.3	448.5	447.0	445.6
32.5°	512.3	489.2	472.6	458.0	446.2	440.9	437.7	435.2	432.2	430.7	427.9
35°	471.6	452.3	436.1	428.0	418.5	414.0	411.5	407.9	405.2	403.8	403.4
37.5°	433.5	416.6	406.0	395.6	391.5	388.7	385.4	383.0	382.1	381.9	381.5
40°	408.7	394.9	385.4	377.0	375.2	371.0	368.2	366.1	366.1	366.5	366.1
42.5°	386.2	373.8	365.4	358.2	356.1	353.5	350.7	350.6	351.2	352.3	351.2
45°	352.0	343.2	337.2	333.7	329.8	327.3	327.0	328.1	328.4	328.8	329.8
47.5°	320.6	314.7	309.3	305.5	303.8	303.3	302.9	304.7	306.4	307.1	308.7
50°	302.0	295.3	290.8	288.3	286.9	286.2	286.9	289.0	290.4	292.2	293.2
52.5°	281.2	276.4	273.3	271.4	270.8	271.3	271.4	273.8	276.1	276.6	277.2
55°	252.4	248.8	248.2	245.0	246.4	246.0	247.8	249.2	251.3	253.4	253.8
57.5°	223.7	220.8	219.0	219.2	219.6	221.2	222.6	225.2	227.4	229.6	229.9
60°	204.5	203.1	202.1	202.1	202.7	204.9	206.6	209.1	210.5	211.9	212.9
62.5°	187.1	185.7	184.5	185.1	187.0	188.2	190.3	191.6	193.0	194.4	194.9
65°	159.5	158.7	159.9	160.5	160.9	162.6	165.1	166.2	167.6	168.2	170.7
67.5°	134.0	134.2	134.0	135.1	137.0	137.5	139.8	142.3	142.6	143.9	145.5
70°	116.9	117.5	118.3	118.9	120.7	121.4	123.2	124.2	125.6	126.7	127.8
72.5°	101.1	101.2	102.0	101.8	103.3	104.8	106.3	107.4	108.8	110.1	111.1
75°	77.8	77.8	78.5	78.9	80.6	82.4	82.0	82.8	84.2	85.6	86.2
77.5°	56.8	56.1	56.8	57.1	57.7	59.2	59.5	60.5	62.1	61.6	62.4
80°	43.3	42.2	43.3	43.6	43.6	45.4	45.4	46.1	47.1	46.1	47.1
82.5°	30.9	30.4	31.2	31.3	31.9	31.9	32.4	32.6	33.6	33.2	33.6
85°	15.5	15.2	15.5	15.2	15.5	15.8	15.8	15.5	15.5	16.2	15.2
87.5°	5.5	5.3	5.1	5.2	5.1	4.9	4.7	4.7	4.8	4.3	4.3
90°	3.3	4.0	4.4	5.0	5.6	6.1	6.4	6.8	7.1	7.4	7.7
92.5°	5.8	6.0	6.2	6.5	6.8	7.1	7.3	7.4	7.6	7.7	7.9
95°	10.8	10.0	10.5	10.9	11.4	11.9	12.3	12.5	12.9	13.2	13.4
97.5°	14.1	11.5	12.6	13.7	14.8	15.9	16.2	16.5	16.7	17.0	17.2
100°	16.9	12.7	13.9	15.1	16.2	17.3	17.9	18.5	19.0	19.5	19.9
102.5°	62.2	56.4	46.8	37.1	27.5	17.8	18.6	19.2	20.0	20.6	21.1
105°	100.8	92.6	74.1	55.6	37.0	18.6	19.3	20.1	20.8	21.6	22.1
107.5°	125.0	114.7	92.6	70.4	48.2	26.0	25.3	24.5	23.8	23.0	22.7
110°	140.7	131.6	112.1	92.5	72.9	53.3	46.6	39.8	33.0	26.2	23.0



TEST NUMBER: P331285-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	155.6	153.8	149.0	144.2	139.3	134.5	109.8	85.1	60.4	35.7	23.5
115°	179.8	181.3	182.9	184.6	186.3	188.0	156.7	125.4	94.0	62.6	44.5
117.5°	202.4	203.6	204.8	205.9	207.1	208.3	200.7	193.1	185.5	178.0	166.2
120°	217.4	218.5	219.7	220.9	222.2	223.4	224.2	225.0	225.8	226.6	222.4
122.5°	231.3	232.4	233.8	235.1	236.5	237.8	238.3	238.7	239.2	239.7	239.0
125°	251.3	252.4	253.6	255.0	256.2	257.5	258.0	258.4	258.9	259.4	259.8
127.5°	270.5	271.5	272.4	273.4	274.4	275.3	276.0	276.7	277.4	278.1	278.4
130°	282.9	283.8	284.6	285.3	286.1	286.8	287.5	288.2	289.0	289.7	290.1
132.5°	294.5	295.2	296.0	296.7	297.5	298.2	298.9	299.5	300.1	300.8	301.0
135°	310.9	311.8	312.4	313.0	313.6	314.2	314.9	315.6	316.2	316.9	317.2
137.5°	325.6	326.4	327.1	327.7	328.5	329.1	329.8	330.5	331.1	331.8	332.0
140°	335.3	335.9	336.7	337.4	338.2	338.8	339.5	340.1	340.7	341.3	341.5
142.5°	343.8	344.5	345.3	346.2	347.0	347.9	348.5	349.0	349.6	350.2	350.2
145°	355.3	355.9	357.0	358.3	359.4	360.5	361.0	361.5	361.9	362.4	362.5
147.5°	366.6	367.0	368.2	369.4	370.5	371.6	371.9	372.3	372.7	373.1	373.1
150°	373.5	373.9	374.9	376.1	377.1	378.2	378.6	379.0	379.4	379.8	379.8
152.5°	379.9	380.1	381.2	382.2	383.2	384.3	384.7	385.1	385.5	385.9	385.9
155°	389.2	389.3	390.1	390.9	391.7	392.5	392.9	393.3	393.7	394.2	394.1
157.5°	397.0	397.1	397.7	398.2	398.8	399.4	399.8	400.3	400.8	401.1	401.1
160°	401.9	401.9	402.3	402.7	403.1	403.5	403.9	404.4	404.7	405.1	405.1
162.5°	405.8	405.8	406.0	406.4	406.8	407.2	407.6	408.0	408.5	409.0	409.0
165°	411.0	410.9	411.1	411.3	411.5	411.7	412.2	412.6	413.1	413.6	413.6
167.5°	414.9	414.8	415.0	415.2	415.4	415.6	416.0	416.5	417.0	417.5	417.4
170°	417.1	417.0	417.1	417.3	417.4	417.5	418.0	418.5	419.0	419.4	419.3
172.5°	418.6	418.4	418.6	418.7	418.9	419.0	419.4	419.9	420.4	420.8	420.8
175°	420.2	420.0	420.2	420.3	420.5	420.6	421.0	421.5	422.0	422.4	422.4
177.5°	420.8	420.8	420.8	420.8	420.8	420.9	421.3	421.7	422.1	422.4	422.4
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331285-830  
 CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	878.4	877.9	877.9	875.3	877.9	877.9	878.4	881.3	882.1	882.7	881.6
5°	814.9	813.8	812.1	813.8	812.1	813.8	814.9	819.8	822.3	824.7	826.9
7.5°	752.1	747.8	747.2	743.0	747.2	747.8	752.1	754.3	759.2	764.8	769.9
10°	706.2	703.3	702.9	696.3	702.9	703.3	706.2	712.1	717.0	723.7	730.8
12.5°	671.2	664.4	665.8	661.9	665.8	664.4	671.2	671.3	677.0	681.2	692.2
15°	610.7	610.7	609.4	603.3	609.4	610.7	610.7	620.2	622.0	628.7	638.2
17.5°	567.3	566.6	563.2	564.9	563.2	566.6	567.3	574.3	575.4	584.4	592.2
20°	541.4	539.2	535.1	535.1	535.1	539.2	541.4	545.3	549.8	555.1	561.8
22.5°	516.9	516.7	512.3	513.7	512.3	516.7	516.9	520.5	524.8	530.7	536.2
25°	488.2	485.4	483.3	484.4	483.3	485.4	488.2	488.6	493.5	497.4	500.9
27.5°	461.1	459.5	459.4	456.5	459.4	459.5	461.1	461.9	464.8	467.0	470.3
30°	445.3	441.8	442.4	440.7	442.4	441.8	445.3	445.6	447.0	448.5	452.3
32.5°	427.3	426.0	425.3	423.8	425.3	426.0	427.3	427.9	430.7	432.2	435.2
35°	402.7	403.0	401.2	402.0	401.2	403.0	402.7	403.4	403.8	405.2	407.9
37.5°	381.3	382.4	381.5	381.7	381.5	382.4	381.3	381.5	381.9	382.1	383.0
40°	367.1	367.1	367.1	368.2	367.1	367.1	367.1	366.1	366.5	366.1	366.1
42.5°	353.6	353.1	352.5	352.4	352.5	353.1	353.6	351.2	352.3	351.2	350.6
45°	330.5	331.6	332.0	330.2	332.0	331.6	330.5	329.8	328.8	328.4	328.1
47.5°	309.6	309.7	309.6	311.1	309.6	309.7	309.6	308.7	307.1	306.4	304.7
50°	295.0	294.3	295.0	294.3	295.0	294.3	295.0	293.2	292.2	290.4	289.0
52.5°	279.5	279.7	279.2	279.1	279.2	279.7	279.5	277.2	276.6	276.1	273.8
55°	255.2	255.9	255.5	255.5	255.5	255.9	255.2	253.8	253.4	251.3	249.2
57.5°	230.1	230.7	231.2	229.6	231.2	230.7	230.1	229.9	229.6	227.4	225.2
60°	212.6	214.3	214.1	213.3	214.1	214.3	212.6	212.9	211.9	210.5	209.1
62.5°	196.5	197.2	197.1	197.0	197.1	197.2	196.5	194.9	194.4	193.0	191.6
65°	171.7	172.5	171.4	172.5	171.4	172.5	171.7	170.7	168.2	167.6	166.2
67.5°	145.1	145.3	146.1	146.6	146.1	145.3	145.1	145.5	143.9	142.6	142.3
70°	128.5	128.1	129.2	130.3	129.2	128.1	128.5	127.8	126.7	125.6	124.2
72.5°	111.0	111.8	111.4	112.3	111.4	111.8	111.0	111.1	110.1	108.8	107.4
75°	85.6	86.6	86.2	87.3	86.2	86.6	85.6	86.2	85.6	84.2	82.8
77.5°	61.8	61.9	61.8	62.4	61.8	61.9	61.8	62.4	61.6	62.1	60.5
80°	47.1	46.5	45.7	47.1	45.7	46.5	47.1	47.1	46.1	47.1	46.1
82.5°	32.8	33.3	32.5	32.5	32.5	33.3	32.8	33.6	33.2	33.6	32.6
85°	15.2	14.8	14.0	14.0	14.0	14.8	15.2	15.2	16.2	15.5	15.5
87.5°	4.3	4.1	4.1	3.9	4.1	4.1	4.3	4.3	4.3	4.8	4.7
90°	7.8	7.9	8.1	8.2	8.1	7.9	7.8	7.7	7.4	7.1	6.8
92.5°	8.0	8.1	8.1	8.2	8.1	8.1	8.0	7.9	7.7	7.6	7.4
95°	13.3	13.2	13.2	13.1	13.2	13.2	13.3	13.4	13.2	12.9	12.5
97.5°	17.2	17.3	17.4	17.5	17.4	17.3	17.2	17.2	17.0	16.7	16.5
100°	20.0	20.2	20.3	20.5	20.3	20.2	20.0	19.9	19.5	19.0	18.5
102.5°	21.3	21.5	21.7	21.9	21.7	21.5	21.3	21.1	20.6	20.0	19.2
105°	22.3	22.6	22.9	23.2	22.9	22.6	22.3	22.1	21.6	20.8	20.1
107.5°	23.0	23.3	23.6	23.8	23.6	23.3	23.0	22.7	23.0	23.8	24.5
110°	23.3	23.6	23.8	24.0	23.8	23.6	23.3	23.0	26.2	33.0	39.8



TEST NUMBER: P331285-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	23.7	23.8	24.1	24.3	24.1	23.8	23.7	23.5	35.7	60.4	85.1
115°	39.6	34.8	29.9	25.0	29.9	34.8	39.6	44.5	62.6	94.0	125.4
117.5°	150.1	134.1	118.1	102.1	118.1	134.1	150.1	166.2	178.0	185.5	193.1
120°	213.3	204.2	195.0	185.9	195.0	204.2	213.3	222.4	226.6	225.8	225.0
122.5°	237.3	235.5	233.8	232.0	233.8	235.5	237.3	239.0	239.7	239.2	238.7
125°	260.0	260.1	260.3	260.5	260.3	260.1	260.0	259.8	259.4	258.9	258.4
127.5°	278.5	278.5	278.5	278.6	278.5	278.5	278.5	278.4	278.1	277.4	276.7
130°	290.0	289.9	289.9	289.8	289.9	289.9	290.0	290.1	289.7	289.0	288.2
132.5°	301.0	301.0	300.9	300.8	300.9	301.0	301.0	301.0	300.8	300.1	299.5
135°	317.1	316.9	316.8	316.6	316.8	316.9	317.1	317.2	316.9	316.2	315.6
137.5°	331.8	331.6	331.3	331.1	331.3	331.6	331.8	332.0	331.8	331.1	330.5
140°	341.1	340.8	340.4	340.1	340.4	340.8	341.1	341.5	341.3	340.7	340.1
142.5°	349.9	349.6	349.2	348.8	349.2	349.6	349.9	350.2	350.2	349.6	349.0
145°	362.1	361.8	361.5	361.1	361.5	361.8	362.1	362.5	362.4	361.9	361.5
147.5°	372.8	372.5	372.2	371.9	372.2	372.5	372.8	373.1	373.1	372.7	372.3
150°	379.6	379.2	378.8	378.5	378.8	379.2	379.6	379.8	379.8	379.4	379.0
152.5°	385.4	385.0	384.6	384.1	384.6	385.0	385.4	385.9	385.9	385.5	385.1
155°	393.5	393.0	392.5	391.9	392.5	393.0	393.5	394.1	394.2	393.7	393.3
157.5°	400.6	400.1	399.5	399.1	399.5	400.1	400.6	401.1	401.1	400.8	400.3
160°	404.6	404.2	403.7	403.2	403.7	404.2	404.6	405.1	405.1	404.7	404.4
162.5°	408.3	407.7	407.2	406.6	407.2	407.7	408.3	409.0	409.0	408.5	408.0
165°	413.1	412.6	412.2	411.7	412.2	412.6	413.1	413.6	413.6	413.1	412.6
167.5°	416.8	416.1	415.6	414.9	415.6	416.1	416.8	417.4	417.5	417.0	416.5
170°	418.8	418.1	417.5	416.9	417.5	418.1	418.8	419.3	419.4	419.0	418.5
172.5°	420.2	419.6	419.0	418.4	419.0	419.6	420.2	420.8	420.8	420.4	419.9
175°	421.7	421.0	420.3	419.6	420.3	421.0	421.7	422.4	422.4	422.0	421.5
177.5°	421.9	421.4	420.9	420.5	420.9	421.4	421.9	422.4	422.4	422.1	421.7
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331285-830  
 CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	880.1	883.3	888.1	893.1	896.2	902.1	903.8	906.6	909.2	915.0	921.2
5°	829.3	834.2	845.8	852.2	861.0	871.2	877.9	885.0	892.7	906.1	918.4
7.5°	774.9	783.1	797.5	809.4	821.9	836.5	847.1	861.0	872.5	891.4	909.5
10°	738.5	750.1	763.2	777.2	794.8	810.3	825.1	842.7	856.8	879.3	900.4
12.5°	705.9	707.6	726.2	741.8	765.8	784.9	802.0	824.6	838.5	865.3	887.5
15°	648.8	659.3	676.2	688.5	717.0	741.3	765.3	788.8	804.6	837.7	867.0
17.5°	600.7	610.4	627.7	647.9	668.4	692.5	723.5	748.4	769.9	807.7	842.3
20°	570.2	582.2	599.8	620.6	638.6	665.0	691.6	720.2	743.4	786.0	826.5
22.5°	544.3	553.7	568.0	588.4	608.1	632.3	661.6	692.6	717.0	762.9	804.0
25°	507.9	515.7	524.8	541.8	563.9	590.3	613.2	647.3	682.9	725.9	775.4
27.5°	475.1	480.6	488.7	503.6	520.8	545.4	570.9	603.2	639.0	685.6	738.0
30°	455.2	458.6	466.7	479.1	496.0	515.3	541.0	572.0	608.6	655.8	707.8
32.5°	437.7	440.9	446.2	458.0	472.6	489.2	512.3	543.3	578.2	624.5	682.2
35°	411.5	414.0	418.5	428.0	436.1	452.3	471.6	499.8	532.5	576.9	636.8
37.5°	385.4	388.7	391.5	395.6	406.0	416.6	433.5	457.2	489.4	534.1	591.2
40°	368.2	371.0	375.2	377.0	385.4	394.9	408.7	430.5	462.9	503.7	559.3
42.5°	350.7	353.5	356.1	358.2	365.4	373.8	386.2	404.9	433.6	473.3	528.4
45°	327.0	327.3	329.8	333.7	337.2	343.2	352.0	368.2	390.4	427.7	477.7
47.5°	302.9	303.3	303.8	305.5	309.3	314.7	320.6	333.8	353.6	383.4	432.1
50°	286.9	286.2	286.9	288.3	290.8	295.3	302.0	311.5	327.7	355.5	400.2
52.5°	271.4	271.3	270.8	271.4	273.3	276.4	281.2	289.3	303.8	329.3	368.7
55°	247.8	246.0	246.4	245.0	248.2	248.8	252.4	259.1	271.7	289.4	326.3
57.5°	222.6	221.2	219.6	219.2	219.0	220.8	223.7	228.9	238.7	254.1	284.1
60°	206.6	204.9	202.7	202.1	202.1	203.1	204.5	208.4	217.5	231.3	255.9
62.5°	190.3	188.2	187.0	185.1	184.5	185.7	187.1	189.8	196.4	209.3	230.5
65°	165.1	162.6	160.9	160.5	159.9	158.7	159.5	162.3	167.6	177.8	194.6
67.5°	139.8	137.5	137.0	135.1	134.0	134.2	134.0	136.5	139.6	148.4	161.0
70°	123.2	121.4	120.7	118.9	118.3	117.5	116.9	118.9	122.2	129.5	140.4
72.5°	106.3	104.8	103.3	101.8	102.0	101.2	101.1	102.4	105.0	111.8	120.2
75°	82.0	82.4	80.6	78.9	78.5	77.8	77.8	78.9	79.9	85.2	91.9
77.5°	59.5	59.2	57.7	57.1	56.8	56.1	56.8	57.5	58.1	61.6	66.5
80°	45.4	45.4	43.6	43.6	43.3	42.2	43.3	42.6	44.0	47.5	51.1
82.5°	32.4	31.9	31.9	31.3	31.2	30.4	30.9	31.6	32.1	34.6	36.7
85°	15.8	15.8	15.5	15.2	15.5	15.2	15.5	15.8	16.2	17.2	19.0
87.5°	4.7	4.9	5.1	5.2	5.1	5.3	5.5	5.6	6.0	6.1	6.2
90°	6.4	6.1	5.6	5.0	4.4	4.0	3.3	2.5	1.8	1.0	0.3
92.5°	7.3	7.1	6.8	6.5	6.2	6.0	5.8	5.9	6.0	6.1	6.1
95°	12.3	11.9	11.4	10.9	10.5	10.0	10.8	13.1	15.4	17.5	19.8
97.5°	16.2	15.9	14.8	13.7	12.6	11.5	14.1	20.5	26.7	33.0	39.3
100°	17.9	17.3	16.2	15.1	13.9	12.7	16.9	26.1	35.3	44.7	53.9
102.5°	18.6	17.8	27.5	37.1	46.8	56.4	62.2	64.2	66.1	68.1	70.0
105°	19.3	18.6	37.0	55.6	74.1	92.6	100.8	98.8	96.7	94.6	92.7
107.5°	25.3	26.0	48.2	70.4	92.6	114.7	125.0	123.4	121.7	120.1	118.4
110°	46.6	53.3	72.9	92.5	112.1	131.6	140.7	139.3	137.9	136.4	135.0



TEST NUMBER: P331285-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	109.8	134.5	139.3	144.2	149.0	153.8	155.6	154.4	153.2	151.8	150.6
115°	156.7	188.0	186.3	184.6	182.9	181.3	179.8	178.7	177.6	176.3	175.2
117.5°	200.7	208.3	207.1	205.9	204.8	203.6	202.4	201.1	199.8	198.5	197.3
120°	224.2	223.4	222.2	220.9	219.7	218.5	217.4	216.4	215.4	214.3	213.3
122.5°	238.3	237.8	236.5	235.1	233.8	232.4	231.3	230.2	229.1	228.1	227.0
125°	258.0	257.5	256.2	255.0	253.6	252.4	251.3	250.4	249.5	248.6	247.8
127.5°	276.0	275.3	274.4	273.4	272.4	271.5	270.5	269.6	268.5	267.6	266.6
130°	287.5	286.8	286.1	285.3	284.6	283.8	282.9	281.8	280.7	279.7	278.5
132.5°	298.9	298.2	297.5	296.7	296.0	295.2	294.5	293.5	292.6	291.6	290.8
135°	314.9	314.2	313.6	313.0	312.4	311.8	310.9	309.8	308.8	307.6	306.6
137.5°	329.8	329.1	328.5	327.7	327.1	326.4	325.6	324.9	324.1	323.4	322.6
140°	339.5	338.8	338.2	337.4	336.7	335.9	335.3	334.7	334.1	333.7	333.1
142.5°	348.5	347.9	347.0	346.2	345.3	344.5	343.8	343.4	342.8	342.3	341.9
145°	361.0	360.5	359.4	358.3	357.0	355.9	355.3	355.4	355.5	355.6	355.6
147.5°	371.9	371.6	370.5	369.4	368.2	367.0	366.6	366.8	367.1	367.4	367.7
150°	378.6	378.2	377.1	376.1	374.9	373.9	373.5	374.0	374.5	374.9	375.4
152.5°	384.7	384.3	383.2	382.2	381.2	380.1	379.9	380.4	381.0	381.5	382.0
155°	392.9	392.5	391.7	390.9	390.1	389.3	389.2	389.7	390.4	391.0	391.6
157.5°	399.8	399.4	398.8	398.2	397.7	397.1	397.0	397.6	398.0	398.6	399.1
160°	403.9	403.5	403.1	402.7	402.3	401.9	401.9	402.3	402.7	403.1	403.5
162.5°	407.6	407.2	406.8	406.4	406.0	405.8	405.8	406.1	406.6	407.0	407.4
165°	412.2	411.7	411.5	411.3	411.1	410.9	411.0	411.4	411.8	412.3	412.6
167.5°	416.0	415.6	415.4	415.2	415.0	414.8	414.9	415.3	415.8	416.1	416.5
170°	418.0	417.5	417.4	417.3	417.1	417.0	417.1	417.5	417.9	418.3	418.8
172.5°	419.4	419.0	418.9	418.7	418.6	418.4	418.6	419.0	419.3	419.8	420.2
175°	421.0	420.6	420.5	420.3	420.2	420.0	420.2	420.7	421.1	421.6	422.1
177.5°	421.3	420.9	420.8	420.8	420.8	420.8	420.8	421.2	421.6	422.0	422.4
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331285-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	920.7	922.1	926.6	931.1	936.1	937.5	939.8	937.8	937.3	942.6	946.6
5°	923.3	929.6	942.0	953.2	962.7	969.4	976.5	979.3	984.6	991.9	1001.1
7.5°	920.3	932.6	952.1	968.5	986.3	999.2	1009.3	1017.9	1028.2	1042.3	1057.5
10°	917.0	933.5	957.1	977.1	999.0	1015.5	1029.3	1042.6	1058.1	1077.5	1097.5
12.5°	910.8	930.4	959.9	983.6	1011.6	1027.9	1046.4	1075.3	1091.9	1118.9	1147.1
15°	898.3	920.1	961.3	990.5	1022.2	1053.2	1087.3	1114.7	1142.3	1158.1	1197.9
17.5°	879.8	911.8	957.4	991.6	1031.8	1080.5	1118.9	1150.1	1181.8	1207.4	1227.4
20°	864.9	899.8	951.8	992.7	1040.5	1093.0	1137.0	1168.7	1196.1	1217.6	1229.9
22.5°	846.0	889.9	940.6	988.4	1049.5	1101.5	1147.6	1172.6	1195.5	1206.0	1210.7
25°	816.2	869.1	926.4	984.9	1053.9	1108.8	1151.0	1166.2	1172.9	1162.6	1145.8
27.5°	784.3	843.1	910.2	978.3	1051.2	1104.0	1134.3	1131.9	1120.6	1087.5	1061.1
30°	760.3	825.1	897.2	971.5	1044.7	1096.1	1113.7	1096.1	1070.4	1033.5	995.8
32.5°	735.3	802.3	883.4	962.0	1032.9	1078.1	1081.9	1051.6	1011.8	969.9	922.8
35°	697.3	769.9	857.4	940.6	1007.8	1036.3	1019.4	965.9	918.7	861.4	797.3
37.5°	654.4	734.5	822.4	909.2	970.2	977.6	935.7	879.3	812.8	745.4	670.0
40°	622.4	707.2	797.7	885.2	939.1	931.4	877.9	816.0	736.7	654.4	584.3
42.5°	593.6	678.4	770.6	856.6	899.8	878.4	816.0	739.9	654.8	577.2	513.1
45°	543.8	631.1	725.5	808.5	833.2	794.8	712.1	627.6	543.8	479.1	428.4
47.5°	495.6	581.8	675.2	748.3	757.1	705.4	615.0	528.1	456.1	403.3	367.6
50°	460.1	546.7	639.2	704.4	701.5	639.2	546.3	463.5	403.4	360.8	336.9
52.5°	428.2	510.0	599.0	658.2	643.3	575.3	486.6	413.2	363.7	330.4	308.7
55°	378.7	454.4	538.9	586.4	559.0	483.6	408.7	349.5	312.9	287.9	271.1
57.5°	329.6	400.6	472.9	502.2	471.8	402.3	339.8	296.9	269.4	250.8	239.9
60°	299.2	361.2	425.6	450.9	414.6	352.7	303.4	265.0	242.9	227.7	217.9
62.5°	268.8	324.2	385.0	398.8	365.6	313.3	269.7	237.7	219.5	206.0	196.8
65°	227.4	272.8	319.0	328.1	297.5	256.9	222.4	201.7	185.5	175.7	168.2
67.5°	186.5	222.9	255.6	263.0	236.2	208.1	183.1	165.1	154.1	145.9	139.7
70°	162.3	191.1	217.9	223.9	202.4	177.4	158.4	143.9	134.1	127.1	121.1
72.5°	136.7	160.7	182.9	187.0	169.5	150.3	134.8	123.4	114.7	110.2	104.4
75°	104.5	118.7	135.9	137.0	125.4	113.7	101.7	94.3	89.7	84.2	81.3
77.5°	73.8	84.8	94.7	96.6	89.7	81.8	75.1	69.3	65.4	62.8	60.2
80°	56.4	65.1	69.4	71.8	66.9	61.3	57.4	53.5	51.1	49.3	47.5
82.5°	40.2	45.7	49.7	51.6	48.8	45.5	41.6	39.4	37.5	36.0	35.4
85°	20.5	22.9	25.4	26.0	25.4	23.9	21.9	21.9	20.7	20.5	20.5
87.5°	7.3	8.5	8.7	9.7	9.2	9.3	9.4	9.2	9.1	8.9	8.7
90°	1.0	1.8	2.5	3.3	4.0	4.4	5.0	5.6	6.1	6.4	6.8
92.5°	6.1	6.0	5.9	5.8	6.0	6.2	6.5	6.8	7.1	7.3	7.4
95°	17.5	15.4	13.1	10.8	10.0	10.5	10.9	11.4	11.9	12.3	12.5
97.5°	33.0	26.7	20.5	14.1	11.5	12.6	13.7	14.8	15.9	16.2	16.5
100°	44.7	35.3	26.1	16.9	12.7	13.9	15.1	16.2	17.3	17.9	18.5
102.5°	68.1	66.1	64.2	62.2	56.4	46.8	37.1	27.5	17.8	18.6	19.2
105°	94.6	96.7	98.8	100.8	92.6	74.1	55.6	37.0	18.6	19.3	20.1
107.5°	120.1	121.7	123.4	125.0	114.7	92.6	70.4	48.2	26.0	25.3	24.5
110°	136.4	137.9	139.3	140.7	131.6	112.1	92.5	72.9	53.3	46.6	39.8





TEST NUMBER: P331285-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	151.8	153.2	154.4	155.6	153.8	149.0	144.2	139.3	134.5	109.8	85.1
115°	176.3	177.6	178.7	179.8	181.3	182.9	184.6	186.3	188.0	156.7	125.4
117.5°	198.5	199.8	201.1	202.4	203.6	204.8	205.9	207.1	208.3	200.7	193.1
120°	214.3	215.4	216.4	217.4	218.5	219.7	220.9	222.2	223.4	224.2	225.0
122.5°	228.1	229.1	230.2	231.3	232.4	233.8	235.1	236.5	237.8	238.3	238.7
125°	248.6	249.5	250.4	251.3	252.4	253.6	255.0	256.2	257.5	258.0	258.4
127.5°	267.6	268.5	269.6	270.5	271.5	272.4	273.4	274.4	275.3	276.0	276.7
130°	279.7	280.7	281.8	282.9	283.8	284.6	285.3	286.1	286.8	287.5	288.2
132.5°	291.6	292.6	293.5	294.5	295.2	296.0	296.7	297.5	298.2	298.9	299.5
135°	307.6	308.8	309.8	310.9	311.8	312.4	313.0	313.6	314.2	314.9	315.6
137.5°	323.4	324.1	324.9	325.6	326.4	327.1	327.7	328.5	329.1	329.8	330.5
140°	333.7	334.1	334.7	335.3	335.9	336.7	337.4	338.2	338.8	339.5	340.1
142.5°	342.3	342.8	343.4	343.8	344.5	345.3	346.2	347.0	347.9	348.5	349.0
145°	355.6	355.5	355.4	355.3	355.9	357.0	358.3	359.4	360.5	361.0	361.5
147.5°	367.4	367.1	366.8	366.6	367.0	368.2	369.4	370.5	371.6	371.9	372.3
150°	374.9	374.5	374.0	373.5	373.9	374.9	376.1	377.1	378.2	378.6	379.0
152.5°	381.5	381.0	380.4	379.9	380.1	381.2	382.2	383.2	384.3	384.7	385.1
155°	391.0	390.4	389.7	389.2	389.3	390.1	390.9	391.7	392.5	392.9	393.3
157.5°	398.6	398.0	397.6	397.0	397.1	397.7	398.2	398.8	399.4	399.8	400.3
160°	403.1	402.7	402.3	401.9	401.9	402.3	402.7	403.1	403.5	403.9	404.4
162.5°	407.0	406.6	406.1	405.8	405.8	406.0	406.4	406.8	407.2	407.6	408.0
165°	412.3	411.8	411.4	411.0	410.9	411.1	411.3	411.5	411.7	412.2	412.6
167.5°	416.1	415.8	415.3	414.9	414.8	415.0	415.2	415.4	415.6	416.0	416.5
170°	418.3	417.9	417.5	417.1	417.0	417.1	417.3	417.4	417.5	418.0	418.5
172.5°	419.8	419.3	419.0	418.6	418.4	418.6	418.7	418.9	419.0	419.4	419.9
175°	421.6	421.1	420.7	420.2	420.0	420.2	420.3	420.5	420.6	421.0	421.5
177.5°	422.0	421.6	421.2	420.8	420.8	420.8	420.8	420.8	420.9	421.3	421.7
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1	421.1



TEST NUMBER: P331285-830  
 CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	915.9	915.9	915.9	915.9	915.9	915.9	915.9
2.5°	950.0	953.9	953.9	954.5	958.9	958.5	958.2
5°	1011.0	1016.9	1017.7	1024.0	1028.2	1026.8	1022.9
7.5°	1068.5	1079.6	1088.1	1092.8	1098.3	1101.7	1100.2
10°	1114.1	1130.3	1140.1	1146.8	1154.9	1160.9	1158.8
12.5°	1155.5	1174.8	1188.3	1199.8	1200.8	1208.5	1203.2
15°	1220.0	1240.5	1242.6	1251.0	1257.7	1257.0	1257.4
17.5°	1241.3	1247.9	1249.2	1249.4	1249.5	1247.1	1241.7
20°	1233.8	1231.3	1225.3	1220.8	1212.7	1211.5	1204.6
22.5°	1197.7	1189.9	1174.9	1165.0	1152.4	1149.1	1147.1
25°	1126.7	1109.5	1085.5	1062.7	1056.3	1044.1	1047.5
27.5°	1029.4	1002.5	976.6	958.0	941.2	922.7	928.0
30°	960.9	930.7	894.1	865.9	848.0	830.4	827.2
32.5°	879.3	834.9	794.1	769.3	741.8	730.7	718.5
35°	738.5	695.2	654.7	619.9	599.8	584.3	570.2
37.5°	611.8	562.0	529.3	501.1	486.6	477.8	479.9
40°	533.3	489.7	465.7	444.2	430.8	424.5	425.9
42.5°	469.7	437.0	417.3	402.6	393.1	389.6	388.7
45°	397.4	379.1	362.9	354.5	349.9	346.0	343.6
47.5°	348.2	333.2	324.0	319.1	315.0	311.1	311.0
50°	318.6	308.7	302.4	297.1	293.9	291.1	293.6
52.5°	296.1	287.0	280.7	276.0	274.8	272.2	272.2
55°	262.6	255.5	251.0	246.8	244.7	243.3	241.5
57.5°	232.1	225.5	221.3	218.6	214.6	213.2	212.6
60°	210.5	205.2	201.0	197.5	195.7	192.9	192.9
62.5°	190.5	185.2	181.3	178.6	175.7	174.6	174.8
65°	161.6	157.3	153.4	150.6	150.0	147.9	148.5
67.5°	135.0	132.1	128.1	126.5	125.2	124.0	123.2
70°	117.3	114.4	112.3	110.2	109.1	109.1	109.1
72.5°	102.3	98.9	97.6	95.0	95.6	94.4	93.3
75°	79.2	77.1	76.1	74.9	73.2	73.2	73.2
77.5°	58.2	57.7	56.4	55.2	54.9	54.5	54.7
80°	45.1	44.7	44.0	44.0	43.3	43.0	42.2
82.5°	34.6	33.7	33.3	33.0	32.9	32.8	32.7
85°	19.7	19.0	19.0	19.3	18.7	18.7	19.0
87.5°	9.0	9.0	8.9	8.9	9.2	9.0	9.0
90°	7.1	7.4	7.7	7.8	7.9	8.1	8.2
92.5°	7.6	7.7	7.9	8.0	8.1	8.1	8.2
95°	12.9	13.2	13.4	13.3	13.2	13.2	13.1
97.5°	16.7	17.0	17.2	17.2	17.3	17.4	17.5
100°	19.0	19.5	19.9	20.0	20.2	20.3	20.5
102.5°	20.0	20.6	21.1	21.3	21.5	21.7	21.9
105°	20.8	21.6	22.1	22.3	22.6	22.9	23.2
107.5°	23.8	23.0	22.7	23.0	23.3	23.6	23.8
110°	33.0	26.2	23.0	23.3	23.6	23.8	24.0



TEST NUMBER: P331285-830

CATALOG NUMBER: SA2XXDIP-C485D330U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	60.4	35.7	23.5	23.7	23.8	24.1	24.3
115°	94.0	62.6	44.5	39.6	34.8	29.9	25.0
117.5°	185.5	178.0	166.2	150.1	134.1	118.1	102.1
120°	225.8	226.6	222.4	213.3	204.2	195.0	185.9
122.5°	239.2	239.7	239.0	237.3	235.5	233.8	232.0
125°	258.9	259.4	259.8	260.0	260.1	260.3	260.5
127.5°	277.4	278.1	278.4	278.5	278.5	278.5	278.6
130°	289.0	289.7	290.1	290.0	289.9	289.9	289.8
132.5°	300.1	300.8	301.0	301.0	301.0	300.9	300.8
135°	316.2	316.9	317.2	317.1	316.9	316.8	316.6
137.5°	331.1	331.8	332.0	331.8	331.6	331.3	331.1
140°	340.7	341.3	341.5	341.1	340.8	340.4	340.1
142.5°	349.6	350.2	350.2	349.9	349.6	349.2	348.8
145°	361.9	362.4	362.5	362.1	361.8	361.5	361.1
147.5°	372.7	373.1	373.1	372.8	372.5	372.2	371.9
150°	379.4	379.8	379.8	379.6	379.2	378.8	378.5
152.5°	385.5	385.9	385.9	385.4	385.0	384.6	384.1
155°	393.7	394.2	394.1	393.5	393.0	392.5	391.9
157.5°	400.8	401.1	401.1	400.6	400.1	399.5	399.1
160°	404.7	405.1	405.1	404.6	404.2	403.7	403.2
162.5°	408.5	409.0	409.0	408.3	407.7	407.2	406.6
165°	413.1	413.6	413.6	413.1	412.6	412.2	411.7
167.5°	417.0	417.5	417.4	416.8	416.1	415.6	414.9
170°	419.0	419.4	419.3	418.8	418.1	417.5	416.9
172.5°	420.4	420.8	420.8	420.2	419.6	419.0	418.4
175°	422.0	422.4	422.4	421.7	421.0	420.3	419.6
177.5°	422.1	422.4	422.4	421.9	421.4	420.9	420.5
180°	421.1	421.1	421.1	421.1	421.1	421.1	421.1

(END OF REPORT)