

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331649

Luminaire Tested: **SA2XXRDIP-C485D330U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331649
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D330U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2869.7 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 27.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331649

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331649

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	65	65	65	59
1	100	96	92	89	94	90	87	84	78	76	74	68	66	64	58	57	56	51
2	92	85	79	74	86	79	74	70	69	65	62	60	57	55	52	50	48	44
3	84	75	68	62	78	70	64	59	62	57	53	54	50	47	46	44	41	38
4	77	67	59	53	72	63	56	51	55	50	46	48	44	41	42	39	36	33
5	71	60	52	46	66	56	49	44	50	44	40	44	39	36	38	35	32	29
6	66	54	46	40	61	51	44	39	45	39	35	40	35	32	35	31	28	26
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	26	23	21
9	53	41	34	29	50	39	32	27	35	29	25	31	26	23	27	24	21	19
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	25	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13324	13324	13324
5°	13374	13157	13230
10°	13273	12942	12832
15°	13120	12558	12197
20°	12909	12010	11407
25°	12693	11389	10644
30°	12392	10750	9663
35°	12100	10054	8803
40°	11805	9335	7807
45°	11460	8526	6907
50°	11105	7709	6021
55°	10742	6832	5171
60°	10320	5909	4292
65°	9845	4963	3908
70°	9272	4088	3597
75°	8571	3724	3356
80°	7569	3329	3059
85°	5947	2631	2631



TEST NUMBER: P331649

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.2	2.7
10°-20°	212.1	7.4
20°-30°	297.8	10.4
30°-40°	324.8	11.3
40°-50°	298.6	10.4
50°-60°	234.5	8.2
60°-70°	152.9	5.3
70°-80°	78.8	2.7
80°-90°	22.1	0.8
90°-100°	26.5	0.9
100°-110°	82.4	2.9
110°-120°	140.8	4.9
120°-130°	185.2	6.5
130°-140°	207.9	7.2
140°-150°	203.8	7.1
150°-160°	171.0	6.0
160°-170°	113.4	4.0
170°-180°	39.6	1.4
0°-30°	587.2	20.5
0°-40°	912.0	31.8
0°-60°	1445.1	50.4
0°-90°	1699.0	59.2
90°-120°	249.8	8.7
90°-150°	846.7	29.5
90°-180°	1171.0	40.8
0°-180°	2869.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	825	825	825	825	825	
5°	825	821	812	818	816	78
15°	785	776	751	738	730	221
25°	712	687	639	610	598	327
35°	614	574	510	465	447	384
45°	502	450	373	322	302	387
55°	382	322	243	200	184	341
65°	258	197	130	106	102	255
75°	137	87	60	55	54	145
85°	32	17	14	14	14	38
90°	0	5	12	12	12	2
95°	18	22	23	23	22	21
105°	76	77	78	78	78	80
115°	141	143	143	142	141	140
125°	206	209	208	207	206	184
135°	266	270	271	270	269	205
145°	323	325	328	328	326	202
155°	369	370	371	373	372	170
165°	402	401	401	404	402	113
175°	418	417	416	418	416	40
180°	419	419	419	419	419	



TEST NUMBER: P331649

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	828.2	827.6	826.9	826.2	825.6	824.5	823.1	821.6	820.1	818.7	820.0
5°	825.2	824.4	823.6	822.8	821.9	820.4	818.3	816.1	814.0	811.8	813.3
7.5°	816.7	815.7	814.7	813.6	812.6	810.8	808.3	805.8	803.3	800.8	801.2
10°	809.6	808.4	807.2	806.1	804.9	802.7	799.4	796.0	792.7	789.4	788.9
12.5°	800.6	799.2	797.7	796.3	794.9	792.1	787.8	783.6	779.3	775.1	774.2
15°	784.9	783.1	781.3	779.4	777.6	773.9	768.2	762.6	757.0	751.3	748.2
17.5°	765.7	762.9	760.1	757.3	754.5	749.5	742.3	735.0	727.8	720.5	716.8
20°	751.3	748.0	744.7	741.4	738.0	732.2	723.9	715.6	707.3	699.0	694.9
22.5°	735.8	732.1	728.3	724.6	720.9	714.4	705.0	695.6	686.3	676.9	671.6
25°	712.5	707.2	701.9	696.5	691.2	683.1	672.1	661.2	650.2	639.3	632.5
27.5°	684.4	678.6	672.8	667.1	661.3	652.2	639.9	627.5	615.2	602.8	594.9
30°	664.7	658.4	652.1	645.8	639.5	629.7	616.4	603.1	589.8	576.6	568.1
32.5°	645.6	638.2	630.8	623.5	616.1	605.6	592.1	578.5	565.0	551.5	541.8
35°	613.9	605.4	597.0	588.5	580.0	568.5	553.9	539.3	524.7	510.1	499.6
37.5°	582.2	572.9	563.6	554.3	545.1	532.6	517.1	501.5	485.9	470.4	458.8
40°	560.1	550.2	540.2	530.3	520.3	507.3	491.2	475.1	459.0	442.9	431.1
42.5°	537.4	526.9	516.4	506.0	495.5	481.9	465.3	448.6	432.0	415.4	403.2
45°	501.9	490.8	479.6	468.5	457.4	443.1	425.7	408.3	390.8	373.4	361.6
47.5°	467.2	455.4	443.7	431.9	420.1	405.2	387.2	369.2	351.2	333.2	321.5
50°	442.1	430.3	418.6	406.8	395.0	380.0	361.7	343.5	325.2	306.9	295.5
52.5°	417.6	405.3	393.0	380.7	368.4	353.3	335.4	317.6	299.7	281.9	270.8
55°	381.6	368.7	355.7	342.8	329.9	314.4	296.5	278.6	260.6	242.7	232.8
57.5°	344.7	331.5	318.2	304.9	291.6	276.4	259.2	241.9	224.7	207.5	198.3
60°	319.6	306.4	293.1	279.8	266.5	251.4	234.3	217.2	200.1	183.0	174.5
62.5°	295.1	281.9	268.6	255.3	242.0	227.3	211.0	194.7	178.4	162.1	154.0
65°	257.7	244.2	230.8	217.3	203.9	189.7	174.8	159.8	144.9	129.9	124.3
67.5°	221.5	208.2	194.8	181.5	168.1	154.7	141.3	127.9	114.4	101.0	98.4
70°	196.4	183.5	170.5	157.6	144.6	132.4	121.0	109.5	98.1	86.6	85.0
72.5°	172.5	160.1	147.7	135.3	122.9	112.1	102.9	93.7	84.5	75.3	73.9
75°	137.4	125.8	114.2	102.6	90.9	82.3	76.7	71.0	65.4	59.7	58.6
77.5°	102.9	92.7	82.5	72.3	62.2	55.7	53.0	50.3	47.5	44.8	44.1
80°	81.4	72.9	64.5	56.0	47.5	42.5	40.8	39.2	37.5	35.8	35.2
82.5°	61.7	55.1	48.5	41.9	35.3	31.4	30.3	29.1	28.0	26.9	26.5
85°	32.1	28.6	25.1	21.7	18.2	16.2	15.7	15.2	14.7	14.2	14.2
87.5°	9.6	8.8	7.9	7.0	6.1	5.9	6.2	6.6	6.9	7.3	7.1
90°	0.4	1.3	2.2	3.2	4.1	5.5	7.2	8.9	10.6	12.4	12.2
92.5°	6.3	7.0	7.7	8.4	9.1	9.6	10.0	10.4	10.8	11.2	11.3
95°	18.4	19.2	19.9	20.7	21.5	22.0	22.1	22.3	22.5	22.6	22.6
97.5°	33.6	34.3	34.9	35.6	36.3	36.8	37.1	37.4	37.7	38.0	38.0
100°	44.9	45.5	46.1	46.8	47.4	47.8	48.0	48.3	48.5	48.8	48.8
102.5°	56.7	57.2	57.7	58.2	58.7	59.2	59.4	59.7	60.0	60.3	60.4
105°	76.0	76.2	76.4	76.7	76.9	77.1	77.3	77.4	77.6	77.7	77.9
107.5°	95.3	95.7	96.0	96.4	96.7	96.9	96.9	96.9	96.9	96.9	96.9
110°	107.8	108.2	108.7	109.2	109.6	109.9	109.9	109.9	109.9	109.9	109.9



TEST NUMBER: P331649

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.3	121.8	122.3	122.7	123.2	123.4	123.3	123.3	123.2	123.2	123.0
115°	141.3	141.8	142.3	142.7	143.2	143.4	143.2	143.0	142.9	142.7	142.7
117.5°	161.2	161.9	162.5	163.1	163.8	163.9	163.4	163.0	162.5	162.1	161.9
120°	174.5	175.2	175.8	176.4	177.0	177.0	176.4	175.8	175.2	174.5	174.5
122.5°	186.7	187.4	188.2	188.9	189.7	189.9	189.4	189.0	188.5	188.1	187.9
125°	205.6	206.3	207.0	207.7	208.4	208.7	208.4	208.2	208.0	207.7	207.5
127.5°	224.1	225.0	225.9	226.7	227.6	227.9	227.7	227.4	227.1	226.8	226.5
130°	235.7	236.7	237.7	238.7	239.7	240.2	240.0	239.9	239.7	239.5	239.4
132.5°	248.7	249.5	250.3	251.1	252.0	252.4	252.4	252.5	252.5	252.5	252.2
135°	266.0	266.9	267.8	268.6	269.5	270.0	270.2	270.3	270.5	270.6	270.5
137.5°	284.3	285.0	285.7	286.5	287.2	287.6	287.8	288.0	288.2	288.4	288.4
140°	295.4	296.1	296.8	297.5	298.2	298.7	299.1	299.5	299.9	300.3	300.3
142.5°	306.7	307.4	308.1	308.8	309.5	310.0	310.2	310.5	310.8	311.0	311.1
145°	322.9	323.5	324.0	324.6	325.1	325.6	326.1	326.6	327.0	327.5	327.6
147.5°	337.4	338.1	338.7	339.4	340.0	340.5	340.8	341.2	341.5	341.8	342.0
150°	347.3	347.8	348.2	348.7	349.2	349.6	349.9	350.2	350.5	350.8	351.1
152.5°	356.1	356.5	357.0	357.5	357.9	358.4	358.7	359.1	359.5	359.9	360.2
155°	369.2	369.4	369.7	369.9	370.1	370.4	370.6	370.8	371.1	371.3	371.7
157.5°	380.4	380.6	380.7	380.9	381.1	381.2	381.4	381.5	381.6	381.8	382.3
160°	387.2	387.4	387.5	387.7	387.8	388.0	388.0	388.1	388.2	388.3	388.7
162.5°	393.4	393.5	393.5	393.5	393.6	393.6	393.7	393.8	393.9	393.9	394.5
165°	401.7	401.6	401.5	401.5	401.4	401.3	401.3	401.3	401.3	401.3	401.9
167.5°	408.6	408.4	408.2	407.9	407.7	407.6	407.5	407.5	407.5	407.5	408.0
170°	412.3	412.1	411.8	411.6	411.4	411.2	411.1	411.0	411.0	410.9	411.4
172.5°	414.8	414.6	414.4	414.1	413.9	413.7	413.7	413.6	413.5	413.4	414.0
175°	418.0	417.7	417.5	417.2	417.0	416.8	416.7	416.5	416.3	416.2	416.7
177.5°	419.2	419.0	418.8	418.7	418.5	418.3	418.2	418.1	417.9	417.8	418.2
180°	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7



TEST NUMBER: P331649

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	821.3	822.7	824.0	824.5	824.3	824.0	823.7	823.5
5°	814.8	816.3	817.8	818.3	817.8	817.3	816.8	816.3
7.5°	801.6	802.0	802.5	802.3	801.4	800.5	799.7	798.8
10°	788.4	787.9	787.4	786.7	785.7	784.7	783.7	782.7
12.5°	773.3	772.4	771.5	770.2	768.5	766.9	765.2	763.6
15°	745.0	741.9	738.7	736.3	734.6	733.0	731.3	729.7
17.5°	713.0	709.3	705.5	702.2	699.4	696.5	693.7	690.8
20°	690.7	686.6	682.4	678.5	674.9	671.2	667.6	663.9
22.5°	666.2	660.9	655.6	651.5	648.8	646.1	643.4	640.6
25°	625.7	618.9	612.1	607.4	604.9	602.4	600.0	597.5
27.5°	587.0	579.0	571.1	565.2	561.2	557.3	553.3	549.4
30°	559.6	551.2	542.7	536.2	531.7	527.3	522.8	518.3
32.5°	532.1	522.5	512.8	505.9	501.7	497.5	493.2	489.0
35°	489.2	478.7	468.3	461.2	457.6	453.9	450.3	446.6
37.5°	447.3	435.8	424.3	416.4	412.3	408.1	403.9	399.7
40°	419.3	407.5	395.7	387.7	383.4	379.1	374.7	370.4
42.5°	391.0	378.8	366.7	358.5	354.3	350.1	345.9	341.7
45°	349.8	338.1	326.3	318.4	314.4	310.4	306.4	302.5
47.5°	309.8	298.1	286.4	278.7	275.1	271.5	267.8	264.2
50°	284.0	272.6	261.1	253.7	250.2	246.7	243.2	239.7
52.5°	259.7	248.7	237.6	230.5	227.3	224.1	220.8	217.6
55°	222.8	212.8	202.9	196.3	193.2	190.0	186.9	183.7
57.5°	189.2	180.1	171.0	165.1	162.4	159.8	157.1	154.4
60°	166.0	157.6	149.1	143.6	140.9	138.2	135.6	132.9
62.5°	145.9	137.9	129.8	125.0	123.4	121.8	120.2	118.6
65°	118.7	113.0	107.4	104.3	103.8	103.3	102.8	102.3
67.5°	95.8	93.2	90.6	89.1	88.5	88.0	87.5	86.9
70°	83.3	81.7	80.0	78.8	78.2	77.5	76.8	76.2
72.5°	72.5	71.1	69.7	68.8	68.4	68.0	67.6	67.2
75°	57.4	56.3	55.1	54.4	54.3	54.1	53.9	53.8
77.5°	43.5	42.8	42.2	41.7	41.4	41.2	40.9	40.6
80°	34.5	33.9	33.2	32.9	32.9	32.9	32.9	32.9
82.5°	26.1	25.7	25.3	25.1	25.1	25.1	25.1	25.1
85°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	6.9	6.8	6.6	6.5	6.5	6.6	6.6	6.6
90°	12.1	11.9	11.7	11.7	11.8	11.9	11.9	12.0
92.5°	11.3	11.3	11.4	11.4	11.4	11.4	11.4	11.4
95°	22.6	22.6	22.6	22.5	22.4	22.2	22.1	21.9
97.5°	38.0	38.0	38.0	38.0	38.0	38.0	38.0	37.9
100°	48.8	48.8	48.8	48.7	48.6	48.6	48.5	48.4
102.5°	60.5	60.5	60.6	60.6	60.5	60.4	60.4	60.3
105°	78.0	78.2	78.4	78.4	78.4	78.4	78.4	78.4
107.5°	97.0	97.1	97.1	97.0	96.6	96.3	95.9	95.5
110°	109.9	109.9	109.9	109.8	109.5	109.3	109.1	108.8



TEST NUMBER: P331649

CATALOG NUMBER: SA2XXRDIP-C485D330U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	122.8	122.6	122.4	122.2	122.1	121.9	121.7	121.5
115°	142.6	142.5	142.4	142.3	142.0	141.8	141.6	141.3
117.5°	161.7	161.5	161.3	161.1	160.9	160.7	160.4	160.2
120°	174.5	174.5	174.5	174.4	174.2	173.9	173.7	173.5
122.5°	187.7	187.5	187.3	187.2	187.0	186.8	186.6	186.5
125°	207.3	207.0	206.8	206.6	206.6	206.5	206.4	206.3
127.5°	226.3	226.0	225.7	225.4	225.2	224.9	224.7	224.4
130°	239.2	239.1	238.9	238.7	238.4	238.0	237.7	237.4
132.5°	251.8	251.5	251.2	250.9	250.6	250.4	250.1	249.9
135°	270.5	270.4	270.3	270.2	269.9	269.7	269.5	269.2
137.5°	288.3	288.2	288.2	288.0	287.7	287.4	287.1	286.7
140°	300.3	300.3	300.3	300.1	299.8	299.5	299.2	298.9
142.5°	311.2	311.2	311.3	311.2	310.9	310.5	310.2	309.9
145°	327.7	327.7	327.8	327.7	327.4	327.1	326.8	326.4
147.5°	342.1	342.3	342.5	342.4	342.1	341.8	341.5	341.2
150°	351.3	351.5	351.8	351.8	351.5	351.3	351.1	350.8
152.5°	360.5	360.8	361.1	361.1	360.8	360.5	360.2	359.9
155°	372.1	372.5	372.9	373.0	372.7	372.5	372.3	372.0
157.5°	382.8	383.4	383.9	384.0	383.6	383.2	382.9	382.5
160°	389.2	389.7	390.2	390.2	389.9	389.6	389.3	389.0
162.5°	395.0	395.5	396.1	396.1	395.8	395.4	395.0	394.6
165°	402.4	403.0	403.5	403.6	403.2	402.8	402.4	402.1
167.5°	408.6	409.1	409.7	409.8	409.4	408.9	408.5	408.1
170°	412.0	412.5	413.1	413.1	412.7	412.2	411.7	411.2
172.5°	414.5	415.1	415.6	415.7	415.2	414.7	414.3	413.8
175°	417.3	417.8	418.4	418.4	418.0	417.5	417.0	416.5
177.5°	418.6	418.9	419.3	419.3	418.9	418.6	418.2	417.8
180°	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7

(END OF REPORT)