

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331310-830

Luminaire Tested: **SA2XXDIP-C485D725U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331310-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C485D725U830-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4307.1 lumens  
Efficiency: N/A  
Efficacy: 112.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 38.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331310-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331310-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43				43
1	96	92	88	85	88	84	81	78	70	67	65	56	55	53	44	43	42	36				36
2	88	80	74	69	80	74	68	64	61	57	54	50	47	45	39	37	35	31				31
3	80	71	63	58	73	65	58	53	54	49	45	44	40	38	34	32	30	26				26
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22				22
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19				19
6	62	50	42	36	56	46	39	34	39	33	29	32	28	24	25	22	20	17				17
7	57	45	37	32	52	41	34	30	35	29	26	29	25	22	23	20	18	15				15
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13				13
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	17	14	12				12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11				11

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	11820	11820	11820
5°	11866	11694	11763
10°	11795	11576	11632
15°	11649	11425	11413
20°	11442	11201	11187
25°	11236	10922	10922
30°	10972	10670	10577
35°	10724	10364	10212
40°	10416	10060	9866
45°	10111	9757	9515
50°	9779	9442	9105
55°	9433	9073	8740
60°	9045	8638	8318
65°	8630	8202	7824
70°	8105	7676	7312
75°	7380	7068	6900
80°	6546	6341	6025
85°	5335	5076	4557



TEST NUMBER: P331310-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.8	1.6
10°-20°	193.7	4.5
20°-30°	284.7	6.6
30°-40°	330.7	7.7
40°-50°	330.4	7.7
50°-60°	288.1	6.7
60°-70°	213.0	4.9
70°-80°	120.7	2.8
80°-90°	35.9	0.8
90°-100°	55.3	1.3
100°-110°	171.8	4.0
110°-120°	293.7	6.8
120°-130°	386.2	9.0
130°-140°	433.5	10.1
140°-150°	425.0	9.9
150°-160°	356.5	8.3
160°-170°	236.5	5.5
170°-180°	82.6	1.9
0°-30°	547.2	12.7
0°-40°	878.0	20.4
0°-60°	1496.4	34.7
0°-90°	1866.0	43.3
90°-120°	520.8	12.1
90°-150°	1765.5	41.0
90°-180°	2441.0	56.7
0°-180°	4307.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	732	732	732	732	732	
5°	732	729	722	727	726	69
15°	697	692	684	686	683	196
25°	631	625	613	614	613	290
35°	544	537	526	522	518	340
45°	443	438	427	420	417	342
55°	335	331	322	314	310	299
65°	226	222	215	208	205	223
75°	118	117	113	109	111	126
85°	29	28	27	25	25	33
90°	1	10	26	24	25	3
95°	38	45	47	47	46	44
105°	158	161	162	163	164	167
115°	295	299	298	297	295	291
125°	429	435	433	431	430	383
135°	555	562	564	564	561	428
145°	673	678	683	683	681	421
155°	770	772	774	778	776	354
165°	838	837	837	842	838	236
175°	872	869	868	872	869	83
180°	873	873	873	873	873	



TEST NUMBER: P331310-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	735.5	734.8	734.2	733.6	732.9	732.0	730.6	729.2	727.8	726.4	727.7
5°	732.1	731.4	730.8	730.2	729.6	728.4	726.7	725.0	723.2	721.5	722.7
7.5°	725.6	724.6	723.7	722.6	721.7	720.4	718.6	716.9	715.1	713.3	714.6
10°	719.4	718.3	717.2	716.1	715.0	713.5	711.6	709.8	707.9	706.1	707.3
12.5°	711.0	710.0	709.0	708.0	707.1	705.7	703.8	701.9	700.0	698.1	699.0
15°	696.9	696.0	695.0	694.1	693.1	691.6	689.6	687.6	685.5	683.5	684.1
17.5°	678.8	678.0	677.0	676.1	675.1	673.6	671.6	669.5	667.4	665.3	666.1
20°	665.9	665.0	664.0	663.1	662.1	660.6	658.4	656.2	654.0	651.9	652.3
22.5°	653.0	651.7	650.4	649.0	647.7	646.0	643.9	641.9	639.8	637.7	637.8
25°	630.7	629.4	628.2	627.0	625.8	623.8	621.1	618.4	615.8	613.1	613.4
27.5°	605.4	604.3	603.1	602.0	600.9	599.3	597.2	595.0	593.0	590.9	590.4
30°	588.5	587.2	586.0	584.8	583.4	581.6	579.3	577.0	574.7	572.3	571.8
32.5°	570.4	569.5	568.4	567.4	566.5	564.7	562.2	559.8	557.3	554.9	554.0
35°	544.1	542.5	541.0	539.4	537.9	535.8	533.4	530.8	528.3	525.8	524.9
37.5°	514.4	513.0	511.7	510.3	508.9	507.0	504.4	502.0	499.5	497.0	495.8
40°	494.2	492.9	491.6	490.4	489.2	487.3	484.7	482.3	479.8	477.3	475.9
42.5°	474.5	473.2	471.9	470.7	469.5	467.6	465.1	462.6	460.1	457.5	456.0
45°	442.8	441.7	440.5	439.5	438.4	436.7	434.3	432.0	429.6	427.3	425.6
47.5°	411.2	410.2	409.2	408.1	407.1	405.4	402.9	400.5	398.0	395.6	393.8
50°	389.3	388.5	387.7	386.9	386.2	384.7	382.5	380.3	378.1	375.9	373.7
52.5°	367.9	366.8	365.8	364.8	363.7	362.2	360.1	358.1	356.0	353.9	352.1
55°	335.1	334.1	333.2	332.2	331.3	329.9	328.0	326.1	324.2	322.3	320.6
57.5°	302.1	301.3	300.6	299.9	299.2	297.7	295.7	293.6	291.5	289.5	287.6
60°	280.1	279.6	278.9	278.2	277.7	276.3	274.1	271.8	269.7	267.5	265.8
62.5°	258.7	257.8	256.7	255.7	254.8	253.4	251.8	250.1	248.4	246.7	245.1
65°	225.9	225.0	224.0	223.1	222.3	220.9	219.4	217.8	216.2	214.7	213.3
67.5°	192.6	191.8	191.1	190.3	189.5	188.5	187.1	185.7	184.3	182.9	181.8
70°	171.7	171.2	170.5	169.8	169.3	168.2	166.8	165.4	164.0	162.6	161.6
72.5°	150.3	149.8	149.1	148.5	147.9	147.1	146.2	145.2	144.4	143.5	142.3
75°	118.3	117.9	117.6	117.3	117.0	116.5	115.6	114.9	114.1	113.3	112.4
77.5°	89.5	89.0	88.5	87.9	87.4	87.0	86.7	86.3	86.1	85.8	85.3
80°	70.4	70.2	70.1	69.9	69.7	69.6	69.2	68.9	68.6	68.2	67.8
82.5°	52.4	52.3	52.3	52.3	52.2	52.1	51.9	51.7	51.6	51.4	50.8
85°	28.8	28.7	28.6	28.4	28.3	28.1	27.9	27.8	27.6	27.4	27.0
87.5°	10.3	10.5	10.6	10.7	10.8	11.1	11.6	12.1	12.5	13.0	12.6
90°	0.8	2.7	4.7	6.6	8.6	11.4	15.0	18.6	22.1	25.8	25.4
92.5°	13.1	14.5	16.0	17.4	18.9	20.0	20.8	21.7	22.6	23.5	23.5
95°	38.3	40.0	41.6	43.3	44.9	45.8	46.2	46.5	46.8	47.1	47.1
97.5°	70.0	71.4	72.9	74.3	75.8	76.8	77.4	78.0	78.6	79.3	79.3
100°	93.6	94.9	96.1	97.5	98.8	99.7	100.2	100.7	101.1	101.7	101.7
102.5°	118.3	119.3	120.5	121.5	122.5	123.4	123.9	124.6	125.2	125.8	125.9
105°	158.4	158.9	159.4	159.9	160.3	160.8	161.1	161.5	161.7	162.1	162.4
107.5°	198.8	199.5	200.2	201.0	201.6	202.0	202.0	202.0	202.0	202.0	202.2
110°	224.7	225.6	226.7	227.6	228.7	229.1	229.1	229.1	229.1	229.1	229.1



TEST NUMBER: P331310-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	253.0	254.0	255.0	255.9	256.9	257.3	257.2	257.1	256.9	256.8	256.5
115°	294.7	295.7	296.6	297.7	298.6	299.0	298.6	298.3	297.9	297.7	297.5
117.5°	336.2	337.5	338.8	340.2	341.5	341.7	340.7	339.9	338.9	338.0	337.6
120°	363.9	365.2	366.6	367.9	369.2	369.2	367.9	366.6	365.2	363.9	363.9
122.5°	389.3	390.9	392.5	394.0	395.6	395.9	395.0	394.1	393.1	392.2	391.8
125°	428.8	430.3	431.7	433.2	434.7	435.2	434.7	434.1	433.7	433.2	432.7
127.5°	467.2	469.1	471.0	472.9	474.7	475.3	474.8	474.2	473.5	473.0	472.4
130°	491.4	493.5	495.7	497.8	499.9	500.8	500.5	500.1	499.8	499.5	499.2
132.5°	518.5	520.3	522.0	523.7	525.5	526.3	526.4	526.5	526.5	526.6	525.9
135°	554.8	556.6	558.4	560.2	561.9	563.0	563.4	563.6	564.0	564.3	564.2
137.5°	593.0	594.4	595.9	597.4	598.8	599.7	600.2	600.6	601.1	601.4	601.3
140°	616.0	617.4	618.9	620.3	621.8	622.9	623.8	624.6	625.4	626.2	626.2
142.5°	639.5	640.9	642.4	643.9	645.4	646.4	647.0	647.5	648.1	648.7	648.8
145°	673.4	674.5	675.7	676.8	678.0	679.0	680.0	681.0	681.9	683.0	683.2
147.5°	703.6	704.9	706.3	707.7	709.1	710.1	710.8	711.4	712.1	712.8	713.0
150°	724.2	725.2	726.1	727.2	728.1	729.0	729.6	730.3	730.9	731.6	732.1
152.5°	742.4	743.5	744.4	745.5	746.4	747.2	748.1	748.9	749.6	750.5	751.0
155°	769.9	770.3	770.9	771.4	771.8	772.3	772.8	773.4	773.8	774.3	775.1
157.5°	793.3	793.6	794.0	794.3	794.7	794.9	795.2	795.5	795.8	796.1	797.2
160°	807.5	807.8	808.1	808.4	808.8	809.0	809.2	809.4	809.5	809.6	810.7
162.5°	820.4	820.5	820.6	820.6	820.7	820.8	821.0	821.1	821.3	821.4	822.6
165°	837.6	837.5	837.4	837.2	837.0	836.9	836.9	836.9	836.9	836.9	838.1
167.5°	852.1	851.6	851.1	850.6	850.2	849.9	849.9	849.8	849.8	849.7	850.9
170°	859.8	859.3	858.8	858.3	857.8	857.4	857.3	857.1	857.0	856.8	858.0
172.5°	865.1	864.6	864.1	863.6	863.1	862.8	862.6	862.4	862.3	862.1	863.3
175°	871.6	871.1	870.5	870.1	869.6	869.2	868.8	868.6	868.2	867.9	869.0
177.5°	874.2	873.8	873.5	873.0	872.6	872.3	872.0	871.8	871.5	871.3	872.0
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331310-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	729.0	730.2	731.4	732.0	731.7	731.4	731.2	730.9
5°	724.1	725.3	726.5	727.0	726.7	726.3	726.0	725.8
7.5°	715.9	717.1	718.4	718.8	718.5	718.1	717.7	717.5
10°	708.5	709.8	711.1	711.4	711.0	710.5	710.0	709.5
12.5°	699.9	700.8	701.6	701.9	701.5	701.3	700.9	700.5
15°	684.8	685.4	686.0	685.9	685.1	684.4	683.6	682.8
17.5°	666.8	667.5	668.3	668.2	667.4	666.8	666.0	665.2
20°	652.8	653.3	653.7	653.7	653.0	652.3	651.8	651.1
22.5°	637.9	638.0	638.1	638.0	637.6	637.3	636.9	636.5
25°	613.8	614.1	614.3	614.3	614.1	613.8	613.4	613.1
27.5°	589.9	589.5	589.0	588.4	587.7	586.9	586.2	585.4
30°	571.4	570.9	570.4	569.9	569.2	568.6	568.0	567.3
32.5°	553.2	552.3	551.5	550.7	550.1	549.5	548.8	548.2
35°	524.0	523.0	522.1	521.2	520.5	519.6	518.9	518.1
37.5°	494.6	493.5	492.4	491.3	490.6	489.8	489.1	488.4
40°	474.5	473.1	471.6	470.6	470.0	469.4	468.7	468.1
42.5°	454.5	453.0	451.4	450.3	449.3	448.5	447.6	446.7
45°	423.9	422.2	420.4	419.2	418.6	418.0	417.4	416.7
47.5°	392.0	390.1	388.3	387.0	386.1	385.2	384.3	383.3
50°	371.6	369.3	367.1	365.6	364.9	364.1	363.3	362.5
52.5°	350.3	348.5	346.7	345.3	344.2	343.2	342.1	341.1
55°	318.7	316.8	314.9	313.6	312.7	312.0	311.2	310.5
57.5°	285.8	283.9	282.1	280.9	280.2	279.7	279.1	278.4
60°	264.0	262.3	260.6	259.5	259.0	258.5	258.1	257.6
62.5°	243.5	241.9	240.3	239.2	238.6	238.0	237.4	236.8
65°	211.9	210.5	209.1	207.9	207.2	206.4	205.7	204.8
67.5°	180.7	179.6	178.5	177.7	177.0	176.3	175.8	175.1
70°	160.4	159.3	158.3	157.4	156.7	156.1	155.5	154.9
72.5°	141.3	140.2	139.1	138.3	137.8	137.2	136.8	136.3
75°	111.4	110.6	109.6	109.2	109.6	109.9	110.2	110.6
77.5°	84.8	84.4	83.9	83.4	82.9	82.6	82.1	81.6
80°	67.3	66.8	66.4	66.0	65.7	65.4	65.0	64.8
82.5°	50.2	49.6	49.0	48.6	48.6	48.5	48.4	48.4
85°	26.5	26.0	25.5	25.3	25.1	25.0	24.8	24.6
87.5°	12.2	11.7	11.3	11.0	10.9	10.8	10.7	10.7
90°	25.2	24.8	24.5	24.4	24.6	24.7	24.9	25.1
92.5°	23.6	23.7	23.7	23.8	23.8	23.8	23.8	23.8
95°	47.1	47.1	47.1	47.0	46.7	46.4	46.0	45.7
97.5°	79.3	79.3	79.3	79.3	79.3	79.2	79.2	79.1
100°	101.7	101.7	101.7	101.6	101.4	101.2	101.1	100.9
102.5°	126.1	126.2	126.4	126.3	126.2	126.0	125.8	125.6
105°	162.8	163.1	163.4	163.5	163.5	163.5	163.5	163.5
107.5°	202.3	202.4	202.6	202.3	201.5	200.8	200.0	199.3
110°	229.1	229.1	229.1	228.8	228.4	227.9	227.4	226.9





TEST NUMBER: P331310-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	256.0	255.6	255.2	254.9	254.5	254.1	253.8	253.4
115°	297.3	297.2	297.0	296.6	296.1	295.7	295.2	294.7
117.5°	337.2	336.9	336.4	336.0	335.5	335.0	334.5	334.0
120°	363.9	363.9	363.9	363.7	363.2	362.7	362.2	361.7
122.5°	391.4	391.1	390.7	390.3	389.9	389.6	389.2	388.9
125°	432.3	431.7	431.2	430.9	430.7	430.6	430.5	430.3
127.5°	471.8	471.2	470.6	470.0	469.6	469.0	468.5	468.0
130°	498.9	498.5	498.2	497.7	497.0	496.4	495.8	495.1
132.5°	525.2	524.4	523.8	523.1	522.5	522.1	521.5	521.0
135°	564.0	563.8	563.6	563.4	562.9	562.4	561.8	561.4
137.5°	601.2	601.1	601.0	600.6	599.9	599.3	598.6	597.9
140°	626.2	626.2	626.2	625.8	625.3	624.6	624.0	623.3
142.5°	648.8	649.0	649.1	648.8	648.2	647.5	647.0	646.3
145°	683.2	683.4	683.6	683.3	682.7	682.0	681.4	680.7
147.5°	713.4	713.8	714.2	714.1	713.4	712.8	712.2	711.5
150°	732.5	733.0	733.6	733.6	733.0	732.5	732.1	731.6
152.5°	751.7	752.3	752.9	752.9	752.3	751.7	751.0	750.5
155°	775.9	776.7	777.6	777.8	777.2	776.7	776.3	775.8
157.5°	798.3	799.5	800.6	800.7	799.9	799.2	798.3	797.6
160°	811.6	812.7	813.6	813.8	813.1	812.5	811.8	811.2
162.5°	823.7	824.8	826.0	826.0	825.3	824.5	823.7	822.9
165°	839.2	840.4	841.5	841.7	840.8	840.0	839.2	838.4
167.5°	852.1	853.2	854.3	854.5	853.7	852.8	852.0	851.1
170°	859.1	860.3	861.4	861.5	860.5	859.5	858.6	857.5
172.5°	864.4	865.5	866.7	866.8	865.8	864.8	863.8	862.9
175°	870.2	871.3	872.4	872.5	871.6	870.5	869.6	868.6
177.5°	872.8	873.6	874.4	874.4	873.6	872.8	872.0	871.3
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0

(END OF REPORT)