

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331311-830

Luminaire Tested: **SA2XXDIP-C485D725U830-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331311-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C485D725U830-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4532.0 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331311-830
CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331311-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	78	78	78	63	63	63	48	48	48	41				
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	35				
2	87	80	74	69	79	73	68	63	60	56	53	48	46	43	37	36	34	29				
3	80	70	63	57	72	64	58	53	53	48	45	43	39	37	33	31	29	25				
4	73	62	54	48	66	57	50	45	47	42	38	38	34	31	30	27	25	21				
5	67	55	47	41	61	51	44	38	42	37	33	34	30	27	27	24	22	18				
6	61	50	42	36	56	45	38	33	38	33	29	31	27	24	24	21	19	16				
7	57	45	37	31	52	41	34	29	34	29	25	28	24	21	22	19	17	14				
8	53	40	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13				
9	49	37	30	25	45	34	27	23	29	23	20	23	20	17	19	16	14	12				
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11820	11820	11820
5°	11866	11694	11763
10°	11795	11576	11632
15°	11649	11425	11413
20°	11442	11201	11187
25°	11236	10922	10922
30°	10972	10670	10577
35°	10724	10364	10212
40°	10416	10060	9866
45°	10111	9757	9515
50°	9779	9442	9105
55°	9433	9073	8740
60°	9045	8638	8318
65°	8630	8202	7824
70°	8105	7676	7312
75°	7380	7068	6900
80°	6546	6341	6025
85°	5335	5076	4557



TEST NUMBER: P331311-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.8	1.5
10°-20°	193.7	4.3
20°-30°	284.7	6.3
30°-40°	330.7	7.3
40°-50°	330.4	7.3
50°-60°	288.1	6.4
60°-70°	213.0	4.7
70°-80°	120.7	2.7
80°-90°	35.9	0.8
90°-100°	153.2	3.4
100°-110°	519.8	11.5
110°-120°	552.3	12.2
120°-130°	454.6	10.0
130°-140°	365.1	8.1
140°-150°	275.9	6.1
150°-160°	193.9	4.3
160°-170°	114.1	2.5
170°-180°	37.1	0.8
0°-30°	547.2	12.1
0°-40°	878.0	19.4
0°-60°	1496.4	33.0
0°-90°	1866.0	41.2
90°-120°	1225.3	27.0
90°-150°	2320.9	51.2
90°-180°	2666.0	58.8
0°-180°	4532.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	732	732	732	732	732	
5°	732	729	722	727	726	69
15°	697	692	684	686	683	196
25°	631	625	613	614	613	290
35°	544	537	526	522	518	340
45°	443	438	427	420	417	342
55°	335	331	322	314	310	299
65°	226	222	215	208	205	223
75°	118	117	113	109	111	126
85°	29	28	27	25	25	33
90°	1	10	25	24	24	3
95°	26	63	289	109	84	27
105°	90	136	546	976	830	96
115°	158	200	457	943	1093	157
125°	221	262	439	764	886	196
135°	259	310	434	642	735	200
145°	296	340	432	536	586	186
155°	337	364	419	474	493	155
165°	367	378	402	426	432	103
175°	382	383	386	391	390	36
180°	383	383	383	383	383	



TEST NUMBER: P331311-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	735.5	734.8	734.2	733.6	732.9	732.0	730.6	729.2	727.8	726.4	727.7
5°	732.1	731.4	730.8	730.2	729.6	728.4	726.7	725.0	723.2	721.5	722.7
7.5°	725.6	724.6	723.7	722.6	721.7	720.4	718.6	716.9	715.1	713.3	714.6
10°	719.4	718.3	717.2	716.1	715.0	713.5	711.6	709.8	707.9	706.1	707.3
12.5°	711.0	710.0	709.0	708.0	707.1	705.7	703.8	701.9	700.0	698.1	699.0
15°	696.9	696.0	695.0	694.1	693.1	691.6	689.6	687.6	685.5	683.5	684.1
17.5°	678.8	678.0	677.0	676.1	675.1	673.6	671.6	669.5	667.4	665.3	666.1
20°	665.9	665.0	664.0	663.1	662.1	660.6	658.4	656.2	654.0	651.9	652.3
22.5°	653.0	651.7	650.4	649.0	647.7	646.0	643.9	641.9	639.8	637.7	637.8
25°	630.7	629.4	628.2	627.0	625.8	623.8	621.1	618.4	615.8	613.1	613.4
27.5°	605.4	604.3	603.1	602.0	600.9	599.3	597.2	595.0	593.0	590.9	590.4
30°	588.5	587.2	586.0	584.8	583.4	581.6	579.3	577.0	574.7	572.3	571.8
32.5°	570.4	569.5	568.4	567.4	566.5	564.7	562.2	559.8	557.3	554.9	554.0
35°	544.1	542.5	541.0	539.4	537.9	535.8	533.4	530.8	528.3	525.8	524.9
37.5°	514.4	513.0	511.7	510.3	508.9	507.0	504.4	502.0	499.5	497.0	495.8
40°	494.2	492.9	491.6	490.4	489.2	487.3	484.7	482.3	479.8	477.3	475.9
42.5°	474.5	473.2	471.9	470.7	469.5	467.6	465.1	462.6	460.1	457.5	456.0
45°	442.8	441.7	440.5	439.5	438.4	436.7	434.3	432.0	429.6	427.3	425.6
47.5°	411.2	410.2	409.2	408.1	407.1	405.4	402.9	400.5	398.0	395.6	393.8
50°	389.3	388.5	387.7	386.9	386.2	384.7	382.5	380.3	378.1	375.9	373.7
52.5°	367.9	366.8	365.8	364.8	363.7	362.2	360.1	358.1	356.0	353.9	352.1
55°	335.1	334.1	333.2	332.2	331.3	329.9	328.0	326.1	324.2	322.3	320.6
57.5°	302.1	301.3	300.6	299.9	299.2	297.7	295.7	293.6	291.5	289.5	287.6
60°	280.1	279.6	278.9	278.2	277.7	276.3	274.1	271.8	269.7	267.5	265.8
62.5°	258.7	257.8	256.7	255.7	254.8	253.4	251.8	250.1	248.4	246.7	245.1
65°	225.9	225.0	224.0	223.1	222.3	220.9	219.4	217.8	216.2	214.7	213.3
67.5°	192.6	191.8	191.1	190.3	189.5	188.5	187.1	185.7	184.3	182.9	181.8
70°	171.7	171.2	170.5	169.8	169.3	168.2	166.8	165.4	164.0	162.6	161.6
72.5°	150.3	149.8	149.1	148.5	147.9	147.1	146.2	145.2	144.4	143.5	142.3
75°	118.3	117.9	117.6	117.3	117.0	116.5	115.6	114.9	114.1	113.3	112.4
77.5°	89.5	89.0	88.5	87.9	87.4	87.0	86.7	86.3	86.1	85.8	85.3
80°	70.4	70.2	70.1	69.9	69.7	69.6	69.2	68.9	68.6	68.2	67.8
82.5°	52.4	52.3	52.3	52.3	52.2	52.1	51.9	51.7	51.6	51.4	50.8
85°	28.8	28.7	28.6	28.4	28.3	28.1	27.9	27.8	27.6	27.4	27.0
87.5°	10.3	10.5	10.8	10.8	10.9	11.1	11.6	12.3	13.0	12.9	12.3
90°	0.8	2.9	5.9	7.4	8.9	11.0	14.7	19.9	24.3	25.1	24.3
92.5°	9.0	13.0	18.3	21.5	26.5	33.5	50.1	73.5	94.4	95.8	80.9
95°	25.8	28.7	36.1	42.7	54.5	72.2	106.1	170.2	255.7	288.8	252.7
97.5°	42.0	46.0	53.8	63.8	77.4	97.4	140.0	229.3	371.4	493.0	517.3
100°	56.7	58.9	65.6	77.4	92.1	112.7	151.7	241.7	400.8	582.0	688.2
102.5°	70.3	71.9	78.5	90.3	105.7	126.3	162.4	242.2	389.6	585.0	751.8
105°	89.9	92.8	98.0	109.1	125.3	145.9	180.5	246.1	367.7	545.9	742.0
107.5°	111.1	113.5	118.5	128.7	144.7	165.5	199.1	256.3	356.8	504.1	677.2
110°	125.3	128.2	132.6	142.2	157.7	179.1	211.4	264.5	354.4	484.1	636.6



TEST NUMBER: P331311-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	138.2	141.2	146.2	155.1	170.0	192.0	223.3	273.3	355.0	471.1	608.3
115°	158.4	162.1	166.5	175.3	190.1	210.0	241.7	286.6	358.1	456.9	573.3
117.5°	179.4	182.3	186.7	194.5	208.7	229.3	258.6	300.8	363.4	449.9	551.1
120°	192.3	195.3	199.6	206.3	221.0	241.7	270.4	310.2	366.9	445.7	539.3
122.5°	204.7	207.1	211.4	218.7	233.4	254.7	281.6	318.5	371.1	443.4	529.3
125°	221.0	223.3	227.6	236.5	251.3	271.8	298.4	331.6	377.2	439.1	515.0
127.5°	234.0	237.0	243.2	252.9	267.0	288.2	314.1	343.7	383.6	436.6	501.7
130°	241.7	244.6	251.9	262.3	277.0	297.7	323.5	351.5	388.3	435.5	492.9
132.5°	248.7	252.3	260.2	271.2	286.4	307.1	331.7	359.1	393.0	434.9	485.9
135°	259.4	262.3	271.2	282.2	299.2	319.8	343.4	369.1	398.6	433.9	476.0
137.5°	269.4	272.9	281.7	293.5	310.4	329.5	352.8	376.8	403.6	433.9	469.0
140°	277.0	279.9	288.8	300.6	316.8	336.0	358.1	380.9	406.0	433.2	465.0
142.5°	284.6	287.1	295.3	307.1	322.7	340.7	362.2	384.5	407.7	433.2	460.8
145°	296.1	299.2	306.5	317.5	332.2	348.5	368.4	389.0	409.6	431.8	455.3
147.5°	308.6	310.8	317.8	328.0	340.3	354.7	373.4	391.5	410.3	429.1	449.8
150°	316.8	319.1	324.9	334.5	345.5	358.8	375.8	392.7	409.6	427.3	445.0
152.5°	325.1	326.1	332.0	340.4	350.8	363.0	378.1	393.3	408.5	424.4	440.9
155°	336.7	337.4	341.9	350.0	358.1	369.1	381.6	394.2	406.7	419.2	433.2
157.5°	346.5	347.1	350.7	357.8	364.3	373.5	384.2	394.2	403.3	414.0	426.0
160°	352.9	353.6	356.6	362.5	368.4	376.5	385.3	394.2	401.5	410.4	420.8
162.5°	359.4	358.9	361.9	366.6	371.9	378.2	386.0	393.6	399.8	407.5	415.9
165°	366.9	366.2	367.7	372.1	375.8	380.2	386.8	392.0	396.4	401.5	408.2
167.5°	373.2	372.2	373.5	376.4	379.0	381.8	386.6	391.0	393.0	396.4	400.5
170°	377.2	375.8	376.5	378.7	380.2	382.4	386.1	389.7	391.2	393.4	396.4
172.5°	379.6	378.7	378.2	380.5	381.4	383.0	385.5	388.0	388.9	389.9	392.3
175°	382.4	381.6	380.9	382.4	382.4	383.1	384.6	386.1	385.3	386.1	386.8
177.5°	383.7	382.6	381.9	383.1	383.1	383.1	383.7	384.9	383.7	383.1	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1



TEST NUMBER: P331311-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	732.1	732.1	732.1	732.1	732.1	732.1	732.1	732.1
2.5°	729.0	730.2	731.4	732.0	731.7	731.4	731.2	730.9
5°	724.1	725.3	726.5	727.0	726.7	726.3	726.0	725.8
7.5°	715.9	717.1	718.4	718.8	718.5	718.1	717.7	717.5
10°	708.5	709.8	711.1	711.4	711.0	710.5	710.0	709.5
12.5°	699.9	700.8	701.6	701.9	701.5	701.3	700.9	700.5
15°	684.8	685.4	686.0	685.9	685.1	684.4	683.6	682.8
17.5°	666.8	667.5	668.3	668.2	667.4	666.8	666.0	665.2
20°	652.8	653.3	653.7	653.7	653.0	652.3	651.8	651.1
22.5°	637.9	638.0	638.1	638.0	637.6	637.3	636.9	636.5
25°	613.8	614.1	614.3	614.3	614.1	613.8	613.4	613.1
27.5°	589.9	589.5	589.0	588.4	587.7	586.9	586.2	585.4
30°	571.4	570.9	570.4	569.9	569.2	568.6	568.0	567.3
32.5°	553.2	552.3	551.5	550.7	550.1	549.5	548.8	548.2
35°	524.0	523.0	522.1	521.2	520.5	519.6	518.9	518.1
37.5°	494.6	493.5	492.4	491.3	490.6	489.8	489.1	488.4
40°	474.5	473.1	471.6	470.6	470.0	469.4	468.7	468.1
42.5°	454.5	453.0	451.4	450.3	449.3	448.5	447.6	446.7
45°	423.9	422.2	420.4	419.2	418.6	418.0	417.4	416.7
47.5°	392.0	390.1	388.3	387.0	386.1	385.2	384.3	383.3
50°	371.6	369.3	367.1	365.6	364.9	364.1	363.3	362.5
52.5°	350.3	348.5	346.7	345.3	344.2	343.2	342.1	341.1
55°	318.7	316.8	314.9	313.6	312.7	312.0	311.2	310.5
57.5°	285.8	283.9	282.1	280.9	280.2	279.7	279.1	278.4
60°	264.0	262.3	260.6	259.5	259.0	258.5	258.1	257.6
62.5°	243.5	241.9	240.3	239.2	238.6	238.0	237.4	236.8
65°	211.9	210.5	209.1	207.9	207.2	206.4	205.7	204.8
67.5°	180.7	179.6	178.5	177.7	177.0	176.3	175.8	175.1
70°	160.4	159.3	158.3	157.4	156.7	156.1	155.5	154.9
72.5°	141.3	140.2	139.1	138.3	137.8	137.2	136.8	136.3
75°	111.4	110.6	109.6	109.2	109.6	109.9	110.2	110.6
77.5°	84.8	84.4	83.9	83.4	82.9	82.6	82.1	81.6
80°	67.3	66.8	66.4	66.0	65.7	65.4	65.0	64.8
82.5°	50.2	49.6	49.0	48.6	48.6	48.5	48.4	48.4
85°	26.5	26.0	25.5	25.3	25.1	25.0	24.8	24.6
87.5°	11.9	11.2	11.1	11.0	10.8	10.7	10.7	10.5
90°	23.6	22.1	23.6	24.3	24.3	24.3	24.3	24.3
92.5°	64.3	55.1	48.9	44.4	43.7	41.4	42.0	40.8
95°	193.0	148.1	117.2	100.9	91.3	85.5	83.2	84.0
97.5°	450.4	368.5	288.8	235.6	200.4	182.3	171.5	165.3
100°	672.7	581.4	480.4	391.2	330.1	298.4	277.0	263.7
102.5°	818.3	797.7	723.8	629.3	562.9	508.8	482.1	464.2
105°	895.2	978.5	988.1	963.7	918.0	872.3	840.7	830.4
107.5°	839.8	965.2	1041.8	1077.5	1083.3	1080.7	1074.4	1060.6
110°	792.0	924.0	1018.2	1078.6	1110.3	1124.4	1131.0	1130.2



TEST NUMBER: P331311-830

CATALOG NUMBER: SA2XXDIP-C485D725U830-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	748.5	875.0	975.8	1045.1	1089.1	1112.6	1125.1	1129.1
115°	694.7	808.2	904.7	980.6	1032.9	1066.9	1086.0	1092.7
117.5°	654.4	754.0	841.6	912.8	966.1	1001.9	1022.1	1027.7
120°	634.3	725.8	803.8	870.9	922.5	957.1	978.5	985.8
122.5°	618.5	702.2	776.1	836.7	883.0	917.0	936.0	942.2
125°	595.3	671.2	736.0	791.3	834.1	862.0	880.4	886.4
127.5°	572.5	641.1	702.3	753.3	790.6	816.8	832.7	837.4
130°	557.7	621.1	679.3	727.9	764.0	789.1	803.8	809.7
132.5°	543.6	602.3	655.7	701.4	737.0	762.0	775.5	780.8
135°	523.9	572.5	621.1	662.3	694.1	718.4	731.6	734.6
137.5°	508.1	548.7	587.4	623.3	652.2	673.2	684.8	689.2
140°	498.0	533.5	567.3	599.7	623.3	642.4	653.6	658.0
142.5°	489.8	519.9	549.0	576.2	598.6	616.0	625.8	626.7
145°	478.2	502.5	525.4	546.7	564.4	576.9	584.3	586.4
147.5°	469.2	488.3	506.1	521.8	536.4	546.4	551.4	552.7
150°	462.7	478.9	494.4	507.7	518.7	527.5	532.0	532.7
152.5°	456.2	471.3	484.4	495.9	504.5	512.2	515.5	515.6
155°	447.2	459.0	470.0	478.2	486.3	491.4	494.4	492.9
157.5°	436.8	446.7	455.9	462.2	468.0	472.3	473.6	473.6
160°	430.3	438.4	446.5	451.7	456.9	460.5	461.2	461.2
162.5°	423.8	430.7	437.6	441.7	446.8	449.3	450.1	449.4
165°	414.1	419.2	424.4	427.3	430.3	433.2	433.2	432.5
167.5°	404.8	408.8	412.3	415.0	416.3	417.9	417.7	416.9
170°	400.1	402.3	405.2	406.7	407.5	409.6	408.9	407.5
172.5°	394.7	396.4	398.8	399.6	400.4	401.4	400.7	399.8
175°	389.0	389.7	390.5	391.2	391.2	392.0	391.2	389.7
177.5°	384.9	384.9	385.5	385.5	385.5	385.5	384.9	383.7
180°	383.1	383.1	383.1	383.1	383.1	383.1	383.1	383.1

(END OF REPORT)