

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331662

Luminaire Tested: **SA2XXRDIP-C485D725U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331662
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C485D725U835-4F0-1E-UDD-F4
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4529.6 lumens
Efficiency: N/A
Efficacy: 118.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 38.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331662
CATALOG NUMBER: SA2XXRDIP-C485D725U835-4F0-1E-UDD-F4

Luminous Intensity Polar Plot





TEST NUMBER: P331662

CATALOG NUMBER: SA2XXRDIP-C485D725U835-4F0-1E-UDD-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38
1	95	91	88	84	86	83	80	77	67	65	63	53	52	50	40	39	38	32
2	87	80	74	69	79	73	68	64	59	56	53	47	45	43	36	34	33	28
3	80	71	64	58	72	64	58	54	53	48	45	42	39	36	32	30	28	24
4	73	63	55	49	66	57	51	46	47	42	39	38	34	32	29	27	25	21
5	67	56	48	42	61	51	44	39	42	37	33	34	30	28	26	24	22	18
6	62	50	42	37	56	46	39	34	38	33	29	31	27	24	24	21	19	16
7	57	45	38	32	52	42	35	30	35	30	26	28	24	22	22	19	17	15
8	53	41	34	29	48	38	31	27	32	27	23	26	22	19	20	17	16	13
9	49	38	30	26	45	35	28	24	29	24	21	24	20	17	19	16	14	12
10	46	35	28	23	42	32	26	21	27	22	19	22	18	16	17	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13324	13324	13324
5°	13374	13157	13230
10°	13273	12942	12832
15°	13120	12558	12197
20°	12909	12010	11407
25°	12693	11389	10644
30°	12392	10750	9663
35°	12100	10054	8803
40°	11805	9335	7807
45°	11460	8526	6907
50°	11105	7709	6021
55°	10742	6832	5171
60°	10320	5909	4292
65°	9845	4963	3908
70°	9272	4088	3597
75°	8571	3724	3356
80°	7569	3329	3059
85°	5947	2631	2631



TEST NUMBER: P331662

CATALOG NUMBER: SA2XXRDIP-C485D725U835-4F0-1E-UDD-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.2	1.7
10°-20°	212.1	4.7
20°-30°	297.8	6.6
30°-40°	324.8	7.2
40°-50°	298.6	6.6
50°-60°	234.5	5.2
60°-70°	152.9	3.4
70°-80°	78.8	1.7
80°-90°	24.1	0.5
90°-100°	162.5	3.6
100°-110°	551.5	12.2
110°-120°	585.9	12.9
120°-130°	482.3	10.6
130°-140°	387.3	8.6
140°-150°	292.7	6.5
150°-160°	205.7	4.5
160°-170°	121.1	2.7
170°-180°	39.4	0.9
0°-30°	587.2	13.0
0°-40°	912.0	20.1
0°-60°	1445.1	31.9
0°-90°	1701.0	37.6
90°-120°	1300.0	28.7
90°-150°	2462.4	54.4
90°-180°	2829.0	62.5
0°-180°	4529.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	825	825	825	825	825	
5°	825	821	812	818	816	78
15°	785	776	751	738	730	221
25°	712	687	639	610	598	327
35°	614	574	510	465	447	384
45°	502	450	373	322	302	387
55°	382	322	243	200	184	341
65°	258	197	130	106	102	255
75°	137	87	60	55	54	145
85°	32	17	14	14	14	38
90°	1	11	27	25	26	3
95°	27	67	306	116	89	29
105°	95	144	579	1035	881	101
115°	168	212	485	1000	1159	167
125°	234	278	466	810	940	208
135°	275	328	460	681	779	213
145°	314	361	458	569	622	197
155°	357	386	445	503	523	164
165°	389	401	426	452	459	110
175°	406	406	410	415	414	39
180°	406	406	406	406	406	



TEST NUMBER: P331662

CATALOG NUMBER: SA2XXRDIP-C485D725U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	828.2	827.6	826.9	826.2	825.6	824.5	823.1	821.6	820.1	818.7	820.0
5°	825.2	824.4	823.6	822.8	821.9	820.4	818.3	816.1	814.0	811.8	813.3
7.5°	816.7	815.7	814.7	813.6	812.6	810.8	808.3	805.8	803.3	800.8	801.2
10°	809.6	808.4	807.2	806.1	804.9	802.7	799.4	796.0	792.7	789.4	788.9
12.5°	800.6	799.2	797.7	796.3	794.9	792.1	787.8	783.6	779.3	775.1	774.2
15°	784.9	783.1	781.3	779.4	777.6	773.9	768.2	762.6	757.0	751.3	748.2
17.5°	765.7	762.9	760.1	757.3	754.5	749.5	742.3	735.0	727.8	720.5	716.8
20°	751.3	748.0	744.7	741.4	738.0	732.2	723.9	715.6	707.3	699.0	694.9
22.5°	735.8	732.1	728.3	724.6	720.9	714.4	705.0	695.6	686.3	676.9	671.6
25°	712.5	707.2	701.9	696.5	691.2	683.1	672.1	661.2	650.2	639.3	632.5
27.5°	684.4	678.6	672.8	667.1	661.3	652.2	639.9	627.5	615.2	602.8	594.9
30°	664.7	658.4	652.1	645.8	639.5	629.7	616.4	603.1	589.8	576.6	568.1
32.5°	645.6	638.2	630.8	623.5	616.1	605.6	592.1	578.5	565.0	551.5	541.8
35°	613.9	605.4	597.0	588.5	580.0	568.5	553.9	539.3	524.7	510.1	499.6
37.5°	582.2	572.9	563.6	554.3	545.1	532.6	517.1	501.5	485.9	470.4	458.8
40°	560.1	550.2	540.2	530.3	520.3	507.3	491.2	475.1	459.0	442.9	431.1
42.5°	537.4	526.9	516.4	506.0	495.5	481.9	465.3	448.6	432.0	415.4	403.2
45°	501.9	490.8	479.6	468.5	457.4	443.1	425.7	408.3	390.8	373.4	361.6
47.5°	467.2	455.4	443.7	431.9	420.1	405.2	387.2	369.2	351.2	333.2	321.5
50°	442.1	430.3	418.6	406.8	395.0	380.0	361.7	343.5	325.2	306.9	295.5
52.5°	417.6	405.3	393.0	380.7	368.4	353.3	335.4	317.6	299.7	281.9	270.8
55°	381.6	368.7	355.7	342.8	329.9	314.4	296.5	278.6	260.6	242.7	232.8
57.5°	344.7	331.5	318.2	304.9	291.6	276.4	259.2	241.9	224.7	207.5	198.3
60°	319.6	306.4	293.1	279.8	266.5	251.4	234.3	217.2	200.1	183.0	174.5
62.5°	295.1	281.9	268.6	255.3	242.0	227.3	211.0	194.7	178.4	162.1	154.0
65°	257.7	244.2	230.8	217.3	203.9	189.7	174.8	159.8	144.9	129.9	124.3
67.5°	221.5	208.2	194.8	181.5	168.1	154.7	141.3	127.9	114.4	101.0	98.4
70°	196.4	183.5	170.5	157.6	144.6	132.4	121.0	109.5	98.1	86.6	85.0
72.5°	172.5	160.1	147.7	135.3	122.9	112.1	102.9	93.7	84.5	75.3	73.9
75°	137.4	125.8	114.2	102.6	90.9	82.3	76.7	71.0	65.4	59.7	58.6
77.5°	102.9	92.7	82.5	72.3	62.2	55.7	53.0	50.3	47.5	44.8	44.1
80°	81.4	72.9	64.5	56.0	47.5	42.5	40.8	39.2	37.5	35.8	35.2
82.5°	61.7	55.1	48.5	41.9	35.3	31.4	30.3	29.1	28.0	26.9	26.5
85°	32.1	28.6	25.1	21.7	18.2	16.2	15.7	15.2	14.7	14.2	14.2
87.5°	9.7	9.1	8.7	7.9	7.2	7.1	7.9	9.0	9.9	10.1	9.8
90°	0.8	3.1	6.3	7.8	9.4	11.7	15.6	21.1	25.8	26.6	25.8
92.5°	9.5	13.8	19.4	22.8	28.1	35.5	53.2	78.0	100.2	101.6	85.8
95°	27.4	30.5	38.3	45.3	57.8	76.6	112.6	180.6	271.3	306.4	268.1
97.5°	44.6	48.8	57.1	67.7	82.1	103.3	148.5	243.3	394.0	523.1	548.8
100°	60.2	62.5	69.6	82.1	97.7	119.6	161.0	256.4	425.2	617.5	730.1
102.5°	74.6	76.3	83.3	95.8	112.1	134.0	172.3	257.0	413.4	620.7	797.6
105°	95.4	98.5	104.0	115.7	132.9	154.8	191.5	261.1	390.1	579.2	787.2
107.5°	117.9	120.4	125.7	136.5	153.5	175.6	211.2	271.9	378.5	534.8	718.5
110°	132.9	136.0	140.7	150.9	167.3	190.0	224.3	280.6	376.0	513.6	675.4



TEST NUMBER: P331662

CATALOG NUMBER: SA2XXRDIP-C485D725U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.6	149.8	155.1	164.6	180.4	203.7	236.9	290.0	376.6	499.8	645.4
115°	168.1	172.0	176.7	186.0	201.7	222.8	256.4	304.1	379.9	484.7	608.2
117.5°	190.3	193.4	198.1	206.4	221.4	243.3	274.4	319.1	385.5	477.3	584.7
120°	204.0	207.2	211.8	218.9	234.5	256.4	286.9	329.1	389.3	472.9	572.2
122.5°	217.2	219.7	224.3	232.0	247.6	270.2	298.8	337.9	393.7	470.4	561.6
125°	234.5	236.9	241.5	250.9	266.6	288.4	316.6	351.8	400.2	465.9	546.4
127.5°	248.3	251.4	258.0	268.3	283.3	305.8	333.2	364.7	407.0	463.2	532.3
130°	256.4	259.5	267.3	278.3	293.9	315.8	343.2	372.9	412.0	462.0	523.0
132.5°	263.9	267.7	276.1	287.7	303.9	325.8	351.9	381.0	417.0	461.4	515.5
135°	275.2	278.3	287.7	299.4	317.4	339.3	364.3	391.6	422.9	460.4	505.0
137.5°	285.8	289.5	298.9	311.4	329.3	349.6	374.3	399.8	428.2	460.3	497.6
140°	293.9	297.0	306.4	318.9	336.1	356.5	379.9	404.1	430.7	459.6	493.3
142.5°	302.0	304.6	313.3	325.8	342.4	361.5	384.3	407.9	432.6	459.6	488.9
145°	314.2	317.4	325.2	336.9	352.5	369.7	390.9	412.7	434.6	458.1	483.1
147.5°	327.4	329.7	337.2	348.0	361.0	376.3	396.2	415.4	435.3	455.3	477.2
150°	336.1	338.5	344.7	354.9	366.6	380.7	398.7	416.6	434.6	453.4	472.1
152.5°	344.9	346.0	352.2	361.1	372.2	385.1	401.2	417.3	433.4	450.3	467.8
155°	357.2	358.0	362.7	371.3	379.9	391.6	404.9	418.2	431.5	444.8	459.6
157.5°	367.6	368.3	372.1	379.6	386.5	396.3	407.6	418.2	427.9	439.2	452.0
160°	374.4	375.2	378.3	384.6	390.9	399.4	408.8	418.2	426.0	435.4	446.4
162.5°	381.3	380.8	384.0	389.0	394.6	401.3	409.5	417.6	424.2	432.3	441.3
165°	389.3	388.5	390.1	394.8	398.7	403.4	410.4	415.9	420.6	426.0	433.1
167.5°	395.9	394.9	396.3	399.3	402.1	405.1	410.2	414.8	417.0	420.6	424.9
170°	400.2	398.7	399.4	401.8	403.4	405.7	409.6	413.5	415.1	417.4	420.6
172.5°	402.7	401.8	401.3	403.7	404.6	406.3	409.0	411.6	412.6	413.7	416.2
175°	405.7	404.9	404.1	405.7	405.7	406.5	408.0	409.6	408.8	409.6	410.4
177.5°	407.1	405.9	405.2	406.5	406.5	406.5	407.1	408.4	407.1	406.5	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331662

CATALOG NUMBER: SA2XXRDIP-C485D725U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	825.2	825.2	825.2	825.2	825.2	825.2	825.2	825.2
2.5°	821.3	822.7	824.0	824.5	824.3	824.0	823.7	823.5
5°	814.8	816.3	817.8	818.3	817.8	817.3	816.8	816.3
7.5°	801.6	802.0	802.5	802.3	801.4	800.5	799.7	798.8
10°	788.4	787.9	787.4	786.7	785.7	784.7	783.7	782.7
12.5°	773.3	772.4	771.5	770.2	768.5	766.9	765.2	763.6
15°	745.0	741.9	738.7	736.3	734.6	733.0	731.3	729.7
17.5°	713.0	709.3	705.5	702.2	699.4	696.5	693.7	690.8
20°	690.7	686.6	682.4	678.5	674.9	671.2	667.6	663.9
22.5°	666.2	660.9	655.6	651.5	648.8	646.1	643.4	640.6
25°	625.7	618.9	612.1	607.4	604.9	602.4	600.0	597.5
27.5°	587.0	579.0	571.1	565.2	561.2	557.3	553.3	549.4
30°	559.6	551.2	542.7	536.2	531.7	527.3	522.8	518.3
32.5°	532.1	522.5	512.8	505.9	501.7	497.5	493.2	489.0
35°	489.2	478.7	468.3	461.2	457.6	453.9	450.3	446.6
37.5°	447.3	435.8	424.3	416.4	412.3	408.1	403.9	399.7
40°	419.3	407.5	395.7	387.7	383.4	379.1	374.7	370.4
42.5°	391.0	378.8	366.7	358.5	354.3	350.1	345.9	341.7
45°	349.8	338.1	326.3	318.4	314.4	310.4	306.4	302.5
47.5°	309.8	298.1	286.4	278.7	275.1	271.5	267.8	264.2
50°	284.0	272.6	261.1	253.7	250.2	246.7	243.2	239.7
52.5°	259.7	248.7	237.6	230.5	227.3	224.1	220.8	217.6
55°	222.8	212.8	202.9	196.3	193.2	190.0	186.9	183.7
57.5°	189.2	180.1	171.0	165.1	162.4	159.8	157.1	154.4
60°	166.0	157.6	149.1	143.6	140.9	138.2	135.6	132.9
62.5°	145.9	137.9	129.8	125.0	123.4	121.8	120.2	118.6
65°	118.7	113.0	107.4	104.3	103.8	103.3	102.8	102.3
67.5°	95.8	93.2	90.6	89.1	88.5	88.0	87.5	86.9
70°	83.3	81.7	80.0	78.8	78.2	77.5	76.8	76.2
72.5°	72.5	71.1	69.7	68.8	68.4	68.0	67.6	67.2
75°	57.4	56.3	55.1	54.4	54.3	54.1	53.9	53.8
77.5°	43.5	42.8	42.2	41.7	41.4	41.2	40.9	40.6
80°	34.5	33.9	33.2	32.9	32.9	32.9	32.9	32.9
82.5°	26.1	25.7	25.3	25.1	25.1	25.1	25.1	25.1
85°	14.2	14.2	14.2	14.2	14.2	14.2	14.2	14.2
87.5°	9.5	9.1	9.3	9.3	9.3	9.3	9.3	9.3
90°	25.0	23.5	25.0	25.8	25.8	25.8	25.8	25.8
92.5°	68.2	58.5	51.9	47.1	46.4	43.9	44.6	43.3
95°	204.8	157.1	124.3	107.1	96.9	90.7	88.3	89.1
97.5°	477.9	391.0	306.4	250.0	212.6	193.4	182.0	175.4
100°	713.7	616.8	509.7	415.1	350.2	316.6	293.9	279.8
102.5°	868.2	846.3	767.9	667.7	597.2	539.8	511.5	492.5
105°	949.8	1038.1	1048.3	1022.5	974.0	925.5	891.9	881.0
107.5°	891.0	1024.0	1105.3	1143.2	1149.3	1146.6	1139.9	1125.3
110°	840.3	980.3	1080.3	1144.4	1178.0	1192.9	1199.9	1199.1



TEST NUMBER: P331662

CATALOG NUMBER: SA2XXRDIP-C485D725U835-4F0-1E-UDD-F4

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	794.1	928.3	1035.3	1108.8	1155.5	1180.4	1193.7	1197.9
115°	737.1	857.5	959.9	1040.4	1095.9	1131.9	1152.2	1159.3
117.5°	694.3	800.0	892.9	968.4	1025.0	1063.0	1084.4	1090.3
120°	673.0	770.0	852.8	924.0	978.7	1015.4	1038.1	1045.9
122.5°	656.2	745.0	823.4	887.7	936.8	972.9	993.1	999.6
125°	631.6	712.1	780.9	839.5	884.9	914.6	934.1	940.4
127.5°	607.4	680.2	745.1	799.2	838.8	866.6	883.5	888.5
130°	591.7	659.0	720.7	772.3	810.6	837.2	852.8	859.1
132.5°	576.7	639.0	695.7	744.2	781.9	808.4	822.8	828.4
135°	555.8	607.4	659.0	702.7	736.4	762.2	776.2	779.4
137.5°	539.1	582.2	623.2	661.3	692.0	714.2	726.5	731.2
140°	528.4	566.0	601.9	636.3	661.3	681.6	693.4	698.1
142.5°	519.7	551.6	582.5	611.3	635.1	653.5	664.0	664.9
145°	507.3	533.1	557.4	580.0	598.8	612.1	619.9	622.2
147.5°	497.8	518.1	537.0	553.6	569.1	579.7	585.0	586.4
150°	490.9	508.1	524.5	538.6	550.3	559.7	564.4	565.2
152.5°	484.0	500.0	513.9	526.1	535.3	543.4	546.9	547.0
155°	474.5	487.0	498.7	507.3	515.9	521.4	524.5	523.0
157.5°	463.4	473.9	483.7	490.4	496.5	501.1	502.5	502.5
160°	456.5	465.1	473.7	479.2	484.7	488.6	489.3	489.3
162.5°	449.6	457.0	464.3	468.6	474.0	476.7	477.5	476.8
165°	439.3	444.8	450.3	453.4	456.5	459.6	459.6	458.9
167.5°	429.5	433.7	437.4	440.3	441.7	443.4	443.2	442.3
170°	424.5	426.8	429.9	431.5	432.3	434.6	433.8	432.3
172.5°	418.8	420.6	423.1	424.0	424.8	425.9	425.1	424.2
175°	412.7	413.5	414.3	415.1	415.1	415.9	415.1	413.5
177.5°	408.4	408.4	409.0	409.0	409.0	409.0	408.4	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5

(END OF REPORT)