

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331366-830

Luminaire Tested: **SA2XXDIP-C675D1080U830-4F0-1E-UDD-A**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331366-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1080 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6823.4 lumens  
Efficiency: N/A  
Efficacy: 119.9 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 56.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331366-830  
CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	47	47	47	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	52	42	42	41	35
2	88	81	75	70	80	74	69	65	61	57	54	49	46	44	38	36	35	30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26
4	74	63	56	50	67	58	51	46	48	43	40	39	36	33	31	28	26	22
5	68	57	49	43	61	52	45	40	43	38	34	35	32	29	28	25	23	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	22	23	20	18	16
8	54	42	34	29	49	39	32	27	32	27	24	27	23	20	21	19	17	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13
10	47	35	28	23	43	32	26	22	27	23	19	23	19	16	18	16	14	12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	20215	20215	20215	20215
5°	22663	20345	18029	20345
10°	25968	20179	15603	20179
15°	28727	19809	13785	19809
20°	28290	19411	12565	19411
25°	25509	18884	11794	18884
30°	21080	18040	11231	18040
35°	15364	17156	10831	17156
40°	12271	16115	10608	16115
45°	10723	14908	10305	14908
50°	10078	13742	10105	13742
55°	9292	12555	9833	12555
60°	8512	11296	9416	11296
65°	7755	10166	9005	10166
70°	7039	9064	8403	9064
75°	6245	7829	7442	7829
80°	5374	6481	5997	6481
85°	4817	4817	3557	4817



TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	119.2	1.7
10°-20°	346.6	5.1
20°-30°	503.1	7.4
30°-40°	530.9	7.8
40°-50°	470.0	6.9
50°-60°	375.1	5.5
60°-70°	254.9	3.7
70°-80°	130.7	1.9
80°-90°	34.9	0.5
90°-100°	46.2	0.7
100°-110°	169.4	2.5
110°-120°	452.8	6.6
120°-130°	747.4	11.0
130°-140°	794.9	11.6
140°-150°	738.8	10.8
150°-160°	594.0	8.7
160°-170°	382.8	5.6
170°-180°	131.8	1.9
0°-30°	968.9	14.2
0°-40°	1499.8	22.0
0°-60°	2344.9	34.4
0°-90°	2765.5	40.5
90°-120°	668.4	9.8
90°-150°	2949.4	43.2
90°-180°	4058.0	59.5
0°-180°	6823.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1252	1252	1252	1252	1252	
5°	1398	1255	1112	1255	1398	140
15°	1719	1185	825	1185	1719	474
25°	1432	1060	662	1060	1432	647
35°	780	870	550	870	780	507
45°	470	653	451	653	470	369
55°	330	446	349	446	330	296
65°	203	266	236	266	203	202
75°	100	126	119	126	100	107
85°	26	26	19	26	26	29
90°	27	1	27	1	27	13
95°	43	65	43	65	43	40
105°	76	305	76	305	76	79
115°	82	576	82	576	82	206
125°	857	815	857	815	857	741
135°	1041	1008	1041	1008	1041	802
145°	1187	1169	1187	1169	1187	743
155°	1288	1288	1288	1288	1288	595
165°	1354	1357	1354	1357	1354	382
175°	1380	1388	1380	1388	1380	131
180°	1385	1385	1385	1385	1385	



TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1309.7	1310.0	1310.9	1304.7	1303.9	1303.9	1298.5	1293.9	1288.5	1281.2	1282.0
5°	1398.3	1403.5	1405.4	1399.7	1391.0	1390.1	1381.9	1368.4	1355.8	1345.8	1338.6
7.5°	1503.9	1506.0	1501.3	1493.6	1487.2	1475.7	1460.5	1445.6	1424.7	1405.5	1391.3
10°	1583.9	1586.9	1578.7	1567.6	1558.5	1545.0	1522.9	1500.2	1472.8	1446.3	1425.1
12.5°	1644.7	1651.9	1641.4	1639.9	1624.3	1605.8	1579.4	1568.0	1529.4	1492.5	1469.8
15°	1718.6	1718.2	1719.2	1710.1	1698.5	1695.5	1667.6	1637.4	1583.0	1561.3	1523.8
17.5°	1697.3	1704.6	1708.0	1707.9	1707.6	1705.8	1696.9	1677.7	1650.5	1615.3	1572.0
20°	1646.5	1656.1	1657.6	1668.7	1674.9	1683.1	1686.4	1681.1	1664.3	1634.9	1597.4
22.5°	1568.0	1570.7	1575.2	1592.4	1606.0	1626.5	1637.2	1655.0	1648.5	1634.2	1602.8
25°	1431.9	1427.1	1444.0	1452.6	1483.8	1516.6	1540.2	1566.1	1589.2	1603.2	1594.0
27.5°	1268.5	1261.3	1286.5	1309.5	1334.9	1370.4	1407.1	1450.5	1486.6	1531.7	1547.2
30°	1130.7	1135.0	1159.1	1183.6	1222.1	1272.1	1313.5	1361.2	1412.7	1463.2	1498.3
32.5°	982.1	998.8	1014.0	1051.6	1085.4	1141.3	1201.9	1261.5	1325.7	1383.1	1437.5
35°	779.5	798.7	819.9	847.3	894.9	950.3	1009.5	1089.8	1177.4	1255.8	1320.3
37.5°	656.1	653.0	665.2	684.9	723.6	768.2	836.3	915.8	1018.8	1111.0	1201.9
40°	582.2	580.2	588.9	607.2	636.6	669.3	729.0	798.7	894.5	1007.0	1115.3
42.5°	531.4	532.5	537.3	550.3	570.3	597.3	642.0	701.3	789.0	895.0	1011.3
45°	469.6	473.0	478.2	484.6	496.1	518.2	543.2	585.6	654.9	743.4	857.9
47.5°	425.2	425.3	430.6	436.1	443.0	455.4	475.9	502.4	551.3	623.4	721.8
50°	401.2	397.9	401.8	406.0	413.3	422.0	435.5	460.4	493.1	551.4	633.7
52.5°	372.0	372.1	375.6	377.2	383.7	392.3	404.6	422.0	451.6	497.1	564.8
55°	330.1	332.4	334.4	337.2	343.1	349.3	358.9	370.5	393.6	427.7	477.8
57.5°	290.6	291.3	293.3	298.8	302.5	308.2	317.4	327.8	342.9	368.2	405.8
60°	263.6	263.6	267.5	269.9	274.8	280.5	287.8	297.8	311.3	332.0	362.3
62.5°	239.0	238.7	240.2	244.1	247.8	253.2	260.4	269.0	281.6	300.0	325.0
65°	203.0	202.1	205.0	205.9	209.8	215.1	220.8	230.0	240.1	253.5	275.7
67.5°	168.4	169.6	171.1	173.0	175.0	180.6	184.5	191.0	199.4	210.7	225.6
70°	149.1	149.1	149.1	150.6	153.4	156.4	160.2	165.5	173.7	183.3	196.8
72.5°	127.6	129.1	130.6	129.8	133.5	135.2	139.8	142.8	150.6	156.7	168.7
75°	100.1	100.1	100.1	102.5	104.0	105.4	108.3	111.1	115.0	122.7	128.9
77.5°	74.6	74.5	74.9	75.5	77.1	78.8	79.6	82.3	85.9	89.4	94.7
80°	57.8	58.7	59.2	60.1	60.1	61.1	61.5	64.9	67.4	69.7	73.1
82.5°	44.7	44.9	45.0	45.1	45.5	46.1	47.3	48.4	49.3	51.3	53.9
85°	26.0	25.5	25.5	26.5	26.0	26.0	27.0	27.9	27.9	28.4	29.8
87.5°	15.5	15.4	15.6	15.2	15.1	15.3	15.1	14.4	14.6	14.8	14.8
90°	27.1	26.6	26.2	25.7	25.3	24.5	23.4	22.2	21.1	20.1	18.3
92.5°	27.1	26.8	26.5	26.3	26.0	25.5	25.0	24.4	23.8	23.3	22.3
95°	43.1	43.3	43.5	43.7	44.0	43.5	42.4	41.3	40.2	39.1	37.5
97.5°	57.5	57.2	57.0	56.7	56.5	55.9	55.0	54.1	53.2	52.3	48.7
100°	67.1	66.7	66.3	65.8	65.3	64.3	62.5	60.7	58.9	57.1	53.3
102.5°	71.9	71.4	70.7	70.0	69.5	68.0	65.7	63.3	61.1	58.7	90.4
105°	76.2	75.2	74.4	73.5	72.6	70.9	68.4	66.0	63.5	61.1	121.9
107.5°	78.3	77.5	76.5	75.7	74.8	75.6	78.0	80.6	83.0	85.6	158.4
110°	79.2	78.2	77.4	76.4	75.6	86.2	108.6	130.8	153.1	175.3	239.7



TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	79.9	79.3	78.5	77.9	77.1	117.3	198.6	279.8	361.1	442.2	458.2
115°	82.2	98.2	114.2	130.3	146.3	205.9	309.0	412.0	515.1	618.2	612.7
117.5°	335.5	388.1	440.8	493.5	546.2	585.0	609.9	634.9	659.8	684.8	680.9
120°	611.2	641.2	671.3	701.3	731.4	745.2	742.4	739.8	737.1	734.4	730.5
122.5°	762.7	768.5	774.4	780.2	786.0	788.2	786.6	784.9	783.3	781.7	777.4
125°	856.7	856.0	855.4	854.7	854.0	852.9	851.3	849.8	848.2	846.7	842.4
127.5°	916.0	915.9	915.8	915.6	915.5	914.3	912.0	909.7	907.5	905.2	902.0
130°	952.9	953.1	953.3	953.6	953.8	952.6	950.2	947.7	945.3	942.8	940.4
132.5°	988.9	989.2	989.4	989.6	989.9	988.9	986.8	984.7	982.6	980.5	978.1
135°	1041.0	1041.5	1041.9	1042.4	1042.8	1041.9	1039.7	1037.5	1035.3	1033.0	1031.0
137.5°	1088.5	1089.3	1090.1	1090.8	1091.6	1090.8	1088.6	1086.5	1084.3	1082.1	1079.9
140°	1118.2	1119.3	1120.4	1121.5	1122.7	1122.2	1120.2	1118.2	1116.2	1114.2	1111.7
142.5°	1147.1	1148.2	1149.2	1150.4	1151.5	1151.1	1149.3	1147.5	1145.7	1143.9	1141.0
145°	1187.3	1188.5	1189.6	1190.7	1191.8	1191.6	1190.0	1188.5	1186.8	1185.3	1181.6
147.5°	1222.8	1223.7	1224.6	1225.6	1226.5	1226.4	1225.3	1224.1	1222.9	1221.8	1218.0
150°	1244.4	1245.6	1246.7	1247.7	1248.9	1248.8	1247.5	1246.1	1244.8	1243.4	1239.9
152.5°	1262.9	1264.3	1265.8	1267.2	1268.8	1268.9	1267.5	1266.1	1264.8	1263.5	1260.1
155°	1288.5	1290.3	1292.1	1293.8	1295.6	1295.9	1294.6	1293.2	1291.8	1290.5	1287.9
157.5°	1311.9	1313.7	1315.4	1317.2	1318.9	1319.0	1317.5	1316.0	1314.5	1313.0	1311.1
160°	1325.6	1327.2	1328.7	1330.3	1331.8	1331.9	1330.6	1329.3	1327.9	1326.6	1325.3
162.5°	1336.8	1338.7	1340.7	1342.6	1344.4	1344.7	1343.1	1341.6	1340.1	1338.6	1337.5
165°	1353.7	1355.2	1356.8	1358.3	1359.9	1359.9	1358.3	1356.8	1355.2	1353.7	1353.0
167.5°	1364.2	1366.3	1368.3	1370.3	1372.2	1372.5	1370.9	1369.4	1367.8	1366.3	1365.6
170°	1370.6	1372.7	1374.7	1376.7	1378.7	1378.9	1377.3	1375.8	1374.2	1372.7	1372.2
172.5°	1375.5	1377.5	1379.5	1381.5	1383.6	1383.7	1382.1	1380.6	1379.0	1377.5	1377.1
175°	1379.7	1382.0	1384.1	1386.4	1388.6	1388.9	1387.4	1385.8	1384.3	1382.7	1382.2
177.5°	1382.3	1383.9	1385.5	1387.1	1388.7	1388.9	1387.6	1386.4	1385.2	1383.9	1383.7
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1284.7	1281.6	1279.7	1272.7	1266.6	1260.5	1258.5	1259.2	1250.8	1242.7	1239.3
5°	1334.7	1325.1	1316.0	1303.0	1287.6	1270.7	1262.1	1255.3	1238.5	1220.2	1209.7
7.5°	1379.6	1365.8	1348.2	1323.7	1301.4	1274.9	1258.0	1243.1	1218.4	1192.7	1176.9
10°	1406.9	1388.1	1365.5	1335.7	1308.2	1276.0	1253.4	1230.8	1201.9	1171.1	1151.9
12.5°	1430.4	1405.0	1382.8	1344.5	1312.1	1271.8	1244.9	1213.1	1182.7	1146.1	1127.3
15°	1486.3	1439.6	1397.2	1354.0	1314.0	1257.7	1227.9	1185.1	1145.1	1099.9	1078.3
17.5°	1529.5	1477.1	1410.3	1355.3	1308.7	1246.4	1202.6	1151.3	1104.1	1052.3	1022.9
20°	1554.2	1493.9	1422.3	1356.9	1301.0	1229.8	1182.2	1129.7	1074.4	1016.2	984.4
22.5°	1568.8	1505.5	1434.6	1351.0	1285.6	1216.4	1156.4	1098.9	1042.8	980.1	946.7
25°	1573.4	1515.6	1440.6	1346.2	1266.4	1188.0	1115.8	1060.0	992.1	933.4	884.9
27.5°	1550.5	1509.1	1436.9	1337.2	1244.2	1152.4	1072.0	1008.8	937.2	873.5	824.6
30°	1522.4	1498.3	1428.0	1327.9	1226.4	1127.8	1039.2	967.6	896.4	831.9	781.8
32.5°	1478.8	1473.7	1411.9	1314.8	1207.6	1096.6	1005.0	932.6	853.7	790.3	742.6
35°	1393.5	1416.5	1377.5	1285.6	1172.1	1052.3	953.2	870.4	788.6	728.0	683.2
37.5°	1278.9	1336.2	1326.1	1242.8	1124.2	1004.0	894.6	808.0	730.1	668.9	625.0
40°	1200.0	1273.1	1283.7	1210.1	1090.3	966.7	850.6	764.6	688.5	632.7	588.4
42.5°	1115.3	1200.8	1229.8	1170.8	1053.3	927.4	811.4	722.2	647.0	592.7	553.5
45°	973.4	1086.5	1138.9	1105.2	991.6	862.7	743.4	652.9	584.6	533.6	503.3
47.5°	840.7	964.2	1034.7	1022.8	923.0	795.3	677.4	590.6	524.1	483.3	456.2
50°	746.8	873.7	958.9	962.8	873.7	747.2	628.9	547.1	486.0	448.0	425.8
52.5°	665.2	786.4	879.3	899.7	818.7	697.2	585.4	504.0	450.2	415.2	395.4
55°	558.6	661.1	764.0	801.6	736.6	621.1	517.7	446.0	395.5	371.5	354.1
57.5°	464.4	549.9	645.0	686.5	646.4	547.5	450.5	388.3	347.3	326.2	312.9
60°	414.7	482.1	566.8	616.3	581.7	493.7	409.0	349.8	316.1	297.4	284.8
62.5°	368.5	428.2	499.8	545.2	526.3	443.3	367.4	315.2	286.1	268.4	259.5
65°	304.1	351.3	406.6	448.5	435.9	372.9	310.9	266.1	243.0	229.0	221.8
67.5°	250.4	284.5	322.8	359.5	349.4	304.7	255.0	220.1	202.8	190.9	186.5
70°	216.5	242.5	276.6	306.0	297.8	261.3	221.8	192.0	177.1	166.9	162.6
72.5°	184.2	205.6	231.6	255.6	250.1	219.7	186.8	164.3	152.8	143.5	139.9
75°	139.0	155.4	171.3	187.2	185.7	162.1	142.9	125.5	116.4	109.2	107.7
77.5°	102.6	111.8	122.6	132.1	129.4	115.9	100.9	91.0	84.2	79.4	78.6
80°	78.4	83.7	91.4	98.1	94.8	89.0	77.0	69.7	64.9	60.1	58.2
82.5°	56.8	62.2	66.8	70.4	67.9	62.5	55.0	50.1	47.2	44.0	43.2
85°	29.8	32.7	34.7	35.6	34.7	31.3	27.9	26.0	23.6	22.1	21.7
87.5°	14.8	14.5	14.1	14.5	12.8	12.3	10.3	8.7	8.8	8.9	8.6
90°	16.5	14.7	12.9	10.8	8.4	5.9	3.5	1.0	3.5	5.9	8.4
92.5°	21.5	20.5	19.7	19.3	19.6	19.8	20.0	20.3	20.0	19.8	19.6
95°	36.0	34.4	32.8	35.7	43.1	50.4	57.8	65.1	57.8	50.4	43.1
97.5°	45.1	41.5	37.9	46.5	67.1	87.8	108.6	129.2	108.6	87.8	67.1
100°	49.6	45.7	41.9	55.3	85.9	116.3	146.8	177.4	146.8	116.3	85.9
102.5°	122.1	153.7	185.4	204.4	210.8	217.4	223.8	230.3	223.8	217.4	210.8
105°	182.7	243.5	304.3	331.3	324.6	317.9	311.3	304.6	311.3	317.9	324.6
107.5°	231.4	304.3	377.2	410.9	405.5	400.1	394.7	389.4	394.7	400.1	405.5
110°	304.1	368.3	432.7	462.6	457.9	453.3	448.6	443.8	448.6	453.3	457.9





TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	474.1	489.9	505.9	511.7	507.6	503.4	499.4	495.2	499.4	503.4	507.6
115°	607.1	601.5	596.0	591.3	587.5	583.7	579.9	576.2	579.9	583.7	587.5
117.5°	677.1	673.3	669.4	665.4	661.2	657.0	652.7	648.5	652.7	657.0	661.2
120°	726.4	722.5	718.4	714.7	711.4	708.0	704.7	701.3	704.7	708.0	711.4
122.5°	773.0	768.6	764.3	760.3	756.9	753.3	749.8	746.3	749.8	753.3	756.9
125°	838.2	834.0	829.7	826.1	823.3	820.4	817.5	814.6	817.5	820.4	823.3
127.5°	898.8	895.7	892.5	889.4	886.2	883.0	879.8	876.6	879.8	883.0	886.2
130°	937.9	935.5	933.0	930.0	926.5	922.9	919.4	915.8	919.4	922.9	926.5
132.5°	975.6	973.2	970.7	968.0	965.0	962.0	958.9	955.8	958.9	962.0	965.0
135°	1029.0	1027.0	1025.0	1022.2	1018.7	1015.1	1011.5	1008.0	1011.5	1015.1	1018.7
137.5°	1077.6	1075.3	1073.0	1070.6	1068.2	1065.6	1063.2	1060.6	1063.2	1065.6	1068.2
140°	1109.3	1106.8	1104.4	1102.3	1100.5	1098.7	1096.9	1095.1	1096.9	1098.7	1100.5
142.5°	1138.2	1135.4	1132.7	1130.4	1128.8	1127.2	1125.6	1124.0	1125.6	1127.2	1128.8
145°	1177.7	1173.9	1170.2	1168.4	1168.7	1168.8	1169.0	1169.3	1169.0	1168.8	1168.7
147.5°	1214.3	1210.6	1206.8	1205.4	1206.3	1207.1	1208.0	1208.8	1208.0	1207.1	1206.3
150°	1236.3	1232.8	1229.2	1228.2	1229.7	1231.3	1232.8	1234.4	1232.8	1231.3	1229.7
152.5°	1256.7	1253.3	1249.9	1249.2	1250.8	1252.5	1254.3	1256.0	1254.3	1252.5	1250.8
155°	1285.2	1282.5	1279.9	1279.5	1281.5	1283.6	1285.5	1287.5	1285.5	1283.6	1281.5
157.5°	1309.2	1307.4	1305.5	1305.4	1307.1	1308.8	1310.5	1312.2	1310.5	1308.8	1307.1
160°	1323.9	1322.6	1321.3	1321.3	1322.6	1323.9	1325.3	1326.6	1325.3	1323.9	1322.6
162.5°	1336.3	1335.1	1334.0	1334.1	1335.4	1336.7	1338.1	1339.4	1338.1	1336.7	1335.4
165°	1352.4	1351.6	1350.9	1351.3	1352.6	1354.0	1355.3	1356.7	1355.3	1354.0	1352.6
167.5°	1365.0	1364.4	1363.8	1364.1	1365.5	1366.8	1368.2	1369.5	1368.2	1366.8	1365.5
170°	1371.8	1371.4	1370.9	1371.4	1372.7	1374.0	1375.4	1376.7	1375.4	1374.0	1372.7
172.5°	1376.6	1376.2	1375.7	1376.2	1377.5	1378.8	1380.2	1381.5	1380.2	1378.8	1377.5
175°	1381.9	1381.4	1380.9	1381.5	1383.1	1384.6	1386.2	1387.7	1386.2	1384.6	1383.1
177.5°	1383.6	1383.4	1383.2	1383.7	1385.0	1386.2	1387.5	1388.7	1387.5	1386.2	1385.0
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1235.4	1233.1	1225.0	1220.8	1213.8	1207.3	1203.1	1205.0	1206.5	1205.8	1204.6
5°	1200.0	1190.8	1176.9	1164.9	1156.2	1140.3	1133.6	1130.2	1127.4	1124.0	1120.6
7.5°	1157.8	1143.4	1123.4	1106.3	1090.1	1070.4	1059.1	1052.3	1045.5	1037.8	1031.1
10°	1127.8	1107.6	1086.5	1062.3	1043.1	1025.3	1009.5	998.9	989.3	980.1	973.4
12.5°	1096.3	1073.0	1046.8	1013.9	992.7	967.2	964.8	946.1	931.1	925.5	917.6
15°	1046.0	1013.3	980.1	941.1	924.3	901.2	886.7	872.3	859.3	850.2	847.8
17.5°	988.9	946.6	913.6	885.6	858.0	834.3	821.0	809.5	798.8	786.6	784.9
20°	945.5	908.9	872.8	848.3	819.9	795.8	779.5	767.9	758.7	751.6	745.3
22.5°	904.3	864.2	831.2	804.4	776.4	757.0	744.0	732.9	725.3	717.3	711.4
25°	838.2	806.9	770.8	740.5	717.4	704.9	694.3	684.7	679.9	674.6	667.9
27.5°	780.3	745.6	711.8	688.3	668.1	657.0	649.4	642.9	638.4	635.3	631.5
30°	739.5	704.4	678.0	654.9	638.0	627.0	622.2	618.3	613.0	611.1	609.2
32.5°	700.3	668.6	646.0	625.9	609.9	602.7	598.2	594.8	590.7	588.7	584.8
35°	644.7	618.3	596.2	585.0	572.1	565.8	562.5	557.6	553.8	551.9	551.4
37.5°	592.5	569.5	555.0	540.7	535.3	531.4	526.8	523.5	522.4	522.1	521.6
40°	558.6	539.9	526.9	515.3	512.9	507.1	503.3	500.4	500.4	500.9	500.4
42.5°	527.8	511.0	499.5	489.6	486.7	483.2	479.4	479.2	480.0	481.6	480.0
45°	481.2	469.1	460.9	456.1	450.8	447.4	447.0	448.5	448.9	449.4	450.8
47.5°	438.2	430.3	422.8	417.5	415.2	414.6	414.1	416.6	418.9	419.7	422.0
50°	412.8	403.7	397.5	394.1	392.1	391.2	392.1	395.0	396.9	399.4	400.8
52.5°	384.4	377.9	373.5	371.0	370.2	370.8	371.0	374.3	377.3	378.1	378.9
55°	345.0	340.2	339.2	334.9	336.8	336.3	338.7	340.6	343.6	346.4	346.9
57.5°	305.8	301.9	299.3	299.6	300.2	302.4	304.3	307.7	310.9	313.9	314.1
60°	279.6	277.6	276.2	276.2	277.1	280.0	282.5	285.8	287.8	289.6	291.1
62.5°	255.7	253.7	252.3	253.1	255.6	257.3	260.1	261.9	263.8	265.8	266.5
65°	217.9	217.0	218.5	219.4	219.9	222.3	225.6	227.1	229.0	230.0	233.4
67.5°	183.2	183.4	183.2	184.5	187.4	187.9	191.1	194.4	194.8	196.7	198.9
70°	159.8	160.7	161.6	162.6	165.0	166.0	168.4	169.8	171.7	173.2	174.7
72.5°	138.2	138.4	139.3	139.1	141.2	143.3	145.3	146.8	148.6	150.5	151.9
75°	106.3	106.3	107.3	107.7	110.2	112.6	112.1	113.1	115.0	116.9	117.9
77.5°	77.7	76.6	77.7	78.1	78.9	81.0	81.3	82.7	84.8	84.2	85.3
80°	59.2	57.8	59.2	59.7	59.7	62.1	62.1	63.1	64.5	63.1	64.5
82.5°	42.2	41.6	42.6	42.7	43.5	43.5	44.4	44.6	46.0	45.3	46.0
85°	21.2	20.7	21.2	20.7	21.2	21.7	21.7	21.2	21.2	22.1	20.7
87.5°	8.7	8.8	8.7	9.0	9.0	9.0	8.9	9.0	9.3	8.8	8.9
90°	10.8	12.9	14.7	16.5	18.3	20.1	21.1	22.2	23.4	24.5	25.3
92.5°	19.3	19.7	20.5	21.5	22.3	23.3	23.8	24.4	25.0	25.5	26.0
95°	35.7	32.8	34.4	36.0	37.5	39.1	40.2	41.3	42.4	43.5	44.0
97.5°	46.5	37.9	41.5	45.1	48.7	52.3	53.2	54.1	55.0	55.9	56.5
100°	55.3	41.9	45.7	49.6	53.3	57.1	58.9	60.7	62.5	64.3	65.3
102.5°	204.4	185.4	153.7	122.1	90.4	58.7	61.1	63.3	65.7	68.0	69.5
105°	331.3	304.3	243.5	182.7	121.9	61.1	63.5	66.0	68.4	70.9	72.6
107.5°	410.9	377.2	304.3	231.4	158.4	85.6	83.0	80.6	78.0	75.6	74.8
110°	462.6	432.7	368.3	304.1	239.7	175.3	153.1	130.8	108.6	86.2	75.6



TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	511.7	505.9	489.9	474.1	458.2	442.2	361.1	279.8	198.6	117.3	77.1
115°	591.3	596.0	601.5	607.1	612.7	618.2	515.1	412.0	309.0	205.9	146.3
117.5°	665.4	669.4	673.3	677.1	680.9	684.8	659.8	634.9	609.9	585.0	546.2
120°	714.7	718.4	722.5	726.4	730.5	734.4	737.1	739.8	742.4	745.2	731.4
122.5°	760.3	764.3	768.6	773.0	777.4	781.7	783.3	784.9	786.6	788.2	786.0
125°	826.1	829.7	834.0	838.2	842.4	846.7	848.2	849.8	851.3	852.9	854.0
127.5°	889.4	892.5	895.7	898.8	902.0	905.2	907.5	909.7	912.0	914.3	915.5
130°	930.0	933.0	935.5	937.9	940.4	942.8	945.3	947.7	950.2	952.6	953.8
132.5°	968.0	970.7	973.2	975.6	978.1	980.5	982.6	984.7	986.8	988.9	989.9
135°	1022.2	1025.0	1027.0	1029.0	1031.0	1033.0	1035.3	1037.5	1039.7	1041.9	1042.8
137.5°	1070.6	1073.0	1075.3	1077.6	1079.9	1082.1	1084.3	1086.5	1088.6	1090.8	1091.6
140°	1102.3	1104.4	1106.8	1109.3	1111.7	1114.2	1116.2	1118.2	1120.2	1122.2	1122.7
142.5°	1130.4	1132.7	1135.4	1138.2	1141.0	1143.9	1145.7	1147.5	1149.3	1151.1	1151.5
145°	1168.4	1170.2	1173.9	1177.7	1181.6	1185.3	1186.8	1188.5	1190.0	1191.6	1191.8
147.5°	1205.4	1206.8	1210.6	1214.3	1218.0	1221.8	1222.9	1224.1	1225.3	1226.4	1226.5
150°	1228.2	1229.2	1232.8	1236.3	1239.9	1243.4	1244.8	1246.1	1247.5	1248.8	1248.9
152.5°	1249.2	1249.9	1253.3	1256.7	1260.1	1263.5	1264.8	1266.1	1267.5	1268.9	1268.8
155°	1279.5	1279.9	1282.5	1285.2	1287.9	1290.5	1291.8	1293.2	1294.6	1295.9	1295.6
157.5°	1305.4	1305.5	1307.4	1309.2	1311.1	1313.0	1314.5	1316.0	1317.5	1319.0	1318.9
160°	1321.3	1321.3	1322.6	1323.9	1325.3	1326.6	1327.9	1329.3	1330.6	1331.9	1331.8
162.5°	1334.1	1334.0	1335.1	1336.3	1337.5	1338.6	1340.1	1341.6	1343.1	1344.7	1344.4
165°	1351.3	1350.9	1351.6	1352.4	1353.0	1353.7	1355.2	1356.8	1358.3	1359.9	1359.9
167.5°	1364.1	1363.8	1364.4	1365.0	1365.6	1366.3	1367.8	1369.4	1370.9	1372.5	1372.2
170°	1371.4	1370.9	1371.4	1371.8	1372.2	1372.7	1374.2	1375.8	1377.3	1378.9	1378.7
172.5°	1376.2	1375.7	1376.2	1376.6	1377.1	1377.5	1379.0	1380.6	1382.1	1383.7	1383.6
175°	1381.5	1380.9	1381.4	1381.9	1382.2	1382.7	1384.3	1385.8	1387.4	1388.9	1388.6
177.5°	1383.7	1383.2	1383.4	1383.6	1383.7	1383.9	1385.2	1386.4	1387.6	1388.9	1388.7
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1200.8	1200.0	1200.0	1196.6	1200.0	1200.0	1200.8	1204.6	1205.8	1206.5	1205.0
5°	1113.9	1112.4	1110.0	1112.4	1110.0	1112.4	1113.9	1120.6	1124.0	1127.4	1130.2
7.5°	1027.9	1022.2	1021.3	1015.6	1021.3	1022.2	1027.9	1031.1	1037.8	1045.5	1052.3
10°	965.2	961.3	960.8	951.7	960.8	961.3	965.2	973.4	980.1	989.3	998.9
12.5°	917.5	908.2	910.0	904.7	910.0	908.2	917.5	917.6	925.5	931.1	946.1
15°	834.8	834.8	832.8	824.7	832.8	834.8	834.8	847.8	850.2	859.3	872.3
17.5°	775.4	774.5	769.9	772.1	769.9	774.5	775.4	784.9	786.6	798.8	809.5
20°	740.0	737.2	731.3	731.3	731.3	737.2	740.0	745.3	751.6	758.7	767.9
22.5°	706.5	706.3	700.2	702.1	700.2	706.3	706.5	711.4	717.3	725.3	732.9
25°	667.3	663.5	660.6	662.0	660.6	663.5	667.3	667.9	674.6	679.9	684.7
27.5°	630.2	628.1	627.9	624.0	627.9	628.1	630.2	631.5	635.3	638.4	642.9
30°	608.7	603.9	604.8	602.4	604.8	603.9	608.7	609.2	611.1	613.0	618.3
32.5°	584.0	582.3	581.4	579.3	581.4	582.3	584.0	584.8	588.7	590.7	594.8
35°	550.4	550.9	548.6	549.5	548.6	550.9	550.4	551.4	551.9	553.8	557.6
37.5°	521.1	522.6	521.5	521.8	521.5	522.6	521.1	521.6	522.1	522.4	523.5
40°	501.8	501.8	501.8	503.3	501.8	501.8	501.8	500.4	500.9	500.4	500.4
42.5°	483.3	482.6	481.8	481.7	481.8	482.6	483.3	480.0	481.6	480.0	479.2
45°	451.8	453.3	453.7	451.3	453.7	453.3	451.8	450.8	449.4	448.9	448.5
47.5°	423.2	423.4	423.2	425.4	423.2	423.4	423.2	422.0	419.7	418.9	416.6
50°	403.2	402.3	403.2	402.3	403.2	402.3	403.2	400.8	399.4	396.9	395.0
52.5°	382.0	382.2	381.6	381.4	381.6	382.2	382.0	378.9	378.1	377.3	374.3
55°	348.8	349.8	349.3	349.3	349.3	349.8	348.8	346.9	346.4	343.6	340.6
57.5°	314.5	315.4	316.0	313.9	316.0	315.4	314.5	314.1	313.9	310.9	307.7
60°	290.6	293.0	292.6	291.6	292.6	293.0	290.6	291.1	289.6	287.8	285.8
62.5°	268.7	269.6	269.5	269.3	269.5	269.6	268.7	266.5	265.8	263.8	261.9
65°	234.8	235.7	234.3	235.7	234.3	235.7	234.8	233.4	230.0	229.0	227.1
67.5°	198.3	198.6	199.7	200.4	199.7	198.6	198.3	198.9	196.7	194.8	194.4
70°	175.6	175.1	176.5	178.0	176.5	175.1	175.6	174.7	173.2	171.7	169.8
72.5°	151.7	152.8	152.3	153.4	152.3	152.8	151.7	151.9	150.5	148.6	146.8
75°	116.9	118.4	117.9	119.3	117.9	118.4	116.9	117.9	116.9	115.0	113.1
77.5°	84.5	84.6	84.5	85.3	84.5	84.6	84.5	85.3	84.2	84.8	82.7
80°	64.5	63.5	62.6	64.5	62.6	63.5	64.5	64.5	63.1	64.5	63.1
82.5°	44.9	45.4	44.5	44.5	44.5	45.4	44.9	46.0	45.3	46.0	44.6
85°	20.7	20.2	19.2	19.2	19.2	20.2	20.7	20.7	22.1	21.2	21.2
87.5°	9.0	8.7	8.8	8.5	8.8	8.7	9.0	8.9	8.8	9.3	9.0
90°	25.7	26.2	26.6	27.1	26.6	26.2	25.7	25.3	24.5	23.4	22.2
92.5°	26.3	26.5	26.8	27.1	26.8	26.5	26.3	26.0	25.5	25.0	24.4
95°	43.7	43.5	43.3	43.1	43.3	43.5	43.7	44.0	43.5	42.4	41.3
97.5°	56.7	57.0	57.2	57.5	57.2	57.0	56.7	56.5	55.9	55.0	54.1
100°	65.8	66.3	66.7	67.1	66.7	66.3	65.8	65.3	64.3	62.5	60.7
102.5°	70.0	70.7	71.4	71.9	71.4	70.7	70.0	69.5	68.0	65.7	63.3
105°	73.5	74.4	75.2	76.2	75.2	74.4	73.5	72.6	70.9	68.4	66.0
107.5°	75.7	76.5	77.5	78.3	77.5	76.5	75.7	74.8	75.6	78.0	80.6
110°	76.4	77.4	78.2	79.2	78.2	77.4	76.4	75.6	86.2	108.6	130.8



TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	77.9	78.5	79.3	79.9	79.3	78.5	77.9	77.1	117.3	198.6	279.8
115°	130.3	114.2	98.2	82.2	98.2	114.2	130.3	146.3	205.9	309.0	412.0
117.5°	493.5	440.8	388.1	335.5	388.1	440.8	493.5	546.2	585.0	609.9	634.9
120°	701.3	671.3	641.2	611.2	641.2	671.3	701.3	731.4	745.2	742.4	739.8
122.5°	780.2	774.4	768.5	762.7	768.5	774.4	780.2	786.0	788.2	786.6	784.9
125°	854.7	855.4	856.0	856.7	856.0	855.4	854.7	854.0	852.9	851.3	849.8
127.5°	915.6	915.8	915.9	916.0	915.9	915.8	915.6	915.5	914.3	912.0	909.7
130°	953.6	953.3	953.1	952.9	953.1	953.3	953.6	953.8	952.6	950.2	947.7
132.5°	989.6	989.4	989.2	988.9	989.2	989.4	989.6	989.9	988.9	986.8	984.7
135°	1042.4	1041.9	1041.5	1041.0	1041.5	1041.9	1042.4	1042.8	1041.9	1039.7	1037.5
137.5°	1090.8	1090.1	1089.3	1088.5	1089.3	1090.1	1090.8	1091.6	1090.8	1088.6	1086.5
140°	1121.5	1120.4	1119.3	1118.2	1119.3	1120.4	1121.5	1122.7	1122.2	1120.2	1118.2
142.5°	1150.4	1149.2	1148.2	1147.1	1148.2	1149.2	1150.4	1151.5	1151.1	1149.3	1147.5
145°	1190.7	1189.6	1188.5	1187.3	1188.5	1189.6	1190.7	1191.8	1191.6	1190.0	1188.5
147.5°	1225.6	1224.6	1223.7	1222.8	1223.7	1224.6	1225.6	1226.5	1226.4	1225.3	1224.1
150°	1247.7	1246.7	1245.6	1244.4	1245.6	1246.7	1247.7	1248.9	1248.8	1247.5	1246.1
152.5°	1267.2	1265.8	1264.3	1262.9	1264.3	1265.8	1267.2	1268.8	1268.9	1267.5	1266.1
155°	1293.8	1292.1	1290.3	1288.5	1290.3	1292.1	1293.8	1295.6	1295.9	1294.6	1293.2
157.5°	1317.2	1315.4	1313.7	1311.9	1313.7	1315.4	1317.2	1318.9	1319.0	1317.5	1316.0
160°	1330.3	1328.7	1327.2	1325.6	1327.2	1328.7	1330.3	1331.8	1331.9	1330.6	1329.3
162.5°	1342.6	1340.7	1338.7	1336.8	1338.7	1340.7	1342.6	1344.4	1344.7	1343.1	1341.6
165°	1358.3	1356.8	1355.2	1353.7	1355.2	1356.8	1358.3	1359.9	1359.9	1358.3	1356.8
167.5°	1370.3	1368.3	1366.3	1364.2	1366.3	1368.3	1370.3	1372.2	1372.5	1370.9	1369.4
170°	1376.7	1374.7	1372.7	1370.6	1372.7	1374.7	1376.7	1378.7	1378.9	1377.3	1375.8
172.5°	1381.5	1379.5	1377.5	1375.5	1377.5	1379.5	1381.5	1383.6	1383.7	1382.1	1380.6
175°	1386.4	1384.1	1382.0	1379.7	1382.0	1384.1	1386.4	1388.6	1388.9	1387.4	1385.8
177.5°	1387.1	1385.5	1383.9	1382.3	1383.9	1385.5	1387.1	1388.7	1388.9	1387.6	1386.4
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1203.1	1207.3	1213.8	1220.8	1225.0	1233.1	1235.4	1239.3	1242.7	1250.8	1259.2
5°	1133.6	1140.3	1156.2	1164.9	1176.9	1190.8	1200.0	1209.7	1220.2	1238.5	1255.3
7.5°	1059.1	1070.4	1090.1	1106.3	1123.4	1143.4	1157.8	1176.9	1192.7	1218.4	1243.1
10°	1009.5	1025.3	1043.1	1062.3	1086.5	1107.6	1127.8	1151.9	1171.1	1201.9	1230.8
12.5°	964.8	967.2	992.7	1013.9	1046.8	1073.0	1096.3	1127.3	1146.1	1182.7	1213.1
15°	886.7	901.2	924.3	941.1	980.1	1013.3	1046.0	1078.3	1099.9	1145.1	1185.1
17.5°	821.0	834.3	858.0	885.6	913.6	946.6	988.9	1022.9	1052.3	1104.1	1151.3
20°	779.5	795.8	819.9	848.3	872.8	908.9	945.5	984.4	1016.2	1074.4	1129.7
22.5°	744.0	757.0	776.4	804.4	831.2	864.2	904.3	946.7	980.1	1042.8	1098.9
25°	694.3	704.9	717.4	740.5	770.8	806.9	838.2	884.9	933.4	992.1	1060.0
27.5°	649.4	657.0	668.1	688.3	711.8	745.6	780.3	824.6	873.5	937.2	1008.8
30°	622.2	627.0	638.0	654.9	678.0	704.4	739.5	781.8	831.9	896.4	967.6
32.5°	598.2	602.7	609.9	625.9	646.0	668.6	700.3	742.6	790.3	853.7	932.6
35°	562.5	565.8	572.1	585.0	596.2	618.3	644.7	683.2	728.0	788.6	870.4
37.5°	526.8	531.4	535.3	540.7	555.0	569.5	592.5	625.0	668.9	730.1	808.0
40°	503.3	507.1	512.9	515.3	526.9	539.9	558.6	588.4	632.7	688.5	764.6
42.5°	479.4	483.2	486.7	489.6	499.5	511.0	527.8	553.5	592.7	647.0	722.2
45°	447.0	447.4	450.8	456.1	460.9	469.1	481.2	503.3	533.6	584.6	652.9
47.5°	414.1	414.6	415.2	417.5	422.8	430.3	438.2	456.2	483.3	524.1	590.6
50°	392.1	391.2	392.1	394.1	397.5	403.7	412.8	425.8	448.0	486.0	547.1
52.5°	371.0	370.8	370.2	371.0	373.5	377.9	384.4	395.4	415.2	450.2	504.0
55°	338.7	336.3	336.8	334.9	339.2	340.2	345.0	354.1	371.5	395.5	446.0
57.5°	304.3	302.4	300.2	299.6	299.3	301.9	305.8	312.9	326.2	347.3	388.3
60°	282.5	280.0	277.1	276.2	276.2	277.6	279.6	284.8	297.4	316.1	349.8
62.5°	260.1	257.3	255.6	253.1	252.3	253.7	255.7	259.5	268.4	286.1	315.2
65°	225.6	222.3	219.9	219.4	218.5	217.0	217.9	221.8	229.0	243.0	266.1
67.5°	191.1	187.9	187.4	184.5	183.2	183.4	183.2	186.5	190.9	202.8	220.1
70°	168.4	166.0	165.0	162.6	161.6	160.7	159.8	162.6	166.9	177.1	192.0
72.5°	145.3	143.3	141.2	139.1	139.3	138.4	138.2	139.9	143.5	152.8	164.3
75°	112.1	112.6	110.2	107.7	107.3	106.3	106.3	107.7	109.2	116.4	125.5
77.5°	81.3	81.0	78.9	78.1	77.7	76.6	77.7	78.6	79.4	84.2	91.0
80°	62.1	62.1	59.7	59.7	59.2	57.8	59.2	58.2	60.1	64.9	69.7
82.5°	44.4	43.5	43.5	42.7	42.6	41.6	42.2	43.2	44.0	47.2	50.1
85°	21.7	21.7	21.2	20.7	21.2	20.7	21.2	21.7	22.1	23.6	26.0
87.5°	8.9	9.0	9.0	9.0	8.7	8.8	8.7	8.6	8.9	8.8	8.7
90°	21.1	20.1	18.3	16.5	14.7	12.9	10.8	8.4	5.9	3.5	1.0
92.5°	23.8	23.3	22.3	21.5	20.5	19.7	19.3	19.6	19.8	20.0	20.3
95°	40.2	39.1	37.5	36.0	34.4	32.8	35.7	43.1	50.4	57.8	65.1
97.5°	53.2	52.3	48.7	45.1	41.5	37.9	46.5	67.1	87.8	108.6	129.2
100°	58.9	57.1	53.3	49.6	45.7	41.9	55.3	85.9	116.3	146.8	177.4
102.5°	61.1	58.7	90.4	122.1	153.7	185.4	204.4	210.8	217.4	223.8	230.3
105°	63.5	61.1	121.9	182.7	243.5	304.3	331.3	324.6	317.9	311.3	304.6
107.5°	83.0	85.6	158.4	231.4	304.3	377.2	410.9	405.5	400.1	394.7	389.4
110°	153.1	175.3	239.7	304.1	368.3	432.7	462.6	457.9	453.3	448.6	443.8



TEST NUMBER: P331366-830  
 CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	361.1	442.2	458.2	474.1	489.9	505.9	511.7	507.6	503.4	499.4	495.2
115°	515.1	618.2	612.7	607.1	601.5	596.0	591.3	587.5	583.7	579.9	576.2
117.5°	659.8	684.8	680.9	677.1	673.3	669.4	665.4	661.2	657.0	652.7	648.5
120°	737.1	734.4	730.5	726.4	722.5	718.4	714.7	711.4	708.0	704.7	701.3
122.5°	783.3	781.7	777.4	773.0	768.6	764.3	760.3	756.9	753.3	749.8	746.3
125°	848.2	846.7	842.4	838.2	834.0	829.7	826.1	823.3	820.4	817.5	814.6
127.5°	907.5	905.2	902.0	898.8	895.7	892.5	889.4	886.2	883.0	879.8	876.6
130°	945.3	942.8	940.4	937.9	935.5	933.0	930.0	926.5	922.9	919.4	915.8
132.5°	982.6	980.5	978.1	975.6	973.2	970.7	968.0	965.0	962.0	958.9	955.8
135°	1035.3	1033.0	1031.0	1029.0	1027.0	1025.0	1022.2	1018.7	1015.1	1011.5	1008.0
137.5°	1084.3	1082.1	1079.9	1077.6	1075.3	1073.0	1070.6	1068.2	1065.6	1063.2	1060.6
140°	1116.2	1114.2	1111.7	1109.3	1106.8	1104.4	1102.3	1100.5	1098.7	1096.9	1095.1
142.5°	1145.7	1143.9	1141.0	1138.2	1135.4	1132.7	1130.4	1128.8	1127.2	1125.6	1124.0
145°	1186.8	1185.3	1181.6	1177.7	1173.9	1170.2	1168.4	1168.7	1168.8	1169.0	1169.3
147.5°	1222.9	1221.8	1218.0	1214.3	1210.6	1206.8	1205.4	1206.3	1207.1	1208.0	1208.8
150°	1244.8	1243.4	1239.9	1236.3	1232.8	1229.2	1228.2	1229.7	1231.3	1232.8	1234.4
152.5°	1264.8	1263.5	1260.1	1256.7	1253.3	1249.9	1249.2	1250.8	1252.5	1254.3	1256.0
155°	1291.8	1290.5	1287.9	1285.2	1282.5	1279.9	1279.5	1281.5	1283.6	1285.5	1287.5
157.5°	1314.5	1313.0	1311.1	1309.2	1307.4	1305.5	1305.4	1307.1	1308.8	1310.5	1312.2
160°	1327.9	1326.6	1325.3	1323.9	1322.6	1321.3	1321.3	1322.6	1323.9	1325.3	1326.6
162.5°	1340.1	1338.6	1337.5	1336.3	1335.1	1334.0	1334.1	1335.4	1336.7	1338.1	1339.4
165°	1355.2	1353.7	1353.0	1352.4	1351.6	1350.9	1351.3	1352.6	1354.0	1355.3	1356.7
167.5°	1367.8	1366.3	1365.6	1365.0	1364.4	1363.8	1364.1	1365.5	1366.8	1368.2	1369.5
170°	1374.2	1372.7	1372.2	1371.8	1371.4	1370.9	1371.4	1372.7	1374.0	1375.4	1376.7
172.5°	1379.0	1377.5	1377.1	1376.6	1376.2	1375.7	1376.2	1377.5	1378.8	1380.2	1381.5
175°	1384.3	1382.7	1382.2	1381.9	1381.4	1380.9	1381.5	1383.1	1384.6	1386.2	1387.7
177.5°	1385.2	1383.9	1383.7	1383.6	1383.4	1383.2	1383.7	1385.0	1386.2	1387.5	1388.7
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1258.5	1260.5	1266.6	1272.7	1279.7	1281.6	1284.7	1282.0	1281.2	1288.5	1293.9
5°	1262.1	1270.7	1287.6	1303.0	1316.0	1325.1	1334.7	1338.6	1345.8	1355.8	1368.4
7.5°	1258.0	1274.9	1301.4	1323.7	1348.2	1365.8	1379.6	1391.3	1405.5	1424.7	1445.6
10°	1253.4	1276.0	1308.2	1335.7	1365.5	1388.1	1406.9	1425.1	1446.3	1472.8	1500.2
12.5°	1244.9	1271.8	1312.1	1344.5	1382.8	1405.0	1430.4	1469.8	1492.5	1529.4	1568.0
15°	1227.9	1257.7	1314.0	1354.0	1397.2	1439.6	1486.3	1523.8	1561.3	1583.0	1637.4
17.5°	1202.6	1246.4	1308.7	1355.3	1410.3	1477.1	1529.5	1572.0	1615.3	1650.5	1677.7
20°	1182.2	1229.8	1301.0	1356.9	1422.3	1493.9	1554.2	1597.4	1634.9	1664.3	1681.1
22.5°	1156.4	1216.4	1285.6	1351.0	1434.6	1505.5	1568.8	1602.8	1634.2	1648.5	1655.0
25°	1115.8	1188.0	1266.4	1346.2	1440.6	1515.6	1573.4	1594.0	1603.2	1589.2	1566.1
27.5°	1072.0	1152.4	1244.2	1337.2	1436.9	1509.1	1550.5	1547.2	1531.7	1486.6	1450.5
30°	1039.2	1127.8	1226.4	1327.9	1428.0	1498.3	1522.4	1498.3	1463.2	1412.7	1361.2
32.5°	1005.0	1096.6	1207.6	1314.8	1411.9	1473.7	1478.8	1437.5	1383.1	1325.7	1261.5
35°	953.2	1052.3	1172.1	1285.6	1377.5	1416.5	1393.5	1320.3	1255.8	1177.4	1089.8
37.5°	894.6	1004.0	1124.2	1242.8	1326.1	1336.2	1278.9	1201.9	1111.0	1018.8	915.8
40°	850.6	966.7	1090.3	1210.1	1283.7	1273.1	1200.0	1115.3	1007.0	894.5	798.7
42.5°	811.4	927.4	1053.3	1170.8	1229.8	1200.8	1115.3	1011.3	895.0	789.0	701.3
45°	743.4	862.7	991.6	1105.2	1138.9	1086.5	973.4	857.9	743.4	654.9	585.6
47.5°	677.4	795.3	923.0	1022.8	1034.7	964.2	840.7	721.8	623.4	551.3	502.4
50°	628.9	747.2	873.7	962.8	958.9	873.7	746.8	633.7	551.4	493.1	460.4
52.5°	585.4	697.2	818.7	899.7	879.3	786.4	665.2	564.8	497.1	451.6	422.0
55°	517.7	621.1	736.6	801.6	764.0	661.1	558.6	477.8	427.7	393.6	370.5
57.5°	450.5	547.5	646.4	686.5	645.0	549.9	464.4	405.8	368.2	342.9	327.8
60°	409.0	493.7	581.7	616.3	566.8	482.1	414.7	362.3	332.0	311.3	297.8
62.5°	367.4	443.3	526.3	545.2	499.8	428.2	368.5	325.0	300.0	281.6	269.0
65°	310.9	372.9	435.9	448.5	406.6	351.3	304.1	275.7	253.5	240.1	230.0
67.5°	255.0	304.7	349.4	359.5	322.8	284.5	250.4	225.6	210.7	199.4	191.0
70°	221.8	261.3	297.8	306.0	276.6	242.5	216.5	196.8	183.3	173.7	165.5
72.5°	186.8	219.7	250.1	255.6	231.6	205.6	184.2	168.7	156.7	150.6	142.8
75°	142.9	162.1	185.7	187.2	171.3	155.4	139.0	128.9	122.7	115.0	111.1
77.5°	100.9	115.9	129.4	132.1	122.6	111.8	102.6	94.7	89.4	85.9	82.3
80°	77.0	89.0	94.8	98.1	91.4	83.7	78.4	73.1	69.7	67.4	64.9
82.5°	55.0	62.5	67.9	70.4	66.8	62.2	56.8	53.9	51.3	49.3	48.4
85°	27.9	31.3	34.7	35.6	34.7	32.7	29.8	29.8	28.4	27.9	27.9
87.5°	10.3	12.3	12.8	14.5	14.1	14.5	14.8	14.8	14.8	14.6	14.4
90°	3.5	5.9	8.4	10.8	12.9	14.7	16.5	18.3	20.1	21.1	22.2
92.5°	20.0	19.8	19.6	19.3	19.7	20.5	21.5	22.3	23.3	23.8	24.4
95°	57.8	50.4	43.1	35.7	32.8	34.4	36.0	37.5	39.1	40.2	41.3
97.5°	108.6	87.8	67.1	46.5	37.9	41.5	45.1	48.7	52.3	53.2	54.1
100°	146.8	116.3	85.9	55.3	41.9	45.7	49.6	53.3	57.1	58.9	60.7
102.5°	223.8	217.4	210.8	204.4	185.4	153.7	122.1	90.4	58.7	61.1	63.3
105°	311.3	317.9	324.6	331.3	304.3	243.5	182.7	121.9	61.1	63.5	66.0
107.5°	394.7	400.1	405.5	410.9	377.2	304.3	231.4	158.4	85.6	83.0	80.6
110°	448.6	453.3	457.9	462.6	432.7	368.3	304.1	239.7	175.3	153.1	130.8





TEST NUMBER: P331366-830  
 CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	499.4	503.4	507.6	511.7	505.9	489.9	474.1	458.2	442.2	361.1	279.8
115°	579.9	583.7	587.5	591.3	596.0	601.5	607.1	612.7	618.2	515.1	412.0
117.5°	652.7	657.0	661.2	665.4	669.4	673.3	677.1	680.9	684.8	659.8	634.9
120°	704.7	708.0	711.4	714.7	718.4	722.5	726.4	730.5	734.4	737.1	739.8
122.5°	749.8	753.3	756.9	760.3	764.3	768.6	773.0	777.4	781.7	783.3	784.9
125°	817.5	820.4	823.3	826.1	829.7	834.0	838.2	842.4	846.7	848.2	849.8
127.5°	879.8	883.0	886.2	889.4	892.5	895.7	898.8	902.0	905.2	907.5	909.7
130°	919.4	922.9	926.5	930.0	933.0	935.5	937.9	940.4	942.8	945.3	947.7
132.5°	958.9	962.0	965.0	968.0	970.7	973.2	975.6	978.1	980.5	982.6	984.7
135°	1011.5	1015.1	1018.7	1022.2	1025.0	1027.0	1029.0	1031.0	1033.0	1035.3	1037.5
137.5°	1063.2	1065.6	1068.2	1070.6	1073.0	1075.3	1077.6	1079.9	1082.1	1084.3	1086.5
140°	1096.9	1098.7	1100.5	1102.3	1104.4	1106.8	1109.3	1111.7	1114.2	1116.2	1118.2
142.5°	1125.6	1127.2	1128.8	1130.4	1132.7	1135.4	1138.2	1141.0	1143.9	1145.7	1147.5
145°	1169.0	1168.8	1168.7	1168.4	1170.2	1173.9	1177.7	1181.6	1185.3	1186.8	1188.5
147.5°	1208.0	1207.1	1206.3	1205.4	1206.8	1210.6	1214.3	1218.0	1221.8	1222.9	1224.1
150°	1232.8	1231.3	1229.7	1228.2	1229.2	1232.8	1236.3	1239.9	1243.4	1244.8	1246.1
152.5°	1254.3	1252.5	1250.8	1249.2	1249.9	1253.3	1256.7	1260.1	1263.5	1264.8	1266.1
155°	1285.5	1283.6	1281.5	1279.5	1279.9	1282.5	1285.2	1287.9	1290.5	1291.8	1293.2
157.5°	1310.5	1308.8	1307.1	1305.4	1305.5	1307.4	1309.2	1311.1	1313.0	1314.5	1316.0
160°	1325.3	1323.9	1322.6	1321.3	1321.3	1322.6	1323.9	1325.3	1326.6	1327.9	1329.3
162.5°	1338.1	1336.7	1335.4	1334.1	1334.0	1335.1	1336.3	1337.5	1338.6	1340.1	1341.6
165°	1355.3	1354.0	1352.6	1351.3	1350.9	1351.6	1352.4	1353.0	1353.7	1355.2	1356.8
167.5°	1368.2	1366.8	1365.5	1364.1	1363.8	1364.4	1365.0	1365.6	1366.3	1367.8	1369.4
170°	1375.4	1374.0	1372.7	1371.4	1370.9	1371.4	1371.8	1372.2	1372.7	1374.2	1375.8
172.5°	1380.2	1378.8	1377.5	1376.2	1375.7	1376.2	1376.6	1377.1	1377.5	1379.0	1380.6
175°	1386.2	1384.6	1383.1	1381.5	1380.9	1381.4	1381.9	1382.2	1382.7	1384.3	1385.8
177.5°	1387.5	1386.2	1385.0	1383.7	1383.2	1383.4	1383.6	1383.7	1383.9	1385.2	1386.4
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7



TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0	1252.0
2.5°	1298.5	1303.9	1303.9	1304.7	1310.9	1310.0	1309.7
5°	1381.9	1390.1	1391.0	1399.7	1405.4	1403.5	1398.3
7.5°	1460.5	1475.7	1487.2	1493.6	1501.3	1506.0	1503.9
10°	1522.9	1545.0	1558.5	1567.6	1578.7	1586.9	1583.9
12.5°	1579.4	1605.8	1624.3	1639.9	1641.4	1651.9	1644.7
15°	1667.6	1695.5	1698.5	1710.1	1719.2	1718.2	1718.6
17.5°	1696.9	1705.8	1707.6	1707.9	1708.0	1704.6	1697.3
20°	1686.4	1683.1	1674.9	1668.7	1657.6	1656.1	1646.5
22.5°	1637.2	1626.5	1606.0	1592.4	1575.2	1570.7	1568.0
25°	1540.2	1516.6	1483.8	1452.6	1444.0	1427.1	1431.9
27.5°	1407.1	1370.4	1334.9	1309.5	1286.5	1261.3	1268.5
30°	1313.5	1272.1	1222.1	1183.6	1159.1	1135.0	1130.7
32.5°	1201.9	1141.3	1085.4	1051.6	1014.0	998.8	982.1
35°	1009.5	950.3	894.9	847.3	819.9	798.7	779.5
37.5°	836.3	768.2	723.6	684.9	665.2	653.0	656.1
40°	729.0	669.3	636.6	607.2	588.9	580.2	582.2
42.5°	642.0	597.3	570.3	550.3	537.3	532.5	531.4
45°	543.2	518.2	496.1	484.6	478.2	473.0	469.6
47.5°	475.9	455.4	443.0	436.1	430.6	425.3	425.2
50°	435.5	422.0	413.3	406.0	401.8	397.9	401.2
52.5°	404.6	392.3	383.7	377.2	375.6	372.1	372.0
55°	358.9	349.3	343.1	337.2	334.4	332.4	330.1
57.5°	317.4	308.2	302.5	298.8	293.3	291.3	290.6
60°	287.8	280.5	274.8	269.9	267.5	263.6	263.6
62.5°	260.4	253.2	247.8	244.1	240.2	238.7	239.0
65°	220.8	215.1	209.8	205.9	205.0	202.1	203.0
67.5°	184.5	180.6	175.0	173.0	171.1	169.6	168.4
70°	160.2	156.4	153.4	150.6	149.1	149.1	149.1
72.5°	139.8	135.2	133.5	129.8	130.6	129.1	127.6
75°	108.3	105.4	104.0	102.5	100.1	100.1	100.1
77.5°	79.6	78.8	77.1	75.5	74.9	74.5	74.6
80°	61.5	61.1	60.1	60.1	59.2	58.7	57.8
82.5°	47.3	46.1	45.5	45.1	45.0	44.9	44.7
85°	27.0	26.0	26.0	26.5	25.5	25.5	26.0
87.5°	15.1	15.3	15.1	15.2	15.6	15.4	15.5
90°	23.4	24.5	25.3	25.7	26.2	26.6	27.1
92.5°	25.0	25.5	26.0	26.3	26.5	26.8	27.1
95°	42.4	43.5	44.0	43.7	43.5	43.3	43.1
97.5°	55.0	55.9	56.5	56.7	57.0	57.2	57.5
100°	62.5	64.3	65.3	65.8	66.3	66.7	67.1
102.5°	65.7	68.0	69.5	70.0	70.7	71.4	71.9
105°	68.4	70.9	72.6	73.5	74.4	75.2	76.2
107.5°	78.0	75.6	74.8	75.7	76.5	77.5	78.3
110°	108.6	86.2	75.6	76.4	77.4	78.2	79.2



TEST NUMBER: P331366-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	198.6	117.3	77.1	77.9	78.5	79.3	79.9
115°	309.0	205.9	146.3	130.3	114.2	98.2	82.2
117.5°	609.9	585.0	546.2	493.5	440.8	388.1	335.5
120°	742.4	745.2	731.4	701.3	671.3	641.2	611.2
122.5°	786.6	788.2	786.0	780.2	774.4	768.5	762.7
125°	851.3	852.9	854.0	854.7	855.4	856.0	856.7
127.5°	912.0	914.3	915.5	915.6	915.8	915.9	916.0
130°	950.2	952.6	953.8	953.6	953.3	953.1	952.9
132.5°	986.8	988.9	989.9	989.6	989.4	989.2	988.9
135°	1039.7	1041.9	1042.8	1042.4	1041.9	1041.5	1041.0
137.5°	1088.6	1090.8	1091.6	1090.8	1090.1	1089.3	1088.5
140°	1120.2	1122.2	1122.7	1121.5	1120.4	1119.3	1118.2
142.5°	1149.3	1151.1	1151.5	1150.4	1149.2	1148.2	1147.1
145°	1190.0	1191.6	1191.8	1190.7	1189.6	1188.5	1187.3
147.5°	1225.3	1226.4	1226.5	1225.6	1224.6	1223.7	1222.8
150°	1247.5	1248.8	1248.9	1247.7	1246.7	1245.6	1244.4
152.5°	1267.5	1268.9	1268.8	1267.2	1265.8	1264.3	1262.9
155°	1294.6	1295.9	1295.6	1293.8	1292.1	1290.3	1288.5
157.5°	1317.5	1319.0	1318.9	1317.2	1315.4	1313.7	1311.9
160°	1330.6	1331.9	1331.8	1330.3	1328.7	1327.2	1325.6
162.5°	1343.1	1344.7	1344.4	1342.6	1340.7	1338.7	1336.8
165°	1358.3	1359.9	1359.9	1358.3	1356.8	1355.2	1353.7
167.5°	1370.9	1372.5	1372.2	1370.3	1368.3	1366.3	1364.2
170°	1377.3	1378.9	1378.7	1376.7	1374.7	1372.7	1370.6
172.5°	1382.1	1383.7	1383.6	1381.5	1379.5	1377.5	1375.5
175°	1387.4	1388.9	1388.6	1386.4	1384.1	1382.0	1379.7
177.5°	1387.6	1388.9	1388.7	1387.1	1385.5	1383.9	1382.3
180°	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7	1384.7

(END OF REPORT)