

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331699

Luminaire Tested: **SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331699
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1080 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6847.9 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	44	44	44	37
1	95	91	88	85	86	83	80	77	68	65	64	53	52	51	40	39	38	32
2	87	81	75	70	79	73	69	64	60	56	54	47	45	43	36	35	33	28
3	80	71	64	59	72	65	59	55	53	49	46	42	40	37	32	31	29	25
4	74	63	56	50	67	58	52	47	48	43	40	38	35	32	29	27	26	22
5	68	57	49	44	61	52	45	41	43	38	34	35	31	29	27	25	23	19
6	63	51	44	38	57	47	40	36	39	34	30	32	28	25	25	22	20	17
7	58	46	39	34	53	43	36	31	36	31	27	29	25	23	23	20	18	16
8	54	42	35	30	49	39	32	28	33	28	24	27	23	20	21	19	17	14
9	50	39	32	27	46	36	29	25	30	25	22	25	21	19	20	17	15	13
10	47	36	29	24	43	33	27	23	28	23	20	23	19	17	18	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	23720	23720	23720	23720
5°	26491	23869	21162	23869
10°	29391	23700	18344	23700
15°	30837	23353	14454	23353
20°	26734	22838	12507	22838
25°	17533	22133	11166	22133
30°	11801	21280	10107	21280
35°	9558	20203	9116	20203
40°	8500	19032	8435	19032
45°	7693	17657	7531	17657
50°	7001	16297	6975	16297
55°	6581	14787	6494	14787
60°	5506	13401	5438	13401
65°	4642	12168	5265	12168
70°	4291	10867	4966	10867
75°	4011	9457	4585	9457
80°	3701	7782	4082	7782
85°	3409	6150	3594	6150



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	139.3	2.0
10°-20°	388.0	5.7
20°-30°	500.0	7.3
30°-40°	475.2	6.9
40°-50°	407.1	5.9
50°-60°	310.0	4.5
60°-70°	196.0	2.9
70°-80°	97.9	1.4
80°-90°	29.1	0.4
90°-100°	49.0	0.7
100°-110°	179.7	2.6
110°-120°	480.4	7.0
120°-130°	793.0	11.6
130°-140°	843.3	12.3
140°-150°	783.8	11.4
150°-160°	630.2	9.2
160°-170°	406.1	5.9
170°-180°	139.8	2.0
0°-30°	1027.3	15.0
0°-40°	1502.5	21.9
0°-60°	2219.6	32.4
0°-90°	2542.5	37.1
90°-120°	709.1	10.4
90°-150°	3129.2	45.7
90°-180°	4305.0	62.9
0°-180°	6847.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1634	1473	1306	1473	1634	161
15°	1845	1397	865	1397	1845	498
25°	984	1242	627	1242	984	467
35°	485	1025	462	1025	485	310
45°	337	773	330	773	337	261
55°	234	525	231	525	234	205
65°	122	318	138	318	122	124
75°	64	152	74	152	64	68
85°	18	33	19	33	18	20
90°	29	1	29	1	29	13
95°	46	69	46	69	46	43
105°	81	323	81	323	81	84
115°	87	611	87	611	87	218
125°	909	864	909	864	909	786
135°	1104	1069	1104	1069	1104	851
145°	1260	1241	1260	1241	1260	788
155°	1367	1366	1367	1366	1367	631
165°	1436	1439	1436	1439	1436	405
175°	1464	1472	1464	1472	1464	139
180°	1469	1469	1469	1469	1469	



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1528.7	1529.9	1531.2	1528.3	1528.3	1525.8	1520.5	1516.5	1505.0	1503.4	1503.4
5°	1634.5	1633.4	1635.5	1628.9	1619.7	1617.6	1607.9	1595.2	1581.9	1567.1	1564.0
7.5°	1739.6	1738.1	1734.0	1732.9	1725.8	1710.4	1694.8	1678.2	1656.1	1634.6	1623.8
10°	1792.7	1809.6	1799.3	1781.5	1785.1	1761.1	1748.3	1726.4	1708.0	1675.8	1668.7
12.5°	1845.0	1851.6	1848.4	1838.2	1833.6	1817.0	1799.8	1780.7	1746.8	1717.9	1692.8
15°	1844.8	1854.5	1857.0	1854.0	1856.5	1855.5	1846.3	1830.5	1800.9	1769.2	1741.7
17.5°	1708.6	1715.3	1732.1	1743.4	1757.7	1787.9	1802.8	1808.6	1804.2	1786.2	1766.8
20°	1555.9	1544.6	1591.6	1615.6	1636.0	1687.0	1730.9	1747.8	1774.8	1774.3	1769.2
22.5°	1339.4	1342.1	1386.6	1415.1	1474.7	1525.7	1575.8	1639.2	1691.5	1726.1	1746.4
25°	984.2	1003.6	1048.0	1086.8	1153.1	1248.1	1334.3	1434.4	1528.8	1603.3	1674.3
27.5°	739.1	740.6	775.8	811.6	851.0	928.8	1037.4	1156.9	1291.5	1402.6	1530.4
30°	633.0	629.9	644.7	666.7	700.3	760.6	842.2	959.7	1093.9	1261.3	1410.4
32.5°	557.8	558.0	569.2	585.4	613.4	654.0	709.9	805.3	932.2	1096.8	1271.5
35°	484.9	484.4	492.6	504.3	516.1	542.1	580.4	630.4	717.7	871.3	1050.0
37.5°	432.7	434.9	438.9	446.2	459.2	473.7	496.7	530.3	592.4	683.3	833.5
40°	403.3	404.3	409.9	416.0	423.7	434.9	453.8	480.8	526.3	598.8	708.5
42.5°	376.3	377.3	381.3	387.0	393.0	404.3	419.9	443.3	480.1	536.7	627.2
45°	336.9	336.9	340.5	343.0	349.7	359.9	372.6	392.0	417.6	459.4	519.6
47.5°	299.9	300.0	302.4	306.8	311.0	318.9	331.5	347.3	365.9	398.3	449.7
50°	278.7	279.2	280.7	284.3	286.9	294.0	303.7	317.5	336.9	361.9	404.8
52.5°	261.6	261.2	263.2	264.7	266.5	271.6	278.8	291.0	308.3	330.1	365.6
55°	233.8	231.7	234.8	237.4	238.9	240.9	245.0	252.7	267.5	285.9	312.4
57.5°	199.1	198.3	200.4	202.8	207.6	213.1	216.5	221.4	229.1	242.3	268.6
60°	170.5	170.5	175.1	176.6	182.2	189.4	196.5	200.6	208.3	216.9	236.3
62.5°	145.2	145.6	147.7	149.3	152.4	161.2	171.2	180.2	187.4	195.7	208.6
65°	121.5	122.5	122.5	123.5	125.6	127.6	131.7	138.8	151.6	163.3	173.0
67.5°	103.1	103.4	103.7	104.7	105.3	107.5	109.1	112.3	115.3	126.4	138.4
70°	90.9	92.4	91.9	92.9	93.4	94.4	96.5	98.0	102.6	105.2	112.3
72.5°	79.4	80.5	80.4	81.1	82.4	82.6	84.2	85.8	88.7	90.9	94.7
75°	64.3	63.8	64.3	65.3	65.8	66.4	66.4	68.4	69.9	72.0	74.5
77.5°	49.6	50.1	50.0	50.1	50.2	51.1	51.0	52.0	53.5	54.5	55.7
80°	39.8	40.3	39.8	40.3	40.8	41.3	40.8	41.3	42.9	43.9	43.9
82.5°	30.8	30.9	31.2	31.3	31.4	31.5	32.3	32.4	33.5	33.3	33.7
85°	18.4	17.9	17.9	17.9	18.4	18.9	18.4	18.4	18.9	18.9	18.9
87.5°	12.3	12.6	12.5	12.4	12.3	12.1	11.9	12.1	11.4	11.6	10.8
90°	28.7	28.2	27.8	27.3	26.8	26.0	24.8	23.6	22.4	21.3	19.4
92.5°	28.7	28.4	28.1	27.9	27.6	27.1	26.5	25.9	25.3	24.7	23.7
95°	45.7	45.9	46.2	46.4	46.7	46.2	45.0	43.8	42.6	41.5	39.8
97.5°	61.0	60.7	60.5	60.2	59.9	59.3	58.3	57.4	56.4	55.5	51.7
100°	71.2	70.8	70.3	69.8	69.3	68.2	66.3	64.4	62.5	60.6	56.6
102.5°	76.3	75.7	75.0	74.3	73.7	72.1	69.7	67.2	64.8	62.3	59.9
105°	80.8	79.8	78.9	78.0	77.0	75.2	72.6	70.0	67.4	64.8	62.3
107.5°	83.1	82.2	81.2	80.3	79.4	80.2	82.8	85.5	88.1	90.8	168.1
110°	84.0	83.0	82.1	81.1	80.2	91.5	115.2	138.8	162.4	186.0	254.3



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.8	84.1	83.3	82.6	81.8	124.5	210.7	296.9	383.1	469.2	486.1
115°	87.2	104.2	121.2	138.2	155.2	218.4	327.8	437.1	546.5	655.9	650.0
117.5°	355.9	411.8	467.7	523.6	579.5	620.7	647.1	673.6	700.0	726.5	722.4
120°	648.5	680.3	712.2	744.1	776.0	790.6	787.7	784.9	782.0	779.2	775.0
122.5°	809.2	815.4	821.6	827.8	833.9	836.2	834.5	832.8	831.1	829.4	824.8
125°	908.9	908.2	907.5	906.8	906.1	904.9	903.2	901.6	899.9	898.3	893.8
127.5°	971.8	971.7	971.6	971.4	971.3	970.0	967.6	965.2	962.8	960.4	957.0
130°	1011.0	1011.2	1011.4	1011.7	1011.9	1010.7	1008.1	1005.5	1002.9	1000.3	997.7
132.5°	1049.2	1049.5	1049.7	1049.9	1050.2	1049.2	1047.0	1044.7	1042.5	1040.3	1037.7
135°	1104.5	1105.0	1105.4	1105.9	1106.4	1105.4	1103.1	1100.7	1098.4	1096.0	1093.9
137.5°	1154.9	1155.7	1156.5	1157.3	1158.1	1157.3	1155.0	1152.7	1150.4	1148.1	1145.7
140°	1186.4	1187.5	1188.7	1189.9	1191.1	1190.6	1188.5	1186.4	1184.2	1182.1	1179.5
142.5°	1217.0	1218.2	1219.3	1220.5	1221.7	1221.3	1219.4	1217.4	1215.5	1213.6	1210.6
145°	1259.7	1260.9	1262.1	1263.3	1264.4	1264.2	1262.5	1260.9	1259.2	1257.6	1253.6
147.5°	1297.3	1298.3	1299.3	1300.3	1301.3	1301.2	1300.0	1298.7	1297.5	1296.3	1292.3
150°	1320.3	1321.5	1322.7	1323.8	1325.0	1324.9	1323.5	1322.1	1320.7	1319.2	1315.5
152.5°	1339.9	1341.4	1343.0	1344.5	1346.1	1346.2	1344.8	1343.3	1341.9	1340.5	1336.9
155°	1367.1	1369.0	1370.9	1372.7	1374.6	1374.9	1373.5	1372.0	1370.6	1369.2	1366.4
157.5°	1391.9	1393.8	1395.6	1397.5	1399.3	1399.4	1397.8	1396.2	1394.6	1393.0	1391.0
160°	1406.4	1408.1	1409.7	1411.4	1413.0	1413.1	1411.7	1410.3	1408.9	1407.5	1406.1
162.5°	1418.3	1420.3	1422.4	1424.4	1426.4	1426.7	1425.0	1423.4	1421.8	1420.2	1419.0
165°	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8	1441.1	1439.5	1437.8	1436.2	1435.5
167.5°	1447.4	1449.6	1451.7	1453.8	1455.9	1456.2	1454.5	1452.9	1451.2	1449.6	1448.9
170°	1454.2	1456.4	1458.5	1460.6	1462.7	1463.0	1461.3	1459.7	1458.0	1456.4	1455.9
172.5°	1459.3	1461.5	1463.6	1465.7	1467.9	1468.1	1466.4	1464.8	1463.1	1461.5	1461.0
175°	1463.8	1466.2	1468.5	1470.9	1473.3	1473.6	1472.0	1470.3	1468.7	1467.0	1466.5
177.5°	1466.6	1468.3	1470.0	1471.7	1473.4	1473.6	1472.2	1470.9	1469.6	1468.3	1468.1
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1504.2	1500.9	1498.1	1490.7	1487.1	1478.9	1477.7	1477.3	1466.6	1456.4	1453.6
5°	1555.9	1547.7	1535.4	1521.1	1506.3	1491.0	1480.8	1472.7	1452.2	1432.8	1421.6
7.5°	1607.9	1590.4	1569.2	1542.2	1519.6	1494.3	1475.5	1458.7	1429.7	1401.9	1383.2
10°	1646.7	1618.1	1590.1	1552.8	1523.7	1495.1	1468.6	1445.6	1412.9	1376.2	1350.1
12.5°	1670.8	1639.4	1600.7	1564.2	1526.6	1490.2	1454.7	1425.2	1386.8	1348.8	1317.9
15°	1703.4	1669.7	1622.7	1570.7	1522.2	1474.7	1433.9	1397.1	1347.1	1301.7	1263.9
17.5°	1730.0	1683.7	1633.2	1573.0	1516.9	1456.5	1403.9	1357.0	1301.3	1246.5	1202.0
20°	1738.6	1692.7	1634.5	1574.2	1507.9	1436.9	1380.3	1329.2	1269.5	1209.8	1158.7
22.5°	1733.3	1697.6	1632.8	1560.8	1492.8	1418.5	1354.5	1295.3	1229.1	1168.1	1108.9
25°	1697.3	1685.0	1623.8	1545.1	1467.6	1381.3	1307.3	1242.4	1166.9	1101.6	1037.2
27.5°	1613.2	1639.7	1601.7	1518.0	1431.7	1339.2	1256.0	1182.2	1103.8	1030.3	966.2
30°	1532.4	1593.1	1576.8	1499.2	1402.7	1311.9	1218.5	1141.4	1057.7	982.1	918.8
32.5°	1421.7	1522.1	1538.0	1473.1	1373.3	1273.5	1175.6	1098.9	1011.5	931.9	870.2
35°	1245.5	1395.6	1464.5	1423.1	1323.1	1215.4	1114.3	1025.0	937.2	858.6	797.3
37.5°	1035.3	1239.7	1354.5	1357.5	1265.6	1153.6	1043.6	954.9	865.0	787.8	721.6
40°	898.9	1120.4	1270.0	1303.2	1225.6	1104.6	993.3	903.0	815.2	739.6	663.6
42.5°	776.4	997.1	1181.0	1238.7	1177.0	1056.8	945.2	850.7	765.4	693.9	616.2
45°	627.9	820.8	1023.5	1126.6	1092.4	981.1	863.2	773.3	693.2	631.4	556.9
47.5°	529.6	665.6	861.7	1001.2	1000.6	899.0	783.0	697.0	622.7	564.8	504.4
50°	473.7	592.1	758.0	916.3	929.5	844.3	734.0	648.8	579.4	518.6	470.1
52.5°	423.5	521.1	670.2	821.9	859.7	785.9	678.9	600.2	532.8	477.0	435.4
55°	357.8	433.4	546.7	688.6	745.8	693.7	598.8	525.3	470.6	423.7	387.9
57.5°	302.7	359.4	450.3	564.6	631.1	598.4	520.0	460.3	413.6	371.1	342.9
60°	268.0	314.4	391.5	487.0	560.5	537.5	470.6	415.0	375.2	338.4	311.9
62.5°	235.3	275.2	341.3	418.8	486.2	476.7	422.0	375.4	340.5	307.0	284.5
65°	189.4	218.5	270.0	330.8	384.9	389.5	350.2	318.5	287.4	260.8	240.9
67.5°	150.8	169.8	206.1	257.3	297.8	312.3	288.3	264.1	239.4	218.9	201.6
70°	127.1	142.4	169.0	210.3	247.6	262.9	249.1	230.2	208.8	191.9	177.1
72.5°	103.0	117.9	137.5	167.8	199.8	216.3	211.5	198.0	180.6	166.6	152.6
75°	77.6	82.2	95.5	115.9	140.9	155.2	158.8	151.6	137.8	127.1	118.9
77.5°	57.4	60.1	66.5	77.2	93.5	106.3	111.5	110.7	101.2	94.9	87.3
80°	45.9	47.5	50.5	55.1	67.4	80.1	83.7	83.7	77.1	74.5	66.9
82.5°	34.9	36.0	37.9	40.4	46.1	57.3	61.3	62.1	57.9	54.5	48.5
85°	19.9	19.4	20.4	21.9	23.0	26.0	32.2	33.2	32.2	28.1	26.5
87.5°	10.4	10.5	10.1	9.2	9.1	9.0	10.5	12.1	10.9	10.2	9.9
90°	17.5	15.6	13.7	11.5	8.9	6.3	3.7	1.1	3.7	6.3	8.9
92.5°	22.8	21.8	20.9	20.5	20.8	21.0	21.2	21.5	21.2	21.0	20.8
95°	38.2	36.5	34.8	37.9	45.7	53.5	61.3	69.1	61.3	53.5	45.7
97.5°	47.8	44.0	40.2	49.3	71.2	93.2	115.2	137.1	115.2	93.2	71.2
100°	52.6	48.5	44.5	58.7	91.1	123.4	155.8	188.2	155.8	123.4	91.1
102.5°	129.5	163.1	196.7	216.9	223.7	230.6	237.4	244.3	237.4	230.6	223.7
105°	193.8	258.3	322.8	351.5	344.4	337.3	330.3	323.2	330.3	337.3	344.4
107.5°	245.5	322.8	400.2	436.0	430.2	424.5	418.8	413.1	418.8	424.5	430.2
110°	322.6	390.8	459.1	490.8	485.8	480.9	475.9	470.9	475.9	480.9	485.8



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	503.0	519.8	536.7	542.9	538.5	534.1	529.8	525.4	529.8	534.1	538.5
115°	644.1	638.2	632.3	627.3	623.3	619.3	615.3	611.3	615.3	619.3	623.3
117.5°	718.4	714.3	710.2	706.0	701.5	697.0	692.5	688.0	692.5	697.0	701.5
120°	770.7	766.5	762.2	758.3	754.8	751.2	747.7	744.1	747.7	751.2	754.8
122.5°	820.1	815.5	810.9	806.7	803.0	799.2	795.5	791.8	795.5	799.2	803.0
125°	889.3	884.8	880.3	876.5	873.5	870.4	867.3	864.3	867.3	870.4	873.5
127.5°	953.6	950.3	946.9	943.6	940.2	936.8	933.4	930.0	933.4	936.8	940.2
130°	995.1	992.5	989.9	986.7	983.0	979.2	975.4	971.6	975.4	979.2	983.0
132.5°	1035.1	1032.5	1029.9	1027.0	1023.8	1020.6	1017.4	1014.1	1017.4	1020.6	1023.8
135°	1091.7	1089.6	1087.5	1084.5	1080.8	1077.0	1073.2	1069.4	1073.2	1077.0	1080.8
137.5°	1143.3	1140.9	1138.4	1135.9	1133.3	1130.6	1128.0	1125.3	1128.0	1130.6	1133.3
140°	1176.9	1174.3	1171.7	1169.5	1167.6	1165.7	1163.8	1161.9	1163.8	1165.7	1167.6
142.5°	1207.6	1204.6	1201.7	1199.3	1197.6	1195.9	1194.2	1192.5	1194.2	1195.9	1197.6
145°	1249.5	1245.5	1241.5	1239.6	1239.9	1240.1	1240.3	1240.6	1240.3	1240.1	1239.9
147.5°	1288.3	1284.4	1280.4	1278.9	1279.8	1280.7	1281.6	1282.5	1281.6	1280.7	1279.8
150°	1311.7	1307.9	1304.1	1303.1	1304.7	1306.4	1308.0	1309.7	1308.0	1306.4	1304.7
152.5°	1333.3	1329.7	1326.1	1325.3	1327.1	1328.9	1330.8	1332.6	1330.8	1328.9	1327.1
155°	1363.5	1360.7	1357.9	1357.5	1359.6	1361.8	1363.9	1366.0	1363.9	1361.8	1359.6
157.5°	1389.0	1387.1	1385.1	1385.0	1386.8	1388.6	1390.4	1392.2	1390.4	1388.6	1386.8
160°	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1406.1	1404.6	1403.2
162.5°	1417.8	1416.5	1415.3	1415.4	1416.8	1418.2	1419.7	1421.1	1419.7	1418.2	1416.8
165°	1434.8	1434.0	1433.3	1433.7	1435.1	1436.5	1437.9	1439.4	1437.9	1436.5	1435.1
167.5°	1448.2	1447.6	1446.9	1447.3	1448.7	1450.1	1451.6	1453.0	1451.6	1450.1	1448.7
170°	1455.4	1455.0	1454.5	1455.0	1456.4	1457.8	1459.2	1460.6	1459.2	1457.8	1456.4
172.5°	1460.5	1460.1	1459.6	1460.1	1461.5	1462.9	1464.3	1465.7	1464.3	1462.9	1461.5
175°	1466.1	1465.6	1465.1	1465.7	1467.4	1469.0	1470.7	1472.3	1470.7	1469.0	1467.4
177.5°	1467.9	1467.7	1467.5	1468.1	1469.4	1470.7	1472.1	1473.4	1472.1	1470.7	1469.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1448.3	1445.4	1440.1	1431.9	1427.0	1418.4	1412.7	1416.0	1416.8	1416.0	1415.2
5°	1409.4	1398.6	1383.8	1369.5	1356.3	1342.0	1333.8	1330.2	1323.1	1319.0	1317.0
7.5°	1362.3	1343.8	1322.9	1298.0	1276.8	1254.7	1243.4	1237.7	1223.1	1215.2	1208.2
10°	1327.2	1298.1	1277.2	1244.5	1224.6	1195.5	1175.6	1176.1	1156.2	1144.9	1136.8
12.5°	1288.4	1256.4	1221.6	1192.2	1164.5	1141.2	1117.2	1107.5	1086.3	1075.5	1053.5
15°	1224.1	1186.8	1150.1	1110.2	1082.2	1045.9	1011.2	968.8	934.6	905.0	896.9
17.5°	1153.8	1107.7	1070.8	1024.1	976.0	915.0	874.8	850.2	829.6	814.0	802.3
20°	1105.6	1058.7	1019.4	948.9	884.1	842.8	813.2	794.3	772.8	756.0	746.8
22.5°	1055.0	1006.0	952.4	873.8	823.3	790.1	763.7	742.0	727.5	714.3	706.0
25°	983.1	929.5	841.2	787.1	746.3	711.6	693.2	679.9	664.6	646.7	638.6
27.5°	907.2	821.9	758.5	718.3	679.3	656.7	640.2	620.4	606.7	598.7	590.2
30°	850.4	765.2	715.7	671.8	644.2	619.2	599.8	588.6	575.3	561.5	555.9
32.5°	787.1	719.0	671.6	635.0	607.0	585.7	570.4	552.2	542.6	534.1	522.4
35°	708.5	657.0	613.6	584.0	557.4	540.1	522.2	511.5	494.1	487.0	482.4
37.5°	641.9	597.2	564.9	533.6	512.6	493.4	482.5	465.4	457.9	448.0	438.3
40°	604.4	560.5	529.3	503.8	480.3	466.0	452.3	438.5	427.2	422.7	410.9
42.5°	566.0	530.3	499.1	471.1	455.4	440.3	422.9	412.8	401.1	393.7	386.4
45°	513.0	481.4	454.8	431.8	414.5	398.7	387.4	370.6	364.0	349.1	343.0
47.5°	466.5	437.0	411.7	389.9	372.9	362.6	346.2	333.0	322.4	313.3	305.5
50°	433.4	408.9	384.4	365.0	349.7	334.9	318.0	311.4	295.0	290.4	285.9
52.5°	403.2	379.9	357.4	338.4	323.1	308.7	293.9	285.2	274.2	269.6	266.3
55°	360.9	338.4	317.0	300.1	284.8	270.0	260.8	250.1	245.0	241.4	237.4
57.5°	318.4	298.2	281.8	264.7	249.3	237.6	226.9	220.5	215.2	210.5	205.6
60°	291.5	272.1	257.3	241.4	225.6	215.9	207.8	200.1	194.0	186.8	184.8
62.5°	262.9	245.9	232.4	216.9	203.2	194.3	186.5	179.3	171.9	161.5	158.6
65°	223.6	210.3	196.0	183.3	171.0	162.3	151.1	142.9	139.9	138.8	138.3
67.5°	188.1	175.5	163.2	150.2	139.0	131.0	125.3	124.0	121.9	121.3	119.9
70°	164.4	152.6	140.4	128.1	117.4	115.9	113.8	111.8	109.2	108.2	107.2
72.5°	143.1	131.0	118.7	108.9	104.3	102.4	100.4	98.3	96.6	95.6	94.9
75°	109.7	98.5	90.4	86.8	84.2	82.7	79.6	78.1	77.1	75.5	75.0
77.5°	79.0	72.7	68.9	66.7	64.0	62.4	60.6	59.1	58.0	57.7	56.9
80°	60.2	57.2	54.6	51.6	50.5	48.5	48.0	46.5	47.0	45.4	45.4
82.5°	46.8	42.9	40.7	39.3	38.3	36.7	36.1	35.4	35.5	34.4	34.4
85°	24.0	23.0	21.9	20.9	20.9	19.4	19.9	19.4	19.4	18.4	17.9
87.5°	10.1	10.1	9.7	10.0	10.4	10.4	10.6	10.4	10.7	10.9	10.7
90°	11.5	13.7	15.6	17.5	19.4	21.3	22.4	23.6	24.8	26.0	26.8
92.5°	20.5	20.9	21.8	22.8	23.7	24.7	25.3	25.9	26.5	27.1	27.6
95°	37.9	34.8	36.5	38.2	39.8	41.5	42.6	43.8	45.0	46.2	46.7
97.5°	49.3	40.2	44.0	47.8	51.7	55.5	56.4	57.4	58.3	59.3	59.9
100°	58.7	44.5	48.5	52.6	56.6	60.6	62.5	64.4	66.3	68.2	69.3
102.5°	216.9	196.7	163.1	129.5	95.9	62.3	64.8	67.2	69.7	72.1	73.7
105°	351.5	322.8	258.3	193.8	129.3	64.8	67.4	70.0	72.6	75.2	77.0
107.5°	436.0	400.2	322.8	245.5	168.1	90.8	88.1	85.5	82.8	80.2	79.4
110°	490.8	459.1	390.8	322.6	254.3	186.0	162.4	138.8	115.2	91.5	80.2



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	542.9	536.7	519.8	503.0	486.1	469.2	383.1	296.9	210.7	124.5	81.8
115°	627.3	632.3	638.2	644.1	650.0	655.9	546.5	437.1	327.8	218.4	155.2
117.5°	706.0	710.2	714.3	718.4	722.4	726.5	700.0	673.6	647.1	620.7	579.5
120°	758.3	762.2	766.5	770.7	775.0	779.2	782.0	784.9	787.7	790.6	776.0
122.5°	806.7	810.9	815.5	820.1	824.8	829.4	831.1	832.8	834.5	836.2	833.9
125°	876.5	880.3	884.8	889.3	893.8	898.3	899.9	901.6	903.2	904.9	906.1
127.5°	943.6	946.9	950.3	953.6	957.0	960.4	962.8	965.2	967.6	970.0	971.3
130°	986.7	989.9	992.5	995.1	997.7	1000.3	1002.9	1005.5	1008.1	1010.7	1011.9
132.5°	1027.0	1029.9	1032.5	1035.1	1037.7	1040.3	1042.5	1044.7	1047.0	1049.2	1050.2
135°	1084.5	1087.5	1089.6	1091.7	1093.9	1096.0	1098.4	1100.7	1103.1	1105.4	1106.4
137.5°	1135.9	1138.4	1140.9	1143.3	1145.7	1148.1	1150.4	1152.7	1155.0	1157.3	1158.1
140°	1169.5	1171.7	1174.3	1176.9	1179.5	1182.1	1184.2	1186.4	1188.5	1190.6	1191.1
142.5°	1199.3	1201.7	1204.6	1207.6	1210.6	1213.6	1215.5	1217.4	1219.4	1221.3	1221.7
145°	1239.6	1241.5	1245.5	1249.5	1253.6	1257.6	1259.2	1260.9	1262.5	1264.2	1264.4
147.5°	1278.9	1280.4	1284.4	1288.3	1292.3	1296.3	1297.5	1298.7	1300.0	1301.2	1301.3
150°	1303.1	1304.1	1307.9	1311.7	1315.5	1319.2	1320.7	1322.1	1323.5	1324.9	1325.0
152.5°	1325.3	1326.1	1329.7	1333.3	1336.9	1340.5	1341.9	1343.3	1344.8	1346.2	1346.1
155°	1357.5	1357.9	1360.7	1363.5	1366.4	1369.2	1370.6	1372.0	1373.5	1374.9	1374.6
157.5°	1385.0	1385.1	1387.1	1389.0	1391.0	1393.0	1394.6	1396.2	1397.8	1399.4	1399.3
160°	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1408.9	1410.3	1411.7	1413.1	1413.0
162.5°	1415.4	1415.3	1416.5	1417.8	1419.0	1420.2	1421.8	1423.4	1425.0	1426.7	1426.4
165°	1433.7	1433.3	1434.0	1434.8	1435.5	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8
167.5°	1447.3	1446.9	1447.6	1448.2	1448.9	1449.6	1451.2	1452.9	1454.5	1456.2	1455.9
170°	1455.0	1454.5	1455.0	1455.4	1455.9	1456.4	1458.0	1459.7	1461.3	1463.0	1462.7
172.5°	1460.1	1459.6	1460.1	1460.5	1461.0	1461.5	1463.1	1464.8	1466.4	1468.1	1467.9
175°	1465.7	1465.1	1465.6	1466.1	1466.5	1467.0	1468.7	1470.3	1472.0	1473.6	1473.3
177.5°	1468.1	1467.5	1467.7	1467.9	1468.1	1468.3	1469.6	1470.9	1472.2	1473.6	1473.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1410.7	1411.5	1410.3	1411.1	1410.3	1411.5	1410.7	1415.2	1416.0	1416.8	1416.0
5°	1314.4	1308.3	1307.3	1305.7	1307.3	1308.3	1314.4	1317.0	1319.0	1323.1	1330.2
7.5°	1199.5	1198.5	1196.0	1192.4	1196.0	1198.5	1199.5	1208.2	1215.2	1223.1	1237.7
10°	1125.5	1123.0	1122.5	1118.9	1122.5	1123.0	1125.5	1136.8	1144.9	1156.2	1176.1
12.5°	1039.0	1022.5	1020.8	1011.9	1020.8	1022.5	1039.0	1053.5	1075.5	1086.3	1107.5
15°	884.6	881.6	871.3	864.7	871.3	881.6	884.6	896.9	905.0	934.6	968.8
17.5°	796.4	786.4	783.2	781.8	783.2	786.4	796.4	802.3	814.0	829.6	850.2
20°	739.6	730.5	728.9	727.9	728.9	730.5	739.6	746.8	756.0	772.8	794.3
22.5°	700.4	690.8	686.9	683.8	686.9	690.8	700.4	706.0	714.3	727.5	742.0
25°	633.5	629.9	627.9	626.8	627.9	629.9	633.5	638.6	646.7	664.6	679.9
27.5°	581.1	573.2	571.7	569.1	571.7	573.2	581.1	590.2	598.7	606.7	620.4
30°	551.3	548.7	545.2	542.1	545.2	548.7	551.3	555.9	561.5	575.3	588.6
32.5°	516.2	514.0	510.9	509.4	510.9	514.0	516.2	522.4	534.1	542.6	552.2
35°	477.3	470.1	467.1	462.5	467.1	470.1	477.3	482.4	487.0	494.1	511.5
37.5°	436.1	432.4	428.1	429.6	428.1	432.4	436.1	438.3	448.0	457.9	465.4
40°	404.3	401.7	400.7	400.2	400.7	401.7	404.3	410.9	422.7	427.2	438.5
42.5°	379.0	371.9	369.3	369.2	369.3	371.9	379.0	386.4	393.7	401.1	412.8
45°	340.5	333.8	329.2	329.8	329.2	333.8	340.5	343.0	349.1	364.0	370.6
47.5°	301.1	300.9	298.0	298.9	298.0	300.9	301.1	305.5	313.3	322.4	333.0
50°	282.3	279.2	277.2	277.7	277.2	279.2	282.3	285.9	290.4	295.0	311.4
52.5°	264.3	261.7	260.0	262.2	260.0	261.7	264.3	266.3	269.6	274.2	285.2
55°	234.8	231.7	231.2	230.7	231.2	231.7	234.8	237.4	241.4	245.0	250.1
57.5°	201.8	199.8	196.7	195.4	196.7	199.8	201.8	205.6	210.5	215.2	220.5
60°	178.1	174.1	169.0	168.4	169.0	174.1	178.1	184.8	186.8	194.0	200.1
62.5°	156.5	155.7	154.7	154.6	154.7	155.7	156.5	158.6	161.5	171.9	179.3
65°	137.3	136.8	137.3	137.8	137.3	136.8	137.3	138.3	138.8	139.9	142.9
67.5°	119.7	118.7	117.8	118.2	117.8	118.7	119.7	119.9	121.3	121.9	124.0
70°	106.2	105.7	105.2	105.2	105.2	105.7	106.2	107.2	108.2	109.2	111.8
72.5°	93.1	93.0	92.5	92.1	92.5	93.0	93.1	94.9	95.6	96.6	98.3
75°	74.5	73.5	73.5	73.5	73.5	73.5	74.5	75.0	75.5	77.1	78.1
77.5°	56.8	56.3	55.7	55.3	55.7	56.3	56.8	56.9	57.7	58.0	59.1
80°	44.9	44.4	43.9	43.9	43.9	44.4	44.9	45.4	45.4	47.0	46.5
82.5°	34.3	33.8	33.7	33.3	33.7	33.8	34.3	34.4	34.4	35.5	35.4
85°	18.4	18.9	18.4	19.4	18.4	18.9	18.4	17.9	18.4	19.4	19.4
87.5°	10.8	10.5	11.0	10.6	11.0	10.5	10.8	10.7	10.9	10.7	10.4
90°	27.3	27.8	28.2	28.7	28.2	27.8	27.3	26.8	26.0	24.8	23.6
92.5°	27.9	28.1	28.4	28.7	28.4	28.1	27.9	27.6	27.1	26.5	25.9
95°	46.4	46.2	45.9	45.7	45.9	46.2	46.4	46.7	46.2	45.0	43.8
97.5°	60.2	60.5	60.7	61.0	60.7	60.5	60.2	59.9	59.3	58.3	57.4
100°	69.8	70.3	70.8	71.2	70.8	70.3	69.8	69.3	68.2	66.3	64.4
102.5°	74.3	75.0	75.7	76.3	75.7	75.0	74.3	73.7	72.1	69.7	67.2
105°	78.0	78.9	79.8	80.8	79.8	78.9	78.0	77.0	75.2	72.6	70.0
107.5°	80.3	81.2	82.2	83.1	82.2	81.2	80.3	79.4	80.2	82.8	85.5
110°	81.1	82.1	83.0	84.0	83.0	82.1	81.1	80.2	91.5	115.2	138.8



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	82.6	83.3	84.1	84.8	84.1	83.3	82.6	81.8	124.5	210.7	296.9
115°	138.2	121.2	104.2	87.2	104.2	121.2	138.2	155.2	218.4	327.8	437.1
117.5°	523.6	467.7	411.8	355.9	411.8	467.7	523.6	579.5	620.7	647.1	673.6
120°	744.1	712.2	680.3	648.5	680.3	712.2	744.1	776.0	790.6	787.7	784.9
122.5°	827.8	821.6	815.4	809.2	815.4	821.6	827.8	833.9	836.2	834.5	832.8
125°	906.8	907.5	908.2	908.9	908.2	907.5	906.8	906.1	904.9	903.2	901.6
127.5°	971.4	971.6	971.7	971.8	971.7	971.6	971.4	971.3	970.0	967.6	965.2
130°	1011.7	1011.4	1011.2	1011.0	1011.2	1011.4	1011.7	1011.9	1010.7	1008.1	1005.5
132.5°	1049.9	1049.7	1049.5	1049.2	1049.5	1049.7	1049.9	1050.2	1049.2	1047.0	1044.7
135°	1105.9	1105.4	1105.0	1104.5	1105.0	1105.4	1105.9	1106.4	1105.4	1103.1	1100.7
137.5°	1157.3	1156.5	1155.7	1154.9	1155.7	1156.5	1157.3	1158.1	1157.3	1155.0	1152.7
140°	1189.9	1188.7	1187.5	1186.4	1187.5	1188.7	1189.9	1191.1	1190.6	1188.5	1186.4
142.5°	1220.5	1219.3	1218.2	1217.0	1218.2	1219.3	1220.5	1221.7	1221.3	1219.4	1217.4
145°	1263.3	1262.1	1260.9	1259.7	1260.9	1262.1	1263.3	1264.4	1264.2	1262.5	1260.9
147.5°	1300.3	1299.3	1298.3	1297.3	1298.3	1299.3	1300.3	1301.3	1301.2	1300.0	1298.7
150°	1323.8	1322.7	1321.5	1320.3	1321.5	1322.7	1323.8	1325.0	1324.9	1323.5	1322.1
152.5°	1344.5	1343.0	1341.4	1339.9	1341.4	1343.0	1344.5	1346.1	1346.2	1344.8	1343.3
155°	1372.7	1370.9	1369.0	1367.1	1369.0	1370.9	1372.7	1374.6	1374.9	1373.5	1372.0
157.5°	1397.5	1395.6	1393.8	1391.9	1393.8	1395.6	1397.5	1399.3	1399.4	1397.8	1396.2
160°	1411.4	1409.7	1408.1	1406.4	1408.1	1409.7	1411.4	1413.0	1413.1	1411.7	1410.3
162.5°	1424.4	1422.4	1420.3	1418.3	1420.3	1422.4	1424.4	1426.4	1426.7	1425.0	1423.4
165°	1441.1	1439.5	1437.8	1436.2	1437.8	1439.5	1441.1	1442.8	1442.8	1441.1	1439.5
167.5°	1453.8	1451.7	1449.6	1447.4	1449.6	1451.7	1453.8	1455.9	1456.2	1454.5	1452.9
170°	1460.6	1458.5	1456.4	1454.2	1456.4	1458.5	1460.6	1462.7	1463.0	1461.3	1459.7
172.5°	1465.7	1463.6	1461.5	1459.3	1461.5	1463.6	1465.7	1467.9	1468.1	1466.4	1464.8
175°	1470.9	1468.5	1466.2	1463.8	1466.2	1468.5	1470.9	1473.3	1473.6	1472.0	1470.3
177.5°	1471.7	1470.0	1468.3	1466.6	1468.3	1470.0	1471.7	1473.4	1473.6	1472.2	1470.9
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1412.7	1418.4	1427.0	1431.9	1440.1	1445.4	1448.3	1453.6	1456.4	1466.6	1477.3
5°	1333.8	1342.0	1356.3	1369.5	1383.8	1398.6	1409.4	1421.6	1432.8	1452.2	1472.7
7.5°	1243.4	1254.7	1276.8	1298.0	1322.9	1343.8	1362.3	1383.2	1401.9	1429.7	1458.7
10°	1175.6	1195.5	1224.6	1244.5	1277.2	1298.1	1327.2	1350.1	1376.2	1412.9	1445.6
12.5°	1117.2	1141.2	1164.5	1192.2	1221.6	1256.4	1288.4	1317.9	1348.8	1386.8	1425.2
15°	1011.2	1045.9	1082.2	1110.2	1150.1	1186.8	1224.1	1263.9	1301.7	1347.1	1397.1
17.5°	874.8	915.0	976.0	1024.1	1070.8	1107.7	1153.8	1202.0	1246.5	1301.3	1357.0
20°	813.2	842.8	884.1	948.9	1019.4	1058.7	1105.6	1158.7	1209.8	1269.5	1329.2
22.5°	763.7	790.1	823.3	873.8	952.4	1006.0	1055.0	1108.9	1168.1	1229.1	1295.3
25°	693.2	711.6	746.3	787.1	841.2	929.5	983.1	1037.2	1101.6	1166.9	1242.4
27.5°	640.2	656.7	679.3	718.3	758.5	821.9	907.2	966.2	1030.3	1103.8	1182.2
30°	599.8	619.2	644.2	671.8	715.7	765.2	850.4	918.8	982.1	1057.7	1141.4
32.5°	570.4	585.7	607.0	635.0	671.6	719.0	787.1	870.2	931.9	1011.5	1098.9
35°	522.2	540.1	557.4	584.0	613.6	657.0	708.5	797.3	858.6	937.2	1025.0
37.5°	482.5	493.4	512.6	533.6	564.9	597.2	641.9	721.6	787.8	865.0	954.9
40°	452.3	466.0	480.3	503.8	529.3	560.5	604.4	663.6	739.6	815.2	903.0
42.5°	422.9	440.3	455.4	471.1	499.1	530.3	566.0	616.2	693.9	765.4	850.7
45°	387.4	398.7	414.5	431.8	454.8	481.4	513.0	556.9	631.4	693.2	773.3
47.5°	346.2	362.6	372.9	389.9	411.7	437.0	466.5	504.4	564.8	622.7	697.0
50°	318.0	334.9	349.7	365.0	384.4	408.9	433.4	470.1	518.6	579.4	648.8
52.5°	293.9	308.7	323.1	338.4	357.4	379.9	403.2	435.4	477.0	532.8	600.2
55°	260.8	270.0	284.8	300.1	317.0	338.4	360.9	387.9	423.7	470.6	525.3
57.5°	226.9	237.6	249.3	264.7	281.8	298.2	318.4	342.9	371.1	413.6	460.3
60°	207.8	215.9	225.6	241.4	257.3	272.1	291.5	311.9	338.4	375.2	415.0
62.5°	186.5	194.3	203.2	216.9	232.4	245.9	262.9	284.5	307.0	340.5	375.4
65°	151.1	162.3	171.0	183.3	196.0	210.3	223.6	240.9	260.8	287.4	318.5
67.5°	125.3	131.0	139.0	150.2	163.2	175.5	188.1	201.6	218.9	239.4	264.1
70°	113.8	115.9	117.4	128.1	140.4	152.6	164.4	177.1	191.9	208.8	230.2
72.5°	100.4	102.4	104.3	108.9	118.7	131.0	143.1	152.6	166.6	180.6	198.0
75°	79.6	82.7	84.2	86.8	90.4	98.5	109.7	118.9	127.1	137.8	151.6
77.5°	60.6	62.4	64.0	66.7	68.9	72.7	79.0	87.3	94.9	101.2	110.7
80°	48.0	48.5	50.5	51.6	54.6	57.2	60.2	66.9	74.5	77.1	83.7
82.5°	36.1	36.7	38.3	39.3	40.7	42.9	46.8	48.5	54.5	57.9	62.1
85°	19.9	19.4	20.9	20.9	21.9	23.0	24.0	26.5	28.1	32.2	33.2
87.5°	10.6	10.4	10.4	10.0	9.7	10.1	10.1	9.9	10.2	10.9	12.1
90°	22.4	21.3	19.4	17.5	15.6	13.7	11.5	8.9	6.3	3.7	1.1
92.5°	25.3	24.7	23.7	22.8	21.8	20.9	20.5	20.8	21.0	21.2	21.5
95°	42.6	41.5	39.8	38.2	36.5	34.8	37.9	45.7	53.5	61.3	69.1
97.5°	56.4	55.5	51.7	47.8	44.0	40.2	49.3	71.2	93.2	115.2	137.1
100°	62.5	60.6	56.6	52.6	48.5	44.5	58.7	91.1	123.4	155.8	188.2
102.5°	64.8	62.3	95.9	129.5	163.1	196.7	216.9	223.7	230.6	237.4	244.3
105°	67.4	64.8	129.3	193.8	258.3	322.8	351.5	344.4	337.3	330.3	323.2
107.5°	88.1	90.8	168.1	245.5	322.8	400.2	436.0	430.2	424.5	418.8	413.1
110°	162.4	186.0	254.3	322.6	390.8	459.1	490.8	485.8	480.9	475.9	470.9



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	383.1	469.2	486.1	503.0	519.8	536.7	542.9	538.5	534.1	529.8	525.4
115°	546.5	655.9	650.0	644.1	638.2	632.3	627.3	623.3	619.3	615.3	611.3
117.5°	700.0	726.5	722.4	718.4	714.3	710.2	706.0	701.5	697.0	692.5	688.0
120°	782.0	779.2	775.0	770.7	766.5	762.2	758.3	754.8	751.2	747.7	744.1
122.5°	831.1	829.4	824.8	820.1	815.5	810.9	806.7	803.0	799.2	795.5	791.8
125°	899.9	898.3	893.8	889.3	884.8	880.3	876.5	873.5	870.4	867.3	864.3
127.5°	962.8	960.4	957.0	953.6	950.3	946.9	943.6	940.2	936.8	933.4	930.0
130°	1002.9	1000.3	997.7	995.1	992.5	989.9	986.7	983.0	979.2	975.4	971.6
132.5°	1042.5	1040.3	1037.7	1035.1	1032.5	1029.9	1027.0	1023.8	1020.6	1017.4	1014.1
135°	1098.4	1096.0	1093.9	1091.7	1089.6	1087.5	1084.5	1080.8	1077.0	1073.2	1069.4
137.5°	1150.4	1148.1	1145.7	1143.3	1140.9	1138.4	1135.9	1133.3	1130.6	1128.0	1125.3
140°	1184.2	1182.1	1179.5	1176.9	1174.3	1171.7	1169.5	1167.6	1165.7	1163.8	1161.9
142.5°	1215.5	1213.6	1210.6	1207.6	1204.6	1201.7	1199.3	1197.6	1195.9	1194.2	1192.5
145°	1259.2	1257.6	1253.6	1249.5	1245.5	1241.5	1239.6	1239.9	1240.1	1240.3	1240.6
147.5°	1297.5	1296.3	1292.3	1288.3	1284.4	1280.4	1278.9	1279.8	1280.7	1281.6	1282.5
150°	1320.7	1319.2	1315.5	1311.7	1307.9	1304.1	1303.1	1304.7	1306.4	1308.0	1309.7
152.5°	1341.9	1340.5	1336.9	1333.3	1329.7	1326.1	1325.3	1327.1	1328.9	1330.8	1332.6
155°	1370.6	1369.2	1366.4	1363.5	1360.7	1357.9	1357.5	1359.6	1361.8	1363.9	1366.0
157.5°	1394.6	1393.0	1391.0	1389.0	1387.1	1385.1	1385.0	1386.8	1388.6	1390.4	1392.2
160°	1408.9	1407.5	1406.1	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5
162.5°	1421.8	1420.2	1419.0	1417.8	1416.5	1415.3	1415.4	1416.8	1418.2	1419.7	1421.1
165°	1437.8	1436.2	1435.5	1434.8	1434.0	1433.3	1433.7	1435.1	1436.5	1437.9	1439.4
167.5°	1451.2	1449.6	1448.9	1448.2	1447.6	1446.9	1447.3	1448.7	1450.1	1451.6	1453.0
170°	1458.0	1456.4	1455.9	1455.4	1455.0	1454.5	1455.0	1456.4	1457.8	1459.2	1460.6
172.5°	1463.1	1461.5	1461.0	1460.5	1460.1	1459.6	1460.1	1461.5	1462.9	1464.3	1465.7
175°	1468.7	1467.0	1466.5	1466.1	1465.6	1465.1	1465.7	1467.4	1469.0	1470.7	1472.3
177.5°	1469.6	1468.3	1468.1	1467.9	1467.7	1467.5	1468.1	1469.4	1470.7	1472.1	1473.4
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1477.7	1478.9	1487.1	1490.7	1498.1	1500.9	1504.2	1503.4	1503.4	1505.0	1516.5
5°	1480.8	1491.0	1506.3	1521.1	1535.4	1547.7	1555.9	1564.0	1567.1	1581.9	1595.2
7.5°	1475.5	1494.3	1519.6	1542.2	1569.2	1590.4	1607.9	1623.8	1634.6	1656.1	1678.2
10°	1468.6	1495.1	1523.7	1552.8	1590.1	1618.1	1646.7	1668.7	1675.8	1708.0	1726.4
12.5°	1454.7	1490.2	1526.6	1564.2	1600.7	1639.4	1670.8	1692.8	1717.9	1746.8	1780.7
15°	1433.9	1474.7	1522.2	1570.7	1622.7	1669.7	1703.4	1741.7	1769.2	1800.9	1830.5
17.5°	1403.9	1456.5	1516.9	1573.0	1633.2	1683.7	1730.0	1766.8	1786.2	1804.2	1808.6
20°	1380.3	1436.9	1507.9	1574.2	1634.5	1692.7	1738.6	1769.2	1774.3	1774.8	1747.8
22.5°	1354.5	1418.5	1492.8	1560.8	1632.8	1697.6	1733.3	1746.4	1726.1	1691.5	1639.2
25°	1307.3	1381.3	1467.6	1545.1	1623.8	1685.0	1697.3	1674.3	1603.3	1528.8	1434.4
27.5°	1256.0	1339.2	1431.7	1518.0	1601.7	1639.7	1613.2	1530.4	1402.6	1291.5	1156.9
30°	1218.5	1311.9	1402.7	1499.2	1576.8	1593.1	1532.4	1410.4	1261.3	1093.9	959.7
32.5°	1175.6	1273.5	1373.3	1473.1	1538.0	1522.1	1421.7	1271.5	1096.8	932.2	805.3
35°	1114.3	1215.4	1323.1	1423.1	1464.5	1395.6	1245.5	1050.0	871.3	717.7	630.4
37.5°	1043.6	1153.6	1265.6	1357.5	1354.5	1239.7	1035.3	833.5	683.3	592.4	530.3
40°	993.3	1104.6	1225.6	1303.2	1270.0	1120.4	898.9	708.5	598.8	526.3	480.8
42.5°	945.2	1056.8	1177.0	1238.7	1181.0	997.1	776.4	627.2	536.7	480.1	443.3
45°	863.2	981.1	1092.4	1126.6	1023.5	820.8	627.9	519.6	459.4	417.6	392.0
47.5°	783.0	899.0	1000.6	1001.2	861.7	665.6	529.6	449.7	398.3	365.9	347.3
50°	734.0	844.3	929.5	916.3	758.0	592.1	473.7	404.8	361.9	336.9	317.5
52.5°	678.9	785.9	859.7	821.9	670.2	521.1	423.5	365.6	330.1	308.3	291.0
55°	598.8	693.7	745.8	688.6	546.7	433.4	357.8	312.4	285.9	267.5	252.7
57.5°	520.0	598.4	631.1	564.6	450.3	359.4	302.7	268.6	242.3	229.1	221.4
60°	470.6	537.5	560.5	487.0	391.5	314.4	268.0	236.3	216.9	208.3	200.6
62.5°	422.0	476.7	486.2	418.8	341.3	275.2	235.3	208.6	195.7	187.4	180.2
65°	350.2	389.5	384.9	330.8	270.0	218.5	189.4	173.0	163.3	151.6	138.8
67.5°	288.3	312.3	297.8	257.3	206.1	169.8	150.8	138.4	126.4	115.3	112.3
70°	249.1	262.9	247.6	210.3	169.0	142.4	127.1	112.3	105.2	102.6	98.0
72.5°	211.5	216.3	199.8	167.8	137.5	117.9	103.0	94.7	90.9	88.7	85.8
75°	158.8	155.2	140.9	115.9	95.5	82.2	77.6	74.5	72.0	69.9	68.4
77.5°	111.5	106.3	93.5	77.2	66.5	60.1	57.4	55.7	54.5	53.5	52.0
80°	83.7	80.1	67.4	55.1	50.5	47.5	45.9	43.9	43.9	42.9	41.3
82.5°	61.3	57.3	46.1	40.4	37.9	36.0	34.9	33.7	33.3	33.5	32.4
85°	32.2	26.0	23.0	21.9	20.4	19.4	19.9	18.9	18.9	18.9	18.4
87.5°	10.5	9.0	9.1	9.2	10.1	10.5	10.4	10.8	11.6	11.4	12.1
90°	3.7	6.3	8.9	11.5	13.7	15.6	17.5	19.4	21.3	22.4	23.6
92.5°	21.2	21.0	20.8	20.5	20.9	21.8	22.8	23.7	24.7	25.3	25.9
95°	61.3	53.5	45.7	37.9	34.8	36.5	38.2	39.8	41.5	42.6	43.8
97.5°	115.2	93.2	71.2	49.3	40.2	44.0	47.8	51.7	55.5	56.4	57.4
100°	155.8	123.4	91.1	58.7	44.5	48.5	52.6	56.6	60.6	62.5	64.4
102.5°	237.4	230.6	223.7	216.9	196.7	163.1	129.5	95.9	62.3	64.8	67.2
105°	330.3	337.3	344.4	351.5	322.8	258.3	193.8	129.3	64.8	67.4	70.0
107.5°	418.8	424.5	430.2	436.0	400.2	322.8	245.5	168.1	90.8	88.1	85.5
110°	475.9	480.9	485.8	490.8	459.1	390.8	322.6	254.3	186.0	162.4	138.8



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	529.8	534.1	538.5	542.9	536.7	519.8	503.0	486.1	469.2	383.1	296.9
115°	615.3	619.3	623.3	627.3	632.3	638.2	644.1	650.0	655.9	546.5	437.1
117.5°	692.5	697.0	701.5	706.0	710.2	714.3	718.4	722.4	726.5	700.0	673.6
120°	747.7	751.2	754.8	758.3	762.2	766.5	770.7	775.0	779.2	782.0	784.9
122.5°	795.5	799.2	803.0	806.7	810.9	815.5	820.1	824.8	829.4	831.1	832.8
125°	867.3	870.4	873.5	876.5	880.3	884.8	889.3	893.8	898.3	899.9	901.6
127.5°	933.4	936.8	940.2	943.6	946.9	950.3	953.6	957.0	960.4	962.8	965.2
130°	975.4	979.2	983.0	986.7	989.9	992.5	995.1	997.7	1000.3	1002.9	1005.5
132.5°	1017.4	1020.6	1023.8	1027.0	1029.9	1032.5	1035.1	1037.7	1040.3	1042.5	1044.7
135°	1073.2	1077.0	1080.8	1084.5	1087.5	1089.6	1091.7	1093.9	1096.0	1098.4	1100.7
137.5°	1128.0	1130.6	1133.3	1135.9	1138.4	1140.9	1143.3	1145.7	1148.1	1150.4	1152.7
140°	1163.8	1165.7	1167.6	1169.5	1171.7	1174.3	1176.9	1179.5	1182.1	1184.2	1186.4
142.5°	1194.2	1195.9	1197.6	1199.3	1201.7	1204.6	1207.6	1210.6	1213.6	1215.5	1217.4
145°	1240.3	1240.1	1239.9	1239.6	1241.5	1245.5	1249.5	1253.6	1257.6	1259.2	1260.9
147.5°	1281.6	1280.7	1279.8	1278.9	1280.4	1284.4	1288.3	1292.3	1296.3	1297.5	1298.7
150°	1308.0	1306.4	1304.7	1303.1	1304.1	1307.9	1311.7	1315.5	1319.2	1320.7	1322.1
152.5°	1330.8	1328.9	1327.1	1325.3	1326.1	1329.7	1333.3	1336.9	1340.5	1341.9	1343.3
155°	1363.9	1361.8	1359.6	1357.5	1357.9	1360.7	1363.5	1366.4	1369.2	1370.6	1372.0
157.5°	1390.4	1388.6	1386.8	1385.0	1385.1	1387.1	1389.0	1391.0	1393.0	1394.6	1396.2
160°	1406.1	1404.6	1403.2	1401.8	1401.8	1403.2	1404.6	1406.1	1407.5	1408.9	1410.3
162.5°	1419.7	1418.2	1416.8	1415.4	1415.3	1416.5	1417.8	1419.0	1420.2	1421.8	1423.4
165°	1437.9	1436.5	1435.1	1433.7	1433.3	1434.0	1434.8	1435.5	1436.2	1437.8	1439.5
167.5°	1451.6	1450.1	1448.7	1447.3	1446.9	1447.6	1448.2	1448.9	1449.6	1451.2	1452.9
170°	1459.2	1457.8	1456.4	1455.0	1454.5	1455.0	1455.4	1455.9	1456.4	1458.0	1459.7
172.5°	1464.3	1462.9	1461.5	1460.1	1459.6	1460.1	1460.5	1461.0	1461.5	1463.1	1464.8
175°	1470.7	1469.0	1467.4	1465.7	1465.1	1465.6	1466.1	1466.5	1467.0	1468.7	1470.3
177.5°	1472.1	1470.7	1469.4	1468.1	1467.5	1467.7	1467.9	1468.1	1468.3	1469.6	1470.9
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1520.5	1525.8	1528.3	1528.3	1531.2	1529.9	1528.7
5°	1607.9	1617.6	1619.7	1628.9	1635.5	1633.4	1634.5
7.5°	1694.8	1710.4	1725.8	1732.9	1734.0	1738.1	1739.6
10°	1748.3	1761.1	1785.1	1781.5	1799.3	1809.6	1792.7
12.5°	1799.8	1817.0	1833.6	1838.2	1848.4	1851.6	1845.0
15°	1846.3	1855.5	1856.5	1854.0	1857.0	1854.5	1844.8
17.5°	1802.8	1787.9	1757.7	1743.4	1732.1	1715.3	1708.6
20°	1730.9	1687.0	1636.0	1615.6	1591.6	1544.6	1555.9
22.5°	1575.8	1525.7	1474.7	1415.1	1386.6	1342.1	1339.4
25°	1334.3	1248.1	1153.1	1086.8	1048.0	1003.6	984.2
27.5°	1037.4	928.8	851.0	811.6	775.8	740.6	739.1
30°	842.2	760.6	700.3	666.7	644.7	629.9	633.0
32.5°	709.9	654.0	613.4	585.4	569.2	558.0	557.8
35°	580.4	542.1	516.1	504.3	492.6	484.4	484.9
37.5°	496.7	473.7	459.2	446.2	438.9	434.9	432.7
40°	453.8	434.9	423.7	416.0	409.9	404.3	403.3
42.5°	419.9	404.3	393.0	387.0	381.3	377.3	376.3
45°	372.6	359.9	349.7	343.0	340.5	336.9	336.9
47.5°	331.5	318.9	311.0	306.8	302.4	300.0	299.9
50°	303.7	294.0	286.9	284.3	280.7	279.2	278.7
52.5°	278.8	271.6	266.5	264.7	263.2	261.2	261.6
55°	245.0	240.9	238.9	237.4	234.8	231.7	233.8
57.5°	216.5	213.1	207.6	202.8	200.4	198.3	199.1
60°	196.5	189.4	182.2	176.6	175.1	170.5	170.5
62.5°	171.2	161.2	152.4	149.3	147.7	145.6	145.2
65°	131.7	127.6	125.6	123.5	122.5	122.5	121.5
67.5°	109.1	107.5	105.3	104.7	103.7	103.4	103.1
70°	96.5	94.4	93.4	92.9	91.9	92.4	90.9
72.5°	84.2	82.6	82.4	81.1	80.4	80.5	79.4
75°	66.4	66.4	65.8	65.3	64.3	63.8	64.3
77.5°	51.0	51.1	50.2	50.1	50.0	50.1	49.6
80°	40.8	41.3	40.8	40.3	39.8	40.3	39.8
82.5°	32.3	31.5	31.4	31.3	31.2	30.9	30.8
85°	18.4	18.9	18.4	17.9	17.9	17.9	18.4
87.5°	11.9	12.1	12.3	12.4	12.5	12.6	12.3
90°	24.8	26.0	26.8	27.3	27.8	28.2	28.7
92.5°	26.5	27.1	27.6	27.9	28.1	28.4	28.7
95°	45.0	46.2	46.7	46.4	46.2	45.9	45.7
97.5°	58.3	59.3	59.9	60.2	60.5	60.7	61.0
100°	66.3	68.2	69.3	69.8	70.3	70.8	71.2
102.5°	69.7	72.1	73.7	74.3	75.0	75.7	76.3
105°	72.6	75.2	77.0	78.0	78.9	79.8	80.8
107.5°	82.8	80.2	79.4	80.3	81.2	82.2	83.1
110°	115.2	91.5	80.2	81.1	82.1	83.0	84.0



TEST NUMBER: P331699

CATALOG NUMBER: SA2XXRDIP-C675D1080U835-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	210.7	124.5	81.8	82.6	83.3	84.1	84.8
115°	327.8	218.4	155.2	138.2	121.2	104.2	87.2
117.5°	647.1	620.7	579.5	523.6	467.7	411.8	355.9
120°	787.7	790.6	776.0	744.1	712.2	680.3	648.5
122.5°	834.5	836.2	833.9	827.8	821.6	815.4	809.2
125°	903.2	904.9	906.1	906.8	907.5	908.2	908.9
127.5°	967.6	970.0	971.3	971.4	971.6	971.7	971.8
130°	1008.1	1010.7	1011.9	1011.7	1011.4	1011.2	1011.0
132.5°	1047.0	1049.2	1050.2	1049.9	1049.7	1049.5	1049.2
135°	1103.1	1105.4	1106.4	1105.9	1105.4	1105.0	1104.5
137.5°	1155.0	1157.3	1158.1	1157.3	1156.5	1155.7	1154.9
140°	1188.5	1190.6	1191.1	1189.9	1188.7	1187.5	1186.4
142.5°	1219.4	1221.3	1221.7	1220.5	1219.3	1218.2	1217.0
145°	1262.5	1264.2	1264.4	1263.3	1262.1	1260.9	1259.7
147.5°	1300.0	1301.2	1301.3	1300.3	1299.3	1298.3	1297.3
150°	1323.5	1324.9	1325.0	1323.8	1322.7	1321.5	1320.3
152.5°	1344.8	1346.2	1346.1	1344.5	1343.0	1341.4	1339.9
155°	1373.5	1374.9	1374.6	1372.7	1370.9	1369.0	1367.1
157.5°	1397.8	1399.4	1399.3	1397.5	1395.6	1393.8	1391.9
160°	1411.7	1413.1	1413.0	1411.4	1409.7	1408.1	1406.4
162.5°	1425.0	1426.7	1426.4	1424.4	1422.4	1420.3	1418.3
165°	1441.1	1442.8	1442.8	1441.1	1439.5	1437.8	1436.2
167.5°	1454.5	1456.2	1455.9	1453.8	1451.7	1449.6	1447.4
170°	1461.3	1463.0	1462.7	1460.6	1458.5	1456.4	1454.2
172.5°	1466.4	1468.1	1467.9	1465.7	1463.6	1461.5	1459.3
175°	1472.0	1473.6	1473.3	1470.9	1468.5	1466.2	1463.8
177.5°	1472.2	1473.6	1473.4	1471.7	1470.0	1468.3	1466.6
180°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1

(END OF REPORT)