

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331370-830

Luminaire Tested: **SA2XXDIP-C675D1080U830-4F0-1E-UDD-D1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331370-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D1080U830-4F0-1E-UDD-D1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, DROP SATIN WHITE DIFFUSER
UPLIGHT 1080 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6165.8 lumens
Efficiency: N/A
Efficacy: 108.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.32 / 1.42
Luminous Opening: Rectangular w/ Sides (W: 0.17' x L: 4' x H: 0.08')
CIE Type: Semi-Indirect

Input Watts (W): 56.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331370-830
CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-D1

Luminous Intensity Polar Plot





TEST NUMBER: P331370-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-D1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37
1	94	89	85	81	85	81	77	74	65	62	60	50	49	47	37	36	35	29
2	85	77	71	65	76	70	64	59	56	52	49	43	41	38	32	30	28	23
3	77	67	60	54	69	61	54	49	49	44	40	38	35	32	28	26	24	19
4	70	59	51	45	63	54	47	41	43	38	34	34	30	27	25	22	20	16
5	64	53	44	38	58	48	40	35	39	33	29	30	26	23	22	19	17	14
6	59	47	39	33	53	43	35	30	35	29	25	27	23	20	20	17	15	12
7	55	42	34	29	49	38	31	26	31	26	22	24	21	18	18	15	13	10
8	50	38	30	25	45	35	28	23	28	23	19	22	18	16	17	14	12	9
9	47	35	27	22	42	32	25	20	26	21	17	20	17	14	15	13	11	8
10	44	32	24	20	39	29	23	18	24	19	15	19	15	12	14	11	10	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10719	10719	10719
5°	10771	10318	10278
10°	10704	10013	9900
15°	10557	9691	9503
20°	10370	9345	9120
25°	10186	9011	8772
30°	9928	8668	8421
35°	9665	8338	8176
40°	9388	8055	7929
45°	9124	7803	7719
50°	8843	7574	7511
55°	8548	7331	7300
60°	8188	7076	7078
65°	7811	6777	6812
70°	7390	6457	6525
75°	6853	6143	6262
80°	6004	5822	5995
85°	5192	5544	5785



TEST NUMBER: P331370-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-D1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.9	1.0
10°-20°	180.4	2.9
20°-30°	273.4	4.4
30°-40°	333.0	5.4
40°-50°	358.2	5.8
50°-60°	347.9	5.6
60°-70°	303.7	4.9
70°-80°	233.8	3.8
80°-90°	162.1	2.6
90°-100°	190.3	3.1
100°-110°	334.3	5.4
110°-120°	488.6	7.9
120°-130°	603.1	9.8
130°-140°	656.4	10.6
140°-150°	633.8	10.3
150°-160°	529.8	8.6
160°-170°	351.4	5.7
170°-180°	122.8	2.0
0°-30°	516.7	8.4
0°-40°	849.6	13.8
0°-60°	1555.7	25.2
0°-90°	2255.4	36.6
90°-120°	1013.2	16.4
90°-150°	2906.4	47.1
90°-180°	3910.0	63.4
0°-180°	6165.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	664	664	664	664	664	
5°	666	663	657	663	662	63
15°	635	637	637	645	645	179
25°	577	584	593	604	607	265
35°	498	514	532	552	560	311
45°	408	434	468	496	507	315
55°	313	348	397	431	444	279
65°	214	261	318	356	370	212
75°	118	173	234	274	288	125
85°	35	94	156	195	210	37
90°	11	81	165	200	214	9
95°	65	121	181	216	227	71
105°	240	273	324	358	370	254
115°	442	460	500	527	535	437
125°	639	650	676	698	707	571
135°	825	837	849	868	873	638
145°	1001	1008	1015	1021	1022	625
155°	1144	1147	1151	1156	1153	526
165°	1245	1244	1244	1251	1246	351
175°	1295	1292	1290	1297	1291	123
180°	1297	1297	1297	1297	1297	



TEST NUMBER: P331370-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	663.9	663.9	663.9	663.9	663.9	663.9	663.9	663.9	663.9	663.9	663.9
2.5°	667.8	667.2	666.8	666.2	665.7	664.9	663.6	662.4	661.3	660.1	660.9
5°	665.8	665.2	664.6	663.9	663.3	662.3	661.0	659.8	658.5	657.1	658.5
7.5°	659.9	659.4	659.0	658.6	658.2	657.4	656.5	655.4	654.5	653.6	655.1
10°	655.3	654.8	654.4	653.9	653.6	653.0	652.3	651.8	651.1	650.4	652.1
12.5°	647.5	647.6	647.7	647.8	647.9	647.7	647.2	646.8	646.3	645.8	647.5
15°	635.1	635.5	635.9	636.3	636.8	637.0	637.0	637.0	637.0	637.0	638.9
17.5°	618.9	619.8	620.7	621.6	622.5	623.3	624.0	624.6	625.3	626.0	628.0
20°	608.1	609.2	610.2	611.3	612.4	613.3	614.2	615.1	616.0	616.8	619.2
22.5°	596.5	597.8	599.1	600.3	601.5	602.8	604.0	605.1	606.3	607.6	609.9
25°	577.3	578.8	580.3	581.8	583.3	585.0	586.9	588.9	590.8	592.7	595.3
27.5°	554.2	556.7	559.1	561.6	564.0	566.4	568.6	570.9	573.2	575.4	578.6
30°	538.9	541.6	544.4	547.1	550.0	552.7	555.5	558.3	561.1	563.8	567.2
32.5°	521.9	525.0	528.1	531.2	534.4	537.6	540.9	544.1	547.4	550.7	554.7
35°	497.5	501.1	504.7	508.3	512.0	515.9	519.9	524.0	528.0	532.1	536.8
37.5°	470.9	475.1	479.3	483.4	487.7	492.4	497.7	502.9	508.1	513.4	518.7
40°	453.2	457.9	462.6	467.3	472.0	477.2	483.1	488.8	494.6	500.3	505.9
42.5°	436.3	440.9	445.6	450.3	455.1	460.7	467.4	474.0	480.6	487.3	493.3
45°	407.9	413.8	419.5	425.3	431.0	437.7	445.2	452.7	460.1	467.6	474.3
47.5°	380.0	386.3	392.7	398.9	405.2	412.7	421.5	430.3	439.0	447.8	454.8
50°	360.8	367.5	374.1	380.7	387.3	395.5	405.1	414.7	424.3	433.9	441.2
52.5°	342.3	349.3	356.3	363.3	370.2	378.8	388.9	399.1	409.2	419.3	426.8
55°	312.7	320.4	328.1	335.8	343.5	352.9	364.0	375.1	386.3	397.4	405.1
57.5°	283.4	292.2	300.9	309.5	318.2	328.2	339.5	350.8	362.2	373.5	381.8
60°	262.7	271.8	281.1	290.3	299.4	310.2	322.3	334.5	346.7	358.9	367.0
62.5°	244.2	253.7	263.3	272.8	282.4	293.2	305.4	317.5	329.8	342.0	350.6
65°	213.6	224.0	234.6	245.1	255.5	267.0	279.7	292.3	304.9	317.5	326.3
67.5°	185.5	196.4	207.5	218.4	229.3	241.2	254.1	267.0	279.9	292.8	301.7
70°	165.5	176.6	187.8	198.9	210.0	222.2	235.4	248.6	261.9	275.2	284.4
72.5°	147.0	158.4	169.9	181.4	192.8	205.3	218.8	232.1	245.6	259.0	268.1
75°	118.4	130.4	142.3	154.3	166.3	179.1	192.7	206.4	220.1	233.8	243.0
77.5°	90.7	103.2	115.7	128.2	140.7	154.0	167.9	181.8	195.7	209.5	218.8
80°	72.2	85.2	98.2	111.3	124.3	137.8	151.7	165.6	179.5	193.4	202.4
82.5°	56.7	69.7	82.5	95.4	108.3	121.7	135.8	149.9	163.9	178.0	187.0
85°	34.7	47.9	61.2	74.4	87.7	101.1	114.8	128.5	142.2	155.9	164.9
87.5°	19.0	32.4	45.7	59.1	72.4	86.4	101.2	115.9	130.7	145.4	154.1
90°	10.7	26.0	41.4	56.6	72.0	89.2	108.2	127.2	146.3	165.3	173.4
92.5°	28.4	42.0	55.7	69.4	83.1	97.2	111.6	126.0	140.4	154.9	163.3
95°	64.7	77.1	89.6	102.1	114.5	127.4	140.8	154.1	167.4	180.7	188.9
97.5°	110.7	121.9	132.9	144.0	155.0	167.2	180.5	193.7	207.0	220.2	228.1
100°	145.8	155.6	165.5	175.3	185.2	196.5	209.2	221.9	234.6	247.3	255.2
102.5°	181.8	190.6	199.3	208.1	217.0	227.6	240.2	252.7	265.2	277.9	285.8
105°	240.2	247.1	254.1	261.0	268.0	277.2	288.8	300.4	312.0	323.6	331.6
107.5°	300.0	306.0	312.1	318.1	324.1	332.4	343.1	353.7	364.4	375.0	382.5
110°	337.8	343.6	349.2	355.0	360.7	368.8	379.3	389.7	400.3	410.8	417.5



TEST NUMBER: P331370-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	379.8	384.8	389.9	395.0	400.0	407.5	417.2	427.0	436.8	446.5	452.8
115°	441.8	445.6	449.4	453.2	457.0	463.5	472.7	481.7	490.9	500.0	506.2
117.5°	502.6	506.1	509.5	513.0	516.5	522.0	529.5	537.1	544.6	552.1	557.9
120°	543.8	546.6	549.3	552.1	555.0	559.7	566.3	572.9	579.5	586.1	592.1
122.5°	581.4	584.1	586.7	589.5	592.1	596.8	603.5	610.1	616.8	623.5	628.8
125°	639.1	641.3	643.5	645.7	647.9	652.1	658.2	664.3	670.3	676.5	681.6
127.5°	696.3	698.8	701.3	704.0	706.5	710.1	714.7	719.3	724.1	728.7	733.1
130°	732.2	735.1	738.1	741.0	743.9	747.4	751.5	755.4	759.5	763.5	768.1
132.5°	772.5	774.9	777.2	779.6	781.9	784.9	788.4	792.0	795.6	799.2	803.0
135°	825.4	828.0	830.8	833.4	836.1	838.8	841.3	844.0	846.6	849.2	853.5
137.5°	882.1	884.2	886.4	888.5	890.7	892.5	894.1	895.7	897.3	898.8	902.6
140°	916.2	918.2	920.2	922.2	924.2	926.0	927.7	929.3	930.9	932.6	935.9
142.5°	951.3	953.3	955.3	957.2	959.2	960.6	961.6	962.4	963.4	964.3	967.2
145°	1000.7	1002.4	1004.1	1005.8	1007.5	1009.1	1010.5	1012.0	1013.4	1014.9	1016.4
147.5°	1045.6	1047.6	1049.6	1051.7	1053.8	1055.3	1056.2	1057.2	1058.2	1059.1	1059.9
150°	1076.2	1077.7	1079.1	1080.6	1082.0	1083.3	1084.3	1085.2	1086.2	1087.2	1087.9
152.5°	1103.3	1104.8	1106.3	1107.8	1109.2	1110.5	1111.7	1112.9	1114.1	1115.2	1116.2
155°	1144.2	1144.8	1145.6	1146.3	1147.1	1147.7	1148.5	1149.2	1150.0	1150.7	1151.9
157.5°	1178.9	1179.4	1179.9	1180.3	1180.9	1181.3	1181.8	1182.2	1182.6	1183.1	1184.8
160°	1200.0	1200.4	1200.9	1201.4	1201.9	1202.2	1202.5	1202.8	1203.0	1203.2	1204.7
162.5°	1219.2	1219.3	1219.4	1219.5	1219.7	1219.7	1220.0	1220.2	1220.5	1220.8	1222.4
165°	1244.8	1244.6	1244.3	1244.1	1243.9	1243.8	1243.8	1243.8	1243.8	1243.8	1245.5
167.5°	1266.3	1265.6	1264.8	1264.1	1263.4	1263.0	1262.9	1262.9	1262.8	1262.8	1264.5
170°	1277.7	1277.0	1276.2	1275.4	1274.8	1274.3	1274.0	1273.8	1273.6	1273.3	1275.0
172.5°	1285.5	1284.9	1284.1	1283.4	1282.6	1282.1	1282.0	1281.7	1281.4	1281.2	1282.9
175°	1295.2	1294.5	1293.7	1293.0	1292.3	1291.7	1291.2	1290.7	1290.2	1289.7	1291.5
177.5°	1299.1	1298.5	1298.0	1297.4	1296.8	1296.3	1295.9	1295.5	1295.1	1294.8	1295.9
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4



TEST NUMBER: P331370-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	663.9	663.9	663.9	663.9	663.9	663.9	663.9	663.9
2.5°	661.8	662.6	663.5	663.7	663.4	663.1	662.7	662.4
5°	659.8	661.0	662.3	662.9	662.6	662.4	662.2	661.9
7.5°	656.6	658.2	659.7	660.3	660.2	659.9	659.7	659.5
10°	653.8	655.5	657.3	658.0	657.8	657.6	657.4	657.1
12.5°	649.2	650.9	652.7	653.4	653.2	653.0	652.8	652.5
15°	640.8	642.7	644.7	645.5	645.4	645.1	644.9	644.7
17.5°	630.0	632.1	634.0	635.1	635.1	635.1	635.1	635.1
20°	621.5	623.9	626.1	627.4	627.4	627.4	627.4	627.4
22.5°	612.3	614.6	616.9	618.3	618.6	619.0	619.3	619.6
25°	597.9	600.4	602.9	604.5	605.2	605.9	606.5	607.2
27.5°	581.9	585.1	588.4	590.2	590.7	591.2	591.6	592.1
30°	570.7	574.1	577.5	579.6	580.2	580.9	581.5	582.1
32.5°	558.6	562.6	566.5	569.0	570.2	571.4	572.5	573.6
35°	541.5	546.2	550.9	554.0	555.5	557.0	558.5	560.0
37.5°	523.9	529.0	534.3	537.7	539.3	540.8	542.4	544.0
40°	511.4	517.0	522.5	526.3	528.2	530.2	532.1	534.0
42.5°	499.4	505.5	511.5	515.6	517.5	519.4	521.3	523.2
45°	480.9	487.5	494.2	498.5	500.7	502.8	504.9	507.1
47.5°	461.7	468.6	475.5	480.1	482.5	484.8	487.2	489.6
50°	448.5	455.7	463.1	467.9	470.2	472.6	474.9	477.2
52.5°	434.2	441.7	449.1	454.1	456.6	459.1	461.7	464.2
55°	412.7	420.5	428.2	433.4	436.2	438.9	441.8	444.5
57.5°	390.1	398.4	406.7	412.3	415.1	417.9	420.8	423.6
60°	375.1	383.2	391.4	397.0	399.9	402.9	406.0	409.0
62.5°	359.2	367.9	376.5	382.3	385.0	387.9	390.7	393.5
65°	335.1	343.8	352.6	358.4	361.2	363.9	366.7	369.5
67.5°	310.6	319.4	328.3	334.2	337.1	340.0	342.9	345.8
70°	293.6	302.7	312.0	317.8	320.4	323.0	325.6	328.1
72.5°	277.1	286.1	295.1	301.1	304.3	307.4	310.4	313.5
75°	252.2	261.4	270.6	276.5	279.4	282.1	284.9	287.7
77.5°	227.9	237.0	246.2	252.2	255.2	258.3	261.2	264.2
80°	211.3	220.4	229.3	235.4	238.3	241.3	244.3	247.3
82.5°	196.0	204.9	214.0	219.8	222.6	225.5	228.3	231.1
85°	173.8	182.9	191.8	197.7	200.8	203.8	206.8	209.7
87.5°	162.7	171.4	179.9	185.7	188.4	191.2	194.0	196.8
90°	181.4	189.5	197.6	203.0	205.9	208.7	211.5	214.2
92.5°	171.8	180.3	188.8	194.4	197.0	199.6	202.2	204.8
95°	197.0	205.1	213.2	218.3	220.4	222.4	224.6	226.7
97.5°	236.0	243.9	251.8	257.0	259.5	261.9	264.5	266.9
100°	263.2	271.1	279.0	284.0	286.1	288.1	290.3	292.4
102.5°	293.7	301.6	309.5	314.6	316.7	318.8	320.9	323.0
105°	339.6	347.5	355.5	360.6	363.0	365.3	367.7	370.0
107.5°	389.8	397.2	404.5	408.9	410.1	411.3	412.6	413.8
110°	424.4	431.3	438.1	442.3	443.9	445.5	447.2	448.8



TEST NUMBER: P331370-830

CATALOG NUMBER: SA2XXDIP-C675D1080U830-4F0-1E-UDD-D1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	459.0	465.3	471.6	475.6	477.4	479.2	481.1	482.9
115°	512.4	518.6	524.7	528.7	530.3	531.9	533.5	535.1
117.5°	563.6	569.4	575.1	578.7	580.2	581.6	583.1	584.6
120°	598.0	604.1	610.0	613.8	615.5	617.1	618.7	620.3
122.5°	634.0	639.2	644.4	647.8	649.2	650.7	652.2	653.7
125°	686.5	691.6	696.6	700.0	701.7	703.4	705.0	706.7
127.5°	737.5	742.0	746.4	749.1	750.3	751.4	752.4	753.6
130°	772.8	777.4	782.0	784.8	785.5	786.2	786.9	787.7
132.5°	806.9	810.8	814.7	817.1	818.0	819.0	819.9	820.9
135°	857.7	862.0	866.2	868.8	869.8	870.8	871.8	872.8
137.5°	906.3	910.0	913.8	915.9	916.3	916.9	917.4	917.8
140°	939.3	942.8	946.2	948.1	948.4	948.7	949.0	949.3
142.5°	970.2	973.1	976.0	977.5	977.7	977.8	978.0	978.1
145°	1017.9	1019.5	1021.1	1021.8	1021.9	1022.0	1022.1	1022.2
147.5°	1060.5	1061.3	1062.0	1062.2	1061.7	1061.3	1060.9	1060.5
150°	1088.6	1089.4	1090.1	1090.1	1089.4	1088.6	1087.9	1087.2
152.5°	1117.1	1117.9	1118.9	1118.9	1117.9	1117.1	1116.2	1115.2
155°	1153.1	1154.3	1155.6	1155.7	1155.1	1154.3	1153.6	1152.8
157.5°	1186.4	1188.1	1189.7	1190.0	1188.7	1187.6	1186.5	1185.2
160°	1206.2	1207.6	1209.1	1209.3	1208.3	1207.4	1206.4	1205.4
162.5°	1224.1	1225.7	1227.4	1227.6	1226.4	1225.3	1224.1	1222.9
165°	1247.2	1248.9	1250.6	1250.8	1249.6	1248.4	1247.2	1245.9
167.5°	1266.2	1267.9	1269.6	1269.8	1268.6	1267.2	1266.0	1264.8
170°	1276.7	1278.4	1280.1	1280.3	1278.7	1277.3	1275.8	1274.4
172.5°	1284.6	1286.3	1288.0	1288.1	1286.7	1285.2	1283.7	1282.2
175°	1293.2	1294.9	1296.6	1296.7	1295.2	1293.7	1292.3	1290.8
177.5°	1297.1	1298.3	1299.4	1299.4	1298.3	1297.1	1295.9	1294.8
180°	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4	1297.4

(END OF REPORT)