

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331679

Luminaire Tested: **SA2XXRDIP-C675D330U835-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331679
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXRDIP-C675D330U835-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 330 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3492.4 lumens
Efficiency: N/A
Efficacy: 99.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 35
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331679
CATALOG NUMBER: SA2XXRDIP-C675D330U835-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331679

CATALOG NUMBER: SA2XXRDIP-C675D330U835-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	105	105	105	105	92	92	92	81	81	81	71	71	71	66				
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	61	57				
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49				
3	86	76	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46	42				
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	43	40	37				
5	73	61	53	47	68	58	51	45	52	46	42	47	42	39	42	38	35	32				
6	67	55	47	41	63	53	45	40	47	41	37	43	38	34	38	34	31	29				
7	62	50	42	37	59	48	41	35	43	37	33	39	34	31	35	31	28	26				
8	58	46	38	33	55	44	37	32	40	34	30	36	31	27	32	28	25	23				
9	54	42	35	30	51	40	33	29	37	31	27	33	28	25	30	26	23	21				
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21	19				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18213	18213	18213
5°	18282	17985	18084
10°	18143	17690	17539
15°	17934	17167	16672
20°	17646	16417	15593
25°	17350	15567	14549
30°	16940	14693	13209
35°	16539	13742	12033
40°	16136	12760	10671
45°	15664	11654	9439
50°	15179	10540	8231
55°	14686	9340	7068
60°	14108	8076	5867
65°	13456	6785	5345
70°	12675	5589	4914
75°	11715	5097	4585
80°	10349	4556	4175
85°	8133	3594	3594



TEST NUMBER: P331679

CATALOG NUMBER: SA2XXRDIP-C675D330U835-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.6	3.0
10°-20°	289.9	8.3
20°-30°	407.1	11.7
30°-40°	443.9	12.7
40°-50°	408.2	11.7
50°-60°	320.6	9.2
60°-70°	209.0	6.0
70°-80°	107.8	3.1
80°-90°	29.6	0.8
90°-100°	26.5	0.8
100°-110°	82.4	2.4
110°-120°	140.8	4.0
120°-130°	185.2	5.3
130°-140°	207.9	6.0
140°-150°	203.8	5.8
150°-160°	171.0	4.9
160°-170°	113.4	3.2
170°-180°	39.6	1.1
0°-30°	802.6	23.0
0°-40°	1246.6	35.7
0°-60°	1975.3	56.6
0°-90°	2321.8	66.5
90°-120°	249.8	7.2
90°-150°	846.7	24.2
90°-180°	1171.0	33.5
0°-180°	3492.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1110	1118	1116	107
15°	1073	1060	1027	1008	997	302
25°	974	939	874	833	817	448
35°	839	785	697	635	610	525
45°	686	615	510	441	413	529
55°	522	440	332	273	251	466
65°	352	269	178	145	140	349
75°	188	118	82	75	74	199
85°	44	23	19	19	19	52
90°	0	5	12	12	12	3
95°	18	22	23	23	22	21
105°	76	77	78	78	78	80
115°	141	143	143	142	141	140
125°	206	209	208	207	206	184
135°	266	270	271	270	269	205
145°	323	325	328	328	326	202
155°	369	370	371	373	372	170
165°	402	401	401	404	402	113
175°	418	417	416	418	416	40
180°	419	419	419	419	419	



TEST NUMBER: P331679

CATALOG NUMBER: SA2XXRDIP-C675D330U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1132.1	1131.2	1130.3	1129.4	1128.5	1127.0	1125.0	1123.0	1121.1	1119.1	1120.9
5°	1128.0	1126.9	1125.8	1124.6	1123.5	1121.5	1118.5	1115.6	1112.6	1109.7	1111.7
7.5°	1116.4	1115.0	1113.6	1112.2	1110.8	1108.3	1104.9	1101.5	1098.0	1094.6	1095.1
10°	1106.6	1105.0	1103.4	1101.8	1100.2	1097.2	1092.6	1088.1	1083.6	1079.0	1078.4
12.5°	1094.3	1092.4	1090.4	1088.5	1086.5	1082.7	1076.9	1071.1	1065.2	1059.4	1058.2
15°	1072.9	1070.4	1067.9	1065.4	1062.9	1057.8	1050.1	1042.4	1034.7	1027.0	1022.7
17.5°	1046.6	1042.8	1039.0	1035.1	1031.3	1024.5	1014.6	1004.7	994.8	984.9	979.8
20°	1027.0	1022.4	1017.9	1013.4	1008.8	1000.9	989.5	978.2	966.9	955.5	949.8
22.5°	1005.7	1000.7	995.6	990.5	985.4	976.5	963.7	950.9	938.1	925.3	918.0
25°	973.9	966.6	959.4	952.1	944.9	933.7	918.8	903.8	888.8	873.8	864.5
27.5°	935.5	927.6	919.7	911.8	903.9	891.5	874.7	857.8	840.9	824.0	813.2
30°	908.6	899.9	891.3	882.7	874.1	860.7	842.5	824.4	806.2	788.1	776.5
32.5°	882.4	872.3	862.3	852.2	842.1	827.8	809.3	790.8	772.3	753.8	740.6
35°	839.1	827.6	816.0	804.4	792.9	777.1	757.1	737.2	717.2	697.2	682.9
37.5°	795.9	783.1	770.4	757.7	745.0	728.0	706.8	685.5	664.2	642.9	627.2
40°	765.6	752.0	738.4	724.8	711.2	693.4	671.4	649.4	627.4	605.4	589.3
42.5°	734.6	720.3	705.9	691.6	677.3	658.7	636.0	613.3	590.5	567.8	551.1
45°	686.0	670.8	655.6	640.4	625.2	605.7	581.9	558.1	534.2	510.4	494.3
47.5°	638.6	622.5	606.4	590.3	574.2	553.9	529.3	504.7	480.1	455.5	439.5
50°	604.3	588.2	572.1	556.0	539.9	519.4	494.4	469.5	444.5	419.6	403.9
52.5°	570.9	554.0	537.2	520.4	503.5	482.9	458.5	434.1	409.7	385.3	370.2
55°	521.7	504.0	486.3	468.6	450.9	429.8	405.3	380.8	356.3	331.8	318.2
57.5°	471.2	453.1	434.9	416.8	398.6	377.8	354.2	330.7	307.1	283.6	271.1
60°	436.9	418.8	400.6	382.5	364.3	343.6	320.2	296.8	273.5	250.1	238.5
62.5°	403.4	385.3	367.1	349.0	330.8	310.6	288.4	266.1	243.8	221.5	210.5
65°	352.2	333.8	315.4	297.1	278.7	259.3	238.9	218.5	198.0	177.6	169.9
67.5°	302.8	284.5	266.3	248.1	229.8	211.5	193.1	174.8	156.4	138.0	134.5
70°	268.5	250.8	233.1	215.4	197.7	181.0	165.4	149.7	134.1	118.4	116.1
72.5°	235.8	218.8	201.9	184.9	167.9	153.2	140.6	128.0	115.5	102.9	101.0
75°	187.8	172.0	156.1	140.2	124.3	112.5	104.8	97.1	89.4	81.7	80.1
77.5°	140.7	126.7	112.8	98.9	85.0	76.1	72.4	68.7	65.0	61.3	60.3
80°	111.3	99.7	88.1	76.6	65.0	58.1	55.8	53.5	51.3	49.0	48.1
82.5°	84.3	75.3	66.3	57.2	48.2	42.9	41.4	39.8	38.3	36.8	36.2
85°	43.9	39.1	34.4	29.6	24.8	22.1	21.4	20.8	20.1	19.4	19.4
87.5°	13.1	11.9	10.6	9.3	8.1	7.6	8.0	8.3	8.7	9.0	8.8
90°	0.4	1.3	2.2	3.2	4.1	5.5	7.2	8.9	10.6	12.4	12.2
92.5°	6.3	7.0	7.7	8.4	9.1	9.6	10.0	10.4	10.8	11.2	11.3
95°	18.4	19.2	19.9	20.7	21.5	22.0	22.1	22.3	22.5	22.6	22.6
97.5°	33.6	34.3	34.9	35.6	36.3	36.8	37.1	37.4	37.7	38.0	38.0
100°	44.9	45.5	46.1	46.8	47.4	47.8	48.0	48.3	48.5	48.8	48.8
102.5°	56.7	57.2	57.7	58.2	58.7	59.2	59.4	59.7	60.0	60.3	60.4
105°	76.0	76.2	76.4	76.7	76.9	77.1	77.3	77.4	77.6	77.7	77.9
107.5°	95.3	95.7	96.0	96.4	96.7	96.9	96.9	96.9	96.9	96.9	96.9
110°	107.8	108.2	108.7	109.2	109.6	109.9	109.9	109.9	109.9	109.9	109.9



TEST NUMBER: P331679

CATALOG NUMBER: SA2XXRDIP-C675D330U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	121.3	121.8	122.3	122.7	123.2	123.4	123.3	123.3	123.2	123.2	123.0
115°	141.3	141.8	142.3	142.7	143.2	143.4	143.2	143.0	142.9	142.7	142.7
117.5°	161.2	161.9	162.5	163.1	163.8	163.9	163.4	163.0	162.5	162.1	161.9
120°	174.5	175.2	175.8	176.4	177.0	177.0	176.4	175.8	175.2	174.5	174.5
122.5°	186.7	187.4	188.2	188.9	189.7	189.9	189.4	189.0	188.5	188.1	187.9
125°	205.6	206.3	207.0	207.7	208.4	208.7	208.4	208.2	208.0	207.7	207.5
127.5°	224.1	225.0	225.9	226.7	227.6	227.9	227.7	227.4	227.1	226.8	226.5
130°	235.7	236.7	237.7	238.7	239.7	240.2	240.0	239.9	239.7	239.5	239.4
132.5°	248.7	249.5	250.3	251.1	252.0	252.4	252.4	252.5	252.5	252.5	252.2
135°	266.0	266.9	267.8	268.6	269.5	270.0	270.2	270.3	270.5	270.6	270.5
137.5°	284.3	285.0	285.7	286.5	287.2	287.6	287.8	288.0	288.2	288.4	288.4
140°	295.4	296.1	296.8	297.5	298.2	298.7	299.1	299.5	299.9	300.3	300.3
142.5°	306.7	307.4	308.1	308.8	309.5	310.0	310.2	310.5	310.8	311.0	311.1
145°	322.9	323.5	324.0	324.6	325.1	325.6	326.1	326.6	327.0	327.5	327.6
147.5°	337.4	338.1	338.7	339.4	340.0	340.5	340.8	341.2	341.5	341.8	342.0
150°	347.3	347.8	348.2	348.7	349.2	349.6	349.9	350.2	350.5	350.8	351.1
152.5°	356.1	356.5	357.0	357.5	357.9	358.4	358.7	359.1	359.5	359.9	360.2
155°	369.2	369.4	369.7	369.9	370.1	370.4	370.6	370.8	371.1	371.3	371.7
157.5°	380.4	380.6	380.7	380.9	381.1	381.2	381.4	381.5	381.6	381.8	382.3
160°	387.2	387.4	387.5	387.7	387.8	388.0	388.0	388.1	388.2	388.3	388.7
162.5°	393.4	393.5	393.5	393.5	393.6	393.6	393.7	393.8	393.9	393.9	394.5
165°	401.7	401.6	401.5	401.5	401.4	401.3	401.3	401.3	401.3	401.3	401.9
167.5°	408.6	408.4	408.2	407.9	407.7	407.6	407.5	407.5	407.5	407.5	408.0
170°	412.3	412.1	411.8	411.6	411.4	411.2	411.1	411.0	411.0	410.9	411.4
172.5°	414.8	414.6	414.4	414.1	413.9	413.7	413.7	413.6	413.5	413.4	414.0
175°	418.0	417.7	417.5	417.2	417.0	416.8	416.7	416.5	416.3	416.2	416.7
177.5°	419.2	419.0	418.8	418.7	418.5	418.3	418.2	418.1	417.9	417.8	418.2
180°	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7



TEST NUMBER: P331679

CATALOG NUMBER: SA2XXRDIP-C675D330U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1122.7	1124.5	1126.3	1127.0	1126.7	1126.3	1126.0	1125.6
5°	1113.7	1115.8	1117.8	1118.5	1117.8	1117.1	1116.5	1115.8
7.5°	1095.7	1096.3	1096.9	1096.6	1095.4	1094.3	1093.1	1091.9
10°	1077.7	1077.0	1076.3	1075.3	1073.9	1072.6	1071.2	1069.8
12.5°	1057.0	1055.8	1054.5	1052.8	1050.5	1048.3	1046.0	1043.7
15°	1018.4	1014.0	1009.7	1006.4	1004.2	1001.9	999.6	997.4
17.5°	974.7	969.5	964.4	959.9	956.0	952.1	948.2	944.3
20°	944.2	938.5	932.8	927.5	922.5	917.5	912.5	907.5
22.5°	910.7	903.4	896.1	890.6	886.8	883.1	879.4	875.7
25°	855.2	845.9	836.6	830.3	826.9	823.5	820.1	816.7
27.5°	802.3	791.5	780.7	772.5	767.1	761.7	756.3	750.9
30°	765.0	753.4	741.8	733.0	726.8	720.7	714.6	708.5
32.5°	727.4	714.2	701.0	691.5	685.7	680.0	674.2	668.5
35°	668.7	654.4	640.1	630.4	625.4	620.4	615.5	610.5
37.5°	611.4	595.7	580.0	569.2	563.5	557.8	552.1	546.4
40°	573.1	557.0	540.9	529.9	524.0	518.1	512.2	506.3
42.5°	534.5	517.8	501.2	490.0	484.3	478.6	472.9	467.1
45°	478.2	462.1	446.0	435.2	429.8	424.3	418.9	413.4
47.5°	423.5	407.5	391.4	381.0	376.0	371.1	366.1	361.2
50°	388.3	372.6	357.0	346.7	342.0	337.2	332.5	327.7
52.5°	355.1	339.9	324.8	315.1	310.7	306.3	301.9	297.5
55°	304.6	290.9	277.3	268.4	264.1	259.7	255.4	251.1
57.5°	258.6	246.2	233.7	225.6	222.0	218.4	214.7	211.1
60°	227.0	215.4	203.8	196.2	192.6	189.0	185.3	181.7
62.5°	199.5	188.4	177.4	170.8	168.6	166.5	164.3	162.1
65°	162.2	154.5	146.8	142.6	141.9	141.2	140.5	139.9
67.5°	130.9	127.4	123.9	121.7	121.0	120.3	119.6	118.8
70°	113.9	111.6	109.3	107.8	106.8	105.9	105.0	104.1
72.5°	99.1	97.2	95.3	94.1	93.5	93.0	92.4	91.9
75°	78.5	76.9	75.3	74.4	74.2	74.0	73.7	73.5
77.5°	59.4	58.5	57.6	57.0	56.6	56.3	55.9	55.5
80°	47.2	46.3	45.4	44.9	44.9	44.9	44.9	44.9
82.5°	35.7	35.1	34.6	34.3	34.3	34.3	34.3	34.3
85°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	8.6	8.4	8.2	8.1	8.1	8.1	8.1	8.1
90°	12.1	11.9	11.7	11.7	11.8	11.9	11.9	12.0
92.5°	11.3	11.3	11.4	11.4	11.4	11.4	11.4	11.4
95°	22.6	22.6	22.6	22.5	22.4	22.2	22.1	21.9
97.5°	38.0	38.0	38.0	38.0	38.0	38.0	38.0	37.9
100°	48.8	48.8	48.8	48.7	48.6	48.6	48.5	48.4
102.5°	60.5	60.5	60.6	60.6	60.5	60.4	60.4	60.3
105°	78.0	78.2	78.4	78.4	78.4	78.4	78.4	78.4
107.5°	97.0	97.1	97.1	97.0	96.6	96.3	95.9	95.5
110°	109.9	109.9	109.9	109.8	109.5	109.3	109.1	108.8



TEST NUMBER: P331679

CATALOG NUMBER: SA2XXRDIP-C675D330U835-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	122.8	122.6	122.4	122.2	122.1	121.9	121.7	121.5
115°	142.6	142.5	142.4	142.3	142.0	141.8	141.6	141.3
117.5°	161.7	161.5	161.3	161.1	160.9	160.7	160.4	160.2
120°	174.5	174.5	174.5	174.4	174.2	173.9	173.7	173.5
122.5°	187.7	187.5	187.3	187.2	187.0	186.8	186.6	186.5
125°	207.3	207.0	206.8	206.6	206.6	206.5	206.4	206.3
127.5°	226.3	226.0	225.7	225.4	225.2	224.9	224.7	224.4
130°	239.2	239.1	238.9	238.7	238.4	238.0	237.7	237.4
132.5°	251.8	251.5	251.2	250.9	250.6	250.4	250.1	249.9
135°	270.5	270.4	270.3	270.2	269.9	269.7	269.5	269.2
137.5°	288.3	288.2	288.2	288.0	287.7	287.4	287.1	286.7
140°	300.3	300.3	300.3	300.1	299.8	299.5	299.2	298.9
142.5°	311.2	311.2	311.3	311.2	310.9	310.5	310.2	309.9
145°	327.7	327.7	327.8	327.7	327.4	327.1	326.8	326.4
147.5°	342.1	342.3	342.5	342.4	342.1	341.8	341.5	341.2
150°	351.3	351.5	351.8	351.8	351.5	351.3	351.1	350.8
152.5°	360.5	360.8	361.1	361.1	360.8	360.5	360.2	359.9
155°	372.1	372.5	372.9	373.0	372.7	372.5	372.3	372.0
157.5°	382.8	383.4	383.9	384.0	383.6	383.2	382.9	382.5
160°	389.2	389.7	390.2	390.2	389.9	389.6	389.3	389.0
162.5°	395.0	395.5	396.1	396.1	395.8	395.4	395.0	394.6
165°	402.4	403.0	403.5	403.6	403.2	402.8	402.4	402.1
167.5°	408.6	409.1	409.7	409.8	409.4	408.9	408.5	408.1
170°	412.0	412.5	413.1	413.1	412.7	412.2	411.7	411.2
172.5°	414.5	415.1	415.6	415.7	415.2	414.7	414.3	413.8
175°	417.3	417.8	418.4	418.4	418.0	417.5	417.0	416.5
177.5°	418.6	418.9	419.3	419.3	418.9	418.6	418.2	417.8
180°	418.7	418.7	418.7	418.7	418.7	418.7	418.7	418.7

(END OF REPORT)