

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331689

Luminaire Tested: **SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331689  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5371.2 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331689  
CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

### Luminous Intensity Polar Plot





TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	98	98	98	98	82	82	82	67	67	67	54	54	54	47
1	98	94	90	87	90	87	83	81	73	71	69	60	59	57	49	48	47	41
2	90	83	77	72	82	77	72	67	65	61	58	54	51	49	44	42	41	36
3	82	74	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	53	70	61	54	49	52	47	43	44	40	37	36	33	31	28
5	70	59	51	46	64	55	48	43	47	42	38	40	36	33	33	30	28	25
6	65	53	46	40	60	50	43	38	43	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	23	20
8	56	44	37	32	52	41	35	30	36	31	27	31	27	24	26	23	21	18
9	52	41	33	29	48	38	31	27	33	28	24	28	24	22	24	21	19	17
10	49	37	30	26	45	35	29	25	31	26	22	26	22	20	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	23720	23720	23720	23720
5°	26491	23869	21162	23869
10°	29391	23700	18344	23700
15°	30837	23353	14454	23353
20°	26734	22838	12507	22838
25°	17533	22133	11166	22133
30°	11801	21280	10107	21280
35°	9558	20203	9116	20203
40°	8500	19032	8435	19032
45°	7693	17657	7531	17657
50°	7001	16297	6975	16297
55°	6581	14787	6494	14787
60°	5506	13401	5438	13401
65°	4642	12168	5265	12168
70°	4291	10867	4966	10867
75°	4011	9457	4585	9457
80°	3701	7782	4082	7782
85°	3409	6150	3594	6150



TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.3	2.6
10°-20°	388.0	7.2
20°-30°	500.0	9.3
30°-40°	475.2	8.8
40°-50°	407.1	7.6
50°-60°	310.0	5.8
60°-70°	196.0	3.6
70°-80°	97.9	1.8
80°-90°	29.1	0.5
90°-100°	162.5	3.0
100°-110°	551.5	10.3
110°-120°	585.9	10.9
120°-130°	482.3	9.0
130°-140°	387.3	7.2
140°-150°	292.7	5.4
150°-160°	205.7	3.8
160°-170°	121.1	2.3
170°-180°	39.4	0.7
0°-30°	1027.3	19.1
0°-40°	1502.5	28.0
0°-60°	2219.6	41.3
0°-90°	2542.6	47.3
90°-120°	1300.0	24.2
90°-150°	2462.4	45.8
90°-180°	2829.0	52.7
0°-180°	5371.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1634	1473	1306	1473	1634	161
15°	1845	1397	865	1397	1845	498
25°	984	1242	627	1242	984	467
35°	485	1025	462	1025	485	310
45°	337	773	330	773	337	261
55°	234	525	231	525	234	205
65°	122	318	138	318	122	124
75°	64	152	74	152	64	68
85°	18	33	19	33	18	20
90°	26	1	26	1	26	15
95°	89	27	89	27	89	116
105°	881	95	881	95	881	852
115°	1159	168	1159	168	1159	1135
125°	940	234	940	234	940	850
135°	779	275	779	275	779	605
145°	622	314	622	314	622	395
155°	523	357	523	357	523	244
165°	459	389	459	389	459	131
175°	414	406	414	406	414	40
180°	406	406	406	406	406	



TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1528.7	1529.9	1531.2	1528.3	1528.3	1525.8	1520.5	1516.5	1505.0	1503.4	1503.4
5°	1634.5	1633.4	1635.5	1628.9	1619.7	1617.6	1607.9	1595.2	1581.9	1567.1	1564.0
7.5°	1739.6	1738.1	1734.0	1732.9	1725.8	1710.4	1694.8	1678.2	1656.1	1634.6	1623.8
10°	1792.7	1809.6	1799.3	1781.5	1785.1	1761.1	1748.3	1726.4	1708.0	1675.8	1668.7
12.5°	1845.0	1851.6	1848.4	1838.2	1833.6	1817.0	1799.8	1780.7	1746.8	1717.9	1692.8
15°	1844.8	1854.5	1857.0	1854.0	1856.5	1855.5	1846.3	1830.5	1800.9	1769.2	1741.7
17.5°	1708.6	1715.3	1732.1	1743.4	1757.7	1787.9	1802.8	1808.6	1804.2	1786.2	1766.8
20°	1555.9	1544.6	1591.6	1615.6	1636.0	1687.0	1730.9	1747.8	1774.8	1774.3	1769.2
22.5°	1339.4	1342.1	1386.6	1415.1	1474.7	1525.7	1575.8	1639.2	1691.5	1726.1	1746.4
25°	984.2	1003.6	1048.0	1086.8	1153.1	1248.1	1334.3	1434.4	1528.8	1603.3	1674.3
27.5°	739.1	740.6	775.8	811.6	851.0	928.8	1037.4	1156.9	1291.5	1402.6	1530.4
30°	633.0	629.9	644.7	666.7	700.3	760.6	842.2	959.7	1093.9	1261.3	1410.4
32.5°	557.8	558.0	569.2	585.4	613.4	654.0	709.9	805.3	932.2	1096.8	1271.5
35°	484.9	484.4	492.6	504.3	516.1	542.1	580.4	630.4	717.7	871.3	1050.0
37.5°	432.7	434.9	438.9	446.2	459.2	473.7	496.7	530.3	592.4	683.3	833.5
40°	403.3	404.3	409.9	416.0	423.7	434.9	453.8	480.8	526.3	598.8	708.5
42.5°	376.3	377.3	381.3	387.0	393.0	404.3	419.9	443.3	480.1	536.7	627.2
45°	336.9	336.9	340.5	343.0	349.7	359.9	372.6	392.0	417.6	459.4	519.6
47.5°	299.9	300.0	302.4	306.8	311.0	318.9	331.5	347.3	365.9	398.3	449.7
50°	278.7	279.2	280.7	284.3	286.9	294.0	303.7	317.5	336.9	361.9	404.8
52.5°	261.6	261.2	263.2	264.7	266.5	271.6	278.8	291.0	308.3	330.1	365.6
55°	233.8	231.7	234.8	237.4	238.9	240.9	245.0	252.7	267.5	285.9	312.4
57.5°	199.1	198.3	200.4	202.8	207.6	213.1	216.5	221.4	229.1	242.3	268.6
60°	170.5	170.5	175.1	176.6	182.2	189.4	196.5	200.6	208.3	216.9	236.3
62.5°	145.2	145.6	147.7	149.3	152.4	161.2	171.2	180.2	187.4	195.7	208.6
65°	121.5	122.5	122.5	123.5	125.6	127.6	131.7	138.8	151.6	163.3	173.0
67.5°	103.1	103.4	103.7	104.7	105.3	107.5	109.1	112.3	115.3	126.4	138.4
70°	90.9	92.4	91.9	92.9	93.4	94.4	96.5	98.0	102.6	105.2	112.3
72.5°	79.4	80.5	80.4	81.1	82.4	82.6	84.2	85.8	88.7	90.9	94.7
75°	64.3	63.8	64.3	65.3	65.8	66.4	66.4	68.4	69.9	72.0	74.5
77.5°	49.6	50.1	50.0	50.1	50.2	51.1	51.0	52.0	53.5	54.5	55.7
80°	39.8	40.3	39.8	40.3	40.8	41.3	40.8	41.3	42.9	43.9	43.9
82.5°	30.8	30.9	31.2	31.3	31.4	31.5	32.3	32.4	33.5	33.3	33.7
85°	18.4	17.9	17.9	17.9	18.4	18.9	18.4	18.4	18.9	18.9	18.9
87.5°	11.7	12.1	12.1	12.1	12.1	11.9	11.6	12.4	12.1	12.7	12.1
90°	25.8	25.8	25.8	25.8	25.8	25.0	23.5	25.0	25.8	26.6	25.8
92.5°	43.3	44.6	43.9	46.4	47.1	51.9	58.5	68.2	85.8	101.6	100.2
95°	89.1	88.3	90.7	96.9	107.1	124.3	157.1	204.8	268.1	306.4	271.3
97.5°	175.4	182.0	193.4	212.6	250.0	306.4	391.0	477.9	548.8	523.1	394.0
100°	279.8	293.9	316.6	350.2	415.1	509.7	616.8	713.7	730.1	617.5	425.2
102.5°	492.5	511.5	539.8	597.2	667.7	767.9	846.3	868.2	797.6	620.7	413.4
105°	881.0	891.9	925.5	974.0	1022.5	1048.3	1038.1	949.8	787.2	579.2	390.1
107.5°	1125.3	1139.9	1146.6	1149.3	1143.2	1105.3	1024.0	891.0	718.5	534.8	378.5
110°	1199.1	1199.9	1192.9	1178.0	1144.4	1080.3	980.3	840.3	675.4	513.6	376.0



TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	1197.9	1193.7	1180.4	1155.5	1108.8	1035.3	928.3	794.1	645.4	499.8	376.6
115°	1159.3	1152.2	1131.9	1095.9	1040.4	959.9	857.5	737.1	608.2	484.7	379.9
117.5°	1090.3	1084.4	1063.0	1025.0	968.4	892.9	800.0	694.3	584.7	477.3	385.5
120°	1045.9	1038.1	1015.4	978.7	924.0	852.8	770.0	673.0	572.2	472.9	389.3
122.5°	999.6	993.1	972.9	936.8	887.7	823.4	745.0	656.2	561.6	470.4	393.7
125°	940.4	934.1	914.6	884.9	839.5	780.9	712.1	631.6	546.4	465.9	400.2
127.5°	888.5	883.5	866.6	838.8	799.2	745.1	680.2	607.4	532.3	463.2	407.0
130°	859.1	852.8	837.2	810.6	772.3	720.7	659.0	591.7	523.0	462.0	412.0
132.5°	828.4	822.8	808.4	781.9	744.2	695.7	639.0	576.7	515.5	461.4	417.0
135°	779.4	776.2	762.2	736.4	702.7	659.0	607.4	555.8	505.0	460.4	422.9
137.5°	731.2	726.5	714.2	692.0	661.3	623.2	582.2	539.1	497.6	460.3	428.2
140°	698.1	693.4	681.6	661.3	636.3	601.9	566.0	528.4	493.3	459.6	430.7
142.5°	664.9	664.0	653.5	635.1	611.3	582.5	551.6	519.7	488.9	459.6	432.6
145°	622.2	619.9	612.1	598.8	580.0	557.4	533.1	507.3	483.1	458.1	434.6
147.5°	586.4	585.0	579.7	569.1	553.6	537.0	518.1	497.8	477.2	455.3	435.3
150°	565.2	564.4	559.7	550.3	538.6	524.5	508.1	490.9	472.1	453.4	434.6
152.5°	547.0	546.9	543.4	535.3	526.1	513.9	500.0	484.0	467.8	450.3	433.4
155°	523.0	524.5	521.4	515.9	507.3	498.7	487.0	474.5	459.6	444.8	431.5
157.5°	502.5	502.5	501.1	496.5	490.4	483.7	473.9	463.4	452.0	439.2	427.9
160°	489.3	489.3	488.6	484.7	479.2	473.7	465.1	456.5	446.4	435.4	426.0
162.5°	476.8	477.5	476.7	474.0	468.6	464.3	457.0	449.6	441.3	432.3	424.2
165°	458.9	459.6	459.6	456.5	453.4	450.3	444.8	439.3	433.1	426.0	420.6
167.5°	442.3	443.2	443.4	441.7	440.3	437.4	433.7	429.5	424.9	420.6	417.0
170°	432.3	433.8	434.6	432.3	431.5	429.9	426.8	424.5	420.6	417.4	415.1
172.5°	424.2	425.1	425.9	424.8	424.0	423.1	420.6	418.8	416.2	413.7	412.6
175°	413.5	415.1	415.9	415.1	415.1	414.3	413.5	412.7	410.4	409.6	408.8
177.5°	407.1	408.4	409.0	409.0	409.0	409.0	408.4	408.4	407.1	406.5	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1504.2	1500.9	1498.1	1490.7	1487.1	1478.9	1477.7	1477.3	1466.6	1456.4	1453.6
5°	1555.9	1547.7	1535.4	1521.1	1506.3	1491.0	1480.8	1472.7	1452.2	1432.8	1421.6
7.5°	1607.9	1590.4	1569.2	1542.2	1519.6	1494.3	1475.5	1458.7	1429.7	1401.9	1383.2
10°	1646.7	1618.1	1590.1	1552.8	1523.7	1495.1	1468.6	1445.6	1412.9	1376.2	1350.1
12.5°	1670.8	1639.4	1600.7	1564.2	1526.6	1490.2	1454.7	1425.2	1386.8	1348.8	1317.9
15°	1703.4	1669.7	1622.7	1570.7	1522.2	1474.7	1433.9	1397.1	1347.1	1301.7	1263.9
17.5°	1730.0	1683.7	1633.2	1573.0	1516.9	1456.5	1403.9	1357.0	1301.3	1246.5	1202.0
20°	1738.6	1692.7	1634.5	1574.2	1507.9	1436.9	1380.3	1329.2	1269.5	1209.8	1158.7
22.5°	1733.3	1697.6	1632.8	1560.8	1492.8	1418.5	1354.5	1295.3	1229.1	1168.1	1108.9
25°	1697.3	1685.0	1623.8	1545.1	1467.6	1381.3	1307.3	1242.4	1166.9	1101.6	1037.2
27.5°	1613.2	1639.7	1601.7	1518.0	1431.7	1339.2	1256.0	1182.2	1103.8	1030.3	966.2
30°	1532.4	1593.1	1576.8	1499.2	1402.7	1311.9	1218.5	1141.4	1057.7	982.1	918.8
32.5°	1421.7	1522.1	1538.0	1473.1	1373.3	1273.5	1175.6	1098.9	1011.5	931.9	870.2
35°	1245.5	1395.6	1464.5	1423.1	1323.1	1215.4	1114.3	1025.0	937.2	858.6	797.3
37.5°	1035.3	1239.7	1354.5	1357.5	1265.6	1153.6	1043.6	954.9	865.0	787.8	721.6
40°	898.9	1120.4	1270.0	1303.2	1225.6	1104.6	993.3	903.0	815.2	739.6	663.6
42.5°	776.4	997.1	1181.0	1238.7	1177.0	1056.8	945.2	850.7	765.4	693.9	616.2
45°	627.9	820.8	1023.5	1126.6	1092.4	981.1	863.2	773.3	693.2	631.4	556.9
47.5°	529.6	665.6	861.7	1001.2	1000.6	899.0	783.0	697.0	622.7	564.8	504.4
50°	473.7	592.1	758.0	916.3	929.5	844.3	734.0	648.8	579.4	518.6	470.1
52.5°	423.5	521.1	670.2	821.9	859.7	785.9	678.9	600.2	532.8	477.0	435.4
55°	357.8	433.4	546.7	688.6	745.8	693.7	598.8	525.3	470.6	423.7	387.9
57.5°	302.7	359.4	450.3	564.6	631.1	598.4	520.0	460.3	413.6	371.1	342.9
60°	268.0	314.4	391.5	487.0	560.5	537.5	470.6	415.0	375.2	338.4	311.9
62.5°	235.3	275.2	341.3	418.8	486.2	476.7	422.0	375.4	340.5	307.0	284.5
65°	189.4	218.5	270.0	330.8	384.9	389.5	350.2	318.5	287.4	260.8	240.9
67.5°	150.8	169.8	206.1	257.3	297.8	312.3	288.3	264.1	239.4	218.9	201.6
70°	127.1	142.4	169.0	210.3	247.6	262.9	249.1	230.2	208.8	191.9	177.1
72.5°	103.0	117.9	137.5	167.8	199.8	216.3	211.5	198.0	180.6	166.6	152.6
75°	77.6	82.2	95.5	115.9	140.9	155.2	158.8	151.6	137.8	127.1	118.9
77.5°	57.4	60.1	66.5	77.2	93.5	106.3	111.5	110.7	101.2	94.9	87.3
80°	45.9	47.5	50.5	55.1	67.4	80.1	83.7	83.7	77.1	74.5	66.9
82.5°	34.9	36.0	37.9	40.4	46.1	57.3	61.3	62.1	57.9	54.5	48.5
85°	19.9	19.4	20.4	21.9	23.0	26.0	32.2	33.2	32.2	28.1	26.5
87.5°	11.2	10.5	9.7	8.8	8.9	9.0	10.4	12.0	10.8	10.2	9.7
90°	21.1	15.6	11.7	9.4	7.8	6.3	3.1	0.8	3.1	6.3	7.8
92.5°	78.0	53.2	35.5	28.1	22.8	19.4	13.8	9.5	13.8	19.4	22.8
95°	180.6	112.6	76.6	57.8	45.3	38.3	30.5	27.4	30.5	38.3	45.3
97.5°	243.3	148.5	103.3	82.1	67.7	57.1	48.8	44.6	48.8	57.1	67.7
100°	256.4	161.0	119.6	97.7	82.1	69.6	62.5	60.2	62.5	69.6	82.1
102.5°	257.0	172.3	134.0	112.1	95.8	83.3	76.3	74.6	76.3	83.3	95.8
105°	261.1	191.5	154.8	132.9	115.7	104.0	98.5	95.4	98.5	104.0	115.7
107.5°	271.9	211.2	175.6	153.5	136.5	125.7	120.4	117.9	120.4	125.7	136.5
110°	280.6	224.3	190.0	167.3	150.9	140.7	136.0	132.9	136.0	140.7	150.9





TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	290.0	236.9	203.7	180.4	164.6	155.1	149.8	146.6	149.8	155.1	164.6
115°	304.1	256.4	222.8	201.7	186.0	176.7	172.0	168.1	172.0	176.7	186.0
117.5°	319.1	274.4	243.3	221.4	206.4	198.1	193.4	190.3	193.4	198.1	206.4
120°	329.1	286.9	256.4	234.5	218.9	211.8	207.2	204.0	207.2	211.8	218.9
122.5°	337.9	298.8	270.2	247.6	232.0	224.3	219.7	217.2	219.7	224.3	232.0
125°	351.8	316.6	288.4	266.6	250.9	241.5	236.9	234.5	236.9	241.5	250.9
127.5°	364.7	333.2	305.8	283.3	268.3	258.0	251.4	248.3	251.4	258.0	268.3
130°	372.9	343.2	315.8	293.9	278.3	267.3	259.5	256.4	259.5	267.3	278.3
132.5°	381.0	351.9	325.8	303.9	287.7	276.1	267.7	263.9	267.7	276.1	287.7
135°	391.6	364.3	339.3	317.4	299.4	287.7	278.3	275.2	278.3	287.7	299.4
137.5°	399.8	374.3	349.6	329.3	311.4	298.9	289.5	285.8	289.5	298.9	311.4
140°	404.1	379.9	356.5	336.1	318.9	306.4	297.0	293.9	297.0	306.4	318.9
142.5°	407.9	384.3	361.5	342.4	325.8	313.3	304.6	302.0	304.6	313.3	325.8
145°	412.7	390.9	369.7	352.5	336.9	325.2	317.4	314.2	317.4	325.2	336.9
147.5°	415.4	396.2	376.3	361.0	348.0	337.2	329.7	327.4	329.7	337.2	348.0
150°	416.6	398.7	380.7	366.6	354.9	344.7	338.5	336.1	338.5	344.7	354.9
152.5°	417.3	401.2	385.1	372.2	361.1	352.2	346.0	344.9	346.0	352.2	361.1
155°	418.2	404.9	391.6	379.9	371.3	362.7	358.0	357.2	358.0	362.7	371.3
157.5°	418.2	407.6	396.3	386.5	379.6	372.1	368.3	367.6	368.3	372.1	379.6
160°	418.2	408.8	399.4	390.9	384.6	378.3	375.2	374.4	375.2	378.3	384.6
162.5°	417.6	409.5	401.3	394.6	389.0	384.0	380.8	381.3	380.8	384.0	389.0
165°	415.9	410.4	403.4	398.7	394.8	390.1	388.5	389.3	388.5	390.1	394.8
167.5°	414.8	410.2	405.1	402.1	399.3	396.3	394.9	395.9	394.9	396.3	399.3
170°	413.5	409.6	405.7	403.4	401.8	399.4	398.7	400.2	398.7	399.4	401.8
172.5°	411.6	409.0	406.3	404.6	403.7	401.3	401.8	402.7	401.8	401.3	403.7
175°	409.6	408.0	406.5	405.7	405.7	404.1	404.9	405.7	404.9	404.1	405.7
177.5°	408.4	407.1	406.5	406.5	406.5	405.2	405.9	407.1	405.9	405.2	406.5
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1448.3	1445.4	1440.1	1431.9	1427.0	1418.4	1412.7	1416.0	1416.8	1416.0	1415.2
5°	1409.4	1398.6	1383.8	1369.5	1356.3	1342.0	1333.8	1330.2	1323.1	1319.0	1317.0
7.5°	1362.3	1343.8	1322.9	1298.0	1276.8	1254.7	1243.4	1237.7	1223.1	1215.2	1208.2
10°	1327.2	1298.1	1277.2	1244.5	1224.6	1195.5	1175.6	1176.1	1156.2	1144.9	1136.8
12.5°	1288.4	1256.4	1221.6	1192.2	1164.5	1141.2	1117.2	1107.5	1086.3	1075.5	1053.5
15°	1224.1	1186.8	1150.1	1110.2	1082.2	1045.9	1011.2	968.8	934.6	905.0	896.9
17.5°	1153.8	1107.7	1070.8	1024.1	976.0	915.0	874.8	850.2	829.6	814.0	802.3
20°	1105.6	1058.7	1019.4	948.9	884.1	842.8	813.2	794.3	772.8	756.0	746.8
22.5°	1055.0	1006.0	952.4	873.8	823.3	790.1	763.7	742.0	727.5	714.3	706.0
25°	983.1	929.5	841.2	787.1	746.3	711.6	693.2	679.9	664.6	646.7	638.6
27.5°	907.2	821.9	758.5	718.3	679.3	656.7	640.2	620.4	606.7	598.7	590.2
30°	850.4	765.2	715.7	671.8	644.2	619.2	599.8	588.6	575.3	561.5	555.9
32.5°	787.1	719.0	671.6	635.0	607.0	585.7	570.4	552.2	542.6	534.1	522.4
35°	708.5	657.0	613.6	584.0	557.4	540.1	522.2	511.5	494.1	487.0	482.4
37.5°	641.9	597.2	564.9	533.6	512.6	493.4	482.5	465.4	457.9	448.0	438.3
40°	604.4	560.5	529.3	503.8	480.3	466.0	452.3	438.5	427.2	422.7	410.9
42.5°	566.0	530.3	499.1	471.1	455.4	440.3	422.9	412.8	401.1	393.7	386.4
45°	513.0	481.4	454.8	431.8	414.5	398.7	387.4	370.6	364.0	349.1	343.0
47.5°	466.5	437.0	411.7	389.9	372.9	362.6	346.2	333.0	322.4	313.3	305.5
50°	433.4	408.9	384.4	365.0	349.7	334.9	318.0	311.4	295.0	290.4	285.9
52.5°	403.2	379.9	357.4	338.4	323.1	308.7	293.9	285.2	274.2	269.6	266.3
55°	360.9	338.4	317.0	300.1	284.8	270.0	260.8	250.1	245.0	241.4	237.4
57.5°	318.4	298.2	281.8	264.7	249.3	237.6	226.9	220.5	215.2	210.5	205.6
60°	291.5	272.1	257.3	241.4	225.6	215.9	207.8	200.1	194.0	186.8	184.8
62.5°	262.9	245.9	232.4	216.9	203.2	194.3	186.5	179.3	171.9	161.5	158.6
65°	223.6	210.3	196.0	183.3	171.0	162.3	151.1	142.9	139.9	138.8	138.3
67.5°	188.1	175.5	163.2	150.2	139.0	131.0	125.3	124.0	121.9	121.3	119.9
70°	164.4	152.6	140.4	128.1	117.4	115.9	113.8	111.8	109.2	108.2	107.2
72.5°	143.1	131.0	118.7	108.9	104.3	102.4	100.4	98.3	96.6	95.6	94.9
75°	109.7	98.5	90.4	86.8	84.2	82.7	79.6	78.1	77.1	75.5	75.0
77.5°	79.0	72.7	68.9	66.7	64.0	62.4	60.6	59.1	58.0	57.7	56.9
80°	60.2	57.2	54.6	51.6	50.5	48.5	48.0	46.5	47.0	45.4	45.4
82.5°	46.8	42.9	40.7	39.3	38.3	36.7	36.1	35.4	35.5	34.4	34.4
85°	24.0	23.0	21.9	20.9	20.9	19.4	19.9	19.4	19.4	18.4	17.9
87.5°	9.6	9.7	9.7	10.8	11.7	11.4	11.3	10.7	10.4	10.7	10.5
90°	9.4	11.7	15.6	21.1	25.8	26.6	25.8	25.0	23.5	25.0	25.8
92.5°	28.1	35.5	53.2	78.0	100.2	101.6	85.8	68.2	58.5	51.9	47.1
95°	57.8	76.6	112.6	180.6	271.3	306.4	268.1	204.8	157.1	124.3	107.1
97.5°	82.1	103.3	148.5	243.3	394.0	523.1	548.8	477.9	391.0	306.4	250.0
100°	97.7	119.6	161.0	256.4	425.2	617.5	730.1	713.7	616.8	509.7	415.1
102.5°	112.1	134.0	172.3	257.0	413.4	620.7	797.6	868.2	846.3	767.9	667.7
105°	132.9	154.8	191.5	261.1	390.1	579.2	787.2	949.8	1038.1	1048.3	1022.5
107.5°	153.5	175.6	211.2	271.9	378.5	534.8	718.5	891.0	1024.0	1105.3	1143.2
110°	167.3	190.0	224.3	280.6	376.0	513.6	675.4	840.3	980.3	1080.3	1144.4



TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	180.4	203.7	236.9	290.0	376.6	499.8	645.4	794.1	928.3	1035.3	1108.8
115°	201.7	222.8	256.4	304.1	379.9	484.7	608.2	737.1	857.5	959.9	1040.4
117.5°	221.4	243.3	274.4	319.1	385.5	477.3	584.7	694.3	800.0	892.9	968.4
120°	234.5	256.4	286.9	329.1	389.3	472.9	572.2	673.0	770.0	852.8	924.0
122.5°	247.6	270.2	298.8	337.9	393.7	470.4	561.6	656.2	745.0	823.4	887.7
125°	266.6	288.4	316.6	351.8	400.2	465.9	546.4	631.6	712.1	780.9	839.5
127.5°	283.3	305.8	333.2	364.7	407.0	463.2	532.3	607.4	680.2	745.1	799.2
130°	293.9	315.8	343.2	372.9	412.0	462.0	523.0	591.7	659.0	720.7	772.3
132.5°	303.9	325.8	351.9	381.0	417.0	461.4	515.5	576.7	639.0	695.7	744.2
135°	317.4	339.3	364.3	391.6	422.9	460.4	505.0	555.8	607.4	659.0	702.7
137.5°	329.3	349.6	374.3	399.8	428.2	460.3	497.6	539.1	582.2	623.2	661.3
140°	336.1	356.5	379.9	404.1	430.7	459.6	493.3	528.4	566.0	601.9	636.3
142.5°	342.4	361.5	384.3	407.9	432.6	459.6	488.9	519.7	551.6	582.5	611.3
145°	352.5	369.7	390.9	412.7	434.6	458.1	483.1	507.3	533.1	557.4	580.0
147.5°	361.0	376.3	396.2	415.4	435.3	455.3	477.2	497.8	518.1	537.0	553.6
150°	366.6	380.7	398.7	416.6	434.6	453.4	472.1	490.9	508.1	524.5	538.6
152.5°	372.2	385.1	401.2	417.3	433.4	450.3	467.8	484.0	500.0	513.9	526.1
155°	379.9	391.6	404.9	418.2	431.5	444.8	459.6	474.5	487.0	498.7	507.3
157.5°	386.5	396.3	407.6	418.2	427.9	439.2	452.0	463.4	473.9	483.7	490.4
160°	390.9	399.4	408.8	418.2	426.0	435.4	446.4	456.5	465.1	473.7	479.2
162.5°	394.6	401.3	409.5	417.6	424.2	432.3	441.3	449.6	457.0	464.3	468.6
165°	398.7	403.4	410.4	415.9	420.6	426.0	433.1	439.3	444.8	450.3	453.4
167.5°	402.1	405.1	410.2	414.8	417.0	420.6	424.9	429.5	433.7	437.4	440.3
170°	403.4	405.7	409.6	413.5	415.1	417.4	420.6	424.5	426.8	429.9	431.5
172.5°	404.6	406.3	409.0	411.6	412.6	413.7	416.2	418.8	420.6	423.1	424.0
175°	405.7	406.5	408.0	409.6	408.8	409.6	410.4	412.7	413.5	414.3	415.1
177.5°	406.5	406.5	407.1	408.4	407.1	406.5	407.1	408.4	408.4	409.0	409.0
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1410.7	1411.5	1410.3	1411.1	1410.3	1411.5	1410.7	1415.2	1416.0	1416.8	1416.0
5°	1314.4	1308.3	1307.3	1305.7	1307.3	1308.3	1314.4	1317.0	1319.0	1323.1	1330.2
7.5°	1199.5	1198.5	1196.0	1192.4	1196.0	1198.5	1199.5	1208.2	1215.2	1223.1	1237.7
10°	1125.5	1123.0	1122.5	1118.9	1122.5	1123.0	1125.5	1136.8	1144.9	1156.2	1176.1
12.5°	1039.0	1022.5	1020.8	1011.9	1020.8	1022.5	1039.0	1053.5	1075.5	1086.3	1107.5
15°	884.6	881.6	871.3	864.7	871.3	881.6	884.6	896.9	905.0	934.6	968.8
17.5°	796.4	786.4	783.2	781.8	783.2	786.4	796.4	802.3	814.0	829.6	850.2
20°	739.6	730.5	728.9	727.9	728.9	730.5	739.6	746.8	756.0	772.8	794.3
22.5°	700.4	690.8	686.9	683.8	686.9	690.8	700.4	706.0	714.3	727.5	742.0
25°	633.5	629.9	627.9	626.8	627.9	629.9	633.5	638.6	646.7	664.6	679.9
27.5°	581.1	573.2	571.7	569.1	571.7	573.2	581.1	590.2	598.7	606.7	620.4
30°	551.3	548.7	545.2	542.1	545.2	548.7	551.3	555.9	561.5	575.3	588.6
32.5°	516.2	514.0	510.9	509.4	510.9	514.0	516.2	522.4	534.1	542.6	552.2
35°	477.3	470.1	467.1	462.5	467.1	470.1	477.3	482.4	487.0	494.1	511.5
37.5°	436.1	432.4	428.1	429.6	428.1	432.4	436.1	438.3	448.0	457.9	465.4
40°	404.3	401.7	400.7	400.2	400.7	401.7	404.3	410.9	422.7	427.2	438.5
42.5°	379.0	371.9	369.3	369.2	369.3	371.9	379.0	386.4	393.7	401.1	412.8
45°	340.5	333.8	329.2	329.8	329.2	333.8	340.5	343.0	349.1	364.0	370.6
47.5°	301.1	300.9	298.0	298.9	298.0	300.9	301.1	305.5	313.3	322.4	333.0
50°	282.3	279.2	277.2	277.7	277.2	279.2	282.3	285.9	290.4	295.0	311.4
52.5°	264.3	261.7	260.0	262.2	260.0	261.7	264.3	266.3	269.6	274.2	285.2
55°	234.8	231.7	231.2	230.7	231.2	231.7	234.8	237.4	241.4	245.0	250.1
57.5°	201.8	199.8	196.7	195.4	196.7	199.8	201.8	205.6	210.5	215.2	220.5
60°	178.1	174.1	169.0	168.4	169.0	174.1	178.1	184.8	186.8	194.0	200.1
62.5°	156.5	155.7	154.7	154.6	154.7	155.7	156.5	158.6	161.5	171.9	179.3
65°	137.3	136.8	137.3	137.8	137.3	136.8	137.3	138.3	138.8	139.9	142.9
67.5°	119.7	118.7	117.8	118.2	117.8	118.7	119.7	119.9	121.3	121.9	124.0
70°	106.2	105.7	105.2	105.2	105.2	105.7	106.2	107.2	108.2	109.2	111.8
72.5°	93.1	93.0	92.5	92.1	92.5	93.0	93.1	94.9	95.6	96.6	98.3
75°	74.5	73.5	73.5	73.5	73.5	73.5	74.5	75.0	75.5	77.1	78.1
77.5°	56.8	56.3	55.7	55.3	55.7	56.3	56.8	56.9	57.7	58.0	59.1
80°	44.9	44.4	43.9	43.9	43.9	44.4	44.9	45.4	45.4	47.0	46.5
82.5°	34.3	33.8	33.7	33.3	33.7	33.8	34.3	34.4	34.4	35.5	35.4
85°	18.4	18.9	18.4	19.4	18.4	18.9	18.4	17.9	18.4	19.4	19.4
87.5°	10.5	10.1	10.5	10.1	10.5	10.1	10.5	10.5	10.7	10.4	10.7
90°	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.8	25.0	23.5	25.0
92.5°	46.4	43.9	44.6	43.3	44.6	43.9	46.4	47.1	51.9	58.5	68.2
95°	96.9	90.7	88.3	89.1	88.3	90.7	96.9	107.1	124.3	157.1	204.8
97.5°	212.6	193.4	182.0	175.4	182.0	193.4	212.6	250.0	306.4	391.0	477.9
100°	350.2	316.6	293.9	279.8	293.9	316.6	350.2	415.1	509.7	616.8	713.7
102.5°	597.2	539.8	511.5	492.5	511.5	539.8	597.2	667.7	767.9	846.3	868.2
105°	974.0	925.5	891.9	881.0	891.9	925.5	974.0	1022.5	1048.3	1038.1	949.8
107.5°	1149.3	1146.6	1139.9	1125.3	1139.9	1146.6	1149.3	1143.2	1105.3	1024.0	891.0
110°	1178.0	1192.9	1199.9	1199.1	1199.9	1192.9	1178.0	1144.4	1080.3	980.3	840.3



TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	1155.5	1180.4	1193.7	1197.9	1193.7	1180.4	1155.5	1108.8	1035.3	928.3	794.1
115°	1095.9	1131.9	1152.2	1159.3	1152.2	1131.9	1095.9	1040.4	959.9	857.5	737.1
117.5°	1025.0	1063.0	1084.4	1090.3	1084.4	1063.0	1025.0	968.4	892.9	800.0	694.3
120°	978.7	1015.4	1038.1	1045.9	1038.1	1015.4	978.7	924.0	852.8	770.0	673.0
122.5°	936.8	972.9	993.1	999.6	993.1	972.9	936.8	887.7	823.4	745.0	656.2
125°	884.9	914.6	934.1	940.4	934.1	914.6	884.9	839.5	780.9	712.1	631.6
127.5°	838.8	866.6	883.5	888.5	883.5	866.6	838.8	799.2	745.1	680.2	607.4
130°	810.6	837.2	852.8	859.1	852.8	837.2	810.6	772.3	720.7	659.0	591.7
132.5°	781.9	808.4	822.8	828.4	822.8	808.4	781.9	744.2	695.7	639.0	576.7
135°	736.4	762.2	776.2	779.4	776.2	762.2	736.4	702.7	659.0	607.4	555.8
137.5°	692.0	714.2	726.5	731.2	726.5	714.2	692.0	661.3	623.2	582.2	539.1
140°	661.3	681.6	693.4	698.1	693.4	681.6	661.3	636.3	601.9	566.0	528.4
142.5°	635.1	653.5	664.0	664.9	664.0	653.5	635.1	611.3	582.5	551.6	519.7
145°	598.8	612.1	619.9	622.2	619.9	612.1	598.8	580.0	557.4	533.1	507.3
147.5°	569.1	579.7	585.0	586.4	585.0	579.7	569.1	553.6	537.0	518.1	497.8
150°	550.3	559.7	564.4	565.2	564.4	559.7	550.3	538.6	524.5	508.1	490.9
152.5°	535.3	543.4	546.9	547.0	546.9	543.4	535.3	526.1	513.9	500.0	484.0
155°	515.9	521.4	524.5	523.0	524.5	521.4	515.9	507.3	498.7	487.0	474.5
157.5°	496.5	501.1	502.5	502.5	502.5	501.1	496.5	490.4	483.7	473.9	463.4
160°	484.7	488.6	489.3	489.3	489.3	488.6	484.7	479.2	473.7	465.1	456.5
162.5°	474.0	476.7	477.5	476.8	477.5	476.7	474.0	468.6	464.3	457.0	449.6
165°	456.5	459.6	459.6	458.9	459.6	459.6	456.5	453.4	450.3	444.8	439.3
167.5°	441.7	443.4	443.2	442.3	443.2	443.4	441.7	440.3	437.4	433.7	429.5
170°	432.3	434.6	433.8	432.3	433.8	434.6	432.3	431.5	429.9	426.8	424.5
172.5°	424.8	425.9	425.1	424.2	425.1	425.9	424.8	424.0	423.1	420.6	418.8
175°	415.1	415.9	415.1	413.5	415.1	415.9	415.1	415.1	414.3	413.5	412.7
177.5°	409.0	409.0	408.4	407.1	408.4	409.0	409.0	409.0	409.0	408.4	408.4
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1412.7	1418.4	1427.0	1431.9	1440.1	1445.4	1448.3	1453.6	1456.4	1466.6	1477.3
5°	1333.8	1342.0	1356.3	1369.5	1383.8	1398.6	1409.4	1421.6	1432.8	1452.2	1472.7
7.5°	1243.4	1254.7	1276.8	1298.0	1322.9	1343.8	1362.3	1383.2	1401.9	1429.7	1458.7
10°	1175.6	1195.5	1224.6	1244.5	1277.2	1298.1	1327.2	1350.1	1376.2	1412.9	1445.6
12.5°	1117.2	1141.2	1164.5	1192.2	1221.6	1256.4	1288.4	1317.9	1348.8	1386.8	1425.2
15°	1011.2	1045.9	1082.2	1110.2	1150.1	1186.8	1224.1	1263.9	1301.7	1347.1	1397.1
17.5°	874.8	915.0	976.0	1024.1	1070.8	1107.7	1153.8	1202.0	1246.5	1301.3	1357.0
20°	813.2	842.8	884.1	948.9	1019.4	1058.7	1105.6	1158.7	1209.8	1269.5	1329.2
22.5°	763.7	790.1	823.3	873.8	952.4	1006.0	1055.0	1108.9	1168.1	1229.1	1295.3
25°	693.2	711.6	746.3	787.1	841.2	929.5	983.1	1037.2	1101.6	1166.9	1242.4
27.5°	640.2	656.7	679.3	718.3	758.5	821.9	907.2	966.2	1030.3	1103.8	1182.2
30°	599.8	619.2	644.2	671.8	715.7	765.2	850.4	918.8	982.1	1057.7	1141.4
32.5°	570.4	585.7	607.0	635.0	671.6	719.0	787.1	870.2	931.9	1011.5	1098.9
35°	522.2	540.1	557.4	584.0	613.6	657.0	708.5	797.3	858.6	937.2	1025.0
37.5°	482.5	493.4	512.6	533.6	564.9	597.2	641.9	721.6	787.8	865.0	954.9
40°	452.3	466.0	480.3	503.8	529.3	560.5	604.4	663.6	739.6	815.2	903.0
42.5°	422.9	440.3	455.4	471.1	499.1	530.3	566.0	616.2	693.9	765.4	850.7
45°	387.4	398.7	414.5	431.8	454.8	481.4	513.0	556.9	631.4	693.2	773.3
47.5°	346.2	362.6	372.9	389.9	411.7	437.0	466.5	504.4	564.8	622.7	697.0
50°	318.0	334.9	349.7	365.0	384.4	408.9	433.4	470.1	518.6	579.4	648.8
52.5°	293.9	308.7	323.1	338.4	357.4	379.9	403.2	435.4	477.0	532.8	600.2
55°	260.8	270.0	284.8	300.1	317.0	338.4	360.9	387.9	423.7	470.6	525.3
57.5°	226.9	237.6	249.3	264.7	281.8	298.2	318.4	342.9	371.1	413.6	460.3
60°	207.8	215.9	225.6	241.4	257.3	272.1	291.5	311.9	338.4	375.2	415.0
62.5°	186.5	194.3	203.2	216.9	232.4	245.9	262.9	284.5	307.0	340.5	375.4
65°	151.1	162.3	171.0	183.3	196.0	210.3	223.6	240.9	260.8	287.4	318.5
67.5°	125.3	131.0	139.0	150.2	163.2	175.5	188.1	201.6	218.9	239.4	264.1
70°	113.8	115.9	117.4	128.1	140.4	152.6	164.4	177.1	191.9	208.8	230.2
72.5°	100.4	102.4	104.3	108.9	118.7	131.0	143.1	152.6	166.6	180.6	198.0
75°	79.6	82.7	84.2	86.8	90.4	98.5	109.7	118.9	127.1	137.8	151.6
77.5°	60.6	62.4	64.0	66.7	68.9	72.7	79.0	87.3	94.9	101.2	110.7
80°	48.0	48.5	50.5	51.6	54.6	57.2	60.2	66.9	74.5	77.1	83.7
82.5°	36.1	36.7	38.3	39.3	40.7	42.9	46.8	48.5	54.5	57.9	62.1
85°	19.9	19.4	20.9	20.9	21.9	23.0	24.0	26.5	28.1	32.2	33.2
87.5°	11.3	11.4	11.7	10.8	9.7	9.7	9.6	9.7	10.2	10.8	12.0
90°	25.8	26.6	25.8	21.1	15.6	11.7	9.4	7.8	6.3	3.1	0.8
92.5°	85.8	101.6	100.2	78.0	53.2	35.5	28.1	22.8	19.4	13.8	9.5
95°	268.1	306.4	271.3	180.6	112.6	76.6	57.8	45.3	38.3	30.5	27.4
97.5°	548.8	523.1	394.0	243.3	148.5	103.3	82.1	67.7	57.1	48.8	44.6
100°	730.1	617.5	425.2	256.4	161.0	119.6	97.7	82.1	69.6	62.5	60.2
102.5°	797.6	620.7	413.4	257.0	172.3	134.0	112.1	95.8	83.3	76.3	74.6
105°	787.2	579.2	390.1	261.1	191.5	154.8	132.9	115.7	104.0	98.5	95.4
107.5°	718.5	534.8	378.5	271.9	211.2	175.6	153.5	136.5	125.7	120.4	117.9
110°	675.4	513.6	376.0	280.6	224.3	190.0	167.3	150.9	140.7	136.0	132.9



TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	645.4	499.8	376.6	290.0	236.9	203.7	180.4	164.6	155.1	149.8	146.6
115°	608.2	484.7	379.9	304.1	256.4	222.8	201.7	186.0	176.7	172.0	168.1
117.5°	584.7	477.3	385.5	319.1	274.4	243.3	221.4	206.4	198.1	193.4	190.3
120°	572.2	472.9	389.3	329.1	286.9	256.4	234.5	218.9	211.8	207.2	204.0
122.5°	561.6	470.4	393.7	337.9	298.8	270.2	247.6	232.0	224.3	219.7	217.2
125°	546.4	465.9	400.2	351.8	316.6	288.4	266.6	250.9	241.5	236.9	234.5
127.5°	532.3	463.2	407.0	364.7	333.2	305.8	283.3	268.3	258.0	251.4	248.3
130°	523.0	462.0	412.0	372.9	343.2	315.8	293.9	278.3	267.3	259.5	256.4
132.5°	515.5	461.4	417.0	381.0	351.9	325.8	303.9	287.7	276.1	267.7	263.9
135°	505.0	460.4	422.9	391.6	364.3	339.3	317.4	299.4	287.7	278.3	275.2
137.5°	497.6	460.3	428.2	399.8	374.3	349.6	329.3	311.4	298.9	289.5	285.8
140°	493.3	459.6	430.7	404.1	379.9	356.5	336.1	318.9	306.4	297.0	293.9
142.5°	488.9	459.6	432.6	407.9	384.3	361.5	342.4	325.8	313.3	304.6	302.0
145°	483.1	458.1	434.6	412.7	390.9	369.7	352.5	336.9	325.2	317.4	314.2
147.5°	477.2	455.3	435.3	415.4	396.2	376.3	361.0	348.0	337.2	329.7	327.4
150°	472.1	453.4	434.6	416.6	398.7	380.7	366.6	354.9	344.7	338.5	336.1
152.5°	467.8	450.3	433.4	417.3	401.2	385.1	372.2	361.1	352.2	346.0	344.9
155°	459.6	444.8	431.5	418.2	404.9	391.6	379.9	371.3	362.7	358.0	357.2
157.5°	452.0	439.2	427.9	418.2	407.6	396.3	386.5	379.6	372.1	368.3	367.6
160°	446.4	435.4	426.0	418.2	408.8	399.4	390.9	384.6	378.3	375.2	374.4
162.5°	441.3	432.3	424.2	417.6	409.5	401.3	394.6	389.0	384.0	380.8	381.3
165°	433.1	426.0	420.6	415.9	410.4	403.4	398.7	394.8	390.1	388.5	389.3
167.5°	424.9	420.6	417.0	414.8	410.2	405.1	402.1	399.3	396.3	394.9	395.9
170°	420.6	417.4	415.1	413.5	409.6	405.7	403.4	401.8	399.4	398.7	400.2
172.5°	416.2	413.7	412.6	411.6	409.0	406.3	404.6	403.7	401.3	401.8	402.7
175°	410.4	409.6	408.8	409.6	408.0	406.5	405.7	405.7	404.1	404.9	405.7
177.5°	407.1	406.5	407.1	408.4	407.1	406.5	406.5	406.5	405.2	405.9	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5





TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1477.7	1478.9	1487.1	1490.7	1498.1	1500.9	1504.2	1503.4	1503.4	1505.0	1516.5
5°	1480.8	1491.0	1506.3	1521.1	1535.4	1547.7	1555.9	1564.0	1567.1	1581.9	1595.2
7.5°	1475.5	1494.3	1519.6	1542.2	1569.2	1590.4	1607.9	1623.8	1634.6	1656.1	1678.2
10°	1468.6	1495.1	1523.7	1552.8	1590.1	1618.1	1646.7	1668.7	1675.8	1708.0	1726.4
12.5°	1454.7	1490.2	1526.6	1564.2	1600.7	1639.4	1670.8	1692.8	1717.9	1746.8	1780.7
15°	1433.9	1474.7	1522.2	1570.7	1622.7	1669.7	1703.4	1741.7	1769.2	1800.9	1830.5
17.5°	1403.9	1456.5	1516.9	1573.0	1633.2	1683.7	1730.0	1766.8	1786.2	1804.2	1808.6
20°	1380.3	1436.9	1507.9	1574.2	1634.5	1692.7	1738.6	1769.2	1774.3	1774.8	1747.8
22.5°	1354.5	1418.5	1492.8	1560.8	1632.8	1697.6	1733.3	1746.4	1726.1	1691.5	1639.2
25°	1307.3	1381.3	1467.6	1545.1	1623.8	1685.0	1697.3	1674.3	1603.3	1528.8	1434.4
27.5°	1256.0	1339.2	1431.7	1518.0	1601.7	1639.7	1613.2	1530.4	1402.6	1291.5	1156.9
30°	1218.5	1311.9	1402.7	1499.2	1576.8	1593.1	1532.4	1410.4	1261.3	1093.9	959.7
32.5°	1175.6	1273.5	1373.3	1473.1	1538.0	1522.1	1421.7	1271.5	1096.8	932.2	805.3
35°	1114.3	1215.4	1323.1	1423.1	1464.5	1395.6	1245.5	1050.0	871.3	717.7	630.4
37.5°	1043.6	1153.6	1265.6	1357.5	1354.5	1239.7	1035.3	833.5	683.3	592.4	530.3
40°	993.3	1104.6	1225.6	1303.2	1270.0	1120.4	898.9	708.5	598.8	526.3	480.8
42.5°	945.2	1056.8	1177.0	1238.7	1181.0	997.1	776.4	627.2	536.7	480.1	443.3
45°	863.2	981.1	1092.4	1126.6	1023.5	820.8	627.9	519.6	459.4	417.6	392.0
47.5°	783.0	899.0	1000.6	1001.2	861.7	665.6	529.6	449.7	398.3	365.9	347.3
50°	734.0	844.3	929.5	916.3	758.0	592.1	473.7	404.8	361.9	336.9	317.5
52.5°	678.9	785.9	859.7	821.9	670.2	521.1	423.5	365.6	330.1	308.3	291.0
55°	598.8	693.7	745.8	688.6	546.7	433.4	357.8	312.4	285.9	267.5	252.7
57.5°	520.0	598.4	631.1	564.6	450.3	359.4	302.7	268.6	242.3	229.1	221.4
60°	470.6	537.5	560.5	487.0	391.5	314.4	268.0	236.3	216.9	208.3	200.6
62.5°	422.0	476.7	486.2	418.8	341.3	275.2	235.3	208.6	195.7	187.4	180.2
65°	350.2	389.5	384.9	330.8	270.0	218.5	189.4	173.0	163.3	151.6	138.8
67.5°	288.3	312.3	297.8	257.3	206.1	169.8	150.8	138.4	126.4	115.3	112.3
70°	249.1	262.9	247.6	210.3	169.0	142.4	127.1	112.3	105.2	102.6	98.0
72.5°	211.5	216.3	199.8	167.8	137.5	117.9	103.0	94.7	90.9	88.7	85.8
75°	158.8	155.2	140.9	115.9	95.5	82.2	77.6	74.5	72.0	69.9	68.4
77.5°	111.5	106.3	93.5	77.2	66.5	60.1	57.4	55.7	54.5	53.5	52.0
80°	83.7	80.1	67.4	55.1	50.5	47.5	45.9	43.9	43.9	42.9	41.3
82.5°	61.3	57.3	46.1	40.4	37.9	36.0	34.9	33.7	33.3	33.5	32.4
85°	32.2	26.0	23.0	21.9	20.4	19.4	19.9	18.9	18.9	18.9	18.4
87.5°	10.4	9.0	8.9	8.8	9.7	10.5	11.2	12.1	12.7	12.1	12.4
90°	3.1	6.3	7.8	9.4	11.7	15.6	21.1	25.8	26.6	25.8	25.0
92.5°	13.8	19.4	22.8	28.1	35.5	53.2	78.0	100.2	101.6	85.8	68.2
95°	30.5	38.3	45.3	57.8	76.6	112.6	180.6	271.3	306.4	268.1	204.8
97.5°	48.8	57.1	67.7	82.1	103.3	148.5	243.3	394.0	523.1	548.8	477.9
100°	62.5	69.6	82.1	97.7	119.6	161.0	256.4	425.2	617.5	730.1	713.7
102.5°	76.3	83.3	95.8	112.1	134.0	172.3	257.0	413.4	620.7	797.6	868.2
105°	98.5	104.0	115.7	132.9	154.8	191.5	261.1	390.1	579.2	787.2	949.8
107.5°	120.4	125.7	136.5	153.5	175.6	211.2	271.9	378.5	534.8	718.5	891.0
110°	136.0	140.7	150.9	167.3	190.0	224.3	280.6	376.0	513.6	675.4	840.3





TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	149.8	155.1	164.6	180.4	203.7	236.9	290.0	376.6	499.8	645.4	794.1
115°	172.0	176.7	186.0	201.7	222.8	256.4	304.1	379.9	484.7	608.2	737.1
117.5°	193.4	198.1	206.4	221.4	243.3	274.4	319.1	385.5	477.3	584.7	694.3
120°	207.2	211.8	218.9	234.5	256.4	286.9	329.1	389.3	472.9	572.2	673.0
122.5°	219.7	224.3	232.0	247.6	270.2	298.8	337.9	393.7	470.4	561.6	656.2
125°	236.9	241.5	250.9	266.6	288.4	316.6	351.8	400.2	465.9	546.4	631.6
127.5°	251.4	258.0	268.3	283.3	305.8	333.2	364.7	407.0	463.2	532.3	607.4
130°	259.5	267.3	278.3	293.9	315.8	343.2	372.9	412.0	462.0	523.0	591.7
132.5°	267.7	276.1	287.7	303.9	325.8	351.9	381.0	417.0	461.4	515.5	576.7
135°	278.3	287.7	299.4	317.4	339.3	364.3	391.6	422.9	460.4	505.0	555.8
137.5°	289.5	298.9	311.4	329.3	349.6	374.3	399.8	428.2	460.3	497.6	539.1
140°	297.0	306.4	318.9	336.1	356.5	379.9	404.1	430.7	459.6	493.3	528.4
142.5°	304.6	313.3	325.8	342.4	361.5	384.3	407.9	432.6	459.6	488.9	519.7
145°	317.4	325.2	336.9	352.5	369.7	390.9	412.7	434.6	458.1	483.1	507.3
147.5°	329.7	337.2	348.0	361.0	376.3	396.2	415.4	435.3	455.3	477.2	497.8
150°	338.5	344.7	354.9	366.6	380.7	398.7	416.6	434.6	453.4	472.1	490.9
152.5°	346.0	352.2	361.1	372.2	385.1	401.2	417.3	433.4	450.3	467.8	484.0
155°	358.0	362.7	371.3	379.9	391.6	404.9	418.2	431.5	444.8	459.6	474.5
157.5°	368.3	372.1	379.6	386.5	396.3	407.6	418.2	427.9	439.2	452.0	463.4
160°	375.2	378.3	384.6	390.9	399.4	408.8	418.2	426.0	435.4	446.4	456.5
162.5°	380.8	384.0	389.0	394.6	401.3	409.5	417.6	424.2	432.3	441.3	449.6
165°	388.5	390.1	394.8	398.7	403.4	410.4	415.9	420.6	426.0	433.1	439.3
167.5°	394.9	396.3	399.3	402.1	405.1	410.2	414.8	417.0	420.6	424.9	429.5
170°	398.7	399.4	401.8	403.4	405.7	409.6	413.5	415.1	417.4	420.6	424.5
172.5°	401.8	401.3	403.7	404.6	406.3	409.0	411.6	412.6	413.7	416.2	418.8
175°	404.9	404.1	405.7	405.7	406.5	408.0	409.6	408.8	409.6	410.4	412.7
177.5°	405.9	405.2	406.5	406.5	406.5	407.1	408.4	407.1	406.5	407.1	408.4
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1520.5	1525.8	1528.3	1528.3	1531.2	1529.9	1528.7
5°	1607.9	1617.6	1619.7	1628.9	1635.5	1633.4	1634.5
7.5°	1694.8	1710.4	1725.8	1732.9	1734.0	1738.1	1739.6
10°	1748.3	1761.1	1785.1	1781.5	1799.3	1809.6	1792.7
12.5°	1799.8	1817.0	1833.6	1838.2	1848.4	1851.6	1845.0
15°	1846.3	1855.5	1856.5	1854.0	1857.0	1854.5	1844.8
17.5°	1802.8	1787.9	1757.7	1743.4	1732.1	1715.3	1708.6
20°	1730.9	1687.0	1636.0	1615.6	1591.6	1544.6	1555.9
22.5°	1575.8	1525.7	1474.7	1415.1	1386.6	1342.1	1339.4
25°	1334.3	1248.1	1153.1	1086.8	1048.0	1003.6	984.2
27.5°	1037.4	928.8	851.0	811.6	775.8	740.6	739.1
30°	842.2	760.6	700.3	666.7	644.7	629.9	633.0
32.5°	709.9	654.0	613.4	585.4	569.2	558.0	557.8
35°	580.4	542.1	516.1	504.3	492.6	484.4	484.9
37.5°	496.7	473.7	459.2	446.2	438.9	434.9	432.7
40°	453.8	434.9	423.7	416.0	409.9	404.3	403.3
42.5°	419.9	404.3	393.0	387.0	381.3	377.3	376.3
45°	372.6	359.9	349.7	343.0	340.5	336.9	336.9
47.5°	331.5	318.9	311.0	306.8	302.4	300.0	299.9
50°	303.7	294.0	286.9	284.3	280.7	279.2	278.7
52.5°	278.8	271.6	266.5	264.7	263.2	261.2	261.6
55°	245.0	240.9	238.9	237.4	234.8	231.7	233.8
57.5°	216.5	213.1	207.6	202.8	200.4	198.3	199.1
60°	196.5	189.4	182.2	176.6	175.1	170.5	170.5
62.5°	171.2	161.2	152.4	149.3	147.7	145.6	145.2
65°	131.7	127.6	125.6	123.5	122.5	122.5	121.5
67.5°	109.1	107.5	105.3	104.7	103.7	103.4	103.1
70°	96.5	94.4	93.4	92.9	91.9	92.4	90.9
72.5°	84.2	82.6	82.4	81.1	80.4	80.5	79.4
75°	66.4	66.4	65.8	65.3	64.3	63.8	64.3
77.5°	51.0	51.1	50.2	50.1	50.0	50.1	49.6
80°	40.8	41.3	40.8	40.3	39.8	40.3	39.8
82.5°	32.3	31.5	31.4	31.3	31.2	30.9	30.8
85°	18.4	18.9	18.4	17.9	17.9	17.9	18.4
87.5°	11.6	11.9	12.1	12.1	12.1	12.1	11.7
90°	23.5	25.0	25.8	25.8	25.8	25.8	25.8
92.5°	58.5	51.9	47.1	46.4	43.9	44.6	43.3
95°	157.1	124.3	107.1	96.9	90.7	88.3	89.1
97.5°	391.0	306.4	250.0	212.6	193.4	182.0	175.4
100°	616.8	509.7	415.1	350.2	316.6	293.9	279.8
102.5°	846.3	767.9	667.7	597.2	539.8	511.5	492.5
105°	1038.1	1048.3	1022.5	974.0	925.5	891.9	881.0
107.5°	1024.0	1105.3	1143.2	1149.3	1146.6	1139.9	1125.3
110°	980.3	1080.3	1144.4	1178.0	1192.9	1199.9	1199.1



TEST NUMBER: P331689

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-A4

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	928.3	1035.3	1108.8	1155.5	1180.4	1193.7	1197.9
115°	857.5	959.9	1040.4	1095.9	1131.9	1152.2	1159.3
117.5°	800.0	892.9	968.4	1025.0	1063.0	1084.4	1090.3
120°	770.0	852.8	924.0	978.7	1015.4	1038.1	1045.9
122.5°	745.0	823.4	887.7	936.8	972.9	993.1	999.6
125°	712.1	780.9	839.5	884.9	914.6	934.1	940.4
127.5°	680.2	745.1	799.2	838.8	866.6	883.5	888.5
130°	659.0	720.7	772.3	810.6	837.2	852.8	859.1
132.5°	639.0	695.7	744.2	781.9	808.4	822.8	828.4
135°	607.4	659.0	702.7	736.4	762.2	776.2	779.4
137.5°	582.2	623.2	661.3	692.0	714.2	726.5	731.2
140°	566.0	601.9	636.3	661.3	681.6	693.4	698.1
142.5°	551.6	582.5	611.3	635.1	653.5	664.0	664.9
145°	533.1	557.4	580.0	598.8	612.1	619.9	622.2
147.5°	518.1	537.0	553.6	569.1	579.7	585.0	586.4
150°	508.1	524.5	538.6	550.3	559.7	564.4	565.2
152.5°	500.0	513.9	526.1	535.3	543.4	546.9	547.0
155°	487.0	498.7	507.3	515.9	521.4	524.5	523.0
157.5°	473.9	483.7	490.4	496.5	501.1	502.5	502.5
160°	465.1	473.7	479.2	484.7	488.6	489.3	489.3
162.5°	457.0	464.3	468.6	474.0	476.7	477.5	476.8
165°	444.8	450.3	453.4	456.5	459.6	459.6	458.9
167.5°	433.7	437.4	440.3	441.7	443.4	443.2	442.3
170°	426.8	429.9	431.5	432.3	434.6	433.8	432.3
172.5°	420.6	423.1	424.0	424.8	425.9	425.1	424.2
175°	413.5	414.3	415.1	415.1	415.9	415.1	413.5
177.5°	408.4	409.0	409.0	409.0	409.0	408.4	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5

(END OF REPORT)