

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331692

Luminaire Tested: **SA2XXRDIP-C675D725U835-4F0-1E-UDD-F4**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331692  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-16,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F4  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 725 LUMENS PER FOOT, BATWING OPTIC  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5152.3 lumens  
Efficiency: N/A  
Efficacy: 112.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 45.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331692  
CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F4

### Luminous Intensity Polar Plot





TEST NUMBER: P331692

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F4

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	45				
1	97	93	89	86	89	85	82	79	71	69	67	58	57	55	46	45	44	39				
2	89	82	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33				
3	81	72	65	60	74	67	60	56	56	51	48	46	43	40	37	35	33	29				
4	75	64	57	51	68	59	53	47	50	45	41	41	38	35	33	31	29	25				
5	69	57	49	44	63	53	46	41	45	40	36	37	33	30	30	27	25	22				
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	22	20				
7	59	47	39	34	54	43	36	32	37	32	28	31	27	24	25	22	20	17				
8	54	42	35	30	50	39	33	28	34	28	25	28	24	21	23	20	18	16				
9	51	39	32	27	47	36	30	25	31	26	22	26	22	19	22	19	16	14				
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18213	18213	18213
5°	18282	17985	18084
10°	18143	17690	17539
15°	17934	17167	16672
20°	17646	16417	15593
25°	17350	15567	14549
30°	16940	14693	13209
35°	16539	13742	12033
40°	16136	12760	10671
45°	15664	11654	9439
50°	15179	10540	8231
55°	14686	9340	7068
60°	14108	8076	5867
65°	13456	6785	5345
70°	12675	5589	4914
75°	11715	5097	4585
80°	10349	4556	4175
85°	8133	3594	3594



TEST NUMBER: P331692

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F4

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.6	2.0
10°-20°	289.9	5.6
20°-30°	407.1	7.9
30°-40°	443.9	8.6
40°-50°	408.2	7.9
50°-60°	320.6	6.2
60°-70°	209.0	4.1
70°-80°	107.8	2.1
80°-90°	31.6	0.6
90°-100°	162.5	3.2
100°-110°	551.5	10.7
110°-120°	585.9	11.4
120°-130°	482.3	9.4
130°-140°	387.3	7.5
140°-150°	292.7	5.7
150°-160°	205.7	4.0
160°-170°	121.1	2.4
170°-180°	39.4	0.8
0°-30°	802.6	15.6
0°-40°	1246.6	24.2
0°-60°	1975.3	38.3
0°-90°	2323.7	45.1
90°-120°	1300.0	25.2
90°-150°	2462.4	47.8
90°-180°	2829.0	54.9
0°-180°	5152.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1128	1128	1128	1128	1128	
5°	1128	1122	1110	1118	1116	107
15°	1073	1060	1027	1008	997	302
25°	974	939	874	833	817	448
35°	839	785	697	635	610	525
45°	686	615	510	441	413	529
55°	522	440	332	273	251	466
65°	352	269	178	145	140	349
75°	188	118	82	75	74	199
85°	44	23	19	19	19	52
90°	1	11	27	25	26	3
95°	27	67	306	116	89	29
105°	95	144	579	1035	881	101
115°	168	212	485	1000	1159	167
125°	234	278	466	810	940	208
135°	275	328	460	681	779	213
145°	314	361	458	569	622	197
155°	357	386	445	503	523	164
165°	389	401	426	452	459	110
175°	406	406	410	415	414	39
180°	406	406	406	406	406	



TEST NUMBER: P331692

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1132.1	1131.2	1130.3	1129.4	1128.5	1127.0	1125.0	1123.0	1121.1	1119.1	1120.9
5°	1128.0	1126.9	1125.8	1124.6	1123.5	1121.5	1118.5	1115.6	1112.6	1109.7	1111.7
7.5°	1116.4	1115.0	1113.6	1112.2	1110.8	1108.3	1104.9	1101.5	1098.0	1094.6	1095.1
10°	1106.6	1105.0	1103.4	1101.8	1100.2	1097.2	1092.6	1088.1	1083.6	1079.0	1078.4
12.5°	1094.3	1092.4	1090.4	1088.5	1086.5	1082.7	1076.9	1071.1	1065.2	1059.4	1058.2
15°	1072.9	1070.4	1067.9	1065.4	1062.9	1057.8	1050.1	1042.4	1034.7	1027.0	1022.7
17.5°	1046.6	1042.8	1039.0	1035.1	1031.3	1024.5	1014.6	1004.7	994.8	984.9	979.8
20°	1027.0	1022.4	1017.9	1013.4	1008.8	1000.9	989.5	978.2	966.9	955.5	949.8
22.5°	1005.7	1000.7	995.6	990.5	985.4	976.5	963.7	950.9	938.1	925.3	918.0
25°	973.9	966.6	959.4	952.1	944.9	933.7	918.8	903.8	888.8	873.8	864.5
27.5°	935.5	927.6	919.7	911.8	903.9	891.5	874.7	857.8	840.9	824.0	813.2
30°	908.6	899.9	891.3	882.7	874.1	860.7	842.5	824.4	806.2	788.1	776.5
32.5°	882.4	872.3	862.3	852.2	842.1	827.8	809.3	790.8	772.3	753.8	740.6
35°	839.1	827.6	816.0	804.4	792.9	777.1	757.1	737.2	717.2	697.2	682.9
37.5°	795.9	783.1	770.4	757.7	745.0	728.0	706.8	685.5	664.2	642.9	627.2
40°	765.6	752.0	738.4	724.8	711.2	693.4	671.4	649.4	627.4	605.4	589.3
42.5°	734.6	720.3	705.9	691.6	677.3	658.7	636.0	613.3	590.5	567.8	551.1
45°	686.0	670.8	655.6	640.4	625.2	605.7	581.9	558.1	534.2	510.4	494.3
47.5°	638.6	622.5	606.4	590.3	574.2	553.9	529.3	504.7	480.1	455.5	439.5
50°	604.3	588.2	572.1	556.0	539.9	519.4	494.4	469.5	444.5	419.6	403.9
52.5°	570.9	554.0	537.2	520.4	503.5	482.9	458.5	434.1	409.7	385.3	370.2
55°	521.7	504.0	486.3	468.6	450.9	429.8	405.3	380.8	356.3	331.8	318.2
57.5°	471.2	453.1	434.9	416.8	398.6	377.8	354.2	330.7	307.1	283.6	271.1
60°	436.9	418.8	400.6	382.5	364.3	343.6	320.2	296.8	273.5	250.1	238.5
62.5°	403.4	385.3	367.1	349.0	330.8	310.6	288.4	266.1	243.8	221.5	210.5
65°	352.2	333.8	315.4	297.1	278.7	259.3	238.9	218.5	198.0	177.6	169.9
67.5°	302.8	284.5	266.3	248.1	229.8	211.5	193.1	174.8	156.4	138.0	134.5
70°	268.5	250.8	233.1	215.4	197.7	181.0	165.4	149.7	134.1	118.4	116.1
72.5°	235.8	218.8	201.9	184.9	167.9	153.2	140.6	128.0	115.5	102.9	101.0
75°	187.8	172.0	156.1	140.2	124.3	112.5	104.8	97.1	89.4	81.7	80.1
77.5°	140.7	126.7	112.8	98.9	85.0	76.1	72.4	68.7	65.0	61.3	60.3
80°	111.3	99.7	88.1	76.6	65.0	58.1	55.8	53.5	51.3	49.0	48.1
82.5°	84.3	75.3	66.3	57.2	48.2	42.9	41.4	39.8	38.3	36.8	36.2
85°	43.9	39.1	34.4	29.6	24.8	22.1	21.4	20.8	20.1	19.4	19.4
87.5°	13.2	12.2	11.4	10.3	9.1	8.9	9.7	10.8	11.7	11.8	11.5
90°	0.8	3.1	6.3	7.8	9.4	11.7	15.6	21.1	25.8	26.6	25.8
92.5°	9.5	13.8	19.4	22.8	28.1	35.5	53.2	78.0	100.2	101.6	85.8
95°	27.4	30.5	38.3	45.3	57.8	76.6	112.6	180.6	271.3	306.4	268.1
97.5°	44.6	48.8	57.1	67.7	82.1	103.3	148.5	243.3	394.0	523.1	548.8
100°	60.2	62.5	69.6	82.1	97.7	119.6	161.0	256.4	425.2	617.5	730.1
102.5°	74.6	76.3	83.3	95.8	112.1	134.0	172.3	257.0	413.4	620.7	797.6
105°	95.4	98.5	104.0	115.7	132.9	154.8	191.5	261.1	390.1	579.2	787.2
107.5°	117.9	120.4	125.7	136.5	153.5	175.6	211.2	271.9	378.5	534.8	718.5
110°	132.9	136.0	140.7	150.9	167.3	190.0	224.3	280.6	376.0	513.6	675.4



TEST NUMBER: P331692

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	146.6	149.8	155.1	164.6	180.4	203.7	236.9	290.0	376.6	499.8	645.4
115°	168.1	172.0	176.7	186.0	201.7	222.8	256.4	304.1	379.9	484.7	608.2
117.5°	190.3	193.4	198.1	206.4	221.4	243.3	274.4	319.1	385.5	477.3	584.7
120°	204.0	207.2	211.8	218.9	234.5	256.4	286.9	329.1	389.3	472.9	572.2
122.5°	217.2	219.7	224.3	232.0	247.6	270.2	298.8	337.9	393.7	470.4	561.6
125°	234.5	236.9	241.5	250.9	266.6	288.4	316.6	351.8	400.2	465.9	546.4
127.5°	248.3	251.4	258.0	268.3	283.3	305.8	333.2	364.7	407.0	463.2	532.3
130°	256.4	259.5	267.3	278.3	293.9	315.8	343.2	372.9	412.0	462.0	523.0
132.5°	263.9	267.7	276.1	287.7	303.9	325.8	351.9	381.0	417.0	461.4	515.5
135°	275.2	278.3	287.7	299.4	317.4	339.3	364.3	391.6	422.9	460.4	505.0
137.5°	285.8	289.5	298.9	311.4	329.3	349.6	374.3	399.8	428.2	460.3	497.6
140°	293.9	297.0	306.4	318.9	336.1	356.5	379.9	404.1	430.7	459.6	493.3
142.5°	302.0	304.6	313.3	325.8	342.4	361.5	384.3	407.9	432.6	459.6	488.9
145°	314.2	317.4	325.2	336.9	352.5	369.7	390.9	412.7	434.6	458.1	483.1
147.5°	327.4	329.7	337.2	348.0	361.0	376.3	396.2	415.4	435.3	455.3	477.2
150°	336.1	338.5	344.7	354.9	366.6	380.7	398.7	416.6	434.6	453.4	472.1
152.5°	344.9	346.0	352.2	361.1	372.2	385.1	401.2	417.3	433.4	450.3	467.8
155°	357.2	358.0	362.7	371.3	379.9	391.6	404.9	418.2	431.5	444.8	459.6
157.5°	367.6	368.3	372.1	379.6	386.5	396.3	407.6	418.2	427.9	439.2	452.0
160°	374.4	375.2	378.3	384.6	390.9	399.4	408.8	418.2	426.0	435.4	446.4
162.5°	381.3	380.8	384.0	389.0	394.6	401.3	409.5	417.6	424.2	432.3	441.3
165°	389.3	388.5	390.1	394.8	398.7	403.4	410.4	415.9	420.6	426.0	433.1
167.5°	395.9	394.9	396.3	399.3	402.1	405.1	410.2	414.8	417.0	420.6	424.9
170°	400.2	398.7	399.4	401.8	403.4	405.7	409.6	413.5	415.1	417.4	420.6
172.5°	402.7	401.8	401.3	403.7	404.6	406.3	409.0	411.6	412.6	413.7	416.2
175°	405.7	404.9	404.1	405.7	405.7	406.5	408.0	409.6	408.8	409.6	410.4
177.5°	407.1	405.9	405.2	406.5	406.5	406.5	407.1	408.4	407.1	406.5	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5



TEST NUMBER: P331692

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0	1128.0
2.5°	1122.7	1124.5	1126.3	1127.0	1126.7	1126.3	1126.0	1125.6
5°	1113.7	1115.8	1117.8	1118.5	1117.8	1117.1	1116.5	1115.8
7.5°	1095.7	1096.3	1096.9	1096.6	1095.4	1094.3	1093.1	1091.9
10°	1077.7	1077.0	1076.3	1075.3	1073.9	1072.6	1071.2	1069.8
12.5°	1057.0	1055.8	1054.5	1052.8	1050.5	1048.3	1046.0	1043.7
15°	1018.4	1014.0	1009.7	1006.4	1004.2	1001.9	999.6	997.4
17.5°	974.7	969.5	964.4	959.9	956.0	952.1	948.2	944.3
20°	944.2	938.5	932.8	927.5	922.5	917.5	912.5	907.5
22.5°	910.7	903.4	896.1	890.6	886.8	883.1	879.4	875.7
25°	855.2	845.9	836.6	830.3	826.9	823.5	820.1	816.7
27.5°	802.3	791.5	780.7	772.5	767.1	761.7	756.3	750.9
30°	765.0	753.4	741.8	733.0	726.8	720.7	714.6	708.5
32.5°	727.4	714.2	701.0	691.5	685.7	680.0	674.2	668.5
35°	668.7	654.4	640.1	630.4	625.4	620.4	615.5	610.5
37.5°	611.4	595.7	580.0	569.2	563.5	557.8	552.1	546.4
40°	573.1	557.0	540.9	529.9	524.0	518.1	512.2	506.3
42.5°	534.5	517.8	501.2	490.0	484.3	478.6	472.9	467.1
45°	478.2	462.1	446.0	435.2	429.8	424.3	418.9	413.4
47.5°	423.5	407.5	391.4	381.0	376.0	371.1	366.1	361.2
50°	388.3	372.6	357.0	346.7	342.0	337.2	332.5	327.7
52.5°	355.1	339.9	324.8	315.1	310.7	306.3	301.9	297.5
55°	304.6	290.9	277.3	268.4	264.1	259.7	255.4	251.1
57.5°	258.6	246.2	233.7	225.6	222.0	218.4	214.7	211.1
60°	227.0	215.4	203.8	196.2	192.6	189.0	185.3	181.7
62.5°	199.5	188.4	177.4	170.8	168.6	166.5	164.3	162.1
65°	162.2	154.5	146.8	142.6	141.9	141.2	140.5	139.9
67.5°	130.9	127.4	123.9	121.7	121.0	120.3	119.6	118.8
70°	113.9	111.6	109.3	107.8	106.8	105.9	105.0	104.1
72.5°	99.1	97.2	95.3	94.1	93.5	93.0	92.4	91.9
75°	78.5	76.9	75.3	74.4	74.2	74.0	73.7	73.5
77.5°	59.4	58.5	57.6	57.0	56.6	56.3	55.9	55.5
80°	47.2	46.3	45.4	44.9	44.9	44.9	44.9	44.9
82.5°	35.7	35.1	34.6	34.3	34.3	34.3	34.3	34.3
85°	19.4	19.4	19.4	19.4	19.4	19.4	19.4	19.4
87.5°	11.2	10.7	10.8	10.9	10.9	10.9	10.9	10.9
90°	25.0	23.5	25.0	25.8	25.8	25.8	25.8	25.8
92.5°	68.2	58.5	51.9	47.1	46.4	43.9	44.6	43.3
95°	204.8	157.1	124.3	107.1	96.9	90.7	88.3	89.1
97.5°	477.9	391.0	306.4	250.0	212.6	193.4	182.0	175.4
100°	713.7	616.8	509.7	415.1	350.2	316.6	293.9	279.8
102.5°	868.2	846.3	767.9	667.7	597.2	539.8	511.5	492.5
105°	949.8	1038.1	1048.3	1022.5	974.0	925.5	891.9	881.0
107.5°	891.0	1024.0	1105.3	1143.2	1149.3	1146.6	1139.9	1125.3
110°	840.3	980.3	1080.3	1144.4	1178.0	1192.9	1199.9	1199.1





TEST NUMBER: P331692

CATALOG NUMBER: SA2XXRDIP-C675D725U835-4F0-1E-UDD-F4

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	794.1	928.3	1035.3	1108.8	1155.5	1180.4	1193.7	1197.9
115°	737.1	857.5	959.9	1040.4	1095.9	1131.9	1152.2	1159.3
117.5°	694.3	800.0	892.9	968.4	1025.0	1063.0	1084.4	1090.3
120°	673.0	770.0	852.8	924.0	978.7	1015.4	1038.1	1045.9
122.5°	656.2	745.0	823.4	887.7	936.8	972.9	993.1	999.6
125°	631.6	712.1	780.9	839.5	884.9	914.6	934.1	940.4
127.5°	607.4	680.2	745.1	799.2	838.8	866.6	883.5	888.5
130°	591.7	659.0	720.7	772.3	810.6	837.2	852.8	859.1
132.5°	576.7	639.0	695.7	744.2	781.9	808.4	822.8	828.4
135°	555.8	607.4	659.0	702.7	736.4	762.2	776.2	779.4
137.5°	539.1	582.2	623.2	661.3	692.0	714.2	726.5	731.2
140°	528.4	566.0	601.9	636.3	661.3	681.6	693.4	698.1
142.5°	519.7	551.6	582.5	611.3	635.1	653.5	664.0	664.9
145°	507.3	533.1	557.4	580.0	598.8	612.1	619.9	622.2
147.5°	497.8	518.1	537.0	553.6	569.1	579.7	585.0	586.4
150°	490.9	508.1	524.5	538.6	550.3	559.7	564.4	565.2
152.5°	484.0	500.0	513.9	526.1	535.3	543.4	546.9	547.0
155°	474.5	487.0	498.7	507.3	515.9	521.4	524.5	523.0
157.5°	463.4	473.9	483.7	490.4	496.5	501.1	502.5	502.5
160°	456.5	465.1	473.7	479.2	484.7	488.6	489.3	489.3
162.5°	449.6	457.0	464.3	468.6	474.0	476.7	477.5	476.8
165°	439.3	444.8	450.3	453.4	456.5	459.6	459.6	458.9
167.5°	429.5	433.7	437.4	440.3	441.7	443.4	443.2	442.3
170°	424.5	426.8	429.9	431.5	432.3	434.6	433.8	432.3
172.5°	418.8	420.6	423.1	424.0	424.8	425.9	425.1	424.2
175°	412.7	413.5	414.3	415.1	415.1	415.9	415.1	413.5
177.5°	408.4	408.4	409.0	409.0	409.0	409.0	408.4	407.1
180°	406.5	406.5	406.5	406.5	406.5	406.5	406.5	406.5

(END OF REPORT)