

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331355-830

Luminaire Tested: **SA2XXDIP-C675D725U830-4F0-1E-UDD-F1**

Issue Date: 10/7/2019

Test Information

Test Method: LM-79-08
Report Number: P331355-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 10/7/2019
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: SA2XXDIP-C675D725U830-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 725 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4990.5 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 45.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331355-830
CATALOG NUMBER: SA2XXDIP-C675D725U830-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331355-830

CATALOG NUMBER: SA2XXDIP-C675D725U830-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	84	84	84	70	70	70	57	57	57	51				
1	98	94	90	86	90	87	83	80	74	71	69	62	60	58	50	49	48	43				
2	89	82	76	70	82	76	70	66	64	60	57	54	51	49	44	42	41	36				
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	39	37	35	31				
4	74	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30	26				
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26	23				
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	25	23	20				
7	58	46	38	32	54	43	36	31	37	31	27	31	27	24	26	23	20	18				
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18	16				
9	50	38	31	26	46	36	29	24	31	25	22	26	22	19	22	19	16	14				
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	21	17	15	13				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16157	16157	16157
5°	16219	15985	16078
10°	16123	15823	15901
15°	15921	15616	15600
20°	15639	15309	15292
25°	15358	14931	14931
30°	14997	14585	14458
35°	14661	14168	13957
40°	14235	13748	13487
45°	13819	13337	13006
50°	13366	12906	12446
55°	12892	12405	11944
60°	12368	11806	11370
65°	11801	11213	10697
70°	11084	10494	9994
75°	10081	9669	9426
80°	8945	8675	8229
85°	7317	6947	6224



TEST NUMBER: P331355-830

CATALOG NUMBER: SA2XXDIP-C675D725U830-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	1.9
10°-20°	264.8	5.3
20°-30°	389.2	7.8
30°-40°	452.1	9.1
40°-50°	451.6	9.0
50°-60°	393.8	7.9
60°-70°	291.2	5.8
70°-80°	164.9	3.3
80°-90°	47.8	1.0
90°-100°	55.3	1.1
100°-110°	171.8	3.4
110°-120°	293.7	5.9
120°-130°	386.2	7.7
130°-140°	433.5	8.7
140°-150°	425.0	8.5
150°-160°	356.5	7.1
160°-170°	236.5	4.7
170°-180°	82.6	1.7
0°-30°	748.0	15.0
0°-40°	1200.1	24.0
0°-60°	2045.4	41.0
0°-90°	2549.4	51.1
90°-120°	520.8	10.4
90°-150°	1765.5	35.4
90°-180°	2441.0	48.9
0°-180°	4990.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	1001	996	986	993	992	95
15°	952	946	934	938	933	268
25°	862	854	838	840	838	396
35°	744	734	719	713	708	464
45°	605	598	584	574	570	467
55°	458	452	441	430	424	409
65°	309	303	294	285	280	305
75°	162	160	155	150	151	173
85°	40	38	38	35	34	45
90°	1	10	26	24	25	4
95°	38	45	47	47	46	44
105°	158	161	162	163	164	167
115°	295	299	298	297	295	291
125°	429	435	433	431	430	383
135°	555	562	564	564	561	428
145°	673	678	683	683	681	421
155°	770	772	774	778	776	354
165°	838	837	837	842	838	236
175°	872	869	868	872	869	83
180°	873	873	873	873	873	



TEST NUMBER: P331355-830

CATALOG NUMBER: SA2XXDIP-C675D725U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	1005.3	1004.5	1003.6	1002.8	1001.9	1000.5	998.6	996.7	994.9	993.0	994.7
5°	1000.7	999.8	999.0	998.2	997.3	995.7	993.3	991.0	988.6	986.3	988.0
7.5°	991.8	990.5	989.2	987.9	986.6	984.7	982.3	979.9	977.5	975.1	976.8
10°	983.4	981.8	980.3	978.8	977.4	975.3	972.8	970.3	967.6	965.1	966.8
12.5°	971.9	970.5	969.1	967.8	966.5	964.6	962.0	959.4	956.9	954.3	955.5
15°	952.5	951.3	950.0	948.8	947.4	945.4	942.6	939.8	937.1	934.2	935.2
17.5°	927.9	926.6	925.4	924.1	922.8	920.8	917.9	915.1	912.3	909.5	910.5
20°	910.2	909.0	907.7	906.3	905.1	903.0	899.9	897.0	894.0	891.0	891.6
22.5°	892.5	890.7	888.9	887.1	885.3	883.1	880.2	877.4	874.6	871.8	871.9
25°	862.1	860.4	858.8	857.0	855.3	852.6	848.9	845.4	841.7	838.1	838.5
27.5°	827.5	826.0	824.4	822.8	821.3	819.2	816.2	813.4	810.5	807.7	807.0
30°	804.4	802.7	801.0	799.3	797.6	795.1	791.9	788.7	785.5	782.3	781.7
32.5°	779.8	778.4	777.0	775.6	774.3	771.9	768.5	765.2	761.8	758.4	757.2
35°	743.8	741.7	739.5	737.4	735.2	732.4	729.1	725.6	722.2	718.8	717.5
37.5°	703.1	701.3	699.4	697.5	695.7	693.0	689.6	686.2	682.8	679.3	677.7
40°	675.4	673.7	672.0	670.3	668.6	666.1	662.6	659.2	655.8	652.3	650.4
42.5°	648.6	646.8	645.1	643.4	641.7	639.1	635.7	632.3	628.9	625.5	623.3
45°	605.2	603.7	602.2	600.8	599.3	596.9	593.7	590.5	587.3	584.1	581.7
47.5°	562.1	560.7	559.3	557.9	556.5	554.1	550.7	547.4	544.1	540.7	538.3
50°	532.1	531.0	530.0	528.9	527.8	525.8	522.8	519.8	516.8	513.8	510.9
52.5°	502.8	501.4	500.0	498.6	497.2	495.1	492.3	489.5	486.6	483.8	481.4
55°	458.0	456.8	455.4	454.1	452.9	450.9	448.4	445.8	443.3	440.7	438.1
57.5°	412.9	412.0	410.9	409.9	408.9	407.0	404.2	401.3	398.5	395.7	393.1
60°	383.0	382.1	381.3	380.4	379.6	377.6	374.7	371.6	368.6	365.6	363.3
62.5°	353.7	352.3	351.0	349.6	348.3	346.4	344.1	341.8	339.5	337.1	335.0
65°	308.9	307.6	306.3	305.0	303.7	302.0	299.9	297.7	295.6	293.5	291.5
67.5°	263.3	262.2	261.2	260.1	259.1	257.7	255.7	253.8	251.9	250.0	248.5
70°	234.8	233.9	233.1	232.2	231.4	230.0	228.0	226.1	224.2	222.3	220.7
72.5°	205.6	204.6	203.8	202.9	202.1	201.0	199.8	198.6	197.4	196.0	194.6
75°	161.6	161.2	160.8	160.3	159.9	159.2	158.2	157.0	156.0	155.0	153.6
77.5°	122.4	121.7	120.9	120.2	119.5	118.9	118.5	118.0	117.6	117.2	116.6
80°	96.2	96.0	95.8	95.6	95.4	95.0	94.6	94.2	93.8	93.3	92.7
82.5°	71.6	71.5	71.5	71.4	71.4	71.3	71.0	70.8	70.5	70.2	69.5
85°	39.5	39.2	39.0	38.8	38.5	38.4	38.2	38.0	37.7	37.5	36.9
87.5°	14.0	14.0	14.1	14.1	14.2	14.4	14.8	15.2	15.6	15.9	15.4
90°	0.8	2.7	4.7	6.6	8.6	11.4	15.0	18.6	22.1	25.8	25.4
92.5°	13.1	14.5	16.0	17.4	18.9	20.0	20.8	21.7	22.6	23.5	23.5
95°	38.3	40.0	41.6	43.3	44.9	45.8	46.2	46.5	46.8	47.1	47.1
97.5°	70.0	71.4	72.9	74.3	75.8	76.8	77.4	78.0	78.6	79.3	79.3
100°	93.6	94.9	96.1	97.5	98.8	99.7	100.2	100.7	101.1	101.7	101.7
102.5°	118.3	119.3	120.5	121.5	122.5	123.4	123.9	124.6	125.2	125.8	125.9
105°	158.4	158.9	159.4	159.9	160.3	160.8	161.1	161.5	161.7	162.1	162.4
107.5°	198.8	199.5	200.2	201.0	201.6	202.0	202.0	202.0	202.0	202.0	202.2
110°	224.7	225.6	226.7	227.6	228.7	229.1	229.1	229.1	229.1	229.1	229.1



TEST NUMBER: P331355-830

CATALOG NUMBER: SA2XXDIP-C675D725U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	253.0	254.0	255.0	255.9	256.9	257.3	257.2	257.1	256.9	256.8	256.5
115°	294.7	295.7	296.6	297.7	298.6	299.0	298.6	298.3	297.9	297.7	297.5
117.5°	336.2	337.5	338.8	340.2	341.5	341.7	340.7	339.9	338.9	338.0	337.6
120°	363.9	365.2	366.6	367.9	369.2	369.2	367.9	366.6	365.2	363.9	363.9
122.5°	389.3	390.9	392.5	394.0	395.6	395.9	395.0	394.1	393.1	392.2	391.8
125°	428.8	430.3	431.7	433.2	434.7	435.2	434.7	434.1	433.7	433.2	432.7
127.5°	467.2	469.1	471.0	472.9	474.7	475.3	474.8	474.2	473.5	473.0	472.4
130°	491.4	493.5	495.7	497.8	499.9	500.8	500.5	500.1	499.8	499.5	499.2
132.5°	518.5	520.3	522.0	523.7	525.5	526.3	526.4	526.5	526.5	526.6	525.9
135°	554.8	556.6	558.4	560.2	561.9	563.0	563.4	563.6	564.0	564.3	564.2
137.5°	593.0	594.4	595.9	597.4	598.8	599.7	600.2	600.6	601.1	601.4	601.3
140°	616.0	617.4	618.9	620.3	621.8	622.9	623.8	624.6	625.4	626.2	626.2
142.5°	639.5	640.9	642.4	643.9	645.4	646.4	647.0	647.5	648.1	648.7	648.8
145°	673.4	674.5	675.7	676.8	678.0	679.0	680.0	681.0	681.9	683.0	683.2
147.5°	703.6	704.9	706.3	707.7	709.1	710.1	710.8	711.4	712.1	712.8	713.0
150°	724.2	725.2	726.1	727.2	728.1	729.0	729.6	730.3	730.9	731.6	732.1
152.5°	742.4	743.5	744.4	745.5	746.4	747.2	748.1	748.9	749.6	750.5	751.0
155°	769.9	770.3	770.9	771.4	771.8	772.3	772.8	773.4	773.8	774.3	775.1
157.5°	793.3	793.6	794.0	794.3	794.7	794.9	795.2	795.5	795.8	796.1	797.2
160°	807.5	807.8	808.1	808.4	808.8	809.0	809.2	809.4	809.5	809.6	810.7
162.5°	820.4	820.5	820.6	820.6	820.7	820.8	821.0	821.1	821.3	821.4	822.6
165°	837.6	837.5	837.4	837.2	837.0	836.9	836.9	836.9	836.9	836.9	838.1
167.5°	852.1	851.6	851.1	850.6	850.2	849.9	849.9	849.8	849.8	849.7	850.9
170°	859.8	859.3	858.8	858.3	857.8	857.4	857.3	857.1	857.0	856.8	858.0
172.5°	865.1	864.6	864.1	863.6	863.1	862.8	862.6	862.4	862.3	862.1	863.3
175°	871.6	871.1	870.5	870.1	869.6	869.2	868.8	868.6	868.2	867.9	869.0
177.5°	874.2	873.8	873.5	873.0	872.6	872.3	872.0	871.8	871.5	871.3	872.0
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0



TEST NUMBER: P331355-830

CATALOG NUMBER: SA2XXDIP-C675D725U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7	1000.7
2.5°	996.4	998.2	999.8	1000.5	1000.1	999.8	999.5	999.2
5°	989.7	991.4	993.1	993.7	993.3	992.9	992.5	992.0
7.5°	978.5	980.2	981.9	982.5	982.0	981.7	981.2	980.7
10°	968.5	970.3	971.9	972.4	971.9	971.2	970.5	969.9
12.5°	956.7	957.9	959.1	959.4	958.9	958.6	958.1	957.6
15°	936.0	936.9	937.7	937.6	936.5	935.5	934.4	933.3
17.5°	911.4	912.4	913.4	913.4	912.4	911.3	910.3	909.3
20°	892.3	893.0	893.5	893.4	892.6	891.7	890.9	890.0
22.5°	872.0	872.1	872.2	872.0	871.6	871.0	870.5	870.1
25°	839.0	839.3	839.8	839.8	839.3	839.0	838.5	838.1
27.5°	806.3	805.8	805.1	804.3	803.2	802.2	801.2	800.1
30°	781.0	780.3	779.7	778.9	778.1	777.2	776.4	775.5
32.5°	756.1	755.0	753.8	752.8	752.0	751.1	750.2	749.3
35°	716.2	714.9	713.6	712.5	711.4	710.3	709.3	708.1
37.5°	676.2	674.6	673.0	671.7	670.6	669.6	668.6	667.6
40°	648.6	646.6	644.7	643.3	642.4	641.6	640.7	639.9
42.5°	621.2	619.2	617.1	615.4	614.2	613.0	611.8	610.6
45°	579.4	577.0	574.7	573.1	572.2	571.4	570.5	569.6
47.5°	535.8	533.3	530.8	529.0	527.7	526.5	525.3	524.1
50°	507.8	504.8	501.8	499.8	498.7	497.7	496.6	495.5
52.5°	478.8	476.4	473.9	471.9	470.5	469.1	467.7	466.3
55°	435.5	433.0	430.5	428.6	427.5	426.5	425.4	424.3
57.5°	390.6	388.0	385.6	383.9	383.0	382.3	381.4	380.6
60°	360.9	358.5	356.2	354.8	354.1	353.5	352.8	352.1
62.5°	332.8	330.6	328.5	327.0	326.1	325.3	324.5	323.7
65°	289.6	287.7	285.8	284.3	283.2	282.1	281.1	280.0
67.5°	246.9	245.5	244.0	242.8	242.0	241.1	240.3	239.4
70°	219.2	217.8	216.3	215.1	214.2	213.4	212.5	211.7
72.5°	193.1	191.6	190.1	189.0	188.3	187.7	187.0	186.2
75°	152.3	151.1	149.8	149.4	149.8	150.2	150.6	151.1
77.5°	115.9	115.3	114.6	114.0	113.4	112.8	112.3	111.6
80°	92.1	91.4	90.8	90.2	89.8	89.4	89.0	88.5
82.5°	68.6	67.8	67.0	66.5	66.4	66.4	66.3	66.2
85°	36.3	35.6	35.0	34.5	34.3	34.1	33.9	33.6
87.5°	14.8	14.2	13.6	13.3	13.1	13.0	12.8	12.7
90°	25.2	24.8	24.5	24.4	24.6	24.7	24.9	25.1
92.5°	23.6	23.7	23.7	23.8	23.8	23.8	23.8	23.8
95°	47.1	47.1	47.1	47.0	46.7	46.4	46.0	45.7
97.5°	79.3	79.3	79.3	79.3	79.3	79.2	79.2	79.1
100°	101.7	101.7	101.7	101.6	101.4	101.2	101.1	100.9
102.5°	126.1	126.2	126.4	126.3	126.2	126.0	125.8	125.6
105°	162.8	163.1	163.4	163.5	163.5	163.5	163.5	163.5
107.5°	202.3	202.4	202.6	202.3	201.5	200.8	200.0	199.3
110°	229.1	229.1	229.1	228.8	228.4	227.9	227.4	226.9



TEST NUMBER: P331355-830

CATALOG NUMBER: SA2XXDIP-C675D725U830-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	256.0	255.6	255.2	254.9	254.5	254.1	253.8	253.4
115°	297.3	297.2	297.0	296.6	296.1	295.7	295.2	294.7
117.5°	337.2	336.9	336.4	336.0	335.5	335.0	334.5	334.0
120°	363.9	363.9	363.9	363.7	363.2	362.7	362.2	361.7
122.5°	391.4	391.1	390.7	390.3	389.9	389.6	389.2	388.9
125°	432.3	431.7	431.2	430.9	430.7	430.6	430.5	430.3
127.5°	471.8	471.2	470.6	470.0	469.6	469.0	468.5	468.0
130°	498.9	498.5	498.2	497.7	497.0	496.4	495.8	495.1
132.5°	525.2	524.4	523.8	523.1	522.5	522.1	521.5	521.0
135°	564.0	563.8	563.6	563.4	562.9	562.4	561.8	561.4
137.5°	601.2	601.1	601.0	600.6	599.9	599.3	598.6	597.9
140°	626.2	626.2	626.2	625.8	625.3	624.6	624.0	623.3
142.5°	648.8	649.0	649.1	648.8	648.2	647.5	647.0	646.3
145°	683.2	683.4	683.6	683.3	682.7	682.0	681.4	680.7
147.5°	713.4	713.8	714.2	714.1	713.4	712.8	712.2	711.5
150°	732.5	733.0	733.6	733.6	733.0	732.5	732.1	731.6
152.5°	751.7	752.3	752.9	752.9	752.3	751.7	751.0	750.5
155°	775.9	776.7	777.6	777.8	777.2	776.7	776.3	775.8
157.5°	798.3	799.5	800.6	800.7	799.9	799.2	798.3	797.6
160°	811.6	812.7	813.6	813.8	813.1	812.5	811.8	811.2
162.5°	823.7	824.8	826.0	826.0	825.3	824.5	823.7	822.9
165°	839.2	840.4	841.5	841.7	840.8	840.0	839.2	838.4
167.5°	852.1	853.2	854.3	854.5	853.7	852.8	852.0	851.1
170°	859.1	860.3	861.4	861.5	860.5	859.5	858.6	857.5
172.5°	864.4	865.5	866.7	866.8	865.8	864.8	863.8	862.9
175°	870.2	871.3	872.4	872.5	871.6	870.5	869.6	868.6
177.5°	872.8	873.6	874.4	874.4	873.6	872.8	872.0	871.3
180°	873.0	873.0	873.0	873.0	873.0	873.0	873.0	873.0

(END OF REPORT)