

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331694

Luminaire Tested: **SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1**

Issue Date: 10/7/2019

**Test Information**

Test Method: LM-79-08  
Report Number: P331694  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 10/7/2019  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT PENDANT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 925 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5850.3 lumens  
Efficiency: N/A  
Efficacy: 112.5 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 52  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331694  
CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	82	73	66	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42	42	38	35	33	31	29	25
5	69	58	50	45	63	54	47	42	45	40	37	38	34	31	30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20
7	59	48	40	35	54	44	37	33	38	33	29	32	28	25	26	23	21	18
8	55	43	36	31	51	40	34	29	35	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	23720	23720	23720	23720
5°	26491	23869	21162	23869
10°	29391	23700	18344	23700
15°	30837	23353	14454	23353
20°	26734	22838	12507	22838
25°	17533	22133	11166	22133
30°	11801	21280	10107	21280
35°	9558	20203	9116	20203
40°	8500	19032	8435	19032
45°	7693	17657	7531	17657
50°	7001	16297	6975	16297
55°	6581	14787	6494	14787
60°	5506	13401	5438	13401
65°	4642	12168	5265	12168
70°	4291	10867	4966	10867
75°	4011	9457	4585	9457
80°	3701	7782	4082	7782
85°	3409	6150	3594	6150



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.3	2.4
10°-20°	388.0	6.6
20°-30°	500.0	8.5
30°-40°	475.2	8.1
40°-50°	407.1	7.0
50°-60°	310.0	5.3
60°-70°	196.0	3.3
70°-80°	97.9	1.7
80°-90°	30.2	0.5
90°-100°	74.9	1.3
100°-110°	232.7	4.0
110°-120°	397.8	6.8
120°-130°	523.2	8.9
130°-140°	587.2	10.0
140°-150°	575.7	9.8
150°-160°	482.9	8.3
160°-170°	320.3	5.5
170°-180°	111.9	1.9
0°-30°	1027.3	17.6
0°-40°	1502.5	25.7
0°-60°	2219.6	37.9
0°-90°	2543.6	43.5
90°-120°	705.5	12.1
90°-150°	2391.6	40.9
90°-180°	3307.0	56.5
0°-180°	5850.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1469	1469	1469	1469	1469	
5°	1634	1473	1306	1473	1634	161
15°	1845	1397	865	1397	1845	498
25°	984	1242	627	1242	984	467
35°	485	1025	462	1025	485	310
45°	337	773	330	773	337	261
55°	234	525	231	525	234	205
65°	122	318	138	318	122	124
75°	64	152	74	152	64	68
85°	18	33	19	33	18	21
90°	34	1	34	1	34	16
95°	62	52	62	52	62	69
105°	222	215	222	215	222	233
115°	399	399	399	399	399	394
125°	583	581	583	581	583	520
135°	760	752	760	752	760	585
145°	922	912	922	912	922	576
155°	1051	1043	1051	1043	1051	484
165°	1136	1135	1136	1135	1136	320
175°	1177	1181	1177	1181	1177	112
180°	1183	1183	1183	1183	1183	



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1528.7	1529.9	1531.2	1528.3	1528.3	1525.8	1520.5	1516.5	1505.0	1503.4	1503.4
5°	1634.5	1633.4	1635.5	1628.9	1619.7	1617.6	1607.9	1595.2	1581.9	1567.1	1564.0
7.5°	1739.6	1738.1	1734.0	1732.9	1725.8	1710.4	1694.8	1678.2	1656.1	1634.6	1623.8
10°	1792.7	1809.6	1799.3	1781.5	1785.1	1761.1	1748.3	1726.4	1708.0	1675.8	1668.7
12.5°	1845.0	1851.6	1848.4	1838.2	1833.6	1817.0	1799.8	1780.7	1746.8	1717.9	1692.8
15°	1844.8	1854.5	1857.0	1854.0	1856.5	1855.5	1846.3	1830.5	1800.9	1769.2	1741.7
17.5°	1708.6	1715.3	1732.1	1743.4	1757.7	1787.9	1802.8	1808.6	1804.2	1786.2	1766.8
20°	1555.9	1544.6	1591.6	1615.6	1636.0	1687.0	1730.9	1747.8	1774.8	1774.3	1769.2
22.5°	1339.4	1342.1	1386.6	1415.1	1474.7	1525.7	1575.8	1639.2	1691.5	1726.1	1746.4
25°	984.2	1003.6	1048.0	1086.8	1153.1	1248.1	1334.3	1434.4	1528.8	1603.3	1674.3
27.5°	739.1	740.6	775.8	811.6	851.0	928.8	1037.4	1156.9	1291.5	1402.6	1530.4
30°	633.0	629.9	644.7	666.7	700.3	760.6	842.2	959.7	1093.9	1261.3	1410.4
32.5°	557.8	558.0	569.2	585.4	613.4	654.0	709.9	805.3	932.2	1096.8	1271.5
35°	484.9	484.4	492.6	504.3	516.1	542.1	580.4	630.4	717.7	871.3	1050.0
37.5°	432.7	434.9	438.9	446.2	459.2	473.7	496.7	530.3	592.4	683.3	833.5
40°	403.3	404.3	409.9	416.0	423.7	434.9	453.8	480.8	526.3	598.8	708.5
42.5°	376.3	377.3	381.3	387.0	393.0	404.3	419.9	443.3	480.1	536.7	627.2
45°	336.9	336.9	340.5	343.0	349.7	359.9	372.6	392.0	417.6	459.4	519.6
47.5°	299.9	300.0	302.4	306.8	311.0	318.9	331.5	347.3	365.9	398.3	449.7
50°	278.7	279.2	280.7	284.3	286.9	294.0	303.7	317.5	336.9	361.9	404.8
52.5°	261.6	261.2	263.2	264.7	266.5	271.6	278.8	291.0	308.3	330.1	365.6
55°	233.8	231.7	234.8	237.4	238.9	240.9	245.0	252.7	267.5	285.9	312.4
57.5°	199.1	198.3	200.4	202.8	207.6	213.1	216.5	221.4	229.1	242.3	268.6
60°	170.5	170.5	175.1	176.6	182.2	189.4	196.5	200.6	208.3	216.9	236.3
62.5°	145.2	145.6	147.7	149.3	152.4	161.2	171.2	180.2	187.4	195.7	208.6
65°	121.5	122.5	122.5	123.5	125.6	127.6	131.7	138.8	151.6	163.3	173.0
67.5°	103.1	103.4	103.7	104.7	105.3	107.5	109.1	112.3	115.3	126.4	138.4
70°	90.9	92.4	91.9	92.9	93.4	94.4	96.5	98.0	102.6	105.2	112.3
72.5°	79.4	80.5	80.4	81.1	82.4	82.6	84.2	85.8	88.7	90.9	94.7
75°	64.3	63.8	64.3	65.3	65.8	66.4	66.4	68.4	69.9	72.0	74.5
77.5°	49.6	50.1	50.0	50.1	50.2	51.1	51.0	52.0	53.5	54.5	55.7
80°	39.8	40.3	39.8	40.3	40.8	41.3	40.8	41.3	42.9	43.9	43.9
82.5°	30.8	30.9	31.2	31.3	31.4	31.5	32.3	32.4	33.5	33.3	33.7
85°	18.4	17.9	17.9	17.9	18.4	18.9	18.4	18.4	18.9	18.9	18.9
87.5°	13.3	13.7	13.6	13.6	13.6	13.6	13.7	14.2	13.8	14.3	13.0
90°	33.9	33.7	33.5	33.3	33.0	33.2	33.6	34.0	34.5	34.9	30.0
92.5°	32.3	32.3	32.2	32.2	32.2	32.1	32.0	31.9	31.8	31.7	30.6
95°	61.9	62.3	62.8	63.2	63.6	63.9	63.9	63.9	63.9	63.9	63.4
97.5°	107.2	107.2	107.3	107.3	107.4	107.4	107.4	107.4	107.4	107.4	106.5
100°	136.7	136.9	137.2	137.4	137.6	137.7	137.7	137.7	137.7	137.7	137.1
102.5°	170.3	170.5	170.7	170.9	171.1	171.2	171.0	170.8	170.6	170.5	169.6
105°	221.5	221.5	221.5	221.5	221.5	221.3	220.9	220.4	220.0	219.5	219.1
107.5°	269.8	270.9	271.9	272.9	273.9	274.3	274.2	274.0	273.8	273.6	273.6
110°	307.4	308.0	308.7	309.4	310.0	310.4	310.4	310.4	310.4	310.4	310.4



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	343.3	343.8	344.3	344.8	345.2	345.8	346.3	346.8	347.4	347.9	348.1
115°	399.2	399.8	400.5	401.2	401.8	402.3	402.5	402.7	403.0	403.2	403.6
117.5°	452.5	453.1	453.8	454.5	455.1	455.7	456.3	456.8	457.3	457.9	459.1
120°	490.0	490.7	491.3	492.0	492.7	493.0	493.0	493.0	493.0	493.0	494.8
122.5°	526.7	527.2	527.7	528.2	528.7	529.2	529.7	530.2	530.8	531.3	532.6
125°	582.8	583.0	583.2	583.5	583.7	584.1	584.8	585.5	586.1	586.8	587.5
127.5°	633.9	634.6	635.3	636.0	636.7	637.5	638.3	639.1	639.9	640.7	641.5
130°	670.6	671.5	672.4	673.3	674.2	674.8	675.3	675.7	676.2	676.6	677.1
132.5°	705.8	706.5	707.2	707.9	708.6	709.4	710.4	711.4	712.4	713.3	713.2
135°	760.4	761.1	761.8	762.4	763.1	763.5	763.8	764.0	764.2	764.4	764.0
137.5°	809.9	810.8	811.7	812.6	813.5	814.0	814.2	814.4	814.6	814.7	814.2
140°	844.3	845.2	846.0	846.9	847.8	848.3	848.3	848.3	848.3	848.3	847.2
142.5°	875.4	876.3	877.2	878.1	879.0	879.3	879.1	879.0	878.8	878.6	877.8
145°	922.1	923.0	923.9	924.8	925.7	926.0	925.8	925.5	925.3	925.1	923.8
147.5°	963.8	964.7	965.5	966.4	967.2	967.4	966.9	966.4	965.9	965.4	964.5
150°	991.0	991.6	992.3	993.0	993.6	993.6	993.0	992.3	991.6	991.0	990.1
152.5°	1016.5	1017.4	1018.2	1019.0	1019.9	1019.9	1019.0	1018.2	1017.4	1016.5	1015.4
155°	1050.8	1051.5	1052.2	1052.8	1053.5	1053.3	1052.2	1051.1	1050.0	1048.8	1048.2
157.5°	1080.4	1081.4	1082.5	1083.6	1084.6	1084.4	1082.9	1081.4	1079.9	1078.4	1078.0
160°	1098.7	1099.6	1100.5	1101.4	1102.3	1102.1	1100.7	1099.4	1098.1	1096.7	1096.5
162.5°	1114.7	1115.8	1116.8	1117.9	1119.0	1118.7	1117.2	1115.7	1114.2	1112.7	1112.5
165°	1135.7	1136.8	1137.9	1139.0	1140.1	1139.9	1138.3	1136.8	1135.2	1133.7	1133.7
167.5°	1152.8	1154.0	1155.1	1156.3	1157.4	1157.2	1155.7	1154.1	1152.6	1151.0	1151.1
170°	1161.6	1162.9	1164.3	1165.6	1166.9	1166.8	1165.3	1163.7	1162.2	1160.6	1160.8
172.5°	1168.8	1170.1	1171.5	1172.8	1174.1	1174.0	1172.5	1170.9	1169.4	1167.8	1168.0
175°	1176.6	1177.9	1179.2	1180.6	1181.9	1181.8	1180.2	1178.7	1177.1	1175.6	1176.0
177.5°	1180.2	1181.2	1182.3	1183.4	1184.4	1184.4	1183.4	1182.3	1181.2	1180.2	1180.5
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1504.2	1500.9	1498.1	1490.7	1487.1	1478.9	1477.7	1477.3	1466.6	1456.4	1453.6
5°	1555.9	1547.7	1535.4	1521.1	1506.3	1491.0	1480.8	1472.7	1452.2	1432.8	1421.6
7.5°	1607.9	1590.4	1569.2	1542.2	1519.6	1494.3	1475.5	1458.7	1429.7	1401.9	1383.2
10°	1646.7	1618.1	1590.1	1552.8	1523.7	1495.1	1468.6	1445.6	1412.9	1376.2	1350.1
12.5°	1670.8	1639.4	1600.7	1564.2	1526.6	1490.2	1454.7	1425.2	1386.8	1348.8	1317.9
15°	1703.4	1669.7	1622.7	1570.7	1522.2	1474.7	1433.9	1397.1	1347.1	1301.7	1263.9
17.5°	1730.0	1683.7	1633.2	1573.0	1516.9	1456.5	1403.9	1357.0	1301.3	1246.5	1202.0
20°	1738.6	1692.7	1634.5	1574.2	1507.9	1436.9	1380.3	1329.2	1269.5	1209.8	1158.7
22.5°	1733.3	1697.6	1632.8	1560.8	1492.8	1418.5	1354.5	1295.3	1229.1	1168.1	1108.9
25°	1697.3	1685.0	1623.8	1545.1	1467.6	1381.3	1307.3	1242.4	1166.9	1101.6	1037.2
27.5°	1613.2	1639.7	1601.7	1518.0	1431.7	1339.2	1256.0	1182.2	1103.8	1030.3	966.2
30°	1532.4	1593.1	1576.8	1499.2	1402.7	1311.9	1218.5	1141.4	1057.7	982.1	918.8
32.5°	1421.7	1522.1	1538.0	1473.1	1373.3	1273.5	1175.6	1098.9	1011.5	931.9	870.2
35°	1245.5	1395.6	1464.5	1423.1	1323.1	1215.4	1114.3	1025.0	937.2	858.6	797.3
37.5°	1035.3	1239.7	1354.5	1357.5	1265.6	1153.6	1043.6	954.9	865.0	787.8	721.6
40°	898.9	1120.4	1270.0	1303.2	1225.6	1104.6	993.3	903.0	815.2	739.6	663.6
42.5°	776.4	997.1	1181.0	1238.7	1177.0	1056.8	945.2	850.7	765.4	693.9	616.2
45°	627.9	820.8	1023.5	1126.6	1092.4	981.1	863.2	773.3	693.2	631.4	556.9
47.5°	529.6	665.6	861.7	1001.2	1000.6	899.0	783.0	697.0	622.7	564.8	504.4
50°	473.7	592.1	758.0	916.3	929.5	844.3	734.0	648.8	579.4	518.6	470.1
52.5°	423.5	521.1	670.2	821.9	859.7	785.9	678.9	600.2	532.8	477.0	435.4
55°	357.8	433.4	546.7	688.6	745.8	693.7	598.8	525.3	470.6	423.7	387.9
57.5°	302.7	359.4	450.3	564.6	631.1	598.4	520.0	460.3	413.6	371.1	342.9
60°	268.0	314.4	391.5	487.0	560.5	537.5	470.6	415.0	375.2	338.4	311.9
62.5°	235.3	275.2	341.3	418.8	486.2	476.7	422.0	375.4	340.5	307.0	284.5
65°	189.4	218.5	270.0	330.8	384.9	389.5	350.2	318.5	287.4	260.8	240.9
67.5°	150.8	169.8	206.1	257.3	297.8	312.3	288.3	264.1	239.4	218.9	201.6
70°	127.1	142.4	169.0	210.3	247.6	262.9	249.1	230.2	208.8	191.9	177.1
72.5°	103.0	117.9	137.5	167.8	199.8	216.3	211.5	198.0	180.6	166.6	152.6
75°	77.6	82.2	95.5	115.9	140.9	155.2	158.8	151.6	137.8	127.1	118.9
77.5°	57.4	60.1	66.5	77.2	93.5	106.3	111.5	110.7	101.2	94.9	87.3
80°	45.9	47.5	50.5	55.1	67.4	80.1	83.7	83.7	77.1	74.5	66.9
82.5°	34.9	36.0	37.9	40.4	46.1	57.3	61.3	62.1	57.9	54.5	48.5
85°	19.9	19.4	20.4	21.9	23.0	26.0	32.2	33.2	32.2	28.1	26.5
87.5°	12.0	11.4	10.4	9.3	9.1	9.0	10.5	12.0	10.9	10.2	10.0
90°	25.2	20.3	15.4	11.6	9.0	6.3	3.7	1.0	3.7	6.3	9.0
92.5°	29.4	28.3	27.1	25.6	23.6	21.7	19.7	17.8	19.7	21.7	23.6
95°	63.0	62.5	62.1	60.8	58.5	56.3	54.1	51.9	54.1	56.3	58.5
97.5°	105.7	104.9	104.0	102.6	100.7	98.7	96.8	94.8	96.8	98.7	100.7
100°	136.4	135.7	135.1	133.8	132.1	130.3	128.5	126.7	128.5	130.3	132.1
102.5°	168.8	167.9	167.1	165.9	164.5	163.1	161.7	160.3	161.7	163.1	164.5
105°	218.7	218.2	217.8	217.2	216.6	215.9	215.2	214.6	215.2	215.9	216.6
107.5°	273.6	273.6	273.6	273.2	272.2	271.2	270.2	269.2	270.2	271.2	272.2
110°	310.4	310.4	310.4	309.7	308.4	307.0	305.7	304.4	305.7	307.0	308.4





TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	348.2	348.4	348.6	348.0	346.7	345.4	344.0	342.7	344.0	345.4	346.7
115°	404.1	404.5	404.9	404.5	403.2	401.8	400.5	399.2	400.5	401.8	403.2
117.5°	460.3	461.6	462.8	462.6	460.8	459.0	457.2	455.5	457.2	459.0	460.8
120°	496.5	498.3	500.1	500.1	498.3	496.5	494.8	493.0	494.8	496.5	498.3
122.5°	533.8	535.0	536.3	535.8	533.7	531.6	529.4	527.3	529.4	531.6	533.7
125°	588.1	588.8	589.5	588.8	586.8	584.8	582.8	580.8	582.8	584.8	586.8
127.5°	642.3	643.1	643.9	643.0	640.5	638.0	635.4	632.9	635.4	638.0	640.5
130°	677.5	677.9	678.4	677.2	674.3	671.4	668.5	665.6	668.5	671.4	674.3
132.5°	713.2	713.1	713.0	711.8	709.4	707.1	704.7	702.4	704.7	707.1	709.4
135°	763.5	763.1	762.7	761.2	758.8	756.3	753.9	751.5	753.9	756.3	758.8
137.5°	813.6	813.0	812.4	811.1	809.1	807.1	805.1	803.2	805.1	807.1	809.1
140°	846.0	844.9	843.8	842.3	840.3	838.3	836.3	834.3	836.3	838.3	840.3
142.5°	877.1	876.3	875.6	874.2	872.2	870.2	868.2	866.2	868.2	870.2	872.2
145°	922.4	921.1	919.8	918.3	916.8	915.2	913.7	912.1	913.7	915.2	916.8
147.5°	963.6	962.8	961.9	960.5	958.6	956.8	954.9	953.0	954.9	956.8	958.6
150°	989.2	988.3	987.4	986.3	985.0	983.6	982.3	981.0	982.3	983.6	985.0
152.5°	1014.4	1013.3	1012.3	1011.1	1009.7	1008.4	1007.1	1005.7	1007.1	1008.4	1009.7
155°	1047.5	1046.9	1046.2	1045.5	1044.9	1044.2	1043.5	1042.9	1043.5	1044.2	1044.9
157.5°	1077.6	1077.2	1076.8	1076.4	1075.9	1075.5	1075.0	1074.6	1075.0	1075.5	1075.9
160°	1096.3	1096.1	1095.9	1095.5	1095.1	1094.6	1094.2	1093.8	1094.2	1094.6	1095.1
162.5°	1112.3	1112.1	1111.8	1111.7	1111.6	1111.5	1111.4	1111.3	1111.4	1111.5	1111.6
165°	1133.7	1133.7	1133.7	1133.8	1134.0	1134.2	1134.5	1134.7	1134.5	1134.2	1134.0
167.5°	1151.1	1151.2	1151.2	1151.6	1152.2	1152.9	1153.6	1154.2	1153.6	1152.9	1152.2
170°	1161.1	1161.3	1161.5	1161.9	1162.6	1163.3	1163.9	1164.6	1163.9	1163.3	1162.6
172.5°	1168.2	1168.5	1168.7	1169.1	1169.8	1170.5	1171.1	1171.8	1171.1	1170.5	1169.8
175°	1176.5	1176.9	1177.4	1177.9	1178.6	1179.2	1179.9	1180.6	1179.9	1179.2	1178.6
177.5°	1180.9	1181.2	1181.6	1182.0	1182.6	1183.1	1183.6	1184.2	1183.6	1183.1	1182.6
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1448.3	1445.4	1440.1	1431.9	1427.0	1418.4	1412.7	1416.0	1416.8	1416.0	1415.2
5°	1409.4	1398.6	1383.8	1369.5	1356.3	1342.0	1333.8	1330.2	1323.1	1319.0	1317.0
7.5°	1362.3	1343.8	1322.9	1298.0	1276.8	1254.7	1243.4	1237.7	1223.1	1215.2	1208.2
10°	1327.2	1298.1	1277.2	1244.5	1224.6	1195.5	1175.6	1176.1	1156.2	1144.9	1136.8
12.5°	1288.4	1256.4	1221.6	1192.2	1164.5	1141.2	1117.2	1107.5	1086.3	1075.5	1053.5
15°	1224.1	1186.8	1150.1	1110.2	1082.2	1045.9	1011.2	968.8	934.6	905.0	896.9
17.5°	1153.8	1107.7	1070.8	1024.1	976.0	915.0	874.8	850.2	829.6	814.0	802.3
20°	1105.6	1058.7	1019.4	948.9	884.1	842.8	813.2	794.3	772.8	756.0	746.8
22.5°	1055.0	1006.0	952.4	873.8	823.3	790.1	763.7	742.0	727.5	714.3	706.0
25°	983.1	929.5	841.2	787.1	746.3	711.6	693.2	679.9	664.6	646.7	638.6
27.5°	907.2	821.9	758.5	718.3	679.3	656.7	640.2	620.4	606.7	598.7	590.2
30°	850.4	765.2	715.7	671.8	644.2	619.2	599.8	588.6	575.3	561.5	555.9
32.5°	787.1	719.0	671.6	635.0	607.0	585.7	570.4	552.2	542.6	534.1	522.4
35°	708.5	657.0	613.6	584.0	557.4	540.1	522.2	511.5	494.1	487.0	482.4
37.5°	641.9	597.2	564.9	533.6	512.6	493.4	482.5	465.4	457.9	448.0	438.3
40°	604.4	560.5	529.3	503.8	480.3	466.0	452.3	438.5	427.2	422.7	410.9
42.5°	566.0	530.3	499.1	471.1	455.4	440.3	422.9	412.8	401.1	393.7	386.4
45°	513.0	481.4	454.8	431.8	414.5	398.7	387.4	370.6	364.0	349.1	343.0
47.5°	466.5	437.0	411.7	389.9	372.9	362.6	346.2	333.0	322.4	313.3	305.5
50°	433.4	408.9	384.4	365.0	349.7	334.9	318.0	311.4	295.0	290.4	285.9
52.5°	403.2	379.9	357.4	338.4	323.1	308.7	293.9	285.2	274.2	269.6	266.3
55°	360.9	338.4	317.0	300.1	284.8	270.0	260.8	250.1	245.0	241.4	237.4
57.5°	318.4	298.2	281.8	264.7	249.3	237.6	226.9	220.5	215.2	210.5	205.6
60°	291.5	272.1	257.3	241.4	225.6	215.9	207.8	200.1	194.0	186.8	184.8
62.5°	262.9	245.9	232.4	216.9	203.2	194.3	186.5	179.3	171.9	161.5	158.6
65°	223.6	210.3	196.0	183.3	171.0	162.3	151.1	142.9	139.9	138.8	138.3
67.5°	188.1	175.5	163.2	150.2	139.0	131.0	125.3	124.0	121.9	121.3	119.9
70°	164.4	152.6	140.4	128.1	117.4	115.9	113.8	111.8	109.2	108.2	107.2
72.5°	143.1	131.0	118.7	108.9	104.3	102.4	100.4	98.3	96.6	95.6	94.9
75°	109.7	98.5	90.4	86.8	84.2	82.7	79.6	78.1	77.1	75.5	75.0
77.5°	79.0	72.7	68.9	66.7	64.0	62.4	60.6	59.1	58.0	57.7	56.9
80°	60.2	57.2	54.6	51.6	50.5	48.5	48.0	46.5	47.0	45.4	45.4
82.5°	46.8	42.9	40.7	39.3	38.3	36.7	36.1	35.4	35.5	34.4	34.4
85°	24.0	23.0	21.9	20.9	20.9	19.4	19.9	19.4	19.4	18.4	17.9
87.5°	10.1	10.4	10.6	11.6	12.5	13.1	13.0	12.5	12.4	12.3	11.9
90°	11.6	15.4	20.3	25.2	30.0	34.9	34.5	34.0	33.6	33.2	33.0
92.5°	25.6	27.1	28.3	29.4	30.6	31.7	31.8	31.9	32.0	32.1	32.2
95°	60.8	62.1	62.5	63.0	63.4	63.9	63.9	63.9	63.9	63.9	63.6
97.5°	102.6	104.0	104.9	105.7	106.5	107.4	107.4	107.4	107.4	107.4	107.4
100°	133.8	135.1	135.7	136.4	137.1	137.7	137.7	137.7	137.7	137.7	137.6
102.5°	165.9	167.1	167.9	168.8	169.6	170.5	170.6	170.8	171.0	171.2	171.1
105°	217.2	217.8	218.2	218.7	219.1	219.5	220.0	220.4	220.9	221.3	221.5
107.5°	273.2	273.6	273.6	273.6	273.6	273.6	273.8	274.0	274.2	274.3	273.9
110°	309.7	310.4	310.4	310.4	310.4	310.4	310.4	310.4	310.4	310.4	310.0



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	348.0	348.6	348.4	348.2	348.1	347.9	347.4	346.8	346.3	345.8	345.2
115°	404.5	404.9	404.5	404.1	403.6	403.2	403.0	402.7	402.5	402.3	401.8
117.5°	462.6	462.8	461.6	460.3	459.1	457.9	457.3	456.8	456.3	455.7	455.1
120°	500.1	500.1	498.3	496.5	494.8	493.0	493.0	493.0	493.0	493.0	492.7
122.5°	535.8	536.3	535.0	533.8	532.6	531.3	530.8	530.2	529.7	529.2	528.7
125°	588.8	589.5	588.8	588.1	587.5	586.8	586.1	585.5	584.8	584.1	583.7
127.5°	643.0	643.9	643.1	642.3	641.5	640.7	639.9	639.1	638.3	637.5	636.7
130°	677.2	678.4	677.9	677.5	677.1	676.6	676.2	675.7	675.3	674.8	674.2
132.5°	711.8	713.0	713.1	713.2	713.2	713.3	712.4	711.4	710.4	709.4	708.6
135°	761.2	762.7	763.1	763.5	764.0	764.4	764.2	764.0	763.8	763.5	763.1
137.5°	811.1	812.4	813.0	813.6	814.2	814.7	814.6	814.4	814.2	814.0	813.5
140°	842.3	843.8	844.9	846.0	847.2	848.3	848.3	848.3	848.3	848.3	847.8
142.5°	874.2	875.6	876.3	877.1	877.8	878.6	878.8	879.0	879.1	879.3	879.0
145°	918.3	919.8	921.1	922.4	923.8	925.1	925.3	925.5	925.8	926.0	925.7
147.5°	960.5	961.9	962.8	963.6	964.5	965.4	965.9	966.4	966.9	967.4	967.2
150°	986.3	987.4	988.3	989.2	990.1	991.0	991.6	992.3	993.0	993.6	993.6
152.5°	1011.1	1012.3	1013.3	1014.4	1015.4	1016.5	1017.4	1018.2	1019.0	1019.9	1019.9
155°	1045.5	1046.2	1046.9	1047.5	1048.2	1048.8	1050.0	1051.1	1052.2	1053.3	1053.5
157.5°	1076.4	1076.8	1077.2	1077.6	1078.0	1078.4	1079.9	1081.4	1082.9	1084.4	1084.6
160°	1095.5	1095.9	1096.1	1096.3	1096.5	1096.7	1098.1	1099.4	1100.7	1102.1	1102.3
162.5°	1111.7	1111.8	1112.1	1112.3	1112.5	1112.7	1114.2	1115.7	1117.2	1118.7	1119.0
165°	1133.8	1133.7	1133.7	1133.7	1133.7	1133.7	1135.2	1136.8	1138.3	1139.9	1140.1
167.5°	1151.6	1151.2	1151.2	1151.1	1151.1	1151.0	1152.6	1154.1	1155.7	1157.2	1157.4
170°	1161.9	1161.5	1161.3	1161.1	1160.8	1160.6	1162.2	1163.7	1165.3	1166.8	1166.9
172.5°	1169.1	1168.7	1168.5	1168.2	1168.0	1167.8	1169.4	1170.9	1172.5	1174.0	1174.1
175°	1177.9	1177.4	1176.9	1176.5	1176.0	1175.6	1177.1	1178.7	1180.2	1181.8	1181.9
177.5°	1182.0	1181.6	1181.2	1180.9	1180.5	1180.2	1181.2	1182.3	1183.4	1184.4	1184.4
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1410.7	1411.5	1410.3	1411.1	1410.3	1411.5	1410.7	1415.2	1416.0	1416.8	1416.0
5°	1314.4	1308.3	1307.3	1305.7	1307.3	1308.3	1314.4	1317.0	1319.0	1323.1	1330.2
7.5°	1199.5	1198.5	1196.0	1192.4	1196.0	1198.5	1199.5	1208.2	1215.2	1223.1	1237.7
10°	1125.5	1123.0	1122.5	1118.9	1122.5	1123.0	1125.5	1136.8	1144.9	1156.2	1176.1
12.5°	1039.0	1022.5	1020.8	1011.9	1020.8	1022.5	1039.0	1053.5	1075.5	1086.3	1107.5
15°	884.6	881.6	871.3	864.7	871.3	881.6	884.6	896.9	905.0	934.6	968.8
17.5°	796.4	786.4	783.2	781.8	783.2	786.4	796.4	802.3	814.0	829.6	850.2
20°	739.6	730.5	728.9	727.9	728.9	730.5	739.6	746.8	756.0	772.8	794.3
22.5°	700.4	690.8	686.9	683.8	686.9	690.8	700.4	706.0	714.3	727.5	742.0
25°	633.5	629.9	627.9	626.8	627.9	629.9	633.5	638.6	646.7	664.6	679.9
27.5°	581.1	573.2	571.7	569.1	571.7	573.2	581.1	590.2	598.7	606.7	620.4
30°	551.3	548.7	545.2	542.1	545.2	548.7	551.3	555.9	561.5	575.3	588.6
32.5°	516.2	514.0	510.9	509.4	510.9	514.0	516.2	522.4	534.1	542.6	552.2
35°	477.3	470.1	467.1	462.5	467.1	470.1	477.3	482.4	487.0	494.1	511.5
37.5°	436.1	432.4	428.1	429.6	428.1	432.4	436.1	438.3	448.0	457.9	465.4
40°	404.3	401.7	400.7	400.2	400.7	401.7	404.3	410.9	422.7	427.2	438.5
42.5°	379.0	371.9	369.3	369.2	369.3	371.9	379.0	386.4	393.7	401.1	412.8
45°	340.5	333.8	329.2	329.8	329.2	333.8	340.5	343.0	349.1	364.0	370.6
47.5°	301.1	300.9	298.0	298.9	298.0	300.9	301.1	305.5	313.3	322.4	333.0
50°	282.3	279.2	277.2	277.7	277.2	279.2	282.3	285.9	290.4	295.0	311.4
52.5°	264.3	261.7	260.0	262.2	260.0	261.7	264.3	266.3	269.6	274.2	285.2
55°	234.8	231.7	231.2	230.7	231.2	231.7	234.8	237.4	241.4	245.0	250.1
57.5°	201.8	199.8	196.7	195.4	196.7	199.8	201.8	205.6	210.5	215.2	220.5
60°	178.1	174.1	169.0	168.4	169.0	174.1	178.1	184.8	186.8	194.0	200.1
62.5°	156.5	155.7	154.7	154.6	154.7	155.7	156.5	158.6	161.5	171.9	179.3
65°	137.3	136.8	137.3	137.8	137.3	136.8	137.3	138.3	138.8	139.9	142.9
67.5°	119.7	118.7	117.8	118.2	117.8	118.7	119.7	119.9	121.3	121.9	124.0
70°	106.2	105.7	105.2	105.2	105.2	105.7	106.2	107.2	108.2	109.2	111.8
72.5°	93.1	93.0	92.5	92.1	92.5	93.0	93.1	94.9	95.6	96.6	98.3
75°	74.5	73.5	73.5	73.5	73.5	73.5	74.5	75.0	75.5	77.1	78.1
77.5°	56.8	56.3	55.7	55.3	55.7	56.3	56.8	56.9	57.7	58.0	59.1
80°	44.9	44.4	43.9	43.9	43.9	44.4	44.9	45.4	45.4	47.0	46.5
82.5°	34.3	33.8	33.7	33.3	33.7	33.8	34.3	34.4	34.4	35.5	35.4
85°	18.4	18.9	18.4	19.4	18.4	18.9	18.4	17.9	18.4	19.4	19.4
87.5°	12.0	11.6	12.1	11.7	12.1	11.6	12.0	11.9	12.3	12.4	12.5
90°	33.3	33.5	33.7	33.9	33.7	33.5	33.3	33.0	33.2	33.6	34.0
92.5°	32.2	32.2	32.3	32.3	32.3	32.2	32.2	32.2	32.1	32.0	31.9
95°	63.2	62.8	62.3	61.9	62.3	62.8	63.2	63.6	63.9	63.9	63.9
97.5°	107.3	107.3	107.2	107.2	107.2	107.3	107.3	107.4	107.4	107.4	107.4
100°	137.4	137.2	136.9	136.7	136.9	137.2	137.4	137.6	137.7	137.7	137.7
102.5°	170.9	170.7	170.5	170.3	170.5	170.7	170.9	171.1	171.2	171.0	170.8
105°	221.5	221.5	221.5	221.5	221.5	221.5	221.5	221.5	221.3	220.9	220.4
107.5°	272.9	271.9	270.9	269.8	270.9	271.9	272.9	273.9	274.3	274.2	274.0
110°	309.4	308.7	308.0	307.4	308.0	308.7	309.4	310.0	310.4	310.4	310.4



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	344.8	344.3	343.8	343.3	343.8	344.3	344.8	345.2	345.8	346.3	346.8
115°	401.2	400.5	399.8	399.2	399.8	400.5	401.2	401.8	402.3	402.5	402.7
117.5°	454.5	453.8	453.1	452.5	453.1	453.8	454.5	455.1	455.7	456.3	456.8
120°	492.0	491.3	490.7	490.0	490.7	491.3	492.0	492.7	493.0	493.0	493.0
122.5°	528.2	527.7	527.2	526.7	527.2	527.7	528.2	528.7	529.2	529.7	530.2
125°	583.5	583.2	583.0	582.8	583.0	583.2	583.5	583.7	584.1	584.8	585.5
127.5°	636.0	635.3	634.6	633.9	634.6	635.3	636.0	636.7	637.5	638.3	639.1
130°	673.3	672.4	671.5	670.6	671.5	672.4	673.3	674.2	674.8	675.3	675.7
132.5°	707.9	707.2	706.5	705.8	706.5	707.2	707.9	708.6	709.4	710.4	711.4
135°	762.4	761.8	761.1	760.4	761.1	761.8	762.4	763.1	763.5	763.8	764.0
137.5°	812.6	811.7	810.8	809.9	810.8	811.7	812.6	813.5	814.0	814.2	814.4
140°	846.9	846.0	845.2	844.3	845.2	846.0	846.9	847.8	848.3	848.3	848.3
142.5°	878.1	877.2	876.3	875.4	876.3	877.2	878.1	879.0	879.3	879.1	879.0
145°	924.8	923.9	923.0	922.1	923.0	923.9	924.8	925.7	926.0	925.8	925.5
147.5°	966.4	965.5	964.7	963.8	964.7	965.5	966.4	967.2	967.4	966.9	966.4
150°	993.0	992.3	991.6	991.0	991.6	992.3	993.0	993.6	993.6	993.0	992.3
152.5°	1019.0	1018.2	1017.4	1016.5	1017.4	1018.2	1019.0	1019.9	1019.9	1019.0	1018.2
155°	1052.8	1052.2	1051.5	1050.8	1051.5	1052.2	1052.8	1053.5	1053.3	1052.2	1051.1
157.5°	1083.6	1082.5	1081.4	1080.4	1081.4	1082.5	1083.6	1084.6	1084.4	1082.9	1081.4
160°	1101.4	1100.5	1099.6	1098.7	1099.6	1100.5	1101.4	1102.3	1102.1	1100.7	1099.4
162.5°	1117.9	1116.8	1115.8	1114.7	1115.8	1116.8	1117.9	1119.0	1118.7	1117.2	1115.7
165°	1139.0	1137.9	1136.8	1135.7	1136.8	1137.9	1139.0	1140.1	1139.9	1138.3	1136.8
167.5°	1156.3	1155.1	1154.0	1152.8	1154.0	1155.1	1156.3	1157.4	1157.2	1155.7	1154.1
170°	1165.6	1164.3	1162.9	1161.6	1162.9	1164.3	1165.6	1166.9	1166.8	1165.3	1163.7
172.5°	1172.8	1171.5	1170.1	1168.8	1170.1	1171.5	1172.8	1174.1	1174.0	1172.5	1170.9
175°	1180.6	1179.2	1177.9	1176.6	1177.9	1179.2	1180.6	1181.9	1181.8	1180.2	1178.7
177.5°	1183.4	1182.3	1181.2	1180.2	1181.2	1182.3	1183.4	1184.4	1184.4	1183.4	1182.3
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1412.7	1418.4	1427.0	1431.9	1440.1	1445.4	1448.3	1453.6	1456.4	1466.6	1477.3
5°	1333.8	1342.0	1356.3	1369.5	1383.8	1398.6	1409.4	1421.6	1432.8	1452.2	1472.7
7.5°	1243.4	1254.7	1276.8	1298.0	1322.9	1343.8	1362.3	1383.2	1401.9	1429.7	1458.7
10°	1175.6	1195.5	1224.6	1244.5	1277.2	1298.1	1327.2	1350.1	1376.2	1412.9	1445.6
12.5°	1117.2	1141.2	1164.5	1192.2	1221.6	1256.4	1288.4	1317.9	1348.8	1386.8	1425.2
15°	1011.2	1045.9	1082.2	1110.2	1150.1	1186.8	1224.1	1263.9	1301.7	1347.1	1397.1
17.5°	874.8	915.0	976.0	1024.1	1070.8	1107.7	1153.8	1202.0	1246.5	1301.3	1357.0
20°	813.2	842.8	884.1	948.9	1019.4	1058.7	1105.6	1158.7	1209.8	1269.5	1329.2
22.5°	763.7	790.1	823.3	873.8	952.4	1006.0	1055.0	1108.9	1168.1	1229.1	1295.3
25°	693.2	711.6	746.3	787.1	841.2	929.5	983.1	1037.2	1101.6	1166.9	1242.4
27.5°	640.2	656.7	679.3	718.3	758.5	821.9	907.2	966.2	1030.3	1103.8	1182.2
30°	599.8	619.2	644.2	671.8	715.7	765.2	850.4	918.8	982.1	1057.7	1141.4
32.5°	570.4	585.7	607.0	635.0	671.6	719.0	787.1	870.2	931.9	1011.5	1098.9
35°	522.2	540.1	557.4	584.0	613.6	657.0	708.5	797.3	858.6	937.2	1025.0
37.5°	482.5	493.4	512.6	533.6	564.9	597.2	641.9	721.6	787.8	865.0	954.9
40°	452.3	466.0	480.3	503.8	529.3	560.5	604.4	663.6	739.6	815.2	903.0
42.5°	422.9	440.3	455.4	471.1	499.1	530.3	566.0	616.2	693.9	765.4	850.7
45°	387.4	398.7	414.5	431.8	454.8	481.4	513.0	556.9	631.4	693.2	773.3
47.5°	346.2	362.6	372.9	389.9	411.7	437.0	466.5	504.4	564.8	622.7	697.0
50°	318.0	334.9	349.7	365.0	384.4	408.9	433.4	470.1	518.6	579.4	648.8
52.5°	293.9	308.7	323.1	338.4	357.4	379.9	403.2	435.4	477.0	532.8	600.2
55°	260.8	270.0	284.8	300.1	317.0	338.4	360.9	387.9	423.7	470.6	525.3
57.5°	226.9	237.6	249.3	264.7	281.8	298.2	318.4	342.9	371.1	413.6	460.3
60°	207.8	215.9	225.6	241.4	257.3	272.1	291.5	311.9	338.4	375.2	415.0
62.5°	186.5	194.3	203.2	216.9	232.4	245.9	262.9	284.5	307.0	340.5	375.4
65°	151.1	162.3	171.0	183.3	196.0	210.3	223.6	240.9	260.8	287.4	318.5
67.5°	125.3	131.0	139.0	150.2	163.2	175.5	188.1	201.6	218.9	239.4	264.1
70°	113.8	115.9	117.4	128.1	140.4	152.6	164.4	177.1	191.9	208.8	230.2
72.5°	100.4	102.4	104.3	108.9	118.7	131.0	143.1	152.6	166.6	180.6	198.0
75°	79.6	82.7	84.2	86.8	90.4	98.5	109.7	118.9	127.1	137.8	151.6
77.5°	60.6	62.4	64.0	66.7	68.9	72.7	79.0	87.3	94.9	101.2	110.7
80°	48.0	48.5	50.5	51.6	54.6	57.2	60.2	66.9	74.5	77.1	83.7
82.5°	36.1	36.7	38.3	39.3	40.7	42.9	46.8	48.5	54.5	57.9	62.1
85°	19.9	19.4	20.9	20.9	21.9	23.0	24.0	26.5	28.1	32.2	33.2
87.5°	13.0	13.1	12.5	11.6	10.6	10.4	10.1	10.0	10.2	10.9	12.0
90°	34.5	34.9	30.0	25.2	20.3	15.4	11.6	9.0	6.3	3.7	1.0
92.5°	31.8	31.7	30.6	29.4	28.3	27.1	25.6	23.6	21.7	19.7	17.8
95°	63.9	63.9	63.4	63.0	62.5	62.1	60.8	58.5	56.3	54.1	51.9
97.5°	107.4	107.4	106.5	105.7	104.9	104.0	102.6	100.7	98.7	96.8	94.8
100°	137.7	137.7	137.1	136.4	135.7	135.1	133.8	132.1	130.3	128.5	126.7
102.5°	170.6	170.5	169.6	168.8	167.9	167.1	165.9	164.5	163.1	161.7	160.3
105°	220.0	219.5	219.1	218.7	218.2	217.8	217.2	216.6	215.9	215.2	214.6
107.5°	273.8	273.6	273.6	273.6	273.6	273.6	273.2	272.2	271.2	270.2	269.2
110°	310.4	310.4	310.4	310.4	310.4	310.4	309.7	308.4	307.0	305.7	304.4



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	347.4	347.9	348.1	348.2	348.4	348.6	348.0	346.7	345.4	344.0	342.7
115°	403.0	403.2	403.6	404.1	404.5	404.9	404.5	403.2	401.8	400.5	399.2
117.5°	457.3	457.9	459.1	460.3	461.6	462.8	462.6	460.8	459.0	457.2	455.5
120°	493.0	493.0	494.8	496.5	498.3	500.1	500.1	498.3	496.5	494.8	493.0
122.5°	530.8	531.3	532.6	533.8	535.0	536.3	535.8	533.7	531.6	529.4	527.3
125°	586.1	586.8	587.5	588.1	588.8	589.5	588.8	586.8	584.8	582.8	580.8
127.5°	639.9	640.7	641.5	642.3	643.1	643.9	643.0	640.5	638.0	635.4	632.9
130°	676.2	676.6	677.1	677.5	677.9	678.4	677.2	674.3	671.4	668.5	665.6
132.5°	712.4	713.3	713.2	713.2	713.1	713.0	711.8	709.4	707.1	704.7	702.4
135°	764.2	764.4	764.0	763.5	763.1	762.7	761.2	758.8	756.3	753.9	751.5
137.5°	814.6	814.7	814.2	813.6	813.0	812.4	811.1	809.1	807.1	805.1	803.2
140°	848.3	848.3	847.2	846.0	844.9	843.8	842.3	840.3	838.3	836.3	834.3
142.5°	878.8	878.6	877.8	877.1	876.3	875.6	874.2	872.2	870.2	868.2	866.2
145°	925.3	925.1	923.8	922.4	921.1	919.8	918.3	916.8	915.2	913.7	912.1
147.5°	965.9	965.4	964.5	963.6	962.8	961.9	960.5	958.6	956.8	954.9	953.0
150°	991.6	991.0	990.1	989.2	988.3	987.4	986.3	985.0	983.6	982.3	981.0
152.5°	1017.4	1016.5	1015.4	1014.4	1013.3	1012.3	1011.1	1009.7	1008.4	1007.1	1005.7
155°	1050.0	1048.8	1048.2	1047.5	1046.9	1046.2	1045.5	1044.9	1044.2	1043.5	1042.9
157.5°	1079.9	1078.4	1078.0	1077.6	1077.2	1076.8	1076.4	1075.9	1075.5	1075.0	1074.6
160°	1098.1	1096.7	1096.5	1096.3	1096.1	1095.9	1095.5	1095.1	1094.6	1094.2	1093.8
162.5°	1114.2	1112.7	1112.5	1112.3	1112.1	1111.8	1111.7	1111.6	1111.5	1111.4	1111.3
165°	1135.2	1133.7	1133.7	1133.7	1133.7	1133.7	1133.8	1134.0	1134.2	1134.5	1134.7
167.5°	1152.6	1151.0	1151.1	1151.1	1151.2	1151.2	1151.6	1152.2	1152.9	1153.6	1154.2
170°	1162.2	1160.6	1160.8	1161.1	1161.3	1161.5	1161.9	1162.6	1163.3	1163.9	1164.6
172.5°	1169.4	1167.8	1168.0	1168.2	1168.5	1168.7	1169.1	1169.8	1170.5	1171.1	1171.8
175°	1177.1	1175.6	1176.0	1176.5	1176.9	1177.4	1177.9	1178.6	1179.2	1179.9	1180.6
177.5°	1181.2	1180.2	1180.5	1180.9	1181.2	1181.6	1182.0	1182.6	1183.1	1183.6	1184.2
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1477.7	1478.9	1487.1	1490.7	1498.1	1500.9	1504.2	1503.4	1503.4	1505.0	1516.5
5°	1480.8	1491.0	1506.3	1521.1	1535.4	1547.7	1555.9	1564.0	1567.1	1581.9	1595.2
7.5°	1475.5	1494.3	1519.6	1542.2	1569.2	1590.4	1607.9	1623.8	1634.6	1656.1	1678.2
10°	1468.6	1495.1	1523.7	1552.8	1590.1	1618.1	1646.7	1668.7	1675.8	1708.0	1726.4
12.5°	1454.7	1490.2	1526.6	1564.2	1600.7	1639.4	1670.8	1692.8	1717.9	1746.8	1780.7
15°	1433.9	1474.7	1522.2	1570.7	1622.7	1669.7	1703.4	1741.7	1769.2	1800.9	1830.5
17.5°	1403.9	1456.5	1516.9	1573.0	1633.2	1683.7	1730.0	1766.8	1786.2	1804.2	1808.6
20°	1380.3	1436.9	1507.9	1574.2	1634.5	1692.7	1738.6	1769.2	1774.3	1774.8	1747.8
22.5°	1354.5	1418.5	1492.8	1560.8	1632.8	1697.6	1733.3	1746.4	1726.1	1691.5	1639.2
25°	1307.3	1381.3	1467.6	1545.1	1623.8	1685.0	1697.3	1674.3	1603.3	1528.8	1434.4
27.5°	1256.0	1339.2	1431.7	1518.0	1601.7	1639.7	1613.2	1530.4	1402.6	1291.5	1156.9
30°	1218.5	1311.9	1402.7	1499.2	1576.8	1593.1	1532.4	1410.4	1261.3	1093.9	959.7
32.5°	1175.6	1273.5	1373.3	1473.1	1538.0	1522.1	1421.7	1271.5	1096.8	932.2	805.3
35°	1114.3	1215.4	1323.1	1423.1	1464.5	1395.6	1245.5	1050.0	871.3	717.7	630.4
37.5°	1043.6	1153.6	1265.6	1357.5	1354.5	1239.7	1035.3	833.5	683.3	592.4	530.3
40°	993.3	1104.6	1225.6	1303.2	1270.0	1120.4	898.9	708.5	598.8	526.3	480.8
42.5°	945.2	1056.8	1177.0	1238.7	1181.0	997.1	776.4	627.2	536.7	480.1	443.3
45°	863.2	981.1	1092.4	1126.6	1023.5	820.8	627.9	519.6	459.4	417.6	392.0
47.5°	783.0	899.0	1000.6	1001.2	861.7	665.6	529.6	449.7	398.3	365.9	347.3
50°	734.0	844.3	929.5	916.3	758.0	592.1	473.7	404.8	361.9	336.9	317.5
52.5°	678.9	785.9	859.7	821.9	670.2	521.1	423.5	365.6	330.1	308.3	291.0
55°	598.8	693.7	745.8	688.6	546.7	433.4	357.8	312.4	285.9	267.5	252.7
57.5°	520.0	598.4	631.1	564.6	450.3	359.4	302.7	268.6	242.3	229.1	221.4
60°	470.6	537.5	560.5	487.0	391.5	314.4	268.0	236.3	216.9	208.3	200.6
62.5°	422.0	476.7	486.2	418.8	341.3	275.2	235.3	208.6	195.7	187.4	180.2
65°	350.2	389.5	384.9	330.8	270.0	218.5	189.4	173.0	163.3	151.6	138.8
67.5°	288.3	312.3	297.8	257.3	206.1	169.8	150.8	138.4	126.4	115.3	112.3
70°	249.1	262.9	247.6	210.3	169.0	142.4	127.1	112.3	105.2	102.6	98.0
72.5°	211.5	216.3	199.8	167.8	137.5	117.9	103.0	94.7	90.9	88.7	85.8
75°	158.8	155.2	140.9	115.9	95.5	82.2	77.6	74.5	72.0	69.9	68.4
77.5°	111.5	106.3	93.5	77.2	66.5	60.1	57.4	55.7	54.5	53.5	52.0
80°	83.7	80.1	67.4	55.1	50.5	47.5	45.9	43.9	43.9	42.9	41.3
82.5°	61.3	57.3	46.1	40.4	37.9	36.0	34.9	33.7	33.3	33.5	32.4
85°	32.2	26.0	23.0	21.9	20.4	19.4	19.9	18.9	18.9	18.9	18.4
87.5°	10.5	9.0	9.1	9.3	10.4	11.4	12.0	13.0	14.3	13.8	14.2
90°	3.7	6.3	9.0	11.6	15.4	20.3	25.2	30.0	34.9	34.5	34.0
92.5°	19.7	21.7	23.6	25.6	27.1	28.3	29.4	30.6	31.7	31.8	31.9
95°	54.1	56.3	58.5	60.8	62.1	62.5	63.0	63.4	63.9	63.9	63.9
97.5°	96.8	98.7	100.7	102.6	104.0	104.9	105.7	106.5	107.4	107.4	107.4
100°	128.5	130.3	132.1	133.8	135.1	135.7	136.4	137.1	137.7	137.7	137.7
102.5°	161.7	163.1	164.5	165.9	167.1	167.9	168.8	169.6	170.5	170.6	170.8
105°	215.2	215.9	216.6	217.2	217.8	218.2	218.7	219.1	219.5	220.0	220.4
107.5°	270.2	271.2	272.2	273.2	273.6	273.6	273.6	273.6	273.6	273.8	274.0
110°	305.7	307.0	308.4	309.7	310.4	310.4	310.4	310.4	310.4	310.4	310.4





TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	344.0	345.4	346.7	348.0	348.6	348.4	348.2	348.1	347.9	347.4	346.8
115°	400.5	401.8	403.2	404.5	404.9	404.5	404.1	403.6	403.2	403.0	402.7
117.5°	457.2	459.0	460.8	462.6	462.8	461.6	460.3	459.1	457.9	457.3	456.8
120°	494.8	496.5	498.3	500.1	500.1	498.3	496.5	494.8	493.0	493.0	493.0
122.5°	529.4	531.6	533.7	535.8	536.3	535.0	533.8	532.6	531.3	530.8	530.2
125°	582.8	584.8	586.8	588.8	589.5	588.8	588.1	587.5	586.8	586.1	585.5
127.5°	635.4	638.0	640.5	643.0	643.9	643.1	642.3	641.5	640.7	639.9	639.1
130°	668.5	671.4	674.3	677.2	678.4	677.9	677.5	677.1	676.6	676.2	675.7
132.5°	704.7	707.1	709.4	711.8	713.0	713.1	713.2	713.2	713.3	712.4	711.4
135°	753.9	756.3	758.8	761.2	762.7	763.1	763.5	764.0	764.4	764.2	764.0
137.5°	805.1	807.1	809.1	811.1	812.4	813.0	813.6	814.2	814.7	814.6	814.4
140°	836.3	838.3	840.3	842.3	843.8	844.9	846.0	847.2	848.3	848.3	848.3
142.5°	868.2	870.2	872.2	874.2	875.6	876.3	877.1	877.8	878.6	878.8	879.0
145°	913.7	915.2	916.8	918.3	919.8	921.1	922.4	923.8	925.1	925.3	925.5
147.5°	954.9	956.8	958.6	960.5	961.9	962.8	963.6	964.5	965.4	965.9	966.4
150°	982.3	983.6	985.0	986.3	987.4	988.3	989.2	990.1	991.0	991.6	992.3
152.5°	1007.1	1008.4	1009.7	1011.1	1012.3	1013.3	1014.4	1015.4	1016.5	1017.4	1018.2
155°	1043.5	1044.2	1044.9	1045.5	1046.2	1046.9	1047.5	1048.2	1048.8	1050.0	1051.1
157.5°	1075.0	1075.5	1075.9	1076.4	1076.8	1077.2	1077.6	1078.0	1078.4	1079.9	1081.4
160°	1094.2	1094.6	1095.1	1095.5	1095.9	1096.1	1096.3	1096.5	1096.7	1098.1	1099.4
162.5°	1111.4	1111.5	1111.6	1111.7	1111.8	1112.1	1112.3	1112.5	1112.7	1114.2	1115.7
165°	1134.5	1134.2	1134.0	1133.8	1133.7	1133.7	1133.7	1133.7	1133.7	1135.2	1136.8
167.5°	1153.6	1152.9	1152.2	1151.6	1151.2	1151.2	1151.1	1151.1	1151.0	1152.6	1154.1
170°	1163.9	1163.3	1162.6	1161.9	1161.5	1161.3	1161.1	1160.8	1160.6	1162.2	1163.7
172.5°	1171.1	1170.5	1169.8	1169.1	1168.7	1168.5	1168.2	1168.0	1167.8	1169.4	1170.9
175°	1179.9	1179.2	1178.6	1177.9	1177.4	1176.9	1176.5	1176.0	1175.6	1177.1	1178.7
177.5°	1183.6	1183.1	1182.6	1182.0	1181.6	1181.2	1180.9	1180.5	1180.2	1181.2	1182.3
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1	1469.1
2.5°	1520.5	1525.8	1528.3	1528.3	1531.2	1529.9	1528.7
5°	1607.9	1617.6	1619.7	1628.9	1635.5	1633.4	1634.5
7.5°	1694.8	1710.4	1725.8	1732.9	1734.0	1738.1	1739.6
10°	1748.3	1761.1	1785.1	1781.5	1799.3	1809.6	1792.7
12.5°	1799.8	1817.0	1833.6	1838.2	1848.4	1851.6	1845.0
15°	1846.3	1855.5	1856.5	1854.0	1857.0	1854.5	1844.8
17.5°	1802.8	1787.9	1757.7	1743.4	1732.1	1715.3	1708.6
20°	1730.9	1687.0	1636.0	1615.6	1591.6	1544.6	1555.9
22.5°	1575.8	1525.7	1474.7	1415.1	1386.6	1342.1	1339.4
25°	1334.3	1248.1	1153.1	1086.8	1048.0	1003.6	984.2
27.5°	1037.4	928.8	851.0	811.6	775.8	740.6	739.1
30°	842.2	760.6	700.3	666.7	644.7	629.9	633.0
32.5°	709.9	654.0	613.4	585.4	569.2	558.0	557.8
35°	580.4	542.1	516.1	504.3	492.6	484.4	484.9
37.5°	496.7	473.7	459.2	446.2	438.9	434.9	432.7
40°	453.8	434.9	423.7	416.0	409.9	404.3	403.3
42.5°	419.9	404.3	393.0	387.0	381.3	377.3	376.3
45°	372.6	359.9	349.7	343.0	340.5	336.9	336.9
47.5°	331.5	318.9	311.0	306.8	302.4	300.0	299.9
50°	303.7	294.0	286.9	284.3	280.7	279.2	278.7
52.5°	278.8	271.6	266.5	264.7	263.2	261.2	261.6
55°	245.0	240.9	238.9	237.4	234.8	231.7	233.8
57.5°	216.5	213.1	207.6	202.8	200.4	198.3	199.1
60°	196.5	189.4	182.2	176.6	175.1	170.5	170.5
62.5°	171.2	161.2	152.4	149.3	147.7	145.6	145.2
65°	131.7	127.6	125.6	123.5	122.5	122.5	121.5
67.5°	109.1	107.5	105.3	104.7	103.7	103.4	103.1
70°	96.5	94.4	93.4	92.9	91.9	92.4	90.9
72.5°	84.2	82.6	82.4	81.1	80.4	80.5	79.4
75°	66.4	66.4	65.8	65.3	64.3	63.8	64.3
77.5°	51.0	51.1	50.2	50.1	50.0	50.1	49.6
80°	40.8	41.3	40.8	40.3	39.8	40.3	39.8
82.5°	32.3	31.5	31.4	31.3	31.2	30.9	30.8
85°	18.4	18.9	18.4	17.9	17.9	17.9	18.4
87.5°	13.7	13.6	13.6	13.6	13.6	13.7	13.3
90°	33.6	33.2	33.0	33.3	33.5	33.7	33.9
92.5°	32.0	32.1	32.2	32.2	32.2	32.3	32.3
95°	63.9	63.9	63.6	63.2	62.8	62.3	61.9
97.5°	107.4	107.4	107.4	107.3	107.3	107.2	107.2
100°	137.7	137.7	137.6	137.4	137.2	136.9	136.7
102.5°	171.0	171.2	171.1	170.9	170.7	170.5	170.3
105°	220.9	221.3	221.5	221.5	221.5	221.5	221.5
107.5°	274.2	274.3	273.9	272.9	271.9	270.9	269.8
110°	310.4	310.4	310.0	309.4	308.7	308.0	307.4



TEST NUMBER: P331694

CATALOG NUMBER: SA2XXRDIP-C675D925U835-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	346.3	345.8	345.2	344.8	344.3	343.8	343.3
115°	402.5	402.3	401.8	401.2	400.5	399.8	399.2
117.5°	456.3	455.7	455.1	454.5	453.8	453.1	452.5
120°	493.0	493.0	492.7	492.0	491.3	490.7	490.0
122.5°	529.7	529.2	528.7	528.2	527.7	527.2	526.7
125°	584.8	584.1	583.7	583.5	583.2	583.0	582.8
127.5°	638.3	637.5	636.7	636.0	635.3	634.6	633.9
130°	675.3	674.8	674.2	673.3	672.4	671.5	670.6
132.5°	710.4	709.4	708.6	707.9	707.2	706.5	705.8
135°	763.8	763.5	763.1	762.4	761.8	761.1	760.4
137.5°	814.2	814.0	813.5	812.6	811.7	810.8	809.9
140°	848.3	848.3	847.8	846.9	846.0	845.2	844.3
142.5°	879.1	879.3	879.0	878.1	877.2	876.3	875.4
145°	925.8	926.0	925.7	924.8	923.9	923.0	922.1
147.5°	966.9	967.4	967.2	966.4	965.5	964.7	963.8
150°	993.0	993.6	993.6	993.0	992.3	991.6	991.0
152.5°	1019.0	1019.9	1019.9	1019.0	1018.2	1017.4	1016.5
155°	1052.2	1053.3	1053.5	1052.8	1052.2	1051.5	1050.8
157.5°	1082.9	1084.4	1084.6	1083.6	1082.5	1081.4	1080.4
160°	1100.7	1102.1	1102.3	1101.4	1100.5	1099.6	1098.7
162.5°	1117.2	1118.7	1119.0	1117.9	1116.8	1115.8	1114.7
165°	1138.3	1139.9	1140.1	1139.0	1137.9	1136.8	1135.7
167.5°	1155.7	1157.2	1157.4	1156.3	1155.1	1154.0	1152.8
170°	1165.3	1166.8	1166.9	1165.6	1164.3	1162.9	1161.6
172.5°	1172.5	1174.0	1174.1	1172.8	1171.5	1170.1	1168.8
175°	1180.2	1181.8	1181.9	1180.6	1179.2	1177.9	1176.6
177.5°	1183.4	1184.4	1184.4	1183.4	1182.3	1181.2	1180.2
180°	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6	1182.6

(END OF REPORT)